

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999790

Luminaire Tested: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999790
REPORT IS A COMBINATION OF REPORTS P988345 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4682.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47			40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40			35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35			30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31			26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27			23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24			21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	21			18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19			17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18			15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16			14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16945	16945	16945	16945
5°	16986	17998	17044	14379
10°	16798	19025	16917	11875
15°	16433	19030	16712	8920
20°	15995	15731	16343	7359
25°	15464	9830	15797	6261
30°	14786	6293	15187	5389
35°	13959	4837	14411	4612
40°	13038	4066	13597	4034
45°	12056	3460	12560	3387
50°	11048	2940	11565	2930
55°	9931	2556	10467	2521
60°	8940	1948	9413	1924
65°	8013	1466	8489	1663
70°	6990	1171	7540	1355
75°	5907	898	6450	1026
80°	4694	610	5046	673
85°	3263	315	3574	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15501 cd/sqm

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	2.2
10°-20°	283.4	6.1
20°-30°	364.8	7.8
30°-40°	346.1	7.4
40°-50°	296.6	6.3
50°-60°	225.9	4.8
60°-70°	142.4	3.0
70°-80°	71.1	1.5
80°-90°	20.0	0.4
90°-100°	31.8	0.7
100°-110°	118.7	2.5
110°-120°	314.7	6.7
120°-130°	522.0	11.1
130°-140°	554.5	11.8
140°-150°	515.4	11.0
150°-160°	414.3	8.8
160°-170°	267.0	5.7
170°-180°	91.9	2.0
0°-30°	749.7	16.0
0°-40°	1095.8	23.4
0°-60°	1618.2	34.6
0°-90°	1851.7	39.5
90°-120°	465.3	9.9
90°-150°	2057.1	43.9
90°-180°	2830.0	60.4
0°-180°	4682.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1070	1070	1070	1070	1070	
5°	1071	1191	1075	952	1071	102
15°	1010	1344	1027	630	1010	284
25°	896	717	915	457	896	411
35°	735	353	759	337	735	460
45°	552	246	575	240	552	426
55°	373	170	393	168	373	336
65°	225	88	239	100	225	224
75°	106	47	115	54	106	114
85°	23	13	25	14	23	26
90°	1	19	1	19	1	4
95°	45	30	45	30	45	54
105°	212	53	212	53	212	227
115°	402	57	402	57	402	395
125°	568	597	568	597	568	507
135°	703	726	703	726	703	543
145°	815	828	815	828	815	510
155°	898	898	898	898	898	414
165°	946	944	946	944	946	267
175°	968	962	968	962	968	92
180°	965	965	965	965	965	

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1077.2	1081.7	1083.9	1086.9	1093.6	1098.1	1104.7	1106.2	1105.5	1108.5	1100.3
5°	1071.3	1080.9	1089.9	1097.3	1109.2	1116.6	1124.8	1134.5	1136.7	1147.9	1141.2
7.5°	1063.1	1077.2	1089.9	1104.7	1122.6	1132.3	1144.9	1159.8	1166.5	1179.9	1183.6
10°	1049.7	1069.8	1091.4	1107.0	1131.5	1148.6	1160.5	1184.3	1200.0	1220.1	1217.1
12.5°	1028.1	1054.2	1083.2	1109.2	1141.2	1152.4	1174.7	1199.2	1219.3	1237.9	1254.3
15°	1009.5	1039.3	1071.3	1103.3	1139.7	1160.5	1182.9	1214.8	1236.4	1269.2	1283.3
17.5°	984.2	1022.2	1060.1	1095.8	1139.0	1162.8	1190.3	1221.5	1253.5	1284.8	1295.9
20°	958.2	999.1	1040.0	1088.4	1137.5	1160.5	1188.8	1227.5	1258.7	1283.3	1283.3
22.5°	926.9	976.8	1023.7	1069.8	1123.3	1156.8	1185.8	1231.2	1253.5	1258.7	1238.7
25°	895.7	945.5	996.9	1054.2	1115.2	1144.9	1177.7	1220.1	1227.5	1206.7	1154.6
27.5°	858.5	914.3	972.3	1034.1	1098.1	1135.2	1165.0	1193.3	1179.1	1123.3	1042.3
30°	820.6	880.8	946.3	1005.1	1082.4	1116.6	1141.9	1150.1	1105.5	1014.7	909.8
32.5°	781.1	839.9	909.1	979.8	1057.9	1090.6	1107.0	1085.4	1003.6	889.0	761.0
35°	735.0	801.2	873.4	947.0	1024.4	1049.0	1058.6	1005.8	900.9	752.9	625.7
37.5°	693.3	759.6	836.9	912.1	987.2	1000.6	990.9	908.3	775.2	628.6	504.4
40°	644.2	714.9	790.8	874.9	936.6	940.3	916.5	809.4	644.2	506.6	430.0
42.5°	598.9	670.3	746.2	831.7	878.6	865.9	834.0	693.3	537.9	436.7	374.9
45°	552.0	619.7	701.5	777.4	810.9	781.1	732.8	583.2	451.6	375.7	328.1
47.5°	506.6	569.9	650.9	723.9	729.8	696.3	639.0	488.8	391.3	330.3	291.6
50°	462.0	525.2	601.1	661.4	655.4	609.3	544.6	424.8	340.0	291.6	259.6
52.5°	417.3	474.6	548.3	595.9	570.6	526.0	462.0	360.1	296.8	254.4	229.9
55°	372.7	426.3	489.5	528.9	488.8	437.4	392.1	308.7	257.4	223.2	204.6
57.5°	335.5	377.9	435.9	459.8	411.4	371.2	331.8	265.6	223.2	198.6	177.1
60°	294.6	333.3	380.9	395.0	345.2	312.5	279.0	224.7	191.2	169.6	155.5
62.5°	259.6	291.6	328.1	328.1	284.2	259.6	234.3	188.2	160.7	143.6	136.9
65°	225.4	248.5	274.5	271.5	234.3	212.8	192.7	155.5	134.7	122.7	116.1
67.5°	191.9	209.8	226.9	216.5	189.7	171.1	152.5	125.7	111.6	103.4	94.5
70°	161.4	175.6	184.5	174.8	148.0	132.4	119.0	101.2	90.0	79.6	74.4
72.5°	135.4	141.3	144.3	132.4	110.1	101.2	91.5	78.9	69.2	64.0	62.5
75°	105.6	110.8	108.6	99.7	81.1	74.4	67.0	58.0	55.8	52.8	51.3
77.5°	82.6	82.6	78.9	70.7	58.0	52.8	49.8	45.4	43.1	42.4	40.9
80°	58.8	58.0	55.8	46.9	39.4	36.5	36.5	33.5	32.7	31.2	31.2
82.5°	38.7	38.7	35.7	28.3	26.0	25.3	24.5	23.1	23.1	22.3	22.3
85°	23.1	21.6	17.9	15.6	14.9	14.9	14.1	13.4	14.1	13.4	13.4
87.5°	10.4	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.4	40.3	35.2	30.1	25.0	22.4	22.9	24.0	25.1	26.1	27.2
97.5°	81.7	69.0	56.3	43.6	30.9	24.5	25.7	28.2	30.7	33.1	35.6
100°	123.6	102.3	81.1	59.8	38.5	27.9	29.2	31.9	34.5	37.2	39.8
102.5°	169.8	169.5	169.2	168.9	168.6	168.4	154.3	126.0	97.7	69.5	41.2
105°	212.4	217.0	221.7	226.3	231.0	233.3	212.1	169.7	127.4	85.0	42.6
107.5°	262.0	265.9	269.7	273.6	277.5	279.4	253.2	200.9	148.6	96.3	44.0
110°	309.5	312.7	316.0	319.2	322.5	324.1	301.7	256.8	212.0	167.1	122.3

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	354.2	357.0	359.8	362.6	365.4	366.8	365.5	362.8	360.2	357.5	354.9
115°	401.7	404.3	407.0	409.6	412.3	413.6	415.5	419.4	423.3	427.1	431.0
117.5°	442.9	446.0	449.1	452.2	455.3	456.9	458.2	460.8	463.5	466.1	468.7
120°	489.0	491.3	493.7	496.0	498.3	499.5	500.9	503.7	506.5	509.3	512.1
122.5°	528.1	530.6	533.1	535.6	538.1	539.3	540.9	544.0	547.1	550.2	553.3
125°	567.9	569.9	571.9	574.0	576.0	577.0	578.5	581.4	584.4	587.3	590.3
127.5°	604.3	606.5	608.6	610.8	612.9	614.0	615.2	617.5	619.8	622.2	624.5
130°	638.5	641.0	643.5	646.0	648.5	649.7	650.6	652.3	654.0	655.7	657.4
132.5°	673.4	675.4	677.4	679.5	681.5	682.5	683.4	685.1	686.8	688.5	690.2
135°	702.8	705.3	707.7	710.2	712.7	713.9	714.6	716.0	717.4	718.8	720.2
137.5°	733.5	735.4	737.2	739.1	741.0	741.9	742.7	744.2	745.8	747.3	748.9
140°	763.5	764.7	766.0	767.2	768.5	769.1	770.0	771.7	773.4	775.1	776.8
142.5°	788.7	789.8	790.9	792.0	793.1	793.6	794.6	796.6	798.7	800.7	802.7
145°	815.2	815.0	814.9	814.7	814.6	814.5	815.8	818.5	821.1	823.8	826.4
147.5°	838.3	837.8	837.4	836.9	836.4	836.2	837.5	840.2	842.8	845.5	848.1
150°	860.6	859.5	858.5	857.4	856.3	855.8	857.0	859.5	862.0	864.4	866.9
152.5°	879.5	878.3	877.0	875.8	874.5	873.9	875.1	877.4	879.7	882.1	884.4
155°	897.7	896.3	894.9	893.5	892.1	891.4	892.3	894.2	896.1	897.9	899.8
157.5°	912.3	911.1	909.8	908.6	907.3	906.7	907.4	908.8	910.2	911.6	913.0
160°	924.9	924.0	923.0	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9
162.5°	936.1	935.2	934.2	933.3	932.4	931.9	932.3	933.1	933.8	934.6	935.4
165°	945.9	945.0	944.0	943.1	942.2	941.7	941.9	942.4	942.9	943.3	943.8
167.5°	953.6	952.7	951.7	950.8	949.9	949.4	949.6	950.1	950.6	951.0	951.5
170°	959.8	958.9	957.9	957.0	956.1	955.6	955.8	956.1	956.4	956.7	957.0
172.5°	964.0	963.1	962.1	961.2	960.3	959.8	960.0	960.3	960.6	960.9	961.2
175°	967.5	966.4	965.3	964.2	963.1	962.6	962.8	963.1	963.4	963.7	964.0
177.5°	968.9	967.8	966.7	965.6	964.5	964.0	964.1	964.2	964.4	964.5	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1108.5	1110.0	1112.2	1122.6	1124.1	1127.1	1125.6	1125.6	1126.3	1124.8	1125.6
5°	1156.1	1158.3	1169.5	1182.1	1185.1	1182.1	1185.8	1191.0	1191.0	1191.0	1189.6
7.5°	1200.7	1208.9	1221.5	1240.1	1243.9	1247.6	1254.3	1249.8	1251.3	1258.0	1255.8
10°	1243.9	1255.8	1269.9	1285.5	1293.7	1298.9	1301.9	1308.6	1324.2	1306.4	1313.0
12.5°	1284.8	1301.9	1316.8	1333.9	1339.8	1346.5	1348.8	1354.7	1354.7	1354.0	1359.2
15°	1311.6	1327.2	1340.6	1351.7	1353.2	1351.7	1350.2	1351.0	1353.2	1344.3	1349.5
17.5°	1317.5	1319.0	1323.5	1319.0	1319.7	1304.1	1295.2	1293.0	1272.1	1272.9	1290.0
20°	1288.5	1263.2	1256.5	1232.0	1217.1	1176.9	1175.4	1164.3	1120.4	1133.8	1130.8
22.5°	1208.9	1165.7	1108.5	1080.2	1066.1	1023.7	990.9	967.9	952.2	936.6	929.9
25°	1104.0	1034.1	953.0	897.2	889.0	849.6	789.3	761.0	727.6	717.2	735.0
27.5°	968.6	877.8	786.3	700.8	685.2	649.5	619.0	598.9	560.2	558.0	559.4
30°	784.9	693.3	616.7	560.9	522.2	505.9	485.8	470.9	455.3	461.2	462.7
32.5°	645.0	558.0	486.5	456.8	438.9	428.5	411.4	401.7	395.0	392.8	392.1
35°	512.6	454.5	422.6	393.5	383.1	375.7	363.0	358.6	352.6	353.4	353.4
37.5°	438.9	390.6	366.8	351.9	342.2	338.5	330.3	325.8	322.1	320.6	322.9
40°	378.7	345.2	330.3	316.9	308.7	307.2	302.8	297.6	293.1	293.9	296.1
42.5°	334.8	315.4	297.6	287.2	281.2	279.0	275.3	271.5	271.5	269.3	268.6
45°	299.8	284.2	269.3	259.6	255.9	252.9	248.5	247.7	244.8	245.5	246.2
47.5°	268.6	255.9	244.8	235.1	231.4	230.6	226.2	223.2	223.2	222.4	221.7
50°	240.3	227.6	218.0	212.8	207.6	206.1	205.3	204.6	203.1	203.1	203.8
52.5°	217.2	204.6	197.1	192.7	189.7	188.2	188.2	187.5	187.5	187.5	186.7
55°	191.9	181.5	175.6	174.1	172.6	171.8	171.1	169.6	168.9	170.4	168.9
57.5°	168.1	164.4	159.2	157.7	154.0	154.0	151.8	150.3	148.8	150.3	150.3
60°	149.5	144.3	141.3	136.9	133.9	130.9	127.2	126.5	125.0	124.2	123.5
62.5°	130.2	125.7	118.3	111.6	107.1	104.2	102.7	101.9	101.9	101.2	101.2
65°	108.6	98.2	94.5	92.2	91.5	90.8	89.3	88.5	89.3	88.5	89.3
67.5°	84.8	83.3	81.1	79.6	78.9	78.1	78.1	77.4	77.4	77.4	77.4
70°	73.6	69.9	69.2	67.7	67.7	67.0	67.0	67.0	67.0	66.2	67.7
72.5°	61.0	58.8	58.0	57.3	57.3	57.3	56.5	56.5	56.5	55.8	56.5
75°	49.8	49.1	47.6	47.6	46.9	47.6	46.9	46.9	46.1	46.9	46.9
77.5°	40.2	39.4	38.7	38.7	37.9	37.9	37.9	37.9	37.9	37.9	38.7
80°	30.5	29.8	29.0	29.8	29.0	29.8	29.0	29.0	29.8	29.0	29.0
82.5°	22.3	21.6	21.6	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
85°	13.4	12.6	12.6	13.4	12.6	13.4	12.6	12.6	12.6	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.0	28.8	29.5	30.3	30.7	30.6	30.5	30.3	30.2	30.0	30.2
97.5°	36.1	36.5	37.0	37.5	37.7	37.8	37.9	38.1	38.2	38.4	38.2
100°	41.0	42.3	43.5	44.8	45.4	45.6	45.9	46.2	46.5	46.8	46.5
102.5°	42.9	44.6	46.3	48.0	48.9	49.1	49.6	50.1	50.5	51.0	50.5
105°	44.3	46.0	47.7	49.4	50.3	50.6	51.2	51.9	52.5	53.1	52.5
107.5°	45.7	47.4	49.1	50.8	51.7	52.0	52.6	53.3	53.9	54.5	53.9
110°	106.8	91.2	75.7	60.2	52.4	52.7	53.3	54.0	54.6	55.2	54.6

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.0	221.1	154.2	87.3	53.8	54.0	54.5	55.0	55.4	55.9	55.4
115°	359.1	287.3	215.4	143.5	107.6	102.0	90.8	79.7	68.5	57.3	68.5
117.5°	446.5	424.3	402.1	379.9	368.8	348.5	307.8	267.1	226.5	185.8	226.5
120°	513.9	515.8	517.6	519.5	520.4	509.9	489.0	468.0	447.1	426.1	447.1
122.5°	554.2	555.2	556.1	557.0	557.5	557.6	557.7	557.9	558.0	558.2	558.0
125°	591.4	592.5	593.6	594.7	595.2	595.4	595.9	596.4	596.8	597.3	596.8
127.5°	626.1	627.6	629.2	630.7	631.5	631.6	631.7	631.9	632.0	632.2	632.0
130°	659.1	660.8	662.5	664.2	665.0	664.9	664.8	664.6	664.5	664.3	664.5
132.5°	691.6	693.0	694.4	695.8	696.5	696.4	696.3	696.1	696.0	695.8	696.0
135°	721.8	723.3	724.9	726.4	727.2	727.0	726.7	726.4	726.1	725.8	726.1
137.5°	750.5	752.0	753.6	755.1	755.9	755.7	755.2	754.7	754.3	753.8	754.3
140°	778.2	779.6	781.0	782.4	783.1	782.7	781.9	781.2	780.4	779.6	780.4
142.5°	803.9	805.2	806.4	807.7	808.3	807.9	807.1	806.4	805.6	804.8	805.6
145°	827.5	828.6	829.7	830.8	831.3	830.9	830.1	829.4	828.6	827.8	828.6
147.5°	848.9	849.7	850.4	851.2	851.6	851.3	850.7	850.0	849.4	848.8	849.4
150°	867.8	868.8	869.7	870.6	871.1	870.7	869.9	869.2	868.4	867.6	868.4
152.5°	885.3	886.3	887.2	888.1	888.6	888.1	887.0	885.9	884.8	883.7	884.8
155°	900.7	901.7	902.6	903.5	904.0	903.4	902.1	900.9	899.6	898.4	899.6
157.5°	914.1	915.2	916.3	917.4	917.9	917.3	916.0	914.8	913.5	912.3	913.5
160°	925.8	926.8	927.7	928.6	929.1	928.6	927.5	926.4	925.3	924.2	925.3
162.5°	936.5	937.6	938.7	939.8	940.3	939.6	938.2	936.8	935.4	934.0	935.4
165°	944.9	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	944.9
167.5°	952.6	953.6	954.7	955.8	956.3	955.6	954.2	952.9	951.5	950.1	951.5
170°	958.1	959.2	960.3	961.4	961.9	961.2	959.8	958.4	957.0	955.6	957.0
172.5°	962.3	963.4	964.5	965.6	966.1	965.4	964.0	962.6	961.2	959.8	961.2
175°	965.1	966.2	967.3	968.4	968.9	968.1	966.6	965.0	963.5	961.9	963.5
177.5°	965.8	966.9	968.0	969.1	969.6	968.9	967.5	966.1	964.7	963.3	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1128.6	1123.3	1121.9	1123.3	1121.9	1122.6	1117.4	1098.1	1103.3	1095.1	1099.5
5°	1192.5	1188.1	1178.4	1176.9	1175.4	1173.9	1166.5	1149.4	1142.7	1131.5	1130.8
7.5°	1253.5	1253.5	1246.1	1240.9	1234.2	1229.0	1219.3	1194.0	1183.6	1170.2	1162.8
10°	1313.8	1294.4	1302.6	1297.4	1281.1	1278.1	1260.2	1245.4	1225.3	1211.9	1200.0
12.5°	1356.9	1351.0	1343.5	1339.1	1334.6	1325.0	1313.0	1275.1	1264.7	1237.9	1224.5
15°	1355.5	1351.7	1354.0	1354.0	1352.5	1350.2	1340.6	1313.0	1295.2	1269.2	1246.1
17.5°	1282.5	1292.2	1301.9	1308.6	1323.5	1330.2	1339.1	1322.7	1311.6	1289.2	1264.7
20°	1155.3	1179.1	1207.4	1213.4	1226.8	1266.2	1284.0	1298.2	1302.6	1295.2	1275.1
22.5°	978.3	998.4	1066.8	1065.3	1084.7	1131.5	1183.6	1226.0	1259.5	1278.1	1270.6
25°	766.3	794.5	831.0	858.5	921.7	991.7	1056.4	1124.1	1182.1	1233.4	1246.1
27.5°	579.5	616.7	645.7	682.2	714.2	796.8	880.1	985.7	1053.4	1150.9	1201.5
30°	468.7	485.8	514.8	531.9	547.5	610.8	705.3	809.4	928.4	1040.8	1127.8
32.5°	400.2	412.1	433.7	441.2	457.5	499.9	559.4	654.7	777.4	913.6	1028.1
35°	359.3	372.0	376.4	383.1	396.5	423.3	464.2	533.4	644.2	777.4	914.3
37.5°	324.4	331.1	343.7	348.2	352.6	372.7	400.2	448.6	522.2	631.6	783.4
40°	299.8	303.5	310.2	313.9	316.9	331.1	355.6	388.3	442.6	526.0	665.8
42.5°	273.8	278.2	282.7	287.2	290.9	302.0	316.9	348.2	384.6	447.8	549.0
45°	248.5	251.5	256.7	259.6	264.8	273.8	287.2	308.7	341.5	381.6	463.5
47.5°	225.4	229.1	231.4	235.1	238.8	248.5	261.1	275.3	302.0	341.5	401.0
50°	204.6	209.0	212.0	212.8	215.7	224.7	235.1	250.7	267.8	298.3	350.4
52.5°	189.7	190.4	192.7	195.7	194.9	200.1	209.8	221.7	239.5	264.1	302.0
55°	172.6	174.8	176.3	177.1	177.1	181.5	186.7	197.9	212.0	232.1	264.1
57.5°	151.0	153.3	157.7	159.2	161.4	163.7	165.9	173.3	185.2	204.6	230.6
60°	128.7	130.2	134.7	137.6	139.1	145.1	148.0	154.0	160.7	174.8	199.4
62.5°	103.4	104.9	107.1	110.1	113.1	122.0	129.4	135.4	140.6	150.3	170.4
65°	90.0	90.8	92.2	93.0	93.7	97.5	104.2	112.3	122.0	129.4	141.3
67.5°	78.1	78.9	79.6	81.1	81.8	82.6	85.6	87.8	97.5	107.9	116.8
70°	67.0	68.4	69.2	69.2	69.9	71.4	72.9	75.9	78.9	84.1	95.2
72.5°	56.5	57.3	58.8	58.8	58.8	60.3	61.7	63.2	64.7	67.7	72.2
75°	46.9	48.4	48.4	48.4	49.1	49.1	50.6	52.1	53.6	55.8	57.3
77.5°	38.7	38.7	38.7	38.7	39.4	39.4	40.2	41.7	42.4	43.1	44.6
80°	29.0	29.8	29.8	29.8	30.5	30.5	30.5	32.0	32.7	32.7	34.2
82.5°	21.6	21.6	21.6	22.3	21.6	22.3	22.3	23.1	22.3	23.1	23.8
85°	13.4	13.4	13.4	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.3	30.5	30.6	30.7	30.3	29.5	28.8	28.0	27.2	26.1	25.1
97.5°	38.1	37.9	37.8	37.7	37.5	37.0	36.5	36.1	35.6	33.1	30.7
100°	46.2	45.9	45.6	45.4	44.8	43.5	42.3	41.0	39.8	37.2	34.5
102.5°	50.1	49.6	49.1	48.9	48.0	46.3	44.6	42.9	41.2	39.5	37.7
105°	51.9	51.2	50.6	50.3	49.4	47.7	46.0	44.3	42.6	40.9	39.2
107.5°	53.3	52.6	52.0	51.7	50.8	49.1	47.4	45.7	44.0	42.3	40.6
110°	54.0	53.3	52.7	52.4	50.2	48.5	46.8	45.1	43.4	41.7	40.0

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.0	54.5	54.0	53.8	87.3	154.2	221.1	288.0	354.9	357.5	360.2
115°	79.7	90.8	102.0	107.6	143.5	215.4	287.3	359.1	431.0	427.1	423.3
117.5°	267.1	307.8	348.5	368.8	379.9	402.1	424.3	446.5	468.7	466.1	463.5
120°	468.0	489.0	509.9	520.4	519.5	517.6	515.8	513.9	512.1	509.3	506.5
122.5°	557.9	557.7	557.6	557.5	557.0	556.1	555.2	554.2	553.3	550.2	547.1
125°	596.4	595.9	595.4	595.2	594.7	593.6	592.5	591.4	590.3	587.3	584.4
127.5°	631.9	631.7	631.6	631.5	630.7	629.2	627.6	626.1	624.5	622.2	619.8
130°	664.6	664.8	664.9	665.0	664.2	662.5	660.8	659.1	657.4	655.7	654.0
132.5°	696.1	696.3	696.4	696.5	695.8	694.4	693.0	691.6	690.2	688.5	686.8
135°	726.4	726.7	727.0	727.2	726.4	724.9	723.3	721.8	720.2	718.8	717.4
137.5°	754.7	755.2	755.7	755.9	755.1	753.6	752.0	750.5	748.9	747.3	745.8
140°	781.2	781.9	782.7	783.1	782.4	781.0	779.6	778.2	776.8	775.1	773.4
142.5°	806.4	807.1	807.9	808.3	807.7	806.4	805.2	803.9	802.7	800.7	798.7
145°	829.4	830.1	830.9	831.3	830.8	829.7	828.6	827.5	826.4	823.8	821.1
147.5°	850.0	850.7	851.3	851.6	851.2	850.4	849.7	848.9	848.1	845.5	842.8
150°	869.2	869.9	870.7	871.1	870.6	869.7	868.8	867.8	866.9	864.4	862.0
152.5°	885.9	887.0	888.1	888.6	888.1	887.2	886.3	885.3	884.4	882.1	879.7
155°	900.9	902.1	903.4	904.0	903.5	902.6	901.7	900.7	899.8	897.9	896.1
157.5°	914.8	916.0	917.3	917.9	917.4	916.3	915.2	914.1	913.0	911.6	910.2
160°	926.4	927.5	928.6	929.1	928.6	927.7	926.8	925.8	924.9	924.0	923.0
162.5°	936.8	938.2	939.6	940.3	939.8	938.7	937.6	936.5	935.4	934.6	933.8
165°	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	943.3	942.9
167.5°	952.9	954.2	955.6	956.3	955.8	954.7	953.6	952.6	951.5	951.0	950.6
170°	958.4	959.8	961.2	961.9	961.4	960.3	959.2	958.1	957.0	956.7	956.4
172.5°	962.6	964.0	965.4	966.1	965.6	964.5	963.4	962.3	961.2	960.9	960.6
175°	965.0	966.6	968.1	968.9	968.4	967.3	966.2	965.1	964.0	963.7	963.4
177.5°	966.1	967.5	968.9	969.6	969.1	968.0	966.9	965.8	964.7	964.5	964.4
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1092.8	1089.1	1089.1	1086.9	1086.9	1075.0	1075.0	1078.7	1074.2	1069.0	1061.6
5°	1121.1	1112.9	1110.7	1107.7	1098.1	1083.2	1077.2	1075.0	1066.1	1054.9	1042.3
7.5°	1147.9	1134.5	1127.8	1121.1	1108.5	1087.6	1075.7	1067.5	1054.2	1037.0	1020.7
10°	1173.9	1156.8	1139.7	1131.5	1113.7	1087.6	1070.5	1057.1	1037.8	1014.7	991.7
12.5°	1197.7	1162.0	1159.1	1142.7	1116.6	1086.9	1060.9	1041.5	1017.0	990.2	963.4
15°	1218.6	1182.1	1164.3	1149.4	1115.2	1078.0	1050.4	1026.6	993.9	963.4	930.7
17.5°	1229.0	1189.6	1177.7	1153.1	1118.1	1069.8	1032.6	1003.6	967.9	931.4	894.2
20°	1239.4	1193.3	1173.9	1156.8	1109.2	1054.2	1012.5	979.0	939.6	896.4	855.5
22.5°	1244.6	1193.3	1170.2	1146.4	1100.3	1037.0	987.9	948.5	902.4	858.5	809.4
25°	1235.7	1188.8	1161.3	1136.7	1084.7	1016.2	959.7	915.0	865.9	816.1	766.3
27.5°	1213.4	1178.4	1146.4	1121.1	1063.1	989.4	929.9	879.3	828.7	773.0	722.4
30°	1171.7	1156.1	1130.8	1102.5	1039.3	965.6	895.0	842.9	787.1	731.3	678.5
32.5°	1107.0	1120.4	1104.0	1079.5	1011.0	932.9	857.8	804.9	743.9	683.7	635.3
35°	1028.1	1075.7	1066.8	1049.7	981.3	897.9	822.8	758.8	697.8	636.8	588.5
37.5°	941.8	1014.0	1021.4	1011.0	947.0	862.2	779.6	717.2	654.7	592.9	543.8
40°	823.5	934.4	958.2	962.7	911.3	819.1	732.8	671.8	610.0	549.8	490.3
42.5°	714.9	854.8	884.5	903.1	865.9	776.7	689.6	621.9	560.9	506.6	447.1
45°	613.0	758.8	807.2	831.0	814.6	728.3	638.3	575.1	519.3	469.4	412.1
47.5°	508.1	654.7	722.4	760.3	760.3	679.2	589.2	526.7	473.1	430.7	380.2
50°	438.2	560.2	630.1	680.0	693.3	629.4	544.6	483.6	433.0	386.8	348.2
52.5°	373.5	482.8	540.8	592.9	631.6	575.8	494.7	439.7	389.8	346.7	316.2
55°	322.9	404.7	457.5	514.8	558.0	521.5	446.4	392.8	349.7	313.9	287.9
57.5°	274.5	345.9	389.1	439.7	485.8	458.3	398.0	351.9	313.9	282.7	259.6
60°	233.6	291.6	325.1	364.5	421.8	402.5	352.6	310.2	279.7	251.5	232.1
62.5°	198.6	244.8	273.0	301.3	353.4	344.4	305.8	273.0	247.0	223.2	206.8
65°	162.9	200.9	223.2	247.7	289.4	293.1	261.9	238.8	215.0	194.2	179.3
67.5°	131.7	161.4	181.5	202.4	235.8	246.2	224.7	205.3	185.2	168.1	154.7
70°	106.4	127.2	142.1	158.5	186.0	198.6	187.5	174.1	157.7	143.6	131.7
72.5°	84.1	97.5	106.4	119.0	141.3	154.0	153.3	141.3	129.4	119.8	110.1
75°	61.7	72.2	79.6	87.8	105.6	117.5	120.5	115.3	103.4	96.0	88.5
77.5°	46.9	52.8	56.5	62.5	75.1	85.6	90.0	88.5	80.3	74.4	69.2
80°	35.7	37.2	38.7	40.9	51.3	61.0	64.0	63.2	58.8	56.5	50.6
82.5°	25.3	26.0	26.8	27.5	31.2	39.4	42.4	43.9	40.2	37.9	32.7
85°	14.9	15.6	15.6	17.1	17.9	20.1	25.3	25.3	24.5	21.6	20.8
87.5°	7.4	7.4	6.7	6.7	7.4	8.2	9.7	11.2	9.7	8.9	8.2
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.0	22.9	22.4	25.0	30.1	35.2	40.3	45.4	40.3	35.2	30.1
97.5°	28.2	25.7	24.5	30.9	43.6	56.3	69.0	81.7	69.0	56.3	43.6
100°	31.9	29.2	27.9	38.5	59.8	81.1	102.3	123.6	102.3	81.1	59.8
102.5°	126.0	154.3	168.4	168.6	168.9	169.2	169.5	169.8	169.5	169.2	168.9
105°	169.7	212.1	233.3	231.0	226.3	221.7	217.0	212.4	217.0	221.7	226.3
107.5°	200.9	253.2	279.4	277.5	273.6	269.7	265.9	262.0	265.9	269.7	273.6
110°	256.8	301.7	324.1	322.5	319.2	316.0	312.7	309.5	312.7	316.0	319.2

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	362.8	365.5	366.8	365.4	362.6	359.8	357.0	354.2	357.0	359.8	362.6
115°	419.4	415.5	413.6	412.3	409.6	407.0	404.3	401.7	404.3	407.0	409.6
117.5°	460.8	458.2	456.9	455.3	452.2	449.1	446.0	442.9	446.0	449.1	452.2
120°	503.7	500.9	499.5	498.3	496.0	493.7	491.3	489.0	491.3	493.7	496.0
122.5°	544.0	540.9	539.3	538.1	535.6	533.1	530.6	528.1	530.6	533.1	535.6
125°	581.4	578.5	577.0	576.0	574.0	571.9	569.9	567.9	569.9	571.9	574.0
127.5°	617.5	615.2	614.0	612.9	610.8	608.6	606.5	604.3	606.5	608.6	610.8
130°	652.3	650.6	649.7	648.5	646.0	643.5	641.0	638.5	641.0	643.5	646.0
132.5°	685.1	683.4	682.5	681.5	679.5	677.4	675.4	673.4	675.4	677.4	679.5
135°	716.0	714.6	713.9	712.7	710.2	707.7	705.3	702.8	705.3	707.7	710.2
137.5°	744.2	742.7	741.9	741.0	739.1	737.2	735.4	733.5	735.4	737.2	739.1
140°	771.7	770.0	769.1	768.5	767.2	766.0	764.7	763.5	764.7	766.0	767.2
142.5°	796.6	794.6	793.6	793.1	792.0	790.9	789.8	788.7	789.8	790.9	792.0
145°	818.5	815.8	814.5	814.6	814.7	814.9	815.0	815.2	815.0	814.9	814.7
147.5°	840.2	837.5	836.2	836.4	836.9	837.4	837.8	838.3	837.8	837.4	836.9
150°	859.5	857.0	855.8	856.3	857.4	858.5	859.5	860.6	859.5	858.5	857.4
152.5°	877.4	875.1	873.9	874.5	875.8	877.0	878.3	879.5	878.3	877.0	875.8
155°	894.2	892.3	891.4	892.1	893.5	894.9	896.3	897.7	896.3	894.9	893.5
157.5°	908.8	907.4	906.7	907.3	908.6	909.8	911.1	912.3	911.1	909.8	908.6
160°	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9	924.0	923.0	922.1
162.5°	933.1	932.3	931.9	932.4	933.3	934.2	935.2	936.1	935.2	934.2	933.3
165°	942.4	941.9	941.7	942.2	943.1	944.0	945.0	945.9	945.0	944.0	943.1
167.5°	950.1	949.6	949.4	949.9	950.8	951.7	952.7	953.6	952.7	951.7	950.8
170°	956.1	955.8	955.6	956.1	957.0	957.9	958.9	959.8	958.9	957.9	957.0
172.5°	960.3	960.0	959.8	960.3	961.2	962.1	963.1	964.0	963.1	962.1	961.2
175°	963.1	962.8	962.6	963.1	964.2	965.3	966.4	967.5	966.4	965.3	964.2
177.5°	964.2	964.1	964.0	964.5	965.6	966.7	967.8	968.9	967.8	966.7	965.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1058.6	1059.4	1061.6	1054.9	1044.5	1040.0	1026.6	1024.4	1022.2	1022.2	1024.4
5°	1034.8	1031.8	1032.6	1019.9	1005.1	996.1	977.5	980.5	970.8	964.9	966.4
7.5°	1008.8	1000.6	999.9	983.5	964.9	948.5	929.2	924.7	915.8	905.4	900.9
10°	976.0	970.1	958.9	940.3	916.5	903.1	877.1	861.5	859.2	843.6	837.7
12.5°	942.6	932.2	921.0	895.0	868.2	846.6	827.3	810.1	798.2	784.9	775.9
15°	903.9	891.2	878.6	851.1	819.8	798.2	769.2	743.9	709.0	681.4	665.8
17.5°	861.5	847.3	830.2	799.7	769.2	739.5	685.9	656.2	631.6	615.2	605.6
20°	817.6	802.0	784.9	754.4	701.5	649.5	619.7	596.6	581.8	565.4	553.5
22.5°	771.5	755.1	736.5	688.9	633.1	596.6	573.6	552.0	530.4	521.5	515.5
25°	728.3	713.4	689.6	624.9	581.0	547.5	521.5	507.4	496.2	484.3	473.1
27.5°	683.7	656.2	622.7	568.4	540.8	506.6	488.0	477.6	458.3	450.1	444.9
30°	630.1	599.6	567.6	528.9	496.9	473.1	456.0	438.9	427.8	419.6	410.7
32.5°	575.8	546.8	526.7	486.5	462.7	438.2	421.8	411.4	395.0	389.8	386.1
35°	528.9	504.4	486.5	453.8	431.5	409.2	397.3	381.6	371.2	361.6	355.6
37.5°	482.8	469.4	450.8	423.3	399.5	381.6	365.3	360.1	345.9	340.7	334.8
40°	450.8	430.7	415.1	391.3	371.2	351.9	341.5	329.6	319.9	311.7	309.5
42.5°	412.1	397.3	388.3	362.3	341.5	330.3	317.7	304.3	296.8	290.1	282.0
45°	383.1	369.7	357.1	336.3	317.7	303.5	292.4	283.4	270.8	267.8	255.2
47.5°	352.6	339.2	329.6	308.7	291.6	278.2	270.0	258.1	247.7	241.0	235.1
50°	322.1	311.0	302.0	284.2	269.3	255.2	244.0	232.1	227.6	216.5	212.8
52.5°	293.1	285.7	276.0	258.9	244.0	232.1	220.2	210.5	203.8	197.9	193.4
55°	268.6	256.7	252.2	233.6	220.9	208.3	197.9	191.9	183.8	180.0	176.3
57.5°	241.0	234.3	226.9	212.8	198.6	186.7	179.3	170.4	165.9	161.4	158.5
60°	217.2	207.6	201.6	189.7	177.1	165.9	159.2	152.5	146.6	142.8	136.9
62.5°	189.7	182.3	178.5	165.9	155.5	145.1	139.1	132.4	128.0	121.3	113.8
65°	165.9	159.9	155.5	145.1	135.4	125.7	119.8	111.6	105.6	101.9	101.2
67.5°	145.1	140.6	133.9	124.2	114.6	107.1	100.4	93.7	93.0	91.5	91.5
70°	122.0	117.5	113.8	103.4	95.2	87.0	85.6	83.3	81.1	80.3	78.9
72.5°	101.9	98.2	93.7	84.8	76.6	74.4	72.9	71.4	69.2	68.4	67.7
75°	82.6	77.4	74.4	66.2	64.0	62.5	61.0	58.8	57.3	56.5	55.1
77.5°	63.2	58.0	58.0	53.6	52.1	49.8	48.4	46.9	46.1	44.6	44.6
80°	44.6	44.6	43.1	40.9	38.7	37.9	35.7	35.0	34.2	35.0	33.5
82.5°	32.7	29.8	29.8	28.3	26.8	26.0	24.5	24.5	23.8	23.8	23.8
85°	18.6	18.6	17.9	16.4	15.6	15.6	14.9	14.9	14.1	14.1	13.4
87.5°	7.4	6.7	7.4	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	22.9	24.0	25.1	26.1	27.2	28.0	28.8	29.5	30.3
97.5°	30.9	24.5	25.7	28.2	30.7	33.1	35.6	36.1	36.5	37.0	37.5
100°	38.5	27.9	29.2	31.9	34.5	37.2	39.8	41.0	42.3	43.5	44.8
102.5°	168.6	168.4	154.3	126.0	97.7	69.5	41.2	42.9	44.6	46.3	48.0
105°	231.0	233.3	212.1	169.7	127.4	85.0	42.6	44.3	46.0	47.7	49.4
107.5°	277.5	279.4	253.2	200.9	148.6	96.3	44.0	45.7	47.4	49.1	50.8
110°	322.5	324.1	301.7	256.8	212.0	167.1	122.3	106.8	91.2	75.7	60.2

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	365.4	366.8	365.5	362.8	360.2	357.5	354.9	288.0	221.1	154.2	87.3
115°	412.3	413.6	415.5	419.4	423.3	427.1	431.0	359.1	287.3	215.4	143.5
117.5°	455.3	456.9	458.2	460.8	463.5	466.1	468.7	446.5	424.3	402.1	379.9
120°	498.3	499.5	500.9	503.7	506.5	509.3	512.1	513.9	515.8	517.6	519.5
122.5°	538.1	539.3	540.9	544.0	547.1	550.2	553.3	554.2	555.2	556.1	557.0
125°	576.0	577.0	578.5	581.4	584.4	587.3	590.3	591.4	592.5	593.6	594.7
127.5°	612.9	614.0	615.2	617.5	619.8	622.2	624.5	626.1	627.6	629.2	630.7
130°	648.5	649.7	650.6	652.3	654.0	655.7	657.4	659.1	660.8	662.5	664.2
132.5°	681.5	682.5	683.4	685.1	686.8	688.5	690.2	691.6	693.0	694.4	695.8
135°	712.7	713.9	714.6	716.0	717.4	718.8	720.2	721.8	723.3	724.9	726.4
137.5°	741.0	741.9	742.7	744.2	745.8	747.3	748.9	750.5	752.0	753.6	755.1
140°	768.5	769.1	770.0	771.7	773.4	775.1	776.8	778.2	779.6	781.0	782.4
142.5°	793.1	793.6	794.6	796.6	798.7	800.7	802.7	803.9	805.2	806.4	807.7
145°	814.6	814.5	815.8	818.5	821.1	823.8	826.4	827.5	828.6	829.7	830.8
147.5°	836.4	836.2	837.5	840.2	842.8	845.5	848.1	848.9	849.7	850.4	851.2
150°	856.3	855.8	857.0	859.5	862.0	864.4	866.9	867.8	868.8	869.7	870.6
152.5°	874.5	873.9	875.1	877.4	879.7	882.1	884.4	885.3	886.3	887.2	888.1
155°	892.1	891.4	892.3	894.2	896.1	897.9	899.8	900.7	901.7	902.6	903.5
157.5°	907.3	906.7	907.4	908.8	910.2	911.6	913.0	914.1	915.2	916.3	917.4
160°	921.2	920.7	921.2	922.1	923.0	924.0	924.9	925.8	926.8	927.7	928.6
162.5°	932.4	931.9	932.3	933.1	933.8	934.6	935.4	936.5	937.6	938.7	939.8
165°	942.2	941.7	941.9	942.4	942.9	943.3	943.8	944.9	946.0	947.1	948.2
167.5°	949.9	949.4	949.6	950.1	950.6	951.0	951.5	952.6	953.6	954.7	955.8
170°	956.1	955.6	955.8	956.1	956.4	956.7	957.0	958.1	959.2	960.3	961.4
172.5°	960.3	959.8	960.0	960.3	960.6	960.9	961.2	962.3	963.4	964.5	965.6
175°	963.1	962.6	962.8	963.1	963.4	963.7	964.0	965.1	966.2	967.3	968.4
177.5°	964.5	964.0	964.1	964.2	964.4	964.5	964.7	965.8	966.9	968.0	969.1
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1024.4	1022.9	1018.4	1019.9	1017.7	1017.7	1016.2	1016.2	1016.2	1019.9	1017.7
5°	968.6	963.4	958.2	956.0	953.7	951.5	951.5	950.8	957.4	956.0	961.9
7.5°	899.4	897.9	887.5	887.5	883.8	882.3	886.0	886.8	887.5	889.0	892.7
10°	837.7	834.0	819.1	820.6	818.3	815.4	817.6	816.1	821.3	822.8	821.3
12.5°	764.8	758.1	741.7	733.5	724.6	717.9	726.1	720.1	741.0	746.9	763.3
15°	668.1	655.4	644.2	644.2	636.1	630.1	633.8	640.5	645.0	651.7	654.7
17.5°	603.3	598.1	589.2	584.0	581.8	579.5	579.5	582.5	592.2	591.4	597.4
20°	548.3	545.3	540.8	534.1	531.9	530.4	530.4	530.4	537.1	543.1	546.8
22.5°	510.3	508.1	505.1	496.2	491.7	490.3	494.0	496.2	501.4	505.9	509.6
25°	472.4	467.2	462.0	459.0	456.8	456.8	458.3	459.0	461.2	463.5	467.9
27.5°	441.2	437.4	430.0	421.8	421.8	419.6	421.1	422.6	427.8	435.2	438.9
30°	406.2	405.4	402.5	399.5	396.5	395.0	398.0	400.2	401.0	404.7	404.7
32.5°	380.9	375.7	370.5	367.5	366.0	365.3	366.0	369.0	369.0	373.5	378.7
35°	355.6	352.6	347.4	342.2	340.7	337.0	340.0	343.0	348.2	350.4	352.6
37.5°	328.1	324.4	322.1	320.6	317.7	318.4	316.2	320.6	325.1	324.4	325.8
40°	307.2	300.6	293.9	293.1	292.4	291.6	291.6	292.4	295.3	298.3	302.8
42.5°	280.5	278.2	272.3	266.3	264.8	263.4	261.9	264.8	270.8	276.0	278.2
45°	252.9	250.0	248.5	244.0	241.0	240.3	238.8	242.5	247.7	250.0	251.5
47.5°	227.6	226.9	222.4	223.2	220.9	221.7	220.9	223.2	223.2	225.4	226.9
50°	210.5	208.3	206.1	204.6	202.4	202.4	201.6	202.4	205.3	208.3	207.6
52.5°	193.4	189.7	189.0	188.2	186.7	188.2	186.0	186.7	189.7	191.2	190.4
55°	173.3	172.6	171.1	169.6	168.9	168.1	168.1	168.1	171.1	173.3	174.1
57.5°	157.7	154.0	151.0	151.0	148.0	147.3	148.8	149.5	151.8	153.3	154.7
60°	136.1	134.7	130.2	128.0	123.5	122.7	122.7	125.7	129.4	134.7	136.1
62.5°	113.1	110.8	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.8	110.8
65°	100.4	101.2	100.4	99.7	100.4	100.4	99.7	99.7	99.7	100.4	101.2
67.5°	90.0	89.3	90.0	89.3	88.5	88.5	87.8	88.5	89.3	90.0	90.0
70°	78.1	78.1	77.4	78.1	77.4	76.6	75.9	75.9	77.4	78.1	78.1
72.5°	67.0	67.0	66.2	66.2	64.7	64.7	65.5	64.7	64.7	67.0	67.0
75°	55.8	55.1	54.3	54.3	53.6	53.6	53.6	52.8	54.3	54.3	55.1
77.5°	43.9	43.9	43.9	43.1	43.1	42.4	42.4	43.1	43.1	43.1	43.9
80°	33.5	33.5	33.5	32.7	32.0	32.0	32.0	32.0	32.0	32.7	32.0
82.5°	23.1	23.1	23.1	23.1	23.1	22.3	22.3	22.3	23.1	23.1	22.3
85°	14.1	13.4	14.1	14.1	13.4	14.1	13.4	13.4	12.6	12.6	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.7	30.6	30.5	30.3	30.2	30.0	30.2	30.3	30.5	30.6	30.7
97.5°	37.7	37.8	37.9	38.1	38.2	38.4	38.2	38.1	37.9	37.8	37.7
100°	45.4	45.6	45.9	46.2	46.5	46.8	46.5	46.2	45.9	45.6	45.4
102.5°	48.9	49.1	49.6	50.1	50.5	51.0	50.5	50.1	49.6	49.1	48.9
105°	50.3	50.6	51.2	51.9	52.5	53.1	52.5	51.9	51.2	50.6	50.3
107.5°	51.7	52.0	52.6	53.3	53.9	54.5	53.9	53.3	52.6	52.0	51.7
110°	52.4	52.7	53.3	54.0	54.6	55.2	54.6	54.0	53.3	52.7	52.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.8	54.0	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	53.8
115°	107.6	102.0	90.8	79.7	68.5	57.3	68.5	79.7	90.8	102.0	107.6
117.5°	368.8	348.5	307.8	267.1	226.5	185.8	226.5	267.1	307.8	348.5	368.8
120°	520.4	509.9	489.0	468.0	447.1	426.1	447.1	468.0	489.0	509.9	520.4
122.5°	557.5	557.6	557.7	557.9	558.0	558.2	558.0	557.9	557.7	557.6	557.5
125°	595.2	595.4	595.9	596.4	596.8	597.3	596.8	596.4	595.9	595.4	595.2
127.5°	631.5	631.6	631.7	631.9	632.0	632.2	632.0	631.9	631.7	631.6	631.5
130°	665.0	664.9	664.8	664.6	664.5	664.3	664.5	664.6	664.8	664.9	665.0
132.5°	696.5	696.4	696.3	696.1	696.0	695.8	696.0	696.1	696.3	696.4	696.5
135°	727.2	727.0	726.7	726.4	726.1	725.8	726.1	726.4	726.7	727.0	727.2
137.5°	755.9	755.7	755.2	754.7	754.3	753.8	754.3	754.7	755.2	755.7	755.9
140°	783.1	782.7	781.9	781.2	780.4	779.6	780.4	781.2	781.9	782.7	783.1
142.5°	808.3	807.9	807.1	806.4	805.6	804.8	805.6	806.4	807.1	807.9	808.3
145°	831.3	830.9	830.1	829.4	828.6	827.8	828.6	829.4	830.1	830.9	831.3
147.5°	851.6	851.3	850.7	850.0	849.4	848.8	849.4	850.0	850.7	851.3	851.6
150°	871.1	870.7	869.9	869.2	868.4	867.6	868.4	869.2	869.9	870.7	871.1
152.5°	888.6	888.1	887.0	885.9	884.8	883.7	884.8	885.9	887.0	888.1	888.6
155°	904.0	903.4	902.1	900.9	899.6	898.4	899.6	900.9	902.1	903.4	904.0
157.5°	917.9	917.3	916.0	914.8	913.5	912.3	913.5	914.8	916.0	917.3	917.9
160°	929.1	928.6	927.5	926.4	925.3	924.2	925.3	926.4	927.5	928.6	929.1
162.5°	940.3	939.6	938.2	936.8	935.4	934.0	935.4	936.8	938.2	939.6	940.3
165°	948.7	948.2	947.1	946.0	944.9	943.8	944.9	946.0	947.1	948.2	948.7
167.5°	956.3	955.6	954.2	952.9	951.5	950.1	951.5	952.9	954.2	955.6	956.3
170°	961.9	961.2	959.8	958.4	957.0	955.6	957.0	958.4	959.8	961.2	961.9
172.5°	966.1	965.4	964.0	962.6	961.2	959.8	961.2	962.6	964.0	965.4	966.1
175°	968.9	968.1	966.6	965.0	963.5	961.9	963.5	965.0	966.6	968.1	968.9
177.5°	969.6	968.9	967.5	966.1	964.7	963.3	964.7	966.1	967.5	968.9	969.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1019.9	1023.7	1022.2	1014.0	1022.2	1024.4	1028.9	1033.3	1036.3	1040.8	1044.5
5°	956.0	963.4	967.9	963.4	978.3	980.5	990.9	996.9	1005.8	1013.2	1019.2
7.5°	895.7	901.7	910.6	912.1	921.0	931.4	946.3	961.2	975.3	982.7	989.4
10°	831.0	841.4	854.8	851.8	865.2	881.6	897.2	921.0	932.9	946.3	958.2
12.5°	766.3	773.0	790.8	796.8	816.1	828.7	850.3	865.2	895.0	910.6	921.0
15°	653.2	680.7	703.0	729.8	755.1	778.9	798.2	825.0	851.1	863.0	880.1
17.5°	601.8	614.5	627.9	641.3	674.0	716.4	750.6	779.6	802.0	817.6	837.7
20°	548.3	560.9	575.8	588.5	608.5	639.0	681.4	731.3	758.1	774.4	793.8
22.5°	510.3	522.2	531.9	543.1	558.7	581.0	613.0	674.8	710.5	730.5	747.7
25°	469.4	484.3	494.7	502.9	515.5	540.1	566.1	601.1	665.1	680.7	704.5
27.5°	441.2	445.6	457.5	470.2	482.8	496.2	523.0	552.7	595.9	630.1	659.1
30°	407.7	418.8	430.0	435.2	446.4	465.7	482.1	514.1	547.5	574.3	609.3
32.5°	382.4	389.1	396.5	409.2	419.6	433.0	449.3	476.1	504.4	521.5	548.3
35°	354.1	358.6	374.2	379.4	389.8	403.2	419.6	440.4	470.9	484.3	503.6
37.5°	327.3	337.7	342.2	354.1	363.8	377.2	389.1	412.9	433.0	448.6	466.4
40°	306.5	311.0	319.1	329.6	337.7	348.2	363.0	380.2	401.7	414.4	430.0
42.5°	281.2	284.9	295.3	301.3	314.7	324.4	333.3	354.1	373.5	383.1	398.8
45°	253.7	262.6	269.3	281.2	288.6	300.6	311.7	326.6	344.4	355.6	364.5
47.5°	229.9	238.8	245.5	256.7	268.6	273.8	285.7	301.3	317.7	326.6	339.2
50°	210.5	213.5	226.2	231.4	244.0	254.4	262.6	276.0	293.9	299.1	309.5
52.5°	191.9	194.2	202.4	209.0	220.2	229.1	239.5	252.2	267.1	275.3	283.4
55°	175.6	177.1	180.8	188.2	195.7	206.8	216.5	228.4	241.0	250.0	257.4
57.5°	157.0	159.9	162.9	167.4	174.8	185.2	195.7	206.8	217.2	223.2	232.9
60°	135.4	139.9	145.1	150.3	155.5	162.9	174.8	185.2	194.9	200.1	207.6
62.5°	112.3	121.3	125.7	131.7	136.1	142.8	151.8	163.7	170.4	177.1	183.0
65°	101.2	101.9	102.7	108.6	116.8	123.5	131.7	140.6	151.0	155.5	159.9
67.5°	90.0	90.8	92.2	93.0	96.0	103.4	112.3	122.0	130.2	133.2	137.6
70°	78.9	78.9	81.8	82.6	83.3	84.1	91.5	101.2	108.6	112.3	117.5
72.5°	67.0	67.7	69.2	69.9	71.4	72.9	75.1	80.3	89.3	93.0	98.9
75°	55.1	55.8	56.5	57.3	59.5	60.3	62.5	65.5	69.2	73.6	77.4
77.5°	43.9	43.9	44.6	46.1	47.6	48.4	50.6	52.1	53.6	55.8	58.8
80°	32.7	33.5	33.5	35.0	35.0	35.7	36.5	38.7	40.2	41.7	43.1
82.5°	22.3	23.8	23.8	23.8	24.5	25.3	26.0	26.0	27.5	28.3	30.5
85°	13.4	14.1	14.1	14.1	13.4	14.9	14.9	15.6	15.6	15.6	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.3	29.5	28.8	28.0	27.2	26.1	25.1	24.0	22.9	22.4	25.0
97.5°	37.5	37.0	36.5	36.1	35.6	33.1	30.7	28.2	25.7	24.5	30.9
100°	44.8	43.5	42.3	41.0	39.8	37.2	34.5	31.9	29.2	27.9	38.5
102.5°	48.0	46.3	44.6	42.9	41.2	69.5	97.7	126.0	154.3	168.4	168.6
105°	49.4	47.7	46.0	44.3	42.6	85.0	127.4	169.7	212.1	233.3	231.0
107.5°	50.8	49.1	47.4	45.7	44.0	96.3	148.6	200.9	253.2	279.4	277.5
110°	60.2	75.7	91.2	106.8	122.3	167.1	212.0	256.8	301.7	324.1	322.5

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.3	154.2	221.1	288.0	354.9	357.5	360.2	362.8	365.5	366.8	365.4
115°	143.5	215.4	287.3	359.1	431.0	427.1	423.3	419.4	415.5	413.6	412.3
117.5°	379.9	402.1	424.3	446.5	468.7	466.1	463.5	460.8	458.2	456.9	455.3
120°	519.5	517.6	515.8	513.9	512.1	509.3	506.5	503.7	500.9	499.5	498.3
122.5°	557.0	556.1	555.2	554.2	553.3	550.2	547.1	544.0	540.9	539.3	538.1
125°	594.7	593.6	592.5	591.4	590.3	587.3	584.4	581.4	578.5	577.0	576.0
127.5°	630.7	629.2	627.6	626.1	624.5	622.2	619.8	617.5	615.2	614.0	612.9
130°	664.2	662.5	660.8	659.1	657.4	655.7	654.0	652.3	650.6	649.7	648.5
132.5°	695.8	694.4	693.0	691.6	690.2	688.5	686.8	685.1	683.4	682.5	681.5
135°	726.4	724.9	723.3	721.8	720.2	718.8	717.4	716.0	714.6	713.9	712.7
137.5°	755.1	753.6	752.0	750.5	748.9	747.3	745.8	744.2	742.7	741.9	741.0
140°	782.4	781.0	779.6	778.2	776.8	775.1	773.4	771.7	770.0	769.1	768.5
142.5°	807.7	806.4	805.2	803.9	802.7	800.7	798.7	796.6	794.6	793.6	793.1
145°	830.8	829.7	828.6	827.5	826.4	823.8	821.1	818.5	815.8	814.5	814.6
147.5°	851.2	850.4	849.7	848.9	848.1	845.5	842.8	840.2	837.5	836.2	836.4
150°	870.6	869.7	868.8	867.8	866.9	864.4	862.0	859.5	857.0	855.8	856.3
152.5°	888.1	887.2	886.3	885.3	884.4	882.1	879.7	877.4	875.1	873.9	874.5
155°	903.5	902.6	901.7	900.7	899.8	897.9	896.1	894.2	892.3	891.4	892.1
157.5°	917.4	916.3	915.2	914.1	913.0	911.6	910.2	908.8	907.4	906.7	907.3
160°	928.6	927.7	926.8	925.8	924.9	924.0	923.0	922.1	921.2	920.7	921.2
162.5°	939.8	938.7	937.6	936.5	935.4	934.6	933.8	933.1	932.3	931.9	932.4
165°	948.2	947.1	946.0	944.9	943.8	943.3	942.9	942.4	941.9	941.7	942.2
167.5°	955.8	954.7	953.6	952.6	951.5	951.0	950.6	950.1	949.6	949.4	949.9
170°	961.4	960.3	959.2	958.1	957.0	956.7	956.4	956.1	955.8	955.6	956.1
172.5°	965.6	964.5	963.4	962.3	961.2	960.9	960.6	960.3	960.0	959.8	960.3
175°	968.4	967.3	966.2	965.1	964.0	963.7	963.4	963.1	962.8	962.6	963.1
177.5°	969.1	968.0	966.9	965.8	964.7	964.5	964.4	964.2	964.1	964.0	964.5
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1070.5	1070.5	1070.5	1070.5
2.5°	1051.2	1049.0	1062.3	1077.2
5°	1029.6	1033.3	1050.4	1071.3
7.5°	1007.3	1015.5	1035.6	1063.1
10°	976.0	990.9	1021.4	1049.7
12.5°	945.5	965.6	994.6	1028.1
15°	911.3	933.6	969.3	1009.5
17.5°	873.4	898.7	940.3	984.2
20°	833.2	866.7	910.6	958.2
22.5°	788.6	828.7	874.1	926.9
25°	745.4	789.3	834.7	895.7
27.5°	703.0	746.2	796.8	858.5
30°	660.6	700.0	754.4	820.6
32.5°	615.2	656.2	713.4	781.1
35°	573.6	614.5	668.1	735.0
37.5°	528.9	572.8	624.2	693.3
40°	476.9	528.2	578.0	644.2
42.5°	433.7	488.0	536.4	598.9
45°	399.5	450.8	491.0	552.0
47.5°	367.5	409.2	450.1	506.6
50°	337.0	369.0	411.4	462.0
52.5°	305.8	333.3	369.7	417.3
55°	277.5	303.5	336.3	372.7
57.5°	251.5	270.0	302.8	335.5
60°	222.4	241.8	267.1	294.6
62.5°	197.9	212.8	236.6	259.6
65°	171.8	186.0	203.8	225.4
67.5°	148.0	160.7	174.8	191.9
70°	126.5	136.1	146.6	161.4
72.5°	103.4	113.8	123.5	135.4
75°	84.8	89.3	97.5	105.6
77.5°	65.5	71.4	75.9	82.6
80°	46.9	52.1	53.6	58.8
82.5°	31.2	34.2	37.2	38.7
85°	17.9	19.3	22.3	23.1
87.5°	6.7	7.4	8.9	10.4
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.2	40.3	45.4
97.5°	43.6	56.3	69.0	81.7
100°	59.8	81.1	102.3	123.6
102.5°	168.9	169.2	169.5	169.8
105°	226.3	221.7	217.0	212.4
107.5°	273.6	269.7	265.9	262.0
110°	319.2	316.0	312.7	309.5

TEST NUMBER: P999790

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	362.6	359.8	357.0	354.2
115°	409.6	407.0	404.3	401.7
117.5°	452.2	449.1	446.0	442.9
120°	496.0	493.7	491.3	489.0
122.5°	535.6	533.1	530.6	528.1
125°	574.0	571.9	569.9	567.9
127.5°	610.8	608.6	606.5	604.3
130°	646.0	643.5	641.0	638.5
132.5°	679.5	677.4	675.4	673.4
135°	710.2	707.7	705.3	702.8
137.5°	739.1	737.2	735.4	733.5
140°	767.2	766.0	764.7	763.5
142.5°	792.0	790.9	789.8	788.7
145°	814.7	814.9	815.0	815.2
147.5°	836.9	837.4	837.8	838.3
150°	857.4	858.5	859.5	860.6
152.5°	875.8	877.0	878.3	879.5
155°	893.5	894.9	896.3	897.7
157.5°	908.6	909.8	911.1	912.3
160°	922.1	923.0	924.0	924.9
162.5°	933.3	934.2	935.2	936.1
165°	943.1	944.0	945.0	945.9
167.5°	950.8	951.7	952.7	953.6
170°	957.0	957.9	958.9	959.8
172.5°	961.2	962.1	963.1	964.0
175°	964.2	965.3	966.4	967.5
177.5°	965.6	966.7	967.8	968.9
180°	965.4	965.4	965.4	965.4

(END OF REPORT)