

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999829

Luminaire Tested: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999829
REPORT IS A COMBINATION OF REPORTS P988384 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5468.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34		
1	95	91	87	84	85	82	79	76	66	64	62	51	49	48	37	36	36	29		
2	87	80	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25		
3	79	71	64	58	71	64	58	54	52	48	44	40	38	35	30	28	27	22		
4	73	63	55	50	66	57	51	46	46	42	38	36	33	31	27	25	24	20		
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	17		
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16		
7	57	46	38	33	52	42	35	31	34	30	26	27	24	21	21	19	17	14		
8	53	42	34	29	48	38	32	27	31	27	23	25	22	19	19	17	15	13		
9	50	38	31	26	45	35	29	24	29	24	21	23	20	17	18	16	14	12		
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16800	16800	16800	16800
5°	16838	17843	16897	14255
10°	16653	18861	16771	11771
15°	16292	18866	16568	8843
20°	15857	15595	16202	7295
25°	15331	9745	15661	6206
30°	14658	6240	15056	5343
35°	13839	4794	14287	4573
40°	12927	4030	13479	4000
45°	11951	3431	12451	3357
50°	10952	2914	11464	2904
55°	9846	2533	10376	2500
60°	8864	1932	9331	1908
65°	7945	1454	8415	1650
70°	6929	1161	7475	1344
75°	5857	890	6394	1016
80°	4655	605	5006	666
85°	3235	313	3546	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15368 cd/sqm

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	1.8
10°-20°	281.0	5.1
20°-30°	361.6	6.6
30°-40°	343.1	6.3
40°-50°	294.0	5.4
50°-60°	223.9	4.1
60°-70°	141.2	2.6
70°-80°	70.5	1.3
80°-90°	20.3	0.4
90°-100°	40.9	0.7
100°-110°	152.3	2.8
110°-120°	403.9	7.4
120°-130°	669.8	12.3
130°-140°	711.5	13.0
140°-150°	661.3	12.1
150°-160°	531.6	9.7
160°-170°	342.6	6.3
170°-180°	117.9	2.2
0°-30°	743.3	13.6
0°-40°	1086.3	19.9
0°-60°	1604.3	29.3
0°-90°	1836.2	33.6
90°-120°	597.0	10.9
90°-150°	2639.7	48.3
90°-180°	3632.0	66.4
0°-180°	5468.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1061	1061	1061	1061	1061	
5°	1062	1181	1066	943	1062	101
15°	1001	1333	1018	625	1001	282
25°	888	711	907	453	888	408
35°	729	350	752	334	729	456
45°	547	243	570	238	547	422
55°	370	169	389	167	370	333
65°	224	88	237	100	224	222
75°	105	46	114	53	105	113
85°	23	13	25	14	23	26
90°	1	24	1	24	1	5
95°	58	38	58	38	58	69
105°	272	68	272	68	272	291
115°	515	74	515	74	515	507
125°	729	766	729	766	729	650
135°	902	931	902	931	902	697
145°	1046	1062	1046	1062	1046	654
155°	1152	1153	1152	1153	1152	531
165°	1214	1211	1214	1211	1214	343
175°	1242	1234	1242	1234	1242	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.9	1072.3	1074.5	1077.5	1084.1	1088.6	1095.2	1096.7	1095.9	1098.9	1090.8
5°	1062.0	1071.6	1080.4	1087.8	1099.6	1107.0	1115.1	1124.7	1126.9	1138.0	1131.3
7.5°	1053.9	1067.9	1080.4	1095.2	1112.9	1122.5	1135.0	1149.8	1156.4	1169.7	1173.4
10°	1040.6	1060.5	1081.9	1097.4	1121.7	1138.7	1150.5	1174.1	1189.6	1209.5	1206.6
12.5°	1019.2	1045.0	1073.8	1099.6	1131.3	1142.4	1164.5	1188.9	1208.8	1227.2	1243.4
15°	1000.8	1030.3	1062.0	1093.7	1129.9	1150.5	1172.6	1204.3	1225.7	1258.2	1272.2
17.5°	975.7	1013.3	1050.9	1086.3	1129.1	1152.7	1180.0	1211.0	1242.7	1273.7	1284.7
20°	949.9	990.5	1031.0	1079.0	1127.6	1150.5	1178.5	1216.9	1247.9	1272.2	1272.2
22.5°	918.9	968.3	1014.8	1060.5	1113.6	1146.8	1175.6	1220.6	1242.7	1247.9	1227.9
25°	888.0	937.4	988.3	1045.0	1105.5	1135.0	1167.5	1209.5	1216.9	1196.2	1144.6
27.5°	851.1	906.4	963.9	1025.1	1088.6	1125.4	1154.9	1183.0	1168.9	1113.6	1033.2
30°	813.5	873.2	938.1	996.4	1073.1	1107.0	1132.1	1140.2	1095.9	1006.0	902.0
32.5°	774.4	832.6	901.2	971.3	1048.7	1081.2	1097.4	1076.0	994.9	881.3	754.5
35°	728.7	794.3	865.8	938.8	1015.5	1039.9	1049.5	997.1	893.1	746.4	620.2
37.5°	687.4	753.0	829.7	904.2	978.7	991.9	982.4	900.5	768.5	623.2	500.0
40°	638.7	708.7	784.0	867.3	928.5	932.2	908.6	802.4	638.7	502.2	426.3
42.5°	593.7	664.5	739.7	824.5	871.0	858.5	826.7	687.4	533.2	432.9	371.7
45°	547.2	614.3	695.5	770.7	803.9	774.4	726.4	578.2	447.7	372.4	325.2
47.5°	502.2	564.9	645.3	717.6	723.5	690.3	633.5	484.5	387.9	327.5	289.1
50°	458.0	520.7	595.9	655.6	649.7	604.0	539.9	421.1	337.0	289.1	257.4
52.5°	413.7	470.5	543.5	590.7	565.7	521.4	458.0	357.0	294.3	252.2	227.9
55°	369.5	422.6	485.3	524.4	484.5	433.7	388.7	306.1	255.2	221.3	202.8
57.5°	332.6	374.7	432.2	455.8	407.8	368.0	328.9	263.3	221.3	196.9	175.5
60°	292.1	330.4	377.6	391.6	342.2	309.8	276.6	222.7	189.5	168.2	154.1
62.5°	257.4	289.1	325.2	325.2	281.7	257.4	232.3	186.6	159.3	142.3	135.7
65°	223.5	246.3	272.1	269.2	232.3	210.9	191.0	154.1	133.5	121.7	115.1
67.5°	190.3	208.0	224.9	214.6	188.1	169.6	151.2	124.6	110.6	102.5	93.7
70°	160.0	174.1	182.9	173.3	146.8	131.3	118.0	100.3	89.2	78.9	73.8
72.5°	134.2	140.1	143.1	131.3	109.2	100.3	90.7	78.2	68.6	63.4	62.0
75°	104.7	109.9	107.7	98.8	80.4	73.8	66.4	57.5	55.3	52.4	50.9
77.5°	81.9	81.9	78.2	70.1	57.5	52.4	49.4	45.0	42.8	42.0	40.6
80°	58.3	57.5	55.3	46.5	39.1	36.1	36.1	33.2	32.5	31.0	31.0
82.5°	38.4	38.4	35.4	28.0	25.8	25.1	24.3	22.9	22.9	22.1	22.1
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.0	13.3	14.0	13.3	13.3
87.5°	10.3	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.7	16.3	17.9
92.5°	22.4	21.6	20.8	20.0	19.2	18.8	19.1	19.7	20.3	20.9	21.5
95°	58.3	51.7	45.1	38.6	32.0	28.7	29.4	30.8	32.2	33.6	35.0
97.5°	104.9	88.6	72.2	55.9	39.6	31.4	33.0	36.2	39.3	42.5	45.7
100°	158.7	131.4	104.1	76.8	49.5	35.9	37.6	41.0	44.3	47.7	51.1
102.5°	217.8	217.4	217.0	216.6	216.2	216.0	197.9	161.6	125.4	89.1	52.9
105°	272.5	278.5	284.5	290.4	296.4	299.4	272.2	217.8	163.5	109.1	54.7
107.5°	336.2	341.2	346.2	351.1	356.1	358.6	325.0	257.9	190.8	123.6	56.5
110°	397.1	401.3	405.5	409.6	413.8	415.9	387.1	329.6	272.0	214.5	156.9

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	454.5	458.1	461.7	465.2	468.8	470.6	468.9	465.5	462.2	458.8	455.4
115°	515.4	518.8	522.2	525.6	529.0	530.7	533.2	538.2	543.1	548.1	553.1
117.5°	568.3	572.3	576.3	580.2	584.2	586.2	587.9	591.3	594.7	598.1	601.5
120°	627.5	630.5	633.5	636.4	639.4	640.9	642.7	646.3	649.9	653.5	657.1
122.5°	677.7	680.9	684.1	687.2	690.4	692.0	694.0	698.0	702.0	706.0	710.0
125°	728.8	731.4	734.0	736.5	739.1	740.4	742.3	746.1	749.9	753.7	757.5
127.5°	775.4	778.2	781.0	783.7	786.5	787.9	789.4	792.4	795.4	798.4	801.4
130°	819.3	822.5	825.7	828.9	832.1	833.7	834.8	837.0	839.1	841.3	843.5
132.5°	864.1	866.7	869.3	871.9	874.5	875.8	876.9	879.1	881.2	883.4	885.6
135°	901.8	905.0	908.2	911.3	914.5	916.1	917.0	918.8	920.6	922.4	924.2
137.5°	941.2	943.6	946.0	948.4	950.8	952.0	953.0	955.0	956.9	958.9	960.9
140°	979.8	981.4	983.0	984.5	986.1	986.9	988.0	990.2	992.4	994.6	996.8
142.5°	1012.0	1013.4	1014.8	1016.2	1017.6	1018.3	1019.6	1022.2	1024.8	1027.4	1030.0
145°	1046.1	1045.9	1045.7	1045.5	1045.3	1045.2	1046.9	1050.3	1053.6	1057.0	1060.4
147.5°	1075.7	1075.1	1074.5	1073.9	1073.3	1073.0	1074.7	1078.1	1081.4	1084.8	1088.2
150°	1104.4	1103.0	1101.6	1100.2	1098.8	1098.1	1099.7	1102.9	1106.0	1109.2	1112.4
152.5°	1128.6	1127.0	1125.4	1123.8	1122.2	1121.4	1122.9	1125.9	1128.8	1131.8	1134.8
155°	1151.9	1150.1	1148.3	1146.5	1144.7	1143.8	1145.0	1147.4	1149.8	1152.2	1154.6
157.5°	1170.7	1169.1	1167.5	1165.9	1164.3	1163.5	1164.4	1166.2	1168.0	1169.8	1171.6
160°	1186.8	1185.6	1184.4	1183.3	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8
162.5°	1201.2	1200.0	1198.8	1197.6	1196.4	1195.8	1196.3	1197.3	1198.3	1199.3	1200.3
165°	1213.7	1212.5	1211.3	1210.2	1209.0	1208.4	1208.7	1209.3	1209.8	1210.4	1211.0
167.5°	1223.6	1222.4	1221.2	1220.0	1218.8	1218.2	1218.5	1219.1	1219.7	1220.3	1220.9
170°	1231.7	1230.5	1229.3	1228.1	1226.9	1226.3	1226.5	1226.9	1227.3	1227.7	1228.1
172.5°	1237.0	1235.8	1234.6	1233.5	1232.3	1231.7	1231.9	1232.3	1232.7	1233.1	1233.5
175°	1241.5	1240.1	1238.7	1237.3	1235.9	1235.2	1235.4	1235.8	1236.2	1236.6	1237.0
177.5°	1243.3	1241.9	1240.5	1239.1	1237.7	1237.0	1237.1	1237.3	1237.5	1237.7	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1098.9	1100.4	1102.6	1112.9	1114.4	1117.3	1115.8	1115.8	1116.6	1115.1	1115.8
5°	1146.1	1148.3	1159.4	1171.9	1174.8	1171.9	1175.6	1180.7	1180.7	1180.7	1179.3
7.5°	1190.3	1198.4	1211.0	1229.4	1233.1	1236.8	1243.4	1239.0	1240.5	1247.1	1244.9
10°	1233.1	1244.9	1258.9	1274.4	1282.5	1287.7	1290.6	1297.3	1312.8	1295.1	1301.7
12.5°	1273.7	1290.6	1305.4	1322.3	1328.2	1334.9	1337.1	1343.0	1343.0	1342.3	1347.4
15°	1300.2	1315.7	1329.0	1340.0	1341.5	1340.0	1338.6	1339.3	1341.5	1332.7	1337.8
17.5°	1306.1	1307.6	1312.0	1307.6	1308.3	1292.8	1284.0	1281.8	1261.1	1261.9	1278.8
20°	1277.4	1252.3	1245.6	1221.3	1206.6	1166.7	1165.3	1154.2	1110.7	1124.0	1121.0
22.5°	1198.4	1155.7	1098.9	1070.9	1056.8	1014.8	982.4	959.5	944.0	928.5	921.9
25°	1094.5	1025.1	944.7	889.4	881.3	842.2	782.5	754.5	721.3	711.0	728.7
27.5°	960.2	870.3	779.5	694.7	679.2	643.8	613.6	593.7	555.3	553.1	554.6
30°	778.1	687.4	611.4	556.1	517.7	501.5	481.6	466.8	451.4	457.3	458.7
32.5°	639.4	553.1	482.3	452.8	435.1	424.8	407.8	398.3	391.6	389.4	388.7
35°	508.1	450.6	418.9	390.1	379.8	372.4	359.9	355.5	349.6	350.3	350.3
37.5°	435.1	387.2	363.6	348.8	339.3	335.6	327.5	323.0	319.3	317.9	320.1
40°	375.4	342.2	327.5	314.2	306.1	304.6	300.2	295.0	290.6	291.3	293.5
42.5°	331.9	312.7	295.0	284.7	278.8	276.6	272.9	269.2	269.2	267.0	266.2
45°	297.2	281.7	267.0	257.4	253.7	250.8	246.3	245.6	242.6	243.4	244.1
47.5°	266.2	253.7	242.6	233.1	229.4	228.6	224.2	221.3	221.3	220.5	219.8
50°	238.2	225.7	216.1	210.9	205.8	204.3	203.6	202.8	201.3	201.3	202.1
52.5°	215.4	202.8	195.4	191.0	188.1	186.6	186.6	185.9	185.9	185.9	185.1
55°	190.3	180.0	174.1	172.6	171.1	170.4	169.6	168.2	167.4	168.9	167.4
57.5°	166.7	163.0	157.8	156.4	152.7	152.7	150.5	149.0	147.5	149.0	149.0
60°	148.2	143.1	140.1	135.7	132.8	129.8	126.1	125.4	123.9	123.2	122.4
62.5°	129.1	124.6	117.3	110.6	106.2	103.3	101.8	101.0	101.0	100.3	100.3
65°	107.7	97.4	93.7	91.5	90.7	90.0	88.5	87.8	88.5	87.8	88.5
67.5°	84.1	82.6	80.4	78.9	78.2	77.4	77.4	76.7	76.7	76.7	76.7
70°	73.0	69.3	68.6	67.1	67.1	66.4	66.4	66.4	66.4	65.6	67.1
72.5°	60.5	58.3	57.5	56.8	56.8	56.8	56.1	56.1	56.1	55.3	56.1
75°	49.4	48.7	47.2	47.2	46.5	47.2	46.5	46.5	45.7	46.5	46.5
77.5°	39.8	39.1	38.4	38.4	37.6	37.6	37.6	37.6	37.6	37.6	38.4
80°	30.2	29.5	28.8	29.5	28.8	29.5	28.8	28.8	29.5	28.8	28.8
82.5°	22.1	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.5	12.5	13.3	12.5	13.3	12.5	12.5	12.5	13.3	13.3
87.5°	5.9	6.6	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.6
90°	18.9	19.9	20.9	21.9	22.4	22.6	23.0	23.4	23.8	24.2	23.8
92.5°	21.9	22.3	22.7	23.1	23.3	23.4	23.6	23.8	24.0	24.2	24.0
95°	36.0	37.0	37.9	38.9	39.4	39.3	39.1	38.9	38.7	38.5	38.7
97.5°	46.3	46.9	47.5	48.1	48.4	48.5	48.7	48.9	49.1	49.3	49.1
100°	52.7	54.3	55.9	57.5	58.3	58.5	58.9	59.3	59.7	60.1	59.7
102.5°	55.1	57.3	59.4	61.6	62.7	63.0	63.6	64.2	64.8	65.4	64.8
105°	56.9	59.1	61.2	63.4	64.5	64.9	65.7	66.5	67.3	68.1	67.3
107.5°	58.7	60.9	63.0	65.2	66.3	66.7	67.5	68.3	69.1	69.9	69.1
110°	137.0	117.0	97.1	77.2	67.2	67.6	68.4	69.2	70.0	70.8	70.0

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	369.5	283.7	197.8	111.9	69.0	69.3	69.9	70.5	71.1	71.7	71.1
115°	460.9	368.6	276.4	184.1	138.0	130.8	116.5	102.2	87.8	73.5	87.8
117.5°	573.0	544.5	516.0	487.5	473.3	447.2	395.0	342.8	290.6	238.4	290.6
120°	659.5	661.9	664.2	666.6	667.8	654.4	627.5	600.6	573.7	546.8	573.7
122.5°	711.2	712.4	713.5	714.7	715.3	715.4	715.6	715.8	716.0	716.2	716.0
125°	758.9	760.3	761.6	763.0	763.7	764.0	764.6	765.2	765.8	766.4	765.8
127.5°	803.4	805.4	807.4	809.4	810.4	810.5	810.7	810.8	811.0	811.2	811.0
130°	845.7	847.9	850.1	852.3	853.4	853.3	853.1	852.9	852.7	852.5	852.7
132.5°	887.4	889.2	891.0	892.8	893.7	893.6	893.4	893.2	893.0	892.8	893.0
135°	926.2	928.2	930.2	932.2	933.2	933.0	932.6	932.2	931.8	931.4	931.8
137.5°	962.9	964.9	966.9	968.9	969.9	969.6	969.0	968.4	967.8	967.2	967.8
140°	998.6	1000.4	1002.2	1004.0	1004.9	1004.4	1003.4	1002.4	1001.4	1000.4	1001.4
142.5°	1031.6	1033.2	1034.7	1036.3	1037.1	1036.6	1035.6	1034.7	1033.7	1032.7	1033.7
145°	1061.8	1063.2	1064.6	1066.0	1066.7	1066.2	1065.2	1064.2	1063.2	1062.2	1063.2
147.5°	1089.2	1090.2	1091.2	1092.2	1092.7	1092.3	1091.5	1090.7	1089.9	1089.1	1089.9
150°	1113.6	1114.8	1116.0	1117.2	1117.8	1117.3	1116.3	1115.3	1114.3	1113.3	1114.3
152.5°	1136.0	1137.2	1138.4	1139.6	1140.2	1139.5	1138.1	1136.8	1135.4	1134.0	1135.4
155°	1155.8	1157.0	1158.1	1159.3	1159.9	1159.1	1157.5	1156.0	1154.4	1152.8	1154.4
157.5°	1173.0	1174.4	1175.8	1177.2	1177.9	1177.1	1175.5	1173.9	1172.3	1170.7	1172.3
160°	1188.0	1189.2	1190.4	1191.6	1192.2	1191.5	1190.1	1188.7	1187.3	1185.9	1187.3
162.5°	1201.7	1203.1	1204.5	1205.9	1206.6	1205.7	1203.9	1202.1	1200.3	1198.5	1200.3
165°	1212.4	1213.8	1215.2	1216.6	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1212.4
167.5°	1222.3	1223.7	1225.1	1226.5	1227.2	1226.3	1224.5	1222.7	1220.9	1219.1	1220.9
170°	1229.5	1230.9	1232.2	1233.6	1234.3	1233.4	1231.6	1229.9	1228.1	1226.3	1228.1
172.5°	1234.9	1236.3	1237.6	1239.0	1239.7	1238.8	1237.0	1235.3	1233.5	1231.7	1233.5
175°	1238.4	1239.8	1241.2	1242.6	1243.3	1242.3	1240.3	1238.3	1236.3	1234.3	1236.3
177.5°	1239.3	1240.7	1242.1	1243.5	1244.2	1243.3	1241.5	1239.7	1237.9	1236.1	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1118.8	1113.6	1112.2	1113.6	1112.2	1112.9	1107.7	1088.6	1093.7	1085.6	1090.0
5°	1182.2	1177.8	1168.2	1166.7	1165.3	1163.8	1156.4	1139.4	1132.8	1121.7	1121.0
7.5°	1242.7	1242.7	1235.3	1230.2	1223.5	1218.4	1208.8	1183.7	1173.4	1160.1	1152.7
10°	1302.4	1283.3	1291.4	1286.2	1270.0	1267.0	1249.3	1234.6	1214.7	1201.4	1189.6
12.5°	1345.2	1339.3	1331.9	1327.5	1323.1	1313.5	1301.7	1264.1	1253.8	1227.2	1213.9
15°	1343.7	1340.0	1342.3	1342.3	1340.8	1338.6	1329.0	1301.7	1284.0	1258.2	1235.3
17.5°	1271.5	1281.0	1290.6	1297.3	1312.0	1318.7	1327.5	1311.3	1300.2	1278.1	1253.8
20°	1145.3	1168.9	1197.0	1202.9	1216.1	1255.2	1272.9	1286.9	1291.4	1284.0	1264.1
22.5°	969.8	989.7	1057.6	1056.1	1075.3	1121.7	1173.4	1215.4	1248.6	1267.0	1259.7
25°	759.6	787.7	823.8	851.1	913.8	983.1	1047.3	1114.4	1171.9	1222.8	1235.3
27.5°	574.5	611.4	640.2	676.3	708.0	789.9	872.5	977.2	1044.3	1140.9	1191.1
30°	464.6	481.6	510.4	527.3	542.8	605.5	699.2	802.4	920.4	1031.8	1118.1
32.5°	396.8	408.6	430.0	437.3	453.6	495.6	554.6	649.0	770.7	905.7	1019.2
35°	356.2	368.8	373.2	379.8	393.1	419.6	460.2	528.8	638.7	770.7	906.4
37.5°	321.6	328.2	340.7	345.2	349.6	369.5	396.8	444.7	517.7	626.1	776.6
40°	297.2	300.9	307.5	311.2	314.2	328.2	352.5	385.0	438.8	521.4	660.1
42.5°	271.4	275.8	280.3	284.7	288.4	299.4	314.2	345.2	381.3	444.0	544.3
45°	246.3	249.3	254.4	257.4	262.6	271.4	284.7	306.1	338.5	378.3	459.5
47.5°	223.5	227.2	229.4	233.1	236.7	246.3	258.9	272.9	299.4	338.5	397.5
50°	202.8	207.2	210.2	210.9	213.9	222.7	233.1	248.5	265.5	295.7	347.4
52.5°	188.1	188.8	191.0	194.0	193.2	198.4	208.0	219.8	237.5	261.8	299.4
55°	171.1	173.3	174.8	175.5	175.5	180.0	185.1	196.2	210.2	230.1	261.8
57.5°	149.7	151.9	156.4	157.8	160.0	162.3	164.5	171.8	183.6	202.8	228.6
60°	127.6	129.1	133.5	136.4	137.9	143.8	146.8	152.7	159.3	173.3	197.7
62.5°	102.5	104.0	106.2	109.2	112.1	121.0	128.3	134.2	139.4	149.0	168.9
65°	89.2	90.0	91.5	92.2	92.9	96.6	103.3	111.4	121.0	128.3	140.1
67.5°	77.4	78.2	78.9	80.4	81.1	81.9	84.8	87.0	96.6	106.9	115.8
70°	66.4	67.9	68.6	68.6	69.3	70.8	72.3	75.2	78.2	83.3	94.4
72.5°	56.1	56.8	58.3	58.3	58.3	59.7	61.2	62.7	64.2	67.1	71.5
75°	46.5	47.9	47.9	47.9	48.7	48.7	50.2	51.6	53.1	55.3	56.8
77.5°	38.4	38.4	38.4	38.4	39.1	39.1	39.8	41.3	42.0	42.8	44.3
80°	28.8	29.5	29.5	29.5	30.2	30.2	30.2	31.7	32.5	32.5	33.9
82.5°	21.4	21.4	21.4	22.1	21.4	22.1	22.1	22.9	22.1	22.9	23.6
85°	13.3	13.3	13.3	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.8
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.4	6.6	6.6
90°	23.4	23.0	22.6	22.4	21.9	20.9	19.9	18.9	17.9	16.3	14.7
92.5°	23.8	23.6	23.4	23.3	23.1	22.7	22.3	21.9	21.5	20.9	20.3
95°	38.9	39.1	39.3	39.4	38.9	37.9	37.0	36.0	35.0	33.6	32.2
97.5°	48.9	48.7	48.5	48.4	48.1	47.5	46.9	46.3	45.7	42.5	39.3
100°	59.3	58.9	58.5	58.3	57.5	55.9	54.3	52.7	51.1	47.7	44.3
102.5°	64.2	63.6	63.0	62.7	61.6	59.4	57.3	55.1	52.9	49.1	45.4
105°	66.5	65.7	64.9	64.5	63.4	61.2	59.1	56.9	54.7	50.1	46.5
107.5°	68.3	67.5	66.7	66.3	65.2	63.0	60.9	58.7	56.5	52.6	49.0
110°	69.2	68.4	67.6	67.2	77.2	97.1	117.0	137.0	156.9	214.5	272.0

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	70.5	69.9	69.3	69.0	111.9	197.8	283.7	369.5	455.4	458.8	462.2
115°	102.2	116.5	130.8	138.0	184.1	276.4	368.6	460.9	553.1	548.1	543.1
117.5°	342.8	395.0	447.2	473.3	487.5	516.0	544.5	573.0	601.5	598.1	594.7
120°	600.6	627.5	654.4	667.8	666.6	664.2	661.9	659.5	657.1	653.5	649.9
122.5°	715.8	715.6	715.4	715.3	714.7	713.5	712.4	711.2	710.0	706.0	702.0
125°	765.2	764.6	764.0	763.7	763.0	761.6	760.3	758.9	757.5	753.7	749.9
127.5°	810.8	810.7	810.5	810.4	809.4	807.4	805.4	803.4	801.4	798.4	795.4
130°	852.9	853.1	853.3	853.4	852.3	850.1	847.9	845.7	843.5	841.3	839.1
132.5°	893.2	893.4	893.6	893.7	892.8	891.0	889.2	887.4	885.6	883.4	881.2
135°	932.2	932.6	933.0	933.2	932.2	930.2	928.2	926.2	924.2	922.4	920.6
137.5°	968.4	969.0	969.6	969.9	968.9	966.9	964.9	962.9	960.9	958.9	956.9
140°	1002.4	1003.4	1004.4	1004.9	1004.0	1002.2	1000.4	998.6	996.8	994.6	992.4
142.5°	1034.7	1035.6	1036.6	1037.1	1036.3	1034.7	1033.2	1031.6	1030.0	1027.4	1024.8
145°	1064.2	1065.2	1066.2	1066.7	1066.0	1064.6	1063.2	1061.8	1060.4	1057.0	1053.6
147.5°	1090.7	1091.5	1092.3	1092.7	1092.2	1091.2	1090.2	1089.2	1088.2	1084.8	1081.4
150°	1115.3	1116.3	1117.3	1117.8	1117.2	1116.0	1114.8	1113.6	1112.4	1109.2	1106.0
152.5°	1136.8	1138.1	1139.5	1140.2	1139.6	1138.4	1137.2	1136.0	1134.8	1131.8	1128.8
155°	1156.0	1157.5	1159.1	1159.9	1159.3	1158.1	1157.0	1155.8	1154.6	1152.2	1149.8
157.5°	1173.9	1175.5	1177.1	1177.9	1177.2	1175.8	1174.4	1173.0	1171.6	1169.8	1168.0
160°	1188.7	1190.1	1191.5	1192.2	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1184.4
162.5°	1202.1	1203.9	1205.7	1206.6	1205.9	1204.5	1203.1	1201.7	1200.3	1199.3	1198.3
165°	1213.8	1215.2	1216.6	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1210.4	1209.8
167.5°	1222.7	1224.5	1226.3	1227.2	1226.5	1225.1	1223.7	1222.3	1220.9	1220.3	1219.7
170°	1229.9	1231.6	1233.4	1234.3	1233.6	1232.2	1230.9	1229.5	1228.1	1227.7	1227.3
172.5°	1235.3	1237.0	1238.8	1239.7	1239.0	1237.6	1236.3	1234.9	1233.5	1233.1	1232.7
175°	1238.3	1240.3	1242.3	1243.3	1242.6	1241.2	1239.8	1238.4	1237.0	1236.6	1236.2
177.5°	1239.7	1241.5	1243.3	1244.2	1243.5	1242.1	1240.7	1239.3	1237.9	1237.7	1237.5
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1083.4	1079.7	1079.7	1077.5	1077.5	1065.7	1065.7	1069.4	1065.0	1059.8	1052.4
5°	1111.4	1103.3	1101.1	1098.1	1088.6	1073.8	1067.9	1065.7	1056.8	1045.8	1033.2
7.5°	1138.0	1124.7	1118.1	1111.4	1098.9	1078.2	1066.4	1058.3	1045.0	1028.1	1011.9
10°	1163.8	1146.8	1129.9	1121.7	1104.0	1078.2	1061.3	1048.0	1028.8	1006.0	983.1
12.5°	1187.4	1152.0	1149.0	1132.8	1107.0	1077.5	1051.7	1032.5	1008.2	981.6	955.1
15°	1208.0	1171.9	1154.2	1139.4	1105.5	1068.6	1041.4	1017.8	985.3	955.1	922.6
17.5°	1218.4	1179.3	1167.5	1143.1	1108.5	1060.5	1023.7	994.9	959.5	923.4	886.5
20°	1228.7	1183.0	1163.8	1146.8	1099.6	1045.0	1003.7	970.6	931.5	888.7	848.1
22.5°	1233.8	1183.0	1160.1	1136.5	1090.8	1028.1	979.4	940.3	894.6	851.1	802.4
25°	1225.0	1178.5	1151.2	1126.9	1075.3	1007.4	951.4	907.1	858.5	809.0	759.6
27.5°	1202.9	1168.2	1136.5	1111.4	1053.9	980.9	921.9	871.7	821.6	766.3	716.1
30°	1161.6	1146.1	1121.0	1093.0	1030.3	957.3	887.2	835.6	780.3	725.0	672.6
32.5°	1097.4	1110.7	1094.5	1070.1	1002.3	924.8	850.3	798.0	737.5	677.8	629.8
35°	1019.2	1066.4	1057.6	1040.6	972.8	890.2	815.7	752.3	691.8	631.3	583.4
37.5°	933.7	1005.2	1012.6	1002.3	938.8	854.8	772.9	711.0	649.0	587.8	539.1
40°	816.4	926.3	949.9	954.3	903.4	812.0	726.4	666.0	604.8	545.0	486.0
42.5°	708.7	847.4	876.9	895.3	858.5	770.0	683.7	616.6	556.1	502.2	443.2
45°	607.7	752.3	800.2	823.8	807.6	722.0	632.8	570.1	514.8	465.4	408.6
47.5°	503.7	649.0	716.1	753.7	753.7	673.3	584.1	522.2	469.1	427.0	376.9
50°	434.4	555.3	624.7	674.1	687.4	623.9	539.9	479.4	429.2	383.5	345.2
52.5°	370.2	478.6	536.2	587.8	626.1	570.8	490.4	435.9	386.5	343.7	313.4
55°	320.1	401.2	453.6	510.4	553.1	517.0	442.5	389.4	346.6	311.2	285.4
57.5°	272.1	342.9	385.7	435.9	481.6	454.3	394.6	348.8	311.2	280.3	257.4
60°	231.6	289.1	322.3	361.4	418.2	399.0	349.6	307.5	277.3	249.3	230.1
62.5°	196.9	242.6	270.7	298.7	350.3	341.5	303.1	270.7	244.9	221.3	205.0
65°	161.5	199.1	221.3	245.6	286.9	290.6	259.6	236.7	213.1	192.5	177.7
67.5°	130.5	160.0	180.0	200.6	233.8	244.1	222.7	203.6	183.6	166.7	153.4
70°	105.5	126.1	140.9	157.1	184.4	196.9	185.9	172.6	156.4	142.3	130.5
72.5°	83.3	96.6	105.5	118.0	140.1	152.7	151.9	140.1	128.3	118.7	109.2
75°	61.2	71.5	78.9	87.0	104.7	116.5	119.5	114.3	102.5	95.1	87.8
77.5°	46.5	52.4	56.1	62.0	74.5	84.8	89.2	87.8	79.7	73.8	68.6
80°	35.4	36.9	38.4	40.6	50.9	60.5	63.4	62.7	58.3	56.1	50.2
82.5°	25.1	25.8	26.6	27.3	31.0	39.1	42.0	43.5	39.8	37.6	32.5
85°	14.8	15.5	15.5	17.0	17.7	19.9	25.1	25.1	24.3	21.4	20.7
87.5°	7.4	7.4	6.6	6.6	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.7	19.1	18.8	19.2	20.0	20.8	21.6	22.4	21.6	20.8	20.0
95°	30.8	29.4	28.7	32.0	38.6	45.1	51.7	58.3	51.7	45.1	38.6
97.5°	36.2	33.0	31.4	39.6	55.9	72.2	88.6	104.9	88.6	72.2	55.9
100°	41.0	37.6	35.9	49.5	76.8	104.1	131.4	158.7	131.4	104.1	76.8
102.5°	161.6	197.9	216.0	216.2	216.6	217.0	217.4	217.8	217.4	217.0	216.6
105°	217.8	272.2	299.4	296.4	290.4	284.5	278.5	272.5	278.5	284.5	290.4
107.5°	257.9	325.0	358.6	356.1	351.1	346.2	341.2	336.2	341.2	346.2	351.1
110°	329.6	387.1	415.9	413.8	409.6	405.5	401.3	397.1	401.3	405.5	409.6

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	465.5	468.9	470.6	468.8	465.2	461.7	458.1	454.5	458.1	461.7	465.2
115°	538.2	533.2	530.7	529.0	525.6	522.2	518.8	515.4	518.8	522.2	525.6
117.5°	591.3	587.9	586.2	584.2	580.2	576.3	572.3	568.3	572.3	576.3	580.2
120°	646.3	642.7	640.9	639.4	636.4	633.5	630.5	627.5	630.5	633.5	636.4
122.5°	698.0	694.0	692.0	690.4	687.2	684.1	680.9	677.7	680.9	684.1	687.2
125°	746.1	742.3	740.4	739.1	736.5	734.0	731.4	728.8	731.4	734.0	736.5
127.5°	792.4	789.4	787.9	786.5	783.7	781.0	778.2	775.4	778.2	781.0	783.7
130°	837.0	834.8	833.7	832.1	828.9	825.7	822.5	819.3	822.5	825.7	828.9
132.5°	879.1	876.9	875.8	874.5	871.9	869.3	866.7	864.1	866.7	869.3	871.9
135°	918.8	917.0	916.1	914.5	911.3	908.2	905.0	901.8	905.0	908.2	911.3
137.5°	955.0	953.0	952.0	950.8	948.4	946.0	943.6	941.2	943.6	946.0	948.4
140°	990.2	988.0	986.9	986.1	984.5	983.0	981.4	979.8	981.4	983.0	984.5
142.5°	1022.2	1019.6	1018.3	1017.6	1016.2	1014.8	1013.4	1012.0	1013.4	1014.8	1016.2
145°	1050.3	1046.9	1045.2	1045.3	1045.5	1045.7	1045.9	1046.1	1045.9	1045.7	1045.5
147.5°	1078.1	1074.7	1073.0	1073.3	1073.9	1074.5	1075.1	1075.7	1075.1	1074.5	1073.9
150°	1102.9	1099.7	1098.1	1098.8	1100.2	1101.6	1103.0	1104.4	1103.0	1101.6	1100.2
152.5°	1125.9	1122.9	1121.4	1122.2	1123.8	1125.4	1127.0	1128.6	1127.0	1125.4	1123.8
155°	1147.4	1145.0	1143.8	1144.7	1146.5	1148.3	1150.1	1151.9	1150.1	1148.3	1146.5
157.5°	1166.2	1164.4	1163.5	1164.3	1165.9	1167.5	1169.1	1170.7	1169.1	1167.5	1165.9
160°	1183.3	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8	1185.6	1184.4	1183.3
162.5°	1197.3	1196.3	1195.8	1196.4	1197.6	1198.8	1200.0	1201.2	1200.0	1198.8	1197.6
165°	1209.3	1208.7	1208.4	1209.0	1210.2	1211.3	1212.5	1213.7	1212.5	1211.3	1210.2
167.5°	1219.1	1218.5	1218.2	1218.8	1220.0	1221.2	1222.4	1223.6	1222.4	1221.2	1220.0
170°	1226.9	1226.5	1226.3	1226.9	1228.1	1229.3	1230.5	1231.7	1230.5	1229.3	1228.1
172.5°	1232.3	1231.9	1231.7	1232.3	1233.5	1234.6	1235.8	1237.0	1235.8	1234.6	1233.5
175°	1235.8	1235.4	1235.2	1235.9	1237.3	1238.7	1240.1	1241.5	1240.1	1238.7	1237.3
177.5°	1237.3	1237.1	1237.0	1237.7	1239.1	1240.5	1241.9	1243.3	1241.9	1240.5	1239.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1049.5	1050.2	1052.4	1045.8	1035.5	1031.0	1017.8	1015.5	1013.3	1013.3	1015.5
5°	1025.9	1022.9	1023.7	1011.1	996.4	987.5	969.1	972.0	962.4	956.5	958.0
7.5°	1000.1	991.9	991.2	975.0	956.5	940.3	921.1	916.7	907.9	897.5	893.1
10°	967.6	961.7	950.6	932.2	908.6	895.3	869.5	854.0	851.8	836.3	830.4
12.5°	934.4	924.1	913.0	887.2	860.7	839.3	820.1	803.1	791.3	778.1	769.2
15°	896.1	883.5	871.0	843.7	812.7	791.3	762.6	737.5	702.8	675.6	660.1
17.5°	854.0	840.0	823.1	792.8	762.6	733.1	680.0	650.5	626.1	609.9	600.3
20°	810.5	795.0	778.1	747.8	695.5	643.8	614.3	591.5	576.7	560.5	548.7
22.5°	764.8	748.6	730.1	682.9	627.6	591.5	568.6	547.2	525.8	517.0	511.1
25°	722.0	707.3	683.7	619.5	576.0	542.8	517.0	503.0	491.9	480.1	469.1
27.5°	677.8	650.5	617.3	563.5	536.2	502.2	483.8	473.5	454.3	446.2	441.0
30°	624.7	594.4	562.7	524.4	492.7	469.1	452.1	435.1	424.1	416.0	407.1
32.5°	570.8	542.1	522.2	482.3	458.7	434.4	418.2	407.8	391.6	386.5	382.8
35°	524.4	500.0	482.3	449.9	427.8	405.6	393.8	378.3	368.0	358.4	352.5
37.5°	478.6	465.4	446.9	419.6	396.0	378.3	362.1	357.0	342.9	337.8	331.9
40°	446.9	427.0	411.5	387.9	368.0	348.8	338.5	326.7	317.1	309.0	306.8
42.5°	408.6	393.8	385.0	359.2	338.5	327.5	314.9	301.6	294.3	287.6	279.5
45°	379.8	366.5	354.0	333.4	314.9	300.9	289.8	281.0	268.5	265.5	253.0
47.5°	349.6	336.3	326.7	306.1	289.1	275.8	267.7	255.9	245.6	239.0	233.1
50°	319.3	308.3	299.4	281.7	267.0	253.0	241.9	230.1	225.7	214.6	210.9
52.5°	290.6	283.2	273.6	256.7	241.9	230.1	218.3	208.7	202.1	196.2	191.8
55°	266.2	254.4	250.0	231.6	219.0	206.5	196.2	190.3	182.2	178.5	174.8
57.5°	239.0	232.3	224.9	210.9	196.9	185.1	177.7	168.9	164.5	160.0	157.1
60°	215.4	205.8	199.9	188.1	175.5	164.5	157.8	151.2	145.3	141.6	135.7
62.5°	188.1	180.7	177.0	164.5	154.1	143.8	137.9	131.3	126.9	120.2	112.8
65°	164.5	158.6	154.1	143.8	134.2	124.6	118.7	110.6	104.7	101.0	100.3
67.5°	143.8	139.4	132.8	123.2	113.6	106.2	99.6	92.9	92.2	90.7	90.7
70°	121.0	116.5	112.8	102.5	94.4	86.3	84.8	82.6	80.4	79.7	78.2
72.5°	101.0	97.4	92.9	84.1	76.0	73.8	72.3	70.8	68.6	67.9	67.1
75°	81.9	76.7	73.8	65.6	63.4	62.0	60.5	58.3	56.8	56.1	54.6
77.5°	62.7	57.5	57.5	53.1	51.6	49.4	47.9	46.5	45.7	44.3	44.3
80°	44.3	44.3	42.8	40.6	38.4	37.6	35.4	34.7	33.9	34.7	33.2
82.5°	32.5	29.5	29.5	28.0	26.6	25.8	24.3	24.3	23.6	23.6	23.6
85°	18.4	18.4	17.7	16.2	15.5	15.5	14.8	14.8	14.0	14.0	13.3
87.5°	7.4	6.6	7.4	6.6	6.6	5.9	5.9	5.9	5.2	5.9	5.2
90°	9.7	10.8	11.6	13.2	14.7	16.3	17.9	18.9	19.9	20.9	21.9
92.5°	19.2	18.8	19.1	19.7	20.3	20.9	21.5	21.9	22.3	22.7	23.1
95°	32.0	28.7	29.4	30.8	32.2	33.6	35.0	36.0	37.0	37.9	38.9
97.5°	39.6	31.4	33.0	36.2	39.3	42.5	45.7	46.3	46.9	47.5	48.1
100°	49.5	35.9	37.6	41.0	44.3	47.7	51.1	52.7	54.3	55.9	57.5
102.5°	216.2	216.0	197.9	161.6	125.4	89.1	52.9	55.1	57.3	59.4	61.6
105°	296.4	299.4	272.2	217.8	163.5	109.1	54.7	56.9	59.1	61.2	63.4
107.5°	356.1	358.6	325.0	257.9	190.8	123.6	56.5	58.7	60.9	63.0	65.2
110°	413.8	415.9	387.1	329.6	272.0	214.5	156.9	137.0	117.0	97.1	77.2

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	468.8	470.6	468.9	465.5	462.2	458.8	455.4	369.5	283.7	197.8	111.9
115°	529.0	530.7	533.2	538.2	543.1	548.1	553.1	460.9	368.6	276.4	184.1
117.5°	584.2	586.2	587.9	591.3	594.7	598.1	601.5	573.0	544.5	516.0	487.5
120°	639.4	640.9	642.7	646.3	649.9	653.5	657.1	659.5	661.9	664.2	666.6
122.5°	690.4	692.0	694.0	698.0	702.0	706.0	710.0	711.2	712.4	713.5	714.7
125°	739.1	740.4	742.3	746.1	749.9	753.7	757.5	758.9	760.3	761.6	763.0
127.5°	786.5	787.9	789.4	792.4	795.4	798.4	801.4	803.4	805.4	807.4	809.4
130°	832.1	833.7	834.8	837.0	839.1	841.3	843.5	845.7	847.9	850.1	852.3
132.5°	874.5	875.8	876.9	879.1	881.2	883.4	885.6	887.4	889.2	891.0	892.8
135°	914.5	916.1	917.0	918.8	920.6	922.4	924.2	926.2	928.2	930.2	932.2
137.5°	950.8	952.0	953.0	955.0	956.9	958.9	960.9	962.9	964.9	966.9	968.9
140°	986.1	986.9	988.0	990.2	992.4	994.6	996.8	998.6	1000.4	1002.2	1004.0
142.5°	1017.6	1018.3	1019.6	1022.2	1024.8	1027.4	1030.0	1031.6	1033.2	1034.7	1036.3
145°	1045.3	1045.2	1046.9	1050.3	1053.6	1057.0	1060.4	1061.8	1063.2	1064.6	1066.0
147.5°	1073.3	1073.0	1074.7	1078.1	1081.4	1084.8	1088.2	1089.2	1090.2	1091.2	1092.2
150°	1098.8	1098.1	1099.7	1102.9	1106.0	1109.2	1112.4	1113.6	1114.8	1116.0	1117.2
152.5°	1122.2	1121.4	1122.9	1125.9	1128.8	1131.8	1134.8	1136.0	1137.2	1138.4	1139.6
155°	1144.7	1143.8	1145.0	1147.4	1149.8	1152.2	1154.6	1155.8	1157.0	1158.1	1159.3
157.5°	1164.3	1163.5	1164.4	1166.2	1168.0	1169.8	1171.6	1173.0	1174.4	1175.8	1177.2
160°	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8	1188.0	1189.2	1190.4	1191.6
162.5°	1196.4	1195.8	1196.3	1197.3	1198.3	1199.3	1200.3	1201.7	1203.1	1204.5	1205.9
165°	1209.0	1208.4	1208.7	1209.3	1209.8	1210.4	1211.0	1212.4	1213.8	1215.2	1216.6
167.5°	1218.8	1218.2	1218.5	1219.1	1219.7	1220.3	1220.9	1222.3	1223.7	1225.1	1226.5
170°	1226.9	1226.3	1226.5	1226.9	1227.3	1227.7	1228.1	1229.5	1230.9	1232.2	1233.6
172.5°	1232.3	1231.7	1231.9	1232.3	1232.7	1233.1	1233.5	1234.9	1236.3	1237.6	1239.0
175°	1235.9	1235.2	1235.4	1235.8	1236.2	1236.6	1237.0	1238.4	1239.8	1241.2	1242.6
177.5°	1237.7	1237.0	1237.1	1237.3	1237.5	1237.7	1237.9	1239.3	1240.7	1242.1	1243.5
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1015.5	1014.1	1009.6	1011.1	1008.9	1008.9	1007.4	1007.4	1007.4	1011.1	1008.9
5°	960.2	955.1	949.9	947.7	945.5	943.3	943.3	942.5	949.2	947.7	953.6
7.5°	891.6	890.2	879.8	879.8	876.2	874.7	878.4	879.1	879.8	881.3	885.0
10°	830.4	826.7	812.0	813.5	811.3	808.3	810.5	809.0	814.2	815.7	814.2
12.5°	758.2	751.5	735.3	727.2	718.3	711.7	719.8	713.9	734.6	740.5	756.7
15°	662.3	649.7	638.7	638.7	630.6	624.7	628.4	635.0	639.4	646.1	649.0
17.5°	598.1	593.0	584.1	578.9	576.7	574.5	574.5	577.5	587.1	586.3	592.2
20°	543.5	540.6	536.2	529.5	527.3	525.8	525.8	525.8	532.5	538.4	542.1
22.5°	505.9	503.7	500.8	491.9	487.5	486.0	489.7	491.9	497.1	501.5	505.2
25°	468.3	463.2	458.0	455.0	452.8	452.8	454.3	455.0	457.3	459.5	463.9
27.5°	437.3	433.7	426.3	418.2	418.2	416.0	417.4	418.9	424.1	431.4	435.1
30°	402.7	401.9	399.0	396.0	393.1	391.6	394.6	396.8	397.5	401.2	401.2
32.5°	377.6	372.4	367.3	364.3	362.9	362.1	362.9	365.8	365.8	370.2	375.4
35°	352.5	349.6	344.4	339.3	337.8	334.1	337.0	340.0	345.2	347.4	349.6
37.5°	325.2	321.6	319.3	317.9	314.9	315.7	313.4	317.9	322.3	321.6	323.0
40°	304.6	298.0	291.3	290.6	289.8	289.1	289.1	289.8	292.8	295.7	300.2
42.5°	278.0	275.8	269.9	264.0	262.6	261.1	259.6	262.6	268.5	273.6	275.8
45°	250.8	247.8	246.3	241.9	239.0	238.2	236.7	240.4	245.6	247.8	249.3
47.5°	225.7	224.9	220.5	221.3	219.0	219.8	219.0	221.3	221.3	223.5	224.9
50°	208.7	206.5	204.3	202.8	200.6	200.6	199.9	200.6	203.6	206.5	205.8
52.5°	191.8	188.1	187.3	186.6	185.1	186.6	184.4	185.1	188.1	189.5	188.8
55°	171.8	171.1	169.6	168.2	167.4	166.7	166.7	166.7	169.6	171.8	172.6
57.5°	156.4	152.7	149.7	149.7	146.8	146.0	147.5	148.2	150.5	151.9	153.4
60°	135.0	133.5	129.1	126.9	122.4	121.7	121.7	124.6	128.3	133.5	135.0
62.5°	112.1	109.9	109.2	109.2	109.2	109.2	109.2	109.2	109.2	109.9	109.9
65°	99.6	100.3	99.6	98.8	99.6	99.6	98.8	98.8	98.8	99.6	100.3
67.5°	89.2	88.5	89.2	88.5	87.8	87.8	87.0	87.8	88.5	89.2	89.2
70°	77.4	77.4	76.7	77.4	76.7	76.0	75.2	75.2	76.7	77.4	77.4
72.5°	66.4	66.4	65.6	65.6	64.2	64.2	64.9	64.2	64.2	66.4	66.4
75°	55.3	54.6	53.8	53.8	53.1	53.1	53.1	52.4	53.8	53.8	54.6
77.5°	43.5	43.5	43.5	42.8	42.8	42.0	42.0	42.8	42.8	42.8	43.5
80°	33.2	33.2	33.2	32.5	31.7	31.7	31.7	31.7	31.7	32.5	31.7
82.5°	22.9	22.9	22.9	22.9	22.9	22.1	22.1	22.1	22.9	22.9	22.1
85°	14.0	13.3	14.0	14.0	13.3	14.0	13.3	13.3	12.5	12.5	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	22.4	22.6	23.0	23.4	23.8	24.2	23.8	23.4	23.0	22.6	22.4
92.5°	23.3	23.4	23.6	23.8	24.0	24.2	24.0	23.8	23.6	23.4	23.3
95°	39.4	39.3	39.1	38.9	38.7	38.5	38.7	38.9	39.1	39.3	39.4
97.5°	48.4	48.5	48.7	48.9	49.1	49.3	49.1	48.9	48.7	48.5	48.4
100°	58.3	58.5	58.9	59.3	59.7	60.1	59.7	59.3	58.9	58.5	58.3
102.5°	62.7	63.0	63.6	64.2	64.8	65.4	64.8	64.2	63.6	63.0	62.7
105°	64.5	64.9	65.7	66.5	67.3	68.1	67.3	66.5	65.7	64.9	64.5
107.5°	66.3	66.7	67.5	68.3	69.1	69.9	69.1	68.3	67.5	66.7	66.3
110°	67.2	67.6	68.4	69.2	70.0	70.8	70.0	69.2	68.4	67.6	67.2

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.0	69.3	69.9	70.5	71.1	71.7	71.1	70.5	69.9	69.3	69.0
115°	138.0	130.8	116.5	102.2	87.8	73.5	87.8	102.2	116.5	130.8	138.0
117.5°	473.3	447.2	395.0	342.8	290.6	238.4	290.6	342.8	395.0	447.2	473.3
120°	667.8	654.4	627.5	600.6	573.7	546.8	573.7	600.6	627.5	654.4	667.8
122.5°	715.3	715.4	715.6	715.8	716.0	716.2	716.0	715.8	715.6	715.4	715.3
125°	763.7	764.0	764.6	765.2	765.8	766.4	765.8	765.2	764.6	764.0	763.7
127.5°	810.4	810.5	810.7	810.8	811.0	811.2	811.0	810.8	810.7	810.5	810.4
130°	853.4	853.3	853.1	852.9	852.7	852.5	852.7	852.9	853.1	853.3	853.4
132.5°	893.7	893.6	893.4	893.2	893.0	892.8	893.0	893.2	893.4	893.6	893.7
135°	933.2	933.0	932.6	932.2	931.8	931.4	931.8	932.2	932.6	933.0	933.2
137.5°	969.9	969.6	969.0	968.4	967.8	967.2	967.8	968.4	969.0	969.6	969.9
140°	1004.9	1004.4	1003.4	1002.4	1001.4	1000.4	1001.4	1002.4	1003.4	1004.4	1004.9
142.5°	1037.1	1036.6	1035.6	1034.7	1033.7	1032.7	1033.7	1034.7	1035.6	1036.6	1037.1
145°	1066.7	1066.2	1065.2	1064.2	1063.2	1062.2	1063.2	1064.2	1065.2	1066.2	1066.7
147.5°	1092.7	1092.3	1091.5	1090.7	1089.9	1089.1	1089.9	1090.7	1091.5	1092.3	1092.7
150°	1117.8	1117.3	1116.3	1115.3	1114.3	1113.3	1114.3	1115.3	1116.3	1117.3	1117.8
152.5°	1140.2	1139.5	1138.1	1136.8	1135.4	1134.0	1135.4	1136.8	1138.1	1139.5	1140.2
155°	1159.9	1159.1	1157.5	1156.0	1154.4	1152.8	1154.4	1156.0	1157.5	1159.1	1159.9
157.5°	1177.9	1177.1	1175.5	1173.9	1172.3	1170.7	1172.3	1173.9	1175.5	1177.1	1177.9
160°	1192.2	1191.5	1190.1	1188.7	1187.3	1185.9	1187.3	1188.7	1190.1	1191.5	1192.2
162.5°	1206.6	1205.7	1203.9	1202.1	1200.3	1198.5	1200.3	1202.1	1203.9	1205.7	1206.6
165°	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1212.4	1213.8	1215.2	1216.6	1217.3
167.5°	1227.2	1226.3	1224.5	1222.7	1220.9	1219.1	1220.9	1222.7	1224.5	1226.3	1227.2
170°	1234.3	1233.4	1231.6	1229.9	1228.1	1226.3	1228.1	1229.9	1231.6	1233.4	1234.3
172.5°	1239.7	1238.8	1237.0	1235.3	1233.5	1231.7	1233.5	1235.3	1237.0	1238.8	1239.7
175°	1243.3	1242.3	1240.3	1238.3	1236.3	1234.3	1236.3	1238.3	1240.3	1242.3	1243.3
177.5°	1244.2	1243.3	1241.5	1239.7	1237.9	1236.1	1237.9	1239.7	1241.5	1243.3	1244.2
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1011.1	1014.8	1013.3	1005.2	1013.3	1015.5	1020.0	1024.4	1027.3	1031.8	1035.5
5°	947.7	955.1	959.5	955.1	969.8	972.0	982.4	988.3	997.1	1004.5	1010.4
7.5°	888.0	893.9	902.7	904.2	913.0	923.4	938.1	952.9	966.9	974.2	980.9
10°	823.8	834.1	847.4	844.4	857.7	873.9	889.4	913.0	924.8	938.1	949.9
12.5°	759.6	766.3	784.0	789.9	809.0	821.6	843.0	857.7	887.2	902.7	913.0
15°	647.5	674.8	696.9	723.5	748.6	772.2	791.3	817.9	843.7	855.5	872.5
17.5°	596.6	609.2	622.5	635.7	668.2	710.2	744.1	772.9	795.0	810.5	830.4
20°	543.5	556.1	570.8	583.4	603.3	633.5	675.6	725.0	751.5	767.7	786.9
22.5°	505.9	517.7	527.3	538.4	553.9	576.0	607.7	668.9	704.3	724.2	741.2
25°	465.4	480.1	490.4	498.6	511.1	535.4	561.2	595.9	659.3	674.8	698.4
27.5°	437.3	441.8	453.6	466.1	478.6	491.9	518.5	548.0	590.7	624.7	653.4
30°	404.2	415.2	426.3	431.4	442.5	461.7	477.9	509.6	542.8	569.4	604.0
32.5°	379.1	385.7	393.1	405.6	416.0	429.2	445.5	472.0	500.0	517.0	543.5
35°	351.1	355.5	371.0	376.1	386.5	399.7	416.0	436.6	466.8	480.1	499.3
37.5°	324.5	334.8	339.3	351.1	360.6	373.9	385.7	409.3	429.2	444.7	462.4
40°	303.9	308.3	316.4	326.7	334.8	345.2	359.9	376.9	398.3	410.8	426.3
42.5°	278.8	282.5	292.8	298.7	312.0	321.6	330.4	351.1	370.2	379.8	395.3
45°	251.5	260.3	267.0	278.8	286.2	298.0	309.0	323.8	341.5	352.5	361.4
47.5°	227.9	236.7	243.4	254.4	266.2	271.4	283.2	298.7	314.9	323.8	336.3
50°	208.7	211.7	224.2	229.4	241.9	252.2	260.3	273.6	291.3	296.5	306.8
52.5°	190.3	192.5	200.6	207.2	218.3	227.2	237.5	250.0	264.8	272.9	281.0
55°	174.1	175.5	179.2	186.6	194.0	205.0	214.6	226.4	239.0	247.8	255.2
57.5°	155.6	158.6	161.5	165.9	173.3	183.6	194.0	205.0	215.4	221.3	230.8
60°	134.2	138.7	143.8	149.0	154.1	161.5	173.3	183.6	193.2	198.4	205.8
62.5°	111.4	120.2	124.6	130.5	135.0	141.6	150.5	162.3	168.9	175.5	181.4
65°	100.3	101.0	101.8	107.7	115.8	122.4	130.5	139.4	149.7	154.1	158.6
67.5°	89.2	90.0	91.5	92.2	95.1	102.5	111.4	121.0	129.1	132.0	136.4
70°	78.2	78.2	81.1	81.9	82.6	83.3	90.7	100.3	107.7	111.4	116.5
72.5°	66.4	67.1	68.6	69.3	70.8	72.3	74.5	79.7	88.5	92.2	98.1
75°	54.6	55.3	56.1	56.8	59.0	59.7	62.0	64.9	68.6	73.0	76.7
77.5°	43.5	43.5	44.3	45.7	47.2	47.9	50.2	51.6	53.1	55.3	58.3
80°	32.5	33.2	33.2	34.7	34.7	35.4	36.1	38.4	39.8	41.3	42.8
82.5°	22.1	23.6	23.6	23.6	24.3	25.1	25.8	25.8	27.3	28.0	30.2
85°	13.3	14.0	14.0	14.0	13.3	14.8	14.8	15.5	15.5	15.5	16.2
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.6	6.6
90°	21.9	20.9	19.9	18.9	17.9	16.3	14.7	13.2	11.6	10.8	9.7
92.5°	23.1	22.7	22.3	21.9	21.5	20.9	20.3	19.7	19.1	18.8	19.2
95°	38.9	37.9	37.0	36.0	35.0	33.6	32.2	30.8	29.4	28.7	32.0
97.5°	48.1	47.5	46.9	46.3	45.7	42.5	39.3	36.2	33.0	31.4	39.6
100°	57.5	55.9	54.3	52.7	51.1	47.7	44.3	41.0	37.6	35.9	49.5
102.5°	61.6	59.4	57.3	55.1	52.9	89.1	125.4	161.6	197.9	216.0	216.2
105°	63.4	61.2	59.1	56.9	54.7	109.1	163.5	217.8	272.2	299.4	296.4
107.5°	65.2	63.0	60.9	58.7	56.5	123.6	190.8	257.9	325.0	358.6	356.1
110°	77.2	97.1	117.0	137.0	156.9	214.5	272.0	329.6	387.1	415.9	413.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	111.9	197.8	283.7	369.5	455.4	458.8	462.2	465.5	468.9	470.6	468.8
115°	184.1	276.4	368.6	460.9	553.1	548.1	543.1	538.2	533.2	530.7	529.0
117.5°	487.5	516.0	544.5	573.0	601.5	598.1	594.7	591.3	587.9	586.2	584.2
120°	666.6	664.2	661.9	659.5	657.1	653.5	649.9	646.3	642.7	640.9	639.4
122.5°	714.7	713.5	712.4	711.2	710.0	706.0	702.0	698.0	694.0	692.0	690.4
125°	763.0	761.6	760.3	758.9	757.5	753.7	749.9	746.1	742.3	740.4	739.1
127.5°	809.4	807.4	805.4	803.4	801.4	798.4	795.4	792.4	789.4	787.9	786.5
130°	852.3	850.1	847.9	845.7	843.5	841.3	839.1	837.0	834.8	833.7	832.1
132.5°	892.8	891.0	889.2	887.4	885.6	883.4	881.2	879.1	876.9	875.8	874.5
135°	932.2	930.2	928.2	926.2	924.2	922.4	920.6	918.8	917.0	916.1	914.5
137.5°	968.9	966.9	964.9	962.9	960.9	958.9	956.9	955.0	953.0	952.0	950.8
140°	1004.0	1002.2	1000.4	998.6	996.8	994.6	992.4	990.2	988.0	986.9	986.1
142.5°	1036.3	1034.7	1033.2	1031.6	1030.0	1027.4	1024.8	1022.2	1019.6	1018.3	1017.6
145°	1066.0	1064.6	1063.2	1061.8	1060.4	1057.0	1053.6	1050.3	1046.9	1045.2	1045.3
147.5°	1092.2	1091.2	1090.2	1089.2	1088.2	1084.8	1081.4	1078.1	1074.7	1073.0	1073.3
150°	1117.2	1116.0	1114.8	1113.6	1112.4	1109.2	1106.0	1102.9	1099.7	1098.1	1098.8
152.5°	1139.6	1138.4	1137.2	1136.0	1134.8	1131.8	1128.8	1125.9	1122.9	1121.4	1122.2
155°	1159.3	1158.1	1157.0	1155.8	1154.6	1152.2	1149.8	1147.4	1145.0	1143.8	1144.7
157.5°	1177.2	1175.8	1174.4	1173.0	1171.6	1169.8	1168.0	1166.2	1164.4	1163.5	1164.3
160°	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1184.4	1183.3	1182.1	1181.5	1182.1
162.5°	1205.9	1204.5	1203.1	1201.7	1200.3	1199.3	1198.3	1197.3	1196.3	1195.8	1196.4
165°	1216.6	1215.2	1213.8	1212.4	1211.0	1210.4	1209.8	1209.3	1208.7	1208.4	1209.0
167.5°	1226.5	1225.1	1223.7	1222.3	1220.9	1220.3	1219.7	1219.1	1218.5	1218.2	1218.8
170°	1233.6	1232.2	1230.9	1229.5	1228.1	1227.7	1227.3	1226.9	1226.5	1226.3	1226.9
172.5°	1239.0	1237.6	1236.3	1234.9	1233.5	1233.1	1232.7	1232.3	1231.9	1231.7	1232.3
175°	1242.6	1241.2	1239.8	1238.4	1237.0	1236.6	1236.2	1235.8	1235.4	1235.2	1235.9
177.5°	1243.5	1242.1	1240.7	1239.3	1237.9	1237.7	1237.5	1237.3	1237.1	1237.0	1237.7
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1061.3	1061.3	1061.3	1061.3
2.5°	1042.1	1039.9	1053.2	1067.9
5°	1020.7	1024.4	1041.4	1062.0
7.5°	998.6	1006.7	1026.6	1053.9
10°	967.6	982.4	1012.6	1040.6
12.5°	937.4	957.3	986.0	1019.2
15°	903.4	925.6	961.0	1000.8
17.5°	865.8	890.9	932.2	975.7
20°	826.0	859.2	902.7	949.9
22.5°	781.8	821.6	866.6	918.9
25°	739.0	782.5	827.5	888.0
27.5°	696.9	739.7	789.9	851.1
30°	654.9	694.0	747.8	813.5
32.5°	609.9	650.5	707.3	774.4
35°	568.6	609.2	662.3	728.7
37.5°	524.4	567.9	618.8	687.4
40°	472.7	523.6	573.0	638.7
42.5°	430.0	483.8	531.7	593.7
45°	396.0	446.9	486.8	547.2
47.5°	364.3	405.6	446.2	502.2
50°	334.1	365.8	407.8	458.0
52.5°	303.1	330.4	366.5	413.7
55°	275.1	300.9	333.4	369.5
57.5°	249.3	267.7	300.2	332.6
60°	220.5	239.7	264.8	292.1
62.5°	196.2	210.9	234.5	257.4
65°	170.4	184.4	202.1	223.5
67.5°	146.8	159.3	173.3	190.3
70°	125.4	135.0	145.3	160.0
72.5°	102.5	112.8	122.4	134.2
75°	84.1	88.5	96.6	104.7
77.5°	64.9	70.8	75.2	81.9
80°	46.5	51.6	53.1	58.3
82.5°	31.0	33.9	36.9	38.4
85°	17.7	19.2	22.1	22.9
87.5°	6.6	7.4	8.9	10.3
90°	7.5	5.3	3.1	0.9
92.5°	20.0	20.8	21.6	22.4
95°	38.6	45.1	51.7	58.3
97.5°	55.9	72.2	88.6	104.9
100°	76.8	104.1	131.4	158.7
102.5°	216.6	217.0	217.4	217.8
105°	290.4	284.5	278.5	272.5
107.5°	351.1	346.2	341.2	336.2
110°	409.6	405.5	401.3	397.1



TEST NUMBER: P999829

CATALOG NUMBER: SA2XXRDIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	465.2	461.7	458.1	454.5
115°	525.6	522.2	518.8	515.4
117.5°	580.2	576.3	572.3	568.3
120°	636.4	633.5	630.5	627.5
122.5°	687.2	684.1	680.9	677.7
125°	736.5	734.0	731.4	728.8
127.5°	783.7	781.0	778.2	775.4
130°	828.9	825.7	822.5	819.3
132.5°	871.9	869.3	866.7	864.1
135°	911.3	908.2	905.0	901.8
137.5°	948.4	946.0	943.6	941.2
140°	984.5	983.0	981.4	979.8
142.5°	1016.2	1014.8	1013.4	1012.0
145°	1045.5	1045.7	1045.9	1046.1
147.5°	1073.9	1074.5	1075.1	1075.7
150°	1100.2	1101.6	1103.0	1104.4
152.5°	1123.8	1125.4	1127.0	1128.6
155°	1146.5	1148.3	1150.1	1151.9
157.5°	1165.9	1167.5	1169.1	1170.7
160°	1183.3	1184.4	1185.6	1186.8
162.5°	1197.6	1198.8	1200.0	1201.2
165°	1210.2	1211.3	1212.5	1213.7
167.5°	1220.0	1221.2	1222.4	1223.6
170°	1228.1	1229.3	1230.5	1231.7
172.5°	1233.5	1234.6	1235.8	1237.0
175°	1237.3	1238.7	1240.1	1241.5
177.5°	1239.1	1240.5	1241.9	1243.3
180°	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)