

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998083

Luminaire Tested: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998083
REPORT IS A COMBINATION OF REPORTS P983820 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5430.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	101	101	101	101	90	90	90	90		68	68	68		49	49	49		32	32	32
1	92	88	84	81	82	78	75	73		60	58	56		43	42	41		28	28	27
2	84	77	71	66	74	69	64	60		53	50	47		38	36	35		25	24	23
3	77	68	61	55	68	61	55	50		47	43	40		34	32	30		22	21	20
4	70	60	53	47	62	54	47	43		42	37	34		30	28	25		20	19	17
5	64	53	46	40	57	48	41	36		37	33	29		27	24	22		18	16	15
6	59	48	40	35	52	43	36	32		33	29	25		25	22	19		17	15	13
7	55	43	36	30	48	39	32	28		30	26	22		22	19	17		15	13	12
8	51	39	32	27	45	35	29	24		28	23	20		21	17	15		14	12	11
9	47	35	28	24	42	32	26	22		25	21	18		19	16	14		13	11	10
10	44	32	26	21	39	29	23	19		23	19	16		17	14	12		12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9026	9026	9026	9026
5°	9047	9623	9082	7656
10°	8942	10506	8998	6312
15°	8725	11080	8846	5317
20°	8589	10405	8589	4622
25°	8316	8938	8353	4132
30°	7865	7027	8014	3744
35°	7466	4859	7591	3424
40°	7007	3669	7088	3171
45°	6443	3015	6548	2896
50°	5952	2646	5964	2652
55°	5396	2254	5430	2386
60°	4801	1883	4867	2082
65°	4269	1532	4348	1779
70°	3737	1201	3833	1435
75°	3138	873	3261	1039
80°	2451	553	2627	618
85°	1610	277	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9330 cd/sqm

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	1.0
10°-20°	158.1	2.9
20°-30°	229.4	4.2
30°-40°	241.8	4.5
40°-50°	214.0	3.9
50°-60°	170.9	3.1
60°-70°	116.1	2.1
70°-80°	59.4	1.1
80°-90°	17.9	0.3
90°-100°	233.3	4.3
100°-110°	821.7	15.1
110°-120°	863.0	15.9
120°-130°	709.9	13.1
130°-140°	570.3	10.5
140°-150°	430.8	7.9
150°-160°	302.9	5.6
160°-170°	178.3	3.3
170°-180°	58.0	1.1
0°-30°	441.8	8.1
0°-40°	683.6	12.6
0°-60°	1068.5	19.7
0°-90°	1261.8	23.2
90°-120°	1918.0	35.3
90°-150°	3629.0	66.8
90°-180°	4168.0	76.8
0°-180°	5430.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	570	570	570	570	570	
5°	571	637	573	507	571	54
15°	536	783	543	376	536	151
25°	482	652	484	302	482	220
35°	393	355	400	250	393	246
45°	295	214	300	206	295	229
55°	202	150	204	159	202	181
65°	120	92	122	107	120	119
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	38	1	38	1	3
95°	40	131	40	131	40	42
105°	140	1297	140	1297	140	149
115°	248	1707	248	1707	248	245
125°	345	1385	345	1385	345	307
135°	405	1148	405	1148	405	313
145°	463	916	463	916	463	290
155°	526	770	526	770	526	242
165°	573	676	573	676	573	162
175°	597	609	597	609	597	57
180°	598	598	598	598	598	

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	573.3	574.6	576.8	577.2	581.6	585.1	589.0	589.0	590.3	589.9	586.4
5°	570.6	574.6	580.3	585.1	593.0	596.5	601.7	605.7	609.2	611.8	611.4
7.5°	566.2	573.3	581.6	590.8	601.3	607.4	614.9	621.9	626.7	631.1	634.2
10°	558.8	570.6	582.0	594.3	607.9	616.2	625.0	634.2	641.6	649.9	657.8
12.5°	548.7	565.8	579.8	596.0	612.7	621.9	635.9	642.9	657.4	678.4	684.1
15°	536.0	559.2	572.4	593.0	614.9	622.3	641.6	653.0	682.8	696.0	711.7
17.5°	524.2	550.0	567.6	591.2	612.7	627.2	646.0	669.2	694.2	713.1	730.6
20°	514.5	539.5	560.5	586.8	614.0	632.4	652.1	680.2	707.4	726.6	740.2
22.5°	492.6	524.6	549.1	578.5	611.4	636.8	655.6	686.3	715.7	727.5	739.4
25°	481.7	509.3	537.8	571.1	609.6	639.9	656.1	690.3	716.1	720.5	723.1
27.5°	461.5	492.6	525.9	564.0	609.2	634.6	655.2	686.3	706.9	703.9	696.0
30°	436.5	474.6	511.5	552.7	603.1	630.7	649.9	678.4	689.0	673.2	659.2
32.5°	418.1	454.0	494.8	542.6	596.0	622.3	641.2	663.5	665.7	637.2	613.6
35°	393.1	433.0	479.0	529.4	584.2	607.9	625.4	639.0	628.5	588.6	560.5
37.5°	370.8	410.2	459.3	510.6	568.0	591.2	605.2	607.4	581.6	546.5	505.3
40°	346.2	387.0	438.3	492.2	550.0	570.2	578.9	572.4	535.1	494.4	446.6
42.5°	321.7	362.0	417.2	472.5	527.2	544.3	547.8	529.9	484.3	436.5	381.3
45°	295.0	337.0	392.2	447.9	500.9	510.6	511.0	485.2	431.3	381.3	330.0
47.5°	273.0	312.0	366.8	422.5	467.2	473.8	471.1	441.3	382.6	326.5	281.8
50°	248.9	286.2	340.5	395.3	433.4	435.2	428.6	386.1	328.7	277.4	241.9
52.5°	223.1	260.8	310.7	363.3	397.5	394.9	382.2	336.6	282.7	240.2	213.0
55°	202.5	235.8	282.7	334.0	358.1	350.6	336.6	290.1	247.6	211.7	188.0
57.5°	179.7	209.1	255.1	299.8	313.8	306.8	292.8	249.4	209.9	182.8	167.0
60°	158.2	184.9	225.3	262.5	273.5	266.0	249.8	210.8	182.3	159.5	147.7
62.5°	138.5	161.7	195.5	229.7	234.0	226.6	212.6	181.0	156.5	138.5	129.7
65°	120.1	142.0	169.2	195.0	199.0	191.1	176.6	153.8	133.2	121.8	113.5
67.5°	102.1	119.6	143.8	162.6	164.8	157.3	145.5	127.1	114.4	102.1	96.0
70°	86.3	99.5	118.3	133.7	134.5	127.5	121.4	104.7	95.1	86.3	81.5
72.5°	71.0	80.2	94.7	106.1	106.5	102.1	96.4	85.9	77.6	71.4	66.6
75°	56.1	64.0	72.8	82.8	82.4	78.9	74.5	67.9	60.9	57.0	54.8
77.5°	43.0	47.8	54.8	61.4	61.4	59.6	57.0	52.2	47.8	43.8	41.6
80°	30.7	33.7	39.4	41.6	42.5	42.1	39.9	36.4	34.6	31.6	30.7
82.5°	19.7	21.9	24.5	26.7	28.0	27.2	26.7	25.0	22.4	21.5	20.6
85°	11.4	12.3	13.6	14.9	15.3	14.9	15.8	14.5	13.1	13.1	12.7
87.5°	4.8	5.3	6.1	6.1	6.6	6.6	6.1	6.6	6.6	6.1	5.7
90°	1.2	4.6	9.2	11.5	13.8	15.6	17.3	23.0	31.1	38.0	39.1
92.5°	17.3	24.2	33.4	39.1	48.3	54.6	61.0	92.1	135.8	175.0	177.3
95°	40.3	44.9	56.4	66.8	85.2	99.0	112.8	165.7	265.9	399.4	451.2
97.5°	59.9	66.8	79.4	94.4	115.1	130.6	146.2	214.1	353.4	568.6	735.5
100°	88.6	92.1	102.4	120.9	143.9	160.0	176.1	237.1	377.5	626.2	909.3
102.5°	115.1	117.4	127.8	146.2	170.3	186.4	202.6	257.8	378.7	604.3	915.1
105°	140.4	145.0	153.1	170.3	195.7	211.8	227.9	282.0	384.4	574.4	852.9
107.5°	168.0	171.5	179.6	195.7	221.0	237.1	253.2	306.2	397.1	558.2	795.3
110°	195.7	200.3	207.2	222.1	246.3	263.0	279.7	330.3	413.2	553.6	756.2

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.0	225.6	233.7	247.5	270.5	287.8	305.0	353.4	430.5	554.8	730.9
115°	247.5	253.2	260.1	273.9	297.0	312.5	328.0	377.5	447.7	559.4	713.6
117.5°	275.1	279.7	286.6	299.3	321.1	337.2	353.4	399.4	466.2	566.3	704.4
120°	300.4	305.0	311.9	322.3	345.3	361.4	377.5	422.4	484.6	573.2	696.4
122.5°	324.6	328.0	334.9	346.5	369.5	386.2	402.9	444.3	500.7	581.3	691.8
125°	345.3	348.8	355.7	369.5	392.5	408.6	424.7	466.2	518.0	589.3	686.0
127.5°	362.6	367.2	376.4	391.3	413.2	429.9	446.6	486.9	534.1	597.4	682.6
130°	377.5	382.1	393.6	409.8	432.8	448.9	465.0	505.3	549.0	606.6	680.2
132.5°	391.3	397.1	409.8	427.0	451.2	467.3	483.4	521.4	564.0	615.8	679.1
135°	405.2	409.8	423.6	440.8	467.3	483.4	499.5	536.4	576.7	622.7	677.9
137.5°	417.8	423.6	437.4	455.8	482.3	497.2	512.2	549.0	587.0	629.6	677.9
140°	432.8	437.4	451.2	469.6	494.9	509.9	524.9	559.4	595.1	634.2	676.8
142.5°	447.7	451.2	463.9	482.3	506.4	520.2	534.1	567.4	602.0	637.7	676.8
145°	462.7	467.3	478.8	496.1	519.1	531.8	544.4	575.5	607.7	640.0	674.5
147.5°	478.8	482.3	493.8	509.9	529.5	541.0	552.5	582.4	611.2	641.1	671.0
150°	494.9	498.4	507.6	522.6	539.8	550.2	560.5	587.0	613.5	640.0	667.6
152.5°	511.0	512.2	521.4	534.1	550.2	559.4	568.6	591.6	614.6	637.7	661.8
155°	526.0	527.2	534.1	546.7	559.4	568.0	576.7	596.2	615.8	635.4	654.9
157.5°	538.7	539.8	545.6	557.1	567.4	574.9	582.4	599.7	615.8	630.8	648.0
160°	551.3	552.5	557.1	566.3	575.5	581.8	588.2	602.0	615.8	627.3	641.1
162.5°	564.0	562.8	567.4	574.4	582.4	587.0	591.6	603.1	614.6	623.8	635.4
165°	573.2	572.1	574.4	581.3	587.0	590.4	593.9	604.3	612.3	619.2	627.3
167.5°	581.3	580.1	582.4	587.0	591.6	593.9	596.2	604.3	611.2	614.6	620.4
170°	589.3	587.0	588.2	591.6	593.9	595.6	597.4	603.1	608.9	611.2	614.6
172.5°	593.9	592.8	591.6	595.1	596.2	597.4	598.5	602.0	605.4	606.6	607.7
175°	597.4	596.2	595.1	597.4	597.4	598.0	598.5	600.8	603.1	602.0	603.1
177.5°	599.7	597.4	596.2	598.5	598.5	598.5	598.5	599.7	602.0	599.7	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	592.5	593.0	593.9	598.2	600.4	600.9	599.1	603.1	604.4	603.1	602.2
5°	620.6	623.2	628.5	634.2	633.7	634.2	636.8	639.4	640.3	636.8	638.1
7.5°	645.1	650.4	656.1	664.8	664.8	669.2	671.0	673.2	678.4	675.8	674.9
10°	673.2	680.2	690.7	704.7	705.2	709.6	713.9	720.9	723.1	721.4	722.3
12.5°	708.2	721.8	722.7	738.0	745.1	745.9	752.9	751.6	756.0	756.0	763.5
15°	723.6	744.6	756.4	771.3	775.7	770.5	776.2	782.3	782.7	782.7	782.3
17.5°	751.2	759.5	771.3	779.2	781.0	781.0	781.4	784.1	782.3	778.8	781.4
20°	756.9	760.4	764.8	763.9	764.8	760.4	756.0	751.6	752.1	749.9	756.4
22.5°	746.4	745.5	735.4	728.8	728.8	720.1	711.7	707.8	703.9	705.2	707.4
25°	720.1	706.5	694.2	684.6	682.4	668.4	657.0	653.5	646.9	652.1	653.0
27.5°	678.0	662.7	642.9	634.6	623.2	617.5	609.6	599.1	585.5	593.4	592.1
30°	632.9	610.1	593.9	573.7	555.7	554.4	539.5	522.0	515.0	515.0	518.9
32.5°	582.5	552.2	528.5	500.1	482.5	475.1	457.1	439.6	443.5	430.4	435.2
35°	523.7	483.8	454.0	426.4	413.3	404.5	381.3	371.6	361.1	355.0	366.4
37.5°	467.6	421.6	383.5	353.2	348.4	332.6	316.9	310.7	304.6	307.2	306.8
40°	399.3	358.5	324.3	300.7	292.3	284.9	274.4	266.9	263.0	265.2	265.6
42.5°	337.5	303.3	277.9	261.2	254.2	248.9	243.7	237.5	236.2	236.2	238.0
45°	289.7	261.6	244.6	231.0	227.0	223.1	219.1	216.5	215.6	213.9	215.2
47.5°	251.6	229.2	218.7	208.6	204.2	203.4	199.8	198.5	196.8	196.3	196.8
50°	219.6	205.5	195.9	190.2	187.1	185.8	184.1	181.4	180.6	182.8	181.9
52.5°	197.2	184.1	178.8	173.1	171.4	169.6	167.0	167.4	167.0	166.1	166.1
55°	174.9	166.5	161.3	156.9	156.5	154.7	152.5	151.6	151.2	150.3	151.6
57.5°	156.9	150.3	145.5	141.6	139.8	139.8	137.6	135.9	135.9	135.4	135.9
60°	138.9	132.4	129.3	125.3	124.0	123.6	122.3	121.4	120.1	120.1	120.1
62.5°	122.3	117.0	113.5	110.0	110.4	108.3	106.5	105.6	105.6	106.1	106.1
65°	106.5	103.0	98.6	95.5	94.7	94.2	93.4	92.9	91.6	92.5	92.5
67.5°	92.0	87.2	84.6	83.3	82.0	81.5	80.6	79.8	79.3	78.9	79.8
70°	77.6	73.6	71.4	70.6	69.2	68.8	68.4	67.1	67.5	67.9	68.4
72.5°	64.4	60.9	60.5	57.9	57.9	57.9	56.1	57.0	56.5	55.7	56.5
75°	50.8	49.1	48.2	46.9	47.3	46.9	46.5	45.1	45.1	45.6	46.0
77.5°	40.3	38.6	38.1	36.8	35.9	36.8	35.9	35.5	35.5	35.9	35.9
80°	29.8	28.9	27.6	27.6	27.6	27.2	27.2	27.2	26.7	26.3	26.7
82.5°	19.7	19.7	19.3	18.8	19.3	18.4	18.8	18.8	18.8	18.8	18.8
85°	12.7	12.3	12.3	11.8	11.8	11.8	12.3	11.4	11.4	11.8	11.8
87.5°	5.7	5.7	5.7	6.1	5.7	5.7	5.7	6.1	5.7	5.7	5.7
90°	38.0	36.8	34.5	36.8	37.4	38.0	38.0	38.0	38.0	38.0	38.0
92.5°	148.5	116.3	99.0	86.3	81.7	77.1	76.0	71.4	72.5	70.2	72.5
95°	394.8	301.6	231.4	183.0	170.4	157.7	142.7	133.5	130.1	131.2	130.1
97.5°	741.3	616.9	492.6	376.4	341.8	307.3	262.4	239.4	226.7	219.8	226.7
100°	1075.0	1050.9	908.1	750.5	680.8	611.2	515.7	466.2	432.8	412.1	432.8
102.5°	1199.4	1335.2	1330.6	1225.8	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3
105°	1159.1	1398.5	1528.5	1543.5	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3
107.5°	1073.9	1330.6	1523.9	1636.7	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3
110°	994.5	1237.3	1443.4	1590.7	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	939.2	1152.2	1347.8	1507.8	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3
115°	895.5	1085.4	1262.7	1413.4	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6
117.5°	865.6	1030.2	1189.0	1329.4	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7
120°	842.5	991.0	1133.7	1255.8	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5
122.5°	823.0	959.9	1087.7	1201.7	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7
125°	804.6	930.0	1048.6	1149.9	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5
127.5°	787.3	900.1	1009.4	1106.1	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2
130°	770.0	871.3	970.3	1061.2	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8
132.5°	756.2	843.7	933.5	1015.2	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5
135°	743.6	818.4	894.3	970.3	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0
137.5°	734.3	797.7	863.3	925.4	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0
140°	726.3	778.1	833.3	886.3	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9
142.5°	718.2	762.0	806.9	850.6	870.8	890.9	925.4	951.9	966.9	966.9	966.9
145°	711.3	747.0	785.0	820.7	837.4	854.1	881.7	901.2	912.8	916.2	912.8
147.5°	704.4	735.5	766.6	795.3	808.0	820.7	844.8	861.0	869.0	871.3	869.0
150°	695.2	722.8	748.2	772.3	782.6	793.0	810.3	824.1	831.0	832.2	831.0
152.5°	687.2	710.2	733.2	752.8	761.4	770.0	782.7	794.2	798.8	798.8	798.8
155°	676.8	698.7	717.1	734.3	740.6	747.0	759.7	767.7	772.3	770.0	772.3
157.5°	667.6	684.9	701.0	715.9	721.1	726.3	735.5	742.4	744.7	744.7	744.7
160°	657.2	672.2	684.9	697.5	701.6	705.6	713.6	719.4	720.5	720.5	720.5
162.5°	648.0	659.5	669.9	680.2	683.1	686.0	694.1	697.5	698.7	697.5	698.7
165°	637.7	646.9	654.9	663.0	665.3	667.6	672.2	676.8	676.8	675.6	676.8
167.5°	627.3	634.2	641.1	646.9	649.2	651.5	653.8	656.1	656.1	654.9	656.1
170°	619.2	625.0	628.5	633.1	634.2	635.4	636.5	640.0	638.8	636.5	638.8
172.5°	611.2	614.6	616.9	620.4	621.0	621.5	622.7	623.8	622.7	621.5	622.7
175°	604.3	607.7	608.9	610.0	610.6	611.2	611.2	612.3	611.2	608.9	611.2
177.5°	599.7	602.0	602.0	603.1	603.1	603.1	603.1	603.1	602.0	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	604.4	601.3	598.7	599.1	601.3	599.5	595.2	589.5	587.3	584.6	587.3
5°	640.7	638.1	632.9	633.3	632.0	630.2	623.2	614.4	614.4	607.4	606.6
7.5°	676.7	672.7	669.2	668.4	663.5	660.0	653.9	641.6	636.8	628.5	623.7
10°	717.0	713.9	710.0	705.2	702.5	696.4	686.3	668.4	659.6	648.2	639.9
12.5°	757.8	757.3	748.6	738.9	738.5	728.8	721.8	697.7	685.9	670.5	650.8
15°	783.6	781.4	776.6	771.8	773.1	762.6	746.8	718.3	710.4	692.0	671.0
17.5°	783.2	783.2	781.9	781.0	779.7	776.6	767.8	749.0	736.3	713.1	693.3
20°	758.2	763.9	765.2	764.8	769.2	771.3	770.9	759.1	749.0	728.4	708.2
22.5°	708.2	721.4	727.1	730.6	739.8	744.6	756.0	751.6	749.0	733.7	716.6
25°	661.8	666.2	683.3	684.1	696.8	708.7	720.1	727.5	737.2	731.5	717.0
27.5°	601.7	611.8	624.1	633.3	635.9	660.0	678.9	692.9	714.8	716.6	711.7
30°	533.8	538.6	558.8	571.1	585.1	602.6	629.8	653.9	673.6	691.6	697.7
32.5°	451.0	470.7	482.5	497.4	509.7	540.8	574.1	605.2	628.0	658.3	671.4
35°	375.2	390.5	410.7	416.8	439.1	465.4	508.8	548.7	583.3	614.0	640.7
37.5°	312.5	324.8	346.2	355.9	369.0	402.8	439.1	488.7	530.3	568.0	601.3
40°	269.5	278.7	295.0	298.0	309.0	339.7	369.0	415.5	470.7	521.5	557.9
42.5°	240.2	244.6	255.5	259.5	266.5	287.1	313.4	357.2	408.5	461.1	512.3
45°	219.1	222.2	228.8	232.3	241.0	250.2	271.7	306.8	347.1	400.1	455.4
47.5°	200.3	204.2	206.9	209.1	213.9	224.0	238.0	263.8	302.4	351.1	404.5
50°	184.5	185.8	190.6	191.1	194.2	200.7	213.9	229.7	260.3	299.8	351.5
52.5°	168.7	170.0	173.1	176.2	177.5	182.8	191.5	204.7	227.5	258.6	304.6
55°	153.0	154.7	157.8	160.0	161.3	165.7	170.9	183.6	201.6	223.5	261.2
57.5°	137.2	141.1	142.0	143.3	145.5	150.3	155.1	162.6	176.6	196.8	224.4
60°	122.3	123.6	126.7	128.0	130.2	132.8	138.9	144.6	154.7	170.5	195.5
62.5°	106.9	110.0	111.3	112.6	114.4	117.5	121.4	127.5	136.3	149.0	168.7
65°	93.8	94.2	96.9	98.6	100.4	102.6	106.5	112.2	117.5	129.3	143.8
67.5°	81.1	82.0	82.8	84.6	86.8	89.0	92.5	95.5	102.1	110.0	121.4
70°	68.8	68.8	71.0	72.3	71.9	74.5	77.1	80.6	85.5	92.9	102.1
72.5°	57.9	57.4	59.2	59.6	60.5	62.2	64.0	67.5	70.1	75.8	82.8
75°	46.0	46.9	47.8	47.8	49.1	50.4	52.2	53.9	57.0	60.5	65.7
77.5°	36.4	36.4	37.3	37.7	39.0	38.6	40.3	42.1	44.3	47.3	51.3
80°	26.7	27.6	27.6	27.6	28.0	28.5	30.2	31.6	32.9	35.1	36.8
82.5°	18.8	18.8	19.7	19.7	19.7	20.6	20.6	21.0	21.9	23.2	24.5
85°	11.8	11.8	11.8	12.3	11.8	12.3	13.1	12.7	13.1	14.0	14.0
87.5°	5.7	5.7	5.7	5.7	5.7	6.1	5.7	6.1	6.6	6.6	6.6
90°	38.0	38.0	38.0	37.4	36.8	34.5	36.8	38.0	39.1	38.0	31.1
92.5°	71.4	76.0	77.1	81.7	86.3	99.0	116.3	148.5	177.3	175.0	135.8
95°	133.5	142.7	157.7	170.4	183.0	231.4	301.6	394.8	451.2	399.4	265.9
97.5°	239.4	262.4	307.3	341.8	376.4	492.6	616.9	741.3	735.5	568.6	353.4
100°	466.2	515.7	611.2	680.8	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5
102.5°	877.1	970.3	1076.2	1151.0	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7
105°	1362.8	1434.2	1505.5	1524.5	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4
107.5°	1671.3	1681.6	1682.8	1659.8	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1
110°	1756.4	1734.6	1685.1	1637.9	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1733.4	1693.1	1619.5	1563.6	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5
115°	1666.7	1613.7	1532.0	1472.7	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7
117.5°	1582.6	1526.2	1442.2	1385.8	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2
120°	1495.2	1441.1	1360.5	1308.2	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6
122.5°	1416.9	1363.9	1293.7	1247.7	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7
125°	1346.7	1302.9	1236.2	1193.1	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0
127.5°	1286.8	1245.4	1186.7	1146.4	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1
130°	1232.7	1193.6	1137.2	1099.2	1061.2	970.3	871.3	770.0	680.2	606.6	549.0
132.5°	1179.8	1140.7	1085.4	1050.3	1015.2	933.5	843.7	756.2	679.1	615.8	564.0
135°	1122.2	1084.3	1034.8	1002.6	970.3	894.3	818.4	743.6	677.9	622.7	576.7
137.5°	1063.5	1030.2	983.0	954.2	925.4	863.3	797.7	734.3	677.9	629.6	587.0
140°	1003.7	973.8	936.9	911.6	886.3	833.3	778.1	726.3	676.8	634.2	595.1
142.5°	951.9	925.4	890.9	870.8	850.6	806.9	762.0	718.2	676.8	637.7	602.0
145°	901.2	881.7	854.1	837.4	820.7	785.0	747.0	711.3	674.5	640.0	607.7
147.5°	861.0	844.8	820.7	808.0	795.3	766.6	735.5	704.4	671.0	641.1	611.2
150°	824.1	810.3	793.0	782.6	772.3	748.2	722.8	695.2	667.6	640.0	613.5
152.5°	794.2	782.7	770.0	761.4	752.8	733.2	710.2	687.2	661.8	637.7	614.6
155°	767.7	759.7	747.0	740.6	734.3	717.1	698.7	676.8	654.9	635.4	615.8
157.5°	742.4	735.5	726.3	721.1	715.9	701.0	684.9	667.6	648.0	630.8	615.8
160°	719.4	713.6	705.6	701.6	697.5	684.9	672.2	657.2	641.1	627.3	615.8
162.5°	697.5	694.1	686.0	683.1	680.2	669.9	659.5	648.0	635.4	623.8	614.6
165°	676.8	672.2	667.6	665.3	663.0	654.9	646.9	637.7	627.3	619.2	612.3
167.5°	656.1	653.8	651.5	649.2	646.9	641.1	634.2	627.3	620.4	614.6	611.2
170°	640.0	636.5	635.4	634.2	633.1	628.5	625.0	619.2	614.6	611.2	608.9
172.5°	623.8	622.7	621.5	621.0	620.4	616.9	614.6	611.2	607.7	606.6	605.4
175°	612.3	611.2	611.2	610.6	610.0	608.9	607.7	604.3	603.1	602.0	603.1
177.5°	603.1	603.1	603.1	603.1	603.1	602.0	602.0	599.7	598.5	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	585.1	582.9	581.6	582.5	579.8	573.3	573.3	575.4	572.8	570.2	566.2
5°	601.3	596.9	594.3	593.9	587.7	577.2	575.0	572.8	567.1	561.0	554.4
7.5°	617.1	609.2	604.8	601.7	593.0	579.4	573.7	568.9	559.7	550.5	542.1
10°	630.2	618.8	613.6	608.8	597.4	580.3	571.1	562.3	550.5	538.6	528.1
12.5°	640.7	627.6	621.0	614.0	600.0	577.6	566.2	552.2	540.4	524.6	514.1
15°	658.3	631.1	625.0	618.4	603.9	573.3	559.2	543.4	527.2	506.2	494.8
17.5°	672.3	635.9	635.5	621.5	602.6	571.5	550.0	529.4	511.9	490.9	472.9
20°	680.6	643.4	636.4	621.9	598.2	559.7	537.3	514.5	495.7	470.3	452.3
22.5°	687.6	653.9	635.5	618.0	589.0	555.7	522.9	501.4	475.5	447.9	430.8
25°	690.3	656.1	636.8	616.6	582.5	544.3	507.1	483.8	454.9	429.9	406.7
27.5°	690.7	655.6	632.0	610.9	573.3	529.4	491.3	466.8	434.8	405.8	382.6
30°	686.3	650.8	629.4	606.6	564.5	515.8	472.0	444.8	410.7	381.7	357.6
32.5°	673.2	641.2	623.7	598.7	553.1	497.0	453.6	423.4	387.4	358.9	335.7
35°	651.3	629.4	610.1	586.8	538.2	479.5	435.2	399.7	363.3	336.2	314.2
37.5°	624.1	612.3	594.3	571.5	521.1	463.7	414.6	375.2	338.8	312.5	291.0
40°	587.3	590.3	572.8	552.2	500.9	442.2	387.9	350.2	316.0	291.4	270.4
42.5°	547.4	560.1	550.0	530.3	478.6	418.5	368.1	326.5	293.2	267.8	250.2
45°	504.4	526.4	520.2	505.8	455.4	393.6	340.1	299.8	270.4	245.9	230.5
47.5°	457.5	488.7	488.7	478.1	429.5	368.6	316.0	274.8	245.9	228.3	213.4
50°	409.8	444.8	450.5	443.5	400.6	340.1	286.6	249.4	224.4	207.3	196.3
52.5°	359.8	400.6	411.1	407.6	369.9	312.9	262.5	226.1	203.4	188.5	178.8
55°	312.0	359.4	370.8	372.1	337.0	283.1	235.8	203.8	181.9	171.8	163.5
57.5°	266.9	312.5	325.2	327.4	303.7	255.9	210.8	182.8	163.0	154.7	148.1
60°	228.3	266.5	283.1	287.9	267.3	224.4	187.6	160.4	145.5	137.6	131.5
62.5°	196.8	227.5	245.0	246.3	237.1	196.8	163.5	140.7	128.0	121.0	117.9
65°	166.1	193.7	204.2	209.5	202.0	170.5	141.1	122.3	112.2	106.1	103.0
67.5°	141.6	159.1	167.9	174.9	167.4	143.8	120.1	104.7	97.3	91.2	89.4
70°	116.1	130.6	137.2	144.2	137.6	119.6	102.6	88.5	82.0	77.1	74.9
72.5°	92.9	104.3	110.4	114.8	110.9	96.0	82.0	72.3	67.5	64.0	62.7
75°	73.6	81.5	85.0	88.1	86.3	74.9	66.2	58.3	53.9	50.8	50.0
77.5°	56.1	61.8	65.7	66.6	64.4	57.0	49.5	44.7	41.2	39.4	38.6
80°	39.9	43.4	45.6	46.9	44.7	41.6	36.4	32.9	29.8	27.6	27.2
82.5°	26.7	28.5	30.2	29.8	28.9	26.3	23.2	21.5	20.2	18.4	18.4
85°	15.3	15.8	16.7	17.1	16.7	14.9	13.1	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	3.9
90°	23.0	17.3	15.6	13.8	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.1	61.0	54.6	48.3	39.1	33.4	24.2	17.3	24.2	33.4	39.1
95°	165.7	112.8	99.0	85.2	66.8	56.4	44.9	40.3	44.9	56.4	66.8
97.5°	214.1	146.2	130.6	115.1	94.4	79.4	66.8	59.9	66.8	79.4	94.4
100°	237.1	176.1	160.0	143.9	120.9	102.4	92.1	88.6	92.1	102.4	120.9
102.5°	257.8	202.6	186.4	170.3	146.2	127.8	117.4	115.1	117.4	127.8	146.2
105°	282.0	227.9	211.8	195.7	170.3	153.1	145.0	140.4	145.0	153.1	170.3
107.5°	306.2	253.2	237.1	221.0	195.7	179.6	171.5	168.0	171.5	179.6	195.7
110°	330.3	279.7	263.0	246.3	222.1	207.2	200.3	195.7	200.3	207.2	222.1

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	353.4	305.0	287.8	270.5	247.5	233.7	225.6	221.0	225.6	233.7	247.5
115°	377.5	328.0	312.5	297.0	273.9	260.1	253.2	247.5	253.2	260.1	273.9
117.5°	399.4	353.4	337.2	321.1	299.3	286.6	279.7	275.1	279.7	286.6	299.3
120°	422.4	377.5	361.4	345.3	322.3	311.9	305.0	300.4	305.0	311.9	322.3
122.5°	444.3	402.9	386.2	369.5	346.5	334.9	328.0	324.6	328.0	334.9	346.5
125°	466.2	424.7	408.6	392.5	369.5	355.7	348.8	345.3	348.8	355.7	369.5
127.5°	486.9	446.6	429.9	413.2	391.3	376.4	367.2	362.6	367.2	376.4	391.3
130°	505.3	465.0	448.9	432.8	409.8	393.6	382.1	377.5	382.1	393.6	409.8
132.5°	521.4	483.4	467.3	451.2	427.0	409.8	397.1	391.3	397.1	409.8	427.0
135°	536.4	499.5	483.4	467.3	440.8	423.6	409.8	405.2	409.8	423.6	440.8
137.5°	549.0	512.2	497.2	482.3	455.8	437.4	423.6	417.8	423.6	437.4	455.8
140°	559.4	524.9	509.9	494.9	469.6	451.2	437.4	432.8	437.4	451.2	469.6
142.5°	567.4	534.1	520.2	506.4	482.3	463.9	451.2	447.7	451.2	463.9	482.3
145°	575.5	544.4	531.8	519.1	496.1	478.8	467.3	462.7	467.3	478.8	496.1
147.5°	582.4	552.5	541.0	529.5	509.9	493.8	482.3	478.8	482.3	493.8	509.9
150°	587.0	560.5	550.2	539.8	522.6	507.6	498.4	494.9	498.4	507.6	522.6
152.5°	591.6	568.6	559.4	550.2	534.1	521.4	512.2	511.0	512.2	521.4	534.1
155°	596.2	576.7	568.0	559.4	546.7	534.1	527.2	526.0	527.2	534.1	546.7
157.5°	599.7	582.4	574.9	567.4	557.1	545.6	539.8	538.7	539.8	545.6	557.1
160°	602.0	588.2	581.8	575.5	566.3	557.1	552.5	551.3	552.5	557.1	566.3
162.5°	603.1	591.6	587.0	582.4	574.4	567.4	562.8	564.0	562.8	567.4	574.4
165°	604.3	593.9	590.4	587.0	581.3	574.4	572.1	573.2	572.1	574.4	581.3
167.5°	604.3	596.2	593.9	591.6	587.0	582.4	580.1	581.3	580.1	582.4	587.0
170°	603.1	597.4	595.6	593.9	591.6	588.2	587.0	589.3	587.0	588.2	591.6
172.5°	602.0	598.5	597.4	596.2	595.1	591.6	592.8	593.9	592.8	591.6	595.1
175°	600.8	598.5	598.0	597.4	597.4	595.1	596.2	597.4	596.2	595.1	597.4
177.5°	599.7	598.5	598.5	598.5	598.5	596.2	597.4	599.7	597.4	596.2	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	564.0	566.2	565.8	561.4	556.6	552.7	545.2	546.1	543.4	543.9	546.5
5°	550.0	550.0	548.3	542.1	534.2	529.9	521.5	519.3	514.1	513.6	513.2
7.5°	535.1	532.9	530.7	522.0	512.3	505.3	493.9	491.3	486.0	482.5	480.8
10°	517.6	514.5	510.1	500.1	488.2	479.5	467.6	464.1	454.0	449.7	447.0
12.5°	498.3	496.6	489.5	481.2	461.9	452.3	435.2	438.7	428.6	419.9	418.5
15°	479.0	472.5	468.5	454.9	431.7	427.3	413.7	406.7	397.5	390.5	390.5
17.5°	460.2	450.1	441.3	426.9	409.8	397.5	387.4	383.9	372.5	365.5	364.2
20°	435.2	423.8	421.6	401.0	389.2	375.6	366.0	357.2	348.9	345.8	343.6
22.5°	411.5	398.4	394.9	377.3	365.5	351.9	342.3	336.2	330.0	327.8	323.9
25°	386.1	378.2	373.0	354.1	341.0	328.3	321.7	317.3	311.6	311.2	308.5
27.5°	361.6	354.1	348.9	330.9	321.2	309.4	304.2	299.3	296.3	295.0	293.6
30°	340.5	332.2	326.1	312.9	301.1	291.4	287.1	284.0	282.2	280.1	279.6
32.5°	317.3	312.5	304.2	294.1	284.9	275.7	273.0	270.8	268.2	267.3	266.9
35°	297.6	291.0	285.7	274.4	270.4	262.5	259.5	257.7	254.2	253.3	252.4
37.5°	278.3	272.2	266.5	259.5	252.0	247.6	245.9	243.2	241.5	241.9	241.0
40°	259.0	254.2	249.8	242.4	238.0	235.8	232.3	229.7	228.8	229.2	228.8
42.5°	240.2	235.8	233.2	227.5	223.1	220.9	218.7	216.1	217.4	217.4	218.7
45°	223.1	219.1	217.4	213.0	210.4	206.9	204.7	204.2	206.0	205.5	205.5
47.5°	205.5	204.2	202.0	198.1	194.6	192.4	192.0	192.0	193.7	194.6	194.2
50°	192.0	189.3	186.7	183.6	181.0	180.1	178.8	179.7	181.4	181.4	182.3
52.5°	174.9	173.1	172.2	169.6	167.9	167.9	167.9	168.3	169.6	170.9	170.5
55°	160.0	158.7	157.8	156.5	154.3	154.7	154.3	155.1	156.5	157.8	158.7
57.5°	144.2	143.8	142.9	140.7	140.7	140.2	141.6	142.0	144.2	145.1	146.4
60°	130.2	128.9	128.9	127.1	127.1	127.1	128.4	129.7	131.5	131.9	132.8
62.5°	115.3	115.3	114.8	113.5	113.5	114.8	115.3	117.0	117.9	117.9	119.2
65°	101.2	100.8	100.4	100.8	101.2	101.2	102.6	103.4	104.3	104.7	105.2
67.5°	87.2	86.8	87.7	87.2	88.1	89.8	89.4	90.7	92.0	92.0	92.5
70°	74.1	74.9	74.5	75.4	74.9	75.8	77.1	77.6	77.6	78.0	79.3
72.5°	61.8	61.8	61.8	61.4	61.8	62.7	63.5	64.0	64.9	65.3	66.6
75°	50.0	50.0	49.1	50.0	50.0	50.8	51.7	51.7	51.7	52.6	53.9
77.5°	37.7	38.1	37.7	38.6	38.6	39.0	39.9	39.4	40.3	40.8	41.2
80°	27.6	27.2	27.2	27.2	27.6	27.6	28.5	28.9	28.9	30.2	29.4
82.5°	17.5	18.0	17.5	18.0	18.0	18.4	18.0	18.4	18.8	19.7	19.3
85°	10.1	9.6	9.6	10.1	9.6	9.6	10.1	9.6	10.1	9.6	10.1
87.5°	3.9	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	13.8	15.6	17.3	23.0	31.1	38.0	39.1	38.0	36.8	34.5	36.8
92.5°	48.3	54.6	61.0	92.1	135.8	175.0	177.3	148.5	116.3	99.0	86.3
95°	85.2	99.0	112.8	165.7	265.9	399.4	451.2	394.8	301.6	231.4	183.0
97.5°	115.1	130.6	146.2	214.1	353.4	568.6	735.5	741.3	616.9	492.6	376.4
100°	143.9	160.0	176.1	237.1	377.5	626.2	909.3	1075.0	1050.9	908.1	750.5
102.5°	170.3	186.4	202.6	257.8	378.7	604.3	915.1	1199.4	1335.2	1330.6	1225.8
105°	195.7	211.8	227.9	282.0	384.4	574.4	852.9	1159.1	1398.5	1528.5	1543.5
107.5°	221.0	237.1	253.2	306.2	397.1	558.2	795.3	1073.9	1330.6	1523.9	1636.7
110°	246.3	263.0	279.7	330.3	413.2	553.6	756.2	994.5	1237.3	1443.4	1590.7

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	270.5	287.8	305.0	353.4	430.5	554.8	730.9	939.2	1152.2	1347.8	1507.8
115°	297.0	312.5	328.0	377.5	447.7	559.4	713.6	895.5	1085.4	1262.7	1413.4
117.5°	321.1	337.2	353.4	399.4	466.2	566.3	704.4	865.6	1030.2	1189.0	1329.4
120°	345.3	361.4	377.5	422.4	484.6	573.2	696.4	842.5	991.0	1133.7	1255.8
122.5°	369.5	386.2	402.9	444.3	500.7	581.3	691.8	823.0	959.9	1087.7	1201.7
125°	392.5	408.6	424.7	466.2	518.0	589.3	686.0	804.6	930.0	1048.6	1149.9
127.5°	413.2	429.9	446.6	486.9	534.1	597.4	682.6	787.3	900.1	1009.4	1106.1
130°	432.8	448.9	465.0	505.3	549.0	606.6	680.2	770.0	871.3	970.3	1061.2
132.5°	451.2	467.3	483.4	521.4	564.0	615.8	679.1	756.2	843.7	933.5	1015.2
135°	467.3	483.4	499.5	536.4	576.7	622.7	677.9	743.6	818.4	894.3	970.3
137.5°	482.3	497.2	512.2	549.0	587.0	629.6	677.9	734.3	797.7	863.3	925.4
140°	494.9	509.9	524.9	559.4	595.1	634.2	676.8	726.3	778.1	833.3	886.3
142.5°	506.4	520.2	534.1	567.4	602.0	637.7	676.8	718.2	762.0	806.9	850.6
145°	519.1	531.8	544.4	575.5	607.7	640.0	674.5	711.3	747.0	785.0	820.7
147.5°	529.5	541.0	552.5	582.4	611.2	641.1	671.0	704.4	735.5	766.6	795.3
150°	539.8	550.2	560.5	587.0	613.5	640.0	667.6	695.2	722.8	748.2	772.3
152.5°	550.2	559.4	568.6	591.6	614.6	637.7	661.8	687.2	710.2	733.2	752.8
155°	559.4	568.0	576.7	596.2	615.8	635.4	654.9	676.8	698.7	717.1	734.3
157.5°	567.4	574.9	582.4	599.7	615.8	630.8	648.0	667.6	684.9	701.0	715.9
160°	575.5	581.8	588.2	602.0	615.8	627.3	641.1	657.2	672.2	684.9	697.5
162.5°	582.4	587.0	591.6	603.1	614.6	623.8	635.4	648.0	659.5	669.9	680.2
165°	587.0	590.4	593.9	604.3	612.3	619.2	627.3	637.7	646.9	654.9	663.0
167.5°	591.6	593.9	596.2	604.3	611.2	614.6	620.4	627.3	634.2	641.1	646.9
170°	593.9	595.6	597.4	603.1	608.9	611.2	614.6	619.2	625.0	628.5	633.1
172.5°	596.2	597.4	598.5	602.0	605.4	606.6	607.7	611.2	614.6	616.9	620.4
175°	597.4	598.0	598.5	600.8	603.1	602.0	603.1	604.3	607.7	608.9	610.0
177.5°	598.5	598.5	598.5	599.7	602.0	599.7	598.5	599.7	602.0	602.0	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	543.4	544.8	541.7	540.8	541.7	538.6	539.5	540.4	540.4	541.7	542.6
5°	511.9	510.1	507.1	506.2	505.3	506.6	505.8	507.1	507.5	510.6	511.0
7.5°	480.8	478.1	475.5	472.9	472.0	469.8	472.0	472.0	475.1	474.2	476.4
10°	444.0	443.5	440.0	438.7	437.0	433.4	438.3	437.0	439.1	443.1	444.0
12.5°	416.8	412.0	414.2	408.0	410.2	406.7	407.1	407.1	410.7	411.1	410.2
15°	390.9	387.0	381.3	378.7	377.3	375.6	381.3	381.7	379.1	385.2	383.0
17.5°	364.6	364.6	359.4	358.1	354.6	356.3	355.4	355.9	355.0	359.4	361.6
20°	341.8	339.7	337.9	338.3	334.0	333.1	332.2	333.1	336.2	339.2	340.1
22.5°	323.4	322.1	317.7	318.6	315.1	316.4	315.6	317.7	318.2	318.2	321.2
25°	305.9	304.2	304.6	302.8	301.5	301.5	300.2	301.5	303.3	304.2	304.6
27.5°	292.8	291.4	289.3	287.9	288.8	286.6	288.4	289.7	289.7	288.8	289.7
30°	277.0	277.9	277.9	273.5	275.2	274.4	275.7	276.5	276.5	277.0	276.1
32.5°	266.5	263.8	263.4	263.0	263.0	261.2	261.2	262.5	263.0	263.4	264.7
35°	252.4	252.4	250.2	251.6	249.8	250.2	249.8	250.2	251.1	249.8	251.1
37.5°	239.7	240.2	239.3	240.2	240.6	239.7	238.9	240.6	239.7	239.7	238.9
40°	228.8	228.3	228.8	228.8	228.8	229.2	228.3	228.3	228.3	227.5	226.6
42.5°	219.6	216.9	217.8	218.3	216.9	216.9	217.4	216.9	218.3	215.6	215.6
45°	206.4	205.5	206.0	206.0	206.9	205.5	206.4	206.9	205.5	205.1	204.2
47.5°	194.6	195.5	194.6	195.5	195.5	196.3	194.6	195.0	195.5	193.7	192.4
50°	182.8	182.8	184.1	183.6	184.1	183.2	183.2	182.8	183.2	182.3	181.0
52.5°	171.8	170.5	172.7	172.2	171.8	171.4	170.9	171.4	170.5	169.6	169.6
55°	158.2	158.2	159.5	160.0	160.0	159.1	158.2	158.7	158.2	157.8	157.3
57.5°	147.3	145.5	146.4	146.8	146.8	145.5	146.4	145.5	145.5	145.9	144.6
60°	133.2	133.2	132.4	133.7	133.7	132.8	132.8	133.2	132.4	131.9	131.5
62.5°	118.3	118.8	120.1	120.5	121.0	120.1	119.2	119.6	119.6	118.3	118.8
65°	105.6	106.5	108.3	107.8	106.9	107.4	106.5	106.9	105.6	106.1	104.7
67.5°	93.4	92.9	93.4	93.4	94.2	93.8	92.9	92.9	92.5	93.8	92.5
70°	80.2	80.2	80.2	80.2	80.6	81.1	80.2	79.3	79.8	78.9	78.4
72.5°	66.6	67.1	66.6	67.5	66.2	67.1	67.1	66.6	66.2	66.2	66.2
75°	53.9	54.8	53.5	53.9	53.5	54.3	53.9	53.9	53.0	52.6	53.0
77.5°	41.2	41.6	40.8	41.2	40.8	41.2	41.2	40.8	40.8	40.8	40.8
80°	29.4	29.8	29.4	28.9	28.5	29.4	28.5	28.9	29.4	28.9	29.8
82.5°	18.8	18.8	18.4	18.8	18.0	18.0	18.4	18.4	18.0	18.8	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.6	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	37.4	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.4
92.5°	81.7	77.1	76.0	71.4	72.5	70.2	72.5	71.4	76.0	77.1	81.7
95°	170.4	157.7	142.7	133.5	130.1	131.2	130.1	133.5	142.7	157.7	170.4
97.5°	341.8	307.3	262.4	239.4	226.7	219.8	226.7	239.4	262.4	307.3	341.8
100°	680.8	611.2	515.7	466.2	432.8	412.1	432.8	466.2	515.7	611.2	680.8
102.5°	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3	877.1	970.3	1076.2	1151.0
105°	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3	1362.8	1434.2	1505.5	1524.5
107.5°	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3	1671.3	1681.6	1682.8	1659.8
110°	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8	1756.4	1734.6	1685.1	1637.9

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3	1733.4	1693.1	1619.5	1563.6
115°	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6	1666.7	1613.7	1532.0	1472.7
117.5°	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7	1582.6	1526.2	1442.2	1385.8
120°	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5	1495.2	1441.1	1360.5	1308.2
122.5°	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7	1416.9	1363.9	1293.7	1247.7
125°	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5	1346.7	1302.9	1236.2	1193.1
127.5°	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2	1286.8	1245.4	1186.7	1146.4
130°	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8	1232.7	1193.6	1137.2	1099.2
132.5°	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5	1179.8	1140.7	1085.4	1050.3
135°	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0	1122.2	1084.3	1034.8	1002.6
137.5°	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0	1063.5	1030.2	983.0	954.2
140°	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9	1003.7	973.8	936.9	911.6
142.5°	870.8	890.9	925.4	951.9	966.9	966.9	966.9	951.9	925.4	890.9	870.8
145°	837.4	854.1	881.7	901.2	912.8	916.2	912.8	901.2	881.7	854.1	837.4
147.5°	808.0	820.7	844.8	861.0	869.0	871.3	869.0	861.0	844.8	820.7	808.0
150°	782.6	793.0	810.3	824.1	831.0	832.2	831.0	824.1	810.3	793.0	782.6
152.5°	761.4	770.0	782.7	794.2	798.8	798.8	798.8	794.2	782.7	770.0	761.4
155°	740.6	747.0	759.7	767.7	772.3	770.0	772.3	767.7	759.7	747.0	740.6
157.5°	721.1	726.3	735.5	742.4	744.7	744.7	744.7	742.4	735.5	726.3	721.1
160°	701.6	705.6	713.6	719.4	720.5	720.5	720.5	719.4	713.6	705.6	701.6
162.5°	683.1	686.0	694.1	697.5	698.7	697.5	698.7	697.5	694.1	686.0	683.1
165°	665.3	667.6	672.2	676.8	676.8	675.6	676.8	676.8	672.2	667.6	665.3
167.5°	649.2	651.5	653.8	656.1	656.1	654.9	656.1	656.1	653.8	651.5	649.2
170°	634.2	635.4	636.5	640.0	638.8	636.5	638.8	640.0	636.5	635.4	634.2
172.5°	621.0	621.5	622.7	623.8	622.7	621.5	622.7	623.8	622.7	621.5	621.0
175°	610.6	611.2	611.2	612.3	611.2	608.9	611.2	612.3	611.2	611.2	610.6
177.5°	603.1	603.1	603.1	603.1	602.0	599.7	602.0	603.1	603.1	603.1	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	541.3	544.8	543.4	538.6	544.3	544.3	548.3	548.3	553.1	554.8	557.5
5°	510.6	513.2	515.4	513.2	517.2	523.3	526.8	529.9	536.4	539.1	543.0
7.5°	477.7	482.5	484.7	484.7	491.3	498.3	505.3	509.7	518.9	522.4	526.4
10°	445.7	451.4	455.8	455.4	466.3	470.7	479.5	489.5	498.7	504.0	509.7
12.5°	412.0	415.0	421.2	429.9	432.6	440.5	450.5	463.2	479.9	484.7	493.0
15°	383.9	392.2	397.1	401.0	407.1	414.6	425.6	437.8	454.5	465.0	473.8
17.5°	360.3	371.2	374.3	373.4	381.3	392.7	405.4	414.6	429.5	442.2	450.5
20°	341.0	345.4	350.6	352.8	358.9	371.2	383.5	394.0	406.3	416.4	426.0
22.5°	321.7	325.2	329.6	333.5	338.3	345.4	357.2	370.3	382.2	391.8	402.8
25°	305.9	308.1	312.0	315.1	320.4	325.2	333.5	348.0	362.0	367.7	377.3
27.5°	290.6	292.3	295.0	298.5	301.1	305.9	313.4	325.2	339.7	345.4	358.5
30°	277.0	278.3	280.9	282.7	284.0	289.7	295.4	304.6	315.6	323.4	333.1
32.5°	264.3	265.6	268.2	268.7	270.4	273.5	278.7	287.1	296.7	303.3	311.6
35°	250.2	251.1	253.8	254.6	255.9	258.6	262.5	268.7	277.4	282.2	289.7
37.5°	239.3	238.9	240.6	241.9	243.7	245.0	246.3	252.4	259.0	263.4	269.1
40°	227.5	226.6	227.0	228.8	229.7	231.4	231.4	237.5	241.9	245.4	249.8
42.5°	215.6	215.2	214.3	215.2	216.1	216.5	216.9	221.3	225.7	228.8	233.6
45°	203.8	203.4	202.5	202.9	202.9	203.8	205.1	206.9	209.9	212.6	215.2
47.5°	192.8	192.0	190.6	190.2	191.1	191.1	191.1	192.8	195.9	196.8	199.4
50°	181.4	180.1	178.4	177.5	177.5	177.1	177.9	178.4	181.0	181.9	184.1
52.5°	169.2	168.3	166.5	164.8	165.2	164.3	164.8	165.2	166.1	167.4	168.7
55°	156.9	155.1	153.8	153.4	152.1	152.1	150.8	152.5	152.1	152.5	154.3
57.5°	145.1	143.3	141.1	140.2	138.9	138.5	137.6	137.2	137.6	138.9	140.2
60°	131.0	130.2	128.9	127.5	126.7	125.3	124.5	124.5	124.0	124.0	124.5
62.5°	117.5	117.0	115.3	114.8	113.9	113.1	111.8	110.9	110.9	111.8	112.2
65°	104.3	103.9	102.6	102.1	99.9	99.0	98.6	98.2	97.3	97.3	97.3
67.5°	92.0	90.7	90.7	88.5	86.8	85.9	85.0	84.6	84.6	84.6	85.0
70°	78.4	78.4	77.1	75.8	74.1	74.5	73.2	71.9	71.9	71.0	71.4
72.5°	65.3	64.9	63.5	63.1	61.8	60.5	59.6	60.5	59.2	58.7	59.2
75°	52.6	52.2	51.3	50.4	50.8	49.5	48.2	47.8	47.8	46.9	46.9
77.5°	40.3	41.2	39.4	39.0	38.1	37.3	36.8	36.4	36.4	36.4	37.3
80°	28.0	28.5	28.5	27.6	28.0	26.7	26.7	26.7	25.4	25.9	26.3
82.5°	18.0	18.0	17.5	18.0	17.5	17.5	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.6	9.2	10.1	9.6	9.6	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	36.8	34.5	36.8	38.0	39.1	38.0	31.1	23.0	17.3	15.6	13.8
92.5°	86.3	99.0	116.3	148.5	177.3	175.0	135.8	92.1	61.0	54.6	48.3
95°	183.0	231.4	301.6	394.8	451.2	399.4	265.9	165.7	112.8	99.0	85.2
97.5°	376.4	492.6	616.9	741.3	735.5	568.6	353.4	214.1	146.2	130.6	115.1
100°	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5	237.1	176.1	160.0	143.9
102.5°	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7	257.8	202.6	186.4	170.3
105°	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4	282.0	227.9	211.8	195.7
107.5°	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1	306.2	253.2	237.1	221.0
110°	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2	330.3	279.7	263.0	246.3

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5	353.4	305.0	287.8	270.5
115°	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7	377.5	328.0	312.5	297.0
117.5°	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2	399.4	353.4	337.2	321.1
120°	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6	422.4	377.5	361.4	345.3
122.5°	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7	444.3	402.9	386.2	369.5
125°	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0	466.2	424.7	408.6	392.5
127.5°	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1	486.9	446.6	429.9	413.2
130°	1061.2	970.3	871.3	770.0	680.2	606.6	549.0	505.3	465.0	448.9	432.8
132.5°	1015.2	933.5	843.7	756.2	679.1	615.8	564.0	521.4	483.4	467.3	451.2
135°	970.3	894.3	818.4	743.6	677.9	622.7	576.7	536.4	499.5	483.4	467.3
137.5°	925.4	863.3	797.7	734.3	677.9	629.6	587.0	549.0	512.2	497.2	482.3
140°	886.3	833.3	778.1	726.3	676.8	634.2	595.1	559.4	524.9	509.9	494.9
142.5°	850.6	806.9	762.0	718.2	676.8	637.7	602.0	567.4	534.1	520.2	506.4
145°	820.7	785.0	747.0	711.3	674.5	640.0	607.7	575.5	544.4	531.8	519.1
147.5°	795.3	766.6	735.5	704.4	671.0	641.1	611.2	582.4	552.5	541.0	529.5
150°	772.3	748.2	722.8	695.2	667.6	640.0	613.5	587.0	560.5	550.2	539.8
152.5°	752.8	733.2	710.2	687.2	661.8	637.7	614.6	591.6	568.6	559.4	550.2
155°	734.3	717.1	698.7	676.8	654.9	635.4	615.8	596.2	576.7	568.0	559.4
157.5°	715.9	701.0	684.9	667.6	648.0	630.8	615.8	599.7	582.4	574.9	567.4
160°	697.5	684.9	672.2	657.2	641.1	627.3	615.8	602.0	588.2	581.8	575.5
162.5°	680.2	669.9	659.5	648.0	635.4	623.8	614.6	603.1	591.6	587.0	582.4
165°	663.0	654.9	646.9	637.7	627.3	619.2	612.3	604.3	593.9	590.4	587.0
167.5°	646.9	641.1	634.2	627.3	620.4	614.6	611.2	604.3	596.2	593.9	591.6
170°	633.1	628.5	625.0	619.2	614.6	611.2	608.9	603.1	597.4	595.6	593.9
172.5°	620.4	616.9	614.6	611.2	607.7	606.6	605.4	602.0	598.5	597.4	596.2
175°	610.0	608.9	607.7	604.3	603.1	602.0	603.1	600.8	598.5	598.0	597.4
177.5°	603.1	602.0	602.0	599.7	598.5	599.7	602.0	599.7	598.5	598.5	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	570.2	570.2	570.2	570.2
2.5°	559.7	559.7	566.2	573.3
5°	547.4	550.5	561.0	570.6
7.5°	535.6	540.8	554.0	566.2
10°	521.1	528.1	544.3	558.8
12.5°	507.1	513.6	532.5	548.7
15°	487.4	495.7	515.8	536.0
17.5°	467.6	476.0	500.5	524.2
20°	444.4	455.4	483.0	514.5
22.5°	422.9	436.5	467.2	492.6
25°	399.3	420.3	448.8	481.7
27.5°	378.2	399.3	428.2	461.5
30°	354.6	376.0	405.8	436.5
32.5°	331.8	351.5	380.4	418.1
35°	308.1	326.9	355.0	393.1
37.5°	286.6	305.0	335.7	370.8
40°	265.6	284.9	311.2	346.2
42.5°	245.9	263.0	286.6	321.7
45°	227.9	240.2	262.1	295.0
47.5°	209.1	220.0	240.2	273.0
50°	191.5	200.7	218.3	248.9
52.5°	174.4	182.3	198.5	223.1
55°	159.1	166.5	178.4	202.5
57.5°	143.3	149.0	160.4	179.7
60°	128.0	133.2	142.4	158.2
62.5°	112.6	117.0	125.8	138.5
65°	99.0	102.6	109.1	120.1
67.5°	85.9	88.1	93.4	102.1
70°	73.2	74.9	79.3	86.3
72.5°	59.6	61.4	66.2	71.0
75°	48.2	48.6	52.2	56.1
77.5°	37.7	37.3	39.9	43.0
80°	25.9	27.2	29.4	30.7
82.5°	17.5	18.0	18.8	19.7
85°	9.6	10.1	10.1	11.4
87.5°	3.9	4.4	4.4	4.8
90°	11.5	9.2	4.6	1.2
92.5°	39.1	33.4	24.2	17.3
95°	66.8	56.4	44.9	40.3
97.5°	94.4	79.4	66.8	59.9
100°	120.9	102.4	92.1	88.6
102.5°	146.2	127.8	117.4	115.1
105°	170.3	153.1	145.0	140.4
107.5°	195.7	179.6	171.5	168.0
110°	222.1	207.2	200.3	195.7

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	247.5	233.7	225.6	221.0
115°	273.9	260.1	253.2	247.5
117.5°	299.3	286.6	279.7	275.1
120°	322.3	311.9	305.0	300.4
122.5°	346.5	334.9	328.0	324.6
125°	369.5	355.7	348.8	345.3
127.5°	391.3	376.4	367.2	362.6
130°	409.8	393.6	382.1	377.5
132.5°	427.0	409.8	397.1	391.3
135°	440.8	423.6	409.8	405.2
137.5°	455.8	437.4	423.6	417.8
140°	469.6	451.2	437.4	432.8
142.5°	482.3	463.9	451.2	447.7
145°	496.1	478.8	467.3	462.7
147.5°	509.9	493.8	482.3	478.8
150°	522.6	507.6	498.4	494.9
152.5°	534.1	521.4	512.2	511.0
155°	546.7	534.1	527.2	526.0
157.5°	557.1	545.6	539.8	538.7
160°	566.3	557.1	552.5	551.3
162.5°	574.4	567.4	562.8	564.0
165°	581.3	574.4	572.1	573.2
167.5°	587.0	582.4	580.1	581.3
170°	591.6	588.2	587.0	589.3
172.5°	595.1	591.6	592.8	593.9
175°	597.4	595.1	596.2	597.4
177.5°	598.5	596.2	597.4	599.7
180°	598.5	598.5	598.5	598.5

TEST NUMBER: P998083

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.22	10.87	11.38	12.01	13.63	7.71	8.36	8.87	9.51	11.12
	3H	11.02	11.60	12.18	12.75	14.37	9.04	9.62	10.21	10.78	12.40
	4H	11.17	11.73	12.35	12.88	14.51	9.49	10.05	10.67	11.20	12.83
	6H	11.21	11.72	12.39	12.87	14.51	9.79	10.30	10.97	11.45	13.09
	8H	11.18	11.67	12.37	12.84	14.47	9.87	10.35	11.05	11.52	13.15
	12H	11.14	11.60	12.33	12.76	14.41	9.90	10.36	11.09	11.52	13.18
4H	2H	10.24	10.79	11.42	11.94	13.57	8.13	8.69	9.32	9.84	11.47
	3H	11.20	11.66	12.39	12.84	14.48	9.58	10.04	10.76	11.21	12.85
	4H	11.47	11.89	12.66	13.06	14.72	10.10	10.53	11.29	11.69	13.35
	6H	11.58	11.95	12.78	13.14	14.78	10.47	10.83	11.66	12.02	13.67
	8H	11.58	11.92	12.77	13.10	14.76	10.58	10.91	11.77	12.09	13.76
	12H	11.53	11.84	12.74	13.03	14.70	10.62	10.93	11.83	12.12	13.79
8H	4H	11.46	11.80	12.65	12.98	14.64	10.23	10.57	11.42	11.75	13.41
	6H	11.63	11.91	12.84	13.13	14.79	10.65	10.93	11.87	12.16	13.82
	8H	11.66	11.90	12.88	13.10	14.78	10.80	11.05	12.02	12.24	13.93
	12H	11.63	11.85	12.85	13.04	14.76	10.89	11.10	12.11	12.30	14.01
12H	4H	11.41	11.71	12.61	12.90	14.57	10.19	10.50	11.40	11.69	13.36
	6H	11.61	11.85	12.82	13.05	14.73	10.65	10.90	11.87	12.10	13.78
	8H	11.63	11.84	12.85	13.04	14.75	10.80	11.01	12.02	12.21	13.92