

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998124

Luminaire Tested: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998124
REPORT IS A COMBINATION OF REPORTS P983862 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5446.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32	23		
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	28	27	20		
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	17		
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	22	21	20	15		
4	70	60	53	47	62	54	47	43	42	37	34	30	28	25	20	19	17	13		
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15	11		
6	59	48	40	35	52	43	36	32	33	29	25	25	22	19	17	15	13	10		
7	55	43	36	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9		
8	51	39	32	27	45	35	29	24	28	23	20	21	17	15	14	12	11	8		
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7		
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9054	9054	9054	9054
5°	9075	9654	9110	7680
10°	8971	10539	9027	6332
15°	8753	11116	8875	5334
20°	8617	10438	8617	4636
25°	8342	8967	8380	4146
30°	7890	7049	8041	3755
35°	7490	4874	7616	3435
40°	7029	3680	7110	3181
45°	6462	3025	6567	2906
50°	5971	2654	5983	2661
55°	5412	2262	5446	2394
60°	4816	1890	4882	2089
65°	4284	1537	4362	1784
70°	3750	1205	3846	1438
75°	3149	875	3273	1043
80°	2459	555	2635	620
85°	1610	280	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9360 cd/sqm

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.0
10°-20°	158.6	2.9
20°-30°	230.1	4.2
30°-40°	242.6	4.5
40°-50°	214.7	3.9
50°-60°	171.4	3.1
60°-70°	116.4	2.1
70°-80°	59.6	1.1
80°-90°	17.9	0.3
90°-100°	234.0	4.3
100°-110°	824.0	15.1
110°-120°	865.4	15.9
120°-130°	712.0	13.1
130°-140°	572.0	10.5
140°-150°	432.0	7.9
150°-160°	303.7	5.6
160°-170°	178.8	3.3
170°-180°	58.2	1.1
0°-30°	443.2	8.1
0°-40°	685.8	12.6
0°-60°	1071.9	19.7
0°-90°	1265.9	23.2
90°-120°	1923.5	35.3
90°-150°	3639.5	66.8
90°-180°	4180.0	76.8
0°-180°	5446.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	572	639	575	508	572	54
15°	538	785	545	377	538	152
25°	483	654	485	302	483	221
35°	394	356	401	251	394	247
45°	296	215	301	206	296	230
55°	203	151	204	160	203	181
65°	120	93	123	108	120	120
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	38	1	38	1	3
95°	40	132	40	132	40	42
105°	141	1301	141	1301	141	150
115°	248	1712	248	1712	248	246
125°	346	1389	346	1389	346	308
135°	406	1151	406	1151	406	314
145°	464	919	464	919	464	291
155°	528	772	528	772	528	243
165°	575	678	575	678	575	162
175°	599	611	599	611	599	57
180°	600	600	600	600	600	

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	575.1	576.4	578.6	579.0	583.4	586.9	590.9	590.9	592.2	591.8	588.3
5°	572.4	576.4	582.1	586.9	594.9	598.4	603.7	607.6	611.1	613.8	613.3
7.5°	568.0	575.1	583.4	592.7	603.2	609.4	616.8	623.9	628.7	633.1	636.2
10°	560.6	572.4	583.9	596.2	609.8	618.2	627.0	636.2	643.7	652.0	659.9
12.5°	550.5	567.6	581.7	597.9	614.6	623.9	637.9	645.0	659.5	680.6	686.3
15°	537.7	561.0	574.2	594.9	616.8	624.3	643.7	655.1	685.0	698.2	714.0
17.5°	525.8	551.8	569.4	593.1	614.6	629.2	648.1	671.4	696.4	715.3	732.9
20°	516.2	541.2	562.3	588.7	616.0	634.4	654.2	682.4	709.6	729.0	742.6
22.5°	494.2	526.3	550.9	580.4	613.3	638.8	657.7	688.5	718.0	729.8	741.7
25°	483.2	510.9	539.5	572.9	611.6	641.9	658.2	692.5	718.4	722.8	725.4
27.5°	463.0	494.2	527.6	565.8	611.1	636.6	657.3	688.5	709.2	706.1	698.2
30°	437.9	476.2	513.1	554.4	605.0	632.7	652.0	680.6	691.1	675.3	661.2
32.5°	419.4	455.5	496.4	544.3	597.9	624.3	643.2	665.6	667.8	639.3	615.5
35°	394.4	434.4	480.5	531.1	586.1	609.8	627.4	641.0	630.5	590.5	562.3
37.5°	372.0	411.5	460.8	512.2	569.8	593.1	607.2	609.4	583.4	548.3	506.9
40°	347.3	388.2	439.7	493.7	551.8	572.0	580.8	574.2	536.8	495.9	448.0
42.5°	322.7	363.2	418.6	474.0	528.9	546.1	549.6	531.5	485.8	437.9	382.5
45°	295.9	338.1	393.5	449.3	502.5	512.2	512.6	486.7	432.6	382.5	331.1
47.5°	273.9	313.0	368.0	423.8	468.7	475.3	472.6	442.7	383.8	327.5	282.7
50°	249.7	287.1	341.6	396.6	434.8	436.6	430.0	387.3	329.7	278.3	242.7
52.5°	223.8	261.6	311.7	364.5	398.8	396.1	383.4	337.7	283.6	240.9	213.7
55°	203.1	236.5	283.6	335.0	359.2	351.7	337.7	291.1	248.4	212.4	188.6
57.5°	180.3	209.7	255.9	300.7	314.8	307.8	293.7	250.2	210.6	183.3	167.5
60°	158.7	185.5	226.0	263.4	274.3	266.9	250.6	211.5	182.9	160.0	148.2
62.5°	138.9	162.2	196.1	230.4	234.8	227.3	213.2	181.6	157.0	138.9	130.1
65°	120.5	142.4	169.7	195.6	199.6	191.7	177.2	154.3	133.7	122.2	113.9
67.5°	102.4	120.0	144.2	163.1	165.3	157.8	146.0	127.5	114.8	102.4	96.3
70°	86.6	99.8	118.7	134.1	135.0	127.9	121.8	105.1	95.4	86.6	81.8
72.5°	71.2	80.5	95.0	106.4	106.8	102.4	96.7	86.2	77.8	71.7	66.8
75°	56.3	64.2	73.0	83.1	82.7	79.1	74.7	68.1	61.1	57.2	55.0
77.5°	43.1	47.9	55.0	61.6	61.6	59.8	57.2	52.3	47.9	44.0	41.8
80°	30.8	33.9	39.6	41.8	42.6	42.2	40.0	36.5	34.7	31.7	30.8
82.5°	19.8	22.0	24.6	26.8	28.1	27.3	26.8	25.1	22.4	21.5	20.7
85°	11.4	12.3	13.6	14.9	15.4	14.9	15.8	14.5	13.2	13.2	12.8
87.5°	4.8	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	1.2	4.6	9.2	11.5	13.9	15.6	17.3	23.1	31.2	38.1	39.2
92.5°	17.3	24.2	33.5	39.2	48.5	54.8	61.2	92.3	136.2	175.5	177.8
95°	40.4	45.0	56.6	67.0	85.4	99.2	113.1	166.2	266.6	400.6	452.5
97.5°	60.0	67.0	79.6	94.7	115.4	131.0	146.6	214.7	354.4	570.2	737.6
100°	88.9	92.3	102.7	121.2	144.3	160.4	176.6	237.8	378.6	628.0	911.9
102.5°	115.4	117.7	128.1	146.6	170.8	187.0	203.2	258.6	379.8	606.0	917.7
105°	140.8	145.4	153.5	170.8	196.2	212.4	228.6	282.8	385.5	576.0	855.4
107.5°	168.5	172.0	180.1	196.2	221.6	237.8	254.0	307.0	398.2	559.8	797.6
110°	196.2	200.9	207.8	222.8	247.0	263.8	280.5	331.3	414.4	555.2	758.4

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.6	226.2	234.3	248.2	271.3	288.6	305.9	354.4	431.7	556.4	733.0
115°	248.2	254.0	260.9	274.7	297.8	313.4	329.0	378.6	449.0	561.0	715.7
117.5°	275.9	280.5	287.4	300.1	322.1	338.2	354.4	400.6	467.5	567.9	706.4
120°	301.3	305.9	312.8	323.2	346.3	362.5	378.6	423.6	486.0	574.9	698.4
122.5°	325.5	329.0	335.9	347.5	370.5	387.2	404.0	445.6	502.1	582.9	693.7
125°	346.3	349.8	356.7	370.5	393.6	409.8	425.9	467.5	519.4	591.0	688.0
127.5°	363.6	368.2	377.5	392.5	414.4	431.2	447.9	488.3	535.6	599.1	684.5
130°	378.6	383.2	394.8	410.9	434.0	450.2	466.3	506.7	550.6	608.3	682.2
132.5°	392.5	398.2	410.9	428.3	452.5	468.6	484.8	522.9	565.6	617.6	681.1
135°	406.3	410.9	424.8	442.1	468.7	484.8	501.0	537.9	578.3	624.5	679.9
137.5°	419.0	424.8	438.6	457.1	483.7	498.7	513.7	550.6	588.7	631.4	679.9
140°	434.0	438.6	452.5	471.0	496.4	511.4	526.4	561.0	596.8	636.0	678.7
142.5°	449.0	452.5	465.2	483.7	507.9	521.8	535.6	569.1	603.7	639.5	678.7
145°	464.0	468.7	480.2	497.5	520.6	533.3	546.0	577.2	609.5	641.8	676.4
147.5°	480.2	483.7	495.2	511.4	531.0	542.6	554.1	584.1	612.9	643.0	673.0
150°	496.4	499.8	509.1	524.1	541.4	551.8	562.2	588.7	615.3	641.8	669.5
152.5°	512.5	513.7	522.9	535.6	551.8	561.0	570.2	593.3	616.4	639.5	663.7
155°	527.5	528.7	535.6	548.3	561.0	569.6	578.3	597.9	617.6	637.2	656.8
157.5°	540.2	541.4	547.1	558.7	569.1	576.6	584.1	601.4	617.6	632.6	649.9
160°	552.9	554.1	558.7	567.9	577.2	583.6	589.9	603.7	617.6	629.1	643.0
162.5°	565.6	564.5	569.1	576.0	584.1	588.7	593.3	604.9	616.4	625.6	637.2
165°	574.9	573.7	576.0	582.9	588.7	592.2	595.6	606.0	614.1	621.0	629.1
167.5°	582.9	581.8	584.1	588.7	593.3	595.6	597.9	606.0	612.9	616.4	622.2
170°	591.0	588.7	589.9	593.3	595.6	597.4	599.1	604.9	610.6	612.9	616.4
172.5°	595.6	594.5	593.3	596.8	597.9	599.0	600.2	603.7	607.2	608.3	609.5
175°	599.1	597.9	596.8	599.1	599.1	599.7	600.2	602.6	604.9	603.7	604.9
177.5°	601.4	599.1	597.9	600.2	600.2	600.2	600.2	601.4	603.7	601.4	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	594.4	594.9	595.7	600.1	602.3	602.8	601.0	605.0	606.3	605.0	604.1
5°	622.6	625.2	630.5	636.2	635.7	636.2	638.8	641.5	642.3	638.8	640.1
7.5°	647.2	652.5	658.2	667.0	667.0	671.4	673.1	675.3	680.6	678.0	677.1
10°	675.3	682.4	692.9	707.0	707.4	711.8	716.2	723.2	725.4	723.7	724.6
12.5°	710.5	724.1	725.0	740.4	747.4	748.3	755.3	754.0	758.4	758.4	765.9
15°	725.9	747.0	758.9	773.8	778.2	772.9	778.6	784.8	785.2	785.2	784.8
17.5°	753.6	761.9	773.8	781.7	783.5	783.5	783.9	786.6	784.8	781.3	783.9
20°	759.3	762.8	767.2	766.3	767.2	762.8	758.4	754.0	754.5	752.3	758.9
22.5°	748.7	747.9	737.7	731.2	731.2	722.4	714.0	710.1	706.1	707.4	709.6
25°	722.4	708.7	696.4	686.7	684.6	670.5	659.0	655.5	648.9	654.2	655.1
27.5°	680.2	664.8	645.0	636.6	625.2	619.5	611.6	601.0	587.4	595.3	594.0
30°	634.9	612.0	595.7	575.5	557.5	556.2	541.2	523.6	516.6	516.6	520.6
32.5°	584.3	554.0	530.2	501.7	484.1	476.6	458.6	441.0	444.9	431.7	436.6
35°	525.4	485.4	455.5	427.8	414.6	405.8	382.5	372.8	362.3	356.1	367.6
37.5°	469.1	423.0	384.7	354.4	349.5	333.7	317.9	311.7	305.6	308.2	307.8
40°	400.5	359.6	325.3	301.6	293.3	285.8	275.2	267.8	263.8	266.0	266.4
42.5°	338.5	304.2	278.7	262.0	255.0	249.7	244.5	238.3	237.0	237.0	238.7
45°	290.6	262.5	245.3	231.7	227.7	223.8	219.8	217.2	216.3	214.6	215.9
47.5°	252.4	229.9	219.4	209.3	204.9	204.0	200.5	199.2	197.4	197.0	197.4
50°	220.3	206.2	196.5	190.8	187.7	186.4	184.7	182.0	181.1	183.3	182.5
52.5°	197.8	184.7	179.4	173.7	171.9	170.1	167.5	167.9	167.5	166.6	166.6
55°	175.4	167.1	161.8	157.4	157.0	155.2	153.0	152.1	151.7	150.8	152.1
57.5°	157.4	150.8	146.0	142.0	140.3	140.3	138.1	136.3	136.3	135.9	136.3
60°	139.4	132.8	129.7	125.7	124.4	124.0	122.7	121.8	120.5	120.5	120.5
62.5°	122.7	117.4	113.9	110.4	110.8	108.6	106.8	106.0	106.0	106.4	106.4
65°	106.8	103.3	98.9	95.8	95.0	94.5	93.6	93.2	91.9	92.8	92.8
67.5°	92.3	87.5	84.9	83.5	82.2	81.8	80.9	80.0	79.6	79.1	80.0
70°	77.8	73.9	71.7	70.8	69.5	69.0	68.6	67.3	67.7	68.1	68.6
72.5°	64.6	61.1	60.7	58.0	58.0	58.0	56.3	57.2	56.7	55.8	56.7
75°	51.0	49.2	48.4	47.0	47.5	47.0	46.6	45.3	45.3	45.7	46.2
77.5°	40.4	38.7	38.3	36.9	36.1	36.9	36.1	35.6	35.6	36.1	36.1
80°	29.9	29.0	27.7	27.7	27.7	27.3	27.3	27.3	26.8	26.4	26.8
82.5°	19.8	19.8	19.3	18.9	19.3	18.5	18.9	18.9	18.9	18.9	18.9
85°	12.8	12.3	12.3	11.9	11.9	11.9	12.3	11.4	11.4	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	38.1	36.9	34.6	36.9	37.5	38.1	38.1	38.1	38.1	38.1	38.1
92.5°	148.9	116.6	99.3	86.6	81.9	77.3	76.2	71.6	72.7	70.4	72.7
95°	395.9	302.4	232.0	183.5	170.8	158.1	143.1	133.9	130.4	131.6	130.4
97.5°	743.4	618.7	494.1	377.5	342.8	308.2	263.2	240.1	227.4	220.5	227.4
100°	1078.1	1053.9	910.8	752.6	682.8	612.9	517.1	467.5	434.0	413.2	434.0
102.5°	1202.8	1339.0	1334.4	1229.4	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7
105°	1162.4	1402.5	1532.9	1547.9	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1
107.5°	1077.0	1334.4	1528.3	1641.4	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1
110°	997.3	1240.9	1447.5	1595.3	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	941.9	1155.5	1351.7	1512.2	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3
115°	898.1	1088.5	1266.3	1417.5	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5
117.5°	868.1	1033.1	1192.4	1333.2	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4
120°	845.0	993.9	1137.0	1259.4	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9
122.5°	825.3	962.7	1090.8	1205.1	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8
125°	806.9	932.7	1051.6	1153.2	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4
127.5°	789.6	902.7	1012.3	1109.3	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9
130°	772.2	873.8	973.1	1064.3	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4
132.5°	758.4	846.1	936.2	1018.1	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0
135°	745.7	820.7	896.9	973.1	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2
137.5°	736.5	799.9	865.7	928.1	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1
140°	728.4	780.3	835.7	888.8	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9
142.5°	720.3	764.2	809.2	853.0	873.2	893.4	928.1	954.6	969.6	969.6	969.6
145°	713.4	749.2	787.2	823.0	839.8	856.5	884.2	903.8	915.4	918.8	915.4
147.5°	706.4	737.6	768.8	797.6	810.3	823.0	847.3	863.4	871.5	873.8	871.5
150°	697.2	724.9	750.3	774.6	785.0	795.3	812.6	826.5	833.4	834.6	833.4
152.5°	689.1	712.2	735.3	754.9	763.6	772.2	784.9	796.5	801.1	801.1	801.1
155°	678.7	700.7	719.1	736.5	742.8	749.2	761.9	769.9	774.6	772.2	774.6
157.5°	669.5	686.8	703.0	718.0	723.2	728.4	737.6	744.5	746.8	746.8	746.8
160°	659.1	674.1	686.8	699.5	703.6	707.6	715.7	721.5	722.6	722.6	722.6
162.5°	649.9	661.4	671.8	682.2	685.1	688.0	696.1	699.5	700.7	699.5	700.7
165°	639.5	648.7	656.8	664.9	667.2	669.5	674.1	678.7	678.7	677.6	678.7
167.5°	629.1	636.0	643.0	648.7	651.0	653.3	655.7	658.0	658.0	656.8	658.0
170°	621.0	626.8	630.3	634.9	636.0	637.2	638.3	641.8	640.6	638.3	640.6
172.5°	612.9	616.4	618.7	622.2	622.8	623.3	624.5	625.6	624.5	623.3	624.5
175°	606.0	609.5	610.6	611.8	612.3	612.9	612.9	614.1	612.9	610.6	612.9
177.5°	601.4	603.7	603.7	604.9	604.9	604.9	604.9	604.9	603.7	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	606.3	603.2	600.6	601.0	603.2	601.5	597.1	591.3	589.1	586.5	589.1
5°	642.8	640.1	634.9	635.3	634.0	632.2	625.2	616.4	616.4	609.4	608.5
7.5°	678.8	674.9	671.4	670.5	665.6	662.1	656.0	643.7	638.8	630.5	625.6
10°	719.3	716.2	712.2	707.4	704.8	698.6	688.5	670.5	661.7	650.3	641.9
12.5°	760.2	759.7	750.9	741.3	740.8	731.2	724.1	699.9	688.1	672.7	652.9
15°	786.1	783.9	779.1	774.2	775.6	765.0	749.2	720.6	712.7	694.2	673.1
17.5°	785.7	785.7	784.4	783.5	782.2	779.1	770.3	751.4	738.6	715.3	695.5
20°	760.6	766.3	767.6	767.2	771.6	773.8	773.4	761.5	751.4	730.7	710.5
22.5°	710.5	723.7	729.4	732.9	742.1	747.0	758.4	754.0	751.4	736.0	718.8
25°	663.9	668.3	685.4	686.3	699.1	710.9	722.4	729.8	739.5	733.8	719.3
27.5°	603.7	613.8	626.1	635.3	637.9	662.1	681.0	695.1	717.1	718.8	714.0
30°	535.5	540.3	560.6	572.9	586.9	604.5	631.8	656.0	675.8	693.8	699.9
32.5°	452.4	472.2	484.1	499.0	511.3	542.5	576.0	607.2	630.0	660.4	673.6
35°	376.3	391.7	412.0	418.1	440.5	466.9	510.4	550.5	585.2	616.0	642.8
37.5°	313.5	325.8	347.3	357.0	370.2	404.0	440.5	490.2	532.0	569.8	603.2
40°	270.4	279.6	295.9	299.0	310.0	340.7	370.2	416.8	472.2	523.2	559.7
42.5°	240.9	245.3	256.3	260.3	267.3	288.0	314.4	358.3	409.8	462.5	514.0
45°	219.8	222.9	229.5	233.0	241.8	251.0	272.6	307.8	348.2	401.4	456.8
47.5°	200.9	204.9	207.5	209.7	214.6	224.7	238.7	264.7	303.4	352.2	405.8
50°	185.1	186.4	191.3	191.7	194.8	201.4	214.6	230.4	261.2	300.7	352.6
52.5°	169.3	170.6	173.7	176.7	178.1	183.3	192.1	205.3	228.2	259.4	305.6
55°	153.4	155.2	158.3	160.5	161.8	166.2	171.5	184.2	202.2	224.2	262.0
57.5°	137.6	141.6	142.4	143.8	146.0	150.8	155.6	163.1	177.2	197.4	225.1
60°	122.7	124.0	127.1	128.4	130.6	133.2	139.4	145.1	155.2	171.0	196.1
62.5°	107.3	110.4	111.7	113.0	114.8	117.8	121.8	127.9	136.7	149.5	169.3
65°	94.1	94.5	97.2	98.9	100.7	102.9	106.8	112.6	117.8	129.7	144.2
67.5°	81.3	82.2	83.1	84.9	87.1	89.3	92.8	95.8	102.4	110.4	121.8
70°	69.0	69.0	71.2	72.5	72.1	74.7	77.4	80.9	85.7	93.2	102.4
72.5°	58.0	57.6	59.4	59.8	60.7	62.4	64.2	67.7	70.3	76.1	83.1
75°	46.2	47.0	47.9	47.9	49.2	50.6	52.3	54.1	57.2	60.7	65.9
77.5°	36.5	36.5	37.4	37.8	39.1	38.7	40.4	42.2	44.4	47.5	51.4
80°	26.8	27.7	27.7	27.7	28.1	28.6	30.3	31.7	33.0	35.2	36.9
82.5°	18.9	18.9	19.8	19.8	19.8	20.7	20.7	21.1	22.0	23.3	24.6
85°	11.9	11.9	11.9	12.3	11.9	12.3	13.2	12.8	13.2	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	38.1	38.1	38.1	37.5	36.9	34.6	36.9	38.1	39.2	38.1	31.2
92.5°	71.6	76.2	77.3	81.9	86.6	99.3	116.6	148.9	177.8	175.5	136.2
95°	133.9	143.1	158.1	170.8	183.5	232.0	302.4	395.9	452.5	400.6	266.6
97.5°	240.1	263.2	308.2	342.8	377.5	494.1	618.7	743.4	737.6	570.2	354.4
100°	467.5	517.1	612.9	682.8	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6
102.5°	879.6	973.1	1079.3	1154.4	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8
105°	1366.7	1438.3	1509.9	1528.9	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5
107.5°	1676.1	1686.5	1687.6	1664.5	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2
110°	1761.5	1739.6	1689.9	1642.6	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1738.4	1698.0	1624.1	1568.2	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7
115°	1671.5	1618.4	1536.4	1477.0	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0
117.5°	1587.2	1530.6	1446.4	1389.8	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5
120°	1499.5	1445.2	1364.4	1311.9	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0
122.5°	1421.0	1367.9	1297.5	1251.3	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1
125°	1350.6	1306.7	1239.7	1196.4	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4
127.5°	1290.5	1249.0	1190.1	1149.7	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6
130°	1236.3	1197.0	1140.5	1102.4	1064.3	973.1	873.8	772.2	682.2	608.3	550.6
132.5°	1183.2	1143.9	1088.5	1053.3	1018.1	936.2	846.1	758.4	681.1	617.6	565.6
135°	1125.5	1087.4	1037.7	1005.4	973.1	896.9	820.7	745.7	679.9	624.5	578.3
137.5°	1066.6	1033.1	985.8	957.0	928.1	865.7	799.9	736.5	679.9	631.4	588.7
140°	1006.6	976.6	939.6	914.2	888.8	835.7	780.3	728.4	678.7	636.0	596.8
142.5°	954.6	928.1	893.4	873.2	853.0	809.2	764.2	720.3	678.7	639.5	603.7
145°	903.8	884.2	856.5	839.8	823.0	787.2	749.2	713.4	676.4	641.8	609.5
147.5°	863.4	847.3	823.0	810.3	797.6	768.8	737.6	706.4	673.0	643.0	612.9
150°	826.5	812.6	795.3	785.0	774.6	750.3	724.9	697.2	669.5	641.8	615.3
152.5°	796.5	784.9	772.2	763.6	754.9	735.3	712.2	689.1	663.7	639.5	616.4
155°	769.9	761.9	749.2	742.8	736.5	719.1	700.7	678.7	656.8	637.2	617.6
157.5°	744.5	737.6	728.4	723.2	718.0	703.0	686.8	669.5	649.9	632.6	617.6
160°	721.5	715.7	707.6	703.6	699.5	686.8	674.1	659.1	643.0	629.1	617.6
162.5°	699.5	696.1	688.0	685.1	682.2	671.8	661.4	649.9	637.2	625.6	616.4
165°	678.7	674.1	669.5	667.2	664.9	656.8	648.7	639.5	629.1	621.0	614.1
167.5°	658.0	655.7	653.3	651.0	648.7	643.0	636.0	629.1	622.2	616.4	612.9
170°	641.8	638.3	637.2	636.0	634.9	630.3	626.8	621.0	616.4	612.9	610.6
172.5°	625.6	624.5	623.3	622.8	622.2	618.7	616.4	612.9	609.5	608.3	607.2
175°	614.1	612.9	612.9	612.3	611.8	610.6	609.5	606.0	604.9	603.7	604.9
177.5°	604.9	604.9	604.9	604.9	604.9	603.7	603.7	601.4	600.2	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	586.9	584.7	583.4	584.3	581.7	575.1	575.1	577.3	574.6	572.0	568.0
5°	603.2	598.8	596.2	595.7	589.6	579.0	576.8	574.6	568.9	562.8	556.2
7.5°	619.0	611.1	606.7	603.7	594.9	581.2	575.5	570.7	561.4	552.2	543.9
10°	632.2	620.8	615.5	610.7	599.3	582.1	572.9	564.1	552.2	540.3	529.8
12.5°	642.8	629.6	623.0	616.0	601.9	579.5	568.0	554.0	542.1	526.3	515.7
15°	660.4	633.1	627.0	620.4	605.9	575.1	561.0	545.2	528.9	507.8	496.4
17.5°	674.4	637.9	637.5	623.4	604.5	573.3	551.8	531.1	513.5	492.4	474.4
20°	682.8	645.4	638.4	623.9	600.1	561.4	539.0	516.2	497.3	471.8	453.7
22.5°	689.8	656.0	637.5	619.9	590.9	557.5	524.5	503.0	477.0	449.3	432.2
25°	692.5	658.2	638.8	618.6	584.3	546.1	508.7	485.4	456.4	431.3	408.0
27.5°	692.9	657.7	634.0	612.9	575.1	531.1	492.9	468.2	436.1	407.1	383.8
30°	688.5	652.9	631.4	608.5	566.3	517.5	473.5	446.3	412.0	382.9	358.8
32.5°	675.3	643.2	625.6	600.6	554.9	498.6	455.0	424.7	388.7	360.1	336.8
35°	653.3	631.4	612.0	588.7	539.9	481.0	436.6	401.0	364.5	337.2	315.2
37.5°	626.1	614.2	596.2	573.3	522.8	465.2	415.9	376.3	339.9	313.5	291.9
40°	589.1	592.2	574.6	554.0	502.5	443.6	389.1	351.3	317.0	292.4	271.3
42.5°	549.1	561.9	551.8	532.0	480.1	419.9	369.3	327.5	294.1	268.6	251.0
45°	506.0	528.0	521.9	507.4	456.8	394.8	341.2	300.7	271.3	246.6	231.3
47.5°	459.0	490.2	490.2	479.7	430.9	369.8	317.0	275.7	246.6	229.1	214.1
50°	411.1	446.3	452.0	444.9	401.8	341.2	287.5	250.2	225.1	208.0	197.0
52.5°	361.0	401.8	412.4	408.9	371.1	313.9	263.4	226.9	204.0	189.1	179.4
55°	313.0	360.5	372.0	373.3	338.1	284.0	236.5	204.4	182.5	172.3	164.0
57.5°	267.8	313.5	326.2	328.4	304.7	256.8	211.5	183.3	163.6	155.2	148.6
60°	229.1	267.3	284.0	288.9	268.2	225.1	188.2	160.9	146.0	138.1	131.9
62.5°	197.4	228.2	245.8	247.1	237.9	197.4	164.0	141.1	128.4	121.3	118.3
65°	166.6	194.3	204.9	210.2	202.7	171.0	141.6	122.7	112.6	106.4	103.3
67.5°	142.0	159.6	168.4	175.4	167.9	144.2	120.5	105.1	97.6	91.4	89.7
70°	116.5	131.0	137.6	144.6	138.1	120.0	102.9	88.8	82.2	77.4	75.2
72.5°	93.2	104.6	110.8	115.2	111.2	96.3	82.2	72.5	67.7	64.2	62.9
75°	73.9	81.8	85.3	88.4	86.6	75.2	66.4	58.5	54.1	51.0	50.1
77.5°	56.3	62.0	65.9	66.8	64.6	57.2	49.7	44.8	41.3	39.6	38.7
80°	40.0	43.5	45.7	47.0	44.8	41.8	36.5	33.0	29.9	27.7	27.3
82.5°	26.8	28.6	30.3	29.9	29.0	26.4	23.3	21.5	20.2	18.5	18.5
85°	15.4	15.8	16.7	17.1	16.7	14.9	13.2	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	4.0
90°	23.1	17.3	15.6	13.9	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.3	61.2	54.8	48.5	39.2	33.5	24.2	17.3	24.2	33.5	39.2
95°	166.2	113.1	99.2	85.4	67.0	56.6	45.0	40.4	45.0	56.6	67.0
97.5°	214.7	146.6	131.0	115.4	94.7	79.6	67.0	60.0	67.0	79.6	94.7
100°	237.8	176.6	160.4	144.3	121.2	102.7	92.3	88.9	92.3	102.7	121.2
102.5°	258.6	203.2	187.0	170.8	146.6	128.1	117.7	115.4	117.7	128.1	146.6
105°	282.8	228.6	212.4	196.2	170.8	153.5	145.4	140.8	145.4	153.5	170.8
107.5°	307.0	254.0	237.8	221.6	196.2	180.1	172.0	168.5	172.0	180.1	196.2
110°	331.3	280.5	263.8	247.0	222.8	207.8	200.9	196.2	200.9	207.8	222.8

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	354.4	305.9	288.6	271.3	248.2	234.3	226.2	221.6	226.2	234.3	248.2
115°	378.6	329.0	313.4	297.8	274.7	260.9	254.0	248.2	254.0	260.9	274.7
117.5°	400.6	354.4	338.2	322.1	300.1	287.4	280.5	275.9	280.5	287.4	300.1
120°	423.6	378.6	362.5	346.3	323.2	312.8	305.9	301.3	305.9	312.8	323.2
122.5°	445.6	404.0	387.2	370.5	347.5	335.9	329.0	325.5	329.0	335.9	347.5
125°	467.5	425.9	409.8	393.6	370.5	356.7	349.8	346.3	349.8	356.7	370.5
127.5°	488.3	447.9	431.2	414.4	392.5	377.5	368.2	363.6	368.2	377.5	392.5
130°	506.7	466.3	450.2	434.0	410.9	394.8	383.2	378.6	383.2	394.8	410.9
132.5°	522.9	484.8	468.6	452.5	428.3	410.9	398.2	392.5	398.2	410.9	428.3
135°	537.9	501.0	484.8	468.7	442.1	424.8	410.9	406.3	410.9	424.8	442.1
137.5°	550.6	513.7	498.7	483.7	457.1	438.6	424.8	419.0	424.8	438.6	457.1
140°	561.0	526.4	511.4	496.4	471.0	452.5	438.6	434.0	438.6	452.5	471.0
142.5°	569.1	535.6	521.8	507.9	483.7	465.2	452.5	449.0	452.5	465.2	483.7
145°	577.2	546.0	533.3	520.6	497.5	480.2	468.7	464.0	468.7	480.2	497.5
147.5°	584.1	554.1	542.6	531.0	511.4	495.2	483.7	480.2	483.7	495.2	511.4
150°	588.7	562.2	551.8	541.4	524.1	509.1	499.8	496.4	499.8	509.1	524.1
152.5°	593.3	570.2	561.0	551.8	535.6	522.9	513.7	512.5	513.7	522.9	535.6
155°	597.9	578.3	569.6	561.0	548.3	535.6	528.7	527.5	528.7	535.6	548.3
157.5°	601.4	584.1	576.6	569.1	558.7	547.1	541.4	540.2	541.4	547.1	558.7
160°	603.7	589.9	583.6	577.2	567.9	558.7	554.1	552.9	554.1	558.7	567.9
162.5°	604.9	593.3	588.7	584.1	576.0	569.1	564.5	565.6	564.5	569.1	576.0
165°	606.0	595.6	592.2	588.7	582.9	576.0	573.7	574.9	573.7	576.0	582.9
167.5°	606.0	597.9	595.6	593.3	588.7	584.1	581.8	582.9	581.8	584.1	588.7
170°	604.9	599.1	597.4	595.6	593.3	589.9	588.7	591.0	588.7	589.9	593.3
172.5°	603.7	600.2	599.0	597.9	596.8	593.3	594.5	595.6	594.5	593.3	596.8
175°	602.6	600.2	599.7	599.1	599.1	596.8	597.9	599.1	597.9	596.8	599.1
177.5°	601.4	600.2	600.2	600.2	600.2	597.9	599.1	601.4	599.1	597.9	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	565.8	568.0	567.6	563.2	558.4	554.4	546.9	547.8	545.2	545.6	548.3
5°	551.8	551.8	550.0	543.9	535.9	531.5	523.2	521.0	515.7	515.3	514.8
7.5°	536.8	534.6	532.4	523.6	514.0	506.9	495.5	492.9	487.6	484.1	482.3
10°	519.2	516.2	511.8	501.7	489.8	481.0	469.1	465.6	455.5	451.1	448.5
12.5°	499.9	498.1	491.1	482.7	463.4	453.7	436.6	440.1	430.0	421.2	419.9
15°	480.5	474.0	470.0	456.4	433.1	428.7	415.0	408.0	398.8	391.7	391.7
17.5°	461.6	451.5	442.7	428.2	411.1	398.8	388.7	385.1	373.7	366.7	365.4
20°	436.6	425.2	423.0	402.3	390.4	376.8	367.1	358.3	350.0	346.9	344.7
22.5°	412.8	399.7	396.1	378.5	366.7	353.0	343.4	337.2	331.1	328.9	324.9
25°	387.3	379.4	374.2	355.2	342.1	329.3	322.7	318.3	312.6	312.2	309.5
27.5°	362.7	355.2	350.0	331.9	322.3	310.4	305.1	300.3	297.2	295.9	294.6
30°	341.6	333.3	327.1	313.9	302.0	292.4	288.0	284.9	283.1	280.9	280.5
32.5°	318.3	313.5	305.1	295.0	285.8	276.5	273.9	271.7	269.1	268.2	267.8
35°	298.5	291.9	286.7	275.2	271.3	263.4	260.3	258.5	255.0	254.1	253.2
37.5°	279.2	273.0	267.3	260.3	252.8	248.4	246.6	244.0	242.3	242.7	241.8
40°	259.8	255.0	250.6	243.1	238.7	236.5	233.0	230.4	229.5	229.9	229.5
42.5°	240.9	236.5	233.9	228.2	223.8	221.6	219.4	216.8	218.1	218.1	219.4
45°	223.8	219.8	218.1	213.7	211.0	207.5	205.3	204.9	206.6	206.2	206.2
47.5°	206.2	204.9	202.7	198.7	195.2	193.0	192.6	192.6	194.3	195.2	194.8
50°	192.6	189.9	187.3	184.2	181.6	180.7	179.4	180.3	182.0	182.0	182.9
52.5°	175.4	173.7	172.8	170.1	168.4	168.4	168.4	168.8	170.1	171.5	171.0
55°	160.5	159.2	158.3	157.0	154.8	155.2	154.8	155.6	157.0	158.3	159.2
57.5°	144.6	144.2	143.3	141.1	141.1	140.7	142.0	142.4	144.6	145.5	146.8
60°	130.6	129.3	129.3	127.5	127.5	127.5	128.8	130.1	131.9	132.3	133.2
62.5°	115.6	115.6	115.2	113.9	113.9	115.2	115.6	117.4	118.3	118.3	119.6
65°	101.6	101.1	100.7	101.1	101.6	101.6	102.9	103.8	104.6	105.1	105.5
67.5°	87.5	87.1	87.9	87.5	88.4	90.1	89.7	91.0	92.3	92.3	92.8
70°	74.3	75.2	74.7	75.6	75.2	76.1	77.4	77.8	77.8	78.3	79.6
72.5°	62.0	62.0	62.0	61.6	62.0	62.9	63.8	64.2	65.1	65.5	66.8
75°	50.1	50.1	49.2	50.1	50.1	51.0	51.9	51.9	51.9	52.8	54.1
77.5°	37.8	38.3	37.8	38.7	38.7	39.1	40.0	39.6	40.4	40.9	41.3
80°	27.7	27.3	27.3	27.3	27.7	27.7	28.6	29.0	29.0	30.3	29.5
82.5°	17.6	18.0	17.6	18.0	18.0	18.5	18.0	18.5	18.9	19.8	19.3
85°	10.1	9.7	9.7	10.1	9.7	9.7	10.1	9.7	10.1	9.7	10.1
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	13.9	15.6	17.3	23.1	31.2	38.1	39.2	38.1	36.9	34.6	36.9
92.5°	48.5	54.8	61.2	92.3	136.2	175.5	177.8	148.9	116.6	99.3	86.6
95°	85.4	99.2	113.1	166.2	266.6	400.6	452.5	395.9	302.4	232.0	183.5
97.5°	115.4	131.0	146.6	214.7	354.4	570.2	737.6	743.4	618.7	494.1	377.5
100°	144.3	160.4	176.6	237.8	378.6	628.0	911.9	1078.1	1053.9	910.8	752.6
102.5°	170.8	187.0	203.2	258.6	379.8	606.0	917.7	1202.8	1339.0	1334.4	1229.4
105°	196.2	212.4	228.6	282.8	385.5	576.0	855.4	1162.4	1402.5	1532.9	1547.9
107.5°	221.6	237.8	254.0	307.0	398.2	559.8	797.6	1077.0	1334.4	1528.3	1641.4
110°	247.0	263.8	280.5	331.3	414.4	555.2	758.4	997.3	1240.9	1447.5	1595.3

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.3	288.6	305.9	354.4	431.7	556.4	733.0	941.9	1155.5	1351.7	1512.2
115°	297.8	313.4	329.0	378.6	449.0	561.0	715.7	898.1	1088.5	1266.3	1417.5
117.5°	322.1	338.2	354.4	400.6	467.5	567.9	706.4	868.1	1033.1	1192.4	1333.2
120°	346.3	362.5	378.6	423.6	486.0	574.9	698.4	845.0	993.9	1137.0	1259.4
122.5°	370.5	387.2	404.0	445.6	502.1	582.9	693.7	825.3	962.7	1090.8	1205.1
125°	393.6	409.8	425.9	467.5	519.4	591.0	688.0	806.9	932.7	1051.6	1153.2
127.5°	414.4	431.2	447.9	488.3	535.6	599.1	684.5	789.6	902.7	1012.3	1109.3
130°	434.0	450.2	466.3	506.7	550.6	608.3	682.2	772.2	873.8	973.1	1064.3
132.5°	452.5	468.6	484.8	522.9	565.6	617.6	681.1	758.4	846.1	936.2	1018.1
135°	468.7	484.8	501.0	537.9	578.3	624.5	679.9	745.7	820.7	896.9	973.1
137.5°	483.7	498.7	513.7	550.6	588.7	631.4	679.9	736.5	799.9	865.7	928.1
140°	496.4	511.4	526.4	561.0	596.8	636.0	678.7	728.4	780.3	835.7	888.8
142.5°	507.9	521.8	535.6	569.1	603.7	639.5	678.7	720.3	764.2	809.2	853.0
145°	520.6	533.3	546.0	577.2	609.5	641.8	676.4	713.4	749.2	787.2	823.0
147.5°	531.0	542.6	554.1	584.1	612.9	643.0	673.0	706.4	737.6	768.8	797.6
150°	541.4	551.8	562.2	588.7	615.3	641.8	669.5	697.2	724.9	750.3	774.6
152.5°	551.8	561.0	570.2	593.3	616.4	639.5	663.7	689.1	712.2	735.3	754.9
155°	561.0	569.6	578.3	597.9	617.6	637.2	656.8	678.7	700.7	719.1	736.5
157.5°	569.1	576.6	584.1	601.4	617.6	632.6	649.9	669.5	686.8	703.0	718.0
160°	577.2	583.6	589.9	603.7	617.6	629.1	643.0	659.1	674.1	686.8	699.5
162.5°	584.1	588.7	593.3	604.9	616.4	625.6	637.2	649.9	661.4	671.8	682.2
165°	588.7	592.2	595.6	606.0	614.1	621.0	629.1	639.5	648.7	656.8	664.9
167.5°	593.3	595.6	597.9	606.0	612.9	616.4	622.2	629.1	636.0	643.0	648.7
170°	595.6	597.4	599.1	604.9	610.6	612.9	616.4	621.0	626.8	630.3	634.9
172.5°	597.9	599.0	600.2	603.7	607.2	608.3	609.5	612.9	616.4	618.7	622.2
175°	599.1	599.7	600.2	602.6	604.9	603.7	604.9	606.0	609.5	610.6	611.8
177.5°	600.2	600.2	600.2	601.4	603.7	601.4	600.2	601.4	603.7	603.7	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	545.2	546.5	543.4	542.5	543.4	540.3	541.2	542.1	542.1	543.4	544.3
5°	513.5	511.8	508.7	507.8	506.9	508.2	507.4	508.7	509.1	512.2	512.6
7.5°	482.3	479.7	477.0	474.4	473.5	471.3	473.5	473.5	476.6	475.7	477.9
10°	445.4	444.9	441.4	440.1	438.3	434.8	439.7	438.3	440.5	444.5	445.4
12.5°	418.1	413.3	415.5	409.3	411.5	408.0	408.4	408.4	412.0	412.4	411.5
15°	392.2	388.2	382.5	379.9	378.5	376.8	382.5	382.9	380.3	386.5	384.3
17.5°	365.8	365.8	360.5	359.2	355.7	357.4	356.6	357.0	356.1	360.5	362.7
20°	342.9	340.7	339.0	339.4	335.0	334.1	333.3	334.1	337.2	340.3	341.2
22.5°	324.5	323.1	318.8	319.6	316.1	317.4	316.6	318.8	319.2	319.2	322.3
25°	306.9	305.1	305.6	303.8	302.5	302.5	301.2	302.5	304.2	305.1	305.6
27.5°	293.7	292.4	290.2	288.9	289.7	287.5	289.3	290.6	290.6	289.7	290.6
30°	277.9	278.7	278.7	274.3	276.1	275.2	276.5	277.4	277.4	277.9	277.0
32.5°	267.3	264.7	264.2	263.8	263.8	262.0	262.0	263.4	263.8	264.2	265.6
35°	253.2	253.2	251.0	252.4	250.6	251.0	250.6	251.0	251.9	250.6	251.9
37.5°	240.5	240.9	240.1	240.9	241.4	240.5	239.6	241.4	240.5	240.5	239.6
40°	229.5	229.1	229.5	229.5	229.5	229.9	229.1	229.1	229.1	228.2	227.3
42.5°	220.3	217.6	218.5	219.0	217.6	217.6	218.1	217.6	219.0	216.3	216.3
45°	207.1	206.2	206.6	206.6	207.5	206.2	207.1	207.5	206.2	205.8	204.9
47.5°	195.2	196.1	195.2	196.1	196.1	197.0	195.2	195.6	196.1	194.3	193.0
50°	183.3	183.3	184.7	184.2	184.7	183.8	183.8	183.3	183.8	182.9	181.6
52.5°	172.3	171.0	173.2	172.8	172.3	171.9	171.5	171.9	171.0	170.1	170.1
55°	158.7	158.7	160.0	160.5	160.5	159.6	158.7	159.2	158.7	158.3	157.8
57.5°	147.7	146.0	146.8	147.3	147.3	146.0	146.8	146.0	146.0	146.4	145.1
60°	133.7	133.7	132.8	134.1	134.1	133.2	133.2	133.7	132.8	132.3	131.9
62.5°	118.7	119.1	120.5	120.9	121.3	120.5	119.6	120.0	120.0	118.7	119.1
65°	106.0	106.8	108.6	108.2	107.3	107.7	106.8	107.3	106.0	106.4	105.1
67.5°	93.6	93.2	93.6	93.6	94.5	94.1	93.2	93.2	92.8	94.1	92.8
70°	80.5	80.5	80.5	80.5	80.9	81.3	80.5	79.6	80.0	79.1	78.7
72.5°	66.8	67.3	66.8	67.7	66.4	67.3	67.3	66.8	66.4	66.4	66.4
75°	54.1	55.0	53.6	54.1	53.6	54.5	54.1	54.1	53.2	52.8	53.2
77.5°	41.3	41.8	40.9	41.3	40.9	41.3	41.3	40.9	40.9	40.9	40.9
80°	29.5	29.9	29.5	29.0	28.6	29.5	28.6	29.0	29.5	29.0	29.9
82.5°	18.9	18.9	18.5	18.9	18.0	18.0	18.5	18.5	18.0	18.9	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.7	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	37.5	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	37.5
92.5°	81.9	77.3	76.2	71.6	72.7	70.4	72.7	71.6	76.2	77.3	81.9
95°	170.8	158.1	143.1	133.9	130.4	131.6	130.4	133.9	143.1	158.1	170.8
97.5°	342.8	308.2	263.2	240.1	227.4	220.5	227.4	240.1	263.2	308.2	342.8
100°	682.8	612.9	517.1	467.5	434.0	413.2	434.0	467.5	517.1	612.9	682.8
102.5°	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7	879.6	973.1	1079.3	1154.4
105°	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1	1366.7	1438.3	1509.9	1528.9
107.5°	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1	1676.1	1686.5	1687.6	1664.5
110°	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9	1761.5	1739.6	1689.9	1642.6

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3	1738.4	1698.0	1624.1	1568.2
115°	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5	1671.5	1618.4	1536.4	1477.0
117.5°	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4	1587.2	1530.6	1446.4	1389.8
120°	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9	1499.5	1445.2	1364.4	1311.9
122.5°	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8	1421.0	1367.9	1297.5	1251.3
125°	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4	1350.6	1306.7	1239.7	1196.4
127.5°	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9	1290.5	1249.0	1190.1	1149.7
130°	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4	1236.3	1197.0	1140.5	1102.4
132.5°	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0	1183.2	1143.9	1088.5	1053.3
135°	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2	1125.5	1087.4	1037.7	1005.4
137.5°	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1	1066.6	1033.1	985.8	957.0
140°	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9	1006.6	976.6	939.6	914.2
142.5°	873.2	893.4	928.1	954.6	969.6	969.6	969.6	954.6	928.1	893.4	873.2
145°	839.8	856.5	884.2	903.8	915.4	918.8	915.4	903.8	884.2	856.5	839.8
147.5°	810.3	823.0	847.3	863.4	871.5	873.8	871.5	863.4	847.3	823.0	810.3
150°	785.0	795.3	812.6	826.5	833.4	834.6	833.4	826.5	812.6	795.3	785.0
152.5°	763.6	772.2	784.9	796.5	801.1	801.1	801.1	796.5	784.9	772.2	763.6
155°	742.8	749.2	761.9	769.9	774.6	772.2	774.6	769.9	761.9	749.2	742.8
157.5°	723.2	728.4	737.6	744.5	746.8	746.8	746.8	744.5	737.6	728.4	723.2
160°	703.6	707.6	715.7	721.5	722.6	722.6	722.6	721.5	715.7	707.6	703.6
162.5°	685.1	688.0	696.1	699.5	700.7	699.5	700.7	699.5	696.1	688.0	685.1
165°	667.2	669.5	674.1	678.7	678.7	677.6	678.7	678.7	674.1	669.5	667.2
167.5°	651.0	653.3	655.7	658.0	658.0	656.8	658.0	658.0	655.7	653.3	651.0
170°	636.0	637.2	638.3	641.8	640.6	638.3	640.6	641.8	638.3	637.2	636.0
172.5°	622.8	623.3	624.5	625.6	624.5	623.3	624.5	625.6	624.5	623.3	622.8
175°	612.3	612.9	612.9	614.1	612.9	610.6	612.9	614.1	612.9	612.9	612.3
177.5°	604.9	604.9	604.9	604.9	603.7	601.4	603.7	604.9	604.9	604.9	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	543.0	546.5	545.2	540.3	546.1	546.1	550.0	550.0	554.9	556.6	559.2
5°	512.2	514.8	517.0	514.8	518.8	525.0	528.5	531.5	538.1	540.8	544.7
7.5°	479.2	484.1	486.3	486.3	492.9	499.9	506.9	511.3	520.6	524.1	528.0
10°	447.1	452.8	457.2	456.8	467.8	472.2	481.0	491.1	500.3	505.6	511.3
12.5°	413.3	416.4	422.5	431.3	433.9	441.9	452.0	464.7	481.4	486.3	494.6
15°	385.1	393.5	398.3	402.3	408.4	415.9	426.9	439.2	455.9	466.5	475.3
17.5°	361.4	372.4	375.5	374.6	382.5	393.9	406.7	415.9	430.9	443.6	452.0
20°	342.1	346.5	351.7	353.9	360.1	372.4	384.7	395.3	407.6	417.7	427.3
22.5°	322.7	326.2	330.6	334.6	339.4	346.5	358.3	371.5	383.4	393.1	404.0
25°	306.9	309.1	313.0	316.1	321.4	326.2	334.6	349.1	363.2	368.9	378.5
27.5°	291.5	293.3	295.9	299.4	302.0	306.9	314.4	326.2	340.7	346.5	359.6
30°	277.9	279.2	281.8	283.6	284.9	290.6	296.3	305.6	316.6	324.5	334.1
32.5°	265.1	266.4	269.1	269.5	271.3	274.3	279.6	288.0	297.6	304.2	312.6
35°	251.0	251.9	254.6	255.4	256.8	259.4	263.4	269.5	278.3	283.1	290.6
37.5°	240.1	239.6	241.4	242.7	244.5	245.8	247.1	253.2	259.8	264.2	270.0
40°	228.2	227.3	227.7	229.5	230.4	232.1	232.1	238.3	242.7	246.2	250.6
42.5°	216.3	215.9	215.0	215.9	216.8	217.2	217.6	222.0	226.4	229.5	234.3
45°	204.4	204.0	203.1	203.6	203.6	204.4	205.8	207.5	210.6	213.2	215.9
47.5°	193.5	192.6	191.3	190.8	191.7	191.7	191.7	193.5	196.5	197.4	200.0
50°	182.0	180.7	178.9	178.1	178.1	177.6	178.5	178.9	181.6	182.5	184.7
52.5°	169.7	168.8	167.1	165.3	165.8	164.9	165.3	165.8	166.6	167.9	169.3
55°	157.4	155.6	154.3	153.9	152.6	152.6	151.2	153.0	152.6	153.0	154.8
57.5°	145.5	143.8	141.6	140.7	139.4	138.9	138.1	137.6	138.1	139.4	140.7
60°	131.5	130.6	129.3	127.9	127.1	125.7	124.9	124.9	124.4	124.4	124.9
62.5°	117.8	117.4	115.6	115.2	114.3	113.4	112.1	111.2	111.2	112.1	112.6
65°	104.6	104.2	102.9	102.4	100.2	99.4	98.9	98.5	97.6	97.6	97.6
67.5°	92.3	91.0	91.0	88.8	87.1	86.2	85.3	84.9	84.9	84.9	85.3
70°	78.7	78.7	77.4	76.1	74.3	74.7	73.4	72.1	72.1	71.2	71.7
72.5°	65.5	65.1	63.8	63.3	62.0	60.7	59.8	60.7	59.4	58.9	59.4
75°	52.8	52.3	51.4	50.6	51.0	49.7	48.4	47.9	47.9	47.0	47.0
77.5°	40.4	41.3	39.6	39.1	38.3	37.4	36.9	36.5	36.5	36.5	37.4
80°	28.1	28.6	28.6	27.7	28.1	26.8	26.8	26.8	25.5	25.9	26.4
82.5°	18.0	18.0	17.6	18.0	17.6	17.6	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.7	9.2	10.1	9.7	9.7	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	36.9	34.6	36.9	38.1	39.2	38.1	31.2	23.1	17.3	15.6	13.9
92.5°	86.6	99.3	116.6	148.9	177.8	175.5	136.2	92.3	61.2	54.8	48.5
95°	183.5	232.0	302.4	395.9	452.5	400.6	266.6	166.2	113.1	99.2	85.4
97.5°	377.5	494.1	618.7	743.4	737.6	570.2	354.4	214.7	146.6	131.0	115.4
100°	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6	237.8	176.6	160.4	144.3
102.5°	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8	258.6	203.2	187.0	170.8
105°	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5	282.8	228.6	212.4	196.2
107.5°	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2	307.0	254.0	237.8	221.6
110°	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4	331.3	280.5	263.8	247.0

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7	354.4	305.9	288.6	271.3
115°	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0	378.6	329.0	313.4	297.8
117.5°	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5	400.6	354.4	338.2	322.1
120°	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0	423.6	378.6	362.5	346.3
122.5°	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1	445.6	404.0	387.2	370.5
125°	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4	467.5	425.9	409.8	393.6
127.5°	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6	488.3	447.9	431.2	414.4
130°	1064.3	973.1	873.8	772.2	682.2	608.3	550.6	506.7	466.3	450.2	434.0
132.5°	1018.1	936.2	846.1	758.4	681.1	617.6	565.6	522.9	484.8	468.6	452.5
135°	973.1	896.9	820.7	745.7	679.9	624.5	578.3	537.9	501.0	484.8	468.7
137.5°	928.1	865.7	799.9	736.5	679.9	631.4	588.7	550.6	513.7	498.7	483.7
140°	888.8	835.7	780.3	728.4	678.7	636.0	596.8	561.0	526.4	511.4	496.4
142.5°	853.0	809.2	764.2	720.3	678.7	639.5	603.7	569.1	535.6	521.8	507.9
145°	823.0	787.2	749.2	713.4	676.4	641.8	609.5	577.2	546.0	533.3	520.6
147.5°	797.6	768.8	737.6	706.4	673.0	643.0	612.9	584.1	554.1	542.6	531.0
150°	774.6	750.3	724.9	697.2	669.5	641.8	615.3	588.7	562.2	551.8	541.4
152.5°	754.9	735.3	712.2	689.1	663.7	639.5	616.4	593.3	570.2	561.0	551.8
155°	736.5	719.1	700.7	678.7	656.8	637.2	617.6	597.9	578.3	569.6	561.0
157.5°	718.0	703.0	686.8	669.5	649.9	632.6	617.6	601.4	584.1	576.6	569.1
160°	699.5	686.8	674.1	659.1	643.0	629.1	617.6	603.7	589.9	583.6	577.2
162.5°	682.2	671.8	661.4	649.9	637.2	625.6	616.4	604.9	593.3	588.7	584.1
165°	664.9	656.8	648.7	639.5	629.1	621.0	614.1	606.0	595.6	592.2	588.7
167.5°	648.7	643.0	636.0	629.1	622.2	616.4	612.9	606.0	597.9	595.6	593.3
170°	634.9	630.3	626.8	621.0	616.4	612.9	610.6	604.9	599.1	597.4	595.6
172.5°	622.2	618.7	616.4	612.9	609.5	608.3	607.2	603.7	600.2	599.0	597.9
175°	611.8	610.6	609.5	606.0	604.9	603.7	604.9	602.6	600.2	599.7	599.1
177.5°	604.9	603.7	603.7	601.4	600.2	601.4	603.7	601.4	600.2	600.2	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	572.0	572.0	572.0	572.0
2.5°	561.4	561.4	568.0	575.1
5°	549.1	552.2	562.8	572.4
7.5°	537.3	542.5	555.7	568.0
10°	522.8	529.8	546.1	560.6
12.5°	508.7	515.3	534.2	550.5
15°	488.9	497.3	517.5	537.7
17.5°	469.1	477.5	502.1	525.8
20°	445.8	456.8	484.5	516.2
22.5°	424.3	437.9	468.7	494.2
25°	400.5	421.6	450.2	483.2
27.5°	379.4	400.5	429.5	463.0
30°	355.7	377.2	407.1	437.9
32.5°	332.8	352.6	381.6	419.4
35°	309.1	328.0	356.1	394.4
37.5°	287.5	306.0	336.8	372.0
40°	266.4	285.8	312.2	347.3
42.5°	246.6	263.8	287.5	322.7
45°	228.6	240.9	262.9	295.9
47.5°	209.7	220.7	240.9	273.9
50°	192.1	201.4	219.0	249.7
52.5°	175.0	182.9	199.2	223.8
55°	159.6	167.1	178.9	203.1
57.5°	143.8	149.5	160.9	180.3
60°	128.4	133.7	142.9	158.7
62.5°	113.0	117.4	126.2	138.9
65°	99.4	102.9	109.5	120.5
67.5°	86.2	88.4	93.6	102.4
70°	73.4	75.2	79.6	86.6
72.5°	59.8	61.6	66.4	71.2
75°	48.4	48.8	52.3	56.3
77.5°	37.8	37.4	40.0	43.1
80°	25.9	27.3	29.5	30.8
82.5°	17.6	18.0	18.9	19.8
85°	9.7	10.1	10.1	11.4
87.5°	4.0	4.4	4.4	4.8
90°	11.5	9.2	4.6	1.2
92.5°	39.2	33.5	24.2	17.3
95°	67.0	56.6	45.0	40.4
97.5°	94.7	79.6	67.0	60.0
100°	121.2	102.7	92.3	88.9
102.5°	146.6	128.1	117.7	115.4
105°	170.8	153.5	145.4	140.8
107.5°	196.2	180.1	172.0	168.5
110°	222.8	207.8	200.9	196.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	248.2	234.3	226.2	221.6
115°	274.7	260.9	254.0	248.2
117.5°	300.1	287.4	280.5	275.9
120°	323.2	312.8	305.9	301.3
122.5°	347.5	335.9	329.0	325.5
125°	370.5	356.7	349.8	346.3
127.5°	392.5	377.5	368.2	363.6
130°	410.9	394.8	383.2	378.6
132.5°	428.3	410.9	398.2	392.5
135°	442.1	424.8	410.9	406.3
137.5°	457.1	438.6	424.8	419.0
140°	471.0	452.5	438.6	434.0
142.5°	483.7	465.2	452.5	449.0
145°	497.5	480.2	468.7	464.0
147.5°	511.4	495.2	483.7	480.2
150°	524.1	509.1	499.8	496.4
152.5°	535.6	522.9	513.7	512.5
155°	548.3	535.6	528.7	527.5
157.5°	558.7	547.1	541.4	540.2
160°	567.9	558.7	554.1	552.9
162.5°	576.0	569.1	564.5	565.6
165°	582.9	576.0	573.7	574.9
167.5°	588.7	584.1	581.8	582.9
170°	593.3	589.9	588.7	591.0
172.5°	596.8	593.3	594.5	595.6
175°	599.1	596.8	597.9	599.1
177.5°	600.2	597.9	599.1	601.4
180°	600.2	600.2	600.2	600.2

TEST NUMBER: P998124

CATALOG NUMBER: SA2XXDIP-B290D1080UB40-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.23	10.88	11.39	12.03	13.64	7.73	8.38	8.89	9.52	11.13
	3H	11.03	11.61	12.20	12.76	14.39	9.05	9.64	10.22	10.79	12.41
	4H	11.19	11.74	12.36	12.89	14.52	9.51	10.06	10.68	11.21	12.84
	6H	11.22	11.73	12.41	12.88	14.52	9.80	10.31	10.99	11.47	13.11
	8H	11.19	11.68	12.38	12.85	14.48	9.88	10.36	11.07	11.53	13.17
	12H	11.15	11.61	12.34	12.77	14.43	9.92	10.37	11.11	11.54	13.19
4H	2H	10.25	10.80	11.43	11.95	13.58	8.15	8.70	9.33	9.85	11.48
	3H	11.21	11.67	12.40	12.85	14.49	9.59	10.05	10.78	11.23	12.87
	4H	11.48	11.90	12.67	13.07	14.73	10.11	10.54	11.30	11.70	13.36
	6H	11.60	11.96	12.79	13.15	14.80	10.48	10.84	11.68	12.03	13.68
	8H	11.59	11.93	12.78	13.11	14.77	10.59	10.93	11.78	12.11	13.77
	12H	11.54	11.85	12.75	13.04	14.71	10.63	10.94	11.84	12.13	13.80
8H	4H	11.47	11.81	12.66	12.99	14.65	10.24	10.58	11.43	11.76	13.42
	6H	11.64	11.92	12.85	13.14	14.80	10.67	10.95	11.88	12.17	13.83
	8H	11.67	11.91	12.89	13.11	14.79	10.82	11.06	12.03	12.26	13.94
	12H	11.65	11.86	12.87	13.06	14.77	10.90	11.11	12.12	12.31	14.02
12H	4H	11.42	11.73	12.63	12.92	14.59	10.20	10.51	11.41	11.70	13.37
	6H	11.62	11.86	12.84	13.06	14.74	10.67	10.91	11.88	12.11	13.79
	8H	11.64	11.86	12.86	13.05	14.77	10.81	11.03	12.03	12.22	13.94