

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998343

Luminaire Tested: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998343
REPORT IS A COMBINATION OF REPORTS P984083 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4546.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	45	44	32	31	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9105	9105	9105	9105
5°	9126	9708	9161	7724
10°	9021	10597	9077	6367
15°	8802	11178	8924	5364
20°	8664	10495	8664	4662
25°	8389	9016	8427	4169
30°	7933	7088	8085	3777
35°	7532	4901	7657	3455
40°	7070	3701	7148	3199
45°	6497	3040	6604	2922
50°	6005	2670	6017	2675
55°	5441	2274	5478	2407
60°	4843	1899	4910	2101
65°	4305	1545	4383	1794
70°	3772	1212	3867	1447
75°	3166	880	3289	1049
80°	2467	557	2651	622
85°	1624	280	1752	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9412 cd/sqm

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	1.2
10°-20°	159.5	3.5
20°-30°	231.4	5.1
30°-40°	244.0	5.4
40°-50°	215.9	4.7
50°-60°	172.4	3.8
60°-70°	117.1	2.6
70°-80°	59.9	1.3
80°-90°	17.5	0.4
90°-100°	72.4	1.6
100°-110°	230.3	5.1
110°-120°	394.0	8.7
120°-130°	518.2	11.4
130°-140°	581.7	12.8
140°-150°	570.4	12.5
150°-160°	478.5	10.5
160°-170°	317.3	7.0
170°-180°	110.9	2.4
0°-30°	445.7	9.8
0°-40°	689.6	15.2
0°-60°	1077.9	23.7
0°-90°	1272.3	28.0
90°-120°	696.7	15.3
90°-150°	2367.0	52.1
90°-180°	3274.0	72.0
0°-180°	4546.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	575	575	575	575	575	
5°	576	642	578	511	576	55
15°	541	790	548	379	541	153
25°	486	658	488	304	486	222
35°	397	358	403	252	397	248
45°	298	216	302	207	298	231
55°	204	152	206	160	204	182
65°	121	93	123	108	121	120
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	34	1	34	1	4
95°	51	61	51	61	51	57
105°	212	219	212	219	212	224
115°	395	395	395	395	395	391
125°	575	577	575	577	575	514
135°	744	753	744	753	744	575
145°	903	913	903	913	903	564
155°	1033	1040	1033	1040	1033	475
165°	1124	1124	1124	1124	1124	317
175°	1169	1165	1169	1165	1169	111
180°	1171	1171	1171	1171	1171	

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	578.3	579.6	581.8	582.2	586.7	590.2	594.2	594.2	595.5	595.1	591.5
5°	575.6	579.6	585.3	590.2	598.2	601.7	607.0	611.0	614.5	617.2	616.7
7.5°	571.2	578.3	586.7	595.9	606.6	612.7	620.3	627.3	632.2	636.6	639.7
10°	563.7	575.6	587.1	599.5	613.2	621.6	630.4	639.7	647.2	655.6	663.6
12.5°	553.5	570.7	584.9	601.3	618.1	627.3	641.5	648.6	663.1	684.4	690.1
15°	540.7	564.1	577.4	598.2	620.3	627.8	647.2	658.7	688.8	702.1	718.0
17.5°	528.7	554.8	572.5	596.4	618.1	632.6	651.7	675.1	700.3	719.3	737.0
20°	519.0	544.2	565.4	592.0	619.4	637.9	657.8	686.1	713.5	733.0	746.7
22.5°	496.9	529.2	553.9	583.6	616.7	642.4	661.4	692.3	721.9	733.9	745.8
25°	485.9	513.7	542.5	576.1	615.0	645.5	661.8	696.3	722.4	726.8	729.5
27.5°	465.5	496.9	530.5	569.0	614.5	640.2	660.9	692.3	713.1	710.0	702.1
30°	440.3	478.8	515.9	557.5	608.3	636.2	655.6	684.4	695.0	679.1	664.9
32.5°	421.8	458.0	499.1	547.3	601.3	627.8	646.8	669.3	671.5	642.8	618.9
35°	396.6	436.8	483.2	534.1	589.3	613.2	630.9	644.6	634.0	593.7	565.4
37.5°	374.0	413.8	463.3	515.0	573.0	596.4	610.5	612.7	586.7	551.3	509.7
40°	349.3	390.4	442.1	496.5	554.8	575.2	584.0	577.4	539.8	498.7	450.5
42.5°	324.5	365.2	420.9	476.6	531.8	549.1	552.6	534.5	488.5	440.3	384.6
45°	297.5	340.0	395.7	451.8	505.3	515.0	515.5	489.4	435.0	384.6	332.9
47.5°	275.4	314.8	370.0	426.2	471.3	477.9	475.3	445.2	386.0	329.4	284.3
50°	251.1	288.7	343.5	398.8	437.2	439.0	432.4	389.5	331.6	279.8	244.0
52.5°	225.0	263.0	313.4	366.5	401.0	398.3	385.5	339.5	285.2	242.3	214.9
55°	204.2	237.8	285.2	336.9	361.2	353.7	339.5	292.7	249.8	213.5	189.7
57.5°	181.3	210.9	257.3	302.4	316.5	309.5	295.3	251.6	211.8	184.4	168.4
60°	159.6	186.6	227.2	264.8	275.9	268.4	252.0	212.6	183.9	160.9	149.0
62.5°	139.7	163.1	197.2	231.7	236.1	228.6	214.4	182.6	157.8	139.7	130.9
65°	121.1	143.2	170.6	196.7	200.7	192.8	178.2	155.2	134.4	122.9	114.5
67.5°	103.0	120.7	145.0	164.0	166.2	158.7	146.8	128.2	115.4	103.0	96.8
70°	87.1	100.4	119.4	134.8	135.7	128.7	122.5	105.7	95.9	87.1	82.2
72.5°	71.6	80.9	95.5	107.0	107.4	103.0	97.3	86.7	78.3	72.1	67.2
75°	56.6	64.5	73.4	83.6	83.1	79.6	75.2	68.5	61.5	57.5	55.3
77.5°	43.3	48.2	55.3	61.9	61.9	60.1	57.5	52.6	48.2	44.2	42.0
80°	30.9	34.0	39.8	42.0	42.9	42.4	40.2	36.7	34.9	31.8	30.9
82.5°	19.9	22.1	24.8	27.0	28.3	27.4	27.0	25.2	22.5	21.7	20.8
85°	11.5	12.4	13.7	15.0	15.5	15.0	15.9	14.6	13.3	13.3	12.8
87.5°	4.9	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	1.0	3.6	6.2	8.9	11.5	12.8	15.2	20.1	24.9	29.8	34.6
92.5°	21.7	23.5	25.2	27.0	28.7	29.6	29.7	29.9	30.2	30.4	30.6
95°	51.4	53.6	55.8	58.0	60.2	61.3	61.5	61.9	62.4	62.8	63.2
97.5°	86.0	88.0	90.0	91.9	93.9	94.9	95.3	96.2	97.1	97.9	98.8
100°	125.5	127.3	129.0	130.8	132.5	133.4	133.7	134.4	135.1	135.7	136.4
102.5°	167.0	168.3	169.6	170.9	172.2	172.9	173.3	174.2	175.1	176.0	176.9
105°	212.4	213.1	213.7	214.4	215.1	215.4	215.6	216.1	216.5	217.0	217.4
107.5°	257.9	258.8	259.7	260.6	261.5	261.9	261.9	261.9	261.9	261.9	261.9
110°	301.4	302.7	304.0	305.3	306.6	307.3	307.3	307.3	307.3	307.3	307.3

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	348.8	350.1	351.4	352.7	354.0	354.7	354.6	354.4	354.1	353.9	353.7
115°	395.2	396.5	397.9	399.2	400.5	401.2	401.0	400.5	400.1	399.6	399.2
117.5°	441.7	443.5	445.2	447.0	448.7	449.6	449.1	448.0	446.9	445.8	444.7
120°	488.1	489.9	491.6	493.4	495.1	496.0	495.1	493.4	491.6	489.9	488.1
122.5°	530.6	532.8	535.0	537.2	539.4	540.5	540.0	538.9	537.8	536.7	535.6
125°	575.1	577.1	579.1	581.0	583.0	584.0	583.7	583.0	582.3	581.7	581.0
127.5°	618.6	621.0	623.4	625.8	628.2	629.4	629.0	628.1	627.2	626.4	625.5
130°	659.1	661.9	664.8	667.6	670.5	671.9	671.7	671.2	670.8	670.3	669.9
132.5°	704.5	706.7	708.9	711.1	713.3	714.4	714.5	714.7	715.0	715.2	715.4
135°	744.1	746.5	748.9	751.3	753.7	754.9	755.1	755.6	756.0	756.5	756.9
137.5°	787.5	789.5	791.5	793.4	795.4	796.4	796.6	797.1	797.5	798.0	798.4
140°	826.1	828.1	830.1	832.0	834.0	835.0	835.5	836.6	837.7	838.8	839.9
142.5°	865.6	867.6	869.6	871.5	873.5	874.5	874.8	875.5	876.1	876.8	877.4
145°	903.1	904.7	906.2	907.8	909.3	910.1	910.8	912.1	913.4	914.7	916.0
147.5°	936.7	938.7	940.7	942.6	944.6	945.6	946.0	946.9	947.8	948.7	949.6
150°	971.3	972.6	973.9	975.2	976.5	977.2	977.6	978.5	979.4	980.3	981.2
152.5°	1002.0	1003.3	1004.6	1005.9	1007.2	1007.9	1008.4	1009.5	1010.6	1011.7	1012.8
155°	1032.6	1033.2	1033.9	1034.5	1035.2	1035.5	1035.8	1036.5	1037.2	1037.8	1038.5
157.5°	1059.3	1059.7	1060.1	1060.6	1061.0	1061.2	1061.4	1061.9	1062.3	1062.8	1063.2
160°	1083.0	1083.4	1083.9	1084.3	1084.8	1085.0	1085.1	1085.3	1085.5	1085.7	1085.9
162.5°	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.8	1105.0	1105.3	1105.5	1105.7
165°	1123.5	1123.3	1123.1	1122.8	1122.6	1122.5	1122.5	1122.5	1122.5	1122.5	1122.5
167.5°	1140.3	1139.6	1139.0	1138.3	1137.6	1137.3	1137.3	1137.3	1137.3	1137.3	1137.3
170°	1153.1	1152.5	1151.8	1151.2	1150.5	1150.2	1150.1	1149.9	1149.6	1149.4	1149.2
172.5°	1162.0	1161.4	1160.7	1160.1	1159.4	1159.1	1159.0	1158.8	1158.5	1158.3	1158.1
175°	1168.9	1168.3	1167.6	1167.0	1166.3	1166.0	1165.8	1165.3	1164.9	1164.4	1164.0
177.5°	1172.9	1172.2	1171.6	1170.9	1170.2	1169.9	1169.7	1169.3	1168.8	1168.4	1168.0
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	597.7	598.2	599.0	603.5	605.7	606.1	604.3	608.3	609.7	608.3	607.4
5°	626.0	628.7	634.0	639.7	639.3	639.7	642.4	645.0	645.9	642.4	643.7
7.5°	650.8	656.1	661.8	670.7	670.7	675.1	676.9	679.1	684.4	681.7	680.8
10°	679.1	686.1	696.7	710.9	711.3	715.8	720.2	727.3	729.5	727.7	728.6
12.5°	714.4	728.1	729.0	744.5	751.6	752.5	759.5	758.2	762.6	762.6	770.1
15°	729.9	751.1	763.1	778.1	782.5	777.2	783.0	789.1	789.6	789.6	789.1
17.5°	757.8	766.2	778.1	786.1	787.8	787.8	788.3	790.9	789.1	785.6	788.3
20°	763.5	767.0	771.5	770.6	771.5	767.0	762.6	758.2	758.6	756.4	763.1
22.5°	752.9	752.0	741.8	735.2	735.2	726.4	718.0	714.0	710.0	711.3	713.5
25°	726.4	712.7	700.3	690.6	688.3	674.2	662.7	659.2	652.5	657.8	658.7
27.5°	683.9	668.5	648.6	640.2	628.7	622.9	615.0	604.3	590.6	598.6	597.3
30°	638.4	615.4	599.0	578.7	560.6	559.3	544.2	526.5	519.5	519.5	523.4
32.5°	587.5	557.0	533.2	504.4	486.8	479.2	461.1	443.4	447.4	434.1	439.0
35°	528.3	488.1	458.0	430.2	416.9	408.1	384.6	374.9	364.3	358.1	369.6
37.5°	471.7	425.3	386.8	356.3	351.5	335.6	319.6	313.4	307.3	309.9	309.5
40°	402.8	361.6	327.2	303.3	294.9	287.4	276.8	269.2	265.3	267.5	267.9
42.5°	340.4	305.9	280.3	263.5	256.4	251.1	245.8	239.6	238.3	238.3	240.1
45°	292.2	263.9	246.7	233.0	229.0	225.0	221.0	218.4	217.5	215.7	217.1
47.5°	253.8	231.2	220.6	210.4	206.0	205.1	201.6	200.3	198.5	198.1	198.5
50°	221.5	207.3	197.6	191.9	188.8	187.4	185.7	183.0	182.1	184.4	183.5
52.5°	198.9	185.7	180.4	174.6	172.9	171.1	168.4	168.9	168.4	167.6	167.6
55°	176.4	168.0	162.7	158.3	157.8	156.1	153.9	153.0	152.5	151.6	153.0
57.5°	158.3	151.6	146.8	142.8	141.0	141.0	138.8	137.1	137.1	136.6	137.1
60°	140.1	133.5	130.4	126.4	125.1	124.7	123.3	122.5	121.1	121.1	121.1
62.5°	123.3	118.0	114.5	111.0	111.4	109.2	107.4	106.5	106.5	107.0	107.0
65°	107.4	103.9	99.5	96.4	95.5	95.1	94.2	93.7	92.4	93.3	93.3
67.5°	92.8	88.0	85.3	84.0	82.7	82.2	81.3	80.5	80.0	79.6	80.5
70°	78.3	74.3	72.1	71.2	69.9	69.4	69.0	67.6	68.1	68.5	69.0
72.5°	65.0	61.5	61.0	58.4	58.4	58.4	56.6	57.5	57.0	56.1	57.0
75°	51.3	49.5	48.6	47.3	47.7	47.3	46.9	45.5	45.5	46.0	46.4
77.5°	40.7	38.9	38.5	37.1	36.3	37.1	36.3	35.8	35.8	36.3	36.3
80°	30.1	29.2	27.9	27.9	27.9	27.4	27.4	27.4	27.0	26.5	27.0
82.5°	19.9	19.9	19.5	19.0	19.5	18.6	19.0	19.0	19.0	19.0	19.0
85°	12.8	12.4	12.4	11.9	11.9	11.9	12.4	11.5	11.5	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	34.2	33.7	33.3	32.8	32.6	32.7	32.9	33.2	33.4	33.6	33.4
92.5°	30.8	31.0	31.3	31.5	31.6	31.6	31.6	31.6	31.6	31.6	31.6
95°	63.2	63.2	63.2	63.2	63.2	63.0	62.6	62.1	61.7	61.3	61.7
97.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8
100°	136.4	136.4	136.4	136.4	136.4	136.3	136.1	135.8	135.6	135.4	135.6
102.5°	177.1	177.3	177.6	177.8	177.9	177.8	177.6	177.3	177.1	176.9	177.1
105°	217.8	218.3	218.7	219.2	219.4	219.4	219.4	219.4	219.4	219.4	219.4
107.5°	262.1	262.3	262.5	262.7	262.8	262.3	261.2	260.1	259.0	257.9	259.0
110°	307.3	307.3	307.3	307.3	307.3	307.0	306.3	305.6	305.0	304.3	305.0

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	353.1	352.4	351.8	351.1	350.8	350.6	350.1	349.7	349.2	348.8	349.2
115°	399.0	398.8	398.5	398.3	398.2	397.9	397.2	396.5	395.9	395.2	395.9
117.5°	444.0	443.4	442.7	442.0	441.7	441.4	440.7	440.0	439.4	438.7	439.4
120°	488.1	488.1	488.1	488.1	488.1	487.8	487.1	486.5	485.8	485.2	485.8
122.5°	534.9	534.3	533.6	532.9	532.6	532.4	531.9	531.5	531.0	530.6	531.0
125°	580.3	579.7	579.0	578.3	578.0	577.9	577.7	577.5	577.3	577.1	577.3
127.5°	624.6	623.7	622.8	621.9	621.5	621.2	620.5	619.9	619.2	618.6	619.2
130°	669.5	669.1	668.6	668.2	668.0	667.6	666.7	665.8	664.9	664.0	664.9
132.5°	714.3	713.2	712.1	711.0	710.5	710.2	709.5	708.8	708.2	707.5	708.2
135°	756.7	756.5	756.2	756.0	755.9	755.6	754.9	754.2	753.6	752.9	753.6
137.5°	798.2	798.0	797.7	797.5	797.4	797.0	796.1	795.2	794.4	793.5	794.4
140°	839.9	839.9	839.9	839.9	839.9	839.5	838.6	837.7	836.8	835.9	836.8
142.5°	877.6	877.8	878.1	878.3	878.4	878.0	877.1	876.2	875.4	874.5	875.4
145°	916.2	916.4	916.7	916.9	917.0	916.6	915.7	914.8	913.9	913.0	913.9
147.5°	950.0	950.5	950.9	951.4	951.6	951.2	950.3	949.4	948.5	947.6	948.5
150°	981.9	982.5	983.2	983.9	984.2	983.9	983.2	982.5	981.9	981.2	981.9
152.5°	1013.7	1014.6	1015.5	1016.4	1016.8	1016.4	1015.5	1014.6	1013.7	1012.8	1013.7
155°	1039.6	1040.7	1041.8	1042.9	1043.5	1043.2	1042.5	1041.8	1041.2	1040.5	1041.2
157.5°	1064.7	1066.3	1067.8	1069.3	1070.1	1069.6	1068.5	1067.4	1066.3	1065.2	1066.3
160°	1087.2	1088.6	1089.9	1091.2	1091.9	1091.5	1090.6	1089.7	1088.8	1087.9	1088.8
162.5°	1107.2	1108.8	1110.3	1111.8	1112.6	1112.1	1111.0	1109.9	1108.8	1107.7	1108.8
165°	1124.0	1125.6	1127.1	1128.6	1129.4	1128.9	1127.8	1126.7	1125.6	1124.5	1125.6
167.5°	1138.8	1140.4	1141.9	1143.4	1144.2	1143.7	1142.6	1141.5	1140.4	1139.3	1140.4
170°	1150.7	1152.3	1153.8	1155.3	1156.1	1155.4	1154.1	1152.8	1151.5	1150.2	1151.5
172.5°	1159.6	1161.2	1162.7	1164.2	1165.0	1164.3	1163.0	1161.7	1160.4	1159.1	1160.4
175°	1165.5	1167.1	1168.6	1170.1	1170.9	1170.2	1168.9	1167.6	1166.3	1165.0	1166.3
177.5°	1169.3	1170.6	1171.9	1173.2	1173.9	1173.2	1171.9	1170.6	1169.3	1168.0	1169.3
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	609.7	606.6	603.9	604.3	606.6	604.8	600.4	594.6	592.4	589.8	592.4
5°	646.3	643.7	638.4	638.8	637.5	635.7	628.7	619.8	619.8	612.7	611.9
7.5°	682.6	678.6	675.1	674.2	669.3	665.8	659.6	647.2	642.4	634.0	629.1
10°	723.3	720.2	716.2	711.3	708.7	702.5	692.3	674.2	665.4	653.9	645.5
12.5°	764.4	763.9	755.1	745.4	744.9	735.2	728.1	703.8	691.9	676.4	656.5
15°	790.5	788.3	783.4	778.5	779.9	769.3	753.3	724.6	716.6	698.1	676.9
17.5°	790.0	790.0	788.7	787.8	786.5	783.4	774.6	755.5	742.7	719.3	699.4
20°	764.8	770.6	771.9	771.5	775.9	778.1	777.7	765.7	755.5	734.8	714.4
22.5°	714.4	727.7	733.4	737.0	746.3	751.1	762.6	758.2	755.5	740.1	722.8
25°	667.6	672.0	689.2	690.1	702.9	714.9	726.4	733.9	743.6	737.9	723.3
27.5°	607.0	617.2	629.5	638.8	641.5	665.8	684.8	699.0	721.1	722.8	718.0
30°	538.5	543.3	563.7	576.1	590.2	607.9	635.3	659.6	679.5	697.6	703.8
32.5°	454.9	474.8	486.8	501.8	514.2	545.5	579.1	610.5	633.5	664.0	677.3
35°	378.4	393.9	414.2	420.4	443.0	469.5	513.3	553.5	588.4	619.4	646.3
37.5°	315.2	327.6	349.3	359.0	372.2	406.3	443.0	492.9	534.9	573.0	606.6
40°	271.9	281.2	297.5	300.6	311.7	342.6	372.2	419.1	474.8	526.1	562.8
42.5°	242.3	246.7	257.7	261.7	268.8	289.6	316.1	360.3	412.0	465.1	516.8
45°	221.0	224.1	230.8	234.3	243.2	252.4	274.1	309.5	350.1	403.6	459.3
47.5°	202.0	206.0	208.7	210.9	215.7	225.9	240.1	266.1	305.0	354.1	408.1
50°	186.1	187.4	192.3	192.8	195.8	202.5	215.7	231.7	262.6	302.4	354.6
52.5°	170.2	171.5	174.6	177.7	179.0	184.4	193.2	206.5	229.4	260.8	307.3
55°	154.3	156.1	159.2	161.4	162.7	167.1	172.4	185.2	203.4	225.5	263.5
57.5°	138.4	142.4	143.2	144.6	146.8	151.6	156.5	164.0	178.2	198.5	226.4
60°	123.3	124.7	127.8	129.1	131.3	134.0	140.1	145.9	156.1	172.0	197.2
62.5°	107.9	111.0	112.3	113.6	115.4	118.5	122.5	128.7	137.5	150.3	170.2
65°	94.6	95.1	97.7	99.5	101.2	103.5	107.4	113.2	118.5	130.4	145.0
67.5°	81.8	82.7	83.6	85.3	87.5	89.7	93.3	96.4	103.0	111.0	122.5
70°	69.4	69.4	71.6	72.9	72.5	75.2	77.8	81.3	86.2	93.7	103.0
72.5°	58.4	57.9	59.7	60.1	61.0	62.8	64.5	68.1	70.7	76.5	83.6
75°	46.4	47.3	48.2	48.2	49.5	50.8	52.6	54.4	57.5	61.0	66.3
77.5°	36.7	36.7	37.6	38.0	39.3	38.9	40.7	42.4	44.7	47.7	51.7
80°	27.0	27.9	27.9	27.9	28.3	28.7	30.5	31.8	33.2	35.4	37.1
82.5°	19.0	19.0	19.9	19.9	19.9	20.8	20.8	21.2	22.1	23.4	24.8
85°	11.9	11.9	11.9	12.4	11.9	12.4	13.3	12.8	13.3	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	33.2	32.9	32.7	32.6	32.8	33.3	33.7	34.2	34.6	29.8	24.9
92.5°	31.6	31.6	31.6	31.6	31.5	31.3	31.0	30.8	30.6	30.4	30.2
95°	62.1	62.6	63.0	63.2	63.2	63.2	63.2	63.2	63.2	62.8	62.4
97.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	97.9	97.1
100°	135.8	136.1	136.3	136.4	136.4	136.4	136.4	136.4	136.4	135.7	135.1
102.5°	177.3	177.6	177.8	177.9	177.8	177.6	177.3	177.1	176.9	176.0	175.1
105°	219.4	219.4	219.4	219.4	219.2	218.7	218.3	217.8	217.4	217.0	216.5
107.5°	260.1	261.2	262.3	262.8	262.7	262.5	262.3	262.1	261.9	261.9	261.9
110°	305.6	306.3	307.0	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	349.7	350.1	350.6	350.8	351.1	351.8	352.4	353.1	353.7	353.9	354.1
115°	396.5	397.2	397.9	398.2	398.3	398.5	398.8	399.0	399.2	399.6	400.1
117.5°	440.0	440.7	441.4	441.7	442.0	442.7	443.4	444.0	444.7	445.8	446.9
120°	486.5	487.1	487.8	488.1	488.1	488.1	488.1	488.1	488.1	489.9	491.6
122.5°	531.5	531.9	532.4	532.6	532.9	533.6	534.3	534.9	535.6	536.7	537.8
125°	577.5	577.7	577.9	578.0	578.3	579.0	579.7	580.3	581.0	581.7	582.3
127.5°	619.9	620.5	621.2	621.5	621.9	622.8	623.7	624.6	625.5	626.4	627.2
130°	665.8	666.7	667.6	668.0	668.2	668.6	669.1	669.5	669.9	670.3	670.8
132.5°	708.8	709.5	710.2	710.5	711.0	712.1	713.2	714.3	715.4	715.2	715.0
135°	754.2	754.9	755.6	755.9	756.0	756.2	756.5	756.7	756.9	756.5	756.0
137.5°	795.2	796.1	797.0	797.4	797.5	797.7	798.0	798.2	798.4	798.0	797.5
140°	837.7	838.6	839.5	839.9	839.9	839.9	839.9	839.9	839.9	838.8	837.7
142.5°	876.2	877.1	878.0	878.4	878.3	878.1	877.8	877.6	877.4	876.8	876.1
145°	914.8	915.7	916.6	917.0	916.9	916.7	916.4	916.2	916.0	914.7	913.4
147.5°	949.4	950.3	951.2	951.6	951.4	950.9	950.5	950.0	949.6	948.7	947.8
150°	982.5	983.2	983.9	984.2	983.9	983.2	982.5	981.9	981.2	980.3	979.4
152.5°	1014.6	1015.5	1016.4	1016.8	1016.4	1015.5	1014.6	1013.7	1012.8	1011.7	1010.6
155°	1041.8	1042.5	1043.2	1043.5	1042.9	1041.8	1040.7	1039.6	1038.5	1037.8	1037.2
157.5°	1067.4	1068.5	1069.6	1070.1	1069.3	1067.8	1066.3	1064.7	1063.2	1062.8	1062.3
160°	1089.7	1090.6	1091.5	1091.9	1091.2	1089.9	1088.6	1087.2	1085.9	1085.7	1085.5
162.5°	1109.9	1111.0	1112.1	1112.6	1111.8	1110.3	1108.8	1107.2	1105.7	1105.5	1105.3
165°	1126.7	1127.8	1128.9	1129.4	1128.6	1127.1	1125.6	1124.0	1122.5	1122.5	1122.5
167.5°	1141.5	1142.6	1143.7	1144.2	1143.4	1141.9	1140.4	1138.8	1137.3	1137.3	1137.3
170°	1152.8	1154.1	1155.4	1156.1	1155.3	1153.8	1152.3	1150.7	1149.2	1149.4	1149.6
172.5°	1161.7	1163.0	1164.3	1165.0	1164.2	1162.7	1161.2	1159.6	1158.1	1158.3	1158.5
175°	1167.6	1168.9	1170.2	1170.9	1170.1	1168.6	1167.1	1165.5	1164.0	1164.4	1164.9
177.5°	1170.6	1171.9	1173.2	1173.9	1173.2	1171.9	1170.6	1169.3	1168.0	1168.4	1168.8
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	590.2	588.0	586.7	587.5	584.9	578.3	578.3	580.5	577.8	575.2	571.2
5°	606.6	602.1	599.5	599.0	592.9	582.2	580.0	577.8	572.1	565.9	559.3
7.5°	622.5	614.5	610.1	607.0	598.2	584.5	578.7	573.8	564.6	555.3	546.9
10°	635.7	624.2	618.9	614.1	602.6	585.3	576.1	567.2	555.3	543.3	532.7
12.5°	646.3	633.1	626.5	619.4	605.2	582.7	571.2	557.0	545.1	529.2	518.6
15°	664.0	636.6	630.4	623.8	609.2	578.3	564.1	548.2	531.8	510.6	499.1
17.5°	678.2	641.5	641.0	626.9	607.9	576.5	554.8	534.1	516.4	495.2	477.0
20°	686.6	649.0	641.9	627.3	603.5	564.6	542.0	519.0	500.0	474.4	456.2
22.5°	693.7	659.6	641.0	623.4	594.2	560.6	527.4	505.8	479.7	451.8	434.6
25°	696.3	661.8	642.4	622.0	587.5	549.1	511.5	488.1	458.9	433.7	410.3
27.5°	696.7	661.4	637.5	616.3	578.3	534.1	495.6	470.8	438.6	409.4	386.0
30°	692.3	656.5	634.9	611.9	569.4	520.3	476.1	448.7	414.2	385.1	360.8
32.5°	679.1	646.8	629.1	603.9	557.9	501.3	457.6	427.1	390.8	362.1	338.6
35°	657.0	634.9	615.4	592.0	542.9	483.7	439.0	403.2	366.5	339.1	317.0
37.5°	629.5	617.6	599.5	576.5	525.7	467.7	418.2	378.4	341.7	315.2	293.6
40°	592.4	595.5	577.8	557.0	505.3	446.1	391.3	353.2	318.8	294.0	272.8
42.5°	552.2	565.0	554.8	534.9	482.8	422.2	371.4	329.4	295.8	270.1	252.4
45°	508.9	531.0	524.8	510.2	459.3	397.0	343.1	302.4	272.8	248.0	232.5
47.5°	461.6	492.9	492.9	482.3	433.3	371.8	318.8	277.2	248.0	230.3	215.3
50°	413.4	448.7	454.5	447.4	404.1	343.1	289.1	251.6	226.4	209.1	198.1
52.5°	363.0	404.1	414.7	411.2	373.1	315.7	264.8	228.1	205.1	190.1	180.4
55°	314.8	362.5	374.0	375.3	340.0	285.6	237.8	205.6	183.5	173.3	164.9
57.5°	269.2	315.2	328.0	330.2	306.4	258.2	212.6	184.4	164.5	156.1	149.4
60°	230.3	268.8	285.6	290.5	269.7	226.4	189.2	161.8	146.8	138.8	132.6
62.5°	198.5	229.4	247.1	248.5	239.2	198.5	164.9	141.9	129.1	122.0	118.9
65°	167.6	195.4	206.0	211.3	203.8	172.0	142.4	123.3	113.2	107.0	103.9
67.5°	142.8	160.5	169.3	176.4	168.9	145.0	121.1	105.7	98.1	92.0	90.2
70°	117.2	131.7	138.4	145.5	138.8	120.7	103.5	89.3	82.7	77.8	75.6
72.5°	93.7	105.2	111.4	115.8	111.9	96.8	82.7	72.9	68.1	64.5	63.2
75°	74.3	82.2	85.8	88.9	87.1	75.6	66.8	58.8	54.4	51.3	50.4
77.5°	56.6	62.3	66.3	67.2	65.0	57.5	50.0	45.1	41.6	39.8	38.9
80°	40.2	43.8	46.0	47.3	45.1	42.0	36.7	33.2	30.1	27.9	27.4
82.5°	27.0	28.7	30.5	30.1	29.2	26.5	23.4	21.7	20.3	18.6	18.6
85°	15.5	15.9	16.8	17.2	16.8	15.0	13.3	12.4	11.5	10.2	10.2
87.5°	6.6	7.1	7.1	7.5	6.6	6.6	5.7	4.9	4.9	4.4	4.0
90°	20.1	15.2	12.8	11.5	8.9	6.2	3.6	1.0	3.6	6.2	8.9
92.5°	29.9	29.7	29.6	28.7	27.0	25.2	23.5	21.7	23.5	25.2	27.0
95°	61.9	61.5	61.3	60.2	58.0	55.8	53.6	51.4	53.6	55.8	58.0
97.5°	96.2	95.3	94.9	93.9	91.9	90.0	88.0	86.0	88.0	90.0	91.9
100°	134.4	133.7	133.4	132.5	130.8	129.0	127.3	125.5	127.3	129.0	130.8
102.5°	174.2	173.3	172.9	172.2	170.9	169.6	168.3	167.0	168.3	169.6	170.9
105°	216.1	215.6	215.4	215.1	214.4	213.7	213.1	212.4	213.1	213.7	214.4
107.5°	261.9	261.9	261.9	261.5	260.6	259.7	258.8	257.9	258.8	259.7	260.6
110°	307.3	307.3	307.3	306.6	305.3	304.0	302.7	301.4	302.7	304.0	305.3

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	354.4	354.6	354.7	354.0	352.7	351.4	350.1	348.8	350.1	351.4	352.7
115°	400.5	401.0	401.2	400.5	399.2	397.9	396.5	395.2	396.5	397.9	399.2
117.5°	448.0	449.1	449.6	448.7	447.0	445.2	443.5	441.7	443.5	445.2	447.0
120°	493.4	495.1	496.0	495.1	493.4	491.6	489.9	488.1	489.9	491.6	493.4
122.5°	538.9	540.0	540.5	539.4	537.2	535.0	532.8	530.6	532.8	535.0	537.2
125°	583.0	583.7	584.0	583.0	581.0	579.1	577.1	575.1	577.1	579.1	581.0
127.5°	628.1	629.0	629.4	628.2	625.8	623.4	621.0	618.6	621.0	623.4	625.8
130°	671.2	671.7	671.9	670.5	667.6	664.8	661.9	659.1	661.9	664.8	667.6
132.5°	714.7	714.5	714.4	713.3	711.1	708.9	706.7	704.5	706.7	708.9	711.1
135°	755.6	755.1	754.9	753.7	751.3	748.9	746.5	744.1	746.5	748.9	751.3
137.5°	797.1	796.6	796.4	795.4	793.4	791.5	789.5	787.5	789.5	791.5	793.4
140°	836.6	835.5	835.0	834.0	832.0	830.1	828.1	826.1	828.1	830.1	832.0
142.5°	875.5	874.8	874.5	873.5	871.5	869.6	867.6	865.6	867.6	869.6	871.5
145°	912.1	910.8	910.1	909.3	907.8	906.2	904.7	903.1	904.7	906.2	907.8
147.5°	946.9	946.0	945.6	944.6	942.6	940.7	938.7	936.7	938.7	940.7	942.6
150°	978.5	977.6	977.2	976.5	975.2	973.9	972.6	971.3	972.6	973.9	975.2
152.5°	1009.5	1008.4	1007.9	1007.2	1005.9	1004.6	1003.3	1002.0	1003.3	1004.6	1005.9
155°	1036.5	1035.8	1035.5	1035.2	1034.5	1033.9	1033.2	1032.6	1033.2	1033.9	1034.5
157.5°	1061.9	1061.4	1061.2	1061.0	1060.6	1060.1	1059.7	1059.3	1059.7	1060.1	1060.6
160°	1085.3	1085.1	1085.0	1084.8	1084.3	1083.9	1083.4	1083.0	1083.4	1083.9	1084.3
162.5°	1105.0	1104.8	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7
165°	1122.5	1122.5	1122.5	1122.6	1122.8	1123.1	1123.3	1123.5	1123.3	1123.1	1122.8
167.5°	1137.3	1137.3	1137.3	1137.6	1138.3	1139.0	1139.6	1140.3	1139.6	1139.0	1138.3
170°	1149.9	1150.1	1150.2	1150.5	1151.2	1151.8	1152.5	1153.1	1152.5	1151.8	1151.2
172.5°	1158.8	1159.0	1159.1	1159.4	1160.1	1160.7	1161.4	1162.0	1161.4	1160.7	1160.1
175°	1165.3	1165.8	1166.0	1166.3	1167.0	1167.6	1168.3	1168.9	1168.3	1167.6	1167.0
177.5°	1169.3	1169.7	1169.9	1170.2	1170.9	1171.6	1172.2	1172.9	1172.2	1171.6	1170.9
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	569.0	571.2	570.7	566.3	561.5	557.5	550.0	550.9	548.2	548.6	551.3
5°	554.8	554.8	553.1	546.9	538.9	534.5	526.1	523.9	518.6	518.1	517.7
7.5°	539.8	537.6	535.4	526.5	516.8	509.7	498.2	495.6	490.3	486.8	485.0
10°	522.1	519.0	514.6	504.4	492.5	483.7	471.7	468.2	458.0	453.6	450.9
12.5°	502.7	500.9	493.8	485.4	466.0	456.2	439.0	442.5	432.4	423.5	422.2
15°	483.2	476.6	472.6	458.9	435.5	431.0	417.3	410.3	401.0	393.9	393.9
17.5°	464.2	454.0	445.2	430.6	413.4	401.0	390.8	387.3	375.8	368.7	367.4
20°	439.0	427.5	425.3	404.5	392.6	378.9	369.2	360.3	351.9	348.8	346.6
22.5°	415.1	401.9	398.3	380.6	368.7	355.0	345.3	339.1	332.9	330.7	326.7
25°	389.5	381.5	376.2	357.2	344.0	331.1	324.5	320.1	314.3	313.9	311.2
27.5°	364.7	357.2	351.9	333.8	324.1	312.1	306.8	302.0	298.9	297.5	296.2
30°	343.5	335.1	328.9	315.7	303.7	294.0	289.6	286.5	284.7	282.5	282.1
32.5°	320.1	315.2	306.8	296.6	287.4	278.1	275.4	273.2	270.6	269.7	269.2
35°	300.2	293.6	288.2	276.8	272.8	264.8	261.7	260.0	256.4	255.5	254.6
37.5°	280.7	274.5	268.8	261.7	254.2	249.8	248.0	245.4	243.6	244.0	243.2
40°	261.3	256.4	252.0	244.5	240.1	237.8	234.3	231.7	230.8	231.2	230.8
42.5°	242.3	237.8	235.2	229.4	225.0	222.8	220.6	218.0	219.3	219.3	220.6
45°	225.0	221.0	219.3	214.9	212.2	208.7	206.5	206.0	207.8	207.3	207.3
47.5°	207.3	206.0	203.8	199.8	196.3	194.1	193.6	193.6	195.4	196.3	195.8
50°	193.6	191.0	188.3	185.2	182.6	181.7	180.4	181.3	183.0	183.0	183.9
52.5°	176.4	174.6	173.7	171.1	169.3	169.3	169.3	169.8	171.1	172.4	172.0
55°	161.4	160.0	159.2	157.8	155.6	156.1	155.6	156.5	157.8	159.2	160.0
57.5°	145.5	145.0	144.1	141.9	141.9	141.5	142.8	143.2	145.5	146.3	147.7
60°	131.3	130.0	130.0	128.2	128.2	128.2	129.5	130.9	132.6	133.1	134.0
62.5°	116.3	116.3	115.8	114.5	114.5	115.8	116.3	118.0	118.9	118.9	120.3
65°	102.1	101.7	101.2	101.7	102.1	102.1	103.5	104.3	105.2	105.7	106.1
67.5°	88.0	87.5	88.4	88.0	88.9	90.6	90.2	91.5	92.8	92.8	93.3
70°	74.7	75.6	75.2	76.0	75.6	76.5	77.8	78.3	78.3	78.7	80.0
72.5°	62.3	62.3	62.3	61.9	62.3	63.2	64.1	64.5	65.4	65.9	67.2
75°	50.4	50.4	49.5	50.4	50.4	51.3	52.2	52.2	52.2	53.1	54.4
77.5°	38.0	38.5	38.0	38.9	38.9	39.3	40.2	39.8	40.7	41.1	41.6
80°	27.9	27.4	27.4	27.4	27.9	27.9	28.7	29.2	29.2	30.5	29.6
82.5°	17.7	18.1	17.7	18.1	18.1	18.6	18.1	18.6	19.0	19.9	19.5
85°	10.2	9.7	9.7	10.2	9.7	9.7	10.2	9.7	10.2	9.7	10.2
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.7	2.7	2.7	2.2
90°	11.5	12.8	15.2	20.1	24.9	29.8	34.6	34.2	33.7	33.3	32.8
92.5°	28.7	29.6	29.7	29.9	30.2	30.4	30.6	30.8	31.0	31.3	31.5
95°	60.2	61.3	61.5	61.9	62.4	62.8	63.2	63.2	63.2	63.2	63.2
97.5°	93.9	94.9	95.3	96.2	97.1	97.9	98.8	98.8	98.8	98.8	98.8
100°	132.5	133.4	133.7	134.4	135.1	135.7	136.4	136.4	136.4	136.4	136.4
102.5°	172.2	172.9	173.3	174.2	175.1	176.0	176.9	177.1	177.3	177.6	177.8
105°	215.1	215.4	215.6	216.1	216.5	217.0	217.4	217.8	218.3	218.7	219.2
107.5°	261.5	261.9	261.9	261.9	261.9	261.9	261.9	262.1	262.3	262.5	262.7
110°	306.6	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	354.0	354.7	354.6	354.4	354.1	353.9	353.7	353.1	352.4	351.8	351.1
115°	400.5	401.2	401.0	400.5	400.1	399.6	399.2	399.0	398.8	398.5	398.3
117.5°	448.7	449.6	449.1	448.0	446.9	445.8	444.7	444.0	443.4	442.7	442.0
120°	495.1	496.0	495.1	493.4	491.6	489.9	488.1	488.1	488.1	488.1	488.1
122.5°	539.4	540.5	540.0	538.9	537.8	536.7	535.6	534.9	534.3	533.6	532.9
125°	583.0	584.0	583.7	583.0	582.3	581.7	581.0	580.3	579.7	579.0	578.3
127.5°	628.2	629.4	629.0	628.1	627.2	626.4	625.5	624.6	623.7	622.8	621.9
130°	670.5	671.9	671.7	671.2	670.8	670.3	669.9	669.5	669.1	668.6	668.2
132.5°	713.3	714.4	714.5	714.7	715.0	715.2	715.4	714.3	713.2	712.1	711.0
135°	753.7	754.9	755.1	755.6	756.0	756.5	756.9	756.7	756.5	756.2	756.0
137.5°	795.4	796.4	796.6	797.1	797.5	798.0	798.4	798.2	798.0	797.7	797.5
140°	834.0	835.0	835.5	836.6	837.7	838.8	839.9	839.9	839.9	839.9	839.9
142.5°	873.5	874.5	874.8	875.5	876.1	876.8	877.4	877.6	877.8	878.1	878.3
145°	909.3	910.1	910.8	912.1	913.4	914.7	916.0	916.2	916.4	916.7	916.9
147.5°	944.6	945.6	946.0	946.9	947.8	948.7	949.6	950.0	950.5	950.9	951.4
150°	976.5	977.2	977.6	978.5	979.4	980.3	981.2	981.9	982.5	983.2	983.9
152.5°	1007.2	1007.9	1008.4	1009.5	1010.6	1011.7	1012.8	1013.7	1014.6	1015.5	1016.4
155°	1035.2	1035.5	1035.8	1036.5	1037.2	1037.8	1038.5	1039.6	1040.7	1041.8	1042.9
157.5°	1061.0	1061.2	1061.4	1061.9	1062.3	1062.8	1063.2	1064.7	1066.3	1067.8	1069.3
160°	1084.8	1085.0	1085.1	1085.3	1085.5	1085.7	1085.9	1087.2	1088.6	1089.9	1091.2
162.5°	1104.7	1104.7	1104.8	1105.0	1105.3	1105.5	1105.7	1107.2	1108.8	1110.3	1111.8
165°	1122.6	1122.5	1122.5	1122.5	1122.5	1122.5	1122.5	1124.0	1125.6	1127.1	1128.6
167.5°	1137.6	1137.3	1137.3	1137.3	1137.3	1137.3	1137.3	1138.8	1140.4	1141.9	1143.4
170°	1150.5	1150.2	1150.1	1149.9	1149.6	1149.4	1149.2	1150.7	1152.3	1153.8	1155.3
172.5°	1159.4	1159.1	1159.0	1158.8	1158.5	1158.3	1158.1	1159.6	1161.2	1162.7	1164.2
175°	1166.3	1166.0	1165.8	1165.3	1164.9	1164.4	1164.0	1165.5	1167.1	1168.6	1170.1
177.5°	1170.2	1169.9	1169.7	1169.3	1168.8	1168.4	1168.0	1169.3	1170.6	1171.9	1173.2
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	548.2	549.5	546.4	545.5	546.4	543.3	544.2	545.1	545.1	546.4	547.3
5°	516.4	514.6	511.5	510.6	509.7	511.1	510.2	511.5	511.9	515.0	515.5
7.5°	485.0	482.3	479.7	477.0	476.1	473.9	476.1	476.1	479.2	478.4	480.6
10°	447.8	447.4	443.9	442.5	440.8	437.2	442.1	440.8	443.0	447.0	447.8
12.5°	420.4	415.6	417.8	411.6	413.8	410.3	410.7	410.7	414.2	414.7	413.8
15°	394.4	390.4	384.6	382.0	380.6	378.9	384.6	385.1	382.4	388.6	386.4
17.5°	367.8	367.8	362.5	361.2	357.7	359.4	358.5	359.0	358.1	362.5	364.7
20°	344.8	342.6	340.9	341.3	336.9	336.0	335.1	336.0	339.1	342.2	343.1
22.5°	326.3	324.9	320.5	321.4	317.9	319.2	318.3	320.5	321.0	321.0	324.1
25°	308.6	306.8	307.3	305.5	304.2	304.2	302.8	304.2	305.9	306.8	307.3
27.5°	295.3	294.0	291.8	290.5	291.3	289.1	290.9	292.2	292.2	291.3	292.2
30°	279.4	280.3	280.3	275.9	277.6	276.8	278.1	279.0	279.0	279.4	278.5
32.5°	268.8	266.1	265.7	265.3	265.3	263.5	263.5	264.8	265.3	265.7	267.0
35°	254.6	254.6	252.4	253.8	252.0	252.4	252.0	252.4	253.3	252.0	253.3
37.5°	241.8	242.3	241.4	242.3	242.7	241.8	240.9	242.7	241.8	241.8	240.9
40°	230.8	230.3	230.8	230.8	230.8	231.2	230.3	230.3	230.3	229.4	228.6
42.5°	221.5	218.8	219.7	220.2	218.8	218.8	219.3	218.8	220.2	217.5	217.5
45°	208.2	207.3	207.8	207.8	208.7	207.3	208.2	208.7	207.3	206.9	206.0
47.5°	196.3	197.2	196.3	197.2	197.2	198.1	196.3	196.7	197.2	195.4	194.1
50°	184.4	184.4	185.7	185.2	185.7	184.8	184.8	184.4	184.8	183.9	182.6
52.5°	173.3	172.0	174.2	173.7	173.3	172.9	172.4	172.9	172.0	171.1	171.1
55°	159.6	159.6	160.9	161.4	161.4	160.5	159.6	160.0	159.6	159.2	158.7
57.5°	148.5	146.8	147.7	148.1	148.1	146.8	147.7	146.8	146.8	147.2	145.9
60°	134.4	134.4	133.5	134.8	134.8	134.0	134.0	134.4	133.5	133.1	132.6
62.5°	119.4	119.8	121.1	121.6	122.0	121.1	120.3	120.7	120.7	119.4	119.8
65°	106.5	107.4	109.2	108.8	107.9	108.3	107.4	107.9	106.5	107.0	105.7
67.5°	94.2	93.7	94.2	94.2	95.1	94.6	93.7	93.7	93.3	94.6	93.3
70°	80.9	80.9	80.9	80.9	81.3	81.8	80.9	80.0	80.5	79.6	79.1
72.5°	67.2	67.6	67.2	68.1	66.8	67.6	67.6	67.2	66.8	66.8	66.8
75°	54.4	55.3	53.9	54.4	53.9	54.8	54.4	54.4	53.5	53.1	53.5
77.5°	41.6	42.0	41.1	41.6	41.1	41.6	41.6	41.1	41.1	41.1	41.1
80°	29.6	30.1	29.6	29.2	28.7	29.6	28.7	29.2	29.6	29.2	30.1
82.5°	19.0	19.0	18.6	19.0	18.1	18.1	18.6	18.6	18.1	19.0	18.1
85°	9.3	9.3	10.2	9.3	8.8	8.8	8.8	9.3	8.8	9.7	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	32.6	32.7	32.9	33.2	33.4	33.6	33.4	33.2	32.9	32.7	32.6
92.5°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6
95°	63.2	63.0	62.6	62.1	61.7	61.3	61.7	62.1	62.6	63.0	63.2
97.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8
100°	136.4	136.3	136.1	135.8	135.6	135.4	135.6	135.8	136.1	136.3	136.4
102.5°	177.9	177.8	177.6	177.3	177.1	176.9	177.1	177.3	177.6	177.8	177.9
105°	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4
107.5°	262.8	262.3	261.2	260.1	259.0	257.9	259.0	260.1	261.2	262.3	262.8
110°	307.3	307.0	306.3	305.6	305.0	304.3	305.0	305.6	306.3	307.0	307.3

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	350.8	350.6	350.1	349.7	349.2	348.8	349.2	349.7	350.1	350.6	350.8
115°	398.2	397.9	397.2	396.5	395.9	395.2	395.9	396.5	397.2	397.9	398.2
117.5°	441.7	441.4	440.7	440.0	439.4	438.7	439.4	440.0	440.7	441.4	441.7
120°	488.1	487.8	487.1	486.5	485.8	485.2	485.8	486.5	487.1	487.8	488.1
122.5°	532.6	532.4	531.9	531.5	531.0	530.6	531.0	531.5	531.9	532.4	532.6
125°	578.0	577.9	577.7	577.5	577.3	577.1	577.3	577.5	577.7	577.9	578.0
127.5°	621.5	621.2	620.5	619.9	619.2	618.6	619.2	619.9	620.5	621.2	621.5
130°	668.0	667.6	666.7	665.8	664.9	664.0	664.9	665.8	666.7	667.6	668.0
132.5°	710.5	710.2	709.5	708.8	708.2	707.5	708.2	708.8	709.5	710.2	710.5
135°	755.9	755.6	754.9	754.2	753.6	752.9	753.6	754.2	754.9	755.6	755.9
137.5°	797.4	797.0	796.1	795.2	794.4	793.5	794.4	795.2	796.1	797.0	797.4
140°	839.9	839.5	838.6	837.7	836.8	835.9	836.8	837.7	838.6	839.5	839.9
142.5°	878.4	878.0	877.1	876.2	875.4	874.5	875.4	876.2	877.1	878.0	878.4
145°	917.0	916.6	915.7	914.8	913.9	913.0	913.9	914.8	915.7	916.6	917.0
147.5°	951.6	951.2	950.3	949.4	948.5	947.6	948.5	949.4	950.3	951.2	951.6
150°	984.2	983.9	983.2	982.5	981.9	981.2	981.9	982.5	983.2	983.9	984.2
152.5°	1016.8	1016.4	1015.5	1014.6	1013.7	1012.8	1013.7	1014.6	1015.5	1016.4	1016.8
155°	1043.5	1043.2	1042.5	1041.8	1041.2	1040.5	1041.2	1041.8	1042.5	1043.2	1043.5
157.5°	1070.1	1069.6	1068.5	1067.4	1066.3	1065.2	1066.3	1067.4	1068.5	1069.6	1070.1
160°	1091.9	1091.5	1090.6	1089.7	1088.8	1087.9	1088.8	1089.7	1090.6	1091.5	1091.9
162.5°	1112.6	1112.1	1111.0	1109.9	1108.8	1107.7	1108.8	1109.9	1111.0	1112.1	1112.6
165°	1129.4	1128.9	1127.8	1126.7	1125.6	1124.5	1125.6	1126.7	1127.8	1128.9	1129.4
167.5°	1144.2	1143.7	1142.6	1141.5	1140.4	1139.3	1140.4	1141.5	1142.6	1143.7	1144.2
170°	1156.1	1155.4	1154.1	1152.8	1151.5	1150.2	1151.5	1152.8	1154.1	1155.4	1156.1
172.5°	1165.0	1164.3	1163.0	1161.7	1160.4	1159.1	1160.4	1161.7	1163.0	1164.3	1165.0
175°	1170.9	1170.2	1168.9	1167.6	1166.3	1165.0	1166.3	1167.6	1168.9	1170.2	1170.9
177.5°	1173.9	1173.2	1171.9	1170.6	1169.3	1168.0	1169.3	1170.6	1171.9	1173.2	1173.9
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	546.0	549.5	548.2	543.3	549.1	549.1	553.1	553.1	557.9	559.7	562.3
5°	515.0	517.7	519.9	517.7	521.7	527.9	531.4	534.5	541.1	543.8	547.8
7.5°	481.9	486.8	489.0	489.0	495.6	502.7	509.7	514.2	523.4	527.0	531.0
10°	449.6	455.4	459.8	459.3	470.4	474.8	483.7	493.8	503.1	508.4	514.2
12.5°	415.6	418.7	424.9	433.7	436.4	444.3	454.5	467.3	484.1	489.0	497.4
15°	387.3	395.7	400.5	404.5	410.7	418.2	429.3	441.7	458.5	469.1	477.9
17.5°	363.4	374.5	377.6	376.7	384.6	396.1	408.9	418.2	433.3	446.1	454.5
20°	344.0	348.4	353.7	355.9	362.1	374.5	386.8	397.4	409.8	420.0	429.7
22.5°	324.5	328.0	332.5	336.4	341.3	348.4	360.3	373.6	385.5	395.2	406.3
25°	308.6	310.8	314.8	317.9	323.2	328.0	336.4	351.0	365.2	370.9	380.6
27.5°	293.1	294.9	297.5	301.1	303.7	308.6	316.1	328.0	342.6	348.4	361.6
30°	279.4	280.7	283.4	285.2	286.5	292.2	298.0	307.3	318.3	326.3	336.0
32.5°	266.6	267.9	270.6	271.0	272.8	275.9	281.2	289.6	299.3	305.9	314.3
35°	252.4	253.3	256.0	256.9	258.2	260.8	264.8	271.0	279.8	284.7	292.2
37.5°	241.4	240.9	242.7	244.0	245.8	247.1	248.5	254.6	261.3	265.7	271.4
40°	229.4	228.6	229.0	230.8	231.7	233.4	233.4	239.6	244.0	247.6	252.0
42.5°	217.5	217.1	216.2	217.1	218.0	218.4	218.8	223.3	227.7	230.8	235.6
45°	205.6	205.1	204.2	204.7	204.7	205.6	206.9	208.7	211.8	214.4	217.1
47.5°	194.5	193.6	192.3	191.9	192.8	192.8	192.8	194.5	197.6	198.5	201.2
50°	183.0	181.7	179.9	179.0	179.0	178.6	179.5	179.9	182.6	183.5	185.7
52.5°	170.6	169.8	168.0	166.2	166.7	165.8	166.2	166.7	167.6	168.9	170.2
55°	158.3	156.5	155.2	154.7	153.4	153.4	152.1	153.9	153.4	153.9	155.6
57.5°	146.3	144.6	142.4	141.5	140.1	139.7	138.8	138.4	138.8	140.1	141.5
60°	132.2	131.3	130.0	128.7	127.8	126.4	125.6	125.6	125.1	125.1	125.6
62.5°	118.5	118.0	116.3	115.8	114.9	114.1	112.7	111.9	111.9	112.7	113.2
65°	105.2	104.8	103.5	103.0	100.8	99.9	99.5	99.0	98.1	98.1	98.1
67.5°	92.8	91.5	91.5	89.3	87.5	86.7	85.8	85.3	85.3	85.3	85.8
70°	79.1	79.1	77.8	76.5	74.7	75.2	73.8	72.5	72.5	71.6	72.1
72.5°	65.9	65.4	64.1	63.7	62.3	61.0	60.1	61.0	59.7	59.2	59.7
75°	53.1	52.6	51.7	50.8	51.3	50.0	48.6	48.2	48.2	47.3	47.3
77.5°	40.7	41.6	39.8	39.3	38.5	37.6	37.1	36.7	36.7	36.7	37.6
80°	28.3	28.7	28.7	27.9	28.3	27.0	27.0	27.0	25.6	26.1	26.5
82.5°	18.1	18.1	17.7	18.1	17.7	17.7	17.2	17.2	16.8	16.8	17.2
85°	10.2	9.7	9.3	10.2	9.7	9.7	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.5	3.5	3.5
90°	32.8	33.3	33.7	34.2	34.6	29.8	24.9	20.1	15.2	12.8	11.5
92.5°	31.5	31.3	31.0	30.8	30.6	30.4	30.2	29.9	29.7	29.6	28.7
95°	63.2	63.2	63.2	63.2	63.2	62.8	62.4	61.9	61.5	61.3	60.2
97.5°	98.8	98.8	98.8	98.8	98.8	97.9	97.1	96.2	95.3	94.9	93.9
100°	136.4	136.4	136.4	136.4	136.4	135.7	135.1	134.4	133.7	133.4	132.5
102.5°	177.8	177.6	177.3	177.1	176.9	176.0	175.1	174.2	173.3	172.9	172.2
105°	219.2	218.7	218.3	217.8	217.4	217.0	216.5	216.1	215.6	215.4	215.1
107.5°	262.7	262.5	262.3	262.1	261.9	261.9	261.9	261.9	261.9	261.9	261.5
110°	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	306.6

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	351.1	351.8	352.4	353.1	353.7	353.9	354.1	354.4	354.6	354.7	354.0
115°	398.3	398.5	398.8	399.0	399.2	399.6	400.1	400.5	401.0	401.2	400.5
117.5°	442.0	442.7	443.4	444.0	444.7	445.8	446.9	448.0	449.1	449.6	448.7
120°	488.1	488.1	488.1	488.1	488.1	489.9	491.6	493.4	495.1	496.0	495.1
122.5°	532.9	533.6	534.3	534.9	535.6	536.7	537.8	538.9	540.0	540.5	539.4
125°	578.3	579.0	579.7	580.3	581.0	581.7	582.3	583.0	583.7	584.0	583.0
127.5°	621.9	622.8	623.7	624.6	625.5	626.4	627.2	628.1	629.0	629.4	628.2
130°	668.2	668.6	669.1	669.5	669.9	670.3	670.8	671.2	671.7	671.9	670.5
132.5°	711.0	712.1	713.2	714.3	715.4	715.2	715.0	714.7	714.5	714.4	713.3
135°	756.0	756.2	756.5	756.7	756.9	756.5	756.0	755.6	755.1	754.9	753.7
137.5°	797.5	797.7	798.0	798.2	798.4	798.0	797.5	797.1	796.6	796.4	795.4
140°	839.9	839.9	839.9	839.9	839.9	838.8	837.7	836.6	835.5	835.0	834.0
142.5°	878.3	878.1	877.8	877.6	877.4	876.8	876.1	875.5	874.8	874.5	873.5
145°	916.9	916.7	916.4	916.2	916.0	914.7	913.4	912.1	910.8	910.1	909.3
147.5°	951.4	950.9	950.5	950.0	949.6	948.7	947.8	946.9	946.0	945.6	944.6
150°	983.9	983.2	982.5	981.9	981.2	980.3	979.4	978.5	977.6	977.2	976.5
152.5°	1016.4	1015.5	1014.6	1013.7	1012.8	1011.7	1010.6	1009.5	1008.4	1007.9	1007.2
155°	1042.9	1041.8	1040.7	1039.6	1038.5	1037.8	1037.2	1036.5	1035.8	1035.5	1035.2
157.5°	1069.3	1067.8	1066.3	1064.7	1063.2	1062.8	1062.3	1061.9	1061.4	1061.2	1061.0
160°	1091.2	1089.9	1088.6	1087.2	1085.9	1085.7	1085.5	1085.3	1085.1	1085.0	1084.8
162.5°	1111.8	1110.3	1108.8	1107.2	1105.7	1105.5	1105.3	1105.0	1104.8	1104.7	1104.7
165°	1128.6	1127.1	1125.6	1124.0	1122.5	1122.5	1122.5	1122.5	1122.5	1122.5	1122.6
167.5°	1143.4	1141.9	1140.4	1138.8	1137.3	1137.3	1137.3	1137.3	1137.3	1137.3	1137.6
170°	1155.3	1153.8	1152.3	1150.7	1149.2	1149.4	1149.6	1149.9	1150.1	1150.2	1150.5
172.5°	1164.2	1162.7	1161.2	1159.6	1158.1	1158.3	1158.5	1158.8	1159.0	1159.1	1159.4
175°	1170.1	1168.6	1167.1	1165.5	1164.0	1164.4	1164.9	1165.3	1165.8	1166.0	1166.3
177.5°	1173.2	1171.9	1170.6	1169.3	1168.0	1168.4	1168.8	1169.3	1169.7	1169.9	1170.2
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	575.2	575.2	575.2	575.2
2.5°	564.6	564.6	571.2	578.3
5°	552.2	555.3	565.9	575.6
7.5°	540.2	545.5	558.8	571.2
10°	525.7	532.7	549.1	563.7
12.5°	511.5	518.1	537.1	553.5
15°	491.6	500.0	520.3	540.7
17.5°	471.7	480.1	504.9	528.7
20°	448.3	459.3	487.2	519.0
22.5°	426.6	440.3	471.3	496.9
25°	402.8	424.0	452.7	485.9
27.5°	381.5	402.8	431.9	465.5
30°	357.7	379.3	409.4	440.3
32.5°	334.7	354.6	383.7	421.8
35°	310.8	329.8	358.1	396.6
37.5°	289.1	307.7	338.6	374.0
40°	267.9	287.4	313.9	349.3
42.5°	248.0	265.3	289.1	324.5
45°	229.9	242.3	264.4	297.5
47.5°	210.9	221.9	242.3	275.4
50°	193.2	202.5	220.2	251.1
52.5°	176.0	183.9	200.3	225.0
55°	160.5	168.0	179.9	204.2
57.5°	144.6	150.3	161.8	181.3
60°	129.1	134.4	143.7	159.6
62.5°	113.6	118.0	126.9	139.7
65°	99.9	103.5	110.1	121.1
67.5°	86.7	88.9	94.2	103.0
70°	73.8	75.6	80.0	87.1
72.5°	60.1	61.9	66.8	71.6
75°	48.6	49.1	52.6	56.6
77.5°	38.0	37.6	40.2	43.3
80°	26.1	27.4	29.6	30.9
82.5°	17.7	18.1	19.0	19.9
85°	9.7	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	8.9	6.2	3.6	1.0
92.5°	27.0	25.2	23.5	21.7
95°	58.0	55.8	53.6	51.4
97.5°	91.9	90.0	88.0	86.0
100°	130.8	129.0	127.3	125.5
102.5°	170.9	169.6	168.3	167.0
105°	214.4	213.7	213.1	212.4
107.5°	260.6	259.7	258.8	257.9
110°	305.3	304.0	302.7	301.4

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	352.7	351.4	350.1	348.8
115°	399.2	397.9	396.5	395.2
117.5°	447.0	445.2	443.5	441.7
120°	493.4	491.6	489.9	488.1
122.5°	537.2	535.0	532.8	530.6
125°	581.0	579.1	577.1	575.1
127.5°	625.8	623.4	621.0	618.6
130°	667.6	664.8	661.9	659.1
132.5°	711.1	708.9	706.7	704.5
135°	751.3	748.9	746.5	744.1
137.5°	793.4	791.5	789.5	787.5
140°	832.0	830.1	828.1	826.1
142.5°	871.5	869.6	867.6	865.6
145°	907.8	906.2	904.7	903.1
147.5°	942.6	940.7	938.7	936.7
150°	975.2	973.9	972.6	971.3
152.5°	1005.9	1004.6	1003.3	1002.0
155°	1034.5	1033.9	1033.2	1032.6
157.5°	1060.6	1060.1	1059.7	1059.3
160°	1084.3	1083.9	1083.4	1083.0
162.5°	1104.7	1104.7	1104.7	1104.7
165°	1122.8	1123.1	1123.3	1123.5
167.5°	1138.3	1139.0	1139.6	1140.3
170°	1151.2	1151.8	1152.5	1153.1
172.5°	1160.1	1160.7	1161.4	1162.0
175°	1167.0	1167.6	1168.3	1168.9
177.5°	1170.9	1171.6	1172.2	1172.9
180°	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998343

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.00	11.67	12.13	12.79	14.35	8.49	9.17	9.62	10.28	11.84
	3H	11.79	12.40	12.93	13.53	15.10	9.82	10.43	10.96	11.55	13.13
	4H	11.95	12.53	13.10	13.66	15.23	10.27	10.85	11.42	11.98	13.55
	6H	11.99	12.52	13.15	13.65	15.24	10.57	11.10	11.73	12.23	13.82
	8H	11.96	12.47	13.12	13.61	15.19	10.65	11.15	11.81	12.30	13.88
	12H	11.92	12.40	13.08	13.54	15.14	10.69	11.16	11.85	12.30	13.91
4H	2H	11.02	11.59	12.17	12.72	14.30	8.91	9.49	10.07	10.62	12.19
	3H	11.98	12.46	13.14	13.61	15.20	10.36	10.84	11.52	11.99	13.58
	4H	12.25	12.69	13.41	13.83	15.44	10.88	11.32	12.05	12.47	14.08
	6H	12.37	12.75	13.54	13.91	15.51	11.25	11.63	12.42	12.80	14.39
	8H	12.36	12.72	13.53	13.87	15.49	11.36	11.71	12.53	12.87	14.48
	12H	12.32	12.64	13.50	13.81	15.43	11.41	11.73	12.59	12.90	14.52
8H	4H	12.24	12.60	13.41	13.75	15.37	11.01	11.36	12.18	12.52	14.14
	6H	12.42	12.71	13.60	13.90	15.52	11.44	11.73	12.63	12.93	14.54
	8H	12.45	12.70	13.64	13.87	15.51	11.59	11.84	12.78	13.02	14.65
	12H	12.42	12.64	13.62	13.82	15.48	11.67	11.90	12.87	13.07	14.74
12H	4H	12.19	12.51	13.38	13.68	15.30	10.98	11.30	12.16	12.47	14.09
	6H	12.39	12.65	13.59	13.82	15.46	11.44	11.69	12.63	12.87	14.50
	8H	12.42	12.64	13.61	13.81	15.48	11.59	11.81	12.78	12.99	14.65