

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998369

Luminaire Tested: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998369
REPORT IS A COMBINATION OF REPORTS P984109 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4745.0 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29
2	84	78	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	21
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	48	42	37	38	33	30	29	25	23	20	18	16
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	36	29	25	28	24	20	21	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8760	8760	8760	8760
5°	8781	9341	8815	7431
10°	8680	10197	8734	6127
15°	8468	10755	8587	5160
20°	8337	10098	8337	4486
25°	8071	8676	8107	4012
30°	7634	6819	7780	3633
35°	7247	4716	7367	3324
40°	6800	3561	6879	3078
45°	6253	2926	6355	2812
50°	5778	2568	5787	2574
55°	5236	2188	5271	2316
60°	4661	1828	4725	2021
65°	4145	1487	4220	1726
70°	3629	1166	3720	1392
75°	3043	846	3166	1009
80°	2379	536	2547	599
85°	1568	270	1681	200

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9055 cd/sqm

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	1.1
10°-20°	153.4	3.2
20°-30°	222.7	4.7
30°-40°	234.7	4.9
40°-50°	207.7	4.4
50°-60°	165.9	3.5
60°-70°	112.7	2.4
70°-80°	57.6	1.2
80°-90°	15.7	0.3
90°-100°	39.6	0.8
100°-110°	147.7	3.1
110°-120°	391.6	8.3
120°-130°	649.6	13.7
130°-140°	690.0	14.5
140°-150°	641.3	13.5
150°-160°	515.6	10.9
160°-170°	332.2	7.0
170°-180°	114.3	2.4
0°-30°	428.8	9.0
0°-40°	663.5	14.0
0°-60°	1037.1	21.9
0°-90°	1223.1	25.8
90°-120°	578.9	12.2
90°-150°	2559.8	53.9
90°-180°	3522.0	74.2
0°-180°	4745.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	553	553	553	553	553	
5°	554	618	556	492	554	53
15°	520	760	528	364	520	147
25°	468	633	470	293	468	214
35°	382	345	388	243	382	239
45°	286	208	291	200	286	222
55°	196	146	198	154	196	175
65°	117	90	119	104	117	116
75°	54	44	57	53	54	58
85°	11	12	12	8	11	13
90°	1	24	1	24	1	4
95°	56	37	56	37	56	67
105°	264	66	264	66	264	282
115°	500	71	500	71	500	492
125°	707	743	707	743	707	630
135°	874	903	874	903	874	676
145°	1014	1030	1014	1030	1014	634
155°	1117	1118	1117	1118	1117	515
165°	1177	1174	1177	1174	1177	333
175°	1204	1197	1204	1197	1204	115
180°	1201	1201	1201	1201	1201	

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	556.4	557.7	559.8	560.2	564.5	567.9	571.7	571.7	573.0	572.6	569.2
5°	553.8	557.7	563.2	567.9	575.5	578.9	584.0	587.9	591.3	593.8	593.4
7.5°	549.6	556.4	564.5	573.4	583.6	589.6	596.8	603.6	608.3	612.5	615.5
10°	542.4	553.8	564.9	576.8	590.0	598.1	606.6	615.5	622.8	630.8	638.5
12.5°	532.6	549.2	562.8	578.5	594.7	603.6	617.2	624.0	638.1	658.5	664.0
15°	520.2	542.8	555.5	575.5	596.8	604.0	622.8	633.8	662.7	675.5	690.8
17.5°	508.7	533.8	550.9	573.8	594.7	608.7	627.0	649.5	673.8	692.1	709.1
20°	499.4	523.6	544.1	569.6	596.0	613.8	633.0	660.2	686.6	705.3	718.5
22.5°	478.1	509.2	533.0	561.5	593.4	618.1	636.4	666.1	694.6	706.1	717.6
25°	467.5	494.3	521.9	554.3	591.7	621.0	636.8	670.0	695.1	699.3	701.9
27.5°	447.9	478.1	510.5	547.5	591.3	615.9	635.9	666.1	686.1	683.2	675.5
30°	423.7	460.7	496.4	536.4	585.3	612.1	630.8	658.5	668.7	653.4	639.8
32.5°	405.8	440.7	480.2	526.6	578.5	604.0	622.3	644.0	646.1	618.5	595.5
35°	381.6	420.3	464.9	513.9	567.0	590.0	607.0	620.2	610.0	571.3	544.1
37.5°	359.9	398.2	445.8	495.6	551.3	573.8	587.4	589.6	564.5	530.4	490.5
40°	336.0	375.6	425.4	477.7	533.8	553.4	561.9	555.5	519.4	479.8	433.5
42.5°	312.2	351.4	405.0	458.6	511.7	528.3	531.7	514.3	470.0	423.7	370.1
45°	286.3	327.1	380.7	434.7	486.2	495.6	496.0	470.9	418.6	370.1	320.3
47.5°	265.0	302.9	356.0	410.1	453.5	459.8	457.3	428.4	371.4	316.9	273.5
50°	241.6	277.8	330.5	383.7	420.7	422.4	416.0	374.8	319.0	269.3	234.8
52.5°	216.5	253.1	301.6	352.6	385.8	383.3	370.9	326.7	274.4	233.1	206.7
55°	196.5	228.9	274.4	324.1	347.5	340.3	326.7	281.6	240.3	205.5	182.5
57.5°	174.4	202.9	247.6	291.0	304.6	297.8	284.2	242.0	203.8	177.4	162.1
60°	153.6	179.5	218.6	254.8	265.4	258.2	242.5	204.6	177.0	154.8	143.4
62.5°	134.4	157.0	189.7	222.9	227.2	219.9	206.3	175.7	151.9	134.4	125.9
65°	116.6	137.8	164.2	189.3	193.1	185.5	171.4	149.3	129.3	118.3	110.2
67.5°	99.1	116.1	139.5	157.8	159.9	152.7	141.2	123.4	111.0	99.1	93.2
70°	83.8	96.6	114.9	129.7	130.6	123.8	117.8	101.7	92.3	83.8	79.1
72.5°	68.9	77.8	91.9	102.9	103.4	99.1	93.6	83.4	75.3	69.3	64.7
75°	54.4	62.1	70.6	80.4	80.0	76.6	72.3	65.9	59.1	55.3	53.2
77.5°	41.7	46.4	53.2	59.6	59.6	57.9	55.3	50.6	46.4	42.5	40.4
80°	29.8	32.8	38.3	40.4	41.3	40.8	38.7	35.3	33.6	30.6	29.8
82.5°	19.1	21.3	23.8	25.9	27.2	26.4	25.9	24.2	21.7	20.8	20.0
85°	11.1	11.9	13.2	14.5	14.9	14.5	15.3	14.0	12.8	12.8	12.3
87.5°	4.7	5.1	6.0	6.0	6.4	6.4	6.0	6.4	6.4	6.0	5.5
90°	0.9	3.0	5.1	7.2	9.3	10.4	11.2	12.7	14.3	15.8	17.4
92.5°	21.7	20.9	20.2	19.4	18.7	18.3	18.6	19.2	19.7	20.3	20.9
95°	56.5	50.1	43.7	37.4	31.0	27.8	28.5	29.8	31.2	32.5	33.9
97.5°	101.7	85.9	70.0	54.2	38.3	30.4	31.9	35.0	38.1	41.2	44.3
100°	153.9	127.4	101.0	74.5	48.0	34.8	36.4	39.7	43.0	46.2	49.5
102.5°	211.2	210.8	210.4	210.1	209.7	209.5	191.9	156.8	121.6	86.5	51.3
105°	264.3	270.1	275.9	281.6	287.4	290.3	263.9	211.2	158.5	105.7	53.0
107.5°	326.0	330.8	335.6	340.5	345.3	347.7	315.2	250.1	185.0	119.9	54.8
110°	385.1	389.1	393.2	397.2	401.3	403.3	375.4	319.6	263.7	207.9	152.1

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	440.7	444.2	447.7	451.2	454.7	456.4	454.8	451.5	448.2	444.9	441.6
115°	499.8	503.1	506.4	509.7	513.0	514.6	517.0	521.8	526.7	531.5	536.3
117.5°	551.1	555.0	558.8	562.7	566.6	568.5	570.1	573.4	576.7	580.0	583.3
120°	608.5	611.4	614.3	617.2	620.1	621.5	623.2	626.7	630.2	633.7	637.2
122.5°	657.2	660.3	663.4	666.5	669.6	671.1	673.0	676.9	680.8	684.6	688.5
125°	706.7	709.2	711.7	714.2	716.7	718.0	719.8	723.5	727.2	730.8	734.5
127.5°	751.9	754.6	757.3	760.0	762.7	764.1	765.5	768.4	771.3	774.2	777.1
130°	794.5	797.6	800.7	803.8	806.9	808.4	809.5	811.6	813.7	815.9	818.0
132.5°	838.0	840.5	843.0	845.5	848.0	849.3	850.4	852.5	854.6	856.7	858.8
135°	874.5	877.6	880.7	883.8	886.9	888.4	889.3	891.0	892.7	894.5	896.2
137.5°	912.7	915.0	917.4	919.7	922.0	923.2	924.2	926.1	928.0	930.0	931.9
140°	950.1	951.7	953.2	954.8	956.3	957.1	958.2	960.3	962.4	964.5	966.6
142.5°	981.4	982.8	984.1	985.5	986.8	987.5	988.8	991.3	993.8	996.3	998.8
145°	1014.4	1014.2	1014.0	1013.9	1013.7	1013.6	1015.2	1018.5	1021.8	1025.0	1028.3
147.5°	1043.1	1042.5	1041.9	1041.4	1040.8	1040.5	1042.1	1045.4	1048.7	1052.0	1055.3
150°	1070.9	1069.6	1068.2	1066.9	1065.6	1064.9	1066.4	1069.5	1072.6	1075.7	1078.8
152.5°	1094.4	1092.9	1091.3	1089.8	1088.3	1087.5	1088.9	1091.8	1094.7	1097.6	1100.5
155°	1117.0	1115.3	1113.5	1111.8	1110.1	1109.2	1110.4	1112.7	1115.0	1117.3	1119.6
157.5°	1135.3	1133.7	1132.2	1130.6	1129.1	1128.3	1129.2	1130.9	1132.6	1134.4	1136.1
160°	1150.9	1149.7	1148.6	1147.4	1146.3	1145.7	1146.3	1147.4	1148.6	1149.7	1150.9
162.5°	1164.8	1163.6	1162.5	1161.3	1160.2	1159.6	1160.1	1161.1	1162.0	1163.0	1164.0
165°	1177.0	1175.8	1174.7	1173.5	1172.4	1171.8	1172.1	1172.7	1173.2	1173.8	1174.4
167.5°	1186.6	1185.4	1184.2	1183.1	1181.9	1181.3	1181.6	1182.2	1182.7	1183.3	1183.9
170°	1194.4	1193.2	1192.1	1190.9	1189.8	1189.2	1189.4	1189.8	1190.1	1190.5	1190.9
172.5°	1199.6	1198.4	1197.3	1196.1	1195.0	1194.4	1194.6	1195.0	1195.3	1195.7	1196.1
175°	1203.9	1202.6	1201.2	1199.9	1198.6	1197.9	1198.1	1198.5	1198.8	1199.2	1199.6
177.5°	1205.7	1204.3	1203.0	1201.6	1200.3	1199.6	1199.7	1199.9	1200.1	1200.3	1200.5
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	575.1	575.5	576.4	580.6	582.8	583.2	581.5	585.3	586.6	585.3	584.5
5°	602.3	604.9	610.0	615.5	615.1	615.5	618.1	620.6	621.5	618.1	619.3
7.5°	626.2	631.3	636.8	645.3	645.3	649.5	651.3	653.4	658.5	655.9	655.1
10°	653.4	660.2	670.4	684.0	684.4	688.7	692.9	699.7	701.9	700.2	701.0
12.5°	687.4	700.6	701.4	716.3	723.1	724.0	730.8	729.5	733.8	733.8	741.0
15°	702.3	722.7	734.2	748.7	752.9	747.8	753.3	759.3	759.7	759.7	759.3
17.5°	729.1	737.2	748.7	756.3	758.0	758.0	758.4	761.0	759.3	755.9	758.4
20°	734.6	738.0	742.3	741.4	742.3	738.0	733.8	729.5	729.9	727.8	734.2
22.5°	724.4	723.6	713.8	707.4	707.4	698.9	690.8	687.0	683.2	684.4	686.6
25°	698.9	685.7	673.8	664.4	662.3	648.7	637.6	634.2	627.9	633.0	633.8
27.5°	658.1	643.2	624.0	615.9	604.9	599.4	591.7	581.5	568.3	576.0	574.7
30°	614.2	592.1	576.4	556.8	539.4	538.1	523.6	506.6	499.8	499.8	503.6
32.5°	565.3	536.0	513.0	485.4	468.3	461.1	443.7	426.7	430.5	417.7	422.4
35°	508.3	469.6	440.7	413.9	401.1	392.6	370.1	360.7	350.5	344.6	355.6
37.5°	453.9	409.2	372.2	342.9	338.2	322.9	307.5	301.6	295.6	298.2	297.8
40°	387.5	348.0	314.8	291.8	283.7	276.5	266.3	259.1	255.2	257.4	257.8
42.5°	327.5	294.4	269.7	253.5	246.7	241.6	236.5	230.6	229.3	229.3	231.0
45°	281.2	253.9	237.4	224.2	220.3	216.5	212.7	210.1	209.3	207.6	208.9
47.5°	244.2	222.5	212.3	202.5	198.2	197.4	194.0	192.7	191.0	190.6	191.0
50°	213.1	199.5	190.1	184.6	181.6	180.4	178.7	176.1	175.3	177.4	176.5
52.5°	191.4	178.7	173.6	168.0	166.3	164.6	162.1	162.5	162.1	161.2	161.2
55°	169.7	161.6	156.5	152.3	151.9	150.2	148.0	147.2	146.8	145.9	147.2
57.5°	152.3	145.9	141.2	137.4	135.7	135.7	133.6	131.9	131.9	131.4	131.9
60°	134.8	128.5	125.5	121.7	120.4	120.0	118.7	117.8	116.6	116.6	116.6
62.5°	118.7	113.6	110.2	106.8	107.2	105.1	103.4	102.5	102.5	102.9	102.9
65°	103.4	100.0	95.7	92.7	91.9	91.5	90.6	90.2	88.9	89.8	89.8
67.5°	89.3	84.6	82.1	80.8	79.5	79.1	78.3	77.4	77.0	76.6	77.4
70°	75.3	71.5	69.3	68.5	67.2	66.8	66.4	65.1	65.5	65.9	66.4
72.5°	62.5	59.1	58.7	56.1	56.1	56.1	54.4	55.3	54.9	54.0	54.9
75°	49.3	47.6	46.8	45.5	45.9	45.5	45.1	43.8	43.8	44.2	44.7
77.5°	39.1	37.4	37.0	35.7	34.9	35.7	34.9	34.5	34.5	34.9	34.9
80°	28.9	28.1	26.8	26.8	26.8	26.4	26.4	26.4	25.9	25.5	25.9
82.5°	19.1	19.1	18.7	18.3	18.7	17.9	18.3	18.3	18.3	18.3	18.3
85°	12.3	11.9	11.9	11.5	11.5	11.5	11.9	11.1	11.1	11.5	11.5
87.5°	5.5	5.5	5.5	6.0	5.5	5.5	5.5	6.0	5.5	5.5	5.5
90°	18.4	19.3	20.3	21.2	21.7	21.9	22.3	22.7	23.1	23.5	23.1
92.5°	21.3	21.7	22.0	22.4	22.6	22.7	22.9	23.1	23.3	23.5	23.3
95°	34.9	35.8	36.8	37.7	38.2	38.1	37.9	37.8	37.6	37.4	37.6
97.5°	44.9	45.5	46.0	46.6	46.9	47.0	47.2	47.4	47.6	47.8	47.6
100°	51.1	52.6	54.2	55.7	56.5	56.7	57.1	57.4	57.8	58.2	57.8
102.5°	53.4	55.5	57.6	59.7	60.8	61.1	61.7	62.3	62.9	63.5	62.9
105°	55.1	57.3	59.4	61.5	62.6	63.0	63.8	64.5	65.3	66.1	65.3
107.5°	56.9	59.0	61.1	63.2	64.3	64.7	65.5	66.2	67.0	67.8	67.0
110°	132.8	113.5	94.2	74.9	65.2	65.6	66.4	67.1	67.9	68.7	67.9

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	358.3	275.1	191.8	108.5	66.9	67.2	67.8	68.3	68.9	69.5	68.9
115°	446.9	357.5	268.0	178.6	133.9	126.9	113.0	99.1	85.2	71.3	85.2
117.5°	555.7	528.1	500.4	472.8	459.0	433.7	383.1	332.4	281.8	231.2	281.8
120°	639.5	641.8	644.1	646.4	647.6	634.6	608.5	582.4	556.4	530.3	556.4
122.5°	689.7	690.8	692.0	693.1	693.7	693.8	694.0	694.1	694.3	694.5	694.3
125°	735.9	737.2	738.6	739.9	740.6	740.9	741.5	742.0	742.6	743.2	742.6
127.5°	779.0	781.0	782.9	784.8	785.8	785.9	786.1	786.3	786.5	786.7	786.5
130°	820.1	822.2	824.3	826.4	827.5	827.4	827.2	827.1	826.9	826.7	826.9
132.5°	860.6	862.3	864.1	865.8	866.7	866.6	866.4	866.2	866.0	865.8	866.0
135°	898.1	900.1	902.0	903.9	904.9	904.7	904.3	904.0	903.6	903.2	903.6
137.5°	933.8	935.8	937.7	939.6	940.6	940.3	939.7	939.1	938.5	937.9	938.5
140°	968.4	970.1	971.9	973.6	974.5	974.0	973.0	972.1	971.1	970.1	971.1
142.5°	1000.3	1001.9	1003.4	1004.9	1005.7	1005.2	1004.3	1003.3	1002.4	1001.4	1002.4
145°	1029.7	1031.0	1032.4	1033.7	1034.4	1033.9	1033.0	1032.0	1031.1	1030.1	1031.1
147.5°	1056.3	1057.2	1058.2	1059.1	1059.6	1059.2	1058.5	1057.7	1057.0	1056.2	1057.0
150°	1080.0	1081.1	1082.3	1083.4	1084.0	1083.5	1082.5	1081.6	1080.6	1079.6	1080.6
152.5°	1101.7	1102.8	1104.0	1105.1	1105.7	1105.0	1103.7	1102.3	1101.0	1099.6	1101.0
155°	1120.8	1121.9	1123.1	1124.2	1124.8	1124.0	1122.5	1121.0	1119.4	1117.9	1119.4
157.5°	1137.5	1138.8	1140.2	1141.5	1142.2	1141.4	1139.9	1138.4	1136.8	1135.3	1136.8
160°	1152.1	1153.2	1154.4	1155.5	1156.1	1155.4	1154.1	1152.7	1151.4	1150.0	1151.4
162.5°	1165.3	1166.7	1168.0	1169.3	1170.0	1169.1	1167.4	1165.7	1163.9	1162.2	1163.9
165°	1175.8	1177.1	1178.5	1179.8	1180.5	1179.8	1178.5	1177.1	1175.8	1174.4	1175.8
167.5°	1185.3	1186.6	1188.0	1189.3	1190.0	1189.1	1187.4	1185.7	1183.9	1182.2	1183.9
170°	1192.3	1193.6	1195.0	1196.3	1197.0	1196.1	1194.4	1192.7	1190.9	1189.2	1190.9
172.5°	1197.5	1198.8	1200.2	1201.5	1202.2	1201.3	1199.6	1197.9	1196.1	1194.4	1196.1
175°	1201.0	1202.3	1203.7	1205.0	1205.7	1204.7	1202.8	1200.9	1198.9	1197.0	1198.9
177.5°	1201.8	1203.2	1204.5	1205.8	1206.5	1205.6	1203.9	1202.2	1200.4	1198.7	1200.4
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	586.6	583.6	581.1	581.5	583.6	581.9	577.7	572.1	570.0	567.5	570.0
5°	621.9	619.3	614.2	614.7	613.4	611.7	604.9	596.4	596.4	589.6	588.7
7.5°	656.8	653.0	649.5	648.7	644.0	640.6	634.7	622.8	618.1	610.0	605.3
10°	695.9	692.9	689.1	684.4	681.9	675.9	666.1	648.7	640.2	629.1	621.0
12.5°	735.5	735.0	726.5	717.2	716.8	707.4	700.6	677.2	665.7	650.8	631.7
15°	760.6	758.4	753.8	749.1	750.4	740.2	724.8	697.2	689.5	671.7	651.3
17.5°	760.1	760.1	758.9	758.0	756.7	753.8	745.3	727.0	714.6	692.1	672.9
20°	735.9	741.4	742.7	742.3	746.5	748.7	748.2	736.8	727.0	707.0	687.4
22.5°	687.4	700.2	705.7	709.1	718.0	722.7	733.8	729.5	727.0	712.1	695.5
25°	642.3	646.6	663.2	664.0	676.3	687.8	698.9	706.1	715.5	710.0	695.9
27.5°	584.0	593.8	605.7	614.7	617.2	640.6	658.9	672.5	693.8	695.5	690.8
30°	518.1	522.8	542.4	554.3	567.9	584.9	611.3	634.7	653.8	671.2	677.2
32.5°	437.7	456.9	468.3	482.8	494.7	524.9	557.2	587.4	609.6	638.9	651.7
35°	364.1	379.0	398.6	404.5	426.2	451.7	493.9	532.6	566.2	596.0	621.9
37.5°	303.3	315.2	336.0	345.4	358.2	390.9	426.2	474.3	514.7	551.3	583.6
40°	261.6	270.5	286.3	289.3	299.9	329.7	358.2	403.3	456.9	506.2	541.5
42.5°	233.1	237.4	248.0	251.8	258.6	278.6	304.1	346.7	396.5	447.5	497.3
45°	212.7	215.7	222.0	225.4	234.0	242.9	263.7	297.8	336.9	388.4	442.0
47.5°	194.4	198.2	200.8	202.9	207.6	217.4	231.0	256.1	293.5	340.7	392.6
50°	179.1	180.4	185.0	185.5	188.4	194.8	207.6	222.9	252.7	291.0	341.2
52.5°	163.8	165.0	168.0	171.0	172.3	177.4	185.9	198.7	220.8	251.0	295.6
55°	148.5	150.2	153.1	155.3	156.5	160.8	165.9	178.2	195.7	216.9	253.5
57.5°	133.1	137.0	137.8	139.1	141.2	145.9	150.6	157.8	171.4	191.0	217.8
60°	118.7	120.0	122.9	124.2	126.3	128.9	134.8	140.4	150.2	165.5	189.7
62.5°	103.8	106.8	108.0	109.3	111.0	114.0	117.8	123.8	132.3	144.6	163.8
65°	91.0	91.5	94.0	95.7	97.4	99.5	103.4	108.9	114.0	125.5	139.5
67.5°	78.7	79.5	80.4	82.1	84.2	86.4	89.8	92.7	99.1	106.8	117.8
70°	66.8	66.8	68.9	70.2	69.8	72.3	74.9	78.3	82.9	90.2	99.1
72.5°	56.1	55.7	57.4	57.9	58.7	60.4	62.1	65.5	68.1	73.6	80.4
75°	44.7	45.5	46.4	46.4	47.6	48.9	50.6	52.3	55.3	58.7	63.8
77.5°	35.3	35.3	36.2	36.6	37.9	37.4	39.1	40.8	43.0	45.9	49.8
80°	25.9	26.8	26.8	26.8	27.2	27.6	29.4	30.6	31.9	34.0	35.7
82.5°	18.3	18.3	19.1	19.1	19.1	20.0	20.0	20.4	21.3	22.5	23.8
85°	11.5	11.5	11.5	11.9	11.5	11.9	12.8	12.3	12.8	13.6	13.6
87.5°	5.5	5.5	5.5	5.5	5.5	6.0	5.5	6.0	6.4	6.4	6.4
90°	22.7	22.3	21.9	21.7	21.2	20.3	19.3	18.4	17.4	15.8	14.3
92.5°	23.1	22.9	22.7	22.6	22.4	22.0	21.7	21.3	20.9	20.3	19.7
95°	37.8	37.9	38.1	38.2	37.7	36.8	35.8	34.9	33.9	32.5	31.2
97.5°	47.4	47.2	47.0	46.9	46.6	46.0	45.5	44.9	44.3	41.2	38.1
100°	57.4	57.1	56.7	56.5	55.7	54.2	52.6	51.1	49.5	46.2	43.0
102.5°	62.3	61.7	61.1	60.8	59.7	57.6	55.5	53.4	51.3	46.5	121.6
105°	64.5	63.8	63.0	62.6	61.5	59.4	57.3	55.1	53.0	105.7	158.5
107.5°	66.2	65.5	64.7	64.3	63.2	61.1	59.0	56.9	54.8	119.9	185.0
110°	67.1	66.4	65.6	65.2	74.9	94.2	113.5	132.8	152.1	207.9	263.7

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	68.3	67.8	67.2	66.9	108.5	191.8	275.1	358.3	441.6	444.9	448.2
115°	99.1	113.0	126.9	133.9	178.6	268.0	357.5	446.9	536.3	531.5	526.7
117.5°	332.4	383.1	433.7	459.0	472.8	500.4	528.1	555.7	583.3	580.0	576.7
120°	582.4	608.5	634.6	647.6	646.4	644.1	641.8	639.5	637.2	633.7	630.2
122.5°	694.1	694.0	693.8	693.7	693.1	692.0	690.8	689.7	688.5	684.6	680.8
125°	742.0	741.5	740.9	740.6	739.9	738.6	737.2	735.9	734.5	730.8	727.2
127.5°	786.3	786.1	785.9	785.8	784.8	782.9	781.0	779.0	777.1	774.2	771.3
130°	827.1	827.2	827.4	827.5	826.4	824.3	822.2	820.1	818.0	815.9	813.7
132.5°	866.2	866.4	866.6	866.7	865.8	864.1	862.3	860.6	858.8	856.7	854.6
135°	904.0	904.3	904.7	904.9	903.9	902.0	900.1	898.1	896.2	894.5	892.7
137.5°	939.1	939.7	940.3	940.6	939.6	937.7	935.8	933.8	931.9	930.0	928.0
140°	972.1	973.0	974.0	974.5	973.6	971.9	970.1	968.4	966.6	964.5	962.4
142.5°	1003.3	1004.3	1005.2	1005.7	1004.9	1003.4	1001.9	1000.3	998.8	996.3	993.8
145°	1032.0	1033.0	1033.9	1034.4	1033.7	1032.4	1031.0	1029.7	1028.3	1025.0	1021.8
147.5°	1057.7	1058.5	1059.2	1059.6	1059.1	1058.2	1057.2	1056.3	1055.3	1052.0	1048.7
150°	1081.6	1082.5	1083.5	1084.0	1083.4	1082.3	1081.1	1080.0	1078.8	1075.7	1072.6
152.5°	1102.3	1103.7	1105.0	1105.7	1105.1	1104.0	1102.8	1101.7	1100.5	1097.6	1094.7
155°	1121.0	1122.5	1124.0	1124.8	1124.2	1123.1	1121.9	1120.8	1119.6	1117.3	1115.0
157.5°	1138.4	1139.9	1141.4	1142.2	1141.5	1140.2	1138.8	1137.5	1136.1	1134.4	1132.6
160°	1152.7	1154.1	1155.4	1156.1	1155.5	1154.4	1153.2	1152.1	1150.9	1149.7	1148.6
162.5°	1165.7	1167.4	1169.1	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1163.0	1162.0
165°	1177.1	1178.5	1179.8	1180.5	1179.8	1178.5	1177.1	1175.8	1174.4	1173.8	1173.2
167.5°	1185.7	1187.4	1189.1	1190.0	1189.3	1188.0	1186.6	1185.3	1183.9	1183.3	1182.7
170°	1192.7	1194.4	1196.1	1197.0	1196.3	1195.0	1193.6	1192.3	1190.9	1190.5	1190.1
172.5°	1197.9	1199.6	1201.3	1202.2	1201.5	1200.2	1198.8	1197.5	1196.1	1195.7	1195.3
175°	1200.9	1202.8	1204.7	1205.7	1205.0	1203.7	1202.3	1201.0	1199.6	1199.2	1198.8
177.5°	1202.2	1203.9	1205.6	1206.5	1205.8	1204.5	1203.2	1201.8	1200.5	1200.3	1200.1
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	567.9	565.7	564.5	565.3	562.8	556.4	556.4	558.5	556.0	553.4	549.6
5°	583.6	579.4	576.8	576.4	570.4	560.2	558.1	556.0	550.4	544.5	538.1
7.5°	598.9	591.3	587.0	584.0	575.5	562.3	556.8	552.1	543.2	534.3	526.2
10°	611.7	600.6	595.5	590.8	579.8	563.2	554.3	545.8	534.3	522.8	512.6
12.5°	621.9	609.1	602.8	596.0	582.3	560.6	549.6	536.0	524.5	509.2	499.0
15°	638.9	612.5	606.6	600.2	586.2	556.4	542.8	527.5	511.7	491.3	480.2
17.5°	652.5	617.2	616.8	603.2	584.9	554.7	533.8	513.9	496.8	476.4	459.0
20°	660.6	624.5	617.6	603.6	580.6	543.2	521.5	499.4	481.1	456.4	439.0
22.5°	667.4	634.7	616.8	599.8	571.7	539.4	507.5	486.6	461.5	434.7	418.1
25°	670.0	636.8	618.1	598.5	565.3	528.3	492.2	469.6	441.5	417.3	394.7
27.5°	670.4	636.4	613.4	593.0	556.4	513.9	476.8	453.0	422.0	393.9	371.4
30°	666.1	631.7	610.8	588.7	547.9	500.7	458.1	431.8	398.6	370.5	347.1
32.5°	653.4	622.3	605.3	581.1	536.8	482.4	440.3	410.9	376.0	348.4	325.8
35°	632.1	610.8	592.1	569.6	522.4	465.4	422.4	387.9	352.6	326.3	305.0
37.5°	605.7	594.3	576.8	554.7	505.8	450.0	402.4	364.1	328.8	303.3	282.4
40°	570.0	573.0	556.0	536.0	486.2	429.2	376.5	339.9	306.7	282.9	262.5
42.5°	531.3	543.6	533.8	514.7	464.5	406.2	357.3	316.9	284.6	259.9	242.9
45°	489.6	510.9	504.9	490.9	442.0	382.0	330.1	291.0	262.5	238.6	223.7
47.5°	444.1	474.3	474.3	464.1	416.9	357.7	306.7	266.7	238.6	221.6	207.2
50°	397.7	431.8	437.3	430.5	388.8	330.1	278.2	242.0	217.8	201.2	190.6
52.5°	349.2	388.8	399.0	395.6	359.0	303.7	254.8	219.5	197.4	182.9	173.6
55°	302.9	348.8	359.9	361.1	327.1	274.8	228.9	197.8	176.5	166.7	158.7
57.5°	259.1	303.3	315.6	317.8	294.8	248.4	204.6	177.4	158.2	150.2	143.8
60°	221.6	258.6	274.8	279.5	259.5	217.8	182.1	155.7	141.2	133.6	127.6
62.5°	191.0	220.8	237.8	239.1	230.1	191.0	158.7	136.5	124.2	117.4	114.4
65°	161.2	188.0	198.2	203.3	196.1	165.5	137.0	118.7	108.9	102.9	100.0
67.5°	137.4	154.4	162.9	169.7	162.5	139.5	116.6	101.7	94.4	88.5	86.8
70°	112.7	126.8	133.1	139.9	133.6	116.1	99.5	85.9	79.5	74.9	72.7
72.5°	90.2	101.2	107.2	111.4	107.6	93.2	79.5	70.2	65.5	62.1	60.8
75°	71.5	79.1	82.5	85.5	83.8	72.7	64.2	56.6	52.3	49.3	48.5
77.5°	54.4	60.0	63.8	64.7	62.5	55.3	48.1	43.4	40.0	38.3	37.4
80°	38.7	42.1	44.2	45.5	43.4	40.4	35.3	31.9	28.9	26.8	26.4
82.5°	25.9	27.6	29.4	28.9	28.1	25.5	22.5	20.8	19.6	17.9	17.9
85°	14.9	15.3	16.2	16.6	16.2	14.5	12.8	11.9	11.1	9.8	9.8
87.5°	6.4	6.8	6.8	7.2	6.4	6.4	5.5	4.7	4.7	4.3	3.8
90°	12.7	11.2	10.4	9.3	7.2	5.1	3.0	0.9	3.0	5.1	7.2
92.5°	19.2	18.6	18.3	18.7	19.4	20.2	20.9	21.7	20.9	20.2	19.4
95°	29.8	28.5	27.8	31.0	37.4	43.7	50.1	56.5	50.1	43.7	37.4
97.5°	35.0	31.9	30.4	38.3	54.2	70.0	85.9	101.7	85.9	70.0	54.2
100°	39.7	36.4	34.8	48.0	74.5	101.0	127.4	153.9	127.4	101.0	74.5
102.5°	156.8	191.9	209.5	209.7	210.1	210.4	210.8	211.2	210.8	210.4	210.1
105°	211.2	263.9	290.3	287.4	281.6	275.9	270.1	264.3	270.1	275.9	281.6
107.5°	250.1	315.2	347.7	345.3	340.5	335.6	330.8	326.0	330.8	335.6	340.5
110°	319.6	375.4	403.3	401.3	397.2	393.2	389.1	385.1	389.1	393.2	397.2

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	451.5	454.8	456.4	454.7	451.2	447.7	444.2	440.7	444.2	447.7	451.2
115°	521.8	517.0	514.6	513.0	509.7	506.4	503.1	499.8	503.1	506.4	509.7
117.5°	573.4	570.1	568.5	566.6	562.7	558.8	555.0	551.1	555.0	558.8	562.7
120°	626.7	623.2	621.5	620.1	617.2	614.3	611.4	608.5	611.4	614.3	617.2
122.5°	676.9	673.0	671.1	669.6	666.5	663.4	660.3	657.2	660.3	663.4	666.5
125°	723.5	719.8	718.0	716.7	714.2	711.7	709.2	706.7	709.2	711.7	714.2
127.5°	768.4	765.5	764.1	762.7	760.0	757.3	754.6	751.9	754.6	757.3	760.0
130°	811.6	809.5	808.4	806.9	803.8	800.7	797.6	794.5	797.6	800.7	803.8
132.5°	852.5	850.4	849.3	848.0	845.5	843.0	840.5	838.0	840.5	843.0	845.5
135°	891.0	889.3	888.4	886.9	883.8	880.7	877.6	874.5	877.6	880.7	883.8
137.5°	926.1	924.2	923.2	922.0	919.7	917.4	915.0	912.7	915.0	917.4	919.7
140°	960.3	958.2	957.1	956.3	954.8	953.2	951.7	950.1	951.7	953.2	954.8
142.5°	991.3	988.8	987.5	986.8	985.5	984.1	982.8	981.4	982.8	984.1	985.5
145°	1018.5	1015.2	1013.6	1013.7	1013.9	1014.0	1014.2	1014.4	1014.2	1014.0	1013.9
147.5°	1045.4	1042.1	1040.5	1040.8	1041.4	1041.9	1042.5	1043.1	1042.5	1041.9	1041.4
150°	1069.5	1066.4	1064.9	1065.6	1066.9	1068.2	1069.6	1070.9	1069.6	1068.2	1066.9
152.5°	1091.8	1088.9	1087.5	1088.3	1089.8	1091.3	1092.9	1094.4	1092.9	1091.3	1089.8
155°	1112.7	1110.4	1109.2	1110.1	1111.8	1113.5	1115.3	1117.0	1115.3	1113.5	1111.8
157.5°	1130.9	1129.2	1128.3	1129.1	1130.6	1132.2	1133.7	1135.3	1133.7	1132.2	1130.6
160°	1147.4	1146.3	1145.7	1146.3	1147.4	1148.6	1149.7	1150.9	1149.7	1148.6	1147.4
162.5°	1161.1	1160.1	1159.6	1160.2	1161.3	1162.5	1163.6	1164.8	1163.6	1162.5	1161.3
165°	1172.7	1172.1	1171.8	1172.4	1173.5	1174.7	1175.8	1177.0	1175.8	1174.7	1173.5
167.5°	1182.2	1181.6	1181.3	1181.9	1183.1	1184.2	1185.4	1186.6	1185.4	1184.2	1183.1
170°	1189.8	1189.4	1189.2	1189.8	1190.9	1192.1	1193.2	1194.4	1193.2	1192.1	1190.9
172.5°	1195.0	1194.6	1194.4	1195.0	1196.1	1197.3	1198.4	1199.6	1198.4	1197.3	1196.1
175°	1198.5	1198.1	1197.9	1198.6	1199.9	1201.2	1202.6	1203.9	1202.6	1201.2	1199.9
177.5°	1199.9	1199.7	1199.6	1200.3	1201.6	1203.0	1204.3	1205.7	1204.3	1203.0	1201.6
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	547.5	549.6	549.2	544.9	540.2	536.4	529.2	530.0	527.5	527.9	530.4
5°	533.8	533.8	532.1	526.2	518.5	514.3	506.2	504.1	499.0	498.5	498.1
7.5°	519.4	517.3	515.1	506.6	497.3	490.5	479.4	476.8	471.7	468.3	466.6
10°	502.4	499.4	495.1	485.4	473.9	465.4	453.9	450.5	440.7	436.4	433.9
12.5°	483.7	482.0	475.1	467.1	448.3	439.0	422.4	425.8	416.0	407.5	406.2
15°	464.9	458.6	454.7	441.5	419.0	414.7	401.6	394.7	385.8	379.0	379.0
17.5°	446.6	436.9	428.4	414.3	397.7	385.8	376.0	372.6	361.6	354.8	353.5
20°	422.4	411.3	409.2	389.2	377.7	364.5	355.2	346.7	338.6	335.6	333.5
22.5°	399.4	386.7	383.3	366.2	354.8	341.6	332.2	326.3	320.3	318.2	314.4
25°	374.8	367.1	362.0	343.7	330.9	318.6	312.2	308.0	302.4	302.0	299.5
27.5°	350.9	343.7	338.6	321.2	311.8	300.3	295.2	290.5	287.6	286.3	285.0
30°	330.5	322.4	316.5	303.7	292.2	282.9	278.6	275.6	273.9	271.8	271.4
32.5°	308.0	303.3	295.2	285.4	276.5	267.6	265.0	262.9	260.3	259.5	259.1
35°	288.8	282.4	277.3	266.3	262.5	254.8	251.8	250.1	246.7	245.9	245.0
37.5°	270.1	264.2	258.6	251.8	244.6	240.3	238.6	236.1	234.4	234.8	234.0
40°	251.4	246.7	242.5	235.2	231.0	228.9	225.4	222.9	222.0	222.5	222.0
42.5°	233.1	228.9	226.3	220.8	216.5	214.4	212.3	209.7	211.0	211.0	212.3
45°	216.5	212.7	211.0	206.7	204.2	200.8	198.7	198.2	199.9	199.5	199.5
47.5°	199.5	198.2	196.1	192.3	188.9	186.7	186.3	186.3	188.0	188.9	188.4
50°	186.3	183.8	181.2	178.2	175.7	174.8	173.6	174.4	176.1	176.1	177.0
52.5°	169.7	168.0	167.2	164.6	162.9	162.9	162.9	163.3	164.6	165.9	165.5
55°	155.3	154.0	153.1	151.9	149.7	150.2	149.7	150.6	151.9	153.1	154.0
57.5°	139.9	139.5	138.7	136.5	136.5	136.1	137.4	137.8	139.9	140.8	142.1
60°	126.3	125.1	125.1	123.4	123.4	123.4	124.6	125.9	127.6	128.0	128.9
62.5°	111.9	111.9	111.4	110.2	110.2	111.4	111.9	113.6	114.4	114.4	115.7
65°	98.3	97.8	97.4	97.8	98.3	98.3	99.5	100.4	101.2	101.7	102.1
67.5°	84.6	84.2	85.1	84.6	85.5	87.2	86.8	88.1	89.3	89.3	89.8
70°	71.9	72.7	72.3	73.2	72.7	73.6	74.9	75.3	75.3	75.7	77.0
72.5°	60.0	60.0	60.0	59.6	60.0	60.8	61.7	62.1	63.0	63.4	64.7
75°	48.5	48.5	47.6	48.5	48.5	49.3	50.2	50.2	50.2	51.0	52.3
77.5°	36.6	37.0	36.6	37.4	37.4	37.9	38.7	38.3	39.1	39.6	40.0
80°	26.8	26.4	26.4	26.4	26.8	26.8	27.6	28.1	28.1	29.4	28.5
82.5°	17.0	17.4	17.0	17.4	17.4	17.9	17.4	17.9	18.3	19.1	18.7
85°	9.8	9.4	9.4	9.8	9.4	9.4	9.8	9.4	9.8	9.4	9.8
87.5°	3.8	3.4	3.4	3.4	3.4	3.0	3.0	2.6	2.6	2.6	2.1
90°	9.3	10.4	11.2	12.7	14.3	15.8	17.4	18.4	19.3	20.3	21.2
92.5°	18.7	18.3	18.6	19.2	19.7	20.3	20.9	21.3	21.7	22.0	22.4
95°	31.0	27.8	28.5	29.8	31.2	32.5	33.9	34.9	35.8	36.8	37.7
97.5°	38.3	30.4	31.9	35.0	38.1	41.2	44.3	44.9	45.5	46.0	46.6
100°	48.0	34.8	36.4	39.7	43.0	46.2	49.5	51.1	52.6	54.2	55.7
102.5°	209.7	209.5	191.9	156.8	121.6	86.5	51.3	53.4	55.5	57.6	59.7
105°	287.4	290.3	263.9	211.2	158.5	105.7	53.0	55.1	57.3	59.4	61.5
107.5°	345.3	347.7	315.2	250.1	185.0	119.9	54.8	56.9	59.0	61.1	63.2
110°	401.3	403.3	375.4	319.6	263.7	207.9	152.1	132.8	113.5	94.2	74.9

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	454.7	456.4	454.8	451.5	448.2	444.9	441.6	358.3	275.1	191.8	108.5
115°	513.0	514.6	517.0	521.8	526.7	531.5	536.3	446.9	357.5	268.0	178.6
117.5°	566.6	568.5	570.1	573.4	576.7	580.0	583.3	555.7	528.1	500.4	472.8
120°	620.1	621.5	623.2	626.7	630.2	633.7	637.2	639.5	641.8	644.1	646.4
122.5°	669.6	671.1	673.0	676.9	680.8	684.6	688.5	689.7	690.8	692.0	693.1
125°	716.7	718.0	719.8	723.5	727.2	730.8	734.5	735.9	737.2	738.6	739.9
127.5°	762.7	764.1	765.5	768.4	771.3	774.2	777.1	779.0	781.0	782.9	784.8
130°	806.9	808.4	809.5	811.6	813.7	815.9	818.0	820.1	822.2	824.3	826.4
132.5°	848.0	849.3	850.4	852.5	854.6	856.7	858.8	860.6	862.3	864.1	865.8
135°	886.9	888.4	889.3	891.0	892.7	894.5	896.2	898.1	900.1	902.0	903.9
137.5°	922.0	923.2	924.2	926.1	928.0	930.0	931.9	933.8	935.8	937.7	939.6
140°	956.3	957.1	958.2	960.3	962.4	964.5	966.6	968.4	970.1	971.9	973.6
142.5°	986.8	987.5	988.8	991.3	993.8	996.3	998.8	1000.3	1001.9	1003.4	1004.9
145°	1013.7	1013.6	1015.2	1018.5	1021.8	1025.0	1028.3	1029.7	1031.0	1032.4	1033.7
147.5°	1040.8	1040.5	1042.1	1045.4	1048.7	1052.0	1055.3	1056.3	1057.2	1058.2	1059.1
150°	1065.6	1064.9	1066.4	1069.5	1072.6	1075.7	1078.8	1080.0	1081.1	1082.3	1083.4
152.5°	1088.3	1087.5	1088.9	1091.8	1094.7	1097.6	1100.5	1101.7	1102.8	1104.0	1105.1
155°	1110.1	1109.2	1110.4	1112.7	1115.0	1117.3	1119.6	1120.8	1121.9	1123.1	1124.2
157.5°	1129.1	1128.3	1129.2	1130.9	1132.6	1134.4	1136.1	1137.5	1138.8	1140.2	1141.5
160°	1146.3	1145.7	1146.3	1147.4	1148.6	1149.7	1150.9	1152.1	1153.2	1154.4	1155.5
162.5°	1160.2	1159.6	1160.1	1161.1	1162.0	1163.0	1164.0	1165.3	1166.7	1168.0	1169.3
165°	1172.4	1171.8	1172.1	1172.7	1173.2	1173.8	1174.4	1175.8	1177.1	1178.5	1179.8
167.5°	1181.9	1181.3	1181.6	1182.2	1182.7	1183.3	1183.9	1185.3	1186.6	1188.0	1189.3
170°	1189.8	1189.2	1189.4	1189.8	1190.1	1190.5	1190.9	1192.3	1193.6	1195.0	1196.3
172.5°	1195.0	1194.4	1194.6	1195.0	1195.3	1195.7	1196.1	1197.5	1198.8	1200.2	1201.5
175°	1198.6	1197.9	1198.1	1198.5	1198.8	1199.2	1199.6	1201.0	1202.3	1203.7	1205.0
177.5°	1200.3	1199.6	1199.7	1199.9	1200.1	1200.3	1200.5	1201.8	1203.2	1204.5	1205.8
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	527.5	528.7	525.8	524.9	525.8	522.8	523.6	524.5	524.5	525.8	526.6
5°	496.8	495.1	492.2	491.3	490.5	491.7	490.9	492.2	492.6	495.6	496.0
7.5°	466.6	464.1	461.5	459.0	458.1	456.0	458.1	458.1	461.1	460.3	462.4
10°	430.9	430.5	427.1	425.8	424.1	420.7	425.4	424.1	426.2	430.1	430.9
12.5°	404.5	399.9	402.0	396.0	398.2	394.7	395.2	395.2	398.6	399.0	398.2
15°	379.4	375.6	370.1	367.5	366.2	364.5	370.1	370.5	368.0	373.9	371.8
17.5°	353.9	353.9	348.8	347.5	344.1	345.8	345.0	345.4	344.6	348.8	350.9
20°	331.8	329.7	328.0	328.4	324.1	323.3	322.4	323.3	326.3	329.2	330.1
22.5°	313.9	312.7	308.4	309.2	305.8	307.1	306.3	308.4	308.8	308.8	311.8
25°	296.9	295.2	295.6	293.9	292.7	292.7	291.4	292.7	294.4	295.2	295.6
27.5°	284.2	282.9	280.7	279.5	280.3	278.2	279.9	281.2	281.2	280.3	281.2
30°	268.8	269.7	269.7	265.4	267.1	266.3	267.6	268.4	268.4	268.8	268.0
32.5°	258.6	256.1	255.7	255.2	255.2	253.5	253.5	254.8	255.2	255.7	256.9
35°	245.0	245.0	242.9	244.2	242.5	242.9	242.5	242.9	243.7	242.5	243.7
37.5°	232.7	233.1	232.3	233.1	233.5	232.7	231.8	233.5	232.7	232.7	231.8
40°	222.0	221.6	222.0	222.0	222.0	222.5	221.6	221.6	221.6	220.8	219.9
42.5°	213.1	210.6	211.4	211.8	210.6	210.6	211.0	210.6	211.8	209.3	209.3
45°	200.4	199.5	199.9	199.9	200.8	199.5	200.4	200.8	199.5	199.1	198.2
47.5°	188.9	189.7	188.9	189.7	189.7	190.6	188.9	189.3	189.7	188.0	186.7
50°	177.4	177.4	178.7	178.2	178.7	177.8	177.8	177.4	177.8	177.0	175.7
52.5°	166.7	165.5	167.6	167.2	166.7	166.3	165.9	166.3	165.5	164.6	164.6
55°	153.6	153.6	154.8	155.3	155.3	154.4	153.6	154.0	153.6	153.1	152.7
57.5°	142.9	141.2	142.1	142.5	142.5	141.2	142.1	141.2	141.2	141.7	140.4
60°	129.3	129.3	128.5	129.7	129.7	128.9	128.9	129.3	128.5	128.0	127.6
62.5°	114.9	115.3	116.6	117.0	117.4	116.6	115.7	116.1	116.1	114.9	115.3
65°	102.5	103.4	105.1	104.6	103.8	104.2	103.4	103.8	102.5	102.9	101.7
67.5°	90.6	90.2	90.6	90.6	91.5	91.0	90.2	90.2	89.8	91.0	89.8
70°	77.8	77.8	77.8	77.8	78.3	78.7	77.8	77.0	77.4	76.6	76.1
72.5°	64.7	65.1	64.7	65.5	64.2	65.1	65.1	64.7	64.2	64.2	64.2
75°	52.3	53.2	51.9	52.3	51.9	52.7	52.3	52.3	51.5	51.0	51.5
77.5°	40.0	40.4	39.6	40.0	39.6	40.0	40.0	39.6	39.6	39.6	39.6
80°	28.5	28.9	28.5	28.1	27.6	28.5	27.6	28.1	28.5	28.1	28.9
82.5°	18.3	18.3	17.9	18.3	17.4	17.4	17.9	17.9	17.4	18.3	17.4
85°	8.9	8.9	9.8	8.9	8.5	8.5	8.5	8.9	8.5	9.4	8.9
87.5°	2.1	1.7	2.1	2.1	1.7	1.7	2.1	1.7	2.1	2.6	1.7
90°	21.7	21.9	22.3	22.7	23.1	23.5	23.1	22.7	22.3	21.9	21.7
92.5°	22.6	22.7	22.9	23.1	23.3	23.5	23.3	23.1	22.9	22.7	22.6
95°	38.2	38.1	37.9	37.8	37.6	37.4	37.6	37.8	37.9	38.1	38.2
97.5°	46.9	47.0	47.2	47.4	47.6	47.8	47.6	47.4	47.2	47.0	46.9
100°	56.5	56.7	57.1	57.4	57.8	58.2	57.8	57.4	57.1	56.7	56.5
102.5°	60.8	61.1	61.7	62.3	62.9	63.5	62.9	62.3	61.7	61.1	60.8
105°	62.6	63.0	63.8	64.5	65.3	66.1	65.3	64.5	63.8	63.0	62.6
107.5°	64.3	64.7	65.5	66.2	67.0	67.8	67.0	66.2	65.5	64.7	64.3
110°	65.2	65.6	66.4	67.1	67.9	68.7	67.9	67.1	66.4	65.6	65.2

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	66.9	67.2	67.8	68.3	68.9	69.5	68.9	68.3	67.8	67.2	66.9
115°	133.9	126.9	113.0	99.1	85.2	71.3	85.2	99.1	113.0	126.9	133.9
117.5°	459.0	433.7	383.1	332.4	281.8	231.2	281.8	332.4	383.1	433.7	459.0
120°	647.6	634.6	608.5	582.4	556.4	530.3	556.4	582.4	608.5	634.6	647.6
122.5°	693.7	693.8	694.0	694.1	694.3	694.5	694.3	694.1	694.0	693.8	693.7
125°	740.6	740.9	741.5	742.0	742.6	743.2	742.6	742.0	741.5	740.9	740.6
127.5°	785.8	785.9	786.1	786.3	786.5	786.7	786.5	786.3	786.1	785.9	785.8
130°	827.5	827.4	827.2	827.1	826.9	826.7	826.9	827.1	827.2	827.4	827.5
132.5°	866.7	866.6	866.4	866.2	866.0	865.8	866.0	866.2	866.4	866.6	866.7
135°	904.9	904.7	904.3	904.0	903.6	903.2	903.6	904.0	904.3	904.7	904.9
137.5°	940.6	940.3	939.7	939.1	938.5	937.9	938.5	939.1	939.7	940.3	940.6
140°	974.5	974.0	973.0	972.1	971.1	970.1	971.1	972.1	973.0	974.0	974.5
142.5°	1005.7	1005.2	1004.3	1003.3	1002.4	1001.4	1002.4	1003.3	1004.3	1005.2	1005.7
145°	1034.4	1033.9	1033.0	1032.0	1031.1	1030.1	1031.1	1032.0	1033.0	1033.9	1034.4
147.5°	1059.6	1059.2	1058.5	1057.7	1057.0	1056.2	1057.0	1057.7	1058.5	1059.2	1059.6
150°	1084.0	1083.5	1082.5	1081.6	1080.6	1079.6	1080.6	1081.6	1082.5	1083.5	1084.0
152.5°	1105.7	1105.0	1103.7	1102.3	1101.0	1099.6	1101.0	1102.3	1103.7	1105.0	1105.7
155°	1124.8	1124.0	1122.5	1121.0	1119.4	1117.9	1119.4	1121.0	1122.5	1124.0	1124.8
157.5°	1142.2	1141.4	1139.9	1138.4	1136.8	1135.3	1136.8	1138.4	1139.9	1141.4	1142.2
160°	1156.1	1155.4	1154.1	1152.7	1151.4	1150.0	1151.4	1152.7	1154.1	1155.4	1156.1
162.5°	1170.0	1169.1	1167.4	1165.7	1163.9	1162.2	1163.9	1165.7	1167.4	1169.1	1170.0
165°	1180.5	1179.8	1178.5	1177.1	1175.8	1174.4	1175.8	1177.1	1178.5	1179.8	1180.5
167.5°	1190.0	1189.1	1187.4	1185.7	1183.9	1182.2	1183.9	1185.7	1187.4	1189.1	1190.0
170°	1197.0	1196.1	1194.4	1192.7	1190.9	1189.2	1190.9	1192.7	1194.4	1196.1	1197.0
172.5°	1202.2	1201.3	1199.6	1197.9	1196.1	1194.4	1196.1	1197.9	1199.6	1201.3	1202.2
175°	1205.7	1204.7	1202.8	1200.9	1198.9	1197.0	1198.9	1200.9	1202.8	1204.7	1205.7
177.5°	1206.5	1205.6	1203.9	1202.2	1200.4	1198.7	1200.4	1202.2	1203.9	1205.6	1206.5
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	525.3	528.7	527.5	522.8	528.3	528.3	532.1	532.1	536.8	538.5	541.1
5°	495.6	498.1	500.2	498.1	501.9	507.9	511.3	514.3	520.7	523.2	527.0
7.5°	463.7	468.3	470.5	470.5	476.8	483.7	490.5	494.7	503.6	507.0	510.9
10°	432.6	438.1	442.4	442.0	452.6	456.9	465.4	475.1	484.1	489.2	494.7
12.5°	399.9	402.8	408.8	417.3	419.8	427.5	437.3	449.6	465.8	470.5	478.5
15°	372.6	380.7	385.4	389.2	395.2	402.4	413.0	425.0	441.1	451.3	459.8
17.5°	349.7	360.3	363.3	362.4	370.1	381.1	393.5	402.4	416.9	429.2	437.3
20°	330.9	335.2	340.3	342.4	348.4	360.3	372.2	382.4	394.3	404.1	413.5
22.5°	312.2	315.6	319.9	323.7	328.4	335.2	346.7	359.4	370.9	380.3	390.9
25°	296.9	299.0	302.9	305.8	310.9	315.6	323.7	337.7	351.4	356.9	366.2
27.5°	282.0	283.7	286.3	289.7	292.2	296.9	304.1	315.6	329.7	335.2	348.0
30°	268.8	270.1	272.7	274.4	275.6	281.2	286.7	295.6	306.3	313.9	323.3
32.5°	256.5	257.8	260.3	260.8	262.5	265.4	270.5	278.6	288.0	294.4	302.4
35°	242.9	243.7	246.3	247.1	248.4	251.0	254.8	260.8	269.3	273.9	281.2
37.5°	232.3	231.8	233.5	234.8	236.5	237.8	239.1	245.0	251.4	255.7	261.2
40°	220.8	219.9	220.3	222.0	222.9	224.6	224.6	230.6	234.8	238.2	242.5
42.5°	209.3	208.9	208.0	208.9	209.7	210.1	210.6	214.8	219.1	222.0	226.7
45°	197.8	197.4	196.5	196.9	196.9	197.8	199.1	200.8	203.8	206.3	208.9
47.5°	187.2	186.3	185.0	184.6	185.5	185.5	185.5	187.2	190.1	191.0	193.5
50°	176.1	174.8	173.1	172.3	172.3	171.9	172.7	173.1	175.7	176.5	178.7
52.5°	164.2	163.3	161.6	159.9	160.4	159.5	159.9	160.4	161.2	162.5	163.8
55°	152.3	150.6	149.3	148.9	147.6	147.6	146.3	148.0	147.6	148.0	149.7
57.5°	140.8	139.1	137.0	136.1	134.8	134.4	133.6	133.1	133.6	134.8	136.1
60°	127.2	126.3	125.1	123.8	122.9	121.7	120.8	120.8	120.4	120.4	120.8
62.5°	114.0	113.6	111.9	111.4	110.6	109.7	108.5	107.6	107.6	108.5	108.9
65°	101.2	100.8	99.5	99.1	97.0	96.1	95.7	95.3	94.4	94.4	94.4
67.5°	89.3	88.1	88.1	85.9	84.2	83.4	82.5	82.1	82.1	82.1	82.5
70°	76.1	76.1	74.9	73.6	71.9	72.3	71.0	69.8	69.8	68.9	69.3
72.5°	63.4	63.0	61.7	61.3	60.0	58.7	57.9	58.7	57.4	57.0	57.4
75°	51.0	50.6	49.8	48.9	49.3	48.1	46.8	46.4	46.4	45.5	45.5
77.5°	39.1	40.0	38.3	37.9	37.0	36.2	35.7	35.3	35.3	35.3	36.2
80°	27.2	27.6	27.6	26.8	27.2	25.9	25.9	25.9	24.7	25.1	25.5
82.5°	17.4	17.4	17.0	17.4	17.0	17.0	16.6	16.6	16.2	16.2	16.6
85°	9.8	9.4	8.9	9.8	9.4	9.4	8.9	8.9	8.9	8.9	8.9
87.5°	2.1	2.6	2.6	2.6	2.6	3.0	3.0	3.0	3.4	3.4	3.4
90°	21.2	20.3	19.3	18.4	17.4	15.8	14.3	12.7	11.2	10.4	9.3
92.5°	22.4	22.0	21.7	21.3	20.9	20.3	19.7	19.2	18.6	18.3	18.7
95°	37.7	36.8	35.8	34.9	33.9	32.5	31.2	29.8	28.5	27.8	31.0
97.5°	46.6	46.0	45.5	44.9	44.3	41.2	38.1	35.0	31.9	30.4	38.3
100°	55.7	54.2	52.6	51.1	49.5	46.2	43.0	39.7	36.4	34.8	48.0
102.5°	59.7	57.6	55.5	53.4	51.3	86.5	121.6	156.8	191.9	209.5	209.7
105°	61.5	59.4	57.3	55.1	53.0	105.7	158.5	211.2	263.9	290.3	287.4
107.5°	63.2	61.1	59.0	56.9	54.8	119.9	185.0	250.1	315.2	347.7	345.3
110°	74.9	94.2	113.5	132.8	152.1	207.9	263.7	319.6	375.4	403.3	401.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	108.5	191.8	275.1	358.3	441.6	444.9	448.2	451.5	454.8	456.4	454.7
115°	178.6	268.0	357.5	446.9	536.3	531.5	526.7	521.8	517.0	514.6	513.0
117.5°	472.8	500.4	528.1	555.7	583.3	580.0	576.7	573.4	570.1	568.5	566.6
120°	646.4	644.1	641.8	639.5	637.2	633.7	630.2	626.7	623.2	621.5	620.1
122.5°	693.1	692.0	690.8	689.7	688.5	684.6	680.8	676.9	673.0	671.1	669.6
125°	739.9	738.6	737.2	735.9	734.5	730.8	727.2	723.5	719.8	718.0	716.7
127.5°	784.8	782.9	781.0	779.0	777.1	774.2	771.3	768.4	765.5	764.1	762.7
130°	826.4	824.3	822.2	820.1	818.0	815.9	813.7	811.6	809.5	808.4	806.9
132.5°	865.8	864.1	862.3	860.6	858.8	856.7	854.6	852.5	850.4	849.3	848.0
135°	903.9	902.0	900.1	898.1	896.2	894.5	892.7	891.0	889.3	888.4	886.9
137.5°	939.6	937.7	935.8	933.8	931.9	930.0	928.0	926.1	924.2	923.2	922.0
140°	973.6	971.9	970.1	968.4	966.6	964.5	962.4	960.3	958.2	957.1	956.3
142.5°	1004.9	1003.4	1001.9	1000.3	998.8	996.3	993.8	991.3	988.8	987.5	986.8
145°	1033.7	1032.4	1031.0	1029.7	1028.3	1025.0	1021.8	1018.5	1015.2	1013.6	1013.7
147.5°	1059.1	1058.2	1057.2	1056.3	1055.3	1052.0	1048.7	1045.4	1042.1	1040.5	1040.8
150°	1083.4	1082.3	1081.1	1080.0	1078.8	1075.7	1072.6	1069.5	1066.4	1064.9	1065.6
152.5°	1105.1	1104.0	1102.8	1101.7	1100.5	1097.6	1094.7	1091.8	1088.9	1087.5	1088.3
155°	1124.2	1123.1	1121.9	1120.8	1119.6	1117.3	1115.0	1112.7	1110.4	1109.2	1110.1
157.5°	1141.5	1140.2	1138.8	1137.5	1136.1	1134.4	1132.6	1130.9	1129.2	1128.3	1129.1
160°	1155.5	1154.4	1153.2	1152.1	1150.9	1149.7	1148.6	1147.4	1146.3	1145.7	1146.3
162.5°	1169.3	1168.0	1166.7	1165.3	1164.0	1163.0	1162.0	1161.1	1160.1	1159.6	1160.2
165°	1179.8	1178.5	1177.1	1175.8	1174.4	1173.8	1173.2	1172.7	1172.1	1171.8	1172.4
167.5°	1189.3	1188.0	1186.6	1185.3	1183.9	1183.3	1182.7	1182.2	1181.6	1181.3	1181.9
170°	1196.3	1195.0	1193.6	1192.3	1190.9	1190.5	1190.1	1189.8	1189.4	1189.2	1189.8
172.5°	1201.5	1200.2	1198.8	1197.5	1196.1	1195.7	1195.3	1195.0	1194.6	1194.4	1195.0
175°	1205.0	1203.7	1202.3	1201.0	1199.6	1199.2	1198.8	1198.5	1198.1	1197.9	1198.6
177.5°	1205.8	1204.5	1203.2	1201.8	1200.5	1200.3	1200.1	1199.9	1199.7	1199.6	1200.3
180°	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3	1201.3

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	553.4	553.4	553.4	553.4
2.5°	543.2	543.2	549.6	556.4
5°	531.3	534.3	544.5	553.8
7.5°	519.8	524.9	537.7	549.6
10°	505.8	512.6	528.3	542.4
12.5°	492.2	498.5	516.8	532.6
15°	473.0	481.1	500.7	520.2
17.5°	453.9	462.0	485.8	508.7
20°	431.3	442.0	468.8	499.4
22.5°	410.5	423.7	453.5	478.1
25°	387.5	407.9	435.6	467.5
27.5°	367.1	387.5	415.6	447.9
30°	344.1	365.0	393.9	423.7
32.5°	322.0	341.2	369.2	405.8
35°	299.0	317.3	344.6	381.6
37.5°	278.2	296.1	325.8	359.9
40°	257.8	276.5	302.0	336.0
42.5°	238.6	255.2	278.2	312.2
45°	221.2	233.1	254.4	286.3
47.5°	202.9	213.5	233.1	265.0
50°	185.9	194.8	211.8	241.6
52.5°	169.3	177.0	192.7	216.5
55°	154.4	161.6	173.1	196.5
57.5°	139.1	144.6	155.7	174.4
60°	124.2	129.3	138.2	153.6
62.5°	109.3	113.6	122.1	134.4
65°	96.1	99.5	105.9	116.6
67.5°	83.4	85.5	90.6	99.1
70°	71.0	72.7	77.0	83.8
72.5°	57.9	59.6	64.2	68.9
75°	46.8	47.2	50.6	54.4
77.5°	36.6	36.2	38.7	41.7
80°	25.1	26.4	28.5	29.8
82.5°	17.0	17.4	18.3	19.1
85°	9.4	9.8	9.8	11.1
87.5°	3.8	4.3	4.3	4.7
90°	7.2	5.1	3.0	0.9
92.5°	19.4	20.2	20.9	21.7
95°	37.4	43.7	50.1	56.5
97.5°	54.2	70.0	85.9	101.7
100°	74.5	101.0	127.4	153.9
102.5°	210.1	210.4	210.8	211.2
105°	281.6	275.9	270.1	264.3
107.5°	340.5	335.6	330.8	326.0
110°	397.2	393.2	389.1	385.1

TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	451.2	447.7	444.2	440.7
115°	509.7	506.4	503.1	499.8
117.5°	562.7	558.8	555.0	551.1
120°	617.2	614.3	611.4	608.5
122.5°	666.5	663.4	660.3	657.2
125°	714.2	711.7	709.2	706.7
127.5°	760.0	757.3	754.6	751.9
130°	803.8	800.7	797.6	794.5
132.5°	845.5	843.0	840.5	838.0
135°	883.8	880.7	877.6	874.5
137.5°	919.7	917.4	915.0	912.7
140°	954.8	953.2	951.7	950.1
142.5°	985.5	984.1	982.8	981.4
145°	1013.9	1014.0	1014.2	1014.4
147.5°	1041.4	1041.9	1042.5	1043.1
150°	1066.9	1068.2	1069.6	1070.9
152.5°	1089.8	1091.3	1092.9	1094.4
155°	1111.8	1113.5	1115.3	1117.0
157.5°	1130.6	1132.2	1133.7	1135.3
160°	1147.4	1148.6	1149.7	1150.9
162.5°	1161.3	1162.5	1163.6	1164.8
165°	1173.5	1174.7	1175.8	1177.0
167.5°	1183.1	1184.2	1185.4	1186.6
170°	1190.9	1192.1	1193.2	1194.4
172.5°	1196.1	1197.3	1198.4	1199.6
175°	1199.9	1201.2	1202.6	1203.9
177.5°	1201.6	1203.0	1204.3	1205.7
180°	1201.3	1201.3	1201.3	1201.3



TEST NUMBER: P998369

CATALOG NUMBER: SA2XXDIP-B290D925UB50-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.53	11.20	11.68	12.33	13.91	8.03	8.69	9.17	9.82	11.40
	3H	11.33	11.92	12.48	13.06	14.66	9.36	9.95	10.51	11.09	12.69
	4H	11.49	12.05	12.65	13.19	14.80	9.81	10.37	10.97	11.51	13.12
	6H	11.53	12.04	12.69	13.19	14.80	10.11	10.63	11.28	11.77	13.38
	8H	11.50	11.99	12.67	13.15	14.75	10.19	10.68	11.36	11.84	13.44
	12H	11.46	11.92	12.63	13.07	14.70	10.22	10.69	11.40	11.84	13.47
4H	2H	10.55	11.12	11.72	12.26	13.86	8.45	9.01	9.62	10.15	11.75
	3H	11.51	11.98	12.69	13.15	14.76	9.89	10.36	11.07	11.53	13.14
	4H	11.78	12.22	12.96	13.37	15.00	10.42	10.85	11.59	12.00	13.64
	6H	11.90	12.27	13.08	13.45	15.07	10.79	11.16	11.97	12.33	13.96
	8H	11.90	12.24	13.08	13.41	15.05	10.89	11.24	12.07	12.41	14.05
	12H	11.85	12.17	13.05	13.34	14.99	10.94	11.25	12.14	12.43	14.08
8H	4H	11.78	12.12	12.96	13.29	14.93	10.55	10.89	11.73	12.06	13.70
	6H	11.95	12.23	13.15	13.44	15.08	10.97	11.26	12.17	12.47	14.10
	8H	11.98	12.23	13.18	13.41	15.07	11.12	11.37	12.33	12.56	14.21
	12H	11.95	12.17	13.16	13.36	15.04	11.21	11.42	12.41	12.61	14.30
12H	4H	11.73	12.04	12.92	13.22	14.86	10.51	10.82	11.71	12.00	13.65
	6H	11.93	12.17	13.13	13.36	15.02	10.97	11.22	12.18	12.41	14.06
	8H	11.95	12.17	13.16	13.35	15.04	11.12	11.34	12.33	12.52	14.21