

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999411

Luminaire Tested: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999411
REPORT IS A COMBINATION OF REPORTS P987962 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6615.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	93	90	94	90	87	84	78	76	74	67	66	64	58	56	55
2	92	85	80	75	86	80	75	71	70	66	63	60	58	55	52	50	48
3	85	76	69	64	79	71	65	60	62	58	54	54	51	48	47	44	42
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	43	40	37
5	72	61	53	48	67	58	51	46	51	46	41	45	41	37	39	36	33
6	67	55	48	42	62	52	45	40	46	41	37	41	37	33	36	32	30
7	62	50	43	37	58	48	41	36	42	37	33	38	33	30	33	30	27
8	58	46	39	34	54	44	37	32	39	34	30	35	30	27	31	27	25
9	54	42	35	30	51	40	34	29	36	31	27	32	28	25	28	25	22
10	51	39	32	28	48	37	31	27	34	28	25	30	26	23	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35136	35136	35136	35136
5°	35219	37321	35341	29815
10°	34832	39447	35078	24620
15°	34076	39460	34652	18497
20°	33166	32618	33887	15259
25°	32063	20381	32758	12981
30°	30656	13049	31490	11176
35°	28945	10028	29881	9564
40°	27037	8430	28191	8366
45°	24998	7174	26042	7022
50°	22907	6096	23978	6075
55°	20592	5297	21703	5228
60°	18538	4040	19518	3991
65°	16616	3041	17604	3448
70°	14495	2429	15634	2811
75°	12251	1860	13375	2126
80°	9732	1266	10467	1394
85°	6752	654	7402	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 32142 cd/sqm

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.5	3.2
10°-20°	587.7	8.9
20°-30°	756.4	11.4
30°-40°	717.5	10.8
40°-50°	615.0	9.3
50°-60°	468.3	7.1
60°-70°	295.3	4.5
70°-80°	147.3	2.2
80°-90°	40.4	0.6
90°-100°	155.4	2.3
100°-110°	547.3	8.3
110°-120°	574.8	8.7
120°-130°	472.9	7.1
130°-140°	379.9	5.7
140°-150°	287.0	4.3
150°-160°	201.7	3.0
160°-170°	118.8	1.8
170°-180°	38.6	0.6
0°-30°	1554.6	23.5
0°-40°	2272.1	34.3
0°-60°	3355.4	50.7
0°-90°	3838.6	58.0
90°-120°	1277.5	19.3
90°-150°	2417.3	36.5
90°-180°	2776.0	42.0
0°-180°	6615.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2220	2220	2220	2220	2220	
5°	2221	2470	2229	1973	2221	211
15°	2093	2787	2129	1307	2093	589
25°	1857	1487	1897	947	1857	853
35°	1524	733	1573	699	1524	954
45°	1145	509	1192	498	1145	883
55°	773	353	814	349	773	696
65°	467	184	495	208	467	464
75°	219	97	239	111	219	237
85°	48	28	52	29	48	54
90°	1	25	1	25	1	5
95°	27	87	27	87	27	28
105°	94	864	94	864	94	99
115°	165	1137	165	1137	165	163
125°	230	922	230	922	230	204
135°	270	764	270	764	270	208
145°	308	610	308	610	308	193
155°	350	513	350	513	350	161
165°	382	450	382	450	382	108
175°	398	406	398	406	398	38
180°	399	399	399	399	399	

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2233.6	2242.9	2247.5	2253.7	2267.6	2276.8	2290.7	2293.8	2292.2	2298.4	2281.5
5°	2221.3	2241.3	2259.9	2275.3	2300.0	2315.4	2332.4	2352.4	2357.0	2380.2	2366.3
7.5°	2204.3	2233.6	2259.9	2290.7	2327.7	2347.8	2374.0	2404.9	2418.7	2446.5	2454.2
10°	2176.6	2218.2	2262.9	2295.3	2346.2	2381.7	2406.4	2455.8	2488.2	2529.8	2523.6
12.5°	2131.8	2185.8	2246.0	2300.0	2366.3	2389.4	2435.7	2486.6	2528.3	2566.8	2600.8
15°	2093.3	2155.0	2221.3	2287.6	2363.2	2406.4	2452.7	2519.0	2563.7	2631.6	2660.9
17.5°	2040.8	2119.5	2198.2	2272.2	2361.7	2411.0	2468.1	2532.9	2599.2	2664.0	2687.1
20°	1986.8	2071.7	2156.5	2256.8	2358.6	2406.4	2465.0	2545.2	2610.0	2660.9	2660.9
22.5°	1922.0	2025.4	2122.6	2218.2	2329.3	2398.7	2458.8	2552.9	2599.2	2610.0	2568.4
25°	1857.2	1960.6	2067.0	2185.8	2312.3	2374.0	2441.9	2529.8	2545.2	2502.0	2394.1
27.5°	1780.1	1895.8	2016.1	2144.2	2276.8	2354.0	2415.7	2474.3	2445.0	2329.3	2161.1
30°	1701.4	1826.4	1962.1	2084.0	2244.4	2315.4	2367.8	2384.8	2292.2	2104.1	1886.6
32.5°	1619.7	1741.6	1885.0	2031.6	2193.5	2261.4	2295.3	2250.6	2080.9	1843.4	1578.0
35°	1524.1	1661.3	1811.0	1963.7	2124.1	2175.0	2195.1	2085.5	1868.0	1561.1	1297.3
37.5°	1437.7	1575.0	1735.4	1891.2	2047.0	2074.7	2054.7	1883.5	1607.4	1303.5	1045.9
40°	1335.9	1482.4	1639.7	1814.1	1942.1	1949.8	1900.4	1678.3	1335.9	1050.5	891.6
42.5°	1241.8	1389.8	1547.2	1724.6	1821.8	1795.5	1729.2	1437.7	1115.3	905.5	777.5
45°	1144.6	1285.0	1454.6	1612.0	1681.4	1619.7	1519.4	1209.4	936.3	779.0	680.3
47.5°	1050.5	1181.6	1349.7	1500.9	1513.3	1443.8	1325.1	1013.5	811.4	684.9	604.7
50°	957.9	1089.0	1246.4	1371.3	1359.0	1263.4	1129.2	880.8	705.0	604.7	538.4
52.5°	865.4	984.2	1136.9	1235.6	1183.1	1090.6	957.9	746.6	615.5	527.6	476.7
55°	772.8	883.9	1015.0	1096.8	1013.5	907.0	812.9	640.2	533.7	462.8	424.2
57.5°	695.7	783.6	903.9	953.3	853.0	769.7	688.0	550.7	462.8	411.9	367.1
60°	610.9	691.1	789.8	819.1	715.7	647.9	578.5	465.9	396.4	351.7	322.4
62.5°	538.4	604.7	680.3	680.3	589.3	538.4	485.9	390.3	333.2	297.7	283.8
65°	467.4	515.2	569.2	563.0	485.9	441.2	399.5	322.4	279.2	254.5	240.6
67.5°	398.0	435.0	470.5	448.9	393.4	354.8	316.2	260.7	231.4	214.4	195.9
70°	334.7	364.0	382.6	362.5	307.0	274.6	246.8	209.8	186.7	165.1	154.3
72.5°	280.7	293.1	299.3	274.6	228.3	209.8	189.7	163.5	143.5	132.7	129.6
75°	219.0	229.8	225.2	206.7	168.1	154.3	138.8	120.3	115.7	109.5	106.4
77.5°	171.2	171.2	163.5	146.5	120.3	109.5	103.4	94.1	89.5	87.9	84.8
80°	121.9	120.3	115.7	97.2	81.8	75.6	75.6	69.4	67.9	64.8	64.8
82.5°	80.2	80.2	74.0	58.6	54.0	52.4	50.9	47.8	47.8	46.3	46.3
85°	47.8	44.7	37.0	32.4	30.9	30.9	29.3	27.8	29.3	27.8	27.8
87.5°	21.6	17.0	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
90°	0.8	3.1	6.1	7.7	9.2	10.4	11.5	15.3	20.7	25.3	26.1
92.5°	11.5	16.1	22.2	26.1	32.2	36.4	40.6	61.3	90.5	116.5	118.1
95°	26.8	29.9	37.6	44.5	56.7	65.9	75.1	110.4	177.1	266.0	300.5
97.5°	39.9	44.5	52.9	62.9	76.7	87.1	97.4	142.6	235.4	378.7	489.9
100°	59.0	61.3	68.2	80.5	95.8	106.6	117.3	157.9	251.5	417.1	605.7
102.5°	76.7	78.2	85.1	97.4	113.5	124.2	134.9	171.7	252.2	402.5	609.5
105°	93.5	96.6	102.0	113.5	130.3	141.0	151.8	187.8	256.1	382.6	568.1
107.5°	111.9	114.2	119.6	130.3	147.2	158.0	168.7	203.9	264.5	371.8	529.8
110°	130.3	133.4	138.0	148.0	164.1	175.2	186.3	220.0	275.2	368.8	503.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	147.2	150.3	155.6	164.8	180.2	191.7	203.2	235.4	286.7	369.5	486.9
115°	164.8	168.7	173.3	182.5	197.8	208.2	218.5	251.5	298.2	372.6	475.4
117.5°	183.2	186.3	190.9	199.3	213.9	224.6	235.4	266.0	310.5	377.2	469.2
120°	200.1	203.2	207.8	214.7	230.0	240.8	251.5	281.4	322.8	381.8	463.9
122.5°	216.2	218.5	223.1	230.8	246.1	257.2	268.3	295.9	333.5	387.2	460.8
125°	230.0	232.3	236.9	246.1	261.4	272.2	282.9	310.5	345.0	392.5	457.0
127.5°	241.5	244.6	250.7	260.7	275.2	286.4	297.5	324.3	355.7	397.9	454.7
130°	251.5	254.5	262.2	272.9	288.3	299.0	309.7	336.6	365.7	404.0	453.1
132.5°	260.7	264.5	272.9	284.4	300.5	311.2	322.0	347.3	375.7	410.2	452.4
135°	269.9	272.9	282.1	293.6	311.3	322.0	332.7	357.3	384.1	414.8	451.6
137.5°	278.3	282.1	291.3	303.6	321.2	331.2	341.2	365.7	391.0	419.4	451.6
140°	288.3	291.3	300.5	312.8	329.7	339.6	349.6	372.6	396.4	422.5	450.8
142.5°	298.2	300.5	309.0	321.2	337.3	346.5	355.7	378.0	401.0	424.8	450.8
145°	308.2	311.3	318.9	330.4	345.8	354.2	362.6	383.3	404.8	426.3	449.3
147.5°	318.9	321.2	328.9	339.6	352.7	360.4	368.0	387.9	407.1	427.1	447.0
150°	329.7	332.0	338.1	348.1	359.6	366.5	373.4	391.0	408.6	426.3	444.7
152.5°	340.4	341.2	347.3	355.7	366.5	372.6	378.7	394.1	409.4	424.8	440.9
155°	350.4	351.1	355.7	364.2	372.6	378.4	384.1	397.1	410.2	423.2	436.3
157.5°	358.8	359.6	363.4	371.1	378.0	383.0	387.9	399.4	410.2	420.2	431.7
160°	367.2	368.0	371.1	377.2	383.3	387.6	391.8	401.0	410.2	417.9	427.1
162.5°	375.7	374.9	378.0	382.6	387.9	391.0	394.1	401.7	409.4	415.6	423.2
165°	381.8	381.0	382.6	387.2	391.0	393.3	395.6	402.5	407.9	412.5	417.9
167.5°	387.2	386.4	387.9	391.0	394.1	395.6	397.1	402.5	407.1	409.4	413.3
170°	392.5	391.0	391.8	394.1	395.6	396.8	397.9	401.7	405.6	407.1	409.4
172.5°	395.6	394.8	394.1	396.4	397.1	397.9	398.7	401.0	403.3	404.0	404.8
175°	397.9	397.1	396.4	397.9	397.9	398.3	398.7	400.2	401.7	401.0	401.7
177.5°	399.4	397.9	397.1	398.7	398.7	398.7	398.7	399.4	401.0	399.4	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2298.4	2301.5	2306.1	2327.7	2330.8	2337.0	2333.9	2333.9	2335.4	2332.4	2333.9
5°	2397.1	2401.8	2424.9	2451.1	2457.3	2451.1	2458.8	2469.6	2469.6	2469.6	2466.6
7.5°	2489.7	2506.7	2532.9	2571.5	2579.2	2586.9	2600.8	2591.5	2594.6	2608.5	2603.8
10°	2579.2	2603.8	2633.2	2665.5	2682.5	2693.3	2699.5	2713.4	2745.8	2708.7	2722.6
12.5°	2664.0	2699.5	2730.3	2765.8	2778.2	2792.0	2796.7	2809.0	2809.0	2807.5	2818.3
15°	2719.5	2751.9	2779.7	2802.8	2805.9	2802.8	2799.8	2801.3	2805.9	2787.4	2798.2
17.5°	2731.9	2735.0	2744.2	2735.0	2736.5	2704.1	2685.6	2681.0	2637.8	2639.3	2674.8
20°	2671.7	2619.3	2605.4	2554.5	2523.6	2440.3	2437.2	2414.1	2323.1	2350.9	2344.7
22.5°	2506.7	2417.2	2298.4	2239.8	2210.5	2122.6	2054.7	2006.9	1974.5	1942.1	1928.2
25°	2289.2	2144.2	1976.0	1860.3	1843.4	1761.6	1636.7	1578.0	1508.6	1487.0	1524.1
27.5°	2008.4	1820.2	1630.5	1453.1	1420.7	1346.7	1283.4	1241.8	1161.5	1156.9	1160.0
30°	1627.4	1437.7	1278.8	1163.1	1082.9	1048.9	1007.3	976.4	944.0	956.4	959.5
32.5°	1337.4	1156.9	1008.8	947.1	910.1	888.5	853.0	833.0	819.1	814.5	812.9
35°	1062.8	942.5	876.2	816.0	794.4	779.0	752.8	743.5	731.2	732.7	732.7
37.5°	910.1	809.8	760.5	729.6	709.6	701.9	684.9	675.6	667.9	664.8	669.5
40°	785.2	715.7	684.9	657.1	640.2	637.1	627.8	617.0	607.8	609.3	613.9
42.5°	694.2	654.0	617.0	595.4	583.1	578.5	570.7	563.0	563.0	558.4	556.9
45°	621.7	589.3	558.4	538.4	530.6	524.5	515.2	513.7	507.5	509.0	510.6
47.5°	556.9	530.6	507.5	487.4	479.7	478.2	468.9	462.8	462.8	461.2	459.7
50°	498.2	472.0	452.0	441.2	430.4	427.3	425.7	424.2	421.1	421.1	422.7
52.5°	450.4	424.2	408.8	399.5	393.4	390.3	390.3	388.7	388.7	388.7	387.2
55°	398.0	376.4	364.0	361.0	357.9	356.3	354.8	351.7	350.2	353.2	350.2
57.5°	348.6	340.9	330.1	327.0	319.3	319.3	314.7	311.6	308.5	311.6	311.6
60°	310.1	299.3	293.1	283.8	277.7	271.5	263.8	262.2	259.2	257.6	256.1
62.5°	269.9	260.7	245.3	231.4	222.1	216.0	212.9	211.3	211.3	209.8	209.8
65°	225.2	203.6	195.9	191.3	189.7	188.2	185.1	183.6	185.1	183.6	185.1
67.5°	175.9	172.8	168.1	165.1	163.5	162.0	162.0	160.4	160.4	160.4	160.4
70°	152.7	145.0	143.5	140.4	140.4	138.8	138.8	138.8	138.8	137.3	140.4
72.5°	126.5	121.9	120.3	118.8	118.8	118.8	117.2	117.2	117.2	115.7	117.2
75°	103.4	101.8	98.7	98.7	97.2	98.7	97.2	97.2	95.6	97.2	97.2
77.5°	83.3	81.8	80.2	80.2	78.7	78.7	78.7	78.7	78.7	78.7	80.2
80°	63.2	61.7	60.2	61.7	60.2	61.7	60.2	60.2	61.7	60.2	60.2
82.5°	46.3	44.7	44.7	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2
85°	27.8	26.2	26.2	27.8	26.2	27.8	26.2	26.2	26.2	27.8	27.8
87.5°	12.3	13.9	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	13.9
90°	25.3	24.5	23.0	24.5	24.9	25.3	25.3	25.3	25.3	25.3	25.3
92.5°	98.9	77.4	65.9	57.5	54.4	51.4	50.6	47.5	48.3	46.8	48.3
95°	263.0	200.9	154.1	121.9	113.4	105.0	95.1	88.9	86.6	87.4	86.6
97.5°	493.8	410.9	328.1	250.7	227.7	204.7	174.8	159.5	151.0	146.4	151.0
100°	716.1	700.0	604.9	499.9	453.5	407.1	343.5	310.5	288.3	274.5	288.3
102.5°	798.9	889.4	886.3	816.5	766.7	716.9	646.3	584.2	555.1	535.2	555.1
105°	772.1	931.5	1018.2	1028.1	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8
107.5°	715.3	886.3	1015.1	1090.2	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3
110°	662.4	824.2	961.4	1059.6	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	625.6	767.5	897.8	1004.4	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2
115°	596.5	723.0	841.1	941.5	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1
117.5°	576.6	686.2	792.0	885.5	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9
120°	561.2	660.1	755.2	836.5	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2
122.5°	548.2	639.4	724.5	800.4	831.1	861.8	908.5	943.8	963.0	969.1	963.0
125°	535.9	619.5	698.5	765.9	794.6	823.4	867.9	897.0	916.2	922.3	916.2
127.5°	524.4	599.6	672.4	736.8	763.6	790.5	829.6	857.2	874.0	878.6	874.0
130°	512.9	580.4	646.3	706.9	732.2	757.5	795.1	821.1	836.5	842.6	836.5
132.5°	503.7	562.0	621.8	676.2	699.6	723.0	759.8	785.9	799.7	805.0	799.7
135°	495.3	545.1	595.7	646.3	667.8	689.3	722.2	747.5	761.3	764.4	761.3
137.5°	489.2	531.3	575.0	616.4	635.6	654.8	686.2	708.4	720.7	725.3	720.7
140°	483.8	518.3	555.1	590.4	607.2	624.1	648.6	668.6	680.1	684.7	680.1
142.5°	478.4	507.6	537.5	566.6	580.0	593.4	616.4	634.1	644.0	644.0	644.0
145°	473.8	497.6	522.9	546.7	557.8	568.9	587.3	600.3	608.0	610.3	608.0
147.5°	469.2	489.9	510.6	529.8	538.2	546.7	562.8	573.5	578.9	580.4	578.9
150°	463.1	481.5	498.4	514.5	521.4	528.3	539.8	549.0	553.6	554.3	553.6
152.5°	457.7	473.1	488.4	501.4	507.2	512.9	521.4	529.0	532.1	532.1	532.1
155°	450.8	465.4	477.7	489.2	493.4	497.6	506.0	511.4	514.5	512.9	514.5
157.5°	444.7	456.2	466.9	476.9	480.4	483.8	489.9	494.5	496.1	496.1	496.1
160°	437.8	447.8	456.2	464.6	467.3	470.0	475.4	479.2	480.0	480.0	480.0
162.5°	431.7	439.3	446.2	453.1	455.0	457.0	462.3	464.6	465.4	464.6	465.4
165°	424.8	430.9	436.3	441.6	443.2	444.7	447.8	450.8	450.8	450.1	450.8
167.5°	417.9	422.5	427.1	430.9	432.4	434.0	435.5	437.0	437.0	436.3	437.0
170°	412.5	416.3	418.6	421.7	422.4	423.2	424.0	426.3	425.5	424.0	425.5
172.5°	407.1	409.4	410.9	413.3	413.6	414.0	414.8	415.6	414.8	414.0	414.8
175°	402.5	404.8	405.6	406.3	406.7	407.1	407.1	407.9	407.1	405.6	407.1
177.5°	399.4	401.0	401.0	401.7	401.7	401.7	401.7	401.7	401.0	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2340.1	2329.3	2326.2	2329.3	2326.2	2327.7	2316.9	2276.8	2287.6	2270.7	2279.9
5°	2472.7	2463.5	2443.4	2440.3	2437.2	2434.2	2418.7	2383.3	2369.4	2346.2	2344.7
7.5°	2599.2	2599.2	2583.8	2573.0	2559.1	2548.3	2528.3	2475.8	2454.2	2426.5	2411.0
10°	2724.2	2684.1	2701.0	2690.2	2656.3	2650.1	2613.1	2582.3	2540.6	2512.8	2488.2
12.5°	2813.6	2801.3	2785.9	2776.6	2767.4	2747.3	2722.6	2644.0	2622.4	2566.8	2539.1
15°	2810.5	2802.8	2807.5	2807.5	2804.4	2799.8	2779.7	2722.6	2685.6	2631.6	2583.8
17.5°	2659.4	2679.4	2699.5	2713.4	2744.2	2758.1	2776.6	2742.7	2719.5	2673.3	2622.4
20°	2395.6	2445.0	2503.6	2515.9	2543.7	2625.4	2662.5	2691.8	2701.0	2685.6	2644.0
22.5°	2028.5	2070.1	2212.0	2209.0	2249.1	2346.2	2454.2	2542.1	2611.6	2650.1	2634.7
25°	1588.8	1647.5	1723.0	1780.1	1911.2	2056.2	2190.4	2330.8	2451.1	2557.6	2583.8
27.5°	1201.7	1278.8	1338.9	1414.5	1480.9	1652.1	1824.9	2043.9	2184.3	2386.3	2491.2
30°	971.8	1007.3	1067.5	1102.9	1135.3	1266.4	1462.3	1678.3	1925.1	2158.0	2338.5
32.5°	829.9	854.6	899.3	914.7	948.7	1036.6	1160.0	1357.5	1612.0	1894.3	2131.8
35°	745.1	771.3	780.5	794.4	822.2	877.7	962.6	1106.0	1335.9	1612.0	1895.8
37.5°	672.6	686.4	712.7	721.9	731.2	772.8	829.9	930.2	1082.9	1309.6	1624.3
40°	621.7	629.4	643.2	651.0	657.1	686.4	737.3	805.2	917.8	1090.6	1380.6
42.5°	567.7	576.9	586.2	595.4	603.1	626.3	657.1	721.9	797.5	928.6	1138.4
45°	515.2	521.4	532.2	538.4	549.2	567.7	595.4	640.2	708.0	791.3	961.0
47.5°	467.4	475.1	479.7	487.4	495.2	515.2	541.4	570.7	626.3	708.0	831.4
50°	424.2	433.5	439.6	441.2	447.3	465.9	487.4	519.8	555.3	618.6	726.5
52.5°	393.4	394.9	399.5	405.7	404.2	414.9	435.0	459.7	496.7	547.6	626.3
55°	357.9	362.5	365.6	367.1	367.1	376.4	387.2	410.3	439.6	481.3	547.6
57.5°	313.1	317.8	327.0	330.1	334.7	339.4	344.0	359.4	384.1	424.2	478.2
60°	266.9	269.9	279.2	285.4	288.5	300.8	307.0	319.3	333.2	362.5	413.4
62.5°	214.4	217.5	222.1	228.3	234.5	253.0	268.4	280.7	291.5	311.6	353.2
65°	186.7	188.2	191.3	192.8	194.4	202.1	216.0	232.9	253.0	268.4	293.1
67.5°	162.0	163.5	165.1	168.1	169.7	171.2	177.4	182.0	202.1	223.7	242.2
70°	138.8	141.9	143.5	143.5	145.0	148.1	151.2	157.3	163.5	174.3	197.4
72.5°	117.2	118.8	121.9	121.9	121.9	124.9	128.0	131.1	134.2	140.4	149.6
75°	97.2	100.3	100.3	100.3	101.8	101.8	104.9	108.0	111.1	115.7	118.8
77.5°	80.2	80.2	80.2	80.2	81.8	81.8	83.3	86.4	87.9	89.5	92.6
80°	60.2	61.7	61.7	61.7	63.2	63.2	63.2	66.3	67.9	67.9	71.0
82.5°	44.7	44.7	44.7	46.3	44.7	46.3	46.3	47.8	46.3	47.8	49.4
85°	27.8	27.8	27.8	29.3	29.3	29.3	29.3	29.3	29.3	29.3	30.9
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	15.4	13.9	13.9
90°	25.3	25.3	25.3	24.9	24.5	23.0	24.5	25.3	26.1	25.3	20.7
92.5°	47.5	50.6	51.4	54.4	57.5	65.9	77.4	98.9	118.1	116.5	90.5
95°	88.9	95.1	105.0	113.4	121.9	154.1	200.9	263.0	300.5	266.0	177.1
97.5°	159.5	174.8	204.7	227.7	250.7	328.1	410.9	493.8	489.9	378.7	235.4
100°	310.5	343.5	407.1	453.5	499.9	604.9	700.0	716.1	605.7	417.1	251.5
102.5°	584.2	646.3	716.9	766.7	816.5	886.3	889.4	798.9	609.5	402.5	252.2
105°	907.8	955.3	1002.8	1015.4	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1
107.5°	1113.2	1120.1	1120.9	1105.6	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5
110°	1170.0	1155.4	1122.4	1091.0	1059.6	961.4	824.2	662.4	503.7	368.8	275.2

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1154.6	1127.8	1078.7	1041.6	1004.4	897.8	767.5	625.6	486.9	369.5	286.7
115°	1110.2	1074.9	1020.5	981.0	941.5	841.1	723.0	596.5	475.4	372.6	298.2
117.5°	1054.2	1016.6	960.7	923.1	885.5	792.0	686.2	576.6	469.2	377.2	310.5
120°	995.9	959.9	906.2	871.4	836.5	755.2	660.1	561.2	463.9	381.8	322.8
122.5°	943.8	908.5	861.8	831.1	800.4	724.5	639.4	548.2	460.8	387.2	333.5
125°	897.0	867.9	823.4	794.6	765.9	698.5	619.5	535.9	457.0	392.5	345.0
127.5°	857.2	829.6	790.5	763.6	736.8	672.4	599.6	524.4	454.7	397.9	355.7
130°	821.1	795.1	757.5	732.2	706.9	646.3	580.4	512.9	453.1	404.0	365.7
132.5°	785.9	759.8	723.0	699.6	676.2	621.8	562.0	503.7	452.4	410.2	375.7
135°	747.5	722.2	689.3	667.8	646.3	595.7	545.1	495.3	451.6	414.8	384.1
137.5°	708.4	686.2	654.8	635.6	616.4	575.0	531.3	489.2	451.6	419.4	391.0
140°	668.6	648.6	624.1	607.2	590.4	555.1	518.3	483.8	450.8	422.5	396.4
142.5°	634.1	616.4	593.4	580.0	566.6	537.5	507.6	478.4	450.8	424.8	401.0
145°	600.3	587.3	568.9	557.8	546.7	522.9	497.6	473.8	449.3	426.3	404.8
147.5°	573.5	562.8	546.7	538.2	529.8	510.6	489.9	469.2	447.0	427.1	407.1
150°	549.0	539.8	528.3	521.4	514.5	498.4	481.5	463.1	444.7	426.3	408.6
152.5°	529.0	521.4	512.9	507.2	501.4	488.4	473.1	457.7	440.9	424.8	409.4
155°	511.4	506.0	497.6	493.4	489.2	477.7	465.4	450.8	436.3	423.2	410.2
157.5°	494.5	489.9	483.8	480.4	476.9	466.9	456.2	444.7	431.7	420.2	410.2
160°	479.2	475.4	470.0	467.3	464.6	456.2	447.8	437.8	427.1	417.9	410.2
162.5°	464.6	462.3	457.0	455.0	453.1	446.2	439.3	431.7	423.2	415.6	409.4
165°	450.8	447.8	444.7	443.2	441.6	436.3	430.9	424.8	417.9	412.5	407.9
167.5°	437.0	435.5	434.0	432.4	430.9	427.1	422.5	417.9	413.3	409.4	407.1
170°	426.3	424.0	423.2	422.4	421.7	418.6	416.3	412.5	409.4	407.1	405.6
172.5°	415.6	414.8	414.0	413.6	413.3	410.9	409.4	407.1	404.8	404.0	403.3
175°	407.9	407.1	407.1	406.7	406.3	405.6	404.8	402.5	401.7	401.0	401.7
177.5°	401.7	401.7	401.7	401.7	401.7	401.0	401.0	399.4	398.7	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2266.0	2258.3	2258.3	2253.7	2253.7	2229.0	2229.0	2236.7	2227.5	2216.7	2201.2
5°	2324.6	2307.7	2303.0	2296.9	2276.8	2246.0	2233.6	2229.0	2210.5	2187.4	2161.1
7.5°	2380.2	2352.4	2338.5	2324.6	2298.4	2255.2	2230.5	2213.6	2185.8	2150.3	2116.4
10°	2434.2	2398.7	2363.2	2346.2	2309.2	2255.2	2219.7	2192.0	2151.9	2104.1	2056.2
12.5°	2483.5	2409.5	2403.3	2369.4	2315.4	2253.7	2199.7	2159.6	2108.7	2053.2	1997.6
15°	2526.7	2451.1	2414.1	2383.3	2312.3	2235.2	2178.1	2128.7	2060.9	1997.6	1929.7
17.5°	2548.3	2466.6	2441.9	2391.0	2318.5	2218.2	2141.1	2080.9	2006.9	1931.3	1854.2
20°	2569.9	2474.3	2434.2	2398.7	2300.0	2185.8	2099.4	2030.0	1948.3	1858.8	1773.9
22.5°	2580.7	2474.3	2426.5	2377.1	2281.5	2150.3	2048.5	1966.8	1871.1	1780.1	1678.3
25°	2562.2	2465.0	2407.9	2357.0	2249.1	2107.1	1989.9	1897.4	1795.5	1692.2	1588.8
27.5°	2515.9	2443.4	2377.1	2324.6	2204.3	2051.6	1928.2	1823.3	1718.4	1602.7	1497.8
30°	2429.5	2397.1	2344.7	2286.1	2155.0	2002.2	1855.7	1747.7	1632.0	1516.3	1406.8
32.5°	2295.3	2323.1	2289.2	2238.3	2096.3	1934.4	1778.6	1669.1	1542.6	1417.6	1317.3
35°	2131.8	2230.5	2212.0	2176.6	2034.6	1861.9	1706.1	1573.4	1446.9	1320.4	1220.2
37.5°	1952.9	2102.5	2117.9	2096.3	1963.7	1787.8	1616.6	1487.0	1357.5	1229.4	1127.6
40°	1707.6	1937.5	1986.8	1996.1	1889.6	1698.4	1519.4	1392.9	1264.9	1140.0	1016.5
42.5°	1482.4	1772.4	1834.1	1872.7	1795.5	1610.4	1430.0	1289.6	1163.1	1050.5	927.1
45°	1271.1	1573.4	1673.7	1723.0	1689.1	1510.2	1323.5	1192.4	1076.7	973.4	854.6
47.5°	1053.6	1357.5	1497.8	1576.5	1576.5	1408.4	1221.7	1092.1	981.1	893.1	788.2
50°	908.6	1161.5	1306.6	1409.9	1437.7	1305.0	1129.2	1002.7	897.8	802.1	721.9
52.5°	774.4	1001.1	1121.4	1229.4	1309.6	1193.9	1025.8	911.7	808.3	718.8	655.6
55°	669.5	839.2	948.7	1067.5	1156.9	1081.3	925.5	814.5	725.0	651.0	597.0
57.5°	569.2	717.3	806.8	911.7	1007.3	950.2	825.3	729.6	651.0	586.2	538.4
60°	484.4	604.7	674.1	755.9	874.6	834.5	731.2	643.2	580.0	521.4	481.3
62.5°	411.9	507.5	566.1	624.7	732.7	714.2	634.0	566.1	512.1	462.8	428.8
65°	337.8	416.5	462.8	513.7	600.1	607.8	543.0	495.2	445.8	402.6	371.8
67.5°	273.0	334.7	376.4	419.6	489.0	510.6	465.9	425.7	384.1	348.6	320.9
70°	220.6	263.8	294.6	328.6	385.6	411.9	388.7	361.0	327.0	297.7	273.0
72.5°	174.3	202.1	220.6	246.8	293.1	319.3	317.8	293.1	268.4	248.4	228.3
75°	128.0	149.6	165.1	182.0	219.0	243.7	249.9	239.1	214.4	199.0	183.6
77.5°	97.2	109.5	117.2	129.6	155.8	177.4	186.7	183.6	166.6	154.3	143.5
80°	74.0	77.1	80.2	84.8	106.4	126.5	132.7	131.1	121.9	117.2	104.9
82.5°	52.4	54.0	55.5	57.1	64.8	81.8	87.9	91.0	83.3	78.7	67.9
85°	30.9	32.4	32.4	35.5	37.0	41.6	52.4	52.4	50.9	44.7	43.2
87.5°	15.4	15.4	13.9	13.9	15.4	17.0	20.1	23.1	20.1	18.5	17.0
90°	15.3	11.5	10.4	9.2	7.7	6.1	3.1	0.8	3.1	6.1	7.7
92.5°	61.3	40.6	36.4	32.2	26.1	22.2	16.1	11.5	16.1	22.2	26.1
95°	110.4	75.1	65.9	56.7	44.5	37.6	29.9	26.8	29.9	37.6	44.5
97.5°	142.6	97.4	87.1	76.7	62.9	52.9	44.5	39.9	44.5	52.9	62.9
100°	157.9	117.3	106.6	95.8	80.5	68.2	61.3	59.0	61.3	68.2	80.5
102.5°	171.7	134.9	124.2	113.5	97.4	85.1	78.2	76.7	78.2	85.1	97.4
105°	187.8	151.8	141.0	130.3	113.5	102.0	96.6	93.5	96.6	102.0	113.5
107.5°	203.9	168.7	158.0	147.2	130.3	119.6	114.2	111.9	114.2	119.6	130.3
110°	220.0	186.3	175.2	164.1	148.0	138.0	133.4	130.3	133.4	138.0	148.0

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	235.4	203.2	191.7	180.2	164.8	155.6	150.3	147.2	150.3	155.6	164.8
115°	251.5	218.5	208.2	197.8	182.5	173.3	168.7	164.8	168.7	173.3	182.5
117.5°	266.0	235.4	224.6	213.9	199.3	190.9	186.3	183.2	186.3	190.9	199.3
120°	281.4	251.5	240.8	230.0	214.7	207.8	203.2	200.1	203.2	207.8	214.7
122.5°	295.9	268.3	257.2	246.1	230.8	223.1	218.5	216.2	218.5	223.1	230.8
125°	310.5	282.9	272.2	261.4	246.1	236.9	232.3	230.0	232.3	236.9	246.1
127.5°	324.3	297.5	286.4	275.2	260.7	250.7	244.6	241.5	244.6	250.7	260.7
130°	336.6	309.7	299.0	288.3	272.9	262.2	254.5	251.5	254.5	262.2	272.9
132.5°	347.3	322.0	311.2	300.5	284.4	272.9	264.5	260.7	264.5	272.9	284.4
135°	357.3	332.7	322.0	311.3	293.6	282.1	272.9	269.9	272.9	282.1	293.6
137.5°	365.7	341.2	331.2	321.2	303.6	291.3	282.1	278.3	282.1	291.3	303.6
140°	372.6	349.6	339.6	329.7	312.8	300.5	291.3	288.3	291.3	300.5	312.8
142.5°	378.0	355.7	346.5	337.3	321.2	309.0	300.5	298.2	300.5	309.0	321.2
145°	383.3	362.6	354.2	345.8	330.4	318.9	311.3	308.2	311.3	318.9	330.4
147.5°	387.9	368.0	360.4	352.7	339.6	328.9	321.2	318.9	321.2	328.9	339.6
150°	391.0	373.4	366.5	359.6	348.1	338.1	332.0	329.7	332.0	338.1	348.1
152.5°	394.1	378.7	372.6	366.5	355.7	347.3	341.2	340.4	341.2	347.3	355.7
155°	397.1	384.1	378.4	372.6	364.2	355.7	351.1	350.4	351.1	355.7	364.2
157.5°	399.4	387.9	383.0	378.0	371.1	363.4	359.6	358.8	359.6	363.4	371.1
160°	401.0	391.8	387.6	383.3	377.2	371.1	368.0	367.2	368.0	371.1	377.2
162.5°	401.7	394.1	391.0	387.9	382.6	378.0	374.9	375.7	374.9	378.0	382.6
165°	402.5	395.6	393.3	391.0	387.2	382.6	381.0	381.8	381.0	382.6	387.2
167.5°	402.5	397.1	395.6	394.1	391.0	387.9	386.4	387.2	386.4	387.9	391.0
170°	401.7	397.9	396.8	395.6	394.1	391.8	391.0	392.5	391.0	391.8	394.1
172.5°	401.0	398.7	397.9	397.1	396.4	394.1	394.8	395.6	394.8	394.1	396.4
175°	400.2	398.7	398.3	397.9	397.9	396.4	397.1	397.9	397.1	396.4	397.9
177.5°	399.4	398.7	398.7	398.7	398.7	397.1	397.9	399.4	397.9	397.1	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2195.1	2196.6	2201.2	2187.4	2165.8	2156.5	2128.7	2124.1	2119.5	2119.5	2124.1
5°	2145.7	2139.5	2141.1	2114.9	2084.0	2065.5	2026.9	2033.1	2013.0	2000.7	2003.8
7.5°	2091.7	2074.7	2073.2	2039.3	2000.7	1966.8	1926.7	1917.4	1898.9	1877.3	1868.0
10°	2023.8	2011.5	1988.4	1949.8	1900.4	1872.7	1818.7	1786.3	1781.7	1749.3	1736.9
12.5°	1954.4	1932.8	1909.7	1855.7	1800.2	1755.4	1715.3	1679.9	1655.2	1627.4	1608.9
15°	1874.2	1848.0	1821.8	1764.7	1699.9	1655.2	1595.0	1542.6	1470.1	1413.0	1380.6
17.5°	1786.3	1757.0	1721.5	1658.3	1595.0	1533.3	1422.2	1360.5	1309.6	1275.7	1255.6
20°	1695.3	1662.9	1627.4	1564.2	1454.6	1346.7	1285.0	1237.1	1206.3	1172.3	1147.7
22.5°	1599.6	1565.7	1527.1	1428.4	1312.7	1237.1	1189.3	1144.6	1099.8	1081.3	1069.0
25°	1510.2	1479.3	1430.0	1295.8	1204.7	1135.3	1081.3	1052.0	1028.9	1004.2	981.1
27.5°	1417.6	1360.5	1291.1	1178.5	1121.4	1050.5	1011.9	990.3	950.2	933.3	922.5
30°	1306.6	1243.3	1177.0	1096.8	1030.4	981.1	945.6	910.1	887.0	870.0	851.5
32.5°	1193.9	1133.8	1092.1	1008.8	959.5	908.6	874.6	853.0	819.1	808.3	800.6
35°	1096.8	1045.9	1008.8	941.0	894.7	848.4	823.7	791.3	769.7	749.7	737.3
37.5°	1001.1	973.4	934.8	877.7	828.4	791.3	757.4	746.6	717.3	706.5	694.2
40°	934.8	893.1	860.8	811.4	769.7	729.6	708.0	683.4	663.3	646.3	641.7
42.5°	854.6	823.7	805.2	751.2	708.0	684.9	658.7	630.9	615.5	601.6	584.6
45°	794.4	766.7	740.4	697.2	658.7	629.4	606.2	587.7	561.5	555.3	529.1
47.5°	731.2	703.4	683.4	640.2	604.7	576.9	560.0	535.3	513.7	499.8	487.4
50°	667.9	644.8	626.3	589.3	558.4	529.1	506.0	481.3	472.0	448.9	441.2
52.5°	607.8	592.3	572.3	536.8	506.0	481.3	456.6	436.5	422.7	410.3	401.1
55°	556.9	532.2	522.9	484.4	458.1	431.9	410.3	398.0	381.0	373.3	365.6
57.5°	499.8	485.9	470.5	441.2	411.9	387.2	371.8	353.2	344.0	334.7	328.6
60°	450.4	430.4	418.0	393.4	367.1	344.0	330.1	316.2	303.9	296.2	283.8
62.5°	393.4	377.9	370.2	344.0	322.4	300.8	288.5	274.6	265.3	251.4	236.0
65°	344.0	331.7	322.4	300.8	280.7	260.7	248.4	231.4	219.0	211.3	209.8
67.5°	300.8	291.5	277.7	257.6	237.6	222.1	208.2	194.4	192.8	189.7	189.7
70°	253.0	243.7	236.0	214.4	197.4	180.5	177.4	172.8	168.1	166.6	163.5
72.5°	211.3	203.6	194.4	175.9	158.9	154.3	151.2	148.1	143.5	141.9	140.4
75°	171.2	160.4	154.3	137.3	132.7	129.6	126.5	121.9	118.8	117.2	114.1
77.5°	131.1	120.3	120.3	111.1	108.0	103.4	100.3	97.2	95.6	92.6	92.6
80°	92.6	92.6	89.5	84.8	80.2	78.7	74.0	72.5	71.0	72.5	69.4
82.5°	67.9	61.7	61.7	58.6	55.5	54.0	50.9	50.9	49.4	49.4	49.4
85°	38.6	38.6	37.0	33.9	32.4	32.4	30.9	30.9	29.3	29.3	27.8
87.5°	15.4	13.9	15.4	13.9	13.9	12.3	12.3	12.3	10.8	12.3	10.8
90°	9.2	10.4	11.5	15.3	20.7	25.3	26.1	25.3	24.5	23.0	24.5
92.5°	32.2	36.4	40.6	61.3	90.5	116.5	118.1	98.9	77.4	65.9	57.5
95°	56.7	65.9	75.1	110.4	177.1	266.0	300.5	263.0	200.9	154.1	121.9
97.5°	76.7	87.1	97.4	142.6	235.4	378.7	489.9	493.8	410.9	328.1	250.7
100°	95.8	106.6	117.3	157.9	251.5	417.1	605.7	716.1	700.0	604.9	499.9
102.5°	113.5	124.2	134.9	171.7	252.2	402.5	609.5	798.9	889.4	886.3	816.5
105°	130.3	141.0	151.8	187.8	256.1	382.6	568.1	772.1	931.5	1018.2	1028.1
107.5°	147.2	158.0	168.7	203.9	264.5	371.8	529.8	715.3	886.3	1015.1	1090.2
110°	164.1	175.2	186.3	220.0	275.2	368.8	503.7	662.4	824.2	961.4	1059.6

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	180.2	191.7	203.2	235.4	286.7	369.5	486.9	625.6	767.5	897.8	1004.4
115°	197.8	208.2	218.5	251.5	298.2	372.6	475.4	596.5	723.0	841.1	941.5
117.5°	213.9	224.6	235.4	266.0	310.5	377.2	469.2	576.6	686.2	792.0	885.5
120°	230.0	240.8	251.5	281.4	322.8	381.8	463.9	561.2	660.1	755.2	836.5
122.5°	246.1	257.2	268.3	295.9	333.5	387.2	460.8	548.2	639.4	724.5	800.4
125°	261.4	272.2	282.9	310.5	345.0	392.5	457.0	535.9	619.5	698.5	765.9
127.5°	275.2	286.4	297.5	324.3	355.7	397.9	454.7	524.4	599.6	672.4	736.8
130°	288.3	299.0	309.7	336.6	365.7	404.0	453.1	512.9	580.4	646.3	706.9
132.5°	300.5	311.2	322.0	347.3	375.7	410.2	452.4	503.7	562.0	621.8	676.2
135°	311.3	322.0	332.7	357.3	384.1	414.8	451.6	495.3	545.1	595.7	646.3
137.5°	321.2	331.2	341.2	365.7	391.0	419.4	451.6	489.2	531.3	575.0	616.4
140°	329.7	339.6	349.6	372.6	396.4	422.5	450.8	483.8	518.3	555.1	590.4
142.5°	337.3	346.5	355.7	378.0	401.0	424.8	450.8	478.4	507.6	537.5	566.6
145°	345.8	354.2	362.6	383.3	404.8	426.3	449.3	473.8	497.6	522.9	546.7
147.5°	352.7	360.4	368.0	387.9	407.1	427.1	447.0	469.2	489.9	510.6	529.8
150°	359.6	366.5	373.4	391.0	408.6	426.3	444.7	463.1	481.5	498.4	514.5
152.5°	366.5	372.6	378.7	394.1	409.4	424.8	440.9	457.7	473.1	488.4	501.4
155°	372.6	378.4	384.1	397.1	410.2	423.2	436.3	450.8	465.4	477.7	489.2
157.5°	378.0	383.0	387.9	399.4	410.2	420.2	431.7	444.7	456.2	466.9	476.9
160°	383.3	387.6	391.8	401.0	410.2	417.9	427.1	437.8	447.8	456.2	464.6
162.5°	387.9	391.0	394.1	401.7	409.4	415.6	423.2	431.7	439.3	446.2	453.1
165°	391.0	393.3	395.6	402.5	407.9	412.5	417.9	424.8	430.9	436.3	441.6
167.5°	394.1	395.6	397.1	402.5	407.1	409.4	413.3	417.9	422.5	427.1	430.9
170°	395.6	396.8	397.9	401.7	405.6	407.1	409.4	412.5	416.3	418.6	421.7
172.5°	397.1	397.9	398.7	401.0	403.3	404.0	404.8	407.1	409.4	410.9	413.3
175°	397.9	398.3	398.7	400.2	401.7	401.0	401.7	402.5	404.8	405.6	406.3
177.5°	398.7	398.7	398.7	399.4	401.0	399.4	398.7	399.4	401.0	401.0	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2124.1	2121.0	2111.8	2114.9	2110.2	2110.2	2107.1	2107.1	2107.1	2114.9	2110.2
5°	2008.4	1997.6	1986.8	1982.2	1977.6	1972.9	1972.9	1971.4	1985.3	1982.2	1994.5
7.5°	1865.0	1861.9	1840.3	1840.3	1832.6	1829.5	1837.2	1838.7	1840.3	1843.4	1851.1
10°	1736.9	1729.2	1698.4	1701.4	1696.8	1690.6	1695.3	1692.2	1703.0	1706.1	1703.0
12.5°	1585.8	1571.9	1537.9	1521.0	1502.5	1488.6	1505.5	1493.2	1536.4	1548.7	1582.7
15°	1385.2	1359.0	1335.9	1335.9	1318.9	1306.6	1314.3	1328.1	1337.4	1351.3	1357.5
17.5°	1251.0	1240.2	1221.7	1210.9	1206.3	1201.7	1201.7	1207.8	1227.9	1226.3	1238.7
20°	1136.9	1130.7	1121.4	1107.6	1102.9	1099.8	1099.8	1099.8	1113.7	1126.1	1133.8
22.5°	1058.2	1053.6	1047.4	1028.9	1019.6	1016.5	1024.3	1028.9	1039.7	1048.9	1056.7
25°	979.5	968.7	957.9	951.8	947.1	947.1	950.2	951.8	956.4	961.0	970.3
27.5°	914.7	907.0	891.6	874.6	874.6	870.0	873.1	876.2	887.0	902.4	910.1
30°	842.2	840.7	834.5	828.4	822.2	819.1	825.3	829.9	831.4	839.2	839.2
32.5°	789.8	779.0	768.2	762.0	758.9	757.4	758.9	765.1	765.1	774.4	785.2
35°	737.3	731.2	720.4	709.6	706.5	698.8	705.0	711.1	721.9	726.5	731.2
37.5°	680.3	672.6	667.9	664.8	658.7	660.2	655.6	664.8	674.1	672.6	675.6
40°	637.1	623.2	609.3	607.8	606.2	604.7	604.7	606.2	612.4	618.6	627.8
42.5°	581.5	576.9	564.6	552.2	549.2	546.1	543.0	549.2	561.5	572.3	576.9
45°	524.5	518.3	515.2	506.0	499.8	498.2	495.2	502.9	513.7	518.3	521.4
47.5°	472.0	470.5	461.2	462.8	458.1	459.7	458.1	462.8	462.8	467.4	470.5
50°	436.5	431.9	427.3	424.2	419.6	419.6	418.0	419.6	425.7	431.9	430.4
52.5°	401.1	393.4	391.8	390.3	387.2	390.3	385.6	387.2	393.4	396.4	394.9
55°	359.4	357.9	354.8	351.7	350.2	348.6	348.6	348.6	354.8	359.4	361.0
57.5°	327.0	319.3	313.1	313.1	307.0	305.4	308.5	310.1	314.7	317.8	320.9
60°	282.3	279.2	269.9	265.3	256.1	254.5	254.5	260.7	268.4	279.2	282.3
62.5°	234.5	229.8	228.3	228.3	228.3	228.3	228.3	228.3	228.3	229.8	229.8
65°	208.2	209.8	208.2	206.7	208.2	208.2	206.7	206.7	206.7	208.2	209.8
67.5°	186.7	185.1	186.7	185.1	183.6	183.6	182.0	183.6	185.1	186.7	186.7
70°	162.0	162.0	160.4	162.0	160.4	158.9	157.3	157.3	160.4	162.0	162.0
72.5°	138.8	138.8	137.3	137.3	134.2	134.2	135.7	134.2	134.2	138.8	138.8
75°	115.7	114.1	112.6	112.6	111.1	111.1	111.1	109.5	112.6	112.6	114.1
77.5°	91.0	91.0	91.0	89.5	89.5	87.9	87.9	89.5	89.5	89.5	91.0
80°	69.4	69.4	69.4	67.9	66.3	66.3	66.3	66.3	66.3	67.9	66.3
82.5°	47.8	47.8	47.8	47.8	47.8	46.3	46.3	46.3	47.8	47.8	46.3
85°	29.3	27.8	29.3	29.3	27.8	29.3	27.8	27.8	26.2	26.2	27.8
87.5°	12.3	10.8	9.3	9.3	10.8	9.3	9.3	9.3	10.8	9.3	9.3
90°	24.9	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	24.9
92.5°	54.4	51.4	50.6	47.5	48.3	46.8	48.3	47.5	50.6	51.4	54.4
95°	113.4	105.0	95.1	88.9	86.6	87.4	86.6	88.9	95.1	105.0	113.4
97.5°	227.7	204.7	174.8	159.5	151.0	146.4	151.0	159.5	174.8	204.7	227.7
100°	453.5	407.1	343.5	310.5	288.3	274.5	288.3	310.5	343.5	407.1	453.5
102.5°	766.7	716.9	646.3	584.2	555.1	535.2	555.1	584.2	646.3	716.9	766.7
105°	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8	907.8	955.3	1002.8	1015.4
107.5°	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3	1113.2	1120.1	1120.9	1105.6
110°	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9	1170.0	1155.4	1122.4	1091.0

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2	1154.6	1127.8	1078.7	1041.6
115°	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1	1110.2	1074.9	1020.5	981.0
117.5°	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9	1054.2	1016.6	960.7	923.1
120°	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2	995.9	959.9	906.2	871.4
122.5°	831.1	861.8	908.5	943.8	963.0	969.1	963.0	943.8	908.5	861.8	831.1
125°	794.6	823.4	867.9	897.0	916.2	922.3	916.2	897.0	867.9	823.4	794.6
127.5°	763.6	790.5	829.6	857.2	874.0	878.6	874.0	857.2	829.6	790.5	763.6
130°	732.2	757.5	795.1	821.1	836.5	842.6	836.5	821.1	795.1	757.5	732.2
132.5°	699.6	723.0	759.8	785.9	799.7	805.0	799.7	785.9	759.8	723.0	699.6
135°	667.8	689.3	722.2	747.5	761.3	764.4	761.3	747.5	722.2	689.3	667.8
137.5°	635.6	654.8	686.2	708.4	720.7	725.3	720.7	708.4	686.2	654.8	635.6
140°	607.2	624.1	648.6	668.6	680.1	684.7	680.1	668.6	648.6	624.1	607.2
142.5°	580.0	593.4	616.4	634.1	644.0	644.0	644.0	634.1	616.4	593.4	580.0
145°	557.8	568.9	587.3	600.3	608.0	610.3	608.0	600.3	587.3	568.9	557.8
147.5°	538.2	546.7	562.8	573.5	578.9	580.4	578.9	573.5	562.8	546.7	538.2
150°	521.4	528.3	539.8	549.0	553.6	554.3	553.6	549.0	539.8	528.3	521.4
152.5°	507.2	512.9	521.4	529.0	532.1	532.1	532.1	529.0	521.4	512.9	507.2
155°	493.4	497.6	506.0	511.4	514.5	512.9	514.5	511.4	506.0	497.6	493.4
157.5°	480.4	483.8	489.9	494.5	496.1	496.1	496.1	494.5	489.9	483.8	480.4
160°	467.3	470.0	475.4	479.2	480.0	480.0	480.0	479.2	475.4	470.0	467.3
162.5°	455.0	457.0	462.3	464.6	465.4	464.6	465.4	464.6	462.3	457.0	455.0
165°	443.2	444.7	447.8	450.8	450.8	450.1	450.8	450.8	447.8	444.7	443.2
167.5°	432.4	434.0	435.5	437.0	437.0	436.3	437.0	437.0	435.5	434.0	432.4
170°	422.4	423.2	424.0	426.3	425.5	424.0	425.5	426.3	424.0	423.2	422.4
172.5°	413.6	414.0	414.8	415.6	414.8	414.0	414.8	415.6	414.8	414.0	413.6
175°	406.7	407.1	407.1	407.9	407.1	405.6	407.1	407.9	407.1	407.1	406.7
177.5°	401.7	401.7	401.7	401.7	401.0	399.4	401.0	401.7	401.7	401.7	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2114.9	2122.6	2119.5	2102.5	2119.5	2124.1	2133.4	2142.6	2148.8	2158.0	2165.8
5°	1982.2	1997.6	2006.9	1997.6	2028.5	2033.1	2054.7	2067.0	2085.5	2101.0	2113.3
7.5°	1857.2	1869.6	1888.1	1891.2	1909.7	1931.3	1962.1	1993.0	2022.3	2037.7	2051.6
10°	1723.0	1744.6	1772.4	1766.2	1794.0	1827.9	1860.3	1909.7	1934.4	1962.1	1986.8
12.5°	1588.8	1602.7	1639.7	1652.1	1692.2	1718.4	1763.1	1794.0	1855.7	1888.1	1909.7
15°	1354.4	1411.4	1457.7	1513.3	1565.7	1615.1	1655.2	1710.7	1764.7	1789.4	1824.9
17.5°	1247.9	1274.2	1301.9	1329.7	1397.6	1485.5	1556.4	1616.6	1662.9	1695.3	1736.9
20°	1136.9	1163.1	1193.9	1220.2	1261.8	1325.1	1413.0	1516.3	1571.9	1605.8	1645.9
22.5°	1058.2	1082.9	1102.9	1126.1	1158.5	1204.7	1271.1	1399.1	1473.1	1514.8	1550.3
25°	973.4	1004.2	1025.8	1042.8	1069.0	1119.9	1173.9	1246.4	1379.1	1411.4	1460.8
27.5°	914.7	924.0	948.7	974.9	1001.1	1028.9	1084.4	1146.1	1235.6	1306.6	1366.7
30°	845.3	868.5	891.6	902.4	925.5	965.6	999.6	1065.9	1135.3	1190.9	1263.4
32.5°	792.9	806.8	822.2	848.4	870.0	897.8	931.7	987.2	1045.9	1081.3	1136.9
35°	734.3	743.5	775.9	786.7	808.3	836.1	870.0	913.2	976.4	1004.2	1044.3
37.5°	678.7	700.3	709.6	734.3	754.3	782.1	806.8	856.1	897.8	930.2	967.2
40°	635.5	644.8	661.8	683.4	700.3	721.9	752.8	788.2	833.0	859.2	891.6
42.5°	583.1	590.8	612.4	624.7	652.5	672.6	691.1	734.3	774.4	794.4	826.8
45°	526.0	544.5	558.4	583.1	598.5	623.2	646.3	677.2	714.2	737.3	755.9
47.5°	476.7	495.2	509.0	532.2	556.9	567.7	592.3	624.7	658.7	677.2	703.4
50°	436.5	442.7	468.9	479.7	506.0	527.6	544.5	572.3	609.3	620.1	641.7
52.5°	398.0	402.6	419.6	433.5	456.6	475.1	496.7	522.9	553.8	570.7	587.7
55°	364.0	367.1	374.8	390.3	405.7	428.8	448.9	473.6	499.8	518.3	533.7
57.5°	325.5	331.7	337.8	347.1	362.5	384.1	405.7	428.8	450.4	462.8	482.8
60°	280.7	290.0	300.8	311.6	322.4	337.8	362.5	384.1	404.2	414.9	430.4
62.5°	232.9	251.4	260.7	273.0	282.3	296.2	314.7	339.4	353.2	367.1	379.5
65°	209.8	211.3	212.9	225.2	242.2	256.1	273.0	291.5	313.1	322.4	331.7
67.5°	186.7	188.2	191.3	192.8	199.0	214.4	232.9	253.0	269.9	276.1	285.4
70°	163.5	163.5	169.7	171.2	172.8	174.3	189.7	209.8	225.2	232.9	243.7
72.5°	138.8	140.4	143.5	145.0	148.1	151.2	155.8	166.6	185.1	192.8	205.2
75°	114.1	115.7	117.2	118.8	123.4	124.9	129.6	135.7	143.5	152.7	160.4
77.5°	91.0	91.0	92.6	95.6	98.7	100.3	104.9	108.0	111.1	115.7	121.9
80°	67.9	69.4	69.4	72.5	72.5	74.0	75.6	80.2	83.3	86.4	89.5
82.5°	46.3	49.4	49.4	49.4	50.9	52.4	54.0	54.0	57.1	58.6	63.2
85°	27.8	29.3	29.3	29.3	27.8	30.9	30.9	32.4	32.4	32.4	33.9
87.5°	10.8	9.3	10.8	10.8	10.8	12.3	10.8	10.8	12.3	13.9	13.9
90°	24.5	23.0	24.5	25.3	26.1	25.3	20.7	15.3	11.5	10.4	9.2
92.5°	57.5	65.9	77.4	98.9	118.1	116.5	90.5	61.3	40.6	36.4	32.2
95°	121.9	154.1	200.9	263.0	300.5	266.0	177.1	110.4	75.1	65.9	56.7
97.5°	250.7	328.1	410.9	493.8	489.9	378.7	235.4	142.6	97.4	87.1	76.7
100°	499.9	604.9	700.0	716.1	605.7	417.1	251.5	157.9	117.3	106.6	95.8
102.5°	816.5	886.3	889.4	798.9	609.5	402.5	252.2	171.7	134.9	124.2	113.5
105°	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1	187.8	151.8	141.0	130.3
107.5°	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5	203.9	168.7	158.0	147.2
110°	1059.6	961.4	824.2	662.4	503.7	368.8	275.2	220.0	186.3	175.2	164.1

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1004.4	897.8	767.5	625.6	486.9	369.5	286.7	235.4	203.2	191.7	180.2
115°	941.5	841.1	723.0	596.5	475.4	372.6	298.2	251.5	218.5	208.2	197.8
117.5°	885.5	792.0	686.2	576.6	469.2	377.2	310.5	266.0	235.4	224.6	213.9
120°	836.5	755.2	660.1	561.2	463.9	381.8	322.8	281.4	251.5	240.8	230.0
122.5°	800.4	724.5	639.4	548.2	460.8	387.2	333.5	295.9	268.3	257.2	246.1
125°	765.9	698.5	619.5	535.9	457.0	392.5	345.0	310.5	282.9	272.2	261.4
127.5°	736.8	672.4	599.6	524.4	454.7	397.9	355.7	324.3	297.5	286.4	275.2
130°	706.9	646.3	580.4	512.9	453.1	404.0	365.7	336.6	309.7	299.0	288.3
132.5°	676.2	621.8	562.0	503.7	452.4	410.2	375.7	347.3	322.0	311.2	300.5
135°	646.3	595.7	545.1	495.3	451.6	414.8	384.1	357.3	332.7	322.0	311.3
137.5°	616.4	575.0	531.3	489.2	451.6	419.4	391.0	365.7	341.2	331.2	321.2
140°	590.4	555.1	518.3	483.8	450.8	422.5	396.4	372.6	349.6	339.6	329.7
142.5°	566.6	537.5	507.6	478.4	450.8	424.8	401.0	378.0	355.7	346.5	337.3
145°	546.7	522.9	497.6	473.8	449.3	426.3	404.8	383.3	362.6	354.2	345.8
147.5°	529.8	510.6	489.9	469.2	447.0	427.1	407.1	387.9	368.0	360.4	352.7
150°	514.5	498.4	481.5	463.1	444.7	426.3	408.6	391.0	373.4	366.5	359.6
152.5°	501.4	488.4	473.1	457.7	440.9	424.8	409.4	394.1	378.7	372.6	366.5
155°	489.2	477.7	465.4	450.8	436.3	423.2	410.2	397.1	384.1	378.4	372.6
157.5°	476.9	466.9	456.2	444.7	431.7	420.2	410.2	399.4	387.9	383.0	378.0
160°	464.6	456.2	447.8	437.8	427.1	417.9	410.2	401.0	391.8	387.6	383.3
162.5°	453.1	446.2	439.3	431.7	423.2	415.6	409.4	401.7	394.1	391.0	387.9
165°	441.6	436.3	430.9	424.8	417.9	412.5	407.9	402.5	395.6	393.3	391.0
167.5°	430.9	427.1	422.5	417.9	413.3	409.4	407.1	402.5	397.1	395.6	394.1
170°	421.7	418.6	416.3	412.5	409.4	407.1	405.6	401.7	397.9	396.8	395.6
172.5°	413.3	410.9	409.4	407.1	404.8	404.0	403.3	401.0	398.7	397.9	397.1
175°	406.3	405.6	404.8	402.5	401.7	401.0	401.7	400.2	398.7	398.3	397.9
177.5°	401.7	401.0	401.0	399.4	398.7	399.4	401.0	399.4	398.7	398.7	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2219.7	2219.7	2219.7	2219.7
2.5°	2179.6	2175.0	2202.8	2233.6
5°	2134.9	2142.6	2178.1	2221.3
7.5°	2088.6	2105.6	2147.2	2204.3
10°	2023.8	2054.7	2117.9	2176.6
12.5°	1960.6	2002.2	2062.4	2131.8
15°	1889.6	1935.9	2010.0	2093.3
17.5°	1811.0	1863.4	1949.8	2040.8
20°	1727.7	1797.1	1888.1	1986.8
22.5°	1635.1	1718.4	1812.5	1922.0
25°	1545.6	1636.7	1730.8	1857.2
27.5°	1457.7	1547.2	1652.1	1780.1
30°	1369.8	1451.6	1564.2	1701.4
32.5°	1275.7	1360.5	1479.3	1619.7
35°	1189.3	1274.2	1385.2	1524.1
37.5°	1096.8	1187.8	1294.2	1437.7
40°	988.8	1095.2	1198.6	1335.9
42.5°	899.3	1011.9	1112.2	1241.8
45°	828.4	934.8	1018.1	1144.6
47.5°	762.0	848.4	933.3	1050.5
50°	698.8	765.1	853.0	957.9
52.5°	634.0	691.1	766.7	865.4
55°	575.4	629.4	697.2	772.8
57.5°	521.4	560.0	627.8	695.7
60°	461.2	501.3	553.8	610.9
62.5°	410.3	441.2	490.5	538.4
65°	356.3	385.6	422.7	467.4
67.5°	307.0	333.2	362.5	398.0
70°	262.2	282.3	303.9	334.7
72.5°	214.4	236.0	256.1	280.7
75°	175.9	185.1	202.1	219.0
77.5°	135.7	148.1	157.3	171.2
80°	97.2	108.0	111.1	121.9
82.5°	64.8	71.0	77.1	80.2
85°	37.0	40.1	46.3	47.8
87.5°	13.9	15.4	18.5	21.6
90°	7.7	6.1	3.1	0.8
92.5°	26.1	22.2	16.1	11.5
95°	44.5	37.6	29.9	26.8
97.5°	62.9	52.9	44.5	39.9
100°	80.5	68.2	61.3	59.0
102.5°	97.4	85.1	78.2	76.7
105°	113.5	102.0	96.6	93.5
107.5°	130.3	119.6	114.2	111.9
110°	148.0	138.0	133.4	130.3

TEST NUMBER: P999411

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	164.8	155.6	150.3	147.2
115°	182.5	173.3	168.7	164.8
117.5°	199.3	190.9	186.3	183.2
120°	214.7	207.8	203.2	200.1
122.5°	230.8	223.1	218.5	216.2
125°	246.1	236.9	232.3	230.0
127.5°	260.7	250.7	244.6	241.5
130°	272.9	262.2	254.5	251.5
132.5°	284.4	272.9	264.5	260.7
135°	293.6	282.1	272.9	269.9
137.5°	303.6	291.3	282.1	278.3
140°	312.8	300.5	291.3	288.3
142.5°	321.2	309.0	300.5	298.2
145°	330.4	318.9	311.3	308.2
147.5°	339.6	328.9	321.2	318.9
150°	348.1	338.1	332.0	329.7
152.5°	355.7	347.3	341.2	340.4
155°	364.2	355.7	351.1	350.4
157.5°	371.1	363.4	359.6	358.8
160°	377.2	371.1	368.0	367.2
162.5°	382.6	378.0	374.9	375.7
165°	387.2	382.6	381.0	381.8
167.5°	391.0	387.9	386.4	387.2
170°	394.1	391.8	391.0	392.5
172.5°	396.4	394.1	394.8	395.6
175°	397.9	396.4	397.1	397.9
177.5°	398.7	397.1	397.9	399.4
180°	398.7	398.7	398.7	398.7

(END OF REPORT)