

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999496

Luminaire Tested: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999496
REPORT IS A COMBINATION OF REPORTS P988048 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5277.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29
1	92	88	84	81	81	78	75	72	59	57	55	42	41	40	26	26	25
2	84	77	71	66	74	68	63	60	52	49	46	37	35	34	24	23	22
3	76	68	61	56	67	60	55	50	46	42	39	33	31	29	21	20	19
4	70	60	53	47	62	53	47	43	41	37	34	30	27	25	19	18	17
5	64	53	46	40	57	48	41	37	37	32	29	27	24	22	17	16	15
6	59	48	40	35	52	43	36	32	33	29	25	24	21	19	16	14	13
7	55	43	36	31	48	39	32	28	30	26	22	22	19	17	15	13	12
8	51	39	32	27	45	35	29	25	27	23	20	20	17	15	13	12	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	12	11	10
10	44	33	26	21	39	29	24	20	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10012	10012	10012	10012
5°	10035	10634	10070	8496
10°	9925	11240	9995	7015
15°	9709	11243	9873	5270
20°	9450	9293	9655	4348
25°	9136	5807	9333	3699
30°	8735	3718	8973	3185
35°	8248	2858	8514	2725
40°	7703	2402	8033	2384
45°	7122	2044	7421	2001
50°	6526	1737	6832	1731
55°	5867	1510	6185	1489
60°	5283	1151	5562	1137
65°	4735	866	5016	982
70°	4131	692	4452	801
75°	3491	530	3810	605
80°	2770	359	2986	397
85°	1921	186	2105	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9159 cd/sqm

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	1.1
10°-20°	167.5	3.2
20°-30°	215.5	4.1
30°-40°	204.5	3.9
40°-50°	175.2	3.3
50°-60°	133.4	2.5
60°-70°	84.2	1.6
70°-80°	42.0	0.8
80°-90°	14.7	0.3
90°-100°	234.0	4.4
100°-110°	824.0	15.6
110°-120°	865.4	16.4
120°-130°	712.0	13.5
130°-140°	572.0	10.8
140°-150°	432.0	8.2
150°-160°	303.7	5.8
160°-170°	178.8	3.4
170°-180°	58.2	1.1
0°-30°	443.0	8.4
0°-40°	647.4	12.3
0°-60°	956.1	18.1
0°-90°	1096.9	20.8
90°-120°	1923.5	36.4
90°-150°	3639.5	69.0
90°-180°	4180.0	79.2
0°-180°	5277.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	632	632	632	632	632	
5°	633	704	635	562	633	60
15°	596	794	606	372	596	168
25°	529	424	541	270	529	243
35°	434	209	448	199	434	272
45°	326	145	340	142	326	252
55°	220	101	232	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	68
85°	14	8	15	8	14	15
90°	1	38	1	38	1	4
95°	40	132	40	132	40	42
105°	141	1301	141	1301	141	150
115°	248	1712	248	1712	248	246
125°	346	1389	346	1389	346	308
135°	406	1151	406	1151	406	314
145°	464	919	464	919	464	291
155°	528	772	528	772	528	243
165°	575	678	575	678	575	162
175°	599	611	599	611	599	57
180°	600	600	600	600	600	

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	636.4	639.1	640.4	642.1	646.1	648.7	652.7	653.6	653.1	654.9	650.1
5°	632.9	638.6	643.9	648.3	655.3	659.7	664.6	670.3	671.6	678.2	674.2
7.5°	628.1	636.4	643.9	652.7	663.2	669.0	676.4	685.2	689.2	697.1	699.3
10°	620.2	632.0	644.8	654.0	668.5	678.6	685.7	699.7	709.0	720.8	719.1
12.5°	607.4	622.8	639.9	655.3	674.2	680.8	694.0	708.5	720.4	731.4	741.0
15°	596.4	614.0	632.9	651.8	673.4	685.7	698.8	717.7	730.5	749.8	758.2
17.5°	581.5	603.9	626.3	647.4	672.9	687.0	703.2	721.7	740.6	759.1	765.7
20°	566.1	590.3	614.5	643.0	672.0	685.7	702.4	725.2	743.7	758.2	758.2
22.5°	547.6	577.1	604.8	632.0	663.7	683.5	700.6	727.4	740.6	743.7	731.8
25°	529.2	558.6	589.0	622.8	658.8	676.4	695.8	720.8	725.2	712.9	682.1
27.5°	507.2	540.2	574.5	610.9	648.7	670.7	688.3	705.0	696.6	663.7	615.8
30°	484.8	520.4	559.1	593.8	639.5	659.7	674.7	679.5	653.1	599.5	537.5
32.5°	461.5	496.2	537.1	578.9	625.0	644.3	654.0	641.3	592.9	525.2	449.6
35°	434.3	473.4	516.0	559.5	605.2	619.7	625.4	594.2	532.3	444.8	369.6
37.5°	409.6	448.8	494.5	538.9	583.3	591.2	585.4	536.7	458.0	371.4	298.0
40°	380.6	422.4	467.2	516.9	553.4	555.6	541.5	478.2	380.6	299.3	254.0
42.5°	353.8	396.0	440.8	491.4	519.1	511.6	492.7	409.6	317.8	258.0	221.5
45°	326.1	366.1	414.5	459.3	479.1	461.5	432.9	344.6	266.8	222.0	193.8
47.5°	299.3	336.7	384.6	427.7	431.2	411.4	377.6	288.8	231.2	195.1	172.3
50°	272.9	310.3	355.1	390.7	387.2	360.0	321.7	251.0	200.9	172.3	153.4
52.5°	246.6	280.4	323.9	352.1	337.1	310.7	272.9	212.7	175.4	150.3	135.8
55°	220.2	251.8	289.2	312.5	288.8	258.4	231.6	182.4	152.1	131.9	120.9
57.5°	198.2	223.3	257.6	271.6	243.1	219.3	196.0	156.9	131.9	117.4	104.6
60°	174.1	196.9	225.0	233.4	203.9	184.6	164.8	132.7	113.0	100.2	91.9
62.5°	153.4	172.3	193.8	193.8	167.9	153.4	138.5	111.2	94.9	84.8	80.9
65°	133.2	146.8	162.2	160.4	138.5	125.7	113.8	91.9	79.6	72.5	68.6
67.5°	113.4	123.9	134.1	127.9	112.1	101.1	90.1	74.3	65.9	61.1	55.8
70°	95.4	103.7	109.0	103.3	87.5	78.2	70.3	59.8	53.2	47.0	44.0
72.5°	80.0	83.5	85.3	78.2	65.0	59.8	54.1	46.6	40.9	37.8	36.9
75°	62.4	65.5	64.2	58.9	47.9	44.0	39.6	34.3	33.0	31.2	30.3
77.5°	48.8	48.8	46.6	41.8	34.3	31.2	29.4	26.8	25.5	25.1	24.2
80°	34.7	34.3	33.0	27.7	23.3	21.5	21.5	19.8	19.3	18.5	18.5
82.5°	22.9	22.9	21.1	16.7	15.4	14.9	14.5	13.6	13.6	13.2	13.2
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.4	7.9	8.4	7.9	7.9
87.5°	6.2	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	1.2	4.6	9.2	11.5	13.9	15.6	17.3	23.1	31.2	38.1	39.2
92.5°	17.3	24.2	33.5	39.2	48.5	54.8	61.2	92.3	136.2	175.5	177.8
95°	40.4	45.0	56.6	67.0	85.4	99.2	113.1	166.2	266.6	400.6	452.5
97.5°	60.0	67.0	79.6	94.7	115.4	131.0	146.6	214.7	354.4	570.2	737.6
100°	88.9	92.3	102.7	121.2	144.3	160.4	176.6	237.8	378.6	628.0	911.9
102.5°	115.4	117.7	128.1	146.6	170.8	187.0	203.2	258.6	379.8	606.0	917.7
105°	140.8	145.4	153.5	170.8	196.2	212.4	228.6	282.8	385.5	576.0	855.4
107.5°	168.5	172.0	180.1	196.2	221.6	237.8	254.0	307.0	398.2	559.8	797.6
110°	196.2	200.9	207.8	222.8	247.0	263.8	280.5	331.3	414.4	555.2	758.4

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.6	226.2	234.3	248.2	271.3	288.6	305.9	354.4	431.7	556.4	733.0
115°	248.2	254.0	260.9	274.7	297.8	313.4	329.0	378.6	449.0	561.0	715.7
117.5°	275.9	280.5	287.4	300.1	322.1	338.2	354.4	400.6	467.5	567.9	706.4
120°	301.3	305.9	312.8	323.2	346.3	362.5	378.6	423.6	486.0	574.9	698.4
122.5°	325.5	329.0	335.9	347.5	370.5	387.2	404.0	445.6	502.1	582.9	693.7
125°	346.3	349.8	356.7	370.5	393.6	409.8	425.9	467.5	519.4	591.0	688.0
127.5°	363.6	368.2	377.5	392.5	414.4	431.2	447.9	488.3	535.6	599.1	684.5
130°	378.6	383.2	394.8	410.9	434.0	450.2	466.3	506.7	550.6	608.3	682.2
132.5°	392.5	398.2	410.9	428.3	452.5	468.6	484.8	522.9	565.6	617.6	681.1
135°	406.3	410.9	424.8	442.1	468.7	484.8	501.0	537.9	578.3	624.5	679.9
137.5°	419.0	424.8	438.6	457.1	483.7	498.7	513.7	550.6	588.7	631.4	679.9
140°	434.0	438.6	452.5	471.0	496.4	511.4	526.4	561.0	596.8	636.0	678.7
142.5°	449.0	452.5	465.2	483.7	507.9	521.8	535.6	569.1	603.7	639.5	678.7
145°	464.0	468.7	480.2	497.5	520.6	533.3	546.0	577.2	609.5	641.8	676.4
147.5°	480.2	483.7	495.2	511.4	531.0	542.6	554.1	584.1	612.9	643.0	673.0
150°	496.4	499.8	509.1	524.1	541.4	551.8	562.2	588.7	615.3	641.8	669.5
152.5°	512.5	513.7	522.9	535.6	551.8	561.0	570.2	593.3	616.4	639.5	663.7
155°	527.5	528.7	535.6	548.3	561.0	569.6	578.3	597.9	617.6	637.2	656.8
157.5°	540.2	541.4	547.1	558.7	569.1	576.6	584.1	601.4	617.6	632.6	649.9
160°	552.9	554.1	558.7	567.9	577.2	583.6	589.9	603.7	617.6	629.1	643.0
162.5°	565.6	564.5	569.1	576.0	584.1	588.7	593.3	604.9	616.4	625.6	637.2
165°	574.9	573.7	576.0	582.9	588.7	592.2	595.6	606.0	614.1	621.0	629.1
167.5°	582.9	581.8	584.1	588.7	593.3	595.6	597.9	606.0	612.9	616.4	622.2
170°	591.0	588.7	589.9	593.3	595.6	597.4	599.1	604.9	610.6	612.9	616.4
172.5°	595.6	594.5	593.3	596.8	597.9	599.0	600.2	603.7	607.2	608.3	609.5
175°	599.1	597.9	596.8	599.1	599.1	599.7	600.2	602.6	604.9	603.7	604.9
177.5°	601.4	599.1	597.9	600.2	600.2	600.2	600.2	601.4	603.7	601.4	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	654.9	655.8	657.1	663.2	664.1	665.9	665.0	665.0	665.4	664.6	665.0
5°	683.0	684.3	690.9	698.4	700.2	698.4	700.6	703.7	703.7	703.7	702.8
7.5°	709.4	714.2	721.7	732.7	734.9	737.1	741.0	738.4	739.3	743.2	741.9
10°	734.9	741.9	750.3	759.5	764.3	767.4	769.2	773.1	782.4	771.8	775.8
12.5°	759.1	769.2	778.0	788.1	791.6	795.5	796.9	800.4	800.4	799.9	803.0
15°	774.9	784.1	792.0	798.6	799.5	798.6	797.7	798.2	799.5	794.2	797.3
17.5°	778.4	779.3	781.9	779.3	779.7	770.5	765.2	763.9	751.6	752.0	762.1
20°	761.3	746.3	742.4	727.9	719.1	695.3	694.5	687.9	661.9	669.8	668.1
22.5°	714.2	688.7	654.9	638.2	629.8	604.8	585.4	571.8	562.6	553.4	549.4
25°	652.3	610.9	563.0	530.1	525.2	501.9	466.3	449.6	429.9	423.7	434.3
27.5°	572.3	518.6	464.6	414.0	404.8	383.7	365.7	353.8	331.0	329.6	330.5
30°	463.7	409.6	364.4	331.4	308.5	298.9	287.0	278.2	269.0	272.5	273.4
32.5°	381.1	329.6	287.4	269.9	259.3	253.2	243.1	237.3	233.4	232.1	231.6
35°	302.8	268.6	249.7	232.5	226.4	222.0	214.5	211.9	208.3	208.8	208.8
37.5°	259.3	230.8	216.7	207.9	202.2	200.0	195.1	192.5	190.3	189.4	190.8
40°	223.7	203.9	195.1	187.2	182.4	181.5	178.9	175.8	173.2	173.6	174.9
42.5°	197.8	186.4	175.8	169.7	166.1	164.8	162.6	160.4	160.4	159.1	158.7
45°	177.1	167.9	159.1	153.4	151.2	149.4	146.8	146.4	144.6	145.0	145.5
47.5°	158.7	151.2	144.6	138.9	136.7	136.3	133.6	131.9	131.9	131.4	131.0
50°	142.0	134.5	128.8	125.7	122.6	121.7	121.3	120.9	120.0	120.0	120.4
52.5°	128.3	120.9	116.5	113.8	112.1	111.2	111.2	110.8	110.8	110.8	110.3
55°	113.4	107.2	103.7	102.8	102.0	101.5	101.1	100.2	99.8	100.7	99.8
57.5°	99.3	97.1	94.1	93.2	91.0	91.0	89.7	88.8	87.9	88.8	88.8
60°	88.3	85.3	83.5	80.9	79.1	77.4	75.2	74.7	73.8	73.4	73.0
62.5°	76.9	74.3	69.9	65.9	63.3	61.5	60.7	60.2	60.2	59.8	59.8
65°	64.2	58.0	55.8	54.5	54.1	53.6	52.7	52.3	52.7	52.3	52.7
67.5°	50.1	49.2	47.9	47.0	46.6	46.2	46.2	45.7	45.7	45.7	45.7
70°	43.5	41.3	40.9	40.0	40.0	39.6	39.6	39.6	39.6	39.1	40.0
72.5°	36.0	34.7	34.3	33.8	33.8	33.8	33.4	33.4	33.4	33.0	33.4
75°	29.4	29.0	28.1	28.1	27.7	28.1	27.7	27.7	27.3	27.7	27.7
77.5°	23.7	23.3	22.9	22.9	22.4	22.4	22.4	22.4	22.4	22.4	22.9
80°	18.0	17.6	17.1	17.6	17.1	17.6	17.1	17.1	17.6	17.1	17.1
82.5°	13.2	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	4.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0
90°	38.1	36.9	34.6	36.9	37.5	38.1	38.1	38.1	38.1	38.1	38.1
92.5°	148.9	116.6	99.3	86.6	81.9	77.3	76.2	71.6	72.7	70.4	72.7
95°	395.9	302.4	232.0	183.5	170.8	158.1	143.1	133.9	130.4	131.6	130.4
97.5°	743.4	618.7	494.1	377.5	342.8	308.2	263.2	240.1	227.4	220.5	227.4
100°	1078.1	1053.9	910.8	752.6	682.8	612.9	517.1	467.5	434.0	413.2	434.0
102.5°	1202.8	1339.0	1334.4	1229.4	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7
105°	1162.4	1402.5	1532.9	1547.9	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1
107.5°	1077.0	1334.4	1528.3	1641.4	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1
110°	997.3	1240.9	1447.5	1595.3	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	941.9	1155.5	1351.7	1512.2	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3
115°	898.1	1088.5	1266.3	1417.5	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5
117.5°	868.1	1033.1	1192.4	1333.2	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4
120°	845.0	993.9	1137.0	1259.4	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9
122.5°	825.3	962.7	1090.8	1205.1	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8
125°	806.9	932.7	1051.6	1153.2	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4
127.5°	789.6	902.7	1012.3	1109.3	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9
130°	772.2	873.8	973.1	1064.3	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4
132.5°	758.4	846.1	936.2	1018.1	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0
135°	745.7	820.7	896.9	973.1	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2
137.5°	736.5	799.9	865.7	928.1	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1
140°	728.4	780.3	835.7	888.8	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9
142.5°	720.3	764.2	809.2	853.0	873.2	893.4	928.1	954.6	969.6	969.6	969.6
145°	713.4	749.2	787.2	823.0	839.8	856.5	884.2	903.8	915.4	918.8	915.4
147.5°	706.4	737.6	768.8	797.6	810.3	823.0	847.3	863.4	871.5	873.8	871.5
150°	697.2	724.9	750.3	774.6	785.0	795.3	812.6	826.5	833.4	834.6	833.4
152.5°	689.1	712.2	735.3	754.9	763.6	772.2	784.9	796.5	801.1	801.1	801.1
155°	678.7	700.7	719.1	736.5	742.8	749.2	761.9	769.9	774.6	772.2	774.6
157.5°	669.5	686.8	703.0	718.0	723.2	728.4	737.6	744.5	746.8	746.8	746.8
160°	659.1	674.1	686.8	699.5	703.6	707.6	715.7	721.5	722.6	722.6	722.6
162.5°	649.9	661.4	671.8	682.2	685.1	688.0	696.1	699.5	700.7	699.5	700.7
165°	639.5	648.7	656.8	664.9	667.2	669.5	674.1	678.7	678.7	677.6	678.7
167.5°	629.1	636.0	643.0	648.7	651.0	653.3	655.7	658.0	658.0	656.8	658.0
170°	621.0	626.8	630.3	634.9	636.0	637.2	638.3	641.8	640.6	638.3	640.6
172.5°	612.9	616.4	618.7	622.2	622.8	623.3	624.5	625.6	624.5	623.3	624.5
175°	606.0	609.5	610.6	611.8	612.3	612.9	612.9	614.1	612.9	610.6	612.9
177.5°	601.4	603.7	603.7	604.9	604.9	604.9	604.9	604.9	603.7	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	666.8	663.7	662.8	663.7	662.8	663.2	660.2	648.7	651.8	647.0	649.6
5°	704.6	701.9	696.2	695.3	694.5	693.6	689.2	679.1	675.1	668.5	668.1
7.5°	740.6	740.6	736.2	733.1	729.2	726.1	720.4	705.4	699.3	691.4	687.0
10°	776.2	764.8	769.6	766.5	756.9	755.1	744.6	735.8	723.9	716.0	709.0
12.5°	801.7	798.2	793.8	791.1	788.5	782.8	775.8	753.3	747.2	731.4	723.5
15°	800.8	798.6	799.9	799.9	799.1	797.7	792.0	775.8	765.2	749.8	736.2
17.5°	757.7	763.5	769.2	773.1	781.9	785.9	791.1	781.5	774.9	761.7	747.2
20°	682.6	696.6	713.4	716.9	724.8	748.1	758.6	767.0	769.6	765.2	753.3
22.5°	578.0	589.8	630.3	629.4	640.8	668.5	699.3	724.3	744.1	755.1	750.7
25°	452.7	469.4	491.0	507.2	544.6	585.9	624.1	664.1	698.4	728.7	736.2
27.5°	342.4	364.4	381.5	403.0	421.9	470.7	520.0	582.4	622.4	679.9	709.8
30°	276.9	287.0	304.2	314.3	323.5	360.9	416.7	478.2	548.5	614.9	666.3
32.5°	236.5	243.5	256.2	260.6	270.3	295.4	330.5	386.8	459.3	539.7	607.4
35°	212.3	219.8	222.4	226.4	234.3	250.1	274.3	315.1	380.6	459.3	540.2
37.5°	191.6	195.6	203.1	205.7	208.3	220.2	236.5	265.0	308.5	373.2	462.8
40°	177.1	179.3	183.3	185.5	187.2	195.6	210.1	229.4	261.5	310.7	393.4
42.5°	161.7	164.4	167.0	169.7	171.9	178.4	187.2	205.7	227.2	264.6	324.4
45°	146.8	148.6	151.6	153.4	156.5	161.7	169.7	182.4	201.7	225.5	273.8
47.5°	133.2	135.4	136.7	138.9	141.1	146.8	154.3	162.6	178.4	201.7	236.9
50°	120.9	123.5	125.3	125.7	127.5	132.7	138.9	148.1	158.2	176.2	207.0
52.5°	112.1	112.5	113.8	115.6	115.2	118.2	123.9	131.0	141.5	156.0	178.4
55°	102.0	103.3	104.2	104.6	104.6	107.2	110.3	116.9	125.3	137.1	156.0
57.5°	89.2	90.5	93.2	94.1	95.4	96.7	98.0	102.4	109.4	120.9	136.3
60°	76.0	76.9	79.6	81.3	82.2	85.7	87.5	91.0	94.9	103.3	117.8
62.5°	61.1	62.0	63.3	65.0	66.8	72.1	76.5	80.0	83.1	88.8	100.7
65°	53.2	53.6	54.5	54.9	55.4	57.6	61.5	66.4	72.1	76.5	83.5
67.5°	46.2	46.6	47.0	47.9	48.3	48.8	50.5	51.9	57.6	63.7	69.0
70°	39.6	40.4	40.9	40.9	41.3	42.2	43.1	44.8	46.6	49.7	56.3
72.5°	33.4	33.8	34.7	34.7	34.7	35.6	36.5	37.4	38.2	40.0	42.6
75°	27.7	28.6	28.6	28.6	29.0	29.0	29.9	30.8	31.6	33.0	33.8
77.5°	22.9	22.9	22.9	22.9	23.3	23.3	23.7	24.6	25.1	25.5	26.4
80°	17.1	17.6	17.6	17.6	18.0	18.0	18.0	18.9	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.2	12.7	13.2	13.2	13.6	13.2	13.6	14.1
85°	7.9	7.9	7.9	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.8
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	38.1	38.1	38.1	37.5	36.9	34.6	36.9	38.1	39.2	38.1	31.2
92.5°	71.6	76.2	77.3	81.9	86.6	99.3	116.6	148.9	177.8	175.5	136.2
95°	133.9	143.1	158.1	170.8	183.5	232.0	302.4	395.9	452.5	400.6	266.6
97.5°	240.1	263.2	308.2	342.8	377.5	494.1	618.7	743.4	737.6	570.2	354.4
100°	467.5	517.1	612.9	682.8	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6
102.5°	879.6	973.1	1079.3	1154.4	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8
105°	1366.7	1438.3	1509.9	1528.9	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5
107.5°	1676.1	1686.5	1687.6	1664.5	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2
110°	1761.5	1739.6	1689.9	1642.6	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1738.4	1698.0	1624.1	1568.2	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7
115°	1671.5	1618.4	1536.4	1477.0	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0
117.5°	1587.2	1530.6	1446.4	1389.8	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5
120°	1499.5	1445.2	1364.4	1311.9	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0
122.5°	1421.0	1367.9	1297.5	1251.3	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1
125°	1350.6	1306.7	1239.7	1196.4	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4
127.5°	1290.5	1249.0	1190.1	1149.7	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6
130°	1236.3	1197.0	1140.5	1102.4	1064.3	973.1	873.8	772.2	682.2	608.3	550.6
132.5°	1183.2	1143.9	1088.5	1053.3	1018.1	936.2	846.1	758.4	681.1	617.6	565.6
135°	1125.5	1087.4	1037.7	1005.4	973.1	896.9	820.7	745.7	679.9	624.5	578.3
137.5°	1066.6	1033.1	985.8	957.0	928.1	865.7	799.9	736.5	679.9	631.4	588.7
140°	1006.6	976.6	939.6	914.2	888.8	835.7	780.3	728.4	678.7	636.0	596.8
142.5°	954.6	928.1	893.4	873.2	853.0	809.2	764.2	720.3	678.7	639.5	603.7
145°	903.8	884.2	856.5	839.8	823.0	787.2	749.2	713.4	676.4	641.8	609.5
147.5°	863.4	847.3	823.0	810.3	797.6	768.8	737.6	706.4	673.0	643.0	612.9
150°	826.5	812.6	795.3	785.0	774.6	750.3	724.9	697.2	669.5	641.8	615.3
152.5°	796.5	784.9	772.2	763.6	754.9	735.3	712.2	689.1	663.7	639.5	616.4
155°	769.9	761.9	749.2	742.8	736.5	719.1	700.7	678.7	656.8	637.2	617.6
157.5°	744.5	737.6	728.4	723.2	718.0	703.0	686.8	669.5	649.9	632.6	617.6
160°	721.5	715.7	707.6	703.6	699.5	686.8	674.1	659.1	643.0	629.1	617.6
162.5°	699.5	696.1	688.0	685.1	682.2	671.8	661.4	649.9	637.2	625.6	616.4
165°	678.7	674.1	669.5	667.2	664.9	656.8	648.7	639.5	629.1	621.0	614.1
167.5°	658.0	655.7	653.3	651.0	648.7	643.0	636.0	629.1	622.2	616.4	612.9
170°	641.8	638.3	637.2	636.0	634.9	630.3	626.8	621.0	616.4	612.9	610.6
172.5°	625.6	624.5	623.3	622.8	622.2	618.7	616.4	612.9	609.5	608.3	607.2
175°	614.1	612.9	612.9	612.3	611.8	610.6	609.5	606.0	604.9	603.7	604.9
177.5°	604.9	604.9	604.9	604.9	604.9	603.7	603.7	601.4	600.2	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	645.7	643.5	643.5	642.1	642.1	635.1	635.1	637.3	634.7	631.6	627.2
5°	662.4	657.5	656.2	654.5	648.7	639.9	636.4	635.1	629.8	623.2	615.8
7.5°	678.2	670.3	666.3	662.4	654.9	642.6	635.6	630.7	622.8	612.7	603.0
10°	693.6	683.5	673.4	668.5	658.0	642.6	632.5	624.6	613.1	599.5	585.9
12.5°	707.6	686.5	684.8	675.1	659.7	642.1	626.8	615.3	600.8	585.0	569.2
15°	719.9	698.4	687.9	679.1	658.8	636.9	620.6	606.5	587.2	569.2	549.8
17.5°	726.1	702.8	695.8	681.3	660.6	632.0	610.1	592.9	571.8	550.3	528.3
20°	732.3	705.0	693.6	683.5	655.3	622.8	598.2	578.4	555.1	529.6	505.5
22.5°	735.3	705.0	691.4	677.3	650.1	612.7	583.7	560.4	533.1	507.2	478.2
25°	730.1	702.4	686.1	671.6	640.8	600.4	567.0	540.6	511.6	482.2	452.7
27.5°	716.9	696.2	677.3	662.4	628.1	584.6	549.4	519.5	489.6	456.7	426.8
30°	692.3	683.0	668.1	651.4	614.0	570.5	528.7	498.0	465.0	432.1	400.8
32.5°	654.0	661.9	652.3	637.8	597.3	551.2	506.8	475.6	439.5	403.9	375.4
35°	607.4	635.6	630.3	620.2	579.7	530.5	486.1	448.3	412.3	376.2	347.7
37.5°	556.4	599.1	603.5	597.3	559.5	509.4	460.6	423.7	386.8	350.3	321.3
40°	486.6	552.0	566.1	568.7	538.4	483.9	432.9	396.9	360.4	324.8	289.6
42.5°	422.4	505.0	522.6	533.6	511.6	458.9	407.4	367.4	331.4	299.3	264.2
45°	362.2	448.3	476.9	491.0	481.3	430.3	377.1	339.8	306.8	277.3	243.5
47.5°	300.2	386.8	426.8	449.2	449.2	401.3	348.1	311.2	279.5	254.5	224.6
50°	258.9	331.0	372.3	401.7	409.6	371.8	321.7	285.7	255.8	228.6	205.7
52.5°	220.6	285.3	319.5	350.3	373.2	340.2	292.3	259.8	230.3	204.8	186.8
55°	190.8	239.1	270.3	304.2	329.6	308.1	263.7	232.1	206.6	185.5	170.1
57.5°	162.2	204.4	229.9	259.8	287.0	270.7	235.1	207.9	185.5	167.0	153.4
60°	138.0	172.3	192.1	215.4	249.2	237.8	208.3	183.3	165.3	148.6	137.1
62.5°	117.4	144.6	161.3	178.0	208.8	203.5	180.6	161.3	145.9	131.9	122.2
65°	96.3	118.7	131.9	146.4	171.0	173.2	154.7	141.1	127.0	114.7	105.9
67.5°	77.8	95.4	107.2	119.6	139.3	145.5	132.7	121.3	109.4	99.3	91.4
70°	62.9	75.2	83.9	93.6	109.9	117.4	110.8	102.8	93.2	84.8	77.8
72.5°	49.7	57.6	62.9	70.3	83.5	91.0	90.5	83.5	76.5	70.8	65.0
75°	36.5	42.6	47.0	51.9	62.4	69.4	71.2	68.1	61.1	56.7	52.3
77.5°	27.7	31.2	33.4	36.9	44.4	50.5	53.2	52.3	47.5	44.0	40.9
80°	21.1	22.0	22.9	24.2	30.3	36.0	37.8	37.4	34.7	33.4	29.9
82.5°	14.9	15.4	15.8	16.3	18.5	23.3	25.1	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.9	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	4.0	4.0	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	23.1	17.3	15.6	13.9	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.3	61.2	54.8	48.5	39.2	33.5	24.2	17.3	24.2	33.5	39.2
95°	166.2	113.1	99.2	85.4	67.0	56.6	45.0	40.4	45.0	56.6	67.0
97.5°	214.7	146.6	131.0	115.4	94.7	79.6	67.0	60.0	67.0	79.6	94.7
100°	237.8	176.6	160.4	144.3	121.2	102.7	92.3	88.9	92.3	102.7	121.2
102.5°	258.6	203.2	187.0	170.8	146.6	128.1	117.7	115.4	117.7	128.1	146.6
105°	282.8	228.6	212.4	196.2	170.8	153.5	145.4	140.8	145.4	153.5	170.8
107.5°	307.0	254.0	237.8	221.6	196.2	180.1	172.0	168.5	172.0	180.1	196.2
110°	331.3	280.5	263.8	247.0	222.8	207.8	200.9	196.2	200.9	207.8	222.8

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	354.4	305.9	288.6	271.3	248.2	234.3	226.2	221.6	226.2	234.3	248.2
115°	378.6	329.0	313.4	297.8	274.7	260.9	254.0	248.2	254.0	260.9	274.7
117.5°	400.6	354.4	338.2	322.1	300.1	287.4	280.5	275.9	280.5	287.4	300.1
120°	423.6	378.6	362.5	346.3	323.2	312.8	305.9	301.3	305.9	312.8	323.2
122.5°	445.6	404.0	387.2	370.5	347.5	335.9	329.0	325.5	329.0	335.9	347.5
125°	467.5	425.9	409.8	393.6	370.5	356.7	349.8	346.3	349.8	356.7	370.5
127.5°	488.3	447.9	431.2	414.4	392.5	377.5	368.2	363.6	368.2	377.5	392.5
130°	506.7	466.3	450.2	434.0	410.9	394.8	383.2	378.6	383.2	394.8	410.9
132.5°	522.9	484.8	468.6	452.5	428.3	410.9	398.2	392.5	398.2	410.9	428.3
135°	537.9	501.0	484.8	468.7	442.1	424.8	410.9	406.3	410.9	424.8	442.1
137.5°	550.6	513.7	498.7	483.7	457.1	438.6	424.8	419.0	424.8	438.6	457.1
140°	561.0	526.4	511.4	496.4	471.0	452.5	438.6	434.0	438.6	452.5	471.0
142.5°	569.1	535.6	521.8	507.9	483.7	465.2	452.5	449.0	452.5	465.2	483.7
145°	577.2	546.0	533.3	520.6	497.5	480.2	468.7	464.0	468.7	480.2	497.5
147.5°	584.1	554.1	542.6	531.0	511.4	495.2	483.7	480.2	483.7	495.2	511.4
150°	588.7	562.2	551.8	541.4	524.1	509.1	499.8	496.4	499.8	509.1	524.1
152.5°	593.3	570.2	561.0	551.8	535.6	522.9	513.7	512.5	513.7	522.9	535.6
155°	597.9	578.3	569.6	561.0	548.3	535.6	528.7	527.5	528.7	535.6	548.3
157.5°	601.4	584.1	576.6	569.1	558.7	547.1	541.4	540.2	541.4	547.1	558.7
160°	603.7	589.9	583.6	577.2	567.9	558.7	554.1	552.9	554.1	558.7	567.9
162.5°	604.9	593.3	588.7	584.1	576.0	569.1	564.5	565.6	564.5	569.1	576.0
165°	606.0	595.6	592.2	588.7	582.9	576.0	573.7	574.9	573.7	576.0	582.9
167.5°	606.0	597.9	595.6	593.3	588.7	584.1	581.8	582.9	581.8	584.1	588.7
170°	604.9	599.1	597.4	595.6	593.3	589.9	588.7	591.0	588.7	589.9	593.3
172.5°	603.7	600.2	599.0	597.9	596.8	593.3	594.5	595.6	594.5	593.3	596.8
175°	602.6	600.2	599.7	599.1	599.1	596.8	597.9	599.1	597.9	596.8	599.1
177.5°	601.4	600.2	600.2	600.2	600.2	597.9	599.1	601.4	599.1	597.9	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	625.4	625.9	627.2	623.2	617.1	614.5	606.5	605.2	603.9	603.9	605.2
5°	611.4	609.6	610.1	602.6	593.8	588.5	577.5	579.3	573.6	570.1	570.9
7.5°	596.0	591.2	590.7	581.1	570.1	560.4	549.0	546.3	541.1	534.9	532.3
10°	576.7	573.1	566.5	555.6	541.5	533.6	518.2	509.0	507.7	498.4	494.9
12.5°	556.9	550.7	544.1	528.7	512.9	500.2	488.8	478.6	471.6	463.7	458.4
15°	534.0	526.6	519.1	502.8	484.4	471.6	454.5	439.5	418.9	402.6	393.4
17.5°	509.0	500.6	490.5	472.5	454.5	436.9	405.2	387.7	373.2	363.5	357.8
20°	483.0	473.8	463.7	445.7	414.5	383.7	366.1	352.5	343.7	334.0	327.0
22.5°	455.8	446.1	435.1	407.0	374.0	352.5	338.9	326.1	313.4	308.1	304.6
25°	430.3	421.5	407.4	369.2	343.3	323.5	308.1	299.8	293.2	286.1	279.5
27.5°	403.9	387.7	367.9	335.8	319.5	299.3	288.3	282.2	270.7	265.9	262.8
30°	372.3	354.3	335.4	312.5	293.6	279.5	269.4	259.3	252.7	247.9	242.6
32.5°	340.2	323.1	311.2	287.4	273.4	258.9	249.2	243.1	233.4	230.3	228.1
35°	312.5	298.0	287.4	268.1	254.9	241.7	234.7	225.5	219.3	213.6	210.1
37.5°	285.3	277.3	266.4	250.1	236.0	225.5	215.8	212.7	204.4	201.3	197.8
40°	266.4	254.5	245.3	231.2	219.3	207.9	201.7	194.7	189.0	184.2	182.8
42.5°	243.5	234.7	229.4	214.0	201.7	195.1	187.7	179.8	175.4	171.4	166.6
45°	226.4	218.4	211.0	198.7	187.7	179.3	172.7	167.5	160.0	158.2	150.8
47.5°	208.3	200.4	194.7	182.4	172.3	164.4	159.5	152.5	146.4	142.4	138.9
50°	190.3	183.7	178.4	167.9	159.1	150.8	144.2	137.1	134.5	127.9	125.7
52.5°	173.2	168.8	163.1	153.0	144.2	137.1	130.1	124.4	120.4	116.9	114.3
55°	158.7	151.6	149.0	138.0	130.5	123.1	116.9	113.4	108.6	106.4	104.2
57.5°	142.4	138.5	134.1	125.7	117.4	110.3	105.9	100.7	98.0	95.4	93.6
60°	128.3	122.6	119.1	112.1	104.6	98.0	94.1	90.1	86.6	84.4	80.9
62.5°	112.1	107.7	105.5	98.0	91.9	85.7	82.2	78.2	75.6	71.6	67.2
65°	98.0	94.5	91.9	85.7	80.0	74.3	70.8	65.9	62.4	60.2	59.8
67.5°	85.7	83.1	79.1	73.4	67.7	63.3	59.3	55.4	54.9	54.1	54.1
70°	72.1	69.4	67.2	61.1	56.3	51.4	50.5	49.2	47.9	47.5	46.6
72.5°	60.2	58.0	55.4	50.1	45.3	44.0	43.1	42.2	40.9	40.4	40.0
75°	48.8	45.7	44.0	39.1	37.8	36.9	36.0	34.7	33.8	33.4	32.5
77.5°	37.4	34.3	34.3	31.6	30.8	29.4	28.6	27.7	27.3	26.4	26.4
80°	26.4	26.4	25.5	24.2	22.9	22.4	21.1	20.7	20.2	20.7	19.8
82.5°	19.3	17.6	17.6	16.7	15.8	15.4	14.5	14.5	14.1	14.1	14.1
85°	11.0	11.0	10.5	9.7	9.2	9.2	8.8	8.8	8.4	8.4	7.9
87.5°	4.4	4.0	4.4	4.0	4.0	3.5	3.5	3.5	3.1	3.5	3.1
90°	13.9	15.6	17.3	23.1	31.2	38.1	39.2	38.1	36.9	34.6	36.9
92.5°	48.5	54.8	61.2	92.3	136.2	175.5	177.8	148.9	116.6	99.3	86.6
95°	85.4	99.2	113.1	166.2	266.6	400.6	452.5	395.9	302.4	232.0	183.5
97.5°	115.4	131.0	146.6	214.7	354.4	570.2	737.6	743.4	618.7	494.1	377.5
100°	144.3	160.4	176.6	237.8	378.6	628.0	911.9	1078.1	1053.9	910.8	752.6
102.5°	170.8	187.0	203.2	258.6	379.8	606.0	917.7	1202.8	1339.0	1334.4	1229.4
105°	196.2	212.4	228.6	282.8	385.5	576.0	855.4	1162.4	1402.5	1532.9	1547.9
107.5°	221.6	237.8	254.0	307.0	398.2	559.8	797.6	1077.0	1334.4	1528.3	1641.4
110°	247.0	263.8	280.5	331.3	414.4	555.2	758.4	997.3	1240.9	1447.5	1595.3



TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.3	288.6	305.9	354.4	431.7	556.4	733.0	941.9	1155.5	1351.7	1512.2
115°	297.8	313.4	329.0	378.6	449.0	561.0	715.7	898.1	1088.5	1266.3	1417.5
117.5°	322.1	338.2	354.4	400.6	467.5	567.9	706.4	868.1	1033.1	1192.4	1333.2
120°	346.3	362.5	378.6	423.6	486.0	574.9	698.4	845.0	993.9	1137.0	1259.4
122.5°	370.5	387.2	404.0	445.6	502.1	582.9	693.7	825.3	962.7	1090.8	1205.1
125°	393.6	409.8	425.9	467.5	519.4	591.0	688.0	806.9	932.7	1051.6	1153.2
127.5°	414.4	431.2	447.9	488.3	535.6	599.1	684.5	789.6	902.7	1012.3	1109.3
130°	434.0	450.2	466.3	506.7	550.6	608.3	682.2	772.2	873.8	973.1	1064.3
132.5°	452.5	468.6	484.8	522.9	565.6	617.6	681.1	758.4	846.1	936.2	1018.1
135°	468.7	484.8	501.0	537.9	578.3	624.5	679.9	745.7	820.7	896.9	973.1
137.5°	483.7	498.7	513.7	550.6	588.7	631.4	679.9	736.5	799.9	865.7	928.1
140°	496.4	511.4	526.4	561.0	596.8	636.0	678.7	728.4	780.3	835.7	888.8
142.5°	507.9	521.8	535.6	569.1	603.7	639.5	678.7	720.3	764.2	809.2	853.0
145°	520.6	533.3	546.0	577.2	609.5	641.8	676.4	713.4	749.2	787.2	823.0
147.5°	531.0	542.6	554.1	584.1	612.9	643.0	673.0	706.4	737.6	768.8	797.6
150°	541.4	551.8	562.2	588.7	615.3	641.8	669.5	697.2	724.9	750.3	774.6
152.5°	551.8	561.0	570.2	593.3	616.4	639.5	663.7	689.1	712.2	735.3	754.9
155°	561.0	569.6	578.3	597.9	617.6	637.2	656.8	678.7	700.7	719.1	736.5
157.5°	569.1	576.6	584.1	601.4	617.6	632.6	649.9	669.5	686.8	703.0	718.0
160°	577.2	583.6	589.9	603.7	617.6	629.1	643.0	659.1	674.1	686.8	699.5
162.5°	584.1	588.7	593.3	604.9	616.4	625.6	637.2	649.9	661.4	671.8	682.2
165°	588.7	592.2	595.6	606.0	614.1	621.0	629.1	639.5	648.7	656.8	664.9
167.5°	593.3	595.6	597.9	606.0	612.9	616.4	622.2	629.1	636.0	643.0	648.7
170°	595.6	597.4	599.1	604.9	610.6	612.9	616.4	621.0	626.8	630.3	634.9
172.5°	597.9	599.0	600.2	603.7	607.2	608.3	609.5	612.9	616.4	618.7	622.2
175°	599.1	599.7	600.2	602.6	604.9	603.7	604.9	606.0	609.5	610.6	611.8
177.5°	600.2	600.2	600.2	601.4	603.7	601.4	600.2	601.4	603.7	603.7	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	605.2	604.3	601.7	602.6	601.3	601.3	600.4	600.4	600.4	602.6	601.3
5°	572.3	569.2	566.1	564.8	563.5	562.2	562.2	561.7	565.7	564.8	568.3
7.5°	531.4	530.5	524.4	524.4	522.2	521.3	523.5	523.9	524.4	525.2	527.4
10°	494.9	492.7	483.9	484.8	483.5	481.7	483.0	482.2	485.2	486.1	485.2
12.5°	451.8	447.9	438.2	433.4	428.1	424.1	429.0	425.5	437.8	441.3	451.0
15°	394.7	387.2	380.6	380.6	375.8	372.3	374.5	378.4	381.1	385.0	386.8
17.5°	356.5	353.4	348.1	345.0	343.7	342.4	342.4	344.1	349.9	349.4	352.9
20°	323.9	322.2	319.5	315.6	314.3	313.4	313.4	313.4	317.3	320.9	323.1
22.5°	301.5	300.2	298.4	293.2	290.5	289.6	291.8	293.2	296.2	298.9	301.1
25°	279.1	276.0	272.9	271.2	269.9	269.9	270.7	271.2	272.5	273.8	276.5
27.5°	260.6	258.4	254.0	249.2	249.2	247.9	248.8	249.7	252.7	257.1	259.3
30°	240.0	239.5	237.8	236.0	234.3	233.4	235.1	236.5	236.9	239.1	239.1
32.5°	225.0	222.0	218.9	217.1	216.2	215.8	216.2	218.0	218.0	220.6	223.7
35°	210.1	208.3	205.3	202.2	201.3	199.1	200.9	202.6	205.7	207.0	208.3
37.5°	193.8	191.6	190.3	189.4	187.7	188.1	186.8	189.4	192.1	191.6	192.5
40°	181.5	177.6	173.6	173.2	172.7	172.3	172.3	172.7	174.5	176.2	178.9
42.5°	165.7	164.4	160.9	157.4	156.5	155.6	154.7	156.5	160.0	163.1	164.4
45°	149.4	147.7	146.8	144.2	142.4	142.0	141.1	143.3	146.4	147.7	148.6
47.5°	134.5	134.1	131.4	131.9	130.5	131.0	130.5	131.9	131.9	133.2	134.1
50°	124.4	123.1	121.7	120.9	119.6	119.6	119.1	119.6	121.3	123.1	122.6
52.5°	114.3	112.1	111.6	111.2	110.3	111.2	109.9	110.3	112.1	113.0	112.5
55°	102.4	102.0	101.1	100.2	99.8	99.3	99.3	99.3	101.1	102.4	102.8
57.5°	93.2	91.0	89.2	89.2	87.5	87.0	87.9	88.3	89.7	90.5	91.4
60°	80.4	79.6	76.9	75.6	73.0	72.5	72.5	74.3	76.5	79.6	80.4
62.5°	66.8	65.5	65.0	65.0	65.0	65.0	65.0	65.0	65.0	65.5	65.5
65°	59.3	59.8	59.3	58.9	59.3	59.3	58.9	58.9	58.9	59.3	59.8
67.5°	53.2	52.7	53.2	52.7	52.3	52.3	51.9	52.3	52.7	53.2	53.2
70°	46.2	46.2	45.7	46.2	45.7	45.3	44.8	44.8	45.7	46.2	46.2
72.5°	39.6	39.6	39.1	39.1	38.2	38.2	38.7	38.2	38.2	39.6	39.6
75°	33.0	32.5	32.1	32.1	31.6	31.6	31.6	31.2	32.1	32.1	32.5
77.5°	25.9	25.9	25.9	25.5	25.5	25.1	25.1	25.5	25.5	25.5	25.9
80°	19.8	19.8	19.8	19.3	18.9	18.9	18.9	18.9	18.9	19.3	18.9
82.5°	13.6	13.6	13.6	13.6	13.6	13.2	13.2	13.2	13.6	13.6	13.2
85°	8.4	7.9	8.4	8.4	7.9	8.4	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	37.5	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	37.5
92.5°	81.9	77.3	76.2	71.6	72.7	70.4	72.7	71.6	76.2	77.3	81.9
95°	170.8	158.1	143.1	133.9	130.4	131.6	130.4	133.9	143.1	158.1	170.8
97.5°	342.8	308.2	263.2	240.1	227.4	220.5	227.4	240.1	263.2	308.2	342.8
100°	682.8	612.9	517.1	467.5	434.0	413.2	434.0	467.5	517.1	612.9	682.8
102.5°	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7	879.6	973.1	1079.3	1154.4
105°	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1	1366.7	1438.3	1509.9	1528.9
107.5°	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1	1676.1	1686.5	1687.6	1664.5
110°	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9	1761.5	1739.6	1689.9	1642.6

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3	1738.4	1698.0	1624.1	1568.2
115°	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5	1671.5	1618.4	1536.4	1477.0
117.5°	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4	1587.2	1530.6	1446.4	1389.8
120°	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9	1499.5	1445.2	1364.4	1311.9
122.5°	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8	1421.0	1367.9	1297.5	1251.3
125°	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4	1350.6	1306.7	1239.7	1196.4
127.5°	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9	1290.5	1249.0	1190.1	1149.7
130°	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4	1236.3	1197.0	1140.5	1102.4
132.5°	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0	1183.2	1143.9	1088.5	1053.3
135°	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2	1125.5	1087.4	1037.7	1005.4
137.5°	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1	1066.6	1033.1	985.8	957.0
140°	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9	1006.6	976.6	939.6	914.2
142.5°	873.2	893.4	928.1	954.6	969.6	969.6	969.6	954.6	928.1	893.4	873.2
145°	839.8	856.5	884.2	903.8	915.4	918.8	915.4	903.8	884.2	856.5	839.8
147.5°	810.3	823.0	847.3	863.4	871.5	873.8	871.5	863.4	847.3	823.0	810.3
150°	785.0	795.3	812.6	826.5	833.4	834.6	833.4	826.5	812.6	795.3	785.0
152.5°	763.6	772.2	784.9	796.5	801.1	801.1	801.1	796.5	784.9	772.2	763.6
155°	742.8	749.2	761.9	769.9	774.6	772.2	774.6	769.9	761.9	749.2	742.8
157.5°	723.2	728.4	737.6	744.5	746.8	746.8	746.8	744.5	737.6	728.4	723.2
160°	703.6	707.6	715.7	721.5	722.6	722.6	722.6	721.5	715.7	707.6	703.6
162.5°	685.1	688.0	696.1	699.5	700.7	699.5	700.7	699.5	696.1	688.0	685.1
165°	667.2	669.5	674.1	678.7	678.7	677.6	678.7	678.7	674.1	669.5	667.2
167.5°	651.0	653.3	655.7	658.0	658.0	656.8	658.0	658.0	655.7	653.3	651.0
170°	636.0	637.2	638.3	641.8	640.6	638.3	640.6	641.8	638.3	637.2	636.0
172.5°	622.8	623.3	624.5	625.6	624.5	623.3	624.5	625.6	624.5	623.3	622.8
175°	612.3	612.9	612.9	614.1	612.9	610.6	612.9	614.1	612.9	612.9	612.3
177.5°	604.9	604.9	604.9	604.9	603.7	601.4	603.7	604.9	604.9	604.9	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	602.6	604.8	603.9	599.1	603.9	605.2	607.9	610.5	612.3	614.9	617.1
5°	564.8	569.2	571.8	569.2	578.0	579.3	585.4	589.0	594.2	598.6	602.2
7.5°	529.2	532.7	538.0	538.9	544.1	550.3	559.1	567.9	576.2	580.6	584.6
10°	491.0	497.1	505.0	503.3	511.2	520.8	530.1	544.1	551.2	559.1	566.1
12.5°	452.7	456.7	467.2	470.7	482.2	489.6	502.4	511.2	528.7	538.0	544.1
15°	385.9	402.2	415.4	431.2	446.1	460.2	471.6	487.4	502.8	509.9	520.0
17.5°	355.6	363.0	371.0	378.9	398.2	423.3	443.5	460.6	473.8	483.0	494.9
20°	323.9	331.4	340.2	347.7	359.5	377.6	402.6	432.1	447.9	457.5	469.0
22.5°	301.5	308.5	314.3	320.9	330.1	343.3	362.2	398.6	419.7	431.6	441.7
25°	277.3	286.1	292.3	297.1	304.6	319.1	334.5	355.1	392.9	402.2	416.2
27.5°	260.6	263.3	270.3	277.8	285.3	293.2	309.0	326.6	352.1	372.3	389.4
30°	240.9	247.5	254.0	257.1	263.7	275.1	284.8	303.7	323.5	339.3	360.0
32.5°	225.9	229.9	234.3	241.7	247.9	255.8	265.5	281.3	298.0	308.1	323.9
35°	209.2	211.9	221.1	224.2	230.3	238.2	247.9	260.2	278.2	286.1	297.6
37.5°	193.4	199.5	202.2	209.2	214.9	222.8	229.9	243.9	255.8	265.0	275.6
40°	181.1	183.7	188.6	194.7	199.5	205.7	214.5	224.6	237.3	244.8	254.0
42.5°	166.1	168.3	174.5	178.0	185.9	191.6	196.9	209.2	220.6	226.4	235.6
45°	149.9	155.2	159.1	166.1	170.5	177.6	184.2	193.0	203.5	210.1	215.4
47.5°	135.8	141.1	145.0	151.6	158.7	161.7	168.8	178.0	187.7	193.0	200.4
50°	124.4	126.1	133.6	136.7	144.2	150.3	155.2	163.1	173.6	176.7	182.8
52.5°	113.4	114.7	119.6	123.5	130.1	135.4	141.5	149.0	157.8	162.6	167.5
55°	103.7	104.6	106.8	111.2	115.6	122.2	127.9	134.9	142.4	147.7	152.1
57.5°	92.7	94.5	96.3	98.9	103.3	109.4	115.6	122.2	128.3	131.9	137.6
60°	80.0	82.6	85.7	88.8	91.9	96.3	103.3	109.4	115.2	118.2	122.6
62.5°	66.4	71.6	74.3	77.8	80.4	84.4	89.7	96.7	100.7	104.6	108.1
65°	59.8	60.2	60.7	64.2	69.0	73.0	77.8	83.1	89.2	91.9	94.5
67.5°	53.2	53.6	54.5	54.9	56.7	61.1	66.4	72.1	76.9	78.7	81.3
70°	46.6	46.6	48.3	48.8	49.2	49.7	54.1	59.8	64.2	66.4	69.4
72.5°	39.6	40.0	40.9	41.3	42.2	43.1	44.4	47.5	52.7	54.9	58.5
75°	32.5	33.0	33.4	33.8	35.2	35.6	36.9	38.7	40.9	43.5	45.7
77.5°	25.9	25.9	26.4	27.3	28.1	28.6	29.9	30.8	31.6	33.0	34.7
80°	19.3	19.8	19.8	20.7	20.7	21.1	21.5	22.9	23.7	24.6	25.5
82.5°	13.2	14.1	14.1	14.1	14.5	14.9	15.4	15.4	16.3	16.7	18.0
85°	7.9	8.4	8.4	8.4	7.9	8.8	8.8	9.2	9.2	9.2	9.7
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	4.0	4.0
90°	36.9	34.6	36.9	38.1	39.2	38.1	31.2	23.1	17.3	15.6	13.9
92.5°	86.6	99.3	116.6	148.9	177.8	175.5	136.2	92.3	61.2	54.8	48.5
95°	183.5	232.0	302.4	395.9	452.5	400.6	266.6	166.2	113.1	99.2	85.4
97.5°	377.5	494.1	618.7	743.4	737.6	570.2	354.4	214.7	146.6	131.0	115.4
100°	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6	237.8	176.6	160.4	144.3
102.5°	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8	258.6	203.2	187.0	170.8
105°	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5	282.8	228.6	212.4	196.2
107.5°	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2	307.0	254.0	237.8	221.6
110°	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4	331.3	280.5	263.8	247.0

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7	354.4	305.9	288.6	271.3
115°	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0	378.6	329.0	313.4	297.8
117.5°	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5	400.6	354.4	338.2	322.1
120°	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0	423.6	378.6	362.5	346.3
122.5°	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1	445.6	404.0	387.2	370.5
125°	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4	467.5	425.9	409.8	393.6
127.5°	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6	488.3	447.9	431.2	414.4
130°	1064.3	973.1	873.8	772.2	682.2	608.3	550.6	506.7	466.3	450.2	434.0
132.5°	1018.1	936.2	846.1	758.4	681.1	617.6	565.6	522.9	484.8	468.6	452.5
135°	973.1	896.9	820.7	745.7	679.9	624.5	578.3	537.9	501.0	484.8	468.7
137.5°	928.1	865.7	799.9	736.5	679.9	631.4	588.7	550.6	513.7	498.7	483.7
140°	888.8	835.7	780.3	728.4	678.7	636.0	596.8	561.0	526.4	511.4	496.4
142.5°	853.0	809.2	764.2	720.3	678.7	639.5	603.7	569.1	535.6	521.8	507.9
145°	823.0	787.2	749.2	713.4	676.4	641.8	609.5	577.2	546.0	533.3	520.6
147.5°	797.6	768.8	737.6	706.4	673.0	643.0	612.9	584.1	554.1	542.6	531.0
150°	774.6	750.3	724.9	697.2	669.5	641.8	615.3	588.7	562.2	551.8	541.4
152.5°	754.9	735.3	712.2	689.1	663.7	639.5	616.4	593.3	570.2	561.0	551.8
155°	736.5	719.1	700.7	678.7	656.8	637.2	617.6	597.9	578.3	569.6	561.0
157.5°	718.0	703.0	686.8	669.5	649.9	632.6	617.6	601.4	584.1	576.6	569.1
160°	699.5	686.8	674.1	659.1	643.0	629.1	617.6	603.7	589.9	583.6	577.2
162.5°	682.2	671.8	661.4	649.9	637.2	625.6	616.4	604.9	593.3	588.7	584.1
165°	664.9	656.8	648.7	639.5	629.1	621.0	614.1	606.0	595.6	592.2	588.7
167.5°	648.7	643.0	636.0	629.1	622.2	616.4	612.9	606.0	597.9	595.6	593.3
170°	634.9	630.3	626.8	621.0	616.4	612.9	610.6	604.9	599.1	597.4	595.6
172.5°	622.2	618.7	616.4	612.9	609.5	608.3	607.2	603.7	600.2	599.0	597.9
175°	611.8	610.6	609.5	606.0	604.9	603.7	604.9	602.6	600.2	599.7	599.1
177.5°	604.9	603.7	603.7	601.4	600.2	601.4	603.7	601.4	600.2	600.2	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	632.5	632.5	632.5	632.5
2.5°	621.1	619.7	627.6	636.4
5°	608.3	610.5	620.6	632.9
7.5°	595.1	600.0	611.8	628.1
10°	576.7	585.4	603.5	620.2
12.5°	558.6	570.5	587.6	607.4
15°	538.4	551.6	572.7	596.4
17.5°	516.0	530.9	555.6	581.5
20°	492.3	512.0	538.0	566.1
22.5°	465.9	489.6	516.4	547.6
25°	440.4	466.3	493.1	529.2
27.5°	415.4	440.8	470.7	507.2
30°	390.3	413.6	445.7	484.8
32.5°	363.5	387.7	421.5	461.5
35°	338.9	363.0	394.7	434.3
37.5°	312.5	338.4	368.8	409.6
40°	281.7	312.1	341.5	380.6
42.5°	256.2	288.3	316.9	353.8
45°	236.0	266.4	290.1	326.1
47.5°	217.1	241.7	265.9	299.3
50°	199.1	218.0	243.1	272.9
52.5°	180.6	196.9	218.4	246.6
55°	163.9	179.3	198.7	220.2
57.5°	148.6	159.5	178.9	198.2
60°	131.4	142.8	157.8	174.1
62.5°	116.9	125.7	139.8	153.4
65°	101.5	109.9	120.4	133.2
67.5°	87.5	94.9	103.3	113.4
70°	74.7	80.4	86.6	95.4
72.5°	61.1	67.2	73.0	80.0
75°	50.1	52.7	57.6	62.4
77.5°	38.7	42.2	44.8	48.8
80°	27.7	30.8	31.6	34.7
82.5°	18.5	20.2	22.0	22.9
85°	10.5	11.4	13.2	13.6
87.5°	4.0	4.4	5.3	6.2
90°	11.5	9.2	4.6	1.2
92.5°	39.2	33.5	24.2	17.3
95°	67.0	56.6	45.0	40.4
97.5°	94.7	79.6	67.0	60.0
100°	121.2	102.7	92.3	88.9
102.5°	146.6	128.1	117.7	115.4
105°	170.8	153.5	145.4	140.8
107.5°	196.2	180.1	172.0	168.5
110°	222.8	207.8	200.9	196.2

TEST NUMBER: P999496

CATALOG NUMBER: SA2XXRDIP-B290D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	248.2	234.3	226.2	221.6
115°	274.7	260.9	254.0	248.2
117.5°	300.1	287.4	280.5	275.9
120°	323.2	312.8	305.9	301.3
122.5°	347.5	335.9	329.0	325.5
125°	370.5	356.7	349.8	346.3
127.5°	392.5	377.5	368.2	363.6
130°	410.9	394.8	383.2	378.6
132.5°	428.3	410.9	398.2	392.5
135°	442.1	424.8	410.9	406.3
137.5°	457.1	438.6	424.8	419.0
140°	471.0	452.5	438.6	434.0
142.5°	483.7	465.2	452.5	449.0
145°	497.5	480.2	468.7	464.0
147.5°	511.4	495.2	483.7	480.2
150°	524.1	509.1	499.8	496.4
152.5°	535.6	522.9	513.7	512.5
155°	548.3	535.6	528.7	527.5
157.5°	558.7	547.1	541.4	540.2
160°	567.9	558.7	554.1	552.9
162.5°	576.0	569.1	564.5	565.6
165°	582.9	576.0	573.7	574.9
167.5°	588.7	584.1	581.8	582.9
170°	593.3	589.9	588.7	591.0
172.5°	596.8	593.3	594.5	595.6
175°	599.1	596.8	597.9	599.1
177.5°	600.2	597.9	599.1	601.4
180°	600.2	600.2	600.2	600.2

(END OF REPORT)