

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999642

Luminaire Tested: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999642
REPORT IS A COMBINATION OF REPORTS P988195 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4377.0 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	20	19
5	65	54	47	41	58	49	42	38	39	34	31	29	26	24	20	18	17
6	60	49	41	36	53	44	38	33	35	30	27	26	23	21	18	16	15
7	56	44	37	31	49	40	33	29	32	27	24	24	21	19	17	15	14
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	13	11
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10075	10075	10075	10075
5°	10100	10702	10135	8550
10°	9987	11313	10059	7060
15°	9772	11315	9936	5304
20°	9510	9353	9717	4376
25°	9195	5844	9394	3723
30°	8791	3743	9031	3205
35°	8299	2876	8569	2743
40°	7754	2417	8083	2399
45°	7168	2058	7467	2014
50°	6569	1749	6875	1742
55°	5905	1519	6225	1500
60°	5316	1159	5599	1145
65°	4764	871	5048	989
70°	4157	697	4482	807
75°	3513	534	3838	609
80°	2786	364	3002	399
85°	1935	188	2119	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9218 cd/sqm

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	1.4
10°-20°	168.5	3.9
20°-30°	216.9	5.0
30°-40°	205.8	4.7
40°-50°	176.3	4.0
50°-60°	134.3	3.1
60°-70°	84.7	1.9
70°-80°	42.3	1.0
80°-90°	14.2	0.3
90°-100°	72.4	1.7
100°-110°	230.3	5.3
110°-120°	394.0	9.0
120°-130°	518.2	11.8
130°-140°	581.7	13.3
140°-150°	570.4	13.0
150°-160°	478.5	10.9
160°-170°	317.3	7.2
170°-180°	110.9	2.5
0°-30°	445.8	10.2
0°-40°	651.5	14.9
0°-60°	962.2	22.0
0°-90°	1103.3	25.2
90°-120°	696.7	15.9
90°-150°	2367.0	54.1
90°-180°	3274.0	74.8
0°-180°	4377.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	636	636	636	636	636	
5°	637	708	639	566	637	60
15°	600	799	610	375	600	169
25°	533	426	544	272	533	245
35°	437	210	451	200	437	273
45°	328	146	342	143	328	253
55°	222	101	234	100	222	200
65°	134	53	142	60	134	133
75°	63	28	69	32	63	68
85°	14	8	15	8	14	16
90°	1	34	1	34	1	4
95°	51	61	51	61	51	57
105°	212	219	212	219	212	224
115°	395	395	395	395	395	391
125°	575	577	575	577	575	514
135°	744	753	744	753	744	575
145°	903	913	903	913	903	564
155°	1033	1040	1033	1040	1033	475
165°	1124	1124	1124	1124	1124	317
175°	1169	1165	1169	1165	1169	111
180°	1171	1171	1171	1171	1171	

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	640.5	643.2	644.5	646.3	650.2	652.9	656.9	657.8	657.3	659.1	654.2
5°	637.0	642.7	648.0	652.5	659.5	664.0	668.8	674.6	675.9	682.5	678.6
7.5°	632.1	640.5	648.0	656.9	667.5	673.2	680.8	689.6	693.6	701.6	703.8
10°	624.1	636.1	648.9	658.2	672.8	683.0	690.1	704.2	713.5	725.4	723.7
12.5°	611.3	626.8	644.0	659.5	678.6	685.2	698.5	713.1	725.0	736.1	745.8
15°	600.3	618.0	637.0	656.0	677.7	690.1	703.3	722.3	735.2	754.6	763.0
17.5°	585.2	607.8	630.3	651.6	677.2	691.4	707.7	726.3	745.3	763.9	770.6
20°	569.7	594.1	618.4	647.1	676.3	690.1	706.9	729.9	748.4	763.0	763.0
22.5°	551.2	580.8	608.7	636.1	667.9	687.8	705.1	732.1	745.3	748.4	736.5
25°	532.6	562.2	592.7	626.8	663.1	680.8	700.2	725.4	729.9	717.5	686.5
27.5°	510.5	543.6	578.1	614.9	652.9	675.0	692.7	709.5	701.1	667.9	619.7
30°	487.9	523.7	562.7	597.6	643.6	664.0	679.0	683.9	657.3	603.4	541.0
32.5°	464.5	499.4	540.5	582.6	629.0	648.5	658.2	645.4	596.7	528.6	452.5
35°	437.0	476.4	519.3	563.1	609.1	623.7	629.5	598.0	535.7	447.6	372.0
37.5°	412.3	451.6	497.6	542.3	587.0	594.9	589.2	540.1	460.9	373.8	299.9
40°	383.1	425.1	470.2	520.2	556.9	559.1	545.0	481.3	383.1	301.2	255.7
42.5°	356.1	398.5	443.7	494.5	522.4	514.9	495.9	412.3	319.8	259.7	222.9
45°	328.2	368.5	417.1	462.2	482.2	464.5	435.7	346.8	268.5	223.4	195.1
47.5°	301.2	338.8	387.0	430.4	433.9	414.0	380.0	290.6	232.7	196.4	173.4
50°	274.7	312.3	357.4	393.2	389.7	362.3	323.8	252.6	202.1	173.4	154.4
52.5°	248.2	282.2	326.0	354.3	339.3	312.7	274.7	214.1	176.5	151.3	136.7
55°	221.6	253.5	291.1	314.5	290.6	260.1	233.1	183.6	153.0	132.7	121.6
57.5°	199.5	224.7	259.2	273.4	244.6	220.7	197.3	157.9	132.7	118.1	105.3
60°	175.2	198.2	226.5	234.9	205.2	185.8	165.9	133.6	113.7	100.9	92.4
62.5°	154.4	173.4	195.1	195.1	169.0	154.4	139.3	111.9	95.5	85.4	81.4
65°	134.0	147.7	163.2	161.5	139.3	126.5	114.6	92.4	80.1	73.0	69.0
67.5°	114.1	124.7	134.9	128.7	112.8	101.7	90.7	74.8	66.4	61.5	56.2
70°	96.0	104.4	109.7	104.0	88.0	78.7	70.8	60.2	53.5	47.3	44.2
72.5°	80.5	84.0	85.8	78.7	65.5	60.2	54.4	46.9	41.1	38.0	37.2
75°	62.8	65.9	64.6	59.3	48.2	44.2	39.8	34.5	33.2	31.4	30.5
77.5°	49.1	49.1	46.9	42.0	34.5	31.4	29.6	27.0	25.7	25.2	24.3
80°	34.9	34.5	33.2	27.9	23.4	21.7	21.7	19.9	19.5	18.6	18.6
82.5°	23.0	23.0	21.2	16.8	15.5	15.0	14.6	13.7	13.7	13.3	13.3
85°	13.7	12.8	10.6	9.3	8.8	8.8	8.4	8.0	8.4	8.0	8.0
87.5°	6.2	4.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	1.0	3.6	6.2	8.9	11.5	12.8	15.2	20.1	24.9	29.8	34.6
92.5°	21.7	23.5	25.2	27.0	28.7	29.6	29.7	29.9	30.2	30.4	30.6
95°	51.4	53.6	55.8	58.0	60.2	61.3	61.5	61.9	62.4	62.8	63.2
97.5°	86.0	88.0	90.0	91.9	93.9	94.9	95.3	96.2	97.1	97.9	98.8
100°	125.5	127.3	129.0	130.8	132.5	133.4	133.7	134.4	135.1	135.7	136.4
102.5°	167.0	168.3	169.6	170.9	172.2	172.9	173.3	174.2	175.1	176.0	176.9
105°	212.4	213.1	213.7	214.4	215.1	215.4	215.6	216.1	216.5	217.0	217.4
107.5°	257.9	258.8	259.7	260.6	261.5	261.9	261.9	261.9	261.9	261.9	261.9
110°	301.4	302.7	304.0	305.3	306.6	307.3	307.3	307.3	307.3	307.3	307.3

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	348.8	350.1	351.4	352.7	354.0	354.7	354.6	354.4	354.1	353.9	353.7
115°	395.2	396.5	397.9	399.2	400.5	401.2	401.0	400.5	400.1	399.6	399.2
117.5°	441.7	443.5	445.2	447.0	448.7	449.6	449.1	448.0	446.9	445.8	444.7
120°	488.1	489.9	491.6	493.4	495.1	496.0	495.1	493.4	491.6	489.9	488.1
122.5°	530.6	532.8	535.0	537.2	539.4	540.5	540.0	538.9	537.8	536.7	535.6
125°	575.1	577.1	579.1	581.0	583.0	584.0	583.7	583.0	582.3	581.7	581.0
127.5°	618.6	621.0	623.4	625.8	628.2	629.4	629.0	628.1	627.2	626.4	625.5
130°	659.1	661.9	664.8	667.6	670.5	671.9	671.7	671.2	670.8	670.3	669.9
132.5°	704.5	706.7	708.9	711.1	713.3	714.4	714.5	714.7	715.0	715.2	715.4
135°	744.1	746.5	748.9	751.3	753.7	754.9	755.1	755.6	756.0	756.5	756.9
137.5°	787.5	789.5	791.5	793.4	795.4	796.4	796.6	797.1	797.5	798.0	798.4
140°	826.1	828.1	830.1	832.0	834.0	835.0	835.5	836.6	837.7	838.8	839.9
142.5°	865.6	867.6	869.6	871.5	873.5	874.5	874.8	875.5	876.1	876.8	877.4
145°	903.1	904.7	906.2	907.8	909.3	910.1	910.8	912.1	913.4	914.7	916.0
147.5°	936.7	938.7	940.7	942.6	944.6	945.6	946.0	946.9	947.8	948.7	949.6
150°	971.3	972.6	973.9	975.2	976.5	977.2	977.6	978.5	979.4	980.3	981.2
152.5°	1002.0	1003.3	1004.6	1005.9	1007.2	1007.9	1008.4	1009.5	1010.6	1011.7	1012.8
155°	1032.6	1033.2	1033.9	1034.5	1035.2	1035.5	1035.8	1036.5	1037.2	1037.8	1038.5
157.5°	1059.3	1059.7	1060.1	1060.6	1061.0	1061.2	1061.4	1061.9	1062.3	1062.8	1063.2
160°	1083.0	1083.4	1083.9	1084.3	1084.8	1085.0	1085.1	1085.3	1085.5	1085.7	1085.9
162.5°	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.8	1105.0	1105.3	1105.5	1105.7
165°	1123.5	1123.3	1123.1	1122.8	1122.6	1122.5	1122.5	1122.5	1122.5	1122.5	1122.5
167.5°	1140.3	1139.6	1139.0	1138.3	1137.6	1137.3	1137.3	1137.3	1137.3	1137.3	1137.3
170°	1153.1	1152.5	1151.8	1151.2	1150.5	1150.2	1150.1	1149.9	1149.6	1149.4	1149.2
172.5°	1162.0	1161.4	1160.7	1160.1	1159.4	1159.1	1159.0	1158.8	1158.5	1158.3	1158.1
175°	1168.9	1168.3	1167.6	1167.0	1166.3	1166.0	1165.8	1165.3	1164.9	1164.4	1164.0
177.5°	1172.9	1172.2	1171.6	1170.9	1170.2	1169.9	1169.7	1169.3	1168.8	1168.4	1168.0
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	659.1	660.0	661.3	667.5	668.4	670.1	669.3	669.3	669.7	668.8	669.3
5°	687.4	688.7	695.4	702.9	704.6	702.9	705.1	708.2	708.2	708.2	707.3
7.5°	713.9	718.8	726.3	737.4	739.6	741.8	745.8	743.1	744.0	748.0	746.7
10°	739.6	746.7	755.1	764.4	769.2	772.3	774.1	778.1	787.4	776.8	780.7
12.5°	763.9	774.1	782.9	793.1	796.7	800.6	802.0	805.5	805.5	805.1	808.2
15°	779.8	789.1	797.1	803.7	804.6	803.7	802.8	803.3	804.6	799.3	802.4
17.5°	783.4	784.3	786.9	784.3	784.7	775.4	770.1	768.8	756.4	756.8	767.0
20°	766.1	751.1	747.1	732.5	723.7	699.8	698.9	692.3	666.2	674.1	672.4
22.5°	718.8	693.1	659.1	642.3	633.9	608.7	589.2	575.5	566.2	556.9	552.9
25°	656.4	614.9	566.6	533.5	528.6	505.2	469.3	452.5	432.6	426.4	437.0
27.5°	575.9	522.0	467.6	416.7	407.4	386.2	368.0	356.1	333.1	331.8	332.6
30°	466.7	412.3	366.7	333.5	310.5	300.8	288.8	280.0	270.7	274.3	275.1
32.5°	383.5	331.8	289.3	271.6	261.0	254.8	244.6	238.9	234.9	233.6	233.1
35°	304.8	270.3	251.2	234.0	227.8	223.4	215.9	213.2	209.7	210.1	210.1
37.5°	261.0	232.2	218.1	209.2	203.5	201.3	196.4	193.7	191.5	190.6	192.0
40°	225.2	205.2	196.4	188.4	183.6	182.7	180.0	176.9	174.3	174.7	176.1
42.5°	199.1	187.6	176.9	170.7	167.2	165.9	163.7	161.5	161.5	160.1	159.7
45°	178.3	169.0	160.1	154.4	152.2	150.4	147.7	147.3	145.5	146.0	146.4
47.5°	159.7	152.2	145.5	139.8	137.6	137.1	134.5	132.7	132.7	132.3	131.8
50°	142.9	135.4	129.6	126.5	123.4	122.5	122.1	121.6	120.8	120.8	121.2
52.5°	129.2	121.6	117.2	114.6	112.8	111.9	111.9	111.5	111.5	111.5	111.0
55°	114.1	107.9	104.4	103.5	102.6	102.2	101.7	100.9	100.4	101.3	100.4
57.5°	100.0	97.8	94.7	93.8	91.6	91.6	90.2	89.4	88.5	89.4	89.4
60°	88.9	85.8	84.0	81.4	79.6	77.9	75.6	75.2	74.3	73.9	73.4
62.5°	77.4	74.8	70.3	66.4	63.7	61.9	61.0	60.6	60.6	60.2	60.2
65°	64.6	58.4	56.2	54.9	54.4	54.0	53.1	52.6	53.1	52.6	53.1
67.5°	50.4	49.5	48.2	47.3	46.9	46.4	46.4	46.0	46.0	46.0	46.0
70°	43.8	41.6	41.1	40.3	40.3	39.8	39.8	39.8	39.8	39.4	40.3
72.5°	36.3	34.9	34.5	34.1	34.1	34.1	33.6	33.6	33.6	33.2	33.6
75°	29.6	29.2	28.3	28.3	27.9	28.3	27.9	27.9	27.4	27.9	27.9
77.5°	23.9	23.4	23.0	23.0	22.6	22.6	22.6	22.6	22.6	22.6	23.0
80°	18.1	17.7	17.3	17.7	17.3	17.7	17.3	17.3	17.7	17.3	17.3
82.5°	13.3	12.8	12.8	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
85°	8.0	7.5	7.5	8.0	7.5	8.0	7.5	7.5	7.5	8.0	8.0
87.5°	3.5	4.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0
90°	34.2	33.7	33.3	32.8	32.6	32.7	32.9	33.2	33.4	33.6	33.4
92.5°	30.8	31.0	31.3	31.5	31.6	31.6	31.6	31.6	31.6	31.6	31.6
95°	63.2	63.2	63.2	63.2	63.2	63.0	62.6	62.1	61.7	61.3	61.7
97.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8
100°	136.4	136.4	136.4	136.4	136.4	136.3	136.1	135.8	135.6	135.4	135.6
102.5°	177.1	177.3	177.6	177.8	177.9	177.8	177.6	177.3	177.1	176.9	177.1
105°	217.8	218.3	218.7	219.2	219.4	219.4	219.4	219.4	219.4	219.4	219.4
107.5°	262.1	262.3	262.5	262.7	262.8	262.3	261.2	260.1	259.0	257.9	259.0
110°	307.3	307.3	307.3	307.3	307.3	307.0	306.3	305.6	305.0	304.3	305.0

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	353.1	352.4	351.8	351.1	350.8	350.6	350.1	349.7	349.2	348.8	349.2
115°	399.0	398.8	398.5	398.3	398.2	397.9	397.2	396.5	395.9	395.2	395.9
117.5°	444.0	443.4	442.7	442.0	441.7	441.4	440.7	440.0	439.4	438.7	439.4
120°	488.1	488.1	488.1	488.1	488.1	487.8	487.1	486.5	485.8	485.2	485.8
122.5°	534.9	534.3	533.6	532.9	532.6	532.4	531.9	531.5	531.0	530.6	531.0
125°	580.3	579.7	579.0	578.3	578.0	577.9	577.7	577.5	577.3	577.1	577.3
127.5°	624.6	623.7	622.8	621.9	621.5	621.2	620.5	619.9	619.2	618.6	619.2
130°	669.5	669.1	668.6	668.2	668.0	667.6	666.7	665.8	664.9	664.0	664.9
132.5°	714.3	713.2	712.1	711.0	710.5	710.2	709.5	708.8	708.2	707.5	708.2
135°	756.7	756.5	756.2	756.0	755.9	755.6	754.9	754.2	753.6	752.9	753.6
137.5°	798.2	798.0	797.7	797.5	797.4	797.0	796.1	795.2	794.4	793.5	794.4
140°	839.9	839.9	839.9	839.9	839.9	839.5	838.6	837.7	836.8	835.9	836.8
142.5°	877.6	877.8	878.1	878.3	878.4	878.0	877.1	876.2	875.4	874.5	875.4
145°	916.2	916.4	916.7	916.9	917.0	916.6	915.7	914.8	913.9	913.0	913.9
147.5°	950.0	950.5	950.9	951.4	951.6	951.2	950.3	949.4	948.5	947.6	948.5
150°	981.9	982.5	983.2	983.9	984.2	983.9	983.2	982.5	981.9	981.2	981.9
152.5°	1013.7	1014.6	1015.5	1016.4	1016.8	1016.4	1015.5	1014.6	1013.7	1012.8	1013.7
155°	1039.6	1040.7	1041.8	1042.9	1043.5	1043.2	1042.5	1041.8	1041.2	1040.5	1041.2
157.5°	1064.7	1066.3	1067.8	1069.3	1070.1	1069.6	1068.5	1067.4	1066.3	1065.2	1066.3
160°	1087.2	1088.6	1089.9	1091.2	1091.9	1091.5	1090.6	1089.7	1088.8	1087.9	1088.8
162.5°	1107.2	1108.8	1110.3	1111.8	1112.6	1112.1	1111.0	1109.9	1108.8	1107.7	1108.8
165°	1124.0	1125.6	1127.1	1128.6	1129.4	1128.9	1127.8	1126.7	1125.6	1124.5	1125.6
167.5°	1138.8	1140.4	1141.9	1143.4	1144.2	1143.7	1142.6	1141.5	1140.4	1139.3	1140.4
170°	1150.7	1152.3	1153.8	1155.3	1156.1	1155.4	1154.1	1152.8	1151.5	1150.2	1151.5
172.5°	1159.6	1161.2	1162.7	1164.2	1165.0	1164.3	1163.0	1161.7	1160.4	1159.1	1160.4
175°	1165.5	1167.1	1168.6	1170.1	1170.9	1170.2	1168.9	1167.6	1166.3	1165.0	1166.3
177.5°	1169.3	1170.6	1171.9	1173.2	1173.9	1173.2	1171.9	1170.6	1169.3	1168.0	1169.3
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	671.0	667.9	667.0	667.9	667.0	667.5	664.4	652.9	656.0	651.1	653.8
5°	709.1	706.4	700.7	699.8	698.9	698.0	693.6	683.4	679.4	672.8	672.4
7.5°	745.3	745.3	740.9	737.8	733.8	730.7	725.0	710.0	703.8	695.8	691.4
10°	781.2	769.7	774.5	771.4	761.7	759.9	749.3	740.5	728.5	720.6	713.5
12.5°	806.8	803.3	798.9	796.2	793.6	787.8	780.7	758.2	752.0	736.1	728.1
15°	805.9	803.7	805.1	805.1	804.2	802.8	797.1	780.7	770.1	754.6	740.9
17.5°	762.6	768.3	774.1	778.1	786.9	790.9	796.2	786.5	779.8	766.6	752.0
20°	687.0	701.1	717.9	721.5	729.4	752.9	763.5	771.9	774.5	770.1	758.2
22.5°	581.7	593.6	634.3	633.4	644.9	672.8	703.8	729.0	748.9	759.9	755.5
25°	455.6	472.4	494.1	510.5	548.1	589.6	628.1	668.4	702.9	733.4	740.9
27.5°	344.6	366.7	384.0	405.6	424.6	473.7	523.3	586.1	626.4	684.3	714.4
30°	278.7	288.8	306.1	316.3	325.6	363.2	419.3	481.3	552.0	618.8	670.6
32.5°	238.0	245.1	257.9	262.3	272.0	297.3	332.6	389.3	462.2	543.2	611.3
35°	213.7	221.2	223.8	227.8	235.8	251.7	276.0	317.2	383.1	462.2	543.6
37.5°	192.9	196.8	204.4	207.0	209.7	221.6	238.0	266.7	310.5	375.5	465.8
40°	178.3	180.5	184.5	186.7	188.4	196.8	211.4	230.9	263.2	312.7	395.9
42.5°	162.8	165.4	168.1	170.7	173.0	179.6	188.4	207.0	228.7	266.3	326.4
45°	147.7	149.5	152.6	154.4	157.5	162.8	170.7	183.6	203.0	226.9	275.6
47.5°	134.0	136.2	137.6	139.8	142.0	147.7	155.3	163.7	179.6	203.0	238.4
50°	121.6	124.3	126.1	126.5	128.3	133.6	139.8	149.1	159.2	177.4	208.3
52.5°	112.8	113.2	114.6	116.3	115.9	119.0	124.7	131.8	142.4	157.0	179.6
55°	102.6	104.0	104.8	105.3	105.3	107.9	111.0	117.7	126.1	138.0	157.0
57.5°	89.8	91.1	93.8	94.7	96.0	97.3	98.6	103.1	110.1	121.6	137.1
60°	76.5	77.4	80.1	81.8	82.7	86.3	88.0	91.6	95.5	104.0	118.5
62.5°	61.5	62.4	63.7	65.5	67.2	72.5	77.0	80.5	83.6	89.4	101.3
65°	53.5	54.0	54.9	55.3	55.7	57.9	61.9	66.8	72.5	77.0	84.0
67.5°	46.4	46.9	47.3	48.2	48.7	49.1	50.9	52.2	57.9	64.1	69.4
70°	39.8	40.7	41.1	41.1	41.6	42.5	43.3	45.1	46.9	50.0	56.6
72.5°	33.6	34.1	34.9	34.9	34.9	35.8	36.7	37.6	38.5	40.3	42.9
75°	27.9	28.8	28.8	28.8	29.2	29.2	30.1	31.0	31.8	33.2	34.1
77.5°	23.0	23.0	23.0	23.0	23.4	23.4	23.9	24.8	25.2	25.7	26.5
80°	17.3	17.7	17.7	17.7	18.1	18.1	18.1	19.0	19.5	19.5	20.3
82.5°	12.8	12.8	12.8	13.3	12.8	13.3	13.3	13.7	13.3	13.7	14.2
85°	8.0	8.0	8.0	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.8
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	33.2	32.9	32.7	32.6	32.8	33.3	33.7	34.2	34.6	29.8	24.9
92.5°	31.6	31.6	31.6	31.6	31.5	31.3	31.0	30.8	30.6	30.4	30.2
95°	62.1	62.6	63.0	63.2	63.2	63.2	63.2	63.2	63.2	62.8	62.4
97.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	97.9	97.1
100°	135.8	136.1	136.3	136.4	136.4	136.4	136.4	136.4	136.4	135.7	135.1
102.5°	177.3	177.6	177.8	177.9	177.8	177.6	177.3	177.1	176.9	176.0	175.1
105°	219.4	219.4	219.4	219.4	219.2	218.7	218.3	217.8	217.4	217.0	216.5
107.5°	260.1	261.2	262.3	262.8	262.7	262.5	262.3	262.1	261.9	261.9	261.9
110°	305.6	306.3	307.0	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	349.7	350.1	350.6	350.8	351.1	351.8	352.4	353.1	353.7	353.9	354.1
115°	396.5	397.2	397.9	398.2	398.3	398.5	398.8	399.0	399.2	399.6	400.1
117.5°	440.0	440.7	441.4	441.7	442.0	442.7	443.4	444.0	444.7	445.8	446.9
120°	486.5	487.1	487.8	488.1	488.1	488.1	488.1	488.1	488.1	489.9	491.6
122.5°	531.5	531.9	532.4	532.6	532.9	533.6	534.3	534.9	535.6	536.7	537.8
125°	577.5	577.7	577.9	578.0	578.3	579.0	579.7	580.3	581.0	581.7	582.3
127.5°	619.9	620.5	621.2	621.5	621.9	622.8	623.7	624.6	625.5	626.4	627.2
130°	665.8	666.7	667.6	668.0	668.2	668.6	669.1	669.5	669.9	670.3	670.8
132.5°	708.8	709.5	710.2	710.5	711.0	712.1	713.2	714.3	715.4	715.2	715.0
135°	754.2	754.9	755.6	755.9	756.0	756.2	756.5	756.7	756.9	756.5	756.0
137.5°	795.2	796.1	797.0	797.4	797.5	797.7	798.0	798.2	798.4	798.0	797.5
140°	837.7	838.6	839.5	839.9	839.9	839.9	839.9	839.9	839.9	838.8	837.7
142.5°	876.2	877.1	878.0	878.4	878.3	878.1	877.8	877.6	877.4	876.8	876.1
145°	914.8	915.7	916.6	917.0	916.9	916.7	916.4	916.2	916.0	914.7	913.4
147.5°	949.4	950.3	951.2	951.6	951.4	950.9	950.5	950.0	949.6	948.7	947.8
150°	982.5	983.2	983.9	984.2	983.9	983.2	982.5	981.9	981.2	980.3	979.4
152.5°	1014.6	1015.5	1016.4	1016.8	1016.4	1015.5	1014.6	1013.7	1012.8	1011.7	1010.6
155°	1041.8	1042.5	1043.2	1043.5	1042.9	1041.8	1040.7	1039.6	1038.5	1037.8	1037.2
157.5°	1067.4	1068.5	1069.6	1070.1	1069.3	1067.8	1066.3	1064.7	1063.2	1062.8	1062.3
160°	1089.7	1090.6	1091.5	1091.9	1091.2	1089.9	1088.6	1087.2	1085.9	1085.7	1085.5
162.5°	1109.9	1111.0	1112.1	1112.6	1111.8	1110.3	1108.8	1107.2	1105.7	1105.5	1105.3
165°	1126.7	1127.8	1128.9	1129.4	1128.6	1127.1	1125.6	1124.0	1122.5	1122.5	1122.5
167.5°	1141.5	1142.6	1143.7	1144.2	1143.4	1141.9	1140.4	1138.8	1137.3	1137.3	1137.3
170°	1152.8	1154.1	1155.4	1156.1	1155.3	1153.8	1152.3	1150.7	1149.2	1149.4	1149.6
172.5°	1161.7	1163.0	1164.3	1165.0	1164.2	1162.7	1161.2	1159.6	1158.1	1158.3	1158.5
175°	1167.6	1168.9	1170.2	1170.9	1170.1	1168.6	1167.1	1165.5	1164.0	1164.4	1164.9
177.5°	1170.6	1171.9	1173.2	1173.9	1173.2	1171.9	1170.6	1169.3	1168.0	1168.4	1168.8
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	649.8	647.6	647.6	646.3	646.3	639.2	639.2	641.4	638.7	635.6	631.2
5°	666.6	661.7	660.4	658.6	652.9	644.0	640.5	639.2	633.9	627.2	619.7
7.5°	682.5	674.6	670.6	666.6	659.1	646.7	639.6	634.8	626.8	616.6	606.9
10°	698.0	687.8	677.7	672.8	662.2	646.7	636.5	628.6	617.1	603.4	589.6
12.5°	712.2	690.9	689.2	679.4	664.0	646.3	630.8	619.3	604.7	588.8	572.8
15°	724.6	702.9	692.3	683.4	663.1	641.0	624.6	610.4	591.0	572.8	553.4
17.5°	730.7	707.3	700.2	685.6	664.8	636.1	614.0	596.7	575.5	553.8	531.7
20°	736.9	709.5	698.0	687.8	659.5	626.8	602.0	582.1	558.7	533.0	508.7
22.5°	740.0	709.5	695.8	681.6	654.2	616.6	587.4	564.0	536.6	510.5	481.3
25°	734.7	706.9	690.5	675.9	644.9	604.2	570.6	544.1	514.9	485.2	455.6
27.5°	721.5	700.7	681.6	666.6	632.1	588.3	552.9	522.8	492.8	459.6	429.5
30°	696.7	687.4	672.4	655.5	618.0	574.2	532.1	501.2	468.0	434.8	403.4
32.5°	658.2	666.2	656.4	641.8	601.1	554.7	510.0	478.6	442.3	406.5	377.8
35°	611.3	639.6	634.3	624.1	583.4	533.9	489.2	451.2	414.9	378.6	349.9
37.5°	560.0	602.9	607.3	601.1	563.1	512.7	463.6	426.4	389.3	352.5	323.4
40°	489.7	555.6	569.7	572.4	541.9	487.0	435.7	399.4	362.7	326.9	291.5
42.5°	425.1	508.2	525.9	537.0	514.9	461.8	410.0	369.8	333.5	301.2	265.8
45°	364.5	451.2	479.9	494.1	484.4	433.1	379.5	341.9	308.8	279.1	245.1
47.5°	302.1	389.3	429.5	452.1	452.1	403.9	350.3	313.2	281.3	256.1	226.0
50°	260.5	333.1	374.7	404.3	412.3	374.2	323.8	287.5	257.4	230.0	207.0
52.5°	222.1	287.1	321.6	352.5	375.5	342.4	294.2	261.4	231.8	206.1	188.0
55°	192.0	240.6	272.0	306.1	331.8	310.1	265.4	233.6	207.9	186.7	171.2
57.5°	163.2	205.7	231.3	261.4	288.8	272.5	236.7	209.2	186.7	168.1	154.4
60°	138.9	173.4	193.3	216.7	250.8	239.3	209.7	184.5	166.3	149.5	138.0
62.5°	118.1	145.5	162.3	179.1	210.1	204.8	181.8	162.3	146.9	132.7	123.0
65°	96.9	119.4	132.7	147.3	172.1	174.3	155.7	142.0	127.8	115.5	106.6
67.5°	78.3	96.0	107.9	120.3	140.2	146.4	133.6	122.1	110.1	100.0	92.0
70°	63.3	75.6	84.5	94.2	110.6	118.1	111.5	103.5	93.8	85.4	78.3
72.5°	50.0	57.9	63.3	70.8	84.0	91.6	91.1	84.0	77.0	71.2	65.5
75°	36.7	42.9	47.3	52.2	62.8	69.9	71.7	68.6	61.5	57.1	52.6
77.5°	27.9	31.4	33.6	37.2	44.7	50.9	53.5	52.6	47.8	44.2	41.1
80°	21.2	22.1	23.0	24.3	30.5	36.3	38.0	37.6	34.9	33.6	30.1
82.5°	15.0	15.5	15.9	16.4	18.6	23.4	25.2	26.1	23.9	22.6	19.5
85°	8.8	9.3	9.3	10.2	10.6	11.9	15.0	15.0	14.6	12.8	12.4
87.5°	4.4	4.4	4.0	4.0	4.4	4.9	5.8	6.6	5.8	5.3	4.9
90°	20.1	15.2	12.8	11.5	8.9	6.2	3.6	1.0	3.6	6.2	8.9
92.5°	29.9	29.7	29.6	28.7	27.0	25.2	23.5	21.7	23.5	25.2	27.0
95°	61.9	61.5	61.3	60.2	58.0	55.8	53.6	51.4	53.6	55.8	58.0
97.5°	96.2	95.3	94.9	93.9	91.9	90.0	88.0	86.0	88.0	90.0	91.9
100°	134.4	133.7	133.4	132.5	130.8	129.0	127.3	125.5	127.3	129.0	130.8
102.5°	174.2	173.3	172.9	172.2	170.9	169.6	168.3	167.0	168.3	169.6	170.9
105°	216.1	215.6	215.4	215.1	214.4	213.7	213.1	212.4	213.1	213.7	214.4
107.5°	261.9	261.9	261.9	261.5	260.6	259.7	258.8	257.9	258.8	259.7	260.6
110°	307.3	307.3	307.3	306.6	305.3	304.0	302.7	301.4	302.7	304.0	305.3

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	354.4	354.6	354.7	354.0	352.7	351.4	350.1	348.8	350.1	351.4	352.7
115°	400.5	401.0	401.2	400.5	399.2	397.9	396.5	395.2	396.5	397.9	399.2
117.5°	448.0	449.1	449.6	448.7	447.0	445.2	443.5	441.7	443.5	445.2	447.0
120°	493.4	495.1	496.0	495.1	493.4	491.6	489.9	488.1	489.9	491.6	493.4
122.5°	538.9	540.0	540.5	539.4	537.2	535.0	532.8	530.6	532.8	535.0	537.2
125°	583.0	583.7	584.0	583.0	581.0	579.1	577.1	575.1	577.1	579.1	581.0
127.5°	628.1	629.0	629.4	628.2	625.8	623.4	621.0	618.6	621.0	623.4	625.8
130°	671.2	671.7	671.9	670.5	667.6	664.8	661.9	659.1	661.9	664.8	667.6
132.5°	714.7	714.5	714.4	713.3	711.1	708.9	706.7	704.5	706.7	708.9	711.1
135°	755.6	755.1	754.9	753.7	751.3	748.9	746.5	744.1	746.5	748.9	751.3
137.5°	797.1	796.6	796.4	795.4	793.4	791.5	789.5	787.5	789.5	791.5	793.4
140°	836.6	835.5	835.0	834.0	832.0	830.1	828.1	826.1	828.1	830.1	832.0
142.5°	875.5	874.8	874.5	873.5	871.5	869.6	867.6	865.6	867.6	869.6	871.5
145°	912.1	910.8	910.1	909.3	907.8	906.2	904.7	903.1	904.7	906.2	907.8
147.5°	946.9	946.0	945.6	944.6	942.6	940.7	938.7	936.7	938.7	940.7	942.6
150°	978.5	977.6	977.2	976.5	975.2	973.9	972.6	971.3	972.6	973.9	975.2
152.5°	1009.5	1008.4	1007.9	1007.2	1005.9	1004.6	1003.3	1002.0	1003.3	1004.6	1005.9
155°	1036.5	1035.8	1035.5	1035.2	1034.5	1033.9	1033.2	1032.6	1033.2	1033.9	1034.5
157.5°	1061.9	1061.4	1061.2	1061.0	1060.6	1060.1	1059.7	1059.3	1059.7	1060.1	1060.6
160°	1085.3	1085.1	1085.0	1084.8	1084.3	1083.9	1083.4	1083.0	1083.4	1083.9	1084.3
162.5°	1105.0	1104.8	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7	1104.7
165°	1122.5	1122.5	1122.5	1122.6	1122.8	1123.1	1123.3	1123.5	1123.3	1123.1	1122.8
167.5°	1137.3	1137.3	1137.3	1137.6	1138.3	1139.0	1139.6	1140.3	1139.6	1139.0	1138.3
170°	1149.9	1150.1	1150.2	1150.5	1151.2	1151.8	1152.5	1153.1	1152.5	1151.8	1151.2
172.5°	1158.8	1159.0	1159.1	1159.4	1160.1	1160.7	1161.4	1162.0	1161.4	1160.7	1160.1
175°	1165.3	1165.8	1166.0	1166.3	1167.0	1167.6	1168.3	1168.9	1168.3	1167.6	1167.0
177.5°	1169.3	1169.7	1169.9	1170.2	1170.9	1171.6	1172.2	1172.9	1172.2	1171.6	1170.9
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	629.5	629.9	631.2	627.2	621.0	618.4	610.4	609.1	607.8	607.8	609.1
5°	615.3	613.5	614.0	606.4	597.6	592.3	581.2	583.0	577.3	573.7	574.6
7.5°	599.8	594.9	594.5	584.8	573.7	564.0	552.5	549.8	544.5	538.3	535.7
10°	580.4	576.8	570.2	559.1	545.0	537.0	521.5	512.2	510.9	501.6	498.1
12.5°	560.4	554.3	547.6	532.1	516.2	503.4	491.9	481.7	474.6	466.7	461.4
15°	537.4	529.9	522.4	506.0	487.5	474.6	457.4	442.3	421.6	405.2	395.9
17.5°	512.2	503.8	493.7	475.5	457.4	439.7	407.8	390.1	375.5	365.8	360.1
20°	486.1	476.8	466.7	448.5	417.1	386.2	368.5	354.8	345.9	336.2	329.1
22.5°	458.7	449.0	437.9	409.6	376.4	354.8	341.0	328.2	315.4	310.1	306.5
25°	433.1	424.2	410.0	371.6	345.5	325.6	310.1	301.7	295.0	288.0	281.3
27.5°	406.5	390.1	370.2	337.9	321.6	301.2	290.2	284.0	272.5	267.6	264.5
30°	374.7	356.5	337.5	314.5	295.5	281.3	271.2	261.0	254.3	249.5	244.2
32.5°	342.4	325.1	313.2	289.3	275.1	260.5	250.8	244.6	234.9	231.8	229.6
35°	314.5	299.9	289.3	269.8	256.6	243.3	236.2	226.9	220.7	215.0	211.4
37.5°	287.1	279.1	268.1	251.7	237.5	226.9	217.2	214.1	205.7	202.6	199.1
40°	268.1	256.1	246.8	232.7	220.7	209.2	203.0	196.0	190.2	185.3	184.0
42.5°	245.1	236.2	230.9	215.4	203.0	196.4	188.9	180.9	176.5	172.5	167.6
45°	227.8	219.8	212.3	199.9	188.9	180.5	173.8	168.5	161.0	159.2	151.7
47.5°	209.7	201.7	196.0	183.6	173.4	165.4	160.6	153.5	147.3	143.3	139.8
50°	191.5	184.9	179.6	169.0	160.1	151.7	145.1	138.0	135.4	128.7	126.5
52.5°	174.3	169.9	164.1	153.9	145.1	138.0	130.9	125.2	121.2	117.7	115.0
55°	159.7	152.6	150.0	138.9	131.4	123.9	117.7	114.1	109.3	107.0	104.8
57.5°	143.3	139.3	134.9	126.5	118.1	111.0	106.6	101.3	98.6	96.0	94.2
60°	129.2	123.4	119.9	112.8	105.3	98.6	94.7	90.7	87.1	84.9	81.4
62.5°	112.8	108.4	106.2	98.6	92.4	86.3	82.7	78.7	76.1	72.1	67.7
65°	98.6	95.1	92.4	86.3	80.5	74.8	71.2	66.4	62.8	60.6	60.2
67.5°	86.3	83.6	79.6	73.9	68.1	63.7	59.7	55.7	55.3	54.4	54.4
70°	72.5	69.9	67.7	61.5	56.6	51.8	50.9	49.5	48.2	47.8	46.9
72.5°	60.6	58.4	55.7	50.4	45.6	44.2	43.3	42.5	41.1	40.7	40.3
75°	49.1	46.0	44.2	39.4	38.0	37.2	36.3	34.9	34.1	33.6	32.7
77.5°	37.6	34.5	34.5	31.8	31.0	29.6	28.8	27.9	27.4	26.5	26.5
80°	26.5	26.5	25.7	24.3	23.0	22.6	21.2	20.8	20.3	20.8	19.9
82.5°	19.5	17.7	17.7	16.8	15.9	15.5	14.6	14.6	14.2	14.2	14.2
85°	11.1	11.1	10.6	9.7	9.3	9.3	8.8	8.8	8.4	8.4	8.0
87.5°	4.4	4.0	4.4	4.0	4.0	3.5	3.5	3.5	3.1	3.5	3.1
90°	11.5	12.8	15.2	20.1	24.9	29.8	34.6	34.2	33.7	33.3	32.8
92.5°	28.7	29.6	29.7	29.9	30.2	30.4	30.6	30.8	31.0	31.3	31.5
95°	60.2	61.3	61.5	61.9	62.4	62.8	63.2	63.2	63.2	63.2	63.2
97.5°	93.9	94.9	95.3	96.2	97.1	97.9	98.8	98.8	98.8	98.8	98.8
100°	132.5	133.4	133.7	134.4	135.1	135.7	136.4	136.4	136.4	136.4	136.4
102.5°	172.2	172.9	173.3	174.2	175.1	176.0	176.9	177.1	177.3	177.6	177.8
105°	215.1	215.4	215.6	216.1	216.5	217.0	217.4	217.8	218.3	218.7	219.2
107.5°	261.5	261.9	261.9	261.9	261.9	261.9	261.9	262.1	262.3	262.5	262.7
110°	306.6	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	354.0	354.7	354.6	354.4	354.1	353.9	353.7	353.1	352.4	351.8	351.1
115°	400.5	401.2	401.0	400.5	400.1	399.6	399.2	399.0	398.8	398.5	398.3
117.5°	448.7	449.6	449.1	448.0	446.9	445.8	444.7	444.0	443.4	442.7	442.0
120°	495.1	496.0	495.1	493.4	491.6	489.9	488.1	488.1	488.1	488.1	488.1
122.5°	539.4	540.5	540.0	538.9	537.8	536.7	535.6	534.9	534.3	533.6	532.9
125°	583.0	584.0	583.7	583.0	582.3	581.7	581.0	580.3	579.7	579.0	578.3
127.5°	628.2	629.4	629.0	628.1	627.2	626.4	625.5	624.6	623.7	622.8	621.9
130°	670.5	671.9	671.7	671.2	670.8	670.3	669.9	669.5	669.1	668.6	668.2
132.5°	713.3	714.4	714.5	714.7	715.0	715.2	715.4	714.3	713.2	712.1	711.0
135°	753.7	754.9	755.1	755.6	756.0	756.5	756.9	756.7	756.5	756.2	756.0
137.5°	795.4	796.4	796.6	797.1	797.5	798.0	798.4	798.2	798.0	797.7	797.5
140°	834.0	835.0	835.5	836.6	837.7	838.8	839.9	839.9	839.9	839.9	839.9
142.5°	873.5	874.5	874.8	875.5	876.1	876.8	877.4	877.6	877.8	878.1	878.3
145°	909.3	910.1	910.8	912.1	913.4	914.7	916.0	916.2	916.4	916.7	916.9
147.5°	944.6	945.6	946.0	946.9	947.8	948.7	949.6	950.0	950.5	950.9	951.4
150°	976.5	977.2	977.6	978.5	979.4	980.3	981.2	981.9	982.5	983.2	983.9
152.5°	1007.2	1007.9	1008.4	1009.5	1010.6	1011.7	1012.8	1013.7	1014.6	1015.5	1016.4
155°	1035.2	1035.5	1035.8	1036.5	1037.2	1037.8	1038.5	1039.6	1040.7	1041.8	1042.9
157.5°	1061.0	1061.2	1061.4	1061.9	1062.3	1062.8	1063.2	1064.7	1066.3	1067.8	1069.3
160°	1084.8	1085.0	1085.1	1085.3	1085.5	1085.7	1085.9	1087.2	1088.6	1089.9	1091.2
162.5°	1104.7	1104.7	1104.8	1105.0	1105.3	1105.5	1105.7	1107.2	1108.8	1110.3	1111.8
165°	1122.6	1122.5	1122.5	1122.5	1122.5	1122.5	1122.5	1124.0	1125.6	1127.1	1128.6
167.5°	1137.6	1137.3	1137.3	1137.3	1137.3	1137.3	1137.3	1138.8	1140.4	1141.9	1143.4
170°	1150.5	1150.2	1150.1	1149.9	1149.6	1149.4	1149.2	1150.7	1152.3	1153.8	1155.3
172.5°	1159.4	1159.1	1159.0	1158.8	1158.5	1158.3	1158.1	1159.6	1161.2	1162.7	1164.2
175°	1166.3	1166.0	1165.8	1165.3	1164.9	1164.4	1164.0	1165.5	1167.1	1168.6	1170.1
177.5°	1170.2	1169.9	1169.7	1169.3	1168.8	1168.4	1168.0	1169.3	1170.6	1171.9	1173.2
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	609.1	608.2	605.6	606.4	605.1	605.1	604.2	604.2	604.2	606.4	605.1
5°	575.9	572.8	569.7	568.4	567.1	565.8	565.8	565.3	569.3	568.4	571.9
7.5°	534.8	533.9	527.7	527.7	525.5	524.6	526.8	527.3	527.7	528.6	530.8
10°	498.1	495.9	487.0	487.9	486.6	484.8	486.1	485.2	488.3	489.2	488.3
12.5°	454.7	450.7	441.0	436.1	430.8	426.9	431.7	428.2	440.6	444.1	453.8
15°	397.2	389.7	383.1	383.1	378.2	374.7	376.9	380.9	383.5	387.5	389.3
17.5°	358.7	355.6	350.3	347.2	345.9	344.6	344.6	346.4	352.1	351.7	355.2
20°	326.0	324.2	321.6	317.6	316.3	315.4	315.4	315.4	319.4	322.9	325.1
22.5°	303.4	302.1	300.3	295.0	292.4	291.5	293.7	295.0	298.1	300.8	303.0
25°	280.9	277.8	274.7	272.9	271.6	271.6	272.5	272.9	274.3	275.6	278.2
27.5°	262.3	260.1	255.7	250.8	250.8	249.5	250.4	251.2	254.3	258.8	261.0
30°	241.5	241.1	239.3	237.5	235.8	234.9	236.7	238.0	238.4	240.6	240.6
32.5°	226.5	223.4	220.3	218.5	217.6	217.2	217.6	219.4	219.4	222.1	225.2
35°	211.4	209.7	206.6	203.5	202.6	200.4	202.1	203.9	207.0	208.3	209.7
37.5°	195.1	192.9	191.5	190.6	188.9	189.3	188.0	190.6	193.3	192.9	193.7
40°	182.7	178.7	174.7	174.3	173.8	173.4	173.4	173.8	175.6	177.4	180.0
42.5°	166.8	165.4	161.9	158.4	157.5	156.6	155.7	157.5	161.0	164.1	165.4
45°	150.4	148.6	147.7	145.1	143.3	142.9	142.0	144.2	147.3	148.6	149.5
47.5°	135.4	134.9	132.3	132.7	131.4	131.8	131.4	132.7	132.7	134.0	134.9
50°	125.2	123.9	122.5	121.6	120.3	120.3	119.9	120.3	122.1	123.9	123.4
52.5°	115.0	112.8	112.4	111.9	111.0	111.9	110.6	111.0	112.8	113.7	113.2
55°	103.1	102.6	101.7	100.9	100.4	100.0	100.0	100.0	101.7	103.1	103.5
57.5°	93.8	91.6	89.8	89.8	88.0	87.6	88.5	88.9	90.2	91.1	92.0
60°	80.9	80.1	77.4	76.1	73.4	73.0	73.0	74.8	77.0	80.1	80.9
62.5°	67.2	65.9	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.9	65.9
65°	59.7	60.2	59.7	59.3	59.7	59.7	59.3	59.3	59.3	59.7	60.2
67.5°	53.5	53.1	53.5	53.1	52.6	52.6	52.2	52.6	53.1	53.5	53.5
70°	46.4	46.4	46.0	46.4	46.0	45.6	45.1	45.1	46.0	46.4	46.4
72.5°	39.8	39.8	39.4	39.4	38.5	38.5	38.9	38.5	38.5	39.8	39.8
75°	33.2	32.7	32.3	32.3	31.8	31.8	31.8	31.4	32.3	32.3	32.7
77.5°	26.1	26.1	26.1	25.7	25.7	25.2	25.2	25.7	25.7	25.7	26.1
80°	19.9	19.9	19.9	19.5	19.0	19.0	19.0	19.0	19.0	19.5	19.0
82.5°	13.7	13.7	13.7	13.7	13.7	13.3	13.3	13.3	13.7	13.7	13.3
85°	8.4	8.0	8.4	8.4	8.0	8.4	8.0	8.0	7.5	7.5	8.0
87.5°	3.5	3.1	2.7	2.7	3.1	2.7	2.7	2.7	3.1	2.7	2.7
90°	32.6	32.7	32.9	33.2	33.4	33.6	33.4	33.2	32.9	32.7	32.6
92.5°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6
95°	63.2	63.0	62.6	62.1	61.7	61.3	61.7	62.1	62.6	63.0	63.2
97.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8
100°	136.4	136.3	136.1	135.8	135.6	135.4	135.6	135.8	136.1	136.3	136.4
102.5°	177.9	177.8	177.6	177.3	177.1	176.9	177.1	177.3	177.6	177.8	177.9
105°	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4
107.5°	262.8	262.3	261.2	260.1	259.0	257.9	259.0	260.1	261.2	262.3	262.8
110°	307.3	307.0	306.3	305.6	305.0	304.3	305.0	305.6	306.3	307.0	307.3

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	350.8	350.6	350.1	349.7	349.2	348.8	349.2	349.7	350.1	350.6	350.8
115°	398.2	397.9	397.2	396.5	395.9	395.2	395.9	396.5	397.2	397.9	398.2
117.5°	441.7	441.4	440.7	440.0	439.4	438.7	439.4	440.0	440.7	441.4	441.7
120°	488.1	487.8	487.1	486.5	485.8	485.2	485.8	486.5	487.1	487.8	488.1
122.5°	532.6	532.4	531.9	531.5	531.0	530.6	531.0	531.5	531.9	532.4	532.6
125°	578.0	577.9	577.7	577.5	577.3	577.1	577.3	577.5	577.7	577.9	578.0
127.5°	621.5	621.2	620.5	619.9	619.2	618.6	619.2	619.9	620.5	621.2	621.5
130°	668.0	667.6	666.7	665.8	664.9	664.0	664.9	665.8	666.7	667.6	668.0
132.5°	710.5	710.2	709.5	708.8	708.2	707.5	708.2	708.8	709.5	710.2	710.5
135°	755.9	755.6	754.9	754.2	753.6	752.9	753.6	754.2	754.9	755.6	755.9
137.5°	797.4	797.0	796.1	795.2	794.4	793.5	794.4	795.2	796.1	797.0	797.4
140°	839.9	839.5	838.6	837.7	836.8	835.9	836.8	837.7	838.6	839.5	839.9
142.5°	878.4	878.0	877.1	876.2	875.4	874.5	875.4	876.2	877.1	878.0	878.4
145°	917.0	916.6	915.7	914.8	913.9	913.0	913.9	914.8	915.7	916.6	917.0
147.5°	951.6	951.2	950.3	949.4	948.5	947.6	948.5	949.4	950.3	951.2	951.6
150°	984.2	983.9	983.2	982.5	981.9	981.2	981.9	982.5	983.2	983.9	984.2
152.5°	1016.8	1016.4	1015.5	1014.6	1013.7	1012.8	1013.7	1014.6	1015.5	1016.4	1016.8
155°	1043.5	1043.2	1042.5	1041.8	1041.2	1040.5	1041.2	1041.8	1042.5	1043.2	1043.5
157.5°	1070.1	1069.6	1068.5	1067.4	1066.3	1065.2	1066.3	1067.4	1068.5	1069.6	1070.1
160°	1091.9	1091.5	1090.6	1089.7	1088.8	1087.9	1088.8	1089.7	1090.6	1091.5	1091.9
162.5°	1112.6	1112.1	1111.0	1109.9	1108.8	1107.7	1108.8	1109.9	1111.0	1112.1	1112.6
165°	1129.4	1128.9	1127.8	1126.7	1125.6	1124.5	1125.6	1126.7	1127.8	1128.9	1129.4
167.5°	1144.2	1143.7	1142.6	1141.5	1140.4	1139.3	1140.4	1141.5	1142.6	1143.7	1144.2
170°	1156.1	1155.4	1154.1	1152.8	1151.5	1150.2	1151.5	1152.8	1154.1	1155.4	1156.1
172.5°	1165.0	1164.3	1163.0	1161.7	1160.4	1159.1	1160.4	1161.7	1163.0	1164.3	1165.0
175°	1170.9	1170.2	1168.9	1167.6	1166.3	1165.0	1166.3	1167.6	1168.9	1170.2	1170.9
177.5°	1173.9	1173.2	1171.9	1170.6	1169.3	1168.0	1169.3	1170.6	1171.9	1173.2	1173.9
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	606.4	608.7	607.8	602.9	607.8	609.1	611.8	614.4	616.2	618.8	621.0
5°	568.4	572.8	575.5	572.8	581.7	583.0	589.2	592.7	598.0	602.5	606.0
7.5°	532.6	536.1	541.4	542.3	547.6	553.8	562.7	571.5	579.9	584.3	588.3
10°	494.1	500.3	508.2	506.5	514.4	524.2	533.5	547.6	554.7	562.7	569.7
12.5°	455.6	459.6	470.2	473.7	485.2	492.8	505.6	514.4	532.1	541.4	547.6
15°	388.4	404.7	418.0	433.9	449.0	463.1	474.6	490.6	506.0	513.1	523.3
17.5°	357.9	365.4	373.3	381.3	400.8	426.0	446.3	463.6	476.8	486.1	498.1
20°	326.0	333.5	342.4	349.9	361.8	380.0	405.2	434.8	450.7	460.5	472.0
22.5°	303.4	310.5	316.3	322.9	332.2	345.5	364.5	401.2	422.4	434.4	444.6
25°	279.1	288.0	294.2	299.0	306.5	321.1	336.6	357.4	395.5	404.7	418.9
27.5°	262.3	265.0	272.0	279.6	287.1	295.0	311.0	328.7	354.3	374.7	391.9
30°	242.4	249.0	255.7	258.8	265.4	276.9	286.6	305.7	325.6	341.5	362.3
32.5°	227.4	231.3	235.8	243.3	249.5	257.4	267.2	283.1	299.9	310.1	326.0
35°	210.6	213.2	222.5	225.6	231.8	239.7	249.5	261.9	280.0	288.0	299.5
37.5°	194.6	200.8	203.5	210.6	216.3	224.3	231.3	245.5	257.4	266.7	277.3
40°	182.2	184.9	189.8	196.0	200.8	207.0	215.9	226.0	238.9	246.4	255.7
42.5°	167.2	169.4	175.6	179.1	187.1	192.9	198.2	210.6	222.1	227.8	237.1
45°	150.8	156.1	160.1	167.2	171.6	178.7	185.3	194.2	204.8	211.4	216.7
47.5°	136.7	142.0	146.0	152.6	159.7	162.8	169.9	179.1	188.9	194.2	201.7
50°	125.2	127.0	134.5	137.6	145.1	151.3	156.1	164.1	174.7	177.8	184.0
52.5°	114.1	115.5	120.3	124.3	130.9	136.2	142.4	150.0	158.8	163.7	168.5
55°	104.4	105.3	107.5	111.9	116.3	123.0	128.7	135.8	143.3	148.6	153.0
57.5°	93.3	95.1	96.9	99.5	104.0	110.1	116.3	123.0	129.2	132.7	138.5
60°	80.5	83.2	86.3	89.4	92.4	96.9	104.0	110.1	115.9	119.0	123.4
62.5°	66.8	72.1	74.8	78.3	80.9	84.9	90.2	97.3	101.3	105.3	108.8
65°	60.2	60.6	61.0	64.6	69.4	73.4	78.3	83.6	89.8	92.4	95.1
67.5°	53.5	54.0	54.9	55.3	57.1	61.5	66.8	72.5	77.4	79.2	81.8
70°	46.9	46.9	48.7	49.1	49.5	50.0	54.4	60.2	64.6	66.8	69.9
72.5°	39.8	40.3	41.1	41.6	42.5	43.3	44.7	47.8	53.1	55.3	58.8
75°	32.7	33.2	33.6	34.1	35.4	35.8	37.2	38.9	41.1	43.8	46.0
77.5°	26.1	26.1	26.5	27.4	28.3	28.8	30.1	31.0	31.8	33.2	34.9
80°	19.5	19.9	19.9	20.8	20.8	21.2	21.7	23.0	23.9	24.8	25.7
82.5°	13.3	14.2	14.2	14.2	14.6	15.0	15.5	15.5	16.4	16.8	18.1
85°	8.0	8.4	8.4	8.4	8.0	8.8	8.8	9.3	9.3	9.3	9.7
87.5°	3.1	2.7	3.1	3.1	3.1	3.5	3.1	3.1	3.5	4.0	4.0
90°	32.8	33.3	33.7	34.2	34.6	29.8	24.9	20.1	15.2	12.8	11.5
92.5°	31.5	31.3	31.0	30.8	30.6	30.4	30.2	29.9	29.7	29.6	28.7
95°	63.2	63.2	63.2	63.2	63.2	62.8	62.4	61.9	61.5	61.3	60.2
97.5°	98.8	98.8	98.8	98.8	98.8	97.9	97.1	96.2	95.3	94.9	93.9
100°	136.4	136.4	136.4	136.4	136.4	135.7	135.1	134.4	133.7	133.4	132.5
102.5°	177.8	177.6	177.3	177.1	176.9	176.0	175.1	174.2	173.3	172.9	172.2
105°	219.2	218.7	218.3	217.8	217.4	217.0	216.5	216.1	215.6	215.4	215.1
107.5°	262.7	262.5	262.3	262.1	261.9	261.9	261.9	261.9	261.9	261.9	261.5
110°	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	306.6

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	351.1	351.8	352.4	353.1	353.7	353.9	354.1	354.4	354.6	354.7	354.0
115°	398.3	398.5	398.8	399.0	399.2	399.6	400.1	400.5	401.0	401.2	400.5
117.5°	442.0	442.7	443.4	444.0	444.7	445.8	446.9	448.0	449.1	449.6	448.7
120°	488.1	488.1	488.1	488.1	488.1	489.9	491.6	493.4	495.1	496.0	495.1
122.5°	532.9	533.6	534.3	534.9	535.6	536.7	537.8	538.9	540.0	540.5	539.4
125°	578.3	579.0	579.7	580.3	581.0	581.7	582.3	583.0	583.7	584.0	583.0
127.5°	621.9	622.8	623.7	624.6	625.5	626.4	627.2	628.1	629.0	629.4	628.2
130°	668.2	668.6	669.1	669.5	669.9	670.3	670.8	671.2	671.7	671.9	670.5
132.5°	711.0	712.1	713.2	714.3	715.4	715.2	715.0	714.7	714.5	714.4	713.3
135°	756.0	756.2	756.5	756.7	756.9	756.5	756.0	755.6	755.1	754.9	753.7
137.5°	797.5	797.7	798.0	798.2	798.4	798.0	797.5	797.1	796.6	796.4	795.4
140°	839.9	839.9	839.9	839.9	839.9	838.8	837.7	836.6	835.5	835.0	834.0
142.5°	878.3	878.1	877.8	877.6	877.4	876.8	876.1	875.5	874.8	874.5	873.5
145°	916.9	916.7	916.4	916.2	916.0	914.7	913.4	912.1	910.8	910.1	909.3
147.5°	951.4	950.9	950.5	950.0	949.6	948.7	947.8	946.9	946.0	945.6	944.6
150°	983.9	983.2	982.5	981.9	981.2	980.3	979.4	978.5	977.6	977.2	976.5
152.5°	1016.4	1015.5	1014.6	1013.7	1012.8	1011.7	1010.6	1009.5	1008.4	1007.9	1007.2
155°	1042.9	1041.8	1040.7	1039.6	1038.5	1037.8	1037.2	1036.5	1035.8	1035.5	1035.2
157.5°	1069.3	1067.8	1066.3	1064.7	1063.2	1062.8	1062.3	1061.9	1061.4	1061.2	1061.0
160°	1091.2	1089.9	1088.6	1087.2	1085.9	1085.7	1085.5	1085.3	1085.1	1085.0	1084.8
162.5°	1111.8	1110.3	1108.8	1107.2	1105.7	1105.5	1105.3	1105.0	1104.8	1104.7	1104.7
165°	1128.6	1127.1	1125.6	1124.0	1122.5	1122.5	1122.5	1122.5	1122.5	1122.5	1122.6
167.5°	1143.4	1141.9	1140.4	1138.8	1137.3	1137.3	1137.3	1137.3	1137.3	1137.3	1137.6
170°	1155.3	1153.8	1152.3	1150.7	1149.2	1149.4	1149.6	1149.9	1150.1	1150.2	1150.5
172.5°	1164.2	1162.7	1161.2	1159.6	1158.1	1158.3	1158.5	1158.8	1159.0	1159.1	1159.4
175°	1170.1	1168.6	1167.1	1165.5	1164.0	1164.4	1164.9	1165.3	1165.8	1166.0	1166.3
177.5°	1173.2	1171.9	1170.6	1169.3	1168.0	1168.4	1168.8	1169.3	1169.7	1169.9	1170.2
180°	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	636.5	636.5	636.5	636.5
2.5°	625.0	623.7	631.7	640.5
5°	612.2	614.4	624.6	637.0
7.5°	598.9	603.8	615.7	632.1
10°	580.4	589.2	607.3	624.1
12.5°	562.2	574.2	591.4	611.3
15°	541.9	555.1	576.4	600.3
17.5°	519.3	534.3	559.1	585.2
20°	495.4	515.3	541.4	569.7
22.5°	468.9	492.8	519.8	551.2
25°	443.2	469.3	496.3	532.6
27.5°	418.0	443.7	473.7	510.5
30°	392.8	416.2	448.5	487.9
32.5°	365.8	390.1	424.2	464.5
35°	341.0	365.4	397.2	437.0
37.5°	314.5	340.6	371.1	412.3
40°	283.5	314.1	343.7	383.1
42.5°	257.9	290.2	318.9	356.1
45°	237.5	268.1	291.9	328.2
47.5°	218.5	243.3	267.6	301.2
50°	200.4	219.4	244.6	274.7
52.5°	181.8	198.2	219.8	248.2
55°	165.0	180.5	199.9	221.6
57.5°	149.5	160.6	180.0	199.5
60°	132.3	143.8	158.8	175.2
62.5°	117.7	126.5	140.7	154.4
65°	102.2	110.6	121.2	134.0
67.5°	88.0	95.5	104.0	114.1
70°	75.2	80.9	87.1	96.0
72.5°	61.5	67.7	73.4	80.5
75°	50.4	53.1	57.9	62.8
77.5°	38.9	42.5	45.1	49.1
80°	27.9	31.0	31.8	34.9
82.5°	18.6	20.3	22.1	23.0
85°	10.6	11.5	13.3	13.7
87.5°	4.0	4.4	5.3	6.2
90°	8.9	6.2	3.6	1.0
92.5°	27.0	25.2	23.5	21.7
95°	58.0	55.8	53.6	51.4
97.5°	91.9	90.0	88.0	86.0
100°	130.8	129.0	127.3	125.5
102.5°	170.9	169.6	168.3	167.0
105°	214.4	213.7	213.1	212.4
107.5°	260.6	259.7	258.8	257.9
110°	305.3	304.0	302.7	301.4

TEST NUMBER: P999642

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	352.7	351.4	350.1	348.8
115°	399.2	397.9	396.5	395.2
117.5°	447.0	445.2	443.5	441.7
120°	493.4	491.6	489.9	488.1
122.5°	537.2	535.0	532.8	530.6
125°	581.0	579.1	577.1	575.1
127.5°	625.8	623.4	621.0	618.6
130°	667.6	664.8	661.9	659.1
132.5°	711.1	708.9	706.7	704.5
135°	751.3	748.9	746.5	744.1
137.5°	793.4	791.5	789.5	787.5
140°	832.0	830.1	828.1	826.1
142.5°	871.5	869.6	867.6	865.6
145°	907.8	906.2	904.7	903.1
147.5°	942.6	940.7	938.7	936.7
150°	975.2	973.9	972.6	971.3
152.5°	1005.9	1004.6	1003.3	1002.0
155°	1034.5	1033.9	1033.2	1032.6
157.5°	1060.6	1060.1	1059.7	1059.3
160°	1084.3	1083.9	1083.4	1083.0
162.5°	1104.7	1104.7	1104.7	1104.7
165°	1122.8	1123.1	1123.3	1123.5
167.5°	1138.3	1139.0	1139.6	1140.3
170°	1151.2	1151.8	1152.5	1153.1
172.5°	1160.1	1160.7	1161.4	1162.0
175°	1167.0	1167.6	1168.3	1168.9
177.5°	1170.9	1171.6	1172.2	1172.9
180°	1170.9	1170.9	1170.9	1170.9

(END OF REPORT)