

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999727

Luminaire Tested: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999727
REPORT IS A COMBINATION OF REPORTS P988282 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3152.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	101	97	93	90	94	90	87	85	79	77	74	68	67	65	58	57	56
2	92	86	80	75	86	80	75	71	70	66	63	61	58	56	53	51	49
3	85	76	69	64	79	72	65	61	63	58	54	55	51	48	47	45	43
4	78	68	61	55	73	64	58	52	57	51	47	50	46	42	43	40	38
5	72	61	54	48	68	58	51	46	51	46	42	45	41	38	39	36	34
6	67	56	48	42	63	53	46	40	47	41	37	41	37	34	36	33	30
7	62	51	43	38	58	48	41	36	43	37	33	38	34	30	33	30	27
8	58	46	39	34	55	44	37	32	39	34	30	35	31	27	31	28	25
9	54	43	35	31	51	41	34	29	36	31	27	33	28	25	29	25	23
10	51	39	32	28	48	37	31	27	34	29	25	30	26	23	27	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17020	17020	17020	17020
5°	17058	18077	17117	14441
10°	16870	19107	16990	11926
15°	16505	19113	16785	8958
20°	16064	15799	16415	7391
25°	15531	9873	15866	6288
30°	14849	6320	15252	5413
35°	14020	4857	14473	4633
40°	13095	4083	13655	4052
45°	12108	3476	12613	3401
50°	11096	2953	11612	2942
55°	9974	2566	10512	2533
60°	8979	1957	9455	1934
65°	8048	1472	8525	1671
70°	7020	1176	7570	1362
75°	5935	902	6478	1030
80°	4710	612	5070	675
85°	3277	315	3588	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15568 cd/sqm

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	3.2
10°-20°	284.7	9.0
20°-30°	366.3	11.6
30°-40°	347.6	11.0
40°-50°	297.9	9.5
50°-60°	226.8	7.2
60°-70°	143.1	4.5
70°-80°	71.4	2.3
80°-90°	19.5	0.6
90°-100°	72.4	2.3
100°-110°	254.9	8.1
110°-120°	267.7	8.5
120°-130°	220.2	7.0
130°-140°	176.9	5.6
140°-150°	133.6	4.2
150°-160°	93.9	3.0
160°-170°	55.3	1.8
170°-180°	18.0	0.6
0°-30°	753.0	23.9
0°-40°	1100.5	34.9
0°-60°	1625.2	51.6
0°-90°	1859.2	59.0
90°-120°	594.9	18.9
90°-150°	1125.6	35.7
90°-180°	1293.0	41.0
0°-180°	3152.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1076	1196	1080	956	1076	102
15°	1014	1350	1031	633	1014	285
25°	900	720	919	459	900	413
35°	738	355	762	338	738	462
45°	554	247	578	241	554	428
55°	374	171	394	169	374	337
65°	226	89	240	101	226	225
75°	106	47	116	54	106	115
85°	23	13	25	14	23	26
90°	0	12	0	12	0	2
95°	12	41	12	41	12	13
105°	44	402	44	402	44	46
115°	77	529	77	529	77	76
125°	107	430	107	430	107	95
135°	126	356	126	356	126	97
145°	144	284	144	284	144	90
155°	163	239	163	239	163	75
165°	178	210	178	210	178	50
175°	185	189	185	189	185	18
180°	186	186	186	186	186	

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1081.9	1086.4	1088.6	1091.6	1098.3	1102.8	1109.5	1111.0	1110.3	1113.3	1105.0
5°	1075.9	1085.6	1094.6	1102.1	1114.0	1121.5	1129.7	1139.4	1141.7	1152.9	1146.1
7.5°	1067.7	1081.9	1094.6	1109.5	1127.5	1137.2	1149.9	1164.8	1171.5	1185.0	1188.7
10°	1054.2	1074.4	1096.1	1111.8	1136.4	1153.6	1165.6	1189.5	1205.2	1225.3	1222.3
12.5°	1032.6	1058.7	1087.9	1114.0	1146.1	1157.3	1179.8	1204.4	1224.6	1243.3	1259.7
15°	1013.9	1043.8	1075.9	1108.0	1144.6	1165.6	1188.0	1220.1	1241.8	1274.6	1288.8
17.5°	988.5	1026.6	1064.7	1100.6	1143.9	1167.8	1195.4	1226.8	1259.0	1290.3	1301.5
20°	962.3	1003.4	1044.5	1093.1	1142.4	1165.6	1194.0	1232.8	1264.2	1288.8	1288.8
22.5°	931.0	981.0	1028.1	1074.4	1128.2	1161.8	1191.0	1236.5	1259.0	1264.2	1244.0
25°	899.6	949.6	1001.2	1058.7	1120.0	1149.9	1182.7	1225.3	1232.8	1211.9	1159.6
27.5°	862.2	918.3	976.5	1038.5	1102.8	1140.2	1170.0	1198.4	1184.2	1128.2	1046.8
30°	824.1	884.6	950.4	1009.4	1087.1	1121.5	1146.9	1155.1	1110.3	1019.1	913.8
32.5°	784.5	843.5	913.0	984.0	1062.5	1095.3	1111.8	1090.1	1007.9	892.8	764.3
35°	738.2	804.7	877.2	951.1	1028.8	1053.5	1063.2	1010.2	904.8	756.1	628.4
37.5°	696.3	762.8	840.5	916.0	991.5	1004.9	995.2	912.3	778.5	631.3	506.6
40°	647.0	718.0	794.2	878.7	940.7	944.4	920.5	812.9	647.0	508.8	431.9
42.5°	601.5	673.2	749.4	835.3	882.4	869.7	837.6	696.3	540.2	438.6	376.6
45°	554.4	622.4	704.6	780.8	814.4	784.5	735.9	585.8	453.5	377.3	329.5
47.5°	508.8	572.3	653.8	727.0	733.0	699.3	641.8	490.9	393.0	331.7	292.9
50°	464.0	527.5	603.7	664.2	658.2	611.9	546.9	426.6	341.4	292.9	260.8
52.5°	419.2	476.7	550.7	598.5	573.1	528.2	464.0	361.6	298.1	255.5	230.9
55°	374.3	428.1	491.6	531.2	490.9	439.3	393.8	310.1	258.5	224.1	205.5
57.5°	337.0	379.6	437.8	461.7	413.2	372.8	333.2	266.7	224.1	199.5	177.8
60°	295.9	334.7	382.5	396.7	346.7	313.8	280.2	225.6	192.0	170.4	156.2
62.5°	260.8	292.9	329.5	329.5	285.4	260.8	235.4	189.0	161.4	144.2	137.5
65°	226.4	249.5	275.7	272.7	235.4	213.7	193.5	156.2	135.2	123.3	116.6
67.5°	192.8	210.7	227.9	217.4	190.5	171.8	153.2	126.3	112.1	103.9	94.9
70°	162.1	176.3	185.3	175.6	148.7	133.0	119.5	101.6	90.4	79.9	74.7
72.5°	136.0	142.0	144.9	133.0	110.6	101.6	91.9	79.2	69.5	64.3	62.8
75°	106.1	111.3	109.1	100.1	81.4	74.7	67.2	58.3	56.0	53.0	51.6
77.5°	82.9	82.9	79.2	71.0	58.3	53.0	50.1	45.6	43.3	42.6	41.1
80°	59.0	58.3	56.0	47.1	39.6	36.6	36.6	33.6	32.9	31.4	31.4
82.5°	38.9	38.9	35.9	28.4	26.2	25.4	24.7	23.2	23.2	22.4	22.4
85°	23.2	21.7	17.9	15.7	14.9	14.9	14.2	13.4	14.2	13.4	13.4
87.5°	10.5	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.4	1.4	2.9	3.6	4.3	4.8	5.4	7.1	9.6	11.8	12.1
92.5°	5.4	7.5	10.4	12.1	15.0	17.0	18.9	28.6	42.1	54.3	55.0
95°	12.5	13.9	17.5	20.7	26.4	30.7	35.0	51.4	82.5	123.9	139.9
97.5°	18.6	20.7	24.6	29.3	35.7	40.5	45.3	66.4	109.6	176.4	228.1
100°	27.5	28.6	31.8	37.5	44.6	49.6	54.6	73.5	117.1	194.2	282.0
102.5°	35.7	36.4	39.6	45.3	52.8	57.8	62.8	80.0	117.5	187.4	283.8
105°	43.6	45.0	47.5	52.8	60.7	65.7	70.7	87.5	119.2	178.1	264.5
107.5°	52.1	53.2	55.7	60.7	68.5	73.5	78.5	95.0	123.2	173.1	246.7
110°	60.7	62.1	64.3	68.9	76.4	81.6	86.8	102.5	128.2	171.7	234.5

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	68.5	70.0	72.5	76.8	83.9	89.2	94.6	109.6	133.5	172.1	226.7
115°	76.8	78.5	80.7	85.0	92.1	96.9	101.7	117.1	138.9	173.5	221.3
117.5°	85.3	86.8	88.9	92.8	99.6	104.6	109.6	123.9	144.6	175.6	218.5
120°	93.2	94.6	96.7	100.0	107.1	112.1	117.1	131.0	150.3	177.8	216.0
122.5°	100.7	101.7	103.9	107.5	114.6	119.8	125.0	137.8	155.3	180.3	214.6
125°	107.1	108.2	110.3	114.6	121.7	126.7	131.7	144.6	160.7	182.8	212.8
127.5°	112.5	113.9	116.7	121.4	128.2	133.4	138.5	151.0	165.6	185.3	211.7
130°	117.1	118.5	122.1	127.1	134.2	139.2	144.2	156.7	170.3	188.1	211.0
132.5°	121.4	123.2	127.1	132.4	139.9	144.9	149.9	161.7	174.9	191.0	210.6
135°	125.7	127.1	131.4	136.7	144.9	149.9	154.9	166.4	178.9	193.1	210.3
137.5°	129.6	131.4	135.7	141.4	149.6	154.2	158.9	170.3	182.1	195.3	210.3
140°	134.2	135.7	139.9	145.7	153.5	158.2	162.8	173.5	184.6	196.7	209.9
142.5°	138.9	139.9	143.9	149.6	157.1	161.4	165.6	176.0	186.7	197.8	209.9
145°	143.5	144.9	148.5	153.9	161.0	165.0	168.9	178.5	188.5	198.5	209.2
147.5°	148.5	149.6	153.2	158.2	164.2	167.8	171.4	180.6	189.6	198.8	208.1
150°	153.5	154.6	157.4	162.1	167.4	170.6	173.9	182.1	190.3	198.5	207.1
152.5°	158.5	158.9	161.7	165.6	170.6	173.5	176.4	183.5	190.6	197.8	205.3
155°	163.1	163.5	165.6	169.6	173.5	176.2	178.9	184.9	191.0	197.1	203.1
157.5°	167.1	167.4	169.2	172.8	176.0	178.3	180.6	186.0	191.0	195.6	201.0
160°	171.0	171.4	172.8	175.6	178.5	180.4	182.4	186.7	191.0	194.6	198.8
162.5°	174.9	174.6	176.0	178.1	180.6	182.0	183.5	187.1	190.6	193.5	197.1
165°	177.8	177.4	178.1	180.3	182.1	183.1	184.2	187.4	189.9	192.1	194.6
167.5°	180.3	179.9	180.6	182.1	183.5	184.2	184.9	187.4	189.6	190.6	192.4
170°	182.8	182.1	182.4	183.5	184.2	184.8	185.3	187.1	188.9	189.6	190.6
172.5°	184.2	183.9	183.5	184.6	184.9	185.2	185.6	186.7	187.8	188.1	188.5
175°	185.3	184.9	184.6	185.3	185.3	185.4	185.6	186.4	187.1	186.7	187.1
177.5°	186.0	185.3	184.9	185.6	185.6	185.6	185.6	186.0	186.7	186.0	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1113.3	1114.8	1117.0	1127.5	1128.9	1131.9	1130.4	1130.4	1131.2	1129.7	1130.4
5°	1161.1	1163.3	1174.5	1187.2	1190.2	1187.2	1191.0	1196.2	1196.2	1196.2	1194.7
7.5°	1205.9	1214.1	1226.8	1245.5	1249.2	1253.0	1259.7	1255.2	1256.7	1263.4	1261.2
10°	1249.2	1261.2	1275.4	1291.1	1299.3	1304.5	1307.5	1314.2	1329.9	1312.0	1318.7
12.5°	1290.3	1307.5	1322.5	1339.6	1345.6	1352.3	1354.6	1360.6	1360.6	1359.8	1365.0
15°	1317.2	1332.9	1346.4	1357.6	1359.1	1357.6	1356.1	1356.8	1359.1	1350.1	1355.3
17.5°	1323.2	1324.7	1329.2	1324.7	1325.5	1309.8	1300.8	1298.6	1277.6	1278.4	1295.6
20°	1294.1	1268.7	1261.9	1237.3	1222.3	1182.0	1180.5	1169.3	1125.2	1138.7	1135.7
22.5°	1214.1	1170.8	1113.3	1084.9	1070.7	1028.1	995.2	972.0	956.4	940.7	933.9
25°	1108.8	1038.5	957.1	901.1	892.8	853.2	792.7	764.3	730.7	720.3	738.2
27.5°	972.8	881.6	789.7	703.8	688.1	652.3	621.6	601.5	562.6	560.4	561.9
30°	788.2	696.3	619.4	563.4	524.5	508.1	487.9	472.9	457.3	463.2	464.7
32.5°	647.8	560.4	488.6	458.8	440.8	430.4	413.2	403.5	396.7	394.5	393.8
35°	514.8	456.5	424.4	395.2	384.8	377.3	364.6	360.1	354.2	354.9	354.9
37.5°	440.8	392.3	368.3	353.4	343.7	340.0	331.7	327.3	323.5	322.0	324.3
40°	380.3	346.7	331.7	318.3	310.1	308.6	304.1	298.9	294.4	295.1	297.4
42.5°	336.2	316.8	298.9	288.4	282.4	280.2	276.4	272.7	272.7	270.5	269.7
45°	301.1	285.4	270.5	260.8	257.0	254.0	249.5	248.8	245.8	246.6	247.3
47.5°	269.7	257.0	245.8	236.1	232.4	231.6	227.1	224.1	224.1	223.4	222.7
50°	241.3	228.6	218.9	213.7	208.5	207.0	206.2	205.5	204.0	204.0	204.7
52.5°	218.2	205.5	198.0	193.5	190.5	189.0	189.0	188.3	188.3	188.3	187.5
55°	192.8	182.3	176.3	174.8	173.3	172.6	171.8	170.4	169.6	171.1	169.6
57.5°	168.9	165.1	159.9	158.4	154.7	154.7	152.4	150.9	149.4	150.9	150.9
60°	150.2	144.9	142.0	137.5	134.5	131.5	127.8	127.0	125.5	124.8	124.0
62.5°	130.8	126.3	118.8	112.1	107.6	104.6	103.1	102.4	102.4	101.6	101.6
65°	109.1	98.6	94.9	92.6	91.9	91.2	89.7	88.9	89.7	88.9	89.7
67.5°	85.2	83.7	81.4	79.9	79.2	78.5	78.5	77.7	77.7	77.7	77.7
70°	74.0	70.2	69.5	68.0	68.0	67.2	67.2	67.2	67.2	66.5	68.0
72.5°	61.3	59.0	58.3	57.5	57.5	57.5	56.8	56.8	56.8	56.0	56.8
75°	50.1	49.3	47.8	47.8	47.1	47.8	47.1	47.1	46.3	47.1	47.1
77.5°	40.3	39.6	38.9	38.9	38.1	38.1	38.1	38.1	38.1	38.1	38.9
80°	30.6	29.9	29.1	29.9	29.1	29.9	29.1	29.1	29.9	29.1	29.1
82.5°	22.4	21.7	21.7	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
85°	13.4	12.7	12.7	13.4	12.7	13.4	12.7	12.7	12.7	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	11.8	11.4	10.7	11.4	11.6	11.8	11.8	11.8	11.8	11.8	11.8
92.5°	46.1	36.1	30.7	26.8	25.4	23.9	23.6	22.1	22.5	21.8	22.5
95°	122.5	93.5	71.8	56.8	52.8	48.9	44.3	41.4	40.3	40.7	40.3
97.5°	229.9	191.4	152.8	116.7	106.0	95.3	81.4	74.3	70.3	68.2	70.3
100°	333.4	325.9	281.7	232.8	211.2	189.6	159.9	144.6	134.2	127.8	134.2
102.5°	372.0	414.1	412.7	380.2	357.0	333.8	301.0	272.0	258.5	249.2	258.5
105°	359.5	433.8	474.1	478.7	472.8	467.0	444.8	422.7	407.3	402.3	407.3
107.5°	333.1	412.7	472.7	507.7	514.8	521.9	521.6	518.4	513.7	505.5	513.7
110°	308.4	383.8	447.7	493.4	508.0	522.7	538.0	544.8	548.0	547.6	548.0

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	291.3	357.4	418.0	467.7	485.0	502.3	525.1	537.6	544.4	546.9	544.4
115°	277.7	336.7	391.6	438.4	456.8	475.2	500.5	516.9	526.2	529.4	526.2
117.5°	268.5	319.5	368.8	412.3	429.8	447.3	473.4	490.9	500.5	503.0	500.5
120°	261.3	307.4	351.6	389.5	405.8	422.0	447.0	463.7	474.1	477.7	474.1
122.5°	255.3	297.7	337.4	372.7	387.0	401.3	423.0	439.5	448.4	451.2	448.4
125°	249.5	288.5	325.2	356.6	370.0	383.4	404.1	417.7	426.6	429.5	426.6
127.5°	244.2	279.2	313.1	343.1	355.6	368.1	386.3	399.1	407.0	409.1	407.0
130°	238.8	270.3	301.0	329.2	341.0	352.7	370.2	382.3	389.5	392.3	389.5
132.5°	234.5	261.7	289.5	314.9	325.8	336.7	353.8	365.9	372.4	374.9	372.4
135°	230.6	253.8	277.4	301.0	311.0	320.9	336.3	348.1	354.5	355.9	354.5
137.5°	227.8	247.4	267.8	287.0	296.0	304.9	319.5	329.9	335.6	337.7	335.6
140°	225.3	241.3	258.5	274.9	282.8	290.6	302.0	311.3	316.7	318.8	316.7
142.5°	222.8	236.3	250.3	263.8	270.0	276.3	287.0	295.2	299.9	299.9	299.9
145°	220.6	231.7	243.5	254.5	259.7	264.9	273.5	279.5	283.1	284.2	283.1
147.5°	218.5	228.1	237.8	246.7	250.6	254.5	262.0	267.0	269.5	270.3	269.5
150°	215.6	224.2	232.1	239.5	242.8	246.0	251.3	255.6	257.8	258.1	257.8
152.5°	213.1	220.3	227.4	233.5	236.2	238.8	242.8	246.3	247.8	247.8	247.8
155°	209.9	216.7	222.4	227.8	229.8	231.7	235.6	238.1	239.5	238.8	239.5
157.5°	207.1	212.4	217.4	222.1	223.7	225.3	228.1	230.3	231.0	231.0	231.0
160°	203.8	208.5	212.4	216.3	217.6	218.8	221.3	223.1	223.5	223.5	223.5
162.5°	201.0	204.6	207.8	211.0	211.9	212.8	215.3	216.3	216.7	216.3	216.7
165°	197.8	200.6	203.1	205.6	206.4	207.1	208.5	209.9	209.9	209.6	209.9
167.5°	194.6	196.7	198.8	200.6	201.4	202.1	202.8	203.5	203.5	203.1	203.5
170°	192.1	193.9	194.9	196.4	196.8	197.1	197.4	198.5	198.1	197.4	198.1
172.5°	189.6	190.6	191.4	192.4	192.6	192.8	193.1	193.5	193.1	192.8	193.1
175°	187.4	188.5	188.9	189.2	189.4	189.6	189.6	189.9	189.6	188.9	189.6
177.5°	186.0	186.7	186.7	187.1	187.1	187.1	187.1	187.1	186.7	186.0	186.7
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1133.4	1128.2	1126.7	1128.2	1126.7	1127.5	1122.2	1102.8	1108.0	1099.8	1104.3
5°	1197.7	1193.2	1183.5	1182.0	1180.5	1179.0	1171.5	1154.4	1147.6	1136.4	1135.7
7.5°	1259.0	1259.0	1251.5	1246.3	1239.5	1234.3	1224.6	1199.2	1188.7	1175.3	1167.8
10°	1319.5	1300.0	1308.3	1303.0	1286.6	1283.6	1265.7	1250.7	1230.6	1217.1	1205.2
12.5°	1362.8	1356.8	1349.4	1344.9	1340.4	1330.7	1318.7	1280.6	1270.2	1243.3	1229.8
15°	1361.3	1357.6	1359.8	1359.8	1358.3	1356.1	1346.4	1318.7	1300.8	1274.6	1251.5
17.5°	1288.1	1297.8	1307.5	1314.2	1329.2	1335.9	1344.9	1328.4	1317.2	1294.8	1270.2
20°	1160.3	1184.2	1212.6	1218.6	1232.1	1271.7	1289.6	1303.8	1308.3	1300.8	1280.6
22.5°	982.5	1002.7	1071.4	1069.9	1089.4	1136.4	1188.7	1231.3	1264.9	1283.6	1276.1
25°	769.6	798.0	834.6	862.2	925.7	996.0	1061.0	1128.9	1187.2	1238.8	1251.5
27.5°	582.0	619.4	648.5	685.1	717.3	800.2	883.9	990.0	1058.0	1155.8	1206.7
30°	470.7	487.9	517.0	534.2	549.9	613.4	708.3	812.9	932.4	1045.3	1132.7
32.5°	402.0	413.9	435.6	443.1	459.5	502.1	561.9	657.5	780.8	917.5	1032.6
35°	360.9	373.6	378.1	384.8	398.2	425.1	466.2	535.7	647.0	780.8	918.3
37.5°	325.8	332.5	345.2	349.7	354.2	374.3	402.0	450.5	524.5	634.3	786.8
40°	301.1	304.8	311.6	315.3	318.3	332.5	357.1	390.0	444.6	528.2	668.7
42.5°	275.0	279.4	283.9	288.4	292.1	303.3	318.3	349.7	386.3	449.8	551.4
45°	249.5	252.5	257.8	260.8	266.0	275.0	288.4	310.1	342.9	383.3	465.5
47.5°	226.4	230.1	232.4	236.1	239.8	249.5	262.3	276.4	303.3	342.9	402.7
50°	205.5	210.0	212.9	213.7	216.7	225.6	236.1	251.8	269.0	299.6	351.9
52.5°	190.5	191.3	193.5	196.5	195.8	201.0	210.7	222.7	240.6	265.2	303.3
55°	173.3	175.6	177.1	177.8	177.8	182.3	187.5	198.7	212.9	233.1	265.2
57.5°	151.7	153.9	158.4	159.9	162.1	164.4	166.6	174.1	186.0	205.5	231.6
60°	129.3	130.8	135.2	138.2	139.7	145.7	148.7	154.7	161.4	175.6	200.2
62.5°	103.9	105.3	107.6	110.6	113.6	122.5	130.0	136.0	141.2	150.9	171.1
65°	90.4	91.2	92.6	93.4	94.1	97.9	104.6	112.8	122.5	130.0	142.0
67.5°	78.5	79.2	79.9	81.4	82.2	82.9	85.9	88.2	97.9	108.3	117.3
70°	67.2	68.7	69.5	69.5	70.2	71.7	73.2	76.2	79.2	84.4	95.6
72.5°	56.8	57.5	59.0	59.0	59.0	60.5	62.0	63.5	65.0	68.0	72.5
75°	47.1	48.6	48.6	48.6	49.3	49.3	50.8	52.3	53.8	56.0	57.5
77.5°	38.9	38.9	38.9	38.9	39.6	39.6	40.3	41.8	42.6	43.3	44.8
80°	29.1	29.9	29.9	29.9	30.6	30.6	30.6	32.1	32.9	32.9	34.4
82.5°	21.7	21.7	21.7	22.4	21.7	22.4	22.4	23.2	22.4	23.2	23.9
85°	13.4	13.4	13.4	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	6.7	6.7
90°	11.8	11.8	11.8	11.6	11.4	10.7	11.4	11.8	12.1	11.8	9.6
92.5°	22.1	23.6	23.9	25.4	26.8	30.7	36.1	46.1	55.0	54.3	42.1
95°	41.4	44.3	48.9	52.8	56.8	71.8	93.5	122.5	139.9	123.9	82.5
97.5°	74.3	81.4	95.3	106.0	116.7	152.8	191.4	229.9	228.1	176.4	109.6
100°	144.6	159.9	189.6	211.2	232.8	281.7	325.9	333.4	282.0	194.2	117.1
102.5°	272.0	301.0	333.8	357.0	380.2	412.7	414.1	372.0	283.8	187.4	117.5
105°	422.7	444.8	467.0	472.8	478.7	474.1	433.8	359.5	264.5	178.1	119.2
107.5°	518.4	521.6	521.9	514.8	507.7	472.7	412.7	333.1	246.7	173.1	123.2
110°	544.8	538.0	522.7	508.0	493.4	447.7	383.8	308.4	234.5	171.7	128.2

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	537.6	525.1	502.3	485.0	467.7	418.0	357.4	291.3	226.7	172.1	133.5
115°	516.9	500.5	475.2	456.8	438.4	391.6	336.7	277.7	221.3	173.5	138.9
117.5°	490.9	473.4	447.3	429.8	412.3	368.8	319.5	268.5	218.5	175.6	144.6
120°	463.7	447.0	422.0	405.8	389.5	351.6	307.4	261.3	216.0	177.8	150.3
122.5°	439.5	423.0	401.3	387.0	372.7	337.4	297.7	255.3	214.6	180.3	155.3
125°	417.7	404.1	383.4	370.0	356.6	325.2	288.5	249.5	212.8	182.8	160.7
127.5°	399.1	386.3	368.1	355.6	343.1	313.1	279.2	244.2	211.7	185.3	165.6
130°	382.3	370.2	352.7	341.0	329.2	301.0	270.3	238.8	211.0	188.1	170.3
132.5°	365.9	353.8	336.7	325.8	314.9	289.5	261.7	234.5	210.6	191.0	174.9
135°	348.1	336.3	320.9	311.0	301.0	277.4	253.8	230.6	210.3	193.1	178.9
137.5°	329.9	319.5	304.9	296.0	287.0	267.8	247.4	227.8	210.3	195.3	182.1
140°	311.3	302.0	290.6	282.8	274.9	258.5	241.3	225.3	209.9	196.7	184.6
142.5°	295.2	287.0	276.3	270.0	263.8	250.3	236.3	222.8	209.9	197.8	186.7
145°	279.5	273.5	264.9	259.7	254.5	243.5	231.7	220.6	209.2	198.5	188.5
147.5°	267.0	262.0	254.5	250.6	246.7	237.8	228.1	218.5	208.1	198.8	189.6
150°	255.6	251.3	246.0	242.8	239.5	232.1	224.2	215.6	207.1	198.5	190.3
152.5°	246.3	242.8	238.8	236.2	233.5	227.4	220.3	213.1	205.3	197.8	190.6
155°	238.1	235.6	231.7	229.8	227.8	222.4	216.7	209.9	203.1	197.1	191.0
157.5°	230.3	228.1	225.3	223.7	222.1	217.4	212.4	207.1	201.0	195.6	191.0
160°	223.1	221.3	218.8	217.6	216.3	212.4	208.5	203.8	198.8	194.6	191.0
162.5°	216.3	215.3	212.8	211.9	211.0	207.8	204.6	201.0	197.1	193.5	190.6
165°	209.9	208.5	207.1	206.4	205.6	203.1	200.6	197.8	194.6	192.1	189.9
167.5°	203.5	202.8	202.1	201.4	200.6	198.8	196.7	194.6	192.4	190.6	189.6
170°	198.5	197.4	197.1	196.8	196.4	194.9	193.9	192.1	190.6	189.6	188.9
172.5°	193.5	193.1	192.8	192.6	192.4	191.4	190.6	189.6	188.5	188.1	187.8
175°	189.9	189.6	189.6	189.4	189.2	188.9	188.5	187.4	187.1	186.7	187.1
177.5°	187.1	187.1	187.1	187.1	187.1	186.7	186.7	186.0	185.6	186.0	186.7
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1097.6	1093.8	1093.8	1091.6	1091.6	1079.6	1079.6	1083.4	1078.9	1073.7	1066.2
5°	1126.0	1117.7	1115.5	1112.5	1102.8	1087.9	1081.9	1079.6	1070.7	1059.5	1046.8
7.5°	1152.9	1139.4	1132.7	1126.0	1113.3	1092.3	1080.4	1072.2	1058.7	1041.5	1025.1
10°	1179.0	1161.8	1144.6	1136.4	1118.5	1092.3	1075.2	1061.7	1042.3	1019.1	996.0
12.5°	1202.9	1167.1	1164.1	1147.6	1121.5	1091.6	1065.4	1046.0	1021.4	994.5	967.6
15°	1223.8	1187.2	1169.3	1154.4	1120.0	1082.6	1055.0	1031.1	998.2	967.6	934.7
17.5°	1234.3	1194.7	1182.7	1158.1	1123.0	1074.4	1037.0	1007.9	972.0	935.4	898.1
20°	1244.8	1198.4	1179.0	1161.8	1114.0	1058.7	1016.9	983.3	943.7	900.3	859.2
22.5°	1250.0	1198.4	1175.3	1151.4	1105.0	1041.5	992.2	952.6	906.3	862.2	812.9
25°	1241.0	1194.0	1166.3	1141.7	1089.4	1020.6	963.8	919.0	869.7	819.6	769.6
27.5°	1218.6	1183.5	1151.4	1126.0	1067.7	993.7	933.9	883.1	832.3	776.3	725.5
30°	1176.8	1161.1	1135.7	1107.3	1043.8	969.8	898.8	846.5	790.5	734.5	681.4
32.5°	1111.8	1125.2	1108.8	1084.1	1015.4	936.9	861.5	808.4	747.2	686.6	638.1
35°	1032.6	1080.4	1071.4	1054.2	985.5	901.8	826.4	762.1	700.8	639.6	591.0
37.5°	945.9	1018.4	1025.8	1015.4	951.1	866.0	783.0	720.3	657.5	595.5	546.2
40°	827.1	938.4	962.3	966.8	915.3	822.6	735.9	674.7	612.7	552.1	492.4
42.5°	718.0	858.5	888.4	907.0	869.7	780.0	692.6	624.6	563.4	508.8	449.0
45°	615.7	762.1	810.7	834.6	818.1	731.5	641.1	577.5	521.5	471.5	413.9
47.5°	510.3	657.5	725.5	763.6	763.6	682.2	591.7	529.0	475.2	432.6	381.8
50°	440.1	562.6	632.8	682.9	696.3	632.1	546.9	485.6	434.8	388.5	349.7
52.5°	375.1	484.9	543.2	595.5	634.3	578.3	496.9	441.6	391.5	348.2	317.5
55°	324.3	406.5	459.5	517.0	560.4	523.8	448.3	394.5	351.2	315.3	289.1
57.5°	275.7	347.4	390.8	441.6	487.9	460.2	399.7	353.4	315.3	283.9	260.8
60°	234.6	292.9	326.5	366.1	423.6	404.2	354.2	311.6	280.9	252.5	233.1
62.5°	199.5	245.8	274.2	302.6	354.9	345.9	307.1	274.2	248.1	224.1	207.7
65°	163.6	201.7	224.1	248.8	290.6	294.4	263.0	239.8	215.9	195.0	180.1
67.5°	132.2	162.1	182.3	203.2	236.8	247.3	225.6	206.2	186.0	168.9	155.4
70°	106.8	127.8	142.7	159.1	186.8	199.5	188.3	174.8	158.4	144.2	132.2
72.5°	84.4	97.9	106.8	119.5	142.0	154.7	153.9	142.0	130.0	120.3	110.6
75°	62.0	72.5	79.9	88.2	106.1	118.1	121.0	115.8	103.9	96.4	88.9
77.5°	47.1	53.0	56.8	62.8	75.5	85.9	90.4	88.9	80.7	74.7	69.5
80°	35.9	37.4	38.9	41.1	51.6	61.3	64.3	63.5	59.0	56.8	50.8
82.5°	25.4	26.2	26.9	27.6	31.4	39.6	42.6	44.1	40.3	38.1	32.9
85°	14.9	15.7	15.7	17.2	17.9	20.2	25.4	25.4	24.7	21.7	20.9
87.5°	7.5	7.5	6.7	6.7	7.5	8.2	9.7	11.2	9.7	9.0	8.2
90°	7.1	5.4	4.8	4.3	3.6	2.9	1.4	0.4	1.4	2.9	3.6
92.5°	28.6	18.9	17.0	15.0	12.1	10.4	7.5	5.4	7.5	10.4	12.1
95°	51.4	35.0	30.7	26.4	20.7	17.5	13.9	12.5	13.9	17.5	20.7
97.5°	66.4	45.3	40.5	35.7	29.3	24.6	20.7	18.6	20.7	24.6	29.3
100°	73.5	54.6	49.6	44.6	37.5	31.8	28.6	27.5	28.6	31.8	37.5
102.5°	80.0	62.8	57.8	52.8	45.3	39.6	36.4	35.7	36.4	39.6	45.3
105°	87.5	70.7	65.7	60.7	52.8	47.5	45.0	43.6	45.0	47.5	52.8
107.5°	95.0	78.5	73.5	68.5	60.7	55.7	53.2	52.1	53.2	55.7	60.7
110°	102.5	86.8	81.6	76.4	68.9	64.3	62.1	60.7	62.1	64.3	68.9

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	109.6	94.6	89.2	83.9	76.8	72.5	70.0	68.5	70.0	72.5	76.8
115°	117.1	101.7	96.9	92.1	85.0	80.7	78.5	76.8	78.5	80.7	85.0
117.5°	123.9	109.6	104.6	99.6	92.8	88.9	86.8	85.3	86.8	88.9	92.8
120°	131.0	117.1	112.1	107.1	100.0	96.7	94.6	93.2	94.6	96.7	100.0
122.5°	137.8	125.0	119.8	114.6	107.5	103.9	101.7	100.7	101.7	103.9	107.5
125°	144.6	131.7	126.7	121.7	114.6	110.3	108.2	107.1	108.2	110.3	114.6
127.5°	151.0	138.5	133.4	128.2	121.4	116.7	113.9	112.5	113.9	116.7	121.4
130°	156.7	144.2	139.2	134.2	127.1	122.1	118.5	117.1	118.5	122.1	127.1
132.5°	161.7	149.9	144.9	139.9	132.4	127.1	123.2	121.4	123.2	127.1	132.4
135°	166.4	154.9	149.9	144.9	136.7	131.4	127.1	125.7	127.1	131.4	136.7
137.5°	170.3	158.9	154.2	149.6	141.4	135.7	131.4	129.6	131.4	135.7	141.4
140°	173.5	162.8	158.2	153.5	145.7	139.9	135.7	134.2	135.7	139.9	145.7
142.5°	176.0	165.6	161.4	157.1	149.6	143.9	139.9	138.9	139.9	143.9	149.6
145°	178.5	168.9	165.0	161.0	153.9	148.5	144.9	143.5	144.9	148.5	153.9
147.5°	180.6	171.4	167.8	164.2	158.2	153.2	149.6	148.5	149.6	153.2	158.2
150°	182.1	173.9	170.6	167.4	162.1	157.4	154.6	153.5	154.6	157.4	162.1
152.5°	183.5	176.4	173.5	170.6	165.6	161.7	158.9	158.5	158.9	161.7	165.6
155°	184.9	178.9	176.2	173.5	169.6	165.6	163.5	163.1	163.5	165.6	169.6
157.5°	186.0	180.6	178.3	176.0	172.8	169.2	167.4	167.1	167.4	169.2	172.8
160°	186.7	182.4	180.4	178.5	175.6	172.8	171.4	171.0	171.4	172.8	175.6
162.5°	187.1	183.5	182.0	180.6	178.1	176.0	174.6	174.9	174.6	176.0	178.1
165°	187.4	184.2	183.1	182.1	180.3	178.1	177.4	177.8	177.4	178.1	180.3
167.5°	187.4	184.9	184.2	183.5	182.1	180.6	179.9	180.3	179.9	180.6	182.1
170°	187.1	185.3	184.8	184.2	183.5	182.4	182.1	182.8	182.1	182.4	183.5
172.5°	186.7	185.6	185.2	184.9	184.6	183.5	183.9	184.2	183.9	183.5	184.6
175°	186.4	185.6	185.4	185.3	185.3	184.6	184.9	185.3	184.9	184.6	185.3
177.5°	186.0	185.6	185.6	185.6	185.6	184.9	185.3	186.0	185.3	184.9	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1063.2	1063.9	1066.2	1059.5	1049.0	1044.5	1031.1	1028.8	1026.6	1026.6	1028.8
5°	1039.3	1036.3	1037.0	1024.3	1009.4	1000.4	981.8	984.7	975.0	969.1	970.6
7.5°	1013.1	1004.9	1004.2	987.7	969.1	952.6	933.2	928.7	919.7	909.3	904.8
10°	980.3	974.3	963.1	944.4	920.5	907.0	880.9	865.2	863.0	847.3	841.3
12.5°	946.6	936.2	925.0	898.8	871.9	850.3	830.8	813.7	801.7	788.2	779.3
15°	907.8	895.1	882.4	854.7	823.4	801.7	772.6	747.2	712.0	684.4	668.7
17.5°	865.2	851.0	833.8	803.2	772.6	742.7	688.9	659.0	634.3	617.9	608.2
20°	821.1	805.4	788.2	757.6	704.6	652.3	622.4	599.2	584.3	567.8	555.9
22.5°	774.8	758.4	739.7	691.9	635.8	599.2	576.1	554.4	532.7	523.8	517.8
25°	731.5	716.5	692.6	627.6	583.5	549.9	523.8	509.6	498.4	486.4	475.2
27.5°	686.6	659.0	625.4	570.8	543.2	508.8	490.1	479.7	460.2	452.0	446.8
30°	632.8	602.2	570.1	531.2	499.1	475.2	458.0	440.8	429.6	421.4	412.4
32.5°	578.3	549.2	529.0	488.6	464.7	440.1	423.6	413.2	396.7	391.5	387.8
35°	531.2	506.6	488.6	455.8	433.3	410.9	399.0	383.3	372.8	363.1	357.1
37.5°	484.9	471.5	452.8	425.1	401.2	383.3	366.9	361.6	347.4	342.2	336.2
40°	452.8	432.6	416.9	393.0	372.8	353.4	342.9	331.0	321.3	313.1	310.8
42.5°	413.9	399.0	390.0	363.9	342.9	331.7	319.0	305.6	298.1	291.4	283.2
45°	384.8	371.3	358.6	337.7	319.0	304.8	293.6	284.7	272.0	269.0	256.3
47.5°	354.2	340.7	331.0	310.1	292.9	279.4	271.2	259.3	248.8	242.1	236.1
50°	323.5	312.3	303.3	285.4	270.5	256.3	245.1	233.1	228.6	217.4	213.7
52.5°	294.4	286.9	277.2	260.0	245.1	233.1	221.2	211.4	204.7	198.7	194.3
55°	269.7	257.8	253.3	234.6	221.9	209.2	198.7	192.8	184.5	180.8	177.1
57.5°	242.1	235.4	227.9	213.7	199.5	187.5	180.1	171.1	166.6	162.1	159.1
60°	218.2	208.5	202.5	190.5	177.8	166.6	159.9	153.2	147.2	143.5	137.5
62.5°	190.5	183.1	179.3	166.6	156.2	145.7	139.7	133.0	128.5	121.8	114.3
65°	166.6	160.6	156.2	145.7	136.0	126.3	120.3	112.1	106.1	102.4	101.6
67.5°	145.7	141.2	134.5	124.8	115.1	107.6	100.9	94.1	93.4	91.9	91.9
70°	122.5	118.1	114.3	103.9	95.6	87.4	85.9	83.7	81.4	80.7	79.2
72.5°	102.4	98.6	94.1	85.2	77.0	74.7	73.2	71.7	69.5	68.7	68.0
75°	82.9	77.7	74.7	66.5	64.3	62.8	61.3	59.0	57.5	56.8	55.3
77.5°	63.5	58.3	58.3	53.8	52.3	50.1	48.6	47.1	46.3	44.8	44.8
80°	44.8	44.8	43.3	41.1	38.9	38.1	35.9	35.1	34.4	35.1	33.6
82.5°	32.9	29.9	29.9	28.4	26.9	26.2	24.7	24.7	23.9	23.9	23.9
85°	18.7	18.7	17.9	16.4	15.7	15.7	14.9	14.9	14.2	14.2	13.4
87.5°	7.5	6.7	7.5	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	4.3	4.8	5.4	7.1	9.6	11.8	12.1	11.8	11.4	10.7	11.4
92.5°	15.0	17.0	18.9	28.6	42.1	54.3	55.0	46.1	36.1	30.7	26.8
95°	26.4	30.7	35.0	51.4	82.5	123.9	139.9	122.5	93.5	71.8	56.8
97.5°	35.7	40.5	45.3	66.4	109.6	176.4	228.1	229.9	191.4	152.8	116.7
100°	44.6	49.6	54.6	73.5	117.1	194.2	282.0	333.4	325.9	281.7	232.8
102.5°	52.8	57.8	62.8	80.0	117.5	187.4	283.8	372.0	414.1	412.7	380.2
105°	60.7	65.7	70.7	87.5	119.2	178.1	264.5	359.5	433.8	474.1	478.7
107.5°	68.5	73.5	78.5	95.0	123.2	173.1	246.7	333.1	412.7	472.7	507.7
110°	76.4	81.6	86.8	102.5	128.2	171.7	234.5	308.4	383.8	447.7	493.4

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.9	89.2	94.6	109.6	133.5	172.1	226.7	291.3	357.4	418.0	467.7
115°	92.1	96.9	101.7	117.1	138.9	173.5	221.3	277.7	336.7	391.6	438.4
117.5°	99.6	104.6	109.6	123.9	144.6	175.6	218.5	268.5	319.5	368.8	412.3
120°	107.1	112.1	117.1	131.0	150.3	177.8	216.0	261.3	307.4	351.6	389.5
122.5°	114.6	119.8	125.0	137.8	155.3	180.3	214.6	255.3	297.7	337.4	372.7
125°	121.7	126.7	131.7	144.6	160.7	182.8	212.8	249.5	288.5	325.2	356.6
127.5°	128.2	133.4	138.5	151.0	165.6	185.3	211.7	244.2	279.2	313.1	343.1
130°	134.2	139.2	144.2	156.7	170.3	188.1	211.0	238.8	270.3	301.0	329.2
132.5°	139.9	144.9	149.9	161.7	174.9	191.0	210.6	234.5	261.7	289.5	314.9
135°	144.9	149.9	154.9	166.4	178.9	193.1	210.3	230.6	253.8	277.4	301.0
137.5°	149.6	154.2	158.9	170.3	182.1	195.3	210.3	227.8	247.4	267.8	287.0
140°	153.5	158.2	162.8	173.5	184.6	196.7	209.9	225.3	241.3	258.5	274.9
142.5°	157.1	161.4	165.6	176.0	186.7	197.8	209.9	222.8	236.3	250.3	263.8
145°	161.0	165.0	168.9	178.5	188.5	198.5	209.2	220.6	231.7	243.5	254.5
147.5°	164.2	167.8	171.4	180.6	189.6	198.8	208.1	218.5	228.1	237.8	246.7
150°	167.4	170.6	173.9	182.1	190.3	198.5	207.1	215.6	224.2	232.1	239.5
152.5°	170.6	173.5	176.4	183.5	190.6	197.8	205.3	213.1	220.3	227.4	233.5
155°	173.5	176.2	178.9	184.9	191.0	197.1	203.1	209.9	216.7	222.4	227.8
157.5°	176.0	178.3	180.6	186.0	191.0	195.6	201.0	207.1	212.4	217.4	222.1
160°	178.5	180.4	182.4	186.7	191.0	194.6	198.8	203.8	208.5	212.4	216.3
162.5°	180.6	182.0	183.5	187.1	190.6	193.5	197.1	201.0	204.6	207.8	211.0
165°	182.1	183.1	184.2	187.4	189.9	192.1	194.6	197.8	200.6	203.1	205.6
167.5°	183.5	184.2	184.9	187.4	189.6	190.6	192.4	194.6	196.7	198.8	200.6
170°	184.2	184.8	185.3	187.1	188.9	189.6	190.6	192.1	193.9	194.9	196.4
172.5°	184.9	185.2	185.6	186.7	187.8	188.1	188.5	189.6	190.6	191.4	192.4
175°	185.3	185.4	185.6	186.4	187.1	186.7	187.1	187.4	188.5	188.9	189.2
177.5°	185.6	185.6	185.6	186.0	186.7	186.0	185.6	186.0	186.7	186.7	187.1
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1028.8	1027.3	1022.9	1024.3	1022.1	1022.1	1020.6	1020.6	1020.6	1024.3	1022.1
5°	972.8	967.6	962.3	960.1	957.9	955.6	955.6	954.9	961.6	960.1	966.1
7.5°	903.3	901.8	891.4	891.4	887.6	886.1	889.9	890.6	891.4	892.8	896.6
10°	841.3	837.6	822.6	824.1	821.9	818.9	821.1	819.6	824.9	826.4	824.9
12.5°	768.1	761.3	744.9	736.7	727.7	721.0	729.2	723.2	744.2	750.1	766.6
15°	670.9	658.2	647.0	647.0	638.8	632.8	636.6	643.3	647.8	654.5	657.5
17.5°	605.9	600.7	591.7	586.5	584.3	582.0	582.0	585.0	594.7	594.0	600.0
20°	550.7	547.7	543.2	536.5	534.2	532.7	532.7	532.7	539.4	545.4	549.2
22.5°	512.5	510.3	507.3	498.4	493.9	492.4	496.1	498.4	503.6	508.1	511.8
25°	474.4	469.2	464.0	461.0	458.8	458.8	460.2	461.0	463.2	465.5	470.0
27.5°	443.1	439.3	431.9	423.6	423.6	421.4	422.9	424.4	429.6	437.1	440.8
30°	407.9	407.2	404.2	401.2	398.2	396.7	399.7	402.0	402.7	406.5	406.5
32.5°	382.5	377.3	372.1	369.1	367.6	366.9	367.6	370.6	370.6	375.1	380.3
35°	357.1	354.2	348.9	343.7	342.2	338.5	341.4	344.4	349.7	351.9	354.2
37.5°	329.5	325.8	323.5	322.0	319.0	319.8	317.5	322.0	326.5	325.8	327.3
40°	308.6	301.9	295.1	294.4	293.6	292.9	292.9	293.6	296.6	299.6	304.1
42.5°	281.7	279.4	273.5	267.5	266.0	264.5	263.0	266.0	272.0	277.2	279.4
45°	254.0	251.0	249.5	245.1	242.1	241.3	239.8	243.6	248.8	251.0	252.5
47.5°	228.6	227.9	223.4	224.1	221.9	222.7	221.9	224.1	224.1	226.4	227.9
50°	211.4	209.2	207.0	205.5	203.2	203.2	202.5	203.2	206.2	209.2	208.5
52.5°	194.3	190.5	189.8	189.0	187.5	189.0	186.8	187.5	190.5	192.0	191.3
55°	174.1	173.3	171.8	170.4	169.6	168.9	168.9	168.9	171.8	174.1	174.8
57.5°	158.4	154.7	151.7	151.7	148.7	147.9	149.4	150.2	152.4	153.9	155.4
60°	136.7	135.2	130.8	128.5	124.0	123.3	123.3	126.3	130.0	135.2	136.7
62.5°	113.6	111.3	110.6	110.6	110.6	110.6	110.6	110.6	110.6	111.3	111.3
65°	100.9	101.6	100.9	100.1	100.9	100.9	100.1	100.1	100.1	100.9	101.6
67.5°	90.4	89.7	90.4	89.7	88.9	88.9	88.2	88.9	89.7	90.4	90.4
70°	78.5	78.5	77.7	78.5	77.7	77.0	76.2	76.2	77.7	78.5	78.5
72.5°	67.2	67.2	66.5	66.5	65.0	65.0	65.7	65.0	65.0	67.2	67.2
75°	56.0	55.3	54.5	54.5	53.8	53.8	53.8	53.0	54.5	54.5	55.3
77.5°	44.1	44.1	44.1	43.3	43.3	42.6	42.6	43.3	43.3	43.3	44.1
80°	33.6	33.6	33.6	32.9	32.1	32.1	32.1	32.1	32.1	32.9	32.1
82.5°	23.2	23.2	23.2	23.2	23.2	22.4	22.4	22.4	23.2	23.2	22.4
85°	14.2	13.4	14.2	14.2	13.4	14.2	13.4	13.4	12.7	12.7	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	11.6	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.6
92.5°	25.4	23.9	23.6	22.1	22.5	21.8	22.5	22.1	23.6	23.9	25.4
95°	52.8	48.9	44.3	41.4	40.3	40.7	40.3	41.4	44.3	48.9	52.8
97.5°	106.0	95.3	81.4	74.3	70.3	68.2	70.3	74.3	81.4	95.3	106.0
100°	211.2	189.6	159.9	144.6	134.2	127.8	134.2	144.6	159.9	189.6	211.2
102.5°	357.0	333.8	301.0	272.0	258.5	249.2	258.5	272.0	301.0	333.8	357.0
105°	472.8	467.0	444.8	422.7	407.3	402.3	407.3	422.7	444.8	467.0	472.8
107.5°	514.8	521.9	521.6	518.4	513.7	505.5	513.7	518.4	521.6	521.9	514.8
110°	508.0	522.7	538.0	544.8	548.0	547.6	548.0	544.8	538.0	522.7	508.0

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	485.0	502.3	525.1	537.6	544.4	546.9	544.4	537.6	525.1	502.3	485.0
115°	456.8	475.2	500.5	516.9	526.2	529.4	526.2	516.9	500.5	475.2	456.8
117.5°	429.8	447.3	473.4	490.9	500.5	503.0	500.5	490.9	473.4	447.3	429.8
120°	405.8	422.0	447.0	463.7	474.1	477.7	474.1	463.7	447.0	422.0	405.8
122.5°	387.0	401.3	423.0	439.5	448.4	451.2	448.4	439.5	423.0	401.3	387.0
125°	370.0	383.4	404.1	417.7	426.6	429.5	426.6	417.7	404.1	383.4	370.0
127.5°	355.6	368.1	386.3	399.1	407.0	409.1	407.0	399.1	386.3	368.1	355.6
130°	341.0	352.7	370.2	382.3	389.5	392.3	389.5	382.3	370.2	352.7	341.0
132.5°	325.8	336.7	353.8	365.9	372.4	374.9	372.4	365.9	353.8	336.7	325.8
135°	311.0	320.9	336.3	348.1	354.5	355.9	354.5	348.1	336.3	320.9	311.0
137.5°	296.0	304.9	319.5	329.9	335.6	337.7	335.6	329.9	319.5	304.9	296.0
140°	282.8	290.6	302.0	311.3	316.7	318.8	316.7	311.3	302.0	290.6	282.8
142.5°	270.0	276.3	287.0	295.2	299.9	299.9	299.9	295.2	287.0	276.3	270.0
145°	259.7	264.9	273.5	279.5	283.1	284.2	283.1	279.5	273.5	264.9	259.7
147.5°	250.6	254.5	262.0	267.0	269.5	270.3	269.5	267.0	262.0	254.5	250.6
150°	242.8	246.0	251.3	255.6	257.8	258.1	257.8	255.6	251.3	246.0	242.8
152.5°	236.2	238.8	242.8	246.3	247.8	247.8	247.8	246.3	242.8	238.8	236.2
155°	229.8	231.7	235.6	238.1	239.5	238.8	239.5	238.1	235.6	231.7	229.8
157.5°	223.7	225.3	228.1	230.3	231.0	231.0	231.0	230.3	228.1	225.3	223.7
160°	217.6	218.8	221.3	223.1	223.5	223.5	223.5	223.1	221.3	218.8	217.6
162.5°	211.9	212.8	215.3	216.3	216.7	216.3	216.7	216.3	215.3	212.8	211.9
165°	206.4	207.1	208.5	209.9	209.9	209.6	209.9	209.9	208.5	207.1	206.4
167.5°	201.4	202.1	202.8	203.5	203.5	203.1	203.5	203.5	202.8	202.1	201.4
170°	196.8	197.1	197.4	198.5	198.1	197.4	198.1	198.5	197.4	197.1	196.8
172.5°	192.6	192.8	193.1	193.5	193.1	192.8	193.1	193.5	193.1	192.8	192.6
175°	189.4	189.6	189.6	189.9	189.6	188.9	189.6	189.9	189.6	189.6	189.4
177.5°	187.1	187.1	187.1	187.1	186.7	186.0	186.7	187.1	187.1	187.1	187.1
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1024.3	1028.1	1026.6	1018.4	1026.6	1028.8	1033.3	1037.8	1040.8	1045.3	1049.0
5°	960.1	967.6	972.0	967.6	982.5	984.7	995.2	1001.2	1010.2	1017.6	1023.6
7.5°	899.6	905.6	914.5	916.0	925.0	935.4	950.4	965.3	979.5	987.0	993.7
10°	834.6	845.0	858.5	855.5	868.9	885.4	901.1	925.0	936.9	950.4	962.3
12.5°	769.6	776.3	794.2	800.2	819.6	832.3	854.0	868.9	898.8	914.5	925.0
15°	656.0	683.6	706.1	733.0	758.4	782.3	801.7	828.6	854.7	866.7	883.9
17.5°	604.4	617.1	630.6	644.0	676.9	719.5	753.9	783.0	805.4	821.1	841.3
20°	550.7	563.4	578.3	591.0	611.2	641.8	684.4	734.5	761.3	777.8	797.2
22.5°	512.5	524.5	534.2	545.4	561.1	583.5	615.7	677.7	713.5	733.7	750.9
25°	471.5	486.4	496.9	505.1	517.8	542.4	568.6	603.7	668.0	683.6	707.6
27.5°	443.1	447.5	459.5	472.2	484.9	498.4	525.2	555.1	598.5	632.8	662.0
30°	409.4	420.6	431.9	437.1	448.3	467.7	484.2	516.3	549.9	576.8	611.9
32.5°	384.0	390.8	398.2	410.9	421.4	434.8	451.3	478.2	506.6	523.8	550.7
35°	355.6	360.1	375.8	381.0	391.5	405.0	421.4	442.3	472.9	486.4	505.8
37.5°	328.7	339.2	343.7	355.6	365.4	378.8	390.8	414.7	434.8	450.5	468.5
40°	307.8	312.3	320.5	331.0	339.2	349.7	364.6	381.8	403.5	416.2	431.9
42.5°	282.4	286.2	296.6	302.6	316.0	325.8	334.7	355.6	375.1	384.8	400.5
45°	254.8	263.7	270.5	282.4	289.9	301.9	313.1	328.0	345.9	357.1	366.1
47.5°	230.9	239.8	246.6	257.8	269.7	275.0	286.9	302.6	319.0	328.0	340.7
50°	211.4	214.4	227.1	232.4	245.1	255.5	263.7	277.2	295.1	300.4	310.8
52.5°	192.8	195.0	203.2	210.0	221.2	230.1	240.6	253.3	268.2	276.4	284.7
55°	176.3	177.8	181.6	189.0	196.5	207.7	217.4	229.4	242.1	251.0	258.5
57.5°	157.6	160.6	163.6	168.1	175.6	186.0	196.5	207.7	218.2	224.1	233.9
60°	136.0	140.5	145.7	150.9	156.2	163.6	175.6	186.0	195.8	201.0	208.5
62.5°	112.8	121.8	126.3	132.2	136.7	143.5	152.4	164.4	171.1	177.8	183.8
65°	101.6	102.4	103.1	109.1	117.3	124.0	132.2	141.2	151.7	156.2	160.6
67.5°	90.4	91.2	92.6	93.4	96.4	103.9	112.8	122.5	130.8	133.7	138.2
70°	79.2	79.2	82.2	82.9	83.7	84.4	91.9	101.6	109.1	112.8	118.1
72.5°	67.2	68.0	69.5	70.2	71.7	73.2	75.5	80.7	89.7	93.4	99.4
75°	55.3	56.0	56.8	57.5	59.8	60.5	62.8	65.7	69.5	74.0	77.7
77.5°	44.1	44.1	44.8	46.3	47.8	48.6	50.8	52.3	53.8	56.0	59.0
80°	32.9	33.6	33.6	35.1	35.1	35.9	36.6	38.9	40.3	41.8	43.3
82.5°	22.4	23.9	23.9	23.9	24.7	25.4	26.2	26.2	27.6	28.4	30.6
85°	13.4	14.2	14.2	14.2	13.4	14.9	14.9	15.7	15.7	15.7	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	11.4	10.7	11.4	11.8	12.1	11.8	9.6	7.1	5.4	4.8	4.3
92.5°	26.8	30.7	36.1	46.1	55.0	54.3	42.1	28.6	18.9	17.0	15.0
95°	56.8	71.8	93.5	122.5	139.9	123.9	82.5	51.4	35.0	30.7	26.4
97.5°	116.7	152.8	191.4	229.9	228.1	176.4	109.6	66.4	45.3	40.5	35.7
100°	232.8	281.7	325.9	333.4	282.0	194.2	117.1	73.5	54.6	49.6	44.6
102.5°	380.2	412.7	414.1	372.0	283.8	187.4	117.5	80.0	62.8	57.8	52.8
105°	478.7	474.1	433.8	359.5	264.5	178.1	119.2	87.5	70.7	65.7	60.7
107.5°	507.7	472.7	412.7	333.1	246.7	173.1	123.2	95.0	78.5	73.5	68.5
110°	493.4	447.7	383.8	308.4	234.5	171.7	128.2	102.5	86.8	81.6	76.4

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	467.7	418.0	357.4	291.3	226.7	172.1	133.5	109.6	94.6	89.2	83.9
115°	438.4	391.6	336.7	277.7	221.3	173.5	138.9	117.1	101.7	96.9	92.1
117.5°	412.3	368.8	319.5	268.5	218.5	175.6	144.6	123.9	109.6	104.6	99.6
120°	389.5	351.6	307.4	261.3	216.0	177.8	150.3	131.0	117.1	112.1	107.1
122.5°	372.7	337.4	297.7	255.3	214.6	180.3	155.3	137.8	125.0	119.8	114.6
125°	356.6	325.2	288.5	249.5	212.8	182.8	160.7	144.6	131.7	126.7	121.7
127.5°	343.1	313.1	279.2	244.2	211.7	185.3	165.6	151.0	138.5	133.4	128.2
130°	329.2	301.0	270.3	238.8	211.0	188.1	170.3	156.7	144.2	139.2	134.2
132.5°	314.9	289.5	261.7	234.5	210.6	191.0	174.9	161.7	149.9	144.9	139.9
135°	301.0	277.4	253.8	230.6	210.3	193.1	178.9	166.4	154.9	149.9	144.9
137.5°	287.0	267.8	247.4	227.8	210.3	195.3	182.1	170.3	158.9	154.2	149.6
140°	274.9	258.5	241.3	225.3	209.9	196.7	184.6	173.5	162.8	158.2	153.5
142.5°	263.8	250.3	236.3	222.8	209.9	197.8	186.7	176.0	165.6	161.4	157.1
145°	254.5	243.5	231.7	220.6	209.2	198.5	188.5	178.5	168.9	165.0	161.0
147.5°	246.7	237.8	228.1	218.5	208.1	198.8	189.6	180.6	171.4	167.8	164.2
150°	239.5	232.1	224.2	215.6	207.1	198.5	190.3	182.1	173.9	170.6	167.4
152.5°	233.5	227.4	220.3	213.1	205.3	197.8	190.6	183.5	176.4	173.5	170.6
155°	227.8	222.4	216.7	209.9	203.1	197.1	191.0	184.9	178.9	176.2	173.5
157.5°	222.1	217.4	212.4	207.1	201.0	195.6	191.0	186.0	180.6	178.3	176.0
160°	216.3	212.4	208.5	203.8	198.8	194.6	191.0	186.7	182.4	180.4	178.5
162.5°	211.0	207.8	204.6	201.0	197.1	193.5	190.6	187.1	183.5	182.0	180.6
165°	205.6	203.1	200.6	197.8	194.6	192.1	189.9	187.4	184.2	183.1	182.1
167.5°	200.6	198.8	196.7	194.6	192.4	190.6	189.6	187.4	184.9	184.2	183.5
170°	196.4	194.9	193.9	192.1	190.6	189.6	188.9	187.1	185.3	184.8	184.2
172.5°	192.4	191.4	190.6	189.6	188.5	188.1	187.8	186.7	185.6	185.2	184.9
175°	189.2	188.9	188.5	187.4	187.1	186.7	187.1	186.4	185.6	185.4	185.3
177.5°	187.1	186.7	186.7	186.0	185.6	186.0	186.7	186.0	185.6	185.6	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1075.2	1075.2	1075.2	1075.2
2.5°	1055.7	1053.5	1066.9	1081.9
5°	1034.1	1037.8	1055.0	1075.9
7.5°	1011.6	1019.9	1040.0	1067.7
10°	980.3	995.2	1025.8	1054.2
12.5°	949.6	969.8	998.9	1032.6
15°	915.3	937.7	973.5	1013.9
17.5°	877.2	902.6	944.4	988.5
20°	836.8	870.4	914.5	962.3
22.5°	792.0	832.3	877.9	931.0
25°	748.6	792.7	838.3	899.6
27.5°	706.1	749.4	800.2	862.2
30°	663.5	703.1	757.6	824.1
32.5°	617.9	659.0	716.5	784.5
35°	576.1	617.1	670.9	738.2
37.5°	531.2	575.3	626.9	696.3
40°	478.9	530.5	580.5	647.0
42.5°	435.6	490.1	538.7	601.5
45°	401.2	452.8	493.1	554.4
47.5°	369.1	410.9	452.0	508.8
50°	338.5	370.6	413.2	464.0
52.5°	307.1	334.7	371.3	419.2
55°	278.7	304.8	337.7	374.3
57.5°	252.5	271.2	304.1	337.0
60°	223.4	242.8	268.2	295.9
62.5°	198.7	213.7	237.6	260.8
65°	172.6	186.8	204.7	226.4
67.5°	148.7	161.4	175.6	192.8
70°	127.0	136.7	147.2	162.1
72.5°	103.9	114.3	124.0	136.0
75°	85.2	89.7	97.9	106.1
77.5°	65.7	71.7	76.2	82.9
80°	47.1	52.3	53.8	59.0
82.5°	31.4	34.4	37.4	38.9
85°	17.9	19.4	22.4	23.2
87.5°	6.7	7.5	9.0	10.5
90°	3.6	2.9	1.4	0.4
92.5°	12.1	10.4	7.5	5.4
95°	20.7	17.5	13.9	12.5
97.5°	29.3	24.6	20.7	18.6
100°	37.5	31.8	28.6	27.5
102.5°	45.3	39.6	36.4	35.7
105°	52.8	47.5	45.0	43.6
107.5°	60.7	55.7	53.2	52.1
110°	68.9	64.3	62.1	60.7

TEST NUMBER: P999727

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.8	72.5	70.0	68.5
115°	85.0	80.7	78.5	76.8
117.5°	92.8	88.9	86.8	85.3
120°	100.0	96.7	94.6	93.2
122.5°	107.5	103.9	101.7	100.7
125°	114.6	110.3	108.2	107.1
127.5°	121.4	116.7	113.9	112.5
130°	127.1	122.1	118.5	117.1
132.5°	132.4	127.1	123.2	121.4
135°	136.7	131.4	127.1	125.7
137.5°	141.4	135.7	131.4	129.6
140°	145.7	139.9	135.7	134.2
142.5°	149.6	143.9	139.9	138.9
145°	153.9	148.5	144.9	143.5
147.5°	158.2	153.2	149.6	148.5
150°	162.1	157.4	154.6	153.5
152.5°	165.6	161.7	158.9	158.5
155°	169.6	165.6	163.5	163.1
157.5°	172.8	169.2	167.4	167.1
160°	175.6	172.8	171.4	171.0
162.5°	178.1	176.0	174.6	174.9
165°	180.3	178.1	177.4	177.8
167.5°	182.1	180.6	179.9	180.3
170°	183.5	182.4	182.1	182.8
172.5°	184.6	183.5	183.9	184.2
175°	185.3	184.6	184.9	185.3
177.5°	185.6	184.9	185.3	186.0
180°	185.6	185.6	185.6	185.6

(END OF REPORT)