

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999733

Luminaire Tested: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999733
REPORT IS A COMBINATION OF REPORTS P988288 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3120.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	101	97	93	90	94	90	87	85	79	77	74	68	67	65	58	57	56
2	92	86	80	75	86	80	75	71	70	66	63	61	58	56	53	51	49
3	85	76	69	64	79	72	65	61	63	58	54	55	51	48	47	45	43
4	78	68	61	55	73	64	58	52	57	51	47	50	46	42	43	40	38
5	72	61	54	48	68	58	51	46	51	46	42	45	41	38	39	36	34
6	67	56	48	42	63	53	46	40	47	41	37	41	37	34	36	33	30
7	62	51	43	38	58	48	41	36	43	37	33	38	34	30	33	30	27
8	58	46	39	34	55	44	37	32	39	34	30	35	31	27	31	28	25
9	54	43	35	31	51	41	34	29	36	31	27	33	28	25	29	25	23
10	51	39	32	28	48	37	31	27	34	28	25	30	26	23	27	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16846	16846	16846	16846
5°	16884	17893	16943	14293
10°	16699	18911	16816	11803
15°	16336	18917	16612	8868
20°	15900	15637	16246	7316
25°	15372	9771	15704	6224
30°	14697	6256	15097	5358
35°	13875	4808	14325	4585
40°	12961	4041	13516	4011
45°	11984	3439	12484	3367
50°	10981	2923	11495	2911
55°	9872	2539	10405	2506
60°	8885	1937	9358	1913
65°	7967	1457	8439	1653
70°	6951	1164	7492	1348
75°	5874	892	6411	1018
80°	4663	605	5022	669
85°	3235	313	3546	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15410 cd/sqm

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	3.2
10°-20°	281.7	9.0
20°-30°	362.6	11.6
30°-40°	344.0	11.0
40°-50°	294.8	9.4
50°-60°	224.5	7.2
60°-70°	141.6	4.5
70°-80°	70.6	2.3
80°-90°	19.3	0.6
90°-100°	71.6	2.3
100°-110°	252.3	8.1
110°-120°	265.0	8.5
120°-130°	218.0	7.0
130°-140°	175.1	5.6
140°-150°	132.3	4.2
150°-160°	93.0	3.0
160°-170°	54.7	1.8
170°-180°	17.8	0.6
0°-30°	745.3	23.9
0°-40°	1089.3	34.9
0°-60°	1608.6	51.6
0°-90°	1840.2	59.0
90°-120°	588.9	18.9
90°-150°	1114.3	35.7
90°-180°	1280.0	41.0
0°-180°	3120.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1064	1064	1064	1064	1064	
5°	1065	1184	1069	946	1065	101
15°	1004	1336	1020	626	1004	282
25°	890	713	910	454	890	409
35°	731	351	754	335	731	457
45°	549	244	572	239	549	424
55°	370	169	390	167	370	334
65°	224	88	237	100	224	222
75°	105	47	115	53	105	114
85°	23	13	25	14	23	26
90°	0	12	0	12	0	2
95°	12	40	12	40	12	13
105°	43	398	43	398	43	46
115°	76	524	76	524	76	75
125°	106	425	106	425	106	94
135°	124	352	124	352	124	96
145°	142	281	142	281	142	89
155°	162	236	162	236	162	74
165°	176	208	176	208	176	50
175°	183	187	183	187	183	17
180°	184	184	184	184	184	

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1070.8	1075.3	1077.5	1080.4	1087.1	1091.5	1098.2	1099.7	1098.9	1101.9	1093.7
5°	1064.9	1074.5	1083.4	1090.8	1102.6	1110.0	1118.1	1127.8	1130.0	1141.1	1134.4
7.5°	1056.8	1070.8	1083.4	1098.2	1115.9	1125.5	1138.1	1152.9	1159.6	1172.9	1176.6
10°	1043.5	1063.4	1084.9	1100.4	1124.8	1141.8	1153.6	1177.3	1192.8	1212.8	1209.8
12.5°	1022.0	1047.9	1076.7	1102.6	1134.4	1145.5	1167.7	1192.1	1212.1	1230.6	1246.8
15°	1003.5	1033.1	1064.9	1096.7	1132.9	1153.6	1175.8	1207.6	1229.1	1261.6	1275.7
17.5°	978.4	1016.1	1053.8	1089.3	1132.2	1155.9	1183.2	1214.3	1246.1	1277.1	1288.2
20°	952.5	993.2	1033.8	1081.9	1130.7	1153.6	1181.7	1220.2	1251.3	1275.7	1275.7
22.5°	921.4	971.0	1017.6	1063.4	1116.7	1149.9	1178.8	1223.9	1246.1	1251.3	1231.3
25°	890.4	939.9	990.9	1047.9	1108.5	1138.1	1170.6	1212.8	1220.2	1199.5	1147.7
27.5°	853.4	908.9	966.5	1027.9	1091.5	1128.5	1158.1	1186.2	1172.1	1116.7	1036.1
30°	815.7	875.6	940.7	999.1	1076.0	1110.0	1135.2	1143.3	1098.9	1008.7	904.4
32.5°	776.5	834.9	903.7	973.9	1051.6	1084.1	1100.4	1078.9	997.6	883.7	756.5
35°	730.6	796.5	868.2	941.4	1018.3	1042.7	1052.3	999.8	895.6	748.4	621.9
37.5°	689.2	755.0	832.0	906.6	981.3	994.6	985.0	902.9	770.6	624.9	501.4
40°	640.4	710.7	786.1	869.7	931.0	934.7	911.1	804.6	640.4	503.6	427.4
42.5°	595.3	666.3	741.7	826.8	873.4	860.8	829.0	689.2	534.7	434.1	372.7
45°	548.7	616.0	697.4	772.8	806.1	776.5	728.4	579.8	448.9	373.5	326.1
47.5°	503.6	566.5	647.1	719.5	725.5	692.2	635.2	485.9	389.0	328.3	289.9
50°	459.2	522.1	597.5	657.4	651.5	605.7	541.3	422.3	338.0	289.9	258.1
52.5°	414.9	471.8	545.0	592.4	567.2	522.8	459.2	357.9	295.1	252.9	228.5
55°	370.5	423.7	486.6	525.8	485.9	434.8	389.7	306.9	255.9	221.9	203.4
57.5°	333.5	375.7	433.4	457.0	409.0	369.0	329.8	264.0	221.9	197.5	176.0
60°	292.8	331.3	378.6	392.7	343.1	310.6	277.3	223.3	190.1	168.6	154.6
62.5°	258.1	289.9	326.1	326.1	282.5	258.1	232.9	187.1	159.7	142.7	136.1
65°	224.1	247.0	272.9	269.9	232.9	211.5	191.5	154.6	133.9	122.0	115.4
67.5°	190.8	208.5	225.6	215.2	188.6	170.1	151.6	125.0	110.9	102.8	93.9
70°	160.5	174.5	183.4	173.8	147.2	131.6	118.3	100.6	89.5	79.1	74.0
72.5°	134.6	140.5	143.5	131.6	109.4	100.6	91.0	78.4	68.8	63.6	62.1
75°	105.0	110.2	108.0	99.1	80.6	74.0	66.6	57.7	55.5	52.5	51.0
77.5°	82.1	82.1	78.4	70.3	57.7	52.5	49.5	45.1	42.9	42.2	40.7
80°	58.4	57.7	55.5	46.6	39.2	36.2	36.2	33.3	32.5	31.1	31.1
82.5°	38.5	38.5	35.5	28.1	25.9	25.1	24.4	22.9	22.9	22.2	22.2
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.1	13.3	14.1	13.3	13.3
87.5°	10.4	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.4	1.4	2.8	3.5	4.2	4.8	5.3	7.1	9.5	11.7	12.0
92.5°	5.3	7.4	10.2	12.0	14.8	16.8	18.7	28.3	41.7	53.7	54.4
95°	12.4	13.8	17.3	20.5	26.2	30.4	34.6	50.9	81.6	122.6	138.5
97.5°	18.4	20.5	24.4	29.0	35.3	40.1	44.9	65.7	108.5	174.6	225.8
100°	27.2	28.3	31.5	37.1	44.2	49.2	54.1	72.8	115.9	192.3	279.2
102.5°	35.3	36.0	39.2	44.9	52.3	57.2	62.2	79.2	116.3	185.5	281.0
105°	43.1	44.5	47.0	52.3	60.1	65.0	70.0	86.6	118.0	176.4	261.9
107.5°	51.6	52.7	55.1	60.1	67.9	72.8	77.8	94.0	121.9	171.4	244.2
110°	60.1	61.5	63.6	68.2	75.6	80.8	85.9	101.4	126.9	170.0	232.2

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	67.9	69.3	71.7	76.0	83.1	88.4	93.7	108.5	132.2	170.3	224.4
115°	76.0	77.8	79.9	84.1	91.2	96.0	100.7	115.9	137.5	171.8	219.1
117.5°	84.5	85.9	88.0	91.9	98.6	103.6	108.5	122.6	143.1	173.9	216.3
120°	92.2	93.7	95.8	99.0	106.0	111.0	115.9	129.7	148.8	176.0	213.8
122.5°	99.7	100.7	102.8	106.4	113.4	118.6	123.7	136.4	153.7	178.5	212.4
125°	106.0	107.1	109.2	113.4	120.5	125.4	130.4	143.1	159.0	180.9	210.6
127.5°	111.3	112.7	115.6	120.2	126.9	132.0	137.1	149.5	164.0	183.4	209.6
130°	115.9	117.3	120.9	125.8	132.9	137.9	142.8	155.1	168.6	186.2	208.9
132.5°	120.2	121.9	125.8	131.1	138.5	143.4	148.4	160.1	173.2	189.1	208.5
135°	124.4	125.8	130.1	135.4	143.5	148.4	153.4	164.7	177.1	191.2	208.2
137.5°	128.3	130.1	134.3	140.0	148.1	152.7	157.3	168.6	180.2	193.3	208.2
140°	132.9	134.3	138.5	144.2	152.0	156.6	161.2	171.8	182.7	194.7	207.8
142.5°	137.5	138.5	142.4	148.1	155.5	159.8	164.0	174.2	184.8	195.8	207.8
145°	142.1	143.5	147.0	152.3	159.4	163.3	167.2	176.7	186.6	196.5	207.1
147.5°	147.0	148.1	151.6	156.6	162.6	166.1	169.6	178.8	187.7	196.9	206.0
150°	152.0	153.0	155.9	160.5	165.8	169.0	172.1	180.2	188.4	196.5	205.0
152.5°	156.9	157.3	160.1	164.0	168.9	171.8	174.6	181.7	188.7	195.8	203.2
155°	161.5	161.9	164.0	167.9	171.8	174.4	177.1	183.1	189.1	195.1	201.1
157.5°	165.4	165.8	167.5	171.1	174.2	176.5	178.8	184.1	189.1	193.7	199.0
160°	169.3	169.6	171.1	173.9	176.7	178.6	180.6	184.8	189.1	192.6	196.9
162.5°	173.2	172.8	174.2	176.4	178.8	180.2	181.7	185.2	188.7	191.6	195.1
165°	176.0	175.6	176.4	178.5	180.2	181.3	182.4	185.5	188.0	190.1	192.6
167.5°	178.5	178.1	178.8	180.2	181.7	182.4	183.1	185.5	187.7	188.7	190.5
170°	180.9	180.2	180.6	181.7	182.4	182.9	183.4	185.2	187.0	187.7	188.7
172.5°	182.4	182.0	181.7	182.7	183.1	183.4	183.8	184.8	185.9	186.2	186.6
175°	183.4	183.1	182.7	183.4	183.4	183.6	183.8	184.5	185.2	184.8	185.2
177.5°	184.1	183.4	183.1	183.8	183.8	183.8	183.8	184.1	184.8	184.1	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1101.9	1103.4	1105.6	1115.9	1117.4	1120.4	1118.9	1118.9	1119.6	1118.1	1118.9
5°	1149.2	1151.4	1162.5	1175.1	1178.0	1175.1	1178.8	1184.0	1184.0	1184.0	1182.5
7.5°	1193.6	1201.7	1214.3	1232.8	1236.5	1240.2	1246.8	1242.4	1243.9	1250.5	1248.3
10°	1236.5	1248.3	1262.3	1277.9	1286.0	1291.2	1294.1	1300.8	1316.3	1298.6	1305.2
12.5°	1277.1	1294.1	1308.9	1325.9	1331.9	1338.5	1340.7	1346.7	1346.7	1345.9	1351.1
15°	1303.8	1319.3	1332.6	1343.7	1345.2	1343.7	1342.2	1343.0	1345.2	1336.3	1341.5
17.5°	1309.7	1311.2	1315.6	1311.2	1311.9	1296.4	1287.5	1285.3	1264.6	1265.3	1282.3
20°	1280.8	1255.7	1249.0	1224.6	1209.8	1169.9	1168.4	1157.3	1113.7	1127.0	1124.1
22.5°	1201.7	1158.8	1101.9	1073.8	1059.7	1017.6	985.0	962.1	946.6	931.0	924.4
25°	1097.4	1027.9	947.3	891.9	883.7	844.5	784.6	756.5	723.2	712.9	730.6
27.5°	962.8	872.6	781.7	696.6	681.1	645.6	615.3	595.3	556.9	554.6	556.1
30°	780.2	689.2	613.1	557.6	519.1	502.9	482.9	468.1	452.6	458.5	460.0
32.5°	641.2	554.6	483.6	454.1	436.3	426.0	409.0	399.3	392.7	390.5	389.7
35°	509.5	451.8	420.0	391.2	380.8	373.5	360.9	356.4	350.5	351.3	351.3
37.5°	436.3	388.2	364.6	349.8	340.2	336.5	328.3	323.9	320.2	318.7	320.9
40°	376.4	343.1	328.3	315.0	306.9	305.4	301.0	295.8	291.4	292.1	294.3
42.5°	332.8	313.6	295.8	285.5	279.5	277.3	273.6	269.9	269.9	267.7	267.0
45°	298.0	282.5	267.7	258.1	254.4	251.4	247.0	246.3	243.3	244.0	244.8
47.5°	267.0	254.4	243.3	233.7	230.0	229.2	224.8	221.9	221.9	221.1	220.4
50°	238.9	226.3	216.7	211.5	206.3	204.8	204.1	203.4	201.9	201.9	202.6
52.5°	215.9	203.4	196.0	191.5	188.6	187.1	187.1	186.4	186.4	186.4	185.6
55°	190.8	180.4	174.5	173.0	171.6	170.8	170.1	168.6	167.9	169.3	167.9
57.5°	167.1	163.4	158.3	156.8	153.1	153.1	150.9	149.4	147.9	149.4	149.4
60°	148.6	143.5	140.5	136.1	133.1	130.2	126.5	125.7	124.2	123.5	122.8
62.5°	129.4	125.0	117.6	110.9	106.5	103.5	102.1	101.3	101.3	100.6	100.6
65°	108.0	97.6	93.9	91.7	91.0	90.2	88.7	88.0	88.7	88.0	88.7
67.5°	84.3	82.8	80.6	79.1	78.4	77.6	77.6	76.9	76.9	76.9	76.9
70°	73.2	69.5	68.8	67.3	67.3	66.6	66.6	66.6	66.6	65.8	67.3
72.5°	60.6	58.4	57.7	56.9	56.9	56.9	56.2	56.2	56.2	55.5	56.2
75°	49.5	48.8	47.3	47.3	46.6	47.3	46.6	46.6	45.8	46.6	46.6
77.5°	39.9	39.2	38.5	38.5	37.7	37.7	37.7	37.7	37.7	37.7	38.5
80°	30.3	29.6	28.8	29.6	28.8	29.6	28.8	28.8	29.6	28.8	28.8
82.5°	22.2	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.6	12.6	13.3	12.6	13.3	12.6	12.6	12.6	13.3	13.3
87.5°	5.9	6.7	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.7
90°	11.7	11.3	10.6	11.3	11.5	11.7	11.7	11.7	11.7	11.7	11.7
92.5°	45.6	35.7	30.4	26.5	25.1	23.7	23.3	21.9	22.3	21.6	22.3
95°	121.2	92.6	71.0	56.2	52.3	48.4	43.8	41.0	39.9	40.3	39.9
97.5°	227.6	189.4	151.3	115.6	105.0	94.4	80.6	73.5	69.6	67.5	69.6
100°	330.1	322.7	278.8	230.4	209.0	187.7	158.3	143.1	132.9	126.5	132.9
102.5°	368.3	410.0	408.5	376.4	353.4	330.4	297.9	269.3	255.9	246.7	255.9
105°	355.9	429.4	469.3	473.9	468.1	462.3	440.4	418.4	403.2	398.3	403.2
107.5°	329.7	408.5	467.9	502.6	509.6	516.7	516.3	513.2	508.6	500.4	508.6
110°	305.4	379.9	443.2	488.4	502.9	517.4	532.6	539.3	542.5	542.1	542.5

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.4	353.8	413.8	463.0	480.2	497.3	519.9	532.2	539.0	541.4	539.0
115°	275.0	333.3	387.7	434.0	452.2	470.4	495.5	511.7	520.9	524.1	520.9
117.5°	265.8	316.3	365.1	408.2	425.5	442.8	468.6	485.9	495.5	498.0	495.5
120°	258.7	304.3	348.1	385.6	401.6	417.7	442.5	459.1	469.3	472.9	469.3
122.5°	252.7	294.7	334.0	369.0	383.1	397.2	418.8	435.1	443.9	446.7	443.9
125°	247.0	285.6	322.0	353.1	366.4	379.6	400.1	413.5	422.3	425.2	422.3
127.5°	241.7	276.4	309.9	339.6	352.0	364.4	382.4	395.1	402.9	405.0	402.9
130°	236.4	267.5	297.9	325.8	337.5	349.2	366.5	378.5	385.6	388.4	385.6
132.5°	232.2	259.1	286.6	311.7	322.5	333.3	350.2	362.3	368.6	371.1	368.6
135°	228.3	251.3	274.6	297.9	307.8	317.7	332.9	344.6	350.9	352.4	350.9
137.5°	225.5	244.9	265.1	284.1	293.0	301.8	316.3	326.6	332.2	334.3	332.2
140°	223.0	238.9	255.9	272.1	279.9	287.7	299.0	308.2	313.5	315.6	313.5
142.5°	220.5	234.0	247.7	261.2	267.4	273.5	284.1	292.3	296.9	296.9	296.9
145°	218.4	229.4	241.0	252.0	257.1	262.2	270.7	276.7	280.3	281.3	280.3
147.5°	216.3	225.8	235.4	244.2	248.1	252.0	259.4	264.4	266.8	267.5	266.8
150°	213.5	221.9	229.7	237.1	240.3	243.5	248.8	253.0	255.2	255.5	255.2
152.5°	211.0	218.1	225.1	231.1	233.8	236.4	240.3	243.9	245.3	245.3	245.3
155°	207.8	214.5	220.2	225.5	227.4	229.4	233.3	235.7	237.1	236.4	237.1
157.5°	205.0	210.3	215.2	219.8	221.4	223.0	225.8	228.0	228.7	228.7	228.7
160°	201.8	206.4	210.3	214.2	215.4	216.6	219.1	220.9	221.2	221.2	221.2
162.5°	199.0	202.5	205.7	208.9	209.8	210.6	213.1	214.2	214.5	214.2	214.5
165°	195.8	198.6	201.1	203.6	204.3	205.0	206.4	207.8	207.8	207.5	207.8
167.5°	192.6	194.7	196.9	198.6	199.3	200.0	200.7	201.4	201.4	201.1	201.4
170°	190.1	191.9	193.0	194.4	194.8	195.1	195.4	196.5	196.1	195.4	196.1
172.5°	187.7	188.7	189.4	190.5	190.6	190.8	191.2	191.6	191.2	190.8	191.2
175°	185.5	186.6	187.0	187.3	187.5	187.7	187.7	188.0	187.7	187.0	187.7
177.5°	184.1	184.8	184.8	185.2	185.2	185.2	185.2	185.2	184.8	184.1	184.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1121.8	1116.7	1115.2	1116.7	1115.2	1115.9	1110.7	1091.5	1096.7	1088.6	1093.0
5°	1185.4	1181.0	1171.4	1169.9	1168.4	1167.0	1159.6	1142.5	1135.9	1124.8	1124.1
7.5°	1246.1	1246.1	1238.7	1233.5	1226.9	1221.7	1212.1	1186.9	1176.6	1163.3	1155.9
10°	1306.0	1286.8	1294.9	1289.7	1273.4	1270.5	1252.7	1237.9	1218.0	1204.7	1192.8
12.5°	1348.9	1343.0	1335.6	1331.1	1326.7	1317.1	1305.2	1267.5	1257.2	1230.6	1217.2
15°	1347.4	1343.7	1345.9	1345.9	1344.4	1342.2	1332.6	1305.2	1287.5	1261.6	1238.7
17.5°	1274.9	1284.5	1294.1	1300.8	1315.6	1322.2	1331.1	1314.9	1303.8	1281.6	1257.2
20°	1148.5	1172.1	1200.2	1206.1	1219.5	1258.7	1276.4	1290.5	1294.9	1287.5	1267.5
22.5°	972.5	992.4	1060.5	1059.0	1078.2	1124.8	1176.6	1218.7	1252.0	1270.5	1263.1
25°	761.7	789.8	826.0	853.4	916.3	985.8	1050.1	1117.4	1175.1	1226.1	1238.7
27.5°	576.1	613.1	641.9	678.1	709.9	792.0	874.8	979.9	1047.2	1144.0	1194.3
30°	465.9	482.9	511.7	528.8	544.3	607.1	701.1	804.6	922.9	1034.6	1121.1
32.5°	397.9	409.7	431.1	438.5	454.8	497.0	556.1	650.8	772.8	908.1	1022.0
35°	357.2	369.8	374.2	380.8	394.2	420.8	461.5	530.2	640.4	772.8	908.9
37.5°	322.4	329.1	341.7	346.1	350.5	370.5	397.9	445.9	519.1	627.8	778.7
40°	298.0	301.7	308.4	312.1	315.0	329.1	353.5	386.0	440.0	522.8	661.9
42.5°	272.1	276.6	281.0	285.5	289.1	300.2	315.0	346.1	382.3	445.2	545.8
45°	247.0	250.0	255.1	258.1	263.3	272.1	285.5	306.9	339.4	379.4	460.7
47.5°	224.1	227.8	230.0	233.7	237.4	247.0	259.6	273.6	300.2	339.4	398.6
50°	203.4	207.8	210.8	211.5	214.5	223.3	233.7	249.2	266.2	296.5	348.3
52.5°	188.6	189.3	191.5	194.5	193.8	198.9	208.5	220.4	238.1	262.5	300.2
55°	171.6	173.8	175.3	176.0	176.0	180.4	185.6	196.7	210.8	230.7	262.5
57.5°	150.1	152.3	156.8	158.3	160.5	162.7	164.9	172.3	184.1	203.4	229.2
60°	127.9	129.4	133.9	136.8	138.3	144.2	147.2	153.1	159.7	173.8	198.2
62.5°	102.8	104.3	106.5	109.4	112.4	121.3	128.7	134.6	139.8	149.4	169.3
65°	89.5	90.2	91.7	92.4	93.2	96.9	103.5	111.7	121.3	128.7	140.5
67.5°	77.6	78.4	79.1	80.6	81.3	82.1	85.0	87.3	96.9	107.2	116.1
70°	66.6	68.0	68.8	68.8	69.5	71.0	72.5	75.4	78.4	83.6	94.7
72.5°	56.2	56.9	58.4	58.4	58.4	59.9	61.4	62.9	64.3	67.3	71.7
75°	46.6	48.1	48.1	48.1	48.8	48.8	50.3	51.8	53.2	55.5	56.9
77.5°	38.5	38.5	38.5	38.5	39.2	39.2	39.9	41.4	42.2	42.9	44.4
80°	28.8	29.6	29.6	29.6	30.3	30.3	30.3	31.8	32.5	32.5	34.0
82.5°	21.4	21.4	21.4	22.2	21.4	22.2	22.2	22.9	22.2	22.9	23.7
85°	13.3	13.3	13.3	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.8
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	11.7	11.7	11.7	11.5	11.3	10.6	11.3	11.7	12.0	11.7	9.5
92.5°	21.9	23.3	23.7	25.1	26.5	30.4	35.7	45.6	54.4	53.7	41.7
95°	41.0	43.8	48.4	52.3	56.2	71.0	92.6	121.2	138.5	122.6	81.6
97.5°	73.5	80.6	94.4	105.0	115.6	151.3	189.4	227.6	225.8	174.6	108.5
100°	143.1	158.3	187.7	209.0	230.4	278.8	322.7	330.1	279.2	192.3	115.9
102.5°	269.3	297.9	330.4	353.4	376.4	408.5	410.0	368.3	281.0	185.5	116.3
105°	418.4	440.4	462.3	468.1	473.9	469.3	429.4	355.9	261.9	176.4	118.0
107.5°	513.2	516.3	516.7	509.6	502.6	467.9	408.5	329.7	244.2	171.4	121.9
110°	539.3	532.6	517.4	502.9	488.4	443.2	379.9	305.4	232.2	170.0	126.9

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	532.2	519.9	497.3	480.2	463.0	413.8	353.8	288.4	224.4	170.3	132.2
115°	511.7	495.5	470.4	452.2	434.0	387.7	333.3	275.0	219.1	171.8	137.5
117.5°	485.9	468.6	442.8	425.5	408.2	365.1	316.3	265.8	216.3	173.9	143.1
120°	459.1	442.5	417.7	401.6	385.6	348.1	304.3	258.7	213.8	176.0	148.8
122.5°	435.1	418.8	397.2	383.1	369.0	334.0	294.7	252.7	212.4	178.5	153.7
125°	413.5	400.1	379.6	366.4	353.1	322.0	285.6	247.0	210.6	180.9	159.0
127.5°	395.1	382.4	364.4	352.0	339.6	309.9	276.4	241.7	209.6	183.4	164.0
130°	378.5	366.5	349.2	337.5	325.8	297.9	267.5	236.4	208.9	186.2	168.6
132.5°	362.3	350.2	333.3	322.5	311.7	286.6	259.1	232.2	208.5	189.1	173.2
135°	344.6	332.9	317.7	307.8	297.9	274.6	251.3	228.3	208.2	191.2	177.1
137.5°	326.6	316.3	301.8	293.0	284.1	265.1	244.9	225.5	208.2	193.3	180.2
140°	308.2	299.0	287.7	279.9	272.1	255.9	238.9	223.0	207.8	194.7	182.7
142.5°	292.3	284.1	273.5	267.4	261.2	247.7	234.0	220.5	207.8	195.8	184.8
145°	276.7	270.7	262.2	257.1	252.0	241.0	229.4	218.4	207.1	196.5	186.6
147.5°	264.4	259.4	252.0	248.1	244.2	235.4	225.8	216.3	206.0	196.9	187.7
150°	253.0	248.8	243.5	240.3	237.1	229.7	221.9	213.5	205.0	196.5	188.4
152.5°	243.9	240.3	236.4	233.8	231.1	225.1	218.1	211.0	203.2	195.8	188.7
155°	235.7	233.3	229.4	227.4	225.5	220.2	214.5	207.8	201.1	195.1	189.1
157.5°	228.0	225.8	223.0	221.4	219.8	215.2	210.3	205.0	199.0	193.7	189.1
160°	220.9	219.1	216.6	215.4	214.2	210.3	206.4	201.8	196.9	192.6	189.1
162.5°	214.2	213.1	210.6	209.8	208.9	205.7	202.5	199.0	195.1	191.6	188.7
165°	207.8	206.4	205.0	204.3	203.6	201.1	198.6	195.8	192.6	190.1	188.0
167.5°	201.4	200.7	200.0	199.3	198.6	196.9	194.7	192.6	190.5	188.7	187.7
170°	196.5	195.4	195.1	194.8	194.4	193.0	191.9	190.1	188.7	187.7	187.0
172.5°	191.6	191.2	190.8	190.6	190.5	189.4	188.7	187.7	186.6	186.2	185.9
175°	188.0	187.7	187.7	187.5	187.3	187.0	186.6	185.5	185.2	184.8	185.2
177.5°	185.2	185.2	185.2	185.2	185.2	184.8	184.8	184.1	183.8	184.1	184.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1086.3	1082.6	1082.6	1080.4	1080.4	1068.6	1068.6	1072.3	1067.9	1062.7	1055.3
5°	1114.4	1106.3	1104.1	1101.1	1091.5	1076.7	1070.8	1068.6	1059.7	1048.6	1036.1
7.5°	1141.1	1127.8	1121.1	1114.4	1101.9	1081.2	1069.3	1061.2	1047.9	1030.9	1014.6
10°	1167.0	1149.9	1132.9	1124.8	1107.1	1081.2	1064.2	1050.8	1031.6	1008.7	985.8
12.5°	1190.6	1155.1	1152.2	1135.9	1110.0	1080.4	1054.5	1035.3	1010.9	984.3	957.7
15°	1211.3	1175.1	1157.3	1142.5	1108.5	1071.6	1044.2	1020.5	988.0	957.7	925.1
17.5°	1221.7	1182.5	1170.6	1146.2	1111.5	1063.4	1026.4	997.6	962.1	925.9	888.9
20°	1232.0	1186.2	1167.0	1149.9	1102.6	1047.9	1006.5	973.2	934.0	891.1	850.4
22.5°	1237.2	1186.2	1163.3	1139.6	1093.7	1030.9	982.1	942.9	897.0	853.4	804.6
25°	1228.3	1181.7	1154.4	1130.0	1078.2	1010.2	954.0	909.6	860.8	811.2	761.7
27.5°	1206.1	1171.4	1139.6	1114.4	1056.8	983.6	924.4	874.1	823.8	768.4	718.1
30°	1164.7	1149.2	1124.1	1096.0	1033.1	959.9	889.6	837.9	782.4	726.9	674.4
32.5°	1100.4	1113.7	1097.4	1073.0	1005.0	927.3	852.7	800.2	739.5	679.6	631.5
35°	1022.0	1069.3	1060.5	1043.5	975.4	892.6	817.9	754.3	693.7	633.0	585.0
37.5°	936.2	1008.0	1015.4	1005.0	941.4	857.1	775.0	712.9	650.8	589.4	540.6
40°	818.6	928.8	952.5	956.9	905.9	814.2	728.4	667.8	606.4	546.5	487.3
42.5°	710.7	849.7	879.3	897.8	860.8	772.1	685.5	618.2	557.6	503.6	444.4
45°	609.4	754.3	802.4	826.0	809.8	724.0	634.5	571.6	516.2	466.6	409.7
47.5°	505.1	650.8	718.1	755.8	755.8	675.2	585.7	523.6	470.3	428.2	377.9
50°	435.6	556.9	626.4	675.9	689.2	625.6	541.3	480.7	430.4	384.5	346.1
52.5°	371.2	479.9	537.6	589.4	627.8	572.4	491.8	437.1	387.5	344.6	314.3
55°	320.9	402.3	454.8	511.7	554.6	518.4	443.7	390.5	347.6	312.1	286.2
57.5°	272.9	343.9	386.8	437.1	482.9	455.5	395.6	349.8	312.1	281.0	258.1
60°	232.2	289.9	323.2	362.4	419.3	400.1	350.5	308.4	278.1	250.0	230.7
62.5°	197.5	243.3	271.4	299.5	351.3	342.4	303.9	271.4	245.5	221.9	205.6
65°	162.0	199.7	221.9	246.3	287.7	291.4	260.3	237.4	213.7	193.0	178.2
67.5°	130.9	160.5	180.4	201.1	234.4	244.8	223.3	204.1	184.1	167.1	153.8
70°	105.8	126.5	141.2	157.5	184.9	197.5	186.4	173.0	156.8	142.7	130.9
72.5°	83.6	96.9	105.8	118.3	140.5	153.1	152.3	140.5	128.7	119.1	109.4
75°	61.4	71.7	79.1	87.3	105.0	116.8	119.8	114.6	102.8	95.4	88.0
77.5°	46.6	52.5	56.2	62.1	74.7	85.0	89.5	88.0	79.9	74.0	68.8
80°	35.5	37.0	38.5	40.7	51.0	60.6	63.6	62.9	58.4	56.2	50.3
82.5°	25.1	25.9	26.6	27.4	31.1	39.2	42.2	43.6	39.9	37.7	32.5
85°	14.8	15.5	15.5	17.0	17.7	20.0	25.1	25.1	24.4	21.4	20.7
87.5°	7.4	7.4	6.7	6.7	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	7.1	5.3	4.8	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	28.3	18.7	16.8	14.8	12.0	10.2	7.4	5.3	7.4	10.2	12.0
95°	50.9	34.6	30.4	26.2	20.5	17.3	13.8	12.4	13.8	17.3	20.5
97.5°	65.7	44.9	40.1	35.3	29.0	24.4	20.5	18.4	20.5	24.4	29.0
100°	72.8	54.1	49.2	44.2	37.1	31.5	28.3	27.2	28.3	31.5	37.1
102.5°	79.2	62.2	57.2	52.3	44.9	39.2	36.0	35.3	36.0	39.2	44.9
105°	86.6	70.0	65.0	60.1	52.3	47.0	44.5	43.1	44.5	47.0	52.3
107.5°	94.0	77.8	72.8	67.9	60.1	55.1	52.7	51.6	52.7	55.1	60.1
110°	101.4	85.9	80.8	75.6	68.2	63.6	61.5	60.1	61.5	63.6	68.2

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	108.5	93.7	88.4	83.1	76.0	71.7	69.3	67.9	69.3	71.7	76.0
115°	115.9	100.7	96.0	91.2	84.1	79.9	77.8	76.0	77.8	79.9	84.1
117.5°	122.6	108.5	103.6	98.6	91.9	88.0	85.9	84.5	85.9	88.0	91.9
120°	129.7	115.9	111.0	106.0	99.0	95.8	93.7	92.2	93.7	95.8	99.0
122.5°	136.4	123.7	118.6	113.4	106.4	102.8	100.7	99.7	100.7	102.8	106.4
125°	143.1	130.4	125.4	120.5	113.4	109.2	107.1	106.0	107.1	109.2	113.4
127.5°	149.5	137.1	132.0	126.9	120.2	115.6	112.7	111.3	112.7	115.6	120.2
130°	155.1	142.8	137.9	132.9	125.8	120.9	117.3	115.9	117.3	120.9	125.8
132.5°	160.1	148.4	143.4	138.5	131.1	125.8	121.9	120.2	121.9	125.8	131.1
135°	164.7	153.4	148.4	143.5	135.4	130.1	125.8	124.4	125.8	130.1	135.4
137.5°	168.6	157.3	152.7	148.1	140.0	134.3	130.1	128.3	130.1	134.3	140.0
140°	171.8	161.2	156.6	152.0	144.2	138.5	134.3	132.9	134.3	138.5	144.2
142.5°	174.2	164.0	159.8	155.5	148.1	142.4	138.5	137.5	138.5	142.4	148.1
145°	176.7	167.2	163.3	159.4	152.3	147.0	143.5	142.1	143.5	147.0	152.3
147.5°	178.8	169.6	166.1	162.6	156.6	151.6	148.1	147.0	148.1	151.6	156.6
150°	180.2	172.1	169.0	165.8	160.5	155.9	153.0	152.0	153.0	155.9	160.5
152.5°	181.7	174.6	171.8	168.9	164.0	160.1	157.3	156.9	157.3	160.1	164.0
155°	183.1	177.1	174.4	171.8	167.9	164.0	161.9	161.5	161.9	164.0	167.9
157.5°	184.1	178.8	176.5	174.2	171.1	167.5	165.8	165.4	165.8	167.5	171.1
160°	184.8	180.6	178.6	176.7	173.9	171.1	169.6	169.3	169.6	171.1	173.9
162.5°	185.2	181.7	180.2	178.8	176.4	174.2	172.8	173.2	172.8	174.2	176.4
165°	185.5	182.4	181.3	180.2	178.5	176.4	175.6	176.0	175.6	176.4	178.5
167.5°	185.5	183.1	182.4	181.7	180.2	178.8	178.1	178.5	178.1	178.8	180.2
170°	185.2	183.4	182.9	182.4	181.7	180.6	180.2	180.9	180.2	180.6	181.7
172.5°	184.8	183.8	183.4	183.1	182.7	181.7	182.0	182.4	182.0	181.7	182.7
175°	184.5	183.8	183.6	183.4	183.4	182.7	183.1	183.4	183.1	182.7	183.4
177.5°	184.1	183.8	183.8	183.8	183.8	183.1	183.4	184.1	183.4	183.1	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1052.3	1053.1	1055.3	1048.6	1038.3	1033.8	1020.5	1018.3	1016.1	1016.1	1018.3
5°	1028.7	1025.7	1026.4	1013.9	999.1	990.2	971.7	974.7	965.1	959.1	960.6
7.5°	1002.8	994.6	993.9	977.6	959.1	942.9	923.7	919.2	910.3	900.0	895.6
10°	970.2	964.3	953.2	934.7	911.1	897.8	871.9	856.4	854.1	838.6	832.7
12.5°	937.0	926.6	915.5	889.6	863.0	841.6	822.3	805.3	793.5	780.2	771.3
15°	898.5	885.9	873.4	846.0	814.9	793.5	764.7	739.5	704.8	677.4	661.9
17.5°	856.4	842.3	825.3	795.0	764.7	735.1	681.8	652.3	627.8	611.6	602.0
20°	812.7	797.2	780.2	749.9	697.4	645.6	616.0	593.1	578.3	562.0	550.2
22.5°	766.9	750.6	732.1	684.8	629.3	593.1	570.2	548.7	527.3	518.4	512.5
25°	724.0	709.2	685.5	621.2	577.6	544.3	518.4	504.3	493.3	481.4	470.3
27.5°	679.6	652.3	619.0	565.0	537.6	503.6	485.1	474.8	455.5	447.4	442.2
30°	626.4	596.0	564.2	525.8	494.0	470.3	453.3	436.3	425.2	417.1	408.2
32.5°	572.4	543.5	523.6	483.6	460.0	435.6	419.3	409.0	392.7	387.5	383.8
35°	525.8	501.4	483.6	451.1	428.9	406.7	394.9	379.4	369.0	359.4	353.5
37.5°	479.9	466.6	448.1	420.8	397.1	379.4	363.1	357.9	343.9	338.7	332.8
40°	448.1	428.2	412.6	389.0	369.0	349.8	339.4	327.6	318.0	309.9	307.6
42.5°	409.7	394.9	386.0	360.1	339.4	328.3	315.8	302.5	295.1	288.4	280.3
45°	380.8	367.5	355.0	334.3	315.8	301.7	290.6	281.8	269.2	266.2	253.7
47.5°	350.5	337.2	327.6	306.9	289.9	276.6	268.4	256.6	246.3	239.6	233.7
50°	320.2	309.1	300.2	282.5	267.7	253.7	242.6	230.7	226.3	215.2	211.5
52.5°	291.4	284.0	274.4	257.4	242.6	230.7	218.9	209.3	202.6	196.7	192.3
55°	267.0	255.1	250.7	232.2	219.6	207.1	196.7	190.8	182.7	179.0	175.3
57.5°	239.6	232.9	225.6	211.5	197.5	185.6	178.2	169.3	164.9	160.5	157.5
60°	215.9	206.3	200.4	188.6	176.0	164.9	158.3	151.6	145.7	142.0	136.1
62.5°	188.6	181.2	177.5	164.9	154.6	144.2	138.3	131.6	127.2	120.5	113.1
65°	164.9	159.0	154.6	144.2	134.6	125.0	119.1	110.9	105.0	101.3	100.6
67.5°	144.2	139.8	133.1	123.5	113.9	106.5	99.8	93.2	92.4	91.0	91.0
70°	121.3	116.8	113.1	102.8	94.7	86.5	85.0	82.8	80.6	79.9	78.4
72.5°	101.3	97.6	93.2	84.3	76.2	74.0	72.5	71.0	68.8	68.0	67.3
75°	82.1	76.9	74.0	65.8	63.6	62.1	60.6	58.4	56.9	56.2	54.7
77.5°	62.9	57.7	57.7	53.2	51.8	49.5	48.1	46.6	45.8	44.4	44.4
80°	44.4	44.4	42.9	40.7	38.5	37.7	35.5	34.8	34.0	34.8	33.3
82.5°	32.5	29.6	29.6	28.1	26.6	25.9	24.4	24.4	23.7	23.7	23.7
85°	18.5	18.5	17.7	16.3	15.5	15.5	14.8	14.8	14.1	14.1	13.3
87.5°	7.4	6.7	7.4	6.7	6.7	5.9	5.9	5.9	5.2	5.9	5.2
90°	4.2	4.8	5.3	7.1	9.5	11.7	12.0	11.7	11.3	10.6	11.3
92.5°	14.8	16.8	18.7	28.3	41.7	53.7	54.4	45.6	35.7	30.4	26.5
95°	26.2	30.4	34.6	50.9	81.6	122.6	138.5	121.2	92.6	71.0	56.2
97.5°	35.3	40.1	44.9	65.7	108.5	174.6	225.8	227.6	189.4	151.3	115.6
100°	44.2	49.2	54.1	72.8	115.9	192.3	279.2	330.1	322.7	278.8	230.4
102.5°	52.3	57.2	62.2	79.2	116.3	185.5	281.0	368.3	410.0	408.5	376.4
105°	60.1	65.0	70.0	86.6	118.0	176.4	261.9	355.9	429.4	469.3	473.9
107.5°	67.9	72.8	77.8	94.0	121.9	171.4	244.2	329.7	408.5	467.9	502.6
110°	75.6	80.8	85.9	101.4	126.9	170.0	232.2	305.4	379.9	443.2	488.4

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.1	88.4	93.7	108.5	132.2	170.3	224.4	288.4	353.8	413.8	463.0
115°	91.2	96.0	100.7	115.9	137.5	171.8	219.1	275.0	333.3	387.7	434.0
117.5°	98.6	103.6	108.5	122.6	143.1	173.9	216.3	265.8	316.3	365.1	408.2
120°	106.0	111.0	115.9	129.7	148.8	176.0	213.8	258.7	304.3	348.1	385.6
122.5°	113.4	118.6	123.7	136.4	153.7	178.5	212.4	252.7	294.7	334.0	369.0
125°	120.5	125.4	130.4	143.1	159.0	180.9	210.6	247.0	285.6	322.0	353.1
127.5°	126.9	132.0	137.1	149.5	164.0	183.4	209.6	241.7	276.4	309.9	339.6
130°	132.9	137.9	142.8	155.1	168.6	186.2	208.9	236.4	267.5	297.9	325.8
132.5°	138.5	143.4	148.4	160.1	173.2	189.1	208.5	232.2	259.1	286.6	311.7
135°	143.5	148.4	153.4	164.7	177.1	191.2	208.2	228.3	251.3	274.6	297.9
137.5°	148.1	152.7	157.3	168.6	180.2	193.3	208.2	225.5	244.9	265.1	284.1
140°	152.0	156.6	161.2	171.8	182.7	194.7	207.8	223.0	238.9	255.9	272.1
142.5°	155.5	159.8	164.0	174.2	184.8	195.8	207.8	220.5	234.0	247.7	261.2
145°	159.4	163.3	167.2	176.7	186.6	196.5	207.1	218.4	229.4	241.0	252.0
147.5°	162.6	166.1	169.6	178.8	187.7	196.9	206.0	216.3	225.8	235.4	244.2
150°	165.8	169.0	172.1	180.2	188.4	196.5	205.0	213.5	221.9	229.7	237.1
152.5°	168.9	171.8	174.6	181.7	188.7	195.8	203.2	211.0	218.1	225.1	231.1
155°	171.8	174.4	177.1	183.1	189.1	195.1	201.1	207.8	214.5	220.2	225.5
157.5°	174.2	176.5	178.8	184.1	189.1	193.7	199.0	205.0	210.3	215.2	219.8
160°	176.7	178.6	180.6	184.8	189.1	192.6	196.9	201.8	206.4	210.3	214.2
162.5°	178.8	180.2	181.7	185.2	188.7	191.6	195.1	199.0	202.5	205.7	208.9
165°	180.2	181.3	182.4	185.5	188.0	190.1	192.6	195.8	198.6	201.1	203.6
167.5°	181.7	182.4	183.1	185.5	187.7	188.7	190.5	192.6	194.7	196.9	198.6
170°	182.4	182.9	183.4	185.2	187.0	187.7	188.7	190.1	191.9	193.0	194.4
172.5°	183.1	183.4	183.8	184.8	185.9	186.2	186.6	187.7	188.7	189.4	190.5
175°	183.4	183.6	183.8	184.5	185.2	184.8	185.2	185.5	186.6	187.0	187.3
177.5°	183.8	183.8	183.8	184.1	184.8	184.1	183.8	184.1	184.8	184.8	185.2
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1018.3	1016.8	1012.4	1013.9	1011.7	1011.7	1010.2	1010.2	1010.2	1013.9	1011.7
5°	962.8	957.7	952.5	950.3	948.1	945.8	945.8	945.1	951.8	950.3	956.2
7.5°	894.1	892.6	882.2	882.2	878.5	877.1	880.8	881.5	882.2	883.7	887.4
10°	832.7	829.0	814.2	815.7	813.5	810.5	812.7	811.2	816.4	817.9	816.4
12.5°	760.2	753.6	737.3	729.2	720.3	713.6	721.8	715.8	736.6	742.5	758.7
15°	664.1	651.5	640.4	640.4	632.3	626.4	630.1	636.7	641.2	647.8	650.8
17.5°	599.7	594.6	585.7	580.5	578.3	576.1	576.1	579.0	588.7	587.9	593.8
20°	545.0	542.1	537.6	531.0	528.8	527.3	527.3	527.3	533.9	539.8	543.5
22.5°	507.3	505.1	502.1	493.3	488.8	487.3	491.0	493.3	498.4	502.9	506.6
25°	469.6	464.4	459.2	456.3	454.1	454.1	455.5	456.3	458.5	460.7	465.2
27.5°	438.5	434.8	427.4	419.3	419.3	417.1	418.6	420.0	425.2	432.6	436.3
30°	403.8	403.0	400.1	397.1	394.2	392.7	395.6	397.9	398.6	402.3	402.3
32.5°	378.6	373.5	368.3	365.3	363.8	363.1	363.8	366.8	366.8	371.2	376.4
35°	353.5	350.5	345.4	340.2	338.7	335.0	338.0	340.9	346.1	348.3	350.5
37.5°	326.1	322.4	320.2	318.7	315.8	316.5	314.3	318.7	323.2	322.4	323.9
40°	305.4	298.8	292.1	291.4	290.6	289.9	289.9	290.6	293.6	296.5	301.0
42.5°	278.8	276.6	270.7	264.7	263.3	261.8	260.3	263.3	269.2	274.4	276.6
45°	251.4	248.5	247.0	242.6	239.6	238.9	237.4	241.1	246.3	248.5	250.0
47.5°	226.3	225.6	221.1	221.9	219.6	220.4	219.6	221.9	221.9	224.1	225.6
50°	209.3	207.1	204.8	203.4	201.1	201.1	200.4	201.1	204.1	207.1	206.3
52.5°	192.3	188.6	187.8	187.1	185.6	187.1	184.9	185.6	188.6	190.1	189.3
55°	172.3	171.6	170.1	168.6	167.9	167.1	167.1	167.1	170.1	172.3	173.0
57.5°	156.8	153.1	150.1	150.1	147.2	146.4	147.9	148.6	150.9	152.3	153.8
60°	135.3	133.9	129.4	127.2	122.8	122.0	122.0	125.0	128.7	133.9	135.3
62.5°	112.4	110.2	109.4	109.4	109.4	109.4	109.4	109.4	109.4	110.2	110.2
65°	99.8	100.6	99.8	99.1	99.8	99.8	99.1	99.1	99.1	99.8	100.6
67.5°	89.5	88.7	89.5	88.7	88.0	88.0	87.3	88.0	88.7	89.5	89.5
70°	77.6	77.6	76.9	77.6	76.9	76.2	75.4	75.4	76.9	77.6	77.6
72.5°	66.6	66.6	65.8	65.8	64.3	64.3	65.1	64.3	64.3	66.6	66.6
75°	55.5	54.7	54.0	54.0	53.2	53.2	53.2	52.5	54.0	54.0	54.7
77.5°	43.6	43.6	43.6	42.9	42.9	42.2	42.2	42.9	42.9	42.9	43.6
80°	33.3	33.3	33.3	32.5	31.8	31.8	31.8	31.8	31.8	32.5	31.8
82.5°	22.9	22.9	22.9	22.9	22.9	22.2	22.2	22.2	22.9	22.9	22.2
85°	14.1	13.3	14.1	14.1	13.3	14.1	13.3	13.3	12.6	12.6	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	11.5	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.5
92.5°	25.1	23.7	23.3	21.9	22.3	21.6	22.3	21.9	23.3	23.7	25.1
95°	52.3	48.4	43.8	41.0	39.9	40.3	39.9	41.0	43.8	48.4	52.3
97.5°	105.0	94.4	80.6	73.5	69.6	67.5	69.6	73.5	80.6	94.4	105.0
100°	209.0	187.7	158.3	143.1	132.9	126.5	132.9	143.1	158.3	187.7	209.0
102.5°	353.4	330.4	297.9	269.3	255.9	246.7	255.9	269.3	297.9	330.4	353.4
105°	468.1	462.3	440.4	418.4	403.2	398.3	403.2	418.4	440.4	462.3	468.1
107.5°	509.6	516.7	516.3	513.2	508.6	500.4	508.6	513.2	516.3	516.7	509.6
110°	502.9	517.4	532.6	539.3	542.5	542.1	542.5	539.3	532.6	517.4	502.9

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	480.2	497.3	519.9	532.2	539.0	541.4	539.0	532.2	519.9	497.3	480.2
115°	452.2	470.4	495.5	511.7	520.9	524.1	520.9	511.7	495.5	470.4	452.2
117.5°	425.5	442.8	468.6	485.9	495.5	498.0	495.5	485.9	468.6	442.8	425.5
120°	401.6	417.7	442.5	459.1	469.3	472.9	469.3	459.1	442.5	417.7	401.6
122.5°	383.1	397.2	418.8	435.1	443.9	446.7	443.9	435.1	418.8	397.2	383.1
125°	366.4	379.6	400.1	413.5	422.3	425.2	422.3	413.5	400.1	379.6	366.4
127.5°	352.0	364.4	382.4	395.1	402.9	405.0	402.9	395.1	382.4	364.4	352.0
130°	337.5	349.2	366.5	378.5	385.6	388.4	385.6	378.5	366.5	349.2	337.5
132.5°	322.5	333.3	350.2	362.3	368.6	371.1	368.6	362.3	350.2	333.3	322.5
135°	307.8	317.7	332.9	344.6	350.9	352.4	350.9	344.6	332.9	317.7	307.8
137.5°	293.0	301.8	316.3	326.6	332.2	334.3	332.2	326.6	316.3	301.8	293.0
140°	279.9	287.7	299.0	308.2	313.5	315.6	313.5	308.2	299.0	287.7	279.9
142.5°	267.4	273.5	284.1	292.3	296.9	296.9	296.9	292.3	284.1	273.5	267.4
145°	257.1	262.2	270.7	276.7	280.3	281.3	280.3	276.7	270.7	262.2	257.1
147.5°	248.1	252.0	259.4	264.4	266.8	267.5	266.8	264.4	259.4	252.0	248.1
150°	240.3	243.5	248.8	253.0	255.2	255.5	255.2	253.0	248.8	243.5	240.3
152.5°	233.8	236.4	240.3	243.9	245.3	245.3	245.3	243.9	240.3	236.4	233.8
155°	227.4	229.4	233.3	235.7	237.1	236.4	237.1	235.7	233.3	229.4	227.4
157.5°	221.4	223.0	225.8	228.0	228.7	228.7	228.7	228.0	225.8	223.0	221.4
160°	215.4	216.6	219.1	220.9	221.2	221.2	221.2	220.9	219.1	216.6	215.4
162.5°	209.8	210.6	213.1	214.2	214.5	214.2	214.5	214.2	213.1	210.6	209.8
165°	204.3	205.0	206.4	207.8	207.8	207.5	207.8	207.8	206.4	205.0	204.3
167.5°	199.3	200.0	200.7	201.4	201.4	201.1	201.4	201.4	200.7	200.0	199.3
170°	194.8	195.1	195.4	196.5	196.1	195.4	196.1	196.5	195.4	195.1	194.8
172.5°	190.6	190.8	191.2	191.6	191.2	190.8	191.2	191.6	191.2	190.8	190.6
175°	187.5	187.7	187.7	188.0	187.7	187.0	187.7	188.0	187.7	187.7	187.5
177.5°	185.2	185.2	185.2	185.2	184.8	184.1	184.8	185.2	185.2	185.2	185.2
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1013.9	1017.6	1016.1	1008.0	1016.1	1018.3	1022.7	1027.2	1030.1	1034.6	1038.3
5°	950.3	957.7	962.1	957.7	972.5	974.7	985.0	990.9	999.8	1007.2	1013.1
7.5°	890.4	896.3	905.2	906.6	915.5	925.9	940.7	955.5	969.5	976.9	983.6
10°	826.0	836.4	849.7	846.7	860.1	876.3	891.9	915.5	927.3	940.7	952.5
12.5°	761.7	768.4	786.1	792.0	811.2	823.8	845.3	860.1	889.6	905.2	915.5
15°	649.3	676.7	698.8	725.5	750.6	774.3	793.5	820.1	846.0	857.8	874.8
17.5°	598.3	610.8	624.1	637.5	670.0	712.2	746.2	775.0	797.2	812.7	832.7
20°	545.0	557.6	572.4	585.0	604.9	635.2	677.4	726.9	753.6	769.8	789.1
22.5°	507.3	519.1	528.8	539.8	555.4	577.6	609.4	670.7	706.2	726.2	743.2
25°	466.6	481.4	491.8	499.9	512.5	536.9	562.8	597.5	661.1	676.7	700.3
27.5°	438.5	443.0	454.8	467.4	479.9	493.3	519.9	549.5	592.4	626.4	655.2
30°	405.3	416.3	427.4	432.6	443.7	462.9	479.2	511.0	544.3	570.9	605.7
32.5°	380.1	386.8	394.2	406.7	417.1	430.4	446.7	473.3	501.4	518.4	545.0
35°	352.0	356.4	372.0	377.2	387.5	400.8	417.1	437.8	468.1	481.4	500.7
37.5°	325.4	335.7	340.2	352.0	361.6	374.9	386.8	410.4	430.4	445.9	463.7
40°	304.7	309.1	317.3	327.6	335.7	346.1	360.9	377.9	399.3	411.9	427.4
42.5°	279.5	283.2	293.6	299.5	312.8	322.4	331.3	352.0	371.2	380.8	396.4
45°	252.2	261.0	267.7	279.5	286.9	298.8	309.9	324.6	342.4	353.5	362.4
47.5°	228.5	237.4	244.0	255.1	267.0	272.1	284.0	299.5	315.8	324.6	337.2
50°	209.3	212.2	224.8	230.0	242.6	252.9	261.0	274.4	292.1	297.3	307.6
52.5°	190.8	193.0	201.1	207.8	218.9	227.8	238.1	250.7	265.5	273.6	281.8
55°	174.5	176.0	179.7	187.1	194.5	205.6	215.2	227.0	239.6	248.5	255.9
57.5°	156.0	159.0	162.0	166.4	173.8	184.1	194.5	205.6	215.9	221.9	231.5
60°	134.6	139.0	144.2	149.4	154.6	162.0	173.8	184.1	193.8	198.9	206.3
62.5°	111.7	120.5	125.0	130.9	135.3	142.0	150.9	162.7	169.3	176.0	181.9
65°	100.6	101.3	102.1	108.0	116.1	122.8	130.9	139.8	150.1	154.6	159.0
67.5°	89.5	90.2	91.7	92.4	95.4	102.8	111.7	121.3	129.4	132.4	136.8
70°	78.4	78.4	81.3	82.1	82.8	83.6	91.0	100.6	108.0	111.7	116.8
72.5°	66.6	67.3	68.8	69.5	71.0	72.5	74.7	79.9	88.7	92.4	98.4
75°	54.7	55.5	56.2	56.9	59.2	59.9	62.1	65.1	68.8	73.2	76.9
77.5°	43.6	43.6	44.4	45.8	47.3	48.1	50.3	51.8	53.2	55.5	58.4
80°	32.5	33.3	33.3	34.8	34.8	35.5	36.2	38.5	39.9	41.4	42.9
82.5°	22.2	23.7	23.7	23.7	24.4	25.1	25.9	25.9	27.4	28.1	30.3
85°	13.3	14.1	14.1	14.1	13.3	14.8	14.8	15.5	15.5	15.5	16.3
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.7	6.7
90°	11.3	10.6	11.3	11.7	12.0	11.7	9.5	7.1	5.3	4.8	4.2
92.5°	26.5	30.4	35.7	45.6	54.4	53.7	41.7	28.3	18.7	16.8	14.8
95°	56.2	71.0	92.6	121.2	138.5	122.6	81.6	50.9	34.6	30.4	26.2
97.5°	115.6	151.3	189.4	227.6	225.8	174.6	108.5	65.7	44.9	40.1	35.3
100°	230.4	278.8	322.7	330.1	279.2	192.3	115.9	72.8	54.1	49.2	44.2
102.5°	376.4	408.5	410.0	368.3	281.0	185.5	116.3	79.2	62.2	57.2	52.3
105°	473.9	469.3	429.4	355.9	261.9	176.4	118.0	86.6	70.0	65.0	60.1
107.5°	502.6	467.9	408.5	329.7	244.2	171.4	121.9	94.0	77.8	72.8	67.9
110°	488.4	443.2	379.9	305.4	232.2	170.0	126.9	101.4	85.9	80.8	75.6

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	463.0	413.8	353.8	288.4	224.4	170.3	132.2	108.5	93.7	88.4	83.1
115°	434.0	387.7	333.3	275.0	219.1	171.8	137.5	115.9	100.7	96.0	91.2
117.5°	408.2	365.1	316.3	265.8	216.3	173.9	143.1	122.6	108.5	103.6	98.6
120°	385.6	348.1	304.3	258.7	213.8	176.0	148.8	129.7	115.9	111.0	106.0
122.5°	369.0	334.0	294.7	252.7	212.4	178.5	153.7	136.4	123.7	118.6	113.4
125°	353.1	322.0	285.6	247.0	210.6	180.9	159.0	143.1	130.4	125.4	120.5
127.5°	339.6	309.9	276.4	241.7	209.6	183.4	164.0	149.5	137.1	132.0	126.9
130°	325.8	297.9	267.5	236.4	208.9	186.2	168.6	155.1	142.8	137.9	132.9
132.5°	311.7	286.6	259.1	232.2	208.5	189.1	173.2	160.1	148.4	143.4	138.5
135°	297.9	274.6	251.3	228.3	208.2	191.2	177.1	164.7	153.4	148.4	143.5
137.5°	284.1	265.1	244.9	225.5	208.2	193.3	180.2	168.6	157.3	152.7	148.1
140°	272.1	255.9	238.9	223.0	207.8	194.7	182.7	171.8	161.2	156.6	152.0
142.5°	261.2	247.7	234.0	220.5	207.8	195.8	184.8	174.2	164.0	159.8	155.5
145°	252.0	241.0	229.4	218.4	207.1	196.5	186.6	176.7	167.2	163.3	159.4
147.5°	244.2	235.4	225.8	216.3	206.0	196.9	187.7	178.8	169.6	166.1	162.6
150°	237.1	229.7	221.9	213.5	205.0	196.5	188.4	180.2	172.1	169.0	165.8
152.5°	231.1	225.1	218.1	211.0	203.2	195.8	188.7	181.7	174.6	171.8	168.9
155°	225.5	220.2	214.5	207.8	201.1	195.1	189.1	183.1	177.1	174.4	171.8
157.5°	219.8	215.2	210.3	205.0	199.0	193.7	189.1	184.1	178.8	176.5	174.2
160°	214.2	210.3	206.4	201.8	196.9	192.6	189.1	184.8	180.6	178.6	176.7
162.5°	208.9	205.7	202.5	199.0	195.1	191.6	188.7	185.2	181.7	180.2	178.8
165°	203.6	201.1	198.6	195.8	192.6	190.1	188.0	185.5	182.4	181.3	180.2
167.5°	198.6	196.9	194.7	192.6	190.5	188.7	187.7	185.5	183.1	182.4	181.7
170°	194.4	193.0	191.9	190.1	188.7	187.7	187.0	185.2	183.4	182.9	182.4
172.5°	190.5	189.4	188.7	187.7	186.6	186.2	185.9	184.8	183.8	183.4	183.1
175°	187.3	187.0	186.6	185.5	185.2	184.8	185.2	184.5	183.8	183.6	183.4
177.5°	185.2	184.8	184.8	184.1	183.8	184.1	184.8	184.1	183.8	183.8	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1064.2	1064.2	1064.2	1064.2
2.5°	1044.9	1042.7	1056.0	1070.8
5°	1023.5	1027.2	1044.2	1064.9
7.5°	1001.3	1009.4	1029.4	1056.8
10°	970.2	985.0	1015.4	1043.5
12.5°	939.9	959.9	988.7	1022.0
15°	905.9	928.1	963.6	1003.5
17.5°	868.2	893.3	934.7	978.4
20°	828.3	861.5	905.2	952.5
22.5°	783.9	823.8	868.9	921.4
25°	741.0	784.6	829.7	890.4
27.5°	698.8	741.7	792.0	853.4
30°	656.7	695.9	749.9	815.7
32.5°	611.6	652.3	709.2	776.5
35°	570.2	610.8	664.1	730.6
37.5°	525.8	569.4	620.5	689.2
40°	474.0	525.1	574.6	640.4
42.5°	431.1	485.1	533.2	595.3
45°	397.1	448.1	488.1	548.7
47.5°	365.3	406.7	447.4	503.6
50°	335.0	366.8	409.0	459.2
52.5°	303.9	331.3	367.5	414.9
55°	275.8	301.7	334.3	370.5
57.5°	250.0	268.4	301.0	333.5
60°	221.1	240.3	265.5	292.8
62.5°	196.7	211.5	235.2	258.1
65°	170.8	184.9	202.6	224.1
67.5°	147.2	159.7	173.8	190.8
70°	125.7	135.3	145.7	160.5
72.5°	102.8	113.1	122.8	134.6
75°	84.3	88.7	96.9	105.0
77.5°	65.1	71.0	75.4	82.1
80°	46.6	51.8	53.2	58.4
82.5°	31.1	34.0	37.0	38.5
85°	17.7	19.2	22.2	22.9
87.5°	6.7	7.4	8.9	10.4
90°	3.5	2.8	1.4	0.4
92.5°	12.0	10.2	7.4	5.3
95°	20.5	17.3	13.8	12.4
97.5°	29.0	24.4	20.5	18.4
100°	37.1	31.5	28.3	27.2
102.5°	44.9	39.2	36.0	35.3
105°	52.3	47.0	44.5	43.1
107.5°	60.1	55.1	52.7	51.6
110°	68.2	63.6	61.5	60.1

TEST NUMBER: P999733

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.0	71.7	69.3	67.9
115°	84.1	79.9	77.8	76.0
117.5°	91.9	88.0	85.9	84.5
120°	99.0	95.8	93.7	92.2
122.5°	106.4	102.8	100.7	99.7
125°	113.4	109.2	107.1	106.0
127.5°	120.2	115.6	112.7	111.3
130°	125.8	120.9	117.3	115.9
132.5°	131.1	125.8	121.9	120.2
135°	135.4	130.1	125.8	124.4
137.5°	140.0	134.3	130.1	128.3
140°	144.2	138.5	134.3	132.9
142.5°	148.1	142.4	138.5	137.5
145°	152.3	147.0	143.5	142.1
147.5°	156.6	151.6	148.1	147.0
150°	160.5	155.9	153.0	152.0
152.5°	164.0	160.1	157.3	156.9
155°	167.9	164.0	161.9	161.5
157.5°	171.1	167.5	165.8	165.4
160°	173.9	171.1	169.6	169.3
162.5°	176.4	174.2	172.8	173.2
165°	178.5	176.4	175.6	176.0
167.5°	180.2	178.8	178.1	178.5
170°	181.7	180.6	180.2	180.9
172.5°	182.7	181.7	182.0	182.4
175°	183.4	182.7	183.1	183.4
177.5°	183.8	183.1	183.4	184.1
180°	183.8	183.8	183.8	183.8

(END OF REPORT)