

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999773

Luminaire Tested: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999773
REPORT IS A COMBINATION OF REPORTS P988328 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3899.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	86	83	81	73	71	69	60	59	57	48	48	47
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	40
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28
6	65	53	46	40	59	50	43	38	43	37	33	36	32	29	30	27	25
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21
9	52	41	33	29	48	38	31	27	33	28	24	28	24	22	24	21	19
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16846	16846	16846	16846
5°	16884	17893	16943	14293
10°	16699	18911	16816	11803
15°	16336	18917	16612	8868
20°	15900	15637	16246	7316
25°	15372	9771	15704	6224
30°	14697	6256	15097	5358
35°	13875	4808	14325	4585
40°	12961	4041	13516	4011
45°	11984	3439	12484	3367
50°	10981	2923	11495	2911
55°	9872	2539	10405	2506
60°	8885	1937	9358	1913
65°	7967	1457	8439	1653
70°	6951	1164	7492	1348
75°	5874	892	6411	1018
80°	4663	605	5022	669
85°	3235	313	3546	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15410 cd/sqm

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	2.6
10°-20°	281.7	7.2
20°-30°	362.6	9.3
30°-40°	344.0	8.8
40°-50°	294.8	7.6
50°-60°	224.5	5.8
60°-70°	141.6	3.6
70°-80°	70.6	1.8
80°-90°	20.1	0.5
90°-100°	115.2	3.0
100°-110°	405.7	10.4
110°-120°	426.1	10.9
120°-130°	350.5	9.0
130°-140°	281.6	7.2
140°-150°	212.7	5.5
150°-160°	149.5	3.8
160°-170°	88.0	2.3
170°-180°	28.6	0.7
0°-30°	745.3	19.1
0°-40°	1089.3	27.9
0°-60°	1608.6	41.3
0°-90°	1840.9	47.2
90°-120°	947.0	24.3
90°-150°	1791.9	46.0
90°-180°	2058.0	52.8
0°-180°	3899.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1064	1064	1064	1064	1064	
5°	1065	1184	1069	946	1065	101
15°	1004	1336	1020	626	1004	282
25°	890	713	910	454	890	409
35°	731	351	754	335	731	457
45°	549	244	572	239	549	424
55°	370	169	390	167	370	334
65°	224	88	237	100	224	222
75°	105	47	115	53	105	114
85°	23	13	25	14	23	26
90°	1	19	1	19	1	3
95°	20	65	20	65	20	21
105°	69	640	69	640	69	74
115°	122	843	122	843	122	121
125°	170	684	170	684	170	152
135°	200	567	200	567	200	155
145°	228	452	228	452	228	143
155°	260	380	260	380	260	120
165°	283	334	283	334	283	80
175°	295	301	295	301	295	28
180°	296	296	296	296	296	

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1070.8	1075.3	1077.5	1080.4	1087.1	1091.5	1098.2	1099.7	1098.9	1101.9	1093.7
5°	1064.9	1074.5	1083.4	1090.8	1102.6	1110.0	1118.1	1127.8	1130.0	1141.1	1134.4
7.5°	1056.8	1070.8	1083.4	1098.2	1115.9	1125.5	1138.1	1152.9	1159.6	1172.9	1176.6
10°	1043.5	1063.4	1084.9	1100.4	1124.8	1141.8	1153.6	1177.3	1192.8	1212.8	1209.8
12.5°	1022.0	1047.9	1076.7	1102.6	1134.4	1145.5	1167.7	1192.1	1212.1	1230.6	1246.8
15°	1003.5	1033.1	1064.9	1096.7	1132.9	1153.6	1175.8	1207.6	1229.1	1261.6	1275.7
17.5°	978.4	1016.1	1053.8	1089.3	1132.2	1155.9	1183.2	1214.3	1246.1	1277.1	1288.2
20°	952.5	993.2	1033.8	1081.9	1130.7	1153.6	1181.7	1220.2	1251.3	1275.7	1275.7
22.5°	921.4	971.0	1017.6	1063.4	1116.7	1149.9	1178.8	1223.9	1246.1	1251.3	1231.3
25°	890.4	939.9	990.9	1047.9	1108.5	1138.1	1170.6	1212.8	1220.2	1199.5	1147.7
27.5°	853.4	908.9	966.5	1027.9	1091.5	1128.5	1158.1	1186.2	1172.1	1116.7	1036.1
30°	815.7	875.6	940.7	999.1	1076.0	1110.0	1135.2	1143.3	1098.9	1008.7	904.4
32.5°	776.5	834.9	903.7	973.9	1051.6	1084.1	1100.4	1078.9	997.6	883.7	756.5
35°	730.6	796.5	868.2	941.4	1018.3	1042.7	1052.3	999.8	895.6	748.4	621.9
37.5°	689.2	755.0	832.0	906.6	981.3	994.6	985.0	902.9	770.6	624.9	501.4
40°	640.4	710.7	786.1	869.7	931.0	934.7	911.1	804.6	640.4	503.6	427.4
42.5°	595.3	666.3	741.7	826.8	873.4	860.8	829.0	689.2	534.7	434.1	372.7
45°	548.7	616.0	697.4	772.8	806.1	776.5	728.4	579.8	448.9	373.5	326.1
47.5°	503.6	566.5	647.1	719.5	725.5	692.2	635.2	485.9	389.0	328.3	289.9
50°	459.2	522.1	597.5	657.4	651.5	605.7	541.3	422.3	338.0	289.9	258.1
52.5°	414.9	471.8	545.0	592.4	567.2	522.8	459.2	357.9	295.1	252.9	228.5
55°	370.5	423.7	486.6	525.8	485.9	434.8	389.7	306.9	255.9	221.9	203.4
57.5°	333.5	375.7	433.4	457.0	409.0	369.0	329.8	264.0	221.9	197.5	176.0
60°	292.8	331.3	378.6	392.7	343.1	310.6	277.3	223.3	190.1	168.6	154.6
62.5°	258.1	289.9	326.1	326.1	282.5	258.1	232.9	187.1	159.7	142.7	136.1
65°	224.1	247.0	272.9	269.9	232.9	211.5	191.5	154.6	133.9	122.0	115.4
67.5°	190.8	208.5	225.6	215.2	188.6	170.1	151.6	125.0	110.9	102.8	93.9
70°	160.5	174.5	183.4	173.8	147.2	131.6	118.3	100.6	89.5	79.1	74.0
72.5°	134.6	140.5	143.5	131.6	109.4	100.6	91.0	78.4	68.8	63.6	62.1
75°	105.0	110.2	108.0	99.1	80.6	74.0	66.6	57.7	55.5	52.5	51.0
77.5°	82.1	82.1	78.4	70.3	57.7	52.5	49.5	45.1	42.9	42.2	40.7
80°	58.4	57.7	55.5	46.6	39.2	36.2	36.2	33.3	32.5	31.1	31.1
82.5°	38.5	38.5	35.5	28.1	25.9	25.1	24.4	22.9	22.9	22.2	22.2
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.1	13.3	14.1	13.3	13.3
87.5°	10.4	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.6	2.3	4.5	5.7	6.8	7.6	8.5	11.4	15.3	18.8	19.3
92.5°	8.5	11.9	16.5	19.3	23.9	27.0	30.1	45.5	67.1	86.4	87.5
95°	19.9	22.2	27.8	33.0	42.1	48.9	55.7	81.8	131.3	197.2	222.8
97.5°	29.6	33.0	39.2	46.6	56.8	64.5	72.2	105.7	174.5	280.8	363.2
100°	43.8	45.5	50.6	59.7	71.0	79.0	87.0	117.1	186.4	309.2	449.0
102.5°	56.8	58.0	63.1	72.2	84.1	92.0	100.0	127.3	187.0	298.4	451.8
105°	69.3	71.6	75.6	84.1	96.6	104.6	112.5	139.2	189.8	283.6	421.1
107.5°	83.0	84.7	88.7	96.6	109.1	117.0	125.0	151.2	196.1	275.6	392.7
110°	96.6	98.9	102.3	109.7	121.6	129.8	138.1	163.1	204.0	273.4	373.4

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	109.1	111.4	115.4	122.2	133.6	142.1	150.6	174.5	212.6	273.9	360.9
115°	122.2	125.0	128.4	135.3	146.6	154.3	162.0	186.4	221.1	276.2	352.4
117.5°	135.8	138.1	141.5	147.8	158.6	166.6	174.5	197.2	230.2	279.6	347.8
120°	148.3	150.6	154.0	159.1	170.5	178.4	186.4	208.6	239.3	283.0	343.8
122.5°	160.3	162.0	165.4	171.1	182.4	190.6	198.9	219.4	247.2	287.0	341.6
125°	170.5	172.2	175.6	182.4	193.8	201.8	209.7	230.2	255.7	291.0	338.7
127.5°	179.0	181.3	185.8	193.2	204.0	212.2	220.5	240.4	263.7	295.0	337.0
130°	186.4	188.7	194.4	202.3	213.7	221.6	229.6	249.5	271.1	299.5	335.9
132.5°	193.2	196.1	202.3	210.9	222.8	230.8	238.7	257.5	278.5	304.1	335.3
135°	200.1	202.3	209.1	217.7	230.7	238.7	246.7	264.8	284.7	307.5	334.7
137.5°	206.3	209.1	216.0	225.1	238.1	245.5	252.9	271.1	289.8	310.9	334.7
140°	213.7	216.0	222.8	231.9	244.4	251.8	259.2	276.2	293.8	313.2	334.2
142.5°	221.1	222.8	229.0	238.1	250.1	256.9	263.7	280.2	297.2	314.9	334.2
145°	228.5	230.7	236.4	245.0	256.3	262.6	268.8	284.2	300.1	316.0	333.0
147.5°	236.4	238.1	243.8	251.8	261.4	267.1	272.8	287.6	301.8	316.6	331.3
150°	244.4	246.1	250.6	258.0	266.5	271.6	276.8	289.8	302.9	316.0	329.6
152.5°	252.3	252.9	257.5	263.7	271.7	276.2	280.8	292.1	303.5	314.9	326.8
155°	259.7	260.3	263.7	270.0	276.2	280.4	284.7	294.4	304.1	313.7	323.4
157.5°	266.0	266.5	269.4	275.1	280.2	283.9	287.6	296.1	304.1	311.4	320.0
160°	272.2	272.8	275.1	279.6	284.2	287.3	290.4	297.2	304.1	309.7	316.6
162.5°	278.5	277.9	280.2	283.6	287.6	289.8	292.1	297.8	303.5	308.0	313.7
165°	283.0	282.5	283.6	287.0	289.8	291.6	293.3	298.4	302.4	305.8	309.7
167.5°	287.0	286.4	287.6	289.8	292.1	293.2	294.4	298.4	301.8	303.5	306.3
170°	291.0	289.8	290.4	292.1	293.3	294.2	295.0	297.8	300.6	301.8	303.5
172.5°	293.3	292.7	292.1	293.8	294.4	295.0	295.5	297.2	298.9	299.5	300.1
175°	295.0	294.4	293.8	295.0	295.0	295.2	295.5	296.7	297.8	297.2	297.8
177.5°	296.1	295.0	294.4	295.5	295.5	295.5	295.5	296.1	297.2	296.1	295.5
180°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1101.9	1103.4	1105.6	1115.9	1117.4	1120.4	1118.9	1118.9	1119.6	1118.1	1118.9
5°	1149.2	1151.4	1162.5	1175.1	1178.0	1175.1	1178.8	1184.0	1184.0	1184.0	1182.5
7.5°	1193.6	1201.7	1214.3	1232.8	1236.5	1240.2	1246.8	1242.4	1243.9	1250.5	1248.3
10°	1236.5	1248.3	1262.3	1277.9	1286.0	1291.2	1294.1	1300.8	1316.3	1298.6	1305.2
12.5°	1277.1	1294.1	1308.9	1325.9	1331.9	1338.5	1340.7	1346.7	1346.7	1345.9	1351.1
15°	1303.8	1319.3	1332.6	1343.7	1345.2	1343.7	1342.2	1343.0	1345.2	1336.3	1341.5
17.5°	1309.7	1311.2	1315.6	1311.2	1311.9	1296.4	1287.5	1285.3	1264.6	1265.3	1282.3
20°	1280.8	1255.7	1249.0	1224.6	1209.8	1169.9	1168.4	1157.3	1113.7	1127.0	1124.1
22.5°	1201.7	1158.8	1101.9	1073.8	1059.7	1017.6	985.0	962.1	946.6	931.0	924.4
25°	1097.4	1027.9	947.3	891.9	883.7	844.5	784.6	756.5	723.2	712.9	730.6
27.5°	962.8	872.6	781.7	696.6	681.1	645.6	615.3	595.3	556.9	554.6	556.1
30°	780.2	689.2	613.1	557.6	519.1	502.9	482.9	468.1	452.6	458.5	460.0
32.5°	641.2	554.6	483.6	454.1	436.3	426.0	409.0	399.3	392.7	390.5	389.7
35°	509.5	451.8	420.0	391.2	380.8	373.5	360.9	356.4	350.5	351.3	351.3
37.5°	436.3	388.2	364.6	349.8	340.2	336.5	328.3	323.9	320.2	318.7	320.9
40°	376.4	343.1	328.3	315.0	306.9	305.4	301.0	295.8	291.4	292.1	294.3
42.5°	332.8	313.6	295.8	285.5	279.5	277.3	273.6	269.9	269.9	267.7	267.0
45°	298.0	282.5	267.7	258.1	254.4	251.4	247.0	246.3	243.3	244.0	244.8
47.5°	267.0	254.4	243.3	233.7	230.0	229.2	224.8	221.9	221.9	221.1	220.4
50°	238.9	226.3	216.7	211.5	206.3	204.8	204.1	203.4	201.9	201.9	202.6
52.5°	215.9	203.4	196.0	191.5	188.6	187.1	187.1	186.4	186.4	186.4	185.6
55°	190.8	180.4	174.5	173.0	171.6	170.8	170.1	168.6	167.9	169.3	167.9
57.5°	167.1	163.4	158.3	156.8	153.1	153.1	150.9	149.4	147.9	149.4	149.4
60°	148.6	143.5	140.5	136.1	133.1	130.2	126.5	125.7	124.2	123.5	122.8
62.5°	129.4	125.0	117.6	110.9	106.5	103.5	102.1	101.3	101.3	100.6	100.6
65°	108.0	97.6	93.9	91.7	91.0	90.2	88.7	88.0	88.7	88.0	88.7
67.5°	84.3	82.8	80.6	79.1	78.4	77.6	77.6	76.9	76.9	76.9	76.9
70°	73.2	69.5	68.8	67.3	67.3	66.6	66.6	66.6	66.6	65.8	67.3
72.5°	60.6	58.4	57.7	56.9	56.9	56.9	56.2	56.2	56.2	55.5	56.2
75°	49.5	48.8	47.3	47.3	46.6	47.3	46.6	46.6	45.8	46.6	46.6
77.5°	39.9	39.2	38.5	38.5	37.7	37.7	37.7	37.7	37.7	37.7	38.5
80°	30.3	29.6	28.8	29.6	28.8	29.6	28.8	28.8	29.6	28.8	28.8
82.5°	22.2	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.6	12.6	13.3	12.6	13.3	12.6	12.6	12.6	13.3	13.3
87.5°	5.9	6.7	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.7
90°	18.8	18.2	17.0	18.2	18.5	18.8	18.8	18.8	18.8	18.8	18.8
92.5°	73.3	57.4	48.9	42.6	40.4	38.1	37.5	35.2	35.8	34.7	35.8
95°	194.9	148.9	114.2	90.4	84.2	77.9	70.5	65.9	64.2	64.8	64.2
97.5°	366.0	304.6	243.2	185.8	168.8	151.7	129.6	118.2	112.0	108.6	112.0
100°	530.8	518.9	448.4	370.6	336.2	301.8	254.6	230.2	213.7	203.5	213.7
102.5°	592.2	659.3	657.0	605.3	568.3	531.4	479.1	433.1	411.5	396.7	411.5
105°	572.3	690.5	754.7	762.1	752.8	743.4	708.1	672.9	648.5	640.5	648.5
107.5°	530.3	657.0	752.5	808.2	819.6	830.9	830.3	825.2	817.8	804.8	817.8
110°	491.0	611.0	712.7	785.4	808.7	832.0	856.5	867.3	872.4	871.8	872.4

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	463.8	568.9	665.5	744.5	772.0	799.6	836.0	855.9	866.7	870.7	866.7
115°	442.2	535.9	623.5	697.9	727.2	756.5	796.8	822.9	837.7	842.8	837.7
117.5°	427.4	508.7	587.1	656.4	684.2	712.1	753.6	781.5	796.8	800.8	796.8
120°	416.0	489.3	559.8	620.1	646.0	671.8	711.6	738.3	754.7	760.4	754.7
122.5°	406.4	474.0	537.1	593.3	616.0	638.8	673.5	699.6	713.8	718.4	713.8
125°	397.3	459.2	517.8	567.8	589.1	610.4	643.4	664.9	679.2	683.7	679.2
127.5°	388.7	444.4	498.4	546.2	566.1	586.0	614.9	635.4	647.9	651.3	647.9
130°	380.2	430.2	479.1	524.0	542.8	561.5	589.4	608.7	620.1	624.6	620.1
132.5°	373.4	416.6	460.9	501.3	518.6	535.9	563.2	582.5	592.8	596.7	592.8
135°	367.1	404.1	441.6	479.1	495.0	510.9	535.4	554.1	564.4	566.6	564.4
137.5°	362.6	393.9	426.2	456.9	471.2	485.4	508.7	525.1	534.2	537.6	534.2
140°	358.6	384.2	411.5	437.6	450.1	462.6	480.8	495.6	504.1	507.5	504.1
142.5°	354.6	376.2	398.4	420.0	430.0	439.9	456.9	470.0	477.4	477.4	477.4
145°	351.2	368.8	387.6	405.2	413.4	421.7	435.3	445.0	450.7	452.4	450.7
147.5°	347.8	363.2	378.5	392.7	399.0	405.2	417.2	425.1	429.1	430.2	429.1
150°	343.3	356.9	369.4	381.4	386.5	391.6	400.1	406.9	410.3	410.9	410.3
152.5°	339.3	350.7	362.0	371.7	376.0	380.2	386.5	392.1	394.4	394.4	394.4
155°	334.2	345.0	354.1	362.6	365.7	368.8	375.1	379.1	381.4	380.2	381.4
157.5°	329.6	338.2	346.1	353.5	356.0	358.6	363.2	366.6	367.7	367.7	367.7
160°	324.5	331.9	338.2	344.4	346.4	348.4	352.4	355.2	355.8	355.8	355.8
162.5°	320.0	325.7	330.8	335.9	337.3	338.7	342.7	344.4	345.0	344.4	345.0
165°	314.9	319.4	323.4	327.4	328.5	329.6	331.9	334.2	334.2	333.6	334.2
167.5°	309.7	313.2	316.6	319.4	320.5	321.7	322.8	323.9	323.9	323.4	323.9
170°	305.8	308.6	310.3	312.6	313.2	313.7	314.3	316.0	315.4	314.3	315.4
172.5°	301.8	303.5	304.6	306.3	306.6	306.9	307.5	308.0	307.5	306.9	307.5
175°	298.4	300.1	300.6	301.2	301.5	301.8	301.8	302.4	301.8	300.6	301.8
177.5°	296.1	297.2	297.2	297.8	297.8	297.8	297.8	297.8	297.2	296.1	297.2
180°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1121.8	1116.7	1115.2	1116.7	1115.2	1115.9	1110.7	1091.5	1096.7	1088.6	1093.0
5°	1185.4	1181.0	1171.4	1169.9	1168.4	1167.0	1159.6	1142.5	1135.9	1124.8	1124.1
7.5°	1246.1	1246.1	1238.7	1233.5	1226.9	1221.7	1212.1	1186.9	1176.6	1163.3	1155.9
10°	1306.0	1286.8	1294.9	1289.7	1273.4	1270.5	1252.7	1237.9	1218.0	1204.7	1192.8
12.5°	1348.9	1343.0	1335.6	1331.1	1326.7	1317.1	1305.2	1267.5	1257.2	1230.6	1217.2
15°	1347.4	1343.7	1345.9	1345.9	1344.4	1342.2	1332.6	1305.2	1287.5	1261.6	1238.7
17.5°	1274.9	1284.5	1294.1	1300.8	1315.6	1322.2	1331.1	1314.9	1303.8	1281.6	1257.2
20°	1148.5	1172.1	1200.2	1206.1	1219.5	1258.7	1276.4	1290.5	1294.9	1287.5	1267.5
22.5°	972.5	992.4	1060.5	1059.0	1078.2	1124.8	1176.6	1218.7	1252.0	1270.5	1263.1
25°	761.7	789.8	826.0	853.4	916.3	985.8	1050.1	1117.4	1175.1	1226.1	1238.7
27.5°	576.1	613.1	641.9	678.1	709.9	792.0	874.8	979.9	1047.2	1144.0	1194.3
30°	465.9	482.9	511.7	528.8	544.3	607.1	701.1	804.6	922.9	1034.6	1121.1
32.5°	397.9	409.7	431.1	438.5	454.8	497.0	556.1	650.8	772.8	908.1	1022.0
35°	357.2	369.8	374.2	380.8	394.2	420.8	461.5	530.2	640.4	772.8	908.9
37.5°	322.4	329.1	341.7	346.1	350.5	370.5	397.9	445.9	519.1	627.8	778.7
40°	298.0	301.7	308.4	312.1	315.0	329.1	353.5	386.0	440.0	522.8	661.9
42.5°	272.1	276.6	281.0	285.5	289.1	300.2	315.0	346.1	382.3	445.2	545.8
45°	247.0	250.0	255.1	258.1	263.3	272.1	285.5	306.9	339.4	379.4	460.7
47.5°	224.1	227.8	230.0	233.7	237.4	247.0	259.6	273.6	300.2	339.4	398.6
50°	203.4	207.8	210.8	211.5	214.5	223.3	233.7	249.2	266.2	296.5	348.3
52.5°	188.6	189.3	191.5	194.5	193.8	198.9	208.5	220.4	238.1	262.5	300.2
55°	171.6	173.8	175.3	176.0	176.0	180.4	185.6	196.7	210.8	230.7	262.5
57.5°	150.1	152.3	156.8	158.3	160.5	162.7	164.9	172.3	184.1	203.4	229.2
60°	127.9	129.4	133.9	136.8	138.3	144.2	147.2	153.1	159.7	173.8	198.2
62.5°	102.8	104.3	106.5	109.4	112.4	121.3	128.7	134.6	139.8	149.4	169.3
65°	89.5	90.2	91.7	92.4	93.2	96.9	103.5	111.7	121.3	128.7	140.5
67.5°	77.6	78.4	79.1	80.6	81.3	82.1	85.0	87.3	96.9	107.2	116.1
70°	66.6	68.0	68.8	68.8	69.5	71.0	72.5	75.4	78.4	83.6	94.7
72.5°	56.2	56.9	58.4	58.4	58.4	59.9	61.4	62.9	64.3	67.3	71.7
75°	46.6	48.1	48.1	48.1	48.8	48.8	50.3	51.8	53.2	55.5	56.9
77.5°	38.5	38.5	38.5	38.5	39.2	39.2	39.9	41.4	42.2	42.9	44.4
80°	28.8	29.6	29.6	29.6	30.3	30.3	30.3	31.8	32.5	32.5	34.0
82.5°	21.4	21.4	21.4	22.2	21.4	22.2	22.2	22.9	22.2	22.9	23.7
85°	13.3	13.3	13.3	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.8
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	18.8	18.8	18.8	18.5	18.2	17.0	18.2	18.8	19.3	18.8	15.3
92.5°	35.2	37.5	38.1	40.4	42.6	48.9	57.4	73.3	87.5	86.4	67.1
95°	65.9	70.5	77.9	84.2	90.4	114.2	148.9	194.9	222.8	197.2	131.3
97.5°	118.2	129.6	151.7	168.8	185.8	243.2	304.6	366.0	363.2	280.8	174.5
100°	230.2	254.6	301.8	336.2	370.6	448.4	518.9	530.8	449.0	309.2	186.4
102.5°	433.1	479.1	531.4	568.3	605.3	657.0	659.3	592.2	451.8	298.4	187.0
105°	672.9	708.1	743.4	752.8	762.1	754.7	690.5	572.3	421.1	283.6	189.8
107.5°	825.2	830.3	830.9	819.6	808.2	752.5	657.0	530.3	392.7	275.6	196.1
110°	867.3	856.5	832.0	808.7	785.4	712.7	611.0	491.0	373.4	273.4	204.0

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	855.9	836.0	799.6	772.0	744.5	665.5	568.9	463.8	360.9	273.9	212.6
115°	822.9	796.8	756.5	727.2	697.9	623.5	535.9	442.2	352.4	276.2	221.1
117.5°	781.5	753.6	712.1	684.2	656.4	587.1	508.7	427.4	347.8	279.6	230.2
120°	738.3	711.6	671.8	646.0	620.1	559.8	489.3	416.0	343.8	283.0	239.3
122.5°	699.6	673.5	638.8	616.0	593.3	537.1	474.0	406.4	341.6	287.0	247.2
125°	664.9	643.4	610.4	589.1	567.8	517.8	459.2	397.3	338.7	291.0	255.7
127.5°	635.4	614.9	586.0	566.1	546.2	498.4	444.4	388.7	337.0	295.0	263.7
130°	608.7	589.4	561.5	542.8	524.0	479.1	430.2	380.2	335.9	299.5	271.1
132.5°	582.5	563.2	535.9	518.6	501.3	460.9	416.6	373.4	335.3	304.1	278.5
135°	554.1	535.4	510.9	495.0	479.1	441.6	404.1	367.1	334.7	307.5	284.7
137.5°	525.1	508.7	485.4	471.2	456.9	426.2	393.9	362.6	334.7	310.9	289.8
140°	495.6	480.8	462.6	450.1	437.6	411.5	384.2	358.6	334.2	313.2	293.8
142.5°	470.0	456.9	439.9	430.0	420.0	398.4	376.2	354.6	334.2	314.9	297.2
145°	445.0	435.3	421.7	413.4	405.2	387.6	368.8	351.2	333.0	316.0	300.1
147.5°	425.1	417.2	405.2	399.0	392.7	378.5	363.2	347.8	331.3	316.6	301.8
150°	406.9	400.1	391.6	386.5	381.4	369.4	356.9	343.3	329.6	316.0	302.9
152.5°	392.1	386.5	380.2	376.0	371.7	362.0	350.7	339.3	326.8	314.9	303.5
155°	379.1	375.1	368.8	365.7	362.6	354.1	345.0	334.2	323.4	313.7	304.1
157.5°	366.6	363.2	358.6	356.0	353.5	346.1	338.2	329.6	320.0	311.4	304.1
160°	355.2	352.4	348.4	346.4	344.4	338.2	331.9	324.5	316.6	309.7	304.1
162.5°	344.4	342.7	338.7	337.3	335.9	330.8	325.7	320.0	313.7	308.0	303.5
165°	334.2	331.9	329.6	328.5	327.4	323.4	319.4	314.9	309.7	305.8	302.4
167.5°	323.9	322.8	321.7	320.5	319.4	316.6	313.2	309.7	306.3	303.5	301.8
170°	316.0	314.3	313.7	313.2	312.6	310.3	308.6	305.8	303.5	301.8	300.6
172.5°	308.0	307.5	306.9	306.6	306.3	304.6	303.5	301.8	300.1	299.5	298.9
175°	302.4	301.8	301.8	301.5	301.2	300.6	300.1	298.4	297.8	297.2	297.8
177.5°	297.8	297.8	297.8	297.8	297.8	297.2	297.2	296.1	295.5	296.1	297.2
180°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1086.3	1082.6	1082.6	1080.4	1080.4	1068.6	1068.6	1072.3	1067.9	1062.7	1055.3
5°	1114.4	1106.3	1104.1	1101.1	1091.5	1076.7	1070.8	1068.6	1059.7	1048.6	1036.1
7.5°	1141.1	1127.8	1121.1	1114.4	1101.9	1081.2	1069.3	1061.2	1047.9	1030.9	1014.6
10°	1167.0	1149.9	1132.9	1124.8	1107.1	1081.2	1064.2	1050.8	1031.6	1008.7	985.8
12.5°	1190.6	1155.1	1152.2	1135.9	1110.0	1080.4	1054.5	1035.3	1010.9	984.3	957.7
15°	1211.3	1175.1	1157.3	1142.5	1108.5	1071.6	1044.2	1020.5	988.0	957.7	925.1
17.5°	1221.7	1182.5	1170.6	1146.2	1111.5	1063.4	1026.4	997.6	962.1	925.9	888.9
20°	1232.0	1186.2	1167.0	1149.9	1102.6	1047.9	1006.5	973.2	934.0	891.1	850.4
22.5°	1237.2	1186.2	1163.3	1139.6	1093.7	1030.9	982.1	942.9	897.0	853.4	804.6
25°	1228.3	1181.7	1154.4	1130.0	1078.2	1010.2	954.0	909.6	860.8	811.2	761.7
27.5°	1206.1	1171.4	1139.6	1114.4	1056.8	983.6	924.4	874.1	823.8	768.4	718.1
30°	1164.7	1149.2	1124.1	1096.0	1033.1	959.9	889.6	837.9	782.4	726.9	674.4
32.5°	1100.4	1113.7	1097.4	1073.0	1005.0	927.3	852.7	800.2	739.5	679.6	631.5
35°	1022.0	1069.3	1060.5	1043.5	975.4	892.6	817.9	754.3	693.7	633.0	585.0
37.5°	936.2	1008.0	1015.4	1005.0	941.4	857.1	775.0	712.9	650.8	589.4	540.6
40°	818.6	928.8	952.5	956.9	905.9	814.2	728.4	667.8	606.4	546.5	487.3
42.5°	710.7	849.7	879.3	897.8	860.8	772.1	685.5	618.2	557.6	503.6	444.4
45°	609.4	754.3	802.4	826.0	809.8	724.0	634.5	571.6	516.2	466.6	409.7
47.5°	505.1	650.8	718.1	755.8	755.8	675.2	585.7	523.6	470.3	428.2	377.9
50°	435.6	556.9	626.4	675.9	689.2	625.6	541.3	480.7	430.4	384.5	346.1
52.5°	371.2	479.9	537.6	589.4	627.8	572.4	491.8	437.1	387.5	344.6	314.3
55°	320.9	402.3	454.8	511.7	554.6	518.4	443.7	390.5	347.6	312.1	286.2
57.5°	272.9	343.9	386.8	437.1	482.9	455.5	395.6	349.8	312.1	281.0	258.1
60°	232.2	289.9	323.2	362.4	419.3	400.1	350.5	308.4	278.1	250.0	230.7
62.5°	197.5	243.3	271.4	299.5	351.3	342.4	303.9	271.4	245.5	221.9	205.6
65°	162.0	199.7	221.9	246.3	287.7	291.4	260.3	237.4	213.7	193.0	178.2
67.5°	130.9	160.5	180.4	201.1	234.4	244.8	223.3	204.1	184.1	167.1	153.8
70°	105.8	126.5	141.2	157.5	184.9	197.5	186.4	173.0	156.8	142.7	130.9
72.5°	83.6	96.9	105.8	118.3	140.5	153.1	152.3	140.5	128.7	119.1	109.4
75°	61.4	71.7	79.1	87.3	105.0	116.8	119.8	114.6	102.8	95.4	88.0
77.5°	46.6	52.5	56.2	62.1	74.7	85.0	89.5	88.0	79.9	74.0	68.8
80°	35.5	37.0	38.5	40.7	51.0	60.6	63.6	62.9	58.4	56.2	50.3
82.5°	25.1	25.9	26.6	27.4	31.1	39.2	42.2	43.6	39.9	37.7	32.5
85°	14.8	15.5	15.5	17.0	17.7	20.0	25.1	25.1	24.4	21.4	20.7
87.5°	7.4	7.4	6.7	6.7	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	11.4	8.5	7.6	6.8	5.7	4.5	2.3	0.6	2.3	4.5	5.7
92.5°	45.5	30.1	27.0	23.9	19.3	16.5	11.9	8.5	11.9	16.5	19.3
95°	81.8	55.7	48.9	42.1	33.0	27.8	22.2	19.9	22.2	27.8	33.0
97.5°	105.7	72.2	64.5	56.8	46.6	39.2	33.0	29.6	33.0	39.2	46.6
100°	117.1	87.0	79.0	71.0	59.7	50.6	45.5	43.8	45.5	50.6	59.7
102.5°	127.3	100.0	92.0	84.1	72.2	63.1	58.0	56.8	58.0	63.1	72.2
105°	139.2	112.5	104.6	96.6	84.1	75.6	71.6	69.3	71.6	75.6	84.1
107.5°	151.2	125.0	117.0	109.1	96.6	88.7	84.7	83.0	84.7	88.7	96.6
110°	163.1	138.1	129.8	121.6	109.7	102.3	98.9	96.6	98.9	102.3	109.7

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	174.5	150.6	142.1	133.6	122.2	115.4	111.4	109.1	111.4	115.4	122.2
115°	186.4	162.0	154.3	146.6	135.3	128.4	125.0	122.2	125.0	128.4	135.3
117.5°	197.2	174.5	166.6	158.6	147.8	141.5	138.1	135.8	138.1	141.5	147.8
120°	208.6	186.4	178.4	170.5	159.1	154.0	150.6	148.3	150.6	154.0	159.1
122.5°	219.4	198.9	190.6	182.4	171.1	165.4	162.0	160.3	162.0	165.4	171.1
125°	230.2	209.7	201.8	193.8	182.4	175.6	172.2	170.5	172.2	175.6	182.4
127.5°	240.4	220.5	212.2	204.0	193.2	185.8	181.3	179.0	181.3	185.8	193.2
130°	249.5	229.6	221.6	213.7	202.3	194.4	188.7	186.4	188.7	194.4	202.3
132.5°	257.5	238.7	230.8	222.8	210.9	202.3	196.1	193.2	196.1	202.3	210.9
135°	264.8	246.7	238.7	230.7	217.7	209.1	202.3	200.1	202.3	209.1	217.7
137.5°	271.1	252.9	245.5	238.1	225.1	216.0	209.1	206.3	209.1	216.0	225.1
140°	276.2	259.2	251.8	244.4	231.9	222.8	216.0	213.7	216.0	222.8	231.9
142.5°	280.2	263.7	256.9	250.1	238.1	229.0	222.8	221.1	222.8	229.0	238.1
145°	284.2	268.8	262.6	256.3	245.0	236.4	230.7	228.5	230.7	236.4	245.0
147.5°	287.6	272.8	267.1	261.4	251.8	243.8	238.1	236.4	238.1	243.8	251.8
150°	289.8	276.8	271.6	266.5	258.0	250.6	246.1	244.4	246.1	250.6	258.0
152.5°	292.1	280.8	276.2	271.7	263.7	257.5	252.9	252.3	252.9	257.5	263.7
155°	294.4	284.7	280.4	276.2	270.0	263.7	260.3	259.7	260.3	263.7	270.0
157.5°	296.1	287.6	283.9	280.2	275.1	269.4	266.5	266.0	266.5	269.4	275.1
160°	297.2	290.4	287.3	284.2	279.6	275.1	272.8	272.2	272.8	275.1	279.6
162.5°	297.8	292.1	289.8	287.6	283.6	280.2	277.9	278.5	277.9	280.2	283.6
165°	298.4	293.3	291.6	289.8	287.0	283.6	282.5	283.0	282.5	283.6	287.0
167.5°	298.4	294.4	293.2	292.1	289.8	287.6	286.4	287.0	286.4	287.6	289.8
170°	297.8	295.0	294.2	293.3	292.1	290.4	289.8	291.0	289.8	290.4	292.1
172.5°	297.2	295.5	295.0	294.4	293.8	292.1	292.7	293.3	292.7	292.1	293.8
175°	296.7	295.5	295.2	295.0	295.0	293.8	294.4	295.0	294.4	293.8	295.0
177.5°	296.1	295.5	295.5	295.5	295.5	294.4	295.0	296.1	295.0	294.4	295.5
180°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1052.3	1053.1	1055.3	1048.6	1038.3	1033.8	1020.5	1018.3	1016.1	1016.1	1018.3
5°	1028.7	1025.7	1026.4	1013.9	999.1	990.2	971.7	974.7	965.1	959.1	960.6
7.5°	1002.8	994.6	993.9	977.6	959.1	942.9	923.7	919.2	910.3	900.0	895.6
10°	970.2	964.3	953.2	934.7	911.1	897.8	871.9	856.4	854.1	838.6	832.7
12.5°	937.0	926.6	915.5	889.6	863.0	841.6	822.3	805.3	793.5	780.2	771.3
15°	898.5	885.9	873.4	846.0	814.9	793.5	764.7	739.5	704.8	677.4	661.9
17.5°	856.4	842.3	825.3	795.0	764.7	735.1	681.8	652.3	627.8	611.6	602.0
20°	812.7	797.2	780.2	749.9	697.4	645.6	616.0	593.1	578.3	562.0	550.2
22.5°	766.9	750.6	732.1	684.8	629.3	593.1	570.2	548.7	527.3	518.4	512.5
25°	724.0	709.2	685.5	621.2	577.6	544.3	518.4	504.3	493.3	481.4	470.3
27.5°	679.6	652.3	619.0	565.0	537.6	503.6	485.1	474.8	455.5	447.4	442.2
30°	626.4	596.0	564.2	525.8	494.0	470.3	453.3	436.3	425.2	417.1	408.2
32.5°	572.4	543.5	523.6	483.6	460.0	435.6	419.3	409.0	392.7	387.5	383.8
35°	525.8	501.4	483.6	451.1	428.9	406.7	394.9	379.4	369.0	359.4	353.5
37.5°	479.9	466.6	448.1	420.8	397.1	379.4	363.1	357.9	343.9	338.7	332.8
40°	448.1	428.2	412.6	389.0	369.0	349.8	339.4	327.6	318.0	309.9	307.6
42.5°	409.7	394.9	386.0	360.1	339.4	328.3	315.8	302.5	295.1	288.4	280.3
45°	380.8	367.5	355.0	334.3	315.8	301.7	290.6	281.8	269.2	266.2	253.7
47.5°	350.5	337.2	327.6	306.9	289.9	276.6	268.4	256.6	246.3	239.6	233.7
50°	320.2	309.1	300.2	282.5	267.7	253.7	242.6	230.7	226.3	215.2	211.5
52.5°	291.4	284.0	274.4	257.4	242.6	230.7	218.9	209.3	202.6	196.7	192.3
55°	267.0	255.1	250.7	232.2	219.6	207.1	196.7	190.8	182.7	179.0	175.3
57.5°	239.6	232.9	225.6	211.5	197.5	185.6	178.2	169.3	164.9	160.5	157.5
60°	215.9	206.3	200.4	188.6	176.0	164.9	158.3	151.6	145.7	142.0	136.1
62.5°	188.6	181.2	177.5	164.9	154.6	144.2	138.3	131.6	127.2	120.5	113.1
65°	164.9	159.0	154.6	144.2	134.6	125.0	119.1	110.9	105.0	101.3	100.6
67.5°	144.2	139.8	133.1	123.5	113.9	106.5	99.8	93.2	92.4	91.0	91.0
70°	121.3	116.8	113.1	102.8	94.7	86.5	85.0	82.8	80.6	79.9	78.4
72.5°	101.3	97.6	93.2	84.3	76.2	74.0	72.5	71.0	68.8	68.0	67.3
75°	82.1	76.9	74.0	65.8	63.6	62.1	60.6	58.4	56.9	56.2	54.7
77.5°	62.9	57.7	57.7	53.2	51.8	49.5	48.1	46.6	45.8	44.4	44.4
80°	44.4	44.4	42.9	40.7	38.5	37.7	35.5	34.8	34.0	34.8	33.3
82.5°	32.5	29.6	29.6	28.1	26.6	25.9	24.4	24.4	23.7	23.7	23.7
85°	18.5	18.5	17.7	16.3	15.5	15.5	14.8	14.8	14.1	14.1	13.3
87.5°	7.4	6.7	7.4	6.7	6.7	5.9	5.9	5.9	5.2	5.9	5.2
90°	6.8	7.6	8.5	11.4	15.3	18.8	19.3	18.8	18.2	17.0	18.2
92.5°	23.9	27.0	30.1	45.5	67.1	86.4	87.5	73.3	57.4	48.9	42.6
95°	42.1	48.9	55.7	81.8	131.3	197.2	222.8	194.9	148.9	114.2	90.4
97.5°	56.8	64.5	72.2	105.7	174.5	280.8	363.2	366.0	304.6	243.2	185.8
100°	71.0	79.0	87.0	117.1	186.4	309.2	449.0	530.8	518.9	448.4	370.6
102.5°	84.1	92.0	100.0	127.3	187.0	298.4	451.8	592.2	659.3	657.0	605.3
105°	96.6	104.6	112.5	139.2	189.8	283.6	421.1	572.3	690.5	754.7	762.1
107.5°	109.1	117.0	125.0	151.2	196.1	275.6	392.7	530.3	657.0	752.5	808.2
110°	121.6	129.8	138.1	163.1	204.0	273.4	373.4	491.0	611.0	712.7	785.4

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	133.6	142.1	150.6	174.5	212.6	273.9	360.9	463.8	568.9	665.5	744.5
115°	146.6	154.3	162.0	186.4	221.1	276.2	352.4	442.2	535.9	623.5	697.9
117.5°	158.6	166.6	174.5	197.2	230.2	279.6	347.8	427.4	508.7	587.1	656.4
120°	170.5	178.4	186.4	208.6	239.3	283.0	343.8	416.0	489.3	559.8	620.1
122.5°	182.4	190.6	198.9	219.4	247.2	287.0	341.6	406.4	474.0	537.1	593.3
125°	193.8	201.8	209.7	230.2	255.7	291.0	338.7	397.3	459.2	517.8	567.8
127.5°	204.0	212.2	220.5	240.4	263.7	295.0	337.0	388.7	444.4	498.4	546.2
130°	213.7	221.6	229.6	249.5	271.1	299.5	335.9	380.2	430.2	479.1	524.0
132.5°	222.8	230.8	238.7	257.5	278.5	304.1	335.3	373.4	416.6	460.9	501.3
135°	230.7	238.7	246.7	264.8	284.7	307.5	334.7	367.1	404.1	441.6	479.1
137.5°	238.1	245.5	252.9	271.1	289.8	310.9	334.7	362.6	393.9	426.2	456.9
140°	244.4	251.8	259.2	276.2	293.8	313.2	334.2	358.6	384.2	411.5	437.6
142.5°	250.1	256.9	263.7	280.2	297.2	314.9	334.2	354.6	376.2	398.4	420.0
145°	256.3	262.6	268.8	284.2	300.1	316.0	333.0	351.2	368.8	387.6	405.2
147.5°	261.4	267.1	272.8	287.6	301.8	316.6	331.3	347.8	363.2	378.5	392.7
150°	266.5	271.6	276.8	289.8	302.9	316.0	329.6	343.3	356.9	369.4	381.4
152.5°	271.7	276.2	280.8	292.1	303.5	314.9	326.8	339.3	350.7	362.0	371.7
155°	276.2	280.4	284.7	294.4	304.1	313.7	323.4	334.2	345.0	354.1	362.6
157.5°	280.2	283.9	287.6	296.1	304.1	311.4	320.0	329.6	338.2	346.1	353.5
160°	284.2	287.3	290.4	297.2	304.1	309.7	316.6	324.5	331.9	338.2	344.4
162.5°	287.6	289.8	292.1	297.8	303.5	308.0	313.7	320.0	325.7	330.8	335.9
165°	289.8	291.6	293.3	298.4	302.4	305.8	309.7	314.9	319.4	323.4	327.4
167.5°	292.1	293.2	294.4	298.4	301.8	303.5	306.3	309.7	313.2	316.6	319.4
170°	293.3	294.2	295.0	297.8	300.6	301.8	303.5	305.8	308.6	310.3	312.6
172.5°	294.4	295.0	295.5	297.2	298.9	299.5	300.1	301.8	303.5	304.6	306.3
175°	295.0	295.2	295.5	296.7	297.8	297.2	297.8	298.4	300.1	300.6	301.2
177.5°	295.5	295.5	295.5	296.1	297.2	296.1	295.5	296.1	297.2	297.2	297.8
180°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1018.3	1016.8	1012.4	1013.9	1011.7	1011.7	1010.2	1010.2	1010.2	1013.9	1011.7
5°	962.8	957.7	952.5	950.3	948.1	945.8	945.8	945.1	951.8	950.3	956.2
7.5°	894.1	892.6	882.2	882.2	878.5	877.1	880.8	881.5	882.2	883.7	887.4
10°	832.7	829.0	814.2	815.7	813.5	810.5	812.7	811.2	816.4	817.9	816.4
12.5°	760.2	753.6	737.3	729.2	720.3	713.6	721.8	715.8	736.6	742.5	758.7
15°	664.1	651.5	640.4	640.4	632.3	626.4	630.1	636.7	641.2	647.8	650.8
17.5°	599.7	594.6	585.7	580.5	578.3	576.1	576.1	579.0	588.7	587.9	593.8
20°	545.0	542.1	537.6	531.0	528.8	527.3	527.3	527.3	533.9	539.8	543.5
22.5°	507.3	505.1	502.1	493.3	488.8	487.3	491.0	493.3	498.4	502.9	506.6
25°	469.6	464.4	459.2	456.3	454.1	454.1	455.5	456.3	458.5	460.7	465.2
27.5°	438.5	434.8	427.4	419.3	419.3	417.1	418.6	420.0	425.2	432.6	436.3
30°	403.8	403.0	400.1	397.1	394.2	392.7	395.6	397.9	398.6	402.3	402.3
32.5°	378.6	373.5	368.3	365.3	363.8	363.1	363.8	366.8	366.8	371.2	376.4
35°	353.5	350.5	345.4	340.2	338.7	335.0	338.0	340.9	346.1	348.3	350.5
37.5°	326.1	322.4	320.2	318.7	315.8	316.5	314.3	318.7	323.2	322.4	323.9
40°	305.4	298.8	292.1	291.4	290.6	289.9	289.9	290.6	293.6	296.5	301.0
42.5°	278.8	276.6	270.7	264.7	263.3	261.8	260.3	263.3	269.2	274.4	276.6
45°	251.4	248.5	247.0	242.6	239.6	238.9	237.4	241.1	246.3	248.5	250.0
47.5°	226.3	225.6	221.1	221.9	219.6	220.4	219.6	221.9	221.9	224.1	225.6
50°	209.3	207.1	204.8	203.4	201.1	201.1	200.4	201.1	204.1	207.1	206.3
52.5°	192.3	188.6	187.8	187.1	185.6	187.1	184.9	185.6	188.6	190.1	189.3
55°	172.3	171.6	170.1	168.6	167.9	167.1	167.1	167.1	170.1	172.3	173.0
57.5°	156.8	153.1	150.1	150.1	147.2	146.4	147.9	148.6	150.9	152.3	153.8
60°	135.3	133.9	129.4	127.2	122.8	122.0	122.0	125.0	128.7	133.9	135.3
62.5°	112.4	110.2	109.4	109.4	109.4	109.4	109.4	109.4	109.4	110.2	110.2
65°	99.8	100.6	99.8	99.1	99.8	99.8	99.1	99.1	99.1	99.8	100.6
67.5°	89.5	88.7	89.5	88.7	88.0	88.0	87.3	88.0	88.7	89.5	89.5
70°	77.6	77.6	76.9	77.6	76.9	76.2	75.4	75.4	76.9	77.6	77.6
72.5°	66.6	66.6	65.8	65.8	64.3	64.3	65.1	64.3	64.3	66.6	66.6
75°	55.5	54.7	54.0	54.0	53.2	53.2	53.2	52.5	54.0	54.0	54.7
77.5°	43.6	43.6	43.6	42.9	42.9	42.2	42.2	42.9	42.9	42.9	43.6
80°	33.3	33.3	33.3	32.5	31.8	31.8	31.8	31.8	31.8	32.5	31.8
82.5°	22.9	22.9	22.9	22.9	22.9	22.2	22.2	22.2	22.9	22.9	22.2
85°	14.1	13.3	14.1	14.1	13.3	14.1	13.3	13.3	12.6	12.6	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	18.5	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.5
92.5°	40.4	38.1	37.5	35.2	35.8	34.7	35.8	35.2	37.5	38.1	40.4
95°	84.2	77.9	70.5	65.9	64.2	64.8	64.2	65.9	70.5	77.9	84.2
97.5°	168.8	151.7	129.6	118.2	112.0	108.6	112.0	118.2	129.6	151.7	168.8
100°	336.2	301.8	254.6	230.2	213.7	203.5	213.7	230.2	254.6	301.8	336.2
102.5°	568.3	531.4	479.1	433.1	411.5	396.7	411.5	433.1	479.1	531.4	568.3
105°	752.8	743.4	708.1	672.9	648.5	640.5	648.5	672.9	708.1	743.4	752.8
107.5°	819.6	830.9	830.3	825.2	817.8	804.8	817.8	825.2	830.3	830.9	819.6
110°	808.7	832.0	856.5	867.3	872.4	871.8	872.4	867.3	856.5	832.0	808.7

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	772.0	799.6	836.0	855.9	866.7	870.7	866.7	855.9	836.0	799.6	772.0
115°	727.2	756.5	796.8	822.9	837.7	842.8	837.7	822.9	796.8	756.5	727.2
117.5°	684.2	712.1	753.6	781.5	796.8	800.8	796.8	781.5	753.6	712.1	684.2
120°	646.0	671.8	711.6	738.3	754.7	760.4	754.7	738.3	711.6	671.8	646.0
122.5°	616.0	638.8	673.5	699.6	713.8	718.4	713.8	699.6	673.5	638.8	616.0
125°	589.1	610.4	643.4	664.9	679.2	683.7	679.2	664.9	643.4	610.4	589.1
127.5°	566.1	586.0	614.9	635.4	647.9	651.3	647.9	635.4	614.9	586.0	566.1
130°	542.8	561.5	589.4	608.7	620.1	624.6	620.1	608.7	589.4	561.5	542.8
132.5°	518.6	535.9	563.2	582.5	592.8	596.7	592.8	582.5	563.2	535.9	518.6
135°	495.0	510.9	535.4	554.1	564.4	566.6	564.4	554.1	535.4	510.9	495.0
137.5°	471.2	485.4	508.7	525.1	534.2	537.6	534.2	525.1	508.7	485.4	471.2
140°	450.1	462.6	480.8	495.6	504.1	507.5	504.1	495.6	480.8	462.6	450.1
142.5°	430.0	439.9	456.9	470.0	477.4	477.4	477.4	470.0	456.9	439.9	430.0
145°	413.4	421.7	435.3	445.0	450.7	452.4	450.7	445.0	435.3	421.7	413.4
147.5°	399.0	405.2	417.2	425.1	429.1	430.2	429.1	425.1	417.2	405.2	399.0
150°	386.5	391.6	400.1	406.9	410.3	410.9	410.3	406.9	400.1	391.6	386.5
152.5°	376.0	380.2	386.5	392.1	394.4	394.4	394.4	392.1	386.5	380.2	376.0
155°	365.7	368.8	375.1	379.1	381.4	380.2	381.4	379.1	375.1	368.8	365.7
157.5°	356.0	358.6	363.2	366.6	367.7	367.7	367.7	366.6	363.2	358.6	356.0
160°	346.4	348.4	352.4	355.2	355.8	355.8	355.8	355.2	352.4	348.4	346.4
162.5°	337.3	338.7	342.7	344.4	345.0	344.4	345.0	344.4	342.7	338.7	337.3
165°	328.5	329.6	331.9	334.2	334.2	333.6	334.2	334.2	331.9	329.6	328.5
167.5°	320.5	321.7	322.8	323.9	323.9	323.4	323.9	323.9	322.8	321.7	320.5
170°	313.2	313.7	314.3	316.0	315.4	314.3	315.4	316.0	314.3	313.7	313.2
172.5°	306.6	306.9	307.5	308.0	307.5	306.9	307.5	308.0	307.5	306.9	306.6
175°	301.5	301.8	301.8	302.4	301.8	300.6	301.8	302.4	301.8	301.8	301.5
177.5°	297.8	297.8	297.8	297.8	297.2	296.1	297.2	297.8	297.8	297.8	297.8
180°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1013.9	1017.6	1016.1	1008.0	1016.1	1018.3	1022.7	1027.2	1030.1	1034.6	1038.3
5°	950.3	957.7	962.1	957.7	972.5	974.7	985.0	990.9	999.8	1007.2	1013.1
7.5°	890.4	896.3	905.2	906.6	915.5	925.9	940.7	955.5	969.5	976.9	983.6
10°	826.0	836.4	849.7	846.7	860.1	876.3	891.9	915.5	927.3	940.7	952.5
12.5°	761.7	768.4	786.1	792.0	811.2	823.8	845.3	860.1	889.6	905.2	915.5
15°	649.3	676.7	698.8	725.5	750.6	774.3	793.5	820.1	846.0	857.8	874.8
17.5°	598.3	610.8	624.1	637.5	670.0	712.2	746.2	775.0	797.2	812.7	832.7
20°	545.0	557.6	572.4	585.0	604.9	635.2	677.4	726.9	753.6	769.8	789.1
22.5°	507.3	519.1	528.8	539.8	555.4	577.6	609.4	670.7	706.2	726.2	743.2
25°	466.6	481.4	491.8	499.9	512.5	536.9	562.8	597.5	661.1	676.7	700.3
27.5°	438.5	443.0	454.8	467.4	479.9	493.3	519.9	549.5	592.4	626.4	655.2
30°	405.3	416.3	427.4	432.6	443.7	462.9	479.2	511.0	544.3	570.9	605.7
32.5°	380.1	386.8	394.2	406.7	417.1	430.4	446.7	473.3	501.4	518.4	545.0
35°	352.0	356.4	372.0	377.2	387.5	400.8	417.1	437.8	468.1	481.4	500.7
37.5°	325.4	335.7	340.2	352.0	361.6	374.9	386.8	410.4	430.4	445.9	463.7
40°	304.7	309.1	317.3	327.6	335.7	346.1	360.9	377.9	399.3	411.9	427.4
42.5°	279.5	283.2	293.6	299.5	312.8	322.4	331.3	352.0	371.2	380.8	396.4
45°	252.2	261.0	267.7	279.5	286.9	298.8	309.9	324.6	342.4	353.5	362.4
47.5°	228.5	237.4	244.0	255.1	267.0	272.1	284.0	299.5	315.8	324.6	337.2
50°	209.3	212.2	224.8	230.0	242.6	252.9	261.0	274.4	292.1	297.3	307.6
52.5°	190.8	193.0	201.1	207.8	218.9	227.8	238.1	250.7	265.5	273.6	281.8
55°	174.5	176.0	179.7	187.1	194.5	205.6	215.2	227.0	239.6	248.5	255.9
57.5°	156.0	159.0	162.0	166.4	173.8	184.1	194.5	205.6	215.9	221.9	231.5
60°	134.6	139.0	144.2	149.4	154.6	162.0	173.8	184.1	193.8	198.9	206.3
62.5°	111.7	120.5	125.0	130.9	135.3	142.0	150.9	162.7	169.3	176.0	181.9
65°	100.6	101.3	102.1	108.0	116.1	122.8	130.9	139.8	150.1	154.6	159.0
67.5°	89.5	90.2	91.7	92.4	95.4	102.8	111.7	121.3	129.4	132.4	136.8
70°	78.4	78.4	81.3	82.1	82.8	83.6	91.0	100.6	108.0	111.7	116.8
72.5°	66.6	67.3	68.8	69.5	71.0	72.5	74.7	79.9	88.7	92.4	98.4
75°	54.7	55.5	56.2	56.9	59.2	59.9	62.1	65.1	68.8	73.2	76.9
77.5°	43.6	43.6	44.4	45.8	47.3	48.1	50.3	51.8	53.2	55.5	58.4
80°	32.5	33.3	33.3	34.8	34.8	35.5	36.2	38.5	39.9	41.4	42.9
82.5°	22.2	23.7	23.7	23.7	24.4	25.1	25.9	25.9	27.4	28.1	30.3
85°	13.3	14.1	14.1	14.1	13.3	14.8	14.8	15.5	15.5	15.5	16.3
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.7	6.7
90°	18.2	17.0	18.2	18.8	19.3	18.8	15.3	11.4	8.5	7.6	6.8
92.5°	42.6	48.9	57.4	73.3	87.5	86.4	67.1	45.5	30.1	27.0	23.9
95°	90.4	114.2	148.9	194.9	222.8	197.2	131.3	81.8	55.7	48.9	42.1
97.5°	185.8	243.2	304.6	366.0	363.2	280.8	174.5	105.7	72.2	64.5	56.8
100°	370.6	448.4	518.9	530.8	449.0	309.2	186.4	117.1	87.0	79.0	71.0
102.5°	605.3	657.0	659.3	592.2	451.8	298.4	187.0	127.3	100.0	92.0	84.1
105°	762.1	754.7	690.5	572.3	421.1	283.6	189.8	139.2	112.5	104.6	96.6
107.5°	808.2	752.5	657.0	530.3	392.7	275.6	196.1	151.2	125.0	117.0	109.1
110°	785.4	712.7	611.0	491.0	373.4	273.4	204.0	163.1	138.1	129.8	121.6

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	744.5	665.5	568.9	463.8	360.9	273.9	212.6	174.5	150.6	142.1	133.6
115°	697.9	623.5	535.9	442.2	352.4	276.2	221.1	186.4	162.0	154.3	146.6
117.5°	656.4	587.1	508.7	427.4	347.8	279.6	230.2	197.2	174.5	166.6	158.6
120°	620.1	559.8	489.3	416.0	343.8	283.0	239.3	208.6	186.4	178.4	170.5
122.5°	593.3	537.1	474.0	406.4	341.6	287.0	247.2	219.4	198.9	190.6	182.4
125°	567.8	517.8	459.2	397.3	338.7	291.0	255.7	230.2	209.7	201.8	193.8
127.5°	546.2	498.4	444.4	388.7	337.0	295.0	263.7	240.4	220.5	212.2	204.0
130°	524.0	479.1	430.2	380.2	335.9	299.5	271.1	249.5	229.6	221.6	213.7
132.5°	501.3	460.9	416.6	373.4	335.3	304.1	278.5	257.5	238.7	230.8	222.8
135°	479.1	441.6	404.1	367.1	334.7	307.5	284.7	264.8	246.7	238.7	230.7
137.5°	456.9	426.2	393.9	362.6	334.7	310.9	289.8	271.1	252.9	245.5	238.1
140°	437.6	411.5	384.2	358.6	334.2	313.2	293.8	276.2	259.2	251.8	244.4
142.5°	420.0	398.4	376.2	354.6	334.2	314.9	297.2	280.2	263.7	256.9	250.1
145°	405.2	387.6	368.8	351.2	333.0	316.0	300.1	284.2	268.8	262.6	256.3
147.5°	392.7	378.5	363.2	347.8	331.3	316.6	301.8	287.6	272.8	267.1	261.4
150°	381.4	369.4	356.9	343.3	329.6	316.0	302.9	289.8	276.8	271.6	266.5
152.5°	371.7	362.0	350.7	339.3	326.8	314.9	303.5	292.1	280.8	276.2	271.7
155°	362.6	354.1	345.0	334.2	323.4	313.7	304.1	294.4	284.7	280.4	276.2
157.5°	353.5	346.1	338.2	329.6	320.0	311.4	304.1	296.1	287.6	283.9	280.2
160°	344.4	338.2	331.9	324.5	316.6	309.7	304.1	297.2	290.4	287.3	284.2
162.5°	335.9	330.8	325.7	320.0	313.7	308.0	303.5	297.8	292.1	289.8	287.6
165°	327.4	323.4	319.4	314.9	309.7	305.8	302.4	298.4	293.3	291.6	289.8
167.5°	319.4	316.6	313.2	309.7	306.3	303.5	301.8	298.4	294.4	293.2	292.1
170°	312.6	310.3	308.6	305.8	303.5	301.8	300.6	297.8	295.0	294.2	293.3
172.5°	306.3	304.6	303.5	301.8	300.1	299.5	298.9	297.2	295.5	295.0	294.4
175°	301.2	300.6	300.1	298.4	297.8	297.2	297.8	296.7	295.5	295.2	295.0
177.5°	297.8	297.2	297.2	296.1	295.5	296.1	297.2	296.1	295.5	295.5	295.5
180°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1064.2	1064.2	1064.2	1064.2
2.5°	1044.9	1042.7	1056.0	1070.8
5°	1023.5	1027.2	1044.2	1064.9
7.5°	1001.3	1009.4	1029.4	1056.8
10°	970.2	985.0	1015.4	1043.5
12.5°	939.9	959.9	988.7	1022.0
15°	905.9	928.1	963.6	1003.5
17.5°	868.2	893.3	934.7	978.4
20°	828.3	861.5	905.2	952.5
22.5°	783.9	823.8	868.9	921.4
25°	741.0	784.6	829.7	890.4
27.5°	698.8	741.7	792.0	853.4
30°	656.7	695.9	749.9	815.7
32.5°	611.6	652.3	709.2	776.5
35°	570.2	610.8	664.1	730.6
37.5°	525.8	569.4	620.5	689.2
40°	474.0	525.1	574.6	640.4
42.5°	431.1	485.1	533.2	595.3
45°	397.1	448.1	488.1	548.7
47.5°	365.3	406.7	447.4	503.6
50°	335.0	366.8	409.0	459.2
52.5°	303.9	331.3	367.5	414.9
55°	275.8	301.7	334.3	370.5
57.5°	250.0	268.4	301.0	333.5
60°	221.1	240.3	265.5	292.8
62.5°	196.7	211.5	235.2	258.1
65°	170.8	184.9	202.6	224.1
67.5°	147.2	159.7	173.8	190.8
70°	125.7	135.3	145.7	160.5
72.5°	102.8	113.1	122.8	134.6
75°	84.3	88.7	96.9	105.0
77.5°	65.1	71.0	75.4	82.1
80°	46.6	51.8	53.2	58.4
82.5°	31.1	34.0	37.0	38.5
85°	17.7	19.2	22.2	22.9
87.5°	6.7	7.4	8.9	10.4
90°	5.7	4.5	2.3	0.6
92.5°	19.3	16.5	11.9	8.5
95°	33.0	27.8	22.2	19.9
97.5°	46.6	39.2	33.0	29.6
100°	59.7	50.6	45.5	43.8
102.5°	72.2	63.1	58.0	56.8
105°	84.1	75.6	71.6	69.3
107.5°	96.6	88.7	84.7	83.0
110°	109.7	102.3	98.9	96.6

TEST NUMBER: P999773

CATALOG NUMBER: SA2XXRDIP-B485D530UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	122.2	115.4	111.4	109.1
115°	135.3	128.4	125.0	122.2
117.5°	147.8	141.5	138.1	135.8
120°	159.1	154.0	150.6	148.3
122.5°	171.1	165.4	162.0	160.3
125°	182.4	175.6	172.2	170.5
127.5°	193.2	185.8	181.3	179.0
130°	202.3	194.4	188.7	186.4
132.5°	210.9	202.3	196.1	193.2
135°	217.7	209.1	202.3	200.1
137.5°	225.1	216.0	209.1	206.3
140°	231.9	222.8	216.0	213.7
142.5°	238.1	229.0	222.8	221.1
145°	245.0	236.4	230.7	228.5
147.5°	251.8	243.8	238.1	236.4
150°	258.0	250.6	246.1	244.4
152.5°	263.7	257.5	252.9	252.3
155°	270.0	263.7	260.3	259.7
157.5°	275.1	269.4	266.5	266.0
160°	279.6	275.1	272.8	272.2
162.5°	283.6	280.2	277.9	278.5
165°	287.0	283.6	282.5	283.0
167.5°	289.8	287.6	286.4	287.0
170°	292.1	290.4	289.8	291.0
172.5°	293.8	292.1	292.7	293.3
175°	295.0	293.8	294.4	295.0
177.5°	295.5	294.4	295.0	296.1
180°	295.5	295.5	295.5	295.5

(END OF REPORT)