

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999813

Luminaire Tested: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999813
REPORT IS A COMBINATION OF REPORTS P988368 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4591.0 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	89	85	87	84	81	78	69	67	65	55	54	53	42	42	41
2	88	81	76	71	80	74	69	65	61	58	55	49	47	45	38	37	35
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	33	31
4	74	64	57	51	67	59	52	48	49	44	41	40	37	34	31	29	27
5	68	57	50	44	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	52	44	39	58	48	41	36	40	35	31	33	29	26	26	24	22
7	59	47	39	34	53	43	37	32	37	32	28	30	26	24	24	22	20
8	54	43	35	30	50	40	33	29	33	29	25	28	24	21	22	20	18
9	51	39	32	27	46	36	30	26	31	26	23	26	22	19	21	18	16
10	48	36	29	25	44	33	27	23	29	24	20	24	20	18	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16846	16846	16846	16846
5°	16884	17893	16943	14293
10°	16699	18911	16816	11803
15°	16336	18917	16612	8868
20°	15900	15637	16246	7316
25°	15372	9771	15704	6224
30°	14697	6256	15097	5358
35°	13875	4808	14325	4585
40°	12961	4041	13516	4011
45°	11984	3439	12484	3367
50°	10981	2923	11495	2911
55°	9872	2539	10405	2506
60°	8885	1937	9358	1913
65°	7967	1457	8439	1653
70°	6951	1164	7492	1348
75°	5874	892	6411	1018
80°	4663	605	5022	669
85°	3235	313	3546	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15410 cd/sqm

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	2.2
10°-20°	281.7	6.1
20°-30°	362.6	7.9
30°-40°	344.0	7.5
40°-50°	294.8	6.4
50°-60°	224.5	4.9
60°-70°	141.6	3.1
70°-80°	70.6	1.5
80°-90°	20.7	0.5
90°-100°	153.9	3.4
100°-110°	542.0	11.8
110°-120°	569.2	12.4
120°-130°	468.3	10.2
130°-140°	376.2	8.2
140°-150°	284.2	6.2
150°-160°	199.8	4.4
160°-170°	117.6	2.6
170°-180°	38.3	0.8
0°-30°	745.3	16.2
0°-40°	1089.3	23.7
0°-60°	1608.6	35.0
0°-90°	1841.5	40.1
90°-120°	1265.1	27.6
90°-150°	2393.8	52.1
90°-180°	2749.0	59.9
0°-180°	4591.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1064	1064	1064	1064	1064	
5°	1065	1184	1069	946	1065	101
15°	1004	1336	1020	626	1004	282
25°	890	713	910	454	890	409
35°	731	351	754	335	731	457
45°	549	244	572	239	549	424
55°	370	169	390	167	370	334
65°	224	88	237	100	224	222
75°	105	47	115	53	105	114
85°	23	13	25	14	23	26
90°	1	25	1	25	1	3
95°	27	87	27	87	27	27
105°	93	856	93	856	93	98
115°	163	1126	163	1126	163	162
125°	228	913	228	913	228	202
135°	267	757	267	757	267	206
145°	305	604	305	604	305	191
155°	347	508	347	508	347	160
165°	378	446	378	446	378	107
175°	394	402	394	402	394	37
180°	395	395	395	395	395	

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1070.8	1075.3	1077.5	1080.4	1087.1	1091.5	1098.2	1099.7	1098.9	1101.9	1093.7
5°	1064.9	1074.5	1083.4	1090.8	1102.6	1110.0	1118.1	1127.8	1130.0	1141.1	1134.4
7.5°	1056.8	1070.8	1083.4	1098.2	1115.9	1125.5	1138.1	1152.9	1159.6	1172.9	1176.6
10°	1043.5	1063.4	1084.9	1100.4	1124.8	1141.8	1153.6	1177.3	1192.8	1212.8	1209.8
12.5°	1022.0	1047.9	1076.7	1102.6	1134.4	1145.5	1167.7	1192.1	1212.1	1230.6	1246.8
15°	1003.5	1033.1	1064.9	1096.7	1132.9	1153.6	1175.8	1207.6	1229.1	1261.6	1275.7
17.5°	978.4	1016.1	1053.8	1089.3	1132.2	1155.9	1183.2	1214.3	1246.1	1277.1	1288.2
20°	952.5	993.2	1033.8	1081.9	1130.7	1153.6	1181.7	1220.2	1251.3	1275.7	1275.7
22.5°	921.4	971.0	1017.6	1063.4	1116.7	1149.9	1178.8	1223.9	1246.1	1251.3	1231.3
25°	890.4	939.9	990.9	1047.9	1108.5	1138.1	1170.6	1212.8	1220.2	1199.5	1147.7
27.5°	853.4	908.9	966.5	1027.9	1091.5	1128.5	1158.1	1186.2	1172.1	1116.7	1036.1
30°	815.7	875.6	940.7	999.1	1076.0	1110.0	1135.2	1143.3	1098.9	1008.7	904.4
32.5°	776.5	834.9	903.7	973.9	1051.6	1084.1	1100.4	1078.9	997.6	883.7	756.5
35°	730.6	796.5	868.2	941.4	1018.3	1042.7	1052.3	999.8	895.6	748.4	621.9
37.5°	689.2	755.0	832.0	906.6	981.3	994.6	985.0	902.9	770.6	624.9	501.4
40°	640.4	710.7	786.1	869.7	931.0	934.7	911.1	804.6	640.4	503.6	427.4
42.5°	595.3	666.3	741.7	826.8	873.4	860.8	829.0	689.2	534.7	434.1	372.7
45°	548.7	616.0	697.4	772.8	806.1	776.5	728.4	579.8	448.9	373.5	326.1
47.5°	503.6	566.5	647.1	719.5	725.5	692.2	635.2	485.9	389.0	328.3	289.9
50°	459.2	522.1	597.5	657.4	651.5	605.7	541.3	422.3	338.0	289.9	258.1
52.5°	414.9	471.8	545.0	592.4	567.2	522.8	459.2	357.9	295.1	252.9	228.5
55°	370.5	423.7	486.6	525.8	485.9	434.8	389.7	306.9	255.9	221.9	203.4
57.5°	333.5	375.7	433.4	457.0	409.0	369.0	329.8	264.0	221.9	197.5	176.0
60°	292.8	331.3	378.6	392.7	343.1	310.6	277.3	223.3	190.1	168.6	154.6
62.5°	258.1	289.9	326.1	326.1	282.5	258.1	232.9	187.1	159.7	142.7	136.1
65°	224.1	247.0	272.9	269.9	232.9	211.5	191.5	154.6	133.9	122.0	115.4
67.5°	190.8	208.5	225.6	215.2	188.6	170.1	151.6	125.0	110.9	102.8	93.9
70°	160.5	174.5	183.4	173.8	147.2	131.6	118.3	100.6	89.5	79.1	74.0
72.5°	134.6	140.5	143.5	131.6	109.4	100.6	91.0	78.4	68.8	63.6	62.1
75°	105.0	110.2	108.0	99.1	80.6	74.0	66.6	57.7	55.5	52.5	51.0
77.5°	82.1	82.1	78.4	70.3	57.7	52.5	49.5	45.1	42.9	42.2	40.7
80°	58.4	57.7	55.5	46.6	39.2	36.2	36.2	33.3	32.5	31.1	31.1
82.5°	38.5	38.5	35.5	28.1	25.9	25.1	24.4	22.9	22.9	22.2	22.2
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.1	13.3	14.1	13.3	13.3
87.5°	10.4	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.8	3.0	6.1	7.6	9.1	10.2	11.4	15.2	20.5	25.1	25.8
92.5°	11.4	15.9	22.0	25.8	31.9	36.0	40.2	60.7	89.6	115.4	116.9
95°	26.6	29.6	37.2	44.0	56.2	65.3	74.4	109.3	175.4	263.5	297.6
97.5°	39.5	44.0	52.4	62.3	75.9	86.2	96.4	141.2	233.1	375.1	485.2
100°	58.5	60.7	67.6	79.7	94.9	105.6	116.2	156.4	249.0	413.0	599.8
102.5°	75.9	77.4	84.3	96.4	112.4	123.0	133.6	170.1	249.8	398.6	603.6
105°	92.6	95.7	101.0	112.4	129.1	139.7	150.3	186.0	253.6	378.9	562.6
107.5°	110.9	113.1	118.4	129.1	145.8	156.4	167.0	202.0	261.9	368.2	524.6
110°	129.1	132.1	136.7	146.5	162.5	173.5	184.5	217.9	272.6	365.2	498.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	145.8	148.8	154.1	163.2	178.4	189.8	201.2	233.1	284.0	366.0	482.1
115°	163.2	167.0	171.6	180.7	195.9	206.2	216.4	249.0	295.3	369.0	470.7
117.5°	181.5	184.5	189.1	197.4	211.8	222.4	233.1	263.5	307.5	373.6	464.7
120°	198.2	201.2	205.8	212.6	227.8	238.4	249.0	278.6	319.6	378.1	459.3
122.5°	214.1	216.4	220.9	228.5	243.7	254.7	265.7	293.1	330.3	383.4	456.3
125°	227.8	230.1	234.6	243.7	258.9	269.5	280.2	307.5	341.7	388.7	452.5
127.5°	239.2	242.2	248.3	258.1	272.6	283.6	294.6	321.2	352.3	394.1	450.2
130°	249.0	252.1	259.7	270.3	285.5	296.1	306.7	333.3	362.2	400.1	448.7
132.5°	258.1	261.9	270.3	281.7	297.6	308.2	318.9	343.9	372.0	406.2	448.0
135°	267.3	270.3	279.4	290.8	308.3	318.9	329.5	353.8	380.4	410.8	447.2
137.5°	275.6	279.4	288.5	300.7	318.1	328.0	337.9	362.2	387.2	415.3	447.2
140°	285.5	288.5	297.6	309.8	326.5	336.4	346.2	369.0	392.5	418.3	446.4
142.5°	295.3	297.6	306.0	318.1	334.1	343.2	352.3	374.3	397.1	420.6	446.4
145°	305.2	308.3	315.8	327.2	342.4	350.8	359.1	379.6	400.9	422.1	444.9
147.5°	315.8	318.1	325.7	336.3	349.3	356.8	364.4	384.2	403.2	422.9	442.6
150°	326.5	328.8	334.8	344.7	356.1	363.0	369.8	387.2	404.7	422.1	440.4
152.5°	337.1	337.9	343.9	352.3	362.9	369.0	375.1	390.3	405.4	420.6	436.6
155°	347.0	347.7	352.3	360.6	369.0	374.7	380.4	393.3	406.2	419.1	432.0
157.5°	355.3	356.1	359.9	367.5	374.3	379.2	384.2	395.6	406.2	416.1	427.5
160°	363.7	364.4	367.5	373.6	379.6	383.8	388.0	397.1	406.2	413.8	422.9
162.5°	372.0	371.3	374.3	378.9	384.2	387.2	390.3	397.8	405.4	411.5	419.1
165°	378.1	377.3	378.9	383.4	387.2	389.5	391.8	398.6	403.9	408.5	413.8
167.5°	383.4	382.7	384.2	387.2	390.3	391.8	393.3	398.6	403.2	405.4	409.2
170°	388.7	387.2	388.0	390.3	391.8	393.0	394.1	397.8	401.6	403.2	405.4
172.5°	391.8	391.0	390.3	392.5	393.3	394.0	394.8	397.1	399.4	400.1	400.9
175°	394.1	393.3	392.5	394.1	394.1	394.5	394.8	396.3	397.8	397.1	397.8
177.5°	395.6	394.1	393.3	394.8	394.8	394.8	394.8	395.6	397.1	395.6	394.8
180°	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1101.9	1103.4	1105.6	1115.9	1117.4	1120.4	1118.9	1118.9	1119.6	1118.1	1118.9
5°	1149.2	1151.4	1162.5	1175.1	1178.0	1175.1	1178.8	1184.0	1184.0	1184.0	1182.5
7.5°	1193.6	1201.7	1214.3	1232.8	1236.5	1240.2	1246.8	1242.4	1243.9	1250.5	1248.3
10°	1236.5	1248.3	1262.3	1277.9	1286.0	1291.2	1294.1	1300.8	1316.3	1298.6	1305.2
12.5°	1277.1	1294.1	1308.9	1325.9	1331.9	1338.5	1340.7	1346.7	1346.7	1345.9	1351.1
15°	1303.8	1319.3	1332.6	1343.7	1345.2	1343.7	1342.2	1343.0	1345.2	1336.3	1341.5
17.5°	1309.7	1311.2	1315.6	1311.2	1311.9	1296.4	1287.5	1285.3	1264.6	1265.3	1282.3
20°	1280.8	1255.7	1249.0	1224.6	1209.8	1169.9	1168.4	1157.3	1113.7	1127.0	1124.1
22.5°	1201.7	1158.8	1101.9	1073.8	1059.7	1017.6	985.0	962.1	946.6	931.0	924.4
25°	1097.4	1027.9	947.3	891.9	883.7	844.5	784.6	756.5	723.2	712.9	730.6
27.5°	962.8	872.6	781.7	696.6	681.1	645.6	615.3	595.3	556.9	554.6	556.1
30°	780.2	689.2	613.1	557.6	519.1	502.9	482.9	468.1	452.6	458.5	460.0
32.5°	641.2	554.6	483.6	454.1	436.3	426.0	409.0	399.3	392.7	390.5	389.7
35°	509.5	451.8	420.0	391.2	380.8	373.5	360.9	356.4	350.5	351.3	351.3
37.5°	436.3	388.2	364.6	349.8	340.2	336.5	328.3	323.9	320.2	318.7	320.9
40°	376.4	343.1	328.3	315.0	306.9	305.4	301.0	295.8	291.4	292.1	294.3
42.5°	332.8	313.6	295.8	285.5	279.5	277.3	273.6	269.9	269.9	267.7	267.0
45°	298.0	282.5	267.7	258.1	254.4	251.4	247.0	246.3	243.3	244.0	244.8
47.5°	267.0	254.4	243.3	233.7	230.0	229.2	224.8	221.9	221.9	221.1	220.4
50°	238.9	226.3	216.7	211.5	206.3	204.8	204.1	203.4	201.9	201.9	202.6
52.5°	215.9	203.4	196.0	191.5	188.6	187.1	187.1	186.4	186.4	186.4	185.6
55°	190.8	180.4	174.5	173.0	171.6	170.8	170.1	168.6	167.9	169.3	167.9
57.5°	167.1	163.4	158.3	156.8	153.1	153.1	150.9	149.4	147.9	149.4	149.4
60°	148.6	143.5	140.5	136.1	133.1	130.2	126.5	125.7	124.2	123.5	122.8
62.5°	129.4	125.0	117.6	110.9	106.5	103.5	102.1	101.3	101.3	100.6	100.6
65°	108.0	97.6	93.9	91.7	91.0	90.2	88.7	88.0	88.7	88.0	88.7
67.5°	84.3	82.8	80.6	79.1	78.4	77.6	77.6	76.9	76.9	76.9	76.9
70°	73.2	69.5	68.8	67.3	67.3	66.6	66.6	66.6	66.6	65.8	67.3
72.5°	60.6	58.4	57.7	56.9	56.9	56.9	56.2	56.2	56.2	55.5	56.2
75°	49.5	48.8	47.3	47.3	46.6	47.3	46.6	46.6	45.8	46.6	46.6
77.5°	39.9	39.2	38.5	38.5	37.7	37.7	37.7	37.7	37.7	37.7	38.5
80°	30.3	29.6	28.8	29.6	28.8	29.6	28.8	28.8	29.6	28.8	28.8
82.5°	22.2	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.6	12.6	13.3	12.6	13.3	12.6	12.6	12.6	13.3	13.3
87.5°	5.9	6.7	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.7
90°	25.1	24.3	22.8	24.3	24.7	25.1	25.1	25.1	25.1	25.1	25.1
92.5°	97.9	76.7	65.3	56.9	53.9	50.9	50.1	47.1	47.8	46.3	47.8
95°	260.4	198.9	152.6	120.7	112.4	104.0	94.1	88.1	85.8	86.6	85.8
97.5°	489.0	407.0	325.0	248.3	225.5	202.7	173.1	157.9	149.6	145.0	149.6
100°	709.1	693.2	599.0	495.0	449.1	403.2	340.1	307.5	285.5	271.8	285.5
102.5°	791.1	880.7	877.7	808.6	759.2	709.9	640.0	578.5	549.7	530.0	549.7
105°	764.6	922.5	1008.3	1018.2	1005.6	993.1	946.0	899.0	866.3	855.7	866.3
107.5°	708.4	877.7	1005.2	1079.7	1094.8	1110.0	1109.3	1102.4	1092.6	1075.1	1092.6
110°	656.0	816.2	952.1	1049.3	1080.4	1111.5	1144.2	1158.6	1165.4	1164.7	1165.4

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	619.5	760.0	889.1	994.6	1031.4	1068.3	1116.9	1143.4	1157.9	1163.2	1157.9
115°	590.7	716.0	832.9	932.4	971.5	1010.6	1064.5	1099.4	1119.1	1126.0	1119.1
117.5°	571.0	679.5	784.3	876.9	914.1	951.3	1006.8	1044.0	1064.5	1069.8	1064.5
120°	555.8	653.7	747.9	828.3	862.8	897.4	950.6	986.3	1008.3	1015.9	1008.3
122.5°	542.9	633.2	717.5	792.7	823.0	853.4	899.7	934.6	953.6	959.7	953.6
125°	530.7	613.5	691.7	758.5	787.0	815.4	859.5	888.3	907.3	913.4	907.3
127.5°	519.3	593.7	665.9	729.6	756.2	782.8	821.5	848.8	865.5	870.1	865.5
130°	507.9	574.8	640.0	700.0	725.0	750.1	787.3	813.2	828.3	834.4	828.3
132.5°	498.8	556.5	615.8	669.7	692.8	716.0	752.4	778.2	791.9	797.2	791.9
135°	490.5	539.8	589.9	640.0	661.3	682.6	715.2	740.3	753.9	757.0	753.9
137.5°	484.4	526.2	569.4	610.4	629.4	648.4	679.5	701.5	713.7	718.2	713.7
140°	479.1	513.3	549.7	584.6	601.3	618.0	642.3	662.1	673.5	678.0	673.5
142.5°	473.8	502.6	532.2	561.1	574.4	587.7	610.4	627.9	637.8	637.8	637.8
145°	469.2	492.8	517.8	541.3	552.3	563.4	581.6	594.5	602.1	604.4	602.1
147.5°	464.7	485.2	505.7	524.6	533.0	541.3	557.3	567.9	573.2	574.8	573.2
150°	458.6	476.8	493.5	509.5	516.3	523.1	534.5	543.6	548.2	548.9	548.2
152.5°	453.3	468.5	483.6	496.5	502.2	507.9	516.3	523.9	526.9	526.9	526.9
155°	446.4	460.9	473.0	484.4	488.6	492.8	501.1	506.4	509.5	507.9	509.5
157.5°	440.4	451.8	462.4	472.3	475.7	479.1	485.2	489.7	491.2	491.2	491.2
160°	433.5	443.4	451.8	460.1	462.8	465.4	470.7	474.5	475.3	475.3	475.3
162.5°	427.5	435.0	441.9	448.7	450.6	452.5	457.8	460.1	460.9	460.1	460.9
165°	420.6	426.7	432.0	437.3	438.8	440.4	443.4	446.4	446.4	445.7	446.4
167.5°	413.8	418.3	422.9	426.7	428.2	429.7	431.3	432.8	432.8	432.0	432.8
170°	408.5	412.3	414.5	417.6	418.4	419.1	419.9	422.1	421.4	419.9	421.4
172.5°	403.2	405.4	407.0	409.2	409.6	410.0	410.8	411.5	410.8	410.0	410.8
175°	398.6	400.9	401.6	402.4	402.8	403.2	403.2	403.9	403.2	401.6	403.2
177.5°	395.6	397.1	397.1	397.8	397.8	397.8	397.8	397.8	397.1	395.6	397.1
180°	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1121.8	1116.7	1115.2	1116.7	1115.2	1115.9	1110.7	1091.5	1096.7	1088.6	1093.0
5°	1185.4	1181.0	1171.4	1169.9	1168.4	1167.0	1159.6	1142.5	1135.9	1124.8	1124.1
7.5°	1246.1	1246.1	1238.7	1233.5	1226.9	1221.7	1212.1	1186.9	1176.6	1163.3	1155.9
10°	1306.0	1286.8	1294.9	1289.7	1273.4	1270.5	1252.7	1237.9	1218.0	1204.7	1192.8
12.5°	1348.9	1343.0	1335.6	1331.1	1326.7	1317.1	1305.2	1267.5	1257.2	1230.6	1217.2
15°	1347.4	1343.7	1345.9	1345.9	1344.4	1342.2	1332.6	1305.2	1287.5	1261.6	1238.7
17.5°	1274.9	1284.5	1294.1	1300.8	1315.6	1322.2	1331.1	1314.9	1303.8	1281.6	1257.2
20°	1148.5	1172.1	1200.2	1206.1	1219.5	1258.7	1276.4	1290.5	1294.9	1287.5	1267.5
22.5°	972.5	992.4	1060.5	1059.0	1078.2	1124.8	1176.6	1218.7	1252.0	1270.5	1263.1
25°	761.7	789.8	826.0	853.4	916.3	985.8	1050.1	1117.4	1175.1	1226.1	1238.7
27.5°	576.1	613.1	641.9	678.1	709.9	792.0	874.8	979.9	1047.2	1144.0	1194.3
30°	465.9	482.9	511.7	528.8	544.3	607.1	701.1	804.6	922.9	1034.6	1121.1
32.5°	397.9	409.7	431.1	438.5	454.8	497.0	556.1	650.8	772.8	908.1	1022.0
35°	357.2	369.8	374.2	380.8	394.2	420.8	461.5	530.2	640.4	772.8	908.9
37.5°	322.4	329.1	341.7	346.1	350.5	370.5	397.9	445.9	519.1	627.8	778.7
40°	298.0	301.7	308.4	312.1	315.0	329.1	353.5	386.0	440.0	522.8	661.9
42.5°	272.1	276.6	281.0	285.5	289.1	300.2	315.0	346.1	382.3	445.2	545.8
45°	247.0	250.0	255.1	258.1	263.3	272.1	285.5	306.9	339.4	379.4	460.7
47.5°	224.1	227.8	230.0	233.7	237.4	247.0	259.6	273.6	300.2	339.4	398.6
50°	203.4	207.8	210.8	211.5	214.5	223.3	233.7	249.2	266.2	296.5	348.3
52.5°	188.6	189.3	191.5	194.5	193.8	198.9	208.5	220.4	238.1	262.5	300.2
55°	171.6	173.8	175.3	176.0	176.0	180.4	185.6	196.7	210.8	230.7	262.5
57.5°	150.1	152.3	156.8	158.3	160.5	162.7	164.9	172.3	184.1	203.4	229.2
60°	127.9	129.4	133.9	136.8	138.3	144.2	147.2	153.1	159.7	173.8	198.2
62.5°	102.8	104.3	106.5	109.4	112.4	121.3	128.7	134.6	139.8	149.4	169.3
65°	89.5	90.2	91.7	92.4	93.2	96.9	103.5	111.7	121.3	128.7	140.5
67.5°	77.6	78.4	79.1	80.6	81.3	82.1	85.0	87.3	96.9	107.2	116.1
70°	66.6	68.0	68.8	68.8	69.5	71.0	72.5	75.4	78.4	83.6	94.7
72.5°	56.2	56.9	58.4	58.4	58.4	59.9	61.4	62.9	64.3	67.3	71.7
75°	46.6	48.1	48.1	48.1	48.8	48.8	50.3	51.8	53.2	55.5	56.9
77.5°	38.5	38.5	38.5	38.5	39.2	39.2	39.9	41.4	42.2	42.9	44.4
80°	28.8	29.6	29.6	29.6	30.3	30.3	30.3	31.8	32.5	32.5	34.0
82.5°	21.4	21.4	21.4	22.2	21.4	22.2	22.2	22.9	22.2	22.9	23.7
85°	13.3	13.3	13.3	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.8
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	25.1	25.1	25.1	24.7	24.3	22.8	24.3	25.1	25.8	25.1	20.5
92.5°	47.1	50.1	50.9	53.9	56.9	65.3	76.7	97.9	116.9	115.4	89.6
95°	88.1	94.1	104.0	112.4	120.7	152.6	198.9	260.4	297.6	263.5	175.4
97.5°	157.9	173.1	202.7	225.5	248.3	325.0	407.0	489.0	485.2	375.1	233.1
100°	307.5	340.1	403.2	449.1	495.0	599.0	693.2	709.1	599.8	413.0	249.0
102.5°	578.5	640.0	709.9	759.2	808.6	877.7	880.7	791.1	603.6	398.6	249.8
105°	899.0	946.0	993.1	1005.6	1018.2	1008.3	922.5	764.6	562.6	378.9	253.6
107.5°	1102.4	1109.3	1110.0	1094.8	1079.7	1005.2	877.7	708.4	524.6	368.2	261.9
110°	1158.6	1144.2	1111.5	1080.4	1049.3	952.1	816.2	656.0	498.8	365.2	272.6

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1143.4	1116.9	1068.3	1031.4	994.6	889.1	760.0	619.5	482.1	366.0	284.0
115°	1099.4	1064.5	1010.6	971.5	932.4	832.9	716.0	590.7	470.7	369.0	295.3
117.5°	1044.0	1006.8	951.3	914.1	876.9	784.3	679.5	571.0	464.7	373.6	307.5
120°	986.3	950.6	897.4	862.8	828.3	747.9	653.7	555.8	459.3	378.1	319.6
122.5°	934.6	899.7	853.4	823.0	792.7	717.5	633.2	542.9	456.3	383.4	330.3
125°	888.3	859.5	815.4	787.0	758.5	691.7	613.5	530.7	452.5	388.7	341.7
127.5°	848.8	821.5	782.8	756.2	729.6	665.9	593.7	519.3	450.2	394.1	352.3
130°	813.2	787.3	750.1	725.0	700.0	640.0	574.8	507.9	448.7	400.1	362.2
132.5°	778.2	752.4	716.0	692.8	669.7	615.8	556.5	498.8	448.0	406.2	372.0
135°	740.3	715.2	682.6	661.3	640.0	589.9	539.8	490.5	447.2	410.8	380.4
137.5°	701.5	679.5	648.4	629.4	610.4	569.4	526.2	484.4	447.2	415.3	387.2
140°	662.1	642.3	618.0	601.3	584.6	549.7	513.3	479.1	446.4	418.3	392.5
142.5°	627.9	610.4	587.7	574.4	561.1	532.2	502.6	473.8	446.4	420.6	397.1
145°	594.5	581.6	563.4	552.3	541.3	517.8	492.8	469.2	444.9	422.1	400.9
147.5°	567.9	557.3	541.3	533.0	524.6	505.7	485.2	464.7	442.6	422.9	403.2
150°	543.6	534.5	523.1	516.3	509.5	493.5	476.8	458.6	440.4	422.1	404.7
152.5°	523.9	516.3	507.9	502.2	496.5	483.6	468.5	453.3	436.6	420.6	405.4
155°	506.4	501.1	492.8	488.6	484.4	473.0	460.9	446.4	432.0	419.1	406.2
157.5°	489.7	485.2	479.1	475.7	472.3	462.4	451.8	440.4	427.5	416.1	406.2
160°	474.5	470.7	465.4	462.8	460.1	451.8	443.4	433.5	422.9	413.8	406.2
162.5°	460.1	457.8	452.5	450.6	448.7	441.9	435.0	427.5	419.1	411.5	405.4
165°	446.4	443.4	440.4	438.8	437.3	432.0	426.7	420.6	413.8	408.5	403.9
167.5°	432.8	431.3	429.7	428.2	426.7	422.9	418.3	413.8	409.2	405.4	403.2
170°	422.1	419.9	419.1	418.4	417.6	414.5	412.3	408.5	405.4	403.2	401.6
172.5°	411.5	410.8	410.0	409.6	409.2	407.0	405.4	403.2	400.9	400.1	399.4
175°	403.9	403.2	403.2	402.8	402.4	401.6	400.9	398.6	397.8	397.1	397.8
177.5°	397.8	397.8	397.8	397.8	397.8	397.1	397.1	395.6	394.8	395.6	397.1
180°	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1086.3	1082.6	1082.6	1080.4	1080.4	1068.6	1068.6	1072.3	1067.9	1062.7	1055.3
5°	1114.4	1106.3	1104.1	1101.1	1091.5	1076.7	1070.8	1068.6	1059.7	1048.6	1036.1
7.5°	1141.1	1127.8	1121.1	1114.4	1101.9	1081.2	1069.3	1061.2	1047.9	1030.9	1014.6
10°	1167.0	1149.9	1132.9	1124.8	1107.1	1081.2	1064.2	1050.8	1031.6	1008.7	985.8
12.5°	1190.6	1155.1	1152.2	1135.9	1110.0	1080.4	1054.5	1035.3	1010.9	984.3	957.7
15°	1211.3	1175.1	1157.3	1142.5	1108.5	1071.6	1044.2	1020.5	988.0	957.7	925.1
17.5°	1221.7	1182.5	1170.6	1146.2	1111.5	1063.4	1026.4	997.6	962.1	925.9	888.9
20°	1232.0	1186.2	1167.0	1149.9	1102.6	1047.9	1006.5	973.2	934.0	891.1	850.4
22.5°	1237.2	1186.2	1163.3	1139.6	1093.7	1030.9	982.1	942.9	897.0	853.4	804.6
25°	1228.3	1181.7	1154.4	1130.0	1078.2	1010.2	954.0	909.6	860.8	811.2	761.7
27.5°	1206.1	1171.4	1139.6	1114.4	1056.8	983.6	924.4	874.1	823.8	768.4	718.1
30°	1164.7	1149.2	1124.1	1096.0	1033.1	959.9	889.6	837.9	782.4	726.9	674.4
32.5°	1100.4	1113.7	1097.4	1073.0	1005.0	927.3	852.7	800.2	739.5	679.6	631.5
35°	1022.0	1069.3	1060.5	1043.5	975.4	892.6	817.9	754.3	693.7	633.0	585.0
37.5°	936.2	1008.0	1015.4	1005.0	941.4	857.1	775.0	712.9	650.8	589.4	540.6
40°	818.6	928.8	952.5	956.9	905.9	814.2	728.4	667.8	606.4	546.5	487.3
42.5°	710.7	849.7	879.3	897.8	860.8	772.1	685.5	618.2	557.6	503.6	444.4
45°	609.4	754.3	802.4	826.0	809.8	724.0	634.5	571.6	516.2	466.6	409.7
47.5°	505.1	650.8	718.1	755.8	755.8	675.2	585.7	523.6	470.3	428.2	377.9
50°	435.6	556.9	626.4	675.9	689.2	625.6	541.3	480.7	430.4	384.5	346.1
52.5°	371.2	479.9	537.6	589.4	627.8	572.4	491.8	437.1	387.5	344.6	314.3
55°	320.9	402.3	454.8	511.7	554.6	518.4	443.7	390.5	347.6	312.1	286.2
57.5°	272.9	343.9	386.8	437.1	482.9	455.5	395.6	349.8	312.1	281.0	258.1
60°	232.2	289.9	323.2	362.4	419.3	400.1	350.5	308.4	278.1	250.0	230.7
62.5°	197.5	243.3	271.4	299.5	351.3	342.4	303.9	271.4	245.5	221.9	205.6
65°	162.0	199.7	221.9	246.3	287.7	291.4	260.3	237.4	213.7	193.0	178.2
67.5°	130.9	160.5	180.4	201.1	234.4	244.8	223.3	204.1	184.1	167.1	153.8
70°	105.8	126.5	141.2	157.5	184.9	197.5	186.4	173.0	156.8	142.7	130.9
72.5°	83.6	96.9	105.8	118.3	140.5	153.1	152.3	140.5	128.7	119.1	109.4
75°	61.4	71.7	79.1	87.3	105.0	116.8	119.8	114.6	102.8	95.4	88.0
77.5°	46.6	52.5	56.2	62.1	74.7	85.0	89.5	88.0	79.9	74.0	68.8
80°	35.5	37.0	38.5	40.7	51.0	60.6	63.6	62.9	58.4	56.2	50.3
82.5°	25.1	25.9	26.6	27.4	31.1	39.2	42.2	43.6	39.9	37.7	32.5
85°	14.8	15.5	15.5	17.0	17.7	20.0	25.1	25.1	24.4	21.4	20.7
87.5°	7.4	7.4	6.7	6.7	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	15.2	11.4	10.2	9.1	7.6	6.1	3.0	0.8	3.0	6.1	7.6
92.5°	60.7	40.2	36.0	31.9	25.8	22.0	15.9	11.4	15.9	22.0	25.8
95°	109.3	74.4	65.3	56.2	44.0	37.2	29.6	26.6	29.6	37.2	44.0
97.5°	141.2	96.4	86.2	75.9	62.3	52.4	44.0	39.5	44.0	52.4	62.3
100°	156.4	116.2	105.6	94.9	79.7	67.6	60.7	58.5	60.7	67.6	79.7
102.5°	170.1	133.6	123.0	112.4	96.4	84.3	77.4	75.9	77.4	84.3	96.4
105°	186.0	150.3	139.7	129.1	112.4	101.0	95.7	92.6	95.7	101.0	112.4
107.5°	202.0	167.0	156.4	145.8	129.1	118.4	113.1	110.9	113.1	118.4	129.1
110°	217.9	184.5	173.5	162.5	146.5	136.7	132.1	129.1	132.1	136.7	146.5

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	233.1	201.2	189.8	178.4	163.2	154.1	148.8	145.8	148.8	154.1	163.2
115°	249.0	216.4	206.2	195.9	180.7	171.6	167.0	163.2	167.0	171.6	180.7
117.5°	263.5	233.1	222.4	211.8	197.4	189.1	184.5	181.5	184.5	189.1	197.4
120°	278.6	249.0	238.4	227.8	212.6	205.8	201.2	198.2	201.2	205.8	212.6
122.5°	293.1	265.7	254.7	243.7	228.5	220.9	216.4	214.1	216.4	220.9	228.5
125°	307.5	280.2	269.5	258.9	243.7	234.6	230.1	227.8	230.1	234.6	243.7
127.5°	321.2	294.6	283.6	272.6	258.1	248.3	242.2	239.2	242.2	248.3	258.1
130°	333.3	306.7	296.1	285.5	270.3	259.7	252.1	249.0	252.1	259.7	270.3
132.5°	343.9	318.9	308.2	297.6	281.7	270.3	261.9	258.1	261.9	270.3	281.7
135°	353.8	329.5	318.9	308.3	290.8	279.4	270.3	267.3	270.3	279.4	290.8
137.5°	362.2	337.9	328.0	318.1	300.7	288.5	279.4	275.6	279.4	288.5	300.7
140°	369.0	346.2	336.4	326.5	309.8	297.6	288.5	285.5	288.5	297.6	309.8
142.5°	374.3	352.3	343.2	334.1	318.1	306.0	297.6	295.3	297.6	306.0	318.1
145°	379.6	359.1	350.8	342.4	327.2	315.8	308.3	305.2	308.3	315.8	327.2
147.5°	384.2	364.4	356.8	349.3	336.3	325.7	318.1	315.8	318.1	325.7	336.3
150°	387.2	369.8	363.0	356.1	344.7	334.8	328.8	326.5	328.8	334.8	344.7
152.5°	390.3	375.1	369.0	362.9	352.3	343.9	337.9	337.1	337.9	343.9	352.3
155°	393.3	380.4	374.7	369.0	360.6	352.3	347.7	347.0	347.7	352.3	360.6
157.5°	395.6	384.2	379.2	374.3	367.5	359.9	356.1	355.3	356.1	359.9	367.5
160°	397.1	388.0	383.8	379.6	373.6	367.5	364.4	363.7	364.4	367.5	373.6
162.5°	397.8	390.3	387.2	384.2	378.9	374.3	371.3	372.0	371.3	374.3	378.9
165°	398.6	391.8	389.5	387.2	383.4	378.9	377.3	378.1	377.3	378.9	383.4
167.5°	398.6	393.3	391.8	390.3	387.2	384.2	382.7	383.4	382.7	384.2	387.2
170°	397.8	394.1	393.0	391.8	390.3	388.0	387.2	388.7	387.2	388.0	390.3
172.5°	397.1	394.8	394.0	393.3	392.5	390.3	391.0	391.8	391.0	390.3	392.5
175°	396.3	394.8	394.5	394.1	394.1	392.5	393.3	394.1	393.3	392.5	394.1
177.5°	395.6	394.8	394.8	394.8	394.8	393.3	394.1	395.6	394.1	393.3	394.8
180°	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1052.3	1053.1	1055.3	1048.6	1038.3	1033.8	1020.5	1018.3	1016.1	1016.1	1018.3
5°	1028.7	1025.7	1026.4	1013.9	999.1	990.2	971.7	974.7	965.1	959.1	960.6
7.5°	1002.8	994.6	993.9	977.6	959.1	942.9	923.7	919.2	910.3	900.0	895.6
10°	970.2	964.3	953.2	934.7	911.1	897.8	871.9	856.4	854.1	838.6	832.7
12.5°	937.0	926.6	915.5	889.6	863.0	841.6	822.3	805.3	793.5	780.2	771.3
15°	898.5	885.9	873.4	846.0	814.9	793.5	764.7	739.5	704.8	677.4	661.9
17.5°	856.4	842.3	825.3	795.0	764.7	735.1	681.8	652.3	627.8	611.6	602.0
20°	812.7	797.2	780.2	749.9	697.4	645.6	616.0	593.1	578.3	562.0	550.2
22.5°	766.9	750.6	732.1	684.8	629.3	593.1	570.2	548.7	527.3	518.4	512.5
25°	724.0	709.2	685.5	621.2	577.6	544.3	518.4	504.3	493.3	481.4	470.3
27.5°	679.6	652.3	619.0	565.0	537.6	503.6	485.1	474.8	455.5	447.4	442.2
30°	626.4	596.0	564.2	525.8	494.0	470.3	453.3	436.3	425.2	417.1	408.2
32.5°	572.4	543.5	523.6	483.6	460.0	435.6	419.3	409.0	392.7	387.5	383.8
35°	525.8	501.4	483.6	451.1	428.9	406.7	394.9	379.4	369.0	359.4	353.5
37.5°	479.9	466.6	448.1	420.8	397.1	379.4	363.1	357.9	343.9	338.7	332.8
40°	448.1	428.2	412.6	389.0	369.0	349.8	339.4	327.6	318.0	309.9	307.6
42.5°	409.7	394.9	386.0	360.1	339.4	328.3	315.8	302.5	295.1	288.4	280.3
45°	380.8	367.5	355.0	334.3	315.8	301.7	290.6	281.8	269.2	266.2	253.7
47.5°	350.5	337.2	327.6	306.9	289.9	276.6	268.4	256.6	246.3	239.6	233.7
50°	320.2	309.1	300.2	282.5	267.7	253.7	242.6	230.7	226.3	215.2	211.5
52.5°	291.4	284.0	274.4	257.4	242.6	230.7	218.9	209.3	202.6	196.7	192.3
55°	267.0	255.1	250.7	232.2	219.6	207.1	196.7	190.8	182.7	179.0	175.3
57.5°	239.6	232.9	225.6	211.5	197.5	185.6	178.2	169.3	164.9	160.5	157.5
60°	215.9	206.3	200.4	188.6	176.0	164.9	158.3	151.6	145.7	142.0	136.1
62.5°	188.6	181.2	177.5	164.9	154.6	144.2	138.3	131.6	127.2	120.5	113.1
65°	164.9	159.0	154.6	144.2	134.6	125.0	119.1	110.9	105.0	101.3	100.6
67.5°	144.2	139.8	133.1	123.5	113.9	106.5	99.8	93.2	92.4	91.0	91.0
70°	121.3	116.8	113.1	102.8	94.7	86.5	85.0	82.8	80.6	79.9	78.4
72.5°	101.3	97.6	93.2	84.3	76.2	74.0	72.5	71.0	68.8	68.0	67.3
75°	82.1	76.9	74.0	65.8	63.6	62.1	60.6	58.4	56.9	56.2	54.7
77.5°	62.9	57.7	57.7	53.2	51.8	49.5	48.1	46.6	45.8	44.4	44.4
80°	44.4	44.4	42.9	40.7	38.5	37.7	35.5	34.8	34.0	34.8	33.3
82.5°	32.5	29.6	29.6	28.1	26.6	25.9	24.4	24.4	23.7	23.7	23.7
85°	18.5	18.5	17.7	16.3	15.5	15.5	14.8	14.8	14.1	14.1	13.3
87.5°	7.4	6.7	7.4	6.7	6.7	5.9	5.9	5.9	5.2	5.9	5.2
90°	9.1	10.2	11.4	15.2	20.5	25.1	25.8	25.1	24.3	22.8	24.3
92.5°	31.9	36.0	40.2	60.7	89.6	115.4	116.9	97.9	76.7	65.3	56.9
95°	56.2	65.3	74.4	109.3	175.4	263.5	297.6	260.4	198.9	152.6	120.7
97.5°	75.9	86.2	96.4	141.2	233.1	375.1	485.2	489.0	407.0	325.0	248.3
100°	94.9	105.6	116.2	156.4	249.0	413.0	599.8	709.1	693.2	599.0	495.0
102.5°	112.4	123.0	133.6	170.1	249.8	398.6	603.6	791.1	880.7	877.7	808.6
105°	129.1	139.7	150.3	186.0	253.6	378.9	562.6	764.6	922.5	1008.3	1018.2
107.5°	145.8	156.4	167.0	202.0	261.9	368.2	524.6	708.4	877.7	1005.2	1079.7
110°	162.5	173.5	184.5	217.9	272.6	365.2	498.8	656.0	816.2	952.1	1049.3

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	178.4	189.8	201.2	233.1	284.0	366.0	482.1	619.5	760.0	889.1	994.6
115°	195.9	206.2	216.4	249.0	295.3	369.0	470.7	590.7	716.0	832.9	932.4
117.5°	211.8	222.4	233.1	263.5	307.5	373.6	464.7	571.0	679.5	784.3	876.9
120°	227.8	238.4	249.0	278.6	319.6	378.1	459.3	555.8	653.7	747.9	828.3
122.5°	243.7	254.7	265.7	293.1	330.3	383.4	456.3	542.9	633.2	717.5	792.7
125°	258.9	269.5	280.2	307.5	341.7	388.7	452.5	530.7	613.5	691.7	758.5
127.5°	272.6	283.6	294.6	321.2	352.3	394.1	450.2	519.3	593.7	665.9	729.6
130°	285.5	296.1	306.7	333.3	362.2	400.1	448.7	507.9	574.8	640.0	700.0
132.5°	297.6	308.2	318.9	343.9	372.0	406.2	448.0	498.8	556.5	615.8	669.7
135°	308.3	318.9	329.5	353.8	380.4	410.8	447.2	490.5	539.8	589.9	640.0
137.5°	318.1	328.0	337.9	362.2	387.2	415.3	447.2	484.4	526.2	569.4	610.4
140°	326.5	336.4	346.2	369.0	392.5	418.3	446.4	479.1	513.3	549.7	584.6
142.5°	334.1	343.2	352.3	374.3	397.1	420.6	446.4	473.8	502.6	532.2	561.1
145°	342.4	350.8	359.1	379.6	400.9	422.1	444.9	469.2	492.8	517.8	541.3
147.5°	349.3	356.8	364.4	384.2	403.2	422.9	442.6	464.7	485.2	505.7	524.6
150°	356.1	363.0	369.8	387.2	404.7	422.1	440.4	458.6	476.8	493.5	509.5
152.5°	362.9	369.0	375.1	390.3	405.4	420.6	436.6	453.3	468.5	483.6	496.5
155°	369.0	374.7	380.4	393.3	406.2	419.1	432.0	446.4	460.9	473.0	484.4
157.5°	374.3	379.2	384.2	395.6	406.2	416.1	427.5	440.4	451.8	462.4	472.3
160°	379.6	383.8	388.0	397.1	406.2	413.8	422.9	433.5	443.4	451.8	460.1
162.5°	384.2	387.2	390.3	397.8	405.4	411.5	419.1	427.5	435.0	441.9	448.7
165°	387.2	389.5	391.8	398.6	403.9	408.5	413.8	420.6	426.7	432.0	437.3
167.5°	390.3	391.8	393.3	398.6	403.2	405.4	409.2	413.8	418.3	422.9	426.7
170°	391.8	393.0	394.1	397.8	401.6	403.2	405.4	408.5	412.3	414.5	417.6
172.5°	393.3	394.0	394.8	397.1	399.4	400.1	400.9	403.2	405.4	407.0	409.2
175°	394.1	394.5	394.8	396.3	397.8	397.1	397.8	398.6	400.9	401.6	402.4
177.5°	394.8	394.8	394.8	395.6	397.1	395.6	394.8	395.6	397.1	397.1	397.8
180°	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1018.3	1016.8	1012.4	1013.9	1011.7	1011.7	1010.2	1010.2	1010.2	1013.9	1011.7
5°	962.8	957.7	952.5	950.3	948.1	945.8	945.8	945.1	951.8	950.3	956.2
7.5°	894.1	892.6	882.2	882.2	878.5	877.1	880.8	881.5	882.2	883.7	887.4
10°	832.7	829.0	814.2	815.7	813.5	810.5	812.7	811.2	816.4	817.9	816.4
12.5°	760.2	753.6	737.3	729.2	720.3	713.6	721.8	715.8	736.6	742.5	758.7
15°	664.1	651.5	640.4	640.4	632.3	626.4	630.1	636.7	641.2	647.8	650.8
17.5°	599.7	594.6	585.7	580.5	578.3	576.1	576.1	579.0	588.7	587.9	593.8
20°	545.0	542.1	537.6	531.0	528.8	527.3	527.3	527.3	533.9	539.8	543.5
22.5°	507.3	505.1	502.1	493.3	488.8	487.3	491.0	493.3	498.4	502.9	506.6
25°	469.6	464.4	459.2	456.3	454.1	454.1	455.5	456.3	458.5	460.7	465.2
27.5°	438.5	434.8	427.4	419.3	419.3	417.1	418.6	420.0	425.2	432.6	436.3
30°	403.8	403.0	400.1	397.1	394.2	392.7	395.6	397.9	398.6	402.3	402.3
32.5°	378.6	373.5	368.3	365.3	363.8	363.1	363.8	366.8	366.8	371.2	376.4
35°	353.5	350.5	345.4	340.2	338.7	335.0	338.0	340.9	346.1	348.3	350.5
37.5°	326.1	322.4	320.2	318.7	315.8	316.5	314.3	318.7	323.2	322.4	323.9
40°	305.4	298.8	292.1	291.4	290.6	289.9	289.9	290.6	293.6	296.5	301.0
42.5°	278.8	276.6	270.7	264.7	263.3	261.8	260.3	263.3	269.2	274.4	276.6
45°	251.4	248.5	247.0	242.6	239.6	238.9	237.4	241.1	246.3	248.5	250.0
47.5°	226.3	225.6	221.1	221.9	219.6	220.4	219.6	221.9	221.9	224.1	225.6
50°	209.3	207.1	204.8	203.4	201.1	201.1	200.4	201.1	204.1	207.1	206.3
52.5°	192.3	188.6	187.8	187.1	185.6	187.1	184.9	185.6	188.6	190.1	189.3
55°	172.3	171.6	170.1	168.6	167.9	167.1	167.1	167.1	170.1	172.3	173.0
57.5°	156.8	153.1	150.1	150.1	147.2	146.4	147.9	148.6	150.9	152.3	153.8
60°	135.3	133.9	129.4	127.2	122.8	122.0	122.0	125.0	128.7	133.9	135.3
62.5°	112.4	110.2	109.4	109.4	109.4	109.4	109.4	109.4	109.4	110.2	110.2
65°	99.8	100.6	99.8	99.1	99.8	99.8	99.1	99.1	99.1	99.8	100.6
67.5°	89.5	88.7	89.5	88.7	88.0	88.0	87.3	88.0	88.7	89.5	89.5
70°	77.6	77.6	76.9	77.6	76.9	76.2	75.4	75.4	76.9	77.6	77.6
72.5°	66.6	66.6	65.8	65.8	64.3	64.3	65.1	64.3	64.3	66.6	66.6
75°	55.5	54.7	54.0	54.0	53.2	53.2	53.2	52.5	54.0	54.0	54.7
77.5°	43.6	43.6	43.6	42.9	42.9	42.2	42.2	42.9	42.9	42.9	43.6
80°	33.3	33.3	33.3	32.5	31.8	31.8	31.8	31.8	31.8	32.5	31.8
82.5°	22.9	22.9	22.9	22.9	22.9	22.2	22.2	22.2	22.9	22.9	22.2
85°	14.1	13.3	14.1	14.1	13.3	14.1	13.3	13.3	12.6	12.6	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	24.7	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	24.7
92.5°	53.9	50.9	50.1	47.1	47.8	46.3	47.8	47.1	50.1	50.9	53.9
95°	112.4	104.0	94.1	88.1	85.8	86.6	85.8	88.1	94.1	104.0	112.4
97.5°	225.5	202.7	173.1	157.9	149.6	145.0	149.6	157.9	173.1	202.7	225.5
100°	449.1	403.2	340.1	307.5	285.5	271.8	285.5	307.5	340.1	403.2	449.1
102.5°	759.2	709.9	640.0	578.5	549.7	530.0	549.7	578.5	640.0	709.9	759.2
105°	1005.6	993.1	946.0	899.0	866.3	855.7	866.3	899.0	946.0	993.1	1005.6
107.5°	1094.8	1110.0	1109.3	1102.4	1092.6	1075.1	1092.6	1102.4	1109.3	1110.0	1094.8
110°	1080.4	1111.5	1144.2	1158.6	1165.4	1164.7	1165.4	1158.6	1144.2	1111.5	1080.4

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1031.4	1068.3	1116.9	1143.4	1157.9	1163.2	1157.9	1143.4	1116.9	1068.3	1031.4
115°	971.5	1010.6	1064.5	1099.4	1119.1	1126.0	1119.1	1099.4	1064.5	1010.6	971.5
117.5°	914.1	951.3	1006.8	1044.0	1064.5	1069.8	1064.5	1044.0	1006.8	951.3	914.1
120°	862.8	897.4	950.6	986.3	1008.3	1015.9	1008.3	986.3	950.6	897.4	862.8
122.5°	823.0	853.4	899.7	934.6	953.6	959.7	953.6	934.6	899.7	853.4	823.0
125°	787.0	815.4	859.5	888.3	907.3	913.4	907.3	888.3	859.5	815.4	787.0
127.5°	756.2	782.8	821.5	848.8	865.5	870.1	865.5	848.8	821.5	782.8	756.2
130°	725.0	750.1	787.3	813.2	828.3	834.4	828.3	813.2	787.3	750.1	725.0
132.5°	692.8	716.0	752.4	778.2	791.9	797.2	791.9	778.2	752.4	716.0	692.8
135°	661.3	682.6	715.2	740.3	753.9	757.0	753.9	740.3	715.2	682.6	661.3
137.5°	629.4	648.4	679.5	701.5	713.7	718.2	713.7	701.5	679.5	648.4	629.4
140°	601.3	618.0	642.3	662.1	673.5	678.0	673.5	662.1	642.3	618.0	601.3
142.5°	574.4	587.7	610.4	627.9	637.8	637.8	637.8	627.9	610.4	587.7	574.4
145°	552.3	563.4	581.6	594.5	602.1	604.4	602.1	594.5	581.6	563.4	552.3
147.5°	533.0	541.3	557.3	567.9	573.2	574.8	573.2	567.9	557.3	541.3	533.0
150°	516.3	523.1	534.5	543.6	548.2	548.9	548.2	543.6	534.5	523.1	516.3
152.5°	502.2	507.9	516.3	523.9	526.9	526.9	526.9	523.9	516.3	507.9	502.2
155°	488.6	492.8	501.1	506.4	509.5	507.9	509.5	506.4	501.1	492.8	488.6
157.5°	475.7	479.1	485.2	489.7	491.2	491.2	491.2	489.7	485.2	479.1	475.7
160°	462.8	465.4	470.7	474.5	475.3	475.3	475.3	474.5	470.7	465.4	462.8
162.5°	450.6	452.5	457.8	460.1	460.9	460.1	460.9	460.1	457.8	452.5	450.6
165°	438.8	440.4	443.4	446.4	446.4	445.7	446.4	446.4	443.4	440.4	438.8
167.5°	428.2	429.7	431.3	432.8	432.8	432.0	432.8	432.8	431.3	429.7	428.2
170°	418.4	419.1	419.9	422.1	421.4	419.9	421.4	422.1	419.9	419.1	418.4
172.5°	409.6	410.0	410.8	411.5	410.8	410.0	410.8	411.5	410.8	410.0	409.6
175°	402.8	403.2	403.2	403.9	403.2	401.6	403.2	403.9	403.2	403.2	402.8
177.5°	397.8	397.8	397.8	397.8	397.1	395.6	397.1	397.8	397.8	397.8	397.8
180°	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2	1064.2
2.5°	1013.9	1017.6	1016.1	1008.0	1016.1	1018.3	1022.7	1027.2	1030.1	1034.6	1038.3
5°	950.3	957.7	962.1	957.7	972.5	974.7	985.0	990.9	999.8	1007.2	1013.1
7.5°	890.4	896.3	905.2	906.6	915.5	925.9	940.7	955.5	969.5	976.9	983.6
10°	826.0	836.4	849.7	846.7	860.1	876.3	891.9	915.5	927.3	940.7	952.5
12.5°	761.7	768.4	786.1	792.0	811.2	823.8	845.3	860.1	889.6	905.2	915.5
15°	649.3	676.7	698.8	725.5	750.6	774.3	793.5	820.1	846.0	857.8	874.8
17.5°	598.3	610.8	624.1	637.5	670.0	712.2	746.2	775.0	797.2	812.7	832.7
20°	545.0	557.6	572.4	585.0	604.9	635.2	677.4	726.9	753.6	769.8	789.1
22.5°	507.3	519.1	528.8	539.8	555.4	577.6	609.4	670.7	706.2	726.2	743.2
25°	466.6	481.4	491.8	499.9	512.5	536.9	562.8	597.5	661.1	676.7	700.3
27.5°	438.5	443.0	454.8	467.4	479.9	493.3	519.9	549.5	592.4	626.4	655.2
30°	405.3	416.3	427.4	432.6	443.7	462.9	479.2	511.0	544.3	570.9	605.7
32.5°	380.1	386.8	394.2	406.7	417.1	430.4	446.7	473.3	501.4	518.4	545.0
35°	352.0	356.4	372.0	377.2	387.5	400.8	417.1	437.8	468.1	481.4	500.7
37.5°	325.4	335.7	340.2	352.0	361.6	374.9	386.8	410.4	430.4	445.9	463.7
40°	304.7	309.1	317.3	327.6	335.7	346.1	360.9	377.9	399.3	411.9	427.4
42.5°	279.5	283.2	293.6	299.5	312.8	322.4	331.3	352.0	371.2	380.8	396.4
45°	252.2	261.0	267.7	279.5	286.9	298.8	309.9	324.6	342.4	353.5	362.4
47.5°	228.5	237.4	244.0	255.1	267.0	272.1	284.0	299.5	315.8	324.6	337.2
50°	209.3	212.2	224.8	230.0	242.6	252.9	261.0	274.4	292.1	297.3	307.6
52.5°	190.8	193.0	201.1	207.8	218.9	227.8	238.1	250.7	265.5	273.6	281.8
55°	174.5	176.0	179.7	187.1	194.5	205.6	215.2	227.0	239.6	248.5	255.9
57.5°	156.0	159.0	162.0	166.4	173.8	184.1	194.5	205.6	215.9	221.9	231.5
60°	134.6	139.0	144.2	149.4	154.6	162.0	173.8	184.1	193.8	198.9	206.3
62.5°	111.7	120.5	125.0	130.9	135.3	142.0	150.9	162.7	169.3	176.0	181.9
65°	100.6	101.3	102.1	108.0	116.1	122.8	130.9	139.8	150.1	154.6	159.0
67.5°	89.5	90.2	91.7	92.4	95.4	102.8	111.7	121.3	129.4	132.4	136.8
70°	78.4	78.4	81.3	82.1	82.8	83.6	91.0	100.6	108.0	111.7	116.8
72.5°	66.6	67.3	68.8	69.5	71.0	72.5	74.7	79.9	88.7	92.4	98.4
75°	54.7	55.5	56.2	56.9	59.2	59.9	62.1	65.1	68.8	73.2	76.9
77.5°	43.6	43.6	44.4	45.8	47.3	48.1	50.3	51.8	53.2	55.5	58.4
80°	32.5	33.3	33.3	34.8	34.8	35.5	36.2	38.5	39.9	41.4	42.9
82.5°	22.2	23.7	23.7	23.7	24.4	25.1	25.9	25.9	27.4	28.1	30.3
85°	13.3	14.1	14.1	14.1	13.3	14.8	14.8	15.5	15.5	15.5	16.3
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.7	6.7
90°	24.3	22.8	24.3	25.1	25.8	25.1	20.5	15.2	11.4	10.2	9.1
92.5°	56.9	65.3	76.7	97.9	116.9	115.4	89.6	60.7	40.2	36.0	31.9
95°	120.7	152.6	198.9	260.4	297.6	263.5	175.4	109.3	74.4	65.3	56.2
97.5°	248.3	325.0	407.0	489.0	485.2	375.1	233.1	141.2	96.4	86.2	75.9
100°	495.0	599.0	693.2	709.1	599.8	413.0	249.0	156.4	116.2	105.6	94.9
102.5°	808.6	877.7	880.7	791.1	603.6	398.6	249.8	170.1	133.6	123.0	112.4
105°	1018.2	1008.3	922.5	764.6	562.6	378.9	253.6	186.0	150.3	139.7	129.1
107.5°	1079.7	1005.2	877.7	708.4	524.6	368.2	261.9	202.0	167.0	156.4	145.8
110°	1049.3	952.1	816.2	656.0	498.8	365.2	272.6	217.9	184.5	173.5	162.5

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	994.6	889.1	760.0	619.5	482.1	366.0	284.0	233.1	201.2	189.8	178.4
115°	932.4	832.9	716.0	590.7	470.7	369.0	295.3	249.0	216.4	206.2	195.9
117.5°	876.9	784.3	679.5	571.0	464.7	373.6	307.5	263.5	233.1	222.4	211.8
120°	828.3	747.9	653.7	555.8	459.3	378.1	319.6	278.6	249.0	238.4	227.8
122.5°	792.7	717.5	633.2	542.9	456.3	383.4	330.3	293.1	265.7	254.7	243.7
125°	758.5	691.7	613.5	530.7	452.5	388.7	341.7	307.5	280.2	269.5	258.9
127.5°	729.6	665.9	593.7	519.3	450.2	394.1	352.3	321.2	294.6	283.6	272.6
130°	700.0	640.0	574.8	507.9	448.7	400.1	362.2	333.3	306.7	296.1	285.5
132.5°	669.7	615.8	556.5	498.8	448.0	406.2	372.0	343.9	318.9	308.2	297.6
135°	640.0	589.9	539.8	490.5	447.2	410.8	380.4	353.8	329.5	318.9	308.3
137.5°	610.4	569.4	526.2	484.4	447.2	415.3	387.2	362.2	337.9	328.0	318.1
140°	584.6	549.7	513.3	479.1	446.4	418.3	392.5	369.0	346.2	336.4	326.5
142.5°	561.1	532.2	502.6	473.8	446.4	420.6	397.1	374.3	352.3	343.2	334.1
145°	541.3	517.8	492.8	469.2	444.9	422.1	400.9	379.6	359.1	350.8	342.4
147.5°	524.6	505.7	485.2	464.7	442.6	422.9	403.2	384.2	364.4	356.8	349.3
150°	509.5	493.5	476.8	458.6	440.4	422.1	404.7	387.2	369.8	363.0	356.1
152.5°	496.5	483.6	468.5	453.3	436.6	420.6	405.4	390.3	375.1	369.0	362.9
155°	484.4	473.0	460.9	446.4	432.0	419.1	406.2	393.3	380.4	374.7	369.0
157.5°	472.3	462.4	451.8	440.4	427.5	416.1	406.2	395.6	384.2	379.2	374.3
160°	460.1	451.8	443.4	433.5	422.9	413.8	406.2	397.1	388.0	383.8	379.6
162.5°	448.7	441.9	435.0	427.5	419.1	411.5	405.4	397.8	390.3	387.2	384.2
165°	437.3	432.0	426.7	420.6	413.8	408.5	403.9	398.6	391.8	389.5	387.2
167.5°	426.7	422.9	418.3	413.8	409.2	405.4	403.2	398.6	393.3	391.8	390.3
170°	417.6	414.5	412.3	408.5	405.4	403.2	401.6	397.8	394.1	393.0	391.8
172.5°	409.2	407.0	405.4	403.2	400.9	400.1	399.4	397.1	394.8	394.0	393.3
175°	402.4	401.6	400.9	398.6	397.8	397.1	397.8	396.3	394.8	394.5	394.1
177.5°	397.8	397.1	397.1	395.6	394.8	395.6	397.1	395.6	394.8	394.8	394.8
180°	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8	394.8

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1064.2	1064.2	1064.2	1064.2
2.5°	1044.9	1042.7	1056.0	1070.8
5°	1023.5	1027.2	1044.2	1064.9
7.5°	1001.3	1009.4	1029.4	1056.8
10°	970.2	985.0	1015.4	1043.5
12.5°	939.9	959.9	988.7	1022.0
15°	905.9	928.1	963.6	1003.5
17.5°	868.2	893.3	934.7	978.4
20°	828.3	861.5	905.2	952.5
22.5°	783.9	823.8	868.9	921.4
25°	741.0	784.6	829.7	890.4
27.5°	698.8	741.7	792.0	853.4
30°	656.7	695.9	749.9	815.7
32.5°	611.6	652.3	709.2	776.5
35°	570.2	610.8	664.1	730.6
37.5°	525.8	569.4	620.5	689.2
40°	474.0	525.1	574.6	640.4
42.5°	431.1	485.1	533.2	595.3
45°	397.1	448.1	488.1	548.7
47.5°	365.3	406.7	447.4	503.6
50°	335.0	366.8	409.0	459.2
52.5°	303.9	331.3	367.5	414.9
55°	275.8	301.7	334.3	370.5
57.5°	250.0	268.4	301.0	333.5
60°	221.1	240.3	265.5	292.8
62.5°	196.7	211.5	235.2	258.1
65°	170.8	184.9	202.6	224.1
67.5°	147.2	159.7	173.8	190.8
70°	125.7	135.3	145.7	160.5
72.5°	102.8	113.1	122.8	134.6
75°	84.3	88.7	96.9	105.0
77.5°	65.1	71.0	75.4	82.1
80°	46.6	51.8	53.2	58.4
82.5°	31.1	34.0	37.0	38.5
85°	17.7	19.2	22.2	22.9
87.5°	6.7	7.4	8.9	10.4
90°	7.6	6.1	3.0	0.8
92.5°	25.8	22.0	15.9	11.4
95°	44.0	37.2	29.6	26.6
97.5°	62.3	52.4	44.0	39.5
100°	79.7	67.6	60.7	58.5
102.5°	96.4	84.3	77.4	75.9
105°	112.4	101.0	95.7	92.6
107.5°	129.1	118.4	113.1	110.9
110°	146.5	136.7	132.1	129.1

TEST NUMBER: P999813

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	163.2	154.1	148.8	145.8
115°	180.7	171.6	167.0	163.2
117.5°	197.4	189.1	184.5	181.5
120°	212.6	205.8	201.2	198.2
122.5°	228.5	220.9	216.4	214.1
125°	243.7	234.6	230.1	227.8
127.5°	258.1	248.3	242.2	239.2
130°	270.3	259.7	252.1	249.0
132.5°	281.7	270.3	261.9	258.1
135°	290.8	279.4	270.3	267.3
137.5°	300.7	288.5	279.4	275.6
140°	309.8	297.6	288.5	285.5
142.5°	318.1	306.0	297.6	295.3
145°	327.2	315.8	308.3	305.2
147.5°	336.3	325.7	318.1	315.8
150°	344.7	334.8	328.8	326.5
152.5°	352.3	343.9	337.9	337.1
155°	360.6	352.3	347.7	347.0
157.5°	367.5	359.9	356.1	355.3
160°	373.6	367.5	364.4	363.7
162.5°	378.9	374.3	371.3	372.0
165°	383.4	378.9	377.3	378.1
167.5°	387.2	384.2	382.7	383.4
170°	390.3	388.0	387.2	388.7
172.5°	392.5	390.3	391.0	391.8
175°	394.1	392.5	393.3	394.1
177.5°	394.8	393.3	394.1	395.6
180°	394.8	394.8	394.8	394.8

(END OF REPORT)