

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999965

Luminaire Tested: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999965
REPORT IS A COMBINATION OF REPORTS P988522 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4643.0 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	55	54	53
2	92	85	79	74	85	79	74	70	68	65	62	59	56	54	50	48	46
3	84	75	68	63	78	70	64	60	61	57	53	53	49	47	45	42	40
4	78	67	60	54	72	63	57	51	55	50	46	48	44	41	41	38	36
5	72	61	53	47	67	57	50	45	50	45	40	43	39	36	37	34	32
6	66	55	47	42	62	52	45	40	45	40	36	40	35	32	34	31	29
7	62	50	42	37	57	47	40	35	42	36	32	36	32	29	32	28	26
8	57	46	38	33	54	43	36	32	38	33	29	34	29	26	29	26	24
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	22
10	50	39	32	27	47	37	30	26	33	28	24	29	25	22	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23476	23476	23476	23476
5°	23531	24936	23613	19921
10°	23273	26356	23438	16450
15°	22767	26365	23153	12359
20°	22160	21793	22641	10196
25°	21423	13618	21886	8673
30°	20483	8719	21040	7468
35°	19339	6701	19966	6390
40°	18063	5632	18837	5589
45°	16701	4794	17400	4692
50°	15305	4074	16020	4058
55°	13760	3540	14501	3493
60°	12384	2699	13042	2667
65°	11102	2031	11760	2304
70°	9688	1622	10446	1879
75°	8190	1242	8939	1420
80°	6499	845	6994	931
85°	4520	437	4944	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21476 cd/sqm

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.7	3.0
10°-20°	392.7	8.5
20°-30°	505.4	10.9
30°-40°	479.4	10.3
40°-50°	410.9	8.8
50°-60°	312.9	6.7
60°-70°	197.3	4.3
70°-80°	98.4	2.1
80°-90°	27.2	0.6
90°-100°	116.3	2.5
100°-110°	409.7	8.8
110°-120°	430.2	9.3
120°-130°	354.0	7.6
130°-140°	284.3	6.1
140°-150°	214.8	4.6
150°-160°	151.0	3.3
160°-170°	88.9	1.9
170°-180°	28.9	0.6
0°-30°	1038.7	22.4
0°-40°	1518.1	32.7
0°-60°	2241.9	48.3
0°-90°	2564.9	55.2
90°-120°	956.2	20.6
90°-150°	1809.3	39.0
90°-180°	2078.0	44.8
0°-180°	4643.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1483	1483	1483	1483	1483	
5°	1484	1650	1489	1318	1484	141
15°	1399	1862	1422	873	1399	393
25°	1241	994	1268	633	1241	570
35°	1018	490	1051	467	1018	637
45°	765	340	797	333	765	590
55°	516	236	544	233	516	465
65°	312	123	331	139	312	310
75°	146	65	160	74	146	158
85°	32	19	35	20	32	36
90°	1	19	1	19	1	3
95°	20	65	20	65	20	21
105°	70	647	70	647	70	74
115°	123	851	123	851	123	122
125°	172	690	172	690	172	153
135°	202	572	202	572	202	156
145°	231	457	231	457	231	145
155°	262	384	262	384	262	121
165°	286	337	286	337	286	81
175°	298	304	298	304	298	28
180°	298	298	298	298	298	

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1492.4	1498.6	1501.7	1505.8	1515.1	1521.2	1530.5	1532.6	1531.6	1535.7	1524.3
5°	1484.1	1497.5	1509.9	1520.2	1536.7	1547.0	1558.3	1571.7	1574.8	1590.3	1581.0
7.5°	1472.8	1492.4	1509.9	1530.5	1555.3	1568.7	1586.2	1606.8	1616.1	1634.6	1639.8
10°	1454.3	1482.1	1512.0	1533.6	1567.6	1591.3	1607.8	1640.8	1662.4	1690.3	1686.1
12.5°	1424.4	1460.4	1500.6	1536.7	1581.0	1596.5	1627.4	1661.4	1689.2	1715.0	1737.7
15°	1398.6	1439.8	1484.1	1528.5	1579.0	1607.8	1638.7	1683.1	1712.9	1758.3	1777.9
17.5°	1363.6	1416.1	1468.7	1518.2	1577.9	1610.9	1649.0	1692.3	1736.7	1779.9	1795.4
20°	1327.5	1384.2	1440.9	1507.8	1575.9	1607.8	1647.0	1700.6	1743.9	1777.9	1777.9
22.5°	1284.2	1353.2	1418.2	1482.1	1556.3	1602.7	1642.9	1705.7	1736.7	1743.9	1716.0
25°	1240.9	1310.0	1381.1	1460.4	1545.0	1586.2	1631.5	1690.3	1700.6	1671.7	1599.6
27.5°	1189.4	1266.7	1347.1	1432.6	1521.2	1572.8	1614.0	1653.2	1633.6	1556.3	1443.9
30°	1136.8	1220.3	1311.0	1392.4	1499.6	1547.0	1582.1	1593.4	1531.6	1405.8	1260.5
32.5°	1082.2	1163.6	1259.5	1357.4	1465.6	1510.9	1533.6	1503.7	1390.4	1231.6	1054.4
35°	1018.3	1110.0	1210.0	1312.0	1419.2	1453.2	1466.6	1393.4	1248.1	1043.0	866.8
37.5°	960.6	1052.3	1159.5	1263.6	1367.7	1386.2	1372.8	1258.4	1073.9	870.9	698.8
40°	892.5	990.5	1095.6	1212.0	1297.6	1302.7	1269.8	1121.4	892.5	701.9	595.7
42.5°	829.7	928.6	1033.7	1152.3	1217.2	1199.7	1155.4	960.6	745.2	605.0	519.4
45°	764.7	858.5	971.9	1077.0	1123.4	1082.2	1015.2	808.0	625.6	520.5	454.5
47.5°	701.9	789.5	901.8	1002.8	1011.1	964.7	885.3	677.1	542.1	457.6	404.0
50°	640.0	727.6	832.8	916.3	908.0	844.1	754.4	588.5	471.0	404.0	359.7
52.5°	578.2	657.6	759.6	825.6	790.5	728.7	640.0	498.8	411.2	352.5	318.5
55°	516.4	590.6	678.2	732.8	677.1	606.0	543.2	427.7	356.6	309.2	283.4
57.5°	464.8	523.6	604.0	636.9	570.0	514.3	459.7	367.9	309.2	275.2	245.3
60°	408.1	461.7	527.7	547.3	478.2	432.9	386.5	311.3	264.9	235.0	215.4
62.5°	359.7	404.0	454.5	454.5	393.7	359.7	324.7	260.8	222.6	198.9	189.6
65°	312.3	344.2	380.3	376.2	324.7	294.8	266.9	215.4	186.5	170.1	160.8
67.5°	265.9	290.6	314.3	299.9	262.8	237.1	211.3	174.2	154.6	143.3	130.9
70°	223.7	243.2	255.6	242.2	205.1	183.5	164.9	140.2	124.7	110.3	103.1
72.5°	187.6	195.8	199.9	183.5	152.5	140.2	126.8	109.2	95.9	88.6	86.6
75°	146.4	153.6	150.5	138.1	112.3	103.1	92.8	80.4	77.3	73.2	71.1
77.5°	114.4	114.4	109.2	97.9	80.4	73.2	69.1	62.9	59.8	58.7	56.7
80°	81.4	80.4	77.3	64.9	54.6	50.5	50.5	46.4	45.3	43.3	43.3
82.5°	53.6	53.6	49.5	39.2	36.1	35.0	34.0	32.0	32.0	30.9	30.9
85°	32.0	29.9	24.7	21.6	20.6	20.6	19.6	18.6	19.6	18.6	18.6
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.6	2.3	4.6	5.7	6.9	7.8	8.6	11.5	15.5	18.9	19.5
92.5°	8.6	12.1	16.6	19.5	24.1	27.2	30.4	45.9	67.7	87.2	88.4
95°	20.1	22.4	28.1	33.3	42.5	49.4	56.2	82.6	132.6	199.1	224.9
97.5°	29.8	33.3	39.6	47.1	57.4	65.2	72.9	106.7	176.2	283.5	366.7
100°	44.2	45.9	51.1	60.3	71.7	79.8	87.8	118.2	188.2	312.2	453.3
102.5°	57.4	58.5	63.7	72.9	84.9	93.0	101.0	128.5	188.8	301.3	456.2
105°	70.0	72.3	76.3	84.9	97.6	105.6	113.6	140.6	191.7	286.4	425.2
107.5°	83.8	85.5	89.5	97.6	110.2	118.2	126.2	152.6	198.0	278.3	396.5
110°	97.6	99.9	103.3	110.8	122.8	131.1	139.4	164.7	206.0	276.0	377.0

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	110.2	112.5	116.5	123.4	134.9	143.5	152.1	176.2	214.6	276.6	364.4
115°	123.4	126.2	129.7	136.6	148.1	155.8	163.5	188.2	223.2	278.9	355.8
117.5°	137.2	139.4	142.9	149.2	160.1	168.1	176.2	199.1	232.4	282.3	351.2
120°	149.8	152.1	155.5	160.7	172.2	180.2	188.2	210.6	241.6	285.8	347.2
122.5°	161.8	163.5	167.0	172.7	184.2	192.5	200.8	221.5	249.6	289.8	344.9
125°	172.2	173.9	177.3	184.2	195.7	203.8	211.8	232.4	258.2	293.8	342.0
127.5°	180.8	183.1	187.6	195.1	206.0	214.4	222.7	242.7	266.3	297.8	340.3
130°	188.2	190.5	196.3	204.3	215.8	223.8	231.8	251.9	273.7	302.4	339.1
132.5°	195.1	198.0	204.3	212.9	224.9	233.0	241.0	260.0	281.2	307.0	338.6
135°	202.0	204.3	211.2	219.8	233.0	241.0	249.1	267.4	287.5	310.5	338.0
137.5°	208.3	211.2	218.1	227.2	240.4	247.9	255.4	273.7	292.7	313.9	338.0
140°	215.8	218.1	224.9	234.1	246.8	254.2	261.7	278.9	296.7	316.2	337.4
142.5°	223.2	224.9	231.3	240.4	252.5	259.4	266.3	282.9	300.1	317.9	337.4
145°	230.7	233.0	238.7	247.3	258.8	265.1	271.4	286.9	303.0	319.1	336.3
147.5°	238.7	240.4	246.2	254.2	264.0	269.7	275.4	290.4	304.7	319.6	334.6
150°	246.8	248.5	253.1	260.5	269.1	274.3	279.5	292.7	305.9	319.1	332.8
152.5°	254.8	255.4	260.0	266.3	274.3	278.9	283.5	295.0	306.4	317.9	330.0
155°	262.2	262.8	266.3	272.6	278.9	283.2	287.5	297.3	307.0	316.8	326.5
157.5°	268.6	269.1	272.0	277.7	282.9	286.6	290.4	299.0	307.0	314.5	323.1
160°	274.9	275.4	277.7	282.3	286.9	290.0	293.2	300.1	307.0	312.7	319.6
162.5°	281.2	280.6	282.9	286.4	290.4	292.7	295.0	300.7	306.4	311.0	316.8
165°	285.8	285.2	286.4	289.8	292.7	294.4	296.1	301.3	305.3	308.7	312.7
167.5°	289.8	289.2	290.4	292.7	295.0	296.2	297.3	301.3	304.7	306.4	309.3
170°	293.8	292.7	293.2	295.0	296.1	297.0	297.8	300.7	303.6	304.7	306.4
172.5°	296.1	295.5	295.0	296.7	297.3	297.8	298.4	300.1	301.8	302.4	303.0
175°	297.8	297.3	296.7	297.8	297.8	298.1	298.4	299.6	300.7	300.1	300.7
177.5°	299.0	297.8	297.3	298.4	298.4	298.4	298.4	299.0	300.1	299.0	298.4
180°	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1535.7	1537.7	1540.8	1555.3	1557.3	1561.4	1559.4	1559.4	1560.4	1558.3	1559.4
5°	1601.6	1604.7	1620.2	1637.7	1641.8	1637.7	1642.9	1650.1	1650.1	1650.1	1648.0
7.5°	1663.5	1674.8	1692.3	1718.1	1723.3	1728.4	1737.7	1731.5	1733.6	1742.8	1739.7
10°	1723.3	1739.7	1759.3	1781.0	1792.3	1799.5	1803.6	1812.9	1834.6	1809.8	1819.1
12.5°	1779.9	1803.6	1824.3	1848.0	1856.2	1865.5	1868.6	1876.8	1876.8	1875.8	1883.0
15°	1817.0	1838.7	1857.2	1872.7	1874.8	1872.7	1870.6	1871.7	1874.8	1862.4	1869.6
17.5°	1825.3	1827.3	1833.5	1827.3	1828.4	1806.7	1794.4	1791.3	1762.4	1763.4	1787.2
20°	1785.1	1750.1	1740.8	1706.8	1686.1	1630.5	1628.4	1613.0	1552.2	1570.7	1566.6
22.5°	1674.8	1615.0	1535.7	1496.5	1476.9	1418.2	1372.8	1340.9	1319.2	1297.6	1288.3
25°	1529.5	1432.6	1320.3	1243.0	1231.6	1177.0	1093.5	1054.4	1008.0	993.6	1018.3
27.5°	1341.9	1216.2	1089.4	970.9	949.2	899.8	857.5	829.7	776.1	773.0	775.1
30°	1087.3	960.6	854.4	777.1	723.5	700.8	673.0	652.4	630.8	639.0	641.1
32.5°	893.6	773.0	674.0	632.8	608.1	593.7	570.0	556.6	547.3	544.2	543.2
35°	710.1	629.7	585.4	545.2	530.8	520.5	503.0	496.8	488.5	489.6	489.6
37.5°	608.1	541.1	508.1	487.5	474.1	468.9	457.6	451.4	446.3	444.2	447.3
40°	524.6	478.2	457.6	439.1	427.7	425.7	419.5	412.3	406.1	407.1	410.2
42.5°	463.8	437.0	412.3	397.8	389.6	386.5	381.3	376.2	376.2	373.1	372.1
45°	415.4	393.7	373.1	359.7	354.5	350.4	344.2	343.2	339.1	340.1	341.1
47.5°	372.1	354.5	339.1	325.7	320.5	319.5	313.3	309.2	309.2	308.2	307.1
50°	332.9	315.4	302.0	294.8	287.6	285.5	284.5	283.4	281.4	281.4	282.4
52.5°	301.0	283.4	273.1	266.9	262.8	260.8	260.8	259.7	259.7	259.7	258.7
55°	265.9	251.5	243.2	241.2	239.1	238.1	237.1	235.0	234.0	236.0	234.0
57.5°	232.9	227.8	220.6	218.5	213.3	213.3	210.3	208.2	206.1	208.2	208.2
60°	207.2	199.9	195.8	189.6	185.5	181.4	176.2	175.2	173.1	172.1	171.1
62.5°	180.4	174.2	163.9	154.6	148.4	144.3	142.2	141.2	141.2	140.2	140.2
65°	150.5	136.0	130.9	127.8	126.8	125.7	123.7	122.6	123.7	122.6	123.7
67.5°	117.5	115.4	112.3	110.3	109.2	108.2	108.2	107.2	107.2	107.2	107.2
70°	102.0	96.9	95.9	93.8	93.8	92.8	92.8	92.8	92.8	91.7	93.8
72.5°	84.5	81.4	80.4	79.4	79.4	79.4	78.3	78.3	78.3	77.3	78.3
75°	69.1	68.0	66.0	66.0	64.9	66.0	64.9	64.9	63.9	64.9	64.9
77.5°	55.7	54.6	53.6	53.6	52.6	52.6	52.6	52.6	52.6	52.6	53.6
80°	42.3	41.2	40.2	41.2	40.2	41.2	40.2	40.2	41.2	40.2	40.2
82.5°	30.9	29.9	29.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9
85°	18.6	17.5	17.5	18.6	17.5	18.6	17.5	17.5	17.5	18.6	18.6
87.5°	8.2	9.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.3
90°	18.9	18.4	17.2	18.4	18.6	18.9	18.9	18.9	18.9	18.9	18.9
92.5°	74.0	58.0	49.4	43.0	40.7	38.4	37.9	35.6	36.2	35.0	36.2
95°	196.8	150.3	115.3	91.2	84.9	78.6	71.2	66.6	64.8	65.4	64.8
97.5°	369.6	307.6	245.6	187.6	170.4	153.2	130.8	119.4	113.0	109.6	113.0
100°	536.0	523.9	452.8	374.2	339.4	304.7	257.1	232.4	215.8	205.4	215.8
102.5°	598.0	665.7	663.4	611.2	573.9	536.6	483.8	437.3	415.5	400.5	415.5
105°	577.9	697.2	762.1	769.5	760.0	750.6	715.0	679.4	654.8	646.7	654.8
107.5°	535.4	663.4	759.8	816.0	827.5	839.0	838.4	833.2	825.8	812.6	825.8
110°	495.8	616.9	719.6	793.1	816.6	840.1	864.8	875.7	880.9	880.3	880.9

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	468.3	574.4	672.0	751.7	779.6	807.4	844.1	864.2	875.1	879.1	875.1
115°	446.5	541.1	629.5	704.7	734.2	763.8	804.5	830.9	845.9	851.0	845.9
117.5°	431.5	513.6	592.8	662.8	690.9	719.0	760.9	789.0	804.5	808.6	804.5
120°	420.1	494.1	565.2	626.1	652.2	678.3	718.5	745.4	762.1	767.8	762.1
122.5°	410.3	478.6	542.3	599.1	622.0	645.0	680.0	706.4	720.8	725.3	720.8
125°	401.1	463.7	522.8	573.3	594.8	616.3	649.6	671.4	685.8	690.3	685.8
127.5°	392.5	448.8	503.3	551.5	571.6	591.6	620.9	641.6	654.2	657.6	654.2
130°	383.9	434.4	483.8	529.1	548.0	567.0	595.1	614.6	626.1	630.7	626.1
132.5°	377.0	420.6	465.4	506.1	523.6	541.1	568.7	588.2	598.5	602.5	598.5
135°	370.7	408.0	445.9	483.8	499.8	515.9	540.6	559.5	569.8	572.1	569.8
137.5°	366.1	397.7	430.4	461.4	475.8	490.1	513.6	530.2	539.4	542.9	539.4
140°	362.1	387.9	415.5	441.9	454.5	467.1	485.5	500.4	509.0	512.4	509.0
142.5°	358.1	379.9	402.3	424.1	434.2	444.2	461.4	474.6	482.0	482.0	482.0
145°	354.6	372.4	391.4	409.2	417.5	425.8	439.6	449.3	455.1	456.8	455.1
147.5°	351.2	366.7	382.2	396.5	402.8	409.2	421.2	429.2	433.3	434.4	433.3
150°	346.6	360.4	373.0	385.1	390.2	395.4	404.0	410.9	414.3	414.9	414.3
152.5°	342.6	354.1	365.5	375.3	379.6	383.9	390.2	396.0	398.3	398.3	398.3
155°	337.4	348.3	357.5	366.1	369.2	372.4	378.7	382.8	385.1	383.9	385.1
157.5°	332.8	341.4	349.5	356.9	359.5	362.1	366.7	370.1	371.3	371.3	371.3
160°	327.7	335.1	341.4	347.8	349.8	351.8	355.8	358.7	359.2	359.2	359.2
162.5°	323.1	328.8	334.0	339.1	340.6	342.0	346.0	347.8	348.3	347.8	348.3
165°	317.9	322.5	326.5	330.5	331.6	332.8	335.1	337.4	337.4	336.9	337.4
167.5°	312.7	316.2	319.6	322.5	323.6	324.8	325.9	327.1	327.1	326.5	327.1
170°	308.7	311.6	313.3	315.6	316.2	316.8	317.3	319.1	318.5	317.3	318.5
172.5°	304.7	306.4	307.6	309.3	309.6	309.9	310.5	311.0	310.5	309.9	310.5
175°	301.3	303.0	303.6	304.1	304.4	304.7	304.7	305.3	304.7	303.6	304.7
177.5°	299.0	300.1	300.1	300.7	300.7	300.7	300.7	300.7	300.1	299.0	300.1
180°	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1563.5	1556.3	1554.2	1556.3	1554.2	1555.3	1548.0	1521.2	1528.5	1517.1	1523.3
5°	1652.1	1646.0	1632.6	1630.5	1628.4	1626.4	1616.1	1592.4	1583.1	1567.6	1566.6
7.5°	1736.7	1736.7	1726.3	1719.1	1709.9	1702.6	1689.2	1654.2	1639.8	1621.2	1610.9
10°	1820.1	1793.3	1804.7	1797.5	1774.8	1770.7	1745.9	1725.3	1697.5	1678.9	1662.4
12.5°	1879.9	1871.7	1861.4	1855.2	1849.0	1835.6	1819.1	1766.5	1752.1	1715.0	1696.5
15°	1877.9	1872.7	1875.8	1875.8	1873.7	1870.6	1857.2	1819.1	1794.4	1758.3	1726.3
17.5°	1776.8	1790.2	1803.6	1812.9	1833.5	1842.8	1855.2	1832.5	1817.0	1786.1	1752.1
20°	1600.6	1633.6	1672.8	1681.0	1699.5	1754.2	1778.9	1798.5	1804.7	1794.4	1766.5
22.5°	1355.3	1383.1	1478.0	1475.9	1502.7	1567.6	1639.8	1698.5	1744.9	1770.7	1760.4
25°	1061.6	1100.7	1151.2	1189.4	1277.0	1373.9	1463.5	1557.3	1637.7	1708.8	1726.3
27.5°	802.9	854.4	894.6	945.1	989.4	1103.8	1219.3	1365.6	1459.4	1594.4	1664.5
30°	649.3	673.0	713.2	736.9	758.6	846.2	977.1	1121.4	1286.3	1441.9	1562.5
32.5°	554.5	571.0	600.9	611.2	633.9	692.6	775.1	907.0	1077.0	1265.6	1424.4
35°	497.8	515.3	521.5	530.8	549.3	586.4	643.1	739.0	892.5	1077.0	1266.7
37.5°	449.4	458.6	476.2	482.3	488.5	516.4	554.5	621.5	723.5	875.0	1085.3
40°	415.4	420.5	429.8	434.9	439.1	458.6	492.7	538.0	613.2	728.7	922.4
42.5°	379.3	385.5	391.6	397.8	403.0	418.4	439.1	482.3	532.8	620.5	760.6
45°	344.2	348.4	355.6	359.7	366.9	379.3	397.8	427.7	473.1	528.7	642.1
47.5°	312.3	317.4	320.5	325.7	330.8	344.2	361.8	381.3	418.4	473.1	555.5
50°	283.4	289.6	293.7	294.8	298.9	311.3	325.7	347.3	371.0	413.3	485.4
52.5°	262.8	263.8	266.9	271.1	270.0	277.2	290.6	307.1	331.9	365.9	418.4
55°	239.1	242.2	244.3	245.3	245.3	251.5	258.7	274.2	293.7	321.6	365.9
57.5°	209.2	212.3	218.5	220.6	223.7	226.7	229.8	240.1	256.6	283.4	319.5
60°	178.3	180.4	186.5	190.7	192.7	201.0	205.1	213.3	222.6	242.2	276.2
62.5°	143.3	145.3	148.4	152.5	156.7	169.0	179.3	187.6	194.8	208.2	236.0
65°	124.7	125.7	127.8	128.8	129.9	135.0	144.3	155.6	169.0	179.3	195.8
67.5°	108.2	109.2	110.3	112.3	113.4	114.4	118.5	121.6	135.0	149.4	161.8
70°	92.8	94.8	95.9	95.9	96.9	98.9	101.0	105.1	109.2	116.5	131.9
72.5°	78.3	79.4	81.4	81.4	81.4	83.5	85.5	87.6	89.7	93.8	100.0
75°	64.9	67.0	67.0	67.0	68.0	68.0	70.1	72.1	74.2	77.3	79.4
77.5°	53.6	53.6	53.6	53.6	54.6	54.6	55.7	57.7	58.7	59.8	61.8
80°	40.2	41.2	41.2	41.2	42.3	42.3	42.3	44.3	45.3	45.3	47.4
82.5°	29.9	29.9	29.9	30.9	29.9	30.9	30.9	32.0	30.9	32.0	33.0
85°	18.6	18.6	18.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.6
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.3	9.3	9.3
90°	18.9	18.9	18.9	18.6	18.4	17.2	18.4	18.9	19.5	18.9	15.5
92.5°	35.6	37.9	38.4	40.7	43.0	49.4	58.0	74.0	88.4	87.2	67.7
95°	66.6	71.2	78.6	84.9	91.2	115.3	150.3	196.8	224.9	199.1	132.6
97.5°	119.4	130.8	153.2	170.4	187.6	245.6	307.6	369.6	366.7	283.5	176.2
100°	232.4	257.1	304.7	339.4	374.2	452.8	523.9	536.0	453.3	312.2	188.2
102.5°	437.3	483.8	536.6	573.9	611.2	663.4	665.7	598.0	456.2	301.3	188.8
105°	679.4	715.0	750.6	760.0	769.5	762.1	697.2	577.9	425.2	286.4	191.7
107.5°	833.2	838.4	839.0	827.5	816.0	759.8	663.4	535.4	396.5	278.3	198.0
110°	875.7	864.8	840.1	816.6	793.1	719.6	616.9	495.8	377.0	276.0	206.0

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	864.2	844.1	807.4	779.6	751.7	672.0	574.4	468.3	364.4	276.6	214.6
115°	830.9	804.5	763.8	734.2	704.7	629.5	541.1	446.5	355.8	278.9	223.2
117.5°	789.0	760.9	719.0	690.9	662.8	592.8	513.6	431.5	351.2	282.3	232.4
120°	745.4	718.5	678.3	652.2	626.1	565.2	494.1	420.1	347.2	285.8	241.6
122.5°	706.4	680.0	645.0	622.0	599.1	542.3	478.6	410.3	344.9	289.8	249.6
125°	671.4	649.6	616.3	594.8	573.3	522.8	463.7	401.1	342.0	293.8	258.2
127.5°	641.6	620.9	591.6	571.6	551.5	503.3	448.8	392.5	340.3	297.8	266.3
130°	614.6	595.1	567.0	548.0	529.1	483.8	434.4	383.9	339.1	302.4	273.7
132.5°	588.2	568.7	541.1	523.6	506.1	465.4	420.6	377.0	338.6	307.0	281.2
135°	559.5	540.6	515.9	499.8	483.8	445.9	408.0	370.7	338.0	310.5	287.5
137.5°	530.2	513.6	490.1	475.8	461.4	430.4	397.7	366.1	338.0	313.9	292.7
140°	500.4	485.5	467.1	454.5	441.9	415.5	387.9	362.1	337.4	316.2	296.7
142.5°	474.6	461.4	444.2	434.2	424.1	402.3	379.9	358.1	337.4	317.9	300.1
145°	449.3	439.6	425.8	417.5	409.2	391.4	372.4	354.6	336.3	319.1	303.0
147.5°	429.2	421.2	409.2	402.8	396.5	382.2	366.7	351.2	334.6	319.6	304.7
150°	410.9	404.0	395.4	390.2	385.1	373.0	360.4	346.6	332.8	319.1	305.9
152.5°	396.0	390.2	383.9	379.6	375.3	365.5	354.1	342.6	330.0	317.9	306.4
155°	382.8	378.7	372.4	369.2	366.1	357.5	348.3	337.4	326.5	316.8	307.0
157.5°	370.1	366.7	362.1	359.5	356.9	349.5	341.4	332.8	323.1	314.5	307.0
160°	358.7	355.8	351.8	349.8	347.8	341.4	335.1	327.7	319.6	312.7	307.0
162.5°	347.8	346.0	342.0	340.6	339.1	334.0	328.8	323.1	316.8	311.0	306.4
165°	337.4	335.1	332.8	331.6	330.5	326.5	322.5	317.9	312.7	308.7	305.3
167.5°	327.1	325.9	324.8	323.6	322.5	319.6	316.2	312.7	309.3	306.4	304.7
170°	319.1	317.3	316.8	316.2	315.6	313.3	311.6	308.7	306.4	304.7	303.6
172.5°	311.0	310.5	309.9	309.6	309.3	307.6	306.4	304.7	303.0	302.4	301.8
175°	305.3	304.7	304.7	304.4	304.1	303.6	303.0	301.3	300.7	300.1	300.7
177.5°	300.7	300.7	300.7	300.7	300.7	300.1	300.1	299.0	298.4	299.0	300.1
180°	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1514.0	1508.9	1508.9	1505.8	1505.8	1489.3	1489.3	1494.4	1488.3	1481.0	1470.7
5°	1553.2	1541.9	1538.8	1534.6	1521.2	1500.6	1492.4	1489.3	1476.9	1461.5	1443.9
7.5°	1590.3	1571.7	1562.5	1553.2	1535.7	1506.8	1490.3	1479.0	1460.4	1436.7	1414.1
10°	1626.4	1602.7	1579.0	1567.6	1542.9	1506.8	1483.1	1464.6	1437.8	1405.8	1373.9
12.5°	1659.4	1609.9	1605.8	1583.1	1547.0	1505.8	1469.7	1442.9	1408.9	1371.8	1334.7
15°	1688.2	1637.7	1613.0	1592.4	1545.0	1493.4	1455.3	1422.3	1377.0	1334.7	1289.3
17.5°	1702.6	1648.0	1631.5	1597.5	1549.1	1482.1	1430.5	1390.4	1340.9	1290.4	1238.8
20°	1717.1	1653.2	1626.4	1602.7	1536.7	1460.4	1402.7	1356.3	1301.7	1241.9	1185.3
22.5°	1724.3	1653.2	1621.2	1588.2	1524.3	1436.7	1368.7	1314.1	1250.2	1189.4	1121.4
25°	1711.9	1647.0	1608.9	1574.8	1502.7	1407.9	1329.5	1267.7	1199.7	1130.6	1061.6
27.5°	1681.0	1632.6	1588.2	1553.2	1472.8	1370.8	1288.3	1218.2	1148.1	1070.8	1000.8
30°	1623.3	1601.6	1566.6	1527.4	1439.8	1337.8	1239.9	1167.7	1090.4	1013.1	940.0
32.5°	1533.6	1552.2	1529.5	1495.5	1400.7	1292.4	1188.3	1115.2	1030.7	947.2	880.2
35°	1424.4	1490.3	1478.0	1454.3	1359.4	1244.0	1139.9	1051.3	966.8	882.2	815.2
37.5°	1304.8	1404.8	1415.1	1400.7	1312.0	1194.5	1080.1	993.6	907.0	821.4	753.4
40°	1140.9	1294.5	1327.5	1333.7	1262.6	1134.8	1015.2	930.7	845.1	761.7	679.2
42.5°	990.5	1184.2	1225.4	1251.2	1199.7	1076.0	955.4	861.6	777.1	701.9	619.4
45°	849.3	1051.3	1118.3	1151.2	1128.6	1009.0	884.3	796.7	719.4	650.3	571.0
47.5°	703.9	907.0	1000.8	1053.3	1053.3	941.0	816.3	729.7	655.5	596.7	526.7
50°	607.1	776.1	873.0	942.0	960.6	871.9	754.4	669.9	599.8	535.9	482.3
52.5°	517.4	668.9	749.3	821.4	875.0	797.7	685.4	609.1	540.1	480.3	438.0
55°	447.3	560.7	633.9	713.2	773.0	722.5	618.4	544.2	484.4	434.9	398.9
57.5°	380.3	479.3	539.0	609.1	673.0	634.9	551.4	487.5	434.9	391.6	359.7
60°	323.6	404.0	450.4	505.0	584.4	557.6	488.5	429.8	387.5	348.4	321.6
62.5°	275.2	339.1	378.3	417.4	489.6	477.2	423.6	378.3	342.2	309.2	286.5
65°	225.7	278.3	309.2	343.2	400.9	406.1	362.8	330.8	297.9	269.0	248.4
67.5°	182.4	223.7	251.5	280.3	326.7	341.1	311.3	284.5	256.6	232.9	214.4
70°	147.4	176.2	196.9	219.5	257.7	275.2	259.7	241.2	218.5	198.9	182.4
72.5°	116.5	135.0	147.4	164.9	195.8	213.3	212.3	195.8	179.3	165.9	152.5
75°	85.5	100.0	110.3	121.6	146.4	162.8	167.0	159.8	143.3	133.0	122.6
77.5°	64.9	73.2	78.3	86.6	104.1	118.5	124.7	122.6	111.3	103.1	95.9
80°	49.5	51.5	53.6	56.7	71.1	84.5	88.6	87.6	81.4	78.3	70.1
82.5°	35.0	36.1	37.1	38.1	43.3	54.6	58.7	60.8	55.7	52.6	45.3
85°	20.6	21.6	21.6	23.7	24.7	27.8	35.0	35.0	34.0	29.9	28.9
87.5°	10.3	10.3	9.3	9.3	10.3	11.3	13.4	15.5	13.4	12.4	11.3
90°	11.5	8.6	7.8	6.9	5.7	4.6	2.3	0.6	2.3	4.6	5.7
92.5°	45.9	30.4	27.2	24.1	19.5	16.6	12.1	8.6	12.1	16.6	19.5
95°	82.6	56.2	49.4	42.5	33.3	28.1	22.4	20.1	22.4	28.1	33.3
97.5°	106.7	72.9	65.2	57.4	47.1	39.6	33.3	29.8	33.3	39.6	47.1
100°	118.2	87.8	79.8	71.7	60.3	51.1	45.9	44.2	45.9	51.1	60.3
102.5°	128.5	101.0	93.0	84.9	72.9	63.7	58.5	57.4	58.5	63.7	72.9
105°	140.6	113.6	105.6	97.6	84.9	76.3	72.3	70.0	72.3	76.3	84.9
107.5°	152.6	126.2	118.2	110.2	97.6	89.5	85.5	83.8	85.5	89.5	97.6
110°	164.7	139.4	131.1	122.8	110.8	103.3	99.9	97.6	99.9	103.3	110.8

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	176.2	152.1	143.5	134.9	123.4	116.5	112.5	110.2	112.5	116.5	123.4
115°	188.2	163.5	155.8	148.1	136.6	129.7	126.2	123.4	126.2	129.7	136.6
117.5°	199.1	176.2	168.1	160.1	149.2	142.9	139.4	137.2	139.4	142.9	149.2
120°	210.6	188.2	180.2	172.2	160.7	155.5	152.1	149.8	152.1	155.5	160.7
122.5°	221.5	200.8	192.5	184.2	172.7	167.0	163.5	161.8	163.5	167.0	172.7
125°	232.4	211.8	203.8	195.7	184.2	177.3	173.9	172.2	173.9	177.3	184.2
127.5°	242.7	222.7	214.4	206.0	195.1	187.6	183.1	180.8	183.1	187.6	195.1
130°	251.9	231.8	223.8	215.8	204.3	196.3	190.5	188.2	190.5	196.3	204.3
132.5°	260.0	241.0	233.0	224.9	212.9	204.3	198.0	195.1	198.0	204.3	212.9
135°	267.4	249.1	241.0	233.0	219.8	211.2	204.3	202.0	204.3	211.2	219.8
137.5°	273.7	255.4	247.9	240.4	227.2	218.1	211.2	208.3	211.2	218.1	227.2
140°	278.9	261.7	254.2	246.8	234.1	224.9	218.1	215.8	218.1	224.9	234.1
142.5°	282.9	266.3	259.4	252.5	240.4	231.3	224.9	223.2	224.9	231.3	240.4
145°	286.9	271.4	265.1	258.8	247.3	238.7	233.0	230.7	233.0	238.7	247.3
147.5°	290.4	275.4	269.7	264.0	254.2	246.2	240.4	238.7	240.4	246.2	254.2
150°	292.7	279.5	274.3	269.1	260.5	253.1	248.5	246.8	248.5	253.1	260.5
152.5°	295.0	283.5	278.9	274.3	266.3	260.0	255.4	254.8	255.4	260.0	266.3
155°	297.3	287.5	283.2	278.9	272.6	266.3	262.8	262.2	262.8	266.3	272.6
157.5°	299.0	290.4	286.6	282.9	277.7	272.0	269.1	268.6	269.1	272.0	277.7
160°	300.1	293.2	290.0	286.9	282.3	277.7	275.4	274.9	275.4	277.7	282.3
162.5°	300.7	295.0	292.7	290.4	286.4	282.9	280.6	281.2	280.6	282.9	286.4
165°	301.3	296.1	294.4	292.7	289.8	286.4	285.2	285.8	285.2	286.4	289.8
167.5°	301.3	297.3	296.2	295.0	292.7	290.4	289.2	289.8	289.2	290.4	292.7
170°	300.7	297.8	297.0	296.1	295.0	293.2	292.7	293.8	292.7	293.2	295.0
172.5°	300.1	298.4	297.8	297.3	296.7	295.0	295.5	296.1	295.5	295.0	296.7
175°	299.6	298.4	298.1	297.8	297.8	296.7	297.3	297.8	297.3	296.7	297.8
177.5°	299.0	298.4	298.4	298.4	298.4	297.3	297.8	299.0	297.8	297.3	298.4
180°	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1466.6	1467.7	1470.7	1461.5	1447.0	1440.9	1422.3	1419.2	1416.1	1416.1	1419.2
5°	1433.6	1429.5	1430.5	1413.0	1392.4	1380.0	1354.3	1358.4	1345.0	1336.8	1338.8
7.5°	1397.6	1386.2	1385.2	1362.5	1336.8	1314.1	1287.3	1281.1	1268.7	1254.3	1248.1
10°	1352.2	1344.0	1328.5	1302.7	1269.8	1251.2	1215.1	1193.5	1190.4	1168.8	1160.5
12.5°	1305.8	1291.4	1275.9	1239.9	1202.8	1172.9	1146.1	1122.4	1105.9	1087.3	1075.0
15°	1252.2	1234.7	1217.2	1179.1	1135.8	1105.9	1065.7	1030.7	982.2	944.1	922.4
17.5°	1193.5	1173.9	1150.2	1108.0	1065.7	1024.5	950.3	909.0	875.0	852.4	839.0
20°	1132.7	1111.0	1087.3	1045.1	971.9	899.8	858.5	826.6	806.0	783.3	766.8
22.5°	1068.8	1046.1	1020.3	954.4	877.1	826.6	794.6	764.7	734.9	722.5	714.2
25°	1009.0	988.4	955.4	865.7	804.9	758.6	722.5	702.9	687.4	671.0	655.5
27.5°	947.2	909.0	862.7	787.4	749.3	701.9	676.1	661.7	634.9	623.5	616.3
30°	873.0	830.7	786.4	732.8	688.5	655.5	631.8	608.1	592.6	581.3	568.9
32.5°	797.7	757.5	729.7	674.0	641.1	607.1	584.4	570.0	547.3	540.1	534.9
35°	732.8	698.8	674.0	628.7	597.8	566.9	550.4	528.7	514.3	500.9	492.7
37.5°	668.9	650.3	624.6	586.4	553.5	528.7	506.1	498.8	479.3	472.0	463.8
40°	624.6	596.7	575.1	542.1	514.3	487.5	473.1	456.6	443.2	431.8	428.8
42.5°	571.0	550.4	538.0	501.9	473.1	457.6	440.1	421.5	411.2	402.0	390.6
45°	530.8	512.2	494.7	465.9	440.1	420.5	405.0	392.7	375.2	371.0	353.5
47.5°	488.5	470.0	456.6	427.7	404.0	385.5	374.1	357.6	343.2	333.9	325.7
50°	446.3	430.8	418.4	393.7	373.1	353.5	338.1	321.6	315.4	299.9	294.8
52.5°	406.1	395.8	382.4	358.7	338.1	321.6	305.1	291.7	282.4	274.2	268.0
55°	372.1	355.6	349.4	323.6	306.1	288.6	274.2	265.9	254.6	249.4	244.3
57.5°	333.9	324.7	314.3	294.8	275.2	258.7	248.4	236.0	229.8	223.7	219.5
60°	301.0	287.6	279.3	262.8	245.3	229.8	220.6	211.3	203.0	197.9	189.6
62.5°	262.8	252.5	247.4	229.8	215.4	201.0	192.7	183.5	177.3	168.0	157.7
65°	229.8	221.6	215.4	201.0	187.6	174.2	165.9	154.6	146.4	141.2	140.2
67.5°	201.0	194.8	185.5	172.1	158.7	148.4	139.1	129.9	128.8	126.8	126.8
70°	169.0	162.8	157.7	143.3	131.9	120.6	118.5	115.4	112.3	111.3	109.2
72.5°	141.2	136.0	129.9	117.5	106.2	103.1	101.0	98.9	95.9	94.8	93.8
75°	114.4	107.2	103.1	91.7	88.6	86.6	84.5	81.4	79.4	78.3	76.3
77.5°	87.6	80.4	80.4	74.2	72.1	69.1	67.0	64.9	63.9	61.8	61.8
80°	61.8	61.8	59.8	56.7	53.6	52.6	49.5	48.4	47.4	48.4	46.4
82.5°	45.3	41.2	41.2	39.2	37.1	36.1	34.0	34.0	33.0	33.0	33.0
85°	25.8	25.8	24.7	22.7	21.6	21.6	20.6	20.6	19.6	19.6	18.6
87.5°	10.3	9.3	10.3	9.3	9.3	8.2	8.2	8.2	7.2	8.2	7.2
90°	6.9	7.8	8.6	11.5	15.5	18.9	19.5	18.9	18.4	17.2	18.4
92.5°	24.1	27.2	30.4	45.9	67.7	87.2	88.4	74.0	58.0	49.4	43.0
95°	42.5	49.4	56.2	82.6	132.6	199.1	224.9	196.8	150.3	115.3	91.2
97.5°	57.4	65.2	72.9	106.7	176.2	283.5	366.7	369.6	307.6	245.6	187.6
100°	71.7	79.8	87.8	118.2	188.2	312.2	453.3	536.0	523.9	452.8	374.2
102.5°	84.9	93.0	101.0	128.5	188.8	301.3	456.2	598.0	665.7	663.4	611.2
105°	97.6	105.6	113.6	140.6	191.7	286.4	425.2	577.9	697.2	762.1	769.5
107.5°	110.2	118.2	126.2	152.6	198.0	278.3	396.5	535.4	663.4	759.8	816.0
110°	122.8	131.1	139.4	164.7	206.0	276.0	377.0	495.8	616.9	719.6	793.1

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	134.9	143.5	152.1	176.2	214.6	276.6	364.4	468.3	574.4	672.0	751.7
115°	148.1	155.8	163.5	188.2	223.2	278.9	355.8	446.5	541.1	629.5	704.7
117.5°	160.1	168.1	176.2	199.1	232.4	282.3	351.2	431.5	513.6	592.8	662.8
120°	172.2	180.2	188.2	210.6	241.6	285.8	347.2	420.1	494.1	565.2	626.1
122.5°	184.2	192.5	200.8	221.5	249.6	289.8	344.9	410.3	478.6	542.3	599.1
125°	195.7	203.8	211.8	232.4	258.2	293.8	342.0	401.1	463.7	522.8	573.3
127.5°	206.0	214.4	222.7	242.7	266.3	297.8	340.3	392.5	448.8	503.3	551.5
130°	215.8	223.8	231.8	251.9	273.7	302.4	339.1	383.9	434.4	483.8	529.1
132.5°	224.9	233.0	241.0	260.0	281.2	307.0	338.6	377.0	420.6	465.4	506.1
135°	233.0	241.0	249.1	267.4	287.5	310.5	338.0	370.7	408.0	445.9	483.8
137.5°	240.4	247.9	255.4	273.7	292.7	313.9	338.0	366.1	397.7	430.4	461.4
140°	246.8	254.2	261.7	278.9	296.7	316.2	337.4	362.1	387.9	415.5	441.9
142.5°	252.5	259.4	266.3	282.9	300.1	317.9	337.4	358.1	379.9	402.3	424.1
145°	258.8	265.1	271.4	286.9	303.0	319.1	336.3	354.6	372.4	391.4	409.2
147.5°	264.0	269.7	275.4	290.4	304.7	319.6	334.6	351.2	366.7	382.2	396.5
150°	269.1	274.3	279.5	292.7	305.9	319.1	332.8	346.6	360.4	373.0	385.1
152.5°	274.3	278.9	283.5	295.0	306.4	317.9	330.0	342.6	354.1	365.5	375.3
155°	278.9	283.2	287.5	297.3	307.0	316.8	326.5	337.4	348.3	357.5	366.1
157.5°	282.9	286.6	290.4	299.0	307.0	314.5	323.1	332.8	341.4	349.5	356.9
160°	286.9	290.0	293.2	300.1	307.0	312.7	319.6	327.7	335.1	341.4	347.8
162.5°	290.4	292.7	295.0	300.7	306.4	311.0	316.8	323.1	328.8	334.0	339.1
165°	292.7	294.4	296.1	301.3	305.3	308.7	312.7	317.9	322.5	326.5	330.5
167.5°	295.0	296.2	297.3	301.3	304.7	306.4	309.3	312.7	316.2	319.6	322.5
170°	296.1	297.0	297.8	300.7	303.6	304.7	306.4	308.7	311.6	313.3	315.6
172.5°	297.3	297.8	298.4	300.1	301.8	302.4	303.0	304.7	306.4	307.6	309.3
175°	297.8	298.1	298.4	299.6	300.7	300.1	300.7	301.3	303.0	303.6	304.1
177.5°	298.4	298.4	298.4	299.0	300.1	299.0	298.4	299.0	300.1	300.1	300.7
180°	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1419.2	1417.1	1411.0	1413.0	1409.9	1409.9	1407.9	1407.9	1407.9	1413.0	1409.9
5°	1341.9	1334.7	1327.5	1324.4	1321.3	1318.2	1318.2	1317.2	1326.5	1324.4	1332.6
7.5°	1246.1	1244.0	1229.6	1229.6	1224.4	1222.4	1227.5	1228.5	1229.6	1231.6	1236.8
10°	1160.5	1155.4	1134.8	1136.8	1133.7	1129.6	1132.7	1130.6	1137.8	1139.9	1137.8
12.5°	1059.5	1050.2	1027.6	1016.2	1003.9	994.6	1005.9	997.7	1026.5	1034.8	1057.5
15°	925.5	908.0	892.5	892.5	881.2	873.0	878.1	887.4	893.6	902.9	907.0
17.5°	835.9	828.6	816.3	809.1	806.0	802.9	802.9	807.0	820.4	819.4	827.6
20°	759.6	755.5	749.3	740.0	736.9	734.9	734.9	734.9	744.1	752.4	757.5
22.5°	707.0	703.9	699.8	687.4	681.3	679.2	684.4	687.4	694.7	700.8	706.0
25°	654.5	647.3	640.0	635.9	632.8	632.8	634.9	635.9	639.0	642.1	648.3
27.5°	611.2	606.0	595.7	584.4	584.4	581.3	583.4	585.4	592.6	602.9	608.1
30°	562.7	561.7	557.6	553.5	549.3	547.3	551.4	554.5	555.5	560.7	560.7
32.5°	527.7	520.5	513.3	509.1	507.1	506.1	507.1	511.2	511.2	517.4	524.6
35°	492.7	488.5	481.3	474.1	472.0	466.9	471.0	475.1	482.3	485.4	488.5
37.5°	454.5	449.4	446.3	444.2	440.1	441.1	438.0	444.2	450.4	449.4	451.4
40°	425.7	416.4	407.1	406.1	405.0	404.0	404.0	405.0	409.2	413.3	419.5
42.5°	388.6	385.5	377.2	369.0	366.9	364.9	362.8	366.9	375.2	382.4	385.5
45°	350.4	346.3	344.2	338.1	333.9	332.9	330.8	336.0	343.2	346.3	348.4
47.5°	315.4	314.3	308.2	309.2	306.1	307.1	306.1	309.2	309.2	312.3	314.3
50°	291.7	288.6	285.5	283.4	280.3	280.3	279.3	280.3	284.5	288.6	287.6
52.5°	268.0	262.8	261.8	260.8	258.7	260.8	257.7	258.7	262.8	264.9	263.8
55°	240.1	239.1	237.1	235.0	234.0	232.9	232.9	232.9	237.1	240.1	241.2
57.5°	218.5	213.3	209.2	209.2	205.1	204.1	206.1	207.2	210.3	212.3	214.4
60°	188.6	186.5	180.4	177.3	171.1	170.1	170.1	174.2	179.3	186.5	188.6
62.5°	156.7	153.6	152.5	152.5	152.5	152.5	152.5	152.5	152.5	153.6	153.6
65°	139.1	140.2	139.1	138.1	139.1	139.1	138.1	138.1	138.1	139.1	140.2
67.5°	124.7	123.7	124.7	123.7	122.6	122.6	121.6	122.6	123.7	124.7	124.7
70°	108.2	108.2	107.2	108.2	107.2	106.2	105.1	105.1	107.2	108.2	108.2
72.5°	92.8	92.8	91.7	91.7	89.7	89.7	90.7	89.7	89.7	92.8	92.8
75°	77.3	76.3	75.2	75.2	74.2	74.2	74.2	73.2	75.2	75.2	76.3
77.5°	60.8	60.8	60.8	59.8	59.8	58.7	58.7	59.8	59.8	59.8	60.8
80°	46.4	46.4	46.4	45.3	44.3	44.3	44.3	44.3	44.3	45.3	44.3
82.5°	32.0	32.0	32.0	32.0	32.0	30.9	30.9	30.9	32.0	32.0	30.9
85°	19.6	18.6	19.6	19.6	18.6	19.6	18.6	18.6	17.5	17.5	18.6
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	18.6	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.6
92.5°	40.7	38.4	37.9	35.6	36.2	35.0	36.2	35.6	37.9	38.4	40.7
95°	84.9	78.6	71.2	66.6	64.8	65.4	64.8	66.6	71.2	78.6	84.9
97.5°	170.4	153.2	130.8	119.4	113.0	109.6	113.0	119.4	130.8	153.2	170.4
100°	339.4	304.7	257.1	232.4	215.8	205.4	215.8	232.4	257.1	304.7	339.4
102.5°	573.9	536.6	483.8	437.3	415.5	400.5	415.5	437.3	483.8	536.6	573.9
105°	760.0	750.6	715.0	679.4	654.8	646.7	654.8	679.4	715.0	750.6	760.0
107.5°	827.5	839.0	838.4	833.2	825.8	812.6	825.8	833.2	838.4	839.0	827.5
110°	816.6	840.1	864.8	875.7	880.9	880.3	880.9	875.7	864.8	840.1	816.6

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	779.6	807.4	844.1	864.2	875.1	879.1	875.1	864.2	844.1	807.4	779.6
115°	734.2	763.8	804.5	830.9	845.9	851.0	845.9	830.9	804.5	763.8	734.2
117.5°	690.9	719.0	760.9	789.0	804.5	808.6	804.5	789.0	760.9	719.0	690.9
120°	652.2	678.3	718.5	745.4	762.1	767.8	762.1	745.4	718.5	678.3	652.2
122.5°	622.0	645.0	680.0	706.4	720.8	725.3	720.8	706.4	680.0	645.0	622.0
125°	594.8	616.3	649.6	671.4	685.8	690.3	685.8	671.4	649.6	616.3	594.8
127.5°	571.6	591.6	620.9	641.6	654.2	657.6	654.2	641.6	620.9	591.6	571.6
130°	548.0	567.0	595.1	614.6	626.1	630.7	626.1	614.6	595.1	567.0	548.0
132.5°	523.6	541.1	568.7	588.2	598.5	602.5	598.5	588.2	568.7	541.1	523.6
135°	499.8	515.9	540.6	559.5	569.8	572.1	569.8	559.5	540.6	515.9	499.8
137.5°	475.8	490.1	513.6	530.2	539.4	542.9	539.4	530.2	513.6	490.1	475.8
140°	454.5	467.1	485.5	500.4	509.0	512.4	509.0	500.4	485.5	467.1	454.5
142.5°	434.2	444.2	461.4	474.6	482.0	482.0	482.0	474.6	461.4	444.2	434.2
145°	417.5	425.8	439.6	449.3	455.1	456.8	455.1	449.3	439.6	425.8	417.5
147.5°	402.8	409.2	421.2	429.2	433.3	434.4	433.3	429.2	421.2	409.2	402.8
150°	390.2	395.4	404.0	410.9	414.3	414.9	414.3	410.9	404.0	395.4	390.2
152.5°	379.6	383.9	390.2	396.0	398.3	398.3	398.3	396.0	390.2	383.9	379.6
155°	369.2	372.4	378.7	382.8	385.1	383.9	385.1	382.8	378.7	372.4	369.2
157.5°	359.5	362.1	366.7	370.1	371.3	371.3	371.3	370.1	366.7	362.1	359.5
160°	349.8	351.8	355.8	358.7	359.2	359.2	359.2	358.7	355.8	351.8	349.8
162.5°	340.6	342.0	346.0	347.8	348.3	347.8	348.3	347.8	346.0	342.0	340.6
165°	331.6	332.8	335.1	337.4	337.4	336.9	337.4	337.4	335.1	332.8	331.6
167.5°	323.6	324.8	325.9	327.1	327.1	326.5	327.1	327.1	325.9	324.8	323.6
170°	316.2	316.8	317.3	319.1	318.5	317.3	318.5	319.1	317.3	316.8	316.2
172.5°	309.6	309.9	310.5	311.0	310.5	309.9	310.5	311.0	310.5	309.9	309.6
175°	304.4	304.7	304.7	305.3	304.7	303.6	304.7	305.3	304.7	304.7	304.4
177.5°	300.7	300.7	300.7	300.7	300.1	299.0	300.1	300.7	300.7	300.7	300.7
180°	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1413.0	1418.2	1416.1	1404.8	1416.1	1419.2	1425.4	1431.6	1435.7	1441.9	1447.0
5°	1324.4	1334.7	1340.9	1334.7	1355.3	1358.4	1372.8	1381.1	1393.4	1403.8	1412.0
7.5°	1240.9	1249.2	1261.5	1263.6	1275.9	1290.4	1311.0	1331.6	1351.2	1361.5	1370.8
10°	1151.2	1165.7	1184.2	1180.1	1198.7	1221.3	1243.0	1275.9	1292.4	1311.0	1327.5
12.5°	1061.6	1070.8	1095.6	1103.8	1130.6	1148.1	1178.0	1198.7	1239.9	1261.5	1275.9
15°	904.9	943.0	974.0	1011.1	1046.1	1079.1	1105.9	1143.0	1179.1	1195.6	1219.3
17.5°	833.8	851.3	869.9	888.4	933.8	992.5	1039.9	1080.1	1111.0	1132.7	1160.5
20°	759.6	777.1	797.7	815.2	843.1	885.3	944.1	1013.1	1050.2	1072.9	1099.7
22.5°	707.0	723.5	736.9	752.4	774.0	804.9	849.3	934.8	984.3	1012.1	1035.8
25°	650.3	671.0	685.4	696.7	714.2	748.3	784.3	832.8	921.4	943.0	976.0
27.5°	611.2	617.4	633.9	651.4	668.9	687.4	724.5	765.8	825.6	873.0	913.2
30°	564.8	580.3	595.7	602.9	618.4	645.2	667.9	712.2	758.6	795.7	844.1
32.5°	529.8	539.0	549.3	566.9	581.3	599.8	622.5	659.6	698.8	722.5	759.6
35°	490.6	496.8	518.4	525.6	540.1	558.6	581.3	610.1	652.4	671.0	697.8
37.5°	453.5	467.9	474.1	490.6	504.0	522.5	539.0	572.0	599.8	621.5	646.2
40°	424.6	430.8	442.2	456.6	467.9	482.3	503.0	526.7	556.6	574.1	595.7
42.5°	389.6	394.7	409.2	417.4	436.0	449.4	461.7	490.6	517.4	530.8	552.4
45°	351.5	363.8	373.1	389.6	399.9	416.4	431.8	452.5	477.2	492.7	505.0
47.5°	318.5	330.8	340.1	355.6	372.1	379.3	395.8	417.4	440.1	452.5	470.0
50°	291.7	295.8	313.3	320.5	338.1	352.5	363.8	382.4	407.1	414.3	428.8
52.5°	265.9	269.0	280.3	289.6	305.1	317.4	331.9	349.4	370.0	381.3	392.7
55°	243.2	245.3	250.4	260.8	271.1	286.5	299.9	316.4	333.9	346.3	356.6
57.5°	217.5	221.6	225.7	231.9	242.2	256.6	271.1	286.5	301.0	309.2	322.6
60°	187.6	193.8	201.0	208.2	215.4	225.7	242.2	256.6	270.0	277.2	287.6
62.5°	155.6	168.0	174.2	182.4	188.6	197.9	210.3	226.7	236.0	245.3	253.5
65°	140.2	141.2	142.2	150.5	161.8	171.1	182.4	194.8	209.2	215.4	221.6
67.5°	124.7	125.7	127.8	128.8	133.0	143.3	155.6	169.0	180.4	184.5	190.7
70°	109.2	109.2	113.4	114.4	115.4	116.5	126.8	140.2	150.5	155.6	162.8
72.5°	92.8	93.8	95.9	96.9	98.9	101.0	104.1	111.3	123.7	128.8	137.1
75°	76.3	77.3	78.3	79.4	82.5	83.5	86.6	90.7	95.9	102.0	107.2
77.5°	60.8	60.8	61.8	63.9	66.0	67.0	70.1	72.1	74.2	77.3	81.4
80°	45.3	46.4	46.4	48.4	48.4	49.5	50.5	53.6	55.7	57.7	59.8
82.5°	30.9	33.0	33.0	33.0	34.0	35.0	36.1	36.1	38.1	39.2	42.3
85°	18.6	19.6	19.6	19.6	18.6	20.6	20.6	21.6	21.6	21.6	22.7
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.3	9.3
90°	18.4	17.2	18.4	18.9	19.5	18.9	15.5	11.5	8.6	7.8	6.9
92.5°	43.0	49.4	58.0	74.0	88.4	87.2	67.7	45.9	30.4	27.2	24.1
95°	91.2	115.3	150.3	196.8	224.9	199.1	132.6	82.6	56.2	49.4	42.5
97.5°	187.6	245.6	307.6	369.6	366.7	283.5	176.2	106.7	72.9	65.2	57.4
100°	374.2	452.8	523.9	536.0	453.3	312.2	188.2	118.2	87.8	79.8	71.7
102.5°	611.2	663.4	665.7	598.0	456.2	301.3	188.8	128.5	101.0	93.0	84.9
105°	769.5	762.1	697.2	577.9	425.2	286.4	191.7	140.6	113.6	105.6	97.6
107.5°	816.0	759.8	663.4	535.4	396.5	278.3	198.0	152.6	126.2	118.2	110.2
110°	793.1	719.6	616.9	495.8	377.0	276.0	206.0	164.7	139.4	131.1	122.8

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	751.7	672.0	574.4	468.3	364.4	276.6	214.6	176.2	152.1	143.5	134.9
115°	704.7	629.5	541.1	446.5	355.8	278.9	223.2	188.2	163.5	155.8	148.1
117.5°	662.8	592.8	513.6	431.5	351.2	282.3	232.4	199.1	176.2	168.1	160.1
120°	626.1	565.2	494.1	420.1	347.2	285.8	241.6	210.6	188.2	180.2	172.2
122.5°	599.1	542.3	478.6	410.3	344.9	289.8	249.6	221.5	200.8	192.5	184.2
125°	573.3	522.8	463.7	401.1	342.0	293.8	258.2	232.4	211.8	203.8	195.7
127.5°	551.5	503.3	448.8	392.5	340.3	297.8	266.3	242.7	222.7	214.4	206.0
130°	529.1	483.8	434.4	383.9	339.1	302.4	273.7	251.9	231.8	223.8	215.8
132.5°	506.1	465.4	420.6	377.0	338.6	307.0	281.2	260.0	241.0	233.0	224.9
135°	483.8	445.9	408.0	370.7	338.0	310.5	287.5	267.4	249.1	241.0	233.0
137.5°	461.4	430.4	397.7	366.1	338.0	313.9	292.7	273.7	255.4	247.9	240.4
140°	441.9	415.5	387.9	362.1	337.4	316.2	296.7	278.9	261.7	254.2	246.8
142.5°	424.1	402.3	379.9	358.1	337.4	317.9	300.1	282.9	266.3	259.4	252.5
145°	409.2	391.4	372.4	354.6	336.3	319.1	303.0	286.9	271.4	265.1	258.8
147.5°	396.5	382.2	366.7	351.2	334.6	319.6	304.7	290.4	275.4	269.7	264.0
150°	385.1	373.0	360.4	346.6	332.8	319.1	305.9	292.7	279.5	274.3	269.1
152.5°	375.3	365.5	354.1	342.6	330.0	317.9	306.4	295.0	283.5	278.9	274.3
155°	366.1	357.5	348.3	337.4	326.5	316.8	307.0	297.3	287.5	283.2	278.9
157.5°	356.9	349.5	341.4	332.8	323.1	314.5	307.0	299.0	290.4	286.6	282.9
160°	347.8	341.4	335.1	327.7	319.6	312.7	307.0	300.1	293.2	290.0	286.9
162.5°	339.1	334.0	328.8	323.1	316.8	311.0	306.4	300.7	295.0	292.7	290.4
165°	330.5	326.5	322.5	317.9	312.7	308.7	305.3	301.3	296.1	294.4	292.7
167.5°	322.5	319.6	316.2	312.7	309.3	306.4	304.7	301.3	297.3	296.2	295.0
170°	315.6	313.3	311.6	308.7	306.4	304.7	303.6	300.7	297.8	297.0	296.1
172.5°	309.3	307.6	306.4	304.7	303.0	302.4	301.8	300.1	298.4	297.8	297.3
175°	304.1	303.6	303.0	301.3	300.7	300.1	300.7	299.6	298.4	298.1	297.8
177.5°	300.7	300.1	300.1	299.0	298.4	299.0	300.1	299.0	298.4	298.4	298.4
180°	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4	298.4

TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1483.1	1483.1	1483.1	1483.1
2.5°	1456.3	1453.2	1471.8	1492.4
5°	1426.4	1431.6	1455.3	1484.1
7.5°	1395.5	1406.8	1434.7	1472.8
10°	1352.2	1372.8	1415.1	1454.3
12.5°	1310.0	1337.8	1378.0	1424.4
15°	1262.6	1293.5	1342.9	1398.6
17.5°	1210.0	1245.0	1302.7	1363.6
20°	1154.3	1200.7	1261.5	1327.5
22.5°	1092.5	1148.1	1211.0	1284.2
25°	1032.7	1093.5	1156.4	1240.9
27.5°	974.0	1033.7	1103.8	1189.4
30°	915.2	969.8	1045.1	1136.8
32.5°	852.4	909.0	988.4	1082.2
35°	794.6	851.3	925.5	1018.3
37.5°	732.8	793.6	864.7	960.6
40°	660.6	731.8	800.8	892.5
42.5°	600.9	676.1	743.1	829.7
45°	553.5	624.6	680.2	764.7
47.5°	509.1	566.9	623.5	701.9
50°	466.9	511.2	570.0	640.0
52.5°	423.6	461.7	512.2	578.2
55°	384.4	420.5	465.9	516.4
57.5°	348.4	374.1	419.5	464.8
60°	308.2	335.0	370.0	408.1
62.5°	274.2	294.8	327.7	359.7
65°	238.1	257.7	282.4	312.3
67.5°	205.1	222.6	242.2	265.9
70°	175.2	188.6	203.0	223.7
72.5°	143.3	157.7	171.1	187.6
75°	117.5	123.7	135.0	146.4
77.5°	90.7	98.9	105.1	114.4
80°	64.9	72.1	74.2	81.4
82.5°	43.3	47.4	51.5	53.6
85°	24.7	26.8	30.9	32.0
87.5°	9.3	10.3	12.4	14.4
90°	5.7	4.6	2.3	0.6
92.5°	19.5	16.6	12.1	8.6
95°	33.3	28.1	22.4	20.1
97.5°	47.1	39.6	33.3	29.8
100°	60.3	51.1	45.9	44.2
102.5°	72.9	63.7	58.5	57.4
105°	84.9	76.3	72.3	70.0
107.5°	97.6	89.5	85.5	83.8
110°	110.8	103.3	99.9	97.6



TEST NUMBER: P999965

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	123.4	116.5	112.5	110.2
115°	136.6	129.7	126.2	123.4
117.5°	149.2	142.9	139.4	137.2
120°	160.7	155.5	152.1	149.8
122.5°	172.7	167.0	163.5	161.8
125°	184.2	177.3	173.9	172.2
127.5°	195.1	187.6	183.1	180.8
130°	204.3	196.3	190.5	188.2
132.5°	212.9	204.3	198.0	195.1
135°	219.8	211.2	204.3	202.0
137.5°	227.2	218.1	211.2	208.3
140°	234.1	224.9	218.1	215.8
142.5°	240.4	231.3	224.9	223.2
145°	247.3	238.7	233.0	230.7
147.5°	254.2	246.2	240.4	238.7
150°	260.5	253.1	248.5	246.8
152.5°	266.3	260.0	255.4	254.8
155°	272.6	266.3	262.8	262.2
157.5°	277.7	272.0	269.1	268.6
160°	282.3	277.7	275.4	274.9
162.5°	286.4	282.9	280.6	281.2
165°	289.8	286.4	285.2	285.8
167.5°	292.7	290.4	289.2	289.8
170°	295.0	293.2	292.7	293.8
172.5°	296.7	295.0	295.5	296.1
175°	297.8	296.7	297.3	297.8
177.5°	298.4	297.3	297.8	299.0
180°	298.4	298.4	298.4	298.4

(END OF REPORT)