

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999976

Luminaire Tested: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999976
REPORT IS A COMBINATION OF REPORTS P988533 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4276.0 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55
2	92	85	79	75	86	80	75	71	70	66	63	60	57	55	51	49	48
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	39	35	33
6	67	55	48	42	62	52	45	40	46	41	37	41	36	33	35	32	30
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27
8	58	46	39	33	54	44	37	32	39	33	30	34	30	27	30	27	24
9	54	42	35	30	51	40	34	29	36	31	27	32	28	25	28	25	22
10	51	39	32	28	48	37	31	26	33	28	24	30	26	22	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22478	22478	22478	22478
5°	22530	23875	22609	19073
10°	22282	25236	22441	15751
15°	21799	25244	22168	11832
20°	21217	20866	21680	9762
25°	20512	13039	20956	8305
30°	19613	8348	20146	7150
35°	18517	6415	19117	6118
40°	17296	5393	18035	5351
45°	15991	4591	16660	4492
50°	14654	3900	15338	3886
55°	13174	3390	13883	3345
60°	11859	2584	12487	2553
65°	10629	1944	11262	2206
70°	9272	1553	10000	1797
75°	7837	1191	8559	1361
80°	6227	809	6698	891
85°	4322	419	4746	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 20563 cd/sqm

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.7	3.1
10°-20°	376.0	8.8
20°-30°	483.9	11.3
30°-40°	459.0	10.7
40°-50°	393.4	9.2
50°-60°	299.6	7.0
60°-70°	188.9	4.4
70°-80°	94.3	2.2
80°-90°	26.1	0.6
90°-100°	40.3	0.9
100°-110°	128.0	3.0
110°-120°	219.1	5.1
120°-130°	288.1	6.7
130°-140°	323.4	7.6
140°-150°	317.1	7.4
150°-160°	266.0	6.2
160°-170°	176.4	4.1
170°-180°	61.7	1.4
0°-30°	994.5	23.3
0°-40°	1453.6	34.0
0°-60°	2146.6	50.2
0°-90°	2455.8	57.4
90°-120°	387.4	9.1
90°-150°	1316.0	30.8
90°-180°	1820.0	42.6
0°-180°	4276.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1420	1420	1420	1420	1420	
5°	1421	1580	1426	1262	1421	135
15°	1339	1783	1362	836	1339	377
25°	1188	951	1214	606	1188	546
35°	975	469	1007	447	975	610
45°	732	326	763	319	732	565
55°	494	226	521	223	494	446
65°	299	117	317	133	299	297
75°	140	62	153	71	140	152
85°	31	18	34	19	31	35
90°	0	19	0	19	0	4
95°	29	34	29	34	29	32
105°	118	122	118	122	118	125
115°	220	220	220	220	220	217
125°	320	321	320	321	320	286
135°	414	419	414	419	414	320
145°	502	508	502	508	502	314
155°	574	578	574	578	574	264
165°	625	625	625	625	625	176
175°	650	648	650	648	650	62
180°	651	651	651	651	651	

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1428.9	1434.8	1437.8	1441.7	1450.6	1456.5	1465.4	1467.4	1466.4	1470.4	1459.5
5°	1421.0	1433.9	1445.7	1455.6	1471.4	1481.2	1492.1	1504.9	1507.9	1522.7	1513.8
7.5°	1410.2	1428.9	1445.7	1465.4	1489.1	1501.9	1518.7	1538.5	1547.3	1565.1	1570.0
10°	1392.4	1419.1	1447.7	1468.4	1501.0	1523.7	1539.4	1571.0	1591.7	1618.4	1614.4
12.5°	1363.8	1398.3	1436.8	1471.4	1513.8	1528.6	1558.2	1590.8	1617.4	1642.1	1663.8
15°	1339.1	1378.6	1421.0	1463.5	1511.8	1539.4	1569.0	1611.5	1640.1	1683.5	1702.3
17.5°	1305.6	1355.9	1406.2	1453.6	1510.8	1542.4	1578.9	1620.4	1662.8	1704.2	1719.0
20°	1271.0	1325.3	1379.6	1443.7	1508.9	1539.4	1576.9	1628.3	1669.7	1702.3	1702.3
22.5°	1229.6	1295.7	1357.9	1419.1	1490.1	1534.5	1573.0	1633.2	1662.8	1669.7	1643.1
25°	1188.1	1254.3	1322.3	1398.3	1479.2	1518.7	1562.1	1618.4	1628.3	1600.6	1531.5
27.5°	1138.8	1212.8	1289.8	1371.7	1456.5	1505.9	1545.4	1582.9	1564.1	1490.1	1382.5
30°	1088.5	1168.4	1255.2	1333.2	1435.8	1481.2	1514.8	1525.6	1466.4	1346.0	1206.9
32.5°	1036.2	1114.1	1205.9	1299.6	1403.3	1446.7	1468.4	1439.8	1331.2	1179.3	1009.5
35°	975.0	1062.8	1158.5	1256.2	1358.9	1391.4	1404.2	1334.2	1195.0	998.7	829.9
37.5°	919.7	1007.5	1110.2	1209.8	1309.5	1327.3	1314.4	1204.9	1028.3	833.9	669.1
40°	854.6	948.3	1049.0	1160.5	1242.4	1247.3	1215.8	1073.7	854.6	672.0	570.4
42.5°	794.4	889.1	989.8	1103.3	1165.4	1148.7	1106.2	919.7	713.5	579.3	497.4
45°	732.2	822.0	930.6	1031.2	1075.6	1036.2	972.0	773.7	599.0	498.3	435.2
47.5°	672.0	755.9	863.5	960.2	968.1	923.7	847.7	648.3	519.1	438.1	386.8
50°	612.8	696.7	797.4	877.3	869.4	808.2	722.4	563.5	451.0	386.8	344.4
52.5°	553.6	629.6	727.3	790.4	756.9	697.7	612.8	477.6	393.7	337.5	304.9
55°	494.4	565.4	649.3	701.6	648.3	580.3	520.1	409.5	341.4	296.0	271.4
57.5°	445.1	501.3	578.3	609.9	545.7	492.4	440.1	352.3	296.0	263.5	234.9
60°	390.8	442.1	505.3	524.0	457.9	414.5	370.1	298.0	253.6	225.0	206.2
62.5°	344.4	386.8	435.2	435.2	377.0	344.4	310.8	249.7	213.2	190.5	181.6
65°	299.0	329.6	364.1	360.2	310.8	282.2	255.6	206.2	178.6	162.8	153.9
67.5°	254.6	278.3	301.0	287.2	251.6	227.0	202.3	166.8	148.0	137.2	125.3
70°	214.1	232.9	244.7	231.9	196.4	175.7	157.9	134.2	119.4	105.6	98.7
72.5°	179.6	187.5	191.4	175.7	146.0	134.2	121.4	104.6	91.8	84.9	82.9
75°	140.1	147.0	144.1	132.2	107.6	98.7	88.8	77.0	74.0	70.1	68.1
77.5°	109.5	109.5	104.6	93.7	77.0	70.1	66.1	60.2	57.2	56.2	54.3
80°	78.0	77.0	74.0	62.2	52.3	48.4	48.4	44.4	43.4	41.4	41.4
82.5°	51.3	51.3	47.4	37.5	34.5	33.6	32.6	30.6	30.6	29.6	29.6
85°	30.6	28.6	23.7	20.7	19.7	19.7	18.7	17.8	18.7	17.8	17.8
87.5°	13.8	10.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	0.5	2.0	3.4	4.9	6.4	7.1	8.4	11.1	13.8	16.5	19.2
92.5°	12.1	13.1	14.1	15.0	16.0	16.5	16.6	16.7	16.8	16.9	17.0
95°	28.6	29.8	31.0	32.3	33.5	34.1	34.2	34.5	34.7	35.0	35.2
97.5°	47.8	48.9	50.0	51.1	52.2	52.7	52.9	53.4	53.9	54.4	54.9
100°	69.8	70.8	71.8	72.7	73.7	74.2	74.4	74.7	75.1	75.4	75.8
102.5°	92.8	93.5	94.3	95.0	95.7	96.1	96.3	96.8	97.3	97.8	98.3
105°	118.1	118.5	118.9	119.2	119.6	119.8	119.9	120.2	120.4	120.7	120.9
107.5°	143.4	143.9	144.4	144.9	145.4	145.6	145.6	145.6	145.6	145.6	145.6
110°	167.6	168.3	169.1	169.8	170.5	170.9	170.9	170.9	170.9	170.9	170.9



TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	193.9	194.6	195.4	196.1	196.8	197.2	197.1	197.0	196.9	196.8	196.7
115°	219.8	220.5	221.3	222.0	222.7	223.1	223.0	222.7	222.5	222.2	222.0
117.5°	245.6	246.6	247.6	248.5	249.5	250.0	249.7	249.1	248.4	247.8	247.2
120°	271.4	272.4	273.4	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4
122.5°	295.0	296.2	297.4	298.7	299.9	300.5	300.2	299.6	299.0	298.4	297.8
125°	319.7	320.8	321.9	323.0	324.1	324.7	324.5	324.1	323.8	323.4	323.0
127.5°	343.9	345.3	346.6	348.0	349.3	350.0	349.8	349.3	348.8	348.3	347.8
130°	366.4	368.0	369.6	371.2	372.8	373.6	373.5	373.2	373.0	372.7	372.5
132.5°	391.7	392.9	394.1	395.4	396.6	397.2	397.3	397.4	397.5	397.7	397.8
135°	413.7	415.0	416.4	417.7	419.0	419.7	419.8	420.1	420.3	420.6	420.8
137.5°	437.9	439.0	440.1	441.2	442.3	442.8	442.9	443.2	443.4	443.7	443.9
140°	459.3	460.4	461.5	462.6	463.7	464.2	464.5	465.1	465.8	466.4	467.0
142.5°	481.3	482.4	483.5	484.6	485.7	486.2	486.4	486.8	487.1	487.5	487.9
145°	502.1	503.0	503.8	504.7	505.6	506.0	506.4	507.1	507.8	508.6	509.3
147.5°	520.8	521.9	523.0	524.1	525.2	525.8	526.0	526.5	527.0	527.5	528.0
150°	540.1	540.8	541.5	542.2	542.9	543.3	543.5	544.0	544.5	545.0	545.5
152.5°	557.1	557.8	558.6	559.3	560.0	560.4	560.7	561.3	561.9	562.5	563.1
155°	574.1	574.5	574.9	575.2	575.6	575.8	576.0	576.3	576.7	577.0	577.4
157.5°	588.9	589.1	589.4	589.6	589.9	590.0	590.1	590.4	590.6	590.9	591.1
160°	602.1	602.3	602.6	602.8	603.1	603.2	603.3	603.4	603.5	603.7	603.8
162.5°	614.2	614.2	614.2	614.2	614.2	614.2	614.3	614.4	614.5	614.7	614.8
165°	624.7	624.6	624.4	624.3	624.2	624.1	624.1	624.1	624.1	624.1	624.1
167.5°	634.0	633.6	633.2	632.9	632.5	632.3	632.3	632.3	632.3	632.3	632.3
170°	641.1	640.7	640.4	640.0	639.7	639.5	639.4	639.3	639.2	639.0	638.9
172.5°	646.1	645.7	645.3	645.0	644.6	644.4	644.3	644.2	644.1	644.0	643.9
175°	649.9	649.5	649.2	648.8	648.5	648.3	648.2	647.9	647.7	647.4	647.2
177.5°	652.1	651.7	651.4	651.0	650.7	650.5	650.4	650.1	649.9	649.6	649.4
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1470.4	1472.3	1475.3	1489.1	1491.1	1495.0	1493.1	1493.1	1494.0	1492.1	1493.1
5°	1533.5	1536.5	1551.3	1568.1	1572.0	1568.1	1573.0	1579.9	1579.9	1579.9	1577.9
7.5°	1592.7	1603.6	1620.4	1645.0	1650.0	1654.9	1663.8	1657.9	1659.8	1668.7	1665.8
10°	1650.0	1665.8	1684.5	1705.2	1716.1	1723.0	1726.9	1735.8	1756.5	1732.9	1741.7
12.5°	1704.2	1726.9	1746.7	1769.4	1777.3	1786.1	1789.1	1797.0	1797.0	1796.0	1802.9
15°	1739.8	1760.5	1778.3	1793.1	1795.0	1793.1	1791.1	1792.1	1795.0	1783.2	1790.1
17.5°	1747.7	1749.6	1755.6	1749.6	1750.6	1729.9	1718.1	1715.1	1687.5	1688.5	1711.1
20°	1709.2	1675.6	1666.7	1634.2	1614.4	1561.2	1559.2	1544.4	1486.2	1503.9	1500.0
22.5°	1603.6	1546.4	1470.4	1432.9	1414.1	1357.9	1314.4	1283.9	1263.1	1242.4	1233.5
25°	1464.4	1371.7	1264.1	1190.1	1179.3	1127.0	1047.0	1009.5	965.1	951.3	975.0
27.5°	1284.8	1164.4	1043.1	929.6	908.9	861.5	821.0	794.4	743.1	740.1	742.1
30°	1041.1	919.7	818.1	744.1	692.7	671.0	644.4	624.7	603.9	611.8	613.8
32.5°	855.6	740.1	645.4	605.9	582.2	568.4	545.7	532.9	524.0	521.0	520.1
35°	679.9	602.9	560.5	522.0	508.2	498.3	481.6	475.6	467.8	468.7	468.7
37.5°	582.2	518.1	486.5	466.8	453.9	449.0	438.1	432.2	427.3	425.3	428.3
40°	502.3	457.9	438.1	420.4	409.5	407.6	401.6	394.7	388.8	389.8	392.8
42.5°	444.1	418.4	394.7	380.9	373.0	370.1	365.1	360.2	360.2	357.2	356.2
45°	397.7	377.0	357.2	344.4	339.5	335.5	329.6	328.6	324.7	325.7	326.6
47.5°	356.2	339.5	324.7	311.8	306.9	305.9	300.0	296.0	296.0	295.1	294.1
50°	318.7	302.0	289.1	282.2	275.3	273.3	272.4	271.4	269.4	269.4	270.4
52.5°	288.2	271.4	261.5	255.6	251.6	249.7	249.7	248.7	248.7	248.7	247.7
55°	254.6	240.8	232.9	230.9	228.9	228.0	227.0	225.0	224.0	226.0	224.0
57.5°	223.0	218.1	211.2	209.2	204.3	204.3	201.3	199.3	197.4	199.3	199.3
60°	198.4	191.4	187.5	181.6	177.6	173.7	168.7	167.8	165.8	164.8	163.8
62.5°	172.7	166.8	156.9	148.0	142.1	138.2	136.2	135.2	135.2	134.2	134.2
65°	144.1	130.3	125.3	122.4	121.4	120.4	118.4	117.4	118.4	117.4	118.4
67.5°	112.5	110.5	107.6	105.6	104.6	103.6	103.6	102.6	102.6	102.6	102.6
70°	97.7	92.8	91.8	89.8	89.8	88.8	88.8	88.8	88.8	87.8	89.8
72.5°	80.9	78.0	77.0	76.0	76.0	76.0	75.0	75.0	75.0	74.0	75.0
75°	66.1	65.1	63.2	63.2	62.2	63.2	62.2	62.2	61.2	62.2	62.2
77.5°	53.3	52.3	51.3	51.3	50.3	50.3	50.3	50.3	50.3	50.3	51.3
80°	40.5	39.5	38.5	39.5	38.5	39.5	38.5	38.5	39.5	38.5	38.5
82.5°	29.6	28.6	28.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6
85°	17.8	16.8	16.8	17.8	16.8	17.8	16.8	16.8	16.8	17.8	17.8
87.5°	7.9	8.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	8.9
90°	19.0	18.7	18.5	18.2	18.1	18.2	18.3	18.4	18.6	18.7	18.6
92.5°	17.1	17.3	17.4	17.5	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.2	35.2	35.2	35.2	35.1	34.8	34.6	34.3	34.1	34.3
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.8	75.8	75.8	75.8	75.7	75.6	75.5	75.4	75.3	75.4
102.5°	98.4	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	98.4
105°	121.1	121.4	121.6	121.9	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	145.7	145.8	145.9	146.0	146.1	145.8	145.2	144.6	144.0	143.4	144.0
110°	170.9	170.9	170.9	170.9	170.9	170.7	170.3	170.0	169.6	169.2	169.6

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	196.3	195.9	195.6	195.2	195.0	194.9	194.6	194.4	194.1	193.9	194.1
115°	221.9	221.7	221.6	221.5	221.4	221.2	220.9	220.5	220.2	219.8	220.2
117.5°	246.8	246.5	246.1	245.8	245.6	245.4	245.0	244.7	244.3	243.9	244.3
120°	271.4	271.4	271.4	271.4	271.4	271.2	270.9	270.5	270.2	269.8	270.2
122.5°	297.4	297.0	296.7	296.3	296.1	296.0	295.7	295.5	295.2	295.0	295.2
125°	322.6	322.3	321.9	321.6	321.4	321.3	321.2	321.1	320.9	320.8	320.9
127.5°	347.3	346.8	346.3	345.8	345.6	345.4	345.0	344.7	344.3	343.9	344.3
130°	372.3	372.0	371.8	371.5	371.4	371.2	370.7	370.2	369.7	369.2	369.7
132.5°	397.2	396.6	395.9	395.3	395.0	394.8	394.5	394.1	393.8	393.4	393.8
135°	420.7	420.6	420.5	420.4	420.3	420.1	419.7	419.4	419.0	418.6	419.0
137.5°	443.8	443.7	443.6	443.5	443.4	443.2	442.7	442.2	441.7	441.2	441.7
140°	467.0	467.0	467.0	467.0	467.0	466.8	466.3	465.8	465.3	464.8	465.3
142.5°	488.0	488.1	488.2	488.3	488.4	488.2	487.7	487.2	486.7	486.2	486.7
145°	509.4	509.5	509.6	509.7	509.8	509.6	509.1	508.6	508.1	507.6	508.1
147.5°	528.2	528.5	528.7	529.0	529.1	528.9	528.4	527.9	527.4	526.9	527.4
150°	545.9	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.9
152.5°	563.6	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	563.6
155°	578.0	578.6	579.3	579.9	580.2	580.0	579.6	579.3	578.9	578.5	578.9
157.5°	592.0	592.8	593.7	594.6	595.0	594.7	594.1	593.4	592.8	592.2	592.8
160°	604.5	605.3	606.0	606.7	607.1	606.9	606.4	605.9	605.4	604.9	605.4
162.5°	615.6	616.5	617.3	618.2	618.6	618.3	617.7	617.1	616.5	615.9	616.5
165°	625.0	625.8	626.7	627.6	628.0	627.7	627.1	626.4	625.8	625.2	625.8
167.5°	633.2	634.0	634.9	635.8	636.2	635.9	635.3	634.6	634.0	633.4	634.0
170°	639.8	640.6	641.5	642.4	642.8	642.4	641.7	641.0	640.2	639.5	640.2
172.5°	644.7	645.6	646.4	647.3	647.7	647.3	646.6	645.9	645.1	644.4	645.1
175°	648.0	648.9	649.7	650.6	651.0	650.6	649.9	649.2	648.4	647.7	648.4
177.5°	650.1	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	650.1
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1497.0	1490.1	1488.1	1490.1	1488.1	1489.1	1482.2	1456.5	1463.5	1452.6	1458.5
5°	1581.9	1576.0	1563.1	1561.2	1559.2	1557.2	1547.3	1524.6	1515.8	1501.0	1500.0
7.5°	1662.8	1662.8	1652.9	1646.0	1637.1	1630.2	1617.4	1583.8	1570.0	1552.3	1542.4
10°	1742.7	1717.1	1727.9	1721.0	1699.3	1695.4	1671.7	1651.9	1625.3	1607.5	1591.7
12.5°	1800.0	1792.1	1782.2	1776.3	1770.4	1757.5	1741.7	1691.4	1677.6	1642.1	1624.3
15°	1798.0	1793.1	1796.0	1796.0	1794.0	1791.1	1778.3	1741.7	1718.1	1683.5	1652.9
17.5°	1701.3	1714.1	1726.9	1735.8	1755.6	1764.4	1776.3	1754.6	1739.8	1710.2	1677.6
20°	1532.5	1564.1	1601.6	1609.5	1627.3	1679.6	1703.3	1722.0	1727.9	1718.1	1691.4
22.5°	1297.7	1324.3	1415.1	1413.1	1438.8	1501.0	1570.0	1626.3	1670.7	1695.4	1685.5
25°	1016.4	1053.9	1102.3	1138.8	1222.7	1315.4	1401.3	1491.1	1568.1	1636.2	1652.9
27.5°	768.7	818.1	856.6	904.9	947.3	1056.9	1167.4	1307.5	1397.3	1526.6	1593.7
30°	621.7	644.4	682.9	705.6	726.3	810.2	935.5	1073.7	1231.6	1380.6	1496.0
32.5°	530.9	546.7	575.3	585.2	606.9	663.1	742.1	868.4	1031.2	1211.8	1363.8
35°	476.6	493.4	499.3	508.2	526.0	561.5	615.8	707.6	854.6	1031.2	1212.8
37.5°	430.3	439.1	455.9	461.8	467.8	494.4	530.9	595.1	692.7	837.8	1039.1
40°	397.7	402.6	411.5	416.4	420.4	439.1	471.7	515.1	587.2	697.7	883.2
42.5°	363.2	369.1	375.0	380.9	385.8	400.6	420.4	461.8	510.2	594.1	728.3
45°	329.6	333.5	340.5	344.4	351.3	363.2	380.9	409.5	453.0	506.2	614.8
47.5°	299.0	303.9	306.9	311.8	316.8	329.6	346.4	365.1	400.6	453.0	531.9
50°	271.4	277.3	281.2	282.2	286.2	298.0	311.8	332.6	355.3	395.7	464.8
52.5°	251.6	252.6	255.6	259.5	258.5	265.5	278.3	294.1	317.8	350.3	400.6
55°	228.9	231.9	233.9	234.9	234.9	240.8	247.7	262.5	281.2	307.9	350.3
57.5°	200.3	203.3	209.2	211.2	214.1	217.1	220.1	229.9	245.7	271.4	305.9
60°	170.7	172.7	178.6	182.6	184.5	192.4	196.4	204.3	213.2	231.9	264.5
62.5°	137.2	139.1	142.1	146.0	150.0	161.8	171.7	179.6	186.5	199.3	226.0
65°	119.4	120.4	122.4	123.4	124.3	129.3	138.2	149.0	161.8	171.7	187.5
67.5°	103.6	104.6	105.6	107.6	108.6	109.5	113.5	116.4	129.3	143.1	154.9
70°	88.8	90.8	91.8	91.8	92.8	94.7	96.7	100.7	104.6	111.5	126.3
72.5°	75.0	76.0	78.0	78.0	78.0	79.9	81.9	83.9	85.9	89.8	95.7
75°	62.2	64.1	64.1	64.1	65.1	65.1	67.1	69.1	71.1	74.0	76.0
77.5°	51.3	51.3	51.3	51.3	52.3	52.3	53.3	55.3	56.2	57.2	59.2
80°	38.5	39.5	39.5	39.5	40.5	40.5	40.5	42.4	43.4	43.4	45.4
82.5°	28.6	28.6	28.6	29.6	28.6	29.6	29.6	30.6	29.6	30.6	31.6
85°	17.8	17.8	17.8	18.7	18.7	18.7	18.7	18.7	18.7	18.7	19.7
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	9.9	8.9	8.9
90°	18.4	18.3	18.2	18.1	18.2	18.5	18.7	19.0	19.2	16.5	13.8
92.5°	17.6	17.6	17.6	17.6	17.5	17.4	17.3	17.1	17.0	16.9	16.8
95°	34.6	34.8	35.1	35.2	35.2	35.2	35.2	35.2	35.2	35.0	34.7
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.4	53.9
100°	75.5	75.6	75.7	75.8	75.8	75.8	75.8	75.8	75.8	75.4	75.1
102.5°	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	97.8	97.3
105°	122.0	122.0	122.0	122.0	121.9	121.6	121.4	121.1	120.9	120.7	120.4
107.5°	144.6	145.2	145.8	146.1	146.0	145.9	145.8	145.7	145.6	145.6	145.6
110°	170.0	170.3	170.7	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	194.4	194.6	194.9	195.0	195.2	195.6	195.9	196.3	196.7	196.8	196.9
115°	220.5	220.9	221.2	221.4	221.5	221.6	221.7	221.9	222.0	222.2	222.5
117.5°	244.7	245.0	245.4	245.6	245.8	246.1	246.5	246.8	247.2	247.8	248.4
120°	270.5	270.9	271.2	271.4	271.4	271.4	271.4	271.4	271.4	272.4	273.4
122.5°	295.5	295.7	296.0	296.1	296.3	296.7	297.0	297.4	297.8	298.4	299.0
125°	321.1	321.2	321.3	321.4	321.6	321.9	322.3	322.6	323.0	323.4	323.8
127.5°	344.7	345.0	345.4	345.6	345.8	346.3	346.8	347.3	347.8	348.3	348.8
130°	370.2	370.7	371.2	371.4	371.5	371.8	372.0	372.3	372.5	372.7	373.0
132.5°	394.1	394.5	394.8	395.0	395.3	395.9	396.6	397.2	397.8	397.7	397.5
135°	419.4	419.7	420.1	420.3	420.4	420.5	420.6	420.7	420.8	420.6	420.3
137.5°	442.2	442.7	443.2	443.4	443.5	443.6	443.7	443.8	443.9	443.7	443.4
140°	465.8	466.3	466.8	467.0	467.0	467.0	467.0	467.0	467.0	466.4	465.8
142.5°	487.2	487.7	488.2	488.4	488.3	488.2	488.1	488.0	487.9	487.5	487.1
145°	508.6	509.1	509.6	509.8	509.7	509.6	509.5	509.4	509.3	508.6	507.8
147.5°	527.9	528.4	528.9	529.1	529.0	528.7	528.5	528.2	528.0	527.5	527.0
150°	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.0	544.5
152.5°	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	562.5	561.9
155°	579.3	579.6	580.0	580.2	579.9	579.3	578.6	578.0	577.4	577.0	576.7
157.5°	593.4	594.1	594.7	595.0	594.6	593.7	592.8	592.0	591.1	590.9	590.6
160°	605.9	606.4	606.9	607.1	606.7	606.0	605.3	604.5	603.8	603.7	603.5
162.5°	617.1	617.7	618.3	618.6	618.2	617.3	616.5	615.6	614.8	614.7	614.5
165°	626.4	627.1	627.7	628.0	627.6	626.7	625.8	625.0	624.1	624.1	624.1
167.5°	634.6	635.3	635.9	636.2	635.8	634.9	634.0	633.2	632.3	632.3	632.3
170°	641.0	641.7	642.4	642.8	642.4	641.5	640.6	639.8	638.9	639.0	639.2
172.5°	645.9	646.6	647.3	647.7	647.3	646.4	645.6	644.7	643.9	644.0	644.1
175°	649.2	649.9	650.6	651.0	650.6	649.7	648.9	648.0	647.2	647.4	647.7
177.5°	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	649.6	649.9
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1449.6	1444.7	1444.7	1441.7	1441.7	1426.0	1426.0	1430.9	1425.0	1418.1	1408.2
5°	1487.1	1476.3	1473.3	1469.4	1456.5	1436.8	1428.9	1426.0	1414.1	1399.3	1382.5
7.5°	1522.7	1504.9	1496.0	1487.1	1470.4	1442.7	1426.9	1416.1	1398.3	1375.6	1353.9
10°	1557.2	1534.5	1511.8	1501.0	1477.3	1442.7	1420.0	1402.3	1376.6	1346.0	1315.4
12.5°	1588.8	1541.4	1537.5	1515.8	1481.2	1441.7	1407.2	1381.6	1349.0	1313.5	1277.9
15°	1616.4	1568.1	1544.4	1524.6	1479.2	1429.9	1393.4	1361.8	1318.4	1277.9	1234.5
17.5°	1630.2	1577.9	1562.1	1529.6	1483.2	1419.1	1369.7	1331.2	1283.9	1235.5	1186.2
20°	1644.0	1582.9	1557.2	1534.5	1471.4	1398.3	1343.1	1298.7	1246.4	1189.1	1134.8
22.5°	1651.0	1582.9	1552.3	1520.7	1459.5	1375.6	1310.5	1258.2	1197.0	1138.8	1073.7
25°	1639.1	1576.9	1540.4	1507.9	1438.8	1348.0	1273.0	1213.8	1148.7	1082.5	1016.4
27.5°	1609.5	1563.1	1520.7	1487.1	1410.2	1312.5	1233.5	1166.4	1099.3	1025.3	958.2
30°	1554.2	1533.5	1500.0	1462.5	1378.6	1280.9	1187.1	1118.1	1044.1	970.0	900.0
32.5°	1468.4	1486.2	1464.4	1431.9	1341.1	1237.5	1137.8	1067.7	986.8	906.9	842.7
35°	1363.8	1426.9	1415.1	1392.4	1301.6	1191.1	1091.4	1006.6	925.6	844.7	780.6
37.5°	1249.3	1345.0	1354.9	1341.1	1256.2	1143.7	1034.2	951.3	868.4	786.5	721.4
40°	1092.4	1239.4	1271.0	1276.9	1208.9	1086.5	972.0	891.1	809.2	729.3	650.3
42.5°	948.3	1133.9	1173.3	1198.0	1148.7	1030.2	914.8	825.0	744.1	672.0	593.1
45°	813.1	1006.6	1070.7	1102.3	1080.6	966.1	846.7	762.8	688.8	622.7	546.7
47.5°	674.0	868.4	958.2	1008.5	1008.5	901.0	781.6	698.7	627.6	571.4	504.3
50°	581.2	743.1	835.8	902.0	919.7	834.9	722.4	641.4	574.3	513.1	461.8
52.5°	495.4	640.4	717.4	786.5	837.8	763.8	656.2	583.2	517.1	459.9	419.4
55°	428.3	536.8	606.9	682.9	740.1	691.8	592.1	521.0	463.8	416.4	381.9
57.5°	364.1	458.9	516.1	583.2	644.4	607.9	527.9	466.8	416.4	375.0	344.4
60°	309.9	386.8	431.2	483.5	559.5	533.9	467.8	411.5	371.0	333.5	307.9
62.5°	263.5	324.7	362.2	399.7	468.7	456.9	405.6	362.2	327.6	296.0	274.3
65°	216.1	266.4	296.0	328.6	383.9	388.8	347.4	316.8	285.2	257.6	237.8
67.5°	174.7	214.1	240.8	268.4	312.8	326.6	298.0	272.4	245.7	223.0	205.3
70°	141.1	168.7	188.5	210.2	246.7	263.5	248.7	230.9	209.2	190.5	174.7
72.5°	111.5	129.3	141.1	157.9	187.5	204.3	203.3	187.5	171.7	158.9	146.0
75°	81.9	95.7	105.6	116.4	140.1	155.9	159.9	153.0	137.2	127.3	117.4
77.5°	62.2	70.1	75.0	82.9	99.7	113.5	119.4	117.4	106.6	98.7	91.8
80°	47.4	49.3	51.3	54.3	68.1	80.9	84.9	83.9	78.0	75.0	67.1
82.5°	33.6	34.5	35.5	36.5	41.4	52.3	56.2	58.2	53.3	50.3	43.4
85°	19.7	20.7	20.7	22.7	23.7	26.6	33.6	33.6	32.6	28.6	27.6
87.5°	9.9	9.9	8.9	8.9	9.9	10.9	12.8	14.8	12.8	11.8	10.9
90°	11.1	8.4	7.1	6.4	4.9	3.4	2.0	0.5	2.0	3.4	4.9
92.5°	16.7	16.6	16.5	16.0	15.0	14.1	13.1	12.1	13.1	14.1	15.0
95°	34.5	34.2	34.1	33.5	32.3	31.0	29.8	28.6	29.8	31.0	32.3
97.5°	53.4	52.9	52.7	52.2	51.1	50.0	48.9	47.8	48.9	50.0	51.1
100°	74.7	74.4	74.2	73.7	72.7	71.8	70.8	69.8	70.8	71.8	72.7
102.5°	96.8	96.3	96.1	95.7	95.0	94.3	93.5	92.8	93.5	94.3	95.0
105°	120.2	119.9	119.8	119.6	119.2	118.9	118.5	118.1	118.5	118.9	119.2
107.5°	145.6	145.6	145.6	145.4	144.9	144.4	143.9	143.4	143.9	144.4	144.9
110°	170.9	170.9	170.9	170.5	169.8	169.1	168.3	167.6	168.3	169.1	169.8

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	197.0	197.1	197.2	196.8	196.1	195.4	194.6	193.9	194.6	195.4	196.1
115°	222.7	223.0	223.1	222.7	222.0	221.3	220.5	219.8	220.5	221.3	222.0
117.5°	249.1	249.7	250.0	249.5	248.5	247.6	246.6	245.6	246.6	247.6	248.5
120°	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4	272.4	273.4	274.3
122.5°	299.6	300.2	300.5	299.9	298.7	297.4	296.2	295.0	296.2	297.4	298.7
125°	324.1	324.5	324.7	324.1	323.0	321.9	320.8	319.7	320.8	321.9	323.0
127.5°	349.3	349.8	350.0	349.3	348.0	346.6	345.3	343.9	345.3	346.6	348.0
130°	373.2	373.5	373.6	372.8	371.2	369.6	368.0	366.4	368.0	369.6	371.2
132.5°	397.4	397.3	397.2	396.6	395.4	394.1	392.9	391.7	392.9	394.1	395.4
135°	420.1	419.8	419.7	419.0	417.7	416.4	415.0	413.7	415.0	416.4	417.7
137.5°	443.2	442.9	442.8	442.3	441.2	440.1	439.0	437.9	439.0	440.1	441.2
140°	465.1	464.5	464.2	463.7	462.6	461.5	460.4	459.3	460.4	461.5	462.6
142.5°	486.8	486.4	486.2	485.7	484.6	483.5	482.4	481.3	482.4	483.5	484.6
145°	507.1	506.4	506.0	505.6	504.7	503.8	503.0	502.1	503.0	503.8	504.7
147.5°	526.5	526.0	525.8	525.2	524.1	523.0	521.9	520.8	521.9	523.0	524.1
150°	544.0	543.5	543.3	542.9	542.2	541.5	540.8	540.1	540.8	541.5	542.2
152.5°	561.3	560.7	560.4	560.0	559.3	558.6	557.8	557.1	557.8	558.6	559.3
155°	576.3	576.0	575.8	575.6	575.2	574.9	574.5	574.1	574.5	574.9	575.2
157.5°	590.4	590.1	590.0	589.9	589.6	589.4	589.1	588.9	589.1	589.4	589.6
160°	603.4	603.3	603.2	603.1	602.8	602.6	602.3	602.1	602.3	602.6	602.8
162.5°	614.4	614.3	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2
165°	624.1	624.1	624.1	624.2	624.3	624.4	624.6	624.7	624.6	624.4	624.3
167.5°	632.3	632.3	632.3	632.5	632.9	633.2	633.6	634.0	633.6	633.2	632.9
170°	639.3	639.4	639.5	639.7	640.0	640.4	640.7	641.1	640.7	640.4	640.0
172.5°	644.2	644.3	644.4	644.6	645.0	645.3	645.7	646.1	645.7	645.3	645.0
175°	647.9	648.2	648.3	648.5	648.8	649.2	649.5	649.9	649.5	649.2	648.8
177.5°	650.1	650.4	650.5	650.7	651.0	651.4	651.7	652.1	651.7	651.4	651.0
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1404.2	1405.2	1408.2	1399.3	1385.5	1379.6	1361.8	1358.9	1355.9	1355.9	1358.9
5°	1372.7	1368.7	1369.7	1352.9	1333.2	1321.4	1296.7	1300.6	1287.8	1279.9	1281.9
7.5°	1338.1	1327.3	1326.3	1304.6	1279.9	1258.2	1232.5	1226.6	1214.8	1201.0	1195.0
10°	1294.7	1286.8	1272.0	1247.3	1215.8	1198.0	1163.5	1142.7	1139.8	1119.1	1111.2
12.5°	1250.3	1236.5	1221.7	1187.1	1151.6	1123.0	1097.3	1074.6	1058.9	1041.1	1029.3
15°	1199.0	1182.2	1165.4	1128.9	1087.5	1058.9	1020.4	986.8	940.4	903.9	883.2
17.5°	1142.7	1124.0	1101.3	1060.8	1020.4	980.9	909.8	870.4	837.8	816.1	803.3
20°	1084.5	1063.8	1041.1	1000.6	930.6	861.5	822.0	791.4	771.7	750.0	734.2
22.5°	1023.3	1001.6	977.0	913.8	839.8	791.4	760.8	732.2	703.6	691.8	683.9
25°	966.1	946.4	914.8	828.9	770.7	726.3	691.8	673.0	658.2	642.4	627.6
27.5°	906.9	870.4	826.0	753.9	717.4	672.0	647.4	633.5	607.9	597.0	590.1
30°	835.8	795.4	752.9	701.6	659.2	627.6	604.9	582.2	567.4	556.6	544.7
32.5°	763.8	725.3	698.7	645.4	613.8	581.2	559.5	545.7	524.0	517.1	512.2
35°	701.6	669.1	645.4	602.0	572.4	542.8	527.0	506.2	492.4	479.6	471.7
37.5°	640.4	622.7	598.0	561.5	529.9	506.2	484.5	477.6	458.9	452.0	444.1
40°	598.0	571.4	550.6	519.1	492.4	466.8	453.0	437.2	424.3	413.5	410.5
42.5°	546.7	527.0	515.1	480.6	453.0	438.1	421.4	403.6	393.7	384.9	374.0
45°	508.2	490.5	473.7	446.0	421.4	402.6	387.8	376.0	359.2	355.3	338.5
47.5°	467.8	450.0	437.2	409.5	386.8	369.1	358.2	342.4	328.6	319.7	311.8
50°	427.3	412.5	400.6	377.0	357.2	338.5	323.7	307.9	302.0	287.2	282.2
52.5°	388.8	378.9	366.1	343.4	323.7	307.9	292.1	279.3	270.4	262.5	256.6
55°	356.2	340.5	334.5	309.9	293.1	276.3	262.5	254.6	243.7	238.8	233.9
57.5°	319.7	310.8	301.0	282.2	263.5	247.7	237.8	226.0	220.1	214.1	210.2
60°	288.2	275.3	267.4	251.6	234.9	220.1	211.2	202.3	194.4	189.5	181.6
62.5°	251.6	241.8	236.8	220.1	206.2	192.4	184.5	175.7	169.7	160.9	151.0
65°	220.1	212.2	206.2	192.4	179.6	166.8	158.9	148.0	140.1	135.2	134.2
67.5°	192.4	186.5	177.6	164.8	152.0	142.1	133.2	124.3	123.4	121.4	121.4
70°	161.8	155.9	151.0	137.2	126.3	115.5	113.5	110.5	107.6	106.6	104.6
72.5°	135.2	130.3	124.3	112.5	101.6	98.7	96.7	94.7	91.8	90.8	89.8
75°	109.5	102.6	98.7	87.8	84.9	82.9	80.9	78.0	76.0	75.0	73.0
77.5°	83.9	77.0	77.0	71.1	69.1	66.1	64.1	62.2	61.2	59.2	59.2
80°	59.2	59.2	57.2	54.3	51.3	50.3	47.4	46.4	45.4	46.4	44.4
82.5°	43.4	39.5	39.5	37.5	35.5	34.5	32.6	32.6	31.6	31.6	31.6
85°	24.7	24.7	23.7	21.7	20.7	20.7	19.7	19.7	18.7	18.7	17.8
87.5°	9.9	8.9	9.9	8.9	8.9	7.9	7.9	7.9	6.9	7.9	6.9
90°	6.4	7.1	8.4	11.1	13.8	16.5	19.2	19.0	18.7	18.5	18.2
92.5°	16.0	16.5	16.6	16.7	16.8	16.9	17.0	17.1	17.3	17.4	17.5
95°	33.5	34.1	34.2	34.5	34.7	35.0	35.2	35.2	35.2	35.2	35.2
97.5°	52.2	52.7	52.9	53.4	53.9	54.4	54.9	54.9	54.9	54.9	54.9
100°	73.7	74.2	74.4	74.7	75.1	75.4	75.8	75.8	75.8	75.8	75.8
102.5°	95.7	96.1	96.3	96.8	97.3	97.8	98.3	98.4	98.6	98.7	98.8
105°	119.6	119.8	119.9	120.2	120.4	120.7	120.9	121.1	121.4	121.6	121.9
107.5°	145.4	145.6	145.6	145.6	145.6	145.6	145.6	145.7	145.8	145.9	146.0
110°	170.5	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	196.8	197.2	197.1	197.0	196.9	196.8	196.7	196.3	195.9	195.6	195.2
115°	222.7	223.1	223.0	222.7	222.5	222.2	222.0	221.9	221.7	221.6	221.5
117.5°	249.5	250.0	249.7	249.1	248.4	247.8	247.2	246.8	246.5	246.1	245.8
120°	275.3	275.8	275.3	274.3	273.4	272.4	271.4	271.4	271.4	271.4	271.4
122.5°	299.9	300.5	300.2	299.6	299.0	298.4	297.8	297.4	297.0	296.7	296.3
125°	324.1	324.7	324.5	324.1	323.8	323.4	323.0	322.6	322.3	321.9	321.6
127.5°	349.3	350.0	349.8	349.3	348.8	348.3	347.8	347.3	346.8	346.3	345.8
130°	372.8	373.6	373.5	373.2	373.0	372.7	372.5	372.3	372.0	371.8	371.5
132.5°	396.6	397.2	397.3	397.4	397.5	397.7	397.8	397.2	396.6	395.9	395.3
135°	419.0	419.7	419.8	420.1	420.3	420.6	420.8	420.7	420.6	420.5	420.4
137.5°	442.3	442.8	442.9	443.2	443.4	443.7	443.9	443.8	443.7	443.6	443.5
140°	463.7	464.2	464.5	465.1	465.8	466.4	467.0	467.0	467.0	467.0	467.0
142.5°	485.7	486.2	486.4	486.8	487.1	487.5	487.9	488.0	488.1	488.2	488.3
145°	505.6	506.0	506.4	507.1	507.8	508.6	509.3	509.4	509.5	509.6	509.7
147.5°	525.2	525.8	526.0	526.5	527.0	527.5	528.0	528.2	528.5	528.7	529.0
150°	542.9	543.3	543.5	544.0	544.5	545.0	545.5	545.9	546.3	546.6	547.0
152.5°	560.0	560.4	560.7	561.3	561.9	562.5	563.1	563.6	564.1	564.6	565.1
155°	575.6	575.8	576.0	576.3	576.7	577.0	577.4	578.0	578.6	579.3	579.9
157.5°	589.9	590.0	590.1	590.4	590.6	590.9	591.1	592.0	592.8	593.7	594.6
160°	603.1	603.2	603.3	603.4	603.5	603.7	603.8	604.5	605.3	606.0	606.7
162.5°	614.2	614.2	614.3	614.4	614.5	614.7	614.8	615.6	616.5	617.3	618.2
165°	624.2	624.1	624.1	624.1	624.1	624.1	624.1	625.0	625.8	626.7	627.6
167.5°	632.5	632.3	632.3	632.3	632.3	632.3	632.3	633.2	634.0	634.9	635.8
170°	639.7	639.5	639.4	639.3	639.2	639.0	638.9	639.8	640.6	641.5	642.4
172.5°	644.6	644.4	644.3	644.2	644.1	644.0	643.9	644.7	645.6	646.4	647.3
175°	648.5	648.3	648.2	647.9	647.7	647.4	647.2	648.0	648.9	649.7	650.6
177.5°	650.7	650.5	650.4	650.1	649.9	649.6	649.4	650.1	650.9	651.6	652.3
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1358.9	1356.9	1351.0	1352.9	1350.0	1350.0	1348.0	1348.0	1348.0	1352.9	1350.0
5°	1284.8	1277.9	1271.0	1268.1	1265.1	1262.1	1262.1	1261.2	1270.0	1268.1	1276.0
7.5°	1193.1	1191.1	1177.3	1177.3	1172.3	1170.4	1175.3	1176.3	1177.3	1179.3	1184.2
10°	1111.2	1106.2	1086.5	1088.5	1085.5	1081.6	1084.5	1082.5	1089.5	1091.4	1089.5
12.5°	1014.5	1005.6	983.9	973.0	961.2	952.3	963.1	955.2	982.9	990.8	1012.5
15°	886.2	869.4	854.6	854.6	843.7	835.8	840.8	849.7	855.6	864.5	868.4
17.5°	800.3	793.4	781.6	774.7	771.7	768.7	768.7	772.7	785.5	784.5	792.4
20°	727.3	723.3	717.4	708.5	705.6	703.6	703.6	703.6	712.5	720.4	725.3
22.5°	677.0	674.0	670.1	658.2	652.3	650.3	655.2	658.2	665.1	671.0	676.0
25°	626.6	619.7	612.8	608.9	605.9	605.9	607.9	608.9	611.8	614.8	620.7
27.5°	585.2	580.3	570.4	559.5	559.5	556.6	558.5	560.5	567.4	577.3	582.2
30°	538.8	537.8	533.9	529.9	526.0	524.0	527.9	530.9	531.9	536.8	536.8
32.5°	505.3	498.3	491.4	487.5	485.5	484.5	485.5	489.5	489.5	495.4	502.3
35°	471.7	467.8	460.8	453.9	452.0	447.0	451.0	454.9	461.8	464.8	467.8
37.5°	435.2	430.3	427.3	425.3	421.4	422.4	419.4	425.3	431.2	430.3	432.2
40°	407.6	398.7	389.8	388.8	387.8	386.8	386.8	387.8	391.8	395.7	401.6
42.5°	372.0	369.1	361.2	353.3	351.3	349.3	347.4	351.3	359.2	366.1	369.1
45°	335.5	331.6	329.6	323.7	319.7	318.7	316.8	321.7	328.6	331.6	333.5
47.5°	302.0	301.0	295.1	296.0	293.1	294.1	293.1	296.0	296.0	299.0	301.0
50°	279.3	276.3	273.3	271.4	268.4	268.4	267.4	268.4	272.4	276.3	275.3
52.5°	256.6	251.6	250.7	249.7	247.7	249.7	246.7	247.7	251.6	253.6	252.6
55°	229.9	228.9	227.0	225.0	224.0	223.0	223.0	223.0	227.0	229.9	230.9
57.5°	209.2	204.3	200.3	200.3	196.4	195.4	197.4	198.4	201.3	203.3	205.3
60°	180.6	178.6	172.7	169.7	163.8	162.8	162.8	166.8	171.7	178.6	180.6
62.5°	150.0	147.0	146.0	146.0	146.0	146.0	146.0	146.0	146.0	147.0	147.0
65°	133.2	134.2	133.2	132.2	133.2	133.2	132.2	132.2	132.2	133.2	134.2
67.5°	119.4	118.4	119.4	118.4	117.4	117.4	116.4	117.4	118.4	119.4	119.4
70°	103.6	103.6	102.6	103.6	102.6	101.6	100.7	100.7	102.6	103.6	103.6
72.5°	88.8	88.8	87.8	87.8	85.9	85.9	86.8	85.9	85.9	88.8	88.8
75°	74.0	73.0	72.0	72.0	71.1	71.1	71.1	70.1	72.0	72.0	73.0
77.5°	58.2	58.2	58.2	57.2	57.2	56.2	56.2	57.2	57.2	57.2	58.2
80°	44.4	44.4	44.4	43.4	42.4	42.4	42.4	42.4	42.4	43.4	42.4
82.5°	30.6	30.6	30.6	30.6	30.6	29.6	29.6	29.6	30.6	30.6	29.6
85°	18.7	17.8	18.7	18.7	17.8	18.7	17.8	17.8	16.8	16.8	17.8
87.5°	7.9	6.9	5.9	5.9	6.9	5.9	5.9	5.9	6.9	5.9	5.9
90°	18.1	18.2	18.3	18.4	18.6	18.7	18.6	18.4	18.3	18.2	18.1
92.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.1	34.8	34.6	34.3	34.1	34.3	34.6	34.8	35.1	35.2
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.7	75.6	75.5	75.4	75.3	75.4	75.5	75.6	75.7	75.8
102.5°	98.9	98.8	98.7	98.6	98.4	98.3	98.4	98.6	98.7	98.8	98.9
105°	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	146.1	145.8	145.2	144.6	144.0	143.4	144.0	144.6	145.2	145.8	146.1
110°	170.9	170.7	170.3	170.0	169.6	169.2	169.6	170.0	170.3	170.7	170.9

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	195.0	194.9	194.6	194.4	194.1	193.9	194.1	194.4	194.6	194.9	195.0
115°	221.4	221.2	220.9	220.5	220.2	219.8	220.2	220.5	220.9	221.2	221.4
117.5°	245.6	245.4	245.0	244.7	244.3	243.9	244.3	244.7	245.0	245.4	245.6
120°	271.4	271.2	270.9	270.5	270.2	269.8	270.2	270.5	270.9	271.2	271.4
122.5°	296.1	296.0	295.7	295.5	295.2	295.0	295.2	295.5	295.7	296.0	296.1
125°	321.4	321.3	321.2	321.1	320.9	320.8	320.9	321.1	321.2	321.3	321.4
127.5°	345.6	345.4	345.0	344.7	344.3	343.9	344.3	344.7	345.0	345.4	345.6
130°	371.4	371.2	370.7	370.2	369.7	369.2	369.7	370.2	370.7	371.2	371.4
132.5°	395.0	394.8	394.5	394.1	393.8	393.4	393.8	394.1	394.5	394.8	395.0
135°	420.3	420.1	419.7	419.4	419.0	418.6	419.0	419.4	419.7	420.1	420.3
137.5°	443.4	443.2	442.7	442.2	441.7	441.2	441.7	442.2	442.7	443.2	443.4
140°	467.0	466.8	466.3	465.8	465.3	464.8	465.3	465.8	466.3	466.8	467.0
142.5°	488.4	488.2	487.7	487.2	486.7	486.2	486.7	487.2	487.7	488.2	488.4
145°	509.8	509.6	509.1	508.6	508.1	507.6	508.1	508.6	509.1	509.6	509.8
147.5°	529.1	528.9	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1
150°	547.2	547.0	546.6	546.3	545.9	545.5	545.9	546.3	546.6	547.0	547.2
152.5°	565.3	565.1	564.6	564.1	563.6	563.1	563.6	564.1	564.6	565.1	565.3
155°	580.2	580.0	579.6	579.3	578.9	578.5	578.9	579.3	579.6	580.0	580.2
157.5°	595.0	594.7	594.1	593.4	592.8	592.2	592.8	593.4	594.1	594.7	595.0
160°	607.1	606.9	606.4	605.9	605.4	604.9	605.4	605.9	606.4	606.9	607.1
162.5°	618.6	618.3	617.7	617.1	616.5	615.9	616.5	617.1	617.7	618.3	618.6
165°	628.0	627.7	627.1	626.4	625.8	625.2	625.8	626.4	627.1	627.7	628.0
167.5°	636.2	635.9	635.3	634.6	634.0	633.4	634.0	634.6	635.3	635.9	636.2
170°	642.8	642.4	641.7	641.0	640.2	639.5	640.2	641.0	641.7	642.4	642.8
172.5°	647.7	647.3	646.6	645.9	645.1	644.4	645.1	645.9	646.6	647.3	647.7
175°	651.0	650.6	649.9	649.2	648.4	647.7	648.4	649.2	649.9	650.6	651.0
177.5°	652.7	652.3	651.6	650.9	650.1	649.4	650.1	650.9	651.6	652.3	652.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1352.9	1357.9	1355.9	1345.0	1355.9	1358.9	1364.8	1370.7	1374.6	1380.6	1385.5
5°	1268.1	1277.9	1283.9	1277.9	1297.7	1300.6	1314.4	1322.3	1334.2	1344.1	1351.9
7.5°	1188.1	1196.0	1207.9	1209.8	1221.7	1235.5	1255.2	1275.0	1293.7	1303.6	1312.5
10°	1102.3	1116.1	1133.9	1129.9	1147.7	1169.4	1190.1	1221.7	1237.5	1255.2	1271.0
12.5°	1016.4	1025.3	1049.0	1056.9	1082.5	1099.3	1127.9	1147.7	1187.1	1207.9	1221.7
15°	866.4	902.9	932.5	968.1	1001.6	1033.2	1058.9	1094.4	1128.9	1144.7	1167.4
17.5°	798.3	815.1	832.9	850.6	894.1	950.3	995.7	1034.2	1063.8	1084.5	1111.2
20°	727.3	744.1	763.8	780.6	807.2	847.7	903.9	970.0	1005.6	1027.3	1052.9
22.5°	677.0	692.7	705.6	720.4	741.1	770.7	813.1	895.0	942.4	969.1	991.8
25°	622.7	642.4	656.2	667.1	683.9	716.4	751.0	797.4	882.2	902.9	934.5
27.5°	585.2	591.1	606.9	623.7	640.4	658.2	693.7	733.2	790.4	835.8	874.3
30°	540.8	555.6	570.4	577.3	592.1	617.8	639.5	681.9	726.3	761.8	808.2
32.5°	507.2	516.1	526.0	542.8	556.6	574.3	596.0	631.6	669.1	691.8	727.3
35°	469.7	475.6	496.4	503.3	517.1	534.9	556.6	584.2	624.7	642.4	668.1
37.5°	434.2	448.0	453.9	469.7	482.6	500.3	516.1	547.7	574.3	595.1	618.7
40°	406.6	412.5	423.3	437.2	448.0	461.8	481.6	504.3	532.9	549.7	570.4
42.5°	373.0	378.0	391.8	399.7	417.4	430.3	442.1	469.7	495.4	508.2	528.9
45°	336.5	348.3	357.2	373.0	382.9	398.7	413.5	433.2	456.9	471.7	483.5
47.5°	304.9	316.8	325.7	340.5	356.2	363.2	378.9	399.7	421.4	433.2	450.0
50°	279.3	283.2	300.0	306.9	323.7	337.5	348.3	366.1	389.8	396.7	410.5
52.5°	254.6	257.6	268.4	277.3	292.1	303.9	317.8	334.5	354.3	365.1	376.0
55°	232.9	234.9	239.8	249.7	259.5	274.3	287.2	303.0	319.7	331.6	341.4
57.5°	208.2	212.2	216.1	222.0	231.9	245.7	259.5	274.3	288.2	296.0	308.9
60°	179.6	185.5	192.4	199.3	206.2	216.1	231.9	245.7	258.5	265.5	275.3
62.5°	149.0	160.9	166.8	174.7	180.6	189.5	201.3	217.1	226.0	234.9	242.8
65°	134.2	135.2	136.2	144.1	154.9	163.8	174.7	186.5	200.3	206.2	212.2
67.5°	119.4	120.4	122.4	123.4	127.3	137.2	149.0	161.8	172.7	176.6	182.6
70°	104.6	104.6	108.6	109.5	110.5	111.5	121.4	134.2	144.1	149.0	155.9
72.5°	88.8	89.8	91.8	92.8	94.7	96.7	99.7	106.6	118.4	123.4	131.2
75°	73.0	74.0	75.0	76.0	78.9	79.9	82.9	86.8	91.8	97.7	102.6
77.5°	58.2	58.2	59.2	61.2	63.2	64.1	67.1	69.1	71.1	74.0	78.0
80°	43.4	44.4	44.4	46.4	46.4	47.4	48.4	51.3	53.3	55.3	57.2
82.5°	29.6	31.6	31.6	31.6	32.6	33.6	34.5	34.5	36.5	37.5	40.5
85°	17.8	18.7	18.7	18.7	17.8	19.7	19.7	20.7	20.7	20.7	21.7
87.5°	6.9	5.9	6.9	6.9	6.9	7.9	6.9	6.9	7.9	8.9	8.9
90°	18.2	18.5	18.7	19.0	19.2	16.5	13.8	11.1	8.4	7.1	6.4
92.5°	17.5	17.4	17.3	17.1	17.0	16.9	16.8	16.7	16.6	16.5	16.0
95°	35.2	35.2	35.2	35.2	35.2	35.0	34.7	34.5	34.2	34.1	33.5
97.5°	54.9	54.9	54.9	54.9	54.9	54.4	53.9	53.4	52.9	52.7	52.2
100°	75.8	75.8	75.8	75.8	75.8	75.4	75.1	74.7	74.4	74.2	73.7
102.5°	98.8	98.7	98.6	98.4	98.3	97.8	97.3	96.8	96.3	96.1	95.7
105°	121.9	121.6	121.4	121.1	120.9	120.7	120.4	120.2	119.9	119.8	119.6
107.5°	146.0	145.9	145.8	145.7	145.6	145.6	145.6	145.6	145.6	145.6	145.4
110°	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.5

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	195.2	195.6	195.9	196.3	196.7	196.8	196.9	197.0	197.1	197.2	196.8
115°	221.5	221.6	221.7	221.9	222.0	222.2	222.5	222.7	223.0	223.1	222.7
117.5°	245.8	246.1	246.5	246.8	247.2	247.8	248.4	249.1	249.7	250.0	249.5
120°	271.4	271.4	271.4	271.4	271.4	272.4	273.4	274.3	275.3	275.8	275.3
122.5°	296.3	296.7	297.0	297.4	297.8	298.4	299.0	299.6	300.2	300.5	299.9
125°	321.6	321.9	322.3	322.6	323.0	323.4	323.8	324.1	324.5	324.7	324.1
127.5°	345.8	346.3	346.8	347.3	347.8	348.3	348.8	349.3	349.8	350.0	349.3
130°	371.5	371.8	372.0	372.3	372.5	372.7	373.0	373.2	373.5	373.6	372.8
132.5°	395.3	395.9	396.6	397.2	397.8	397.7	397.5	397.4	397.3	397.2	396.6
135°	420.4	420.5	420.6	420.7	420.8	420.6	420.3	420.1	419.8	419.7	419.0
137.5°	443.5	443.6	443.7	443.8	443.9	443.7	443.4	443.2	442.9	442.8	442.3
140°	467.0	467.0	467.0	467.0	467.0	466.4	465.8	465.1	464.5	464.2	463.7
142.5°	488.3	488.2	488.1	488.0	487.9	487.5	487.1	486.8	486.4	486.2	485.7
145°	509.7	509.6	509.5	509.4	509.3	508.6	507.8	507.1	506.4	506.0	505.6
147.5°	529.0	528.7	528.5	528.2	528.0	527.5	527.0	526.5	526.0	525.8	525.2
150°	547.0	546.6	546.3	545.9	545.5	545.0	544.5	544.0	543.5	543.3	542.9
152.5°	565.1	564.6	564.1	563.6	563.1	562.5	561.9	561.3	560.7	560.4	560.0
155°	579.9	579.3	578.6	578.0	577.4	577.0	576.7	576.3	576.0	575.8	575.6
157.5°	594.6	593.7	592.8	592.0	591.1	590.9	590.6	590.4	590.1	590.0	589.9
160°	606.7	606.0	605.3	604.5	603.8	603.7	603.5	603.4	603.3	603.2	603.1
162.5°	618.2	617.3	616.5	615.6	614.8	614.7	614.5	614.4	614.3	614.2	614.2
165°	627.6	626.7	625.8	625.0	624.1	624.1	624.1	624.1	624.1	624.1	624.2
167.5°	635.8	634.9	634.0	633.2	632.3	632.3	632.3	632.3	632.3	632.3	632.5
170°	642.4	641.5	640.6	639.8	638.9	639.0	639.2	639.3	639.4	639.5	639.7
172.5°	647.3	646.4	645.6	644.7	643.9	644.0	644.1	644.2	644.3	644.4	644.6
175°	650.6	649.7	648.9	648.0	647.2	647.4	647.7	647.9	648.2	648.3	648.5
177.5°	652.3	651.6	650.9	650.1	649.4	649.6	649.9	650.1	650.4	650.5	650.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1420.0	1420.0	1420.0	1420.0
2.5°	1394.4	1391.4	1409.2	1428.9
5°	1365.8	1370.7	1393.4	1421.0
7.5°	1336.2	1347.0	1373.7	1410.2
10°	1294.7	1314.4	1354.9	1392.4
12.5°	1254.3	1280.9	1319.4	1363.8
15°	1208.9	1238.5	1285.8	1339.1
17.5°	1158.5	1192.1	1247.3	1305.6
20°	1105.2	1149.6	1207.9	1271.0
22.5°	1046.0	1099.3	1159.5	1229.6
25°	988.8	1047.0	1107.2	1188.1
27.5°	932.5	989.8	1056.9	1138.8
30°	876.3	928.6	1000.6	1088.5
32.5°	816.1	870.4	946.4	1036.2
35°	760.8	815.1	886.2	975.0
37.5°	701.6	759.9	827.9	919.7
40°	632.6	700.6	766.8	854.6
42.5°	575.3	647.4	711.5	794.4
45°	529.9	598.0	651.3	732.2
47.5°	487.5	542.8	597.0	672.0
50°	447.0	489.5	545.7	612.8
52.5°	405.6	442.1	490.5	553.6
55°	368.1	402.6	446.0	494.4
57.5°	333.5	358.2	401.6	445.1
60°	295.1	320.7	354.3	390.8
62.5°	262.5	282.2	313.8	344.4
65°	228.0	246.7	270.4	299.0
67.5°	196.4	213.2	231.9	254.6
70°	167.8	180.6	194.4	214.1
72.5°	137.2	151.0	163.8	179.6
75°	112.5	118.4	129.3	140.1
77.5°	86.8	94.7	100.7	109.5
80°	62.2	69.1	71.1	78.0
82.5°	41.4	45.4	49.3	51.3
85°	23.7	25.7	29.6	30.6
87.5°	8.9	9.9	11.8	13.8
90°	4.9	3.4	2.0	0.5
92.5°	15.0	14.1	13.1	12.1
95°	32.3	31.0	29.8	28.6
97.5°	51.1	50.0	48.9	47.8
100°	72.7	71.8	70.8	69.8
102.5°	95.0	94.3	93.5	92.8
105°	119.2	118.9	118.5	118.1
107.5°	144.9	144.4	143.9	143.4
110°	169.8	169.1	168.3	167.6

TEST NUMBER: P999976

CATALOG NUMBER: SA2XXRDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	196.1	195.4	194.6	193.9
115°	222.0	221.3	220.5	219.8
117.5°	248.5	247.6	246.6	245.6
120°	274.3	273.4	272.4	271.4
122.5°	298.7	297.4	296.2	295.0
125°	323.0	321.9	320.8	319.7
127.5°	348.0	346.6	345.3	343.9
130°	371.2	369.6	368.0	366.4
132.5°	395.4	394.1	392.9	391.7
135°	417.7	416.4	415.0	413.7
137.5°	441.2	440.1	439.0	437.9
140°	462.6	461.5	460.4	459.3
142.5°	484.6	483.5	482.4	481.3
145°	504.7	503.8	503.0	502.1
147.5°	524.1	523.0	521.9	520.8
150°	542.2	541.5	540.8	540.1
152.5°	559.3	558.6	557.8	557.1
155°	575.2	574.9	574.5	574.1
157.5°	589.6	589.4	589.1	588.9
160°	602.8	602.6	602.3	602.1
162.5°	614.2	614.2	614.2	614.2
165°	624.3	624.4	624.6	624.7
167.5°	632.9	633.2	633.6	634.0
170°	640.0	640.4	640.7	641.1
172.5°	645.0	645.3	645.7	646.1
175°	648.8	649.2	649.5	649.9
177.5°	651.0	651.4	651.7	652.1
180°	651.0	651.0	651.0	651.0

(END OF REPORT)