

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000023

Luminaire Tested: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000023
REPORT IS A COMBINATION OF REPORTS P988580 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6081.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	97	93	89	86	88	85	82	79	70	68	66	56	55	54	44	43	42
2	88	82	76	71	81	75	70	66	62	59	56	50	48	46	39	38	37
3	81	72	65	60	74	66	61	56	55	51	48	45	42	40	36	34	32
4	75	64	57	51	68	59	53	48	50	45	41	41	37	35	32	30	28
5	69	58	50	45	63	53	47	42	45	40	36	37	33	30	29	27	25
6	64	52	44	39	58	48	41	37	41	36	32	34	30	27	27	24	22
7	59	47	40	34	54	44	37	32	37	32	28	31	27	24	25	22	20
8	55	43	36	31	50	40	33	29	34	29	25	28	25	22	23	20	18
9	51	39	32	28	47	37	30	26	31	26	23	26	23	20	21	19	17
10	48	36	29	25	44	34	28	24	29	24	21	24	21	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23174	23174	23174	23174
5°	23228	24614	23309	19664
10°	22972	26017	23135	16239
15°	22474	26025	22855	12199
20°	21875	21513	22351	10065
25°	21147	13443	21605	8562
30°	20220	8607	20769	7371
35°	19090	6615	19708	6308
40°	17833	5560	18594	5517
45°	16487	4732	17175	4632
50°	15109	4020	15814	4006
55°	13582	3495	14314	3448
60°	12226	2664	12872	2633
65°	10960	2006	11610	2274
70°	9562	1601	10311	1854
75°	8083	1227	8822	1403
80°	6419	835	6906	919
85°	4450	430	4887	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21199 cd/sqm

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	2.3
10°-20°	387.6	6.4
20°-30°	498.8	8.2
30°-40°	473.3	7.8
40°-50°	405.6	6.7
50°-60°	308.9	5.1
60°-70°	194.8	3.2
70°-80°	97.2	1.6
80°-90°	28.3	0.5
90°-100°	198.6	3.3
100°-110°	699.4	11.5
110°-120°	734.5	12.1
120°-130°	604.3	9.9
130°-140°	485.4	8.0
140°-150°	366.7	6.0
150°-160°	257.8	4.2
160°-170°	151.7	2.5
170°-180°	49.4	0.8
0°-30°	1025.3	16.9
0°-40°	1498.6	24.6
0°-60°	2213.0	36.4
0°-90°	2533.3	41.7
90°-120°	1632.5	26.8
90°-150°	3088.8	50.8
90°-180°	3548.0	58.3
0°-180°	6081.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1464	1464	1464	1464	1464	
5°	1465	1629	1470	1301	1465	139
15°	1381	1838	1404	862	1381	388
25°	1225	981	1251	625	1225	562
35°	1005	483	1038	461	1005	629
45°	755	336	786	329	755	583
55°	510	233	537	230	510	459
65°	308	121	327	137	308	306
75°	144	64	158	73	144	156
85°	32	18	35	19	32	36
90°	1	32	1	32	1	4
95°	34	112	34	112	34	35
105°	120	1104	120	1104	120	127
115°	211	1453	211	1453	211	209
125°	294	1179	294	1179	294	261
135°	345	977	345	977	345	266
145°	394	780	394	780	394	247
155°	448	655	448	655	448	206
165°	488	575	488	575	488	138
175°	508	518	508	518	508	48
180°	509	509	509	509	509	

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1473.2	1479.3	1482.3	1486.4	1495.6	1501.7	1510.8	1512.8	1511.8	1515.9	1504.7
5°	1465.0	1478.3	1490.5	1500.6	1516.9	1527.1	1538.3	1551.5	1554.6	1569.8	1560.7
7.5°	1453.8	1473.2	1490.5	1510.8	1535.2	1548.5	1565.8	1586.1	1595.3	1613.6	1618.7
10°	1435.5	1463.0	1492.5	1513.9	1547.4	1570.8	1587.1	1619.7	1641.0	1668.5	1664.4
12.5°	1406.0	1441.6	1481.3	1516.9	1560.7	1575.9	1606.4	1640.0	1667.5	1692.9	1715.3
15°	1380.6	1421.3	1465.0	1508.8	1558.6	1587.1	1617.6	1661.4	1690.9	1735.7	1755.0
17.5°	1346.0	1397.9	1449.8	1498.6	1557.6	1590.2	1627.8	1670.5	1714.3	1757.0	1772.3
20°	1310.4	1366.3	1422.3	1488.4	1555.6	1587.1	1625.8	1678.7	1721.4	1755.0	1755.0
22.5°	1267.7	1335.8	1399.9	1463.0	1536.2	1582.0	1621.7	1683.8	1714.3	1721.4	1693.9
25°	1224.9	1293.1	1363.3	1441.6	1525.1	1565.8	1610.5	1668.5	1678.7	1650.2	1579.0
27.5°	1174.1	1250.4	1329.7	1414.2	1501.7	1552.5	1593.2	1631.9	1612.6	1536.2	1425.4
30°	1122.2	1204.6	1294.1	1374.5	1480.3	1527.1	1561.7	1572.9	1511.8	1387.7	1244.3
32.5°	1068.3	1148.6	1243.2	1339.9	1446.7	1491.5	1513.9	1484.4	1372.5	1215.8	1040.8
35°	1005.2	1095.7	1194.4	1295.1	1400.9	1434.5	1447.7	1375.5	1232.1	1029.6	855.6
37.5°	948.2	1038.7	1144.6	1247.3	1350.1	1368.4	1355.2	1242.2	1060.1	859.7	689.8
40°	881.1	977.7	1081.5	1196.4	1280.9	1286.0	1253.4	1106.9	881.1	692.8	588.0
42.5°	819.0	916.7	1020.4	1137.4	1201.5	1184.2	1140.5	948.2	735.6	597.2	512.8
45°	754.9	847.5	959.4	1063.2	1108.9	1068.3	1002.1	797.6	617.6	513.8	448.7
47.5°	692.8	779.3	890.2	989.9	998.1	952.3	873.9	668.4	535.1	451.7	398.8
50°	631.8	718.3	822.0	904.5	896.3	833.2	744.7	580.9	464.9	398.8	355.1
52.5°	570.8	649.1	749.8	814.9	780.3	719.3	631.8	492.4	405.9	347.9	314.4
55°	509.7	583.0	669.4	723.4	668.4	598.2	536.2	422.2	352.0	305.2	279.8
57.5°	458.8	516.8	596.2	628.7	562.6	507.7	453.8	363.2	305.2	271.6	242.1
60°	402.9	455.8	520.9	540.2	472.1	427.3	381.5	307.2	261.5	232.0	212.6
62.5°	355.1	398.8	448.7	448.7	388.6	355.1	320.5	257.4	219.8	196.4	187.2
65°	308.3	339.8	375.4	371.3	320.5	291.0	263.5	212.6	184.1	167.9	158.7
67.5°	262.5	286.9	310.3	296.1	259.4	234.0	208.6	171.9	152.6	141.4	129.2
70°	220.8	240.1	252.3	239.1	202.5	181.1	162.8	138.4	123.1	108.9	101.7
72.5°	185.2	193.3	197.4	181.1	150.6	138.4	125.1	107.8	94.6	87.5	85.5
75°	144.5	151.6	148.5	136.3	110.9	101.7	91.6	79.4	76.3	72.2	70.2
77.5°	112.9	112.9	107.8	96.7	79.4	72.2	68.2	62.1	59.0	58.0	56.0
80°	80.4	79.4	76.3	64.1	53.9	49.9	49.9	45.8	44.8	42.7	42.7
82.5°	52.9	52.9	48.8	38.7	35.6	34.6	33.6	31.5	31.5	30.5	30.5
85°	31.5	29.5	24.4	21.4	20.3	20.3	19.3	18.3	19.3	18.3	18.3
87.5°	14.2	11.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	1.0	3.9	7.8	9.8	11.8	13.2	14.7	19.6	26.5	32.3	33.3
92.5°	14.7	20.6	28.4	33.3	41.1	46.5	51.9	78.4	115.6	148.9	150.9
95°	34.3	38.2	48.0	56.8	72.5	84.2	96.0	141.1	226.3	340.0	384.0
97.5°	50.9	56.8	67.6	80.3	98.0	111.2	124.4	182.2	300.8	484.0	626.0
100°	75.4	78.4	87.2	102.9	122.5	136.2	149.9	201.8	321.3	532.9	774.0
102.5°	98.0	99.9	108.7	124.4	145.0	158.7	172.4	219.4	322.3	514.3	778.8
105°	119.5	123.4	130.3	145.0	166.5	180.2	194.0	240.0	327.2	488.9	725.9
107.5°	143.0	146.0	152.8	166.5	188.1	201.8	215.5	260.6	338.0	475.1	677.0
110°	166.5	170.5	176.3	189.1	209.7	223.9	238.1	281.2	351.7	471.2	643.7

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.1	192.0	198.9	210.6	230.2	244.9	259.6	300.8	366.4	472.2	622.1
115°	210.6	215.5	221.4	233.2	252.8	266.0	279.2	321.3	381.1	476.1	607.4
117.5°	234.1	238.1	243.9	254.7	273.3	287.0	300.8	340.0	396.8	482.0	599.6
120°	255.7	259.6	265.5	274.3	293.9	307.6	321.3	359.5	412.4	487.9	592.7
122.5°	276.3	279.2	285.1	294.9	314.5	328.7	342.9	378.2	426.2	494.7	588.8
125°	293.9	296.8	302.7	314.5	334.1	347.8	361.5	396.8	440.9	501.6	583.9
127.5°	308.6	312.5	320.4	333.1	351.7	365.9	380.1	414.4	454.6	508.5	581.0
130°	321.3	325.3	335.1	348.8	368.4	382.1	395.8	430.1	467.3	516.3	579.0
132.5°	333.1	338.0	348.8	363.5	384.0	397.8	411.5	443.8	480.0	524.1	578.0
135°	344.8	348.8	360.5	375.2	397.8	411.5	425.2	456.5	490.8	530.0	577.0
137.5°	355.6	360.5	372.3	388.0	410.5	423.2	436.0	467.3	499.6	535.9	577.0
140°	368.4	372.3	384.0	399.7	421.3	434.0	446.7	476.1	506.5	539.8	576.1
142.5°	381.1	384.0	394.8	410.5	431.1	442.8	454.6	483.0	512.4	542.7	576.1
145°	393.8	397.8	407.5	422.2	441.8	452.6	463.4	489.8	517.3	544.7	574.1
147.5°	407.5	410.5	420.3	434.0	450.7	460.4	470.2	495.7	520.2	545.7	571.2
150°	421.3	424.2	432.0	444.8	459.5	468.3	477.1	499.6	522.2	544.7	568.2
152.5°	435.0	436.0	443.8	454.6	468.3	476.2	484.0	503.6	523.2	542.7	563.3
155°	447.7	448.7	454.6	465.4	476.1	483.4	490.8	507.5	524.1	540.8	557.4
157.5°	458.5	459.5	464.4	474.2	483.0	489.4	495.7	510.4	524.1	536.9	551.6
160°	469.3	470.2	474.2	482.0	489.8	495.2	500.6	512.4	524.1	533.9	545.7
162.5°	480.0	479.1	483.0	488.9	495.7	499.6	503.6	513.4	523.2	531.0	540.8
165°	487.9	486.9	488.9	494.7	499.6	502.6	505.5	514.3	521.2	527.1	533.9
167.5°	494.7	493.8	495.7	499.6	503.6	505.6	507.5	514.3	520.2	523.2	528.1
170°	501.6	499.6	500.6	503.6	505.5	507.0	508.5	513.4	518.3	520.2	523.2
172.5°	505.5	504.5	503.6	506.5	507.5	508.4	509.4	512.4	515.3	516.3	517.3
175°	508.5	507.5	506.5	508.5	508.5	509.0	509.4	511.4	513.4	512.4	513.4
177.5°	510.4	508.5	507.5	509.4	509.4	509.4	509.4	510.4	512.4	510.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1515.9	1517.9	1521.0	1535.2	1537.3	1541.3	1539.3	1539.3	1540.3	1538.3	1539.3
5°	1581.0	1584.1	1599.3	1616.6	1620.7	1616.6	1621.7	1628.8	1628.8	1628.8	1626.8
7.5°	1642.1	1653.2	1670.5	1696.0	1701.1	1706.2	1715.3	1709.2	1711.2	1720.4	1717.3
10°	1701.1	1717.3	1736.7	1758.0	1769.2	1776.4	1780.4	1789.6	1810.9	1786.5	1795.7
12.5°	1757.0	1780.4	1800.8	1824.2	1832.3	1841.5	1844.5	1852.7	1852.7	1851.6	1858.8
15°	1793.6	1815.0	1833.3	1848.6	1850.6	1848.6	1846.6	1847.6	1850.6	1838.4	1845.5
17.5°	1801.8	1803.8	1809.9	1803.8	1804.8	1783.5	1771.3	1768.2	1739.7	1740.7	1764.1
20°	1762.1	1727.5	1718.4	1684.8	1664.4	1609.5	1607.5	1592.2	1532.2	1550.5	1546.4
22.5°	1653.2	1594.2	1515.9	1477.2	1457.9	1399.9	1355.2	1323.6	1302.3	1280.9	1271.7
25°	1509.8	1414.2	1303.3	1227.0	1215.8	1161.9	1079.4	1040.8	995.0	980.8	1005.2
27.5°	1324.6	1200.5	1075.4	958.4	937.0	888.2	846.5	819.0	766.1	763.0	765.1
30°	1073.3	948.2	843.4	767.1	714.2	691.8	664.4	644.0	622.6	630.8	632.8
32.5°	882.1	763.0	665.4	624.7	600.3	586.0	562.6	549.4	540.2	537.2	536.2
35°	701.0	621.6	577.9	538.2	524.0	513.8	496.5	490.4	482.2	483.3	483.3
37.5°	600.3	534.1	501.6	481.2	468.0	462.9	451.7	445.6	440.5	438.5	441.5
40°	517.8	472.1	451.7	433.4	422.2	420.2	414.1	407.0	400.8	401.9	404.9
42.5°	457.8	431.4	407.0	392.7	384.6	381.5	376.4	371.3	371.3	368.3	367.3
45°	410.0	388.6	368.3	355.1	350.0	345.9	339.8	338.8	334.7	335.7	336.8
47.5°	367.3	350.0	334.7	321.5	316.4	315.4	309.3	305.2	305.2	304.2	303.2
50°	328.6	311.3	298.1	291.0	283.9	281.8	280.8	279.8	277.7	277.7	278.8
52.5°	297.1	279.8	269.6	263.5	259.4	257.4	257.4	256.4	256.4	256.4	255.4
55°	262.5	248.2	240.1	238.1	236.0	235.0	234.0	232.0	230.9	233.0	230.9
57.5°	229.9	224.8	217.7	215.7	210.6	210.6	207.5	205.5	203.5	205.5	205.5
60°	204.5	197.4	193.3	187.2	183.1	179.1	174.0	173.0	170.9	169.9	168.9
62.5°	178.0	171.9	161.8	152.6	146.5	142.4	140.4	139.4	139.4	138.4	138.4
65°	148.5	134.3	129.2	126.2	125.1	124.1	122.1	121.1	122.1	121.1	122.1
67.5°	116.0	113.9	110.9	108.9	107.8	106.8	106.8	105.8	105.8	105.8	105.8
70°	100.7	95.6	94.6	92.6	92.6	91.6	91.6	91.6	91.6	90.5	92.6
72.5°	83.4	80.4	79.4	78.3	78.3	78.3	77.3	77.3	77.3	76.3	77.3
75°	68.2	67.1	65.1	65.1	64.1	65.1	64.1	64.1	63.1	64.1	64.1
77.5°	54.9	53.9	52.9	52.9	51.9	51.9	51.9	51.9	51.9	51.9	52.9
80°	41.7	40.7	39.7	40.7	39.7	40.7	39.7	39.7	40.7	39.7	39.7
82.5°	30.5	29.5	29.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
85°	18.3	17.3	17.3	18.3	17.3	18.3	17.3	17.3	17.3	18.3	18.3
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2
90°	32.3	31.3	29.4	31.3	31.8	32.3	32.3	32.3	32.3	32.3	32.3
92.5°	126.4	98.9	84.3	73.5	69.6	65.6	64.7	60.7	61.7	59.8	61.7
95°	336.0	256.7	196.9	155.8	145.0	134.2	121.5	113.6	110.7	111.7	110.7
97.5°	630.9	525.1	419.3	320.4	291.0	261.6	223.4	203.8	193.0	187.1	193.0
100°	915.0	894.5	773.0	638.8	579.5	520.2	438.9	396.8	368.4	350.7	368.4
102.5°	1020.8	1136.4	1132.5	1043.4	979.7	916.0	825.9	746.5	709.3	683.8	709.3
105°	986.5	1190.3	1301.0	1313.8	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8
107.5°	914.0	1132.5	1297.1	1393.1	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8
110°	846.4	1053.2	1228.5	1353.9	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	799.4	980.7	1147.2	1283.4	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0
115°	762.2	923.8	1074.7	1203.1	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1
117.5°	736.7	876.8	1012.0	1131.5	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5
120°	717.1	843.5	965.0	1068.8	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0
122.5°	700.5	817.1	925.8	1022.8	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5
125°	684.8	791.6	892.5	978.7	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7
127.5°	670.1	766.1	859.2	941.5	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8
130°	655.4	741.6	825.9	903.3	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8
132.5°	643.7	718.1	794.5	864.1	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8
135°	632.9	696.6	761.2	825.9	853.3	880.7	922.9	955.2	972.8	976.7	972.8
137.5°	625.0	678.9	734.8	787.7	812.2	836.7	876.8	905.2	920.9	926.8	920.9
140°	618.2	662.3	709.3	754.4	776.0	797.5	828.8	854.3	869.0	874.9	869.0
142.5°	611.3	648.6	686.8	724.0	741.2	758.3	787.7	810.2	822.9	822.9	822.9
145°	605.4	635.8	668.1	698.5	712.7	726.9	750.4	767.1	776.9	779.8	776.9
147.5°	599.6	626.0	652.5	677.0	687.8	698.5	719.1	732.8	739.7	741.6	739.7
150°	591.7	615.2	636.8	657.4	666.2	675.0	689.7	701.5	707.3	708.3	707.3
152.5°	584.9	604.5	624.1	640.7	648.0	655.4	666.2	676.0	679.9	679.9	679.9
155°	576.1	594.7	610.3	625.0	630.4	635.8	646.6	653.4	657.4	655.4	657.4
157.5°	568.2	582.9	596.6	609.4	613.8	618.2	626.0	631.9	633.9	633.9	633.9
160°	559.4	572.1	582.9	593.7	597.1	600.5	607.4	612.3	613.3	613.3	613.3
162.5°	551.6	561.4	570.2	579.0	581.4	583.9	590.7	593.7	594.7	593.7	594.7
165°	542.7	550.6	557.4	564.3	566.2	568.2	572.1	576.1	576.1	575.1	576.1
167.5°	533.9	539.8	545.7	550.6	552.6	554.5	556.5	558.4	558.4	557.4	558.4
170°	527.1	532.0	534.9	538.8	539.8	540.8	541.8	544.7	543.7	541.8	543.7
172.5°	520.2	523.2	525.1	528.1	528.6	529.0	530.0	531.0	530.0	529.0	530.0
175°	514.3	517.3	518.3	519.2	519.7	520.2	520.2	521.2	520.2	518.3	520.2
177.5°	510.4	512.4	512.4	513.4	513.4	513.4	513.4	513.4	512.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1543.4	1536.2	1534.2	1536.2	1534.2	1535.2	1528.1	1501.7	1508.8	1497.6	1503.7
5°	1630.9	1624.8	1611.5	1609.5	1607.5	1605.4	1595.3	1571.9	1562.7	1547.4	1546.4
7.5°	1714.3	1714.3	1704.1	1697.0	1687.8	1680.7	1667.5	1632.9	1618.7	1600.3	1590.2
10°	1796.7	1770.2	1781.4	1774.3	1751.9	1747.9	1723.4	1703.1	1675.6	1657.3	1641.0
12.5°	1855.7	1847.6	1837.4	1831.3	1825.2	1812.0	1795.7	1743.8	1729.6	1692.9	1674.6
15°	1853.7	1848.6	1851.6	1851.6	1849.6	1846.6	1833.3	1795.7	1771.3	1735.7	1704.1
17.5°	1754.0	1767.2	1780.4	1789.6	1809.9	1819.1	1831.3	1808.9	1793.6	1763.1	1729.6
20°	1580.0	1612.6	1651.2	1659.4	1677.7	1731.6	1756.0	1775.3	1781.4	1771.3	1743.8
22.5°	1337.9	1365.3	1458.9	1456.9	1483.3	1547.4	1618.7	1676.6	1722.4	1747.9	1737.7
25°	1047.9	1086.6	1136.4	1174.1	1260.5	1356.2	1444.7	1537.3	1616.6	1686.8	1704.1
27.5°	792.5	843.4	883.1	932.9	976.7	1089.6	1203.6	1348.0	1440.6	1573.9	1643.1
30°	641.0	664.4	704.0	727.4	748.8	835.3	964.5	1106.9	1269.7	1423.3	1542.4
32.5°	547.4	563.6	593.1	603.3	625.7	683.7	765.1	895.3	1063.2	1249.3	1406.0
35°	491.4	508.7	514.8	524.0	542.3	578.9	634.8	729.5	881.1	1063.2	1250.4
37.5°	443.6	452.7	470.0	476.1	482.2	509.7	547.4	613.5	714.2	863.8	1071.3
40°	410.0	415.1	424.2	429.3	433.4	452.7	486.3	531.1	605.3	719.3	910.6
42.5°	374.4	380.5	386.6	392.7	397.8	413.1	433.4	476.1	526.0	612.5	750.8
45°	339.8	343.9	351.0	355.1	362.2	374.4	392.7	422.2	467.0	521.9	633.8
47.5°	308.3	313.4	316.4	321.5	326.6	339.8	357.1	376.4	413.1	467.0	548.4
50°	279.8	285.9	290.0	291.0	295.0	307.2	321.5	342.9	366.3	408.0	479.2
52.5°	259.4	260.5	263.5	267.6	266.6	273.7	286.9	303.2	327.6	361.2	413.1
55°	236.0	239.1	241.1	242.1	242.1	248.2	255.4	270.6	290.0	317.4	361.2
57.5°	206.5	209.6	215.7	217.7	220.8	223.8	226.9	237.1	253.3	279.8	315.4
60°	176.0	178.0	184.1	188.2	190.3	198.4	202.5	210.6	219.8	239.1	272.7
62.5°	141.4	143.5	146.5	150.6	154.6	166.9	177.0	185.2	192.3	205.5	233.0
65°	123.1	124.1	126.2	127.2	128.2	133.3	142.4	153.6	166.9	177.0	193.3
67.5°	106.8	107.8	108.9	110.9	111.9	112.9	117.0	120.1	133.3	147.5	159.7
70°	91.6	93.6	94.6	94.6	95.6	97.7	99.7	103.8	107.8	115.0	130.2
72.5°	77.3	78.3	80.4	80.4	80.4	82.4	84.4	86.5	88.5	92.6	98.7
75°	64.1	66.1	66.1	66.1	67.1	67.1	69.2	71.2	73.3	76.3	78.3
77.5°	52.9	52.9	52.9	52.9	53.9	53.9	54.9	57.0	58.0	59.0	61.0
80°	39.7	40.7	40.7	40.7	41.7	41.7	41.7	43.7	44.8	44.8	46.8
82.5°	29.5	29.5	29.5	30.5	29.5	30.5	30.5	31.5	30.5	31.5	32.6
85°	18.3	18.3	18.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	20.3
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	32.3	32.3	32.3	31.8	31.3	29.4	31.3	32.3	33.3	32.3	26.5
92.5°	60.7	64.7	65.6	69.6	73.5	84.3	98.9	126.4	150.9	148.9	115.6
95°	113.6	121.5	134.2	145.0	155.8	196.9	256.7	336.0	384.0	340.0	226.3
97.5°	203.8	223.4	261.6	291.0	320.4	419.3	525.1	630.9	626.0	484.0	300.8
100°	396.8	438.9	520.2	579.5	638.8	773.0	894.5	915.0	774.0	532.9	321.3
102.5°	746.5	825.9	916.0	979.7	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3
105°	1159.9	1220.7	1281.4	1297.6	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2
107.5°	1422.5	1431.3	1432.3	1412.7	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0
110°	1495.0	1476.4	1434.3	1394.1	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1475.4	1441.1	1378.4	1330.9	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4
115°	1418.6	1373.5	1304.0	1253.6	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1
117.5°	1347.1	1299.1	1227.5	1179.5	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8
120°	1272.6	1226.6	1158.0	1113.4	1068.8	965.0	843.5	717.1	592.7	487.9	412.4
122.5°	1206.0	1160.9	1101.2	1062.0	1022.8	925.8	817.1	700.5	588.8	494.7	426.2
125°	1146.2	1109.0	1052.2	1015.4	978.7	892.5	791.6	684.8	583.9	501.6	440.9
127.5°	1095.3	1060.0	1010.1	975.8	941.5	859.2	766.1	670.1	581.0	508.5	454.6
130°	1049.2	1015.9	967.9	935.6	903.3	825.9	741.6	655.4	579.0	516.3	467.3
132.5°	1004.2	970.9	923.8	894.0	864.1	794.5	718.1	643.7	578.0	524.1	480.0
135°	955.2	922.9	880.7	853.3	825.9	761.2	696.6	632.9	577.0	530.0	490.8
137.5°	905.2	876.8	836.7	812.2	787.7	734.8	678.9	625.0	577.0	535.9	499.6
140°	854.3	828.8	797.5	776.0	754.4	709.3	662.3	618.2	576.1	539.8	506.5
142.5°	810.2	787.7	758.3	741.2	724.0	686.8	648.6	611.3	576.1	542.7	512.4
145°	767.1	750.4	726.9	712.7	698.5	668.1	635.8	605.4	574.1	544.7	517.3
147.5°	732.8	719.1	698.5	687.8	677.0	652.5	626.0	599.6	571.2	545.7	520.2
150°	701.5	689.7	675.0	666.2	657.4	636.8	615.2	591.7	568.2	544.7	522.2
152.5°	676.0	666.2	655.4	648.0	640.7	624.1	604.5	584.9	563.3	542.7	523.2
155°	653.4	646.6	635.8	630.4	625.0	610.3	594.7	576.1	557.4	540.8	524.1
157.5°	631.9	626.0	618.2	613.8	609.4	596.6	582.9	568.2	551.6	536.9	524.1
160°	612.3	607.4	600.5	597.1	593.7	582.9	572.1	559.4	545.7	533.9	524.1
162.5°	593.7	590.7	583.9	581.4	579.0	570.2	561.4	551.6	540.8	531.0	523.2
165°	576.1	572.1	568.2	566.2	564.3	557.4	550.6	542.7	533.9	527.1	521.2
167.5°	558.4	556.5	554.5	552.6	550.6	545.7	539.8	533.9	528.1	523.2	520.2
170°	544.7	541.8	540.8	539.8	538.8	534.9	532.0	527.1	523.2	520.2	518.3
172.5°	531.0	530.0	529.0	528.6	528.1	525.1	523.2	520.2	517.3	516.3	515.3
175°	521.2	520.2	520.2	519.7	519.2	518.3	517.3	514.3	513.4	512.4	513.4
177.5°	513.4	513.4	513.4	513.4	513.4	512.4	512.4	510.4	509.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1494.5	1489.4	1489.4	1486.4	1486.4	1470.1	1470.1	1475.2	1469.1	1462.0	1451.8
5°	1533.2	1522.0	1519.0	1514.9	1501.7	1481.3	1473.2	1470.1	1457.9	1442.7	1425.4
7.5°	1569.8	1551.5	1542.4	1533.2	1515.9	1487.4	1471.1	1459.9	1441.6	1418.2	1395.9
10°	1605.4	1582.0	1558.6	1547.4	1523.0	1487.4	1464.0	1445.7	1419.3	1387.7	1356.2
12.5°	1638.0	1589.2	1585.1	1562.7	1527.1	1486.4	1450.8	1424.3	1390.8	1354.1	1317.5
15°	1666.5	1616.6	1592.2	1571.9	1525.1	1474.2	1436.5	1404.0	1359.2	1317.5	1272.7
17.5°	1680.7	1626.8	1610.5	1576.9	1529.1	1463.0	1412.1	1372.5	1323.6	1273.8	1222.9
20°	1695.0	1631.9	1605.4	1582.0	1516.9	1441.6	1384.7	1338.9	1285.0	1225.9	1170.0
22.5°	1702.1	1631.9	1600.3	1567.8	1504.7	1418.2	1351.1	1297.2	1234.1	1174.1	1106.9
25°	1689.9	1625.8	1588.1	1554.6	1483.3	1389.7	1312.4	1251.4	1184.2	1116.1	1047.9
27.5°	1659.4	1611.5	1567.8	1533.2	1453.8	1353.1	1271.7	1202.5	1133.4	1057.1	987.9
30°	1602.4	1581.0	1546.4	1507.8	1421.3	1320.6	1223.9	1152.7	1076.4	1000.1	927.9
32.5°	1513.9	1532.2	1509.8	1476.2	1382.6	1275.8	1173.0	1100.8	1017.4	935.0	868.8
35°	1406.0	1471.1	1458.9	1435.5	1341.9	1228.0	1125.2	1037.7	954.3	870.9	804.8
37.5°	1288.0	1386.7	1396.9	1382.6	1295.1	1179.1	1066.2	980.8	895.3	810.9	743.7
40°	1126.2	1277.8	1310.4	1316.5	1246.3	1120.1	1002.1	918.7	834.3	751.8	670.5
42.5°	977.7	1169.0	1209.7	1235.1	1184.2	1062.1	943.1	850.5	767.1	692.8	611.4
45°	838.3	1037.7	1103.9	1136.4	1114.0	996.0	872.9	786.4	710.1	642.0	563.6
47.5°	694.9	895.3	987.9	1039.8	1039.8	928.9	805.8	720.3	647.1	589.1	519.9
50°	599.2	766.1	861.7	929.9	948.2	860.7	744.7	661.3	592.1	529.0	476.1
52.5°	510.7	660.3	739.6	810.9	863.8	787.5	676.6	601.3	533.1	474.1	432.4
55°	441.5	553.5	625.7	704.0	763.0	713.2	610.4	537.2	478.2	429.3	393.7
57.5°	375.4	473.1	532.1	601.3	664.4	626.7	544.3	481.2	429.3	386.6	355.1
60°	319.5	398.8	444.6	498.5	576.9	550.4	482.2	424.2	382.5	343.9	317.4
62.5°	271.6	334.7	373.4	412.0	483.3	471.0	418.1	373.4	337.8	305.2	282.8
65°	222.8	274.7	305.2	338.8	395.8	400.8	358.1	326.6	294.0	265.5	245.2
67.5°	180.1	220.8	248.2	276.7	322.5	336.8	307.2	280.8	253.3	229.9	211.6
70°	145.5	174.0	194.3	216.7	254.3	271.6	256.4	238.1	215.7	196.4	180.1
72.5°	115.0	133.3	145.5	162.8	193.3	210.6	209.6	193.3	177.0	163.8	150.6
75°	84.4	98.7	108.9	120.1	144.5	160.7	164.8	157.7	141.4	131.2	121.1
77.5°	64.1	72.2	77.3	85.5	102.8	117.0	123.1	121.1	109.9	101.7	94.6
80°	48.8	50.9	52.9	56.0	70.2	83.4	87.5	86.5	80.4	77.3	69.2
82.5°	34.6	35.6	36.6	37.6	42.7	53.9	58.0	60.0	54.9	51.9	44.8
85°	20.3	21.4	21.4	23.4	24.4	27.5	34.6	34.6	33.6	29.5	28.5
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.2	15.3	13.2	12.2	11.2
90°	19.6	14.7	13.2	11.8	9.8	7.8	3.9	1.0	3.9	7.8	9.8
92.5°	78.4	51.9	46.5	41.1	33.3	28.4	20.6	14.7	20.6	28.4	33.3
95°	141.1	96.0	84.2	72.5	56.8	48.0	38.2	34.3	38.2	48.0	56.8
97.5°	182.2	124.4	111.2	98.0	80.3	67.6	56.8	50.9	56.8	67.6	80.3
100°	201.8	149.9	136.2	122.5	102.9	87.2	78.4	75.4	78.4	87.2	102.9
102.5°	219.4	172.4	158.7	145.0	124.4	108.7	99.9	98.0	99.9	108.7	124.4
105°	240.0	194.0	180.2	166.5	145.0	130.3	123.4	119.5	123.4	130.3	145.0
107.5°	260.6	215.5	201.8	188.1	166.5	152.8	146.0	143.0	146.0	152.8	166.5
110°	281.2	238.1	223.9	209.7	189.1	176.3	170.5	166.5	170.5	176.3	189.1

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	300.8	259.6	244.9	230.2	210.6	198.9	192.0	188.1	192.0	198.9	210.6
115°	321.3	279.2	266.0	252.8	233.2	221.4	215.5	210.6	215.5	221.4	233.2
117.5°	340.0	300.8	287.0	273.3	254.7	243.9	238.1	234.1	238.1	243.9	254.7
120°	359.5	321.3	307.6	293.9	274.3	265.5	259.6	255.7	259.6	265.5	274.3
122.5°	378.2	342.9	328.7	314.5	294.9	285.1	279.2	276.3	279.2	285.1	294.9
125°	396.8	361.5	347.8	334.1	314.5	302.7	296.8	293.9	296.8	302.7	314.5
127.5°	414.4	380.1	365.9	351.7	333.1	320.4	312.5	308.6	312.5	320.4	333.1
130°	430.1	395.8	382.1	368.4	348.8	335.1	325.3	321.3	325.3	335.1	348.8
132.5°	443.8	411.5	397.8	384.0	363.5	348.8	338.0	333.1	338.0	348.8	363.5
135°	456.5	425.2	411.5	397.8	375.2	360.5	348.8	344.8	348.8	360.5	375.2
137.5°	467.3	436.0	423.2	410.5	388.0	372.3	360.5	355.6	360.5	372.3	388.0
140°	476.1	446.7	434.0	421.3	399.7	384.0	372.3	368.4	372.3	384.0	399.7
142.5°	483.0	454.6	442.8	431.1	410.5	394.8	384.0	381.1	384.0	394.8	410.5
145°	489.8	463.4	452.6	441.8	422.2	407.5	397.8	393.8	397.8	407.5	422.2
147.5°	495.7	470.2	460.4	450.7	434.0	420.3	410.5	407.5	410.5	420.3	434.0
150°	499.6	477.1	468.3	459.5	444.8	432.0	424.2	421.3	424.2	432.0	444.8
152.5°	503.6	484.0	476.2	468.3	454.6	443.8	436.0	435.0	436.0	443.8	454.6
155°	507.5	490.8	483.4	476.1	465.4	454.6	448.7	447.7	448.7	454.6	465.4
157.5°	510.4	495.7	489.4	483.0	474.2	464.4	459.5	458.5	459.5	464.4	474.2
160°	512.4	500.6	495.2	489.8	482.0	474.2	470.2	469.3	470.2	474.2	482.0
162.5°	513.4	503.6	499.6	495.7	488.9	483.0	479.1	480.0	479.1	483.0	488.9
165°	514.3	505.5	502.6	499.6	494.7	488.9	486.9	487.9	486.9	488.9	494.7
167.5°	514.3	507.5	505.6	503.6	499.6	495.7	493.8	494.7	493.8	495.7	499.6
170°	513.4	508.5	507.0	505.5	503.6	500.6	499.6	501.6	499.6	500.6	503.6
172.5°	512.4	509.4	508.4	507.5	506.5	503.6	504.5	505.5	504.5	503.6	506.5
175°	511.4	509.4	509.0	508.5	508.5	506.5	507.5	508.5	507.5	506.5	508.5
177.5°	510.4	509.4	509.4	509.4	509.4	507.5	508.5	510.4	508.5	507.5	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1447.7	1448.8	1451.8	1442.7	1428.4	1422.3	1404.0	1400.9	1397.9	1397.9	1400.9
5°	1415.2	1411.1	1412.1	1394.8	1374.5	1362.3	1336.8	1340.9	1327.7	1319.5	1321.6
7.5°	1379.6	1368.4	1367.4	1345.0	1319.5	1297.2	1270.7	1264.6	1252.4	1238.2	1232.1
10°	1334.8	1326.7	1311.4	1286.0	1253.4	1235.1	1199.5	1178.1	1175.1	1153.7	1145.6
12.5°	1289.0	1274.8	1259.5	1223.9	1187.3	1157.8	1131.3	1107.9	1091.7	1073.3	1061.1
15°	1236.1	1218.8	1201.5	1163.9	1121.2	1091.7	1052.0	1017.4	969.6	931.9	910.6
17.5°	1178.1	1158.8	1135.4	1093.7	1052.0	1011.3	938.0	897.3	863.8	841.4	828.2
20°	1118.1	1096.7	1073.3	1031.6	959.4	888.2	847.5	815.9	795.6	773.2	756.9
22.5°	1055.0	1032.6	1007.2	942.1	865.8	815.9	784.4	754.9	725.4	713.2	705.0
25°	996.0	975.7	943.1	854.6	794.6	748.8	713.2	693.9	678.6	662.3	647.1
27.5°	935.0	897.3	851.6	777.3	739.6	692.8	667.4	653.2	626.7	615.5	608.4
30°	861.7	820.0	776.3	723.4	679.6	647.1	623.7	600.3	585.0	573.8	561.6
32.5°	787.5	747.8	720.3	665.4	632.8	599.2	576.9	562.6	540.2	533.1	528.0
35°	723.4	689.8	665.4	620.6	590.1	559.6	543.3	521.9	507.7	494.4	486.3
37.5°	660.3	642.0	616.5	578.9	546.3	521.9	499.5	492.4	473.1	466.0	457.8
40°	616.5	589.1	567.7	535.1	507.7	481.2	467.0	450.7	437.5	426.3	423.2
42.5°	563.6	543.3	531.1	495.5	467.0	451.7	434.4	416.1	405.9	396.8	385.6
45°	524.0	505.6	488.3	459.9	434.4	415.1	399.8	387.6	370.3	366.3	349.0
47.5°	482.2	463.9	450.7	422.2	398.8	380.5	369.3	353.0	338.8	329.6	321.5
50°	440.5	425.3	413.1	388.6	368.3	349.0	333.7	317.4	311.3	296.1	291.0
52.5°	400.8	390.7	377.4	354.0	333.7	317.4	301.1	287.9	278.8	270.6	264.5
55°	367.3	351.0	344.9	319.5	302.2	284.9	270.6	262.5	251.3	246.2	241.1
57.5°	329.6	320.5	310.3	291.0	271.6	255.4	245.2	233.0	226.9	220.8	216.7
60°	297.1	283.9	275.7	259.4	242.1	226.9	217.7	208.6	200.4	195.3	187.2
62.5°	259.4	249.3	244.2	226.9	212.6	198.4	190.3	181.1	175.0	165.8	155.7
65°	226.9	218.7	212.6	198.4	185.2	171.9	163.8	152.6	144.5	139.4	138.4
67.5°	198.4	192.3	183.1	169.9	156.7	146.5	137.3	128.2	127.2	125.1	125.1
70°	166.9	160.7	155.7	141.4	130.2	119.0	117.0	113.9	110.9	109.9	107.8
72.5°	139.4	134.3	128.2	116.0	104.8	101.7	99.7	97.7	94.6	93.6	92.6
75°	112.9	105.8	101.7	90.5	87.5	85.5	83.4	80.4	78.3	77.3	75.3
77.5°	86.5	79.4	79.4	73.3	71.2	68.2	66.1	64.1	63.1	61.0	61.0
80°	61.0	61.0	59.0	56.0	52.9	51.9	48.8	47.8	46.8	47.8	45.8
82.5°	44.8	40.7	40.7	38.7	36.6	35.6	33.6	33.6	32.6	32.6	32.6
85°	25.4	25.4	24.4	22.4	21.4	21.4	20.3	20.3	19.3	19.3	18.3
87.5°	10.2	9.2	10.2	9.2	9.2	8.1	8.1	8.1	7.1	8.1	7.1
90°	11.8	13.2	14.7	19.6	26.5	32.3	33.3	32.3	31.3	29.4	31.3
92.5°	41.1	46.5	51.9	78.4	115.6	148.9	150.9	126.4	98.9	84.3	73.5
95°	72.5	84.2	96.0	141.1	226.3	340.0	384.0	336.0	256.7	196.9	155.8
97.5°	98.0	111.2	124.4	182.2	300.8	484.0	626.0	630.9	525.1	419.3	320.4
100°	122.5	136.2	149.9	201.8	321.3	532.9	774.0	915.0	894.5	773.0	638.8
102.5°	145.0	158.7	172.4	219.4	322.3	514.3	778.8	1020.8	1136.4	1132.5	1043.4
105°	166.5	180.2	194.0	240.0	327.2	488.9	725.9	986.5	1190.3	1301.0	1313.8
107.5°	188.1	201.8	215.5	260.6	338.0	475.1	677.0	914.0	1132.5	1297.1	1393.1
110°	209.7	223.9	238.1	281.2	351.7	471.2	643.7	846.4	1053.2	1228.5	1353.9

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.2	244.9	259.6	300.8	366.4	472.2	622.1	799.4	980.7	1147.2	1283.4
115°	252.8	266.0	279.2	321.3	381.1	476.1	607.4	762.2	923.8	1074.7	1203.1
117.5°	273.3	287.0	300.8	340.0	396.8	482.0	599.6	736.7	876.8	1012.0	1131.5
120°	293.9	307.6	321.3	359.5	412.4	487.9	592.7	717.1	843.5	965.0	1068.8
122.5°	314.5	328.7	342.9	378.2	426.2	494.7	588.8	700.5	817.1	925.8	1022.8
125°	334.1	347.8	361.5	396.8	440.9	501.6	583.9	684.8	791.6	892.5	978.7
127.5°	351.7	365.9	380.1	414.4	454.6	508.5	581.0	670.1	766.1	859.2	941.5
130°	368.4	382.1	395.8	430.1	467.3	516.3	579.0	655.4	741.6	825.9	903.3
132.5°	384.0	397.8	411.5	443.8	480.0	524.1	578.0	643.7	718.1	794.5	864.1
135°	397.8	411.5	425.2	456.5	490.8	530.0	577.0	632.9	696.6	761.2	825.9
137.5°	410.5	423.2	436.0	467.3	499.6	535.9	577.0	625.0	678.9	734.8	787.7
140°	421.3	434.0	446.7	476.1	506.5	539.8	576.1	618.2	662.3	709.3	754.4
142.5°	431.1	442.8	454.6	483.0	512.4	542.7	576.1	611.3	648.6	686.8	724.0
145°	441.8	452.6	463.4	489.8	517.3	544.7	574.1	605.4	635.8	668.1	698.5
147.5°	450.7	460.4	470.2	495.7	520.2	545.7	571.2	599.6	626.0	652.5	677.0
150°	459.5	468.3	477.1	499.6	522.2	544.7	568.2	591.7	615.2	636.8	657.4
152.5°	468.3	476.2	484.0	503.6	523.2	542.7	563.3	584.9	604.5	624.1	640.7
155°	476.1	483.4	490.8	507.5	524.1	540.8	557.4	576.1	594.7	610.3	625.0
157.5°	483.0	489.4	495.7	510.4	524.1	536.9	551.6	568.2	582.9	596.6	609.4
160°	489.8	495.2	500.6	512.4	524.1	533.9	545.7	559.4	572.1	582.9	593.7
162.5°	495.7	499.6	503.6	513.4	523.2	531.0	540.8	551.6	561.4	570.2	579.0
165°	499.6	502.6	505.5	514.3	521.2	527.1	533.9	542.7	550.6	557.4	564.3
167.5°	503.6	505.6	507.5	514.3	520.2	523.2	528.1	533.9	539.8	545.7	550.6
170°	505.5	507.0	508.5	513.4	518.3	520.2	523.2	527.1	532.0	534.9	538.8
172.5°	507.5	508.4	509.4	512.4	515.3	516.3	517.3	520.2	523.2	525.1	528.1
175°	508.5	509.0	509.4	511.4	513.4	512.4	513.4	514.3	517.3	518.3	519.2
177.5°	509.4	509.4	509.4	510.4	512.4	510.4	509.4	510.4	512.4	512.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1400.9	1398.9	1392.8	1394.8	1391.8	1391.8	1389.7	1389.7	1389.7	1394.8	1391.8
5°	1324.6	1317.5	1310.4	1307.3	1304.3	1301.2	1301.2	1300.2	1309.4	1307.3	1315.5
7.5°	1230.0	1228.0	1213.7	1213.7	1208.7	1206.6	1211.7	1212.7	1213.7	1215.8	1220.9
10°	1145.6	1140.5	1120.1	1122.2	1119.1	1115.1	1118.1	1116.1	1123.2	1125.2	1123.2
12.5°	1045.9	1036.7	1014.3	1003.1	990.9	981.8	993.0	984.8	1013.3	1021.5	1043.8
15°	913.6	896.3	881.1	881.1	869.9	861.7	866.8	876.0	882.1	891.2	895.3
17.5°	825.1	818.0	805.8	798.6	795.6	792.5	792.5	796.6	809.8	808.8	817.0
20°	749.8	745.7	739.6	730.5	727.4	725.4	725.4	725.4	734.6	742.7	747.8
22.5°	697.9	694.9	690.8	678.6	672.5	670.5	675.5	678.6	685.7	691.8	696.9
25°	646.0	638.9	631.8	627.7	624.7	624.7	626.7	627.7	630.8	633.8	639.9
27.5°	603.3	598.2	588.0	576.9	576.9	573.8	575.8	577.9	585.0	595.2	600.3
30°	555.5	554.5	550.4	546.3	542.3	540.2	544.3	547.4	548.4	553.5	553.5
32.5°	520.9	513.8	506.7	502.6	500.6	499.5	500.6	504.6	504.6	510.7	517.8
35°	486.3	482.2	475.1	468.0	466.0	460.9	464.9	469.0	476.1	479.2	482.2
37.5°	448.7	443.6	440.5	438.5	434.4	435.4	432.4	438.5	444.6	443.6	445.6
40°	420.2	411.0	401.9	400.8	399.8	398.8	398.8	399.8	403.9	408.0	414.1
42.5°	383.6	380.5	372.4	364.2	362.2	360.2	358.1	362.2	370.3	377.4	380.5
45°	345.9	341.8	339.8	333.7	329.6	328.6	326.6	331.7	338.8	341.8	343.9
47.5°	311.3	310.3	304.2	305.2	302.2	303.2	302.2	305.2	305.2	308.3	310.3
50°	287.9	284.9	281.8	279.8	276.7	276.7	275.7	276.7	280.8	284.9	283.9
52.5°	264.5	259.4	258.4	257.4	255.4	257.4	254.3	255.4	259.4	261.5	260.5
55°	237.1	236.0	234.0	232.0	230.9	229.9	229.9	229.9	234.0	237.1	238.1
57.5°	215.7	210.6	206.5	206.5	202.5	201.4	203.5	204.5	207.5	209.6	211.6
60°	186.2	184.1	178.0	175.0	168.9	167.9	167.9	171.9	177.0	184.1	186.2
62.5°	154.6	151.6	150.6	150.6	150.6	150.6	150.6	150.6	150.6	151.6	151.6
65°	137.3	138.4	137.3	136.3	137.3	137.3	136.3	136.3	136.3	137.3	138.4
67.5°	123.1	122.1	123.1	122.1	121.1	121.1	120.1	121.1	122.1	123.1	123.1
70°	106.8	106.8	105.8	106.8	105.8	104.8	103.8	103.8	105.8	106.8	106.8
72.5°	91.6	91.6	90.5	90.5	88.5	88.5	89.5	88.5	88.5	91.6	91.6
75°	76.3	75.3	74.3	74.3	73.3	73.3	73.3	72.2	74.3	74.3	75.3
77.5°	60.0	60.0	60.0	59.0	59.0	58.0	58.0	59.0	59.0	59.0	60.0
80°	45.8	45.8	45.8	44.8	43.7	43.7	43.7	43.7	43.7	44.8	43.7
82.5°	31.5	31.5	31.5	31.5	31.5	30.5	30.5	30.5	31.5	31.5	30.5
85°	19.3	18.3	19.3	19.3	18.3	19.3	18.3	18.3	17.3	17.3	18.3
87.5°	8.1	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	31.8	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	31.8
92.5°	69.6	65.6	64.7	60.7	61.7	59.8	61.7	60.7	64.7	65.6	69.6
95°	145.0	134.2	121.5	113.6	110.7	111.7	110.7	113.6	121.5	134.2	145.0
97.5°	291.0	261.6	223.4	203.8	193.0	187.1	193.0	203.8	223.4	261.6	291.0
100°	579.5	520.2	438.9	396.8	368.4	350.7	368.4	396.8	438.9	520.2	579.5
102.5°	979.7	916.0	825.9	746.5	709.3	683.8	709.3	746.5	825.9	916.0	979.7
105°	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8	1159.9	1220.7	1281.4	1297.6
107.5°	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8	1422.5	1431.3	1432.3	1412.7
110°	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8	1495.0	1476.4	1434.3	1394.1

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0	1475.4	1441.1	1378.4	1330.9
115°	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1	1418.6	1373.5	1304.0	1253.6
117.5°	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5	1347.1	1299.1	1227.5	1179.5
120°	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0	1272.6	1226.6	1158.0	1113.4
122.5°	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5	1206.0	1160.9	1101.2	1062.0
125°	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7	1146.2	1109.0	1052.2	1015.4
127.5°	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8	1095.3	1060.0	1010.1	975.8
130°	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8	1049.2	1015.9	967.9	935.6
132.5°	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8	1004.2	970.9	923.8	894.0
135°	853.3	880.7	922.9	955.2	972.8	976.7	972.8	955.2	922.9	880.7	853.3
137.5°	812.2	836.7	876.8	905.2	920.9	926.8	920.9	905.2	876.8	836.7	812.2
140°	776.0	797.5	828.8	854.3	869.0	874.9	869.0	854.3	828.8	797.5	776.0
142.5°	741.2	758.3	787.7	810.2	822.9	822.9	822.9	810.2	787.7	758.3	741.2
145°	712.7	726.9	750.4	767.1	776.9	779.8	776.9	767.1	750.4	726.9	712.7
147.5°	687.8	698.5	719.1	732.8	739.7	741.6	739.7	732.8	719.1	698.5	687.8
150°	666.2	675.0	689.7	701.5	707.3	708.3	707.3	701.5	689.7	675.0	666.2
152.5°	648.0	655.4	666.2	676.0	679.9	679.9	679.9	676.0	666.2	655.4	648.0
155°	630.4	635.8	646.6	653.4	657.4	655.4	657.4	653.4	646.6	635.8	630.4
157.5°	613.8	618.2	626.0	631.9	633.9	633.9	633.9	631.9	626.0	618.2	613.8
160°	597.1	600.5	607.4	612.3	613.3	613.3	613.3	612.3	607.4	600.5	597.1
162.5°	581.4	583.9	590.7	593.7	594.7	593.7	594.7	593.7	590.7	583.9	581.4
165°	566.2	568.2	572.1	576.1	576.1	575.1	576.1	576.1	572.1	568.2	566.2
167.5°	552.6	554.5	556.5	558.4	558.4	557.4	558.4	558.4	556.5	554.5	552.6
170°	539.8	540.8	541.8	544.7	543.7	541.8	543.7	544.7	541.8	540.8	539.8
172.5°	528.6	529.0	530.0	531.0	530.0	529.0	530.0	531.0	530.0	529.0	528.6
175°	519.7	520.2	520.2	521.2	520.2	518.3	520.2	521.2	520.2	520.2	519.7
177.5°	513.4	513.4	513.4	513.4	512.4	510.4	512.4	513.4	513.4	513.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1394.8	1399.9	1397.9	1386.7	1397.9	1400.9	1407.0	1413.1	1417.2	1423.3	1428.4
5°	1307.3	1317.5	1323.6	1317.5	1337.9	1340.9	1355.2	1363.3	1375.5	1385.7	1393.8
7.5°	1224.9	1233.1	1245.3	1247.3	1259.5	1273.8	1294.1	1314.5	1333.8	1344.0	1353.1
10°	1136.4	1150.7	1169.0	1164.9	1183.2	1205.6	1227.0	1259.5	1275.8	1294.1	1310.4
12.5°	1047.9	1057.1	1081.5	1089.6	1116.1	1133.4	1162.9	1183.2	1223.9	1245.3	1259.5
15°	893.3	930.9	961.4	998.1	1032.6	1065.2	1091.7	1128.3	1163.9	1180.2	1203.6
17.5°	823.1	840.4	858.7	877.0	921.7	979.7	1026.5	1066.2	1096.7	1118.1	1145.6
20°	749.8	767.1	787.5	804.8	832.2	873.9	931.9	1000.1	1036.7	1059.1	1085.5
22.5°	697.9	714.2	727.4	742.7	764.1	794.6	838.3	922.8	971.6	999.1	1022.5
25°	642.0	662.3	676.6	687.8	705.0	738.6	774.2	822.0	909.5	930.9	963.5
27.5°	603.3	609.4	625.7	643.0	660.3	678.6	715.2	755.9	814.9	861.7	901.4
30°	557.5	572.8	588.0	595.2	610.4	636.9	659.3	703.0	748.8	785.4	833.2
32.5°	522.9	532.1	542.3	559.6	573.8	592.1	614.5	651.1	689.8	713.2	749.8
35°	484.3	490.4	511.7	518.9	533.1	551.4	573.8	602.3	644.0	662.3	688.8
37.5°	447.6	461.9	468.0	484.3	497.5	515.8	532.1	564.6	592.1	613.5	637.9
40°	419.2	425.3	436.5	450.7	461.9	476.1	496.5	519.9	549.4	566.7	588.0
42.5°	384.6	389.7	403.9	412.0	430.4	443.6	455.8	484.3	510.7	524.0	545.3
45°	346.9	359.1	368.3	384.6	394.7	411.0	426.3	446.6	471.0	486.3	498.5
47.5°	314.4	326.6	335.7	351.0	367.3	374.4	390.7	412.0	434.4	446.6	463.9
50°	287.9	292.0	309.3	316.4	333.7	347.9	359.1	377.4	401.9	409.0	423.2
52.5°	262.5	265.5	276.7	285.9	301.1	313.4	327.6	344.9	365.2	376.4	387.6
55°	240.1	242.1	247.2	257.4	267.6	282.8	296.1	312.3	329.6	341.8	352.0
57.5°	214.7	218.7	222.8	228.9	239.1	253.3	267.6	282.8	297.1	305.2	318.4
60°	185.2	191.3	198.4	205.5	212.6	222.8	239.1	253.3	266.6	273.7	283.9
62.5°	153.6	165.8	171.9	180.1	186.2	195.3	207.5	223.8	233.0	242.1	250.3
65°	138.4	139.4	140.4	148.5	159.7	168.9	180.1	192.3	206.5	212.6	218.7
67.5°	123.1	124.1	126.2	127.2	131.2	141.4	153.6	166.9	178.0	182.1	188.2
70°	107.8	107.8	111.9	112.9	113.9	115.0	125.1	138.4	148.5	153.6	160.7
72.5°	91.6	92.6	94.6	95.6	97.7	99.7	102.8	109.9	122.1	127.2	135.3
75°	75.3	76.3	77.3	78.3	81.4	82.4	85.5	89.5	94.6	100.7	105.8
77.5°	60.0	60.0	61.0	63.1	65.1	66.1	69.2	71.2	73.3	76.3	80.4
80°	44.8	45.8	45.8	47.8	47.8	48.8	49.9	52.9	54.9	57.0	59.0
82.5°	30.5	32.6	32.6	32.6	33.6	34.6	35.6	35.6	37.6	38.7	41.7
85°	18.3	19.3	19.3	19.3	18.3	20.3	20.3	21.4	21.4	21.4	22.4
87.5°	7.1	6.1	7.1	7.1	7.1	8.1	7.1	7.1	8.1	9.2	9.2
90°	31.3	29.4	31.3	32.3	33.3	32.3	26.5	19.6	14.7	13.2	11.8
92.5°	73.5	84.3	98.9	126.4	150.9	148.9	115.6	78.4	51.9	46.5	41.1
95°	155.8	196.9	256.7	336.0	384.0	340.0	226.3	141.1	96.0	84.2	72.5
97.5°	320.4	419.3	525.1	630.9	626.0	484.0	300.8	182.2	124.4	111.2	98.0
100°	638.8	773.0	894.5	915.0	774.0	532.9	321.3	201.8	149.9	136.2	122.5
102.5°	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3	219.4	172.4	158.7	145.0
105°	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2	240.0	194.0	180.2	166.5
107.5°	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0	260.6	215.5	201.8	188.1
110°	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7	281.2	238.1	223.9	209.7

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4	300.8	259.6	244.9	230.2
115°	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1	321.3	279.2	266.0	252.8
117.5°	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8	340.0	300.8	287.0	273.3
120°	1068.8	965.0	843.5	717.1	592.7	487.9	412.4	359.5	321.3	307.6	293.9
122.5°	1022.8	925.8	817.1	700.5	588.8	494.7	426.2	378.2	342.9	328.7	314.5
125°	978.7	892.5	791.6	684.8	583.9	501.6	440.9	396.8	361.5	347.8	334.1
127.5°	941.5	859.2	766.1	670.1	581.0	508.5	454.6	414.4	380.1	365.9	351.7
130°	903.3	825.9	741.6	655.4	579.0	516.3	467.3	430.1	395.8	382.1	368.4
132.5°	864.1	794.5	718.1	643.7	578.0	524.1	480.0	443.8	411.5	397.8	384.0
135°	825.9	761.2	696.6	632.9	577.0	530.0	490.8	456.5	425.2	411.5	397.8
137.5°	787.7	734.8	678.9	625.0	577.0	535.9	499.6	467.3	436.0	423.2	410.5
140°	754.4	709.3	662.3	618.2	576.1	539.8	506.5	476.1	446.7	434.0	421.3
142.5°	724.0	686.8	648.6	611.3	576.1	542.7	512.4	483.0	454.6	442.8	431.1
145°	698.5	668.1	635.8	605.4	574.1	544.7	517.3	489.8	463.4	452.6	441.8
147.5°	677.0	652.5	626.0	599.6	571.2	545.7	520.2	495.7	470.2	460.4	450.7
150°	657.4	636.8	615.2	591.7	568.2	544.7	522.2	499.6	477.1	468.3	459.5
152.5°	640.7	624.1	604.5	584.9	563.3	542.7	523.2	503.6	484.0	476.2	468.3
155°	625.0	610.3	594.7	576.1	557.4	540.8	524.1	507.5	490.8	483.4	476.1
157.5°	609.4	596.6	582.9	568.2	551.6	536.9	524.1	510.4	495.7	489.4	483.0
160°	593.7	582.9	572.1	559.4	545.7	533.9	524.1	512.4	500.6	495.2	489.8
162.5°	579.0	570.2	561.4	551.6	540.8	531.0	523.2	513.4	503.6	499.6	495.7
165°	564.3	557.4	550.6	542.7	533.9	527.1	521.2	514.3	505.5	502.6	499.6
167.5°	550.6	545.7	539.8	533.9	528.1	523.2	520.2	514.3	507.5	505.6	503.6
170°	538.8	534.9	532.0	527.1	523.2	520.2	518.3	513.4	508.5	507.0	505.5
172.5°	528.1	525.1	523.2	520.2	517.3	516.3	515.3	512.4	509.4	508.4	507.5
175°	519.2	518.3	517.3	514.3	513.4	512.4	513.4	511.4	509.4	509.0	508.5
177.5°	513.4	512.4	512.4	510.4	509.4	510.4	512.4	510.4	509.4	509.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1464.0	1464.0	1464.0	1464.0
2.5°	1437.6	1434.5	1452.8	1473.2
5°	1408.1	1413.1	1436.5	1465.0
7.5°	1377.5	1388.7	1416.2	1453.8
10°	1334.8	1355.2	1396.9	1435.5
12.5°	1293.1	1320.6	1360.2	1406.0
15°	1246.3	1276.8	1325.7	1380.6
17.5°	1194.4	1229.0	1286.0	1346.0
20°	1139.5	1185.3	1245.3	1310.4
22.5°	1078.4	1133.4	1195.4	1267.7
25°	1019.4	1079.4	1141.5	1224.9
27.5°	961.4	1020.4	1089.6	1174.1
30°	903.4	957.4	1031.6	1122.2
32.5°	841.4	897.3	975.7	1068.3
35°	784.4	840.4	913.6	1005.2
37.5°	723.4	783.4	853.6	948.2
40°	652.1	722.3	790.5	881.1
42.5°	593.1	667.4	733.5	819.0
45°	546.3	616.5	671.5	754.9
47.5°	502.6	559.6	615.5	692.8
50°	460.9	504.6	562.6	631.8
52.5°	418.1	455.8	505.6	570.8
55°	379.5	415.1	459.9	509.7
57.5°	343.9	369.3	414.1	458.8
60°	304.2	330.6	365.2	402.9
62.5°	270.6	291.0	323.5	355.1
65°	235.0	254.3	278.8	308.3
67.5°	202.5	219.8	239.1	262.5
70°	173.0	186.2	200.4	220.8
72.5°	141.4	155.7	168.9	185.2
75°	116.0	122.1	133.3	144.5
77.5°	89.5	97.7	103.8	112.9
80°	64.1	71.2	73.3	80.4
82.5°	42.7	46.8	50.9	52.9
85°	24.4	26.5	30.5	31.5
87.5°	9.2	10.2	12.2	14.2
90°	9.8	7.8	3.9	1.0
92.5°	33.3	28.4	20.6	14.7
95°	56.8	48.0	38.2	34.3
97.5°	80.3	67.6	56.8	50.9
100°	102.9	87.2	78.4	75.4
102.5°	124.4	108.7	99.9	98.0
105°	145.0	130.3	123.4	119.5
107.5°	166.5	152.8	146.0	143.0
110°	189.1	176.3	170.5	166.5

TEST NUMBER: P1000023

CATALOG NUMBER: SA2XXRDIP-B675D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	210.6	198.9	192.0	188.1
115°	233.2	221.4	215.5	210.6
117.5°	254.7	243.9	238.1	234.1
120°	274.3	265.5	259.6	255.7
122.5°	294.9	285.1	279.2	276.3
125°	314.5	302.7	296.8	293.9
127.5°	333.1	320.4	312.5	308.6
130°	348.8	335.1	325.3	321.3
132.5°	363.5	348.8	338.0	333.1
135°	375.2	360.5	348.8	344.8
137.5°	388.0	372.3	360.5	355.6
140°	399.7	384.0	372.3	368.4
142.5°	410.5	394.8	384.0	381.1
145°	422.2	407.5	397.8	393.8
147.5°	434.0	420.3	410.5	407.5
150°	444.8	432.0	424.2	421.3
152.5°	454.6	443.8	436.0	435.0
155°	465.4	454.6	448.7	447.7
157.5°	474.2	464.4	459.5	458.5
160°	482.0	474.2	470.2	469.3
162.5°	488.9	483.0	479.1	480.0
165°	494.7	488.9	486.9	487.9
167.5°	499.6	495.7	493.8	494.7
170°	503.6	500.6	499.6	501.6
172.5°	506.5	503.6	504.5	505.5
175°	508.5	506.5	507.5	508.5
177.5°	509.4	507.5	508.5	510.4
180°	509.4	509.4	509.4	509.4

(END OF REPORT)