

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000085

Luminaire Tested: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000085
REPORT IS A COMBINATION OF REPORTS P988642 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7520.0 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	97	93	89	86	89	85	82	80	71	69	67	58	56	55	46	45	44
2	89	82	76	72	81	75	71	66	63	60	57	52	49	47	41	39	38
3	82	73	66	61	75	67	61	56	56	52	48	46	43	41	37	35	33
4	75	65	58	52	69	60	53	48	51	46	42	42	38	36	34	31	29
5	69	58	51	45	63	54	47	42	46	41	37	38	34	31	31	28	26
6	64	53	45	39	59	49	42	37	41	36	32	35	31	28	28	26	23
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21
8	55	44	36	31	51	40	34	29	35	30	26	29	25	23	24	21	19
9	52	40	33	28	47	37	31	26	32	27	23	27	23	21	22	20	18
10	48	37	30	25	44	34	28	24	30	25	21	25	21	19	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30172	30172	30172	30172
5°	30242	32048	30348	25603
10°	29909	33873	30122	21143
15°	29261	33885	29757	15882
20°	28480	28009	29100	13103
25°	27533	17501	28129	11147
30°	26324	11206	27041	9597
35°	24854	8612	25659	8212
40°	23216	7238	24208	7183
45°	21467	6161	22362	6030
50°	19671	5235	20590	5216
55°	17682	4549	18636	4490
60°	15916	3469	16762	3428
65°	14270	2610	15116	2961
70°	12446	2086	13425	2413
75°	10522	1598	11485	1826
80°	8351	1087	8990	1198
85°	5806	560	6357	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27600 cd/sqm

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	2.4
10°-20°	504.7	6.7
20°-30°	649.5	8.6
30°-40°	616.2	8.2
40°-50°	528.1	7.0
50°-60°	402.2	5.3
60°-70°	253.6	3.4
70°-80°	126.5	1.7
80°-90°	36.4	0.5
90°-100°	236.3	3.1
100°-110°	832.3	11.1
110°-120°	874.1	11.6
120°-130°	719.1	9.6
130°-140°	577.7	7.7
140°-150°	436.4	5.8
150°-160°	306.8	4.1
160°-170°	180.6	2.4
170°-180°	58.7	0.8
0°-30°	1334.9	17.8
0°-40°	1951.1	25.9
0°-60°	2881.3	38.3
0°-90°	3297.9	43.9
90°-120°	1942.8	25.8
90°-150°	3676.0	48.9
90°-180°	4222.0	56.1
0°-180°	7520.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1906	1906	1906	1906	1906	
5°	1907	2121	1914	1694	1907	181
15°	1798	2394	1828	1122	1798	506
25°	1595	1277	1629	813	1595	732
35°	1309	629	1351	600	1309	819
45°	983	437	1024	428	983	759
55°	664	303	699	299	664	598
65°	401	158	425	179	401	398
75°	188	84	205	95	188	204
85°	41	24	45	25	41	47
90°	1	38	1	38	1	5
95°	41	133	41	133	41	42
105°	142	1314	142	1314	142	151
115°	251	1729	251	1729	251	249
125°	350	1403	350	1403	350	311
135°	410	1162	410	1162	410	317
145°	469	928	469	928	469	294
155°	533	780	533	780	533	245
165°	581	684	581	684	581	164
175°	605	617	605	617	605	57
180°	606	606	606	606	606	

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1918.0	1926.0	1930.0	1935.3	1947.2	1955.1	1967.0	1969.7	1968.4	1973.7	1959.1
5°	1907.4	1924.7	1940.6	1953.8	1975.0	1988.2	2002.8	2020.0	2024.0	2043.9	2032.0
7.5°	1892.9	1918.0	1940.6	1967.0	1998.8	2016.1	2038.6	2065.1	2077.0	2100.8	2107.5
10°	1869.0	1904.8	1943.2	1971.0	2014.7	2045.2	2066.4	2108.8	2136.6	2172.4	2167.1
12.5°	1830.6	1877.0	1928.6	1975.0	2032.0	2051.8	2091.6	2135.3	2171.0	2204.2	2233.3
15°	1797.5	1850.5	1907.4	1964.4	2029.3	2066.4	2106.1	2163.1	2201.5	2259.8	2285.0
17.5°	1752.5	1820.0	1887.6	1951.1	2028.0	2070.4	2119.4	2175.0	2232.0	2287.6	2307.5
20°	1706.1	1779.0	1851.8	1937.9	2025.3	2066.4	2116.7	2185.6	2241.2	2285.0	2285.0
22.5°	1650.5	1739.2	1822.7	1904.8	2000.2	2059.8	2111.4	2192.2	2232.0	2241.2	2205.5
25°	1594.8	1683.6	1775.0	1877.0	1985.6	2038.6	2096.9	2172.4	2185.6	2148.5	2055.8
27.5°	1528.6	1627.9	1731.3	1841.2	1955.1	2021.4	2074.3	2124.7	2099.5	2000.2	1855.8
30°	1461.0	1568.3	1684.9	1789.5	1927.3	1988.2	2033.3	2047.8	1968.4	1806.8	1620.0
32.5°	1390.8	1495.5	1618.7	1744.5	1883.6	1941.9	1971.0	1932.6	1786.9	1582.9	1355.1
35°	1308.7	1426.6	1555.1	1686.2	1824.0	1867.7	1884.9	1790.9	1604.1	1340.5	1114.0
37.5°	1234.5	1352.4	1490.2	1624.0	1757.8	1781.6	1764.4	1617.3	1380.2	1119.3	898.1
40°	1147.1	1272.9	1408.1	1557.7	1667.7	1674.3	1631.9	1441.2	1147.1	902.1	765.6
42.5°	1066.3	1193.5	1328.6	1480.9	1564.4	1541.8	1484.9	1234.5	957.7	777.5	667.6
45°	982.9	1103.4	1249.1	1384.2	1443.8	1390.8	1304.7	1038.5	804.0	668.9	584.2
47.5°	902.1	1014.7	1159.0	1288.8	1299.4	1239.8	1137.8	870.3	696.7	588.1	519.2
50°	822.6	935.2	1070.3	1177.6	1167.0	1084.9	969.6	756.4	605.3	519.2	462.3
52.5°	743.1	845.1	976.2	1061.0	1016.0	936.5	822.6	641.1	528.5	453.0	409.3
55°	663.6	759.0	871.6	941.8	870.3	778.9	698.1	549.7	458.3	397.4	364.3
57.5°	597.4	672.9	776.2	818.6	732.5	661.0	590.8	472.9	397.4	353.7	315.3
60°	524.5	593.4	678.2	703.4	614.6	556.3	496.7	400.0	340.4	302.0	276.8
62.5°	462.3	519.2	584.2	584.2	506.0	462.3	417.3	335.1	286.1	255.6	243.7
65°	401.4	442.4	488.8	483.5	417.3	378.8	343.1	276.8	239.8	218.6	206.6
67.5°	341.7	373.5	404.0	385.5	337.8	304.7	271.5	223.9	198.7	184.1	168.2
70°	287.4	312.6	328.5	311.3	263.6	235.8	211.9	180.1	160.3	141.7	132.5
72.5°	241.1	251.7	257.0	235.8	196.0	180.1	162.9	140.4	123.2	113.9	111.3
75°	188.1	197.4	193.4	177.5	144.4	132.5	119.2	103.3	99.3	94.0	91.4
77.5°	147.0	147.0	140.4	125.8	103.3	94.0	88.7	80.8	76.8	75.5	72.9
80°	104.6	103.3	99.3	83.5	70.2	64.9	64.9	59.6	58.3	55.6	55.6
82.5°	68.9	68.9	63.6	50.3	46.4	45.0	43.7	41.1	41.1	39.7	39.7
85°	41.1	38.4	31.8	27.8	26.5	26.5	25.2	23.8	25.2	23.8	23.8
87.5°	18.5	14.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	1.2	4.7	9.3	11.7	14.0	15.8	17.5	23.3	31.5	38.5	39.6
92.5°	17.5	24.5	33.8	39.6	49.0	55.4	61.8	93.3	137.6	177.2	179.6
95°	40.8	45.5	57.1	67.6	86.3	100.3	114.3	167.9	269.3	404.6	457.0
97.5°	60.6	67.6	80.4	95.6	116.6	132.4	148.1	216.9	357.9	576.0	745.0
100°	89.8	93.3	103.8	122.4	145.7	162.0	178.4	240.2	382.4	634.3	921.1
102.5°	116.6	118.9	129.4	148.1	172.6	188.9	205.2	261.2	383.6	612.1	926.9
105°	142.2	146.9	155.1	172.6	198.2	214.6	230.9	285.6	389.4	581.8	863.9
107.5°	170.2	173.7	181.9	198.2	223.9	240.2	256.5	310.1	402.2	565.5	805.6
110°	198.2	202.9	209.9	225.0	249.5	266.4	283.3	334.6	418.6	560.8	766.0

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	223.9	228.5	236.7	250.7	274.0	291.5	309.0	357.9	436.1	562.0	740.4
115°	250.7	256.5	263.5	277.5	300.8	316.6	332.3	382.4	453.5	566.6	722.9
117.5°	278.7	283.3	290.3	303.1	325.3	341.6	357.9	404.6	472.2	573.6	713.5
120°	304.3	309.0	316.0	326.5	349.8	366.1	382.4	427.9	490.8	580.6	705.4
122.5°	328.8	332.3	339.3	350.9	374.3	391.2	408.1	450.0	507.2	588.8	700.7
125°	349.8	353.3	360.3	374.3	397.6	413.9	430.2	472.2	524.7	596.9	694.9
127.5°	367.3	371.9	381.3	396.4	418.6	435.5	452.4	493.2	541.0	605.1	691.4
130°	382.4	387.1	398.7	415.1	438.4	454.7	471.0	511.8	556.1	614.4	689.1
132.5°	396.4	402.2	415.1	432.6	457.0	473.4	489.7	528.2	571.3	623.8	687.9
135°	410.4	415.1	429.1	446.5	473.4	489.7	506.0	543.3	584.1	630.8	686.7
137.5°	423.2	429.1	443.0	461.7	488.5	503.6	518.8	556.1	594.6	637.8	686.7
140°	438.4	443.0	457.0	475.7	501.3	516.5	531.7	566.6	602.8	642.4	685.6
142.5°	453.5	457.0	469.9	488.5	513.0	527.0	541.0	574.8	609.8	645.9	685.6
145°	468.7	473.4	485.0	502.5	525.8	538.6	551.5	583.0	615.6	648.2	683.2
147.5°	485.0	488.5	500.2	516.5	536.3	548.0	559.6	590.0	619.1	649.4	679.7
150°	501.3	504.8	514.2	529.3	546.8	557.3	567.8	594.6	621.4	648.2	676.2
152.5°	517.7	518.8	528.2	541.0	557.3	566.6	576.0	599.3	622.6	645.9	670.4
155°	532.8	534.0	541.0	553.8	566.6	575.4	584.1	603.9	623.8	643.6	663.4
157.5°	545.6	546.8	552.6	564.3	574.8	582.4	590.0	607.4	623.8	638.9	656.4
160°	558.5	559.6	564.3	573.6	583.0	589.4	595.8	609.8	623.8	635.4	649.4
162.5°	571.3	570.1	574.8	581.8	590.0	594.6	599.3	610.9	622.6	631.9	643.6
165°	580.6	579.5	581.8	588.8	594.6	598.1	601.6	612.1	620.3	627.3	635.4
167.5°	588.8	587.6	590.0	594.6	599.3	601.6	603.9	612.1	619.1	622.6	628.4
170°	596.9	594.6	595.8	599.3	601.6	603.4	605.1	610.9	616.8	619.1	622.6
172.5°	601.6	600.4	599.3	602.8	603.9	605.1	606.3	609.8	613.3	614.4	615.6
175°	605.1	603.9	602.8	605.1	605.1	605.7	606.3	608.6	610.9	609.8	610.9
177.5°	607.4	605.1	603.9	606.3	606.3	606.3	606.3	607.4	609.8	607.4	606.3
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1973.7	1976.3	1980.3	1998.8	2001.5	2006.8	2004.1	2004.1	2005.5	2002.8	2004.1
5°	2058.4	2062.4	2082.3	2104.8	2110.1	2104.8	2111.4	2120.7	2120.7	2120.7	2118.1
7.5°	2137.9	2152.5	2175.0	2208.1	2214.7	2221.4	2233.3	2225.3	2228.0	2239.9	2235.9
10°	2214.7	2235.9	2261.1	2288.9	2303.5	2312.8	2318.1	2330.0	2357.8	2326.0	2337.9
12.5°	2287.6	2318.1	2344.6	2375.0	2385.6	2397.5	2401.5	2412.1	2412.1	2410.8	2420.1
15°	2335.3	2363.1	2386.9	2406.8	2409.5	2406.8	2404.2	2405.5	2409.5	2393.6	2402.8
17.5°	2345.9	2348.5	2356.5	2348.5	2349.9	2322.0	2306.1	2302.2	2265.1	2266.4	2296.9
20°	2294.2	2249.2	2237.3	2193.6	2167.1	2095.5	2092.9	2073.0	1994.9	2018.7	2013.4
22.5°	2152.5	2075.7	1973.7	1923.3	1898.2	1822.7	1764.4	1723.3	1695.5	1667.7	1655.8
25°	1965.7	1841.2	1696.8	1597.5	1582.9	1512.7	1405.4	1355.1	1295.5	1276.9	1308.7
27.5°	1724.6	1563.0	1400.1	1247.8	1220.0	1156.4	1102.1	1066.3	997.4	993.5	996.1
30°	1397.5	1234.5	1098.1	998.8	929.9	900.7	865.0	838.5	810.7	821.3	823.9
32.5°	1148.4	993.5	866.3	813.3	781.5	763.0	732.5	715.3	703.4	699.4	698.1
35°	912.7	809.3	752.4	700.7	682.2	668.9	646.4	638.5	627.9	629.2	629.2
37.5°	781.5	695.4	653.0	626.5	609.3	602.7	588.1	580.2	573.6	570.9	574.9
40°	674.2	614.6	588.1	564.3	549.7	547.1	539.1	529.8	521.9	523.2	527.2
42.5°	596.1	561.6	529.8	511.3	500.7	496.7	490.1	483.5	483.5	479.5	478.2
45°	533.8	506.0	479.5	462.3	455.7	450.4	442.4	441.1	435.8	437.1	438.4
47.5°	478.2	455.7	435.8	418.6	412.0	410.6	402.7	397.4	397.4	396.1	394.7
50°	427.8	405.3	388.1	378.8	369.6	366.9	365.6	364.3	361.6	361.6	362.9
52.5°	386.8	364.3	351.0	343.1	337.8	335.1	335.1	333.8	333.8	333.8	332.5
55°	341.7	323.2	312.6	310.0	307.3	306.0	304.7	302.0	300.7	303.3	300.7
57.5°	299.4	292.7	283.5	280.8	274.2	274.2	270.2	267.6	264.9	267.6	267.6
60°	266.2	257.0	251.7	243.7	238.4	233.1	226.5	225.2	222.5	221.2	219.9
62.5°	231.8	223.9	210.6	198.7	190.7	185.4	182.8	181.5	181.5	180.1	180.1
65°	193.4	174.8	168.2	164.3	162.9	161.6	159.0	157.6	159.0	157.6	159.0
67.5°	151.0	148.4	144.4	141.7	140.4	139.1	139.1	137.8	137.8	137.8	137.8
70°	131.1	124.5	123.2	120.5	120.5	119.2	119.2	119.2	119.2	117.9	120.5
72.5°	108.6	104.6	103.3	102.0	102.0	102.0	100.7	100.7	100.7	99.3	100.7
75°	88.7	87.4	84.8	84.8	83.5	84.8	83.5	83.5	82.1	83.5	83.5
77.5°	71.5	70.2	68.9	68.9	67.6	67.6	67.6	67.6	67.6	67.6	68.9
80°	54.3	53.0	51.7	53.0	51.7	53.0	51.7	51.7	53.0	51.7	51.7
82.5°	39.7	38.4	38.4	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
85°	23.8	22.5	22.5	23.8	22.5	23.8	22.5	22.5	22.5	23.8	23.8
87.5°	10.6	11.9	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	11.9
90°	38.5	37.3	35.0	37.3	37.9	38.5	38.5	38.5	38.5	38.5	38.5
92.5°	150.4	117.8	100.3	87.4	82.8	78.1	77.0	72.3	73.5	71.1	73.5
95°	399.9	305.5	234.3	185.4	172.6	159.7	144.6	135.2	131.7	132.9	131.7
97.5°	750.8	624.9	499.0	381.3	346.3	311.3	265.8	242.5	229.7	222.7	229.7
100°	1089.0	1064.5	919.9	760.2	689.7	619.1	522.3	472.2	438.4	417.4	438.4
102.5°	1214.9	1352.5	1347.8	1241.7	1165.9	1090.1	982.9	888.4	844.1	813.8	844.1
105°	1174.1	1416.6	1548.3	1563.5	1544.2	1525.0	1452.7	1380.4	1330.3	1314.0	1330.3
107.5°	1087.8	1347.8	1543.7	1657.9	1681.2	1704.6	1703.4	1692.9	1677.7	1650.9	1677.7
110°	1007.3	1253.4	1462.1	1611.3	1659.1	1706.9	1757.0	1779.2	1789.7	1788.5	1789.7



TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	951.4	1167.1	1365.3	1527.3	1583.8	1640.4	1715.1	1755.9	1778.0	1786.2	1778.0
115°	907.1	1099.5	1279.0	1431.7	1491.8	1551.8	1634.6	1688.2	1718.6	1729.0	1718.6
117.5°	876.8	1043.5	1204.4	1346.6	1403.8	1460.9	1546.0	1603.1	1634.6	1642.8	1634.6
120°	853.4	1003.8	1148.4	1272.0	1325.0	1378.1	1459.7	1514.5	1548.3	1560.0	1548.3
122.5°	833.6	972.4	1101.8	1217.2	1263.8	1310.5	1381.6	1435.2	1464.4	1473.7	1464.4
125°	815.0	942.1	1062.1	1164.7	1208.4	1252.2	1319.8	1364.1	1393.3	1402.6	1393.3
127.5°	797.5	911.7	1022.5	1120.4	1161.2	1202.1	1261.5	1303.5	1329.1	1336.1	1329.1
130°	780.0	882.6	982.9	1075.0	1113.4	1151.9	1209.0	1248.7	1272.0	1281.3	1272.0
132.5°	766.0	854.6	945.6	1028.3	1063.9	1099.5	1155.4	1195.1	1216.0	1224.2	1216.0
135°	753.2	829.0	905.9	982.9	1015.6	1048.2	1098.3	1136.8	1157.7	1162.4	1157.7
137.5°	743.9	808.0	874.4	937.4	966.6	995.7	1043.5	1077.3	1096.0	1103.0	1096.0
140°	735.7	788.2	844.1	897.8	923.4	949.1	986.4	1016.7	1034.2	1041.2	1034.2
142.5°	727.5	771.8	817.3	861.6	882.0	902.4	937.4	964.2	979.4	979.4	979.4
145°	720.5	756.7	795.2	831.3	848.2	865.1	893.1	912.9	924.6	928.1	924.6
147.5°	713.5	745.0	776.5	805.6	818.4	831.3	855.8	872.1	880.3	882.6	880.3
150°	704.2	732.2	757.8	782.3	792.8	803.3	820.8	834.8	841.8	843.0	841.8
152.5°	696.0	719.4	742.7	762.5	771.2	780.0	792.8	804.5	809.1	809.1	809.1
155°	685.6	707.7	726.4	743.9	750.3	756.7	769.5	777.7	782.3	780.0	782.3
157.5°	676.2	693.7	710.0	725.2	730.4	735.7	745.0	752.0	754.3	754.3	754.3
160°	665.7	680.9	693.7	706.5	710.6	714.7	722.9	728.7	729.9	729.9	729.9
162.5°	656.4	668.1	678.6	689.1	692.0	694.9	703.0	706.5	707.7	706.5	707.7
165°	645.9	655.2	663.4	671.6	673.9	676.2	680.9	685.6	685.6	684.4	685.6
167.5°	635.4	642.4	649.4	655.2	657.6	659.9	662.2	664.6	664.6	663.4	664.6
170°	627.3	633.1	636.6	641.3	642.4	643.6	644.7	648.2	647.1	644.7	647.1
172.5°	619.1	622.6	624.9	628.4	629.0	629.6	630.8	631.9	630.8	629.6	630.8
175°	612.1	615.6	616.8	617.9	618.5	619.1	619.1	620.3	619.1	616.8	619.1
177.5°	607.4	609.8	609.8	610.9	610.9	610.9	610.9	610.9	609.8	607.4	609.8
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	2009.4	2000.2	1997.5	2000.2	1997.5	1998.8	1989.6	1955.1	1964.4	1949.8	1957.8
5°	2123.3	2115.4	2098.2	2095.5	2092.9	2090.2	2077.0	2046.5	2034.6	2014.7	2013.4
7.5°	2232.0	2232.0	2218.7	2209.4	2197.5	2188.3	2171.0	2126.0	2107.5	2083.6	2070.4
10°	2339.3	2304.8	2319.4	2310.1	2281.0	2275.7	2243.9	2217.4	2181.6	2157.8	2136.6
12.5°	2416.1	2405.5	2392.2	2384.3	2376.3	2359.1	2337.9	2270.4	2251.8	2204.2	2180.3
15°	2413.4	2406.8	2410.8	2410.8	2408.1	2404.2	2386.9	2337.9	2306.1	2259.8	2218.7
17.5°	2283.6	2300.8	2318.1	2330.0	2356.5	2368.4	2384.3	2355.2	2335.3	2295.5	2251.8
20°	2057.1	2099.5	2149.8	2160.4	2184.3	2254.5	2286.3	2311.4	2319.4	2306.1	2270.4
22.5°	1741.9	1777.6	1899.5	1896.8	1931.3	2014.7	2107.5	2183.0	2242.6	2275.7	2262.4
25°	1364.3	1414.7	1479.6	1528.6	1641.2	1765.7	1880.9	2001.5	2104.8	2196.2	2218.7
27.5°	1031.9	1098.1	1149.8	1214.7	1271.6	1418.7	1567.0	1755.1	1875.6	2049.2	2139.2
30°	834.5	865.0	916.6	947.1	974.9	1087.5	1255.7	1441.2	1653.1	1853.1	2008.1
32.5°	712.6	733.8	772.2	785.5	814.6	890.1	996.1	1165.7	1384.2	1626.6	1830.6
35°	639.8	662.3	670.3	682.2	706.0	753.7	826.6	949.7	1147.1	1384.2	1627.9
37.5°	577.5	589.5	612.0	619.9	627.9	663.6	712.6	798.7	929.9	1124.6	1394.8
40°	533.8	540.4	552.4	559.0	564.3	589.5	633.2	691.4	788.1	936.5	1185.5
42.5°	487.5	495.4	503.4	511.3	517.9	537.8	564.3	619.9	684.8	797.4	977.6
45°	442.4	447.7	457.0	462.3	471.6	487.5	511.3	549.7	608.0	679.5	825.2
47.5°	401.4	408.0	412.0	418.6	425.2	442.4	464.9	490.1	537.8	608.0	714.0
50°	364.3	372.2	377.5	378.8	384.1	400.0	418.6	446.4	476.9	531.2	623.9
52.5°	337.8	339.1	343.1	348.4	347.0	356.3	373.5	394.7	426.5	470.2	537.8
55°	307.3	311.3	313.9	315.3	315.3	323.2	332.5	352.3	377.5	413.3	470.2
57.5°	268.9	272.9	280.8	283.5	287.4	291.4	295.4	308.6	329.8	364.3	410.6
60°	229.2	231.8	239.8	245.1	247.7	258.3	263.6	274.2	286.1	311.3	355.0
62.5°	184.1	186.8	190.7	196.0	201.3	217.2	230.5	241.1	250.4	267.6	303.3
65°	160.3	161.6	164.3	165.6	166.9	173.5	185.4	200.0	217.2	230.5	251.7
67.5°	139.1	140.4	141.7	144.4	145.7	147.0	152.3	156.3	173.5	192.1	208.0
70°	119.2	121.9	123.2	123.2	124.5	127.2	129.8	135.1	140.4	149.7	169.6
72.5°	100.7	102.0	104.6	104.6	104.6	107.3	109.9	112.6	115.2	120.5	128.5
75°	83.5	86.1	86.1	86.1	87.4	87.4	90.1	92.7	95.4	99.3	102.0
77.5°	68.9	68.9	68.9	68.9	70.2	70.2	71.5	74.2	75.5	76.8	79.5
80°	51.7	53.0	53.0	53.0	54.3	54.3	54.3	57.0	58.3	58.3	60.9
82.5°	38.4	38.4	38.4	39.7	38.4	39.7	39.7	41.1	39.7	41.1	42.4
85°	23.8	23.8	23.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	26.5
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	13.2	11.9	11.9
90°	38.5	38.5	38.5	37.9	37.3	35.0	37.3	38.5	39.6	38.5	31.5
92.5°	72.3	77.0	78.1	82.8	87.4	100.3	117.8	150.4	179.6	177.2	137.6
95°	135.2	144.6	159.7	172.6	185.4	234.3	305.5	399.9	457.0	404.6	269.3
97.5°	242.5	265.8	311.3	346.3	381.3	499.0	624.9	750.8	745.0	576.0	357.9
100°	472.2	522.3	619.1	689.7	760.2	919.9	1064.5	1089.0	921.1	634.3	382.4
102.5°	888.4	982.9	1090.1	1165.9	1241.7	1347.8	1352.5	1214.9	926.9	612.1	383.6
105°	1380.4	1452.7	1525.0	1544.2	1563.5	1548.3	1416.6	1174.1	863.9	581.8	389.4
107.5°	1692.9	1703.4	1704.6	1681.2	1657.9	1543.7	1347.8	1087.8	805.6	565.5	402.2
110°	1779.2	1757.0	1706.9	1659.1	1611.3	1462.1	1253.4	1007.3	766.0	560.8	418.6

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1755.9	1715.1	1640.4	1583.8	1527.3	1365.3	1167.1	951.4	740.4	562.0	436.1
115°	1688.2	1634.6	1551.8	1491.8	1431.7	1279.0	1099.5	907.1	722.9	566.6	453.5
117.5°	1603.1	1546.0	1460.9	1403.8	1346.6	1204.4	1043.5	876.8	713.5	573.6	472.2
120°	1514.5	1459.7	1378.1	1325.0	1272.0	1148.4	1003.8	853.4	705.4	580.6	490.8
122.5°	1435.2	1381.6	1310.5	1263.8	1217.2	1101.8	972.4	833.6	700.7	588.8	507.2
125°	1364.1	1319.8	1252.2	1208.4	1164.7	1062.1	942.1	815.0	694.9	596.9	524.7
127.5°	1303.5	1261.5	1202.1	1161.2	1120.4	1022.5	911.7	797.5	691.4	605.1	541.0
130°	1248.7	1209.0	1151.9	1113.4	1075.0	982.9	882.6	780.0	689.1	614.4	556.1
132.5°	1195.1	1155.4	1099.5	1063.9	1028.3	945.6	854.6	766.0	687.9	623.8	571.3
135°	1136.8	1098.3	1048.2	1015.6	982.9	905.9	829.0	753.2	686.7	630.8	584.1
137.5°	1077.3	1043.5	995.7	966.6	937.4	874.4	808.0	743.9	686.7	637.8	594.6
140°	1016.7	986.4	949.1	923.4	897.8	844.1	788.2	735.7	685.6	642.4	602.8
142.5°	964.2	937.4	902.4	882.0	861.6	817.3	771.8	727.5	685.6	645.9	609.8
145°	912.9	893.1	865.1	848.2	831.3	795.2	756.7	720.5	683.2	648.2	615.6
147.5°	872.1	855.8	831.3	818.4	805.6	776.5	745.0	713.5	679.7	649.4	619.1
150°	834.8	820.8	803.3	792.8	782.3	757.8	732.2	704.2	676.2	648.2	621.4
152.5°	804.5	792.8	780.0	771.2	762.5	742.7	719.4	696.0	670.4	645.9	622.6
155°	777.7	769.5	756.7	750.3	743.9	726.4	707.7	685.6	663.4	643.6	623.8
157.5°	752.0	745.0	735.7	730.4	725.2	710.0	693.7	676.2	656.4	638.9	623.8
160°	728.7	722.9	714.7	710.6	706.5	693.7	680.9	665.7	649.4	635.4	623.8
162.5°	706.5	703.0	694.9	692.0	689.1	678.6	668.1	656.4	643.6	631.9	622.6
165°	685.6	680.9	676.2	673.9	671.6	663.4	655.2	645.9	635.4	627.3	620.3
167.5°	664.6	662.2	659.9	657.6	655.2	649.4	642.4	635.4	628.4	622.6	619.1
170°	648.2	644.7	643.6	642.4	641.3	636.6	633.1	627.3	622.6	619.1	616.8
172.5°	631.9	630.8	629.6	629.0	628.4	624.9	622.6	619.1	615.6	614.4	613.3
175°	620.3	619.1	619.1	618.5	617.9	616.8	615.6	612.1	610.9	609.8	610.9
177.5°	610.9	610.9	610.9	610.9	610.9	609.8	609.8	607.4	606.3	607.4	609.8
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1945.9	1939.2	1939.2	1935.3	1935.3	1914.1	1914.1	1920.7	1912.7	1903.5	1890.2
5°	1996.2	1981.6	1977.6	1972.3	1955.1	1928.6	1918.0	1914.1	1898.2	1878.3	1855.8
7.5°	2043.9	2020.0	2008.1	1996.2	1973.7	1936.6	1915.4	1900.8	1877.0	1846.5	1817.4
10°	2090.2	2059.8	2029.3	2014.7	1982.9	1936.6	1906.1	1882.3	1847.8	1806.8	1765.7
12.5°	2132.6	2069.0	2063.7	2034.6	1988.2	1935.3	1888.9	1854.5	1810.7	1763.1	1715.4
15°	2169.7	2104.8	2073.0	2046.5	1985.6	1919.4	1870.3	1828.0	1769.7	1715.4	1657.1
17.5°	2188.3	2118.1	2096.9	2053.1	1990.9	1904.8	1838.6	1786.9	1723.3	1658.4	1592.2
20°	2206.8	2124.7	2090.2	2059.8	1975.0	1877.0	1802.8	1743.2	1673.0	1596.2	1523.3
22.5°	2216.1	2124.7	2083.6	2041.2	1959.1	1846.5	1759.1	1688.9	1606.8	1528.6	1441.2
25°	2200.2	2116.7	2067.7	2024.0	1931.3	1809.4	1708.7	1629.3	1541.8	1453.1	1364.3
27.5°	2160.4	2098.2	2041.2	1996.2	1892.9	1761.7	1655.8	1565.7	1475.6	1376.3	1286.2
30°	2086.3	2058.4	2013.4	1963.1	1850.5	1719.3	1593.5	1500.8	1401.4	1302.1	1208.0
32.5°	1971.0	1994.9	1965.7	1922.0	1800.1	1661.1	1527.3	1433.2	1324.6	1217.3	1131.2
35°	1830.6	1915.4	1899.5	1869.0	1747.2	1598.8	1465.0	1351.1	1242.5	1133.9	1047.8
37.5°	1677.0	1805.4	1818.7	1800.1	1686.2	1535.2	1388.2	1276.9	1165.7	1055.7	968.3
40°	1466.3	1663.7	1706.1	1714.0	1622.6	1458.4	1304.7	1196.1	1086.2	978.9	872.9
42.5°	1272.9	1522.0	1575.0	1608.1	1541.8	1382.9	1227.9	1107.4	998.8	902.1	796.1
45°	1091.5	1351.1	1437.2	1479.6	1450.4	1296.8	1136.5	1023.9	924.6	835.8	733.8
47.5°	904.7	1165.7	1286.2	1353.8	1353.8	1209.4	1049.1	937.8	842.5	766.9	676.9
50°	780.2	997.4	1121.9	1210.7	1234.5	1120.6	969.6	861.0	770.9	688.8	619.9
52.5°	665.0	859.7	963.0	1055.7	1124.6	1025.2	880.9	782.8	694.1	617.3	563.0
55°	574.9	720.6	814.6	916.6	993.5	928.6	794.8	699.4	622.6	559.0	512.6
57.5°	488.8	615.9	692.8	782.8	865.0	816.0	708.7	626.5	559.0	503.4	462.3
60°	415.9	519.2	578.9	649.1	751.1	716.6	627.9	552.4	498.1	447.7	413.3
62.5°	353.7	435.8	486.1	536.5	629.2	613.3	544.4	486.1	439.8	397.4	368.2
65°	290.1	357.6	397.4	441.1	515.3	521.9	466.3	425.2	382.8	345.7	319.2
67.5°	234.5	287.4	323.2	360.3	419.9	438.4	400.0	365.6	329.8	299.4	275.5
70°	189.4	226.5	253.0	282.1	331.2	353.7	333.8	310.0	280.8	255.6	234.5
72.5°	149.7	173.5	189.4	211.9	251.7	274.2	272.9	251.7	230.5	213.3	196.0
75°	109.9	128.5	141.7	156.3	188.1	209.3	214.6	205.3	184.1	170.9	157.6
77.5°	83.5	94.0	100.7	111.3	133.8	152.3	160.3	157.6	143.1	132.5	123.2
80°	63.6	66.2	68.9	72.9	91.4	108.6	113.9	112.6	104.6	100.7	90.1
82.5°	45.0	46.4	47.7	49.0	55.6	70.2	75.5	78.2	71.5	67.6	58.3
85°	26.5	27.8	27.8	30.5	31.8	35.8	45.0	45.0	43.7	38.4	37.1
87.5°	13.2	13.2	11.9	11.9	13.2	14.6	17.2	19.9	17.2	15.9	14.6
90°	23.3	17.5	15.8	14.0	11.7	9.3	4.7	1.2	4.7	9.3	11.7
92.5°	93.3	61.8	55.4	49.0	39.6	33.8	24.5	17.5	24.5	33.8	39.6
95°	167.9	114.3	100.3	86.3	67.6	57.1	45.5	40.8	45.5	57.1	67.6
97.5°	216.9	148.1	132.4	116.6	95.6	80.4	67.6	60.6	67.6	80.4	95.6
100°	240.2	178.4	162.0	145.7	122.4	103.8	93.3	89.8	93.3	103.8	122.4
102.5°	261.2	205.2	188.9	172.6	148.1	129.4	118.9	116.6	118.9	129.4	148.1
105°	285.6	230.9	214.6	198.2	172.6	155.1	146.9	142.2	146.9	155.1	172.6
107.5°	310.1	256.5	240.2	223.9	198.2	181.9	173.7	170.2	173.7	181.9	198.2
110°	334.6	283.3	266.4	249.5	225.0	209.9	202.9	198.2	202.9	209.9	225.0

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	357.9	309.0	291.5	274.0	250.7	236.7	228.5	223.9	228.5	236.7	250.7
115°	382.4	332.3	316.6	300.8	277.5	263.5	256.5	250.7	256.5	263.5	277.5
117.5°	404.6	357.9	341.6	325.3	303.1	290.3	283.3	278.7	283.3	290.3	303.1
120°	427.9	382.4	366.1	349.8	326.5	316.0	309.0	304.3	309.0	316.0	326.5
122.5°	450.0	408.1	391.2	374.3	350.9	339.3	332.3	328.8	332.3	339.3	350.9
125°	472.2	430.2	413.9	397.6	374.3	360.3	353.3	349.8	353.3	360.3	374.3
127.5°	493.2	452.4	435.5	418.6	396.4	381.3	371.9	367.3	371.9	381.3	396.4
130°	511.8	471.0	454.7	438.4	415.1	398.7	387.1	382.4	387.1	398.7	415.1
132.5°	528.2	489.7	473.4	457.0	432.6	415.1	402.2	396.4	402.2	415.1	432.6
135°	543.3	506.0	489.7	473.4	446.5	429.1	415.1	410.4	415.1	429.1	446.5
137.5°	556.1	518.8	503.6	488.5	461.7	443.0	429.1	423.2	429.1	443.0	461.7
140°	566.6	531.7	516.5	501.3	475.7	457.0	443.0	438.4	443.0	457.0	475.7
142.5°	574.8	541.0	527.0	513.0	488.5	469.9	457.0	453.5	457.0	469.9	488.5
145°	583.0	551.5	538.6	525.8	502.5	485.0	473.4	468.7	473.4	485.0	502.5
147.5°	590.0	559.6	548.0	536.3	516.5	500.2	488.5	485.0	488.5	500.2	516.5
150°	594.6	567.8	557.3	546.8	529.3	514.2	504.8	501.3	504.8	514.2	529.3
152.5°	599.3	576.0	566.6	557.3	541.0	528.2	518.8	517.7	518.8	528.2	541.0
155°	603.9	584.1	575.4	566.6	553.8	541.0	534.0	532.8	534.0	541.0	553.8
157.5°	607.4	590.0	582.4	574.8	564.3	552.6	546.8	545.6	546.8	552.6	564.3
160°	609.8	595.8	589.4	583.0	573.6	564.3	559.6	558.5	559.6	564.3	573.6
162.5°	610.9	599.3	594.6	590.0	581.8	574.8	570.1	571.3	570.1	574.8	581.8
165°	612.1	601.6	598.1	594.6	588.8	581.8	579.5	580.6	579.5	581.8	588.8
167.5°	612.1	603.9	601.6	599.3	594.6	590.0	587.6	588.8	587.6	590.0	594.6
170°	610.9	605.1	603.4	601.6	599.3	595.8	594.6	596.9	594.6	595.8	599.3
172.5°	609.8	606.3	605.1	603.9	602.8	599.3	600.4	601.6	600.4	599.3	602.8
175°	608.6	606.3	605.7	605.1	605.1	602.8	603.9	605.1	603.9	602.8	605.1
177.5°	607.4	606.3	606.3	606.3	606.3	603.9	605.1	607.4	605.1	603.9	606.3
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1884.9	1886.2	1890.2	1878.3	1859.8	1851.8	1828.0	1824.0	1820.0	1820.0	1824.0
5°	1842.5	1837.2	1838.6	1816.0	1789.5	1773.7	1740.5	1745.8	1728.6	1718.0	1720.7
7.5°	1796.2	1781.6	1780.3	1751.1	1718.0	1688.9	1654.4	1646.5	1630.6	1612.0	1604.1
10°	1737.9	1727.3	1707.4	1674.3	1631.9	1608.1	1561.7	1533.9	1529.9	1502.1	1491.5
12.5°	1678.3	1659.7	1639.9	1593.5	1545.8	1507.4	1473.0	1442.5	1421.3	1397.5	1381.6
15°	1609.4	1586.9	1564.4	1515.4	1459.7	1421.3	1369.6	1324.6	1262.4	1213.3	1185.5
17.5°	1533.9	1508.7	1478.3	1424.0	1369.6	1316.7	1221.3	1168.3	1124.6	1095.5	1078.2
20°	1455.7	1427.9	1397.5	1343.2	1249.1	1156.4	1103.4	1062.3	1035.8	1006.7	985.5
22.5°	1373.6	1344.5	1311.4	1226.6	1127.2	1062.3	1021.3	982.9	944.4	928.6	918.0
25°	1296.8	1270.3	1227.9	1112.7	1034.5	974.9	928.6	903.4	883.5	862.3	842.5
27.5°	1217.3	1168.3	1108.7	1012.0	963.0	902.1	868.9	850.4	816.0	801.4	792.1
30°	1121.9	1067.6	1010.7	941.8	884.8	842.5	812.0	781.5	761.7	747.1	731.2
32.5°	1025.2	973.6	937.8	866.3	823.9	780.2	751.1	732.5	703.4	694.1	687.5
35°	941.8	898.1	866.3	808.0	768.3	728.5	707.3	679.5	661.0	643.8	633.2
37.5°	859.7	835.8	802.7	753.7	711.3	679.5	650.4	641.1	615.9	606.7	596.1
40°	802.7	766.9	739.1	696.7	661.0	626.5	608.0	586.8	569.6	555.0	551.0
42.5°	733.8	707.3	691.4	645.1	608.0	588.1	565.6	541.8	528.5	516.6	502.0
45°	682.2	658.3	635.8	598.7	565.6	540.4	520.6	504.7	482.2	476.9	454.3
47.5°	627.9	604.0	586.8	549.7	519.2	495.4	480.8	459.6	441.1	429.2	418.6
50°	573.6	553.7	537.8	506.0	479.5	454.3	434.5	413.3	405.3	385.5	378.8
52.5°	521.9	508.7	491.4	461.0	434.5	413.3	392.1	374.9	362.9	352.3	344.4
55°	478.2	457.0	449.0	415.9	393.4	370.9	352.3	341.7	327.2	320.6	313.9
57.5°	429.2	417.3	404.0	378.8	353.7	332.5	319.2	303.3	295.4	287.4	282.1
60°	386.8	369.6	359.0	337.8	315.3	295.4	283.5	271.5	260.9	254.3	243.7
62.5°	337.8	324.5	317.9	295.4	276.8	258.3	247.7	235.8	227.8	215.9	202.7
65°	295.4	284.8	276.8	258.3	241.1	223.9	213.3	198.7	188.1	181.5	180.1
67.5°	258.3	250.4	238.4	221.2	204.0	190.7	178.8	166.9	165.6	162.9	162.9
70°	217.2	209.3	202.7	184.1	169.6	155.0	152.3	148.4	144.4	143.1	140.4
72.5°	181.5	174.8	166.9	151.0	136.4	132.5	129.8	127.2	123.2	121.9	120.5
75°	147.0	137.8	132.5	117.9	113.9	111.3	108.6	104.6	102.0	100.7	98.0
77.5°	112.6	103.3	103.3	95.4	92.7	88.7	86.1	83.5	82.1	79.5	79.5
80°	79.5	79.5	76.8	72.9	68.9	67.6	63.6	62.3	60.9	62.3	59.6
82.5°	58.3	53.0	53.0	50.3	47.7	46.4	43.7	43.7	42.4	42.4	42.4
85°	33.1	33.1	31.8	29.1	27.8	27.8	26.5	26.5	25.2	25.2	23.8
87.5°	13.2	11.9	13.2	11.9	11.9	10.6	10.6	10.6	9.3	10.6	9.3
90°	14.0	15.8	17.5	23.3	31.5	38.5	39.6	38.5	37.3	35.0	37.3
92.5°	49.0	55.4	61.8	93.3	137.6	177.2	179.6	150.4	117.8	100.3	87.4
95°	86.3	100.3	114.3	167.9	269.3	404.6	457.0	399.9	305.5	234.3	185.4
97.5°	116.6	132.4	148.1	216.9	357.9	576.0	745.0	750.8	624.9	499.0	381.3
100°	145.7	162.0	178.4	240.2	382.4	634.3	921.1	1089.0	1064.5	919.9	760.2
102.5°	172.6	188.9	205.2	261.2	383.6	612.1	926.9	1214.9	1352.5	1347.8	1241.7
105°	198.2	214.6	230.9	285.6	389.4	581.8	863.9	1174.1	1416.6	1548.3	1563.5
107.5°	223.9	240.2	256.5	310.1	402.2	565.5	805.6	1087.8	1347.8	1543.7	1657.9
110°	249.5	266.4	283.3	334.6	418.6	560.8	766.0	1007.3	1253.4	1462.1	1611.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	274.0	291.5	309.0	357.9	436.1	562.0	740.4	951.4	1167.1	1365.3	1527.3
115°	300.8	316.6	332.3	382.4	453.5	566.6	722.9	907.1	1099.5	1279.0	1431.7
117.5°	325.3	341.6	357.9	404.6	472.2	573.6	713.5	876.8	1043.5	1204.4	1346.6
120°	349.8	366.1	382.4	427.9	490.8	580.6	705.4	853.4	1003.8	1148.4	1272.0
122.5°	374.3	391.2	408.1	450.0	507.2	588.8	700.7	833.6	972.4	1101.8	1217.2
125°	397.6	413.9	430.2	472.2	524.7	596.9	694.9	815.0	942.1	1062.1	1164.7
127.5°	418.6	435.5	452.4	493.2	541.0	605.1	691.4	797.5	911.7	1022.5	1120.4
130°	438.4	454.7	471.0	511.8	556.1	614.4	689.1	780.0	882.6	982.9	1075.0
132.5°	457.0	473.4	489.7	528.2	571.3	623.8	687.9	766.0	854.6	945.6	1028.3
135°	473.4	489.7	506.0	543.3	584.1	630.8	686.7	753.2	829.0	905.9	982.9
137.5°	488.5	503.6	518.8	556.1	594.6	637.8	686.7	743.9	808.0	874.4	937.4
140°	501.3	516.5	531.7	566.6	602.8	642.4	685.6	735.7	788.2	844.1	897.8
142.5°	513.0	527.0	541.0	574.8	609.8	645.9	685.6	727.5	771.8	817.3	861.6
145°	525.8	538.6	551.5	583.0	615.6	648.2	683.2	720.5	756.7	795.2	831.3
147.5°	536.3	548.0	559.6	590.0	619.1	649.4	679.7	713.5	745.0	776.5	805.6
150°	546.8	557.3	567.8	594.6	621.4	648.2	676.2	704.2	732.2	757.8	782.3
152.5°	557.3	566.6	576.0	599.3	622.6	645.9	670.4	696.0	719.4	742.7	762.5
155°	566.6	575.4	584.1	603.9	623.8	643.6	663.4	685.6	707.7	726.4	743.9
157.5°	574.8	582.4	590.0	607.4	623.8	638.9	656.4	676.2	693.7	710.0	725.2
160°	583.0	589.4	595.8	609.8	623.8	635.4	649.4	665.7	680.9	693.7	706.5
162.5°	590.0	594.6	599.3	610.9	622.6	631.9	643.6	656.4	668.1	678.6	689.1
165°	594.6	598.1	601.6	612.1	620.3	627.3	635.4	645.9	655.2	663.4	671.6
167.5°	599.3	601.6	603.9	612.1	619.1	622.6	628.4	635.4	642.4	649.4	655.2
170°	601.6	603.4	605.1	610.9	616.8	619.1	622.6	627.3	633.1	636.6	641.3
172.5°	603.9	605.1	606.3	609.8	613.3	614.4	615.6	619.1	622.6	624.9	628.4
175°	605.1	605.7	606.3	608.6	610.9	609.8	610.9	612.1	615.6	616.8	617.9
177.5°	606.3	606.3	606.3	607.4	609.8	607.4	606.3	607.4	609.8	609.8	610.9
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1824.0	1821.3	1813.4	1816.0	1812.1	1812.1	1809.4	1809.4	1809.4	1816.0	1812.1
5°	1724.6	1715.4	1706.1	1702.1	1698.1	1694.2	1694.2	1692.9	1704.8	1702.1	1712.7
7.5°	1601.5	1598.8	1580.3	1580.3	1573.6	1571.0	1577.6	1578.9	1580.3	1582.9	1589.5
10°	1491.5	1484.9	1458.4	1461.0	1457.1	1451.8	1455.7	1453.1	1462.4	1465.0	1462.4
12.5°	1361.7	1349.8	1320.6	1306.1	1290.2	1278.2	1292.8	1282.2	1319.3	1329.9	1359.0
15°	1189.5	1167.0	1147.1	1147.1	1132.5	1121.9	1128.6	1140.5	1148.4	1160.4	1165.7
17.5°	1074.3	1065.0	1049.1	1039.8	1035.8	1031.9	1031.9	1037.2	1054.4	1053.1	1063.7
20°	976.2	970.9	963.0	951.1	947.1	944.4	944.4	944.4	956.4	967.0	973.6
22.5°	908.7	904.7	899.4	883.5	875.6	872.9	879.5	883.5	892.8	900.7	907.4
25°	841.1	831.9	822.6	817.3	813.3	813.3	816.0	817.3	821.3	825.2	833.2
27.5°	785.5	778.9	765.6	751.1	751.1	747.1	749.7	752.4	761.7	774.9	781.5
30°	723.2	721.9	716.6	711.3	706.0	703.4	708.7	712.6	714.0	720.6	720.6
32.5°	678.2	668.9	659.7	654.4	651.7	650.4	651.7	657.0	657.0	665.0	674.2
35°	633.2	627.9	618.6	609.3	606.7	600.0	605.3	610.6	619.9	623.9	627.9
37.5°	584.2	577.5	573.6	570.9	565.6	566.9	563.0	570.9	578.9	577.5	580.2
40°	547.1	535.1	523.2	521.9	520.6	519.2	519.2	520.6	525.9	531.2	539.1
42.5°	499.4	495.4	484.8	474.2	471.6	468.9	466.3	471.6	482.2	491.4	495.4
45°	450.4	445.1	442.4	434.5	429.2	427.8	425.2	431.8	441.1	445.1	447.7
47.5°	405.3	404.0	396.1	397.4	393.4	394.7	393.4	397.4	397.4	401.4	404.0
50°	374.9	370.9	366.9	364.3	360.3	360.3	359.0	360.3	365.6	370.9	369.6
52.5°	344.4	337.8	336.5	335.1	332.5	335.1	331.2	332.5	337.8	340.4	339.1
55°	308.6	307.3	304.7	302.0	300.7	299.4	299.4	299.4	304.7	308.6	310.0
57.5°	280.8	274.2	268.9	268.9	263.6	262.3	264.9	266.2	270.2	272.9	275.5
60°	242.4	239.8	231.8	227.8	219.9	218.6	218.6	223.9	230.5	239.8	242.4
62.5°	201.3	197.4	196.0	196.0	196.0	196.0	196.0	196.0	196.0	197.4	197.4
65°	178.8	180.1	178.8	177.5	178.8	178.8	177.5	177.5	177.5	178.8	180.1
67.5°	160.3	159.0	160.3	159.0	157.6	157.6	156.3	157.6	159.0	160.3	160.3
70°	139.1	139.1	137.8	139.1	137.8	136.4	135.1	135.1	137.8	139.1	139.1
72.5°	119.2	119.2	117.9	117.9	115.2	115.2	116.6	115.2	115.2	119.2	119.2
75°	99.3	98.0	96.7	96.7	95.4	95.4	95.4	94.0	96.7	96.7	98.0
77.5°	78.2	78.2	78.2	76.8	76.8	75.5	75.5	76.8	76.8	76.8	78.2
80°	59.6	59.6	59.6	58.3	57.0	57.0	57.0	57.0	57.0	58.3	57.0
82.5°	41.1	41.1	41.1	41.1	41.1	39.7	39.7	39.7	41.1	41.1	39.7
85°	25.2	23.8	25.2	25.2	23.8	25.2	23.8	23.8	22.5	22.5	23.8
87.5°	10.6	9.3	7.9	7.9	9.3	7.9	7.9	7.9	9.3	7.9	7.9
90°	37.9	38.5	38.5	38.5	38.5	38.5	38.5	38.5	38.5	38.5	37.9
92.5°	82.8	78.1	77.0	72.3	73.5	71.1	73.5	72.3	77.0	78.1	82.8
95°	172.6	159.7	144.6	135.2	131.7	132.9	131.7	135.2	144.6	159.7	172.6
97.5°	346.3	311.3	265.8	242.5	229.7	222.7	229.7	242.5	265.8	311.3	346.3
100°	689.7	619.1	522.3	472.2	438.4	417.4	438.4	472.2	522.3	619.1	689.7
102.5°	1165.9	1090.1	982.9	888.4	844.1	813.8	844.1	888.4	982.9	1090.1	1165.9
105°	1544.2	1525.0	1452.7	1380.4	1330.3	1314.0	1330.3	1380.4	1452.7	1525.0	1544.2
107.5°	1681.2	1704.6	1703.4	1692.9	1677.7	1650.9	1677.7	1692.9	1703.4	1704.6	1681.2
110°	1659.1	1706.9	1757.0	1779.2	1789.7	1788.5	1789.7	1779.2	1757.0	1706.9	1659.1

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1583.8	1640.4	1715.1	1755.9	1778.0	1786.2	1778.0	1755.9	1715.1	1640.4	1583.8
115°	1491.8	1551.8	1634.6	1688.2	1718.6	1729.0	1718.6	1688.2	1634.6	1551.8	1491.8
117.5°	1403.8	1460.9	1546.0	1603.1	1634.6	1642.8	1634.6	1603.1	1546.0	1460.9	1403.8
120°	1325.0	1378.1	1459.7	1514.5	1548.3	1560.0	1548.3	1514.5	1459.7	1378.1	1325.0
122.5°	1263.8	1310.5	1381.6	1435.2	1464.4	1473.7	1464.4	1435.2	1381.6	1310.5	1263.8
125°	1208.4	1252.2	1319.8	1364.1	1393.3	1402.6	1393.3	1364.1	1319.8	1252.2	1208.4
127.5°	1161.2	1202.1	1261.5	1303.5	1329.1	1336.1	1329.1	1303.5	1261.5	1202.1	1161.2
130°	1113.4	1151.9	1209.0	1248.7	1272.0	1281.3	1272.0	1248.7	1209.0	1151.9	1113.4
132.5°	1063.9	1099.5	1155.4	1195.1	1216.0	1224.2	1216.0	1195.1	1155.4	1099.5	1063.9
135°	1015.6	1048.2	1098.3	1136.8	1157.7	1162.4	1157.7	1136.8	1098.3	1048.2	1015.6
137.5°	966.6	995.7	1043.5	1077.3	1096.0	1103.0	1096.0	1077.3	1043.5	995.7	966.6
140°	923.4	949.1	986.4	1016.7	1034.2	1041.2	1034.2	1016.7	986.4	949.1	923.4
142.5°	882.0	902.4	937.4	964.2	979.4	979.4	979.4	964.2	937.4	902.4	882.0
145°	848.2	865.1	893.1	912.9	924.6	928.1	924.6	912.9	893.1	865.1	848.2
147.5°	818.4	831.3	855.8	872.1	880.3	882.6	880.3	872.1	855.8	831.3	818.4
150°	792.8	803.3	820.8	834.8	841.8	843.0	841.8	834.8	820.8	803.3	792.8
152.5°	771.2	780.0	792.8	804.5	809.1	809.1	809.1	804.5	792.8	780.0	771.2
155°	750.3	756.7	769.5	777.7	782.3	780.0	782.3	777.7	769.5	756.7	750.3
157.5°	730.4	735.7	745.0	752.0	754.3	754.3	754.3	752.0	745.0	735.7	730.4
160°	710.6	714.7	722.9	728.7	729.9	729.9	729.9	728.7	722.9	714.7	710.6
162.5°	692.0	694.9	703.0	706.5	707.7	706.5	707.7	706.5	703.0	694.9	692.0
165°	673.9	676.2	680.9	685.6	685.6	684.4	685.6	685.6	680.9	676.2	673.9
167.5°	657.6	659.9	662.2	664.6	664.6	663.4	664.6	664.6	662.2	659.9	657.6
170°	642.4	643.6	644.7	648.2	647.1	644.7	647.1	648.2	644.7	643.6	642.4
172.5°	629.0	629.6	630.8	631.9	630.8	629.6	630.8	631.9	630.8	629.6	629.0
175°	618.5	619.1	619.1	620.3	619.1	616.8	619.1	620.3	619.1	619.1	618.5
177.5°	610.9	610.9	610.9	610.9	609.8	607.4	609.8	610.9	610.9	610.9	610.9
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1816.0	1822.7	1820.0	1805.4	1820.0	1824.0	1831.9	1839.9	1845.2	1853.1	1859.8
5°	1702.1	1715.4	1723.3	1715.4	1741.9	1745.8	1764.4	1775.0	1790.9	1804.1	1814.7
7.5°	1594.8	1605.4	1621.3	1624.0	1639.9	1658.4	1684.9	1711.4	1736.6	1749.8	1761.7
10°	1479.6	1498.1	1522.0	1516.7	1540.5	1569.7	1597.5	1639.9	1661.1	1684.9	1706.1
12.5°	1364.3	1376.3	1408.1	1418.7	1453.1	1475.6	1514.0	1540.5	1593.5	1621.3	1639.9
15°	1163.0	1212.0	1251.8	1299.4	1344.5	1386.9	1421.3	1469.0	1515.4	1536.5	1567.0
17.5°	1071.6	1094.1	1118.0	1141.8	1200.1	1275.6	1336.5	1388.2	1427.9	1455.7	1491.5
20°	976.2	998.8	1025.2	1047.8	1083.5	1137.8	1213.3	1302.1	1349.8	1378.9	1413.4
22.5°	908.7	929.9	947.1	967.0	994.8	1034.5	1091.5	1201.4	1265.0	1300.8	1331.2
25°	835.8	862.3	880.9	895.4	918.0	961.7	1008.0	1070.3	1184.2	1212.0	1254.4
27.5°	785.5	793.4	814.6	837.2	859.7	883.5	931.2	984.2	1061.0	1121.9	1173.6
30°	725.9	745.8	765.6	774.9	794.8	829.2	858.3	915.3	974.9	1022.6	1084.9
32.5°	680.8	692.8	706.0	728.5	747.1	770.9	800.1	847.8	898.1	928.6	976.2
35°	630.5	638.5	666.3	675.6	694.1	717.9	747.1	784.2	838.5	862.3	896.8
37.5°	582.8	601.4	609.3	630.5	647.7	671.6	692.8	735.2	770.9	798.7	830.5
40°	545.7	553.7	568.3	586.8	601.4	619.9	646.4	676.9	715.3	737.8	765.6
42.5°	500.7	507.3	525.9	536.5	560.3	577.5	593.4	630.5	665.0	682.2	710.0
45°	451.7	467.6	479.5	500.7	513.9	535.1	555.0	581.5	613.3	633.2	649.1
47.5°	409.3	425.2	437.1	457.0	478.2	487.5	508.7	536.5	565.6	581.5	604.0
50°	374.9	380.2	402.7	412.0	434.5	453.0	467.6	491.4	523.2	532.5	551.0
52.5°	341.7	345.7	360.3	372.2	392.1	408.0	426.5	449.0	475.5	490.1	504.7
55°	312.6	315.3	321.9	335.1	348.4	368.2	385.5	406.7	429.2	445.1	458.3
57.5°	279.5	284.8	290.1	298.0	311.3	329.8	348.4	368.2	386.8	397.4	414.6
60°	241.1	249.0	258.3	267.6	276.8	290.1	311.3	329.8	347.0	356.3	369.6
62.5°	200.0	215.9	223.9	234.5	242.4	254.3	270.2	291.4	303.3	315.3	325.9
65°	180.1	181.5	182.8	193.4	208.0	219.9	234.5	250.4	268.9	276.8	284.8
67.5°	160.3	161.6	164.3	165.6	170.9	184.1	200.0	217.2	231.8	237.1	245.1
70°	140.4	140.4	145.7	147.0	148.4	149.7	162.9	180.1	193.4	200.0	209.3
72.5°	119.2	120.5	123.2	124.5	127.2	129.8	133.8	143.1	159.0	165.6	176.2
75°	98.0	99.3	100.7	102.0	106.0	107.3	111.3	116.6	123.2	131.1	137.8
77.5°	78.2	78.2	79.5	82.1	84.8	86.1	90.1	92.7	95.4	99.3	104.6
80°	58.3	59.6	59.6	62.3	62.3	63.6	64.9	68.9	71.5	74.2	76.8
82.5°	39.7	42.4	42.4	42.4	43.7	45.0	46.4	46.4	49.0	50.3	54.3
85°	23.8	25.2	25.2	25.2	23.8	26.5	26.5	27.8	27.8	27.8	29.1
87.5°	9.3	7.9	9.3	9.3	9.3	10.6	9.3	9.3	10.6	11.9	11.9
90°	37.3	35.0	37.3	38.5	39.6	38.5	31.5	23.3	17.5	15.8	14.0
92.5°	87.4	100.3	117.8	150.4	179.6	177.2	137.6	93.3	61.8	55.4	49.0
95°	185.4	234.3	305.5	399.9	457.0	404.6	269.3	167.9	114.3	100.3	86.3
97.5°	381.3	499.0	624.9	750.8	745.0	576.0	357.9	216.9	148.1	132.4	116.6
100°	760.2	919.9	1064.5	1089.0	921.1	634.3	382.4	240.2	178.4	162.0	145.7
102.5°	1241.7	1347.8	1352.5	1214.9	926.9	612.1	383.6	261.2	205.2	188.9	172.6
105°	1563.5	1548.3	1416.6	1174.1	863.9	581.8	389.4	285.6	230.9	214.6	198.2
107.5°	1657.9	1543.7	1347.8	1087.8	805.6	565.5	402.2	310.1	256.5	240.2	223.9
110°	1611.3	1462.1	1253.4	1007.3	766.0	560.8	418.6	334.6	283.3	266.4	249.5

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1527.3	1365.3	1167.1	951.4	740.4	562.0	436.1	357.9	309.0	291.5	274.0
115°	1431.7	1279.0	1099.5	907.1	722.9	566.6	453.5	382.4	332.3	316.6	300.8
117.5°	1346.6	1204.4	1043.5	876.8	713.5	573.6	472.2	404.6	357.9	341.6	325.3
120°	1272.0	1148.4	1003.8	853.4	705.4	580.6	490.8	427.9	382.4	366.1	349.8
122.5°	1217.2	1101.8	972.4	833.6	700.7	588.8	507.2	450.0	408.1	391.2	374.3
125°	1164.7	1062.1	942.1	815.0	694.9	596.9	524.7	472.2	430.2	413.9	397.6
127.5°	1120.4	1022.5	911.7	797.5	691.4	605.1	541.0	493.2	452.4	435.5	418.6
130°	1075.0	982.9	882.6	780.0	689.1	614.4	556.1	511.8	471.0	454.7	438.4
132.5°	1028.3	945.6	854.6	766.0	687.9	623.8	571.3	528.2	489.7	473.4	457.0
135°	982.9	905.9	829.0	753.2	686.7	630.8	584.1	543.3	506.0	489.7	473.4
137.5°	937.4	874.4	808.0	743.9	686.7	637.8	594.6	556.1	518.8	503.6	488.5
140°	897.8	844.1	788.2	735.7	685.6	642.4	602.8	566.6	531.7	516.5	501.3
142.5°	861.6	817.3	771.8	727.5	685.6	645.9	609.8	574.8	541.0	527.0	513.0
145°	831.3	795.2	756.7	720.5	683.2	648.2	615.6	583.0	551.5	538.6	525.8
147.5°	805.6	776.5	745.0	713.5	679.7	649.4	619.1	590.0	559.6	548.0	536.3
150°	782.3	757.8	732.2	704.2	676.2	648.2	621.4	594.6	567.8	557.3	546.8
152.5°	762.5	742.7	719.4	696.0	670.4	645.9	622.6	599.3	576.0	566.6	557.3
155°	743.9	726.4	707.7	685.6	663.4	643.6	623.8	603.9	584.1	575.4	566.6
157.5°	725.2	710.0	693.7	676.2	656.4	638.9	623.8	607.4	590.0	582.4	574.8
160°	706.5	693.7	680.9	665.7	649.4	635.4	623.8	609.8	595.8	589.4	583.0
162.5°	689.1	678.6	668.1	656.4	643.6	631.9	622.6	610.9	599.3	594.6	590.0
165°	671.6	663.4	655.2	645.9	635.4	627.3	620.3	612.1	601.6	598.1	594.6
167.5°	655.2	649.4	642.4	635.4	628.4	622.6	619.1	612.1	603.9	601.6	599.3
170°	641.3	636.6	633.1	627.3	622.6	619.1	616.8	610.9	605.1	603.4	601.6
172.5°	628.4	624.9	622.6	619.1	615.6	614.4	613.3	609.8	606.3	605.1	603.9
175°	617.9	616.8	615.6	612.1	610.9	609.8	610.9	608.6	606.3	605.7	605.1
177.5°	610.9	609.8	609.8	607.4	606.3	607.4	609.8	607.4	606.3	606.3	606.3
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1906.1	1906.1	1906.1	1906.1
2.5°	1871.7	1867.7	1891.5	1918.0
5°	1833.3	1839.9	1870.3	1907.4
7.5°	1793.5	1808.1	1843.9	1892.9
10°	1737.9	1764.4	1818.7	1869.0
12.5°	1683.6	1719.3	1771.0	1830.6
15°	1622.6	1662.4	1726.0	1797.5
17.5°	1555.1	1600.1	1674.3	1752.5
20°	1483.6	1543.2	1621.3	1706.1
22.5°	1404.1	1475.6	1556.4	1650.5
25°	1327.3	1405.4	1486.2	1594.8
27.5°	1251.8	1328.6	1418.7	1528.6
30°	1176.3	1246.5	1343.2	1461.0
32.5°	1095.5	1168.3	1270.3	1390.8
35°	1021.3	1094.1	1189.5	1308.7
37.5°	941.8	1019.9	1111.3	1234.5
40°	849.1	940.5	1029.2	1147.1
42.5°	772.2	868.9	955.0	1066.3
45°	711.3	802.7	874.2	982.9
47.5°	654.4	728.5	801.4	902.1
50°	600.0	657.0	732.5	822.6
52.5°	544.4	593.4	658.3	743.1
55°	494.1	540.4	598.7	663.6
57.5°	447.7	480.8	539.1	597.4
60°	396.1	430.5	475.5	524.5
62.5°	352.3	378.8	421.2	462.3
65°	306.0	331.2	362.9	401.4
67.5°	263.6	286.1	311.3	341.7
70°	225.2	242.4	260.9	287.4
72.5°	184.1	202.7	219.9	241.1
75°	151.0	159.0	173.5	188.1
77.5°	116.6	127.2	135.1	147.0
80°	83.5	92.7	95.4	104.6
82.5°	55.6	60.9	66.2	68.9
85°	31.8	34.4	39.7	41.1
87.5°	11.9	13.2	15.9	18.5
90°	11.7	9.3	4.7	1.2
92.5°	39.6	33.8	24.5	17.5
95°	67.6	57.1	45.5	40.8
97.5°	95.6	80.4	67.6	60.6
100°	122.4	103.8	93.3	89.8
102.5°	148.1	129.4	118.9	116.6
105°	172.6	155.1	146.9	142.2
107.5°	198.2	181.9	173.7	170.2
110°	225.0	209.9	202.9	198.2



TEST NUMBER: P1000085

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	250.7	236.7	228.5	223.9
115°	277.5	263.5	256.5	250.7
117.5°	303.1	290.3	283.3	278.7
120°	326.5	316.0	309.0	304.3
122.5°	350.9	339.3	332.3	328.8
125°	374.3	360.3	353.3	349.8
127.5°	396.4	381.3	371.9	367.3
130°	415.1	398.7	387.1	382.4
132.5°	432.6	415.1	402.2	396.4
135°	446.5	429.1	415.1	410.4
137.5°	461.7	443.0	429.1	423.2
140°	475.7	457.0	443.0	438.4
142.5°	488.5	469.9	457.0	453.5
145°	502.5	485.0	473.4	468.7
147.5°	516.5	500.2	488.5	485.0
150°	529.3	514.2	504.8	501.3
152.5°	541.0	528.2	518.8	517.7
155°	553.8	541.0	534.0	532.8
157.5°	564.3	552.6	546.8	545.6
160°	573.6	564.3	559.6	558.5
162.5°	581.8	574.8	570.1	571.3
165°	588.8	581.8	579.5	580.6
167.5°	594.6	590.0	587.6	588.8
170°	599.3	595.8	594.6	596.9
172.5°	602.8	599.3	600.4	601.6
175°	605.1	602.8	603.9	605.1
177.5°	606.3	603.9	605.1	607.4
180°	606.3	606.3	606.3	606.3

(END OF REPORT)