

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000249

Luminaire Tested: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000249
REPORT IS A COMBINATION OF REPORTS P988809 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6822.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	42	42	42
2	90	83	77	72	83	77	72	68	65	61	58	54	52	49	44	42	41	36	36	36
3	83	74	67	61	76	68	62	57	58	54	50	49	45	43	40	38	36	32	32	32
4	76	66	58	53	70	61	55	50	52	47	43	44	40	37	36	34	32	28	28	28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25	25	25
6	65	53	46	40	60	50	43	38	43	38	34	36	32	29	30	27	25	22	22	22
7	60	48	41	36	55	45	39	34	39	34	30	33	29	26	28	25	23	20	20	20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18	18	18
9	52	41	33	29	48	38	32	27	33	28	24	28	25	22	24	21	19	17	17	17
10	49	37	31	26	45	35	29	25	31	26	22	26	23	20	23	20	17	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29870	29870	29870	29870
5°	29939	31728	30044	25346
10°	29610	33534	29820	20930
15°	28968	33545	29458	15724
20°	28195	27728	28808	12973
25°	27259	17326	27846	11036
30°	26061	11093	26769	9500
35°	24605	8525	25403	8130
40°	22984	7166	23965	7111
45°	21250	6099	22139	5971
50°	19473	5183	20384	5164
55°	17507	4504	18450	4445
60°	15758	3434	16592	3393
65°	14124	2584	14963	2932
70°	12325	2065	13291	2390
75°	10416	1581	11373	1807
80°	8271	1074	8902	1186
85°	5749	555	6300	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27324 cd/sqm

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	2.6
10°-20°	499.6	7.3
20°-30°	643.0	9.4
30°-40°	610.0	8.9
40°-50°	522.8	7.7
50°-60°	398.1	5.8
60°-70°	251.1	3.7
70°-80°	125.3	1.8
80°-90°	35.5	0.5
90°-100°	199.1	2.9
100°-110°	701.3	10.3
110°-120°	736.6	10.8
120°-130°	606.0	8.9
130°-140°	486.8	7.1
140°-150°	367.7	5.4
150°-160°	258.5	3.8
160°-170°	152.2	2.2
170°-180°	49.5	0.7
0°-30°	1321.6	19.4
0°-40°	1931.6	28.3
0°-60°	2852.5	41.8
0°-90°	3264.3	47.8
90°-120°	1637.0	24.0
90°-150°	3097.5	45.4
90°-180°	3558.0	52.2
0°-180°	6822.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1887	1887	1887	1887	1887	
5°	1888	2100	1895	1677	1888	179
15°	1780	2370	1810	1111	1780	501
25°	1579	1264	1613	805	1579	725
35°	1296	623	1338	594	1296	811
45°	973	433	1014	424	973	751
55°	657	300	692	296	657	592
65°	397	156	421	177	397	394
75°	186	83	203	94	186	202
85°	41	24	45	25	41	46
90°	1	32	1	32	1	5
95°	34	112	34	112	34	36
105°	120	1107	120	1107	120	127
115°	211	1457	211	1457	211	209
125°	295	1182	295	1182	295	262
135°	346	980	346	980	346	267
145°	395	782	395	782	395	248
155°	449	657	449	657	449	207
165°	489	577	489	577	489	138
175°	510	520	510	520	510	48
180°	511	511	511	511	511	

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1898.8	1906.7	1910.6	1915.9	1927.7	1935.5	1947.3	1950.0	1948.7	1953.9	1939.5
5°	1888.3	1905.4	1921.1	1934.2	1955.2	1968.3	1982.7	1999.8	2003.7	2023.4	2011.6
7.5°	1873.9	1898.8	1921.1	1947.3	1978.8	1995.9	2018.2	2044.4	2056.2	2079.8	2086.3
10°	1850.3	1885.7	1923.7	1951.3	1994.5	2024.7	2045.7	2087.7	2115.2	2150.6	2145.4
12.5°	1812.3	1858.2	1909.3	1955.2	2011.6	2031.3	2070.6	2113.9	2149.3	2182.1	2210.9
15°	1779.5	1831.9	1888.3	1944.7	2009.0	2045.7	2085.0	2141.4	2179.4	2237.1	2262.1
17.5°	1734.9	1801.8	1868.7	1931.6	2007.7	2049.6	2098.1	2153.2	2209.6	2264.7	2284.4
20°	1689.0	1761.1	1833.3	1918.5	2005.0	2045.7	2095.5	2163.7	2218.8	2262.1	2262.1
22.5°	1633.9	1721.8	1804.4	1885.7	1980.1	2039.1	2090.3	2170.3	2209.6	2218.8	2183.4
25°	1578.9	1666.7	1757.2	1858.2	1965.7	2018.2	2075.9	2150.6	2163.7	2127.0	2035.2
27.5°	1513.3	1611.6	1713.9	1822.8	1935.5	2001.1	2053.6	2103.4	2078.5	1980.1	1837.2
30°	1446.4	1552.6	1668.0	1771.6	1908.0	1968.3	2012.9	2027.3	1948.7	1788.7	1603.8
32.5°	1376.9	1480.5	1602.5	1727.0	1864.7	1922.4	1951.3	1913.2	1769.0	1567.1	1341.5
35°	1295.6	1412.3	1539.5	1669.3	1805.7	1849.0	1866.0	1772.9	1588.0	1327.1	1102.8
37.5°	1222.2	1338.9	1475.3	1607.7	1740.1	1763.8	1746.7	1601.1	1366.4	1108.1	889.1
40°	1135.6	1260.2	1394.0	1542.1	1651.0	1657.5	1615.6	1426.7	1135.6	893.0	758.0
42.5°	1055.6	1181.5	1315.3	1466.1	1548.7	1526.4	1470.0	1222.2	948.1	769.8	660.9
45°	973.0	1092.3	1236.6	1370.3	1429.4	1376.9	1291.7	1028.1	796.0	662.2	578.3
47.5°	893.0	1004.5	1147.4	1275.9	1286.4	1227.4	1126.4	861.5	689.8	582.2	514.0
50°	814.3	925.8	1059.6	1165.8	1155.3	1074.0	959.9	748.8	599.3	514.0	457.7
52.5°	735.7	836.6	966.5	1050.4	1005.8	927.1	814.3	634.7	523.2	448.5	405.2
55°	657.0	751.4	862.9	932.4	861.5	771.1	691.1	544.2	453.7	393.4	360.6
57.5°	591.4	666.2	768.4	810.4	725.2	654.4	584.9	468.1	393.4	350.1	312.1
60°	519.3	587.5	671.4	696.3	608.5	550.8	491.8	396.0	337.0	299.0	274.1
62.5°	457.7	514.0	578.3	578.3	500.9	457.7	413.1	331.8	283.2	253.1	241.3
65°	397.3	438.0	483.9	478.6	413.1	375.0	339.6	274.1	237.4	216.4	204.6
67.5°	338.3	369.8	400.0	381.6	334.4	301.6	268.8	221.6	196.7	182.3	166.5
70°	284.6	309.5	325.2	308.2	261.0	233.4	209.8	178.3	158.7	140.3	131.1
72.5°	238.7	249.2	254.4	233.4	194.1	178.3	161.3	139.0	122.0	112.8	110.2
75°	186.2	195.4	191.5	175.7	142.9	131.1	118.0	102.3	98.4	93.1	90.5
77.5°	145.6	145.6	139.0	124.6	102.3	93.1	87.9	80.0	76.1	74.7	72.1
80°	103.6	102.3	98.4	82.6	69.5	64.3	64.3	59.0	57.7	55.1	55.1
82.5°	68.2	68.2	62.9	49.8	45.9	44.6	43.3	40.7	40.7	39.3	39.3
85°	40.7	38.0	31.5	27.5	26.2	26.2	24.9	23.6	24.9	23.6	23.6
87.5°	18.4	14.4	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
90°	1.0	3.9	7.9	9.8	11.8	13.2	14.7	19.6	26.5	32.4	33.4
92.5°	14.7	20.6	28.5	33.4	41.3	46.7	52.1	78.6	115.9	149.3	151.3
95°	34.4	38.3	48.1	57.0	72.7	84.5	96.3	141.5	226.9	340.9	385.1
97.5°	51.1	57.0	67.8	80.6	98.2	111.5	124.8	182.7	301.6	485.3	627.8
100°	75.6	78.6	87.4	103.2	122.8	136.6	150.3	202.4	322.2	534.4	776.1
102.5°	98.2	100.2	109.1	124.8	145.4	159.2	172.9	220.1	323.2	515.8	781.0
105°	119.9	123.8	130.7	145.4	167.0	180.8	194.5	240.7	328.1	490.2	728.0
107.5°	143.4	146.4	153.3	167.0	188.6	202.4	216.1	261.3	338.9	476.5	678.9
110°	167.0	170.9	176.8	189.6	210.2	224.4	238.7	282.0	352.7	472.6	645.5

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.6	192.6	199.4	211.2	230.9	245.6	260.3	301.6	367.4	473.5	623.9
115°	211.2	216.1	222.0	233.8	253.5	266.8	280.0	322.2	382.2	477.5	609.1
117.5°	234.8	238.7	244.6	255.4	274.1	287.8	301.6	340.9	397.9	483.4	601.3
120°	256.4	260.3	266.2	275.1	294.7	308.4	322.2	360.6	413.6	489.3	594.4
122.5°	277.0	280.0	285.9	295.7	315.4	329.6	343.9	379.2	427.4	496.1	590.4
125°	294.7	297.7	303.6	315.4	335.0	348.8	362.5	397.9	442.1	503.0	585.5
127.5°	309.5	313.4	321.3	334.0	352.7	367.0	381.2	415.6	455.9	509.9	582.6
130°	322.2	326.2	336.0	349.7	369.4	383.2	396.9	431.3	468.6	517.7	580.6
132.5°	334.0	338.9	349.7	364.5	385.1	398.8	412.6	445.0	481.4	525.6	579.6
135°	345.8	349.7	361.5	376.3	398.9	412.6	426.4	457.8	492.2	531.5	578.7
137.5°	356.6	361.5	373.3	389.0	411.6	424.4	437.2	468.6	501.0	537.4	578.7
140°	369.4	373.3	385.1	400.8	422.5	435.2	448.0	477.5	507.9	541.3	577.7
142.5°	382.2	385.1	395.9	411.6	432.3	444.1	455.9	484.3	513.8	544.3	577.7
145°	394.9	398.9	408.7	423.4	443.1	453.9	464.7	491.2	518.7	546.2	575.7
147.5°	408.7	411.6	421.5	435.2	451.9	461.8	471.6	497.1	521.7	547.2	572.8
150°	422.5	425.4	433.3	446.0	460.8	469.6	478.5	501.0	523.6	546.2	569.8
152.5°	436.2	437.2	445.0	455.9	469.6	477.4	485.3	505.0	524.6	544.3	564.9
155°	449.0	450.0	455.9	466.7	477.5	484.8	492.2	508.9	525.6	542.3	559.0
157.5°	459.8	460.8	465.7	475.5	484.3	490.7	497.1	511.9	525.6	538.4	553.1
160°	470.6	471.6	475.5	483.4	491.2	496.6	502.0	513.8	525.6	535.4	547.2
162.5°	481.4	480.4	484.3	490.2	497.1	501.0	505.0	514.8	524.6	532.5	542.3
165°	489.3	488.3	490.2	496.1	501.0	504.0	506.9	515.8	522.7	528.6	535.4
167.5°	496.1	495.2	497.1	501.0	505.0	507.0	508.9	515.8	521.7	524.6	529.5
170°	503.0	501.0	502.0	505.0	506.9	508.4	509.9	514.8	519.7	521.7	524.6
172.5°	506.9	506.0	505.0	507.9	508.9	509.9	510.9	513.8	516.8	517.7	518.7
175°	509.9	508.9	507.9	509.9	509.9	510.4	510.9	512.8	514.8	513.8	514.8
177.5°	511.9	509.9	508.9	510.9	510.9	510.9	510.9	511.9	513.8	511.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1953.9	1956.5	1960.5	1978.8	1981.4	1986.7	1984.1	1984.1	1985.4	1982.7	1984.1
5°	2037.8	2041.8	2061.4	2083.7	2089.0	2083.7	2090.3	2099.5	2099.5	2099.5	2096.8
7.5°	2116.5	2130.9	2153.2	2186.0	2192.6	2199.1	2210.9	2203.1	2205.7	2217.5	2213.5
10°	2192.6	2213.5	2238.5	2266.0	2280.4	2289.6	2294.8	2306.6	2334.2	2302.7	2314.5
12.5°	2264.7	2294.8	2321.1	2351.2	2361.7	2373.5	2377.5	2387.9	2387.9	2386.6	2395.8
15°	2311.9	2339.4	2363.0	2382.7	2385.3	2382.7	2380.1	2381.4	2385.3	2369.6	2378.8
17.5°	2322.4	2325.0	2332.9	2325.0	2326.3	2298.8	2283.0	2279.1	2242.4	2243.7	2273.9
20°	2271.2	2226.7	2214.9	2171.6	2145.4	2074.5	2071.9	2052.2	1974.9	1998.5	1993.2
22.5°	2130.9	2054.9	1953.9	1904.1	1879.1	1804.4	1746.7	1706.1	1678.5	1651.0	1639.2
25°	1946.0	1822.8	1679.8	1581.5	1567.1	1497.5	1391.3	1341.5	1282.5	1264.1	1295.6
27.5°	1707.4	1547.4	1386.1	1235.3	1207.7	1144.8	1091.0	1055.6	987.4	983.5	986.1
30°	1383.5	1222.2	1087.1	988.7	920.6	891.7	856.3	830.1	802.5	813.0	815.7
32.5°	1136.9	983.5	857.6	805.2	773.7	755.3	725.2	708.1	696.3	692.4	691.1
35°	903.5	801.2	744.8	693.7	675.3	662.2	639.9	632.1	621.6	622.9	622.9
37.5°	773.7	688.5	646.5	620.3	603.2	596.7	582.2	574.4	567.8	565.2	569.1
40°	667.5	608.5	582.2	558.6	544.2	541.6	533.7	524.5	516.7	518.0	521.9
42.5°	590.1	556.0	524.5	506.2	495.7	491.8	485.2	478.6	478.6	474.7	473.4
45°	528.5	500.9	474.7	457.7	451.1	445.9	438.0	436.7	431.4	432.7	434.1
47.5°	473.4	451.1	431.4	414.4	407.8	406.5	398.6	393.4	393.4	392.1	390.8
50°	423.6	401.3	384.2	375.0	365.9	363.2	361.9	360.6	358.0	358.0	359.3
52.5°	382.9	360.6	347.5	339.6	334.4	331.8	331.8	330.5	330.5	330.5	329.1
55°	338.3	320.0	309.5	306.9	304.2	302.9	301.6	299.0	297.7	300.3	297.7
57.5°	296.4	289.8	280.6	278.0	271.4	271.4	267.5	264.9	262.3	264.9	264.9
60°	263.6	254.4	249.2	241.3	236.0	230.8	224.2	222.9	220.3	219.0	217.7
62.5°	229.5	221.6	208.5	196.7	188.8	183.6	181.0	179.7	179.7	178.3	178.3
65°	191.5	173.1	166.5	162.6	161.3	160.0	157.4	156.0	157.4	156.0	157.4
67.5°	149.5	146.9	142.9	140.3	139.0	137.7	137.7	136.4	136.4	136.4	136.4
70°	129.8	123.3	122.0	119.3	119.3	118.0	118.0	118.0	118.0	116.7	119.3
72.5°	107.5	103.6	102.3	101.0	101.0	101.0	99.7	99.7	99.7	98.4	99.7
75°	87.9	86.5	83.9	83.9	82.6	83.9	82.6	82.6	81.3	82.6	82.6
77.5°	70.8	69.5	68.2	68.2	66.9	66.9	66.9	66.9	66.9	66.9	68.2
80°	53.8	52.5	51.1	52.5	51.1	52.5	51.1	51.1	52.5	51.1	51.1
82.5°	39.3	38.0	38.0	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7
85°	23.6	22.3	22.3	23.6	22.3	23.6	22.3	22.3	22.3	23.6	23.6
87.5°	10.5	11.8	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	11.8
90°	32.4	31.4	29.5	31.4	31.9	32.4	32.4	32.4	32.4	32.4	32.4
92.5°	126.7	99.2	84.5	73.7	69.8	65.8	64.8	60.9	61.9	59.9	61.9
95°	337.0	257.4	197.5	156.2	145.4	134.6	121.8	114.0	111.0	112.0	111.0
97.5°	632.7	526.6	420.5	321.3	291.8	262.3	224.0	204.3	193.5	187.6	193.5
100°	917.6	897.0	775.1	640.6	581.2	521.7	440.1	397.9	369.4	351.7	369.4
102.5°	1023.7	1139.6	1135.7	1046.3	982.4	918.6	828.2	748.6	711.3	685.7	711.3
105°	989.3	1193.7	1304.7	1317.5	1301.2	1285.0	1224.1	1163.2	1121.0	1107.2	1121.0
107.5°	916.6	1135.7	1300.8	1397.0	1416.6	1436.3	1435.4	1426.5	1413.7	1391.1	1413.7
110°	848.8	1056.1	1232.0	1357.7	1398.0	1438.3	1480.5	1499.2	1508.1	1507.1	1508.1

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	801.7	983.4	1150.4	1287.0	1334.6	1382.3	1445.2	1479.6	1498.2	1505.1	1498.2
115°	764.3	926.4	1077.7	1206.4	1257.0	1307.6	1377.4	1422.6	1448.1	1457.0	1448.1
117.5°	738.8	879.3	1014.9	1134.7	1182.8	1231.0	1302.7	1350.9	1377.4	1384.3	1377.4
120°	719.1	845.9	967.7	1071.8	1116.5	1161.2	1230.0	1276.2	1304.7	1314.5	1304.7
122.5°	702.4	819.4	928.4	1025.7	1065.0	1104.3	1164.2	1209.4	1233.9	1241.8	1233.9
125°	686.7	793.8	895.0	981.5	1018.3	1055.1	1112.1	1149.5	1174.0	1181.9	1174.0
127.5°	672.0	768.3	861.6	944.1	978.5	1012.9	1063.0	1098.4	1120.0	1125.9	1120.0
130°	657.3	743.7	828.2	905.8	938.2	970.7	1018.8	1052.2	1071.8	1079.7	1071.8
132.5°	645.5	720.1	796.8	866.5	896.4	926.4	973.6	1007.0	1024.7	1031.6	1024.7
135°	634.7	698.5	763.4	828.2	855.7	883.2	925.5	957.9	975.6	979.5	975.6
137.5°	626.8	680.8	736.8	789.9	814.4	839.0	879.3	907.8	923.5	929.4	923.5
140°	619.9	664.1	711.3	756.5	778.1	799.7	831.1	856.7	871.4	877.3	871.4
142.5°	613.0	650.4	688.7	726.0	743.2	760.4	789.9	812.5	825.3	825.3	825.3
145°	607.2	637.6	670.0	700.5	714.8	729.0	752.6	769.3	779.1	782.0	779.1
147.5°	601.3	627.8	654.3	678.9	689.7	700.5	721.1	734.9	741.7	743.7	741.7
150°	593.4	617.0	638.6	659.2	668.0	676.9	691.6	703.4	709.3	710.3	709.3
152.5°	586.5	606.2	625.8	642.5	649.9	657.3	668.1	677.9	681.8	681.8	681.8
155°	577.7	596.3	612.1	626.8	632.2	637.6	648.4	655.3	659.2	657.3	659.2
157.5°	569.8	584.6	598.3	611.1	615.5	619.9	627.8	633.7	635.6	635.6	635.6
160°	561.0	573.7	584.6	595.4	598.8	602.2	609.1	614.0	615.0	615.0	615.0
162.5°	553.1	562.9	571.8	580.6	583.0	585.5	592.4	595.4	596.3	595.4	596.3
165°	544.3	552.1	559.0	565.9	567.8	569.8	573.7	577.7	577.7	576.7	577.7
167.5°	535.4	541.3	547.2	552.1	554.1	556.1	558.0	560.0	560.0	559.0	560.0
170°	528.6	533.5	536.4	540.3	541.3	542.3	543.3	546.2	545.3	543.3	545.3
172.5°	521.7	524.6	526.6	529.5	530.0	530.5	531.5	532.5	531.5	530.5	531.5
175°	515.8	518.7	519.7	520.7	521.2	521.7	521.7	522.7	521.7	519.7	521.7
177.5°	511.9	513.8	513.8	514.8	514.8	514.8	514.8	514.8	513.8	511.9	513.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1989.3	1980.1	1977.5	1980.1	1977.5	1978.8	1969.6	1935.5	1944.7	1930.3	1938.2
5°	2102.1	2094.2	2077.2	2074.5	2071.9	2069.3	2056.2	2026.0	2014.2	1994.5	1993.2
7.5°	2209.6	2209.6	2196.5	2187.3	2175.5	2166.3	2149.3	2104.7	2086.3	2062.7	2049.6
10°	2315.8	2281.7	2296.2	2287.0	2258.1	2252.9	2221.4	2195.2	2159.8	2136.2	2115.2
12.5°	2391.9	2381.4	2368.3	2360.4	2352.5	2335.5	2314.5	2247.6	2229.3	2182.1	2158.5
15°	2389.3	2382.7	2386.6	2386.6	2384.0	2380.1	2363.0	2314.5	2283.0	2237.1	2196.5
17.5°	2260.7	2277.8	2294.8	2306.6	2332.9	2344.7	2360.4	2331.6	2311.9	2272.6	2229.3
20°	2036.5	2078.5	2128.3	2138.8	2162.4	2231.9	2263.4	2288.3	2296.2	2283.0	2247.6
22.5°	1724.4	1759.8	1880.5	1877.8	1911.9	1994.5	2086.3	2161.1	2220.1	2252.9	2239.8
25°	1350.7	1400.5	1464.8	1513.3	1624.7	1748.0	1862.1	1981.4	2083.7	2174.2	2196.5
27.5°	1021.5	1087.1	1138.2	1202.5	1258.9	1404.4	1551.3	1737.5	1856.9	2028.6	2117.8
30°	826.1	856.3	907.4	937.6	965.1	1076.6	1243.1	1426.7	1636.6	1834.6	1988.0
32.5°	705.5	726.5	764.5	777.6	806.5	881.2	986.1	1154.0	1370.3	1610.3	1812.3
35°	633.4	655.7	663.5	675.3	698.9	746.2	818.3	940.2	1135.6	1370.3	1611.6
37.5°	571.7	583.5	605.8	613.7	621.6	657.0	705.5	790.7	920.6	1113.3	1380.8
40°	528.5	535.0	546.8	553.4	558.6	583.5	626.8	684.5	780.2	927.1	1173.6
42.5°	482.6	490.4	498.3	506.2	512.7	532.4	558.6	613.7	678.0	789.4	967.8
45°	438.0	443.2	452.4	457.7	466.8	482.6	506.2	544.2	601.9	672.7	817.0
47.5°	397.3	403.9	407.8	414.4	420.9	438.0	460.3	485.2	532.4	601.9	706.8
50°	360.6	368.5	373.7	375.0	380.3	396.0	414.4	441.9	472.1	525.8	617.6
52.5°	334.4	335.7	339.6	344.9	343.6	352.8	369.8	390.8	422.3	465.5	532.4
55°	304.2	308.2	310.8	312.1	312.1	320.0	329.1	348.8	373.7	409.1	465.5
57.5°	266.2	270.1	278.0	280.6	284.6	288.5	292.4	305.5	326.5	360.6	406.5
60°	226.9	229.5	237.4	242.6	245.2	255.7	261.0	271.4	283.2	308.2	351.4
62.5°	182.3	184.9	188.8	194.1	199.3	215.1	228.2	238.7	247.8	264.9	300.3
65°	158.7	160.0	162.6	163.9	165.2	171.8	183.6	198.0	215.1	228.2	249.2
67.5°	137.7	139.0	140.3	142.9	144.2	145.6	150.8	154.7	171.8	190.1	205.9
70°	118.0	120.6	122.0	122.0	123.3	125.9	128.5	133.8	139.0	148.2	167.9
72.5°	99.7	101.0	103.6	103.6	103.6	106.2	108.8	111.5	114.1	119.3	127.2
75°	82.6	85.2	85.2	85.2	86.5	86.5	89.2	91.8	94.4	98.4	101.0
77.5°	68.2	68.2	68.2	68.2	69.5	69.5	70.8	73.4	74.7	76.1	78.7
80°	51.1	52.5	52.5	52.5	53.8	53.8	53.8	56.4	57.7	57.7	60.3
82.5°	38.0	38.0	38.0	39.3	38.0	39.3	39.3	40.7	39.3	40.7	42.0
85°	23.6	23.6	23.6	24.9	24.9	24.9	24.9	24.9	24.9	24.9	26.2
87.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.1	11.8	11.8
90°	32.4	32.4	32.4	31.9	31.4	29.5	31.4	32.4	33.4	32.4	26.5
92.5°	60.9	64.8	65.8	69.8	73.7	84.5	99.2	126.7	151.3	149.3	115.9
95°	114.0	121.8	134.6	145.4	156.2	197.5	257.4	337.0	385.1	340.9	226.9
97.5°	204.3	224.0	262.3	291.8	321.3	420.5	526.6	632.7	627.8	485.3	301.6
100°	397.9	440.1	521.7	581.2	640.6	775.1	897.0	917.6	776.1	534.4	322.2
102.5°	748.6	828.2	918.6	982.4	1046.3	1135.7	1139.6	1023.7	781.0	515.8	323.2
105°	1163.2	1224.1	1285.0	1301.2	1317.5	1304.7	1193.7	989.3	728.0	490.2	328.1
107.5°	1426.5	1435.4	1436.3	1416.6	1397.0	1300.8	1135.7	916.6	678.9	476.5	338.9
110°	1499.2	1480.5	1438.3	1398.0	1357.7	1232.0	1056.1	848.8	645.5	472.6	352.7

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1479.6	1445.2	1382.3	1334.6	1287.0	1150.4	983.4	801.7	623.9	473.5	367.4
115°	1422.6	1377.4	1307.6	1257.0	1206.4	1077.7	926.4	764.3	609.1	477.5	382.2
117.5°	1350.9	1302.7	1231.0	1182.8	1134.7	1014.9	879.3	738.8	601.3	483.4	397.9
120°	1276.2	1230.0	1161.2	1116.5	1071.8	967.7	845.9	719.1	594.4	489.3	413.6
122.5°	1209.4	1164.2	1104.3	1065.0	1025.7	928.4	819.4	702.4	590.4	496.1	427.4
125°	1149.5	1112.1	1055.1	1018.3	981.5	895.0	793.8	686.7	585.5	503.0	442.1
127.5°	1098.4	1063.0	1012.9	978.5	944.1	861.6	768.3	672.0	582.6	509.9	455.9
130°	1052.2	1018.8	970.7	938.2	905.8	828.2	743.7	657.3	580.6	517.7	468.6
132.5°	1007.0	973.6	926.4	896.4	866.5	796.8	720.1	645.5	579.6	525.6	481.4
135°	957.9	925.5	883.2	855.7	828.2	763.4	698.5	634.7	578.7	531.5	492.2
137.5°	907.8	879.3	839.0	814.4	789.9	736.8	680.8	626.8	578.7	537.4	501.0
140°	856.7	831.1	799.7	778.1	756.5	711.3	664.1	619.9	577.7	541.3	507.9
142.5°	812.5	789.9	760.4	743.2	726.0	688.7	650.4	613.0	577.7	544.3	513.8
145°	769.3	752.6	729.0	714.8	700.5	670.0	637.6	607.2	575.7	546.2	518.7
147.5°	734.9	721.1	700.5	689.7	678.9	654.3	627.8	601.3	572.8	547.2	521.7
150°	703.4	691.6	676.9	668.0	659.2	638.6	617.0	593.4	569.8	546.2	523.6
152.5°	677.9	668.1	657.3	649.9	642.5	625.8	606.2	586.5	564.9	544.3	524.6
155°	655.3	648.4	637.6	632.2	626.8	612.1	596.3	577.7	559.0	542.3	525.6
157.5°	633.7	627.8	619.9	615.5	611.1	598.3	584.6	569.8	553.1	538.4	525.6
160°	614.0	609.1	602.2	598.8	595.4	584.6	573.7	561.0	547.2	535.4	525.6
162.5°	595.4	592.4	585.5	583.0	580.6	571.8	562.9	553.1	542.3	532.5	524.6
165°	577.7	573.7	569.8	567.8	565.9	559.0	552.1	544.3	535.4	528.6	522.7
167.5°	560.0	558.0	556.1	554.1	552.1	547.2	541.3	535.4	529.5	524.6	521.7
170°	546.2	543.3	542.3	541.3	540.3	536.4	533.5	528.6	524.6	521.7	519.7
172.5°	532.5	531.5	530.5	530.0	529.5	526.6	524.6	521.7	518.7	517.7	516.8
175°	522.7	521.7	521.7	521.2	520.7	519.7	518.7	515.8	514.8	513.8	514.8
177.5°	514.8	514.8	514.8	514.8	514.8	513.8	513.8	511.9	510.9	511.9	513.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1926.4	1919.8	1919.8	1915.9	1915.9	1894.9	1894.9	1901.4	1893.6	1884.4	1871.3
5°	1976.2	1961.8	1957.8	1952.6	1935.5	1909.3	1898.8	1894.9	1879.1	1859.5	1837.2
7.5°	2023.4	1999.8	1988.0	1976.2	1953.9	1917.2	1896.2	1881.8	1858.2	1828.0	1799.2
10°	2069.3	2039.1	2009.0	1994.5	1963.1	1917.2	1887.0	1863.4	1829.3	1788.7	1748.0
12.5°	2111.3	2048.3	2043.1	2014.2	1968.3	1915.9	1870.0	1835.9	1792.6	1745.4	1698.2
15°	2148.0	2083.7	2052.2	2026.0	1965.7	1900.1	1851.6	1809.6	1751.9	1698.2	1640.5
17.5°	2166.3	2096.8	2075.9	2032.6	1970.9	1885.7	1820.1	1769.0	1706.1	1641.8	1576.2
20°	2184.7	2103.4	2069.3	2039.1	1955.2	1858.2	1784.7	1725.7	1656.2	1580.2	1508.0
22.5°	2193.9	2103.4	2062.7	2020.8	1939.5	1828.0	1741.5	1672.0	1590.7	1513.3	1426.7
25°	2178.1	2095.5	2047.0	2003.7	1911.9	1791.3	1691.6	1612.9	1526.4	1438.5	1350.7
27.5°	2138.8	2077.2	2020.8	1976.2	1873.9	1744.1	1639.2	1550.0	1460.8	1362.5	1273.3
30°	2065.4	2037.8	1993.2	1943.4	1831.9	1702.1	1577.5	1485.7	1387.4	1289.0	1195.9
32.5°	1951.3	1974.9	1946.0	1902.8	1782.1	1644.4	1512.0	1418.9	1311.3	1205.1	1119.9
35°	1812.3	1896.2	1880.5	1850.3	1729.7	1582.8	1450.3	1337.6	1230.0	1122.5	1037.3
37.5°	1660.2	1787.4	1800.5	1782.1	1669.3	1519.8	1374.3	1264.1	1154.0	1045.1	958.6
40°	1451.7	1647.0	1689.0	1696.9	1606.4	1443.8	1291.7	1184.1	1075.3	969.1	864.2
42.5°	1260.2	1506.7	1559.2	1592.0	1526.4	1369.0	1215.6	1096.3	988.7	893.0	788.1
45°	1080.5	1337.6	1422.8	1464.8	1435.9	1283.8	1125.1	1013.7	915.3	827.5	726.5
47.5°	895.6	1154.0	1273.3	1340.2	1340.2	1197.3	1038.6	928.4	834.0	759.3	670.1
50°	772.4	987.4	1110.7	1198.6	1222.2	1109.4	959.9	852.4	763.2	681.9	613.7
52.5°	658.3	851.1	953.3	1045.1	1113.3	1015.0	872.0	775.0	687.1	611.1	557.3
55°	569.1	713.4	806.5	907.4	983.5	919.2	786.8	692.4	616.3	553.4	507.5
57.5°	483.9	609.8	685.8	775.0	856.3	807.8	701.6	620.3	553.4	498.3	457.7
60°	411.8	514.0	573.1	642.6	743.5	709.4	621.6	546.8	493.1	443.2	409.1
62.5°	350.1	431.4	481.3	531.1	622.9	607.2	539.0	481.3	435.4	393.4	364.6
65°	287.2	354.1	393.4	436.7	510.1	516.7	461.6	420.9	379.0	342.3	316.0
67.5°	232.1	284.6	320.0	356.7	415.7	434.1	396.0	361.9	326.5	296.4	272.8
70°	187.5	224.2	250.5	279.3	327.8	350.1	330.5	306.9	278.0	253.1	232.1
72.5°	148.2	171.8	187.5	209.8	249.2	271.4	270.1	249.2	228.2	211.1	194.1
75°	108.8	127.2	140.3	154.7	186.2	207.2	212.4	203.3	182.3	169.2	156.0
77.5°	82.6	93.1	99.7	110.2	132.4	150.8	158.7	156.0	141.6	131.1	122.0
80°	62.9	65.6	68.2	72.1	90.5	107.5	112.8	111.5	103.6	99.7	89.2
82.5°	44.6	45.9	47.2	48.5	55.1	69.5	74.7	77.4	70.8	66.9	57.7
85°	26.2	27.5	27.5	30.2	31.5	35.4	44.6	44.6	43.3	38.0	36.7
87.5°	13.1	13.1	11.8	11.8	13.1	14.4	17.0	19.7	17.0	15.7	14.4
90°	19.6	14.7	13.2	11.8	9.8	7.9	3.9	1.0	3.9	7.9	9.8
92.5°	78.6	52.1	46.7	41.3	33.4	28.5	20.6	14.7	20.6	28.5	33.4
95°	141.5	96.3	84.5	72.7	57.0	48.1	38.3	34.4	38.3	48.1	57.0
97.5°	182.7	124.8	111.5	98.2	80.6	67.8	57.0	51.1	57.0	67.8	80.6
100°	202.4	150.3	136.6	122.8	103.2	87.4	78.6	75.6	78.6	87.4	103.2
102.5°	220.1	172.9	159.2	145.4	124.8	109.1	100.2	98.2	100.2	109.1	124.8
105°	240.7	194.5	180.8	167.0	145.4	130.7	123.8	119.9	123.8	130.7	145.4
107.5°	261.3	216.1	202.4	188.6	167.0	153.3	146.4	143.4	146.4	153.3	167.0
110°	282.0	238.7	224.4	210.2	189.6	176.8	170.9	167.0	170.9	176.8	189.6

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	301.6	260.3	245.6	230.9	211.2	199.4	192.6	188.6	192.6	199.4	211.2
115°	322.2	280.0	266.8	253.5	233.8	222.0	216.1	211.2	216.1	222.0	233.8
117.5°	340.9	301.6	287.8	274.1	255.4	244.6	238.7	234.8	238.7	244.6	255.4
120°	360.6	322.2	308.4	294.7	275.1	266.2	260.3	256.4	260.3	266.2	275.1
122.5°	379.2	343.9	329.6	315.4	295.7	285.9	280.0	277.0	280.0	285.9	295.7
125°	397.9	362.5	348.8	335.0	315.4	303.6	297.7	294.7	297.7	303.6	315.4
127.5°	415.6	381.2	367.0	352.7	334.0	321.3	313.4	309.5	313.4	321.3	334.0
130°	431.3	396.9	383.2	369.4	349.7	336.0	326.2	322.2	326.2	336.0	349.7
132.5°	445.0	412.6	398.8	385.1	364.5	349.7	338.9	334.0	338.9	349.7	364.5
135°	457.8	426.4	412.6	398.9	376.3	361.5	349.7	345.8	349.7	361.5	376.3
137.5°	468.6	437.2	424.4	411.6	389.0	373.3	361.5	356.6	361.5	373.3	389.0
140°	477.5	448.0	435.2	422.5	400.8	385.1	373.3	369.4	373.3	385.1	400.8
142.5°	484.3	455.9	444.1	432.3	411.6	395.9	385.1	382.2	385.1	395.9	411.6
145°	491.2	464.7	453.9	443.1	423.4	408.7	398.9	394.9	398.9	408.7	423.4
147.5°	497.1	471.6	461.8	451.9	435.2	421.5	411.6	408.7	411.6	421.5	435.2
150°	501.0	478.5	469.6	460.8	446.0	433.3	425.4	422.5	425.4	433.3	446.0
152.5°	505.0	485.3	477.4	469.6	455.9	445.0	437.2	436.2	437.2	445.0	455.9
155°	508.9	492.2	484.8	477.5	466.7	455.9	450.0	449.0	450.0	455.9	466.7
157.5°	511.9	497.1	490.7	484.3	475.5	465.7	460.8	459.8	460.8	465.7	475.5
160°	513.8	502.0	496.6	491.2	483.4	475.5	471.6	470.6	471.6	475.5	483.4
162.5°	514.8	505.0	501.0	497.1	490.2	484.3	480.4	481.4	480.4	484.3	490.2
165°	515.8	506.9	504.0	501.0	496.1	490.2	488.3	489.3	488.3	490.2	496.1
167.5°	515.8	508.9	507.0	505.0	501.0	497.1	495.2	496.1	495.2	497.1	501.0
170°	514.8	509.9	508.4	506.9	505.0	502.0	501.0	503.0	501.0	502.0	505.0
172.5°	513.8	510.9	509.9	508.9	507.9	505.0	506.0	506.9	506.0	505.0	507.9
175°	512.8	510.9	510.4	509.9	509.9	507.9	508.9	509.9	508.9	507.9	509.9
177.5°	511.9	510.9	510.9	510.9	510.9	508.9	509.9	511.9	509.9	508.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1866.0	1867.3	1871.3	1859.5	1841.1	1833.3	1809.6	1805.7	1801.8	1801.8	1805.7
5°	1824.1	1818.8	1820.1	1797.8	1771.6	1755.9	1723.1	1728.3	1711.3	1700.8	1703.4
7.5°	1778.2	1763.8	1762.4	1733.6	1700.8	1672.0	1637.9	1630.0	1614.3	1595.9	1588.0
10°	1720.5	1710.0	1690.3	1657.5	1615.6	1592.0	1546.1	1518.5	1514.6	1487.1	1476.6
12.5°	1661.5	1643.1	1623.4	1577.5	1530.3	1492.3	1458.2	1428.0	1407.1	1383.5	1367.7
15°	1593.3	1571.0	1548.7	1500.2	1445.1	1407.1	1355.9	1311.3	1249.7	1201.2	1173.6
17.5°	1518.5	1493.6	1463.5	1409.7	1355.9	1303.5	1209.1	1156.6	1113.3	1084.5	1067.4
20°	1441.2	1413.6	1383.5	1329.7	1236.6	1144.8	1092.3	1051.7	1025.5	996.6	975.6
22.5°	1359.9	1331.0	1298.2	1214.3	1115.9	1051.7	1011.0	973.0	935.0	919.2	908.8
25°	1283.8	1257.6	1215.6	1101.5	1024.2	965.1	919.2	894.3	874.7	853.7	834.0
27.5°	1205.1	1156.6	1097.6	1001.9	953.3	893.0	860.2	841.9	807.8	793.4	784.2
30°	1110.7	1056.9	1000.6	932.4	876.0	834.0	803.9	773.7	754.0	739.6	723.9
32.5°	1015.0	963.8	928.4	857.6	815.7	772.4	743.5	725.2	696.3	687.1	680.6
35°	932.4	889.1	857.6	799.9	760.6	721.2	700.3	672.7	654.4	637.3	626.8
37.5°	851.1	827.5	794.7	746.2	704.2	672.7	643.9	634.7	609.8	600.6	590.1
40°	794.7	759.3	731.7	689.8	654.4	620.3	601.9	580.9	563.9	549.5	545.5
42.5°	726.5	700.3	684.5	638.6	601.9	582.2	559.9	536.3	523.2	511.4	497.0
45°	675.3	651.7	629.4	592.7	559.9	535.0	515.4	499.6	477.3	472.1	449.8
47.5°	621.6	598.0	580.9	544.2	514.0	490.4	476.0	455.0	436.7	424.9	414.4
50°	567.8	548.1	532.4	500.9	474.7	449.8	430.1	409.1	401.3	381.6	375.0
52.5°	516.7	503.6	486.5	456.3	430.1	409.1	388.2	371.1	359.3	348.8	340.9
55°	473.4	452.4	444.5	411.8	389.5	367.2	348.8	338.3	323.9	317.3	310.8
57.5°	424.9	413.1	400.0	375.0	350.1	329.1	316.0	300.3	292.4	284.6	279.3
60°	382.9	365.9	355.4	334.4	312.1	292.4	280.6	268.8	258.3	251.8	241.3
62.5°	334.4	321.3	314.7	292.4	274.1	255.7	245.2	233.4	225.6	213.7	200.6
65°	292.4	281.9	274.1	255.7	238.7	221.6	211.1	196.7	186.2	179.7	178.3
67.5°	255.7	247.8	236.0	219.0	201.9	188.8	177.0	165.2	163.9	161.3	161.3
70°	215.1	207.2	200.6	182.3	167.9	153.4	150.8	146.9	142.9	141.6	139.0
72.5°	179.7	173.1	165.2	149.5	135.1	131.1	128.5	125.9	122.0	120.6	119.3
75°	145.6	136.4	131.1	116.7	112.8	110.2	107.5	103.6	101.0	99.7	97.0
77.5°	111.5	102.3	102.3	94.4	91.8	87.9	85.2	82.6	81.3	78.7	78.7
80°	78.7	78.7	76.1	72.1	68.2	66.9	62.9	61.6	60.3	61.6	59.0
82.5°	57.7	52.5	52.5	49.8	47.2	45.9	43.3	43.3	42.0	42.0	42.0
85°	32.8	32.8	31.5	28.8	27.5	27.5	26.2	26.2	24.9	24.9	23.6
87.5°	13.1	11.8	13.1	11.8	11.8	10.5	10.5	10.5	9.2	10.5	9.2
90°	11.8	13.2	14.7	19.6	26.5	32.4	33.4	32.4	31.4	29.5	31.4
92.5°	41.3	46.7	52.1	78.6	115.9	149.3	151.3	126.7	99.2	84.5	73.7
95°	72.7	84.5	96.3	141.5	226.9	340.9	385.1	337.0	257.4	197.5	156.2
97.5°	98.2	111.5	124.8	182.7	301.6	485.3	627.8	632.7	526.6	420.5	321.3
100°	122.8	136.6	150.3	202.4	322.2	534.4	776.1	917.6	897.0	775.1	640.6
102.5°	145.4	159.2	172.9	220.1	323.2	515.8	781.0	1023.7	1139.6	1135.7	1046.3
105°	167.0	180.8	194.5	240.7	328.1	490.2	728.0	989.3	1193.7	1304.7	1317.5
107.5°	188.6	202.4	216.1	261.3	338.9	476.5	678.9	916.6	1135.7	1300.8	1397.0
110°	210.2	224.4	238.7	282.0	352.7	472.6	645.5	848.8	1056.1	1232.0	1357.7

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.9	245.6	260.3	301.6	367.4	473.5	623.9	801.7	983.4	1150.4	1287.0
115°	253.5	266.8	280.0	322.2	382.2	477.5	609.1	764.3	926.4	1077.7	1206.4
117.5°	274.1	287.8	301.6	340.9	397.9	483.4	601.3	738.8	879.3	1014.9	1134.7
120°	294.7	308.4	322.2	360.6	413.6	489.3	594.4	719.1	845.9	967.7	1071.8
122.5°	315.4	329.6	343.9	379.2	427.4	496.1	590.4	702.4	819.4	928.4	1025.7
125°	335.0	348.8	362.5	397.9	442.1	503.0	585.5	686.7	793.8	895.0	981.5
127.5°	352.7	367.0	381.2	415.6	455.9	509.9	582.6	672.0	768.3	861.6	944.1
130°	369.4	383.2	396.9	431.3	468.6	517.7	580.6	657.3	743.7	828.2	905.8
132.5°	385.1	398.8	412.6	445.0	481.4	525.6	579.6	645.5	720.1	796.8	866.5
135°	398.9	412.6	426.4	457.8	492.2	531.5	578.7	634.7	698.5	763.4	828.2
137.5°	411.6	424.4	437.2	468.6	501.0	537.4	578.7	626.8	680.8	736.8	789.9
140°	422.5	435.2	448.0	477.5	507.9	541.3	577.7	619.9	664.1	711.3	756.5
142.5°	432.3	444.1	455.9	484.3	513.8	544.3	577.7	613.0	650.4	688.7	726.0
145°	443.1	453.9	464.7	491.2	518.7	546.2	575.7	607.2	637.6	670.0	700.5
147.5°	451.9	461.8	471.6	497.1	521.7	547.2	572.8	601.3	627.8	654.3	678.9
150°	460.8	469.6	478.5	501.0	523.6	546.2	569.8	593.4	617.0	638.6	659.2
152.5°	469.6	477.4	485.3	505.0	524.6	544.3	564.9	586.5	606.2	625.8	642.5
155°	477.5	484.8	492.2	508.9	525.6	542.3	559.0	577.7	596.3	612.1	626.8
157.5°	484.3	490.7	497.1	511.9	525.6	538.4	553.1	569.8	584.6	598.3	611.1
160°	491.2	496.6	502.0	513.8	525.6	535.4	547.2	561.0	573.7	584.6	595.4
162.5°	497.1	501.0	505.0	514.8	524.6	532.5	542.3	553.1	562.9	571.8	580.6
165°	501.0	504.0	506.9	515.8	522.7	528.6	535.4	544.3	552.1	559.0	565.9
167.5°	505.0	507.0	508.9	515.8	521.7	524.6	529.5	535.4	541.3	547.2	552.1
170°	506.9	508.4	509.9	514.8	519.7	521.7	524.6	528.6	533.5	536.4	540.3
172.5°	508.9	509.9	510.9	513.8	516.8	517.7	518.7	521.7	524.6	526.6	529.5
175°	509.9	510.4	510.9	512.8	514.8	513.8	514.8	515.8	518.7	519.7	520.7
177.5°	510.9	510.9	510.9	511.9	513.8	511.9	510.9	511.9	513.8	513.8	514.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1805.7	1803.1	1795.2	1797.8	1793.9	1793.9	1791.3	1791.3	1791.3	1797.8	1793.9
5°	1707.4	1698.2	1689.0	1685.1	1681.1	1677.2	1677.2	1675.9	1687.7	1685.1	1695.6
7.5°	1585.4	1582.8	1564.4	1564.4	1557.9	1555.2	1561.8	1563.1	1564.4	1567.1	1573.6
10°	1476.6	1470.0	1443.8	1446.4	1442.5	1437.2	1441.2	1438.5	1447.7	1450.3	1447.7
12.5°	1348.1	1336.3	1307.4	1293.0	1277.2	1265.4	1279.9	1269.4	1306.1	1316.6	1345.4
15°	1177.6	1155.3	1135.6	1135.6	1121.2	1110.7	1117.3	1129.1	1136.9	1148.7	1154.0
17.5°	1063.5	1054.3	1038.6	1029.4	1025.5	1021.5	1021.5	1026.8	1043.8	1042.5	1053.0
20°	966.5	961.2	953.3	941.5	937.6	935.0	935.0	935.0	946.8	957.3	963.8
22.5°	899.6	895.6	890.4	874.7	866.8	864.2	870.7	874.7	883.8	891.7	898.3
25°	832.7	823.5	814.3	809.1	805.2	805.2	807.8	809.1	813.0	817.0	824.8
27.5°	777.6	771.1	758.0	743.5	743.5	739.6	742.2	744.8	754.0	767.1	773.7
30°	716.0	714.7	709.4	704.2	698.9	696.3	701.6	705.5	706.8	713.4	713.4
32.5°	671.4	662.2	653.0	647.8	645.2	643.9	645.2	650.4	650.4	658.3	667.5
35°	626.8	621.6	612.4	603.2	600.6	594.0	599.3	604.5	613.7	617.6	621.6
37.5°	578.3	571.7	567.8	565.2	559.9	561.3	557.3	565.2	573.1	571.7	574.4
40°	541.6	529.8	518.0	516.7	515.4	514.0	514.0	515.4	520.6	525.8	533.7
42.5°	494.4	490.4	480.0	469.5	466.8	464.2	461.6	466.8	477.3	486.5	490.4
45°	445.9	440.6	438.0	430.1	424.9	423.6	420.9	427.5	436.7	440.6	443.2
47.5°	401.3	400.0	392.1	393.4	389.5	390.8	389.5	393.4	393.4	397.3	400.0
50°	371.1	367.2	363.2	360.6	356.7	356.7	355.4	356.7	361.9	367.2	365.9
52.5°	340.9	334.4	333.1	331.8	329.1	331.8	327.8	329.1	334.4	337.0	335.7
55°	305.5	304.2	301.6	299.0	297.7	296.4	296.4	296.4	301.6	305.5	306.9
57.5°	278.0	271.4	266.2	266.2	261.0	259.6	262.3	263.6	267.5	270.1	272.8
60°	240.0	237.4	229.5	225.6	217.7	216.4	216.4	221.6	228.2	237.4	240.0
62.5°	199.3	195.4	194.1	194.1	194.1	194.1	194.1	194.1	194.1	195.4	195.4
65°	177.0	178.3	177.0	175.7	177.0	177.0	175.7	175.7	175.7	177.0	178.3
67.5°	158.7	157.4	158.7	157.4	156.0	156.0	154.7	156.0	157.4	158.7	158.7
70°	137.7	137.7	136.4	137.7	136.4	135.1	133.8	133.8	136.4	137.7	137.7
72.5°	118.0	118.0	116.7	116.7	114.1	114.1	115.4	114.1	114.1	118.0	118.0
75°	98.4	97.0	95.7	95.7	94.4	94.4	94.4	93.1	95.7	95.7	97.0
77.5°	77.4	77.4	77.4	76.1	76.1	74.7	74.7	76.1	76.1	76.1	77.4
80°	59.0	59.0	59.0	57.7	56.4	56.4	56.4	56.4	56.4	57.7	56.4
82.5°	40.7	40.7	40.7	40.7	40.7	39.3	39.3	39.3	40.7	40.7	39.3
85°	24.9	23.6	24.9	24.9	23.6	24.9	23.6	23.6	22.3	22.3	23.6
87.5°	10.5	9.2	7.9	7.9	9.2	7.9	7.9	7.9	9.2	7.9	7.9
90°	31.9	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	31.9
92.5°	69.8	65.8	64.8	60.9	61.9	59.9	61.9	60.9	64.8	65.8	69.8
95°	145.4	134.6	121.8	114.0	111.0	112.0	111.0	114.0	121.8	134.6	145.4
97.5°	291.8	262.3	224.0	204.3	193.5	187.6	193.5	204.3	224.0	262.3	291.8
100°	581.2	521.7	440.1	397.9	369.4	351.7	369.4	397.9	440.1	521.7	581.2
102.5°	982.4	918.6	828.2	748.6	711.3	685.7	711.3	748.6	828.2	918.6	982.4
105°	1301.2	1285.0	1224.1	1163.2	1121.0	1107.2	1121.0	1163.2	1224.1	1285.0	1301.2
107.5°	1416.6	1436.3	1435.4	1426.5	1413.7	1391.1	1413.7	1426.5	1435.4	1436.3	1416.6
110°	1398.0	1438.3	1480.5	1499.2	1508.1	1507.1	1508.1	1499.2	1480.5	1438.3	1398.0

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1334.6	1382.3	1445.2	1479.6	1498.2	1505.1	1498.2	1479.6	1445.2	1382.3	1334.6
115°	1257.0	1307.6	1377.4	1422.6	1448.1	1457.0	1448.1	1422.6	1377.4	1307.6	1257.0
117.5°	1182.8	1231.0	1302.7	1350.9	1377.4	1384.3	1377.4	1350.9	1302.7	1231.0	1182.8
120°	1116.5	1161.2	1230.0	1276.2	1304.7	1314.5	1304.7	1276.2	1230.0	1161.2	1116.5
122.5°	1065.0	1104.3	1164.2	1209.4	1233.9	1241.8	1233.9	1209.4	1164.2	1104.3	1065.0
125°	1018.3	1055.1	1112.1	1149.5	1174.0	1181.9	1174.0	1149.5	1112.1	1055.1	1018.3
127.5°	978.5	1012.9	1063.0	1098.4	1120.0	1125.9	1120.0	1098.4	1063.0	1012.9	978.5
130°	938.2	970.7	1018.8	1052.2	1071.8	1079.7	1071.8	1052.2	1018.8	970.7	938.2
132.5°	896.4	926.4	973.6	1007.0	1024.7	1031.6	1024.7	1007.0	973.6	926.4	896.4
135°	855.7	883.2	925.5	957.9	975.6	979.5	975.6	957.9	925.5	883.2	855.7
137.5°	814.4	839.0	879.3	907.8	923.5	929.4	923.5	907.8	879.3	839.0	814.4
140°	778.1	799.7	831.1	856.7	871.4	877.3	871.4	856.7	831.1	799.7	778.1
142.5°	743.2	760.4	789.9	812.5	825.3	825.3	825.3	812.5	789.9	760.4	743.2
145°	714.8	729.0	752.6	769.3	779.1	782.0	779.1	769.3	752.6	729.0	714.8
147.5°	689.7	700.5	721.1	734.9	741.7	743.7	741.7	734.9	721.1	700.5	689.7
150°	668.0	676.9	691.6	703.4	709.3	710.3	709.3	703.4	691.6	676.9	668.0
152.5°	649.9	657.3	668.1	677.9	681.8	681.8	681.8	677.9	668.1	657.3	649.9
155°	632.2	637.6	648.4	655.3	659.2	657.3	659.2	655.3	648.4	637.6	632.2
157.5°	615.5	619.9	627.8	633.7	635.6	635.6	635.6	633.7	627.8	619.9	615.5
160°	598.8	602.2	609.1	614.0	615.0	615.0	615.0	614.0	609.1	602.2	598.8
162.5°	583.0	585.5	592.4	595.4	596.3	595.4	596.3	595.4	592.4	585.5	583.0
165°	567.8	569.8	573.7	577.7	577.7	576.7	577.7	577.7	573.7	569.8	567.8
167.5°	554.1	556.1	558.0	560.0	560.0	559.0	560.0	560.0	558.0	556.1	554.1
170°	541.3	542.3	543.3	546.2	545.3	543.3	545.3	546.2	543.3	542.3	541.3
172.5°	530.0	530.5	531.5	532.5	531.5	530.5	531.5	532.5	531.5	530.5	530.0
175°	521.2	521.7	521.7	522.7	521.7	519.7	521.7	522.7	521.7	521.7	521.2
177.5°	514.8	514.8	514.8	514.8	513.8	511.9	513.8	514.8	514.8	514.8	514.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1797.8	1804.4	1801.8	1787.4	1801.8	1805.7	1813.6	1821.5	1826.7	1834.6	1841.1
5°	1685.1	1698.2	1706.1	1698.2	1724.4	1728.3	1746.7	1757.2	1772.9	1786.0	1796.5
7.5°	1578.9	1589.3	1605.1	1607.7	1623.4	1641.8	1668.0	1694.3	1719.2	1732.3	1744.1
10°	1464.8	1483.1	1506.7	1501.5	1525.1	1553.9	1581.5	1623.4	1644.4	1668.0	1689.0
12.5°	1350.7	1362.5	1394.0	1404.4	1438.5	1460.8	1498.9	1525.1	1577.5	1605.1	1623.4
15°	1151.4	1199.9	1239.2	1286.4	1331.0	1373.0	1407.1	1454.3	1500.2	1521.2	1551.3
17.5°	1060.9	1083.2	1106.8	1130.4	1188.1	1262.8	1323.1	1374.3	1413.6	1441.2	1476.6
20°	966.5	988.7	1015.0	1037.3	1072.7	1126.4	1201.2	1289.0	1336.3	1365.1	1399.2
22.5°	899.6	920.6	937.6	957.3	984.8	1024.2	1080.5	1189.4	1252.3	1287.7	1317.9
25°	827.5	853.7	872.0	886.5	908.8	952.0	997.9	1059.6	1172.3	1199.9	1241.8
27.5°	777.6	785.5	806.5	828.8	851.1	874.7	921.9	974.3	1050.4	1110.7	1161.8
30°	718.6	738.3	758.0	767.1	786.8	820.9	849.7	906.1	965.1	1012.4	1074.0
32.5°	674.0	685.8	698.9	721.2	739.6	763.2	792.0	839.3	889.1	919.2	966.5
35°	624.2	632.1	659.6	668.8	687.1	710.7	739.6	776.3	830.1	853.7	887.8
37.5°	577.0	595.3	603.2	624.2	641.2	664.8	685.8	727.8	763.2	790.7	822.2
40°	540.3	548.1	562.6	580.9	595.3	613.7	639.9	670.1	708.1	730.4	758.0
42.5°	495.7	502.2	520.6	531.1	554.7	571.7	587.5	624.2	658.3	675.3	702.9
45°	447.2	462.9	474.7	495.7	508.8	529.8	549.5	575.7	607.2	626.8	642.6
47.5°	405.2	420.9	432.7	452.4	473.4	482.6	503.6	531.1	559.9	575.7	598.0
50°	371.1	376.4	398.6	407.8	430.1	448.5	462.9	486.5	518.0	527.2	545.5
52.5°	338.3	342.3	356.7	368.5	388.2	403.9	422.3	444.5	470.8	485.2	499.6
55°	309.5	312.1	318.7	331.8	344.9	364.6	381.6	402.6	424.9	440.6	453.7
57.5°	276.7	281.9	287.2	295.1	308.2	326.5	344.9	364.6	382.9	393.4	410.4
60°	238.7	246.5	255.7	264.9	274.1	287.2	308.2	326.5	343.6	352.8	365.9
62.5°	198.0	213.7	221.6	232.1	240.0	251.8	267.5	288.5	300.3	312.1	322.6
65°	178.3	179.7	181.0	191.5	205.9	217.7	232.1	247.8	266.2	274.1	281.9
67.5°	158.7	160.0	162.6	163.9	169.2	182.3	198.0	215.1	229.5	234.7	242.6
70°	139.0	139.0	144.2	145.6	146.9	148.2	161.3	178.3	191.5	198.0	207.2
72.5°	118.0	119.3	122.0	123.3	125.9	128.5	132.4	141.6	157.4	163.9	174.4
75°	97.0	98.4	99.7	101.0	104.9	106.2	110.2	115.4	122.0	129.8	136.4
77.5°	77.4	77.4	78.7	81.3	83.9	85.2	89.2	91.8	94.4	98.4	103.6
80°	57.7	59.0	59.0	61.6	61.6	62.9	64.3	68.2	70.8	73.4	76.1
82.5°	39.3	42.0	42.0	42.0	43.3	44.6	45.9	45.9	48.5	49.8	53.8
85°	23.6	24.9	24.9	24.9	23.6	26.2	26.2	27.5	27.5	27.5	28.8
87.5°	9.2	7.9	9.2	9.2	9.2	10.5	9.2	9.2	10.5	11.8	11.8
90°	31.4	29.5	31.4	32.4	33.4	32.4	26.5	19.6	14.7	13.2	11.8
92.5°	73.7	84.5	99.2	126.7	151.3	149.3	115.9	78.6	52.1	46.7	41.3
95°	156.2	197.5	257.4	337.0	385.1	340.9	226.9	141.5	96.3	84.5	72.7
97.5°	321.3	420.5	526.6	632.7	627.8	485.3	301.6	182.7	124.8	111.5	98.2
100°	640.6	775.1	897.0	917.6	776.1	534.4	322.2	202.4	150.3	136.6	122.8
102.5°	1046.3	1135.7	1139.6	1023.7	781.0	515.8	323.2	220.1	172.9	159.2	145.4
105°	1317.5	1304.7	1193.7	989.3	728.0	490.2	328.1	240.7	194.5	180.8	167.0
107.5°	1397.0	1300.8	1135.7	916.6	678.9	476.5	338.9	261.3	216.1	202.4	188.6
110°	1357.7	1232.0	1056.1	848.8	645.5	472.6	352.7	282.0	238.7	224.4	210.2

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1287.0	1150.4	983.4	801.7	623.9	473.5	367.4	301.6	260.3	245.6	230.9
115°	1206.4	1077.7	926.4	764.3	609.1	477.5	382.2	322.2	280.0	266.8	253.5
117.5°	1134.7	1014.9	879.3	738.8	601.3	483.4	397.9	340.9	301.6	287.8	274.1
120°	1071.8	967.7	845.9	719.1	594.4	489.3	413.6	360.6	322.2	308.4	294.7
122.5°	1025.7	928.4	819.4	702.4	590.4	496.1	427.4	379.2	343.9	329.6	315.4
125°	981.5	895.0	793.8	686.7	585.5	503.0	442.1	397.9	362.5	348.8	335.0
127.5°	944.1	861.6	768.3	672.0	582.6	509.9	455.9	415.6	381.2	367.0	352.7
130°	905.8	828.2	743.7	657.3	580.6	517.7	468.6	431.3	396.9	383.2	369.4
132.5°	866.5	796.8	720.1	645.5	579.6	525.6	481.4	445.0	412.6	398.8	385.1
135°	828.2	763.4	698.5	634.7	578.7	531.5	492.2	457.8	426.4	412.6	398.9
137.5°	789.9	736.8	680.8	626.8	578.7	537.4	501.0	468.6	437.2	424.4	411.6
140°	756.5	711.3	664.1	619.9	577.7	541.3	507.9	477.5	448.0	435.2	422.5
142.5°	726.0	688.7	650.4	613.0	577.7	544.3	513.8	484.3	455.9	444.1	432.3
145°	700.5	670.0	637.6	607.2	575.7	546.2	518.7	491.2	464.7	453.9	443.1
147.5°	678.9	654.3	627.8	601.3	572.8	547.2	521.7	497.1	471.6	461.8	451.9
150°	659.2	638.6	617.0	593.4	569.8	546.2	523.6	501.0	478.5	469.6	460.8
152.5°	642.5	625.8	606.2	586.5	564.9	544.3	524.6	505.0	485.3	477.4	469.6
155°	626.8	612.1	596.3	577.7	559.0	542.3	525.6	508.9	492.2	484.8	477.5
157.5°	611.1	598.3	584.6	569.8	553.1	538.4	525.6	511.9	497.1	490.7	484.3
160°	595.4	584.6	573.7	561.0	547.2	535.4	525.6	513.8	502.0	496.6	491.2
162.5°	580.6	571.8	562.9	553.1	542.3	532.5	524.6	514.8	505.0	501.0	497.1
165°	565.9	559.0	552.1	544.3	535.4	528.6	522.7	515.8	506.9	504.0	501.0
167.5°	552.1	547.2	541.3	535.4	529.5	524.6	521.7	515.8	508.9	507.0	505.0
170°	540.3	536.4	533.5	528.6	524.6	521.7	519.7	514.8	509.9	508.4	506.9
172.5°	529.5	526.6	524.6	521.7	518.7	517.7	516.8	513.8	510.9	509.9	508.9
175°	520.7	519.7	518.7	515.8	514.8	513.8	514.8	512.8	510.9	510.4	509.9
177.5°	514.8	513.8	513.8	511.9	510.9	511.9	513.8	511.9	510.9	510.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1887.0	1887.0	1887.0	1887.0
2.5°	1852.9	1849.0	1872.6	1898.8
5°	1814.9	1821.5	1851.6	1888.3
7.5°	1775.6	1790.0	1825.4	1873.9
10°	1720.5	1746.7	1800.5	1850.3
12.5°	1666.7	1702.1	1753.3	1812.3
15°	1606.4	1645.7	1708.7	1779.5
17.5°	1539.5	1584.1	1657.5	1734.9
20°	1468.7	1527.7	1605.1	1689.0
22.5°	1390.0	1460.8	1540.8	1633.9
25°	1314.0	1391.3	1471.3	1578.9
27.5°	1239.2	1315.3	1404.4	1513.3
30°	1164.5	1234.0	1329.7	1446.4
32.5°	1084.5	1156.6	1257.6	1376.9
35°	1011.0	1083.2	1177.6	1295.6
37.5°	932.4	1009.7	1100.2	1222.2
40°	840.6	931.1	1018.9	1135.6
42.5°	764.5	860.2	945.5	1055.6
45°	704.2	794.7	865.5	973.0
47.5°	647.8	721.2	793.4	893.0
50°	594.0	650.4	725.2	814.3
52.5°	539.0	587.5	651.7	735.7
55°	489.1	535.0	592.7	657.0
57.5°	443.2	476.0	533.7	591.4
60°	392.1	426.2	470.8	519.3
62.5°	348.8	375.0	417.0	457.7
65°	302.9	327.8	359.3	397.3
67.5°	261.0	283.2	308.2	338.3
70°	222.9	240.0	258.3	284.6
72.5°	182.3	200.6	217.7	238.7
75°	149.5	157.4	171.8	186.2
77.5°	115.4	125.9	133.8	145.6
80°	82.6	91.8	94.4	103.6
82.5°	55.1	60.3	65.6	68.2
85°	31.5	34.1	39.3	40.7
87.5°	11.8	13.1	15.7	18.4
90°	9.8	7.9	3.9	1.0
92.5°	33.4	28.5	20.6	14.7
95°	57.0	48.1	38.3	34.4
97.5°	80.6	67.8	57.0	51.1
100°	103.2	87.4	78.6	75.6
102.5°	124.8	109.1	100.2	98.2
105°	145.4	130.7	123.8	119.9
107.5°	167.0	153.3	146.4	143.4
110°	189.6	176.8	170.9	167.0

TEST NUMBER: P1000249

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	211.2	199.4	192.6	188.6
115°	233.8	222.0	216.1	211.2
117.5°	255.4	244.6	238.7	234.8
120°	275.1	266.2	260.3	256.4
122.5°	295.7	285.9	280.0	277.0
125°	315.4	303.6	297.7	294.7
127.5°	334.0	321.3	313.4	309.5
130°	349.7	336.0	326.2	322.2
132.5°	364.5	349.7	338.9	334.0
135°	376.3	361.5	349.7	345.8
137.5°	389.0	373.3	361.5	356.6
140°	400.8	385.1	373.3	369.4
142.5°	411.6	395.9	385.1	382.2
145°	423.4	408.7	398.9	394.9
147.5°	435.2	421.5	411.6	408.7
150°	446.0	433.3	425.4	422.5
152.5°	455.9	445.0	437.2	436.2
155°	466.7	455.9	450.0	449.0
157.5°	475.5	465.7	460.8	459.8
160°	483.4	475.5	471.6	470.6
162.5°	490.2	484.3	480.4	481.4
165°	496.1	490.2	488.3	489.3
167.5°	501.0	497.1	495.2	496.1
170°	505.0	502.0	501.0	503.0
172.5°	507.9	505.0	506.0	506.9
175°	509.9	507.9	508.9	509.9
177.5°	510.9	508.9	509.9	511.9
180°	510.9	510.9	510.9	510.9

(END OF REPORT)