

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001175

Luminaire Tested: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001175
REPORT IS A COMBINATION OF REPORTS P995791 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6306.0 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20
4	70	60	52	47	62	53	47	42	42	37	34	31	28	25	20	19	17
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4509	4509	4509	4509
5°	4498	5174	4524	3887
10°	4465	6036	4499	3411
15°	4411	6958	4441	3051
20°	4354	7545	4385	2736
25°	4271	7459	4311	2503
30°	4189	6165	4240	2383
35°	4075	4594	4120	2310
40°	3941	3461	3980	2274
45°	3738	2777	3784	2226
50°	3494	2340	3544	2203
55°	3208	2037	3257	2178
60°	2929	1794	3015	2141
65°	2668	1544	2694	2052
70°	2360	1270	2412	1889
75°	2060	976	2046	1606
80°	1620	641	1600	1220
85°	1070	287	997	711

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5831 cd/sqm

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.8	0.9
10°-20°	166.1	2.6
20°-30°	263.9	4.2
30°-40°	293.2	4.7
40°-50°	266.7	4.2
50°-60°	217.9	3.5
60°-70°	155.6	2.5
70°-80°	85.6	1.4
80°-90°	26.3	0.4
90°-100°	51.2	0.8
100°-110°	337.5	5.4
110°-120°	644.4	10.2
120°-130°	818.1	13.0
130°-140°	875.1	13.9
140°-150°	818.3	13.0
150°-160°	659.9	10.5
160°-170°	425.6	6.7
170°-180°	146.7	2.3
0°-30°	483.9	7.7
0°-40°	777.1	12.3
0°-60°	1261.7	20.0
0°-90°	1529.2	24.2
90°-120°	1033.1	16.4
90°-150°	3544.6	56.2
90°-180°	4777.0	75.8
0°-180°	6306.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	553	553	553	553	553	
5°	551	649	554	488	551	52
15°	526	891	530	391	526	148
25°	480	946	485	318	480	221
35°	416	559	421	281	416	260
45°	332	314	336	252	332	256
55°	234	205	237	220	234	210
65°	146	132	147	176	146	144
75°	72	66	71	109	72	75
85°	15	14	14	34	15	17
90°	4	35	4	35	4	4
95°	64	34	64	34	64	78
105°	348	329	348	329	348	364
115°	649	654	649	654	649	639
125°	912	919	912	919	912	815
135°	1132	1140	1132	1140	1132	872
145°	1305	1312	1305	1312	1305	815
155°	1431	1429	1431	1429	1431	660
165°	1509	1502	1509	1502	1509	426
175°	1544	1534	1544	1534	1544	147
180°	1544	1544	1544	1544	1544	

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	553.0	558.5	560.8	562.6	568.6	570.4	570.9	573.6	575.9	576.4	576.4
5°	550.7	559.4	566.3	572.7	582.3	586.5	591.5	597.0	604.3	608.9	611.2
7.5°	547.1	559.9	570.4	581.4	594.7	603.0	607.5	622.2	632.3	640.5	650.6
10°	541.6	558.1	573.2	589.2	608.0	618.1	628.2	646.0	660.2	676.3	689.1
12.5°	533.3	554.8	573.2	595.6	619.0	630.9	642.8	674.0	690.5	704.7	727.6
15°	526.0	547.5	573.6	596.5	625.4	643.3	660.7	680.8	707.0	737.7	759.6
17.5°	517.7	544.8	569.0	601.1	633.2	650.1	664.3	695.5	732.2	762.4	782.6
20°	506.3	533.8	565.8	599.7	637.8	651.1	669.8	711.5	744.5	774.3	807.3
22.5°	493.0	525.1	559.0	591.5	630.9	658.9	679.5	716.1	756.0	790.3	827.5
25°	480.2	515.0	544.8	589.2	630.9	649.7	673.1	716.6	760.1	801.8	839.8
27.5°	466.4	498.9	539.3	574.5	621.7	642.4	667.6	715.2	761.5	803.2	844.0
30°	451.3	486.1	519.6	561.3	607.1	633.7	657.0	708.8	756.0	799.5	837.5
32.5°	434.3	467.3	503.1	542.5	590.6	617.6	646.9	700.1	750.5	788.1	817.4
35°	416.5	449.9	481.1	521.4	570.9	597.9	626.3	685.0	734.9	765.6	782.6
37.5°	396.8	428.4	459.1	498.9	548.4	577.3	606.2	663.0	710.2	735.8	731.2
40°	378.0	406.4	434.8	472.4	524.1	554.8	580.0	637.3	678.6	689.5	674.4
42.5°	356.5	380.7	408.2	446.7	497.1	526.0	557.6	609.8	640.5	635.9	610.3
45°	332.2	353.7	381.2	417.4	468.7	498.5	525.1	574.5	597.0	585.5	538.8
47.5°	308.8	329.9	352.3	388.5	438.5	463.7	490.7	535.1	548.0	523.7	477.0
50°	283.6	301.0	324.4	358.7	405.5	432.1	454.5	490.2	494.8	465.0	416.5
52.5°	259.3	274.0	296.4	330.3	373.9	394.9	416.9	448.6	444.9	414.2	367.5
55°	233.7	247.4	268.0	299.2	337.7	357.8	376.6	404.6	396.8	365.2	324.4
57.5°	212.1	221.8	241.9	270.8	302.4	324.4	340.4	362.4	350.5	318.9	280.9
60°	187.4	199.3	216.3	239.6	270.8	285.4	299.6	314.3	306.1	275.8	241.9
62.5°	164.9	174.1	188.8	211.2	235.5	248.8	263.9	273.1	264.8	236.9	208.5
65°	145.7	153.0	164.5	182.8	206.2	217.2	225.9	234.6	227.7	201.6	181.0
67.5°	124.6	131.0	140.7	155.3	175.0	182.8	191.1	197.0	189.2	171.8	151.7
70°	105.8	110.4	119.6	130.6	144.3	151.7	158.5	164.5	157.6	142.9	127.8
72.5°	86.6	90.3	98.5	106.3	118.7	123.7	128.7	133.3	131.0	117.3	104.9
75°	71.5	72.8	78.3	84.8	92.6	98.0	101.7	104.5	102.6	91.6	83.8
77.5°	54.1	55.9	60.0	65.1	71.9	75.1	77.4	80.2	77.9	69.2	63.7
80°	39.4	39.9	42.2	46.7	51.3	51.8	54.1	57.7	56.4	50.4	46.3
82.5°	25.2	26.6	27.5	30.2	33.4	34.4	35.7	36.7	36.2	32.5	31.2
85°	14.7	14.7	15.6	17.4	18.3	19.7	20.2	20.6	21.5	19.2	17.9
87.5°	6.4	6.9	6.9	7.3	8.2	8.2	8.7	9.2	9.6	9.2	7.8
90°	3.5	6.3	9.1	12.0	14.8	16.2	17.2	19.3	21.3	23.4	25.4
92.5°	17.3	16.8	16.3	15.8	15.3	15.0	16.0	18.1	20.1	22.2	24.2
95°	63.5	54.8	46.0	37.3	28.6	24.2	24.3	24.6	24.9	25.1	25.4
97.5°	121.2	126.8	132.5	138.1	143.8	146.6	133.1	106.2	79.3	52.3	25.4
100°	189.4	194.0	198.6	203.2	207.8	210.1	192.4	157.0	121.6	86.2	50.8
102.5°	265.6	268.7	271.7	274.8	277.9	279.4	280.9	284.0	287.1	290.2	293.3
105°	347.5	349.1	350.6	352.2	353.7	354.5	355.1	356.4	357.7	358.9	360.2
107.5°	422.6	423.4	424.2	424.9	425.7	426.1	427.0	428.8	430.5	432.3	434.1
110°	498.8	499.6	500.4	501.1	501.9	502.3	503.1	504.6	506.1	507.7	509.2

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	572.7	574.2	575.8	577.3	578.8	579.6	579.9	580.4	580.9	581.4	581.9
115°	648.9	649.7	650.5	651.2	652.0	652.4	652.3	652.0	651.7	651.5	651.2
117.5°	717.0	718.0	719.0	720.1	721.1	721.6	722.0	722.8	723.5	724.3	725.1
120°	786.3	787.3	788.3	789.4	790.4	790.9	790.8	790.5	790.3	790.0	789.8
122.5°	851.0	851.5	852.0	852.5	853.0	853.3	853.6	854.1	854.6	855.1	855.6
125°	912.1	913.1	914.2	915.2	916.3	916.8	916.5	916.0	915.5	915.0	914.5
127.5°	971.0	971.3	971.5	971.8	972.1	972.2	972.8	974.1	975.4	976.7	978.0
130°	1027.6	1027.9	1028.1	1028.4	1028.7	1028.8	1029.2	1029.9	1030.7	1031.4	1032.2
132.5°	1079.6	1080.1	1080.6	1081.1	1081.6	1081.9	1082.4	1083.4	1084.5	1085.5	1086.5
135°	1131.5	1131.3	1131.0	1130.8	1130.5	1130.4	1130.9	1131.9	1133.0	1134.0	1135.0
137.5°	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1178.3	1179.6	1180.9	1182.2	1183.5
140°	1222.7	1223.2	1223.7	1224.2	1224.7	1225.0	1225.3	1225.8	1226.3	1226.9	1227.4
142.5°	1263.1	1264.1	1265.2	1266.2	1267.3	1267.8	1267.9	1268.2	1268.4	1268.7	1268.9
145°	1304.7	1305.5	1306.3	1307.0	1307.8	1308.2	1308.2	1308.2	1308.2	1308.2	1308.2
147.5°	1337.0	1338.6	1340.1	1341.7	1343.2	1344.0	1343.9	1343.6	1343.3	1343.1	1342.8
150°	1372.8	1373.8	1374.9	1375.9	1377.0	1377.5	1377.4	1377.1	1376.8	1376.6	1376.3
152.5°	1402.9	1403.7	1404.4	1405.2	1405.9	1406.3	1406.0	1405.5	1405.0	1404.5	1404.0
155°	1430.6	1430.8	1431.1	1431.3	1431.6	1431.7	1431.3	1430.6	1429.8	1429.1	1428.3
157.5°	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.3	1453.3	1452.2	1451.2	1450.2
160°	1475.6	1474.8	1474.0	1473.3	1472.5	1472.1	1472.0	1471.7	1471.5	1471.2	1471.0
162.5°	1494.1	1493.1	1492.1	1491.0	1490.0	1489.5	1489.4	1489.1	1488.8	1488.6	1488.3
165°	1509.1	1507.8	1506.5	1505.2	1503.9	1503.3	1503.3	1503.3	1503.3	1503.3	1503.3
167.5°	1521.8	1520.5	1519.2	1517.9	1516.6	1516.0	1515.9	1515.6	1515.4	1515.1	1514.9
170°	1532.2	1530.6	1529.1	1527.5	1526.0	1525.2	1525.3	1525.6	1525.9	1526.1	1526.4
172.5°	1539.1	1537.6	1536.0	1534.5	1533.0	1532.2	1532.3	1532.6	1532.8	1533.1	1533.3
175°	1543.7	1542.2	1540.6	1539.1	1537.6	1536.8	1536.9	1537.2	1537.4	1537.7	1537.9
177.5°	1547.2	1545.4	1543.6	1541.8	1540.0	1539.1	1539.4	1539.9	1540.4	1540.9	1541.4
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	577.8	586.0	589.7	590.6	595.6	592.4	593.8	593.3	597.0	597.5	597.5
5°	619.9	629.5	632.7	637.3	644.2	646.0	644.6	647.4	652.4	648.8	654.3
7.5°	664.3	674.9	682.2	692.3	694.6	700.5	704.2	707.4	708.3	708.8	709.7
10°	705.6	718.9	729.0	745.9	749.6	752.8	768.8	762.4	770.6	767.9	768.8
12.5°	739.0	765.1	773.4	801.8	804.5	815.5	814.6	824.7	826.5	830.2	826.5
15°	783.0	813.3	826.5	842.6	851.7	864.6	866.9	880.6	886.1	891.1	886.1
17.5°	823.3	839.4	873.3	886.1	892.1	898.9	916.3	921.4	929.6	926.4	935.6
20°	843.5	866.4	902.1	924.1	933.3	939.7	954.4	962.2	965.4	965.4	966.3
22.5°	861.4	894.4	920.9	946.1	954.4	959.0	967.7	973.6	975.0	975.9	976.8
25°	877.4	907.2	928.7	942.9	946.1	946.1	951.2	947.5	941.5	946.1	948.9
27.5°	877.4	898.5	908.1	913.1	913.1	900.8	893.4	878.3	865.5	861.8	870.1
30°	862.7	872.4	859.1	846.7	837.1	828.8	800.0	777.1	772.5	769.3	781.6
32.5°	828.8	816.5	790.3	754.6	740.4	721.6	699.2	681.8	671.2	667.6	664.8
35°	768.8	736.7	702.8	654.7	644.6	620.8	590.1	577.3	559.9	559.4	565.4
37.5°	703.3	653.8	617.2	571.3	557.1	531.9	503.1	489.8	477.9	468.7	479.7
40°	626.8	583.7	527.8	490.2	470.1	456.8	432.5	417.9	412.4	407.8	414.6
42.5°	555.3	508.1	464.6	426.1	409.6	394.5	378.4	364.2	360.1	359.7	364.7
45°	484.3	438.0	397.7	364.7	354.2	345.0	329.4	325.3	318.4	313.8	316.1
47.5°	427.5	379.8	346.4	321.2	312.0	304.2	294.1	287.3	281.3	279.5	282.2
50°	371.6	339.5	305.1	284.1	277.2	269.9	262.1	255.7	252.9	251.1	252.9
52.5°	326.7	292.3	268.9	252.0	245.1	239.6	234.1	231.4	227.7	228.6	230.5
55°	286.4	256.1	236.4	224.0	219.9	217.6	210.8	207.6	206.2	205.3	206.2
57.5°	248.3	226.3	211.7	201.1	195.6	194.3	188.8	188.8	187.4	186.0	186.5
60°	218.1	199.3	185.1	176.9	175.9	173.6	170.0	169.5	166.3	167.7	168.1
62.5°	187.4	172.3	162.7	157.6	154.4	153.5	151.2	150.7	149.4	149.8	148.9
65°	163.1	150.7	141.1	137.0	135.6	135.2	133.3	132.0	131.0	132.0	131.0
67.5°	138.8	130.6	123.2	119.1	117.3	116.8	115.5	114.5	115.0	113.6	114.5
70°	115.9	107.7	103.1	100.8	99.9	98.5	98.5	98.5	98.5	97.6	97.1
72.5°	97.6	89.3	86.1	84.8	83.8	83.4	82.0	82.5	82.0	81.6	83.4
75°	77.4	72.4	69.2	67.8	68.7	67.4	66.0	66.9	65.5	66.0	67.8
77.5°	58.6	56.4	54.5	53.6	52.7	51.8	51.8	50.9	50.9	50.9	50.9
80°	42.6	42.2	38.9	38.5	38.5	37.6	37.6	37.6	37.6	37.1	37.6
82.5°	28.4	27.9	27.0	26.6	25.7	26.1	26.1	25.2	25.2	24.7	25.2
85°	16.5	16.5	15.6	15.1	14.7	15.1	14.2	13.7	14.2	13.7	14.2
87.5°	7.8	6.9	7.3	6.9	6.0	6.4	5.5	6.0	5.5	5.0	6.0
90°	26.9	28.5	30.0	31.5	32.3	32.6	33.1	33.6	34.1	34.6	34.1
92.5°	25.8	27.3	28.9	30.4	31.2	31.2	31.2	31.2	31.2	31.2	31.2
95°	26.9	28.5	30.0	31.5	32.3	32.4	32.7	33.0	33.2	33.5	33.2
97.5°	26.7	28.0	29.3	30.6	31.2	31.3	31.6	31.8	32.1	32.3	32.1
100°	46.4	42.1	37.7	33.4	31.2	31.3	31.6	31.8	32.1	32.3	32.1
102.5°	235.6	177.8	120.1	62.4	33.5	33.5	33.5	33.5	33.5	33.5	33.5
105°	362.5	364.8	367.1	369.4	370.6	366.0	356.8	347.5	338.3	329.1	338.3
107.5°	435.4	436.7	438.0	439.3	439.9	440.4	441.4	442.5	443.5	444.5	443.5
110°	509.7	510.2	510.7	511.2	511.5	511.9	512.7	513.4	514.2	515.0	514.2

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	581.7	581.4	581.2	580.9	580.8	581.3	582.3	583.4	584.4	585.4	584.4
115°	651.7	652.2	652.7	653.2	653.5	653.5	653.5	653.5	653.5	653.5	653.5
117.5°	724.8	724.6	724.3	724.0	723.9	723.9	723.9	723.9	723.9	723.9	723.9
120°	790.3	790.8	791.3	791.8	792.1	791.8	791.3	790.8	790.3	789.8	790.3
122.5°	855.8	856.1	856.3	856.6	856.7	856.4	855.9	855.4	854.9	854.4	854.9
125°	915.3	916.0	916.8	917.5	917.9	918.0	918.3	918.6	918.8	919.1	918.8
127.5°	977.7	977.5	977.2	976.9	976.8	976.7	976.4	976.1	975.9	975.6	975.9
130°	1032.5	1032.7	1033.0	1033.3	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4
132.5°	1086.7	1087.0	1087.2	1087.5	1087.6	1087.5	1087.2	1087.0	1086.7	1086.5	1086.7
135°	1135.5	1136.0	1136.5	1137.0	1137.3	1137.6	1138.1	1138.6	1139.1	1139.6	1139.1
137.5°	1184.0	1184.5	1185.0	1185.5	1185.8	1185.7	1185.4	1185.1	1184.9	1184.6	1184.9
140°	1228.2	1228.9	1229.7	1230.4	1230.8	1230.9	1231.2	1231.5	1231.7	1232.0	1231.7
142.5°	1269.4	1269.9	1270.4	1270.9	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2
145°	1308.4	1308.7	1308.9	1309.2	1309.6	1309.6	1310.1	1310.6	1311.1	1311.6	1311.1
147.5°	1343.1	1343.3	1343.6	1343.9	1344.0	1344.1	1344.4	1344.6	1344.9	1345.1	1344.9
150°	1376.3	1376.3	1376.3	1376.3	1376.3	1376.4	1376.7	1377.0	1377.2	1377.5	1377.2
152.5°	1404.5	1405.0	1405.5	1406.0	1406.3	1406.2	1405.9	1405.7	1405.4	1405.2	1405.4
155°	1429.3	1430.3	1431.4	1432.4	1432.9	1432.5	1431.7	1431.0	1430.2	1429.4	1430.2
157.5°	1451.5	1452.8	1454.1	1455.4	1456.0	1455.4	1454.1	1452.8	1451.5	1450.2	1451.5
160°	1472.5	1474.1	1475.6	1477.1	1477.9	1477.1	1475.6	1474.1	1472.5	1471.0	1472.5
162.5°	1489.8	1491.4	1492.9	1494.4	1495.2	1494.3	1492.5	1490.7	1488.9	1487.1	1488.9
165°	1505.3	1507.4	1509.4	1511.5	1512.5	1511.4	1509.1	1506.8	1504.5	1502.2	1504.5
167.5°	1517.2	1519.5	1521.8	1524.1	1525.2	1523.9	1521.4	1518.8	1516.3	1513.7	1516.3
170°	1528.4	1530.5	1532.5	1534.6	1535.6	1534.3	1531.8	1529.2	1526.7	1524.1	1526.7
172.5°	1535.4	1537.4	1539.5	1541.6	1542.6	1541.2	1538.4	1535.5	1532.7	1529.9	1532.7
175°	1540.2	1542.5	1544.8	1547.1	1548.3	1546.8	1543.7	1540.6	1537.6	1534.5	1537.6
177.5°	1543.4	1545.5	1547.5	1549.6	1550.6	1549.1	1546.0	1542.9	1539.9	1536.8	1539.9
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	596.5	595.2	593.3	593.3	591.0	591.0	587.4	581.0	575.5	573.6	574.5
5°	647.4	647.9	645.1	642.8	638.7	635.5	629.5	618.1	614.4	607.1	602.0
7.5°	705.6	703.8	698.7	695.0	694.1	686.8	674.0	660.2	649.2	641.9	631.4
10°	771.1	763.8	756.4	754.2	748.7	736.3	721.6	706.5	691.4	675.3	657.5
12.5°	826.1	811.9	811.4	805.9	795.4	788.5	771.1	749.6	723.5	705.6	685.4
15°	885.2	871.9	860.9	850.8	845.8	825.6	811.0	783.9	752.8	733.5	719.8
17.5°	927.3	921.4	902.6	898.0	891.1	867.8	844.4	817.8	790.8	763.8	726.7
20°	961.2	957.6	945.2	938.8	927.8	909.5	881.1	850.4	819.2	780.7	745.9
22.5°	975.9	971.3	961.2	955.7	948.9	933.3	909.0	874.2	833.4	799.1	761.9
25°	947.0	955.3	952.5	950.2	947.5	938.3	920.0	889.3	849.5	810.5	764.2
27.5°	882.0	896.2	909.9	911.8	916.3	920.0	912.7	890.7	857.2	816.0	765.1
30°	794.5	800.9	828.8	837.1	843.5	866.9	880.6	875.1	849.5	812.3	765.6
32.5°	682.2	699.2	727.6	747.3	764.7	790.8	826.5	840.7	831.6	801.3	755.1
35°	575.9	596.1	629.1	654.3	671.7	708.8	750.9	781.6	793.1	778.0	736.7
37.5°	488.9	513.2	542.5	552.1	572.3	618.1	676.3	718.9	746.8	748.2	716.1
40°	423.4	435.7	459.1	473.7	493.5	531.9	588.8	645.1	687.3	701.5	684.5
42.5°	367.9	377.5	394.9	412.8	430.7	460.0	512.2	564.9	621.7	650.1	649.7
45°	323.9	334.0	345.9	360.6	373.0	404.6	445.8	499.9	548.9	592.9	603.9
47.5°	285.4	294.1	308.8	315.2	323.5	353.3	389.0	439.4	490.2	540.6	553.5
50°	257.0	264.4	274.4	278.6	287.7	309.7	339.0	379.8	436.2	482.5	506.3
52.5°	231.4	236.9	244.7	247.9	254.3	270.8	297.4	329.4	376.2	423.8	457.3
55°	209.4	213.0	218.5	222.2	226.8	241.5	261.2	290.0	330.3	371.6	404.1
57.5°	188.8	191.5	197.0	198.8	202.5	214.0	227.7	252.0	289.1	325.8	357.4
60°	169.5	171.4	174.6	178.7	181.4	189.2	202.1	222.2	252.0	285.4	311.1
62.5°	151.2	153.9	154.9	156.7	159.0	166.3	176.4	191.1	217.2	244.7	271.7
65°	132.4	134.7	136.5	137.0	139.3	144.8	153.9	166.8	183.7	207.6	232.8
67.5°	115.0	116.4	117.3	119.1	121.4	124.2	131.5	141.1	156.7	175.9	196.1
70°	99.0	99.0	100.3	100.8	103.5	106.8	110.0	119.1	132.9	148.4	162.2
72.5°	81.6	83.8	83.4	85.7	85.2	87.5	91.6	97.6	107.7	120.0	133.3
75°	66.4	67.8	67.8	67.8	68.7	70.6	72.8	78.3	86.1	96.2	104.0
77.5°	51.8	52.7	52.7	52.7	53.1	55.0	57.3	60.9	66.4	72.4	77.0
80°	37.1	38.0	38.0	38.9	38.9	39.4	41.7	43.5	46.3	50.9	55.4
82.5°	25.2	25.7	26.6	26.6	26.1	27.0	27.5	29.3	32.1	33.0	36.2
85°	13.7	14.2	14.7	14.7	15.1	16.0	15.6	17.4	17.4	19.2	20.2
87.5°	5.5	6.4	6.4	6.0	6.4	6.4	6.4	7.3	7.8	8.2	7.8
90°	33.6	33.1	32.6	32.3	31.5	30.0	28.5	26.9	25.4	23.4	21.3
92.5°	31.2	31.2	31.2	31.2	30.4	28.9	27.3	25.8	24.2	22.2	20.1
95°	33.0	32.7	32.4	32.3	31.5	30.0	28.5	26.9	25.4	25.1	24.9
97.5°	31.8	31.6	31.3	31.2	30.6	29.3	28.0	26.7	25.4	52.3	79.3
100°	31.8	31.6	31.3	31.2	33.4	37.7	42.1	46.4	50.8	86.2	121.6
102.5°	33.5	33.5	33.5	33.5	62.4	120.1	177.8	235.6	293.3	290.2	287.1
105°	347.5	356.8	366.0	370.6	369.4	367.1	364.8	362.5	360.2	358.9	357.7
107.5°	442.5	441.4	440.4	439.9	439.3	438.0	436.7	435.4	434.1	432.3	430.5
110°	513.4	512.7	511.9	511.5	511.2	510.7	510.2	509.7	509.2	507.7	506.1

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	583.4	582.3	581.3	580.8	580.9	581.2	581.4	581.7	581.9	581.4	580.9
115°	653.5	653.5	653.5	653.5	653.2	652.7	652.2	651.7	651.2	651.5	651.7
117.5°	723.9	723.9	723.9	723.9	724.0	724.3	724.6	724.8	725.1	724.3	723.5
120°	790.8	791.3	791.8	792.1	791.8	791.3	790.8	790.3	789.8	790.0	790.3
122.5°	855.4	855.9	856.4	856.7	856.6	856.3	856.1	855.8	855.6	855.1	854.6
125°	918.6	918.3	918.0	917.9	917.5	916.8	916.0	915.3	914.5	915.0	915.5
127.5°	976.1	976.4	976.7	976.8	976.9	977.2	977.5	977.7	978.0	976.7	975.4
130°	1033.4	1033.4	1033.4	1033.4	1033.3	1033.0	1032.7	1032.5	1032.2	1031.4	1030.7
132.5°	1087.0	1087.2	1087.5	1087.6	1087.5	1087.2	1087.0	1086.7	1086.5	1085.5	1084.5
135°	1138.6	1138.1	1137.6	1137.3	1137.0	1136.5	1136.0	1135.5	1135.0	1134.0	1133.0
137.5°	1185.1	1185.4	1185.7	1185.8	1185.5	1185.0	1184.5	1184.0	1183.5	1182.2	1180.9
140°	1231.5	1231.2	1230.9	1230.8	1230.4	1229.7	1228.9	1228.2	1227.4	1226.9	1226.3
142.5°	1271.2	1271.2	1271.2	1271.2	1270.9	1270.4	1269.9	1269.4	1268.9	1268.7	1268.4
145°	1310.6	1310.1	1309.6	1309.3	1309.2	1308.9	1308.7	1308.4	1308.2	1308.2	1308.2
147.5°	1344.6	1344.4	1344.1	1344.0	1343.9	1343.6	1343.3	1343.1	1342.8	1343.1	1343.3
150°	1377.0	1376.7	1376.4	1376.3	1376.3	1376.3	1376.3	1376.3	1376.3	1376.6	1376.8
152.5°	1405.7	1405.9	1406.2	1406.3	1406.0	1405.5	1405.0	1404.5	1404.0	1404.5	1405.0
155°	1431.0	1431.7	1432.5	1432.9	1432.4	1431.4	1430.3	1429.3	1428.3	1429.1	1429.8
157.5°	1452.8	1454.1	1455.4	1456.0	1455.4	1454.1	1452.8	1451.5	1450.2	1451.2	1452.2
160°	1474.1	1475.6	1477.1	1477.9	1477.1	1475.6	1474.1	1472.5	1471.0	1471.2	1471.5
162.5°	1490.7	1492.5	1494.3	1495.2	1494.4	1492.9	1491.4	1489.8	1488.3	1488.6	1488.8
165°	1506.8	1509.1	1511.4	1512.5	1511.5	1509.4	1507.4	1505.3	1503.3	1503.3	1503.3
167.5°	1518.8	1521.4	1523.9	1525.2	1524.1	1521.8	1519.5	1517.2	1514.9	1515.1	1515.4
170°	1529.2	1531.8	1534.3	1535.6	1534.6	1532.5	1530.5	1528.4	1526.4	1526.1	1525.9
172.5°	1535.5	1538.4	1541.2	1542.6	1541.6	1539.5	1537.4	1535.4	1533.3	1533.1	1532.8
175°	1540.6	1543.7	1546.8	1548.3	1547.1	1544.8	1542.5	1540.2	1537.9	1537.7	1537.4
177.5°	1542.9	1546.0	1549.1	1550.6	1549.6	1547.5	1545.5	1543.4	1541.4	1540.9	1540.4
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	570.4	568.6	567.2	567.2	563.1	559.0	556.7	555.8	554.8	551.2	546.1
5°	593.8	587.8	583.7	579.6	572.7	565.4	558.1	553.9	548.0	539.7	533.8
7.5°	619.9	605.7	601.1	596.1	582.3	570.0	559.9	551.2	541.6	531.0	520.5
10°	641.9	626.8	616.7	608.0	590.1	573.6	558.5	545.7	533.3	519.6	506.7
12.5°	663.0	641.4	630.9	618.1	599.3	575.5	555.8	539.7	521.4	507.2	491.6
15°	692.3	656.1	638.7	630.4	605.2	577.3	553.5	529.6	514.5	493.0	479.2
17.5°	696.9	667.6	656.1	635.0	604.8	573.2	545.7	521.9	498.9	479.7	461.8
20°	712.9	674.4	656.1	642.8	603.0	570.9	540.6	509.9	488.0	467.3	447.2
22.5°	723.0	679.5	660.2	639.1	601.1	562.6	526.9	500.3	473.3	452.2	436.2
25°	720.2	676.7	655.2	635.5	589.2	550.7	518.7	484.7	459.5	436.6	415.6
27.5°	718.9	669.8	646.9	624.9	581.4	541.1	500.8	473.3	445.3	418.8	403.2
30°	715.2	661.1	634.6	610.7	565.4	523.2	488.9	456.8	428.8	404.6	383.9
32.5°	702.8	646.5	620.8	595.2	548.0	505.8	471.0	441.2	413.3	388.1	368.4
35°	686.3	629.1	601.1	574.1	526.9	484.3	452.2	421.1	394.9	370.7	351.9
37.5°	669.8	608.9	582.8	551.6	508.1	463.7	430.7	402.7	378.4	353.3	332.6
40°	646.0	585.1	556.2	529.6	478.8	437.1	406.9	381.7	357.8	334.0	316.6
42.5°	613.5	559.0	529.2	499.9	452.2	411.0	381.7	359.2	336.8	317.1	297.8
45°	580.5	527.4	500.8	474.7	422.9	383.9	356.9	336.3	317.5	296.0	280.4
47.5°	540.6	495.7	469.2	443.5	394.5	355.5	330.8	311.6	294.1	276.3	261.6
50°	499.9	460.9	436.6	410.1	363.3	328.1	303.8	287.7	273.5	256.6	244.7
52.5°	455.9	422.0	401.4	375.7	334.5	301.9	277.2	261.2	249.2	236.9	226.3
55°	409.1	384.4	362.4	341.8	302.9	273.5	251.5	237.3	229.1	217.6	208.5
57.5°	367.0	343.2	329.9	306.5	272.6	243.7	226.3	214.4	204.8	197.9	190.6
60°	323.0	303.8	289.1	272.2	242.4	218.1	199.8	192.9	182.8	177.8	174.6
62.5°	280.9	267.1	253.4	240.5	214.0	191.1	177.3	168.6	162.7	157.6	154.9
65°	241.0	228.2	218.5	207.1	185.1	166.8	153.9	147.1	141.1	139.7	136.5
67.5°	202.1	196.6	186.0	176.9	158.1	143.9	134.2	125.5	122.3	121.0	118.2
70°	169.1	162.7	154.4	146.6	132.4	120.0	111.3	108.1	103.5	103.1	99.9
72.5°	139.3	131.5	125.5	119.6	109.0	98.0	93.5	88.9	86.6	84.8	83.4
75°	110.4	104.9	100.8	95.8	86.6	79.3	72.8	71.0	69.6	69.2	68.3
77.5°	82.5	78.8	77.0	71.9	65.5	59.1	56.4	53.6	53.6	52.7	53.1
80°	58.6	56.4	54.1	51.3	45.8	43.1	40.8	38.9	38.0	37.6	38.0
82.5°	37.1	35.7	35.3	33.4	29.8	28.4	26.6	25.2	25.2	25.2	25.2
85°	20.6	20.6	20.6	17.9	16.5	15.1	14.2	13.7	13.7	13.7	14.2
87.5°	8.7	8.7	7.3	7.3	6.9	6.0	5.5	5.5	6.0	6.0	6.4
90°	19.3	17.2	16.2	14.8	12.0	9.1	6.3	3.5	6.3	9.1	12.0
92.5°	18.1	16.0	15.0	15.3	15.8	16.3	16.8	17.3	16.8	16.3	15.8
95°	24.6	24.3	24.2	28.6	37.3	46.0	54.8	63.5	54.8	46.0	37.3
97.5°	106.2	133.1	146.6	143.8	138.1	132.5	126.8	121.2	126.8	132.5	138.1
100°	157.0	192.4	210.1	207.8	203.2	198.6	194.0	189.4	194.0	198.6	203.2
102.5°	284.0	280.9	279.4	277.9	274.8	271.7	268.7	265.6	268.7	271.7	274.8
105°	356.4	355.1	354.5	353.7	352.2	350.6	349.1	347.5	349.1	350.6	352.2
107.5°	428.8	427.0	426.1	425.7	424.9	424.2	423.4	422.6	423.4	424.2	424.9
110°	504.6	503.1	502.3	501.9	501.1	500.4	499.6	498.8	499.6	500.4	501.1

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	580.4	579.9	579.6	578.8	577.3	575.8	574.2	572.7	574.2	575.8	577.3
115°	652.0	652.3	652.4	652.0	651.2	650.5	649.7	648.9	649.7	650.5	651.2
117.5°	722.8	722.0	721.6	721.1	720.1	719.0	718.0	717.0	718.0	719.0	720.1
120°	790.5	790.8	790.9	790.4	789.4	788.3	787.3	786.3	787.3	788.3	789.4
122.5°	854.1	853.6	853.3	853.0	852.5	852.0	851.5	851.0	851.5	852.0	852.5
125°	916.0	916.5	916.8	916.3	915.2	914.2	913.1	912.1	913.1	914.2	915.2
127.5°	974.1	972.8	972.2	972.1	971.8	971.5	971.3	971.0	971.3	971.5	971.8
130°	1029.9	1029.2	1028.8	1028.7	1028.4	1028.1	1027.9	1027.6	1027.9	1028.1	1028.4
132.5°	1083.4	1082.4	1081.9	1081.6	1081.1	1080.6	1080.1	1079.6	1080.1	1080.6	1081.1
135°	1131.9	1130.9	1130.4	1130.5	1130.8	1131.0	1131.3	1131.5	1131.3	1131.0	1130.8
137.5°	1179.6	1178.3	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7
140°	1225.8	1225.3	1225.0	1224.7	1224.2	1223.7	1223.2	1222.7	1223.2	1223.7	1224.2
142.5°	1268.2	1267.9	1267.8	1267.3	1266.2	1265.2	1264.1	1263.1	1264.1	1265.2	1266.2
145°	1308.2	1308.2	1308.2	1307.8	1307.0	1306.3	1305.5	1304.7	1305.5	1306.3	1307.0
147.5°	1343.6	1343.9	1344.0	1343.2	1341.7	1340.1	1338.6	1337.0	1338.6	1340.1	1341.7
150°	1377.1	1377.4	1377.5	1377.0	1375.9	1374.9	1373.8	1372.8	1373.8	1374.9	1375.9
152.5°	1405.5	1406.0	1406.3	1405.9	1405.2	1404.4	1403.7	1402.9	1403.7	1404.4	1405.2
155°	1430.6	1431.3	1431.7	1431.6	1431.3	1431.1	1430.8	1430.6	1430.8	1431.1	1431.3
157.5°	1453.3	1454.3	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8
160°	1471.7	1472.0	1472.1	1472.5	1473.3	1474.0	1474.8	1475.6	1474.8	1474.0	1473.3
162.5°	1489.1	1489.4	1489.5	1490.0	1491.0	1492.1	1493.1	1494.1	1493.1	1492.1	1491.0
165°	1503.3	1503.3	1503.3	1503.9	1505.2	1506.5	1507.8	1509.1	1507.8	1506.5	1505.2
167.5°	1515.6	1515.9	1516.0	1516.6	1517.9	1519.2	1520.5	1521.8	1520.5	1519.2	1517.9
170°	1525.6	1525.3	1525.2	1526.0	1527.5	1529.1	1530.6	1532.2	1530.6	1529.1	1527.5
172.5°	1532.6	1532.3	1532.2	1533.0	1534.5	1536.0	1537.6	1539.1	1537.6	1536.0	1534.5
175°	1537.2	1536.9	1536.8	1537.6	1539.1	1540.6	1542.2	1543.7	1542.2	1540.6	1539.1
177.5°	1539.9	1539.4	1539.1	1540.0	1541.8	1543.6	1545.4	1547.2	1545.4	1543.6	1541.8
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	544.8	542.9	543.8	539.3	535.1	529.2	524.1	523.2	522.3	525.1	523.2
5°	529.2	526.9	524.6	519.1	510.9	505.8	498.5	498.0	495.3	491.2	492.1
7.5°	512.2	510.9	507.7	498.9	491.6	482.9	477.0	471.9	469.6	466.0	464.6
10°	498.5	493.5	490.7	481.1	472.4	463.2	455.4	451.8	447.6	444.4	442.1
12.5°	479.7	478.3	470.5	462.8	455.4	444.9	438.9	428.4	422.9	425.6	424.7
15°	467.3	460.9	459.1	448.1	435.7	428.8	417.9	411.0	408.7	404.6	399.5
17.5°	450.8	446.7	440.3	430.2	416.0	406.4	398.6	392.2	389.4	383.9	379.8
20°	435.3	428.4	423.4	414.2	400.4	388.1	378.4	374.3	367.5	362.9	360.6
22.5°	421.1	416.0	408.7	394.9	383.0	371.1	359.7	353.7	347.3	344.5	340.9
25°	403.6	395.4	390.4	375.2	362.4	352.8	342.3	334.5	330.8	326.2	325.3
27.5°	386.7	378.9	373.0	359.7	344.1	331.7	325.3	319.8	313.4	313.4	311.1
30°	369.7	364.2	355.1	342.3	327.6	315.7	308.3	303.3	301.0	299.2	298.7
32.5°	352.8	345.5	340.0	322.6	311.6	300.6	295.1	290.9	288.2	287.7	288.2
35°	335.4	327.1	321.6	306.1	295.1	285.0	282.7	279.0	277.7	277.2	279.5
37.5°	317.1	310.6	303.8	290.9	278.6	272.6	268.0	266.7	266.2	268.9	269.9
40°	300.1	294.6	288.2	274.4	265.3	258.9	256.6	255.2	257.0	259.8	261.2
42.5°	284.1	276.3	271.2	258.9	250.6	247.0	244.2	244.2	246.0	249.2	251.5
45°	267.1	261.2	256.1	245.1	237.8	233.7	233.2	233.7	236.0	238.2	241.0
47.5°	250.6	244.7	239.2	230.0	223.6	221.3	220.8	221.3	225.0	228.2	231.4
50°	235.5	229.1	224.0	215.3	210.3	207.6	208.0	210.3	213.0	217.6	221.8
52.5°	217.6	213.0	208.5	200.7	196.1	194.3	195.6	197.5	202.5	205.7	210.8
55°	200.2	196.1	192.4	186.5	182.8	181.4	182.4	185.1	189.2	194.7	200.7
57.5°	184.2	179.6	175.9	171.8	167.7	168.1	168.6	172.3	177.3	182.4	189.2
60°	166.3	163.6	160.4	155.3	153.5	153.5	154.9	159.0	163.6	171.8	177.8
62.5°	150.3	146.6	144.3	141.1	138.4	138.8	142.0	145.7	151.2	158.1	165.9
65°	133.8	129.7	127.8	125.1	124.2	124.6	126.9	132.4	138.4	144.3	151.7
67.5°	115.5	114.1	112.3	109.5	110.4	110.9	113.2	117.8	124.2	130.1	138.4
70°	99.9	97.1	96.7	94.4	94.4	95.8	100.3	103.5	109.5	115.9	124.6
72.5°	83.4	81.1	81.1	79.3	80.6	82.0	84.3	88.9	94.4	100.8	108.1
75°	66.4	65.5	66.4	65.5	65.5	67.8	70.6	74.2	80.2	87.1	93.0
77.5°	51.3	51.3	50.9	52.2	52.2	53.6	57.3	60.9	65.5	71.0	77.4
80°	37.6	37.6	37.6	38.9	40.3	40.3	42.6	47.2	51.3	55.0	60.9
82.5°	25.7	25.7	25.7	26.6	28.4	28.4	31.2	33.9	38.5	41.7	44.4
85°	15.6	15.6	15.1	16.0	16.5	17.9	20.2	22.0	24.3	27.0	29.8
87.5°	6.9	6.9	7.3	7.8	8.2	9.2	10.1	11.0	13.3	14.2	15.6
90°	14.8	16.2	17.2	19.3	21.3	23.4	25.4	26.9	28.5	30.0	31.5
92.5°	15.3	15.0	16.0	18.1	20.1	22.2	24.2	25.8	27.3	28.9	30.4
95°	28.6	24.2	24.3	24.6	24.9	25.1	25.4	26.9	28.5	30.0	31.5
97.5°	143.8	146.6	133.1	106.2	79.3	52.3	25.4	26.7	28.0	29.3	30.6
100°	207.8	210.1	192.4	157.0	121.6	86.2	50.8	46.4	42.1	37.7	33.4
102.5°	277.9	279.4	280.9	284.0	287.1	290.2	293.3	235.6	177.8	120.1	62.4
105°	353.7	354.5	355.1	356.4	357.7	358.9	360.2	362.5	364.8	367.1	369.4
107.5°	425.7	426.1	427.0	428.8	430.5	432.3	434.1	435.4	436.7	438.0	439.3
110°	501.9	502.3	503.1	504.6	506.1	507.7	509.2	509.7	510.2	510.7	511.2

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	578.8	579.6	579.9	580.4	580.9	581.4	581.9	581.7	581.4	581.2	580.9
115°	652.0	652.4	652.3	652.0	651.7	651.5	651.2	651.7	652.2	652.7	653.2
117.5°	721.1	721.6	722.0	722.8	723.5	724.3	725.1	724.8	724.6	724.3	724.0
120°	790.4	790.9	790.8	790.5	790.3	790.0	789.8	790.3	790.8	791.3	791.8
122.5°	853.0	853.3	853.6	854.1	854.6	855.1	855.6	855.8	856.1	856.3	856.6
125°	916.3	916.8	916.5	916.0	915.5	915.0	914.5	915.3	916.0	916.8	917.5
127.5°	972.1	972.2	972.8	974.1	975.4	976.7	978.0	977.7	977.5	977.2	976.9
130°	1028.7	1028.8	1029.2	1029.9	1030.7	1031.4	1032.2	1032.5	1032.7	1033.0	1033.3
132.5°	1081.6	1081.9	1082.4	1083.4	1084.5	1085.5	1086.5	1086.7	1087.0	1087.2	1087.5
135°	1130.5	1130.4	1130.9	1131.9	1133.0	1134.0	1135.0	1135.5	1136.0	1136.5	1137.0
137.5°	1177.7	1177.7	1178.3	1179.6	1180.9	1182.2	1183.5	1184.0	1184.5	1185.0	1185.5
140°	1224.7	1225.0	1225.3	1225.8	1226.3	1226.9	1227.4	1228.2	1228.9	1229.7	1230.4
142.5°	1267.3	1267.8	1267.9	1268.2	1268.4	1268.7	1268.9	1269.4	1269.9	1270.4	1270.9
145°	1307.8	1308.2	1308.2	1308.2	1308.2	1308.2	1308.2	1308.4	1308.7	1308.9	1309.2
147.5°	1343.2	1344.0	1343.9	1343.6	1343.3	1343.1	1342.8	1343.1	1343.3	1343.6	1343.9
150°	1377.0	1377.5	1377.4	1377.1	1376.8	1376.6	1376.3	1376.3	1376.3	1376.3	1376.3
152.5°	1405.9	1406.3	1406.0	1405.5	1405.0	1404.5	1404.0	1404.5	1405.0	1405.5	1406.0
155°	1431.6	1431.7	1431.3	1430.6	1429.8	1429.1	1428.3	1429.3	1430.3	1431.4	1432.4
157.5°	1454.8	1454.8	1454.3	1453.3	1452.2	1451.2	1450.2	1451.5	1452.8	1454.1	1455.4
160°	1472.5	1472.1	1472.0	1471.7	1471.5	1471.2	1471.0	1472.5	1474.1	1475.6	1477.1
162.5°	1490.0	1489.5	1489.4	1489.1	1488.8	1488.6	1488.3	1489.8	1491.4	1492.9	1494.4
165°	1503.9	1503.3	1503.3	1503.3	1503.3	1503.3	1503.3	1505.3	1507.4	1509.4	1511.5
167.5°	1516.6	1516.0	1515.9	1515.6	1515.4	1515.1	1514.9	1517.2	1519.5	1521.8	1524.1
170°	1526.0	1525.2	1525.3	1525.6	1525.9	1526.1	1526.4	1528.4	1530.5	1532.5	1534.6
172.5°	1533.0	1532.2	1532.3	1532.6	1532.8	1533.1	1533.3	1535.4	1537.4	1539.5	1541.6
175°	1537.6	1536.8	1536.9	1537.2	1537.4	1537.7	1537.9	1540.2	1542.5	1544.8	1547.1
177.5°	1540.0	1539.1	1539.4	1539.9	1540.4	1540.9	1541.4	1543.4	1545.5	1547.5	1549.6
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	521.9	521.4	519.1	520.0	517.3	518.2	519.6	520.0	521.9	520.5	520.0
5°	489.8	488.9	487.5	486.1	485.7	487.5	484.3	485.2	486.1	487.5	489.3
7.5°	463.7	463.2	461.8	459.5	458.6	457.7	458.2	461.4	460.9	460.5	463.7
10°	439.8	440.3	437.6	437.1	434.3	433.9	434.3	435.3	436.6	438.5	438.9
12.5°	415.1	421.1	416.0	414.2	410.1	412.4	413.3	409.1	411.4	412.8	419.7
15°	399.5	396.8	393.6	393.6	391.7	390.8	388.5	391.7	393.6	396.3	395.4
17.5°	378.0	373.4	371.6	369.7	370.2	372.0	367.0	374.3	374.3	375.7	373.4
20°	359.2	355.5	353.3	352.3	351.0	350.0	349.6	351.4	354.2	355.1	357.4
22.5°	339.5	339.5	335.8	334.5	333.5	332.2	334.5	333.1	334.9	336.8	340.4
25°	323.0	323.0	321.6	319.8	318.4	317.5	318.9	318.4	319.8	322.1	323.0
27.5°	309.7	308.3	307.9	307.4	307.0	307.4	307.0	308.3	309.7	310.2	309.3
30°	298.3	296.9	297.4	297.4	297.8	297.4	296.9	298.3	298.7	297.8	298.3
32.5°	287.7	287.7	288.6	289.1	289.1	289.6	290.0	289.1	289.6	288.2	288.6
35°	279.0	279.9	280.9	281.3	281.8	281.3	282.2	281.8	280.9	279.9	279.5
37.5°	270.3	271.2	273.1	273.5	274.9	275.4	274.4	274.4	274.0	272.2	271.2
40°	261.2	262.1	264.4	265.7	266.7	268.0	267.1	267.1	265.3	263.4	262.1
42.5°	252.5	254.3	256.6	258.0	259.8	259.8	259.8	258.9	256.6	254.7	253.4
45°	243.7	244.2	247.4	249.7	251.5	251.5	251.5	250.2	248.8	245.1	243.3
47.5°	234.1	235.5	239.2	241.5	243.3	243.7	243.7	242.4	239.6	236.4	234.1
50°	223.6	225.9	230.0	233.2	235.5	236.4	235.0	234.1	230.9	227.3	224.5
52.5°	213.5	216.3	221.3	224.0	227.3	227.7	227.3	225.9	222.2	217.2	214.9
55°	203.4	205.7	211.2	215.8	218.5	219.5	218.5	216.3	211.7	206.6	204.3
57.5°	192.4	195.6	201.6	206.2	209.4	209.8	208.9	206.6	203.0	196.6	193.3
60°	181.0	185.1	191.1	195.6	199.8	200.2	199.3	196.1	191.5	185.1	182.4
62.5°	169.5	172.7	179.6	184.6	187.9	190.1	188.3	185.1	180.5	174.1	170.0
65°	156.2	160.8	166.8	171.4	175.0	175.5	174.6	171.8	166.8	159.9	156.7
67.5°	143.4	146.6	152.6	158.5	159.9	161.3	159.9	157.2	153.0	147.1	142.5
70°	127.8	130.6	137.9	142.0	143.9	145.2	144.3	141.6	137.9	132.4	128.7
72.5°	112.3	114.5	121.4	124.6	128.3	127.8	127.4	125.5	120.5	116.8	114.5
75°	95.8	98.5	103.1	107.2	108.6	108.6	108.6	107.2	104.0	98.0	95.8
77.5°	80.6	82.0	85.7	88.0	89.3	89.8	89.3	87.1	85.2	81.1	79.7
80°	61.9	65.5	68.3	68.7	70.6	70.6	70.6	69.6	67.8	63.7	63.2
82.5°	46.7	47.6	50.4	51.8	52.7	52.2	52.2	50.4	49.9	47.6	46.7
85°	31.6	33.0	32.5	34.4	34.8	33.9	33.9	34.8	32.5	33.0	31.6
87.5°	17.4	17.4	18.3	17.9	19.7	19.7	18.8	19.2	18.3	17.9	17.4
90°	32.3	32.6	33.1	33.6	34.1	34.6	34.1	33.6	33.1	32.6	32.3
92.5°	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2
95°	32.3	32.4	32.7	33.0	33.2	33.5	33.2	33.0	32.7	32.4	32.3
97.5°	31.2	31.3	31.6	31.8	32.1	32.3	32.1	31.8	31.6	31.3	31.2
100°	31.2	31.3	31.6	31.8	32.1	32.3	32.1	31.8	31.6	31.3	31.2
102.5°	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5
105°	370.6	366.0	356.8	347.5	338.3	329.1	338.3	347.5	356.8	366.0	370.6
107.5°	439.9	440.4	441.4	442.5	443.5	444.5	443.5	442.5	441.4	440.4	439.9
110°	511.5	511.9	512.7	513.4	514.2	515.0	514.2	513.4	512.7	511.9	511.5

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	580.8	581.3	582.3	583.4	584.4	585.4	584.4	583.4	582.3	581.3	580.8
115°	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5
117.5°	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9
120°	792.1	791.8	791.3	790.8	790.3	789.8	790.3	790.8	791.3	791.8	792.1
122.5°	856.7	856.4	855.9	855.4	854.9	854.4	854.9	855.4	855.9	856.4	856.7
125°	917.9	918.0	918.3	918.6	918.8	919.1	918.8	918.6	918.3	918.0	917.9
127.5°	976.8	976.7	976.4	976.1	975.9	975.6	975.9	976.1	976.4	976.7	976.8
130°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4
132.5°	1087.6	1087.5	1087.2	1087.0	1086.7	1086.5	1086.7	1087.0	1087.2	1087.5	1087.6
135°	1137.3	1137.6	1138.1	1138.6	1139.1	1139.6	1139.1	1138.6	1138.1	1137.6	1137.3
137.5°	1185.8	1185.7	1185.4	1185.1	1184.9	1184.6	1184.9	1185.1	1185.4	1185.7	1185.8
140°	1230.8	1230.9	1231.2	1231.5	1231.7	1232.0	1231.7	1231.5	1231.2	1230.9	1230.8
142.5°	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2
145°	1309.3	1309.6	1310.1	1310.6	1311.1	1311.6	1311.1	1310.6	1310.1	1309.6	1309.3
147.5°	1344.0	1344.1	1344.4	1344.6	1344.9	1345.1	1344.9	1344.6	1344.4	1344.1	1344.0
150°	1376.3	1376.4	1376.7	1377.0	1377.2	1377.5	1377.2	1377.0	1376.7	1376.4	1376.3
152.5°	1406.3	1406.2	1405.9	1405.7	1405.4	1405.2	1405.4	1405.7	1405.9	1406.2	1406.3
155°	1432.9	1432.5	1431.7	1431.0	1430.2	1429.4	1430.2	1431.0	1431.7	1432.5	1432.9
157.5°	1456.0	1455.4	1454.1	1452.8	1451.5	1450.2	1451.5	1452.8	1454.1	1455.4	1456.0
160°	1477.9	1477.1	1475.6	1474.1	1472.5	1471.0	1472.5	1474.1	1475.6	1477.1	1477.9
162.5°	1495.2	1494.3	1492.5	1490.7	1488.9	1487.1	1488.9	1490.7	1492.5	1494.3	1495.2
165°	1512.5	1511.4	1509.1	1506.8	1504.5	1502.2	1504.5	1506.8	1509.1	1511.4	1512.5
167.5°	1525.2	1523.9	1521.4	1518.8	1516.3	1513.7	1516.3	1518.8	1521.4	1523.9	1525.2
170°	1535.6	1534.3	1531.8	1529.2	1526.7	1524.1	1526.7	1529.2	1531.8	1534.3	1535.6
172.5°	1542.6	1541.2	1538.4	1535.5	1532.7	1529.9	1532.7	1535.5	1538.4	1541.2	1542.6
175°	1548.3	1546.8	1543.7	1540.6	1537.6	1534.5	1537.6	1540.6	1543.7	1546.8	1548.3
177.5°	1550.6	1549.1	1546.0	1542.9	1539.9	1536.8	1539.9	1542.9	1546.0	1549.1	1550.6
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	520.0	522.8	520.0	521.9	522.8	525.1	526.0	530.1	531.5	534.7	534.7
5°	488.9	490.2	490.7	492.5	494.4	498.9	502.2	508.1	515.0	515.9	520.0
7.5°	463.7	466.0	469.6	468.3	471.5	478.3	482.5	489.8	496.7	500.3	505.4
10°	441.2	444.0	445.3	446.7	452.7	458.6	465.0	470.1	479.2	484.7	488.9
12.5°	422.9	420.6	423.4	428.4	435.3	438.9	447.6	455.4	462.3	468.3	471.9
15°	399.1	400.9	403.6	412.4	414.2	423.4	426.6	435.3	448.1	453.6	458.2
17.5°	376.2	382.1	387.6	390.8	396.3	403.6	412.8	422.4	430.7	437.1	442.6
20°	357.8	363.8	367.0	369.3	374.8	384.9	393.6	405.5	416.0	421.1	428.4
22.5°	343.2	343.2	347.8	354.6	357.8	367.5	374.8	387.6	399.1	405.5	412.4
25°	324.8	327.6	331.3	337.2	341.8	349.6	360.1	371.1	383.5	389.0	397.7
27.5°	309.7	312.9	318.0	319.3	323.9	330.8	341.8	353.7	366.5	372.5	379.8
30°	298.3	300.1	301.9	304.7	308.8	314.8	323.9	334.5	350.0	354.6	363.8
32.5°	288.2	289.1	290.0	292.3	294.6	300.6	307.9	319.3	332.2	339.0	347.3
35°	279.0	278.1	278.6	279.9	282.2	284.5	292.3	301.9	313.8	322.1	328.5
37.5°	270.3	268.5	268.0	268.0	268.9	271.7	277.7	285.9	298.7	305.6	312.0
40°	260.7	258.9	258.0	257.5	257.0	258.9	263.4	271.7	281.8	288.2	295.5
42.5°	251.5	249.7	247.4	247.0	246.0	247.0	250.2	258.0	266.7	273.1	279.0
45°	242.4	239.2	236.4	234.6	235.0	233.7	236.0	241.9	252.0	256.1	262.1
47.5°	232.3	228.6	225.0	223.1	221.3	222.2	223.1	228.2	236.9	241.0	247.0
50°	222.7	217.6	213.5	211.2	209.8	208.9	209.8	214.9	221.3	225.0	230.0
52.5°	211.7	206.6	202.5	198.8	197.0	195.6	196.1	200.7	206.6	210.3	215.3
55°	201.6	195.2	189.7	185.1	183.7	183.3	182.8	186.0	191.1	194.7	198.8
57.5°	190.1	183.7	177.8	172.3	169.5	169.1	169.1	170.0	176.4	179.1	181.4
60°	178.7	171.8	165.4	160.4	156.2	154.9	154.4	156.2	159.4	162.2	165.4
62.5°	165.9	159.0	151.2	146.6	142.5	138.8	140.2	140.7	145.2	146.6	149.4
65°	153.5	145.7	139.3	132.0	127.4	125.1	124.2	125.1	128.7	129.2	131.0
67.5°	139.3	132.0	124.2	119.1	115.0	110.9	110.0	110.0	111.8	113.2	115.5
70°	125.5	118.2	109.5	104.0	99.9	96.2	94.8	94.4	95.8	96.7	99.0
72.5°	109.5	102.2	95.8	89.8	84.8	82.0	80.6	79.7	81.1	82.0	82.5
75°	92.6	86.6	80.2	74.2	71.0	68.3	66.4	65.1	66.0	66.0	66.0
77.5°	76.5	70.6	65.5	61.4	57.3	54.1	52.7	51.3	51.8	51.8	52.7
80°	59.6	55.4	51.3	47.6	44.0	41.2	40.3	38.9	38.0	37.6	37.6
82.5°	44.0	40.8	37.1	33.9	32.1	29.3	28.4	26.6	26.6	26.1	26.1
85°	29.3	27.5	23.8	21.5	20.2	18.8	17.9	17.0	15.6	15.6	15.1
87.5°	15.6	14.7	13.7	11.0	11.0	9.6	9.2	8.7	7.3	7.8	7.8
90°	31.5	30.0	28.5	26.9	25.4	23.4	21.3	19.3	17.2	16.2	14.8
92.5°	30.4	28.9	27.3	25.8	24.2	22.2	20.1	18.1	16.0	15.0	15.3
95°	31.5	30.0	28.5	26.9	25.4	25.1	24.9	24.6	24.3	24.2	28.6
97.5°	30.6	29.3	28.0	26.7	25.4	52.3	79.3	106.2	133.1	146.6	143.8
100°	33.4	37.7	42.1	46.4	50.8	86.2	121.6	157.0	192.4	210.1	207.8
102.5°	62.4	120.1	177.8	235.6	293.3	290.2	287.1	284.0	280.9	279.4	277.9
105°	369.4	367.1	364.8	362.5	360.2	358.9	357.7	356.4	355.1	354.5	353.7
107.5°	439.3	438.0	436.7	435.4	434.1	432.3	430.5	428.8	427.0	426.1	425.7
110°	511.2	510.7	510.2	509.7	509.2	507.7	506.1	504.6	503.1	502.3	501.9

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	580.9	581.2	581.4	581.7	581.9	581.4	580.9	580.4	579.9	579.6	578.8
115°	653.2	652.7	652.2	651.7	651.2	651.5	651.7	652.0	652.3	652.4	652.0
117.5°	724.0	724.3	724.6	724.8	725.1	724.3	723.5	722.8	722.0	721.6	721.1
120°	791.8	791.3	790.8	790.3	789.8	790.0	790.3	790.5	790.8	790.9	790.4
122.5°	856.6	856.3	856.1	855.8	855.6	855.1	854.6	854.1	853.6	853.3	853.0
125°	917.5	916.8	916.0	915.3	914.5	915.0	915.5	916.0	916.5	916.8	916.3
127.5°	976.9	977.2	977.5	977.7	978.0	976.7	975.4	974.1	972.8	972.2	972.1
130°	1033.3	1033.0	1032.7	1032.5	1032.2	1031.4	1030.7	1029.9	1029.2	1028.8	1028.7
132.5°	1087.5	1087.2	1087.0	1086.7	1086.5	1085.5	1084.5	1083.4	1082.4	1081.9	1081.6
135°	1137.0	1136.5	1136.0	1135.5	1135.0	1134.0	1133.0	1131.9	1130.9	1130.4	1130.5
137.5°	1185.5	1185.0	1184.5	1184.0	1183.5	1182.2	1180.9	1179.6	1178.3	1177.7	1177.7
140°	1230.4	1229.7	1228.9	1228.2	1227.4	1226.9	1226.3	1225.8	1225.3	1225.0	1224.7
142.5°	1270.9	1270.4	1269.9	1269.4	1268.9	1268.7	1268.4	1268.2	1267.9	1267.8	1267.3
145°	1309.2	1308.9	1308.7	1308.4	1308.2	1308.2	1308.2	1308.2	1308.2	1308.2	1307.8
147.5°	1343.9	1343.6	1343.3	1343.1	1342.8	1343.1	1343.3	1343.6	1343.9	1344.0	1343.2
150°	1376.3	1376.3	1376.3	1376.3	1376.3	1376.6	1376.8	1377.1	1377.4	1377.5	1377.0
152.5°	1406.0	1405.5	1405.0	1404.5	1404.0	1404.5	1405.0	1405.5	1406.0	1406.3	1405.9
155°	1432.4	1431.4	1430.3	1429.3	1428.3	1429.1	1429.8	1430.6	1431.3	1431.7	1431.6
157.5°	1455.4	1454.1	1452.8	1451.5	1450.2	1451.2	1452.2	1453.3	1454.3	1454.8	1454.8
160°	1477.1	1475.6	1474.1	1472.5	1471.0	1471.2	1471.5	1471.7	1472.0	1472.1	1472.5
162.5°	1494.4	1492.9	1491.4	1489.8	1488.3	1488.6	1488.8	1489.1	1489.4	1489.5	1490.0
165°	1511.5	1509.4	1507.4	1505.3	1503.3	1503.3	1503.3	1503.3	1503.3	1503.3	1503.9
167.5°	1524.1	1521.8	1519.5	1517.2	1514.9	1515.1	1515.4	1515.6	1515.9	1516.0	1516.6
170°	1534.6	1532.5	1530.5	1528.4	1526.4	1526.1	1525.9	1525.6	1525.3	1525.2	1526.0
172.5°	1541.6	1539.5	1537.4	1535.4	1533.3	1533.1	1532.8	1532.6	1532.3	1532.2	1533.0
175°	1547.1	1544.8	1542.5	1540.2	1537.9	1537.7	1537.4	1537.2	1536.9	1536.8	1537.6
177.5°	1549.6	1547.5	1545.5	1543.4	1541.4	1540.9	1540.4	1539.9	1539.4	1539.1	1540.0
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	553.0	553.0	553.0	553.0
2.5°	537.9	542.5	546.6	553.0
5°	526.0	532.4	541.1	550.7
7.5°	512.2	522.3	533.8	547.1
10°	499.4	510.9	525.5	541.6
12.5°	486.1	499.9	515.9	533.3
15°	471.0	484.7	502.6	526.0
17.5°	457.3	473.7	493.0	517.7
20°	441.2	456.8	477.9	506.3
22.5°	427.0	444.9	468.3	493.0
25°	411.4	427.0	450.4	480.2
27.5°	395.9	415.1	437.6	466.4
30°	380.7	396.8	421.1	451.3
32.5°	364.2	383.5	405.9	434.3
35°	346.4	364.7	385.8	416.5
37.5°	330.3	348.2	369.7	396.8
40°	312.5	331.3	351.0	378.0
42.5°	295.1	312.0	331.7	356.5
45°	278.1	292.8	310.6	332.2
47.5°	260.7	273.1	289.6	308.8
50°	241.9	255.2	267.6	283.6
52.5°	224.5	236.0	246.0	259.3
55°	207.6	215.3	223.6	233.7
57.5°	189.7	195.6	201.6	212.1
60°	171.8	177.3	180.5	187.4
62.5°	154.4	156.7	160.8	164.9
65°	135.2	138.4	140.7	145.7
67.5°	117.8	119.1	121.4	124.6
70°	99.4	102.6	103.5	105.8
72.5°	83.8	85.2	86.1	86.6
75°	66.4	67.8	68.7	71.5
77.5°	52.2	51.8	53.6	54.1
80°	38.5	37.1	37.6	39.4
82.5°	25.2	25.7	25.2	25.2
85°	15.6	15.1	14.2	14.7
87.5°	6.9	6.9	6.4	6.4
90°	12.0	9.1	6.3	3.5
92.5°	15.8	16.3	16.8	17.3
95°	37.3	46.0	54.8	63.5
97.5°	138.1	132.5	126.8	121.2
100°	203.2	198.6	194.0	189.4
102.5°	274.8	271.7	268.7	265.6
105°	352.2	350.6	349.1	347.5
107.5°	424.9	424.2	423.4	422.6
110°	501.1	500.4	499.6	498.8

TEST NUMBER: P1001175

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	577.3	575.8	574.2	572.7
115°	651.2	650.5	649.7	648.9
117.5°	720.1	719.0	718.0	717.0
120°	789.4	788.3	787.3	786.3
122.5°	852.5	852.0	851.5	851.0
125°	915.2	914.2	913.1	912.1
127.5°	971.8	971.5	971.3	971.0
130°	1028.4	1028.1	1027.9	1027.6
132.5°	1081.1	1080.6	1080.1	1079.6
135°	1130.8	1131.0	1131.3	1131.5
137.5°	1177.7	1177.7	1177.7	1177.7
140°	1224.2	1223.7	1223.2	1222.7
142.5°	1266.2	1265.2	1264.1	1263.1
145°	1307.0	1306.3	1305.5	1304.7
147.5°	1341.7	1340.1	1338.6	1337.0
150°	1375.9	1374.9	1373.8	1372.8
152.5°	1405.2	1404.4	1403.7	1402.9
155°	1431.3	1431.1	1430.8	1430.6
157.5°	1454.8	1454.8	1454.8	1454.8
160°	1473.3	1474.0	1474.8	1475.6
162.5°	1491.0	1492.1	1493.1	1494.1
165°	1505.2	1506.5	1507.8	1509.1
167.5°	1517.9	1519.2	1520.5	1521.8
170°	1527.5	1529.1	1530.6	1532.2
172.5°	1534.5	1536.0	1537.6	1539.1
175°	1539.1	1540.6	1542.2	1543.7
177.5°	1541.8	1543.6	1545.4	1547.2
180°	1543.7	1543.7	1543.7	1543.7

(END OF REPORT)