

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000511

Luminaire Tested: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000511
REPORT IS A COMBINATION OF REPORTS P995121 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8172.0 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	54	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38
4	76	65	57	51	70	61	54	49	53	48	43	46	41	38	39	36	33
5	70	58	50	44	65	55	47	42	48	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13410	13410	13410	13410
5°	13376	15385	13455	11560
10°	13277	17950	13377	10142
15°	13117	20692	13209	9075
20°	12948	22438	13041	8136
25°	12699	22181	12820	7444
30°	12457	18333	12609	7087
35°	12117	13662	12250	6870
40°	11720	10291	11834	6765
45°	11114	8260	11252	6620
50°	10390	6959	10541	6553
55°	9539	6057	9688	6476
60°	8712	5334	8967	6368
65°	7935	4589	8010	6102
70°	7021	3776	7175	5619
75°	6127	2901	6086	4774
80°	4820	1907	4763	3624
85°	3173	857	2976	2113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 17340 cd/sqm

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	2.0
10°-20°	494.0	6.0
20°-30°	784.8	9.6
30°-40°	872.1	10.7
40°-50°	793.0	9.7
50°-60°	648.1	7.9
60°-70°	462.6	5.7
70°-80°	254.6	3.1
80°-90°	70.8	0.9
90°-100°	361.4	4.4
100°-110°	754.6	9.2
110°-120°	670.7	8.2
120°-130°	564.6	6.9
130°-140°	471.1	5.8
140°-150°	359.7	4.4
150°-160°	252.9	3.1
160°-170°	148.7	1.8
170°-180°	48.4	0.6
0°-30°	1438.9	17.6
0°-40°	2310.9	28.3
0°-60°	3752.1	45.9
0°-90°	4540.0	55.6
90°-120°	1786.7	21.9
90°-150°	3182.1	38.9
90°-180°	3632.0	44.4
0°-180°	8172.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1638	1929	1647	1450	1638	155
15°	1564	2650	1575	1162	1564	441
25°	1428	2814	1442	944	1428	658
35°	1238	1664	1252	837	1238	774
45°	988	933	1000	748	988	762
55°	695	610	706	653	695	625
65°	433	392	437	522	433	428
75°	213	196	211	323	213	223
85°	44	41	41	101	44	51
90°	1	21	1	21	1	5
95°	32	239	32	239	32	35
105°	115	1378	115	1378	115	122
115°	202	1324	202	1324	202	200
125°	281	1056	281	1056	281	251
135°	334	944	334	944	334	258
145°	385	771	385	771	385	242
155°	438	646	438	646	438	202
165°	477	563	477	563	477	135
175°	498	508	498	508	498	47
180°	499	499	499	499	499	

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1644.5	1660.9	1667.7	1673.2	1690.9	1696.3	1697.7	1705.9	1712.7	1714.0	1714.0
5°	1637.7	1663.6	1684.1	1703.1	1731.7	1744.0	1759.0	1775.3	1797.1	1810.8	1817.6
7.5°	1626.8	1665.0	1696.3	1729.0	1768.5	1793.1	1806.7	1850.3	1880.3	1904.8	1934.8
10°	1610.5	1659.5	1704.5	1752.2	1808.0	1838.0	1868.0	1921.1	1963.4	2011.1	2049.2
12.5°	1586.0	1650.0	1704.5	1771.3	1840.7	1876.2	1911.6	2004.2	2053.3	2095.5	2163.7
15°	1564.2	1628.2	1705.9	1774.0	1859.8	1913.0	1964.7	2024.7	2102.3	2193.6	2259.0
17.5°	1539.6	1620.0	1692.2	1787.6	1883.0	1933.4	1975.6	2068.3	2177.3	2267.2	2327.2
20°	1505.6	1587.3	1682.7	1783.5	1896.6	1936.1	1992.0	2116.0	2214.1	2302.6	2400.7
22.5°	1466.1	1561.4	1662.3	1759.0	1876.2	1959.3	2020.6	2129.6	2248.1	2350.3	2460.7
25°	1427.9	1531.5	1620.0	1752.2	1876.2	1932.0	2001.5	2131.0	2260.4	2384.4	2497.5
27.5°	1387.0	1483.8	1603.7	1708.6	1848.9	1910.2	1985.2	2126.9	2264.5	2388.5	2509.7
30°	1342.1	1445.6	1545.1	1669.1	1805.3	1884.3	1953.8	2107.8	2248.1	2377.6	2490.7
32.5°	1291.7	1389.8	1496.0	1613.2	1756.3	1836.7	1923.9	2081.9	2231.8	2343.5	2430.7
35°	1238.5	1338.0	1430.6	1550.5	1697.7	1778.1	1862.5	2036.9	2185.5	2276.7	2327.2
37.5°	1179.9	1273.9	1365.2	1483.8	1630.9	1716.8	1802.6	1971.5	2111.9	2188.2	2174.6
40°	1124.1	1208.5	1293.0	1404.7	1558.7	1650.0	1724.9	1895.2	2017.9	2050.6	2005.6
42.5°	1060.0	1132.2	1214.0	1328.4	1478.3	1564.2	1658.2	1813.5	1904.8	1891.2	1814.9
45°	987.8	1051.9	1133.6	1241.2	1393.8	1482.4	1561.4	1708.6	1775.3	1741.3	1602.3
47.5°	918.3	981.0	1047.8	1155.4	1303.9	1378.9	1459.2	1591.4	1629.6	1557.3	1418.4
50°	843.4	895.2	964.7	1066.8	1205.8	1284.8	1351.6	1457.9	1471.5	1382.9	1238.5
52.5°	771.2	814.8	881.5	982.4	1111.8	1174.5	1239.9	1333.9	1323.0	1231.7	1092.7
55°	694.9	735.8	797.1	889.7	1004.2	1064.1	1120.0	1203.1	1179.9	1085.9	964.7
57.5°	630.8	659.5	719.4	805.2	899.3	964.7	1012.3	1077.7	1042.3	948.3	835.2
60°	557.3	592.7	643.1	712.6	805.2	848.8	891.1	934.7	910.2	820.2	719.4
62.5°	490.5	517.8	561.4	628.1	700.3	739.8	784.8	812.1	787.5	704.4	619.9
65°	433.3	455.1	489.1	543.6	613.1	645.8	671.7	697.6	677.2	599.5	538.2
67.5°	370.6	389.7	418.3	461.9	520.5	543.6	568.2	585.9	562.7	510.9	451.0
70°	314.7	328.4	355.6	388.3	429.2	451.0	471.4	489.1	468.7	425.1	380.1
72.5°	257.5	268.4	292.9	316.1	352.9	367.9	382.9	396.5	389.7	348.8	312.0
75°	212.6	216.6	233.0	252.1	275.2	291.6	302.5	310.7	305.2	272.5	249.3
77.5°	160.8	166.2	178.5	193.5	213.9	223.5	230.3	238.4	231.6	205.7	189.4
80°	117.2	118.5	125.4	139.0	152.6	154.0	160.8	171.7	167.6	149.9	137.6
82.5°	74.9	79.0	81.8	89.9	99.5	102.2	106.3	109.0	107.6	96.7	92.7
85°	43.6	43.6	46.3	51.8	54.5	58.6	60.0	61.3	64.0	57.2	53.1
87.5°	19.1	20.4	20.4	21.8	24.5	24.5	25.9	27.3	28.6	27.3	23.2
90°	1.0	2.9	5.9	6.9	7.8	7.8	7.8	13.7	13.7	15.7	17.6
92.5°	13.7	19.6	30.4	45.1	62.7	75.4	88.2	148.9	244.0	336.0	384.1
95°	32.3	35.3	45.1	57.8	81.3	101.9	122.5	207.7	368.4	602.5	798.5
97.5°	53.9	53.9	62.7	74.5	95.0	112.6	130.3	197.9	336.0	577.1	854.3
100°	74.5	74.5	81.3	93.1	111.7	127.4	143.0	200.8	311.6	511.4	787.7
102.5°	94.1	96.0	101.9	112.7	130.3	145.0	159.7	210.6	304.7	467.3	704.4
105°	114.6	117.6	122.5	134.2	151.9	166.1	180.3	227.3	308.6	445.8	642.7
107.5°	137.2	139.1	144.0	156.8	173.4	187.6	201.8	244.9	320.4	439.9	602.5
110°	159.7	161.7	166.6	178.3	195.9	209.2	222.4	265.5	334.1	441.9	583.9

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	181.3	183.2	189.1	199.9	217.5	230.8	244.0	285.1	348.8	447.7	575.1
115°	201.8	204.8	211.6	221.4	240.0	253.2	266.5	305.7	364.5	455.6	573.1
117.5°	223.4	226.3	232.2	243.0	260.6	274.3	288.0	325.3	380.1	463.4	572.2
120°	244.9	246.9	253.8	264.5	281.2	294.9	308.6	345.8	396.8	472.2	572.2
122.5°	264.5	266.5	273.3	283.1	301.8	315.0	328.2	365.4	412.5	481.0	571.2
125°	281.2	285.1	291.0	301.8	320.4	334.1	347.8	383.1	428.1	489.9	570.2
127.5°	296.9	299.8	306.7	318.4	338.0	351.7	365.4	399.7	441.9	496.7	568.2
130°	309.6	313.5	321.4	336.0	354.7	368.9	383.1	416.4	454.6	504.6	567.3
132.5°	322.3	325.3	336.0	349.8	370.3	383.6	396.8	430.1	467.3	511.4	566.3
135°	334.1	338.0	347.8	364.5	385.0	397.8	410.5	442.8	478.1	518.3	565.3
137.5°	345.8	349.8	360.5	376.2	397.8	410.0	422.3	452.6	485.9	522.2	565.3
140°	358.6	361.5	372.3	389.0	409.5	421.2	433.0	462.4	493.8	527.1	564.3
142.5°	372.3	375.2	385.0	400.7	420.3	431.6	442.8	471.3	499.7	531.0	564.3
145°	385.0	388.0	397.8	411.5	430.1	440.9	451.7	477.1	503.6	532.0	562.4
147.5°	399.7	400.7	409.5	424.2	439.9	449.7	459.5	484.0	507.5	533.0	559.4
150°	413.4	414.4	422.3	434.0	448.7	458.0	467.3	488.9	510.4	533.0	556.5
152.5°	426.2	426.2	434.0	444.8	457.5	465.8	474.2	492.8	512.4	531.0	551.6
155°	437.9	438.9	444.8	454.6	465.4	472.8	480.1	496.7	513.4	529.1	546.7
157.5°	449.7	449.7	455.6	463.4	473.2	479.1	485.0	499.7	513.4	527.1	541.8
160°	460.5	460.5	464.4	471.3	479.1	484.5	489.9	501.6	513.4	524.2	535.9
162.5°	470.3	469.3	472.2	478.1	485.0	488.9	492.8	503.6	513.4	521.2	530.0
165°	477.1	477.1	479.1	484.0	488.9	491.8	494.8	503.6	511.4	517.3	524.2
167.5°	485.0	484.0	485.0	488.9	491.8	494.2	496.7	503.6	509.5	513.4	518.3
170°	489.9	488.9	489.9	492.8	494.8	496.2	497.7	502.6	507.5	509.5	512.4
172.5°	494.8	493.8	493.8	495.7	496.7	497.7	498.7	501.6	505.5	505.5	506.5
175°	497.7	496.7	496.7	497.7	498.7	498.7	498.7	500.6	503.6	502.6	502.6
177.5°	499.7	498.7	497.7	498.7	498.7	498.7	498.7	499.7	501.6	499.7	499.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1718.1	1742.6	1753.5	1756.3	1771.3	1761.7	1765.8	1764.4	1775.3	1776.7	1776.7
5°	1843.5	1872.1	1881.6	1895.2	1915.7	1921.1	1917.0	1925.2	1940.2	1929.3	1945.7
7.5°	1975.6	2007.0	2028.8	2058.7	2065.6	2083.3	2094.2	2103.7	2106.4	2107.8	2110.5
10°	2098.3	2137.8	2167.7	2218.2	2229.1	2238.6	2286.3	2267.2	2291.7	2283.6	2286.3
12.5°	2197.7	2275.4	2299.9	2384.4	2392.6	2425.3	2422.5	2452.5	2458.0	2468.9	2458.0
15°	2328.5	2418.4	2458.0	2505.6	2532.9	2571.0	2577.9	2618.7	2635.1	2650.1	2635.1
17.5°	2448.4	2496.1	2596.9	2635.1	2652.8	2673.2	2725.0	2740.0	2764.5	2755.0	2782.2
20°	2508.4	2576.5	2682.8	2748.2	2775.4	2794.5	2838.1	2861.3	2870.8	2870.8	2873.5
22.5°	2561.5	2659.6	2738.6	2813.6	2838.1	2851.7	2877.6	2895.3	2899.4	2902.1	2904.9
25°	2609.2	2697.8	2761.8	2804.0	2813.6	2813.6	2828.6	2817.7	2799.9	2813.6	2821.7
27.5°	2609.2	2671.9	2700.5	2715.5	2715.5	2678.7	2656.9	2611.9	2573.8	2562.9	2587.4
30°	2565.6	2594.2	2554.7	2517.9	2489.3	2464.8	2378.9	2310.8	2297.2	2287.6	2324.4
32.5°	2464.8	2428.0	2350.3	2244.0	2201.8	2145.9	2079.2	2027.4	1996.1	1985.2	1977.0
35°	2286.3	2190.9	2090.1	1947.0	1917.0	1846.2	1754.9	1716.8	1665.0	1663.6	1681.3
37.5°	2091.4	1944.3	1835.3	1699.0	1656.8	1581.9	1496.0	1456.5	1421.1	1393.8	1426.5
40°	1863.9	1735.8	1569.6	1457.9	1397.9	1358.4	1286.2	1242.6	1226.3	1212.6	1233.1
42.5°	1651.4	1511.0	1381.6	1267.1	1218.1	1173.1	1125.4	1083.2	1070.9	1069.6	1084.6
45°	1440.2	1302.6	1182.7	1084.6	1053.2	1026.0	979.6	967.4	946.9	933.3	940.1
47.5°	1271.2	1129.5	1030.1	955.1	927.9	904.7	874.7	854.3	836.6	831.1	839.3
50°	1105.0	1009.6	907.4	844.8	824.3	802.5	779.4	760.3	752.1	746.7	752.1
52.5°	971.5	869.3	799.8	749.4	728.9	712.6	696.2	688.1	677.2	679.9	685.3
55°	851.6	761.6	703.1	666.3	654.0	647.2	626.8	617.2	613.1	610.4	613.1
57.5°	738.5	673.1	629.5	598.1	581.8	577.7	561.4	561.4	557.3	553.2	554.5
60°	648.6	592.7	550.5	525.9	523.2	516.4	505.5	504.1	494.6	498.7	500.0
62.5°	557.3	512.3	483.7	468.7	459.2	456.4	449.6	448.3	444.2	445.5	442.8
65°	485.1	448.3	419.7	407.4	403.3	401.9	396.5	392.4	389.7	392.4	389.7
67.5°	412.8	388.3	366.5	354.3	348.8	347.4	343.4	340.6	342.0	337.9	340.6
70°	344.7	320.2	306.6	299.8	297.0	292.9	292.9	292.9	292.9	290.2	288.9
72.5°	290.2	265.7	256.2	252.1	249.3	248.0	243.9	245.3	243.9	242.5	248.0
75°	230.3	215.3	205.7	201.7	204.4	200.3	196.2	198.9	194.8	196.2	201.7
77.5°	174.4	167.6	162.1	159.4	156.7	154.0	154.0	151.2	151.2	151.2	151.2
80°	126.7	125.4	115.8	114.5	114.5	111.7	111.7	111.7	111.7	110.4	111.7
82.5°	84.5	83.1	80.4	79.0	76.3	77.7	77.7	74.9	74.9	73.6	74.9
85°	49.1	49.1	46.3	45.0	43.6	45.0	42.2	40.9	42.2	40.9	42.2
87.5°	23.2	20.4	21.8	20.4	17.7	19.1	16.4	17.7	16.4	15.0	17.7
90°	16.7	17.6	18.6	19.6	19.6	19.6	20.6	21.6	20.6	20.6	20.6
92.5°	319.4	236.1	176.4	139.1	126.8	114.6	99.9	93.1	89.2	89.2	89.2
95°	821.0	726.0	574.1	442.8	395.3	347.8	299.8	269.4	251.8	239.1	251.8
97.5°	1029.7	1045.4	969.9	862.2	807.3	752.4	685.8	627.0	597.6	574.1	597.6
100°	1038.5	1181.6	1201.2	1153.1	1116.8	1080.6	995.4	935.6	906.3	898.4	906.3
102.5°	965.0	1174.7	1291.3	1320.7	1310.9	1301.1	1257.0	1217.8	1186.5	1180.6	1186.5
105°	872.9	1097.3	1266.8	1363.8	1383.9	1404.0	1405.9	1398.1	1384.4	1378.5	1384.4
107.5°	797.5	1002.3	1185.5	1320.7	1361.8	1403.0	1446.1	1463.7	1471.6	1472.5	1471.6
110°	743.6	918.0	1087.5	1229.6	1283.4	1337.3	1406.9	1448.0	1465.7	1474.5	1465.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	713.2	856.3	1001.3	1133.5	1187.4	1241.3	1322.6	1374.6	1401.0	1416.7	1401.0
115°	696.6	819.1	939.6	1054.2	1101.2	1148.2	1225.6	1284.4	1315.8	1323.6	1315.8
117.5°	687.8	797.5	899.4	992.5	1033.6	1074.8	1143.3	1194.3	1227.6	1232.5	1227.6
120°	680.9	783.8	874.9	953.3	988.0	1022.8	1078.7	1121.8	1147.3	1158.0	1147.3
122.5°	673.1	772.0	859.2	928.8	958.2	987.6	1032.6	1067.9	1088.5	1099.3	1088.5
125°	664.3	758.3	842.6	910.2	937.2	964.1	1003.2	1031.7	1050.3	1056.2	1050.3
127.5°	652.5	742.6	824.0	891.6	917.0	942.5	981.7	1007.2	1022.8	1028.7	1022.8
130°	641.7	723.0	800.4	867.1	893.0	919.0	959.2	983.7	999.3	1005.2	999.3
132.5°	631.9	702.5	774.0	838.7	864.6	890.6	929.8	958.2	972.9	978.8	972.9
135°	622.1	683.9	747.5	807.3	831.8	856.3	895.5	922.9	938.6	944.5	938.6
137.5°	613.3	666.2	722.1	774.0	796.6	819.1	856.3	884.7	897.4	904.3	897.4
140°	606.5	651.5	697.6	741.7	762.2	782.8	817.1	838.7	852.4	860.2	852.4
142.5°	600.6	637.8	677.0	713.2	730.4	747.5	776.9	796.5	808.3	813.2	808.3
145°	593.7	625.1	658.4	687.8	701.5	715.2	739.7	756.4	766.2	771.0	766.2
147.5°	587.8	614.3	641.7	666.2	677.5	688.8	707.4	722.1	729.9	731.9	729.9
150°	581.0	604.5	627.0	646.6	655.4	664.3	679.9	692.7	698.5	699.5	698.5
152.5°	573.1	593.7	612.3	630.0	636.8	643.7	656.4	666.2	669.2	670.1	669.2
155°	565.3	582.9	598.6	613.3	619.2	625.1	634.9	642.7	645.6	645.6	645.6
157.5°	557.5	571.2	584.9	597.6	602.5	607.4	615.3	621.1	623.1	623.1	623.1
160°	548.6	560.4	571.2	582.0	585.9	589.8	595.7	601.6	602.5	602.5	602.5
162.5°	540.8	549.6	558.4	566.3	569.7	573.1	577.1	582.9	583.9	582.9	583.9
165°	532.0	539.8	545.7	552.6	555.0	557.5	561.4	565.3	564.3	563.3	564.3
167.5°	524.2	530.0	534.9	540.8	542.3	543.8	545.7	548.6	548.6	547.7	548.6
170°	516.3	521.2	524.2	528.1	529.6	531.0	533.0	534.0	533.0	533.0	533.0
172.5°	509.5	513.4	515.3	517.3	518.3	519.3	520.2	521.2	520.2	518.3	520.2
175°	504.6	506.5	507.5	509.5	509.5	509.5	509.5	511.4	509.5	507.5	509.5
177.5°	500.6	501.6	502.6	502.6	503.1	503.6	502.6	503.6	501.6	499.7	501.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1774.0	1769.9	1764.4	1764.4	1757.6	1757.6	1746.7	1727.7	1711.3	1705.9	1708.6
5°	1925.2	1926.6	1918.4	1911.6	1899.3	1889.8	1872.1	1838.0	1827.1	1805.3	1790.3
7.5°	2098.3	2092.8	2077.8	2066.9	2064.2	2042.4	2004.2	1963.4	1930.7	1908.9	1877.5
10°	2293.1	2271.3	2249.5	2242.7	2226.3	2189.5	2145.9	2101.0	2056.0	2008.3	1955.2
12.5°	2456.6	2414.4	2413.0	2396.6	2365.3	2344.9	2293.1	2229.1	2151.4	2098.3	2038.3
15°	2632.4	2592.8	2560.1	2530.2	2515.2	2455.2	2411.6	2331.2	2238.6	2181.4	2140.5
17.5°	2757.7	2740.0	2684.1	2670.5	2650.1	2580.6	2511.1	2432.1	2351.7	2271.3	2160.9
20°	2858.5	2847.6	2810.8	2791.8	2759.1	2704.6	2620.1	2528.8	2436.2	2321.7	2218.2
22.5°	2902.1	2888.5	2858.5	2842.2	2821.7	2775.4	2703.2	2599.7	2478.4	2376.2	2265.8
25°	2816.3	2840.8	2832.6	2825.8	2817.7	2790.4	2735.9	2644.6	2526.1	2410.3	2272.7
27.5°	2622.8	2665.1	2705.9	2711.4	2725.0	2735.9	2714.1	2648.7	2549.2	2426.6	2275.4
30°	2362.6	2381.7	2464.8	2489.3	2508.4	2577.9	2618.7	2602.4	2526.1	2415.7	2276.7
32.5°	2028.8	2079.2	2163.7	2222.2	2274.0	2351.7	2458.0	2500.2	2472.9	2383.0	2245.4
35°	1712.7	1772.6	1870.7	1945.7	1997.4	2107.8	2233.1	2324.4	2358.5	2313.5	2190.9
37.5°	1453.8	1526.0	1613.2	1641.8	1701.8	1838.0	2011.1	2137.8	2220.9	2225.0	2129.6
40°	1259.0	1295.7	1365.2	1408.8	1467.4	1581.9	1750.8	1918.4	2043.8	2086.0	2035.6
42.5°	1094.1	1122.7	1174.5	1227.6	1280.8	1368.0	1523.3	1680.0	1848.9	1933.4	1932.0
45°	963.3	993.3	1028.7	1072.3	1109.1	1203.1	1325.7	1486.5	1632.3	1763.1	1795.8
47.5°	848.8	874.7	918.3	937.4	961.9	1050.5	1156.8	1306.6	1457.9	1607.8	1645.9
50°	764.4	786.2	816.1	828.4	855.7	921.1	1008.3	1129.5	1297.1	1434.7	1505.6
52.5°	688.1	704.4	727.6	737.1	756.2	805.2	884.3	979.6	1118.6	1260.3	1359.8
55°	622.7	633.6	649.9	660.8	674.4	718.0	776.6	862.5	982.4	1105.0	1201.7
57.5°	561.4	569.5	585.9	591.3	602.2	636.3	677.2	749.4	859.7	968.7	1062.8
60°	504.1	509.6	519.1	531.4	539.6	562.7	600.9	660.8	749.4	848.8	925.1
62.5°	449.6	457.8	460.5	466.0	472.8	494.6	524.6	568.2	645.8	727.6	808.0
65°	393.8	400.6	406.0	407.4	414.2	430.6	457.8	496.0	546.4	617.2	692.2
67.5°	342.0	346.1	348.8	354.3	361.1	369.2	391.0	419.7	466.0	523.2	583.2
70°	294.3	294.3	298.4	299.8	307.9	317.5	327.0	354.3	395.1	441.5	482.3
72.5°	242.5	249.3	248.0	254.8	253.4	260.2	272.5	290.2	320.2	357.0	396.5
75°	197.6	201.7	201.7	201.7	204.4	209.8	216.6	233.0	256.2	286.1	309.3
77.5°	154.0	156.7	156.7	156.7	158.1	163.5	170.3	181.2	197.6	215.3	228.9
80°	110.4	113.1	113.1	115.8	115.8	117.2	124.0	129.4	137.6	151.2	164.9
82.5°	74.9	76.3	79.0	79.0	77.7	80.4	81.8	87.2	95.4	98.1	107.6
85°	40.9	42.2	43.6	43.6	45.0	47.7	46.3	51.8	51.8	57.2	60.0
87.5°	16.4	19.1	19.1	17.7	19.1	19.1	19.1	21.8	23.2	24.5	23.2
90°	21.6	20.6	19.6	19.6	19.6	18.6	17.6	16.7	17.6	15.7	13.7
92.5°	93.1	99.9	114.6	126.8	139.1	176.4	236.1	319.4	384.1	336.0	244.0
95°	269.4	299.8	347.8	395.3	442.8	574.1	726.0	821.0	798.5	602.5	368.4
97.5°	627.0	685.8	752.4	807.3	862.2	969.9	1045.4	1029.7	854.3	577.1	336.0
100°	935.6	995.4	1080.6	1116.8	1153.1	1201.2	1181.6	1038.5	787.7	511.4	311.6
102.5°	1217.8	1257.0	1301.1	1310.9	1320.7	1291.3	1174.7	965.0	704.4	467.3	304.7
105°	1398.1	1405.9	1404.0	1383.9	1363.8	1266.8	1097.3	872.9	642.7	445.8	308.6
107.5°	1463.7	1446.1	1403.0	1361.8	1320.7	1185.5	1002.3	797.5	602.5	439.9	320.4
110°	1448.0	1406.9	1337.3	1283.4	1229.6	1087.5	918.0	743.6	583.9	441.9	334.1

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1374.6	1322.6	1241.3	1187.4	1133.5	1001.3	856.3	713.2	575.1	447.7	348.8
115°	1284.4	1225.6	1148.2	1101.2	1054.2	939.6	819.1	696.6	573.1	455.6	364.5
117.5°	1194.3	1143.3	1074.8	1033.6	992.5	899.4	797.5	687.8	572.2	463.4	380.1
120°	1121.8	1078.7	1022.8	988.0	953.3	874.9	783.8	680.9	572.2	472.2	396.8
122.5°	1067.9	1032.6	987.6	958.2	928.8	859.2	772.0	673.1	571.2	481.0	412.5
125°	1031.7	1003.2	964.1	937.2	910.2	842.6	758.3	664.3	570.2	489.9	428.1
127.5°	1007.2	981.7	942.5	917.0	891.6	824.0	742.6	652.5	568.2	496.7	441.9
130°	983.7	959.2	919.0	893.0	867.1	800.4	723.0	641.7	567.3	504.6	454.6
132.5°	958.2	929.8	890.6	864.6	838.7	774.0	702.5	631.9	566.3	511.4	467.3
135°	922.9	895.5	856.3	831.8	807.3	747.5	683.9	622.1	565.3	518.3	478.1
137.5°	884.7	856.3	819.1	796.6	774.0	722.1	666.2	613.3	565.3	522.2	485.9
140°	838.7	817.1	782.8	762.2	741.7	697.6	651.5	606.5	564.3	527.1	493.8
142.5°	796.5	776.9	747.5	730.4	713.2	677.0	637.8	600.6	564.3	531.0	499.7
145°	756.4	739.7	715.2	701.5	687.8	658.4	625.1	593.7	562.4	532.0	503.6
147.5°	722.1	707.4	688.8	677.5	666.2	641.7	614.3	587.8	559.4	533.0	507.5
150°	692.7	679.9	664.3	655.4	646.6	627.0	604.5	581.0	556.5	533.0	510.4
152.5°	666.2	656.4	643.7	636.8	630.0	612.3	593.7	573.1	551.6	531.0	512.4
155°	642.7	634.9	625.1	619.2	613.3	598.6	582.9	565.3	546.7	529.1	513.4
157.5°	621.1	615.3	607.4	602.5	597.6	584.9	571.2	557.5	541.8	527.1	513.4
160°	601.6	595.7	589.8	585.9	582.0	571.2	560.4	548.6	535.9	524.2	513.4
162.5°	582.9	577.1	573.1	569.7	566.3	558.4	549.6	540.8	530.0	521.2	513.4
165°	565.3	561.4	557.5	555.0	552.6	545.7	539.8	532.0	524.2	517.3	511.4
167.5°	548.6	545.7	543.8	542.3	540.8	534.9	530.0	524.2	518.3	513.4	509.5
170°	534.0	533.0	531.0	529.6	528.1	524.2	521.2	516.3	512.4	509.5	507.5
172.5°	521.2	520.2	519.3	518.3	517.3	515.3	513.4	509.5	506.5	505.5	505.5
175°	511.4	509.5	509.5	509.5	509.5	507.5	506.5	504.6	502.6	502.6	503.6
177.5°	503.6	502.6	503.6	503.1	502.6	502.6	501.6	500.6	499.7	499.7	501.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1696.3	1690.9	1686.8	1686.8	1674.5	1662.3	1655.4	1652.7	1650.0	1639.1	1624.1
5°	1765.8	1748.1	1735.8	1723.6	1703.1	1681.3	1659.5	1647.3	1629.6	1605.0	1587.3
7.5°	1843.5	1801.2	1787.6	1772.6	1731.7	1695.0	1665.0	1639.1	1610.5	1579.1	1547.8
10°	1908.9	1863.9	1833.9	1808.0	1754.9	1705.9	1660.9	1622.7	1586.0	1545.1	1506.9
12.5°	1971.5	1907.5	1876.2	1838.0	1782.2	1711.3	1652.7	1605.0	1550.5	1508.3	1462.0
15°	2058.7	1951.1	1899.3	1874.8	1799.9	1716.8	1645.9	1575.1	1530.1	1466.1	1425.2
17.5°	2072.4	1985.2	1951.1	1888.4	1798.5	1704.5	1622.7	1551.9	1483.8	1426.5	1373.4
20°	2120.1	2005.6	1951.1	1911.6	1793.1	1697.7	1607.8	1516.5	1451.1	1389.8	1329.8
22.5°	2150.0	2020.6	1963.4	1900.7	1787.6	1673.2	1566.9	1487.9	1407.5	1344.8	1297.1
25°	2141.9	2012.4	1948.4	1889.8	1752.2	1637.7	1542.4	1441.5	1366.6	1298.5	1235.8
27.5°	2137.8	1992.0	1923.9	1858.5	1729.0	1609.1	1489.2	1407.5	1324.4	1245.3	1199.0
30°	2126.9	1966.1	1887.1	1816.2	1681.3	1556.0	1453.8	1358.4	1275.3	1203.1	1141.8
32.5°	2090.1	1922.5	1846.2	1769.9	1629.6	1504.2	1400.7	1312.1	1229.0	1154.0	1095.5
35°	2041.0	1870.7	1787.6	1707.2	1566.9	1440.2	1344.8	1252.1	1174.5	1102.3	1046.4
37.5°	1992.0	1810.8	1733.1	1640.5	1511.0	1378.9	1280.8	1197.6	1125.4	1050.5	989.2
40°	1921.1	1739.9	1654.1	1575.1	1423.8	1299.8	1209.9	1135.0	1064.1	993.3	941.5
42.5°	1824.4	1662.3	1573.7	1486.5	1344.8	1222.2	1135.0	1068.2	1001.4	942.9	885.6
45°	1726.3	1568.2	1489.2	1411.6	1257.6	1141.8	1061.4	1000.1	944.2	880.2	833.9
47.5°	1607.8	1474.2	1395.2	1318.9	1173.1	1057.3	983.7	926.5	874.7	821.6	778.0
50°	1486.5	1370.7	1298.5	1219.4	1080.5	975.6	903.3	855.7	813.4	763.0	727.6
52.5°	1355.7	1254.9	1193.6	1117.3	994.6	897.9	824.3	776.6	741.2	704.4	673.1
55°	1216.7	1143.1	1077.7	1016.4	900.6	813.4	748.0	705.8	681.3	647.2	619.9
57.5°	1091.4	1020.5	981.0	911.5	810.7	724.9	673.1	637.7	609.0	588.6	566.8
60°	960.6	903.3	859.7	809.3	720.8	648.6	594.1	573.6	543.6	528.7	519.1
62.5°	835.2	794.3	753.5	715.3	636.3	568.2	527.3	501.4	483.7	468.7	460.5
65°	716.7	678.5	649.9	615.9	550.5	496.0	457.8	437.4	419.7	415.6	406.0
67.5°	600.9	584.5	553.2	525.9	470.1	427.8	399.2	373.3	363.8	359.7	351.5
70°	502.8	483.7	459.2	436.0	393.8	357.0	331.1	321.6	307.9	306.6	297.0
72.5°	414.2	391.0	373.3	355.6	324.3	291.6	278.0	264.3	257.5	252.1	248.0
75°	328.4	312.0	299.8	284.8	257.5	235.7	216.6	211.2	207.1	205.7	203.0
77.5°	245.3	234.4	228.9	213.9	194.8	175.8	167.6	159.4	159.4	156.7	158.1
80°	174.4	167.6	160.8	152.6	136.3	128.1	121.3	115.8	113.1	111.7	113.1
82.5°	110.4	106.3	104.9	99.5	88.6	84.5	79.0	74.9	74.9	74.9	74.9
85°	61.3	61.3	61.3	53.1	49.1	45.0	42.2	40.9	40.9	40.9	42.2
87.5°	25.9	25.9	21.8	21.8	20.4	17.7	16.4	16.4	17.7	17.7	19.1
90°	13.7	7.8	7.8	7.8	6.9	5.9	2.9	1.0	2.9	5.9	6.9
92.5°	148.9	88.2	75.4	62.7	45.1	30.4	19.6	13.7	19.6	30.4	45.1
95°	207.7	122.5	101.9	81.3	57.8	45.1	35.3	32.3	35.3	45.1	57.8
97.5°	197.9	130.3	112.6	95.0	74.5	62.7	53.9	53.9	53.9	62.7	74.5
100°	200.8	143.0	127.4	111.7	93.1	81.3	74.5	74.5	74.5	81.3	93.1
102.5°	210.6	159.7	145.0	130.3	112.7	101.9	96.0	94.1	96.0	101.9	112.7
105°	227.3	180.3	166.1	151.9	134.2	122.5	117.6	114.6	117.6	122.5	134.2
107.5°	244.9	201.8	187.6	173.4	156.8	144.0	139.1	137.2	139.1	144.0	156.8
110°	265.5	222.4	209.2	195.9	178.3	166.6	161.7	159.7	161.7	166.6	178.3

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.1	244.0	230.8	217.5	199.9	189.1	183.2	181.3	183.2	189.1	199.9
115°	305.7	266.5	253.2	240.0	221.4	211.6	204.8	201.8	204.8	211.6	221.4
117.5°	325.3	288.0	274.3	260.6	243.0	232.2	226.3	223.4	226.3	232.2	243.0
120°	345.8	308.6	294.9	281.2	264.5	253.8	246.9	244.9	246.9	253.8	264.5
122.5°	365.4	328.2	315.0	301.8	283.1	273.3	266.5	264.5	266.5	273.3	283.1
125°	383.1	347.8	334.1	320.4	301.8	291.0	285.1	281.2	285.1	291.0	301.8
127.5°	399.7	365.4	351.7	338.0	318.4	306.7	299.8	296.9	299.8	306.7	318.4
130°	416.4	383.1	368.9	354.7	336.0	321.4	313.5	309.6	313.5	321.4	336.0
132.5°	430.1	396.8	383.6	370.3	349.8	336.0	325.3	322.3	325.3	336.0	349.8
135°	442.8	410.5	397.8	385.0	364.5	347.8	338.0	334.1	338.0	347.8	364.5
137.5°	452.6	422.3	410.0	397.8	376.2	360.5	349.8	345.8	349.8	360.5	376.2
140°	462.4	433.0	421.2	409.5	389.0	372.3	361.5	358.6	361.5	372.3	389.0
142.5°	471.3	442.8	431.6	420.3	400.7	385.0	375.2	372.3	375.2	385.0	400.7
145°	477.1	451.7	440.9	430.1	411.5	397.8	388.0	385.0	388.0	397.8	411.5
147.5°	484.0	459.5	449.7	439.9	424.2	409.5	400.7	399.7	400.7	409.5	424.2
150°	488.9	467.3	458.0	448.7	434.0	422.3	414.4	413.4	414.4	422.3	434.0
152.5°	492.8	474.2	465.8	457.5	444.8	434.0	426.2	426.2	426.2	434.0	444.8
155°	496.7	480.1	472.8	465.4	454.6	444.8	438.9	437.9	438.9	444.8	454.6
157.5°	499.7	485.0	479.1	473.2	463.4	455.6	449.7	449.7	449.7	455.6	463.4
160°	501.6	489.9	484.5	479.1	471.3	464.4	460.5	460.5	460.5	464.4	471.3
162.5°	503.6	492.8	488.9	485.0	478.1	472.2	469.3	470.3	469.3	472.2	478.1
165°	503.6	494.8	491.8	488.9	484.0	479.1	477.1	477.1	477.1	479.1	484.0
167.5°	503.6	496.7	494.2	491.8	488.9	485.0	484.0	485.0	484.0	485.0	488.9
170°	502.6	497.7	496.2	494.8	492.8	489.9	488.9	489.9	488.9	489.9	492.8
172.5°	501.6	498.7	497.7	496.7	495.7	493.8	493.8	494.8	493.8	493.8	495.7
175°	500.6	498.7	498.7	498.7	497.7	496.7	496.7	497.7	496.7	496.7	497.7
177.5°	499.7	498.7	498.7	498.7	498.7	497.7	498.7	499.7	498.7	497.7	498.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1620.0	1614.6	1617.3	1603.7	1591.4	1573.7	1558.7	1556.0	1553.3	1561.4	1556.0
5°	1573.7	1566.9	1560.1	1543.7	1519.2	1504.2	1482.4	1481.0	1472.9	1460.6	1463.3
7.5°	1523.3	1519.2	1509.7	1483.8	1462.0	1436.1	1418.4	1403.4	1396.6	1385.7	1381.6
10°	1482.4	1467.4	1459.2	1430.6	1404.7	1377.5	1354.3	1343.4	1331.2	1321.6	1314.8
12.5°	1426.5	1422.5	1399.3	1376.1	1354.3	1323.0	1305.3	1273.9	1257.6	1265.8	1263.0
15°	1389.8	1370.7	1365.2	1332.5	1295.7	1275.3	1242.6	1222.2	1215.4	1203.1	1188.1
17.5°	1340.7	1328.4	1309.4	1279.4	1237.2	1208.5	1185.4	1166.3	1158.1	1141.8	1129.5
20°	1294.4	1273.9	1259.0	1231.7	1190.8	1154.0	1125.4	1113.2	1092.7	1079.1	1072.3
22.5°	1252.1	1237.2	1215.4	1174.5	1139.1	1103.6	1069.6	1051.9	1032.8	1024.6	1013.7
25°	1200.4	1175.8	1160.9	1115.9	1077.7	1049.1	1017.8	994.6	983.7	970.1	967.4
27.5°	1150.0	1126.8	1109.1	1069.6	1023.2	986.5	967.4	951.0	932.0	932.0	925.1
30°	1099.5	1083.2	1055.9	1017.8	974.2	938.8	917.0	902.0	895.2	889.7	888.4
32.5°	1049.1	1027.3	1011.0	959.2	926.5	893.8	877.5	865.2	857.0	855.7	857.0
35°	997.4	972.8	956.5	910.2	877.5	847.5	840.7	829.8	825.7	824.3	831.1
37.5°	942.9	923.8	903.3	865.2	828.4	810.7	797.1	793.0	791.6	799.8	802.5
40°	892.4	876.1	857.0	816.1	788.9	769.8	763.0	758.9	764.4	772.5	776.6
42.5°	844.8	821.6	806.6	769.8	745.3	734.4	726.2	726.2	731.7	741.2	748.0
45°	794.3	776.6	761.6	728.9	707.1	694.9	693.5	694.9	701.7	708.5	716.7
47.5°	745.3	727.6	711.2	684.0	664.9	658.1	656.7	658.1	669.0	678.5	688.1
50°	700.3	681.3	666.3	640.4	625.4	617.2	618.6	625.4	633.6	647.2	659.5
52.5°	647.2	633.6	619.9	596.8	583.2	577.7	581.8	587.2	602.2	611.8	626.8
55°	595.4	583.2	572.3	554.5	543.6	539.6	542.3	550.5	562.7	579.1	596.8
57.5°	547.7	534.1	523.2	510.9	498.7	500.0	501.4	512.3	527.3	542.3	562.7
60°	494.6	486.4	476.9	461.9	456.4	456.4	460.5	472.8	486.4	510.9	528.7
62.5°	446.9	436.0	429.2	419.7	411.5	412.8	422.4	433.3	449.6	470.1	493.2
65°	397.9	385.6	380.1	372.0	369.2	370.6	377.4	393.8	411.5	429.2	451.0
67.5°	343.4	339.3	333.8	325.6	328.4	329.7	336.5	350.2	369.2	387.0	411.5
70°	297.0	288.9	287.5	280.7	280.7	284.8	298.4	307.9	325.6	344.7	370.6
72.5°	248.0	241.2	241.2	235.7	239.8	243.9	250.7	264.3	280.7	299.8	321.6
75°	197.6	194.8	197.6	194.8	194.8	201.7	209.8	220.7	238.4	258.9	276.6
77.5°	152.6	152.6	151.2	155.3	155.3	159.4	170.3	181.2	194.8	211.2	230.3
80°	111.7	111.7	111.7	115.8	119.9	119.9	126.7	140.3	152.6	163.5	181.2
82.5°	76.3	76.3	76.3	79.0	84.5	84.5	92.7	100.8	114.5	124.0	132.2
85°	46.3	46.3	45.0	47.7	49.1	53.1	60.0	65.4	72.2	80.4	88.6
87.5°	20.4	20.4	21.8	23.2	24.5	27.3	30.0	32.7	39.5	42.2	46.3
90°	7.8	7.8	7.8	13.7	13.7	15.7	17.6	16.7	17.6	18.6	19.6
92.5°	62.7	75.4	88.2	148.9	244.0	336.0	384.1	319.4	236.1	176.4	139.1
95°	81.3	101.9	122.5	207.7	368.4	602.5	798.5	821.0	726.0	574.1	442.8
97.5°	95.0	112.6	130.3	197.9	336.0	577.1	854.3	1029.7	1045.4	969.9	862.2
100°	111.7	127.4	143.0	200.8	311.6	511.4	787.7	1038.5	1181.6	1201.2	1153.1
102.5°	130.3	145.0	159.7	210.6	304.7	467.3	704.4	965.0	1174.7	1291.3	1320.7
105°	151.9	166.1	180.3	227.3	308.6	445.8	642.7	872.9	1097.3	1266.8	1363.8
107.5°	173.4	187.6	201.8	244.9	320.4	439.9	602.5	797.5	1002.3	1185.5	1320.7
110°	195.9	209.2	222.4	265.5	334.1	441.9	583.9	743.6	918.0	1087.5	1229.6

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	217.5	230.8	244.0	285.1	348.8	447.7	575.1	713.2	856.3	1001.3	1133.5
115°	240.0	253.2	266.5	305.7	364.5	455.6	573.1	696.6	819.1	939.6	1054.2
117.5°	260.6	274.3	288.0	325.3	380.1	463.4	572.2	687.8	797.5	899.4	992.5
120°	281.2	294.9	308.6	345.8	396.8	472.2	572.2	680.9	783.8	874.9	953.3
122.5°	301.8	315.0	328.2	365.4	412.5	481.0	571.2	673.1	772.0	859.2	928.8
125°	320.4	334.1	347.8	383.1	428.1	489.9	570.2	664.3	758.3	842.6	910.2
127.5°	338.0	351.7	365.4	399.7	441.9	496.7	568.2	652.5	742.6	824.0	891.6
130°	354.7	368.9	383.1	416.4	454.6	504.6	567.3	641.7	723.0	800.4	867.1
132.5°	370.3	383.6	396.8	430.1	467.3	511.4	566.3	631.9	702.5	774.0	838.7
135°	385.0	397.8	410.5	442.8	478.1	518.3	565.3	622.1	683.9	747.5	807.3
137.5°	397.8	410.0	422.3	452.6	485.9	522.2	565.3	613.3	666.2	722.1	774.0
140°	409.5	421.2	433.0	462.4	493.8	527.1	564.3	606.5	651.5	697.6	741.7
142.5°	420.3	431.6	442.8	471.3	499.7	531.0	564.3	600.6	637.8	677.0	713.2
145°	430.1	440.9	451.7	477.1	503.6	532.0	562.4	593.7	625.1	658.4	687.8
147.5°	439.9	449.7	459.5	484.0	507.5	533.0	559.4	587.8	614.3	641.7	666.2
150°	448.7	458.0	467.3	488.9	510.4	533.0	556.5	581.0	604.5	627.0	646.6
152.5°	457.5	465.8	474.2	492.8	512.4	531.0	551.6	573.1	593.7	612.3	630.0
155°	465.4	472.8	480.1	496.7	513.4	529.1	546.7	565.3	582.9	598.6	613.3
157.5°	473.2	479.1	485.0	499.7	513.4	527.1	541.8	557.5	571.2	584.9	597.6
160°	479.1	484.5	489.9	501.6	513.4	524.2	535.9	548.6	560.4	571.2	582.0
162.5°	485.0	488.9	492.8	503.6	513.4	521.2	530.0	540.8	549.6	558.4	566.3
165°	488.9	491.8	494.8	503.6	511.4	517.3	524.2	532.0	539.8	545.7	552.6
167.5°	491.8	494.2	496.7	503.6	509.5	513.4	518.3	524.2	530.0	534.9	540.8
170°	494.8	496.2	497.7	502.6	507.5	509.5	512.4	516.3	521.2	524.2	528.1
172.5°	496.7	497.7	498.7	501.6	505.5	505.5	506.5	509.5	513.4	515.3	517.3
175°	498.7	498.7	498.7	500.6	503.6	502.6	502.6	504.6	506.5	507.5	509.5
177.5°	498.7	498.7	498.7	499.7	501.6	499.7	499.7	500.6	501.6	502.6	502.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1551.9	1550.5	1543.7	1546.4	1538.3	1541.0	1545.1	1546.4	1551.9	1547.8	1546.4
5°	1456.5	1453.8	1449.7	1445.6	1444.3	1449.7	1440.2	1442.9	1445.6	1449.7	1455.2
7.5°	1378.9	1377.5	1373.4	1366.6	1363.9	1361.1	1362.5	1372.0	1370.7	1369.3	1378.9
10°	1308.0	1309.4	1301.2	1299.8	1291.7	1290.3	1291.7	1294.4	1298.5	1303.9	1305.3
12.5°	1234.4	1252.1	1237.2	1231.7	1219.4	1226.3	1229.0	1216.7	1223.5	1227.6	1248.1
15°	1188.1	1179.9	1170.4	1170.4	1164.9	1162.2	1155.4	1164.9	1170.4	1178.6	1175.8
17.5°	1124.1	1110.4	1105.0	1099.5	1100.9	1106.4	1091.4	1113.2	1113.2	1117.3	1110.4
20°	1068.2	1057.3	1050.5	1047.8	1043.7	1041.0	1039.6	1045.0	1053.2	1055.9	1062.8
22.5°	1009.6	1009.6	998.7	994.6	991.9	987.8	994.6	990.5	996.0	1001.4	1012.3
25°	960.6	960.6	956.5	951.0	946.9	944.2	948.3	946.9	951.0	957.8	960.6
27.5°	921.1	917.0	915.6	914.2	912.9	914.2	912.9	917.0	921.1	922.4	919.7
30°	887.0	882.9	884.3	884.3	885.6	884.3	882.9	887.0	888.4	885.6	887.0
32.5°	855.7	855.7	858.4	859.7	859.7	861.1	862.5	859.7	861.1	857.0	858.4
35°	829.8	832.5	835.2	836.6	837.9	836.6	839.3	837.9	835.2	832.5	831.1
37.5°	803.9	806.6	812.1	813.4	817.5	818.9	816.1	816.1	814.8	809.3	806.6
40°	776.6	779.4	786.2	790.3	793.0	797.1	794.3	794.3	788.9	783.4	779.4
42.5°	750.7	756.2	763.0	767.1	772.5	772.5	772.5	769.8	763.0	757.6	753.5
45°	724.9	726.2	735.8	742.6	748.0	748.0	748.0	743.9	739.8	728.9	723.5
47.5°	696.2	700.3	711.2	718.0	723.5	724.9	724.9	720.8	712.6	703.1	696.2
50°	664.9	671.7	684.0	693.5	700.3	703.1	699.0	696.2	686.7	675.8	667.6
52.5°	634.9	643.1	658.1	666.3	675.8	677.2	675.8	671.7	660.8	645.8	639.0
55°	605.0	611.8	628.1	641.7	649.9	652.6	649.9	643.1	629.5	614.5	607.7
57.5°	572.3	581.8	599.5	613.1	622.7	624.0	621.3	614.5	603.6	584.5	575.0
60°	538.2	550.5	568.2	581.8	594.1	595.4	592.7	583.2	569.5	550.5	542.3
62.5°	504.1	513.7	534.1	549.1	558.6	565.4	560.0	550.5	536.8	517.8	505.5
65°	464.6	478.2	496.0	509.6	520.5	521.8	519.1	510.9	496.0	475.5	466.0
67.5°	426.5	436.0	453.7	471.4	475.5	479.6	475.5	467.3	455.1	437.4	423.7
70°	380.1	388.3	410.1	422.4	427.8	431.9	429.2	421.0	410.1	393.8	382.9
72.5°	333.8	340.6	361.1	370.6	381.5	380.1	378.8	373.3	358.3	347.4	340.6
75°	284.8	292.9	306.6	318.8	322.9	322.9	322.9	318.8	309.3	291.6	284.8
77.5°	239.8	243.9	254.8	261.6	265.7	267.1	265.7	258.9	253.4	241.2	237.1
80°	183.9	194.8	203.0	204.4	209.8	209.8	209.8	207.1	201.7	189.4	188.0
82.5°	139.0	141.7	149.9	154.0	156.7	155.3	155.3	149.9	148.5	141.7	139.0
85°	94.0	98.1	96.7	102.2	103.6	100.8	100.8	103.6	96.7	98.1	94.0
87.5°	51.8	51.8	54.5	53.1	58.6	58.6	55.9	57.2	54.5	53.1	51.8
90°	19.6	19.6	20.6	21.6	20.6	20.6	20.6	21.6	20.6	19.6	19.6
92.5°	126.8	114.6	99.9	93.1	89.2	89.2	89.2	93.1	99.9	114.6	126.8
95°	395.3	347.8	299.8	269.4	251.8	239.1	251.8	269.4	299.8	347.8	395.3
97.5°	807.3	752.4	685.8	627.0	597.6	574.1	597.6	627.0	685.8	752.4	807.3
100°	1116.8	1080.6	995.4	935.6	906.3	898.4	906.3	935.6	995.4	1080.6	1116.8
102.5°	1310.9	1301.1	1257.0	1217.8	1186.5	1180.6	1186.5	1217.8	1257.0	1301.1	1310.9
105°	1383.9	1404.0	1405.9	1398.1	1384.4	1378.5	1384.4	1398.1	1405.9	1404.0	1383.9
107.5°	1361.8	1403.0	1446.1	1463.7	1471.6	1472.5	1471.6	1463.7	1446.1	1403.0	1361.8
110°	1283.4	1337.3	1406.9	1448.0	1465.7	1474.5	1465.7	1448.0	1406.9	1337.3	1283.4

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1187.4	1241.3	1322.6	1374.6	1401.0	1416.7	1401.0	1374.6	1322.6	1241.3	1187.4
115°	1101.2	1148.2	1225.6	1284.4	1315.8	1323.6	1315.8	1284.4	1225.6	1148.2	1101.2
117.5°	1033.6	1074.8	1143.3	1194.3	1227.6	1232.5	1227.6	1194.3	1143.3	1074.8	1033.6
120°	988.0	1022.8	1078.7	1121.8	1147.3	1158.0	1147.3	1121.8	1078.7	1022.8	988.0
122.5°	958.2	987.6	1032.6	1067.9	1088.5	1099.3	1088.5	1067.9	1032.6	987.6	958.2
125°	937.2	964.1	1003.2	1031.7	1050.3	1056.2	1050.3	1031.7	1003.2	964.1	937.2
127.5°	917.0	942.5	981.7	1007.2	1022.8	1028.7	1022.8	1007.2	981.7	942.5	917.0
130°	893.0	919.0	959.2	983.7	999.3	1005.2	999.3	983.7	959.2	919.0	893.0
132.5°	864.6	890.6	929.8	958.2	972.9	978.8	972.9	958.2	929.8	890.6	864.6
135°	831.8	856.3	895.5	922.9	938.6	944.5	938.6	922.9	895.5	856.3	831.8
137.5°	796.6	819.1	856.3	884.7	897.4	904.3	897.4	884.7	856.3	819.1	796.6
140°	762.2	782.8	817.1	838.7	852.4	860.2	852.4	838.7	817.1	782.8	762.2
142.5°	730.4	747.5	776.9	796.5	808.3	813.2	808.3	796.5	776.9	747.5	730.4
145°	701.5	715.2	739.7	756.4	766.2	771.0	766.2	756.4	739.7	715.2	701.5
147.5°	677.5	688.8	707.4	722.1	729.9	731.9	729.9	722.1	707.4	688.8	677.5
150°	655.4	664.3	679.9	692.7	698.5	699.5	698.5	692.7	679.9	664.3	655.4
152.5°	636.8	643.7	656.4	666.2	669.2	670.1	669.2	666.2	656.4	643.7	636.8
155°	619.2	625.1	634.9	642.7	645.6	645.6	645.6	642.7	634.9	625.1	619.2
157.5°	602.5	607.4	615.3	621.1	623.1	623.1	623.1	621.1	615.3	607.4	602.5
160°	585.9	589.8	595.7	601.6	602.5	602.5	602.5	601.6	595.7	589.8	585.9
162.5°	569.7	573.1	577.1	582.9	583.9	582.9	583.9	582.9	577.1	573.1	569.7
165°	555.0	557.5	561.4	565.3	564.3	563.3	564.3	565.3	561.4	557.5	555.0
167.5°	542.3	543.8	545.7	548.6	548.6	547.7	548.6	548.6	545.7	543.8	542.3
170°	529.6	531.0	533.0	534.0	533.0	533.0	533.0	534.0	533.0	531.0	529.6
172.5°	518.3	519.3	520.2	521.2	520.2	518.3	520.2	521.2	520.2	519.3	518.3
175°	509.5	509.5	509.5	511.4	509.5	507.5	509.5	511.4	509.5	509.5	509.5
177.5°	503.1	503.6	502.6	503.6	501.6	499.7	501.6	503.6	502.6	503.6	503.1
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1546.4	1554.6	1546.4	1551.9	1554.6	1561.4	1564.2	1576.4	1580.5	1590.0	1590.0
5°	1453.8	1457.9	1459.2	1464.7	1470.1	1483.8	1493.3	1511.0	1531.5	1534.2	1546.4
7.5°	1378.9	1385.7	1396.6	1392.5	1402.0	1422.5	1434.7	1456.5	1477.0	1487.9	1502.8
10°	1312.1	1320.3	1324.4	1328.4	1346.2	1363.9	1382.9	1397.9	1425.2	1441.5	1453.8
12.5°	1257.6	1250.8	1259.0	1273.9	1294.4	1305.3	1331.2	1354.3	1374.8	1392.5	1403.4
15°	1186.7	1192.2	1200.4	1226.3	1231.7	1259.0	1268.5	1294.4	1332.5	1348.9	1362.5
17.5°	1118.6	1136.3	1152.7	1162.2	1178.6	1200.4	1227.6	1256.2	1280.8	1299.8	1316.2
20°	1064.1	1081.8	1091.4	1098.2	1114.5	1144.5	1170.4	1205.8	1237.2	1252.1	1273.9
22.5°	1020.5	1020.5	1034.1	1054.6	1064.1	1092.7	1114.5	1152.7	1186.7	1205.8	1226.3
25°	966.0	974.2	985.1	1002.8	1016.4	1039.6	1070.9	1103.6	1140.4	1156.8	1182.7
27.5°	921.1	930.6	945.6	949.7	963.3	983.7	1016.4	1051.9	1090.0	1107.7	1129.5
30°	887.0	892.4	897.9	906.1	918.3	936.0	963.3	994.6	1041.0	1054.6	1081.8
32.5°	857.0	859.7	862.5	869.3	876.1	893.8	915.6	949.7	987.8	1008.3	1032.8
35°	829.8	827.0	828.4	832.5	839.3	846.1	869.3	897.9	933.3	957.8	976.9
37.5°	803.9	798.4	797.1	797.1	799.8	808.0	825.7	850.2	888.4	908.8	927.9
40°	775.3	769.8	767.1	765.7	764.4	769.8	783.4	808.0	837.9	857.0	878.8
42.5°	748.0	742.6	735.8	734.4	731.7	734.4	743.9	767.1	793.0	812.1	829.8
45°	720.8	711.2	703.1	697.6	699.0	694.9	701.7	719.4	749.4	761.6	779.4
47.5°	690.8	679.9	669.0	663.5	658.1	660.8	663.5	678.5	704.4	716.7	734.4
50°	662.2	647.2	634.9	628.1	624.0	621.3	624.0	639.0	658.1	669.0	684.0
52.5°	629.5	614.5	602.2	591.3	585.9	581.8	583.2	596.8	614.5	625.4	640.4
55°	599.5	580.4	564.1	550.5	546.4	545.0	543.6	553.2	568.2	579.1	591.3
57.5°	565.4	546.4	528.7	512.3	504.1	502.8	502.8	505.5	524.6	532.7	539.6
60°	531.4	510.9	491.9	476.9	464.6	460.5	459.2	464.6	474.2	482.3	491.9
62.5°	493.2	472.8	449.6	436.0	423.7	412.8	416.9	418.3	431.9	436.0	444.2
65°	456.4	433.3	414.2	392.4	378.8	372.0	369.2	372.0	382.9	384.2	389.7
67.5°	414.2	392.4	369.2	354.3	342.0	329.7	327.0	327.0	332.5	336.5	343.4
70°	373.3	351.5	325.6	309.3	297.0	286.1	282.0	280.7	284.8	287.5	294.3
72.5°	325.6	303.8	284.8	267.1	252.1	243.9	239.8	237.1	241.2	243.9	245.3
75°	275.2	257.5	238.4	220.7	211.2	203.0	197.6	193.5	196.2	196.2	196.2
77.5°	227.5	209.8	194.8	182.6	170.3	160.8	156.7	152.6	154.0	154.0	156.7
80°	177.1	164.9	152.6	141.7	130.8	122.6	119.9	115.8	113.1	111.7	111.7
82.5°	130.8	121.3	110.4	100.8	95.4	87.2	84.5	79.0	79.0	77.7	77.7
85°	87.2	81.8	70.9	64.0	60.0	55.9	53.1	50.4	46.3	46.3	45.0
87.5°	46.3	43.6	40.9	32.7	32.7	28.6	27.3	25.9	21.8	23.2	23.2
90°	19.6	18.6	17.6	16.7	17.6	15.7	13.7	13.7	7.8	7.8	7.8
92.5°	139.1	176.4	236.1	319.4	384.1	336.0	244.0	148.9	88.2	75.4	62.7
95°	442.8	574.1	726.0	821.0	798.5	602.5	368.4	207.7	122.5	101.9	81.3
97.5°	862.2	969.9	1045.4	1029.7	854.3	577.1	336.0	197.9	130.3	112.6	95.0
100°	1153.1	1201.2	1181.6	1038.5	787.7	511.4	311.6	200.8	143.0	127.4	111.7
102.5°	1320.7	1291.3	1174.7	965.0	704.4	467.3	304.7	210.6	159.7	145.0	130.3
105°	1363.8	1266.8	1097.3	872.9	642.7	445.8	308.6	227.3	180.3	166.1	151.9
107.5°	1320.7	1185.5	1002.3	797.5	602.5	439.9	320.4	244.9	201.8	187.6	173.4
110°	1229.6	1087.5	918.0	743.6	583.9	441.9	334.1	265.5	222.4	209.2	195.9

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1133.5	1001.3	856.3	713.2	575.1	447.7	348.8	285.1	244.0	230.8	217.5
115°	1054.2	939.6	819.1	696.6	573.1	455.6	364.5	305.7	266.5	253.2	240.0
117.5°	992.5	899.4	797.5	687.8	572.2	463.4	380.1	325.3	288.0	274.3	260.6
120°	953.3	874.9	783.8	680.9	572.2	472.2	396.8	345.8	308.6	294.9	281.2
122.5°	928.8	859.2	772.0	673.1	571.2	481.0	412.5	365.4	328.2	315.0	301.8
125°	910.2	842.6	758.3	664.3	570.2	489.9	428.1	383.1	347.8	334.1	320.4
127.5°	891.6	824.0	742.6	652.5	568.2	496.7	441.9	399.7	365.4	351.7	338.0
130°	867.1	800.4	723.0	641.7	567.3	504.6	454.6	416.4	383.1	368.9	354.7
132.5°	838.7	774.0	702.5	631.9	566.3	511.4	467.3	430.1	396.8	383.6	370.3
135°	807.3	747.5	683.9	622.1	565.3	518.3	478.1	442.8	410.5	397.8	385.0
137.5°	774.0	722.1	666.2	613.3	565.3	522.2	485.9	452.6	422.3	410.0	397.8
140°	741.7	697.6	651.5	606.5	564.3	527.1	493.8	462.4	433.0	421.2	409.5
142.5°	713.2	677.0	637.8	600.6	564.3	531.0	499.7	471.3	442.8	431.6	420.3
145°	687.8	658.4	625.1	593.7	562.4	532.0	503.6	477.1	451.7	440.9	430.1
147.5°	666.2	641.7	614.3	587.8	559.4	533.0	507.5	484.0	459.5	449.7	439.9
150°	646.6	627.0	604.5	581.0	556.5	533.0	510.4	488.9	467.3	458.0	448.7
152.5°	630.0	612.3	593.7	573.1	551.6	531.0	512.4	492.8	474.2	465.8	457.5
155°	613.3	598.6	582.9	565.3	546.7	529.1	513.4	496.7	480.1	472.8	465.4
157.5°	597.6	584.9	571.2	557.5	541.8	527.1	513.4	499.7	485.0	479.1	473.2
160°	582.0	571.2	560.4	548.6	535.9	524.2	513.4	501.6	489.9	484.5	479.1
162.5°	566.3	558.4	549.6	540.8	530.0	521.2	513.4	503.6	492.8	488.9	485.0
165°	552.6	545.7	539.8	532.0	524.2	517.3	511.4	503.6	494.8	491.8	488.9
167.5°	540.8	534.9	530.0	524.2	518.3	513.4	509.5	503.6	496.7	494.2	491.8
170°	528.1	524.2	521.2	516.3	512.4	509.5	507.5	502.6	497.7	496.2	494.8
172.5°	517.3	515.3	513.4	509.5	506.5	505.5	505.5	501.6	498.7	497.7	496.7
175°	509.5	507.5	506.5	504.6	502.6	502.6	503.6	500.6	498.7	498.7	498.7
177.5°	502.6	502.6	501.6	500.6	499.7	499.7	501.6	499.7	498.7	498.7	498.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1644.5	1644.5	1644.5	1644.5
2.5°	1599.6	1613.2	1625.5	1644.5
5°	1564.2	1583.2	1609.1	1637.7
7.5°	1523.3	1553.3	1587.3	1626.8
10°	1485.1	1519.2	1562.8	1610.5
12.5°	1445.6	1486.5	1534.2	1586.0
15°	1400.7	1441.5	1494.7	1564.2
17.5°	1359.8	1408.8	1466.1	1539.6
20°	1312.1	1358.4	1421.1	1505.6
22.5°	1269.9	1323.0	1392.5	1466.1
25°	1223.5	1269.9	1339.3	1427.9
27.5°	1177.2	1234.4	1301.2	1387.0
30°	1132.2	1179.9	1252.1	1342.1
32.5°	1083.2	1140.4	1207.2	1291.7
35°	1030.1	1084.6	1147.2	1238.5
37.5°	982.4	1035.5	1099.5	1179.9
40°	929.2	985.1	1043.7	1124.1
42.5°	877.5	927.9	986.5	1060.0
45°	827.0	870.6	923.8	987.8
47.5°	775.3	812.1	861.1	918.3
50°	719.4	758.9	795.7	843.4
52.5°	667.6	701.7	731.7	771.2
55°	617.2	640.4	664.9	694.9
57.5°	564.1	581.8	599.5	630.8
60°	510.9	527.3	536.8	557.3
62.5°	459.2	466.0	478.2	490.5
65°	401.9	411.5	418.3	433.3
67.5°	350.2	354.3	361.1	370.6
70°	295.7	305.2	307.9	314.7
72.5°	249.3	253.4	256.2	257.5
75°	197.6	201.7	204.4	212.6
77.5°	155.3	154.0	159.4	160.8
80°	114.5	110.4	111.7	117.2
82.5°	74.9	76.3	74.9	74.9
85°	46.3	45.0	42.2	43.6
87.5°	20.4	20.4	19.1	19.1
90°	6.9	5.9	2.9	1.0
92.5°	45.1	30.4	19.6	13.7
95°	57.8	45.1	35.3	32.3
97.5°	74.5	62.7	53.9	53.9
100°	93.1	81.3	74.5	74.5
102.5°	112.7	101.9	96.0	94.1
105°	134.2	122.5	117.6	114.6
107.5°	156.8	144.0	139.1	137.2
110°	178.3	166.6	161.7	159.7



TEST NUMBER: P1000511

CATALOG NUMBER: SA4XXDIP-B1020D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	199.9	189.1	183.2	181.3
115°	221.4	211.6	204.8	201.8
117.5°	243.0	232.2	226.3	223.4
120°	264.5	253.8	246.9	244.9
122.5°	283.1	273.3	266.5	264.5
125°	301.8	291.0	285.1	281.2
127.5°	318.4	306.7	299.8	296.9
130°	336.0	321.4	313.5	309.6
132.5°	349.8	336.0	325.3	322.3
135°	364.5	347.8	338.0	334.1
137.5°	376.2	360.5	349.8	345.8
140°	389.0	372.3	361.5	358.6
142.5°	400.7	385.0	375.2	372.3
145°	411.5	397.8	388.0	385.0
147.5°	424.2	409.5	400.7	399.7
150°	434.0	422.3	414.4	413.4
152.5°	444.8	434.0	426.2	426.2
155°	454.6	444.8	438.9	437.9
157.5°	463.4	455.6	449.7	449.7
160°	471.3	464.4	460.5	460.5
162.5°	478.1	472.2	469.3	470.3
165°	484.0	479.1	477.1	477.1
167.5°	488.9	485.0	484.0	485.0
170°	492.8	489.9	488.9	489.9
172.5°	495.7	493.8	493.8	494.8
175°	497.7	496.7	496.7	497.7
177.5°	498.7	497.7	498.7	499.7
180°	498.7	498.7	498.7	498.7

(END OF REPORT)