

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000919

Luminaire Tested: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000919
REPORT IS A COMBINATION OF REPORTS P995532 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9267.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	25
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	25	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15145	15145	15145	15145
5°	15107	17375	15194	13055
10°	14994	20271	15108	11454
15°	14814	23369	14917	10249
20°	14622	25340	14728	9188
25°	14342	25050	14479	8407
30°	14069	20705	14240	8003
35°	13684	15429	13835	7759
40°	13236	11623	13364	7640
45°	12552	9328	12707	7477
50°	11734	7859	11904	7400
55°	10773	6841	10942	7314
60°	9837	6024	10126	7192
65°	8961	5183	9045	6892
70°	7931	4265	8101	6346
75°	6916	3276	6873	5392
80°	5441	2152	5380	4094
85°	3580	968	3362	2387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 19584 cd/sqm

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.7	2.0
10°-20°	557.9	6.0
20°-30°	886.3	9.6
30°-40°	984.9	10.6
40°-50°	895.6	9.7
50°-60°	731.9	7.9
60°-70°	522.4	5.6
70°-80°	287.5	3.1
80°-90°	79.9	0.9
90°-100°	412.0	4.4
100°-110°	860.0	9.3
110°-120°	764.5	8.2
120°-130°	643.5	6.9
130°-140°	536.9	5.8
140°-150°	409.9	4.4
150°-160°	288.2	3.1
160°-170°	169.5	1.8
170°-180°	55.1	0.6
0°-30°	1625.0	17.5
0°-40°	2609.9	28.2
0°-60°	4237.4	45.7
0°-90°	5127.2	55.3
90°-120°	2036.5	22.0
90°-150°	3626.9	39.1
90°-180°	4140.0	44.7
0°-180°	9267.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1857	1857	1857	1857	1857	
5°	1850	2179	1860	1637	1850	176
15°	1766	2993	1779	1313	1766	498
25°	1613	3178	1628	1066	1613	743
35°	1399	1879	1414	945	1399	874
45°	1116	1054	1129	845	1116	860
55°	785	689	797	737	785	706
65°	489	443	494	589	489	483
75°	240	222	238	365	240	252
85°	49	46	46	114	49	57
90°	1	24	1	24	1	5
95°	37	272	37	272	37	40
105°	131	1571	131	1571	131	139
115°	230	1509	230	1509	230	228
125°	320	1204	320	1204	320	286
135°	381	1076	381	1076	381	294
145°	439	879	439	879	439	275
155°	499	736	499	736	499	230
165°	544	642	544	642	544	154
175°	567	578	567	578	567	54
180°	568	568	568	568	568	

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1857.3	1875.7	1883.4	1889.6	1909.6	1915.7	1917.3	1926.5	1934.2	1935.7	1935.7
5°	1849.6	1878.8	1901.9	1923.4	1955.7	1969.6	1986.5	2005.0	2029.6	2045.0	2052.7
7.5°	1837.3	1880.4	1915.7	1952.7	1997.3	2025.0	2040.4	2089.6	2123.5	2151.2	2185.0
10°	1818.8	1874.2	1925.0	1978.8	2041.9	2075.8	2109.6	2169.6	2217.3	2271.2	2314.3
12.5°	1791.1	1863.4	1925.0	2000.4	2078.8	2118.9	2158.9	2263.5	2318.9	2366.6	2443.5
15°	1766.5	1838.8	1926.5	2003.5	2100.4	2160.4	2218.9	2286.6	2374.3	2477.4	2551.2
17.5°	1738.8	1829.6	1911.1	2018.8	2126.5	2183.5	2231.2	2335.8	2458.9	2560.5	2628.2
20°	1700.3	1792.6	1900.4	2014.2	2141.9	2186.6	2249.6	2389.7	2500.5	2600.5	2711.3
22.5°	1655.7	1763.4	1877.3	1986.5	2118.9	2212.7	2282.0	2405.1	2538.9	2654.3	2779.0
25°	1612.6	1729.6	1829.6	1978.8	2118.9	2181.9	2260.4	2406.6	2552.8	2692.8	2820.5
27.5°	1566.4	1675.7	1811.1	1929.6	2088.1	2157.3	2242.0	2402.0	2557.4	2697.4	2834.4
30°	1515.7	1632.6	1744.9	1885.0	2038.8	2128.1	2206.6	2380.4	2538.9	2685.1	2812.8
32.5°	1458.7	1569.5	1689.5	1821.9	1983.4	2074.2	2172.7	2351.2	2520.5	2646.6	2745.1
35°	1398.7	1511.1	1615.7	1751.1	1917.3	2008.1	2103.5	2300.4	2468.2	2571.2	2628.2
37.5°	1332.6	1438.7	1541.8	1675.7	1841.9	1938.8	2035.8	2226.6	2385.1	2471.2	2455.8
40°	1269.5	1364.9	1460.3	1586.4	1760.3	1863.4	1948.1	2140.4	2278.9	2315.8	2265.0
42.5°	1197.1	1278.7	1371.0	1500.3	1669.5	1766.5	1872.7	2048.1	2151.2	2135.8	2049.6
45°	1115.6	1187.9	1280.2	1401.8	1574.1	1674.2	1763.4	1929.6	2005.0	1966.5	1809.6
47.5°	1037.1	1107.9	1183.3	1304.9	1472.6	1557.2	1648.0	1797.3	1840.3	1758.8	1601.8
50°	952.5	1011.0	1089.4	1204.8	1361.8	1451.0	1526.4	1646.5	1661.8	1561.8	1398.7
52.5°	870.9	920.2	995.6	1109.4	1255.6	1326.4	1400.3	1506.4	1494.1	1391.0	1234.1
55°	784.8	830.9	900.2	1004.8	1134.1	1201.8	1264.9	1358.7	1332.6	1226.4	1089.4
57.5°	712.4	744.8	812.5	909.4	1015.6	1089.4	1143.3	1217.1	1177.1	1071.0	943.3
60°	629.3	669.4	726.3	804.8	909.4	958.6	1006.3	1055.6	1027.9	926.3	812.5
62.5°	553.9	584.7	634.0	709.4	790.9	835.5	886.3	917.1	889.4	795.5	700.1
65°	489.3	513.9	552.4	614.0	692.4	729.4	758.6	787.8	764.8	677.0	607.8
67.5°	418.5	440.1	472.4	521.6	587.8	614.0	641.7	661.7	635.5	577.0	509.3
70°	355.5	370.8	401.6	438.5	484.7	509.3	532.4	552.4	529.3	480.1	429.3
72.5°	290.8	303.1	330.8	357.0	398.5	415.5	432.4	447.8	440.1	393.9	352.4
75°	240.0	244.7	263.1	284.7	310.8	329.3	341.6	350.8	344.7	307.7	281.6
77.5°	181.6	187.7	201.6	218.5	241.6	252.4	260.0	269.3	261.6	232.4	213.9
80°	132.3	133.9	141.6	157.0	172.3	173.9	181.6	193.9	189.3	169.3	155.4
82.5°	84.6	89.2	92.3	101.6	112.3	115.4	120.0	123.1	121.6	109.3	104.6
85°	49.2	49.2	52.3	58.5	61.5	66.2	67.7	69.2	72.3	64.6	60.0
87.5°	21.5	23.1	23.1	24.6	27.7	27.7	29.2	30.8	32.3	30.8	26.2
90°	1.1	3.4	6.7	7.8	8.9	8.9	8.9	15.6	15.6	17.9	20.1
92.5°	15.6	22.3	34.6	51.4	71.5	86.0	100.5	169.7	278.1	383.0	437.7
95°	36.9	40.2	51.4	65.9	92.7	116.2	139.6	236.7	419.9	686.8	910.1
97.5°	61.4	61.4	71.5	84.9	108.3	128.4	148.5	225.6	383.0	657.7	973.8
100°	84.9	84.9	92.7	106.1	127.3	145.2	163.0	228.9	355.1	582.9	897.8
102.5°	107.2	109.4	116.1	128.4	148.5	165.2	182.0	240.1	347.3	532.7	802.9
105°	130.7	134.0	139.6	153.0	173.1	189.3	205.5	259.1	351.8	508.1	732.5
107.5°	156.3	158.6	164.2	178.7	197.7	213.8	230.0	279.2	365.2	501.4	686.8
110°	182.0	184.3	189.8	203.2	223.3	238.4	253.5	302.6	380.8	503.6	665.5

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	206.6	208.8	215.5	227.8	247.9	263.0	278.1	325.0	397.5	510.3	655.5
115°	230.0	233.4	241.2	252.4	273.6	288.6	303.7	348.4	415.4	519.3	653.3
117.5°	254.6	258.0	264.7	276.9	297.0	312.6	328.3	370.7	433.3	528.2	652.1
120°	279.2	281.4	289.2	301.5	320.5	336.2	351.8	394.2	452.3	538.2	652.1
122.5°	301.5	303.7	311.6	322.7	343.9	359.0	374.1	416.5	470.1	548.3	651.0
125°	320.5	325.0	331.7	343.9	365.2	380.8	396.4	436.6	488.0	558.3	649.9
127.5°	338.4	341.7	349.5	362.9	385.3	400.9	416.5	455.6	503.6	566.2	647.7
130°	352.9	357.3	366.3	383.0	404.2	420.4	436.6	474.6	518.1	575.1	646.6
132.5°	367.4	370.7	383.0	398.7	422.1	437.2	452.3	490.2	532.7	582.9	645.4
135°	380.8	385.3	396.4	415.4	438.9	453.4	467.9	504.7	544.9	590.7	644.3
137.5°	394.2	398.7	410.9	428.8	453.4	467.4	481.3	515.9	553.9	595.2	644.3
140°	408.7	412.1	424.3	443.3	466.8	480.2	493.6	527.1	562.8	600.8	643.2
142.5°	424.3	427.7	438.9	456.7	479.1	491.9	504.7	537.1	569.5	605.2	643.2
145°	438.9	442.2	453.4	469.0	490.2	502.5	514.8	543.8	574.0	606.4	641.0
147.5°	455.6	456.7	466.8	483.5	501.4	512.6	523.7	551.6	578.4	607.5	637.6
150°	471.2	472.4	481.3	494.7	511.4	522.0	532.7	557.2	581.8	607.5	634.3
152.5°	485.8	485.8	494.7	507.0	521.5	531.0	540.5	561.7	584.0	605.2	628.7
155°	499.2	500.3	507.0	518.1	530.4	538.8	547.2	566.2	585.1	603.0	623.1
157.5°	512.6	512.6	519.3	528.2	539.4	546.1	552.8	569.5	585.1	600.8	617.5
160°	524.8	524.8	529.3	537.1	546.1	552.2	558.3	571.7	585.1	597.4	610.8
162.5°	536.0	534.9	538.2	544.9	552.8	557.2	561.7	574.0	585.1	594.1	604.1
165°	543.8	543.8	546.1	551.6	557.2	560.6	563.9	574.0	582.9	589.6	597.4
167.5°	552.8	551.6	552.8	557.2	560.6	563.4	566.2	574.0	580.7	585.1	590.7
170°	558.3	557.2	558.3	561.7	563.9	565.6	567.3	572.9	578.4	580.7	584.0
172.5°	563.9	562.8	562.8	565.0	566.2	567.3	568.4	571.7	576.2	576.2	577.3
175°	567.3	566.2	566.2	567.3	568.4	568.4	568.4	570.6	574.0	572.9	572.9
177.5°	569.5	568.4	567.3	568.4	568.4	568.4	568.4	569.5	571.7	569.5	569.5
180°	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1940.4	1968.1	1980.4	1983.4	2000.4	1989.6	1994.2	1992.7	2005.0	2006.5	2006.5
5°	2081.9	2114.2	2125.0	2140.4	2163.5	2169.6	2165.0	2174.3	2191.2	2178.9	2197.3
7.5°	2231.2	2266.6	2291.2	2325.0	2332.7	2352.7	2365.1	2375.8	2378.9	2380.4	2383.5
10°	2369.7	2414.3	2448.1	2505.1	2517.4	2528.2	2582.0	2560.5	2588.2	2578.9	2582.0
12.5°	2482.0	2569.7	2597.4	2692.8	2702.0	2739.0	2735.9	2769.7	2775.9	2788.2	2775.9
15°	2629.7	2731.3	2775.9	2829.8	2860.5	2903.6	2911.3	2957.5	2975.9	2992.9	2975.9
17.5°	2765.1	2819.0	2932.9	2975.9	2995.9	3019.0	3077.5	3094.4	3122.1	3111.3	3142.1
20°	2832.8	2909.8	3029.8	3103.7	3134.4	3156.0	3205.2	3231.4	3242.1	3242.1	3245.2
22.5°	2892.8	3003.6	3092.9	3177.5	3205.2	3220.6	3249.8	3269.8	3274.5	3277.5	3280.6
25°	2946.7	3046.7	3119.0	3166.7	3177.5	3177.5	3194.4	3182.1	3162.1	3177.5	3186.7
27.5°	2946.7	3017.5	3049.8	3066.7	3066.7	3025.2	3000.6	2949.8	2906.7	2894.4	2922.1
30°	2897.5	2929.8	2885.2	2843.6	2811.3	2783.6	2686.7	2609.7	2594.3	2583.6	2625.1
32.5°	2783.6	2742.0	2654.3	2534.3	2486.6	2423.5	2348.1	2289.7	2254.3	2242.0	2232.7
35°	2582.0	2474.3	2360.4	2198.9	2165.0	2085.0	1981.9	1938.8	1880.4	1878.8	1898.8
37.5°	2362.0	2195.8	2072.7	1918.8	1871.1	1786.5	1689.5	1644.9	1604.9	1574.1	1611.1
40°	2105.0	1960.4	1772.6	1646.5	1578.8	1534.1	1452.6	1403.3	1384.9	1369.5	1392.6
42.5°	1865.0	1706.5	1560.3	1431.0	1375.6	1324.9	1271.0	1223.3	1209.5	1207.9	1224.8
45°	1626.5	1471.0	1335.6	1224.8	1189.5	1158.7	1106.4	1092.5	1069.4	1054.0	1061.7
47.5°	1435.7	1275.6	1163.3	1078.7	1047.9	1021.7	987.9	964.8	944.8	938.6	947.9
50°	1247.9	1140.2	1024.8	954.0	930.9	906.3	880.2	858.6	849.4	843.2	849.4
52.5°	1097.1	981.7	903.2	846.3	823.2	804.8	786.3	777.1	764.8	767.8	774.0
55°	961.7	860.2	794.0	752.4	738.6	730.9	707.8	697.1	692.4	689.4	692.4
57.5°	834.0	760.1	710.9	675.5	657.0	652.4	634.0	634.0	629.3	624.7	626.3
60°	732.4	669.4	621.7	594.0	590.9	583.2	570.9	569.3	558.6	563.2	564.7
62.5°	629.3	578.6	546.3	529.3	518.6	515.5	507.8	506.2	501.6	503.2	500.1
65°	547.8	506.2	473.9	460.1	455.5	453.9	447.8	443.2	440.1	443.2	440.1
67.5°	466.2	438.5	413.9	400.1	393.9	392.4	387.8	384.7	386.2	381.6	384.7
70°	389.3	361.6	346.2	338.5	335.4	330.8	330.8	330.8	330.8	327.8	326.2
72.5°	327.8	300.1	289.3	284.7	281.6	280.1	275.4	277.0	275.4	273.9	280.1
75°	260.0	243.1	232.4	227.7	230.8	226.2	221.6	224.7	220.0	221.6	227.7
77.5°	197.0	189.3	183.1	180.0	177.0	173.9	173.9	170.8	170.8	170.8	170.8
80°	143.1	141.6	130.8	129.3	129.3	126.2	126.2	126.2	126.2	124.6	126.2
82.5°	95.4	93.9	90.8	89.2	86.2	87.7	87.7	84.6	84.6	83.1	84.6
85°	55.4	55.4	52.3	50.8	49.2	50.8	47.7	46.2	47.7	46.2	47.7
87.5°	26.2	23.1	24.6	23.1	20.0	21.5	18.5	20.0	18.5	16.9	20.0
90°	19.0	20.1	21.2	22.3	22.3	22.3	23.5	24.6	23.5	23.5	23.5
92.5°	364.0	269.1	201.0	158.6	144.6	130.7	113.9	106.1	101.6	101.6	101.6
95°	935.8	827.5	654.4	504.7	450.6	396.4	341.7	307.1	287.0	272.5	287.0
97.5°	1173.6	1191.5	1105.5	982.7	920.2	857.6	781.7	714.7	681.2	654.4	681.2
100°	1183.7	1346.7	1369.1	1314.3	1273.0	1231.7	1134.6	1066.4	1032.9	1024.0	1032.9
102.5°	1099.9	1338.9	1471.8	1505.3	1494.2	1483.0	1432.7	1388.0	1352.3	1345.6	1352.3
105°	995.0	1250.7	1443.9	1554.4	1577.3	1600.2	1602.4	1593.5	1577.9	1571.2	1577.9
107.5°	909.0	1142.4	1351.2	1505.3	1552.2	1599.1	1648.2	1668.3	1677.3	1678.4	1677.3
110°	847.6	1046.3	1239.5	1401.4	1462.8	1524.3	1603.6	1650.5	1670.6	1680.6	1670.6

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	812.9	976.0	1141.3	1292.0	1353.4	1414.8	1507.5	1566.7	1596.9	1614.7	1596.9
115°	794.0	933.6	1070.9	1201.6	1255.2	1308.8	1397.0	1464.0	1499.7	1508.6	1499.7
117.5°	783.9	909.0	1025.1	1131.2	1178.1	1225.0	1303.2	1361.2	1399.2	1404.8	1399.2
120°	776.1	893.4	997.2	1086.5	1126.2	1165.8	1229.5	1278.6	1307.6	1319.9	1307.6
122.5°	767.2	880.0	979.3	1058.6	1092.1	1125.6	1177.0	1217.2	1240.6	1252.9	1240.6
125°	757.1	864.3	960.4	1037.4	1068.1	1098.8	1143.5	1175.9	1197.1	1203.8	1197.1
127.5°	743.7	846.5	939.1	1016.2	1045.2	1074.3	1118.9	1148.0	1165.8	1172.5	1165.8
130°	731.4	824.1	912.3	988.3	1017.9	1047.5	1093.2	1121.2	1139.0	1145.7	1139.0
132.5°	720.3	800.7	882.2	955.9	985.5	1015.1	1059.7	1092.1	1108.9	1115.6	1108.9
135°	709.1	779.4	852.0	920.2	948.1	976.0	1020.7	1051.9	1069.8	1076.5	1069.8
137.5°	699.0	759.3	823.0	882.2	907.9	933.6	976.0	1008.4	1022.9	1030.7	1022.9
140°	691.2	742.6	795.1	845.3	868.8	892.2	931.3	955.9	971.5	980.5	971.5
142.5°	684.5	727.0	771.6	812.9	832.4	852.0	885.5	907.9	921.3	926.9	921.3
145°	676.7	712.4	750.4	783.9	799.6	815.2	843.1	862.1	873.3	878.8	873.3
147.5°	670.0	700.2	731.4	759.3	772.2	785.0	806.2	823.0	831.9	834.2	831.9
150°	662.2	689.0	714.7	737.0	747.0	757.1	775.0	789.5	796.2	797.3	796.2
152.5°	653.3	676.7	697.9	718.0	725.8	733.7	748.2	759.3	762.7	763.8	762.7
155°	644.3	664.4	682.3	699.0	705.7	712.4	723.6	732.5	735.9	735.9	735.9
157.5°	635.4	651.0	666.7	681.2	686.8	692.3	701.3	708.0	710.2	710.2	710.2
160°	625.3	638.7	651.0	663.3	667.8	672.2	678.9	685.6	686.8	686.8	686.8
162.5°	616.4	626.5	636.5	645.4	649.3	653.3	657.7	664.4	665.5	664.4	665.5
165°	606.4	615.3	622.0	629.8	632.6	635.4	639.9	644.3	643.2	642.1	643.2
167.5°	597.4	604.1	609.7	616.4	618.1	619.8	622.0	625.3	625.3	624.2	625.3
170°	588.5	594.1	597.4	601.9	603.6	605.2	607.5	608.6	607.5	607.5	607.5
172.5°	580.7	585.1	587.4	589.6	590.7	591.8	593.0	594.1	593.0	590.7	593.0
175°	575.1	577.3	578.4	580.7	580.7	580.7	580.7	582.9	580.7	578.4	580.7
177.5°	570.6	571.7	572.9	572.9	573.4	574.0	572.9	574.0	571.7	569.5	571.7
180°	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	2003.5	1998.8	1992.7	1992.7	1985.0	1985.0	1972.7	1951.1	1932.7	1926.5	1929.6
5°	2174.3	2175.8	2166.6	2158.9	2145.0	2134.2	2114.2	2075.8	2063.5	2038.8	2021.9
7.5°	2369.7	2363.5	2346.6	2334.3	2331.2	2306.6	2263.5	2217.3	2180.4	2155.8	2120.4
10°	2589.7	2565.1	2540.5	2532.8	2514.3	2472.8	2423.5	2372.7	2322.0	2268.1	2208.1
12.5°	2774.4	2726.7	2725.1	2706.7	2671.3	2648.2	2589.7	2517.4	2429.7	2369.7	2302.0
15°	2972.9	2928.2	2891.3	2857.5	2840.5	2772.8	2723.6	2632.8	2528.2	2463.5	2417.4
17.5°	3114.4	3094.4	3031.3	3015.9	2992.9	2914.4	2835.9	2746.7	2655.9	2565.1	2440.5
20°	3228.3	3216.0	3174.4	3152.9	3116.0	3054.4	2959.0	2855.9	2751.3	2622.0	2505.1
22.5°	3277.5	3262.1	3228.3	3209.8	3186.7	3134.4	3052.9	2935.9	2799.0	2683.6	2558.9
25°	3180.6	3208.3	3199.1	3191.4	3182.1	3151.4	3089.8	2986.7	2852.8	2722.0	2566.6
27.5°	2962.1	3009.8	3056.0	3062.1	3077.5	3089.8	3065.2	2991.3	2879.0	2740.5	2569.7
30°	2668.2	2689.7	2783.6	2811.3	2832.8	2911.3	2957.5	2939.0	2852.8	2728.2	2571.2
32.5°	2291.2	2348.1	2443.5	2509.7	2568.2	2655.9	2775.9	2823.6	2792.8	2691.3	2535.9
35°	1934.2	2001.9	2112.7	2197.3	2255.8	2380.4	2522.0	2625.1	2663.6	2612.8	2474.3
37.5°	1641.8	1723.4	1821.9	1854.2	1921.9	2075.8	2271.2	2414.3	2508.2	2512.8	2405.1
40°	1421.8	1463.3	1541.8	1591.1	1657.2	1786.5	1977.3	2166.6	2308.1	2355.8	2298.9
42.5°	1235.6	1267.9	1326.4	1386.4	1446.4	1544.9	1720.3	1897.3	2088.1	2183.5	2181.9
45°	1087.9	1121.7	1161.8	1211.0	1252.5	1358.7	1497.2	1678.8	1843.4	1991.1	2028.1
47.5°	958.6	987.9	1037.1	1058.7	1086.4	1186.4	1306.4	1475.7	1646.5	1815.7	1858.8
50°	863.2	887.9	921.7	935.6	966.3	1040.2	1138.7	1275.6	1464.9	1620.3	1700.3
52.5°	777.1	795.5	821.7	832.5	854.0	909.4	998.6	1106.4	1263.3	1423.3	1535.7
55°	703.2	715.5	734.0	746.3	761.7	810.9	877.1	974.0	1109.4	1247.9	1357.2
57.5°	634.0	643.2	661.7	667.8	680.1	718.6	764.8	846.3	971.0	1094.0	1200.2
60°	569.3	575.5	586.3	600.1	609.3	635.5	678.6	746.3	846.3	958.6	1044.8
62.5°	507.8	517.0	520.1	526.3	533.9	558.6	592.4	641.7	729.4	821.7	912.5
65°	444.7	452.4	458.5	460.1	467.8	486.2	517.0	560.1	617.0	697.1	781.7
67.5°	386.2	390.8	393.9	400.1	407.8	417.0	441.6	473.9	526.3	590.9	658.6
70°	332.4	332.4	337.0	338.5	347.8	358.5	369.3	400.1	446.2	498.6	544.7
72.5°	273.9	281.6	280.1	287.7	286.2	293.9	307.7	327.8	361.6	403.2	447.8
75°	223.1	227.7	227.7	227.7	230.8	237.0	244.7	263.1	289.3	323.1	349.3
77.5°	173.9	177.0	177.0	177.0	178.5	184.6	192.3	204.7	223.1	243.1	258.5
80°	124.6	127.7	127.7	130.8	130.8	132.3	140.0	146.2	155.4	170.8	186.2
82.5°	84.6	86.2	89.2	89.2	87.7	90.8	92.3	98.5	107.7	110.8	121.6
85°	46.2	47.7	49.2	49.2	50.8	53.9	52.3	58.5	58.5	64.6	67.7
87.5°	18.5	21.5	21.5	20.0	21.5	21.5	21.5	24.6	26.2	27.7	26.2
90°	24.6	23.5	22.3	22.3	22.3	21.2	20.1	19.0	20.1	17.9	15.6
92.5°	106.1	113.9	130.7	144.6	158.6	201.0	269.1	364.0	437.7	383.0	278.1
95°	307.1	341.7	396.4	450.6	504.7	654.4	827.5	935.8	910.1	686.8	419.9
97.5°	714.7	781.7	857.6	920.2	982.7	1105.5	1191.5	1173.6	973.8	657.7	383.0
100°	1066.4	1134.6	1231.7	1273.0	1314.3	1369.1	1346.7	1183.7	897.8	582.9	355.1
102.5°	1388.0	1432.7	1483.0	1494.2	1505.3	1471.8	1338.9	1099.9	802.9	532.7	347.3
105°	1593.5	1602.4	1600.2	1577.3	1554.4	1443.9	1250.7	995.0	732.5	508.1	351.8
107.5°	1668.3	1648.2	1599.1	1552.2	1505.3	1351.2	1142.4	909.0	686.8	501.4	365.2
110°	1650.5	1603.6	1524.3	1462.8	1401.4	1239.5	1046.3	847.6	665.5	503.6	380.8

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1566.7	1507.5	1414.8	1353.4	1292.0	1141.3	976.0	812.9	655.5	510.3	397.5
115°	1464.0	1397.0	1308.8	1255.2	1201.6	1070.9	933.6	794.0	653.3	519.3	415.4
117.5°	1361.2	1303.2	1225.0	1178.1	1131.2	1025.1	909.0	783.9	652.1	528.2	433.3
120°	1278.6	1229.5	1165.8	1126.2	1086.5	997.2	893.4	776.1	652.1	538.2	452.3
122.5°	1217.2	1177.0	1125.6	1092.1	1058.6	979.3	880.0	767.2	651.0	548.3	470.1
125°	1175.9	1143.5	1098.8	1068.1	1037.4	960.4	864.3	757.1	649.9	558.3	488.0
127.5°	1148.0	1118.9	1074.3	1045.2	1016.2	939.1	846.5	743.7	647.7	566.2	503.6
130°	1121.2	1093.2	1047.5	1017.9	988.3	912.3	824.1	731.4	646.6	575.1	518.1
132.5°	1092.1	1059.7	1015.1	985.5	955.9	882.2	800.7	720.3	645.4	582.9	532.7
135°	1051.9	1020.7	976.0	948.1	920.2	852.0	779.4	709.1	644.3	590.7	544.9
137.5°	1008.4	976.0	933.6	907.9	882.2	823.0	759.3	699.0	644.3	595.2	553.9
140°	955.9	931.3	892.2	868.8	845.3	795.1	742.6	691.2	643.2	600.8	562.8
142.5°	907.9	885.5	852.0	832.4	812.9	771.6	727.0	684.5	643.2	605.2	569.5
145°	862.1	843.1	815.2	799.6	783.9	750.4	712.4	676.7	641.0	606.4	574.0
147.5°	823.0	806.2	785.0	772.2	759.3	731.4	700.2	670.0	637.6	607.5	578.4
150°	789.5	775.0	757.1	747.0	737.0	714.7	689.0	662.2	634.3	607.5	581.8
152.5°	759.3	748.2	733.7	725.8	718.0	697.9	676.7	653.3	628.7	605.2	584.0
155°	732.5	723.6	712.4	705.7	699.0	682.3	664.4	644.3	623.1	603.0	585.1
157.5°	708.0	701.3	692.3	686.8	681.2	666.7	651.0	635.4	617.5	600.8	585.1
160°	685.6	678.9	672.2	667.8	663.3	651.0	638.7	625.3	610.8	597.4	585.1
162.5°	664.4	657.7	653.3	649.3	645.4	636.5	626.5	616.4	604.1	594.1	585.1
165°	644.3	639.9	635.4	632.6	629.8	622.0	615.3	606.4	597.4	589.6	582.9
167.5°	625.3	622.0	619.8	618.1	616.4	609.7	604.1	597.4	590.7	585.1	580.7
170°	608.6	607.5	605.2	603.6	601.9	597.4	594.1	588.5	584.0	580.7	578.4
172.5°	594.1	593.0	591.8	590.7	589.6	587.4	585.1	580.7	577.3	576.2	576.2
175°	582.9	580.7	580.7	580.7	580.7	578.4	577.3	575.1	572.9	572.9	574.0
177.5°	574.0	572.9	574.0	573.4	572.9	572.9	571.7	570.6	569.5	569.5	571.7
180°	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1915.7	1909.6	1905.0	1905.0	1891.1	1877.3	1869.6	1866.5	1863.4	1851.1	1834.2
5°	1994.2	1974.2	1960.4	1946.5	1923.4	1898.8	1874.2	1860.3	1840.3	1812.6	1792.6
7.5°	2081.9	2034.2	2018.8	2001.9	1955.7	1914.2	1880.4	1851.1	1818.8	1783.4	1748.0
10°	2155.8	2105.0	2071.2	2041.9	1981.9	1926.5	1875.7	1832.6	1791.1	1744.9	1701.9
12.5°	2226.6	2154.2	2118.9	2075.8	2012.7	1932.7	1866.5	1812.6	1751.1	1703.4	1651.1
15°	2325.0	2203.5	2145.0	2117.3	2032.7	1938.8	1858.8	1778.8	1728.0	1655.7	1609.5
17.5°	2340.4	2242.0	2203.5	2132.7	2031.1	1925.0	1832.6	1752.6	1675.7	1611.1	1551.1
20°	2394.3	2265.0	2203.5	2158.9	2025.0	1917.3	1815.7	1712.6	1638.8	1569.5	1501.8
22.5°	2428.1	2282.0	2217.3	2146.6	2018.8	1889.6	1769.6	1680.3	1589.5	1518.7	1464.9
25°	2418.9	2272.7	2200.4	2134.2	1978.8	1849.6	1741.9	1628.0	1543.4	1466.4	1395.6
27.5°	2414.3	2249.6	2172.7	2098.9	1952.7	1817.3	1681.9	1589.5	1495.7	1406.4	1354.1
30°	2402.0	2220.4	2131.2	2051.2	1898.8	1757.3	1641.8	1534.1	1440.3	1358.7	1289.5
32.5°	2360.4	2171.2	2085.0	1998.8	1840.3	1698.8	1581.8	1481.8	1388.0	1303.3	1237.2
35°	2305.0	2112.7	2018.8	1928.1	1769.6	1626.5	1518.7	1414.1	1326.4	1244.8	1181.8
37.5°	2249.6	2045.0	1957.3	1852.7	1706.5	1557.2	1446.4	1352.6	1271.0	1186.4	1117.1
40°	2169.6	1965.0	1868.0	1778.8	1608.0	1468.0	1366.4	1281.8	1201.8	1121.7	1063.3
42.5°	2060.4	1877.3	1777.3	1678.8	1518.7	1380.3	1281.8	1206.4	1131.0	1064.8	1000.2
45°	1949.6	1771.1	1681.9	1594.1	1420.3	1289.5	1198.7	1129.4	1066.4	994.0	941.7
47.5°	1815.7	1664.9	1575.7	1489.5	1324.9	1194.1	1111.0	1046.3	987.9	927.9	878.6
50°	1678.8	1548.0	1466.4	1377.2	1220.2	1101.7	1020.2	966.3	918.6	861.7	821.7
52.5°	1531.1	1417.2	1347.9	1261.8	1123.3	1014.0	930.9	877.1	837.1	795.5	760.1
55°	1374.1	1291.0	1217.1	1147.9	1017.1	918.6	844.8	797.1	769.4	730.9	700.1
57.5°	1232.5	1152.5	1107.9	1029.4	915.6	818.6	760.1	720.1	687.8	664.7	640.1
60°	1084.8	1020.2	971.0	914.0	814.0	732.4	670.9	647.8	614.0	597.0	586.3
62.5°	943.3	897.1	850.9	807.8	718.6	641.7	595.5	566.3	546.3	529.3	520.1
65°	809.4	766.3	734.0	695.5	621.7	560.1	517.0	493.9	473.9	469.3	458.5
67.5°	678.6	660.1	624.7	594.0	530.9	483.2	450.9	421.6	410.8	406.2	397.0
70°	567.8	546.3	518.6	492.4	444.7	403.2	373.9	363.1	347.8	346.2	335.4
72.5°	467.8	441.6	421.6	401.6	366.2	329.3	313.9	298.5	290.8	284.7	280.1
75°	370.8	352.4	338.5	321.6	290.8	266.2	244.7	238.5	233.9	232.4	229.3
77.5°	277.0	264.7	258.5	241.6	220.0	198.5	189.3	180.0	180.0	177.0	178.5
80°	197.0	189.3	181.6	172.3	153.9	144.6	136.9	130.8	127.7	126.2	127.7
82.5°	124.6	120.0	118.5	112.3	100.0	95.4	89.2	84.6	84.6	84.6	84.6
85°	69.2	69.2	69.2	60.0	55.4	50.8	47.7	46.2	46.2	46.2	47.7
87.5°	29.2	29.2	24.6	24.6	23.1	20.0	18.5	18.5	20.0	20.0	21.5
90°	15.6	8.9	8.9	8.9	7.8	6.7	3.4	1.1	3.4	6.7	7.8
92.5°	169.7	100.5	86.0	71.5	51.4	34.6	22.3	15.6	22.3	34.6	51.4
95°	236.7	139.6	116.2	92.7	65.9	51.4	40.2	36.9	40.2	51.4	65.9
97.5°	225.6	148.5	128.4	108.3	84.9	71.5	61.4	61.4	61.4	71.5	84.9
100°	228.9	163.0	145.2	127.3	106.1	92.7	84.9	84.9	84.9	92.7	106.1
102.5°	240.1	182.0	165.2	148.5	128.4	116.1	109.4	107.2	109.4	116.1	128.4
105°	259.1	205.5	189.3	173.1	153.0	139.6	134.0	130.7	134.0	139.6	153.0
107.5°	279.2	230.0	213.8	197.7	178.7	164.2	158.6	156.3	158.6	164.2	178.7
110°	302.6	253.5	238.4	223.3	203.2	189.8	184.3	182.0	184.3	189.8	203.2

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	325.0	278.1	263.0	247.9	227.8	215.5	208.8	206.6	208.8	215.5	227.8
115°	348.4	303.7	288.6	273.6	252.4	241.2	233.4	230.0	233.4	241.2	252.4
117.5°	370.7	328.3	312.6	297.0	276.9	264.7	258.0	254.6	258.0	264.7	276.9
120°	394.2	351.8	336.2	320.5	301.5	289.2	281.4	279.2	281.4	289.2	301.5
122.5°	416.5	374.1	359.0	343.9	322.7	311.6	303.7	301.5	303.7	311.6	322.7
125°	436.6	396.4	380.8	365.2	343.9	331.7	325.0	320.5	325.0	331.7	343.9
127.5°	455.6	416.5	400.9	385.3	362.9	349.5	341.7	338.4	341.7	349.5	362.9
130°	474.6	436.6	420.4	404.2	383.0	366.3	357.3	352.9	357.3	366.3	383.0
132.5°	490.2	452.3	437.2	422.1	398.7	383.0	370.7	367.4	370.7	383.0	398.7
135°	504.7	467.9	453.4	438.9	415.4	396.4	385.3	380.8	385.3	396.4	415.4
137.5°	515.9	481.3	467.4	453.4	428.8	410.9	398.7	394.2	398.7	410.9	428.8
140°	527.1	493.6	480.2	466.8	443.3	424.3	412.1	408.7	412.1	424.3	443.3
142.5°	537.1	504.7	491.9	479.1	456.7	438.9	427.7	424.3	427.7	438.9	456.7
145°	543.8	514.8	502.5	490.2	469.0	453.4	442.2	438.9	442.2	453.4	469.0
147.5°	551.6	523.7	512.6	501.4	483.5	466.8	456.7	455.6	456.7	466.8	483.5
150°	557.2	532.7	522.0	511.4	494.7	481.3	472.4	471.2	472.4	481.3	494.7
152.5°	561.7	540.5	531.0	521.5	507.0	494.7	485.8	485.8	485.8	494.7	507.0
155°	566.2	547.2	538.8	530.4	518.1	507.0	500.3	499.2	500.3	507.0	518.1
157.5°	569.5	552.8	546.1	539.4	528.2	519.3	512.6	512.6	512.6	519.3	528.2
160°	571.7	558.3	552.2	546.1	537.1	529.3	524.8	524.8	524.8	529.3	537.1
162.5°	574.0	561.7	557.2	552.8	544.9	538.2	534.9	536.0	534.9	538.2	544.9
165°	574.0	563.9	560.6	557.2	551.6	546.1	543.8	543.8	543.8	546.1	551.6
167.5°	574.0	566.2	563.4	560.6	557.2	552.8	551.6	552.8	551.6	552.8	557.2
170°	572.9	567.3	565.6	563.9	561.7	558.3	557.2	558.3	557.2	558.3	561.7
172.5°	571.7	568.4	567.3	566.2	565.0	562.8	562.8	563.9	562.8	562.8	565.0
175°	570.6	568.4	568.4	568.4	567.3	566.2	566.2	567.3	566.2	566.2	567.3
177.5°	569.5	568.4	568.4	568.4	568.4	567.3	568.4	569.5	568.4	567.3	568.4
180°	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1829.6	1823.4	1826.5	1811.1	1797.3	1777.3	1760.3	1757.3	1754.2	1763.4	1757.3
5°	1777.3	1769.6	1761.9	1743.4	1715.7	1698.8	1674.2	1672.6	1663.4	1649.5	1652.6
7.5°	1720.3	1715.7	1704.9	1675.7	1651.1	1621.8	1601.8	1584.9	1577.2	1564.9	1560.3
10°	1674.2	1657.2	1648.0	1615.7	1586.4	1555.7	1529.5	1517.2	1503.4	1492.6	1484.9
12.5°	1611.1	1606.5	1580.3	1554.1	1529.5	1494.1	1474.1	1438.7	1420.3	1429.5	1426.4
15°	1569.5	1548.0	1541.8	1504.9	1463.3	1440.3	1403.3	1380.3	1372.6	1358.7	1341.8
17.5°	1514.1	1500.3	1478.7	1444.9	1397.2	1364.9	1338.7	1317.2	1307.9	1289.5	1275.6
20°	1461.8	1438.7	1421.8	1391.0	1344.9	1303.3	1271.0	1257.2	1234.1	1218.7	1211.0
22.5°	1414.1	1397.2	1372.6	1326.4	1286.4	1246.4	1207.9	1187.9	1166.4	1157.1	1144.8
25°	1355.6	1327.9	1311.0	1260.2	1217.1	1184.8	1149.4	1123.3	1111.0	1095.6	1092.5
27.5°	1298.7	1272.5	1252.5	1207.9	1155.6	1114.1	1092.5	1074.0	1052.5	1052.5	1044.8
30°	1241.8	1223.3	1192.5	1149.4	1100.2	1060.2	1035.6	1018.7	1011.0	1004.8	1003.3
32.5°	1184.8	1160.2	1141.8	1083.3	1046.3	1009.4	991.0	977.1	967.9	966.3	967.9
35°	1126.4	1098.7	1080.2	1027.9	991.0	957.1	949.4	937.1	932.5	930.9	938.6
37.5°	1064.8	1043.3	1020.2	977.1	935.6	915.6	900.2	895.6	894.0	903.2	906.3
40°	1007.9	989.4	967.9	921.7	890.9	869.4	861.7	857.1	863.2	872.5	877.1
42.5°	954.0	927.9	910.9	869.4	841.7	829.4	820.2	820.2	826.3	837.1	844.8
45°	897.1	877.1	860.2	823.2	798.6	784.8	783.2	784.8	792.5	800.1	809.4
47.5°	841.7	821.7	803.2	772.5	750.9	743.2	741.7	743.2	755.5	766.3	777.1
50°	790.9	769.4	752.4	723.2	706.3	697.1	698.6	706.3	715.5	730.9	744.8
52.5°	730.9	715.5	700.1	674.0	658.6	652.4	657.0	663.2	680.1	690.9	707.8
55°	672.4	658.6	646.3	626.3	614.0	609.3	612.4	621.7	635.5	654.0	674.0
57.5°	618.6	603.2	590.9	577.0	563.2	564.7	566.3	578.6	595.5	612.4	635.5
60°	558.6	549.3	538.6	521.6	515.5	515.5	520.1	533.9	549.3	577.0	597.0
62.5°	504.7	492.4	484.7	473.9	464.7	466.2	477.0	489.3	507.8	530.9	557.0
65°	449.3	435.5	429.3	420.1	417.0	418.5	426.2	444.7	464.7	484.7	509.3
67.5°	387.8	383.1	377.0	367.8	370.8	372.4	380.1	395.5	417.0	437.0	464.7
70°	335.4	326.2	324.7	317.0	317.0	321.6	337.0	347.8	367.8	389.3	418.5
72.5°	280.1	272.4	272.4	266.2	270.8	275.4	283.1	298.5	317.0	338.5	363.1
75°	223.1	220.0	223.1	220.0	220.0	227.7	237.0	249.3	269.3	292.4	312.4
77.5°	172.3	172.3	170.8	175.4	175.4	180.0	192.3	204.7	220.0	238.5	260.0
80°	126.2	126.2	126.2	130.8	135.4	135.4	143.1	158.5	172.3	184.6	204.7
82.5°	86.2	86.2	86.2	89.2	95.4	95.4	104.6	113.9	129.3	140.0	149.3
85°	52.3	52.3	50.8	53.9	55.4	60.0	67.7	73.9	81.6	90.8	100.0
87.5°	23.1	23.1	24.6	26.2	27.7	30.8	33.9	36.9	44.6	47.7	52.3
90°	8.9	8.9	8.9	15.6	15.6	17.9	20.1	19.0	20.1	21.2	22.3
92.5°	71.5	86.0	100.5	169.7	278.1	383.0	437.7	364.0	269.1	201.0	158.6
95°	92.7	116.2	139.6	236.7	419.9	686.8	910.1	935.8	827.5	654.4	504.7
97.5°	108.3	128.4	148.5	225.6	383.0	657.7	973.8	1173.6	1191.5	1105.5	982.7
100°	127.3	145.2	163.0	228.9	355.1	582.9	897.8	1183.7	1346.7	1369.1	1314.3
102.5°	148.5	165.2	182.0	240.1	347.3	532.7	802.9	1099.9	1338.9	1471.8	1505.3
105°	173.1	189.3	205.5	259.1	351.8	508.1	732.5	995.0	1250.7	1443.9	1554.4
107.5°	197.7	213.8	230.0	279.2	365.2	501.4	686.8	909.0	1142.4	1351.2	1505.3
110°	223.3	238.4	253.5	302.6	380.8	503.6	665.5	847.6	1046.3	1239.5	1401.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	247.9	263.0	278.1	325.0	397.5	510.3	655.5	812.9	976.0	1141.3	1292.0
115°	273.6	288.6	303.7	348.4	415.4	519.3	653.3	794.0	933.6	1070.9	1201.6
117.5°	297.0	312.6	328.3	370.7	433.3	528.2	652.1	783.9	909.0	1025.1	1131.2
120°	320.5	336.2	351.8	394.2	452.3	538.2	652.1	776.1	893.4	997.2	1086.5
122.5°	343.9	359.0	374.1	416.5	470.1	548.3	651.0	767.2	880.0	979.3	1058.6
125°	365.2	380.8	396.4	436.6	488.0	558.3	649.9	757.1	864.3	960.4	1037.4
127.5°	385.3	400.9	416.5	455.6	503.6	566.2	647.7	743.7	846.5	939.1	1016.2
130°	404.2	420.4	436.6	474.6	518.1	575.1	646.6	731.4	824.1	912.3	988.3
132.5°	422.1	437.2	452.3	490.2	532.7	582.9	645.4	720.3	800.7	882.2	955.9
135°	438.9	453.4	467.9	504.7	544.9	590.7	644.3	709.1	779.4	852.0	920.2
137.5°	453.4	467.4	481.3	515.9	553.9	595.2	644.3	699.0	759.3	823.0	882.2
140°	466.8	480.2	493.6	527.1	562.8	600.8	643.2	691.2	742.6	795.1	845.3
142.5°	479.1	491.9	504.7	537.1	569.5	605.2	643.2	684.5	727.0	771.6	812.9
145°	490.2	502.5	514.8	543.8	574.0	606.4	641.0	676.7	712.4	750.4	783.9
147.5°	501.4	512.6	523.7	551.6	578.4	607.5	637.6	670.0	700.2	731.4	759.3
150°	511.4	522.0	532.7	557.2	581.8	607.5	634.3	662.2	689.0	714.7	737.0
152.5°	521.5	531.0	540.5	561.7	584.0	605.2	628.7	653.3	676.7	697.9	718.0
155°	530.4	538.8	547.2	566.2	585.1	603.0	623.1	644.3	664.4	682.3	699.0
157.5°	539.4	546.1	552.8	569.5	585.1	600.8	617.5	635.4	651.0	666.7	681.2
160°	546.1	552.2	558.3	571.7	585.1	597.4	610.8	625.3	638.7	651.0	663.3
162.5°	552.8	557.2	561.7	574.0	585.1	594.1	604.1	616.4	626.5	636.5	645.4
165°	557.2	560.6	563.9	574.0	582.9	589.6	597.4	606.4	615.3	622.0	629.8
167.5°	560.6	563.4	566.2	574.0	580.7	585.1	590.7	597.4	604.1	609.7	616.4
170°	563.9	565.6	567.3	572.9	578.4	580.7	584.0	588.5	594.1	597.4	601.9
172.5°	566.2	567.3	568.4	571.7	576.2	576.2	577.3	580.7	585.1	587.4	589.6
175°	568.4	568.4	568.4	570.6	574.0	572.9	572.9	575.1	577.3	578.4	580.7
177.5°	568.4	568.4	568.4	569.5	571.7	569.5	569.5	570.6	571.7	572.9	572.9
180°	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1752.6	1751.1	1743.4	1746.5	1737.2	1740.3	1744.9	1746.5	1752.6	1748.0	1746.5
5°	1644.9	1641.8	1637.2	1632.6	1631.1	1637.2	1626.5	1629.5	1632.6	1637.2	1643.4
7.5°	1557.2	1555.7	1551.1	1543.4	1540.3	1537.2	1538.7	1549.5	1548.0	1546.4	1557.2
10°	1477.2	1478.7	1469.5	1468.0	1458.7	1457.2	1458.7	1461.8	1466.4	1472.6	1474.1
12.5°	1394.1	1414.1	1397.2	1391.0	1377.2	1384.9	1388.0	1374.1	1381.8	1386.4	1409.5
15°	1341.8	1332.6	1321.8	1321.8	1315.6	1312.6	1304.9	1315.6	1321.8	1331.0	1327.9
17.5°	1269.5	1254.1	1247.9	1241.8	1243.3	1249.5	1232.5	1257.2	1257.2	1261.8	1254.1
20°	1206.4	1194.1	1186.4	1183.3	1178.7	1175.6	1174.1	1180.2	1189.5	1192.5	1200.2
22.5°	1140.2	1140.2	1127.9	1123.3	1120.2	1115.6	1123.3	1118.7	1124.8	1131.0	1143.3
25°	1084.8	1084.8	1080.2	1074.0	1069.4	1066.4	1071.0	1069.4	1074.0	1081.7	1084.8
27.5°	1040.2	1035.6	1034.0	1032.5	1031.0	1032.5	1031.0	1035.6	1040.2	1041.7	1038.7
30°	1001.7	997.1	998.6	998.6	1000.2	998.6	997.1	1001.7	1003.3	1000.2	1001.7
32.5°	966.3	966.3	969.4	971.0	971.0	972.5	974.0	971.0	972.5	967.9	969.4
35°	937.1	940.2	943.3	944.8	946.3	944.8	947.9	946.3	943.3	940.2	938.6
37.5°	907.9	910.9	917.1	918.6	923.2	924.8	921.7	921.7	920.2	914.0	910.9
40°	877.1	880.2	887.9	892.5	895.6	900.2	897.1	897.1	890.9	884.8	880.2
42.5°	847.9	854.0	861.7	866.3	872.5	872.5	872.5	869.4	861.7	855.5	850.9
45°	818.6	820.2	830.9	838.6	844.8	844.8	844.8	840.2	835.5	823.2	817.1
47.5°	786.3	790.9	803.2	810.9	817.1	818.6	818.6	814.0	804.8	794.0	786.3
50°	750.9	758.6	772.5	783.2	790.9	794.0	789.4	786.3	775.5	763.2	754.0
52.5°	717.1	726.3	743.2	752.4	763.2	764.8	763.2	758.6	746.3	729.4	721.7
55°	683.2	690.9	709.4	724.8	734.0	737.1	734.0	726.3	710.9	694.0	686.3
57.5°	646.3	657.0	677.0	692.4	703.2	704.7	701.7	694.0	681.7	660.1	649.4
60°	607.8	621.7	641.7	657.0	670.9	672.4	669.4	658.6	643.2	621.7	612.4
62.5°	569.3	580.1	603.2	620.1	630.9	638.6	632.4	621.7	606.3	584.7	570.9
65°	524.7	540.1	560.1	575.5	587.8	589.3	586.3	577.0	560.1	537.0	526.3
67.5°	481.6	492.4	512.4	532.4	537.0	541.6	537.0	527.8	513.9	493.9	478.6
70°	429.3	438.5	463.2	477.0	483.2	487.8	484.7	475.5	463.2	444.7	432.4
72.5°	377.0	384.7	407.8	418.5	430.8	429.3	427.8	421.6	404.7	392.4	384.7
75°	321.6	330.8	346.2	360.1	364.7	364.7	364.7	360.1	349.3	329.3	321.6
77.5°	270.8	275.4	287.7	295.4	300.1	301.6	300.1	292.4	286.2	272.4	267.7
80°	207.7	220.0	229.3	230.8	237.0	237.0	237.0	233.9	227.7	213.9	212.3
82.5°	157.0	160.0	169.3	173.9	177.0	175.4	175.4	169.3	167.7	160.0	157.0
85°	106.2	110.8	109.3	115.4	116.9	113.9	113.9	116.9	109.3	110.8	106.2
87.5°	58.5	58.5	61.5	60.0	66.2	66.2	63.1	64.6	61.5	60.0	58.5
90°	22.3	22.3	23.5	24.6	23.5	23.5	23.5	24.6	23.5	22.3	22.3
92.5°	144.6	130.7	113.9	106.1	101.6	101.6	101.6	106.1	113.9	130.7	144.6
95°	450.6	396.4	341.7	307.1	287.0	272.5	287.0	307.1	341.7	396.4	450.6
97.5°	920.2	857.6	781.7	714.7	681.2	654.4	681.2	714.7	781.7	857.6	920.2
100°	1273.0	1231.7	1134.6	1066.4	1032.9	1024.0	1032.9	1066.4	1134.6	1231.7	1273.0
102.5°	1494.2	1483.0	1432.7	1388.0	1352.3	1345.6	1352.3	1388.0	1432.7	1483.0	1494.2
105°	1577.3	1600.2	1602.4	1593.5	1577.9	1571.2	1577.9	1593.5	1602.4	1600.2	1577.3
107.5°	1552.2	1599.1	1648.2	1668.3	1677.3	1678.4	1677.3	1668.3	1648.2	1599.1	1552.2
110°	1462.8	1524.3	1603.6	1650.5	1670.6	1680.6	1670.6	1650.5	1603.6	1524.3	1462.8

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1353.4	1414.8	1507.5	1566.7	1596.9	1614.7	1596.9	1566.7	1507.5	1414.8	1353.4
115°	1255.2	1308.8	1397.0	1464.0	1499.7	1508.6	1499.7	1464.0	1397.0	1308.8	1255.2
117.5°	1178.1	1225.0	1303.2	1361.2	1399.2	1404.8	1399.2	1361.2	1303.2	1225.0	1178.1
120°	1126.2	1165.8	1229.5	1278.6	1307.6	1319.9	1307.6	1278.6	1229.5	1165.8	1126.2
122.5°	1092.1	1125.6	1177.0	1217.2	1240.6	1252.9	1240.6	1217.2	1177.0	1125.6	1092.1
125°	1068.1	1098.8	1143.5	1175.9	1197.1	1203.8	1197.1	1175.9	1143.5	1098.8	1068.1
127.5°	1045.2	1074.3	1118.9	1148.0	1165.8	1172.5	1165.8	1148.0	1118.9	1074.3	1045.2
130°	1017.9	1047.5	1093.2	1121.2	1139.0	1145.7	1139.0	1121.2	1093.2	1047.5	1017.9
132.5°	985.5	1015.1	1059.7	1092.1	1108.9	1115.6	1108.9	1092.1	1059.7	1015.1	985.5
135°	948.1	976.0	1020.7	1051.9	1069.8	1076.5	1069.8	1051.9	1020.7	976.0	948.1
137.5°	907.9	933.6	976.0	1008.4	1022.9	1030.7	1022.9	1008.4	976.0	933.6	907.9
140°	868.8	892.2	931.3	955.9	971.5	980.5	971.5	955.9	931.3	892.2	868.8
142.5°	832.4	852.0	885.5	907.9	921.3	926.9	921.3	907.9	885.5	852.0	832.4
145°	799.6	815.2	843.1	862.1	873.3	878.8	873.3	862.1	843.1	815.2	799.6
147.5°	772.2	785.0	806.2	823.0	831.9	834.2	831.9	823.0	806.2	785.0	772.2
150°	747.0	757.1	775.0	789.5	796.2	797.3	796.2	789.5	775.0	757.1	747.0
152.5°	725.8	733.7	748.2	759.3	762.7	763.8	762.7	759.3	748.2	733.7	725.8
155°	705.7	712.4	723.6	732.5	735.9	735.9	735.9	732.5	723.6	712.4	705.7
157.5°	686.8	692.3	701.3	708.0	710.2	710.2	710.2	708.0	701.3	692.3	686.8
160°	667.8	672.2	678.9	685.6	686.8	686.8	686.8	685.6	678.9	672.2	667.8
162.5°	649.3	653.3	657.7	664.4	665.5	664.4	665.5	664.4	657.7	653.3	649.3
165°	632.6	635.4	639.9	644.3	643.2	642.1	643.2	644.3	639.9	635.4	632.6
167.5°	618.1	619.8	622.0	625.3	625.3	624.2	625.3	625.3	622.0	619.8	618.1
170°	603.6	605.2	607.5	608.6	607.5	607.5	607.5	608.6	607.5	605.2	603.6
172.5°	590.7	591.8	593.0	594.1	593.0	590.7	593.0	594.1	593.0	591.8	590.7
175°	580.7	580.7	580.7	582.9	580.7	578.4	580.7	582.9	580.7	580.7	580.7
177.5°	573.4	574.0	572.9	574.0	571.7	569.5	571.7	574.0	572.9	574.0	573.4
180°	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1746.5	1755.7	1746.5	1752.6	1755.7	1763.4	1766.5	1780.3	1784.9	1795.7	1795.7
5°	1641.8	1646.5	1648.0	1654.2	1660.3	1675.7	1686.5	1706.5	1729.6	1732.6	1746.5
7.5°	1557.2	1564.9	1577.2	1572.6	1583.4	1606.5	1620.3	1644.9	1668.0	1680.3	1697.2
10°	1481.8	1491.0	1495.7	1500.3	1520.3	1540.3	1561.8	1578.8	1609.5	1628.0	1641.8
12.5°	1420.3	1412.6	1421.8	1438.7	1461.8	1474.1	1503.4	1529.5	1552.6	1572.6	1584.9
15°	1340.2	1346.4	1355.6	1384.9	1391.0	1421.8	1432.6	1461.8	1504.9	1523.4	1538.7
17.5°	1263.3	1283.3	1301.8	1312.6	1331.0	1355.6	1386.4	1418.7	1446.4	1468.0	1486.4
20°	1201.8	1221.8	1232.5	1240.2	1258.7	1292.5	1321.8	1361.8	1397.2	1414.1	1438.7
22.5°	1152.5	1152.5	1167.9	1191.0	1201.8	1234.1	1258.7	1301.8	1340.2	1361.8	1384.9
25°	1091.0	1100.2	1112.5	1132.5	1147.9	1174.1	1209.5	1246.4	1287.9	1306.4	1335.6
27.5°	1040.2	1051.0	1067.9	1072.5	1087.9	1111.0	1147.9	1187.9	1231.0	1251.0	1275.6
30°	1001.7	1007.9	1014.0	1023.3	1037.1	1057.1	1087.9	1123.3	1175.6	1191.0	1221.8
32.5°	967.9	971.0	974.0	981.7	989.4	1009.4	1034.0	1072.5	1115.6	1138.7	1166.4
35°	937.1	934.0	935.6	940.2	947.9	955.6	981.7	1014.0	1054.0	1081.7	1103.3
37.5°	907.9	901.7	900.2	900.2	903.2	912.5	932.5	960.2	1003.3	1026.3	1047.9
40°	875.5	869.4	866.3	864.8	863.2	869.4	884.8	912.5	946.3	967.9	992.5
42.5°	844.8	838.6	830.9	829.4	826.3	829.4	840.2	866.3	895.6	917.1	937.1
45°	814.0	803.2	794.0	787.8	789.4	784.8	792.5	812.5	846.3	860.2	880.2
47.5°	780.1	767.8	755.5	749.4	743.2	746.3	749.4	766.3	795.5	809.4	829.4
50°	747.8	730.9	717.1	709.4	704.7	701.7	704.7	721.7	743.2	755.5	772.5
52.5°	710.9	694.0	680.1	667.8	661.7	657.0	658.6	674.0	694.0	706.3	723.2
55°	677.0	655.5	637.0	621.7	617.0	615.5	614.0	624.7	641.7	654.0	667.8
57.5°	638.6	617.0	597.0	578.6	569.3	567.8	567.8	570.9	592.4	601.7	609.3
60°	600.1	577.0	555.5	538.6	524.7	520.1	518.6	524.7	535.5	544.7	555.5
62.5°	557.0	533.9	507.8	492.4	478.6	466.2	470.9	472.4	487.8	492.4	501.6
65°	515.5	489.3	467.8	443.2	427.8	420.1	417.0	420.1	432.4	433.9	440.1
67.5°	467.8	443.2	417.0	400.1	386.2	372.4	369.3	369.3	375.5	380.1	387.8
70°	421.6	397.0	367.8	349.3	335.4	323.1	318.5	317.0	321.6	324.7	332.4
72.5°	367.8	343.1	321.6	301.6	284.7	275.4	270.8	267.7	272.4	275.4	277.0
75°	310.8	290.8	269.3	249.3	238.5	229.3	223.1	218.5	221.6	221.6	221.6
77.5°	257.0	237.0	220.0	206.2	192.3	181.6	177.0	172.3	173.9	173.9	177.0
80°	200.0	186.2	172.3	160.0	147.7	138.5	135.4	130.8	127.7	126.2	126.2
82.5°	147.7	136.9	124.6	113.9	107.7	98.5	95.4	89.2	89.2	87.7	87.7
85°	98.5	92.3	80.0	72.3	67.7	63.1	60.0	56.9	52.3	52.3	50.8
87.5°	52.3	49.2	46.2	36.9	36.9	32.3	30.8	29.2	24.6	26.2	26.2
90°	22.3	21.2	20.1	19.0	20.1	17.9	15.6	15.6	8.9	8.9	8.9
92.5°	158.6	201.0	269.1	364.0	437.7	383.0	278.1	169.7	100.5	86.0	71.5
95°	504.7	654.4	827.5	935.8	910.1	686.8	419.9	236.7	139.6	116.2	92.7
97.5°	982.7	1105.5	1191.5	1173.6	973.8	657.7	383.0	225.6	148.5	128.4	108.3
100°	1314.3	1369.1	1346.7	1183.7	897.8	582.9	355.1	228.9	163.0	145.2	127.3
102.5°	1505.3	1471.8	1338.9	1099.9	802.9	532.7	347.3	240.1	182.0	165.2	148.5
105°	1554.4	1443.9	1250.7	995.0	732.5	508.1	351.8	259.1	205.5	189.3	173.1
107.5°	1505.3	1351.2	1142.4	909.0	686.8	501.4	365.2	279.2	230.0	213.8	197.7
110°	1401.4	1239.5	1046.3	847.6	665.5	503.6	380.8	302.6	253.5	238.4	223.3

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1292.0	1141.3	976.0	812.9	655.5	510.3	397.5	325.0	278.1	263.0	247.9
115°	1201.6	1070.9	933.6	794.0	653.3	519.3	415.4	348.4	303.7	288.6	273.6
117.5°	1131.2	1025.1	909.0	783.9	652.1	528.2	433.3	370.7	328.3	312.6	297.0
120°	1086.5	997.2	893.4	776.1	652.1	538.2	452.3	394.2	351.8	336.2	320.5
122.5°	1058.6	979.3	880.0	767.2	651.0	548.3	470.1	416.5	374.1	359.0	343.9
125°	1037.4	960.4	864.3	757.1	649.9	558.3	488.0	436.6	396.4	380.8	365.2
127.5°	1016.2	939.1	846.5	743.7	647.7	566.2	503.6	455.6	416.5	400.9	385.3
130°	988.3	912.3	824.1	731.4	646.6	575.1	518.1	474.6	436.6	420.4	404.2
132.5°	955.9	882.2	800.7	720.3	645.4	582.9	532.7	490.2	452.3	437.2	422.1
135°	920.2	852.0	779.4	709.1	644.3	590.7	544.9	504.7	467.9	453.4	438.9
137.5°	882.2	823.0	759.3	699.0	644.3	595.2	553.9	515.9	481.3	467.4	453.4
140°	845.3	795.1	742.6	691.2	643.2	600.8	562.8	527.1	493.6	480.2	466.8
142.5°	812.9	771.6	727.0	684.5	643.2	605.2	569.5	537.1	504.7	491.9	479.1
145°	783.9	750.4	712.4	676.7	641.0	606.4	574.0	543.8	514.8	502.5	490.2
147.5°	759.3	731.4	700.2	670.0	637.6	607.5	578.4	551.6	523.7	512.6	501.4
150°	737.0	714.7	689.0	662.2	634.3	607.5	581.8	557.2	532.7	522.0	511.4
152.5°	718.0	697.9	676.7	653.3	628.7	605.2	584.0	561.7	540.5	531.0	521.5
155°	699.0	682.3	664.4	644.3	623.1	603.0	585.1	566.2	547.2	538.8	530.4
157.5°	681.2	666.7	651.0	635.4	617.5	600.8	585.1	569.5	552.8	546.1	539.4
160°	663.3	651.0	638.7	625.3	610.8	597.4	585.1	571.7	558.3	552.2	546.1
162.5°	645.4	636.5	626.5	616.4	604.1	594.1	585.1	574.0	561.7	557.2	552.8
165°	629.8	622.0	615.3	606.4	597.4	589.6	582.9	574.0	563.9	560.6	557.2
167.5°	616.4	609.7	604.1	597.4	590.7	585.1	580.7	574.0	566.2	563.4	560.6
170°	601.9	597.4	594.1	588.5	584.0	580.7	578.4	572.9	567.3	565.6	563.9
172.5°	589.6	587.4	585.1	580.7	577.3	576.2	576.2	571.7	568.4	567.3	566.2
175°	580.7	578.4	577.3	575.1	572.9	572.9	574.0	570.6	568.4	568.4	568.4
177.5°	572.9	572.9	571.7	570.6	569.5	569.5	571.7	569.5	568.4	568.4	568.4
180°	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4	568.4

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1857.3	1857.3	1857.3	1857.3
2.5°	1806.5	1821.9	1835.7	1857.3
5°	1766.5	1788.0	1817.3	1849.6
7.5°	1720.3	1754.2	1792.6	1837.3
10°	1677.2	1715.7	1764.9	1818.8
12.5°	1632.6	1678.8	1732.6	1791.1
15°	1581.8	1628.0	1688.0	1766.5
17.5°	1535.7	1591.1	1655.7	1738.8
20°	1481.8	1534.1	1604.9	1700.3
22.5°	1434.1	1494.1	1572.6	1655.7
25°	1381.8	1434.1	1512.6	1612.6
27.5°	1329.5	1394.1	1469.5	1566.4
30°	1278.7	1332.6	1414.1	1515.7
32.5°	1223.3	1287.9	1363.3	1458.7
35°	1163.3	1224.8	1295.6	1398.7
37.5°	1109.4	1169.4	1241.8	1332.6
40°	1049.4	1112.5	1178.7	1269.5
42.5°	991.0	1047.9	1114.1	1197.1
45°	934.0	983.3	1043.3	1115.6
47.5°	875.5	917.1	972.5	1037.1
50°	812.5	857.1	898.6	952.5
52.5°	754.0	792.5	826.3	870.9
55°	697.1	723.2	750.9	784.8
57.5°	637.0	657.0	677.0	712.4
60°	577.0	595.5	606.3	629.3
62.5°	518.6	526.3	540.1	553.9
65°	453.9	464.7	472.4	489.3
67.5°	395.5	400.1	407.8	418.5
70°	333.9	344.7	347.8	355.5
72.5°	281.6	286.2	289.3	290.8
75°	223.1	227.7	230.8	240.0
77.5°	175.4	173.9	180.0	181.6
80°	129.3	124.6	126.2	132.3
82.5°	84.6	86.2	84.6	84.6
85°	52.3	50.8	47.7	49.2
87.5°	23.1	23.1	21.5	21.5
90°	7.8	6.7	3.4	1.1
92.5°	51.4	34.6	22.3	15.6
95°	65.9	51.4	40.2	36.9
97.5°	84.9	71.5	61.4	61.4
100°	106.1	92.7	84.9	84.9
102.5°	128.4	116.1	109.4	107.2
105°	153.0	139.6	134.0	130.7
107.5°	178.7	164.2	158.6	156.3
110°	203.2	189.8	184.3	182.0

TEST NUMBER: P1000919

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	227.8	215.5	208.8	206.6
115°	252.4	241.2	233.4	230.0
117.5°	276.9	264.7	258.0	254.6
120°	301.5	289.2	281.4	279.2
122.5°	322.7	311.6	303.7	301.5
125°	343.9	331.7	325.0	320.5
127.5°	362.9	349.5	341.7	338.4
130°	383.0	366.3	357.3	352.9
132.5°	398.7	383.0	370.7	367.4
135°	415.4	396.4	385.3	380.8
137.5°	428.8	410.9	398.7	394.2
140°	443.3	424.3	412.1	408.7
142.5°	456.7	438.9	427.7	424.3
145°	469.0	453.4	442.2	438.9
147.5°	483.5	466.8	456.7	455.6
150°	494.7	481.3	472.4	471.2
152.5°	507.0	494.7	485.8	485.8
155°	518.1	507.0	500.3	499.2
157.5°	528.2	519.3	512.6	512.6
160°	537.1	529.3	524.8	524.8
162.5°	544.9	538.2	534.9	536.0
165°	551.6	546.1	543.8	543.8
167.5°	557.2	552.8	551.6	552.8
170°	561.7	558.3	557.2	558.3
172.5°	565.0	562.8	562.8	563.9
175°	567.3	566.2	566.2	567.3
177.5°	568.4	567.3	568.4	569.5
180°	568.4	568.4	568.4	568.4

(END OF REPORT)