

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001129

Luminaire Tested: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001129
REPORT IS A COMBINATION OF REPORTS P995745 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5201.0 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	32	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	47	63	55	48	43	44	39	35	33	30	27	23	21	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4536	4536	4536	4536
5°	4525	5204	4551	3911
10°	4491	6071	4525	3430
15°	4437	6999	4468	3069
20°	4380	7590	4412	2752
25°	4296	7503	4337	2518
30°	4214	6201	4265	2397
35°	4098	4621	4143	2324
40°	3964	3481	4003	2288
45°	3759	2794	3806	2239
50°	3515	2354	3565	2216
55°	3226	2049	3277	2191
60°	2947	1804	3033	2154
65°	2685	1552	2709	2064
70°	2376	1278	2427	1901
75°	2072	982	2058	1615
80°	1629	644	1612	1226
85°	1070	289	1004	715

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5865 cd/sqm

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	1.0
10°-20°	167.1	3.2
20°-30°	265.5	5.1
30°-40°	295.0	5.7
40°-50°	268.3	5.2
50°-60°	219.2	4.2
60°-70°	156.5	3.0
70°-80°	86.1	1.7
80°-90°	25.2	0.5
90°-100°	364.6	7.0
100°-110°	761.2	14.6
110°-120°	676.7	13.0
120°-130°	569.6	11.0
130°-140°	475.2	9.1
140°-150°	362.8	7.0
150°-160°	255.1	4.9
160°-170°	150.0	2.9
170°-180°	48.8	0.9
0°-30°	486.7	9.4
0°-40°	781.7	15.0
0°-60°	1269.2	24.4
0°-90°	1537.0	29.6
90°-120°	1802.5	34.7
90°-150°	3210.1	61.7
90°-180°	3664.0	70.4
0°-180°	5201.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	556	556	556	556	556	
5°	554	653	557	490	554	53
15°	529	896	533	393	529	149
25°	483	952	488	319	483	223
35°	419	563	424	283	419	262
45°	334	316	338	253	334	258
55°	235	206	239	221	235	211
65°	147	133	148	176	147	145
75°	72	66	71	109	72	76
85°	15	14	14	34	15	17
90°	1	21	1	21	1	3
95°	33	241	33	241	33	36
105°	116	1391	116	1391	116	123
115°	204	1335	204	1335	204	202
125°	284	1066	284	1066	284	253
135°	337	953	337	953	337	260
145°	388	778	388	778	388	244
155°	442	651	442	651	442	204
165°	481	568	481	568	481	136
175°	502	512	502	512	502	48
180°	503	503	503	503	503	

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	556.3	561.8	564.1	566.0	571.9	573.8	574.2	577.0	579.3	579.8	579.8
5°	554.0	562.7	569.6	576.1	585.8	589.9	595.0	600.5	607.9	612.5	614.8
7.5°	550.3	563.2	573.8	584.8	598.2	606.5	611.1	625.9	636.0	644.3	654.4
10°	544.8	561.3	576.6	592.7	611.6	621.7	631.9	649.8	664.1	680.2	693.2
12.5°	536.5	558.1	576.6	599.1	622.6	634.6	646.6	677.9	694.5	708.8	731.9
15°	529.1	550.7	577.0	600.1	629.1	647.1	664.6	684.9	711.1	742.0	764.1
17.5°	520.8	548.0	572.4	604.7	636.9	654.0	668.3	699.6	736.5	766.9	787.2
20°	509.3	536.9	569.2	603.3	641.5	654.9	673.8	715.7	748.9	778.9	812.1
22.5°	495.9	528.2	562.3	595.0	634.6	662.7	683.5	720.3	760.4	795.0	832.3
25°	483.0	518.0	548.0	592.7	634.6	653.5	677.0	720.8	764.6	806.5	844.8
27.5°	469.2	501.9	542.4	577.9	625.4	646.1	671.5	719.4	766.0	807.9	848.9
30°	454.0	489.0	522.6	564.6	610.7	637.4	660.9	713.0	760.4	804.2	842.5
32.5°	436.9	470.1	506.0	545.7	594.1	621.3	650.8	704.2	754.9	792.7	822.2
35°	418.9	452.6	483.9	524.5	574.2	601.4	630.0	689.0	739.2	770.1	787.2
37.5°	399.1	430.9	461.8	501.9	551.7	580.7	609.7	666.9	714.4	740.2	735.6
40°	380.2	408.8	437.4	475.2	527.2	558.1	583.5	641.1	682.6	693.6	678.4
42.5°	358.6	383.0	410.6	449.4	500.0	529.1	560.9	613.4	644.3	639.7	613.9
45°	334.1	355.8	383.4	419.9	471.5	501.4	528.2	577.9	600.5	589.0	542.0
47.5°	310.6	331.8	354.4	390.8	441.1	466.4	493.6	538.3	551.2	526.8	479.8
50°	285.3	302.8	326.3	360.9	407.9	434.6	457.2	493.1	497.7	467.8	418.9
52.5°	260.9	275.6	298.2	332.3	376.1	397.3	419.4	451.2	447.5	416.6	369.6
55°	235.0	248.9	269.6	301.0	339.7	359.9	378.8	407.0	399.1	367.3	326.3
57.5°	213.4	223.1	243.3	272.4	304.2	326.3	342.4	364.6	352.6	320.8	282.5
60°	188.5	200.5	217.5	241.0	272.4	287.1	301.4	316.2	307.9	277.4	243.3
62.5°	165.9	175.1	189.9	212.5	236.9	250.3	265.5	274.7	266.4	238.3	209.7
65°	146.6	153.9	165.5	183.9	207.4	218.5	227.2	236.0	229.1	202.8	182.0
67.5°	125.4	131.8	141.5	156.2	176.1	183.9	192.2	198.2	190.3	172.8	152.5
70°	106.5	111.1	120.3	131.3	145.2	152.5	159.5	165.5	158.5	143.8	128.6
72.5°	87.1	90.8	99.1	106.9	119.4	124.4	129.5	134.1	131.8	118.0	105.5
75°	71.9	73.3	78.8	85.3	93.1	98.6	102.3	105.1	103.2	92.2	84.3
77.5°	54.4	56.2	60.4	65.4	72.4	75.6	77.9	80.7	78.3	69.6	64.1
80°	39.6	40.1	42.4	47.0	51.6	52.1	54.4	58.1	56.7	50.7	46.5
82.5°	25.3	26.7	27.7	30.4	33.6	34.6	35.9	36.9	36.4	32.7	31.3
85°	14.7	14.7	15.7	17.5	18.4	19.8	20.3	20.7	21.7	19.4	18.0
87.5°	6.5	6.9	6.9	7.4	8.3	8.3	8.8	9.2	9.7	9.2	7.8
90°	1.0	3.0	5.9	6.9	7.9	7.9	7.9	13.8	13.8	15.8	17.8
92.5°	13.8	19.8	30.6	45.5	63.3	76.2	89.0	150.2	246.1	339.0	387.4
95°	32.6	35.6	45.5	58.3	82.0	102.8	123.5	209.5	371.6	607.8	805.5
97.5°	54.4	54.4	63.3	75.1	95.9	113.7	131.5	199.6	339.0	582.1	861.8
100°	75.1	75.1	82.0	93.9	112.7	128.5	144.3	202.6	314.3	515.9	794.6
102.5°	94.9	96.9	102.8	113.7	131.5	146.3	161.1	212.5	307.4	471.4	710.6
105°	115.6	118.6	123.5	135.4	153.2	167.6	181.9	229.3	311.3	449.7	648.4
107.5°	138.4	140.3	145.3	158.1	174.9	189.2	203.6	247.1	323.2	443.8	607.8
110°	161.1	163.1	168.0	179.9	197.7	211.0	224.4	267.8	337.0	445.7	589.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.8	184.8	190.8	201.6	219.4	232.8	246.1	287.6	351.9	451.7	580.2
115°	203.6	206.6	213.5	223.4	242.1	255.4	268.8	308.4	367.7	459.6	578.2
117.5°	225.3	228.3	234.2	245.1	262.9	276.8	290.6	328.1	383.5	467.5	577.2
120°	247.1	249.1	256.0	266.9	283.7	297.5	311.3	348.9	400.3	476.4	577.2
122.5°	266.9	268.8	275.8	285.6	304.4	317.8	331.1	368.7	416.1	485.3	576.2
125°	283.7	287.6	293.5	304.4	323.2	337.0	350.9	386.4	431.9	494.2	575.2
127.5°	299.5	302.4	309.4	321.2	341.0	354.8	368.7	403.3	445.7	501.1	573.2
130°	312.3	316.3	324.2	339.0	357.8	372.1	386.4	420.1	458.6	509.0	572.3
132.5°	325.2	328.1	339.0	352.8	373.6	387.0	400.3	433.9	471.4	515.9	571.3
135°	337.0	341.0	350.9	367.7	388.4	401.2	414.1	446.7	482.3	522.8	570.3
137.5°	348.9	352.8	363.7	379.5	401.3	413.6	426.0	456.6	490.2	526.8	570.3
140°	361.7	364.7	375.6	392.4	413.1	425.0	436.9	466.5	498.1	531.7	569.3
142.5°	375.6	378.5	388.4	404.2	424.0	435.4	446.7	475.4	504.1	535.7	569.3
145°	388.4	391.4	401.3	415.1	433.9	444.8	455.6	481.3	508.0	536.7	567.3
147.5°	403.3	404.2	413.1	428.0	443.8	453.6	463.5	488.2	512.0	537.7	564.4
150°	417.1	418.1	426.0	437.8	452.7	462.0	471.4	493.2	514.9	537.7	561.4
152.5°	429.9	429.9	437.8	448.7	461.6	470.0	478.4	497.1	516.9	535.7	556.4
155°	441.8	442.8	448.7	458.6	469.5	476.9	484.3	501.1	517.9	533.7	551.5
157.5°	453.7	453.7	459.6	467.5	477.4	483.3	489.2	504.1	517.9	531.7	546.6
160°	464.5	464.5	468.5	475.4	483.3	488.8	494.2	506.0	517.9	528.8	540.6
162.5°	474.4	473.4	476.4	482.3	489.2	493.2	497.1	508.0	517.9	525.8	534.7
165°	481.3	481.3	483.3	488.2	493.2	496.2	499.1	508.0	515.9	521.9	528.8
167.5°	489.2	488.2	489.2	493.2	496.2	498.6	501.1	508.0	513.9	517.9	522.8
170°	494.2	493.2	494.2	497.1	499.1	500.6	502.1	507.0	512.0	513.9	516.9
172.5°	499.1	498.1	498.1	500.1	501.1	502.1	503.1	506.0	510.0	510.0	511.0
175°	502.1	501.1	501.1	502.1	503.1	503.1	503.1	505.1	508.0	507.0	507.0
177.5°	504.1	503.1	502.1	503.1	503.1	503.1	503.1	504.1	506.0	504.1	504.1
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	581.2	589.5	593.1	594.1	599.1	595.9	597.3	596.8	600.5	601.0	601.0
5°	623.6	633.2	636.5	641.1	648.0	649.8	648.4	651.2	656.3	652.6	658.1
7.5°	668.3	678.9	686.2	696.4	698.7	704.7	708.4	711.6	712.5	713.0	713.9
10°	709.7	723.1	733.3	750.3	754.0	757.2	773.3	766.9	775.2	772.4	773.3
12.5°	743.4	769.7	778.0	806.5	809.3	820.4	819.4	829.6	831.4	835.1	831.4
15°	787.6	818.1	831.4	847.5	856.8	869.7	872.0	885.8	891.3	896.4	891.3
17.5°	828.2	844.3	878.4	891.3	897.3	904.2	921.7	926.8	935.1	931.9	941.1
20°	848.5	871.5	907.5	929.6	938.8	945.3	960.0	967.8	971.1	971.1	972.0
22.5°	866.4	899.6	926.4	951.7	960.0	964.6	973.4	979.4	980.7	981.7	982.6
25°	882.6	912.5	934.2	948.5	951.7	951.7	956.8	953.1	947.1	951.7	954.5
27.5°	882.6	903.8	913.5	918.5	918.5	906.1	898.7	883.5	870.6	866.9	875.2
30°	867.8	877.5	864.1	851.7	842.0	833.7	804.7	781.6	777.0	773.8	786.3
32.5°	833.7	821.3	795.0	759.1	744.8	725.9	703.3	685.8	675.2	671.5	668.7
35°	773.3	741.1	707.0	658.6	648.4	624.5	593.6	580.7	563.2	562.7	568.7
37.5°	707.4	657.7	620.8	574.7	560.4	535.1	506.0	492.7	480.7	471.5	482.5
40°	630.5	587.2	530.9	493.1	472.9	459.5	435.1	420.3	414.8	410.2	417.1
42.5°	558.6	511.1	467.3	428.6	412.0	396.8	380.7	366.4	362.2	361.8	366.9
45°	487.1	440.6	400.0	366.9	356.3	347.0	331.4	327.2	320.3	315.7	318.0
47.5°	430.0	382.1	348.4	323.1	313.9	306.0	295.9	289.0	283.0	281.1	283.9
50°	373.8	341.5	306.9	285.7	278.8	271.5	263.6	257.2	254.4	252.6	254.4
52.5°	328.6	294.0	270.5	253.5	246.6	241.0	235.5	232.7	229.1	230.0	231.8
55°	288.0	257.6	237.8	225.4	221.2	218.9	212.0	208.8	207.4	206.5	207.4
57.5°	249.8	227.7	212.9	202.3	196.8	195.4	189.9	189.9	188.5	187.1	187.6
60°	219.4	200.5	186.2	177.9	177.0	174.7	171.0	170.5	167.3	168.7	169.1
62.5°	188.5	173.3	163.6	158.5	155.3	154.4	152.1	151.6	150.2	150.7	149.8
65°	164.1	151.6	141.9	137.8	136.4	136.0	134.1	132.7	131.8	132.7	131.8
67.5°	139.6	131.3	124.0	119.8	118.0	117.5	116.1	115.2	115.7	114.3	115.2
70°	116.6	108.3	103.7	101.4	100.5	99.1	99.1	99.1	99.1	98.2	97.7
72.5°	98.2	89.9	86.6	85.3	84.3	83.9	82.5	83.0	82.5	82.0	83.9
75°	77.9	72.8	69.6	68.2	69.1	67.7	66.4	67.3	65.9	66.4	68.2
77.5°	59.0	56.7	54.8	53.9	53.0	52.1	52.1	51.2	51.2	51.2	51.2
80°	42.9	42.4	39.2	38.7	38.7	37.8	37.8	37.8	37.8	37.3	37.8
82.5°	28.6	28.1	27.2	26.7	25.8	26.3	26.3	25.3	25.3	24.9	25.3
85°	16.6	16.6	15.7	15.2	14.7	15.2	14.3	13.8	14.3	13.8	14.3
87.5°	7.8	6.9	7.4	6.9	6.0	6.5	5.5	6.0	5.5	5.1	6.0
90°	16.8	17.8	18.8	19.8	19.8	19.8	20.8	21.7	20.8	20.8	20.8
92.5°	322.2	238.2	177.9	140.3	128.0	115.6	100.8	93.9	89.9	89.9	89.9
95°	828.2	732.4	579.2	446.7	398.8	350.9	302.4	271.8	254.0	241.2	254.0
97.5°	1038.8	1054.6	978.5	869.8	814.4	759.1	691.9	632.5	602.9	579.2	602.9
100°	1047.7	1192.0	1211.7	1163.3	1126.8	1090.2	1004.2	943.9	914.2	906.3	914.2
102.5°	973.5	1185.0	1302.7	1332.3	1322.4	1312.5	1268.1	1228.5	1196.9	1191.0	1196.9
105°	880.6	1107.0	1277.9	1375.8	1396.0	1416.3	1418.3	1410.4	1396.6	1390.6	1396.6
107.5°	804.5	1011.1	1195.9	1332.3	1373.8	1415.3	1458.8	1476.6	1484.5	1485.5	1484.5
110°	750.2	926.1	1097.1	1240.4	1294.8	1349.1	1419.3	1460.8	1478.6	1487.5	1478.6

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	719.5	863.8	1010.1	1143.5	1197.9	1252.3	1334.3	1386.7	1413.4	1429.2	1413.4
115°	702.7	826.3	947.8	1063.5	1111.0	1158.4	1236.4	1295.7	1327.4	1335.3	1327.4
117.5°	693.8	804.5	907.3	1001.2	1042.7	1084.2	1153.4	1204.8	1238.4	1243.4	1238.4
120°	686.9	790.7	882.6	961.7	996.8	1031.8	1088.2	1131.7	1157.4	1168.2	1157.4
122.5°	679.0	778.8	866.8	937.0	966.6	996.3	1041.7	1077.3	1098.1	1108.9	1098.1
125°	670.1	765.0	850.0	918.2	945.4	972.5	1012.1	1040.7	1059.5	1065.5	1059.5
127.5°	658.2	749.2	831.2	899.4	925.1	950.8	990.3	1016.0	1031.8	1037.8	1031.8
130°	647.4	729.4	807.5	874.7	900.9	927.1	967.6	992.3	1008.1	1014.1	1008.1
132.5°	637.5	708.7	780.8	846.0	872.2	898.4	938.0	966.6	981.4	987.4	981.4
135°	627.6	689.9	754.1	814.4	839.1	863.8	903.4	931.0	946.8	952.8	946.8
137.5°	618.7	672.1	728.4	780.8	803.6	826.3	863.8	892.5	905.3	912.3	905.3
140°	611.8	657.3	703.7	748.2	769.0	789.7	824.3	846.0	859.9	867.8	859.9
142.5°	605.9	643.4	683.0	719.5	736.8	754.1	783.8	803.5	815.4	820.3	815.4
145°	598.9	630.6	664.2	693.8	707.6	721.5	746.2	763.0	772.9	777.8	772.9
147.5°	593.0	619.7	647.4	672.1	683.4	694.8	713.6	728.4	736.3	738.3	736.3
150°	586.1	609.8	632.5	652.3	661.2	670.1	685.9	698.8	704.7	705.7	704.7
152.5°	578.2	598.9	617.7	635.5	642.4	649.4	662.2	672.1	675.0	676.0	675.0
155°	570.3	588.1	603.9	618.7	624.7	630.6	640.5	648.4	651.3	651.3	651.3
157.5°	562.4	576.2	590.1	602.9	607.8	612.8	620.7	626.6	628.6	628.6	628.6
160°	553.5	565.3	576.2	587.1	591.0	595.0	600.9	606.9	607.8	607.8	607.8
162.5°	545.6	554.5	563.4	571.3	574.8	578.2	582.1	588.1	589.1	588.1	589.1
165°	536.7	544.6	550.5	557.4	559.9	562.4	566.3	570.3	569.3	568.3	569.3
167.5°	528.8	534.7	539.6	545.6	547.0	548.5	550.5	553.5	553.5	552.5	553.5
170°	520.9	525.8	528.8	532.7	534.2	535.7	537.7	538.7	537.7	537.7	537.7
172.5°	513.9	517.9	519.9	521.9	522.8	523.8	524.8	525.8	524.8	522.8	524.8
175°	509.0	511.0	512.0	513.9	513.9	513.9	513.9	515.9	513.9	512.0	513.9
177.5°	505.1	506.0	507.0	507.0	507.5	508.0	507.0	508.0	506.0	504.1	506.0
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	600.1	598.7	596.8	596.8	594.5	594.5	590.8	584.4	578.9	577.0	577.9
5°	651.2	651.7	648.9	646.6	642.5	639.2	633.2	621.7	618.0	610.7	605.6
7.5°	709.7	707.9	702.8	699.1	698.2	690.8	677.9	664.1	653.1	645.7	635.1
10°	775.7	768.3	760.9	758.6	753.1	740.6	725.9	710.7	695.5	679.3	661.4
12.5°	831.0	816.7	816.2	810.7	800.1	793.2	775.7	754.0	727.7	709.7	689.5
15°	890.4	877.0	866.0	855.8	850.8	830.5	815.7	788.6	757.2	737.9	724.0
17.5°	932.8	926.8	907.9	903.3	896.4	872.9	849.4	822.7	795.5	768.3	730.9
20°	966.9	963.2	950.8	944.3	933.3	914.8	886.3	855.4	824.0	785.3	750.3
22.5°	981.7	977.1	966.9	961.4	954.5	938.8	914.4	879.3	838.3	803.8	766.4
25°	952.6	960.9	958.2	955.9	953.1	943.9	925.4	894.6	854.5	815.3	768.7
27.5°	887.2	901.5	915.3	917.1	921.7	925.4	918.1	895.9	862.3	820.8	769.7
30°	799.2	805.6	833.7	842.0	848.5	872.0	885.8	880.3	854.5	817.1	770.1
32.5°	686.2	703.3	731.9	751.7	769.2	795.5	831.4	845.7	836.5	806.1	759.5
35°	579.3	599.6	632.8	658.1	675.6	713.0	755.4	786.3	797.8	782.6	741.1
37.5°	491.8	516.2	545.7	555.4	575.6	621.7	680.2	723.1	751.2	752.6	720.3
40°	425.8	438.3	461.8	476.5	496.4	535.1	592.2	648.9	691.3	705.6	688.5
42.5°	370.1	379.8	397.3	415.2	433.2	462.7	515.3	568.3	625.4	654.0	653.5
45°	325.8	336.0	348.0	362.7	375.2	407.0	448.4	502.8	552.1	596.4	607.4
47.5°	287.1	295.9	310.6	317.1	325.4	355.3	391.3	442.0	493.1	543.8	556.7
50°	258.6	265.9	276.1	280.2	289.4	311.6	341.0	382.1	438.8	485.3	509.3
52.5°	232.7	238.3	246.1	249.3	255.8	272.4	299.1	331.4	378.4	426.3	460.0
55°	210.6	214.3	219.8	223.5	228.1	242.9	262.7	291.7	332.3	373.8	406.5
57.5°	189.9	192.6	198.2	200.0	203.7	215.2	229.1	253.5	290.8	327.7	359.5
60°	170.5	172.4	175.6	179.7	182.5	190.3	203.2	223.5	253.5	287.1	312.9
62.5°	152.1	154.9	155.8	157.6	159.9	167.3	177.4	192.2	218.5	246.1	273.3
65°	133.2	135.5	137.3	137.8	140.1	145.6	154.9	167.8	184.8	208.8	234.1
67.5°	115.7	117.1	118.0	119.8	122.1	124.9	132.3	141.9	157.6	177.0	197.3
70°	99.5	99.5	100.9	101.4	104.2	107.4	110.6	119.8	133.7	149.3	163.1
72.5°	82.0	84.3	83.9	86.2	85.7	88.0	92.2	98.2	108.3	120.7	134.1
75°	66.8	68.2	68.2	68.2	69.1	71.0	73.3	78.8	86.6	96.8	104.6
77.5°	52.1	53.0	53.0	53.0	53.5	55.3	57.6	61.3	66.8	72.8	77.4
80°	37.3	38.3	38.3	39.2	39.2	39.6	41.9	43.8	46.5	51.2	55.8
82.5°	25.3	25.8	26.7	26.7	26.3	27.2	27.7	29.5	32.3	33.2	36.4
85°	13.8	14.3	14.7	14.7	15.2	16.1	15.7	17.5	17.5	19.4	20.3
87.5°	5.5	6.5	6.5	6.0	6.5	6.5	6.5	7.4	7.8	8.3	7.8
90°	21.7	20.8	19.8	19.8	19.8	18.8	17.8	16.8	17.8	15.8	13.8
92.5°	93.9	100.8	115.6	128.0	140.3	177.9	238.2	322.2	387.4	339.0	246.1
95°	271.8	302.4	350.9	398.8	446.7	579.2	732.4	828.2	805.5	607.8	371.6
97.5°	632.5	691.9	759.1	814.4	869.8	978.5	1054.6	1038.8	861.8	582.1	339.0
100°	943.9	1004.2	1090.2	1126.8	1163.3	1211.7	1192.0	1047.7	794.6	515.9	314.3
102.5°	1228.5	1268.1	1312.5	1322.4	1332.3	1302.7	1185.0	973.5	710.6	471.4	307.4
105°	1410.4	1418.3	1416.3	1396.0	1375.8	1277.9	1107.0	880.6	648.4	449.7	311.3
107.5°	1476.6	1458.8	1415.3	1373.8	1332.3	1195.9	1011.1	804.5	607.8	443.8	323.2
110°	1460.8	1419.3	1349.1	1294.8	1240.4	1097.1	926.1	750.2	589.1	445.7	337.0

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1386.7	1334.3	1252.3	1197.9	1143.5	1010.1	863.8	719.5	580.2	451.7	351.9
115°	1295.7	1236.4	1158.4	1111.0	1063.5	947.8	826.3	702.7	578.2	459.6	367.7
117.5°	1204.8	1153.4	1084.2	1042.7	1001.2	907.3	804.5	693.8	577.2	467.5	383.5
120°	1131.7	1088.2	1031.8	996.8	961.7	882.6	790.7	686.9	577.2	476.4	400.3
122.5°	1077.3	1041.7	996.3	966.6	937.0	866.8	778.8	679.0	576.2	485.3	416.1
125°	1040.7	1012.1	972.5	945.4	918.2	850.0	765.0	670.1	575.2	494.2	431.9
127.5°	1016.0	990.3	950.8	925.1	899.4	831.2	749.2	658.2	573.2	501.1	445.7
130°	992.3	967.6	927.1	900.9	874.7	807.5	729.4	647.4	572.3	509.0	458.6
132.5°	966.6	938.0	898.4	872.2	846.0	780.8	708.7	637.5	571.3	515.9	471.4
135°	931.0	903.4	863.8	839.1	814.4	754.1	689.9	627.6	570.3	522.8	482.3
137.5°	892.5	863.8	826.3	803.6	780.8	728.4	672.1	618.7	570.3	526.8	490.2
140°	846.0	824.3	789.7	769.0	748.2	703.7	657.3	611.8	569.3	531.7	498.1
142.5°	803.5	783.8	754.1	736.8	719.5	683.0	643.4	605.9	569.3	535.7	504.1
145°	763.0	746.2	721.5	707.6	693.8	664.2	630.6	598.9	567.3	536.7	508.0
147.5°	728.4	713.6	694.8	683.4	672.1	647.4	619.7	593.0	564.4	537.7	512.0
150°	698.8	685.9	670.1	661.2	652.3	632.5	609.8	586.1	561.4	537.7	514.9
152.5°	672.1	662.2	649.4	642.4	635.5	617.7	598.9	578.2	556.4	535.7	516.9
155°	648.4	640.5	630.6	624.7	618.7	603.9	588.1	570.3	551.5	533.7	517.9
157.5°	626.6	620.7	612.8	607.8	602.9	590.1	576.2	562.4	546.6	531.7	517.9
160°	606.9	600.9	595.0	591.0	587.1	576.2	565.3	553.5	540.6	528.8	517.9
162.5°	588.1	582.1	578.2	574.8	571.3	563.4	554.5	545.6	534.7	525.8	517.9
165°	570.3	566.3	562.4	559.9	557.4	550.5	544.6	536.7	528.8	521.9	515.9
167.5°	553.5	550.5	548.5	547.0	545.6	539.6	534.7	528.8	522.8	517.9	513.9
170°	538.7	537.7	535.7	534.2	532.7	528.8	525.8	520.9	516.9	513.9	512.0
172.5°	525.8	524.8	523.8	522.8	521.9	519.9	517.9	513.9	511.0	510.0	510.0
175°	515.9	513.9	513.9	513.9	513.9	512.0	511.0	509.0	507.0	507.0	508.0
177.5°	508.0	507.0	508.0	507.5	507.0	507.0	506.0	505.1	504.1	504.1	506.0
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	573.8	571.9	570.6	570.6	566.4	562.3	560.0	559.0	558.1	554.4	549.4
5°	597.3	591.3	587.2	583.0	576.1	568.7	561.3	557.2	551.2	542.9	536.9
7.5°	623.6	609.3	604.7	599.6	585.8	573.3	563.2	554.4	544.8	534.2	523.6
10°	645.7	630.5	620.3	611.6	593.6	577.0	561.8	548.9	536.5	522.6	509.7
12.5°	666.9	645.2	634.6	621.7	602.8	578.9	559.0	542.9	524.5	510.2	494.5
15°	696.4	660.0	642.5	634.2	608.8	580.7	556.7	532.8	517.6	495.9	482.1
17.5°	701.0	671.5	660.0	638.8	608.4	576.6	548.9	524.9	501.9	482.5	464.6
20°	717.1	678.4	660.0	646.6	606.5	574.2	543.8	513.0	490.8	470.1	449.8
22.5°	727.3	683.5	664.1	642.9	604.7	566.0	530.0	503.3	476.1	454.9	438.8
25°	724.5	680.7	659.0	639.2	592.7	554.0	521.7	487.6	462.3	439.2	418.0
27.5°	723.1	673.8	650.8	628.6	584.8	544.3	503.7	476.1	448.0	421.2	405.6
30°	719.4	665.0	638.3	614.3	568.7	526.3	491.8	459.5	431.4	407.0	386.2
32.5°	707.0	650.3	624.5	598.7	551.2	508.8	473.8	443.8	415.7	390.4	370.5
35°	690.4	632.8	604.7	577.5	530.0	487.1	454.9	423.5	397.3	372.8	354.0
37.5°	673.8	612.5	586.2	554.9	511.1	466.4	433.2	405.1	380.7	355.3	334.6
40°	649.8	588.5	559.5	532.8	481.6	439.7	409.3	383.9	359.9	336.0	318.5
42.5°	617.1	562.3	532.3	502.8	454.9	413.4	383.9	361.3	338.7	318.9	299.6
45°	583.9	530.5	503.7	477.5	425.4	386.2	359.0	338.3	319.4	297.7	282.1
47.5°	543.8	498.7	471.9	446.1	396.8	357.6	332.8	313.4	295.9	277.9	263.2
50°	502.8	463.6	439.2	412.5	365.5	330.0	305.6	289.4	275.1	258.1	246.1
52.5°	458.6	424.5	403.7	377.9	336.4	303.7	278.8	262.7	250.7	238.3	227.7
55°	411.6	386.7	364.6	343.8	304.6	275.1	253.0	238.7	230.4	218.9	209.7
57.5°	369.2	345.2	331.8	308.3	274.2	245.2	227.7	215.7	206.0	199.1	191.7
60°	324.9	305.6	290.8	273.8	243.8	219.4	200.9	194.0	183.9	178.8	175.6
62.5°	282.5	268.7	254.9	242.0	215.2	192.2	178.4	169.6	163.6	158.5	155.8
65°	242.4	229.5	219.8	208.3	186.2	167.8	154.9	147.9	141.9	140.6	137.3
67.5°	203.2	197.7	187.1	177.9	159.0	144.7	135.0	126.3	123.1	121.7	118.9
70°	170.1	163.6	155.3	147.5	133.2	120.7	112.0	108.8	104.2	103.7	100.5
72.5°	140.1	132.3	126.3	120.3	109.7	98.6	94.0	89.4	87.1	85.3	83.9
75°	111.1	105.5	101.4	96.3	87.1	79.7	73.3	71.4	70.1	69.6	68.7
77.5°	83.0	79.3	77.4	72.4	65.9	59.5	56.7	53.9	53.9	53.0	53.5
80°	59.0	56.7	54.4	51.6	46.1	43.3	41.0	39.2	38.3	37.8	38.3
82.5°	37.3	35.9	35.5	33.6	30.0	28.6	26.7	25.3	25.3	25.3	25.3
85°	20.7	20.7	20.7	18.0	16.6	15.2	14.3	13.8	13.8	13.8	14.3
87.5°	8.8	8.8	7.4	7.4	6.9	6.0	5.5	5.5	6.0	6.0	6.5
90°	13.8	7.9	7.9	7.9	6.9	5.9	3.0	1.0	3.0	5.9	6.9
92.5°	150.2	89.0	76.2	63.3	45.5	30.6	19.8	13.8	19.8	30.6	45.5
95°	209.5	123.5	102.8	82.0	58.3	45.5	35.6	32.6	35.6	45.5	58.3
97.5°	199.6	131.5	113.7	95.9	75.1	63.3	54.4	54.4	54.4	63.3	75.1
100°	202.6	144.3	128.5	112.7	93.9	82.0	75.1	75.1	75.1	82.0	93.9
102.5°	212.5	161.1	146.3	131.5	113.7	102.8	96.9	94.9	96.9	102.8	113.7
105°	229.3	181.9	167.6	153.2	135.4	123.5	118.6	115.6	118.6	123.5	135.4
107.5°	247.1	203.6	189.2	174.9	158.1	145.3	140.3	138.4	140.3	145.3	158.1
110°	267.8	224.4	211.0	197.7	179.9	168.0	163.1	161.1	163.1	168.0	179.9

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	287.6	246.1	232.8	219.4	201.6	190.8	184.8	182.8	184.8	190.8	201.6
115°	308.4	268.8	255.4	242.1	223.4	213.5	206.6	203.6	206.6	213.5	223.4
117.5°	328.1	290.6	276.8	262.9	245.1	234.2	228.3	225.3	228.3	234.2	245.1
120°	348.9	311.3	297.5	283.7	266.9	256.0	249.1	247.1	249.1	256.0	266.9
122.5°	368.7	331.1	317.8	304.4	285.6	275.8	268.8	266.9	268.8	275.8	285.6
125°	386.4	350.9	337.0	323.2	304.4	293.5	287.6	283.7	287.6	293.5	304.4
127.5°	403.3	368.7	354.8	341.0	321.2	309.4	302.4	299.5	302.4	309.4	321.2
130°	420.1	386.4	372.1	357.8	339.0	324.2	316.3	312.3	316.3	324.2	339.0
132.5°	433.9	400.3	387.0	373.6	352.8	339.0	328.1	325.2	328.1	339.0	352.8
135°	446.7	414.1	401.2	388.4	367.7	350.9	341.0	337.0	341.0	350.9	367.7
137.5°	456.6	426.0	413.6	401.3	379.5	363.7	352.8	348.9	352.8	363.7	379.5
140°	466.5	436.9	425.0	413.1	392.4	375.6	364.7	361.7	364.7	375.6	392.4
142.5°	475.4	446.7	435.4	424.0	404.2	388.4	378.5	375.6	378.5	388.4	404.2
145°	481.3	455.6	444.8	433.9	415.1	401.3	391.4	388.4	391.4	401.3	415.1
147.5°	488.2	463.5	453.6	443.8	428.0	413.1	404.2	403.3	404.2	413.1	428.0
150°	493.2	471.4	462.0	452.7	437.8	426.0	418.1	417.1	418.1	426.0	437.8
152.5°	497.1	478.4	470.0	461.6	448.7	437.8	429.9	429.9	429.9	437.8	448.7
155°	501.1	484.3	476.9	469.5	458.6	448.7	442.8	441.8	442.8	448.7	458.6
157.5°	504.1	489.2	483.3	477.4	467.5	459.6	453.7	453.7	453.7	459.6	467.5
160°	506.0	494.2	488.8	483.3	475.4	468.5	464.5	464.5	464.5	468.5	475.4
162.5°	508.0	497.1	493.2	489.2	482.3	476.4	473.4	474.4	473.4	476.4	482.3
165°	508.0	499.1	496.2	493.2	488.2	483.3	481.3	481.3	481.3	483.3	488.2
167.5°	508.0	501.1	498.6	496.2	493.2	489.2	488.2	489.2	488.2	489.2	493.2
170°	507.0	502.1	500.6	499.1	497.1	494.2	493.2	494.2	493.2	494.2	497.1
172.5°	506.0	503.1	502.1	501.1	500.1	498.1	498.1	499.1	498.1	498.1	500.1
175°	505.1	503.1	503.1	503.1	502.1	501.1	501.1	502.1	501.1	501.1	502.1
177.5°	504.1	503.1	503.1	503.1	503.1	502.1	503.1	504.1	503.1	502.1	503.1
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	548.0	546.1	547.1	542.4	538.3	532.3	527.2	526.3	525.4	528.2	526.3
5°	532.3	530.0	527.7	522.2	513.9	508.8	501.4	501.0	498.2	494.1	495.0
7.5°	515.3	513.9	510.6	501.9	494.5	485.8	479.8	474.7	472.4	468.7	467.3
10°	501.4	496.4	493.6	483.9	475.2	465.9	458.1	454.4	450.3	447.0	444.7
12.5°	482.5	481.2	473.3	465.5	458.1	447.5	441.5	430.9	425.4	428.2	427.2
15°	470.1	463.6	461.8	450.7	438.3	431.4	420.3	413.4	411.1	407.0	401.9
17.5°	453.5	449.4	442.9	432.8	418.5	408.8	401.0	394.5	391.7	386.2	382.1
20°	437.8	430.9	425.8	416.6	402.8	390.4	380.7	376.5	369.6	365.0	362.7
22.5°	423.5	418.5	411.1	397.3	385.3	373.3	361.8	355.8	349.3	346.6	342.9
25°	406.0	397.7	392.7	377.5	364.6	354.9	344.3	336.4	332.8	328.1	327.2
27.5°	389.0	381.1	375.2	361.8	346.1	333.7	327.2	321.7	315.2	315.2	312.9
30°	371.9	366.4	357.2	344.3	329.5	317.5	310.2	305.1	302.8	301.0	300.5
32.5°	354.9	347.5	342.0	324.5	313.4	302.3	296.8	292.7	289.9	289.4	289.9
35°	337.4	329.1	323.5	307.9	296.8	286.7	284.4	280.7	279.3	278.8	281.1
37.5°	318.9	312.5	305.6	292.7	280.2	274.2	269.6	268.2	267.8	270.5	271.5
40°	301.9	296.3	289.9	276.1	266.8	260.4	258.1	256.7	258.6	261.3	262.7
42.5°	285.7	277.9	272.8	260.4	252.1	248.4	245.6	245.6	247.5	250.7	253.0
45°	268.7	262.7	257.6	246.6	239.2	235.0	234.6	235.0	237.4	239.7	242.4
47.5°	252.1	246.1	240.6	231.4	224.9	222.6	222.1	222.6	226.3	229.5	232.7
50°	236.9	230.4	225.4	216.6	211.5	208.8	209.2	211.5	214.3	218.9	223.1
52.5°	218.9	214.3	209.7	201.9	197.3	195.4	196.8	198.6	203.7	206.9	212.0
55°	201.4	197.3	193.6	187.6	183.9	182.5	183.4	186.2	190.3	195.9	201.9
57.5°	185.3	180.7	177.0	172.8	168.7	169.1	169.6	173.3	178.4	183.4	190.3
60°	167.3	164.5	161.3	156.2	154.4	154.4	155.8	159.9	164.5	172.8	178.8
62.5°	151.2	147.5	145.2	141.9	139.2	139.6	142.9	146.6	152.1	159.0	166.8
65°	134.6	130.4	128.6	125.8	124.9	125.4	127.7	133.2	139.2	145.2	152.5
67.5°	116.1	114.8	112.9	110.1	111.1	111.5	113.8	118.4	124.9	130.9	139.2
70°	100.5	97.7	97.2	94.9	94.9	96.3	100.9	104.2	110.1	116.6	125.4
72.5°	83.9	81.6	81.6	79.7	81.1	82.5	84.8	89.4	94.9	101.4	108.8
75°	66.8	65.9	66.8	65.9	65.9	68.2	71.0	74.7	80.7	87.6	93.6
77.5°	51.6	51.6	51.2	52.5	52.5	53.9	57.6	61.3	65.9	71.4	77.9
80°	37.8	37.8	37.8	39.2	40.6	40.6	42.9	47.5	51.6	55.3	61.3
82.5°	25.8	25.8	25.8	26.7	28.6	28.6	31.3	34.1	38.7	41.9	44.7
85°	15.7	15.7	15.2	16.1	16.6	18.0	20.3	22.1	24.4	27.2	30.0
87.5°	6.9	6.9	7.4	7.8	8.3	9.2	10.1	11.1	13.4	14.3	15.7
90°	7.9	7.9	7.9	13.8	13.8	15.8	17.8	16.8	17.8	18.8	19.8
92.5°	63.3	76.2	89.0	150.2	246.1	339.0	387.4	322.2	238.2	177.9	140.3
95°	82.0	102.8	123.5	209.5	371.6	607.8	805.5	828.2	732.4	579.2	446.7
97.5°	95.9	113.7	131.5	199.6	339.0	582.1	861.8	1038.8	1054.6	978.5	869.8
100°	112.7	128.5	144.3	202.6	314.3	515.9	794.6	1047.7	1192.0	1211.7	1163.3
102.5°	131.5	146.3	161.1	212.5	307.4	471.4	710.6	973.5	1185.0	1302.7	1332.3
105°	153.2	167.6	181.9	229.3	311.3	449.7	648.4	880.6	1107.0	1277.9	1375.8
107.5°	174.9	189.2	203.6	247.1	323.2	443.8	607.8	804.5	1011.1	1195.9	1332.3
110°	197.7	211.0	224.4	267.8	337.0	445.7	589.1	750.2	926.1	1097.1	1240.4

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	219.4	232.8	246.1	287.6	351.9	451.7	580.2	719.5	863.8	1010.1	1143.5
115°	242.1	255.4	268.8	308.4	367.7	459.6	578.2	702.7	826.3	947.8	1063.5
117.5°	262.9	276.8	290.6	328.1	383.5	467.5	577.2	693.8	804.5	907.3	1001.2
120°	283.7	297.5	311.3	348.9	400.3	476.4	577.2	686.9	790.7	882.6	961.7
122.5°	304.4	317.8	331.1	368.7	416.1	485.3	576.2	679.0	778.8	866.8	937.0
125°	323.2	337.0	350.9	386.4	431.9	494.2	575.2	670.1	765.0	850.0	918.2
127.5°	341.0	354.8	368.7	403.3	445.7	501.1	573.2	658.2	749.2	831.2	899.4
130°	357.8	372.1	386.4	420.1	458.6	509.0	572.3	647.4	729.4	807.5	874.7
132.5°	373.6	387.0	400.3	433.9	471.4	515.9	571.3	637.5	708.7	780.8	846.0
135°	388.4	401.2	414.1	446.7	482.3	522.8	570.3	627.6	689.9	754.1	814.4
137.5°	401.3	413.6	426.0	456.6	490.2	526.8	570.3	618.7	672.1	728.4	780.8
140°	413.1	425.0	436.9	466.5	498.1	531.7	569.3	611.8	657.3	703.7	748.2
142.5°	424.0	435.4	446.7	475.4	504.1	535.7	569.3	605.9	643.4	683.0	719.5
145°	433.9	444.8	455.6	481.3	508.0	536.7	567.3	598.9	630.6	664.2	693.8
147.5°	443.8	453.6	463.5	488.2	512.0	537.7	564.4	593.0	619.7	647.4	672.1
150°	452.7	462.0	471.4	493.2	514.9	537.7	561.4	586.1	609.8	632.5	652.3
152.5°	461.6	470.0	478.4	497.1	516.9	535.7	556.4	578.2	598.9	617.7	635.5
155°	469.5	476.9	484.3	501.1	517.9	533.7	551.5	570.3	588.1	603.9	618.7
157.5°	477.4	483.3	489.2	504.1	517.9	531.7	546.6	562.4	576.2	590.1	602.9
160°	483.3	488.8	494.2	506.0	517.9	528.8	540.6	553.5	565.3	576.2	587.1
162.5°	489.2	493.2	497.1	508.0	517.9	525.8	534.7	545.6	554.5	563.4	571.3
165°	493.2	496.2	499.1	508.0	515.9	521.9	528.8	536.7	544.6	550.5	557.4
167.5°	496.2	498.6	501.1	508.0	513.9	517.9	522.8	528.8	534.7	539.6	545.6
170°	499.1	500.6	502.1	507.0	512.0	513.9	516.9	520.9	525.8	528.8	532.7
172.5°	501.1	502.1	503.1	506.0	510.0	510.0	511.0	513.9	517.9	519.9	521.9
175°	503.1	503.1	503.1	505.1	508.0	507.0	507.0	509.0	511.0	512.0	513.9
177.5°	503.1	503.1	503.1	504.1	506.0	504.1	504.1	505.1	506.0	507.0	507.0
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	524.9	524.5	522.2	523.1	520.3	521.2	522.6	523.1	524.9	523.6	523.1
5°	492.7	491.8	490.4	489.0	488.5	490.4	487.1	488.1	489.0	490.4	492.2
7.5°	466.4	465.9	464.6	462.3	461.3	460.4	460.9	464.1	463.6	463.2	466.4
10°	442.4	442.9	440.1	439.7	436.9	436.4	436.9	437.8	439.2	441.1	441.5
12.5°	417.6	423.5	418.5	416.6	412.5	414.8	415.7	411.6	413.9	415.2	422.2
15°	401.9	399.1	395.9	395.9	394.0	393.1	390.8	394.0	395.9	398.7	397.7
17.5°	380.2	375.6	373.8	371.9	372.4	374.2	369.2	376.5	376.5	377.9	375.6
20°	361.3	357.6	355.3	354.4	353.0	352.1	351.6	353.5	356.3	357.2	359.5
22.5°	341.5	341.5	337.8	336.4	335.5	334.1	336.4	335.1	336.9	338.7	342.4
25°	324.9	324.9	323.5	321.7	320.3	319.4	320.8	320.3	321.7	324.0	324.9
27.5°	311.6	310.2	309.7	309.2	308.8	309.2	308.8	310.2	311.6	312.0	311.1
30°	300.0	298.6	299.1	299.1	299.6	299.1	298.6	300.0	300.5	299.6	300.0
32.5°	289.4	289.4	290.4	290.8	290.8	291.3	291.7	290.8	291.3	289.9	290.4
35°	280.7	281.6	282.5	283.0	283.4	283.0	283.9	283.4	282.5	281.6	281.1
37.5°	271.9	272.8	274.7	275.1	276.5	277.0	276.1	276.1	275.6	273.8	272.8
40°	262.7	263.6	265.9	267.3	268.2	269.6	268.7	268.7	266.8	265.0	263.6
42.5°	253.9	255.8	258.1	259.5	261.3	261.3	261.3	260.4	258.1	256.2	254.9
45°	245.2	245.6	248.9	251.2	253.0	253.0	253.0	251.6	250.3	246.6	244.7
47.5°	235.5	236.9	240.6	242.9	244.7	245.2	245.2	243.8	241.0	237.8	235.5
50°	224.9	227.2	231.4	234.6	236.9	237.8	236.4	235.5	232.3	228.6	225.8
52.5°	214.8	217.5	222.6	225.4	228.6	229.1	228.6	227.2	223.5	218.5	216.1
55°	204.6	206.9	212.5	217.1	219.8	220.8	219.8	217.5	212.9	207.9	205.5
57.5°	193.6	196.8	202.8	207.4	210.6	211.1	210.2	207.9	204.2	197.7	194.5
60°	182.0	186.2	192.2	196.8	200.9	201.4	200.5	197.3	192.6	186.2	183.4
62.5°	170.5	173.7	180.7	185.7	189.0	191.3	189.4	186.2	181.6	175.1	171.0
65°	157.2	161.8	167.8	172.4	176.1	176.5	175.6	172.8	167.8	160.8	157.6
67.5°	144.3	147.5	153.5	159.5	160.8	162.2	160.8	158.1	153.9	147.9	143.3
70°	128.6	131.3	138.7	142.9	144.7	146.1	145.2	142.4	138.7	133.2	129.5
72.5°	112.9	115.2	122.1	125.4	129.0	128.6	128.1	126.3	121.2	117.5	115.2
75°	96.3	99.1	103.7	107.8	109.2	109.2	109.2	107.8	104.6	98.6	96.3
77.5°	81.1	82.5	86.2	88.5	89.9	90.3	89.9	87.6	85.7	81.6	80.2
80°	62.2	65.9	68.7	69.1	71.0	71.0	71.0	70.1	68.2	64.1	63.6
82.5°	47.0	47.9	50.7	52.1	53.0	52.5	52.5	50.7	50.2	47.9	47.0
85°	31.8	33.2	32.7	34.6	35.0	34.1	34.1	35.0	32.7	33.2	31.8
87.5°	17.5	17.5	18.4	18.0	19.8	19.8	18.9	19.4	18.4	18.0	17.5
90°	19.8	19.8	20.8	21.7	20.8	20.8	20.8	21.7	20.8	19.8	19.8
92.5°	128.0	115.6	100.8	93.9	89.9	89.9	89.9	93.9	100.8	115.6	128.0
95°	398.8	350.9	302.4	271.8	254.0	241.2	254.0	271.8	302.4	350.9	398.8
97.5°	814.4	759.1	691.9	632.5	602.9	579.2	602.9	632.5	691.9	759.1	814.4
100°	1126.8	1090.2	1004.2	943.9	914.2	906.3	914.2	943.9	1004.2	1090.2	1126.8
102.5°	1322.4	1312.5	1268.1	1228.5	1196.9	1191.0	1196.9	1228.5	1268.1	1312.5	1322.4
105°	1396.0	1416.3	1418.3	1410.4	1396.6	1390.6	1396.6	1410.4	1418.3	1416.3	1396.0
107.5°	1373.8	1415.3	1458.8	1476.6	1484.5	1485.5	1484.5	1476.6	1458.8	1415.3	1373.8
110°	1294.8	1349.1	1419.3	1460.8	1478.6	1487.5	1478.6	1460.8	1419.3	1349.1	1294.8

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1197.9	1252.3	1334.3	1386.7	1413.4	1429.2	1413.4	1386.7	1334.3	1252.3	1197.9
115°	1111.0	1158.4	1236.4	1295.7	1327.4	1335.3	1327.4	1295.7	1236.4	1158.4	1111.0
117.5°	1042.7	1084.2	1153.4	1204.8	1238.4	1243.4	1238.4	1204.8	1153.4	1084.2	1042.7
120°	996.8	1031.8	1088.2	1131.7	1157.4	1168.2	1157.4	1131.7	1088.2	1031.8	996.8
122.5°	966.6	996.3	1041.7	1077.3	1098.1	1108.9	1098.1	1077.3	1041.7	996.3	966.6
125°	945.4	972.5	1012.1	1040.7	1059.5	1065.5	1059.5	1040.7	1012.1	972.5	945.4
127.5°	925.1	950.8	990.3	1016.0	1031.8	1037.8	1031.8	1016.0	990.3	950.8	925.1
130°	900.9	927.1	967.6	992.3	1008.1	1014.1	1008.1	992.3	967.6	927.1	900.9
132.5°	872.2	898.4	938.0	966.6	981.4	987.4	981.4	966.6	938.0	898.4	872.2
135°	839.1	863.8	903.4	931.0	946.8	952.8	946.8	931.0	903.4	863.8	839.1
137.5°	803.6	826.3	863.8	892.5	905.3	912.3	905.3	892.5	863.8	826.3	803.6
140°	769.0	789.7	824.3	846.0	859.9	867.8	859.9	846.0	824.3	789.7	769.0
142.5°	736.8	754.1	783.8	803.5	815.4	820.3	815.4	803.5	783.8	754.1	736.8
145°	707.6	721.5	746.2	763.0	772.9	777.8	772.9	763.0	746.2	721.5	707.6
147.5°	683.4	694.8	713.6	728.4	736.3	738.3	736.3	728.4	713.6	694.8	683.4
150°	661.2	670.1	685.9	698.8	704.7	705.7	704.7	698.8	685.9	670.1	661.2
152.5°	642.4	649.4	662.2	672.1	675.0	676.0	675.0	672.1	662.2	649.4	642.4
155°	624.7	630.6	640.5	648.4	651.3	651.3	651.3	648.4	640.5	630.6	624.7
157.5°	607.8	612.8	620.7	626.6	628.6	628.6	628.6	626.6	620.7	612.8	607.8
160°	591.0	595.0	600.9	606.9	607.8	607.8	607.8	606.9	600.9	595.0	591.0
162.5°	574.8	578.2	582.1	588.1	589.1	588.1	589.1	588.1	582.1	578.2	574.8
165°	559.9	562.4	566.3	570.3	569.3	568.3	569.3	570.3	566.3	562.4	559.9
167.5°	547.0	548.5	550.5	553.5	553.5	552.5	553.5	553.5	550.5	548.5	547.0
170°	534.2	535.7	537.7	538.7	537.7	537.7	537.7	538.7	537.7	535.7	534.2
172.5°	522.8	523.8	524.8	525.8	524.8	522.8	524.8	525.8	524.8	523.8	522.8
175°	513.9	513.9	513.9	515.9	513.9	512.0	513.9	515.9	513.9	513.9	513.9
177.5°	507.5	508.0	507.0	508.0	506.0	504.1	506.0	508.0	507.0	508.0	507.5
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	523.1	525.9	523.1	524.9	525.9	528.2	529.1	533.2	534.6	537.8	537.8
5°	491.8	493.1	493.6	495.4	497.3	501.9	505.1	511.1	518.0	518.9	523.1
7.5°	466.4	468.7	472.4	471.0	474.2	481.2	485.3	492.7	499.6	503.3	508.3
10°	443.8	446.6	448.0	449.4	455.3	461.3	467.8	472.9	482.1	487.6	491.8
12.5°	425.4	423.1	425.8	430.9	437.8	441.5	450.3	458.1	465.0	471.0	474.7
15°	401.4	403.3	406.0	414.8	416.6	425.8	429.1	437.8	450.7	456.3	460.9
17.5°	378.4	384.4	389.9	393.1	398.7	406.0	415.2	424.9	433.2	439.7	445.2
20°	359.9	365.9	369.2	371.5	377.0	387.1	395.9	407.9	418.5	423.5	430.9
22.5°	345.2	345.2	349.8	356.7	359.9	369.6	377.0	389.9	401.4	407.9	414.8
25°	326.8	329.5	333.2	339.2	343.8	351.6	362.2	373.3	385.8	391.3	400.0
27.5°	311.6	314.8	319.8	321.2	325.8	332.8	343.8	355.8	368.7	374.7	382.1
30°	300.0	301.9	303.7	306.5	310.6	316.6	325.8	336.4	352.1	356.7	365.9
32.5°	289.9	290.8	291.7	294.0	296.3	302.3	309.7	321.2	334.1	341.0	349.3
35°	280.7	279.8	280.2	281.6	283.9	286.2	294.0	303.7	315.7	324.0	330.4
37.5°	271.9	270.1	269.6	269.6	270.5	273.3	279.3	287.6	300.5	307.4	313.9
40°	262.2	260.4	259.5	259.0	258.6	260.4	265.0	273.3	283.4	289.9	297.3
42.5°	253.0	251.2	248.9	248.4	247.5	248.4	251.6	259.5	268.2	274.7	280.7
45°	243.8	240.6	237.8	236.0	236.4	235.0	237.4	243.3	253.5	257.6	263.6
47.5°	233.7	230.0	226.3	224.4	222.6	223.5	224.4	229.5	238.3	242.4	248.4
50°	224.0	218.9	214.8	212.5	211.1	210.2	211.1	216.1	222.6	226.3	231.4
52.5°	212.9	207.9	203.7	200.0	198.2	196.8	197.3	201.9	207.9	211.5	216.6
55°	202.8	196.3	190.8	186.2	184.8	184.3	183.9	187.1	192.2	195.9	200.0
57.5°	191.3	184.8	178.8	173.3	170.5	170.1	170.1	171.0	177.4	180.2	182.5
60°	179.7	172.8	166.4	161.3	157.2	155.8	155.3	157.2	160.4	163.1	166.4
62.5°	166.8	159.9	152.1	147.5	143.3	139.6	141.0	141.5	146.1	147.5	150.2
65°	154.4	146.6	140.1	132.7	128.1	125.8	124.9	125.8	129.5	130.0	131.8
67.5°	140.1	132.7	124.9	119.8	115.7	111.5	110.6	110.6	112.5	113.8	116.1
70°	126.3	118.9	110.1	104.6	100.5	96.8	95.4	94.9	96.3	97.2	99.5
72.5°	110.1	102.8	96.3	90.3	85.3	82.5	81.1	80.2	81.6	82.5	83.0
75°	93.1	87.1	80.7	74.7	71.4	68.7	66.8	65.4	66.4	66.4	66.4
77.5°	77.0	71.0	65.9	61.8	57.6	54.4	53.0	51.6	52.1	52.1	53.0
80°	59.9	55.8	51.6	47.9	44.2	41.5	40.6	39.2	38.3	37.8	37.8
82.5°	44.2	41.0	37.3	34.1	32.3	29.5	28.6	26.7	26.7	26.3	26.3
85°	29.5	27.7	24.0	21.7	20.3	18.9	18.0	17.1	15.7	15.7	15.2
87.5°	15.7	14.7	13.8	11.1	11.1	9.7	9.2	8.8	7.4	7.8	7.8
90°	19.8	18.8	17.8	16.8	17.8	15.8	13.8	13.8	7.9	7.9	7.9
92.5°	140.3	177.9	238.2	322.2	387.4	339.0	246.1	150.2	89.0	76.2	63.3
95°	446.7	579.2	732.4	828.2	805.5	607.8	371.6	209.5	123.5	102.8	82.0
97.5°	869.8	978.5	1054.6	1038.8	861.8	582.1	339.0	199.6	131.5	113.7	95.9
100°	1163.3	1211.7	1192.0	1047.7	794.6	515.9	314.3	202.6	144.3	128.5	112.7
102.5°	1332.3	1302.7	1185.0	973.5	710.6	471.4	307.4	212.5	161.1	146.3	131.5
105°	1375.8	1277.9	1107.0	880.6	648.4	449.7	311.3	229.3	181.9	167.6	153.2
107.5°	1332.3	1195.9	1011.1	804.5	607.8	443.8	323.2	247.1	203.6	189.2	174.9
110°	1240.4	1097.1	926.1	750.2	589.1	445.7	337.0	267.8	224.4	211.0	197.7

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1143.5	1010.1	863.8	719.5	580.2	451.7	351.9	287.6	246.1	232.8	219.4
115°	1063.5	947.8	826.3	702.7	578.2	459.6	367.7	308.4	268.8	255.4	242.1
117.5°	1001.2	907.3	804.5	693.8	577.2	467.5	383.5	328.1	290.6	276.8	262.9
120°	961.7	882.6	790.7	686.9	577.2	476.4	400.3	348.9	311.3	297.5	283.7
122.5°	937.0	866.8	778.8	679.0	576.2	485.3	416.1	368.7	331.1	317.8	304.4
125°	918.2	850.0	765.0	670.1	575.2	494.2	431.9	386.4	350.9	337.0	323.2
127.5°	899.4	831.2	749.2	658.2	573.2	501.1	445.7	403.3	368.7	354.8	341.0
130°	874.7	807.5	729.4	647.4	572.3	509.0	458.6	420.1	386.4	372.1	357.8
132.5°	846.0	780.8	708.7	637.5	571.3	515.9	471.4	433.9	400.3	387.0	373.6
135°	814.4	754.1	689.9	627.6	570.3	522.8	482.3	446.7	414.1	401.2	388.4
137.5°	780.8	728.4	672.1	618.7	570.3	526.8	490.2	456.6	426.0	413.6	401.3
140°	748.2	703.7	657.3	611.8	569.3	531.7	498.1	466.5	436.9	425.0	413.1
142.5°	719.5	683.0	643.4	605.9	569.3	535.7	504.1	475.4	446.7	435.4	424.0
145°	693.8	664.2	630.6	598.9	567.3	536.7	508.0	481.3	455.6	444.8	433.9
147.5°	672.1	647.4	619.7	593.0	564.4	537.7	512.0	488.2	463.5	453.6	443.8
150°	652.3	632.5	609.8	586.1	561.4	537.7	514.9	493.2	471.4	462.0	452.7
152.5°	635.5	617.7	598.9	578.2	556.4	535.7	516.9	497.1	478.4	470.0	461.6
155°	618.7	603.9	588.1	570.3	551.5	533.7	517.9	501.1	484.3	476.9	469.5
157.5°	602.9	590.1	576.2	562.4	546.6	531.7	517.9	504.1	489.2	483.3	477.4
160°	587.1	576.2	565.3	553.5	540.6	528.8	517.9	506.0	494.2	488.8	483.3
162.5°	571.3	563.4	554.5	545.6	534.7	525.8	517.9	508.0	497.1	493.2	489.2
165°	557.4	550.5	544.6	536.7	528.8	521.9	515.9	508.0	499.1	496.2	493.2
167.5°	545.6	539.6	534.7	528.8	522.8	517.9	513.9	508.0	501.1	498.6	496.2
170°	532.7	528.8	525.8	520.9	516.9	513.9	512.0	507.0	502.1	500.6	499.1
172.5°	521.9	519.9	517.9	513.9	511.0	510.0	510.0	506.0	503.1	502.1	501.1
175°	513.9	512.0	511.0	509.0	507.0	507.0	508.0	505.1	503.1	503.1	503.1
177.5°	507.0	507.0	506.0	505.1	504.1	504.1	506.0	504.1	503.1	503.1	503.1
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	556.3	556.3	556.3	556.3
2.5°	541.1	545.7	549.8	556.3
5°	529.1	535.5	544.3	554.0
7.5°	515.3	525.4	536.9	550.3
10°	502.4	513.9	528.6	544.8
12.5°	489.0	502.8	518.9	536.5
15°	473.8	487.6	505.6	529.1
17.5°	460.0	476.5	495.9	520.8
20°	443.8	459.5	480.7	509.3
22.5°	429.5	447.5	471.0	495.9
25°	413.9	429.5	453.0	483.0
27.5°	398.2	417.6	440.1	469.2
30°	383.0	399.1	423.5	454.0
32.5°	366.4	385.8	408.3	436.9
35°	348.4	366.9	388.1	418.9
37.5°	332.3	350.3	371.9	399.1
40°	314.3	333.2	353.0	380.2
42.5°	296.8	313.9	333.7	358.6
45°	279.8	294.5	312.5	334.1
47.5°	262.2	274.7	291.3	310.6
50°	243.3	256.7	269.2	285.3
52.5°	225.8	237.4	247.5	260.9
55°	208.8	216.6	224.9	235.0
57.5°	190.8	196.8	202.8	213.4
60°	172.8	178.4	181.6	188.5
62.5°	155.3	157.6	161.8	165.9
65°	136.0	139.2	141.5	146.6
67.5°	118.4	119.8	122.1	125.4
70°	100.0	103.2	104.2	106.5
72.5°	84.3	85.7	86.6	87.1
75°	66.8	68.2	69.1	71.9
77.5°	52.5	52.1	53.9	54.4
80°	38.7	37.3	37.8	39.6
82.5°	25.3	25.8	25.3	25.3
85°	15.7	15.2	14.3	14.7
87.5°	6.9	6.9	6.5	6.5
90°	6.9	5.9	3.0	1.0
92.5°	45.5	30.6	19.8	13.8
95°	58.3	45.5	35.6	32.6
97.5°	75.1	63.3	54.4	54.4
100°	93.9	82.0	75.1	75.1
102.5°	113.7	102.8	96.9	94.9
105°	135.4	123.5	118.6	115.6
107.5°	158.1	145.3	140.3	138.4
110°	179.9	168.0	163.1	161.1

TEST NUMBER: P1001129

CATALOG NUMBER: SA4XXDIP-B350D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	201.6	190.8	184.8	182.8
115°	223.4	213.5	206.6	203.6
117.5°	245.1	234.2	228.3	225.3
120°	266.9	256.0	249.1	247.1
122.5°	285.6	275.8	268.8	266.9
125°	304.4	293.5	287.6	283.7
127.5°	321.2	309.4	302.4	299.5
130°	339.0	324.2	316.3	312.3
132.5°	352.8	339.0	328.1	325.2
135°	367.7	350.9	341.0	337.0
137.5°	379.5	363.7	352.8	348.9
140°	392.4	375.6	364.7	361.7
142.5°	404.2	388.4	378.5	375.6
145°	415.1	401.3	391.4	388.4
147.5°	428.0	413.1	404.2	403.3
150°	437.8	426.0	418.1	417.1
152.5°	448.7	437.8	429.9	429.9
155°	458.6	448.7	442.8	441.8
157.5°	467.5	459.6	453.7	453.7
160°	475.4	468.5	464.5	464.5
162.5°	482.3	476.4	473.4	474.4
165°	488.2	483.3	481.3	481.3
167.5°	493.2	489.2	488.2	489.2
170°	497.1	494.2	493.2	494.2
172.5°	500.1	498.1	498.1	499.1
175°	502.1	501.1	501.1	502.1
177.5°	503.1	502.1	503.1	504.1
180°	503.1	503.1	503.1	503.1

(END OF REPORT)