

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001225

Luminaire Tested: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001225
REPORT IS A COMBINATION OF REPORTS P995841 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2829.0 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4495	4495	4495	4495
5°	4483	5156	4509	3875
10°	4450	6016	4484	3400
15°	4397	6935	4427	3041
20°	4339	7520	4371	2727
25°	4257	7434	4297	2495
30°	4175	6144	4226	2375
35°	4061	4579	4106	2303
40°	3929	3449	3966	2268
45°	3725	2768	3771	2219
50°	3483	2333	3533	2196
55°	3197	2030	3248	2170
60°	2920	1787	3006	2135
65°	2659	1538	2685	2045
70°	2354	1266	2405	1884
75°	2052	973	2040	1600
80°	1616	639	1596	1214
85°	1062	287	997	708

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5812 cd/sqm

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	1.9
10°-20°	165.6	5.9
20°-30°	263.0	9.3
30°-40°	292.3	10.3
40°-50°	265.8	9.4
50°-60°	217.2	7.7
60°-70°	155.1	5.5
70°-80°	85.3	3.0
80°-90°	23.8	0.8
90°-100°	130.1	4.6
100°-110°	271.6	9.6
110°-120°	241.4	8.5
120°-130°	203.2	7.2
130°-140°	169.6	6.0
140°-150°	129.5	4.6
150°-160°	91.0	3.2
160°-170°	53.5	1.9
170°-180°	17.4	0.6
0°-30°	482.3	17.0
0°-40°	774.6	27.4
0°-60°	1257.6	44.5
0°-90°	1521.7	53.8
90°-120°	643.1	22.7
90°-150°	1145.4	40.5
90°-180°	1307.0	46.2
0°-180°	2829.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	551	551	551	551	551	
5°	549	647	552	486	549	52
15°	524	888	528	390	524	148
25°	479	943	483	316	479	221
35°	415	558	420	280	415	259
45°	331	313	335	251	331	255
55°	233	205	237	219	233	209
65°	145	132	147	175	145	143
75°	71	66	71	108	71	75
85°	15	14	14	34	15	17
90°	0	7	0	7	0	2
95°	12	86	12	86	12	13
105°	41	496	41	496	41	44
115°	73	476	73	476	73	72
125°	101	380	101	380	101	90
135°	120	340	120	340	120	93
145°	139	278	139	278	139	87
155°	158	232	158	232	158	73
165°	172	203	172	203	172	49
175°	179	183	179	183	179	17
180°	180	180	180	180	180	

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	551.2	556.7	559.0	560.8	566.7	568.6	569.0	571.8	574.0	574.5	574.5
5°	548.9	557.6	564.4	570.8	580.4	584.5	589.6	595.0	602.3	606.9	609.2
7.5°	545.3	558.1	568.6	579.5	592.8	601.0	605.5	620.2	630.2	638.4	648.5
10°	539.8	556.2	571.3	587.3	606.0	616.0	626.1	643.9	658.1	674.0	686.8
12.5°	531.6	553.0	571.3	593.7	617.0	628.8	640.7	671.8	688.2	702.4	725.2
15°	524.3	545.7	571.8	594.6	623.4	641.2	658.5	678.6	704.6	735.2	757.2
17.5°	516.0	543.0	567.2	599.2	631.1	648.0	662.2	693.2	729.8	759.9	780.0
20°	504.6	532.0	564.0	597.8	635.7	648.9	667.7	709.2	742.1	771.8	804.7
22.5°	491.4	523.3	557.1	589.6	628.8	656.7	677.2	713.8	753.5	787.8	824.7
25°	478.6	513.3	543.0	587.3	628.8	647.6	670.8	714.2	757.6	799.2	837.1
27.5°	464.9	497.3	537.5	572.7	619.7	640.3	665.4	712.9	759.0	800.5	841.2
30°	449.8	484.5	517.9	559.4	605.1	631.6	654.9	706.5	753.5	796.9	834.8
32.5°	432.9	465.8	501.4	540.7	588.6	615.6	644.8	697.8	748.0	785.5	814.7
35°	415.1	448.5	479.5	519.7	569.0	596.0	624.3	682.7	732.5	763.1	780.0
37.5°	395.5	427.0	457.6	497.3	546.6	575.4	604.2	660.8	707.8	733.4	728.8
40°	376.8	405.1	433.4	470.8	522.4	553.0	578.1	635.2	676.3	687.3	672.2
42.5°	355.3	379.5	406.9	445.3	495.5	524.3	555.8	607.8	638.4	633.9	608.3
45°	331.1	352.5	379.9	416.0	467.2	496.9	523.3	572.7	595.0	583.6	537.0
47.5°	307.8	328.8	351.2	387.3	437.0	462.2	489.1	533.4	546.2	522.0	475.4
50°	282.7	300.0	323.3	357.6	404.2	430.6	453.0	488.6	493.2	463.5	415.1
52.5°	258.5	273.1	295.5	329.3	372.6	393.6	415.6	447.1	443.4	412.8	366.2
55°	232.9	246.6	267.2	298.2	336.6	356.7	375.4	403.2	395.5	364.0	323.3
57.5°	211.4	221.0	241.1	269.9	301.4	323.3	339.3	361.2	349.4	317.8	279.9
60°	186.8	198.7	215.5	238.8	269.9	284.5	298.7	313.3	305.1	274.9	241.1
62.5°	164.4	173.5	188.1	210.5	234.7	248.0	263.0	272.2	264.0	236.1	207.8
65°	145.2	152.5	163.9	182.2	205.5	216.5	225.1	233.8	227.0	200.9	180.4
67.5°	124.2	130.6	140.2	154.8	174.4	182.2	190.4	196.4	188.6	171.3	151.2
70°	105.5	110.1	119.2	130.2	143.9	151.2	158.0	163.9	157.1	142.5	127.4
72.5°	86.3	90.0	98.2	105.9	118.3	123.3	128.3	132.9	130.6	116.9	104.6
75°	71.2	72.6	78.1	84.5	92.2	97.7	101.4	104.1	102.3	91.3	83.6
77.5°	53.9	55.7	59.8	64.8	71.7	74.9	77.2	79.9	77.6	69.0	63.5
80°	39.3	39.7	42.0	46.6	51.1	51.6	53.9	57.5	56.2	50.2	46.1
82.5°	25.1	26.5	27.4	30.1	33.3	34.3	35.6	36.5	36.1	32.4	31.1
85°	14.6	14.6	15.5	17.4	18.3	19.6	20.1	20.6	21.5	19.2	17.8
87.5°	6.4	6.9	6.9	7.3	8.2	8.2	8.7	9.1	9.6	9.1	7.8
90°	0.4	1.1	2.1	2.5	2.8	2.8	2.8	4.9	4.9	5.6	6.3
92.5°	4.9	7.1	10.9	16.2	22.6	27.2	31.7	53.6	87.8	121.0	138.2
95°	11.6	12.7	16.2	20.8	29.3	36.7	44.1	74.8	132.6	216.9	287.4
97.5°	19.4	19.4	22.6	26.8	34.2	40.6	46.9	71.2	121.0	207.7	307.5
100°	26.8	26.8	29.3	33.5	40.2	45.8	51.5	72.3	112.1	184.1	283.5
102.5°	33.9	34.6	36.7	40.6	46.9	52.2	57.5	75.8	109.7	168.2	253.5
105°	41.3	42.3	44.1	48.3	54.7	59.8	64.9	81.8	111.1	160.5	231.3
107.5°	49.4	50.1	51.8	56.4	62.4	67.5	72.6	88.2	115.3	158.3	216.9
110°	57.5	58.2	59.9	64.2	70.5	75.2	80.0	95.6	120.2	159.0	210.2

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.2	65.9	68.1	71.9	78.3	83.0	87.8	102.6	125.5	161.2	207.0
115°	72.6	73.7	76.2	79.7	86.4	91.2	95.9	110.0	131.2	164.0	206.3
117.5°	80.4	81.5	83.6	87.5	93.8	98.8	103.7	117.1	136.8	166.8	205.9
120°	88.2	88.9	91.3	95.2	101.2	106.2	111.1	124.5	142.8	170.0	205.9
122.5°	95.2	95.9	98.4	101.9	108.6	113.4	118.1	131.5	148.5	173.1	205.6
125°	101.2	102.6	104.7	108.6	115.3	120.2	125.2	137.9	154.1	176.3	205.2
127.5°	106.8	107.9	110.4	114.6	121.7	126.6	131.5	143.9	159.0	178.8	204.5
130°	111.4	112.8	115.7	121.0	127.7	132.8	137.9	149.9	163.6	181.6	204.2
132.5°	116.0	117.1	121.0	125.9	133.3	138.0	142.8	154.8	168.2	184.1	203.8
135°	120.2	121.7	125.2	131.2	138.6	143.2	147.8	159.4	172.1	186.5	203.5
137.5°	124.5	125.9	129.8	135.4	143.2	147.6	152.0	162.9	174.9	188.0	203.5
140°	129.1	130.1	134.0	140.0	147.4	151.6	155.9	166.4	177.7	189.7	203.1
142.5°	134.0	135.1	138.6	144.2	151.3	155.4	159.4	169.6	179.8	191.1	203.1
145°	138.6	139.6	143.2	148.1	154.8	158.7	162.6	171.7	181.3	191.5	202.4
147.5°	143.9	144.2	147.4	152.7	158.3	161.9	165.4	174.2	182.7	191.8	201.4
150°	148.8	149.2	152.0	156.2	161.5	164.8	168.2	176.0	183.7	191.8	200.3
152.5°	153.4	153.4	156.2	160.1	164.7	167.7	170.7	177.4	184.4	191.1	198.5
155°	157.6	158.0	160.1	163.6	167.5	170.2	172.8	178.8	184.8	190.4	196.8
157.5°	161.9	161.9	164.0	166.8	170.3	172.4	174.6	179.8	184.8	189.7	195.0
160°	165.7	165.7	167.2	169.6	172.4	174.4	176.3	180.6	184.8	188.7	192.9
162.5°	169.3	168.9	170.0	172.1	174.6	176.0	177.4	181.3	184.8	187.6	190.8
165°	171.7	171.7	172.4	174.2	176.0	177.0	178.1	181.3	184.1	186.2	188.7
167.5°	174.6	174.2	174.6	176.0	177.0	177.9	178.8	181.3	183.4	184.8	186.5
170°	176.3	176.0	176.3	177.4	178.1	178.6	179.1	180.9	182.7	183.4	184.4
172.5°	178.1	177.7	177.7	178.4	178.8	179.2	179.5	180.6	182.0	182.0	182.3
175°	179.1	178.8	178.8	179.1	179.5	179.5	179.5	180.2	181.3	180.9	180.9
177.5°	179.8	179.5	179.1	179.5	179.5	179.5	179.5	179.8	180.6	179.8	179.8
180°	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	575.9	584.1	587.7	588.6	593.7	590.5	591.8	591.4	595.0	595.5	595.5
5°	617.9	627.5	630.7	635.2	642.1	643.9	642.5	645.3	650.3	646.6	652.1
7.5°	662.2	672.7	680.0	690.0	692.3	698.2	701.9	705.1	706.0	706.5	707.4
10°	703.3	716.5	726.6	743.5	747.1	750.3	766.3	759.9	768.1	765.4	766.3
12.5°	736.6	762.6	770.9	799.2	801.9	812.9	812.0	822.0	823.8	827.5	823.8
15°	780.4	810.6	823.8	839.8	849.0	861.7	864.0	877.7	883.2	888.2	883.2
17.5°	820.6	836.6	870.4	883.2	889.1	896.0	913.3	918.4	926.6	923.4	932.5
20°	840.7	863.6	899.2	921.1	930.2	936.6	951.2	959.0	962.2	962.2	963.1
22.5°	858.5	891.4	917.9	943.0	951.2	955.8	964.5	970.4	971.8	972.7	973.6
25°	874.5	904.2	925.7	939.8	943.0	943.0	948.0	944.4	938.5	943.0	945.8
27.5°	874.5	895.5	905.1	910.1	910.1	897.8	890.5	875.4	862.7	859.0	867.2
30°	859.9	869.5	856.3	843.9	834.3	826.1	797.3	774.5	769.9	766.7	779.1
32.5°	826.1	813.8	787.8	752.1	738.0	719.3	696.9	679.5	669.0	665.4	662.6
35°	766.3	734.3	700.5	652.6	642.5	618.8	588.2	575.4	558.1	557.6	563.5
37.5°	701.0	651.7	615.1	569.5	555.3	530.2	501.4	488.2	476.3	467.2	478.1
40°	624.7	581.8	526.1	488.6	468.5	455.3	431.1	416.5	411.0	406.4	413.3
42.5°	553.5	506.4	463.1	424.7	408.3	393.2	377.2	363.1	358.9	358.5	363.5
45°	482.7	436.6	396.4	363.5	353.0	343.9	328.3	324.2	317.4	312.8	315.1
47.5°	426.1	378.6	345.2	320.1	311.0	303.2	293.2	286.3	280.4	278.6	281.3
50°	370.4	338.4	304.1	283.1	276.3	269.0	261.2	254.8	252.1	250.3	252.1
52.5°	325.6	291.4	268.1	251.2	244.3	238.8	233.4	230.6	227.0	227.9	229.7
55°	285.4	255.3	235.6	223.3	219.2	216.9	210.1	206.9	205.5	204.6	205.5
57.5°	247.5	225.6	211.0	200.5	195.0	193.6	188.1	188.1	186.8	185.4	185.9
60°	217.4	198.7	184.5	176.3	175.4	173.1	169.4	169.0	165.8	167.1	167.6
62.5°	186.8	171.7	162.1	157.1	153.9	153.0	150.7	150.2	148.9	149.3	148.4
65°	162.6	150.2	140.7	136.5	135.2	134.7	132.9	131.5	130.6	131.5	130.6
67.5°	138.4	130.2	122.8	118.7	116.9	116.5	115.1	114.2	114.6	113.3	114.2
70°	115.5	107.3	102.8	100.5	99.6	98.2	98.2	98.2	98.2	97.3	96.8
72.5°	97.3	89.1	85.9	84.5	83.6	83.1	81.7	82.2	81.7	81.3	83.1
75°	77.2	72.2	69.0	67.6	68.5	67.1	65.8	66.7	65.3	65.8	67.6
77.5°	58.5	56.2	54.3	53.4	52.5	51.6	51.6	50.7	50.7	50.7	50.7
80°	42.5	42.0	38.8	38.4	38.4	37.4	37.4	37.4	37.4	37.0	37.4
82.5°	28.3	27.9	26.9	26.5	25.6	26.0	26.0	25.1	25.1	24.7	25.1
85°	16.4	16.4	15.5	15.1	14.6	15.1	14.2	13.7	14.2	13.7	14.2
87.5°	7.8	6.9	7.3	6.9	5.9	6.4	5.5	5.9	5.5	5.0	5.9
90°	6.0	6.3	6.7	7.1	7.1	7.1	7.4	7.8	7.4	7.4	7.4
92.5°	115.0	85.0	63.5	50.1	45.7	41.3	36.0	33.5	32.1	32.1	32.1
95°	295.5	261.3	206.6	159.4	142.3	125.2	107.9	97.0	90.6	86.0	90.6
97.5°	370.6	376.3	349.1	310.3	290.6	270.8	246.8	225.7	215.1	206.6	215.1
100°	373.8	425.3	432.3	415.1	402.0	389.0	358.3	336.8	326.2	323.4	326.2
102.5°	347.3	422.8	464.8	475.4	471.8	468.3	452.4	438.3	427.0	424.9	427.0
105°	314.2	395.0	456.0	490.9	498.1	505.3	506.0	503.2	498.3	496.2	498.3
107.5°	287.0	360.7	426.7	475.4	490.2	505.0	520.5	526.8	529.7	530.0	529.7
110°	267.7	330.4	391.4	442.6	462.0	481.4	506.4	521.2	527.5	530.7	527.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	256.7	308.2	360.4	408.0	427.4	446.8	476.1	494.8	504.3	509.9	504.3
115°	250.7	294.8	338.2	379.4	396.4	413.3	441.2	462.3	473.6	476.4	473.6
117.5°	247.6	287.0	323.7	357.2	372.0	386.8	411.5	429.9	441.9	443.6	441.9
120°	245.1	282.1	314.9	343.1	355.6	368.2	388.3	403.8	412.9	416.8	412.9
122.5°	242.3	277.9	309.3	334.3	344.9	355.5	371.7	384.4	391.8	395.7	391.8
125°	239.1	272.9	303.3	327.6	337.3	347.0	361.1	371.3	378.0	380.1	378.0
127.5°	234.9	267.3	296.6	320.9	330.0	339.2	353.3	362.5	368.2	370.3	368.2
130°	231.0	260.2	288.1	312.1	321.5	330.8	345.2	354.0	359.7	361.8	359.7
132.5°	227.5	252.8	278.6	301.9	311.2	320.5	334.7	344.9	350.2	352.3	350.2
135°	223.9	246.1	269.1	290.6	299.4	308.2	322.3	332.2	337.8	339.9	337.8
137.5°	220.8	239.8	259.9	278.6	286.7	294.8	308.2	318.4	323.0	325.5	323.0
140°	218.3	234.5	251.1	266.9	274.4	281.8	294.1	301.9	306.8	309.6	306.8
142.5°	216.2	229.6	243.7	256.7	262.9	269.1	279.6	286.7	290.9	292.7	290.9
145°	213.7	225.0	237.0	247.6	252.5	257.4	266.2	272.2	275.8	277.5	275.8
147.5°	211.6	221.1	231.0	239.8	243.8	247.9	254.6	259.9	262.7	263.4	262.7
150°	209.1	217.6	225.7	232.7	235.9	239.1	244.7	249.3	251.4	251.8	251.4
152.5°	206.3	213.7	220.4	226.7	229.2	231.7	236.3	239.8	240.9	241.2	240.9
155°	203.5	209.8	215.5	220.8	222.9	225.0	228.5	231.3	232.4	232.4	232.4
157.5°	200.7	205.6	210.5	215.1	216.8	218.6	221.5	223.6	224.3	224.3	224.3
160°	197.5	201.7	205.6	209.5	210.9	212.3	214.4	216.5	216.9	216.9	216.9
162.5°	194.7	197.8	201.0	203.8	205.0	206.3	207.7	209.8	210.2	209.8	210.2
165°	191.5	194.3	196.4	198.9	199.8	200.7	202.1	203.5	203.1	202.8	203.1
167.5°	188.7	190.8	192.5	194.7	195.2	195.7	196.4	197.5	197.5	197.1	197.5
170°	185.8	187.6	188.7	190.1	190.6	191.1	191.8	192.2	191.8	191.8	191.8
172.5°	183.4	184.8	185.5	186.2	186.6	186.9	187.3	187.6	187.3	186.5	187.3
175°	181.6	182.3	182.7	183.4	183.4	183.4	183.4	184.1	183.4	182.7	183.4
177.5°	180.2	180.6	180.9	180.9	181.1	181.3	180.9	181.3	180.6	179.8	180.6
180°	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	594.6	593.2	591.4	591.4	589.1	589.1	585.5	579.1	573.6	571.8	572.7
5°	645.3	645.7	643.0	640.7	636.6	633.4	627.5	616.0	612.4	605.1	600.1
7.5°	703.3	701.4	696.4	692.8	691.9	684.5	671.8	658.1	647.1	639.8	629.3
10°	768.6	761.3	754.0	751.7	746.2	733.9	719.3	704.2	689.1	673.1	655.3
12.5°	823.4	809.2	808.8	803.3	792.8	785.9	768.6	747.1	721.1	703.3	683.2
15°	882.3	869.0	858.1	848.0	843.0	822.9	808.3	781.4	750.3	731.1	717.4
17.5°	924.3	918.4	899.6	895.1	888.2	864.9	841.6	815.2	788.2	761.3	724.3
20°	958.1	954.4	942.1	935.7	924.8	906.5	878.2	847.6	816.5	778.2	743.5
22.5°	972.7	968.1	958.1	952.6	945.8	930.2	906.0	871.3	830.7	796.4	759.4
25°	943.9	952.2	949.4	947.1	944.4	935.3	917.0	886.4	846.7	807.8	761.7
27.5°	879.1	893.2	906.9	908.8	913.3	917.0	909.7	887.8	854.4	813.3	762.6
30°	791.9	798.3	826.1	834.3	840.7	864.0	877.7	872.2	846.7	809.7	763.1
32.5°	680.0	696.9	725.2	744.8	762.2	788.2	823.8	838.0	828.9	798.7	752.6
35°	574.0	594.1	627.0	652.1	669.5	706.5	748.5	779.1	790.5	775.4	734.3
37.5°	487.3	511.5	540.7	550.3	570.4	616.0	674.0	716.5	744.4	745.7	713.8
40°	422.0	434.3	457.6	472.2	491.8	530.2	586.8	643.0	685.0	699.2	682.3
42.5°	366.7	376.3	393.6	411.5	429.3	458.5	510.6	563.1	619.7	648.0	647.6
45°	322.9	332.9	344.8	359.4	371.7	403.2	444.3	498.2	547.1	590.9	601.9
47.5°	284.5	293.2	307.8	314.2	322.4	352.1	387.7	437.9	488.6	538.9	551.7
50°	256.2	263.5	273.5	277.7	286.8	308.7	337.9	378.6	434.8	480.9	504.6
52.5°	230.6	236.1	243.9	247.1	253.5	269.9	296.4	328.3	374.9	422.4	455.8
55°	208.7	212.4	217.8	221.5	226.1	240.7	260.3	289.1	329.3	370.4	402.8
57.5°	188.1	190.9	196.4	198.2	201.8	213.3	227.0	251.2	288.2	324.7	356.2
60°	169.0	170.8	174.0	178.1	180.8	188.6	201.4	221.5	251.2	284.5	310.1
62.5°	150.7	153.4	154.4	156.2	158.5	165.8	175.8	190.4	216.5	243.9	270.8
65°	132.0	134.3	136.1	136.5	138.8	144.3	153.4	166.2	183.1	206.9	232.0
67.5°	114.6	116.0	116.9	118.7	121.0	123.8	131.1	140.7	156.2	175.4	195.5
70°	98.6	98.6	100.0	100.5	103.2	106.4	109.6	118.7	132.4	148.0	161.7
72.5°	81.3	83.6	83.1	85.4	84.9	87.2	91.3	97.3	107.3	119.6	132.9
75°	66.2	67.6	67.6	67.6	68.5	70.3	72.6	78.1	85.9	95.9	103.7
77.5°	51.6	52.5	52.5	52.5	53.0	54.8	57.1	60.7	66.2	72.2	76.7
80°	37.0	37.9	37.9	38.8	38.8	39.3	41.6	43.4	46.1	50.7	55.3
82.5°	25.1	25.6	26.5	26.5	26.0	26.9	27.4	29.2	32.0	32.9	36.1
85°	13.7	14.2	14.6	14.6	15.1	16.0	15.5	17.4	17.4	19.2	20.1
87.5°	5.5	6.4	6.4	5.9	6.4	6.4	6.4	7.3	7.8	8.2	7.8
90°	7.8	7.4	7.1	7.1	7.1	6.7	6.3	6.0	6.3	5.6	4.9
92.5°	33.5	36.0	41.3	45.7	50.1	63.5	85.0	115.0	138.2	121.0	87.8
95°	97.0	107.9	125.2	142.3	159.4	206.6	261.3	295.5	287.4	216.9	132.6
97.5°	225.7	246.8	270.8	290.6	310.3	349.1	376.3	370.6	307.5	207.7	121.0
100°	336.8	358.3	389.0	402.0	415.1	432.3	425.3	373.8	283.5	184.1	112.1
102.5°	438.3	452.4	468.3	471.8	475.4	464.8	422.8	347.3	253.5	168.2	109.7
105°	503.2	506.0	505.3	498.1	490.9	456.0	395.0	314.2	231.3	160.5	111.1
107.5°	526.8	520.5	505.0	490.2	475.4	426.7	360.7	287.0	216.9	158.3	115.3
110°	521.2	506.4	481.4	462.0	442.6	391.4	330.4	267.7	210.2	159.0	120.2

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	494.8	476.1	446.8	427.4	408.0	360.4	308.2	256.7	207.0	161.2	125.5
115°	462.3	441.2	413.3	396.4	379.4	338.2	294.8	250.7	206.3	164.0	131.2
117.5°	429.9	411.5	386.8	372.0	357.2	323.7	287.0	247.6	205.9	166.8	136.8
120°	403.8	388.3	368.2	355.6	343.1	314.9	282.1	245.1	205.9	170.0	142.8
122.5°	384.4	371.7	355.5	344.9	334.3	309.3	277.9	242.3	205.6	173.1	148.5
125°	371.3	361.1	347.0	337.3	327.6	303.3	272.9	239.1	205.2	176.3	154.1
127.5°	362.5	353.3	339.2	330.0	320.9	296.6	267.3	234.9	204.5	178.8	159.0
130°	354.0	345.2	330.8	321.5	312.1	288.1	260.2	231.0	204.2	181.6	163.6
132.5°	344.9	334.7	320.5	311.2	301.9	278.6	252.8	227.5	203.8	184.1	168.2
135°	332.2	322.3	308.2	299.4	290.6	269.1	246.1	223.9	203.5	186.5	172.1
137.5°	318.4	308.2	294.8	286.7	278.6	259.9	239.8	220.8	203.5	188.0	174.9
140°	301.9	294.1	281.8	274.4	266.9	251.1	234.5	218.3	203.1	189.7	177.7
142.5°	286.7	279.6	269.1	262.9	256.7	243.7	229.6	216.2	203.1	191.1	179.8
145°	272.2	266.2	257.4	252.5	247.6	237.0	225.0	213.7	202.4	191.5	181.3
147.5°	259.9	254.6	247.9	243.8	239.8	231.0	221.1	211.6	201.4	191.8	182.7
150°	249.3	244.7	239.1	235.9	232.7	225.7	217.6	209.1	200.3	191.8	183.7
152.5°	239.8	236.3	231.7	229.2	226.7	220.4	213.7	206.3	198.5	191.1	184.4
155°	231.3	228.5	225.0	222.9	220.8	215.5	209.8	203.5	196.8	190.4	184.8
157.5°	223.6	221.5	218.6	216.8	215.1	210.5	205.6	200.7	195.0	189.7	184.8
160°	216.5	214.4	212.3	210.9	209.5	205.6	201.7	197.5	192.9	188.7	184.8
162.5°	209.8	207.7	206.3	205.0	203.8	201.0	197.8	194.7	190.8	187.6	184.8
165°	203.5	202.1	200.7	199.8	198.9	196.4	194.3	191.5	188.7	186.2	184.1
167.5°	197.5	196.4	195.7	195.2	194.7	192.5	190.8	188.7	186.5	184.8	183.4
170°	192.2	191.8	191.1	190.6	190.1	188.7	187.6	185.8	184.4	183.4	182.7
172.5°	187.6	187.3	186.9	186.6	186.2	185.5	184.8	183.4	182.3	182.0	182.0
175°	184.1	183.4	183.4	183.4	183.4	182.7	182.3	181.6	180.9	180.9	181.3
177.5°	181.3	180.9	181.3	181.1	180.9	180.9	180.6	180.2	179.8	179.8	180.6
180°	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	568.6	566.7	565.4	565.4	561.2	557.1	554.9	553.9	553.0	549.4	544.4
5°	591.8	585.9	581.8	577.7	570.8	563.5	556.2	552.1	546.2	538.0	532.0
7.5°	617.9	603.7	599.2	594.1	580.4	568.1	558.1	549.4	539.8	529.3	518.8
10°	639.8	624.7	614.7	606.0	588.2	571.8	556.7	543.9	531.6	517.9	505.1
12.5°	660.8	639.3	628.8	616.0	597.3	573.6	553.9	538.0	519.7	505.5	490.0
15°	690.0	654.0	636.6	628.4	603.3	575.4	551.7	527.9	512.8	491.4	477.7
17.5°	694.6	665.4	654.0	632.9	602.8	571.3	543.9	520.1	497.3	478.1	460.3
20°	710.6	672.2	654.0	640.7	601.0	569.0	538.9	508.3	486.4	465.8	445.7
22.5°	720.6	677.2	658.1	637.1	599.2	560.8	525.2	498.7	471.7	450.7	434.8
25°	717.9	674.5	653.0	633.4	587.3	548.9	517.0	483.2	458.0	435.2	414.2
27.5°	716.5	667.7	644.8	622.9	579.5	539.3	499.1	471.7	443.9	417.4	401.9
30°	712.9	659.0	632.5	608.7	563.5	521.5	487.3	455.3	427.4	403.2	382.7
32.5°	700.5	644.4	618.8	593.2	546.2	504.2	469.5	439.8	411.9	386.8	367.2
35°	684.1	627.0	599.2	572.2	525.2	482.7	450.7	419.7	393.6	369.4	350.7
37.5°	667.7	606.9	580.9	549.8	506.4	462.2	429.3	401.4	377.2	352.1	331.5
40°	643.9	583.2	554.4	527.9	477.2	435.7	405.5	380.4	356.7	332.9	315.6
42.5°	611.5	557.1	527.5	498.2	450.7	409.6	380.4	358.0	335.7	316.0	296.8
45°	578.6	525.6	499.1	473.1	421.5	382.7	355.7	335.2	316.5	295.0	279.5
47.5°	538.9	494.1	467.6	442.1	393.2	354.4	329.7	310.5	293.2	275.4	260.8
50°	498.2	459.4	435.2	408.7	362.1	327.0	302.8	286.8	272.6	255.7	243.9
52.5°	454.4	420.6	400.0	374.5	333.4	300.9	276.3	260.3	248.4	236.1	225.6
55°	407.8	383.1	361.2	340.7	301.9	272.6	250.7	236.6	228.3	216.9	207.8
57.5°	365.8	342.0	328.8	305.5	271.7	242.9	225.6	213.7	204.1	197.3	190.0
60°	322.0	302.8	288.2	271.3	241.6	217.4	199.1	192.3	182.2	177.2	174.0
62.5°	279.9	266.2	252.5	239.8	213.3	190.4	176.7	168.1	162.1	157.1	154.4
65°	240.2	227.4	217.8	206.4	184.5	166.2	153.4	146.6	140.7	139.3	136.1
67.5°	201.4	195.9	185.4	176.3	157.6	143.4	133.8	125.1	121.9	120.6	117.8
70°	168.5	162.1	153.9	146.1	132.0	119.6	111.0	107.8	103.2	102.8	99.6
72.5°	138.8	131.1	125.1	119.2	108.7	97.7	93.2	88.6	86.3	84.5	83.1
75°	110.1	104.6	100.5	95.4	86.3	79.0	72.6	70.8	69.4	69.0	68.0
77.5°	82.2	78.5	76.7	71.7	65.3	58.9	56.2	53.4	53.4	52.5	53.0
80°	58.5	56.2	53.9	51.1	45.7	42.9	40.6	38.8	37.9	37.4	37.9
82.5°	37.0	35.6	35.2	33.3	29.7	28.3	26.5	25.1	25.1	25.1	25.1
85°	20.6	20.6	20.6	17.8	16.4	15.1	14.2	13.7	13.7	13.7	14.2
87.5°	8.7	8.7	7.3	7.3	6.9	5.9	5.5	5.5	5.9	5.9	6.4
90°	4.9	2.8	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	53.6	31.7	27.2	22.6	16.2	10.9	7.1	4.9	7.1	10.9	16.2
95°	74.8	44.1	36.7	29.3	20.8	16.2	12.7	11.6	12.7	16.2	20.8
97.5°	71.2	46.9	40.6	34.2	26.8	22.6	19.4	19.4	19.4	22.6	26.8
100°	72.3	51.5	45.8	40.2	33.5	29.3	26.8	26.8	26.8	29.3	33.5
102.5°	75.8	57.5	52.2	46.9	40.6	36.7	34.6	33.9	34.6	36.7	40.6
105°	81.8	64.9	59.8	54.7	48.3	44.1	42.3	41.3	42.3	44.1	48.3
107.5°	88.2	72.6	67.5	62.4	56.4	51.8	50.1	49.4	50.1	51.8	56.4
110°	95.6	80.0	75.2	70.5	64.2	59.9	58.2	57.5	58.2	59.9	64.2

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	102.6	87.8	83.0	78.3	71.9	68.1	65.9	65.2	65.9	68.1	71.9
115°	110.0	95.9	91.2	86.4	79.7	76.2	73.7	72.6	73.7	76.2	79.7
117.5°	117.1	103.7	98.8	93.8	87.5	83.6	81.5	80.4	81.5	83.6	87.5
120°	124.5	111.1	106.2	101.2	95.2	91.3	88.9	88.2	88.9	91.3	95.2
122.5°	131.5	118.1	113.4	108.6	101.9	98.4	95.9	95.2	95.9	98.4	101.9
125°	137.9	125.2	120.2	115.3	108.6	104.7	102.6	101.2	102.6	104.7	108.6
127.5°	143.9	131.5	126.6	121.7	114.6	110.4	107.9	106.8	107.9	110.4	114.6
130°	149.9	137.9	132.8	127.7	121.0	115.7	112.8	111.4	112.8	115.7	121.0
132.5°	154.8	142.8	138.0	133.3	125.9	121.0	117.1	116.0	117.1	121.0	125.9
135°	159.4	147.8	143.2	138.6	131.2	125.2	121.7	120.2	121.7	125.2	131.2
137.5°	162.9	152.0	147.6	143.2	135.4	129.8	125.9	124.5	125.9	129.8	135.4
140°	166.4	155.9	151.6	147.4	140.0	134.0	130.1	129.1	130.1	134.0	140.0
142.5°	169.6	159.4	155.4	151.3	144.2	138.6	135.1	134.0	135.1	138.6	144.2
145°	171.7	162.6	158.7	154.8	148.1	143.2	139.6	138.6	139.6	143.2	148.1
147.5°	174.2	165.4	161.9	158.3	152.7	147.4	144.2	143.9	144.2	147.4	152.7
150°	176.0	168.2	164.8	161.5	156.2	152.0	149.2	148.8	149.2	152.0	156.2
152.5°	177.4	170.7	167.7	164.7	160.1	156.2	153.4	153.4	153.4	156.2	160.1
155°	178.8	172.8	170.2	167.5	163.6	160.1	158.0	157.6	158.0	160.1	163.6
157.5°	179.8	174.6	172.4	170.3	166.8	164.0	161.9	161.9	161.9	164.0	166.8
160°	180.6	176.3	174.4	172.4	169.6	167.2	165.7	165.7	165.7	167.2	169.6
162.5°	181.3	177.4	176.0	174.6	172.1	170.0	168.9	169.3	168.9	170.0	172.1
165°	181.3	178.1	177.0	176.0	174.2	172.4	171.7	171.7	171.7	172.4	174.2
167.5°	181.3	178.8	177.9	177.0	176.0	174.6	174.2	174.6	174.2	174.6	176.0
170°	180.9	179.1	178.6	178.1	177.4	176.3	176.0	176.3	176.0	176.3	177.4
172.5°	180.6	179.5	179.2	178.8	178.4	177.7	177.7	178.1	177.7	177.7	178.4
175°	180.2	179.5	179.5	179.5	179.1	178.8	178.8	179.1	178.8	178.8	179.1
177.5°	179.8	179.5	179.5	179.5	179.5	179.1	179.5	179.8	179.5	179.1	179.5
180°	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	543.0	541.2	542.1	537.5	533.4	527.5	522.4	521.5	520.6	523.3	521.5
5°	527.5	525.2	522.9	517.4	509.2	504.2	496.9	496.4	493.7	489.6	490.5
7.5°	510.6	509.2	506.0	497.3	490.0	481.3	475.4	470.4	468.1	464.4	463.1
10°	496.9	491.8	489.1	479.5	470.8	461.7	453.9	450.3	446.2	443.0	440.7
12.5°	478.1	476.8	469.0	461.2	453.9	443.4	437.5	427.0	421.5	424.2	423.3
15°	465.8	459.4	457.6	446.6	434.3	427.4	416.5	409.6	407.4	403.2	398.2
17.5°	449.4	445.3	438.9	428.8	414.7	405.1	397.3	390.9	388.2	382.7	378.6
20°	433.8	427.0	422.0	412.8	399.1	386.8	377.2	373.1	366.2	361.7	359.4
22.5°	419.7	414.7	407.4	393.6	381.8	369.9	358.5	352.5	346.2	343.4	339.8
25°	402.3	394.1	389.1	374.0	361.2	351.6	341.1	333.4	329.7	325.1	324.2
27.5°	385.4	377.7	371.7	358.5	343.0	330.6	324.2	318.8	312.4	312.4	310.1
30°	368.5	363.1	353.9	341.1	326.5	314.6	307.3	302.3	300.0	298.2	297.7
32.5°	351.6	344.3	338.8	321.5	310.5	299.6	294.1	290.0	287.2	286.8	287.2
35°	334.3	326.1	320.6	305.1	294.1	284.0	281.8	278.1	276.7	276.3	278.6
37.5°	316.0	309.6	302.8	290.0	277.7	271.7	267.2	265.8	265.3	268.1	269.0
40°	299.1	293.6	287.2	273.5	264.4	258.0	255.7	254.4	256.2	258.9	260.3
42.5°	283.1	275.4	270.3	258.0	249.8	246.1	243.4	243.4	245.2	248.4	250.7
45°	266.2	260.3	255.3	244.3	237.0	232.9	232.4	232.9	235.2	237.5	240.2
47.5°	249.8	243.9	238.4	229.2	222.9	220.6	220.1	220.6	224.2	227.4	230.6
50°	234.7	228.3	223.3	214.6	209.6	206.9	207.3	209.6	212.4	216.9	221.0
52.5°	216.9	212.4	207.8	200.0	195.5	193.6	195.0	196.8	201.8	205.0	210.1
55°	199.6	195.5	191.8	185.9	182.2	180.8	181.8	184.5	188.6	194.1	200.0
57.5°	183.6	179.0	175.4	171.3	167.1	167.6	168.1	171.7	176.7	181.8	188.6
60°	165.8	163.0	159.8	154.8	153.0	153.0	154.4	158.5	163.0	171.3	177.2
62.5°	149.8	146.1	143.9	140.7	137.9	138.4	141.6	145.2	150.7	157.6	165.3
65°	133.3	129.2	127.4	124.7	123.8	124.2	126.5	132.0	137.9	143.9	151.2
67.5°	115.1	113.7	111.9	109.1	110.1	110.5	112.8	117.4	123.8	129.7	137.9
70°	99.6	96.8	96.4	94.1	94.1	95.4	100.0	103.2	109.1	115.5	124.2
72.5°	83.1	80.8	80.8	79.0	80.4	81.7	84.0	88.6	94.1	100.5	107.8
75°	66.2	65.3	66.2	65.3	65.3	67.6	70.3	74.0	79.9	86.8	92.7
77.5°	51.1	51.1	50.7	52.1	52.1	53.4	57.1	60.7	65.3	70.8	77.2
80°	37.4	37.4	37.4	38.8	40.2	40.2	42.5	47.0	51.1	54.8	60.7
82.5°	25.6	25.6	25.6	26.5	28.3	28.3	31.1	33.8	38.4	41.6	44.3
85°	15.5	15.5	15.1	16.0	16.4	17.8	20.1	21.9	24.2	26.9	29.7
87.5°	6.9	6.9	7.3	7.8	8.2	9.1	10.0	11.0	13.2	14.2	15.5
90°	2.8	2.8	2.8	4.9	4.9	5.6	6.3	6.0	6.3	6.7	7.1
92.5°	22.6	27.2	31.7	53.6	87.8	121.0	138.2	115.0	85.0	63.5	50.1
95°	29.3	36.7	44.1	74.8	132.6	216.9	287.4	295.5	261.3	206.6	159.4
97.5°	34.2	40.6	46.9	71.2	121.0	207.7	307.5	370.6	376.3	349.1	310.3
100°	40.2	45.8	51.5	72.3	112.1	184.1	283.5	373.8	425.3	432.3	415.1
102.5°	46.9	52.2	57.5	75.8	109.7	168.2	253.5	347.3	422.8	464.8	475.4
105°	54.7	59.8	64.9	81.8	111.1	160.5	231.3	314.2	395.0	456.0	490.9
107.5°	62.4	67.5	72.6	88.2	115.3	158.3	216.9	287.0	360.7	426.7	475.4
110°	70.5	75.2	80.0	95.6	120.2	159.0	210.2	267.7	330.4	391.4	442.6

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	78.3	83.0	87.8	102.6	125.5	161.2	207.0	256.7	308.2	360.4	408.0
115°	86.4	91.2	95.9	110.0	131.2	164.0	206.3	250.7	294.8	338.2	379.4
117.5°	93.8	98.8	103.7	117.1	136.8	166.8	205.9	247.6	287.0	323.7	357.2
120°	101.2	106.2	111.1	124.5	142.8	170.0	205.9	245.1	282.1	314.9	343.1
122.5°	108.6	113.4	118.1	131.5	148.5	173.1	205.6	242.3	277.9	309.3	334.3
125°	115.3	120.2	125.2	137.9	154.1	176.3	205.2	239.1	272.9	303.3	327.6
127.5°	121.7	126.6	131.5	143.9	159.0	178.8	204.5	234.9	267.3	296.6	320.9
130°	127.7	132.8	137.9	149.9	163.6	181.6	204.2	231.0	260.2	288.1	312.1
132.5°	133.3	138.0	142.8	154.8	168.2	184.1	203.8	227.5	252.8	278.6	301.9
135°	138.6	143.2	147.8	159.4	172.1	186.5	203.5	223.9	246.1	269.1	290.6
137.5°	143.2	147.6	152.0	162.9	174.9	188.0	203.5	220.8	239.8	259.9	278.6
140°	147.4	151.6	155.9	166.4	177.7	189.7	203.1	218.3	234.5	251.1	266.9
142.5°	151.3	155.4	159.4	169.6	179.8	191.1	203.1	216.2	229.6	243.7	256.7
145°	154.8	158.7	162.6	171.7	181.3	191.5	202.4	213.7	225.0	237.0	247.6
147.5°	158.3	161.9	165.4	174.2	182.7	191.8	201.4	211.6	221.1	231.0	239.8
150°	161.5	164.8	168.2	176.0	183.7	191.8	200.3	209.1	217.6	225.7	232.7
152.5°	164.7	167.7	170.7	177.4	184.4	191.1	198.5	206.3	213.7	220.4	226.7
155°	167.5	170.2	172.8	178.8	184.8	190.4	196.8	203.5	209.8	215.5	220.8
157.5°	170.3	172.4	174.6	179.8	184.8	189.7	195.0	200.7	205.6	210.5	215.1
160°	172.4	174.4	176.3	180.6	184.8	188.7	192.9	197.5	201.7	205.6	209.5
162.5°	174.6	176.0	177.4	181.3	184.8	187.6	190.8	194.7	197.8	201.0	203.8
165°	176.0	177.0	178.1	181.3	184.1	186.2	188.7	191.5	194.3	196.4	198.9
167.5°	177.0	177.9	178.8	181.3	183.4	184.8	186.5	188.7	190.8	192.5	194.7
170°	178.1	178.6	179.1	180.9	182.7	183.4	184.4	185.8	187.6	188.7	190.1
172.5°	178.8	179.2	179.5	180.6	182.0	182.0	182.3	183.4	184.8	185.5	186.2
175°	179.5	179.5	179.5	180.2	181.3	180.9	180.9	181.6	182.3	182.7	183.4
177.5°	179.5	179.5	179.5	179.8	180.6	179.8	179.8	180.2	180.6	180.9	180.9
180°	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	520.1	519.7	517.4	518.3	515.6	516.5	517.9	518.3	520.1	518.8	518.3
5°	488.2	487.3	485.9	484.5	484.1	485.9	482.7	483.6	484.5	485.9	487.7
7.5°	462.2	461.7	460.3	458.0	457.1	456.2	456.7	459.9	459.4	459.0	462.2
10°	438.4	438.9	436.1	435.7	432.9	432.5	432.9	433.8	435.2	437.0	437.5
12.5°	413.7	419.7	414.7	412.8	408.7	411.0	411.9	407.8	410.1	411.5	418.3
15°	398.2	395.5	392.3	392.3	390.5	389.5	387.3	390.5	392.3	395.0	394.1
17.5°	376.8	372.2	370.4	368.5	369.0	370.8	365.8	373.1	373.1	374.5	372.2
20°	358.0	354.4	352.1	351.2	349.8	348.9	348.4	350.3	353.0	353.9	356.2
22.5°	338.4	338.4	334.7	333.4	332.5	331.1	333.4	332.0	333.8	335.7	339.3
25°	322.0	322.0	320.6	318.8	317.4	316.5	317.8	317.4	318.8	321.0	322.0
27.5°	308.7	307.3	306.9	306.4	306.0	306.4	306.0	307.3	308.7	309.2	308.3
30°	297.3	295.9	296.4	296.4	296.8	296.4	295.9	297.3	297.7	296.8	297.3
32.5°	286.8	286.8	287.7	288.2	288.2	288.6	289.1	288.2	288.6	287.2	287.7
35°	278.1	279.0	279.9	280.4	280.9	280.4	281.3	280.9	279.9	279.0	278.6
37.5°	269.4	270.3	272.2	272.6	274.0	274.5	273.5	273.5	273.1	271.3	270.3
40°	260.3	261.2	263.5	264.9	265.8	267.2	266.2	266.2	264.4	262.6	261.2
42.5°	251.6	253.5	255.7	257.1	258.9	258.9	258.9	258.0	255.7	253.9	252.5
45°	242.9	243.4	246.6	248.9	250.7	250.7	250.7	249.3	248.0	244.3	242.5
47.5°	233.4	234.7	238.4	240.7	242.5	242.9	242.9	241.6	238.8	235.6	233.4
50°	222.9	225.1	229.2	232.4	234.7	235.6	234.3	233.4	230.2	226.5	223.8
52.5°	212.8	215.5	220.6	223.3	226.5	227.0	226.5	225.1	221.5	216.5	214.2
55°	202.8	205.0	210.5	215.1	217.8	218.7	217.8	215.5	211.0	206.0	203.7
57.5°	191.8	195.0	200.9	205.5	208.7	209.2	208.2	206.0	202.3	195.9	192.7
60°	180.4	184.5	190.4	195.0	199.1	199.6	198.7	195.5	190.9	184.5	181.8
62.5°	169.0	172.2	179.0	184.0	187.2	189.5	187.7	184.5	179.9	173.5	169.4
65°	155.7	160.3	166.2	170.8	174.4	174.9	174.0	171.3	166.2	159.4	156.2
67.5°	142.9	146.1	152.1	158.0	159.4	160.7	159.4	156.6	152.5	146.6	142.0
70°	127.4	130.2	137.5	141.6	143.4	144.8	143.9	141.1	137.5	132.0	128.3
72.5°	111.9	114.2	121.0	124.2	127.9	127.4	127.0	125.1	120.1	116.5	114.2
75°	95.4	98.2	102.8	106.9	108.2	108.2	108.2	106.9	103.7	97.7	95.4
77.5°	80.4	81.7	85.4	87.7	89.1	89.5	89.1	86.8	84.9	80.8	79.5
80°	61.7	65.3	68.0	68.5	70.3	70.3	70.3	69.4	67.6	63.5	63.0
82.5°	46.6	47.5	50.2	51.6	52.5	52.1	52.1	50.2	49.8	47.5	46.6
85°	31.5	32.9	32.4	34.3	34.7	33.8	33.8	34.7	32.4	32.9	31.5
87.5°	17.4	17.4	18.3	17.8	19.6	19.6	18.7	19.2	18.3	17.8	17.4
90°	7.1	7.1	7.4	7.8	7.4	7.4	7.4	7.8	7.4	7.1	7.1
92.5°	45.7	41.3	36.0	33.5	32.1	32.1	32.1	33.5	36.0	41.3	45.7
95°	142.3	125.2	107.9	97.0	90.6	86.0	90.6	97.0	107.9	125.2	142.3
97.5°	290.6	270.8	246.8	225.7	215.1	206.6	215.1	225.7	246.8	270.8	290.6
100°	402.0	389.0	358.3	336.8	326.2	323.4	326.2	336.8	358.3	389.0	402.0
102.5°	471.8	468.3	452.4	438.3	427.0	424.9	427.0	438.3	452.4	468.3	471.8
105°	498.1	505.3	506.0	503.2	498.3	496.2	498.3	503.2	506.0	505.3	498.1
107.5°	490.2	505.0	520.5	526.8	529.7	530.0	529.7	526.8	520.5	505.0	490.2
110°	462.0	481.4	506.4	521.2	527.5	530.7	527.5	521.2	506.4	481.4	462.0

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	427.4	446.8	476.1	494.8	504.3	509.9	504.3	494.8	476.1	446.8	427.4
115°	396.4	413.3	441.2	462.3	473.6	476.4	473.6	462.3	441.2	413.3	396.4
117.5°	372.0	386.8	411.5	429.9	441.9	443.6	441.9	429.9	411.5	386.8	372.0
120°	355.6	368.2	388.3	403.8	412.9	416.8	412.9	403.8	388.3	368.2	355.6
122.5°	344.9	355.5	371.7	384.4	391.8	395.7	391.8	384.4	371.7	355.5	344.9
125°	337.3	347.0	361.1	371.3	378.0	380.1	378.0	371.3	361.1	347.0	337.3
127.5°	330.0	339.2	353.3	362.5	368.2	370.3	368.2	362.5	353.3	339.2	330.0
130°	321.5	330.8	345.2	354.0	359.7	361.8	359.7	354.0	345.2	330.8	321.5
132.5°	311.2	320.5	334.7	344.9	350.2	352.3	350.2	344.9	334.7	320.5	311.2
135°	299.4	308.2	322.3	332.2	337.8	339.9	337.8	332.2	322.3	308.2	299.4
137.5°	286.7	294.8	308.2	318.4	323.0	325.5	323.0	318.4	308.2	294.8	286.7
140°	274.4	281.8	294.1	301.9	306.8	309.6	306.8	301.9	294.1	281.8	274.4
142.5°	262.9	269.1	279.6	286.7	290.9	292.7	290.9	286.7	279.6	269.1	262.9
145°	252.5	257.4	266.2	272.2	275.8	277.5	275.8	272.2	266.2	257.4	252.5
147.5°	243.8	247.9	254.6	259.9	262.7	263.4	262.7	259.9	254.6	247.9	243.8
150°	235.9	239.1	244.7	249.3	251.4	251.8	251.4	249.3	244.7	239.1	235.9
152.5°	229.2	231.7	236.3	239.8	240.9	241.2	240.9	239.8	236.3	231.7	229.2
155°	222.9	225.0	228.5	231.3	232.4	232.4	232.4	231.3	228.5	225.0	222.9
157.5°	216.8	218.6	221.5	223.6	224.3	224.3	224.3	223.6	221.5	218.6	216.8
160°	210.9	212.3	214.4	216.5	216.9	216.9	216.9	216.5	214.4	212.3	210.9
162.5°	205.0	206.3	207.7	209.8	210.2	209.8	210.2	209.8	207.7	206.3	205.0
165°	199.8	200.7	202.1	203.5	203.1	202.8	203.1	203.5	202.1	200.7	199.8
167.5°	195.2	195.7	196.4	197.5	197.5	197.1	197.5	197.5	196.4	195.7	195.2
170°	190.6	191.1	191.8	192.2	191.8	191.8	191.8	192.2	191.8	191.1	190.6
172.5°	186.6	186.9	187.3	187.6	187.3	186.5	187.3	187.6	187.3	186.9	186.6
175°	183.4	183.4	183.4	184.1	183.4	182.7	183.4	184.1	183.4	183.4	183.4
177.5°	181.1	181.3	180.9	181.3	180.6	179.8	180.6	181.3	180.9	181.3	181.1
180°	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	518.3	521.1	518.3	520.1	521.1	523.3	524.3	528.4	529.7	532.9	532.9
5°	487.3	488.6	489.1	490.9	492.7	497.3	500.5	506.4	513.3	514.2	518.3
7.5°	462.2	464.4	468.1	466.7	469.9	476.8	480.9	488.2	495.0	498.7	503.7
10°	439.8	442.5	443.9	445.3	451.2	457.1	463.5	468.5	477.7	483.2	487.3
12.5°	421.5	419.2	422.0	427.0	433.8	437.5	446.2	453.9	460.8	466.7	470.4
15°	397.8	399.6	402.3	411.0	412.8	422.0	425.2	433.8	446.6	452.1	456.7
17.5°	374.9	380.9	386.3	389.5	395.0	402.3	411.5	421.1	429.3	435.7	441.1
20°	356.7	362.6	365.8	368.1	373.6	383.6	392.3	404.2	414.7	419.7	427.0
22.5°	342.0	342.0	346.6	353.5	356.7	366.2	373.6	386.3	397.8	404.2	411.0
25°	323.8	326.5	330.2	336.1	340.7	348.4	358.9	369.9	382.2	387.7	396.4
27.5°	308.7	311.9	316.9	318.3	322.9	329.7	340.7	352.5	365.3	371.3	378.6
30°	297.3	299.1	300.9	303.7	307.8	313.7	322.9	333.4	348.9	353.5	362.6
32.5°	287.2	288.2	289.1	291.4	293.6	299.6	306.9	318.3	331.1	337.9	346.2
35°	278.1	277.2	277.7	279.0	281.3	283.6	291.4	300.9	312.8	321.0	327.4
37.5°	269.4	267.6	267.2	267.2	268.1	270.8	276.7	285.0	297.7	304.6	311.0
40°	259.8	258.0	257.1	256.6	256.2	258.0	262.6	270.8	280.9	287.2	294.6
42.5°	250.7	248.9	246.6	246.1	245.2	246.1	249.3	257.1	265.8	272.2	278.1
45°	241.6	238.4	235.6	233.8	234.3	232.9	235.2	241.1	251.2	255.3	261.2
47.5°	231.5	227.9	224.2	222.4	220.6	221.5	222.4	227.4	236.1	240.2	246.1
50°	221.9	216.9	212.8	210.5	209.2	208.2	209.2	214.2	220.6	224.2	229.2
52.5°	211.0	206.0	201.8	198.2	196.4	195.0	195.5	200.0	206.0	209.6	214.6
55°	200.9	194.5	189.1	184.5	183.1	182.7	182.2	185.4	190.4	194.1	198.2
57.5°	189.5	183.1	177.2	171.7	169.0	168.5	168.5	169.4	175.8	178.6	180.8
60°	178.1	171.3	164.9	159.8	155.7	154.4	153.9	155.7	158.9	161.7	164.9
62.5°	165.3	158.5	150.7	146.1	142.0	138.4	139.7	140.2	144.8	146.1	148.9
65°	153.0	145.2	138.8	131.5	127.0	124.7	123.8	124.7	128.3	128.8	130.6
67.5°	138.8	131.5	123.8	118.7	114.6	110.5	109.6	109.6	111.4	112.8	115.1
70°	125.1	117.8	109.1	103.7	99.6	95.9	94.5	94.1	95.4	96.4	98.6
72.5°	109.1	101.8	95.4	89.5	84.5	81.7	80.4	79.5	80.8	81.7	82.2
75°	92.2	86.3	79.9	74.0	70.8	68.0	66.2	64.8	65.8	65.8	65.8
77.5°	76.3	70.3	65.3	61.2	57.1	53.9	52.5	51.1	51.6	51.6	52.5
80°	59.4	55.3	51.1	47.5	43.8	41.1	40.2	38.8	37.9	37.4	37.4
82.5°	43.8	40.6	37.0	33.8	32.0	29.2	28.3	26.5	26.5	26.0	26.0
85°	29.2	27.4	23.7	21.5	20.1	18.7	17.8	16.9	15.5	15.5	15.1
87.5°	15.5	14.6	13.7	11.0	11.0	9.6	9.1	8.7	7.3	7.8	7.8
90°	7.1	6.7	6.3	6.0	6.3	5.6	4.9	4.9	2.8	2.8	2.8
92.5°	50.1	63.5	85.0	115.0	138.2	121.0	87.8	53.6	31.7	27.2	22.6
95°	159.4	206.6	261.3	295.5	287.4	216.9	132.6	74.8	44.1	36.7	29.3
97.5°	310.3	349.1	376.3	370.6	307.5	207.7	121.0	71.2	46.9	40.6	34.2
100°	415.1	432.3	425.3	373.8	283.5	184.1	112.1	72.3	51.5	45.8	40.2
102.5°	475.4	464.8	422.8	347.3	253.5	168.2	109.7	75.8	57.5	52.2	46.9
105°	490.9	456.0	395.0	314.2	231.3	160.5	111.1	81.8	64.9	59.8	54.7
107.5°	475.4	426.7	360.7	287.0	216.9	158.3	115.3	88.2	72.6	67.5	62.4
110°	442.6	391.4	330.4	267.7	210.2	159.0	120.2	95.6	80.0	75.2	70.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	408.0	360.4	308.2	256.7	207.0	161.2	125.5	102.6	87.8	83.0	78.3
115°	379.4	338.2	294.8	250.7	206.3	164.0	131.2	110.0	95.9	91.2	86.4
117.5°	357.2	323.7	287.0	247.6	205.9	166.8	136.8	117.1	103.7	98.8	93.8
120°	343.1	314.9	282.1	245.1	205.9	170.0	142.8	124.5	111.1	106.2	101.2
122.5°	334.3	309.3	277.9	242.3	205.6	173.1	148.5	131.5	118.1	113.4	108.6
125°	327.6	303.3	272.9	239.1	205.2	176.3	154.1	137.9	125.2	120.2	115.3
127.5°	320.9	296.6	267.3	234.9	204.5	178.8	159.0	143.9	131.5	126.6	121.7
130°	312.1	288.1	260.2	231.0	204.2	181.6	163.6	149.9	137.9	132.8	127.7
132.5°	301.9	278.6	252.8	227.5	203.8	184.1	168.2	154.8	142.8	138.0	133.3
135°	290.6	269.1	246.1	223.9	203.5	186.5	172.1	159.4	147.8	143.2	138.6
137.5°	278.6	259.9	239.8	220.8	203.5	188.0	174.9	162.9	152.0	147.6	143.2
140°	266.9	251.1	234.5	218.3	203.1	189.7	177.7	166.4	155.9	151.6	147.4
142.5°	256.7	243.7	229.6	216.2	203.1	191.1	179.8	169.6	159.4	155.4	151.3
145°	247.6	237.0	225.0	213.7	202.4	191.5	181.3	171.7	162.6	158.7	154.8
147.5°	239.8	231.0	221.1	211.6	201.4	191.8	182.7	174.2	165.4	161.9	158.3
150°	232.7	225.7	217.6	209.1	200.3	191.8	183.7	176.0	168.2	164.8	161.5
152.5°	226.7	220.4	213.7	206.3	198.5	191.1	184.4	177.4	170.7	167.7	164.7
155°	220.8	215.5	209.8	203.5	196.8	190.4	184.8	178.8	172.8	170.2	167.5
157.5°	215.1	210.5	205.6	200.7	195.0	189.7	184.8	179.8	174.6	172.4	170.3
160°	209.5	205.6	201.7	197.5	192.9	188.7	184.8	180.6	176.3	174.4	172.4
162.5°	203.8	201.0	197.8	194.7	190.8	187.6	184.8	181.3	177.4	176.0	174.6
165°	198.9	196.4	194.3	191.5	188.7	186.2	184.1	181.3	178.1	177.0	176.0
167.5°	194.7	192.5	190.8	188.7	186.5	184.8	183.4	181.3	178.8	177.9	177.0
170°	190.1	188.7	187.6	185.8	184.4	183.4	182.7	180.9	179.1	178.6	178.1
172.5°	186.2	185.5	184.8	183.4	182.3	182.0	182.0	180.6	179.5	179.2	178.8
175°	183.4	182.7	182.3	181.6	180.9	180.9	181.3	180.2	179.5	179.5	179.5
177.5°	180.9	180.9	180.6	180.2	179.8	179.8	180.6	179.8	179.5	179.5	179.5
180°	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5	179.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	551.2	551.2	551.2	551.2
2.5°	536.1	540.7	544.8	551.2
5°	524.3	530.7	539.3	548.9
7.5°	510.6	520.6	532.0	545.3
10°	497.8	509.2	523.8	539.8
12.5°	484.5	498.2	514.2	531.6
15°	469.5	483.2	501.0	524.3
17.5°	455.8	472.2	491.4	516.0
20°	439.8	455.3	476.3	504.6
22.5°	425.6	443.4	466.7	491.4
25°	410.1	425.6	448.9	478.6
27.5°	394.6	413.7	436.1	464.9
30°	379.5	395.5	419.7	449.8
32.5°	363.1	382.2	404.6	432.9
35°	345.2	363.5	384.5	415.1
37.5°	329.3	347.1	368.5	395.5
40°	311.4	330.2	349.8	376.8
42.5°	294.1	311.0	330.6	355.3
45°	277.2	291.8	309.6	331.1
47.5°	259.8	272.2	288.6	307.8
50°	241.1	254.4	266.7	282.7
52.5°	223.8	235.2	245.2	258.5
55°	206.9	214.6	222.9	232.9
57.5°	189.1	195.0	200.9	211.4
60°	171.3	176.7	179.9	186.8
62.5°	153.9	156.2	160.3	164.4
65°	134.7	137.9	140.2	145.2
67.5°	117.4	118.7	121.0	124.2
70°	99.1	102.3	103.2	105.5
72.5°	83.6	84.9	85.9	86.3
75°	66.2	67.6	68.5	71.2
77.5°	52.1	51.6	53.4	53.9
80°	38.4	37.0	37.4	39.3
82.5°	25.1	25.6	25.1	25.1
85°	15.5	15.1	14.2	14.6
87.5°	6.9	6.9	6.4	6.4
90°	2.5	2.1	1.1	0.4
92.5°	16.2	10.9	7.1	4.9
95°	20.8	16.2	12.7	11.6
97.5°	26.8	22.6	19.4	19.4
100°	33.5	29.3	26.8	26.8
102.5°	40.6	36.7	34.6	33.9
105°	48.3	44.1	42.3	41.3
107.5°	56.4	51.8	50.1	49.4
110°	64.2	59.9	58.2	57.5

TEST NUMBER: P1001225

CATALOG NUMBER: SA4XXDIP-B350D365UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	71.9	68.1	65.9	65.2
115°	79.7	76.2	73.7	72.6
117.5°	87.5	83.6	81.5	80.4
120°	95.2	91.3	88.9	88.2
122.5°	101.9	98.4	95.9	95.2
125°	108.6	104.7	102.6	101.2
127.5°	114.6	110.4	107.9	106.8
130°	121.0	115.7	112.8	111.4
132.5°	125.9	121.0	117.1	116.0
135°	131.2	125.2	121.7	120.2
137.5°	135.4	129.8	125.9	124.5
140°	140.0	134.0	130.1	129.1
142.5°	144.2	138.6	135.1	134.0
145°	148.1	143.2	139.6	138.6
147.5°	152.7	147.4	144.2	143.9
150°	156.2	152.0	149.2	148.8
152.5°	160.1	156.2	153.4	153.4
155°	163.6	160.1	158.0	157.6
157.5°	166.8	164.0	161.9	161.9
160°	169.6	167.2	165.7	165.7
162.5°	172.1	170.0	168.9	169.3
165°	174.2	172.4	171.7	171.7
167.5°	176.0	174.6	174.2	174.6
170°	177.4	176.3	176.0	176.3
172.5°	178.4	177.7	177.7	178.1
175°	179.1	178.8	178.8	179.1
177.5°	179.5	179.1	179.5	179.8
180°	179.5	179.5	179.5	179.5

(END OF REPORT)