

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001255

Luminaire Tested: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001255
REPORT IS A COMBINATION OF REPORTS P995874 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2866.0 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54		
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46		
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39		
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33		
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29		
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25		
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22		
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20		
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20	18		
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18	16		
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4553	4553	4553	4553
5°	4542	5224	4569	3926
10°	4509	6095	4542	3444
15°	4455	7027	4486	3082
20°	4397	7620	4429	2763
25°	4313	7532	4354	2527
30°	4230	6225	4282	2407
35°	4115	4639	4160	2333
40°	3980	3495	4018	2297
45°	3774	2805	3821	2248
50°	3528	2363	3580	2225
55°	3240	2057	3290	2199
60°	2958	1811	3045	2163
65°	2694	1559	2720	2072
70°	2385	1282	2436	1909
75°	2081	985	2066	1622
80°	1637	648	1616	1232
85°	1077	291	1011	717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5888 cd/sqm

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	1.9
10°-20°	167.8	5.9
20°-30°	266.5	9.3
30°-40°	296.1	10.3
40°-50°	269.3	9.4
50°-60°	220.1	7.7
60°-70°	157.1	5.5
70°-80°	86.4	3.0
80°-90°	24.1	0.8
90°-100°	131.8	4.6
100°-110°	275.1	9.6
110°-120°	244.6	8.5
120°-130°	205.9	7.2
130°-140°	171.8	6.0
140°-150°	131.1	4.6
150°-160°	92.2	3.2
160°-170°	54.2	1.9
170°-180°	17.6	0.6
0°-30°	488.6	17.0
0°-40°	784.7	27.4
0°-60°	1274.1	44.5
0°-90°	1541.7	53.8
90°-120°	651.5	22.7
90°-150°	1160.2	40.5
90°-180°	1324.0	46.2
0°-180°	2866.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	558	558	558	558	558	
5°	556	655	559	492	556	53
15°	531	900	535	395	531	150
25°	485	955	490	321	485	223
35°	421	565	425	284	421	263
45°	335	317	340	254	335	259
55°	236	207	240	222	236	212
65°	147	133	148	177	147	145
75°	72	67	72	110	72	76
85°	15	14	14	34	15	17
90°	0	8	0	8	0	2
95°	12	87	12	87	12	13
105°	42	503	42	503	42	45
115°	74	483	74	483	74	73
125°	102	385	102	385	102	91
135°	122	344	122	344	122	94
145°	140	281	140	281	140	88
155°	160	235	160	235	160	74
165°	174	205	174	205	174	49
175°	182	185	182	185	182	17
180°	182	182	182	182	182	

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	558.4	564.0	566.3	568.2	574.2	576.0	576.5	579.3	581.6	582.0	582.0
5°	556.1	564.9	571.9	578.3	588.1	592.2	597.3	602.9	610.3	614.9	617.2
7.5°	552.4	565.4	576.0	587.1	600.6	608.9	613.5	628.3	638.5	646.8	657.0
10°	546.9	563.5	578.8	595.0	614.0	624.1	634.3	652.4	666.7	682.9	695.9
12.5°	538.6	560.3	578.8	601.5	625.1	637.1	649.1	680.6	697.3	711.6	734.7
15°	531.2	552.9	579.3	602.4	631.6	649.6	667.2	687.5	713.9	744.9	767.1
17.5°	522.8	550.1	574.6	607.0	639.4	656.5	670.9	702.3	739.4	769.9	790.2
20°	511.3	539.0	571.4	605.6	644.0	657.5	676.4	718.5	751.8	781.9	815.2
22.5°	497.8	530.2	564.5	597.3	637.1	665.3	686.1	723.2	763.4	798.1	835.6
25°	484.9	520.0	550.1	595.0	637.1	656.1	679.7	723.6	767.6	809.7	848.1
27.5°	471.0	503.9	544.6	580.2	627.9	648.7	674.1	722.2	769.0	811.1	852.2
30°	455.7	490.9	524.7	566.8	613.0	639.9	663.5	715.8	763.4	807.4	845.8
32.5°	438.6	471.9	508.0	547.8	596.4	623.7	653.3	707.0	757.9	795.8	825.4
35°	420.6	454.3	485.8	526.5	576.5	603.8	632.5	691.7	742.1	773.1	790.2
37.5°	400.7	432.6	463.6	503.9	553.8	583.0	612.1	669.5	717.1	743.1	738.4
40°	381.7	410.4	439.1	477.0	529.3	560.3	585.7	643.6	685.2	696.3	681.1
42.5°	360.0	384.5	412.2	451.1	502.0	531.2	563.1	615.8	646.8	642.2	616.3
45°	335.4	357.2	384.9	421.5	473.3	503.4	530.2	580.2	602.9	591.3	544.1
47.5°	311.8	333.1	355.8	392.3	442.8	468.2	495.5	540.4	553.4	528.8	481.6
50°	286.4	304.0	327.6	362.3	409.5	436.3	459.0	495.1	499.7	469.6	420.6
52.5°	261.9	276.7	299.4	333.6	377.5	398.8	421.0	453.0	449.3	418.3	371.1
55°	236.0	249.8	270.7	302.1	341.0	361.3	380.3	408.5	400.7	368.8	327.6
57.5°	214.2	223.9	244.3	273.4	305.4	327.6	343.8	366.0	353.9	322.0	283.6
60°	189.2	201.3	218.4	242.0	273.4	288.2	302.6	317.4	309.1	278.5	244.3
62.5°	166.6	175.8	190.6	213.3	237.8	251.2	266.5	275.8	267.4	239.2	210.5
65°	147.1	154.5	166.1	184.6	208.2	219.3	228.1	236.9	229.9	203.6	182.8
67.5°	125.8	132.3	142.0	156.8	176.7	184.6	192.9	199.0	191.1	173.5	153.1
70°	106.9	111.5	120.8	131.9	145.7	153.1	160.1	166.1	159.2	144.4	129.1
72.5°	87.4	91.1	99.5	107.3	119.8	124.9	130.0	134.6	132.3	118.4	106.0
75°	72.2	73.6	79.1	85.6	93.5	99.0	102.7	105.5	103.6	92.5	84.7
77.5°	54.6	56.4	60.6	65.7	72.6	75.9	78.2	81.0	78.7	69.9	64.3
80°	39.8	40.3	42.6	47.2	51.8	52.3	54.6	58.3	56.9	50.9	46.7
82.5°	25.4	26.8	27.8	30.5	33.8	34.7	36.1	37.0	36.6	32.8	31.5
85°	14.8	14.8	15.7	17.6	18.5	19.9	20.4	20.8	21.7	19.4	18.0
87.5°	6.5	6.9	6.9	7.4	8.3	8.3	8.8	9.3	9.7	9.3	7.9
90°	0.4	1.1	2.1	2.5	2.9	2.9	2.9	5.0	5.0	5.7	6.4
92.5°	5.0	7.1	11.1	16.4	22.9	27.5	32.1	54.3	88.9	122.5	140.0
95°	11.8	12.9	16.4	21.1	29.6	37.2	44.7	75.7	134.3	219.7	291.1
97.5°	19.6	19.6	22.9	27.1	34.7	41.1	47.5	72.2	122.5	210.4	311.5
100°	27.1	27.1	29.6	33.9	40.7	46.4	52.2	73.2	113.6	186.5	287.2
102.5°	34.3	35.0	37.2	41.1	47.5	52.8	58.2	76.8	111.1	170.4	256.8
105°	41.8	42.9	44.7	48.9	55.4	60.6	65.7	82.9	112.5	162.5	234.3
107.5°	50.0	50.7	52.5	57.2	63.2	68.4	73.6	89.3	116.8	160.4	219.7
110°	58.2	58.9	60.7	65.0	71.4	76.2	81.1	96.8	121.8	161.1	212.9

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	66.1	66.8	68.9	72.9	79.3	84.1	88.9	104.0	127.2	163.3	209.7
115°	73.6	74.7	77.2	80.7	87.5	92.4	97.2	111.5	132.9	166.1	209.0
117.5°	81.4	82.5	84.7	88.6	95.0	100.0	105.0	118.6	138.6	169.0	208.6
120°	89.3	90.0	92.5	96.4	102.5	107.5	112.5	126.1	144.7	172.2	208.6
122.5°	96.4	97.2	99.7	103.2	110.0	114.8	119.7	133.2	150.4	175.4	208.3
125°	102.5	104.0	106.1	110.0	116.8	121.8	126.8	139.7	156.1	178.6	207.9
127.5°	108.2	109.3	111.8	116.1	123.2	128.2	133.2	145.7	161.1	181.1	207.2
130°	112.9	114.3	117.2	122.5	129.3	134.5	139.7	151.8	165.8	184.0	206.8
132.5°	117.5	118.6	122.5	127.5	135.0	139.8	144.7	156.8	170.4	186.5	206.5
135°	121.8	123.2	126.8	132.9	140.4	145.0	149.7	161.5	174.3	189.0	206.1
137.5°	126.1	127.5	131.5	137.2	145.0	149.5	154.0	165.0	177.2	190.4	206.1
140°	130.7	131.8	135.7	141.8	149.3	153.6	157.9	168.6	180.0	192.2	205.8
142.5°	135.7	136.8	140.4	146.1	153.2	157.4	161.5	171.8	182.2	193.6	205.8
145°	140.4	141.5	145.0	150.0	156.8	160.8	164.7	174.0	183.6	194.0	205.0
147.5°	145.7	146.1	149.3	154.7	160.4	164.0	167.5	176.5	185.0	194.3	204.0
150°	150.7	151.1	154.0	158.2	163.6	167.0	170.4	178.3	186.1	194.3	202.9
152.5°	155.4	155.4	158.2	162.2	166.8	169.9	172.9	179.7	186.8	193.6	201.1
155°	159.7	160.0	162.2	165.8	169.7	172.4	175.0	181.1	187.2	192.9	199.3
157.5°	164.0	164.0	166.1	169.0	172.5	174.6	176.8	182.2	187.2	192.2	197.5
160°	167.9	167.9	169.3	171.8	174.7	176.6	178.6	182.9	187.2	191.1	195.4
162.5°	171.5	171.1	172.2	174.3	176.8	178.2	179.7	183.6	187.2	190.0	193.3
165°	174.0	174.0	174.7	176.5	178.3	179.4	180.4	183.6	186.5	188.6	191.1
167.5°	176.8	176.5	176.8	178.3	179.3	180.2	181.1	183.6	185.8	187.2	189.0
170°	178.6	178.3	178.6	179.7	180.4	181.0	181.5	183.3	185.0	185.8	186.8
172.5°	180.4	180.0	180.0	180.8	181.1	181.4	181.8	182.9	184.3	184.3	184.7
175°	181.5	181.1	181.1	181.5	181.8	181.8	181.8	182.5	183.6	183.3	183.3
177.5°	182.2	181.8	181.5	181.8	181.8	181.8	181.8	182.2	182.9	182.2	182.2
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	583.4	591.8	595.5	596.4	601.5	598.2	599.6	599.2	602.9	603.3	603.3
5°	626.0	635.7	639.0	643.6	650.5	652.4	651.0	653.8	658.8	655.1	660.7
7.5°	670.9	681.5	688.9	699.1	701.4	707.4	711.1	714.4	715.3	715.8	716.7
10°	712.5	725.9	736.1	753.2	756.9	760.2	776.4	769.9	778.2	775.4	776.4
12.5°	746.3	772.7	781.0	809.7	812.5	823.6	822.6	832.8	834.7	838.4	834.7
15°	790.7	821.2	834.7	850.9	860.1	873.1	875.4	889.3	894.8	899.9	894.8
17.5°	831.4	847.6	881.9	894.8	900.8	907.8	925.4	930.4	938.8	935.5	944.8
20°	851.8	874.9	911.0	933.2	942.5	948.9	963.8	971.6	974.9	974.9	975.8
22.5°	869.8	903.1	930.0	955.4	963.8	968.4	977.2	983.2	984.6	985.5	986.4
25°	886.0	916.1	937.8	952.2	955.4	955.4	960.5	956.8	950.8	955.4	958.2
27.5°	886.0	907.3	917.0	922.1	922.1	909.6	902.2	886.9	874.0	870.3	878.6
30°	871.2	880.9	867.5	855.0	845.3	837.0	807.8	784.7	780.1	776.8	789.3
32.5°	837.0	824.5	798.1	762.0	747.7	728.7	706.0	688.5	677.8	674.1	671.3
35°	776.4	744.0	709.7	661.2	651.0	626.9	595.9	583.0	565.4	564.9	570.9
37.5°	710.2	660.2	623.2	577.0	562.6	537.2	508.0	494.6	482.6	473.3	484.4
40°	632.9	589.4	533.0	495.1	474.7	461.3	436.8	422.0	416.4	411.8	418.7
42.5°	560.8	513.1	469.2	430.3	413.6	398.4	382.2	367.8	363.7	363.2	368.3
45°	489.0	442.3	401.6	368.3	357.6	348.4	332.7	328.5	321.6	316.9	319.2
47.5°	431.7	383.6	349.8	324.3	315.1	307.2	297.0	290.1	284.1	282.2	285.0
50°	375.2	342.8	308.1	286.9	279.9	272.5	264.7	258.2	255.4	253.5	255.4
52.5°	329.9	295.2	271.6	254.5	247.5	242.0	236.4	233.7	229.9	230.9	232.7
55°	289.2	258.6	238.7	226.2	222.1	219.8	212.8	209.6	208.2	207.3	208.2
57.5°	250.8	228.6	213.8	203.1	197.6	196.2	190.6	190.6	189.2	187.8	188.3
60°	220.2	201.3	186.9	178.6	177.7	175.4	171.7	171.2	168.0	169.3	169.8
62.5°	189.2	174.0	164.2	159.2	155.9	155.0	152.7	152.2	150.8	151.3	150.4
65°	164.7	152.2	142.5	138.3	137.0	136.5	134.6	133.3	132.3	133.3	132.3
67.5°	140.2	131.9	124.5	120.3	118.4	118.0	116.6	115.7	116.1	114.7	115.7
70°	117.1	108.7	104.1	101.8	100.9	99.5	99.5	99.5	99.5	98.5	98.1
72.5°	98.5	90.2	87.0	85.6	84.7	84.2	82.8	83.3	82.8	82.4	84.2
75°	78.2	73.1	69.9	68.5	69.4	68.0	66.6	67.6	66.2	66.6	68.5
77.5°	59.2	56.9	55.1	54.1	53.2	52.3	52.3	51.4	51.4	51.4	51.4
80°	43.0	42.6	39.3	38.9	38.9	37.9	37.9	37.9	37.9	37.5	37.9
82.5°	28.7	28.2	27.3	26.8	25.9	26.4	26.4	25.4	25.4	25.0	25.4
85°	16.7	16.7	15.7	15.3	14.8	15.3	14.3	13.9	14.3	13.9	14.3
87.5°	7.9	6.9	7.4	6.9	6.0	6.5	5.6	6.0	5.6	5.1	6.0
90°	6.1	6.4	6.8	7.1	7.1	7.1	7.5	7.9	7.5	7.5	7.5
92.5°	116.5	86.1	64.3	50.7	46.2	41.8	36.4	33.9	32.5	32.5	32.5
95°	299.4	264.7	209.3	161.5	144.2	126.8	109.3	98.2	91.8	87.2	91.8
97.5°	375.4	381.2	353.6	314.4	294.4	274.3	250.1	228.6	217.9	209.3	217.9
100°	378.7	430.8	438.0	420.5	407.2	394.0	362.9	341.1	330.4	327.6	330.4
102.5°	351.9	428.3	470.8	481.5	478.0	474.4	458.3	444.0	432.6	430.5	432.6
105°	318.3	400.1	461.9	497.3	504.6	511.9	512.6	509.8	504.8	502.6	504.8
107.5°	290.8	365.4	432.2	481.5	496.5	511.5	527.3	533.7	536.5	536.9	536.5
110°	271.1	334.7	396.5	448.3	468.0	487.6	513.0	528.0	534.4	537.6	534.4

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	260.1	312.2	365.1	413.3	433.0	452.6	482.2	501.2	510.8	516.5	510.8
115°	254.0	298.6	342.6	384.4	401.5	418.7	446.9	468.3	479.7	482.6	479.7
117.5°	250.8	290.8	327.9	361.9	376.9	391.9	416.9	435.5	447.6	449.4	447.6
120°	248.3	285.8	319.0	347.6	360.2	372.9	393.3	409.0	418.3	422.2	418.3
122.5°	245.4	281.5	313.3	338.6	349.4	360.1	376.5	389.4	396.9	400.8	396.9
125°	242.2	276.5	307.2	331.9	341.7	351.5	365.8	376.2	382.9	385.1	382.9
127.5°	237.9	270.8	300.4	325.1	334.4	343.6	357.9	367.2	372.9	375.1	372.9
130°	234.0	263.6	291.9	316.1	325.6	335.1	349.7	358.7	364.4	366.5	364.4
132.5°	230.4	256.1	282.2	305.8	315.2	324.7	339.0	349.4	354.7	356.9	354.7
135°	226.8	249.3	272.6	294.4	303.3	312.2	326.5	336.5	342.2	344.4	342.2
137.5°	223.6	242.9	263.3	282.2	290.4	298.6	312.2	322.6	327.2	329.7	327.2
140°	221.1	237.6	254.3	270.4	277.9	285.4	297.9	305.8	310.8	313.6	310.8
142.5°	219.0	232.6	246.8	260.1	266.4	272.6	283.3	290.4	294.7	296.5	294.7
145°	216.5	227.9	240.1	250.8	255.8	260.8	269.7	275.8	279.3	281.1	279.3
147.5°	214.3	224.0	234.0	242.9	247.0	251.1	257.9	263.3	266.1	266.8	266.1
150°	211.8	220.4	228.6	235.8	239.0	242.2	247.9	252.6	254.7	255.1	254.7
152.5°	209.0	216.5	223.3	229.7	232.2	234.7	239.3	242.9	244.0	244.3	244.0
155°	206.1	212.5	218.3	223.6	225.8	227.9	231.5	234.3	235.4	235.4	235.4
157.5°	203.3	208.3	213.3	217.9	219.7	221.5	224.3	226.5	227.2	227.2	227.2
160°	200.0	204.3	208.3	212.2	213.6	215.0	217.2	219.3	219.7	219.7	219.7
162.5°	197.2	200.4	203.6	206.5	207.8	209.0	210.4	212.5	212.9	212.5	212.9
165°	194.0	196.8	199.0	201.5	202.4	203.3	204.7	206.1	205.8	205.4	205.8
167.5°	191.1	193.3	195.0	197.2	197.8	198.3	199.0	200.0	200.0	199.7	200.0
170°	188.3	190.0	191.1	192.5	193.0	193.6	194.3	194.7	194.3	194.3	194.3
172.5°	185.8	187.2	187.9	188.6	189.0	189.3	189.7	190.0	189.7	189.0	189.7
175°	184.0	184.7	185.0	185.8	185.8	185.8	185.8	186.5	185.8	185.0	185.8
177.5°	182.5	182.9	183.3	183.3	183.4	183.6	183.3	183.6	182.9	182.2	182.9
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	602.4	601.0	599.2	599.2	596.9	596.9	593.1	586.7	581.1	579.3	580.2
5°	653.8	654.2	651.4	649.1	645.0	641.7	635.7	624.1	620.4	613.0	608.0
7.5°	712.5	710.7	705.6	701.9	701.0	693.6	680.6	666.7	655.6	648.2	637.6
10°	778.7	771.3	763.9	761.6	756.0	743.5	728.7	713.4	698.2	682.0	663.9
12.5°	834.2	819.9	819.4	813.8	803.2	796.3	778.7	756.9	730.6	712.5	692.2
15°	893.9	880.5	869.4	859.2	854.1	833.7	818.9	791.6	760.2	740.7	726.9
17.5°	936.5	930.4	911.5	906.8	899.9	876.3	852.7	825.9	798.6	771.3	733.8
20°	970.7	967.0	954.5	948.0	936.9	918.4	889.7	858.7	827.3	788.4	753.2
22.5°	985.5	980.9	970.7	965.1	958.2	942.5	917.9	882.8	841.6	806.9	769.4
25°	956.3	964.7	961.9	959.6	956.8	947.6	929.1	898.1	857.8	818.5	771.7
27.5°	890.6	905.0	918.9	920.7	925.4	929.1	921.6	899.4	865.7	824.0	772.7
30°	802.3	808.8	837.0	845.3	851.8	875.4	889.3	883.7	857.8	820.3	773.1
32.5°	688.9	706.0	734.7	754.6	772.2	798.6	834.7	849.0	839.8	809.2	762.5
35°	581.6	601.9	635.3	660.7	678.3	715.8	758.3	789.3	800.9	785.6	744.0
37.5°	493.7	518.2	547.8	557.5	577.9	624.1	682.9	725.9	754.2	755.5	723.2
40°	427.5	440.0	463.6	478.4	498.3	537.2	594.5	651.4	694.0	708.4	691.2
42.5°	371.5	381.2	398.8	416.9	434.9	464.5	517.3	570.5	627.9	656.5	656.1
45°	327.1	337.3	349.3	364.1	376.6	408.5	450.2	504.8	554.3	598.7	609.8
47.5°	288.2	297.0	311.8	318.3	326.6	356.7	392.8	443.7	495.1	546.0	558.9
50°	259.6	267.0	277.1	281.3	290.6	312.8	342.4	383.6	440.5	487.2	511.3
52.5°	233.7	239.2	247.1	250.3	256.8	273.4	300.3	332.7	379.9	428.0	461.7
55°	211.4	215.1	220.7	224.4	229.0	243.8	263.7	292.9	333.6	375.2	408.1
57.5°	190.6	193.4	199.0	200.8	204.5	216.1	229.9	254.5	291.9	329.0	360.9
60°	171.2	173.0	176.3	180.4	183.2	191.1	204.0	224.4	254.5	288.2	314.2
62.5°	152.7	155.5	156.4	158.2	160.5	168.0	178.1	192.9	219.3	247.1	274.4
65°	133.7	136.0	137.9	138.3	140.7	146.2	155.5	168.4	185.5	209.6	235.0
67.5°	116.1	117.5	118.4	120.3	122.6	125.4	132.8	142.5	158.2	177.7	198.0
70°	99.9	99.9	101.3	101.8	104.6	107.8	111.0	120.3	134.2	149.9	163.8
72.5°	82.4	84.7	84.2	86.5	86.1	88.4	92.5	98.5	108.7	121.2	134.6
75°	67.1	68.5	68.5	68.5	69.4	71.3	73.6	79.1	87.0	97.2	105.0
77.5°	52.3	53.2	53.2	53.2	53.7	55.5	57.8	61.5	67.1	73.1	77.7
80°	37.5	38.4	38.4	39.3	39.3	39.8	42.1	44.0	46.7	51.4	56.0
82.5°	25.4	25.9	26.8	26.8	26.4	27.3	27.8	29.6	32.4	33.3	36.6
85°	13.9	14.3	14.8	14.8	15.3	16.2	15.7	17.6	17.6	19.4	20.4
87.5°	5.6	6.5	6.5	6.0	6.5	6.5	6.5	7.4	7.9	8.3	7.9
90°	7.9	7.5	7.1	7.1	7.1	6.8	6.4	6.1	6.4	5.7	5.0
92.5°	33.9	36.4	41.8	46.2	50.7	64.3	86.1	116.5	140.0	122.5	88.9
95°	98.2	109.3	126.8	144.2	161.5	209.3	264.7	299.4	291.1	219.7	134.3
97.5°	228.6	250.1	274.3	294.4	314.4	353.6	381.2	375.4	311.5	210.4	122.5
100°	341.1	362.9	394.0	407.2	420.5	438.0	430.8	378.7	287.2	186.5	113.6
102.5°	444.0	458.3	474.4	478.0	481.5	470.8	428.3	351.9	256.8	170.4	111.1
105°	509.8	512.6	511.9	504.6	497.3	461.9	400.1	318.3	234.3	162.5	112.5
107.5°	533.7	527.3	511.5	496.5	481.5	432.2	365.4	290.8	219.7	160.4	116.8
110°	528.0	513.0	487.6	468.0	448.3	396.5	334.7	271.1	212.9	161.1	121.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	501.2	482.2	452.6	433.0	413.3	365.1	312.2	260.1	209.7	163.3	127.2
115°	468.3	446.9	418.7	401.5	384.4	342.6	298.6	254.0	209.0	166.1	132.9
117.5°	435.5	416.9	391.9	376.9	361.9	327.9	290.8	250.8	208.6	169.0	138.6
120°	409.0	393.3	372.9	360.2	347.6	319.0	285.8	248.3	208.6	172.2	144.7
122.5°	389.4	376.5	360.1	349.4	338.6	313.3	281.5	245.4	208.3	175.4	150.4
125°	376.2	365.8	351.5	341.7	331.9	307.2	276.5	242.2	207.9	178.6	156.1
127.5°	367.2	357.9	343.6	334.4	325.1	300.4	270.8	237.9	207.2	181.1	161.1
130°	358.7	349.7	335.1	325.6	316.1	291.9	263.6	234.0	206.8	184.0	165.8
132.5°	349.4	339.0	324.7	315.2	305.8	282.2	256.1	230.4	206.5	186.5	170.4
135°	336.5	326.5	312.2	303.3	294.4	272.6	249.3	226.8	206.1	189.0	174.3
137.5°	322.6	312.2	298.6	290.4	282.2	263.3	242.9	223.6	206.1	190.4	177.2
140°	305.8	297.9	285.4	277.9	270.4	254.3	237.6	221.1	205.8	192.2	180.0
142.5°	290.4	283.3	272.6	266.4	260.1	246.8	232.6	219.0	205.8	193.6	182.2
145°	275.8	269.7	260.8	255.8	250.8	240.1	227.9	216.5	205.0	194.0	183.6
147.5°	263.3	257.9	251.1	247.0	242.9	234.0	224.0	214.3	204.0	194.3	185.0
150°	252.6	247.9	242.2	239.0	235.8	228.6	220.4	211.8	202.9	194.3	186.1
152.5°	242.9	239.3	234.7	232.2	229.7	223.3	216.5	209.0	201.1	193.6	186.8
155°	234.3	231.5	227.9	225.8	223.6	218.3	212.5	206.1	199.3	192.9	187.2
157.5°	226.5	224.3	221.5	219.7	217.9	213.3	208.3	203.3	197.5	192.2	187.2
160°	219.3	217.2	215.0	213.6	212.2	208.3	204.3	200.0	195.4	191.1	187.2
162.5°	212.5	210.4	209.0	207.8	206.5	203.6	200.4	197.2	193.3	190.0	187.2
165°	206.1	204.7	203.3	202.4	201.5	199.0	196.8	194.0	191.1	188.6	186.5
167.5°	200.0	199.0	198.3	197.8	197.2	195.0	193.3	191.1	189.0	187.2	185.8
170°	194.7	194.3	193.6	193.0	192.5	191.1	190.0	188.3	186.8	185.8	185.0
172.5°	190.0	189.7	189.3	189.0	188.6	187.9	187.2	185.8	184.7	184.3	184.3
175°	186.5	185.8	185.8	185.8	185.8	185.0	184.7	184.0	183.3	183.3	183.6
177.5°	183.6	183.3	183.6	183.4	183.3	183.3	182.9	182.5	182.2	182.2	182.9
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	576.0	574.2	572.8	572.8	568.6	564.5	562.2	561.2	560.3	556.6	551.5
5°	599.6	593.6	589.4	585.3	578.3	570.9	563.5	559.4	553.4	545.0	539.0
7.5°	626.0	611.7	607.0	601.9	588.1	575.6	565.4	556.6	546.9	536.2	525.6
10°	648.2	632.9	622.8	614.0	595.9	579.3	564.0	551.0	538.6	524.7	511.7
12.5°	669.5	647.7	637.1	624.1	605.2	581.1	561.2	545.0	526.5	512.2	496.5
15°	699.1	662.6	645.0	636.6	611.2	583.0	558.9	534.9	519.6	497.8	484.0
17.5°	703.7	674.1	662.6	641.3	610.7	578.8	551.0	527.0	503.9	484.4	466.4
20°	719.9	681.1	662.6	649.1	608.9	576.5	546.0	515.0	492.7	471.9	451.6
22.5°	730.1	686.1	666.7	645.4	607.0	568.2	532.1	505.2	477.9	456.7	440.5
25°	727.3	683.4	661.6	641.7	595.0	556.1	523.7	489.5	464.1	440.9	419.6
27.5°	725.9	676.4	653.3	631.1	587.1	546.4	505.7	477.9	449.7	422.9	407.2
30°	722.2	667.6	640.8	616.7	570.9	528.4	493.7	461.3	433.1	408.5	387.7
32.5°	709.7	652.8	626.9	601.0	553.4	510.8	475.6	445.6	417.3	391.9	372.0
35°	693.1	635.3	607.0	579.7	532.1	489.0	456.7	425.2	398.8	374.3	355.3
37.5°	676.4	614.9	588.5	557.1	513.1	468.2	434.9	406.7	382.2	356.7	335.9
40°	652.4	590.8	561.7	534.9	483.5	441.4	410.9	385.4	361.3	337.3	319.7
42.5°	619.5	564.5	534.4	504.8	456.7	415.0	385.4	362.7	340.1	320.2	300.7
45°	586.2	532.5	505.7	479.3	427.0	387.7	360.4	339.6	320.6	298.9	283.2
47.5°	546.0	500.6	473.8	447.9	398.4	359.0	334.1	314.6	297.0	279.0	264.2
50°	504.8	465.5	440.9	414.1	366.9	331.3	306.8	290.6	276.2	259.1	247.1
52.5°	460.4	426.1	405.3	379.4	337.8	304.9	279.9	263.7	251.7	239.2	228.6
55°	413.2	388.2	366.0	345.2	305.8	276.2	254.0	239.7	231.3	219.8	210.5
57.5°	370.6	346.5	333.1	309.5	275.3	246.1	228.6	216.5	206.8	199.9	192.5
60°	326.2	306.8	291.9	274.8	244.8	220.2	201.7	194.8	184.6	179.5	176.3
62.5°	283.6	269.7	255.9	242.9	216.1	192.9	179.1	170.3	164.2	159.2	156.4
65°	243.4	230.4	220.7	209.1	186.9	168.4	155.5	148.5	142.5	141.1	137.9
67.5°	204.0	198.5	187.8	178.6	159.6	145.3	135.6	126.8	123.5	122.1	119.4
70°	170.7	164.2	155.9	148.1	133.7	121.2	112.4	109.2	104.6	104.1	100.9
72.5°	140.7	132.8	126.8	120.8	110.1	99.0	94.4	89.8	87.4	85.6	84.2
75°	111.5	106.0	101.8	96.7	87.4	80.0	73.6	71.7	70.3	69.9	68.9
77.5°	83.3	79.6	77.7	72.6	66.2	59.7	56.9	54.1	54.1	53.2	53.7
80°	59.2	56.9	54.6	51.8	46.3	43.5	41.2	39.3	38.4	37.9	38.4
82.5°	37.5	36.1	35.6	33.8	30.1	28.7	26.8	25.4	25.4	25.4	25.4
85°	20.8	20.8	20.8	18.0	16.7	15.3	14.3	13.9	13.9	13.9	14.3
87.5°	8.8	8.8	7.4	7.4	6.9	6.0	5.6	5.6	6.0	6.0	6.5
90°	5.0	2.9	2.9	2.9	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	54.3	32.1	27.5	22.9	16.4	11.1	7.1	5.0	7.1	11.1	16.4
95°	75.7	44.7	37.2	29.6	21.1	16.4	12.9	11.8	12.9	16.4	21.1
97.5°	72.2	47.5	41.1	34.7	27.1	22.9	19.6	19.6	19.6	22.9	27.1
100°	73.2	52.2	46.4	40.7	33.9	29.6	27.1	27.1	27.1	29.6	33.9
102.5°	76.8	58.2	52.8	47.5	41.1	37.2	35.0	34.3	35.0	37.2	41.1
105°	82.9	65.7	60.6	55.4	48.9	44.7	42.9	41.8	42.9	44.7	48.9
107.5°	89.3	73.6	68.4	63.2	57.2	52.5	50.7	50.0	50.7	52.5	57.2
110°	96.8	81.1	76.2	71.4	65.0	60.7	58.9	58.2	58.9	60.7	65.0

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	104.0	88.9	84.1	79.3	72.9	68.9	66.8	66.1	66.8	68.9	72.9
115°	111.5	97.2	92.4	87.5	80.7	77.2	74.7	73.6	74.7	77.2	80.7
117.5°	118.6	105.0	100.0	95.0	88.6	84.7	82.5	81.4	82.5	84.7	88.6
120°	126.1	112.5	107.5	102.5	96.4	92.5	90.0	89.3	90.0	92.5	96.4
122.5°	133.2	119.7	114.8	110.0	103.2	99.7	97.2	96.4	97.2	99.7	103.2
125°	139.7	126.8	121.8	116.8	110.0	106.1	104.0	102.5	104.0	106.1	110.0
127.5°	145.7	133.2	128.2	123.2	116.1	111.8	109.3	108.2	109.3	111.8	116.1
130°	151.8	139.7	134.5	129.3	122.5	117.2	114.3	112.9	114.3	117.2	122.5
132.5°	156.8	144.7	139.8	135.0	127.5	122.5	118.6	117.5	118.6	122.5	127.5
135°	161.5	149.7	145.0	140.4	132.9	126.8	123.2	121.8	123.2	126.8	132.9
137.5°	165.0	154.0	149.5	145.0	137.2	131.5	127.5	126.1	127.5	131.5	137.2
140°	168.6	157.9	153.6	149.3	141.8	135.7	131.8	130.7	131.8	135.7	141.8
142.5°	171.8	161.5	157.4	153.2	146.1	140.4	136.8	135.7	136.8	140.4	146.1
145°	174.0	164.7	160.8	156.8	150.0	145.0	141.5	140.4	141.5	145.0	150.0
147.5°	176.5	167.5	164.0	160.4	154.7	149.3	146.1	145.7	146.1	149.3	154.7
150°	178.3	170.4	167.0	163.6	158.2	154.0	151.1	150.7	151.1	154.0	158.2
152.5°	179.7	172.9	169.9	166.8	162.2	158.2	155.4	155.4	155.4	158.2	162.2
155°	181.1	175.0	172.4	169.7	165.8	162.2	160.0	159.7	160.0	162.2	165.8
157.5°	182.2	176.8	174.6	172.5	169.0	166.1	164.0	164.0	164.0	166.1	169.0
160°	182.9	178.6	176.6	174.7	171.8	169.3	167.9	167.9	167.9	169.3	171.8
162.5°	183.6	179.7	178.2	176.8	174.3	172.2	171.1	171.5	171.1	172.2	174.3
165°	183.6	180.4	179.4	178.3	176.5	174.7	174.0	174.0	174.0	174.7	176.5
167.5°	183.6	181.1	180.2	179.3	178.3	176.8	176.5	176.8	176.5	176.8	178.3
170°	183.3	181.5	181.0	180.4	179.7	178.6	178.3	178.6	178.3	178.6	179.7
172.5°	182.9	181.8	181.4	181.1	180.8	180.0	180.0	180.4	180.0	180.0	180.8
175°	182.5	181.8	181.8	181.8	181.5	181.1	181.1	181.5	181.1	181.1	181.5
177.5°	182.2	181.8	181.8	181.8	181.8	181.5	181.8	182.2	181.8	181.5	181.8
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	550.1	548.3	549.2	544.6	540.4	534.4	529.3	528.4	527.4	530.2	528.4
5°	534.4	532.1	529.8	524.2	515.9	510.8	503.4	502.9	500.2	496.0	496.9
7.5°	517.3	515.9	512.6	503.9	496.5	487.7	481.6	476.6	474.2	470.5	469.2
10°	503.4	498.3	495.5	485.8	477.0	467.8	459.9	456.2	452.0	448.8	446.5
12.5°	484.4	483.0	475.2	467.3	459.9	449.3	443.2	432.6	427.0	429.8	428.9
15°	471.9	465.5	463.6	452.5	440.0	433.1	422.0	415.0	412.7	408.5	403.5
17.5°	455.3	451.1	444.6	434.5	420.1	410.4	402.5	396.1	393.3	387.7	383.6
20°	439.5	432.6	427.5	418.3	404.4	391.9	382.2	378.0	371.1	366.4	364.1
22.5°	425.2	420.1	412.7	398.8	386.8	374.8	363.2	357.2	350.7	347.9	344.2
25°	407.6	399.3	394.2	378.9	366.0	356.3	345.6	337.8	334.1	329.4	328.5
27.5°	390.5	382.6	376.6	363.2	347.5	335.0	328.5	322.9	316.5	316.5	314.2
30°	373.4	367.8	358.6	345.6	330.8	318.8	311.4	306.3	304.0	302.1	301.7
32.5°	356.3	348.9	343.3	325.7	314.6	303.5	298.0	293.8	291.0	290.6	291.0
35°	338.7	330.4	324.8	309.1	298.0	287.8	285.5	281.8	280.4	279.9	282.2
37.5°	320.2	313.7	306.8	293.8	281.3	275.3	270.7	269.3	268.8	271.6	272.5
40°	303.1	297.5	291.0	277.1	267.9	261.4	259.1	257.7	259.6	262.3	263.7
42.5°	286.9	279.0	273.9	261.4	253.1	249.4	246.6	246.6	248.5	251.7	254.0
45°	269.7	263.7	258.6	247.5	240.1	236.0	235.5	236.0	238.3	240.6	243.4
47.5°	253.1	247.1	241.5	232.3	225.8	223.5	223.0	223.5	227.2	230.4	233.7
50°	237.8	231.3	226.2	217.5	212.4	209.6	210.1	212.4	215.1	219.8	223.9
52.5°	219.8	215.1	210.5	202.7	198.0	196.2	197.6	199.4	204.5	207.7	212.8
55°	202.2	198.0	194.3	188.3	184.6	183.2	184.1	186.9	191.1	196.6	202.7
57.5°	186.0	181.4	177.7	173.5	169.3	169.8	170.3	174.0	179.1	184.1	191.1
60°	168.0	165.2	161.9	156.8	155.0	155.0	156.4	160.5	165.2	173.5	179.5
62.5°	151.8	148.1	145.7	142.5	139.7	140.2	143.4	147.1	152.7	159.6	167.5
65°	135.1	130.9	129.1	126.3	125.4	125.8	128.2	133.7	139.7	145.7	153.1
67.5°	116.6	115.2	113.4	110.6	111.5	112.0	114.3	118.9	125.4	131.4	139.7
70°	100.9	98.1	97.6	95.3	95.3	96.7	101.3	104.6	110.6	117.1	125.8
72.5°	84.2	81.9	81.9	80.0	81.4	82.8	85.1	89.8	95.3	101.8	109.2
75°	67.1	66.2	67.1	66.2	66.2	68.5	71.3	75.0	81.0	87.9	93.9
77.5°	51.8	51.8	51.4	52.7	52.7	54.1	57.8	61.5	66.2	71.7	78.2
80°	37.9	37.9	37.9	39.3	40.7	40.7	43.0	47.7	51.8	55.5	61.5
82.5°	25.9	25.9	25.9	26.8	28.7	28.7	31.5	34.2	38.9	42.1	44.9
85°	15.7	15.7	15.3	16.2	16.7	18.0	20.4	22.2	24.5	27.3	30.1
87.5°	6.9	6.9	7.4	7.9	8.3	9.3	10.2	11.1	13.4	14.3	15.7
90°	2.9	2.9	2.9	5.0	5.0	5.7	6.4	6.1	6.4	6.8	7.1
92.5°	22.9	27.5	32.1	54.3	88.9	122.5	140.0	116.5	86.1	64.3	50.7
95°	29.6	37.2	44.7	75.7	134.3	219.7	291.1	299.4	264.7	209.3	161.5
97.5°	34.7	41.1	47.5	72.2	122.5	210.4	311.5	375.4	381.2	353.6	314.4
100°	40.7	46.4	52.2	73.2	113.6	186.5	287.2	378.7	430.8	438.0	420.5
102.5°	47.5	52.8	58.2	76.8	111.1	170.4	256.8	351.9	428.3	470.8	481.5
105°	55.4	60.6	65.7	82.9	112.5	162.5	234.3	318.3	400.1	461.9	497.3
107.5°	63.2	68.4	73.6	89.3	116.8	160.4	219.7	290.8	365.4	432.2	481.5
110°	71.4	76.2	81.1	96.8	121.8	161.1	212.9	271.1	334.7	396.5	448.3

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	79.3	84.1	88.9	104.0	127.2	163.3	209.7	260.1	312.2	365.1	413.3
115°	87.5	92.4	97.2	111.5	132.9	166.1	209.0	254.0	298.6	342.6	384.4
117.5°	95.0	100.0	105.0	118.6	138.6	169.0	208.6	250.8	290.8	327.9	361.9
120°	102.5	107.5	112.5	126.1	144.7	172.2	208.6	248.3	285.8	319.0	347.6
122.5°	110.0	114.8	119.7	133.2	150.4	175.4	208.3	245.4	281.5	313.3	338.6
125°	116.8	121.8	126.8	139.7	156.1	178.6	207.9	242.2	276.5	307.2	331.9
127.5°	123.2	128.2	133.2	145.7	161.1	181.1	207.2	237.9	270.8	300.4	325.1
130°	129.3	134.5	139.7	151.8	165.8	184.0	206.8	234.0	263.6	291.9	316.1
132.5°	135.0	139.8	144.7	156.8	170.4	186.5	206.5	230.4	256.1	282.2	305.8
135°	140.4	145.0	149.7	161.5	174.3	189.0	206.1	226.8	249.3	272.6	294.4
137.5°	145.0	149.5	154.0	165.0	177.2	190.4	206.1	223.6	242.9	263.3	282.2
140°	149.3	153.6	157.9	168.6	180.0	192.2	205.8	221.1	237.6	254.3	270.4
142.5°	153.2	157.4	161.5	171.8	182.2	193.6	205.8	219.0	232.6	246.8	260.1
145°	156.8	160.8	164.7	174.0	183.6	194.0	205.0	216.5	227.9	240.1	250.8
147.5°	160.4	164.0	167.5	176.5	185.0	194.3	204.0	214.3	224.0	234.0	242.9
150°	163.6	167.0	170.4	178.3	186.1	194.3	202.9	211.8	220.4	228.6	235.8
152.5°	166.8	169.9	172.9	179.7	186.8	193.6	201.1	209.0	216.5	223.3	229.7
155°	169.7	172.4	175.0	181.1	187.2	192.9	199.3	206.1	212.5	218.3	223.6
157.5°	172.5	174.6	176.8	182.2	187.2	192.2	197.5	203.3	208.3	213.3	217.9
160°	174.7	176.6	178.6	182.9	187.2	191.1	195.4	200.0	204.3	208.3	212.2
162.5°	176.8	178.2	179.7	183.6	187.2	190.0	193.3	197.2	200.4	203.6	206.5
165°	178.3	179.4	180.4	183.6	186.5	188.6	191.1	194.0	196.8	199.0	201.5
167.5°	179.3	180.2	181.1	183.6	185.8	187.2	189.0	191.1	193.3	195.0	197.2
170°	180.4	181.0	181.5	183.3	185.0	185.8	186.8	188.3	190.0	191.1	192.5
172.5°	181.1	181.4	181.8	182.9	184.3	184.3	184.7	185.8	187.2	187.9	188.6
175°	181.8	181.8	181.8	182.5	183.6	183.3	183.3	184.0	184.7	185.0	185.8
177.5°	181.8	181.8	181.8	182.2	182.9	182.2	182.2	182.5	182.9	183.3	183.3
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	527.0	526.5	524.2	525.1	522.4	523.3	524.7	525.1	527.0	525.6	525.1
5°	494.6	493.7	492.3	490.9	490.4	492.3	489.0	490.0	490.9	492.3	494.1
7.5°	468.2	467.8	466.4	464.1	463.1	462.2	462.7	465.9	465.5	465.0	468.2
10°	444.2	444.6	441.9	441.4	438.6	438.2	438.6	439.5	440.9	442.8	443.2
12.5°	419.2	425.2	420.1	418.3	414.1	416.4	417.3	413.2	415.5	416.9	423.8
15°	403.5	400.7	397.4	397.4	395.6	394.7	392.3	395.6	397.4	400.2	399.3
17.5°	381.7	377.1	375.2	373.4	373.8	375.7	370.6	378.0	378.0	379.4	377.1
20°	362.7	359.0	356.7	355.8	354.4	353.5	353.0	354.9	357.6	358.6	360.9
22.5°	342.8	342.8	339.1	337.8	336.8	335.4	337.8	336.4	338.2	340.1	343.8
25°	326.2	326.2	324.8	322.9	321.6	320.6	322.0	321.6	322.9	325.3	326.2
27.5°	312.8	311.4	310.9	310.5	310.0	310.5	310.0	311.4	312.8	313.2	312.3
30°	301.2	299.8	300.3	300.3	300.7	300.3	299.8	301.2	301.7	300.7	301.2
32.5°	290.6	290.6	291.5	291.9	291.9	292.4	292.9	291.9	292.4	291.0	291.5
35°	281.8	282.7	283.6	284.1	284.5	284.1	285.0	284.5	283.6	282.7	282.2
37.5°	273.0	273.9	275.8	276.2	277.6	278.1	277.1	277.1	276.7	274.8	273.9
40°	263.7	264.7	267.0	268.4	269.3	270.7	269.7	269.7	267.9	266.0	264.7
42.5°	254.9	256.8	259.1	260.5	262.3	262.3	262.3	261.4	259.1	257.2	255.9
45°	246.1	246.6	249.8	252.2	254.0	254.0	254.0	252.6	251.2	247.5	245.7
47.5°	236.4	237.8	241.5	243.8	245.7	246.1	246.1	244.8	242.0	238.7	236.4
50°	225.8	228.1	232.3	235.5	237.8	238.7	237.4	236.4	233.2	229.5	226.7
52.5°	215.6	218.4	223.5	226.2	229.5	229.9	229.5	228.1	224.4	219.3	217.0
55°	205.4	207.7	213.3	217.9	220.7	221.6	220.7	218.4	213.8	208.7	206.4
57.5°	194.3	197.6	203.6	208.2	211.4	211.9	211.0	208.7	205.0	198.5	195.2
60°	182.8	186.9	192.9	197.6	201.7	202.2	201.3	198.0	193.4	186.9	184.1
62.5°	171.2	174.4	181.4	186.5	189.7	192.0	190.2	186.9	182.3	175.8	171.7
65°	157.8	162.4	168.4	173.0	176.7	177.2	176.3	173.5	168.4	161.5	158.2
67.5°	144.8	148.1	154.1	160.1	161.5	162.9	161.5	158.7	154.5	148.5	143.9
70°	129.1	131.9	139.3	143.4	145.3	146.7	145.7	143.0	139.3	133.7	130.0
72.5°	113.4	115.7	122.6	125.8	129.5	129.1	128.6	126.8	121.7	118.0	115.7
75°	96.7	99.5	104.1	108.3	109.7	109.7	109.7	108.3	105.0	99.0	96.7
77.5°	81.4	82.8	86.5	88.8	90.2	90.7	90.2	87.9	86.1	81.9	80.5
80°	62.5	66.2	68.9	69.4	71.3	71.3	71.3	70.3	68.5	64.3	63.8
82.5°	47.2	48.1	50.9	52.3	53.2	52.7	52.7	50.9	50.4	48.1	47.2
85°	31.9	33.3	32.8	34.7	35.2	34.2	34.2	35.2	32.8	33.3	31.9
87.5°	17.6	17.6	18.5	18.0	19.9	19.9	19.0	19.4	18.5	18.0	17.6
90°	7.1	7.1	7.5	7.9	7.5	7.5	7.5	7.9	7.5	7.1	7.1
92.5°	46.2	41.8	36.4	33.9	32.5	32.5	32.5	33.9	36.4	41.8	46.2
95°	144.2	126.8	109.3	98.2	91.8	87.2	91.8	98.2	109.3	126.8	144.2
97.5°	294.4	274.3	250.1	228.6	217.9	209.3	217.9	228.6	250.1	274.3	294.4
100°	407.2	394.0	362.9	341.1	330.4	327.6	330.4	341.1	362.9	394.0	407.2
102.5°	478.0	474.4	458.3	444.0	432.6	430.5	432.6	444.0	458.3	474.4	478.0
105°	504.6	511.9	512.6	509.8	504.8	502.6	504.8	509.8	512.6	511.9	504.6
107.5°	496.5	511.5	527.3	533.7	536.5	536.9	536.5	533.7	527.3	511.5	496.5
110°	468.0	487.6	513.0	528.0	534.4	537.6	534.4	528.0	513.0	487.6	468.0

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	433.0	452.6	482.2	501.2	510.8	516.5	510.8	501.2	482.2	452.6	433.0
115°	401.5	418.7	446.9	468.3	479.7	482.6	479.7	468.3	446.9	418.7	401.5
117.5°	376.9	391.9	416.9	435.5	447.6	449.4	447.6	435.5	416.9	391.9	376.9
120°	360.2	372.9	393.3	409.0	418.3	422.2	418.3	409.0	393.3	372.9	360.2
122.5°	349.4	360.1	376.5	389.4	396.9	400.8	396.9	389.4	376.5	360.1	349.4
125°	341.7	351.5	365.8	376.2	382.9	385.1	382.9	376.2	365.8	351.5	341.7
127.5°	334.4	343.6	357.9	367.2	372.9	375.1	372.9	367.2	357.9	343.6	334.4
130°	325.6	335.1	349.7	358.7	364.4	366.5	364.4	358.7	349.7	335.1	325.6
132.5°	315.2	324.7	339.0	349.4	354.7	356.9	354.7	349.4	339.0	324.7	315.2
135°	303.3	312.2	326.5	336.5	342.2	344.4	342.2	336.5	326.5	312.2	303.3
137.5°	290.4	298.6	312.2	322.6	327.2	329.7	327.2	322.6	312.2	298.6	290.4
140°	277.9	285.4	297.9	305.8	310.8	313.6	310.8	305.8	297.9	285.4	277.9
142.5°	266.4	272.6	283.3	290.4	294.7	296.5	294.7	290.4	283.3	272.6	266.4
145°	255.8	260.8	269.7	275.8	279.3	281.1	279.3	275.8	269.7	260.8	255.8
147.5°	247.0	251.1	257.9	263.3	266.1	266.8	266.1	263.3	257.9	251.1	247.0
150°	239.0	242.2	247.9	252.6	254.7	255.1	254.7	252.6	247.9	242.2	239.0
152.5°	232.2	234.7	239.3	242.9	244.0	244.3	244.0	242.9	239.3	234.7	232.2
155°	225.8	227.9	231.5	234.3	235.4	235.4	235.4	234.3	231.5	227.9	225.8
157.5°	219.7	221.5	224.3	226.5	227.2	227.2	227.2	226.5	224.3	221.5	219.7
160°	213.6	215.0	217.2	219.3	219.7	219.7	219.7	219.3	217.2	215.0	213.6
162.5°	207.8	209.0	210.4	212.5	212.9	212.5	212.9	212.5	210.4	209.0	207.8
165°	202.4	203.3	204.7	206.1	205.8	205.4	205.8	206.1	204.7	203.3	202.4
167.5°	197.8	198.3	199.0	200.0	200.0	199.7	200.0	200.0	199.0	198.3	197.8
170°	193.0	193.6	194.3	194.7	194.3	194.3	194.3	194.7	194.3	193.6	193.0
172.5°	189.0	189.3	189.7	190.0	189.7	189.0	189.7	190.0	189.7	189.3	189.0
175°	185.8	185.8	185.8	186.5	185.8	185.0	185.8	186.5	185.8	185.8	185.8
177.5°	183.4	183.6	183.3	183.6	182.9	182.2	182.9	183.6	183.3	183.6	183.4
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	525.1	527.9	525.1	527.0	527.9	530.2	531.2	535.3	536.7	539.9	539.9
5°	493.7	495.1	495.5	497.4	499.2	503.9	507.1	513.1	520.0	521.0	525.1
7.5°	468.2	470.5	474.2	472.9	476.1	483.0	487.2	494.6	501.5	505.2	510.3
10°	445.6	448.3	449.7	451.1	457.1	463.1	469.6	474.7	484.0	489.5	493.7
12.5°	427.0	424.7	427.5	432.6	439.5	443.2	452.0	459.9	466.8	472.9	476.6
15°	403.0	404.8	407.6	416.4	418.3	427.5	430.8	439.5	452.5	458.0	462.7
17.5°	379.9	385.9	391.4	394.7	400.2	407.6	416.9	426.6	434.9	441.4	446.9
20°	361.3	367.4	370.6	372.9	378.5	388.6	397.4	409.5	420.1	425.2	432.6
22.5°	346.5	346.5	351.2	358.1	361.3	371.1	378.5	391.4	403.0	409.5	416.4
25°	328.0	330.8	334.5	340.5	345.2	353.0	363.7	374.8	387.3	392.8	401.6
27.5°	312.8	316.0	321.1	322.5	327.1	334.1	345.2	357.2	370.1	376.2	383.6
30°	301.2	303.1	304.9	307.7	311.8	317.9	327.1	337.8	353.5	358.1	367.4
32.5°	291.0	291.9	292.9	295.2	297.5	303.5	310.9	322.5	335.4	342.4	350.7
35°	281.8	280.8	281.3	282.7	285.0	287.3	295.2	304.9	316.9	325.3	331.7
37.5°	273.0	271.1	270.7	270.7	271.6	274.4	280.4	288.7	301.7	308.6	315.1
40°	263.3	261.4	260.5	260.0	259.6	261.4	266.0	274.4	284.5	291.0	298.4
42.5°	254.0	252.2	249.8	249.4	248.5	249.4	252.6	260.5	269.3	275.8	281.8
45°	244.8	241.5	238.7	236.9	237.4	236.0	238.3	244.3	254.5	258.6	264.7
47.5°	234.6	230.9	227.2	225.3	223.5	224.4	225.3	230.4	239.2	243.4	249.4
50°	224.9	219.8	215.6	213.3	211.9	211.0	211.9	217.0	223.5	227.2	232.3
52.5°	213.8	208.7	204.5	200.8	199.0	197.6	198.0	202.7	208.7	212.4	217.5
55°	203.6	197.1	191.5	186.9	185.5	185.1	184.6	187.8	192.9	196.6	200.8
57.5°	192.0	185.5	179.5	174.0	171.2	170.7	170.7	171.7	178.1	180.9	183.2
60°	180.4	173.5	167.0	161.9	157.8	156.4	155.9	157.8	161.0	163.8	167.0
62.5°	167.5	160.5	152.7	148.1	143.9	140.2	141.6	142.0	146.7	148.1	150.8
65°	155.0	147.1	140.7	133.3	128.6	126.3	125.4	126.3	130.0	130.5	132.3
67.5°	140.7	133.3	125.4	120.3	116.1	112.0	111.0	111.0	112.9	114.3	116.6
70°	126.8	119.4	110.6	105.0	100.9	97.2	95.8	95.3	96.7	97.6	99.9
72.5°	110.6	103.2	96.7	90.7	85.6	82.8	81.4	80.5	81.9	82.8	83.3
75°	93.5	87.4	81.0	75.0	71.7	68.9	67.1	65.7	66.6	66.6	66.6
77.5°	77.3	71.3	66.2	62.0	57.8	54.6	53.2	51.8	52.3	52.3	53.2
80°	60.1	56.0	51.8	48.1	44.4	41.6	40.7	39.3	38.4	37.9	37.9
82.5°	44.4	41.2	37.5	34.2	32.4	29.6	28.7	26.8	26.8	26.4	26.4
85°	29.6	27.8	24.1	21.7	20.4	19.0	18.0	17.1	15.7	15.7	15.3
87.5°	15.7	14.8	13.9	11.1	11.1	9.7	9.3	8.8	7.4	7.9	7.9
90°	7.1	6.8	6.4	6.1	6.4	5.7	5.0	5.0	2.9	2.9	2.9
92.5°	50.7	64.3	86.1	116.5	140.0	122.5	88.9	54.3	32.1	27.5	22.9
95°	161.5	209.3	264.7	299.4	291.1	219.7	134.3	75.7	44.7	37.2	29.6
97.5°	314.4	353.6	381.2	375.4	311.5	210.4	122.5	72.2	47.5	41.1	34.7
100°	420.5	438.0	430.8	378.7	287.2	186.5	113.6	73.2	52.2	46.4	40.7
102.5°	481.5	470.8	428.3	351.9	256.8	170.4	111.1	76.8	58.2	52.8	47.5
105°	497.3	461.9	400.1	318.3	234.3	162.5	112.5	82.9	65.7	60.6	55.4
107.5°	481.5	432.2	365.4	290.8	219.7	160.4	116.8	89.3	73.6	68.4	63.2
110°	448.3	396.5	334.7	271.1	212.9	161.1	121.8	96.8	81.1	76.2	71.4

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	413.3	365.1	312.2	260.1	209.7	163.3	127.2	104.0	88.9	84.1	79.3
115°	384.4	342.6	298.6	254.0	209.0	166.1	132.9	111.5	97.2	92.4	87.5
117.5°	361.9	327.9	290.8	250.8	208.6	169.0	138.6	118.6	105.0	100.0	95.0
120°	347.6	319.0	285.8	248.3	208.6	172.2	144.7	126.1	112.5	107.5	102.5
122.5°	338.6	313.3	281.5	245.4	208.3	175.4	150.4	133.2	119.7	114.8	110.0
125°	331.9	307.2	276.5	242.2	207.9	178.6	156.1	139.7	126.8	121.8	116.8
127.5°	325.1	300.4	270.8	237.9	207.2	181.1	161.1	145.7	133.2	128.2	123.2
130°	316.1	291.9	263.6	234.0	206.8	184.0	165.8	151.8	139.7	134.5	129.3
132.5°	305.8	282.2	256.1	230.4	206.5	186.5	170.4	156.8	144.7	139.8	135.0
135°	294.4	272.6	249.3	226.8	206.1	189.0	174.3	161.5	149.7	145.0	140.4
137.5°	282.2	263.3	242.9	223.6	206.1	190.4	177.2	165.0	154.0	149.5	145.0
140°	270.4	254.3	237.6	221.1	205.8	192.2	180.0	168.6	157.9	153.6	149.3
142.5°	260.1	246.8	232.6	219.0	205.8	193.6	182.2	171.8	161.5	157.4	153.2
145°	250.8	240.1	227.9	216.5	205.0	194.0	183.6	174.0	164.7	160.8	156.8
147.5°	242.9	234.0	224.0	214.3	204.0	194.3	185.0	176.5	167.5	164.0	160.4
150°	235.8	228.6	220.4	211.8	202.9	194.3	186.1	178.3	170.4	167.0	163.6
152.5°	229.7	223.3	216.5	209.0	201.1	193.6	186.8	179.7	172.9	169.9	166.8
155°	223.6	218.3	212.5	206.1	199.3	192.9	187.2	181.1	175.0	172.4	169.7
157.5°	217.9	213.3	208.3	203.3	197.5	192.2	187.2	182.2	176.8	174.6	172.5
160°	212.2	208.3	204.3	200.0	195.4	191.1	187.2	182.9	178.6	176.6	174.7
162.5°	206.5	203.6	200.4	197.2	193.3	190.0	187.2	183.6	179.7	178.2	176.8
165°	201.5	199.0	196.8	194.0	191.1	188.6	186.5	183.6	180.4	179.4	178.3
167.5°	197.2	195.0	193.3	191.1	189.0	187.2	185.8	183.6	181.1	180.2	179.3
170°	192.5	191.1	190.0	188.3	186.8	185.8	185.0	183.3	181.5	181.0	180.4
172.5°	188.6	187.9	187.2	185.8	184.7	184.3	184.3	182.9	181.8	181.4	181.1
175°	185.8	185.0	184.7	184.0	183.3	183.3	183.6	182.5	181.8	181.8	181.8
177.5°	183.3	183.3	182.9	182.5	182.2	182.2	182.9	182.2	181.8	181.8	181.8
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	558.4	558.4	558.4	558.4
2.5°	543.2	547.8	552.0	558.4
5°	531.2	537.6	546.4	556.1
7.5°	517.3	527.4	539.0	552.4
10°	504.3	515.9	530.7	546.9
12.5°	490.9	504.8	521.0	538.6
15°	475.6	489.5	507.6	531.2
17.5°	461.7	478.4	497.8	522.8
20°	445.6	461.3	482.6	511.3
22.5°	431.2	449.3	472.9	497.8
25°	415.5	431.2	454.8	484.9
27.5°	399.8	419.2	441.9	471.0
30°	384.5	400.7	425.2	455.7
32.5°	367.8	387.3	409.9	438.6
35°	349.8	368.3	389.6	420.6
37.5°	333.6	351.6	373.4	400.7
40°	315.5	334.5	354.4	381.7
42.5°	298.0	315.1	335.0	360.0
45°	280.8	295.6	313.7	335.4
47.5°	263.3	275.8	292.4	311.8
50°	244.3	257.7	270.2	286.4
52.5°	226.7	238.3	248.5	261.9
55°	209.6	217.5	225.8	236.0
57.5°	191.5	197.6	203.6	214.2
60°	173.5	179.1	182.3	189.2
62.5°	155.9	158.2	162.4	166.6
65°	136.5	139.7	142.0	147.1
67.5°	118.9	120.3	122.6	125.8
70°	100.4	103.6	104.6	106.9
72.5°	84.7	86.1	87.0	87.4
75°	67.1	68.5	69.4	72.2
77.5°	52.7	52.3	54.1	54.6
80°	38.9	37.5	37.9	39.8
82.5°	25.4	25.9	25.4	25.4
85°	15.7	15.3	14.3	14.8
87.5°	6.9	6.9	6.5	6.5
90°	2.5	2.1	1.1	0.4
92.5°	16.4	11.1	7.1	5.0
95°	21.1	16.4	12.9	11.8
97.5°	27.1	22.9	19.6	19.6
100°	33.9	29.6	27.1	27.1
102.5°	41.1	37.2	35.0	34.3
105°	48.9	44.7	42.9	41.8
107.5°	57.2	52.5	50.7	50.0
110°	65.0	60.7	58.9	58.2



TEST NUMBER: P1001255

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	72.9	68.9	66.8	66.1
115°	80.7	77.2	74.7	73.6
117.5°	88.6	84.7	82.5	81.4
120°	96.4	92.5	90.0	89.3
122.5°	103.2	99.7	97.2	96.4
125°	110.0	106.1	104.0	102.5
127.5°	116.1	111.8	109.3	108.2
130°	122.5	117.2	114.3	112.9
132.5°	127.5	122.5	118.6	117.5
135°	132.9	126.8	123.2	121.8
137.5°	137.2	131.5	127.5	126.1
140°	141.8	135.7	131.8	130.7
142.5°	146.1	140.4	136.8	135.7
145°	150.0	145.0	141.5	140.4
147.5°	154.7	149.3	146.1	145.7
150°	158.2	154.0	151.1	150.7
152.5°	162.2	158.2	155.4	155.4
155°	165.8	162.2	160.0	159.7
157.5°	169.0	166.1	164.0	164.0
160°	171.8	169.3	167.9	167.9
162.5°	174.3	172.2	171.1	171.5
165°	176.5	174.7	174.0	174.0
167.5°	178.3	176.8	176.5	176.8
170°	179.7	178.6	178.3	178.6
172.5°	180.8	180.0	180.0	180.4
175°	181.5	181.1	181.1	181.5
177.5°	181.8	181.5	181.8	182.2
180°	181.8	181.8	181.8	181.8

(END OF REPORT)