

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001306

Luminaire Tested: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001306
REPORT IS A COMBINATION OF REPORTS P995925 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3655.0 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35
3	80	71	64	58	73	65	59	54	54	49	46	44	41	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	49	38	31	27	32	27	23	26	22	20	21	18	16
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4536	4536	4536	4536
5°	4525	5204	4551	3911
10°	4491	6071	4525	3430
15°	4437	6999	4468	3069
20°	4380	7590	4412	2752
25°	4296	7503	4337	2518
30°	4214	6201	4265	2397
35°	4098	4621	4143	2324
40°	3964	3481	4003	2288
45°	3759	2794	3806	2239
50°	3515	2354	3565	2216
55°	3226	2049	3277	2191
60°	2947	1804	3033	2154
65°	2685	1552	2709	2064
70°	2376	1278	2427	1901
75°	2072	982	2058	1615
80°	1629	644	1612	1226
85°	1070	289	1004	715

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5865 cd/sqm

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	1.5
10°-20°	167.1	4.6
20°-30°	265.5	7.3
30°-40°	295.0	8.1
40°-50°	268.3	7.3
50°-60°	219.2	6.0
60°-70°	156.5	4.3
70°-80°	86.1	2.4
80°-90°	24.4	0.7
90°-100°	210.8	5.8
100°-110°	440.2	12.0
110°-120°	391.3	10.7
120°-130°	329.4	9.0
130°-140°	274.8	7.5
140°-150°	209.8	5.7
150°-160°	147.5	4.0
160°-170°	86.8	2.4
170°-180°	28.2	0.8
0°-30°	486.7	13.3
0°-40°	781.7	21.4
0°-60°	1269.2	34.7
0°-90°	1536.1	42.0
90°-120°	1042.3	28.5
90°-150°	1856.4	50.8
90°-180°	2119.0	58.0
0°-180°	3655.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	556	556	556	556	556	
5°	554	653	557	490	554	53
15°	529	896	533	393	529	149
25°	483	952	488	319	483	223
35°	419	563	424	283	419	262
45°	334	316	338	253	334	258
55°	235	206	239	221	235	211
65°	147	133	148	176	147	145
75°	72	66	71	109	72	76
85°	15	14	14	34	15	17
90°	1	12	1	12	1	2
95°	19	140	19	140	19	21
105°	67	804	67	804	67	71
115°	118	772	118	772	118	117
125°	164	616	164	616	164	146
135°	195	551	195	551	195	151
145°	225	450	225	450	225	141
155°	256	377	256	377	256	118
165°	278	329	278	329	278	79
175°	290	296	290	296	290	28
180°	291	291	291	291	291	

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	556.3	561.8	564.1	566.0	571.9	573.8	574.2	577.0	579.3	579.8	579.8
5°	554.0	562.7	569.6	576.1	585.8	589.9	595.0	600.5	607.9	612.5	614.8
7.5°	550.3	563.2	573.8	584.8	598.2	606.5	611.1	625.9	636.0	644.3	654.4
10°	544.8	561.3	576.6	592.7	611.6	621.7	631.9	649.8	664.1	680.2	693.2
12.5°	536.5	558.1	576.6	599.1	622.6	634.6	646.6	677.9	694.5	708.8	731.9
15°	529.1	550.7	577.0	600.1	629.1	647.1	664.6	684.9	711.1	742.0	764.1
17.5°	520.8	548.0	572.4	604.7	636.9	654.0	668.3	699.6	736.5	766.9	787.2
20°	509.3	536.9	569.2	603.3	641.5	654.9	673.8	715.7	748.9	778.9	812.1
22.5°	495.9	528.2	562.3	595.0	634.6	662.7	683.5	720.3	760.4	795.0	832.3
25°	483.0	518.0	548.0	592.7	634.6	653.5	677.0	720.8	764.6	806.5	844.8
27.5°	469.2	501.9	542.4	577.9	625.4	646.1	671.5	719.4	766.0	807.9	848.9
30°	454.0	489.0	522.6	564.6	610.7	637.4	660.9	713.0	760.4	804.2	842.5
32.5°	436.9	470.1	506.0	545.7	594.1	621.3	650.8	704.2	754.9	792.7	822.2
35°	418.9	452.6	483.9	524.5	574.2	601.4	630.0	689.0	739.2	770.1	787.2
37.5°	399.1	430.9	461.8	501.9	551.7	580.7	609.7	666.9	714.4	740.2	735.6
40°	380.2	408.8	437.4	475.2	527.2	558.1	583.5	641.1	682.6	693.6	678.4
42.5°	358.6	383.0	410.6	449.4	500.0	529.1	560.9	613.4	644.3	639.7	613.9
45°	334.1	355.8	383.4	419.9	471.5	501.4	528.2	577.9	600.5	589.0	542.0
47.5°	310.6	331.8	354.4	390.8	441.1	466.4	493.6	538.3	551.2	526.8	479.8
50°	285.3	302.8	326.3	360.9	407.9	434.6	457.2	493.1	497.7	467.8	418.9
52.5°	260.9	275.6	298.2	332.3	376.1	397.3	419.4	451.2	447.5	416.6	369.6
55°	235.0	248.9	269.6	301.0	339.7	359.9	378.8	407.0	399.1	367.3	326.3
57.5°	213.4	223.1	243.3	272.4	304.2	326.3	342.4	364.6	352.6	320.8	282.5
60°	188.5	200.5	217.5	241.0	272.4	287.1	301.4	316.2	307.9	277.4	243.3
62.5°	165.9	175.1	189.9	212.5	236.9	250.3	265.5	274.7	266.4	238.3	209.7
65°	146.6	153.9	165.5	183.9	207.4	218.5	227.2	236.0	229.1	202.8	182.0
67.5°	125.4	131.8	141.5	156.2	176.1	183.9	192.2	198.2	190.3	172.8	152.5
70°	106.5	111.1	120.3	131.3	145.2	152.5	159.5	165.5	158.5	143.8	128.6
72.5°	87.1	90.8	99.1	106.9	119.4	124.4	129.5	134.1	131.8	118.0	105.5
75°	71.9	73.3	78.8	85.3	93.1	98.6	102.3	105.1	103.2	92.2	84.3
77.5°	54.4	56.2	60.4	65.4	72.4	75.6	77.9	80.7	78.3	69.6	64.1
80°	39.6	40.1	42.4	47.0	51.6	52.1	54.4	58.1	56.7	50.7	46.5
82.5°	25.3	26.7	27.7	30.4	33.6	34.6	35.9	36.9	36.4	32.7	31.3
85°	14.7	14.7	15.7	17.5	18.4	19.8	20.3	20.7	21.7	19.4	18.0
87.5°	6.5	6.9	6.9	7.4	8.3	8.3	8.8	9.2	9.7	9.2	7.8
90°	0.6	1.7	3.4	4.0	4.6	4.6	4.6	8.0	8.0	9.1	10.3
92.5°	8.0	11.4	17.7	26.3	36.6	44.0	51.4	86.9	142.3	196.0	224.0
95°	18.9	20.6	26.3	33.7	47.4	59.4	71.4	121.2	214.9	351.5	465.8
97.5°	31.4	31.4	36.6	43.4	55.4	65.7	76.0	115.5	196.0	336.6	498.4
100°	43.4	43.4	47.4	54.3	65.2	74.3	83.4	117.2	181.8	298.4	459.5
102.5°	54.9	56.0	59.4	65.7	76.0	84.6	93.2	122.9	177.8	272.6	410.9
105°	66.9	68.6	71.4	78.3	88.6	96.9	105.2	132.6	180.0	260.1	374.9
107.5°	80.0	81.2	84.0	91.4	101.2	109.4	117.7	142.9	186.9	256.6	351.5
110°	93.2	94.3	97.2	104.0	114.3	122.0	129.7	154.9	194.9	257.8	340.6

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.7	106.9	110.3	116.6	126.9	134.6	142.3	166.3	203.5	261.2	335.5
115°	117.7	119.5	123.5	129.2	140.0	147.8	155.5	178.3	212.6	265.8	334.4
117.5°	130.3	132.0	135.5	141.7	152.0	160.0	168.0	189.8	221.8	270.3	333.8
120°	142.9	144.0	148.0	154.3	164.0	172.0	180.0	201.8	231.5	275.5	333.8
122.5°	154.3	155.5	159.5	165.2	176.0	183.8	191.5	213.2	240.6	280.6	333.2
125°	164.0	166.3	169.8	176.0	186.9	194.9	202.9	223.5	249.8	285.8	332.6
127.5°	173.2	174.9	178.9	185.8	197.2	205.2	213.2	233.2	257.8	289.8	331.5
130°	180.6	182.9	187.5	196.0	206.9	215.2	223.5	242.9	265.2	294.4	330.9
132.5°	188.0	189.8	196.0	204.0	216.0	223.8	231.5	250.9	272.6	298.4	330.4
135°	194.9	197.2	202.9	212.6	224.6	232.0	239.5	258.3	278.9	302.4	329.8
137.5°	201.8	204.0	210.3	219.5	232.1	239.2	246.3	264.1	283.5	304.6	329.8
140°	209.2	210.9	217.2	226.9	238.9	245.8	252.6	269.8	288.1	307.5	329.2
142.5°	217.2	218.9	224.6	233.8	245.2	251.8	258.3	274.9	291.5	309.8	329.2
145°	224.6	226.3	232.1	240.1	250.9	257.2	263.5	278.3	293.8	310.4	328.1
147.5°	233.2	233.8	238.9	247.5	256.6	262.4	268.1	282.3	296.1	310.9	326.4
150°	241.2	241.8	246.3	253.2	261.8	267.2	272.6	285.2	297.8	310.9	324.6
152.5°	248.6	248.6	253.2	259.5	266.9	271.8	276.6	287.5	298.9	309.8	321.8
155°	255.5	256.1	259.5	265.2	271.5	275.8	280.1	289.8	299.5	308.6	318.9
157.5°	262.3	262.3	265.8	270.3	276.1	279.5	282.9	291.5	299.5	307.5	316.1
160°	268.6	268.6	270.9	274.9	279.5	282.6	285.8	292.6	299.5	305.8	312.6
162.5°	274.3	273.8	275.5	278.9	282.9	285.2	287.5	293.8	299.5	304.1	309.2
165°	278.3	278.3	279.5	282.3	285.2	286.9	288.6	293.8	298.4	301.8	305.8
167.5°	282.9	282.3	282.9	285.2	286.9	288.4	289.8	293.8	297.2	299.5	302.4
170°	285.8	285.2	285.8	287.5	288.6	289.5	290.4	293.2	296.1	297.2	298.9
172.5°	288.6	288.1	288.1	289.2	289.8	290.4	290.9	292.6	294.9	294.9	295.5
175°	290.4	289.8	289.8	290.4	290.9	290.9	290.9	292.1	293.8	293.2	293.2
177.5°	291.5	290.9	290.4	290.9	290.9	290.9	290.9	291.5	292.6	291.5	291.5
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	581.2	589.5	593.1	594.1	599.1	595.9	597.3	596.8	600.5	601.0	601.0
5°	623.6	633.2	636.5	641.1	648.0	649.8	648.4	651.2	656.3	652.6	658.1
7.5°	668.3	678.9	686.2	696.4	698.7	704.7	708.4	711.6	712.5	713.0	713.9
10°	709.7	723.1	733.3	750.3	754.0	757.2	773.3	766.9	775.2	772.4	773.3
12.5°	743.4	769.7	778.0	806.5	809.3	820.4	819.4	829.6	831.4	835.1	831.4
15°	787.6	818.1	831.4	847.5	856.8	869.7	872.0	885.8	891.3	896.4	891.3
17.5°	828.2	844.3	878.4	891.3	897.3	904.2	921.7	926.8	935.1	931.9	941.1
20°	848.5	871.5	907.5	929.6	938.8	945.3	960.0	967.8	971.1	971.1	972.0
22.5°	866.4	899.6	926.4	951.7	960.0	964.6	973.4	979.4	980.7	981.7	982.6
25°	882.6	912.5	934.2	948.5	951.7	951.7	956.8	953.1	947.1	951.7	954.5
27.5°	882.6	903.8	913.5	918.5	918.5	906.1	898.7	883.5	870.6	866.9	875.2
30°	867.8	877.5	864.1	851.7	842.0	833.7	804.7	781.6	777.0	773.8	786.3
32.5°	833.7	821.3	795.0	759.1	744.8	725.9	703.3	685.8	675.2	671.5	668.7
35°	773.3	741.1	707.0	658.6	648.4	624.5	593.6	580.7	563.2	562.7	568.7
37.5°	707.4	657.7	620.8	574.7	560.4	535.1	506.0	492.7	480.7	471.5	482.5
40°	630.5	587.2	530.9	493.1	472.9	459.5	435.1	420.3	414.8	410.2	417.1
42.5°	558.6	511.1	467.3	428.6	412.0	396.8	380.7	366.4	362.2	361.8	366.9
45°	487.1	440.6	400.0	366.9	356.3	347.0	331.4	327.2	320.3	315.7	318.0
47.5°	430.0	382.1	348.4	323.1	313.9	306.0	295.9	289.0	283.0	281.1	283.9
50°	373.8	341.5	306.9	285.7	278.8	271.5	263.6	257.2	254.4	252.6	254.4
52.5°	328.6	294.0	270.5	253.5	246.6	241.0	235.5	232.7	229.1	230.0	231.8
55°	288.0	257.6	237.8	225.4	221.2	218.9	212.0	208.8	207.4	206.5	207.4
57.5°	249.8	227.7	212.9	202.3	196.8	195.4	189.9	189.9	188.5	187.1	187.6
60°	219.4	200.5	186.2	177.9	177.0	174.7	171.0	170.5	167.3	168.7	169.1
62.5°	188.5	173.3	163.6	158.5	155.3	154.4	152.1	151.6	150.2	150.7	149.8
65°	164.1	151.6	141.9	137.8	136.4	136.0	134.1	132.7	131.8	132.7	131.8
67.5°	139.6	131.3	124.0	119.8	118.0	117.5	116.1	115.2	115.7	114.3	115.2
70°	116.6	108.3	103.7	101.4	100.5	99.1	99.1	99.1	99.1	98.2	97.7
72.5°	98.2	89.9	86.6	85.3	84.3	83.9	82.5	83.0	82.5	82.0	83.9
75°	77.9	72.8	69.6	68.2	69.1	67.7	66.4	67.3	65.9	66.4	68.2
77.5°	59.0	56.7	54.8	53.9	53.0	52.1	52.1	51.2	51.2	51.2	51.2
80°	42.9	42.4	39.2	38.7	38.7	37.8	37.8	37.8	37.8	37.3	37.8
82.5°	28.6	28.1	27.2	26.7	25.8	26.3	26.3	25.3	25.3	24.9	25.3
85°	16.6	16.6	15.7	15.2	14.7	15.2	14.3	13.8	14.3	13.8	14.3
87.5°	7.8	6.9	7.4	6.9	6.0	6.5	5.5	6.0	5.5	5.1	6.0
90°	9.7	10.3	10.9	11.4	11.4	11.4	12.0	12.6	12.0	12.0	12.0
92.5°	186.3	137.7	102.9	81.2	74.1	66.9	58.3	54.3	52.0	52.0	52.0
95°	479.0	423.5	334.9	258.3	230.6	202.9	174.9	157.2	146.9	139.5	146.9
97.5°	600.7	609.8	565.8	503.0	471.0	439.0	400.1	365.8	348.6	334.9	348.6
100°	605.8	689.3	700.7	672.7	651.6	630.4	580.7	545.8	528.7	524.1	528.7
102.5°	563.0	685.3	753.3	770.5	764.8	759.0	733.3	710.4	692.2	688.7	692.2
105°	509.3	640.1	739.0	795.6	807.3	819.0	820.2	815.6	807.6	804.2	807.6
107.5°	465.2	584.7	691.6	770.5	794.5	818.5	843.6	853.9	858.5	859.0	858.5
110°	433.8	535.5	634.4	717.3	748.8	780.2	820.8	844.8	855.0	860.2	855.0

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	416.1	499.5	584.1	661.3	692.8	724.2	771.6	801.9	817.3	826.5	817.3
115°	406.4	477.8	548.1	615.0	642.4	669.9	715.0	749.3	767.6	772.2	767.6
117.5°	401.2	465.2	524.7	579.0	603.0	627.0	667.0	696.7	716.2	719.0	716.2
120°	397.2	457.2	510.4	556.1	576.4	596.7	629.3	654.4	669.3	675.6	669.3
122.5°	392.7	450.4	501.3	541.8	559.0	576.1	602.4	623.0	635.0	641.3	635.0
125°	387.5	442.4	491.5	531.0	546.7	562.4	585.3	601.8	612.7	616.1	612.7
127.5°	380.7	433.2	480.7	520.1	535.0	549.8	572.7	587.6	596.7	600.1	596.7
130°	374.4	421.8	467.0	505.8	521.0	536.1	559.6	573.8	583.0	586.4	583.0
132.5°	368.7	409.8	451.5	489.3	504.4	519.5	542.4	559.0	567.6	571.0	567.6
135°	362.9	398.9	436.1	471.0	485.2	499.5	522.4	538.4	547.5	551.0	547.5
137.5°	357.8	388.7	421.2	451.5	464.6	477.8	499.5	516.1	523.5	527.5	523.5
140°	353.8	380.1	406.9	432.7	444.7	456.7	476.7	489.3	497.3	501.8	497.3
142.5°	350.4	372.1	394.9	416.1	426.1	436.1	453.2	464.7	471.5	474.4	471.5
145°	346.4	364.7	384.1	401.2	409.2	417.2	431.5	441.2	447.0	449.8	447.0
147.5°	342.9	358.4	374.4	388.7	395.2	401.8	412.7	421.2	425.8	427.0	425.8
150°	338.9	352.6	365.8	377.2	382.4	387.5	396.7	404.1	407.5	408.1	407.5
152.5°	334.4	346.4	357.2	367.5	371.5	375.5	382.9	388.7	390.4	390.9	390.4
155°	329.8	340.1	349.2	357.8	361.2	364.7	370.4	374.9	376.7	376.7	376.7
157.5°	325.2	333.2	341.2	348.6	351.5	354.4	358.9	362.4	363.5	363.5	363.5
160°	320.1	326.9	333.2	339.5	341.8	344.1	347.5	350.9	351.5	351.5	351.5
162.5°	315.5	320.6	325.8	330.4	332.4	334.4	336.6	340.1	340.6	340.1	340.6
165°	310.4	314.9	318.4	322.4	323.8	325.2	327.5	329.8	329.2	328.6	329.2
167.5°	305.8	309.2	312.1	315.5	316.4	317.2	318.4	320.1	320.1	319.5	320.1
170°	301.2	304.1	305.8	308.1	309.0	309.8	310.9	311.5	310.9	310.9	310.9
172.5°	297.2	299.5	300.6	301.8	302.4	302.9	303.5	304.1	303.5	302.4	303.5
175°	294.4	295.5	296.1	297.2	297.2	297.2	297.2	298.4	297.2	296.1	297.2
177.5°	292.1	292.6	293.2	293.2	293.5	293.8	293.2	293.8	292.6	291.5	292.6
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	600.1	598.7	596.8	596.8	594.5	594.5	590.8	584.4	578.9	577.0	577.9
5°	651.2	651.7	648.9	646.6	642.5	639.2	633.2	621.7	618.0	610.7	605.6
7.5°	709.7	707.9	702.8	699.1	698.2	690.8	677.9	664.1	653.1	645.7	635.1
10°	775.7	768.3	760.9	758.6	753.1	740.6	725.9	710.7	695.5	679.3	661.4
12.5°	831.0	816.7	816.2	810.7	800.1	793.2	775.7	754.0	727.7	709.7	689.5
15°	890.4	877.0	866.0	855.8	850.8	830.5	815.7	788.6	757.2	737.9	724.0
17.5°	932.8	926.8	907.9	903.3	896.4	872.9	849.4	822.7	795.5	768.3	730.9
20°	966.9	963.2	950.8	944.3	933.3	914.8	886.3	855.4	824.0	785.3	750.3
22.5°	981.7	977.1	966.9	961.4	954.5	938.8	914.4	879.3	838.3	803.8	766.4
25°	952.6	960.9	958.2	955.9	953.1	943.9	925.4	894.6	854.5	815.3	768.7
27.5°	887.2	901.5	915.3	917.1	921.7	925.4	918.1	895.9	862.3	820.8	769.7
30°	799.2	805.6	833.7	842.0	848.5	872.0	885.8	880.3	854.5	817.1	770.1
32.5°	686.2	703.3	731.9	751.7	769.2	795.5	831.4	845.7	836.5	806.1	759.5
35°	579.3	599.6	632.8	658.1	675.6	713.0	755.4	786.3	797.8	782.6	741.1
37.5°	491.8	516.2	545.7	555.4	575.6	621.7	680.2	723.1	751.2	752.6	720.3
40°	425.8	438.3	461.8	476.5	496.4	535.1	592.2	648.9	691.3	705.6	688.5
42.5°	370.1	379.8	397.3	415.2	433.2	462.7	515.3	568.3	625.4	654.0	653.5
45°	325.8	336.0	348.0	362.7	375.2	407.0	448.4	502.8	552.1	596.4	607.4
47.5°	287.1	295.9	310.6	317.1	325.4	355.3	391.3	442.0	493.1	543.8	556.7
50°	258.6	265.9	276.1	280.2	289.4	311.6	341.0	382.1	438.8	485.3	509.3
52.5°	232.7	238.3	246.1	249.3	255.8	272.4	299.1	331.4	378.4	426.3	460.0
55°	210.6	214.3	219.8	223.5	228.1	242.9	262.7	291.7	332.3	373.8	406.5
57.5°	189.9	192.6	198.2	200.0	203.7	215.2	229.1	253.5	290.8	327.7	359.5
60°	170.5	172.4	175.6	179.7	182.5	190.3	203.2	223.5	253.5	287.1	312.9
62.5°	152.1	154.9	155.8	157.6	159.9	167.3	177.4	192.2	218.5	246.1	273.3
65°	133.2	135.5	137.3	137.8	140.1	145.6	154.9	167.8	184.8	208.8	234.1
67.5°	115.7	117.1	118.0	119.8	122.1	124.9	132.3	141.9	157.6	177.0	197.3
70°	99.5	99.5	100.9	101.4	104.2	107.4	110.6	119.8	133.7	149.3	163.1
72.5°	82.0	84.3	83.9	86.2	85.7	88.0	92.2	98.2	108.3	120.7	134.1
75°	66.8	68.2	68.2	68.2	69.1	71.0	73.3	78.8	86.6	96.8	104.6
77.5°	52.1	53.0	53.0	53.0	53.5	55.3	57.6	61.3	66.8	72.8	77.4
80°	37.3	38.3	38.3	39.2	39.2	39.6	41.9	43.8	46.5	51.2	55.8
82.5°	25.3	25.8	26.7	26.7	26.3	27.2	27.7	29.5	32.3	33.2	36.4
85°	13.8	14.3	14.7	14.7	15.2	16.1	15.7	17.5	17.5	19.4	20.3
87.5°	5.5	6.5	6.5	6.0	6.5	6.5	6.5	7.4	7.8	8.3	7.8
90°	12.6	12.0	11.4	11.4	11.4	10.9	10.3	9.7	10.3	9.1	8.0
92.5°	54.3	58.3	66.9	74.1	81.2	102.9	137.7	186.3	224.0	196.0	142.3
95°	157.2	174.9	202.9	230.6	258.3	334.9	423.5	479.0	465.8	351.5	214.9
97.5°	365.8	400.1	439.0	471.0	503.0	565.8	609.8	600.7	498.4	336.6	196.0
100°	545.8	580.7	630.4	651.6	672.7	700.7	689.3	605.8	459.5	298.4	181.8
102.5°	710.4	733.3	759.0	764.8	770.5	753.3	685.3	563.0	410.9	272.6	177.8
105°	815.6	820.2	819.0	807.3	795.6	739.0	640.1	509.3	374.9	260.1	180.0
107.5°	853.9	843.6	818.5	794.5	770.5	691.6	584.7	465.2	351.5	256.6	186.9
110°	844.8	820.8	780.2	748.8	717.3	634.4	535.5	433.8	340.6	257.8	194.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	801.9	771.6	724.2	692.8	661.3	584.1	499.5	416.1	335.5	261.2	203.5
115°	749.3	715.0	669.9	642.4	615.0	548.1	477.8	406.4	334.4	265.8	212.6
117.5°	696.7	667.0	627.0	603.0	579.0	524.7	465.2	401.2	333.8	270.3	221.8
120°	654.4	629.3	596.7	576.4	556.1	510.4	457.2	397.2	333.8	275.5	231.5
122.5°	623.0	602.4	576.1	559.0	541.8	501.3	450.4	392.7	333.2	280.6	240.6
125°	601.8	585.3	562.4	546.7	531.0	491.5	442.4	387.5	332.6	285.8	249.8
127.5°	587.6	572.7	549.8	535.0	520.1	480.7	433.2	380.7	331.5	289.8	257.8
130°	573.8	559.6	536.1	521.0	505.8	467.0	421.8	374.4	330.9	294.4	265.2
132.5°	559.0	542.4	519.5	504.4	489.3	451.5	409.8	368.7	330.4	298.4	272.6
135°	538.4	522.4	499.5	485.2	471.0	436.1	398.9	362.9	329.8	302.4	278.9
137.5°	516.1	499.5	477.8	464.6	451.5	421.2	388.7	357.8	329.8	304.6	283.5
140°	489.3	476.7	456.7	444.7	432.7	406.9	380.1	353.8	329.2	307.5	288.1
142.5°	464.7	453.2	436.1	426.1	416.1	394.9	372.1	350.4	329.2	309.8	291.5
145°	441.2	431.5	417.2	409.2	401.2	384.1	364.7	346.4	328.1	310.4	293.8
147.5°	421.2	412.7	401.8	395.2	388.7	374.4	358.4	342.9	326.4	310.9	296.1
150°	404.1	396.7	387.5	382.4	377.2	365.8	352.6	338.9	324.6	310.9	297.8
152.5°	388.7	382.9	375.5	371.5	367.5	357.2	346.4	334.4	321.8	309.8	298.9
155°	374.9	370.4	364.7	361.2	357.8	349.2	340.1	329.8	318.9	308.6	299.5
157.5°	362.4	358.9	354.4	351.5	348.6	341.2	333.2	325.2	316.1	307.5	299.5
160°	350.9	347.5	344.1	341.8	339.5	333.2	326.9	320.1	312.6	305.8	299.5
162.5°	340.1	336.6	334.4	332.4	330.4	325.8	320.6	315.5	309.2	304.1	299.5
165°	329.8	327.5	325.2	323.8	322.4	318.4	314.9	310.4	305.8	301.8	298.4
167.5°	320.1	318.4	317.2	316.4	315.5	312.1	309.2	305.8	302.4	299.5	297.2
170°	311.5	310.9	309.8	309.0	308.1	305.8	304.1	301.2	298.9	297.2	296.1
172.5°	304.1	303.5	302.9	302.4	301.8	300.6	299.5	297.2	295.5	294.9	294.9
175°	298.4	297.2	297.2	297.2	297.2	296.1	295.5	294.4	293.2	293.2	293.8
177.5°	293.8	293.2	293.8	293.5	293.2	293.2	292.6	292.1	291.5	291.5	292.6
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	573.8	571.9	570.6	570.6	566.4	562.3	560.0	559.0	558.1	554.4	549.4
5°	597.3	591.3	587.2	583.0	576.1	568.7	561.3	557.2	551.2	542.9	536.9
7.5°	623.6	609.3	604.7	599.6	585.8	573.3	563.2	554.4	544.8	534.2	523.6
10°	645.7	630.5	620.3	611.6	593.6	577.0	561.8	548.9	536.5	522.6	509.7
12.5°	666.9	645.2	634.6	621.7	602.8	578.9	559.0	542.9	524.5	510.2	494.5
15°	696.4	660.0	642.5	634.2	608.8	580.7	556.7	532.8	517.6	495.9	482.1
17.5°	701.0	671.5	660.0	638.8	608.4	576.6	548.9	524.9	501.9	482.5	464.6
20°	717.1	678.4	660.0	646.6	606.5	574.2	543.8	513.0	490.8	470.1	449.8
22.5°	727.3	683.5	664.1	642.9	604.7	566.0	530.0	503.3	476.1	454.9	438.8
25°	724.5	680.7	659.0	639.2	592.7	554.0	521.7	487.6	462.3	439.2	418.0
27.5°	723.1	673.8	650.8	628.6	584.8	544.3	503.7	476.1	448.0	421.2	405.6
30°	719.4	665.0	638.3	614.3	568.7	526.3	491.8	459.5	431.4	407.0	386.2
32.5°	707.0	650.3	624.5	598.7	551.2	508.8	473.8	443.8	415.7	390.4	370.5
35°	690.4	632.8	604.7	577.5	530.0	487.1	454.9	423.5	397.3	372.8	354.0
37.5°	673.8	612.5	586.2	554.9	511.1	466.4	433.2	405.1	380.7	355.3	334.6
40°	649.8	588.5	559.5	532.8	481.6	439.7	409.3	383.9	359.9	336.0	318.5
42.5°	617.1	562.3	532.3	502.8	454.9	413.4	383.9	361.3	338.7	318.9	299.6
45°	583.9	530.5	503.7	477.5	425.4	386.2	359.0	338.3	319.4	297.7	282.1
47.5°	543.8	498.7	471.9	446.1	396.8	357.6	332.8	313.4	295.9	277.9	263.2
50°	502.8	463.6	439.2	412.5	365.5	330.0	305.6	289.4	275.1	258.1	246.1
52.5°	458.6	424.5	403.7	377.9	336.4	303.7	278.8	262.7	250.7	238.3	227.7
55°	411.6	386.7	364.6	343.8	304.6	275.1	253.0	238.7	230.4	218.9	209.7
57.5°	369.2	345.2	331.8	308.3	274.2	245.2	227.7	215.7	206.0	199.1	191.7
60°	324.9	305.6	290.8	273.8	243.8	219.4	200.9	194.0	183.9	178.8	175.6
62.5°	282.5	268.7	254.9	242.0	215.2	192.2	178.4	169.6	163.6	158.5	155.8
65°	242.4	229.5	219.8	208.3	186.2	167.8	154.9	147.9	141.9	140.6	137.3
67.5°	203.2	197.7	187.1	177.9	159.0	144.7	135.0	126.3	123.1	121.7	118.9
70°	170.1	163.6	155.3	147.5	133.2	120.7	112.0	108.8	104.2	103.7	100.5
72.5°	140.1	132.3	126.3	120.3	109.7	98.6	94.0	89.4	87.1	85.3	83.9
75°	111.1	105.5	101.4	96.3	87.1	79.7	73.3	71.4	70.1	69.6	68.7
77.5°	83.0	79.3	77.4	72.4	65.9	59.5	56.7	53.9	53.9	53.0	53.5
80°	59.0	56.7	54.4	51.6	46.1	43.3	41.0	39.2	38.3	37.8	38.3
82.5°	37.3	35.9	35.5	33.6	30.0	28.6	26.7	25.3	25.3	25.3	25.3
85°	20.7	20.7	20.7	18.0	16.6	15.2	14.3	13.8	13.8	13.8	14.3
87.5°	8.8	8.8	7.4	7.4	6.9	6.0	5.5	5.5	6.0	6.0	6.5
90°	8.0	4.6	4.6	4.6	4.0	3.4	1.7	0.6	1.7	3.4	4.0
92.5°	86.9	51.4	44.0	36.6	26.3	17.7	11.4	8.0	11.4	17.7	26.3
95°	121.2	71.4	59.4	47.4	33.7	26.3	20.6	18.9	20.6	26.3	33.7
97.5°	115.5	76.0	65.7	55.4	43.4	36.6	31.4	31.4	31.4	36.6	43.4
100°	117.2	83.4	74.3	65.2	54.3	47.4	43.4	43.4	43.4	47.4	54.3
102.5°	122.9	93.2	84.6	76.0	65.7	59.4	56.0	54.9	56.0	59.4	65.7
105°	132.6	105.2	96.9	88.6	78.3	71.4	68.6	66.9	68.6	71.4	78.3
107.5°	142.9	117.7	109.4	101.2	91.4	84.0	81.2	80.0	81.2	84.0	91.4
110°	154.9	129.7	122.0	114.3	104.0	97.2	94.3	93.2	94.3	97.2	104.0

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	166.3	142.3	134.6	126.9	116.6	110.3	106.9	105.7	106.9	110.3	116.6
115°	178.3	155.5	147.8	140.0	129.2	123.5	119.5	117.7	119.5	123.5	129.2
117.5°	189.8	168.0	160.0	152.0	141.7	135.5	132.0	130.3	132.0	135.5	141.7
120°	201.8	180.0	172.0	164.0	154.3	148.0	144.0	142.9	144.0	148.0	154.3
122.5°	213.2	191.5	183.8	176.0	165.2	159.5	155.5	154.3	155.5	159.5	165.2
125°	223.5	202.9	194.9	186.9	176.0	169.8	166.3	164.0	166.3	169.8	176.0
127.5°	233.2	213.2	205.2	197.2	185.8	178.9	174.9	173.2	174.9	178.9	185.8
130°	242.9	223.5	215.2	206.9	196.0	187.5	182.9	180.6	182.9	187.5	196.0
132.5°	250.9	231.5	223.8	216.0	204.0	196.0	189.8	188.0	189.8	196.0	204.0
135°	258.3	239.5	232.0	224.6	212.6	202.9	197.2	194.9	197.2	202.9	212.6
137.5°	264.1	246.3	239.2	232.1	219.5	210.3	204.0	201.8	204.0	210.3	219.5
140°	269.8	252.6	245.8	238.9	226.9	217.2	210.9	209.2	210.9	217.2	226.9
142.5°	274.9	258.3	251.8	245.2	233.8	224.6	218.9	217.2	218.9	224.6	233.8
145°	278.3	263.5	257.2	250.9	240.1	232.1	226.3	224.6	226.3	232.1	240.1
147.5°	282.3	268.1	262.4	256.6	247.5	238.9	233.8	233.2	233.8	238.9	247.5
150°	285.2	272.6	267.2	261.8	253.2	246.3	241.8	241.2	241.8	246.3	253.2
152.5°	287.5	276.6	271.8	266.9	259.5	253.2	248.6	248.6	248.6	253.2	259.5
155°	289.8	280.1	275.8	271.5	265.2	259.5	256.1	255.5	256.1	259.5	265.2
157.5°	291.5	282.9	279.5	276.1	270.3	265.8	262.3	262.3	262.3	265.8	270.3
160°	292.6	285.8	282.6	279.5	274.9	270.9	268.6	268.6	268.6	270.9	274.9
162.5°	293.8	287.5	285.2	282.9	278.9	275.5	273.8	274.3	273.8	275.5	278.9
165°	293.8	288.6	286.9	285.2	282.3	279.5	278.3	278.3	278.3	279.5	282.3
167.5°	293.8	289.8	288.4	286.9	285.2	282.9	282.3	282.9	282.3	282.9	285.2
170°	293.2	290.4	289.5	288.6	287.5	285.8	285.2	285.8	285.2	285.8	287.5
172.5°	292.6	290.9	290.4	289.8	289.2	288.1	288.1	288.6	288.1	288.1	289.2
175°	292.1	290.9	290.9	290.9	290.4	289.8	289.8	290.4	289.8	289.8	290.4
177.5°	291.5	290.9	290.9	290.9	290.9	290.4	290.9	291.5	290.9	290.4	290.9
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	548.0	546.1	547.1	542.4	538.3	532.3	527.2	526.3	525.4	528.2	526.3
5°	532.3	530.0	527.7	522.2	513.9	508.8	501.4	501.0	498.2	494.1	495.0
7.5°	515.3	513.9	510.6	501.9	494.5	485.8	479.8	474.7	472.4	468.7	467.3
10°	501.4	496.4	493.6	483.9	475.2	465.9	458.1	454.4	450.3	447.0	444.7
12.5°	482.5	481.2	473.3	465.5	458.1	447.5	441.5	430.9	425.4	428.2	427.2
15°	470.1	463.6	461.8	450.7	438.3	431.4	420.3	413.4	411.1	407.0	401.9
17.5°	453.5	449.4	442.9	432.8	418.5	408.8	401.0	394.5	391.7	386.2	382.1
20°	437.8	430.9	425.8	416.6	402.8	390.4	380.7	376.5	369.6	365.0	362.7
22.5°	423.5	418.5	411.1	397.3	385.3	373.3	361.8	355.8	349.3	346.6	342.9
25°	406.0	397.7	392.7	377.5	364.6	354.9	344.3	336.4	332.8	328.1	327.2
27.5°	389.0	381.1	375.2	361.8	346.1	333.7	327.2	321.7	315.2	315.2	312.9
30°	371.9	366.4	357.2	344.3	329.5	317.5	310.2	305.1	302.8	301.0	300.5
32.5°	354.9	347.5	342.0	324.5	313.4	302.3	296.8	292.7	289.9	289.4	289.9
35°	337.4	329.1	323.5	307.9	296.8	286.7	284.4	280.7	279.3	278.8	281.1
37.5°	318.9	312.5	305.6	292.7	280.2	274.2	269.6	268.2	267.8	270.5	271.5
40°	301.9	296.3	289.9	276.1	266.8	260.4	258.1	256.7	258.6	261.3	262.7
42.5°	285.7	277.9	272.8	260.4	252.1	248.4	245.6	245.6	247.5	250.7	253.0
45°	268.7	262.7	257.6	246.6	239.2	235.0	234.6	235.0	237.4	239.7	242.4
47.5°	252.1	246.1	240.6	231.4	224.9	222.6	222.1	222.6	226.3	229.5	232.7
50°	236.9	230.4	225.4	216.6	211.5	208.8	209.2	211.5	214.3	218.9	223.1
52.5°	218.9	214.3	209.7	201.9	197.3	195.4	196.8	198.6	203.7	206.9	212.0
55°	201.4	197.3	193.6	187.6	183.9	182.5	183.4	186.2	190.3	195.9	201.9
57.5°	185.3	180.7	177.0	172.8	168.7	169.1	169.6	173.3	178.4	183.4	190.3
60°	167.3	164.5	161.3	156.2	154.4	154.4	155.8	159.9	164.5	172.8	178.8
62.5°	151.2	147.5	145.2	141.9	139.2	139.6	142.9	146.6	152.1	159.0	166.8
65°	134.6	130.4	128.6	125.8	124.9	125.4	127.7	133.2	139.2	145.2	152.5
67.5°	116.1	114.8	112.9	110.1	111.1	111.5	113.8	118.4	124.9	130.9	139.2
70°	100.5	97.7	97.2	94.9	94.9	96.3	100.9	104.2	110.1	116.6	125.4
72.5°	83.9	81.6	81.6	79.7	81.1	82.5	84.8	89.4	94.9	101.4	108.8
75°	66.8	65.9	66.8	65.9	65.9	68.2	71.0	74.7	80.7	87.6	93.6
77.5°	51.6	51.6	51.2	52.5	52.5	53.9	57.6	61.3	65.9	71.4	77.9
80°	37.8	37.8	37.8	39.2	40.6	40.6	42.9	47.5	51.6	55.3	61.3
82.5°	25.8	25.8	25.8	26.7	28.6	28.6	31.3	34.1	38.7	41.9	44.7
85°	15.7	15.7	15.2	16.1	16.6	18.0	20.3	22.1	24.4	27.2	30.0
87.5°	6.9	6.9	7.4	7.8	8.3	9.2	10.1	11.1	13.4	14.3	15.7
90°	4.6	4.6	4.6	8.0	8.0	9.1	10.3	9.7	10.3	10.9	11.4
92.5°	36.6	44.0	51.4	86.9	142.3	196.0	224.0	186.3	137.7	102.9	81.2
95°	47.4	59.4	71.4	121.2	214.9	351.5	465.8	479.0	423.5	334.9	258.3
97.5°	55.4	65.7	76.0	115.5	196.0	336.6	498.4	600.7	609.8	565.8	503.0
100°	65.2	74.3	83.4	117.2	181.8	298.4	459.5	605.8	689.3	700.7	672.7
102.5°	76.0	84.6	93.2	122.9	177.8	272.6	410.9	563.0	685.3	753.3	770.5
105°	88.6	96.9	105.2	132.6	180.0	260.1	374.9	509.3	640.1	739.0	795.6
107.5°	101.2	109.4	117.7	142.9	186.9	256.6	351.5	465.2	584.7	691.6	770.5
110°	114.3	122.0	129.7	154.9	194.9	257.8	340.6	433.8	535.5	634.4	717.3

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	126.9	134.6	142.3	166.3	203.5	261.2	335.5	416.1	499.5	584.1	661.3
115°	140.0	147.8	155.5	178.3	212.6	265.8	334.4	406.4	477.8	548.1	615.0
117.5°	152.0	160.0	168.0	189.8	221.8	270.3	333.8	401.2	465.2	524.7	579.0
120°	164.0	172.0	180.0	201.8	231.5	275.5	333.8	397.2	457.2	510.4	556.1
122.5°	176.0	183.8	191.5	213.2	240.6	280.6	333.2	392.7	450.4	501.3	541.8
125°	186.9	194.9	202.9	223.5	249.8	285.8	332.6	387.5	442.4	491.5	531.0
127.5°	197.2	205.2	213.2	233.2	257.8	289.8	331.5	380.7	433.2	480.7	520.1
130°	206.9	215.2	223.5	242.9	265.2	294.4	330.9	374.4	421.8	467.0	505.8
132.5°	216.0	223.8	231.5	250.9	272.6	298.4	330.4	368.7	409.8	451.5	489.3
135°	224.6	232.0	239.5	258.3	278.9	302.4	329.8	362.9	398.9	436.1	471.0
137.5°	232.1	239.2	246.3	264.1	283.5	304.6	329.8	357.8	388.7	421.2	451.5
140°	238.9	245.8	252.6	269.8	288.1	307.5	329.2	353.8	380.1	406.9	432.7
142.5°	245.2	251.8	258.3	274.9	291.5	309.8	329.2	350.4	372.1	394.9	416.1
145°	250.9	257.2	263.5	278.3	293.8	310.4	328.1	346.4	364.7	384.1	401.2
147.5°	256.6	262.4	268.1	282.3	296.1	310.9	326.4	342.9	358.4	374.4	388.7
150°	261.8	267.2	272.6	285.2	297.8	310.9	324.6	338.9	352.6	365.8	377.2
152.5°	266.9	271.8	276.6	287.5	298.9	309.8	321.8	334.4	346.4	357.2	367.5
155°	271.5	275.8	280.1	289.8	299.5	308.6	318.9	329.8	340.1	349.2	357.8
157.5°	276.1	279.5	282.9	291.5	299.5	307.5	316.1	325.2	333.2	341.2	348.6
160°	279.5	282.6	285.8	292.6	299.5	305.8	312.6	320.1	326.9	333.2	339.5
162.5°	282.9	285.2	287.5	293.8	299.5	304.1	309.2	315.5	320.6	325.8	330.4
165°	285.2	286.9	288.6	293.8	298.4	301.8	305.8	310.4	314.9	318.4	322.4
167.5°	286.9	288.4	289.8	293.8	297.2	299.5	302.4	305.8	309.2	312.1	315.5
170°	288.6	289.5	290.4	293.2	296.1	297.2	298.9	301.2	304.1	305.8	308.1
172.5°	289.8	290.4	290.9	292.6	294.9	294.9	295.5	297.2	299.5	300.6	301.8
175°	290.9	290.9	290.9	292.1	293.8	293.2	293.2	294.4	295.5	296.1	297.2
177.5°	290.9	290.9	290.9	291.5	292.6	291.5	291.5	292.1	292.6	293.2	293.2
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	524.9	524.5	522.2	523.1	520.3	521.2	522.6	523.1	524.9	523.6	523.1
5°	492.7	491.8	490.4	489.0	488.5	490.4	487.1	488.1	489.0	490.4	492.2
7.5°	466.4	465.9	464.6	462.3	461.3	460.4	460.9	464.1	463.6	463.2	466.4
10°	442.4	442.9	440.1	439.7	436.9	436.4	436.9	437.8	439.2	441.1	441.5
12.5°	417.6	423.5	418.5	416.6	412.5	414.8	415.7	411.6	413.9	415.2	422.2
15°	401.9	399.1	395.9	395.9	394.0	393.1	390.8	394.0	395.9	398.7	397.7
17.5°	380.2	375.6	373.8	371.9	372.4	374.2	369.2	376.5	376.5	377.9	375.6
20°	361.3	357.6	355.3	354.4	353.0	352.1	351.6	353.5	356.3	357.2	359.5
22.5°	341.5	341.5	337.8	336.4	335.5	334.1	336.4	335.1	336.9	338.7	342.4
25°	324.9	324.9	323.5	321.7	320.3	319.4	320.8	320.3	321.7	324.0	324.9
27.5°	311.6	310.2	309.7	309.2	308.8	309.2	308.8	310.2	311.6	312.0	311.1
30°	300.0	298.6	299.1	299.1	299.6	299.1	298.6	300.0	300.5	299.6	300.0
32.5°	289.4	289.4	290.4	290.8	290.8	291.3	291.7	290.8	291.3	289.9	290.4
35°	280.7	281.6	282.5	283.0	283.4	283.0	283.9	283.4	282.5	281.6	281.1
37.5°	271.9	272.8	274.7	275.1	276.5	277.0	276.1	276.1	275.6	273.8	272.8
40°	262.7	263.6	265.9	267.3	268.2	269.6	268.7	268.7	266.8	265.0	263.6
42.5°	253.9	255.8	258.1	259.5	261.3	261.3	261.3	260.4	258.1	256.2	254.9
45°	245.2	245.6	248.9	251.2	253.0	253.0	253.0	251.6	250.3	246.6	244.7
47.5°	235.5	236.9	240.6	242.9	244.7	245.2	245.2	243.8	241.0	237.8	235.5
50°	224.9	227.2	231.4	234.6	236.9	237.8	236.4	235.5	232.3	228.6	225.8
52.5°	214.8	217.5	222.6	225.4	228.6	229.1	228.6	227.2	223.5	218.5	216.1
55°	204.6	206.9	212.5	217.1	219.8	220.8	219.8	217.5	212.9	207.9	205.5
57.5°	193.6	196.8	202.8	207.4	210.6	211.1	210.2	207.9	204.2	197.7	194.5
60°	182.0	186.2	192.2	196.8	200.9	201.4	200.5	197.3	192.6	186.2	183.4
62.5°	170.5	173.7	180.7	185.7	189.0	191.3	189.4	186.2	181.6	175.1	171.0
65°	157.2	161.8	167.8	172.4	176.1	176.5	175.6	172.8	167.8	160.8	157.6
67.5°	144.3	147.5	153.5	159.5	160.8	162.2	160.8	158.1	153.9	147.9	143.3
70°	128.6	131.3	138.7	142.9	144.7	146.1	145.2	142.4	138.7	133.2	129.5
72.5°	112.9	115.2	122.1	125.4	129.0	128.6	128.1	126.3	121.2	117.5	115.2
75°	96.3	99.1	103.7	107.8	109.2	109.2	109.2	107.8	104.6	98.6	96.3
77.5°	81.1	82.5	86.2	88.5	89.9	90.3	89.9	87.6	85.7	81.6	80.2
80°	62.2	65.9	68.7	69.1	71.0	71.0	71.0	70.1	68.2	64.1	63.6
82.5°	47.0	47.9	50.7	52.1	53.0	52.5	52.5	50.7	50.2	47.9	47.0
85°	31.8	33.2	32.7	34.6	35.0	34.1	34.1	35.0	32.7	33.2	31.8
87.5°	17.5	17.5	18.4	18.0	19.8	19.8	18.9	19.4	18.4	18.0	17.5
90°	11.4	11.4	12.0	12.6	12.0	12.0	12.0	12.6	12.0	11.4	11.4
92.5°	74.1	66.9	58.3	54.3	52.0	52.0	52.0	54.3	58.3	66.9	74.1
95°	230.6	202.9	174.9	157.2	146.9	139.5	146.9	157.2	174.9	202.9	230.6
97.5°	471.0	439.0	400.1	365.8	348.6	334.9	348.6	365.8	400.1	439.0	471.0
100°	651.6	630.4	580.7	545.8	528.7	524.1	528.7	545.8	580.7	630.4	651.6
102.5°	764.8	759.0	733.3	710.4	692.2	688.7	692.2	710.4	733.3	759.0	764.8
105°	807.3	819.0	820.2	815.6	807.6	804.2	807.6	815.6	820.2	819.0	807.3
107.5°	794.5	818.5	843.6	853.9	858.5	859.0	858.5	853.9	843.6	818.5	794.5
110°	748.8	780.2	820.8	844.8	855.0	860.2	855.0	844.8	820.8	780.2	748.8

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	692.8	724.2	771.6	801.9	817.3	826.5	817.3	801.9	771.6	724.2	692.8
115°	642.4	669.9	715.0	749.3	767.6	772.2	767.6	749.3	715.0	669.9	642.4
117.5°	603.0	627.0	667.0	696.7	716.2	719.0	716.2	696.7	667.0	627.0	603.0
120°	576.4	596.7	629.3	654.4	669.3	675.6	669.3	654.4	629.3	596.7	576.4
122.5°	559.0	576.1	602.4	623.0	635.0	641.3	635.0	623.0	602.4	576.1	559.0
125°	546.7	562.4	585.3	601.8	612.7	616.1	612.7	601.8	585.3	562.4	546.7
127.5°	535.0	549.8	572.7	587.6	596.7	600.1	596.7	587.6	572.7	549.8	535.0
130°	521.0	536.1	559.6	573.8	583.0	586.4	583.0	573.8	559.6	536.1	521.0
132.5°	504.4	519.5	542.4	559.0	567.6	571.0	567.6	559.0	542.4	519.5	504.4
135°	485.2	499.5	522.4	538.4	547.5	551.0	547.5	538.4	522.4	499.5	485.2
137.5°	464.6	477.8	499.5	516.1	523.5	527.5	523.5	516.1	499.5	477.8	464.6
140°	444.7	456.7	476.7	489.3	497.3	501.8	497.3	489.3	476.7	456.7	444.7
142.5°	426.1	436.1	453.2	464.7	471.5	474.4	471.5	464.7	453.2	436.1	426.1
145°	409.2	417.2	431.5	441.2	447.0	449.8	447.0	441.2	431.5	417.2	409.2
147.5°	395.2	401.8	412.7	421.2	425.8	427.0	425.8	421.2	412.7	401.8	395.2
150°	382.4	387.5	396.7	404.1	407.5	408.1	407.5	404.1	396.7	387.5	382.4
152.5°	371.5	375.5	382.9	388.7	390.4	390.9	390.4	388.7	382.9	375.5	371.5
155°	361.2	364.7	370.4	374.9	376.7	376.7	376.7	374.9	370.4	364.7	361.2
157.5°	351.5	354.4	358.9	362.4	363.5	363.5	363.5	362.4	358.9	354.4	351.5
160°	341.8	344.1	347.5	350.9	351.5	351.5	351.5	350.9	347.5	344.1	341.8
162.5°	332.4	334.4	336.6	340.1	340.6	340.1	340.6	340.1	336.6	334.4	332.4
165°	323.8	325.2	327.5	329.8	329.2	328.6	329.2	329.8	327.5	325.2	323.8
167.5°	316.4	317.2	318.4	320.1	320.1	319.5	320.1	320.1	318.4	317.2	316.4
170°	309.0	309.8	310.9	311.5	310.9	310.9	310.9	311.5	310.9	309.8	309.0
172.5°	302.4	302.9	303.5	304.1	303.5	302.4	303.5	304.1	303.5	302.9	302.4
175°	297.2	297.2	297.2	298.4	297.2	296.1	297.2	298.4	297.2	297.2	297.2
177.5°	293.5	293.8	293.2	293.8	292.6	291.5	292.6	293.8	293.2	293.8	293.5
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	523.1	525.9	523.1	524.9	525.9	528.2	529.1	533.2	534.6	537.8	537.8
5°	491.8	493.1	493.6	495.4	497.3	501.9	505.1	511.1	518.0	518.9	523.1
7.5°	466.4	468.7	472.4	471.0	474.2	481.2	485.3	492.7	499.6	503.3	508.3
10°	443.8	446.6	448.0	449.4	455.3	461.3	467.8	472.9	482.1	487.6	491.8
12.5°	425.4	423.1	425.8	430.9	437.8	441.5	450.3	458.1	465.0	471.0	474.7
15°	401.4	403.3	406.0	414.8	416.6	425.8	429.1	437.8	450.7	456.3	460.9
17.5°	378.4	384.4	389.9	393.1	398.7	406.0	415.2	424.9	433.2	439.7	445.2
20°	359.9	365.9	369.2	371.5	377.0	387.1	395.9	407.9	418.5	423.5	430.9
22.5°	345.2	345.2	349.8	356.7	359.9	369.6	377.0	389.9	401.4	407.9	414.8
25°	326.8	329.5	333.2	339.2	343.8	351.6	362.2	373.3	385.8	391.3	400.0
27.5°	311.6	314.8	319.8	321.2	325.8	332.8	343.8	355.8	368.7	374.7	382.1
30°	300.0	301.9	303.7	306.5	310.6	316.6	325.8	336.4	352.1	356.7	365.9
32.5°	289.9	290.8	291.7	294.0	296.3	302.3	309.7	321.2	334.1	341.0	349.3
35°	280.7	279.8	280.2	281.6	283.9	286.2	294.0	303.7	315.7	324.0	330.4
37.5°	271.9	270.1	269.6	269.6	270.5	273.3	279.3	287.6	300.5	307.4	313.9
40°	262.2	260.4	259.5	259.0	258.6	260.4	265.0	273.3	283.4	289.9	297.3
42.5°	253.0	251.2	248.9	248.4	247.5	248.4	251.6	259.5	268.2	274.7	280.7
45°	243.8	240.6	237.8	236.0	236.4	235.0	237.4	243.3	253.5	257.6	263.6
47.5°	233.7	230.0	226.3	224.4	222.6	223.5	224.4	229.5	238.3	242.4	248.4
50°	224.0	218.9	214.8	212.5	211.1	210.2	211.1	216.1	222.6	226.3	231.4
52.5°	212.9	207.9	203.7	200.0	198.2	196.8	197.3	201.9	207.9	211.5	216.6
55°	202.8	196.3	190.8	186.2	184.8	184.3	183.9	187.1	192.2	195.9	200.0
57.5°	191.3	184.8	178.8	173.3	170.5	170.1	170.1	171.0	177.4	180.2	182.5
60°	179.7	172.8	166.4	161.3	157.2	155.8	155.3	157.2	160.4	163.1	166.4
62.5°	166.8	159.9	152.1	147.5	143.3	139.6	141.0	141.5	146.1	147.5	150.2
65°	154.4	146.6	140.1	132.7	128.1	125.8	124.9	125.8	129.5	130.0	131.8
67.5°	140.1	132.7	124.9	119.8	115.7	111.5	110.6	110.6	112.5	113.8	116.1
70°	126.3	118.9	110.1	104.6	100.5	96.8	95.4	94.9	96.3	97.2	99.5
72.5°	110.1	102.8	96.3	90.3	85.3	82.5	81.1	80.2	81.6	82.5	83.0
75°	93.1	87.1	80.7	74.7	71.4	68.7	66.8	65.4	66.4	66.4	66.4
77.5°	77.0	71.0	65.9	61.8	57.6	54.4	53.0	51.6	52.1	52.1	53.0
80°	59.9	55.8	51.6	47.9	44.2	41.5	40.6	39.2	38.3	37.8	37.8
82.5°	44.2	41.0	37.3	34.1	32.3	29.5	28.6	26.7	26.7	26.3	26.3
85°	29.5	27.7	24.0	21.7	20.3	18.9	18.0	17.1	15.7	15.7	15.2
87.5°	15.7	14.7	13.8	11.1	11.1	9.7	9.2	8.8	7.4	7.8	7.8
90°	11.4	10.9	10.3	9.7	10.3	9.1	8.0	8.0	4.6	4.6	4.6
92.5°	81.2	102.9	137.7	186.3	224.0	196.0	142.3	86.9	51.4	44.0	36.6
95°	258.3	334.9	423.5	479.0	465.8	351.5	214.9	121.2	71.4	59.4	47.4
97.5°	503.0	565.8	609.8	600.7	498.4	336.6	196.0	115.5	76.0	65.7	55.4
100°	672.7	700.7	689.3	605.8	459.5	298.4	181.8	117.2	83.4	74.3	65.2
102.5°	770.5	753.3	685.3	563.0	410.9	272.6	177.8	122.9	93.2	84.6	76.0
105°	795.6	739.0	640.1	509.3	374.9	260.1	180.0	132.6	105.2	96.9	88.6
107.5°	770.5	691.6	584.7	465.2	351.5	256.6	186.9	142.9	117.7	109.4	101.2
110°	717.3	634.4	535.5	433.8	340.6	257.8	194.9	154.9	129.7	122.0	114.3

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	661.3	584.1	499.5	416.1	335.5	261.2	203.5	166.3	142.3	134.6	126.9
115°	615.0	548.1	477.8	406.4	334.4	265.8	212.6	178.3	155.5	147.8	140.0
117.5°	579.0	524.7	465.2	401.2	333.8	270.3	221.8	189.8	168.0	160.0	152.0
120°	556.1	510.4	457.2	397.2	333.8	275.5	231.5	201.8	180.0	172.0	164.0
122.5°	541.8	501.3	450.4	392.7	333.2	280.6	240.6	213.2	191.5	183.8	176.0
125°	531.0	491.5	442.4	387.5	332.6	285.8	249.8	223.5	202.9	194.9	186.9
127.5°	520.1	480.7	433.2	380.7	331.5	289.8	257.8	233.2	213.2	205.2	197.2
130°	505.8	467.0	421.8	374.4	330.9	294.4	265.2	242.9	223.5	215.2	206.9
132.5°	489.3	451.5	409.8	368.7	330.4	298.4	272.6	250.9	231.5	223.8	216.0
135°	471.0	436.1	398.9	362.9	329.8	302.4	278.9	258.3	239.5	232.0	224.6
137.5°	451.5	421.2	388.7	357.8	329.8	304.6	283.5	264.1	246.3	239.2	232.1
140°	432.7	406.9	380.1	353.8	329.2	307.5	288.1	269.8	252.6	245.8	238.9
142.5°	416.1	394.9	372.1	350.4	329.2	309.8	291.5	274.9	258.3	251.8	245.2
145°	401.2	384.1	364.7	346.4	328.1	310.4	293.8	278.3	263.5	257.2	250.9
147.5°	388.7	374.4	358.4	342.9	326.4	310.9	296.1	282.3	268.1	262.4	256.6
150°	377.2	365.8	352.6	338.9	324.6	310.9	297.8	285.2	272.6	267.2	261.8
152.5°	367.5	357.2	346.4	334.4	321.8	309.8	298.9	287.5	276.6	271.8	266.9
155°	357.8	349.2	340.1	329.8	318.9	308.6	299.5	289.8	280.1	275.8	271.5
157.5°	348.6	341.2	333.2	325.2	316.1	307.5	299.5	291.5	282.9	279.5	276.1
160°	339.5	333.2	326.9	320.1	312.6	305.8	299.5	292.6	285.8	282.6	279.5
162.5°	330.4	325.8	320.6	315.5	309.2	304.1	299.5	293.8	287.5	285.2	282.9
165°	322.4	318.4	314.9	310.4	305.8	301.8	298.4	293.8	288.6	286.9	285.2
167.5°	315.5	312.1	309.2	305.8	302.4	299.5	297.2	293.8	289.8	288.4	286.9
170°	308.1	305.8	304.1	301.2	298.9	297.2	296.1	293.2	290.4	289.5	288.6
172.5°	301.8	300.6	299.5	297.2	295.5	294.9	294.9	292.6	290.9	290.4	289.8
175°	297.2	296.1	295.5	294.4	293.2	293.2	293.8	292.1	290.9	290.9	290.9
177.5°	293.2	293.2	292.6	292.1	291.5	291.5	292.6	291.5	290.9	290.9	290.9
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	556.3	556.3	556.3	556.3
2.5°	541.1	545.7	549.8	556.3
5°	529.1	535.5	544.3	554.0
7.5°	515.3	525.4	536.9	550.3
10°	502.4	513.9	528.6	544.8
12.5°	489.0	502.8	518.9	536.5
15°	473.8	487.6	505.6	529.1
17.5°	460.0	476.5	495.9	520.8
20°	443.8	459.5	480.7	509.3
22.5°	429.5	447.5	471.0	495.9
25°	413.9	429.5	453.0	483.0
27.5°	398.2	417.6	440.1	469.2
30°	383.0	399.1	423.5	454.0
32.5°	366.4	385.8	408.3	436.9
35°	348.4	366.9	388.1	418.9
37.5°	332.3	350.3	371.9	399.1
40°	314.3	333.2	353.0	380.2
42.5°	296.8	313.9	333.7	358.6
45°	279.8	294.5	312.5	334.1
47.5°	262.2	274.7	291.3	310.6
50°	243.3	256.7	269.2	285.3
52.5°	225.8	237.4	247.5	260.9
55°	208.8	216.6	224.9	235.0
57.5°	190.8	196.8	202.8	213.4
60°	172.8	178.4	181.6	188.5
62.5°	155.3	157.6	161.8	165.9
65°	136.0	139.2	141.5	146.6
67.5°	118.4	119.8	122.1	125.4
70°	100.0	103.2	104.2	106.5
72.5°	84.3	85.7	86.6	87.1
75°	66.8	68.2	69.1	71.9
77.5°	52.5	52.1	53.9	54.4
80°	38.7	37.3	37.8	39.6
82.5°	25.3	25.8	25.3	25.3
85°	15.7	15.2	14.3	14.7
87.5°	6.9	6.9	6.5	6.5
90°	4.0	3.4	1.7	0.6
92.5°	26.3	17.7	11.4	8.0
95°	33.7	26.3	20.6	18.9
97.5°	43.4	36.6	31.4	31.4
100°	54.3	47.4	43.4	43.4
102.5°	65.7	59.4	56.0	54.9
105°	78.3	71.4	68.6	66.9
107.5°	91.4	84.0	81.2	80.0
110°	104.0	97.2	94.3	93.2



TEST NUMBER: P1001306

CATALOG NUMBER: SA4XXDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	116.6	110.3	106.9	105.7
115°	129.2	123.5	119.5	117.7
117.5°	141.7	135.5	132.0	130.3
120°	154.3	148.0	144.0	142.9
122.5°	165.2	159.5	155.5	154.3
125°	176.0	169.8	166.3	164.0
127.5°	185.8	178.9	174.9	173.2
130°	196.0	187.5	182.9	180.6
132.5°	204.0	196.0	189.8	188.0
135°	212.6	202.9	197.2	194.9
137.5°	219.5	210.3	204.0	201.8
140°	226.9	217.2	210.9	209.2
142.5°	233.8	224.6	218.9	217.2
145°	240.1	232.1	226.3	224.6
147.5°	247.5	238.9	233.8	233.2
150°	253.2	246.3	241.8	241.2
152.5°	259.5	253.2	248.6	248.6
155°	265.2	259.5	256.1	255.5
157.5°	270.3	265.8	262.3	262.3
160°	274.9	270.9	268.6	268.6
162.5°	278.9	275.5	273.8	274.3
165°	282.3	279.5	278.3	278.3
167.5°	285.2	282.9	282.3	282.9
170°	287.5	285.8	285.2	285.8
172.5°	289.2	288.1	288.1	288.6
175°	290.4	289.8	289.8	290.4
177.5°	290.9	290.4	290.9	291.5
180°	290.9	290.9	290.9	290.9

(END OF REPORT)