

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001342

Luminaire Tested: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001342
REPORT IS A COMBINATION OF REPORTS P995961 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4329.0 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	62	54	48	65	56	50	44	46	41	37	36	32	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	18	16
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	14	13
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4495	4495	4495	4495
5°	4483	5156	4509	3875
10°	4450	6016	4484	3400
15°	4397	6935	4427	3041
20°	4339	7520	4371	2727
25°	4257	7434	4297	2495
30°	4175	6144	4226	2375
35°	4061	4579	4106	2303
40°	3929	3449	3966	2268
45°	3725	2768	3771	2219
50°	3483	2333	3533	2196
55°	3197	2030	3248	2170
60°	2920	1787	3006	2135
65°	2659	1538	2685	2045
70°	2354	1266	2405	1884
75°	2052	973	2040	1600
80°	1616	639	1596	1214
85°	1062	287	997	708

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5812 cd/sqm

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	1.2
10°-20°	165.6	3.8
20°-30°	263.0	6.1
30°-40°	292.3	6.8
40°-50°	265.8	6.1
50°-60°	217.2	5.0
60°-70°	155.1	3.6
70°-80°	85.3	2.0
80°-90°	24.6	0.6
90°-100°	279.3	6.5
100°-110°	583.1	13.5
110°-120°	518.3	12.0
120°-130°	436.3	10.1
130°-140°	364.0	8.4
140°-150°	277.9	6.4
150°-160°	195.4	4.5
160°-170°	114.9	2.7
170°-180°	37.4	0.9
0°-30°	482.3	11.1
0°-40°	774.6	17.9
0°-60°	1257.6	29.0
0°-90°	1522.5	35.2
90°-120°	1380.6	31.9
90°-150°	2458.8	56.8
90°-180°	2806.0	64.8
0°-180°	4329.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	551	551	551	551	551	
5°	549	647	552	486	549	52
15°	524	888	528	390	524	148
25°	479	943	483	316	479	221
35°	415	558	420	280	415	259
45°	331	313	335	251	331	255
55°	233	205	237	219	233	209
65°	145	132	147	175	145	143
75°	71	66	71	108	71	75
85°	15	14	14	34	15	17
90°	1	16	1	16	1	3
95°	25	185	25	185	25	27
105°	89	1065	89	1065	89	94
115°	156	1023	156	1023	156	155
125°	217	816	217	816	217	194
135°	258	730	258	730	258	200
145°	298	596	298	596	298	187
155°	338	499	338	499	338	156
165°	369	435	369	435	369	104
175°	385	392	385	392	385	37
180°	385	385	385	385	385	

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	551.2	556.7	559.0	560.8	566.7	568.6	569.0	571.8	574.0	574.5	574.5
5°	548.9	557.6	564.4	570.8	580.4	584.5	589.6	595.0	602.3	606.9	609.2
7.5°	545.3	558.1	568.6	579.5	592.8	601.0	605.5	620.2	630.2	638.4	648.5
10°	539.8	556.2	571.3	587.3	606.0	616.0	626.1	643.9	658.1	674.0	686.8
12.5°	531.6	553.0	571.3	593.7	617.0	628.8	640.7	671.8	688.2	702.4	725.2
15°	524.3	545.7	571.8	594.6	623.4	641.2	658.5	678.6	704.6	735.2	757.2
17.5°	516.0	543.0	567.2	599.2	631.1	648.0	662.2	693.2	729.8	759.9	780.0
20°	504.6	532.0	564.0	597.8	635.7	648.9	667.7	709.2	742.1	771.8	804.7
22.5°	491.4	523.3	557.1	589.6	628.8	656.7	677.2	713.8	753.5	787.8	824.7
25°	478.6	513.3	543.0	587.3	628.8	647.6	670.8	714.2	757.6	799.2	837.1
27.5°	464.9	497.3	537.5	572.7	619.7	640.3	665.4	712.9	759.0	800.5	841.2
30°	449.8	484.5	517.9	559.4	605.1	631.6	654.9	706.5	753.5	796.9	834.8
32.5°	432.9	465.8	501.4	540.7	588.6	615.6	644.8	697.8	748.0	785.5	814.7
35°	415.1	448.5	479.5	519.7	569.0	596.0	624.3	682.7	732.5	763.1	780.0
37.5°	395.5	427.0	457.6	497.3	546.6	575.4	604.2	660.8	707.8	733.4	728.8
40°	376.8	405.1	433.4	470.8	522.4	553.0	578.1	635.2	676.3	687.3	672.2
42.5°	355.3	379.5	406.9	445.3	495.5	524.3	555.8	607.8	638.4	633.9	608.3
45°	331.1	352.5	379.9	416.0	467.2	496.9	523.3	572.7	595.0	583.6	537.0
47.5°	307.8	328.8	351.2	387.3	437.0	462.2	489.1	533.4	546.2	522.0	475.4
50°	282.7	300.0	323.3	357.6	404.2	430.6	453.0	488.6	493.2	463.5	415.1
52.5°	258.5	273.1	295.5	329.3	372.6	393.6	415.6	447.1	443.4	412.8	366.2
55°	232.9	246.6	267.2	298.2	336.6	356.7	375.4	403.2	395.5	364.0	323.3
57.5°	211.4	221.0	241.1	269.9	301.4	323.3	339.3	361.2	349.4	317.8	279.9
60°	186.8	198.7	215.5	238.8	269.9	284.5	298.7	313.3	305.1	274.9	241.1
62.5°	164.4	173.5	188.1	210.5	234.7	248.0	263.0	272.2	264.0	236.1	207.8
65°	145.2	152.5	163.9	182.2	205.5	216.5	225.1	233.8	227.0	200.9	180.4
67.5°	124.2	130.6	140.2	154.8	174.4	182.2	190.4	196.4	188.6	171.3	151.2
70°	105.5	110.1	119.2	130.2	143.9	151.2	158.0	163.9	157.1	142.5	127.4
72.5°	86.3	90.0	98.2	105.9	118.3	123.3	128.3	132.9	130.6	116.9	104.6
75°	71.2	72.6	78.1	84.5	92.2	97.7	101.4	104.1	102.3	91.3	83.6
77.5°	53.9	55.7	59.8	64.8	71.7	74.9	77.2	79.9	77.6	69.0	63.5
80°	39.3	39.7	42.0	46.6	51.1	51.6	53.9	57.5	56.2	50.2	46.1
82.5°	25.1	26.5	27.4	30.1	33.3	34.3	35.6	36.5	36.1	32.4	31.1
85°	14.6	14.6	15.5	17.4	18.3	19.6	20.1	20.6	21.5	19.2	17.8
87.5°	6.4	6.9	6.9	7.3	8.2	8.2	8.7	9.1	9.6	9.1	7.8
90°	0.8	2.3	4.5	5.3	6.1	6.1	6.1	10.6	10.6	12.1	13.6
92.5°	10.6	15.1	23.5	34.8	48.5	58.3	68.1	115.1	188.5	259.7	296.8
95°	25.0	27.3	34.8	44.7	62.8	78.7	94.6	160.5	284.6	465.6	617.0
97.5°	41.6	41.6	48.5	57.5	73.4	87.1	100.7	152.9	259.7	445.9	660.1
100°	57.5	57.5	62.8	71.9	86.3	98.4	110.5	155.2	240.7	395.2	608.7
102.5°	72.7	74.2	78.7	87.1	100.7	112.0	123.4	162.8	235.4	361.1	544.3
105°	88.6	90.8	94.6	103.7	117.3	128.3	139.3	175.6	238.5	344.5	496.6
107.5°	106.0	107.5	111.3	121.1	134.0	145.0	156.0	189.3	247.6	339.9	465.6
110°	123.4	124.9	128.7	137.8	151.4	161.6	171.8	205.2	258.2	341.4	451.2

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	140.1	141.6	146.1	154.4	168.1	178.3	188.5	220.3	269.5	346.0	444.4
115°	156.0	158.2	163.5	171.1	185.5	195.7	205.9	236.2	281.6	352.0	442.9
117.5°	172.6	174.9	179.4	187.7	201.4	212.0	222.6	251.3	293.7	358.1	442.1
120°	189.3	190.8	196.1	204.4	217.3	227.9	238.5	267.2	306.6	364.9	442.1
122.5°	204.4	205.9	211.2	218.8	233.2	243.4	253.6	282.4	318.7	371.7	441.4
125°	217.3	220.3	224.8	233.2	247.6	258.2	268.7	296.0	330.8	378.5	440.6
127.5°	229.4	231.7	237.0	246.0	261.2	271.8	282.4	308.9	341.4	383.8	439.1
130°	239.2	242.3	248.3	259.7	274.0	285.0	296.0	321.7	351.3	389.9	438.3
132.5°	249.1	251.3	259.7	270.3	286.2	296.4	306.6	332.3	361.1	395.2	437.6
135°	258.2	261.2	268.7	281.6	297.5	307.4	317.2	342.2	369.4	400.5	436.8
137.5°	267.2	270.3	278.6	290.7	307.4	316.8	326.3	349.8	375.5	403.5	436.8
140°	277.1	279.3	287.7	300.5	316.4	325.5	334.6	357.3	381.5	407.3	436.1
142.5°	287.7	289.9	297.5	309.6	324.8	333.5	342.2	364.1	386.1	410.3	436.1
145°	297.5	299.8	307.4	318.0	332.3	340.6	349.0	368.7	389.1	411.1	434.5
147.5°	308.9	309.6	316.4	327.8	339.9	347.5	355.1	374.0	392.1	411.8	432.3
150°	319.5	320.2	326.3	335.4	346.7	353.9	361.1	377.8	394.4	411.8	430.0
152.5°	329.3	329.3	335.4	343.7	353.5	360.0	366.4	380.8	395.9	410.3	426.2
155°	338.4	339.2	343.7	351.3	359.6	365.3	371.0	383.8	396.7	408.8	422.4
157.5°	347.5	347.5	352.0	358.1	365.7	370.2	374.7	386.1	396.7	407.3	418.6
160°	355.8	355.8	358.8	364.1	370.2	374.4	378.5	387.6	396.7	405.0	414.1
162.5°	363.4	362.6	364.9	369.4	374.7	377.8	380.8	389.1	396.7	402.7	409.6
165°	368.7	368.7	370.2	374.0	377.8	380.0	382.3	389.1	395.2	399.7	405.0
167.5°	374.7	374.0	374.7	377.8	380.0	381.9	383.8	389.1	393.7	396.7	400.5
170°	378.5	377.8	378.5	380.8	382.3	383.5	384.6	388.4	392.1	393.7	395.9
172.5°	382.3	381.5	381.5	383.1	383.8	384.6	385.3	387.6	390.6	390.6	391.4
175°	384.6	383.8	383.8	384.6	385.3	385.3	385.3	386.8	389.1	388.4	388.4
177.5°	386.1	385.3	384.6	385.3	385.3	385.3	385.3	386.1	387.6	386.1	386.1
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	575.9	584.1	587.7	588.6	593.7	590.5	591.8	591.4	595.0	595.5	595.5
5°	617.9	627.5	630.7	635.2	642.1	643.9	642.5	645.3	650.3	646.6	652.1
7.5°	662.2	672.7	680.0	690.0	692.3	698.2	701.9	705.1	706.0	706.5	707.4
10°	703.3	716.5	726.6	743.5	747.1	750.3	766.3	759.9	768.1	765.4	766.3
12.5°	736.6	762.6	770.9	799.2	801.9	812.9	812.0	822.0	823.8	827.5	823.8
15°	780.4	810.6	823.8	839.8	849.0	861.7	864.0	877.7	883.2	888.2	883.2
17.5°	820.6	836.6	870.4	883.2	889.1	896.0	913.3	918.4	926.6	923.4	932.5
20°	840.7	863.6	899.2	921.1	930.2	936.6	951.2	959.0	962.2	962.2	963.1
22.5°	858.5	891.4	917.9	943.0	951.2	955.8	964.5	970.4	971.8	972.7	973.6
25°	874.5	904.2	925.7	939.8	943.0	943.0	948.0	944.4	938.5	943.0	945.8
27.5°	874.5	895.5	905.1	910.1	910.1	897.8	890.5	875.4	862.7	859.0	867.2
30°	859.9	869.5	856.3	843.9	834.3	826.1	797.3	774.5	769.9	766.7	779.1
32.5°	826.1	813.8	787.8	752.1	738.0	719.3	696.9	679.5	669.0	665.4	662.6
35°	766.3	734.3	700.5	652.6	642.5	618.8	588.2	575.4	558.1	557.6	563.5
37.5°	701.0	651.7	615.1	569.5	555.3	530.2	501.4	488.2	476.3	467.2	478.1
40°	624.7	581.8	526.1	488.6	468.5	455.3	431.1	416.5	411.0	406.4	413.3
42.5°	553.5	506.4	463.1	424.7	408.3	393.2	377.2	363.1	358.9	358.5	363.5
45°	482.7	436.6	396.4	363.5	353.0	343.9	328.3	324.2	317.4	312.8	315.1
47.5°	426.1	378.6	345.2	320.1	311.0	303.2	293.2	286.3	280.4	278.6	281.3
50°	370.4	338.4	304.1	283.1	276.3	269.0	261.2	254.8	252.1	250.3	252.1
52.5°	325.6	291.4	268.1	251.2	244.3	238.8	233.4	230.6	227.0	227.9	229.7
55°	285.4	255.3	235.6	223.3	219.2	216.9	210.1	206.9	205.5	204.6	205.5
57.5°	247.5	225.6	211.0	200.5	195.0	193.6	188.1	188.1	186.8	185.4	185.9
60°	217.4	198.7	184.5	176.3	175.4	173.1	169.4	169.0	165.8	167.1	167.6
62.5°	186.8	171.7	162.1	157.1	153.9	153.0	150.7	150.2	148.9	149.3	148.4
65°	162.6	150.2	140.7	136.5	135.2	134.7	132.9	131.5	130.6	131.5	130.6
67.5°	138.4	130.2	122.8	118.7	116.9	116.5	115.1	114.2	114.6	113.3	114.2
70°	115.5	107.3	102.8	100.5	99.6	98.2	98.2	98.2	98.2	97.3	96.8
72.5°	97.3	89.1	85.9	84.5	83.6	83.1	81.7	82.2	81.7	81.3	83.1
75°	77.2	72.2	69.0	67.6	68.5	67.1	65.8	66.7	65.3	65.8	67.6
77.5°	58.5	56.2	54.3	53.4	52.5	51.6	51.6	50.7	50.7	50.7	50.7
80°	42.5	42.0	38.8	38.4	38.4	37.4	37.4	37.4	37.4	37.0	37.4
82.5°	28.3	27.9	26.9	26.5	25.6	26.0	26.0	25.1	25.1	24.7	25.1
85°	16.4	16.4	15.5	15.1	14.6	15.1	14.2	13.7	14.2	13.7	14.2
87.5°	7.8	6.9	7.3	6.9	5.9	6.4	5.5	5.9	5.5	5.0	5.9
90°	12.9	13.6	14.4	15.1	15.1	15.1	15.9	16.7	15.9	15.9	15.9
92.5°	246.8	182.4	136.3	107.5	98.0	88.6	77.2	71.9	68.9	68.9	68.9
95°	634.4	561.0	443.6	342.2	305.4	268.7	231.7	208.2	194.6	184.7	194.6
97.5°	795.7	807.8	749.5	666.2	623.8	581.4	529.9	484.5	461.8	443.6	461.8
100°	802.5	913.0	928.1	891.0	863.0	835.0	769.2	723.0	700.3	694.2	700.3
102.5°	745.7	907.7	997.8	1020.5	1013.0	1005.4	971.3	941.0	916.8	912.2	916.8
105°	674.5	847.9	978.9	1053.8	1069.3	1084.8	1086.4	1080.3	1069.7	1065.2	1069.7
107.5°	616.2	774.5	916.0	1020.5	1052.3	1084.1	1117.4	1131.0	1137.1	1137.8	1137.1
110°	574.6	709.3	840.3	950.1	991.8	1033.4	1087.1	1118.9	1132.5	1139.3	1132.5

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	551.1	661.7	773.7	875.9	917.6	959.2	1022.0	1062.1	1082.6	1094.7	1082.6
115°	538.3	632.9	726.0	814.6	851.0	887.3	947.1	992.5	1016.7	1022.8	1016.7
117.5°	531.4	616.2	695.0	766.9	798.7	830.5	883.5	922.8	948.6	952.4	948.6
120°	526.1	605.6	676.0	736.6	763.5	790.4	833.5	866.8	886.5	894.8	886.5
122.5°	520.1	596.5	663.9	717.7	740.4	763.1	797.9	825.2	841.1	849.4	841.1
125°	513.3	585.9	651.1	703.3	724.1	744.9	775.2	797.2	811.5	816.1	811.5
127.5°	504.2	573.8	636.7	688.9	708.6	728.3	758.6	778.2	790.4	794.9	790.4
130°	495.9	558.7	618.5	670.0	690.0	710.1	741.1	760.1	772.2	776.7	772.2
132.5°	488.3	542.8	598.1	648.0	668.1	688.2	718.4	740.4	751.7	756.3	751.7
135°	480.7	528.4	577.6	623.8	642.8	661.7	691.9	713.1	725.2	729.8	725.2
137.5°	473.9	514.8	557.9	598.1	615.5	632.9	661.7	683.6	693.4	698.7	693.4
140°	468.6	503.4	539.0	573.1	589.0	604.9	631.4	648.0	658.6	664.7	658.6
142.5°	464.1	492.8	523.1	551.1	564.4	577.6	600.3	615.5	624.6	628.3	624.6
145°	458.8	483.0	508.7	531.4	542.0	552.6	571.6	584.4	592.0	595.8	592.0
147.5°	454.2	474.7	495.9	514.8	523.5	532.2	546.6	557.9	564.0	565.5	564.0
150°	448.9	467.1	484.5	499.6	506.4	513.3	525.4	535.2	539.8	540.5	539.8
152.5°	442.9	458.8	473.2	486.8	492.1	497.4	507.2	514.8	517.1	517.8	517.1
155°	436.8	450.4	462.6	473.9	478.4	483.0	490.6	496.6	498.9	498.9	498.9
157.5°	430.8	441.4	452.0	461.8	465.6	469.4	475.4	480.0	481.5	481.5	481.5
160°	423.9	433.0	441.4	449.7	452.7	455.7	460.3	464.8	465.6	465.6	465.6
162.5°	417.9	424.7	431.5	437.6	440.2	442.9	445.9	450.4	451.2	450.4	451.2
165°	411.1	417.1	421.7	427.0	428.9	430.8	433.8	436.8	436.1	435.3	436.1
167.5°	405.0	409.6	413.3	417.9	419.0	420.2	421.7	423.9	423.9	423.2	423.9
170°	399.0	402.7	405.0	408.0	409.2	410.3	411.8	412.6	411.8	411.8	411.8
172.5°	393.7	396.7	398.2	399.7	400.4	401.2	402.0	402.7	402.0	400.5	402.0
175°	389.9	391.4	392.1	393.7	393.7	393.7	393.7	395.2	393.7	392.1	393.7
177.5°	386.8	387.6	388.4	388.4	388.8	389.1	388.4	389.1	387.6	386.1	387.6
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	594.6	593.2	591.4	591.4	589.1	589.1	585.5	579.1	573.6	571.8	572.7
5°	645.3	645.7	643.0	640.7	636.6	633.4	627.5	616.0	612.4	605.1	600.1
7.5°	703.3	701.4	696.4	692.8	691.9	684.5	671.8	658.1	647.1	639.8	629.3
10°	768.6	761.3	754.0	751.7	746.2	733.9	719.3	704.2	689.1	673.1	655.3
12.5°	823.4	809.2	808.8	803.3	792.8	785.9	768.6	747.1	721.1	703.3	683.2
15°	882.3	869.0	858.1	848.0	843.0	822.9	808.3	781.4	750.3	731.1	717.4
17.5°	924.3	918.4	899.6	895.1	888.2	864.9	841.6	815.2	788.2	761.3	724.3
20°	958.1	954.4	942.1	935.7	924.8	906.5	878.2	847.6	816.5	778.2	743.5
22.5°	972.7	968.1	958.1	952.6	945.8	930.2	906.0	871.3	830.7	796.4	759.4
25°	943.9	952.2	949.4	947.1	944.4	935.3	917.0	886.4	846.7	807.8	761.7
27.5°	879.1	893.2	906.9	908.8	913.3	917.0	909.7	887.8	854.4	813.3	762.6
30°	791.9	798.3	826.1	834.3	840.7	864.0	877.7	872.2	846.7	809.7	763.1
32.5°	680.0	696.9	725.2	744.8	762.2	788.2	823.8	838.0	828.9	798.7	752.6
35°	574.0	594.1	627.0	652.1	669.5	706.5	748.5	779.1	790.5	775.4	734.3
37.5°	487.3	511.5	540.7	550.3	570.4	616.0	674.0	716.5	744.4	745.7	713.8
40°	422.0	434.3	457.6	472.2	491.8	530.2	586.8	643.0	685.0	699.2	682.3
42.5°	366.7	376.3	393.6	411.5	429.3	458.5	510.6	563.1	619.7	648.0	647.6
45°	322.9	332.9	344.8	359.4	371.7	403.2	444.3	498.2	547.1	590.9	601.9
47.5°	284.5	293.2	307.8	314.2	322.4	352.1	387.7	437.9	488.6	538.9	551.7
50°	256.2	263.5	273.5	277.7	286.8	308.7	337.9	378.6	434.8	480.9	504.6
52.5°	230.6	236.1	243.9	247.1	253.5	269.9	296.4	328.3	374.9	422.4	455.8
55°	208.7	212.4	217.8	221.5	226.1	240.7	260.3	289.1	329.3	370.4	402.8
57.5°	188.1	190.9	196.4	198.2	201.8	213.3	227.0	251.2	288.2	324.7	356.2
60°	169.0	170.8	174.0	178.1	180.8	188.6	201.4	221.5	251.2	284.5	310.1
62.5°	150.7	153.4	154.4	156.2	158.5	165.8	175.8	190.4	216.5	243.9	270.8
65°	132.0	134.3	136.1	136.5	138.8	144.3	153.4	166.2	183.1	206.9	232.0
67.5°	114.6	116.0	116.9	118.7	121.0	123.8	131.1	140.7	156.2	175.4	195.5
70°	98.6	98.6	100.0	100.5	103.2	106.4	109.6	118.7	132.4	148.0	161.7
72.5°	81.3	83.6	83.1	85.4	84.9	87.2	91.3	97.3	107.3	119.6	132.9
75°	66.2	67.6	67.6	67.6	68.5	70.3	72.6	78.1	85.9	95.9	103.7
77.5°	51.6	52.5	52.5	52.5	53.0	54.8	57.1	60.7	66.2	72.2	76.7
80°	37.0	37.9	37.9	38.8	38.8	39.3	41.6	43.4	46.1	50.7	55.3
82.5°	25.1	25.6	26.5	26.5	26.0	26.9	27.4	29.2	32.0	32.9	36.1
85°	13.7	14.2	14.6	14.6	15.1	16.0	15.5	17.4	17.4	19.2	20.1
87.5°	5.5	6.4	6.4	5.9	6.4	6.4	6.4	7.3	7.8	8.2	7.8
90°	16.7	15.9	15.1	15.1	15.1	14.4	13.6	12.9	13.6	12.1	10.6
92.5°	71.9	77.2	88.6	98.0	107.5	136.3	182.4	246.8	296.8	259.7	188.5
95°	208.2	231.7	268.7	305.4	342.2	443.6	561.0	634.4	617.0	465.6	284.6
97.5°	484.5	529.9	581.4	623.8	666.2	749.5	807.8	795.7	660.1	445.9	259.7
100°	723.0	769.2	835.0	863.0	891.0	928.1	913.0	802.5	608.7	395.2	240.7
102.5°	941.0	971.3	1005.4	1013.0	1020.5	997.8	907.7	745.7	544.3	361.1	235.4
105°	1080.3	1086.4	1084.8	1069.3	1053.8	978.9	847.9	674.5	496.6	344.5	238.5
107.5°	1131.0	1117.4	1084.1	1052.3	1020.5	916.0	774.5	616.2	465.6	339.9	247.6
110°	1118.9	1087.1	1033.4	991.8	950.1	840.3	709.3	574.6	451.2	341.4	258.2

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1062.1	1022.0	959.2	917.6	875.9	773.7	661.7	551.1	444.4	346.0	269.5
115°	992.5	947.1	887.3	851.0	814.6	726.0	632.9	538.3	442.9	352.0	281.6
117.5°	922.8	883.5	830.5	798.7	766.9	695.0	616.2	531.4	442.1	358.1	293.7
120°	866.8	833.5	790.4	763.5	736.6	676.0	605.6	526.1	442.1	364.9	306.6
122.5°	825.2	797.9	763.1	740.4	717.7	663.9	596.5	520.1	441.4	371.7	318.7
125°	797.2	775.2	744.9	724.1	703.3	651.1	585.9	513.3	440.6	378.5	330.8
127.5°	778.2	758.6	728.3	708.6	688.9	636.7	573.8	504.2	439.1	383.8	341.4
130°	760.1	741.1	710.1	690.0	670.0	618.5	558.7	495.9	438.3	389.9	351.3
132.5°	740.4	718.4	688.2	668.1	648.0	598.1	542.8	488.3	437.6	395.2	361.1
135°	713.1	691.9	661.7	642.8	623.8	577.6	528.4	480.7	436.8	400.5	369.4
137.5°	683.6	661.7	632.9	615.5	598.1	557.9	514.8	473.9	436.8	403.5	375.5
140°	648.0	631.4	604.9	589.0	573.1	539.0	503.4	468.6	436.1	407.3	381.5
142.5°	615.5	600.3	577.6	564.4	551.1	523.1	492.8	464.1	436.1	410.3	386.1
145°	584.4	571.6	552.6	542.0	531.4	508.7	483.0	458.8	434.5	411.1	389.1
147.5°	557.9	546.6	532.2	523.5	514.8	495.9	474.7	454.2	432.3	411.8	392.1
150°	535.2	525.4	513.3	506.4	499.6	484.5	467.1	448.9	430.0	411.8	394.4
152.5°	514.8	507.2	497.4	492.1	486.8	473.2	458.8	442.9	426.2	410.3	395.9
155°	496.6	490.6	483.0	478.4	473.9	462.6	450.4	436.8	422.4	408.8	396.7
157.5°	480.0	475.4	469.4	465.6	461.8	452.0	441.4	430.8	418.6	407.3	396.7
160°	464.8	460.3	455.7	452.7	449.7	441.4	433.0	423.9	414.1	405.0	396.7
162.5°	450.4	445.9	442.9	440.2	437.6	431.5	424.7	417.9	409.6	402.7	396.7
165°	436.8	433.8	430.8	428.9	427.0	421.7	417.1	411.1	405.0	399.7	395.2
167.5°	423.9	421.7	420.2	419.0	417.9	413.3	409.6	405.0	400.5	396.7	393.7
170°	412.6	411.8	410.3	409.2	408.0	405.0	402.7	399.0	395.9	393.7	392.1
172.5°	402.7	402.0	401.2	400.4	399.7	398.2	396.7	393.7	391.4	390.6	390.6
175°	395.2	393.7	393.7	393.7	393.7	392.1	391.4	389.9	388.4	388.4	389.1
177.5°	389.1	388.4	389.1	388.8	388.4	388.4	387.6	386.8	386.1	386.1	387.6
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	568.6	566.7	565.4	565.4	561.2	557.1	554.9	553.9	553.0	549.4	544.4
5°	591.8	585.9	581.8	577.7	570.8	563.5	556.2	552.1	546.2	538.0	532.0
7.5°	617.9	603.7	599.2	594.1	580.4	568.1	558.1	549.4	539.8	529.3	518.8
10°	639.8	624.7	614.7	606.0	588.2	571.8	556.7	543.9	531.6	517.9	505.1
12.5°	660.8	639.3	628.8	616.0	597.3	573.6	553.9	538.0	519.7	505.5	490.0
15°	690.0	654.0	636.6	628.4	603.3	575.4	551.7	527.9	512.8	491.4	477.7
17.5°	694.6	665.4	654.0	632.9	602.8	571.3	543.9	520.1	497.3	478.1	460.3
20°	710.6	672.2	654.0	640.7	601.0	569.0	538.9	508.3	486.4	465.8	445.7
22.5°	720.6	677.2	658.1	637.1	599.2	560.8	525.2	498.7	471.7	450.7	434.8
25°	717.9	674.5	653.0	633.4	587.3	548.9	517.0	483.2	458.0	435.2	414.2
27.5°	716.5	667.7	644.8	622.9	579.5	539.3	499.1	471.7	443.9	417.4	401.9
30°	712.9	659.0	632.5	608.7	563.5	521.5	487.3	455.3	427.4	403.2	382.7
32.5°	700.5	644.4	618.8	593.2	546.2	504.2	469.5	439.8	411.9	386.8	367.2
35°	684.1	627.0	599.2	572.2	525.2	482.7	450.7	419.7	393.6	369.4	350.7
37.5°	667.7	606.9	580.9	549.8	506.4	462.2	429.3	401.4	377.2	352.1	331.5
40°	643.9	583.2	554.4	527.9	477.2	435.7	405.5	380.4	356.7	332.9	315.6
42.5°	611.5	557.1	527.5	498.2	450.7	409.6	380.4	358.0	335.7	316.0	296.8
45°	578.6	525.6	499.1	473.1	421.5	382.7	355.7	335.2	316.5	295.0	279.5
47.5°	538.9	494.1	467.6	442.1	393.2	354.4	329.7	310.5	293.2	275.4	260.8
50°	498.2	459.4	435.2	408.7	362.1	327.0	302.8	286.8	272.6	255.7	243.9
52.5°	454.4	420.6	400.0	374.5	333.4	300.9	276.3	260.3	248.4	236.1	225.6
55°	407.8	383.1	361.2	340.7	301.9	272.6	250.7	236.6	228.3	216.9	207.8
57.5°	365.8	342.0	328.8	305.5	271.7	242.9	225.6	213.7	204.1	197.3	190.0
60°	322.0	302.8	288.2	271.3	241.6	217.4	199.1	192.3	182.2	177.2	174.0
62.5°	279.9	266.2	252.5	239.8	213.3	190.4	176.7	168.1	162.1	157.1	154.4
65°	240.2	227.4	217.8	206.4	184.5	166.2	153.4	146.6	140.7	139.3	136.1
67.5°	201.4	195.9	185.4	176.3	157.6	143.4	133.8	125.1	121.9	120.6	117.8
70°	168.5	162.1	153.9	146.1	132.0	119.6	111.0	107.8	103.2	102.8	99.6
72.5°	138.8	131.1	125.1	119.2	108.7	97.7	93.2	88.6	86.3	84.5	83.1
75°	110.1	104.6	100.5	95.4	86.3	79.0	72.6	70.8	69.4	69.0	68.0
77.5°	82.2	78.5	76.7	71.7	65.3	58.9	56.2	53.4	53.4	52.5	53.0
80°	58.5	56.2	53.9	51.1	45.7	42.9	40.6	38.8	37.9	37.4	37.9
82.5°	37.0	35.6	35.2	33.3	29.7	28.3	26.5	25.1	25.1	25.1	25.1
85°	20.6	20.6	20.6	17.8	16.4	15.1	14.2	13.7	13.7	13.7	14.2
87.5°	8.7	8.7	7.3	7.3	6.9	5.9	5.5	5.5	5.9	5.9	6.4
90°	10.6	6.1	6.1	6.1	5.3	4.5	2.3	0.8	2.3	4.5	5.3
92.5°	115.1	68.1	58.3	48.5	34.8	23.5	15.1	10.6	15.1	23.5	34.8
95°	160.5	94.6	78.7	62.8	44.7	34.8	27.3	25.0	27.3	34.8	44.7
97.5°	152.9	100.7	87.1	73.4	57.5	48.5	41.6	41.6	41.6	48.5	57.5
100°	155.2	110.5	98.4	86.3	71.9	62.8	57.5	57.5	57.5	62.8	71.9
102.5°	162.8	123.4	112.0	100.7	87.1	78.7	74.2	72.7	74.2	78.7	87.1
105°	175.6	139.3	128.3	117.3	103.7	94.6	90.8	88.6	90.8	94.6	103.7
107.5°	189.3	156.0	145.0	134.0	121.1	111.3	107.5	106.0	107.5	111.3	121.1
110°	205.2	171.8	161.6	151.4	137.8	128.7	124.9	123.4	124.9	128.7	137.8

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	220.3	188.5	178.3	168.1	154.4	146.1	141.6	140.1	141.6	146.1	154.4
115°	236.2	205.9	195.7	185.5	171.1	163.5	158.2	156.0	158.2	163.5	171.1
117.5°	251.3	222.6	212.0	201.4	187.7	179.4	174.9	172.6	174.9	179.4	187.7
120°	267.2	238.5	227.9	217.3	204.4	196.1	190.8	189.3	190.8	196.1	204.4
122.5°	282.4	253.6	243.4	233.2	218.8	211.2	205.9	204.4	205.9	211.2	218.8
125°	296.0	268.7	258.2	247.6	233.2	224.8	220.3	217.3	220.3	224.8	233.2
127.5°	308.9	282.4	271.8	261.2	246.0	237.0	231.7	229.4	231.7	237.0	246.0
130°	321.7	296.0	285.0	274.0	259.7	248.3	242.3	239.2	242.3	248.3	259.7
132.5°	332.3	306.6	296.4	286.2	270.3	259.7	251.3	249.1	251.3	259.7	270.3
135°	342.2	317.2	307.4	297.5	281.6	268.7	261.2	258.2	261.2	268.7	281.6
137.5°	349.8	326.3	316.8	307.4	290.7	278.6	270.3	267.2	270.3	278.6	290.7
140°	357.3	334.6	325.5	316.4	300.5	287.7	279.3	277.1	279.3	287.7	300.5
142.5°	364.1	342.2	333.5	324.8	309.6	297.5	289.9	287.7	289.9	297.5	309.6
145°	368.7	349.0	340.6	332.3	318.0	307.4	299.8	297.5	299.8	307.4	318.0
147.5°	374.0	355.1	347.5	339.9	327.8	316.4	309.6	308.9	309.6	316.4	327.8
150°	377.8	361.1	353.9	346.7	335.4	326.3	320.2	319.5	320.2	326.3	335.4
152.5°	380.8	366.4	360.0	353.5	343.7	335.4	329.3	329.3	329.3	335.4	343.7
155°	383.8	371.0	365.3	359.6	351.3	343.7	339.2	338.4	339.2	343.7	351.3
157.5°	386.1	374.7	370.2	365.7	358.1	352.0	347.5	347.5	347.5	352.0	358.1
160°	387.6	378.5	374.4	370.2	364.1	358.8	355.8	355.8	355.8	358.8	364.1
162.5°	389.1	380.8	377.8	374.7	369.4	364.9	362.6	363.4	362.6	364.9	369.4
165°	389.1	382.3	380.0	377.8	374.0	370.2	368.7	368.7	368.7	370.2	374.0
167.5°	389.1	383.8	381.9	380.0	377.8	374.7	374.0	374.7	374.0	374.7	377.8
170°	388.4	384.6	383.5	382.3	380.8	378.5	377.8	378.5	377.8	378.5	380.8
172.5°	387.6	385.3	384.6	383.8	383.1	381.5	381.5	382.3	381.5	381.5	383.1
175°	386.8	385.3	385.3	385.3	384.6	383.8	383.8	384.6	383.8	383.8	384.6
177.5°	386.1	385.3	385.3	385.3	385.3	384.6	385.3	386.1	385.3	384.6	385.3
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	543.0	541.2	542.1	537.5	533.4	527.5	522.4	521.5	520.6	523.3	521.5
5°	527.5	525.2	522.9	517.4	509.2	504.2	496.9	496.4	493.7	489.6	490.5
7.5°	510.6	509.2	506.0	497.3	490.0	481.3	475.4	470.4	468.1	464.4	463.1
10°	496.9	491.8	489.1	479.5	470.8	461.7	453.9	450.3	446.2	443.0	440.7
12.5°	478.1	476.8	469.0	461.2	453.9	443.4	437.5	427.0	421.5	424.2	423.3
15°	465.8	459.4	457.6	446.6	434.3	427.4	416.5	409.6	407.4	403.2	398.2
17.5°	449.4	445.3	438.9	428.8	414.7	405.1	397.3	390.9	388.2	382.7	378.6
20°	433.8	427.0	422.0	412.8	399.1	386.8	377.2	373.1	366.2	361.7	359.4
22.5°	419.7	414.7	407.4	393.6	381.8	369.9	358.5	352.5	346.2	343.4	339.8
25°	402.3	394.1	389.1	374.0	361.2	351.6	341.1	333.4	329.7	325.1	324.2
27.5°	385.4	377.7	371.7	358.5	343.0	330.6	324.2	318.8	312.4	312.4	310.1
30°	368.5	363.1	353.9	341.1	326.5	314.6	307.3	302.3	300.0	298.2	297.7
32.5°	351.6	344.3	338.8	321.5	310.5	299.6	294.1	290.0	287.2	286.8	287.2
35°	334.3	326.1	320.6	305.1	294.1	284.0	281.8	278.1	276.7	276.3	278.6
37.5°	316.0	309.6	302.8	290.0	277.7	271.7	267.2	265.8	265.3	268.1	269.0
40°	299.1	293.6	287.2	273.5	264.4	258.0	255.7	254.4	256.2	258.9	260.3
42.5°	283.1	275.4	270.3	258.0	249.8	246.1	243.4	243.4	245.2	248.4	250.7
45°	266.2	260.3	255.3	244.3	237.0	232.9	232.4	232.9	235.2	237.5	240.2
47.5°	249.8	243.9	238.4	229.2	222.9	220.6	220.1	220.6	224.2	227.4	230.6
50°	234.7	228.3	223.3	214.6	209.6	206.9	207.3	209.6	212.4	216.9	221.0
52.5°	216.9	212.4	207.8	200.0	195.5	193.6	195.0	196.8	201.8	205.0	210.1
55°	199.6	195.5	191.8	185.9	182.2	180.8	181.8	184.5	188.6	194.1	200.0
57.5°	183.6	179.0	175.4	171.3	167.1	167.6	168.1	171.7	176.7	181.8	188.6
60°	165.8	163.0	159.8	154.8	153.0	153.0	154.4	158.5	163.0	171.3	177.2
62.5°	149.8	146.1	143.9	140.7	137.9	138.4	141.6	145.2	150.7	157.6	165.3
65°	133.3	129.2	127.4	124.7	123.8	124.2	126.5	132.0	137.9	143.9	151.2
67.5°	115.1	113.7	111.9	109.1	110.1	110.5	112.8	117.4	123.8	129.7	137.9
70°	99.6	96.8	96.4	94.1	94.1	95.4	100.0	103.2	109.1	115.5	124.2
72.5°	83.1	80.8	80.8	79.0	80.4	81.7	84.0	88.6	94.1	100.5	107.8
75°	66.2	65.3	66.2	65.3	65.3	67.6	70.3	74.0	79.9	86.8	92.7
77.5°	51.1	51.1	50.7	52.1	52.1	53.4	57.1	60.7	65.3	70.8	77.2
80°	37.4	37.4	37.4	38.8	40.2	40.2	42.5	47.0	51.1	54.8	60.7
82.5°	25.6	25.6	25.6	26.5	28.3	28.3	31.1	33.8	38.4	41.6	44.3
85°	15.5	15.5	15.1	16.0	16.4	17.8	20.1	21.9	24.2	26.9	29.7
87.5°	6.9	6.9	7.3	7.8	8.2	9.1	10.0	11.0	13.2	14.2	15.5
90°	6.1	6.1	6.1	10.6	10.6	12.1	13.6	12.9	13.6	14.4	15.1
92.5°	48.5	58.3	68.1	115.1	188.5	259.7	296.8	246.8	182.4	136.3	107.5
95°	62.8	78.7	94.6	160.5	284.6	465.6	617.0	634.4	561.0	443.6	342.2
97.5°	73.4	87.1	100.7	152.9	259.7	445.9	660.1	795.7	807.8	749.5	666.2
100°	86.3	98.4	110.5	155.2	240.7	395.2	608.7	802.5	913.0	928.1	891.0
102.5°	100.7	112.0	123.4	162.8	235.4	361.1	544.3	745.7	907.7	997.8	1020.5
105°	117.3	128.3	139.3	175.6	238.5	344.5	496.6	674.5	847.9	978.9	1053.8
107.5°	134.0	145.0	156.0	189.3	247.6	339.9	465.6	616.2	774.5	916.0	1020.5
110°	151.4	161.6	171.8	205.2	258.2	341.4	451.2	574.6	709.3	840.3	950.1

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	168.1	178.3	188.5	220.3	269.5	346.0	444.4	551.1	661.7	773.7	875.9
115°	185.5	195.7	205.9	236.2	281.6	352.0	442.9	538.3	632.9	726.0	814.6
117.5°	201.4	212.0	222.6	251.3	293.7	358.1	442.1	531.4	616.2	695.0	766.9
120°	217.3	227.9	238.5	267.2	306.6	364.9	442.1	526.1	605.6	676.0	736.6
122.5°	233.2	243.4	253.6	282.4	318.7	371.7	441.4	520.1	596.5	663.9	717.7
125°	247.6	258.2	268.7	296.0	330.8	378.5	440.6	513.3	585.9	651.1	703.3
127.5°	261.2	271.8	282.4	308.9	341.4	383.8	439.1	504.2	573.8	636.7	688.9
130°	274.0	285.0	296.0	321.7	351.3	389.9	438.3	495.9	558.7	618.5	670.0
132.5°	286.2	296.4	306.6	332.3	361.1	395.2	437.6	488.3	542.8	598.1	648.0
135°	297.5	307.4	317.2	342.2	369.4	400.5	436.8	480.7	528.4	577.6	623.8
137.5°	307.4	316.8	326.3	349.8	375.5	403.5	436.8	473.9	514.8	557.9	598.1
140°	316.4	325.5	334.6	357.3	381.5	407.3	436.1	468.6	503.4	539.0	573.1
142.5°	324.8	333.5	342.2	364.1	386.1	410.3	436.1	464.1	492.8	523.1	551.1
145°	332.3	340.6	349.0	368.7	389.1	411.1	434.5	458.8	483.0	508.7	531.4
147.5°	339.9	347.5	355.1	374.0	392.1	411.8	432.3	454.2	474.7	495.9	514.8
150°	346.7	353.9	361.1	377.8	394.4	411.8	430.0	448.9	467.1	484.5	499.6
152.5°	353.5	360.0	366.4	380.8	395.9	410.3	426.2	442.9	458.8	473.2	486.8
155°	359.6	365.3	371.0	383.8	396.7	408.8	422.4	436.8	450.4	462.6	473.9
157.5°	365.7	370.2	374.7	386.1	396.7	407.3	418.6	430.8	441.4	452.0	461.8
160°	370.2	374.4	378.5	387.6	396.7	405.0	414.1	423.9	433.0	441.4	449.7
162.5°	374.7	377.8	380.8	389.1	396.7	402.7	409.6	417.9	424.7	431.5	437.6
165°	377.8	380.0	382.3	389.1	395.2	399.7	405.0	411.1	417.1	421.7	427.0
167.5°	380.0	381.9	383.8	389.1	393.7	396.7	400.5	405.0	409.6	413.3	417.9
170°	382.3	383.5	384.6	388.4	392.1	393.7	395.9	399.0	402.7	405.0	408.0
172.5°	383.8	384.6	385.3	387.6	390.6	390.6	391.4	393.7	396.7	398.2	399.7
175°	385.3	385.3	385.3	386.8	389.1	388.4	388.4	389.9	391.4	392.1	393.7
177.5°	385.3	385.3	385.3	386.1	387.6	386.1	386.1	386.8	387.6	388.4	388.4
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	520.1	519.7	517.4	518.3	515.6	516.5	517.9	518.3	520.1	518.8	518.3
5°	488.2	487.3	485.9	484.5	484.1	485.9	482.7	483.6	484.5	485.9	487.7
7.5°	462.2	461.7	460.3	458.0	457.1	456.2	456.7	459.9	459.4	459.0	462.2
10°	438.4	438.9	436.1	435.7	432.9	432.5	432.9	433.8	435.2	437.0	437.5
12.5°	413.7	419.7	414.7	412.8	408.7	411.0	411.9	407.8	410.1	411.5	418.3
15°	398.2	395.5	392.3	392.3	390.5	389.5	387.3	390.5	392.3	395.0	394.1
17.5°	376.8	372.2	370.4	368.5	369.0	370.8	365.8	373.1	373.1	374.5	372.2
20°	358.0	354.4	352.1	351.2	349.8	348.9	348.4	350.3	353.0	353.9	356.2
22.5°	338.4	338.4	334.7	333.4	332.5	331.1	333.4	332.0	333.8	335.7	339.3
25°	322.0	322.0	320.6	318.8	317.4	316.5	317.8	317.4	318.8	321.0	322.0
27.5°	308.7	307.3	306.9	306.4	306.0	306.4	306.0	307.3	308.7	309.2	308.3
30°	297.3	295.9	296.4	296.4	296.8	296.4	295.9	297.3	297.7	296.8	297.3
32.5°	286.8	286.8	287.7	288.2	288.2	288.6	289.1	288.2	288.6	287.2	287.7
35°	278.1	279.0	279.9	280.4	280.9	280.4	281.3	280.9	279.9	279.0	278.6
37.5°	269.4	270.3	272.2	272.6	274.0	274.5	273.5	273.5	273.1	271.3	270.3
40°	260.3	261.2	263.5	264.9	265.8	267.2	266.2	266.2	264.4	262.6	261.2
42.5°	251.6	253.5	255.7	257.1	258.9	258.9	258.9	258.0	255.7	253.9	252.5
45°	242.9	243.4	246.6	248.9	250.7	250.7	250.7	249.3	248.0	244.3	242.5
47.5°	233.4	234.7	238.4	240.7	242.5	242.9	242.9	241.6	238.8	235.6	233.4
50°	222.9	225.1	229.2	232.4	234.7	235.6	234.3	233.4	230.2	226.5	223.8
52.5°	212.8	215.5	220.6	223.3	226.5	227.0	226.5	225.1	221.5	216.5	214.2
55°	202.8	205.0	210.5	215.1	217.8	218.7	217.8	215.5	211.0	206.0	203.7
57.5°	191.8	195.0	200.9	205.5	208.7	209.2	208.2	206.0	202.3	195.9	192.7
60°	180.4	184.5	190.4	195.0	199.1	199.6	198.7	195.5	190.9	184.5	181.8
62.5°	169.0	172.2	179.0	184.0	187.2	189.5	187.7	184.5	179.9	173.5	169.4
65°	155.7	160.3	166.2	170.8	174.4	174.9	174.0	171.3	166.2	159.4	156.2
67.5°	142.9	146.1	152.1	158.0	159.4	160.7	159.4	156.6	152.5	146.6	142.0
70°	127.4	130.2	137.5	141.6	143.4	144.8	143.9	141.1	137.5	132.0	128.3
72.5°	111.9	114.2	121.0	124.2	127.9	127.4	127.0	125.1	120.1	116.5	114.2
75°	95.4	98.2	102.8	106.9	108.2	108.2	108.2	106.9	103.7	97.7	95.4
77.5°	80.4	81.7	85.4	87.7	89.1	89.5	89.1	86.8	84.9	80.8	79.5
80°	61.7	65.3	68.0	68.5	70.3	70.3	70.3	69.4	67.6	63.5	63.0
82.5°	46.6	47.5	50.2	51.6	52.5	52.1	52.1	50.2	49.8	47.5	46.6
85°	31.5	32.9	32.4	34.3	34.7	33.8	33.8	34.7	32.4	32.9	31.5
87.5°	17.4	17.4	18.3	17.8	19.6	19.6	18.7	19.2	18.3	17.8	17.4
90°	15.1	15.1	15.9	16.7	15.9	15.9	15.9	16.7	15.9	15.1	15.1
92.5°	98.0	88.6	77.2	71.9	68.9	68.9	68.9	71.9	77.2	88.6	98.0
95°	305.4	268.7	231.7	208.2	194.6	184.7	194.6	208.2	231.7	268.7	305.4
97.5°	623.8	581.4	529.9	484.5	461.8	443.6	461.8	484.5	529.9	581.4	623.8
100°	863.0	835.0	769.2	723.0	700.3	694.2	700.3	723.0	769.2	835.0	863.0
102.5°	1013.0	1005.4	971.3	941.0	916.8	912.2	916.8	941.0	971.3	1005.4	1013.0
105°	1069.3	1084.8	1086.4	1080.3	1069.7	1065.2	1069.7	1080.3	1086.4	1084.8	1069.3
107.5°	1052.3	1084.1	1117.4	1131.0	1137.1	1137.8	1137.1	1131.0	1117.4	1084.1	1052.3
110°	991.8	1033.4	1087.1	1118.9	1132.5	1139.3	1132.5	1118.9	1087.1	1033.4	991.8

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	917.6	959.2	1022.0	1062.1	1082.6	1094.7	1082.6	1062.1	1022.0	959.2	917.6
115°	851.0	887.3	947.1	992.5	1016.7	1022.8	1016.7	992.5	947.1	887.3	851.0
117.5°	798.7	830.5	883.5	922.8	948.6	952.4	948.6	922.8	883.5	830.5	798.7
120°	763.5	790.4	833.5	866.8	886.5	894.8	886.5	866.8	833.5	790.4	763.5
122.5°	740.4	763.1	797.9	825.2	841.1	849.4	841.1	825.2	797.9	763.1	740.4
125°	724.1	744.9	775.2	797.2	811.5	816.1	811.5	797.2	775.2	744.9	724.1
127.5°	708.6	728.3	758.6	778.2	790.4	794.9	790.4	778.2	758.6	728.3	708.6
130°	690.0	710.1	741.1	760.1	772.2	776.7	772.2	760.1	741.1	710.1	690.0
132.5°	668.1	688.2	718.4	740.4	751.7	756.3	751.7	740.4	718.4	688.2	668.1
135°	642.8	661.7	691.9	713.1	725.2	729.8	725.2	713.1	691.9	661.7	642.8
137.5°	615.5	632.9	661.7	683.6	693.4	698.7	693.4	683.6	661.7	632.9	615.5
140°	589.0	604.9	631.4	648.0	658.6	664.7	658.6	648.0	631.4	604.9	589.0
142.5°	564.4	577.6	600.3	615.5	624.6	628.3	624.6	615.5	600.3	577.6	564.4
145°	542.0	552.6	571.6	584.4	592.0	595.8	592.0	584.4	571.6	552.6	542.0
147.5°	523.5	532.2	546.6	557.9	564.0	565.5	564.0	557.9	546.6	532.2	523.5
150°	506.4	513.3	525.4	535.2	539.8	540.5	539.8	535.2	525.4	513.3	506.4
152.5°	492.1	497.4	507.2	514.8	517.1	517.8	517.1	514.8	507.2	497.4	492.1
155°	478.4	483.0	490.6	496.6	498.9	498.9	498.9	496.6	490.6	483.0	478.4
157.5°	465.6	469.4	475.4	480.0	481.5	481.5	481.5	480.0	475.4	469.4	465.6
160°	452.7	455.7	460.3	464.8	465.6	465.6	465.6	464.8	460.3	455.7	452.7
162.5°	440.2	442.9	445.9	450.4	451.2	450.4	451.2	450.4	445.9	442.9	440.2
165°	428.9	430.8	433.8	436.8	436.1	435.3	436.1	436.8	433.8	430.8	428.9
167.5°	419.0	420.2	421.7	423.9	423.9	423.2	423.9	423.9	421.7	420.2	419.0
170°	409.2	410.3	411.8	412.6	411.8	411.8	411.8	412.6	411.8	410.3	409.2
172.5°	400.4	401.2	402.0	402.7	402.0	400.5	402.0	402.7	402.0	401.2	400.4
175°	393.7	393.7	393.7	395.2	393.7	392.1	393.7	395.2	393.7	393.7	393.7
177.5°	388.8	389.1	388.4	389.1	387.6	386.1	387.6	389.1	388.4	389.1	388.8
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2	551.2
2.5°	518.3	521.1	518.3	520.1	521.1	523.3	524.3	528.4	529.7	532.9	532.9
5°	487.3	488.6	489.1	490.9	492.7	497.3	500.5	506.4	513.3	514.2	518.3
7.5°	462.2	464.4	468.1	466.7	469.9	476.8	480.9	488.2	495.0	498.7	503.7
10°	439.8	442.5	443.9	445.3	451.2	457.1	463.5	468.5	477.7	483.2	487.3
12.5°	421.5	419.2	422.0	427.0	433.8	437.5	446.2	453.9	460.8	466.7	470.4
15°	397.8	399.6	402.3	411.0	412.8	422.0	425.2	433.8	446.6	452.1	456.7
17.5°	374.9	380.9	386.3	389.5	395.0	402.3	411.5	421.1	429.3	435.7	441.1
20°	356.7	362.6	365.8	368.1	373.6	383.6	392.3	404.2	414.7	419.7	427.0
22.5°	342.0	342.0	346.6	353.5	356.7	366.2	373.6	386.3	397.8	404.2	411.0
25°	323.8	326.5	330.2	336.1	340.7	348.4	358.9	369.9	382.2	387.7	396.4
27.5°	308.7	311.9	316.9	318.3	322.9	329.7	340.7	352.5	365.3	371.3	378.6
30°	297.3	299.1	300.9	303.7	307.8	313.7	322.9	333.4	348.9	353.5	362.6
32.5°	287.2	288.2	289.1	291.4	293.6	299.6	306.9	318.3	331.1	337.9	346.2
35°	278.1	277.2	277.7	279.0	281.3	283.6	291.4	300.9	312.8	321.0	327.4
37.5°	269.4	267.6	267.2	267.2	268.1	270.8	276.7	285.0	297.7	304.6	311.0
40°	259.8	258.0	257.1	256.6	256.2	258.0	262.6	270.8	280.9	287.2	294.6
42.5°	250.7	248.9	246.6	246.1	245.2	246.1	249.3	257.1	265.8	272.2	278.1
45°	241.6	238.4	235.6	233.8	234.3	232.9	235.2	241.1	251.2	255.3	261.2
47.5°	231.5	227.9	224.2	222.4	220.6	221.5	222.4	227.4	236.1	240.2	246.1
50°	221.9	216.9	212.8	210.5	209.2	208.2	209.2	214.2	220.6	224.2	229.2
52.5°	211.0	206.0	201.8	198.2	196.4	195.0	195.5	200.0	206.0	209.6	214.6
55°	200.9	194.5	189.1	184.5	183.1	182.7	182.2	185.4	190.4	194.1	198.2
57.5°	189.5	183.1	177.2	171.7	169.0	168.5	168.5	169.4	175.8	178.6	180.8
60°	178.1	171.3	164.9	159.8	155.7	154.4	153.9	155.7	158.9	161.7	164.9
62.5°	165.3	158.5	150.7	146.1	142.0	138.4	139.7	140.2	144.8	146.1	148.9
65°	153.0	145.2	138.8	131.5	127.0	124.7	123.8	124.7	128.3	128.8	130.6
67.5°	138.8	131.5	123.8	118.7	114.6	110.5	109.6	109.6	111.4	112.8	115.1
70°	125.1	117.8	109.1	103.7	99.6	95.9	94.5	94.1	95.4	96.4	98.6
72.5°	109.1	101.8	95.4	89.5	84.5	81.7	80.4	79.5	80.8	81.7	82.2
75°	92.2	86.3	79.9	74.0	70.8	68.0	66.2	64.8	65.8	65.8	65.8
77.5°	76.3	70.3	65.3	61.2	57.1	53.9	52.5	51.1	51.6	51.6	52.5
80°	59.4	55.3	51.1	47.5	43.8	41.1	40.2	38.8	37.9	37.4	37.4
82.5°	43.8	40.6	37.0	33.8	32.0	29.2	28.3	26.5	26.5	26.0	26.0
85°	29.2	27.4	23.7	21.5	20.1	18.7	17.8	16.9	15.5	15.5	15.1
87.5°	15.5	14.6	13.7	11.0	11.0	9.6	9.1	8.7	7.3	7.8	7.8
90°	15.1	14.4	13.6	12.9	13.6	12.1	10.6	10.6	6.1	6.1	6.1
92.5°	107.5	136.3	182.4	246.8	296.8	259.7	188.5	115.1	68.1	58.3	48.5
95°	342.2	443.6	561.0	634.4	617.0	465.6	284.6	160.5	94.6	78.7	62.8
97.5°	666.2	749.5	807.8	795.7	660.1	445.9	259.7	152.9	100.7	87.1	73.4
100°	891.0	928.1	913.0	802.5	608.7	395.2	240.7	155.2	110.5	98.4	86.3
102.5°	1020.5	997.8	907.7	745.7	544.3	361.1	235.4	162.8	123.4	112.0	100.7
105°	1053.8	978.9	847.9	674.5	496.6	344.5	238.5	175.6	139.3	128.3	117.3
107.5°	1020.5	916.0	774.5	616.2	465.6	339.9	247.6	189.3	156.0	145.0	134.0
110°	950.1	840.3	709.3	574.6	451.2	341.4	258.2	205.2	171.8	161.6	151.4

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	875.9	773.7	661.7	551.1	444.4	346.0	269.5	220.3	188.5	178.3	168.1
115°	814.6	726.0	632.9	538.3	442.9	352.0	281.6	236.2	205.9	195.7	185.5
117.5°	766.9	695.0	616.2	531.4	442.1	358.1	293.7	251.3	222.6	212.0	201.4
120°	736.6	676.0	605.6	526.1	442.1	364.9	306.6	267.2	238.5	227.9	217.3
122.5°	717.7	663.9	596.5	520.1	441.4	371.7	318.7	282.4	253.6	243.4	233.2
125°	703.3	651.1	585.9	513.3	440.6	378.5	330.8	296.0	268.7	258.2	247.6
127.5°	688.9	636.7	573.8	504.2	439.1	383.8	341.4	308.9	282.4	271.8	261.2
130°	670.0	618.5	558.7	495.9	438.3	389.9	351.3	321.7	296.0	285.0	274.0
132.5°	648.0	598.1	542.8	488.3	437.6	395.2	361.1	332.3	306.6	296.4	286.2
135°	623.8	577.6	528.4	480.7	436.8	400.5	369.4	342.2	317.2	307.4	297.5
137.5°	598.1	557.9	514.8	473.9	436.8	403.5	375.5	349.8	326.3	316.8	307.4
140°	573.1	539.0	503.4	468.6	436.1	407.3	381.5	357.3	334.6	325.5	316.4
142.5°	551.1	523.1	492.8	464.1	436.1	410.3	386.1	364.1	342.2	333.5	324.8
145°	531.4	508.7	483.0	458.8	434.5	411.1	389.1	368.7	349.0	340.6	332.3
147.5°	514.8	495.9	474.7	454.2	432.3	411.8	392.1	374.0	355.1	347.5	339.9
150°	499.6	484.5	467.1	448.9	430.0	411.8	394.4	377.8	361.1	353.9	346.7
152.5°	486.8	473.2	458.8	442.9	426.2	410.3	395.9	380.8	366.4	360.0	353.5
155°	473.9	462.6	450.4	436.8	422.4	408.8	396.7	383.8	371.0	365.3	359.6
157.5°	461.8	452.0	441.4	430.8	418.6	407.3	396.7	386.1	374.7	370.2	365.7
160°	449.7	441.4	433.0	423.9	414.1	405.0	396.7	387.6	378.5	374.4	370.2
162.5°	437.6	431.5	424.7	417.9	409.6	402.7	396.7	389.1	380.8	377.8	374.7
165°	427.0	421.7	417.1	411.1	405.0	399.7	395.2	389.1	382.3	380.0	377.8
167.5°	417.9	413.3	409.6	405.0	400.5	396.7	393.7	389.1	383.8	381.9	380.0
170°	408.0	405.0	402.7	399.0	395.9	393.7	392.1	388.4	384.6	383.5	382.3
172.5°	399.7	398.2	396.7	393.7	391.4	390.6	390.6	387.6	385.3	384.6	383.8
175°	393.7	392.1	391.4	389.9	388.4	388.4	389.1	386.8	385.3	385.3	385.3
177.5°	388.4	388.4	387.6	386.8	386.1	386.1	387.6	386.1	385.3	385.3	385.3
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	551.2	551.2	551.2	551.2
2.5°	536.1	540.7	544.8	551.2
5°	524.3	530.7	539.3	548.9
7.5°	510.6	520.6	532.0	545.3
10°	497.8	509.2	523.8	539.8
12.5°	484.5	498.2	514.2	531.6
15°	469.5	483.2	501.0	524.3
17.5°	455.8	472.2	491.4	516.0
20°	439.8	455.3	476.3	504.6
22.5°	425.6	443.4	466.7	491.4
25°	410.1	425.6	448.9	478.6
27.5°	394.6	413.7	436.1	464.9
30°	379.5	395.5	419.7	449.8
32.5°	363.1	382.2	404.6	432.9
35°	345.2	363.5	384.5	415.1
37.5°	329.3	347.1	368.5	395.5
40°	311.4	330.2	349.8	376.8
42.5°	294.1	311.0	330.6	355.3
45°	277.2	291.8	309.6	331.1
47.5°	259.8	272.2	288.6	307.8
50°	241.1	254.4	266.7	282.7
52.5°	223.8	235.2	245.2	258.5
55°	206.9	214.6	222.9	232.9
57.5°	189.1	195.0	200.9	211.4
60°	171.3	176.7	179.9	186.8
62.5°	153.9	156.2	160.3	164.4
65°	134.7	137.9	140.2	145.2
67.5°	117.4	118.7	121.0	124.2
70°	99.1	102.3	103.2	105.5
72.5°	83.6	84.9	85.9	86.3
75°	66.2	67.6	68.5	71.2
77.5°	52.1	51.6	53.4	53.9
80°	38.4	37.0	37.4	39.3
82.5°	25.1	25.6	25.1	25.1
85°	15.5	15.1	14.2	14.6
87.5°	6.9	6.9	6.4	6.4
90°	5.3	4.5	2.3	0.8
92.5°	34.8	23.5	15.1	10.6
95°	44.7	34.8	27.3	25.0
97.5°	57.5	48.5	41.6	41.6
100°	71.9	62.8	57.5	57.5
102.5°	87.1	78.7	74.2	72.7
105°	103.7	94.6	90.8	88.6
107.5°	121.1	111.3	107.5	106.0
110°	137.8	128.7	124.9	123.4

TEST NUMBER: P1001342

CATALOG NUMBER: SA4XXDIP-B350D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	154.4	146.1	141.6	140.1
115°	171.1	163.5	158.2	156.0
117.5°	187.7	179.4	174.9	172.6
120°	204.4	196.1	190.8	189.3
122.5°	218.8	211.2	205.9	204.4
125°	233.2	224.8	220.3	217.3
127.5°	246.0	237.0	231.7	229.4
130°	259.7	248.3	242.3	239.2
132.5°	270.3	259.7	251.3	249.1
135°	281.6	268.7	261.2	258.2
137.5°	290.7	278.6	270.3	267.2
140°	300.5	287.7	279.3	277.1
142.5°	309.6	297.5	289.9	287.7
145°	318.0	307.4	299.8	297.5
147.5°	327.8	316.4	309.6	308.9
150°	335.4	326.3	320.2	319.5
152.5°	343.7	335.4	329.3	329.3
155°	351.3	343.7	339.2	338.4
157.5°	358.1	352.0	347.5	347.5
160°	364.1	358.8	355.8	355.8
162.5°	369.4	364.9	362.6	363.4
165°	374.0	370.2	368.7	368.7
167.5°	377.8	374.7	374.0	374.7
170°	380.8	378.5	377.8	378.5
172.5°	383.1	381.5	381.5	382.3
175°	384.6	383.8	383.8	384.6
177.5°	385.3	384.6	385.3	386.1
180°	385.3	385.3	385.3	385.3

(END OF REPORT)