

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001551

Luminaire Tested: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001551
REPORT IS A COMBINATION OF REPORTS P996173 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3874.0 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61
2	93	86	79	74	87	81	75	71	72	68	64	64	61	58	57	54	52
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	45
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24
9	53	41	33	28	50	39	32	27	35	30	25	32	27	24	29	25	22
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7660	7660	7660	7660
5°	7640	8788	7685	6603
10°	7584	10252	7641	5793
15°	7492	11819	7544	5183
20°	7395	12816	7449	4647
25°	7254	12669	7323	4252
30°	7116	10472	7202	4048
35°	6921	7803	6997	3924
40°	6694	5878	6759	3864
45°	6348	4718	6427	3781
50°	5934	3975	6020	3743
55°	5448	3459	5533	3699
60°	4976	3046	5121	3637
65°	4533	2621	4575	3486
70°	4011	2157	4098	3210
75°	3498	1657	3475	2726
80°	2751	1088	2719	2069
85°	1812	488	1696	1207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9904 cd/sqm

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	2.4
10°-20°	282.2	7.3
20°-30°	448.3	11.6
30°-40°	498.1	12.9
40°-50°	453.0	11.7
50°-60°	370.2	9.6
60°-70°	264.2	6.8
70°-80°	145.4	3.8
80°-90°	40.3	1.0
90°-100°	30.1	0.8
100°-110°	90.1	2.3
110°-120°	153.1	4.0
120°-130°	201.9	5.2
130°-140°	226.8	5.9
140°-150°	222.9	5.8
150°-160°	187.5	4.8
160°-170°	124.8	3.2
170°-180°	43.7	1.1
0°-30°	821.9	21.2
0°-40°	1320.0	34.1
0°-60°	2143.1	55.3
0°-90°	2593.0	66.9
90°-120°	273.3	7.1
90°-150°	925.0	23.9
90°-180°	1281.0	33.1
0°-180°	3874.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	939	939	939	939	939	
5°	935	1102	941	828	935	89
15°	893	1514	900	664	893	252
25°	816	1607	823	539	816	376
35°	707	950	715	478	707	442
45°	564	533	571	427	564	435
55°	397	349	403	373	397	357
65°	248	224	250	298	248	244
75°	121	112	121	184	121	127
85°	25	23	23	58	25	29
90°	1	11	1	11	1	3
95°	21	28	21	28	21	23
105°	83	87	83	87	83	88
115°	156	154	156	154	156	154
125°	227	225	227	225	227	202
135°	292	293	292	293	292	226
145°	355	356	355	356	355	222
155°	407	407	407	407	407	187
165°	443	442	443	442	443	125
175°	461	459	461	459	461	44
180°	462	462	462	462	462	

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	939.3	948.7	952.6	955.7	965.8	968.9	969.7	974.3	978.2	979.0	979.0
5°	935.4	950.2	961.9	972.8	989.1	996.1	1004.7	1014.0	1026.5	1034.3	1038.2
7.5°	929.2	951.0	968.9	987.6	1010.1	1024.2	1031.9	1056.8	1074.0	1088.0	1105.1
10°	919.9	947.9	973.6	1000.8	1032.7	1049.8	1067.0	1097.3	1121.4	1148.7	1170.5
12.5°	905.9	942.4	973.6	1011.7	1051.4	1071.6	1091.9	1144.8	1172.8	1196.9	1235.8
15°	893.4	930.0	974.3	1013.3	1062.3	1092.6	1122.2	1156.5	1200.8	1253.0	1290.3
17.5°	879.4	925.3	966.6	1021.0	1075.5	1104.3	1128.4	1181.4	1243.6	1295.0	1329.2
20°	859.9	906.6	961.1	1018.7	1083.3	1105.9	1137.8	1208.6	1264.6	1315.2	1371.2
22.5°	837.4	891.9	949.4	1004.7	1071.6	1119.1	1154.1	1216.4	1284.1	1342.4	1405.5
25°	815.6	874.7	925.3	1000.8	1071.6	1103.5	1143.2	1217.2	1291.1	1361.9	1426.5
27.5°	792.2	847.5	916.0	975.9	1056.1	1091.1	1133.9	1214.8	1293.4	1364.2	1433.5
30°	766.6	825.7	882.5	953.3	1031.2	1076.3	1116.0	1203.9	1284.1	1358.0	1422.6
32.5°	737.8	793.8	854.5	921.4	1003.1	1049.1	1098.9	1189.1	1274.7	1338.6	1388.4
35°	707.4	764.2	817.1	885.6	969.7	1015.6	1063.8	1163.5	1248.3	1300.4	1329.2
37.5°	673.9	727.6	779.8	847.5	931.5	980.6	1029.6	1126.1	1206.3	1249.8	1242.1
40°	642.0	690.3	738.5	802.4	890.3	942.4	985.2	1082.5	1152.6	1171.2	1145.6
42.5°	605.5	646.7	693.4	758.8	844.4	893.4	947.1	1035.8	1088.0	1080.2	1036.6
45°	564.2	600.8	647.5	709.0	796.1	846.7	891.9	975.9	1014.0	994.6	915.2
47.5°	524.5	560.3	598.5	659.9	744.8	787.6	833.5	909.0	930.8	889.5	810.1
50°	481.7	511.3	551.0	609.4	688.7	733.9	772.0	832.7	840.5	789.9	707.4
52.5°	440.5	465.4	503.5	561.1	635.0	670.8	708.2	761.9	755.7	703.5	624.1
55°	396.9	420.2	455.3	508.2	573.6	607.8	639.7	687.2	673.9	620.3	551.0
57.5°	360.3	376.7	410.9	459.9	513.6	551.0	578.2	615.6	595.3	541.6	477.1
60°	318.3	338.5	367.3	407.0	459.9	484.8	509.0	533.9	519.9	468.5	410.9
62.5°	280.2	295.7	320.6	358.8	400.0	422.6	448.3	463.8	449.8	402.3	354.1
65°	247.5	259.9	279.4	310.5	350.2	368.9	383.7	398.5	386.8	342.4	307.4
67.5°	211.7	222.6	238.9	263.8	297.3	310.5	324.5	334.6	321.4	291.8	257.6
70°	179.8	187.6	203.1	221.8	245.1	257.6	269.3	279.4	267.7	242.8	217.1
72.5°	147.1	153.3	167.3	180.5	201.6	210.1	218.7	226.5	222.6	199.2	178.2
75°	121.4	123.7	133.1	144.0	157.2	166.5	172.8	177.4	174.3	155.6	142.4
77.5°	91.8	94.9	101.9	110.5	122.2	127.6	131.5	136.2	132.3	117.5	108.2
80°	66.9	67.7	71.6	79.4	87.2	87.9	91.8	98.1	95.7	85.6	78.6
82.5°	42.8	45.1	46.7	51.4	56.8	58.4	60.7	62.3	61.5	55.3	52.9
85°	24.9	24.9	26.5	29.6	31.1	33.5	34.2	35.0	36.6	32.7	30.4
87.5°	10.9	11.7	11.7	12.5	14.0	14.0	14.8	15.6	16.3	15.6	13.2
90°	1.1	2.0	2.8	3.7	4.6	5.0	5.3	6.0	6.6	7.3	7.9
92.5°	9.3	10.3	11.3	12.4	13.4	13.9	14.1	14.5	14.9	15.3	15.7
95°	21.4	22.1	22.8	23.5	24.2	24.6	24.9	25.4	26.0	26.5	27.1
97.5°	34.3	34.9	35.5	36.2	36.8	37.1	37.4	38.1	38.7	39.4	40.0
100°	50.0	50.3	50.6	50.9	51.2	51.4	51.8	52.5	53.2	53.9	54.6
102.5°	66.4	66.5	66.6	66.7	66.8	66.8	67.1	67.7	68.4	69.0	69.6
105°	83.2	83.3	83.4	83.5	83.6	83.6	83.8	84.1	84.4	84.7	85.0
107.5°	100.7	100.8	100.8	100.9	101.0	101.0	101.0	101.1	101.2	101.3	101.4
110°	118.5	118.7	118.9	119.0	119.2	119.3	119.3	119.2	119.1	119.0	118.9

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	137.1	137.1	137.1	137.1	137.1	137.1	137.0	136.9	136.7	136.6	136.4
115°	155.7	155.7	155.7	155.7	155.7	155.7	155.6	155.5	155.3	155.2	155.0
117.5°	173.2	173.2	173.2	173.2	173.2	173.2	173.2	173.1	173.0	172.9	172.8
120°	190.7	191.0	191.3	191.6	191.9	192.1	192.0	191.7	191.5	191.2	191.0
122.5°	208.9	209.0	209.0	209.1	209.2	209.2	209.2	209.1	209.0	209.0	208.9
125°	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.6	226.5	226.5	226.4
127.5°	242.8	243.0	243.3	243.5	243.8	243.9	243.8	243.7	243.5	243.4	243.2
130°	259.9	260.1	260.4	260.6	260.9	261.0	261.0	261.0	261.0	261.0	261.0
132.5°	277.4	277.6	277.8	277.9	278.1	278.2	278.2	278.1	278.0	277.9	277.8
135°	292.4	292.9	293.4	293.9	294.4	294.6	294.6	294.6	294.6	294.6	294.6
137.5°	309.2	309.4	309.7	309.9	310.2	310.3	310.4	310.5	310.7	310.8	311.0
140°	326.0	326.2	326.3	326.5	326.6	326.7	326.7	326.7	326.7	326.7	326.7
142.5°	341.4	341.6	341.7	341.9	342.0	342.1	342.1	342.0	341.9	341.8	341.7
145°	355.3	355.6	355.9	356.2	356.5	356.7	356.7	356.8	356.9	357.0	357.1
147.5°	369.6	370.0	370.4	370.7	371.1	371.3	371.3	371.2	371.1	371.1	371.0
150°	382.4	382.7	383.0	383.3	383.6	383.8	383.8	383.8	383.8	383.8	383.8
152.5°	394.6	394.8	394.9	395.1	395.2	395.3	395.3	395.4	395.5	395.5	395.6
155°	407.1	407.1	407.1	407.1	407.1	407.1	407.1	407.0	406.9	406.8	406.7
157.5°	417.8	417.6	417.5	417.3	417.2	417.1	417.1	417.1	417.1	417.1	417.1
160°	427.1	427.0	426.9	426.8	426.7	426.7	426.7	426.6	426.5	426.4	426.3
162.5°	435.6	435.4	435.2	434.9	434.7	434.6	434.6	434.5	434.4	434.3	434.2
165°	443.1	442.9	442.6	442.4	442.1	442.0	441.9	441.8	441.6	441.5	441.3
167.5°	449.2	448.9	448.6	448.3	448.0	447.8	447.8	447.8	447.8	447.8	447.8
170°	454.2	453.8	453.4	453.0	452.6	452.4	452.4	452.5	452.6	452.7	452.8
172.5°	457.8	457.5	457.1	456.8	456.5	456.3	456.3	456.3	456.3	456.3	456.3
175°	461.0	460.6	460.2	459.8	459.4	459.2	459.2	459.1	459.0	458.9	458.8
177.5°	462.4	462.0	461.6	461.2	460.8	460.6	460.6	460.6	460.6	460.6	460.6
180°	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	981.3	995.4	1001.6	1003.1	1011.7	1006.3	1008.6	1007.8	1014.0	1014.8	1014.8
5°	1052.9	1069.3	1074.7	1082.5	1094.2	1097.3	1095.0	1099.6	1108.2	1102.0	1111.3
7.5°	1128.4	1146.3	1158.8	1175.9	1179.8	1189.9	1196.1	1201.6	1203.1	1203.9	1205.5
10°	1198.5	1221.0	1238.2	1267.0	1273.2	1278.6	1305.9	1295.0	1309.0	1304.3	1305.9
12.5°	1255.3	1299.6	1313.7	1361.9	1366.6	1385.3	1383.7	1400.8	1403.9	1410.2	1403.9
15°	1330.0	1381.4	1403.9	1431.2	1446.7	1468.5	1472.4	1495.8	1505.1	1513.7	1505.1
17.5°	1398.5	1425.7	1483.3	1505.1	1515.2	1526.9	1556.5	1565.0	1579.0	1573.6	1589.1
20°	1432.7	1471.6	1532.3	1569.7	1585.3	1596.2	1621.1	1634.3	1639.7	1639.7	1641.3
22.5°	1463.1	1519.1	1564.2	1607.0	1621.1	1628.8	1643.6	1653.7	1656.1	1657.6	1659.2
25°	1490.3	1540.9	1577.5	1601.6	1607.0	1607.0	1615.6	1609.4	1599.3	1607.0	1611.7
27.5°	1490.3	1526.1	1542.5	1551.0	1551.0	1530.0	1517.6	1491.9	1470.1	1463.9	1477.9
30°	1465.4	1481.8	1459.2	1438.2	1421.8	1407.8	1358.8	1319.9	1312.1	1306.7	1327.7
32.5°	1407.8	1386.8	1342.4	1281.7	1257.6	1225.7	1187.6	1158.0	1140.1	1133.9	1129.2
35°	1305.9	1251.4	1193.8	1112.1	1095.0	1054.5	1002.4	980.6	951.0	950.2	960.3
37.5°	1194.6	1110.5	1048.3	970.5	946.3	903.5	854.5	831.9	811.7	796.1	814.8
40°	1064.6	991.5	896.5	832.7	798.5	775.9	734.7	709.7	700.4	692.6	704.3
42.5°	943.2	863.1	789.1	723.8	695.7	670.1	642.8	618.7	611.7	610.9	619.5
45°	822.6	744.0	675.5	619.5	601.6	586.0	559.5	552.5	540.9	533.1	537.0
47.5°	726.1	645.2	588.3	545.5	530.0	516.7	499.6	488.0	477.8	474.7	479.4
50°	631.1	576.7	518.3	482.5	470.8	458.4	445.1	434.3	429.6	426.5	429.6
52.5°	554.9	496.5	456.8	428.0	416.4	407.0	397.7	393.0	386.8	388.3	391.5
55°	486.4	435.0	401.6	380.6	373.6	369.7	358.0	352.5	350.2	348.6	350.2
57.5°	421.8	384.4	359.5	341.6	332.3	330.0	320.6	320.6	318.3	316.0	316.7
60°	370.4	338.5	314.4	300.4	298.8	294.9	288.7	287.9	282.5	284.8	285.6
62.5°	318.3	292.6	276.3	267.7	262.3	260.7	256.8	256.0	253.7	254.5	252.9
65°	277.1	256.0	239.7	232.7	230.4	229.6	226.5	224.1	222.6	224.1	222.6
67.5°	235.8	221.8	209.3	202.3	199.2	198.4	196.1	194.6	195.3	193.0	194.6
70°	196.9	182.9	175.1	171.2	169.7	167.3	167.3	167.3	167.3	165.8	165.0
72.5°	165.8	151.8	146.3	144.0	142.4	141.6	139.3	140.1	139.3	138.5	141.6
75°	131.5	123.0	117.5	115.2	116.7	114.4	112.1	113.6	111.3	112.1	115.2
77.5°	99.6	95.7	92.6	91.1	89.5	87.9	87.9	86.4	86.4	86.4	86.4
80°	72.4	71.6	66.1	65.4	65.4	63.8	63.8	63.8	63.8	63.0	63.8
82.5°	48.3	47.5	45.9	45.1	43.6	44.4	44.4	42.8	42.8	42.0	42.8
85°	28.0	28.0	26.5	25.7	24.9	25.7	24.1	23.3	24.1	23.3	24.1
87.5°	13.2	11.7	12.5	11.7	10.1	10.9	9.3	10.1	9.3	8.6	10.1
90°	8.4	8.8	9.3	9.8	10.0	10.1	10.2	10.4	10.5	10.7	10.5
92.5°	15.9	16.2	16.4	16.7	16.8	16.8	16.9	17.0	17.0	17.1	17.0
95°	27.3	27.6	27.8	28.1	28.2	28.2	28.2	28.2	28.2	28.2	28.2
97.5°	40.3	40.6	40.9	41.2	41.4	41.4	41.4	41.4	41.4	41.4	41.4
100°	54.8	54.9	55.1	55.2	55.3	55.3	55.3	55.3	55.3	55.3	55.3
102.5°	69.8	70.1	70.3	70.6	70.7	70.7	70.8	70.9	71.0	71.1	71.0
105°	85.2	85.5	85.7	86.0	86.1	86.2	86.4	86.7	86.9	87.1	86.9
107.5°	101.7	102.0	102.3	102.6	102.8	102.8	102.7	102.6	102.6	102.5	102.6
110°	118.7	118.6	118.4	118.3	118.2	118.3	118.6	118.8	119.1	119.3	119.1

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4
115°	154.9	154.8	154.7	154.6	154.6	154.6	154.5	154.4	154.4	154.3	154.4
117.5°	172.6	172.3	172.1	171.8	171.7	171.6	171.4	171.1	170.9	170.7	170.9
120°	190.6	190.2	189.8	189.4	189.2	189.3	189.5	189.6	189.8	190.0	189.8
122.5°	208.7	208.4	208.2	207.9	207.8	207.6	207.2	206.8	206.4	206.0	206.4
125°	226.2	226.1	225.9	225.8	225.7	225.6	225.5	225.3	225.2	225.0	225.2
127.5°	243.0	242.8	242.7	242.5	242.4	242.4	242.3	242.2	242.2	242.1	242.2
130°	260.8	260.7	260.5	260.4	260.3	260.1	259.8	259.5	259.2	258.9	259.2
132.5°	277.6	277.5	277.3	277.2	277.1	277.1	277.0	276.9	276.8	276.7	276.8
135°	294.4	294.3	294.1	294.0	293.9	293.8	293.5	293.3	293.0	292.8	293.0
137.5°	310.8	310.5	310.3	310.0	309.9	309.9	310.0	310.1	310.2	310.3	310.2
140°	326.6	326.6	326.5	326.4	326.4	326.4	326.3	326.2	326.1	326.0	326.1
142.5°	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7
145°	357.0	356.9	356.8	356.7	356.7	356.6	356.3	356.1	355.8	355.6	355.8
147.5°	370.9	370.8	370.7	370.6	370.6	370.6	370.5	370.4	370.4	370.3	370.4
150°	383.8	383.8	383.8	383.8	383.8	383.8	383.7	383.6	383.6	383.5	383.6
152.5°	395.8	396.1	396.3	396.6	396.7	396.6	396.3	396.1	395.8	395.6	395.8
155°	407.0	407.3	407.6	407.9	408.1	407.9	407.6	407.3	407.0	406.7	407.0
157.5°	417.3	417.5	417.8	418.0	418.1	418.0	417.8	417.5	417.3	417.1	417.3
160°	426.5	426.8	427.0	427.3	427.4	427.2	426.8	426.4	426.0	425.6	426.0
162.5°	434.7	435.1	435.6	436.1	436.3	436.1	435.7	435.4	435.0	434.6	435.0
165°	441.8	442.3	442.8	443.3	443.5	443.3	443.0	442.7	442.3	442.0	442.3
167.5°	448.3	448.7	449.2	449.7	449.9	449.7	449.2	448.7	448.3	447.8	448.3
170°	453.3	453.7	454.2	454.7	454.9	454.6	454.1	453.5	453.0	452.4	453.0
172.5°	456.9	457.4	458.0	458.5	458.8	458.5	458.0	457.4	456.9	456.3	456.9
175°	459.4	459.9	460.5	461.0	461.3	461.0	460.5	459.9	459.4	458.8	459.4
177.5°	461.2	461.7	462.3	462.8	463.1	462.8	462.2	461.5	460.9	460.3	460.9
180°	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	1013.3	1010.9	1007.8	1007.8	1003.9	1003.9	997.7	986.8	977.5	974.3	975.9
5°	1099.6	1100.4	1095.7	1091.9	1084.9	1079.4	1069.3	1049.8	1043.6	1031.2	1022.6
7.5°	1198.5	1195.4	1186.8	1180.6	1179.0	1166.6	1144.8	1121.4	1102.8	1090.3	1072.4
10°	1309.8	1297.3	1284.9	1281.0	1271.6	1250.6	1225.7	1200.0	1174.4	1147.1	1116.8
12.5°	1403.2	1379.0	1378.2	1368.9	1351.0	1339.3	1309.8	1273.2	1228.8	1198.5	1164.2
15°	1503.5	1481.0	1462.3	1445.2	1436.6	1402.4	1377.5	1331.6	1278.6	1245.9	1222.6
17.5°	1575.1	1565.0	1533.1	1525.3	1513.7	1474.0	1434.3	1389.1	1343.2	1297.3	1234.3
20°	1632.7	1626.5	1605.5	1594.6	1575.9	1544.8	1496.5	1444.4	1391.5	1326.1	1267.0
22.5°	1657.6	1649.9	1632.7	1623.4	1611.7	1585.3	1544.0	1484.9	1415.6	1357.2	1294.2
25°	1608.6	1622.6	1617.9	1614.1	1609.4	1593.8	1562.7	1510.5	1442.8	1376.7	1298.1
27.5°	1498.1	1522.2	1545.6	1548.7	1556.5	1562.7	1550.2	1512.9	1456.1	1386.0	1299.6
30°	1349.5	1360.3	1407.8	1421.8	1432.7	1472.4	1495.8	1486.4	1442.8	1379.8	1300.4
32.5°	1158.8	1187.6	1235.8	1269.3	1298.9	1343.2	1403.9	1428.1	1412.5	1361.1	1282.5
35°	978.2	1012.5	1068.5	1111.3	1140.9	1203.9	1275.5	1327.7	1347.1	1321.4	1251.4
37.5°	830.4	871.6	921.4	937.8	972.0	1049.8	1148.7	1221.0	1268.5	1270.9	1216.4
40°	719.1	740.1	779.8	804.7	838.2	903.5	1000.0	1095.7	1167.3	1191.5	1162.7
42.5°	624.9	641.3	670.8	701.2	731.5	781.3	870.1	959.6	1056.1	1104.3	1103.5
45°	550.2	567.3	587.6	612.5	633.5	687.2	757.2	849.1	932.3	1007.0	1025.7
47.5°	484.8	499.6	524.5	535.4	549.4	600.0	660.7	746.3	832.7	918.3	940.1
50°	436.6	449.0	466.2	473.2	488.7	526.1	575.9	645.2	740.9	819.5	859.9
52.5°	393.0	402.3	415.6	421.0	431.9	459.9	505.1	559.5	638.9	719.9	776.7
55°	355.7	361.9	371.2	377.4	385.2	410.1	443.6	492.6	561.1	631.1	686.4
57.5°	320.6	325.3	334.6	337.8	344.0	363.4	386.8	428.0	491.1	553.3	607.0
60°	287.9	291.1	296.5	303.5	308.2	321.4	343.2	377.4	428.0	484.8	528.4
62.5°	256.8	261.5	263.0	266.2	270.0	282.5	299.6	324.5	368.9	415.6	461.5
65°	224.9	228.8	231.9	232.7	236.6	245.9	261.5	283.3	312.1	352.5	395.3
67.5°	195.3	197.7	199.2	202.3	206.2	210.9	223.4	239.7	266.2	298.8	333.1
70°	168.1	168.1	170.4	171.2	175.9	181.3	186.8	202.3	225.7	252.1	275.5
72.5°	138.5	142.4	141.6	145.5	144.8	148.6	155.6	165.8	182.9	203.9	226.5
75°	112.8	115.2	115.2	115.2	116.7	119.8	123.7	133.1	146.3	163.4	176.7
77.5°	87.9	89.5	89.5	89.5	90.3	93.4	97.3	103.5	112.8	123.0	130.7
80°	63.0	64.6	64.6	66.1	66.1	66.9	70.8	73.9	78.6	86.4	94.2
82.5°	42.8	43.6	45.1	45.1	44.4	45.9	46.7	49.8	54.5	56.0	61.5
85°	23.3	24.1	24.9	24.9	25.7	27.2	26.5	29.6	29.6	32.7	34.2
87.5°	9.3	10.9	10.9	10.1	10.9	10.9	10.9	12.5	13.2	14.0	13.2
90°	10.4	10.2	10.1	10.0	9.8	9.3	8.8	8.4	7.9	7.3	6.6
92.5°	17.0	16.9	16.8	16.8	16.7	16.4	16.2	15.9	15.7	15.3	14.9
95°	28.2	28.2	28.2	28.2	28.1	27.8	27.6	27.3	27.1	26.5	26.0
97.5°	41.4	41.4	41.4	41.4	41.2	40.9	40.6	40.3	40.0	39.4	38.7
100°	55.3	55.3	55.3	55.3	55.2	55.1	54.9	54.8	54.6	53.9	53.2
102.5°	70.9	70.8	70.7	70.7	70.6	70.3	70.1	69.8	69.6	69.0	68.4
105°	86.7	86.4	86.2	86.1	86.0	85.7	85.5	85.2	85.0	84.7	84.4
107.5°	102.6	102.7	102.8	102.8	102.6	102.3	102.0	101.7	101.4	101.3	101.2
110°	118.8	118.6	118.3	118.2	118.3	118.4	118.6	118.7	118.9	119.0	119.1

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.6	136.7
115°	154.4	154.5	154.6	154.6	154.6	154.7	154.8	154.9	155.0	155.2	155.3
117.5°	171.1	171.4	171.6	171.7	171.8	172.1	172.3	172.6	172.8	172.9	173.0
120°	189.6	189.5	189.3	189.2	189.4	189.8	190.2	190.6	191.0	191.2	191.5
122.5°	206.8	207.2	207.6	207.8	207.9	208.2	208.4	208.7	208.9	209.0	209.0
125°	225.3	225.5	225.6	225.7	225.8	225.9	226.1	226.2	226.4	226.5	226.5
127.5°	242.2	242.3	242.4	242.4	242.5	242.7	242.8	243.0	243.2	243.4	243.5
130°	259.5	259.8	260.1	260.3	260.4	260.5	260.7	260.8	261.0	261.0	261.0
132.5°	276.9	277.0	277.1	277.1	277.2	277.3	277.5	277.6	277.8	277.9	278.0
135°	293.3	293.5	293.8	293.9	294.0	294.1	294.3	294.4	294.6	294.6	294.6
137.5°	310.1	310.0	309.9	309.9	310.0	310.3	310.5	310.8	311.0	310.8	310.7
140°	326.2	326.3	326.4	326.4	326.4	326.5	326.6	326.6	326.7	326.7	326.7
142.5°	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.8	341.9
145°	356.1	356.3	356.6	356.7	356.7	356.8	356.9	357.0	357.1	357.0	356.9
147.5°	370.4	370.5	370.6	370.6	370.6	370.7	370.8	370.9	371.0	371.1	371.1
150°	383.6	383.7	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
152.5°	396.1	396.3	396.6	396.7	396.6	396.3	396.1	395.8	395.6	395.5	395.5
155°	407.3	407.6	407.9	408.1	407.9	407.6	407.3	407.0	406.7	406.8	406.9
157.5°	417.5	417.8	418.0	418.1	418.0	417.8	417.5	417.3	417.1	417.1	417.1
160°	426.4	426.8	427.2	427.4	427.3	427.0	426.8	426.5	426.3	426.4	426.5
162.5°	435.4	435.7	436.1	436.3	436.1	435.6	435.1	434.7	434.2	434.3	434.4
165°	442.7	443.0	443.3	443.5	443.3	442.8	442.3	441.8	441.3	441.5	441.6
167.5°	448.7	449.2	449.7	449.9	449.7	449.2	448.7	448.3	447.8	447.8	447.8
170°	453.5	454.1	454.6	454.9	454.7	454.2	453.7	453.3	452.8	452.7	452.6
172.5°	457.4	458.0	458.5	458.8	458.5	458.0	457.4	456.9	456.3	456.3	456.3
175°	459.9	460.5	461.0	461.3	461.0	460.5	459.9	459.4	458.8	458.9	459.0
177.5°	461.5	462.2	462.8	463.1	462.8	462.3	461.7	461.2	460.6	460.6	460.6
180°	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	968.9	965.8	963.5	963.5	956.4	949.4	945.6	944.0	942.4	936.2	927.7
5°	1008.6	998.5	991.5	984.5	972.8	960.3	947.9	940.9	930.8	916.8	906.6
7.5°	1052.9	1028.8	1021.0	1012.5	989.1	968.1	951.0	936.2	919.9	902.0	884.1
10°	1090.3	1064.6	1047.5	1032.7	1002.4	974.3	948.7	926.9	905.9	882.5	860.7
12.5°	1126.1	1089.5	1071.6	1049.8	1017.9	977.5	944.0	916.8	885.6	861.5	835.0
15°	1175.9	1114.4	1084.9	1070.8	1028.0	980.6	940.1	899.6	874.0	837.4	814.0
17.5°	1183.7	1133.9	1114.4	1078.6	1027.3	973.6	926.9	886.4	847.5	814.8	784.5
20°	1210.9	1145.6	1114.4	1091.9	1024.2	969.7	918.3	866.2	828.8	793.8	759.6
22.5°	1228.0	1154.1	1121.4	1085.6	1021.0	955.7	895.0	849.8	803.9	768.1	740.9
25°	1223.4	1149.4	1112.9	1079.4	1000.8	935.4	881.0	823.4	780.6	741.7	705.9
27.5°	1221.0	1137.8	1098.9	1061.5	987.6	919.1	850.6	803.9	756.4	711.3	684.8
30°	1214.8	1123.0	1077.9	1037.4	960.3	888.7	830.4	775.9	728.4	687.2	652.2
32.5°	1193.8	1098.1	1054.5	1010.9	930.8	859.2	800.0	749.4	702.0	659.2	625.7
35°	1165.8	1068.5	1021.0	975.1	895.0	822.6	768.1	715.2	670.8	629.6	597.7
37.5°	1137.8	1034.3	989.9	937.0	863.1	787.6	731.5	684.1	642.8	600.0	565.0
40°	1097.3	993.8	944.8	899.6	813.3	742.4	691.1	648.3	607.8	567.3	537.8
42.5°	1042.1	949.4	898.9	849.1	768.1	698.1	648.3	610.1	572.0	538.5	505.9
45°	986.0	895.7	850.6	806.2	718.3	652.2	606.2	571.2	539.3	502.7	476.3
47.5°	918.3	842.0	796.9	753.3	670.1	603.9	561.9	529.2	499.6	469.3	444.4
50°	849.1	782.9	741.7	696.5	617.1	557.2	516.0	488.7	464.6	435.8	415.6
52.5°	774.3	716.8	681.7	638.1	568.1	512.9	470.8	443.6	423.4	402.3	384.4
55°	695.0	652.9	615.6	580.6	514.4	464.6	427.2	403.1	389.1	369.7	354.1
57.5°	623.4	582.9	560.3	520.6	463.0	414.0	384.4	364.2	347.9	336.2	323.7
60°	548.7	516.0	491.1	462.3	411.7	370.4	339.3	327.6	310.5	302.0	296.5
62.5°	477.1	453.7	430.4	408.6	363.4	324.5	301.2	286.4	276.3	267.7	263.0
65°	409.3	387.6	371.2	351.8	314.4	283.3	261.5	249.8	239.7	237.4	231.9
67.5°	343.2	333.9	316.0	300.4	268.5	244.4	228.0	213.2	207.8	205.5	200.8
70°	287.2	276.3	262.3	249.0	224.9	203.9	189.1	183.7	175.9	175.1	169.7
72.5°	236.6	223.4	213.2	203.1	185.2	166.5	158.8	151.0	147.1	144.0	141.6
75°	187.6	178.2	171.2	162.7	147.1	134.6	123.7	120.6	118.3	117.5	116.0
77.5°	140.1	133.9	130.7	122.2	111.3	100.4	95.7	91.1	91.1	89.5	90.3
80°	99.6	95.7	91.8	87.2	77.8	73.2	69.3	66.1	64.6	63.8	64.6
82.5°	63.0	60.7	59.9	56.8	50.6	48.3	45.1	42.8	42.8	42.8	42.8
85°	35.0	35.0	35.0	30.4	28.0	25.7	24.1	23.3	23.3	23.3	24.1
87.5°	14.8	14.8	12.5	12.5	11.7	10.1	9.3	9.3	10.1	10.1	10.9
90°	6.0	5.3	5.0	4.6	3.7	2.8	2.0	1.1	2.0	2.8	3.7
92.5°	14.5	14.1	13.9	13.4	12.4	11.3	10.3	9.3	10.3	11.3	12.4
95°	25.4	24.9	24.6	24.2	23.5	22.8	22.1	21.4	22.1	22.8	23.5
97.5°	38.1	37.4	37.1	36.8	36.2	35.5	34.9	34.3	34.9	35.5	36.2
100°	52.5	51.8	51.4	51.2	50.9	50.6	50.3	50.0	50.3	50.6	50.9
102.5°	67.7	67.1	66.8	66.8	66.7	66.6	66.5	66.4	66.5	66.6	66.7
105°	84.1	83.8	83.6	83.6	83.5	83.4	83.3	83.2	83.3	83.4	83.5
107.5°	101.1	101.0	101.0	101.0	100.9	100.8	100.8	100.7	100.8	100.8	100.9
110°	119.2	119.3	119.3	119.2	119.0	118.9	118.7	118.5	118.7	118.9	119.0

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	136.9	137.0	137.1	137.1	137.1	137.1	137.1	137.1	137.1	137.1	137.1
115°	155.5	155.6	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7
117.5°	173.1	173.2	173.2	173.2	173.2	173.2	173.2	173.2	173.2	173.2	173.2
120°	191.7	192.0	192.1	191.9	191.6	191.3	191.0	190.7	191.0	191.3	191.6
122.5°	209.1	209.2	209.2	209.2	209.1	209.0	209.0	208.9	209.0	209.0	209.1
125°	226.6	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7
127.5°	243.7	243.8	243.9	243.8	243.5	243.3	243.0	242.8	243.0	243.3	243.5
130°	261.0	261.0	261.0	260.9	260.6	260.4	260.1	259.9	260.1	260.4	260.6
132.5°	278.1	278.2	278.2	278.1	277.9	277.8	277.6	277.4	277.6	277.8	277.9
135°	294.6	294.6	294.6	294.4	293.9	293.4	292.9	292.4	292.9	293.4	293.9
137.5°	310.5	310.4	310.3	310.2	309.9	309.7	309.4	309.2	309.4	309.7	309.9
140°	326.7	326.7	326.7	326.6	326.5	326.3	326.2	326.0	326.2	326.3	326.5
142.5°	342.0	342.1	342.1	342.0	341.9	341.7	341.6	341.4	341.6	341.7	341.9
145°	356.8	356.7	356.7	356.5	356.2	355.9	355.6	355.3	355.6	355.9	356.2
147.5°	371.2	371.3	371.3	371.1	370.7	370.4	370.0	369.6	370.0	370.4	370.7
150°	383.8	383.8	383.8	383.6	383.3	383.0	382.7	382.4	382.7	383.0	383.3
152.5°	395.4	395.3	395.3	395.2	395.1	394.9	394.8	394.6	394.8	394.9	395.1
155°	407.0	407.1	407.1	407.1	407.1	407.1	407.1	407.1	407.1	407.1	407.1
157.5°	417.1	417.1	417.1	417.2	417.3	417.5	417.6	417.8	417.6	417.5	417.3
160°	426.6	426.7	426.7	426.7	426.8	426.9	427.0	427.1	427.0	426.9	426.8
162.5°	434.5	434.6	434.6	434.7	434.9	435.2	435.4	435.6	435.4	435.2	434.9
165°	441.8	441.9	442.0	442.1	442.4	442.6	442.9	443.1	442.9	442.6	442.4
167.5°	447.8	447.8	447.8	448.0	448.3	448.6	448.9	449.2	448.9	448.6	448.3
170°	452.5	452.4	452.4	452.6	453.0	453.4	453.8	454.2	453.8	453.4	453.0
172.5°	456.3	456.3	456.3	456.5	456.8	457.1	457.5	457.8	457.5	457.1	456.8
175°	459.1	459.2	459.2	459.4	459.8	460.2	460.6	461.0	460.6	460.2	459.8
177.5°	460.6	460.6	460.6	460.8	461.2	461.6	462.0	462.4	462.0	461.6	461.2
180°	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	925.3	922.2	923.8	916.0	909.0	898.9	890.3	888.7	887.2	891.9	888.7
5°	898.9	895.0	891.1	881.7	867.7	859.2	846.7	845.9	841.3	834.3	835.8
7.5°	870.1	867.7	862.3	847.5	835.0	820.3	810.1	801.6	797.7	791.5	789.1
10°	846.7	838.2	833.5	817.1	802.4	786.8	773.6	767.3	760.3	754.9	751.0
12.5°	814.8	812.5	799.2	786.0	773.6	755.7	745.5	727.6	718.3	723.0	721.4
15°	793.8	782.9	779.8	761.1	740.1	728.4	709.7	698.1	694.2	687.2	678.6
17.5°	765.8	758.8	747.9	730.8	706.6	690.3	677.1	666.2	661.5	652.2	645.2
20°	739.3	727.6	719.1	703.5	680.2	659.2	642.8	635.8	624.1	616.4	612.5
22.5°	715.2	706.6	694.2	670.8	650.6	630.4	610.9	600.8	589.9	585.2	579.0
25°	685.6	671.6	663.1	637.4	615.6	599.2	581.3	568.1	561.9	554.1	552.5
27.5°	656.8	643.6	633.5	610.9	584.5	563.4	552.5	543.2	532.3	532.3	528.4
30°	628.0	618.7	603.1	581.3	556.4	536.2	523.7	515.2	511.3	508.2	507.4
32.5°	599.2	586.8	577.4	547.9	529.2	510.5	501.2	494.2	489.5	488.7	489.5
35°	569.7	555.7	546.3	519.9	501.2	484.1	480.2	473.9	471.6	470.8	474.7
37.5°	538.5	527.6	516.0	494.2	473.2	463.0	455.3	452.9	452.2	456.8	458.4
40°	509.7	500.4	489.5	466.2	450.6	439.7	435.8	433.5	436.6	441.3	443.6
42.5°	482.5	469.3	460.7	439.7	425.7	419.5	414.8	414.8	417.9	423.4	427.2
45°	453.7	443.6	435.0	416.4	403.9	396.9	396.1	396.9	400.8	404.7	409.3
47.5°	425.7	415.6	406.2	390.7	379.8	375.9	375.1	375.9	382.1	387.6	393.0
50°	400.0	389.1	380.6	365.8	357.2	352.5	353.3	357.2	361.9	369.7	376.7
52.5°	369.7	361.9	354.1	340.9	333.1	330.0	332.3	335.4	344.0	349.4	358.0
55°	340.1	333.1	326.9	316.7	310.5	308.2	309.7	314.4	321.4	330.7	340.9
57.5°	312.8	305.1	298.8	291.8	284.8	285.6	286.4	292.6	301.2	309.7	321.4
60°	282.5	277.8	272.4	263.8	260.7	260.7	263.0	270.0	277.8	291.8	302.0
62.5°	255.3	249.0	245.1	239.7	235.0	235.8	241.3	247.5	256.8	268.5	281.7
65°	227.2	220.2	217.1	212.5	210.9	211.7	215.6	224.9	235.0	245.1	257.6
67.5°	196.1	193.8	190.7	186.0	187.6	188.3	192.2	200.0	210.9	221.0	235.0
70°	169.7	165.0	164.2	160.3	160.3	162.7	170.4	175.9	186.0	196.9	211.7
72.5°	141.6	137.7	137.7	134.6	137.0	139.3	143.2	151.0	160.3	171.2	183.7
75°	112.8	111.3	112.8	111.3	111.3	115.2	119.8	126.1	136.2	147.9	158.0
77.5°	87.2	87.2	86.4	88.7	88.7	91.1	97.3	103.5	111.3	120.6	131.5
80°	63.8	63.8	63.8	66.1	68.5	68.5	72.4	80.2	87.2	93.4	103.5
82.5°	43.6	43.6	43.6	45.1	48.3	48.3	52.9	57.6	65.4	70.8	75.5
85°	26.5	26.5	25.7	27.2	28.0	30.4	34.2	37.4	41.2	45.9	50.6
87.5°	11.7	11.7	12.5	13.2	14.0	15.6	17.1	18.7	22.6	24.1	26.5
90°	4.6	5.0	5.3	6.0	6.6	7.3	7.9	8.4	8.8	9.3	9.8
92.5°	13.4	13.9	14.1	14.5	14.9	15.3	15.7	15.9	16.2	16.4	16.7
95°	24.2	24.6	24.9	25.4	26.0	26.5	27.1	27.3	27.6	27.8	28.1
97.5°	36.8	37.1	37.4	38.1	38.7	39.4	40.0	40.3	40.6	40.9	41.2
100°	51.2	51.4	51.8	52.5	53.2	53.9	54.6	54.8	54.9	55.1	55.2
102.5°	66.8	66.8	67.1	67.7	68.4	69.0	69.6	69.8	70.1	70.3	70.6
105°	83.6	83.6	83.8	84.1	84.4	84.7	85.0	85.2	85.5	85.7	86.0
107.5°	101.0	101.0	101.0	101.1	101.2	101.3	101.4	101.7	102.0	102.3	102.6
110°	119.2	119.3	119.3	119.2	119.1	119.0	118.9	118.7	118.6	118.4	118.3

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	137.1	137.1	137.0	136.9	136.7	136.6	136.4	136.4	136.4	136.4	136.4
115°	155.7	155.7	155.6	155.5	155.3	155.2	155.0	154.9	154.8	154.7	154.6
117.5°	173.2	173.2	173.2	173.1	173.0	172.9	172.8	172.6	172.3	172.1	171.8
120°	191.9	192.1	192.0	191.7	191.5	191.2	191.0	190.6	190.2	189.8	189.4
122.5°	209.2	209.2	209.2	209.1	209.0	209.0	208.9	208.7	208.4	208.2	207.9
125°	226.7	226.7	226.7	226.6	226.5	226.5	226.4	226.2	226.1	225.9	225.8
127.5°	243.8	243.9	243.8	243.7	243.5	243.4	243.2	243.0	242.8	242.7	242.5
130°	260.9	261.0	261.0	261.0	261.0	261.0	261.0	260.8	260.7	260.5	260.4
132.5°	278.1	278.2	278.2	278.1	278.0	277.9	277.8	277.6	277.5	277.3	277.2
135°	294.4	294.6	294.6	294.6	294.6	294.6	294.6	294.4	294.3	294.1	294.0
137.5°	310.2	310.3	310.4	310.5	310.7	310.8	311.0	310.8	310.5	310.3	310.0
140°	326.6	326.7	326.7	326.7	326.7	326.7	326.7	326.6	326.6	326.5	326.4
142.5°	342.0	342.1	342.1	342.0	341.9	341.8	341.7	341.7	341.7	341.7	341.7
145°	356.5	356.7	356.7	356.8	356.9	357.0	357.1	357.0	356.9	356.8	356.7
147.5°	371.1	371.3	371.3	371.2	371.1	371.1	371.0	370.9	370.8	370.7	370.6
150°	383.6	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
152.5°	395.2	395.3	395.3	395.4	395.5	395.5	395.6	395.8	396.1	396.3	396.6
155°	407.1	407.1	407.1	407.0	406.9	406.8	406.7	407.0	407.3	407.6	407.9
157.5°	417.2	417.1	417.1	417.1	417.1	417.1	417.1	417.3	417.5	417.8	418.0
160°	426.7	426.7	426.7	426.6	426.5	426.4	426.3	426.5	426.8	427.0	427.3
162.5°	434.7	434.6	434.6	434.5	434.4	434.3	434.2	434.7	435.1	435.6	436.1
165°	442.1	442.0	441.9	441.8	441.6	441.5	441.3	441.8	442.3	442.8	443.3
167.5°	448.0	447.8	447.8	447.8	447.8	447.8	447.8	448.3	448.7	449.2	449.7
170°	452.6	452.4	452.4	452.5	452.6	452.7	452.8	453.3	453.7	454.2	454.7
172.5°	456.5	456.3	456.3	456.3	456.3	456.3	456.3	456.9	457.4	458.0	458.5
175°	459.4	459.2	459.2	459.1	459.0	458.9	458.8	459.4	459.9	460.5	461.0
177.5°	460.8	460.6	460.6	460.6	460.6	460.6	460.6	461.2	461.7	462.3	462.8
180°	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	886.4	885.6	881.7	883.3	878.6	880.2	882.5	883.3	886.4	884.1	883.3
5°	831.9	830.4	828.0	825.7	824.9	828.0	822.6	824.1	825.7	828.0	831.2
7.5°	787.6	786.8	784.5	780.6	779.0	777.5	778.2	783.7	782.9	782.1	787.6
10°	747.1	747.9	743.2	742.4	737.8	737.0	737.8	739.3	741.7	744.8	745.5
12.5°	705.1	715.2	706.6	703.5	696.5	700.4	702.0	695.0	698.9	701.2	712.9
15°	678.6	673.9	668.5	668.5	665.4	663.8	659.9	665.4	668.5	673.2	671.6
17.5°	642.0	634.3	631.1	628.0	628.8	631.9	623.4	635.8	635.8	638.1	634.3
20°	610.1	603.9	600.0	598.5	596.1	594.6	593.8	596.9	601.6	603.1	607.0
22.5°	576.7	576.7	570.4	568.1	566.6	564.2	568.1	565.8	568.9	572.0	578.2
25°	548.7	548.7	546.3	543.2	540.9	539.3	541.6	540.9	543.2	547.1	548.7
27.5°	526.1	523.7	523.0	522.2	521.4	522.2	521.4	523.7	526.1	526.9	525.3
30°	506.6	504.3	505.1	505.1	505.9	505.1	504.3	506.6	507.4	505.9	506.6
32.5°	488.7	488.7	490.3	491.1	491.1	491.8	492.6	491.1	491.8	489.5	490.3
35°	473.9	475.5	477.1	477.8	478.6	477.8	479.4	478.6	477.1	475.5	474.7
37.5°	459.2	460.7	463.8	464.6	466.9	467.7	466.2	466.2	465.4	462.3	460.7
40°	443.6	445.1	449.0	451.4	452.9	455.3	453.7	453.7	450.6	447.5	445.1
42.5°	428.8	431.9	435.8	438.1	441.3	441.3	441.3	439.7	435.8	432.7	430.4
45°	414.0	414.8	420.2	424.1	427.2	427.2	427.2	424.9	422.6	416.4	413.2
47.5°	397.7	400.0	406.2	410.1	413.2	414.0	414.0	411.7	407.0	401.6	397.7
50°	379.8	383.7	390.7	396.1	400.0	401.6	399.2	397.7	392.2	386.0	381.3
52.5°	362.7	367.3	375.9	380.6	386.0	386.8	386.0	383.7	377.4	368.9	365.0
55°	345.5	349.4	358.8	366.5	371.2	372.8	371.2	367.3	359.5	351.0	347.1
57.5°	326.9	332.3	342.4	350.2	355.7	356.4	354.9	351.0	344.8	333.9	328.4
60°	307.4	314.4	324.5	332.3	339.3	340.1	338.5	333.1	325.3	314.4	309.7
62.5°	287.9	293.4	305.1	313.6	319.1	323.0	319.9	314.4	306.6	295.7	288.7
65°	265.4	273.2	283.3	291.1	297.3	298.1	296.5	291.8	283.3	271.6	266.2
67.5°	243.6	249.0	259.2	269.3	271.6	273.9	271.6	266.9	259.9	249.8	242.0
70°	217.1	221.8	234.2	241.3	244.4	246.7	245.1	240.5	234.2	224.9	218.7
72.5°	190.7	194.6	206.2	211.7	217.9	217.1	216.3	213.2	204.7	198.4	194.6
75°	162.7	167.3	175.1	182.1	184.4	184.4	184.4	182.1	176.7	166.5	162.7
77.5°	137.0	139.3	145.5	149.4	151.8	152.5	151.8	147.9	144.8	137.7	135.4
80°	105.1	111.3	116.0	116.7	119.8	119.8	119.8	118.3	115.2	108.2	107.4
82.5°	79.4	80.9	85.6	87.9	89.5	88.7	88.7	85.6	84.8	80.9	79.4
85°	53.7	56.0	55.3	58.4	59.1	57.6	57.6	59.1	55.3	56.0	53.7
87.5°	29.6	29.6	31.1	30.4	33.5	33.5	31.9	32.7	31.1	30.4	29.6
90°	10.0	10.1	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	10.0
92.5°	16.8	16.8	16.9	17.0	17.0	17.1	17.0	17.0	16.9	16.8	16.8
95°	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2
97.5°	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
100°	55.3	55.3	55.3	55.3	55.3	55.3	55.3	55.3	55.3	55.3	55.3
102.5°	70.7	70.7	70.8	70.9	71.0	71.1	71.0	70.9	70.8	70.7	70.7
105°	86.1	86.2	86.4	86.7	86.9	87.1	86.9	86.7	86.4	86.2	86.1
107.5°	102.8	102.8	102.7	102.6	102.6	102.5	102.6	102.6	102.7	102.8	102.8
110°	118.2	118.3	118.6	118.8	119.1	119.3	119.1	118.8	118.6	118.3	118.2

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4
115°	154.6	154.6	154.5	154.4	154.4	154.3	154.4	154.4	154.5	154.6	154.6
117.5°	171.7	171.6	171.4	171.1	170.9	170.7	170.9	171.1	171.4	171.6	171.7
120°	189.2	189.3	189.5	189.6	189.8	190.0	189.8	189.6	189.5	189.3	189.2
122.5°	207.8	207.6	207.2	206.8	206.4	206.0	206.4	206.8	207.2	207.6	207.8
125°	225.7	225.6	225.5	225.3	225.2	225.0	225.2	225.3	225.5	225.6	225.7
127.5°	242.4	242.4	242.3	242.2	242.2	242.1	242.2	242.2	242.3	242.4	242.4
130°	260.3	260.1	259.8	259.5	259.2	258.9	259.2	259.5	259.8	260.1	260.3
132.5°	277.1	277.1	277.0	276.9	276.8	276.7	276.8	276.9	277.0	277.1	277.1
135°	293.9	293.8	293.5	293.3	293.0	292.8	293.0	293.3	293.5	293.8	293.9
137.5°	309.9	309.9	310.0	310.1	310.2	310.3	310.2	310.1	310.0	309.9	309.9
140°	326.4	326.4	326.3	326.2	326.1	326.0	326.1	326.2	326.3	326.4	326.4
142.5°	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7	341.7
145°	356.7	356.6	356.3	356.1	355.8	355.6	355.8	356.1	356.3	356.6	356.7
147.5°	370.6	370.6	370.5	370.4	370.4	370.3	370.4	370.4	370.5	370.6	370.6
150°	383.8	383.8	383.7	383.6	383.6	383.5	383.6	383.6	383.7	383.8	383.8
152.5°	396.7	396.6	396.3	396.1	395.8	395.6	395.8	396.1	396.3	396.6	396.7
155°	408.1	407.9	407.6	407.3	407.0	406.7	407.0	407.3	407.6	407.9	408.1
157.5°	418.1	418.0	417.8	417.5	417.3	417.1	417.3	417.5	417.8	418.0	418.1
160°	427.4	427.2	426.8	426.4	426.0	425.6	426.0	426.4	426.8	427.2	427.4
162.5°	436.3	436.1	435.7	435.4	435.0	434.6	435.0	435.4	435.7	436.1	436.3
165°	443.5	443.3	443.0	442.7	442.3	442.0	442.3	442.7	443.0	443.3	443.5
167.5°	449.9	449.7	449.2	448.7	448.3	447.8	448.3	448.7	449.2	449.7	449.9
170°	454.9	454.6	454.1	453.5	453.0	452.4	453.0	453.5	454.1	454.6	454.9
172.5°	458.8	458.5	458.0	457.4	456.9	456.3	456.9	457.4	458.0	458.5	458.8
175°	461.3	461.0	460.5	459.9	459.4	458.8	459.4	459.9	460.5	461.0	461.3
177.5°	463.1	462.8	462.2	461.5	460.9	460.3	460.9	461.5	462.2	462.8	463.1
180°	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	883.3	888.0	883.3	886.4	888.0	891.9	893.4	900.4	902.7	908.2	908.2
5°	830.4	832.7	833.5	836.6	839.7	847.5	852.9	863.1	874.7	876.3	883.3
7.5°	787.6	791.5	797.7	795.4	800.8	812.5	819.5	831.9	843.6	849.8	858.4
10°	749.4	754.1	756.4	758.8	768.9	779.0	789.9	798.5	814.0	823.4	830.4
12.5°	718.3	714.4	719.1	727.6	739.3	745.5	760.3	773.6	785.2	795.4	801.6
15°	677.8	681.0	685.6	700.4	703.5	719.1	724.5	739.3	761.1	770.4	778.2
17.5°	638.9	649.0	658.4	663.8	673.2	685.6	701.2	717.5	731.5	742.4	751.8
20°	607.8	617.9	623.4	627.3	636.6	653.7	668.5	688.7	706.6	715.2	727.6
22.5°	582.9	582.9	590.7	602.4	607.8	624.1	636.6	658.4	677.8	688.7	700.4
25°	551.8	556.4	562.7	572.8	580.6	593.8	611.7	630.4	651.4	660.7	675.5
27.5°	526.1	531.5	540.1	542.4	550.2	561.9	580.6	600.8	622.6	632.7	645.2
30°	506.6	509.7	512.9	517.5	524.5	534.6	550.2	568.1	594.6	602.4	617.9
32.5°	489.5	491.1	492.6	496.5	500.4	510.5	523.0	542.4	564.2	575.9	589.9
35°	473.9	472.4	473.2	475.5	479.4	483.3	496.5	512.9	533.1	547.1	558.0
37.5°	459.2	456.0	455.3	455.3	456.8	461.5	471.6	485.6	507.4	519.1	530.0
40°	442.8	439.7	438.1	437.4	436.6	439.7	447.5	461.5	478.6	489.5	502.0
42.5°	427.2	424.1	420.2	419.5	417.9	419.5	424.9	438.1	452.9	463.8	473.9
45°	411.7	406.2	401.6	398.5	399.2	396.9	400.8	410.9	428.0	435.0	445.1
47.5°	394.6	388.3	382.1	379.0	375.9	377.4	379.0	387.6	402.3	409.3	419.5
50°	378.2	369.7	362.7	358.8	356.4	354.9	356.4	365.0	375.9	382.1	390.7
52.5°	359.5	351.0	344.0	337.8	334.6	332.3	333.1	340.9	351.0	357.2	365.8
55°	342.4	331.5	322.2	314.4	312.1	311.3	310.5	316.0	324.5	330.7	337.8
57.5°	323.0	312.1	302.0	292.6	287.9	287.2	287.2	288.7	299.6	304.3	308.2
60°	303.5	291.8	280.9	272.4	265.4	263.0	262.3	265.4	270.8	275.5	280.9
62.5°	281.7	270.0	256.8	249.0	242.0	235.8	238.1	238.9	246.7	249.0	253.7
65°	260.7	247.5	236.6	224.1	216.3	212.5	210.9	212.5	218.7	219.5	222.6
67.5°	236.6	224.1	210.9	202.3	195.3	188.3	186.8	186.8	189.9	192.2	196.1
70°	213.2	200.8	186.0	176.7	169.7	163.4	161.1	160.3	162.7	164.2	168.1
72.5°	186.0	173.5	162.7	152.5	144.0	139.3	137.0	135.4	137.7	139.3	140.1
75°	157.2	147.1	136.2	126.1	120.6	116.0	112.8	110.5	112.1	112.1	112.1
77.5°	130.0	119.8	111.3	104.3	97.3	91.8	89.5	87.2	87.9	87.9	89.5
80°	101.2	94.2	87.2	80.9	74.7	70.0	68.5	66.1	64.6	63.8	63.8
82.5°	74.7	69.3	63.0	57.6	54.5	49.8	48.3	45.1	45.1	44.4	44.4
85°	49.8	46.7	40.5	36.6	34.2	31.9	30.4	28.8	26.5	26.5	25.7
87.5°	26.5	24.9	23.3	18.7	18.7	16.3	15.6	14.8	12.5	13.2	13.2
90°	9.8	9.3	8.8	8.4	7.9	7.3	6.6	6.0	5.3	5.0	4.6
92.5°	16.7	16.4	16.2	15.9	15.7	15.3	14.9	14.5	14.1	13.9	13.4
95°	28.1	27.8	27.6	27.3	27.1	26.5	26.0	25.4	24.9	24.6	24.2
97.5°	41.2	40.9	40.6	40.3	40.0	39.4	38.7	38.1	37.4	37.1	36.8
100°	55.2	55.1	54.9	54.8	54.6	53.9	53.2	52.5	51.8	51.4	51.2
102.5°	70.6	70.3	70.1	69.8	69.6	69.0	68.4	67.7	67.1	66.8	66.8
105°	86.0	85.7	85.5	85.2	85.0	84.7	84.4	84.1	83.8	83.6	83.6
107.5°	102.6	102.3	102.0	101.7	101.4	101.3	101.2	101.1	101.0	101.0	101.0
110°	118.3	118.4	118.6	118.7	118.9	119.0	119.1	119.2	119.3	119.3	119.2

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	136.4	136.4	136.4	136.4	136.4	136.6	136.7	136.9	137.0	137.1	137.1
115°	154.6	154.7	154.8	154.9	155.0	155.2	155.3	155.5	155.6	155.7	155.7
117.5°	171.8	172.1	172.3	172.6	172.8	172.9	173.0	173.1	173.2	173.2	173.2
120°	189.4	189.8	190.2	190.6	191.0	191.2	191.5	191.7	192.0	192.1	191.9
122.5°	207.9	208.2	208.4	208.7	208.9	209.0	209.0	209.1	209.2	209.2	209.2
125°	225.8	225.9	226.1	226.2	226.4	226.5	226.5	226.6	226.7	226.7	226.7
127.5°	242.5	242.7	242.8	243.0	243.2	243.4	243.5	243.7	243.8	243.9	243.8
130°	260.4	260.5	260.7	260.8	261.0	261.0	261.0	261.0	261.0	261.0	260.9
132.5°	277.2	277.3	277.5	277.6	277.8	277.9	278.0	278.1	278.2	278.2	278.1
135°	294.0	294.1	294.3	294.4	294.6	294.6	294.6	294.6	294.6	294.6	294.4
137.5°	310.0	310.3	310.5	310.8	311.0	310.8	310.7	310.5	310.4	310.3	310.2
140°	326.4	326.5	326.6	326.6	326.7	326.7	326.7	326.7	326.7	326.7	326.6
142.5°	341.7	341.7	341.7	341.7	341.7	341.8	341.9	342.0	342.1	342.1	342.0
145°	356.7	356.8	356.9	357.0	357.1	357.0	356.9	356.8	356.7	356.7	356.5
147.5°	370.6	370.7	370.8	370.9	371.0	371.1	371.1	371.2	371.3	371.3	371.1
150°	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.6
152.5°	396.6	396.3	396.1	395.8	395.6	395.5	395.5	395.4	395.3	395.3	395.2
155°	407.9	407.6	407.3	407.0	406.7	406.8	406.9	407.0	407.1	407.1	407.1
157.5°	418.0	417.8	417.5	417.3	417.1	417.1	417.1	417.1	417.1	417.1	417.2
160°	427.3	427.0	426.8	426.5	426.3	426.4	426.5	426.6	426.7	426.7	426.7
162.5°	436.1	435.6	435.1	434.7	434.2	434.3	434.4	434.5	434.6	434.6	434.7
165°	443.3	442.8	442.3	441.8	441.3	441.5	441.6	441.8	441.9	442.0	442.1
167.5°	449.7	449.2	448.7	448.3	447.8	447.8	447.8	447.8	447.8	447.8	448.0
170°	454.7	454.2	453.7	453.3	452.8	452.7	452.6	452.5	452.4	452.4	452.6
172.5°	458.5	458.0	457.4	456.9	456.3	456.3	456.3	456.3	456.3	456.3	456.5
175°	461.0	460.5	459.9	459.4	458.8	458.9	459.0	459.1	459.2	459.2	459.4
177.5°	462.8	462.3	461.7	461.2	460.6	460.6	460.6	460.6	460.6	460.6	460.8
180°	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7	461.7

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	939.3	939.3	939.3	939.3
2.5°	913.6	921.4	928.4	939.3
5°	893.4	904.3	919.1	935.4
7.5°	870.1	887.2	906.6	929.2
10°	848.3	867.7	892.6	919.9
12.5°	825.7	849.1	876.3	905.9
15°	800.0	823.4	853.7	893.4
17.5°	776.7	804.7	837.4	879.4
20°	749.4	775.9	811.7	859.9
22.5°	725.3	755.7	795.4	837.4
25°	698.9	725.3	765.0	815.6
27.5°	672.4	705.1	743.2	792.2
30°	646.7	673.9	715.2	766.6
32.5°	618.7	651.4	689.5	737.8
35°	588.3	619.5	655.3	707.4
37.5°	561.1	591.5	628.0	673.9
40°	530.8	562.7	596.1	642.0
42.5°	501.2	530.0	563.4	605.5
45°	472.4	497.3	527.6	564.2
47.5°	442.8	463.8	491.8	524.5
50°	410.9	433.5	454.5	481.7
52.5°	381.3	400.8	417.9	440.5
55°	352.5	365.8	379.8	396.9
57.5°	322.2	332.3	342.4	360.3
60°	291.8	301.2	306.6	318.3
62.5°	262.3	266.2	273.2	280.2
65°	229.6	235.0	238.9	247.5
67.5°	200.0	202.3	206.2	211.7
70°	168.9	174.3	175.9	179.8
72.5°	142.4	144.8	146.3	147.1
75°	112.8	115.2	116.7	121.4
77.5°	88.7	87.9	91.1	91.8
80°	65.4	63.0	63.8	66.9
82.5°	42.8	43.6	42.8	42.8
85°	26.5	25.7	24.1	24.9
87.5°	11.7	11.7	10.9	10.9
90°	3.7	2.8	2.0	1.1
92.5°	12.4	11.3	10.3	9.3
95°	23.5	22.8	22.1	21.4
97.5°	36.2	35.5	34.9	34.3
100°	50.9	50.6	50.3	50.0
102.5°	66.7	66.6	66.5	66.4
105°	83.5	83.4	83.3	83.2
107.5°	100.9	100.8	100.8	100.7
110°	119.0	118.9	118.7	118.5

TEST NUMBER: P1001551

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	137.1	137.1	137.1	137.1
115°	155.7	155.7	155.7	155.7
117.5°	173.2	173.2	173.2	173.2
120°	191.6	191.3	191.0	190.7
122.5°	209.1	209.0	209.0	208.9
125°	226.7	226.7	226.7	226.7
127.5°	243.5	243.3	243.0	242.8
130°	260.6	260.4	260.1	259.9
132.5°	277.9	277.8	277.6	277.4
135°	293.9	293.4	292.9	292.4
137.5°	309.9	309.7	309.4	309.2
140°	326.5	326.3	326.2	326.0
142.5°	341.9	341.7	341.6	341.4
145°	356.2	355.9	355.6	355.3
147.5°	370.7	370.4	370.0	369.6
150°	383.3	383.0	382.7	382.4
152.5°	395.1	394.9	394.8	394.6
155°	407.1	407.1	407.1	407.1
157.5°	417.3	417.5	417.6	417.8
160°	426.8	426.9	427.0	427.1
162.5°	434.9	435.2	435.4	435.6
165°	442.4	442.6	442.9	443.1
167.5°	448.3	448.6	448.9	449.2
170°	453.0	453.4	453.8	454.2
172.5°	456.8	457.1	457.5	457.8
175°	459.8	460.2	460.6	461.0
177.5°	461.2	461.6	462.0	462.4
180°	461.7	461.7	461.7	461.7

(END OF REPORT)