

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001568

Luminaire Tested: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001568
REPORT IS A COMBINATION OF REPORTS P996190 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3897.0 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	93	89	95	91	88	85	80	78	75	70	68	67	61	60	59
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	54	52	50
3	84	75	68	62	79	71	64	59	63	58	53	55	51	48	48	45	43
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	39	35	33
6	66	54	45	40	62	51	43	38	45	39	35	40	35	32	36	32	29
7	61	49	40	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	40	33	28	50	38	32	27	35	29	25	31	26	23	28	24	21
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7335	7335	7335	7335
5°	7316	8414	7359	6323
10°	7261	9817	7316	5547
15°	7174	11317	7225	4964
20°	7082	12272	7132	4450
25°	6946	12131	7012	4071
30°	6813	10027	6897	3876
35°	6627	7472	6700	3758
40°	6410	5629	6473	3699
45°	6079	4518	6154	3621
50°	5683	3806	5765	3584
55°	5218	3313	5299	3542
60°	4765	2917	4904	3483
65°	4340	2510	4381	3338
70°	3840	2065	3924	3073
75°	3352	1586	3328	2611
80°	2636	1043	2603	1983
85°	1732	470	1630	1155

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9484 cd/sqm

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	2.2
10°-20°	270.2	6.9
20°-30°	429.2	11.0
30°-40°	477.0	12.2
40°-50°	433.7	11.1
50°-60°	354.5	9.1
60°-70°	253.0	6.5
70°-80°	139.2	3.6
80°-90°	38.6	1.0
90°-100°	15.2	0.4
100°-110°	99.9	2.6
110°-120°	190.8	4.9
120°-130°	242.2	6.2
130°-140°	259.1	6.6
140°-150°	242.2	6.2
150°-160°	195.4	5.0
160°-170°	126.0	3.2
170°-180°	43.4	1.1
0°-30°	787.0	20.2
0°-40°	1263.9	32.4
0°-60°	2052.1	52.7
0°-90°	2482.9	63.7
90°-120°	305.8	7.8
90°-150°	1049.3	26.9
90°-180°	1414.0	36.3
0°-180°	3897.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	900	900	900	900	900	
5°	896	1055	901	793	896	85
15°	856	1449	862	636	856	241
25°	781	1539	788	516	781	360
35°	677	910	685	458	677	423
45°	540	510	547	409	540	417
55°	380	334	386	357	380	342
65°	237	215	239	285	237	234
75°	116	107	116	177	116	122
85°	24	22	22	55	24	28
90°	1	10	1	10	1	2
95°	19	10	19	10	19	23
105°	103	97	103	97	103	108
115°	192	194	192	194	192	189
125°	270	272	270	272	270	241
135°	335	337	335	337	335	258
145°	386	388	386	388	386	241
155°	424	423	424	423	424	195
165°	447	445	447	445	447	126
175°	457	454	457	454	457	44
180°	457	457	457	457	457	

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	899.5	908.4	912.1	915.1	924.8	927.8	928.5	933.0	936.7	937.5	937.5
5°	895.7	909.9	921.1	931.5	947.2	953.9	962.1	971.0	982.9	990.4	994.1
7.5°	889.8	910.6	927.8	945.7	967.3	980.7	988.1	1012.0	1028.4	1041.8	1058.2
10°	880.8	907.7	932.3	958.3	988.9	1005.3	1021.7	1050.7	1073.8	1099.9	1120.8
12.5°	867.4	902.4	932.3	968.8	1006.8	1026.1	1045.5	1096.2	1123.0	1146.1	1183.4
15°	855.5	890.5	933.0	970.3	1017.2	1046.3	1074.6	1107.4	1149.9	1199.8	1235.5
17.5°	842.1	886.0	925.5	977.7	1029.9	1057.4	1080.5	1131.2	1190.8	1240.0	1272.8
20°	823.5	868.2	920.3	975.5	1037.3	1058.9	1089.5	1157.3	1211.0	1259.4	1313.1
22.5°	801.8	854.0	909.1	962.1	1026.1	1071.6	1105.1	1164.8	1229.6	1285.5	1345.8
25°	781.0	837.6	886.0	958.3	1026.1	1056.7	1094.7	1165.5	1236.3	1304.1	1366.0
27.5°	758.6	811.5	877.1	934.5	1011.2	1044.8	1085.8	1163.3	1238.5	1306.3	1372.7
30°	734.0	790.7	845.1	912.9	987.4	1030.6	1068.6	1152.8	1229.6	1300.4	1362.2
32.5°	706.5	760.1	818.2	882.3	960.6	1004.5	1052.2	1138.7	1220.6	1281.8	1329.4
35°	677.4	731.8	782.5	848.0	928.5	972.5	1018.7	1114.1	1195.3	1245.2	1272.8
37.5°	645.3	696.8	746.7	811.5	892.0	939.0	985.9	1078.3	1155.1	1196.8	1189.3
40°	614.8	661.0	707.2	768.3	852.5	902.4	943.4	1036.6	1103.6	1121.5	1096.9
42.5°	579.8	619.3	664.0	726.6	808.5	855.5	906.9	991.9	1041.8	1034.3	992.6
45°	540.3	575.3	620.0	678.9	762.3	810.8	854.0	934.5	971.0	952.4	876.4
47.5°	502.3	536.5	573.1	631.9	713.2	754.1	798.1	870.4	891.3	851.8	775.8
50°	461.3	489.6	527.6	583.5	659.5	702.7	739.2	797.4	804.8	756.4	677.4
52.5°	421.8	445.6	482.1	537.3	608.1	642.4	678.1	729.6	723.6	673.7	597.7
55°	380.1	402.4	435.9	486.6	549.2	582.0	612.6	658.0	645.3	593.9	527.6
57.5°	345.0	360.7	393.5	440.4	491.8	527.6	553.7	589.5	570.1	518.7	456.8
60°	304.8	324.2	351.7	389.7	440.4	464.3	487.4	511.2	497.8	448.6	393.5
62.5°	268.3	283.2	307.0	343.5	383.0	404.6	429.2	444.1	430.7	385.3	339.1
65°	237.0	248.9	267.5	297.3	335.3	353.2	367.4	381.5	370.4	327.9	294.4
67.5°	202.7	213.1	228.8	252.6	284.7	297.3	310.8	320.4	307.8	279.5	246.7
70°	172.1	179.6	194.5	212.4	234.7	246.7	257.8	267.5	256.4	232.5	207.9
72.5°	140.8	146.8	160.2	172.9	193.0	201.2	209.4	216.9	213.1	190.8	170.7
75°	116.3	118.5	127.4	137.9	150.5	159.5	165.4	169.9	166.9	149.0	136.4
77.5°	87.9	90.9	97.6	105.8	117.0	122.2	125.9	130.4	126.7	112.5	103.6
80°	64.1	64.8	68.6	76.0	83.5	84.2	87.9	93.9	91.7	82.0	75.3
82.5°	41.0	43.2	44.7	49.2	54.4	55.9	58.1	59.6	58.9	52.9	50.7
85°	23.8	23.8	25.3	28.3	29.8	32.0	32.8	33.5	35.0	31.3	29.1
87.5°	10.4	11.2	11.2	11.9	13.4	13.4	14.2	14.9	15.6	14.9	12.7
90°	1.0	1.8	2.7	3.5	4.4	4.8	5.1	5.7	6.3	6.9	7.5
92.5°	5.1	4.9	4.8	4.6	4.5	4.4	4.7	5.3	6.0	6.6	7.2
95°	18.8	16.2	13.6	11.1	8.5	7.2	7.2	7.3	7.4	7.4	7.5
97.5°	35.9	37.6	39.2	40.9	42.6	43.4	39.4	31.4	23.5	15.5	7.5
100°	56.1	57.5	58.8	60.2	61.5	62.2	57.0	46.5	36.0	25.5	15.0
102.5°	78.6	79.5	80.4	81.3	82.2	82.7	83.2	84.1	85.0	85.9	86.8
105°	102.9	103.3	103.8	104.2	104.7	104.9	105.1	105.5	105.8	106.2	106.6
107.5°	125.1	125.3	125.5	125.8	126.0	126.1	126.4	126.9	127.4	128.0	128.5
110°	147.7	147.9	148.1	148.4	148.6	148.7	148.9	149.4	149.8	150.3	150.7

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	169.5	170.0	170.4	170.9	171.4	171.6	171.7	171.8	172.0	172.1	172.3
115°	192.1	192.3	192.5	192.8	193.0	193.1	193.1	193.0	192.9	192.9	192.8
117.5°	212.3	212.6	212.9	213.2	213.5	213.6	213.7	213.9	214.2	214.4	214.6
120°	232.8	233.1	233.4	233.7	234.0	234.1	234.1	234.0	233.9	233.9	233.8
122.5°	251.9	252.1	252.2	252.4	252.5	252.6	252.7	252.8	253.0	253.1	253.3
125°	270.0	270.3	270.6	270.9	271.2	271.4	271.3	271.2	271.0	270.9	270.7
127.5°	287.4	287.5	287.6	287.7	287.8	287.8	288.0	288.4	288.7	289.1	289.5
130°	304.2	304.3	304.3	304.4	304.5	304.5	304.6	304.9	305.1	305.4	305.6
132.5°	319.6	319.8	319.9	320.1	320.2	320.3	320.4	320.7	321.0	321.3	321.6
135°	335.0	334.9	334.8	334.7	334.6	334.6	334.8	335.1	335.4	335.7	336.0
137.5°	348.6	348.6	348.6	348.6	348.6	348.6	348.8	349.2	349.5	349.9	350.3
140°	362.0	362.1	362.3	362.4	362.5	362.6	362.7	362.8	363.0	363.1	363.3
142.5°	373.9	374.2	374.5	374.8	375.1	375.3	375.3	375.4	375.5	375.5	375.6
145°	386.2	386.4	386.7	386.9	387.2	387.3	387.3	387.3	387.3	387.3	387.3
147.5°	395.8	396.2	396.7	397.1	397.6	397.8	397.8	397.7	397.6	397.6	397.5
150°	406.4	406.7	407.0	407.3	407.6	407.8	407.8	407.7	407.6	407.5	407.4
152.5°	415.3	415.5	415.7	416.0	416.2	416.3	416.2	416.1	415.9	415.8	415.6
155°	423.5	423.6	423.6	423.7	423.8	423.8	423.7	423.5	423.2	423.0	422.8
157.5°	430.7	430.7	430.7	430.7	430.7	430.7	430.5	430.2	429.9	429.6	429.3
160°	436.8	436.6	436.4	436.1	435.9	435.8	435.8	435.7	435.6	435.5	435.4
162.5°	442.3	442.0	441.7	441.4	441.1	440.9	440.9	440.8	440.7	440.7	440.6
165°	446.7	446.3	445.9	445.6	445.2	445.0	445.0	445.0	445.0	445.0	445.0
167.5°	450.5	450.1	449.7	449.4	449.0	448.8	448.8	448.7	448.6	448.5	448.4
170°	453.6	453.1	452.7	452.2	451.7	451.5	451.5	451.6	451.7	451.8	451.9
172.5°	455.6	455.2	454.7	454.3	453.8	453.6	453.6	453.7	453.8	453.8	453.9
175°	457.0	456.5	456.1	455.6	455.1	454.9	454.9	455.0	455.1	455.2	455.3
177.5°	458.0	457.5	456.9	456.4	455.9	455.6	455.7	455.8	456.0	456.1	456.3
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0



TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	939.7	953.1	959.1	960.6	968.8	963.5	965.8	965.0	971.0	971.7	971.7
5°	1008.3	1023.9	1029.1	1036.6	1047.8	1050.7	1048.5	1053.0	1061.2	1055.2	1064.2
7.5°	1080.5	1097.7	1109.6	1126.0	1129.7	1139.4	1145.4	1150.6	1152.1	1152.8	1154.3
10°	1147.6	1169.2	1185.6	1213.2	1219.2	1224.4	1250.5	1240.0	1253.4	1249.0	1250.5
12.5°	1202.0	1244.5	1257.9	1304.1	1308.6	1326.5	1325.0	1341.4	1344.3	1350.3	1344.3
15°	1273.6	1322.7	1344.3	1370.4	1385.3	1406.2	1409.9	1432.3	1441.2	1449.4	1441.2
17.5°	1339.1	1365.2	1420.4	1441.2	1450.9	1462.1	1490.4	1498.6	1512.0	1506.8	1521.7
20°	1371.9	1409.2	1467.3	1503.1	1518.0	1528.4	1552.3	1564.9	1570.1	1570.1	1571.6
22.5°	1401.0	1454.6	1497.9	1538.8	1552.3	1559.7	1573.9	1583.6	1585.8	1587.3	1588.8
25°	1427.1	1475.5	1510.5	1533.6	1538.8	1538.8	1547.0	1541.1	1531.4	1538.8	1543.3
27.5°	1427.1	1461.3	1477.0	1485.2	1485.2	1465.1	1453.1	1428.6	1407.7	1401.7	1415.1
30°	1403.2	1418.9	1397.3	1377.1	1361.5	1348.1	1301.1	1263.9	1256.4	1251.2	1271.3
32.5°	1348.1	1328.0	1285.5	1227.4	1204.3	1173.7	1137.2	1108.9	1091.7	1085.8	1081.3
35°	1250.5	1198.3	1143.1	1064.9	1048.5	1009.8	959.8	939.0	910.6	909.9	919.6
37.5°	1143.9	1063.4	1003.8	929.3	906.2	865.2	818.2	796.6	777.2	762.3	780.2
40°	1019.4	949.4	858.5	797.4	764.6	743.0	703.5	679.6	670.7	663.2	674.4
42.5°	903.2	826.4	755.6	693.0	666.2	641.6	615.5	592.4	585.7	585.0	593.2
45°	787.7	712.4	646.8	593.2	576.0	561.1	535.8	529.1	517.9	510.5	514.2
47.5°	695.3	617.8	563.4	522.4	507.5	494.8	478.4	467.2	457.6	454.6	459.0
50°	604.4	552.2	496.3	462.0	450.8	438.9	426.3	415.8	411.4	408.4	411.4
52.5°	531.3	475.4	437.4	409.9	398.7	389.7	380.8	376.3	370.4	371.9	374.8
55°	465.8	416.6	384.5	364.4	357.7	354.0	342.8	337.6	335.3	333.9	335.3
57.5°	403.9	368.1	344.3	327.1	318.2	316.0	307.0	307.0	304.8	302.6	303.3
60°	354.7	324.2	301.1	287.6	286.2	282.4	276.5	275.7	270.5	272.7	273.5
62.5°	304.8	280.2	264.5	256.4	251.1	249.6	245.9	245.2	242.9	243.7	242.2
65°	265.3	245.2	229.5	222.8	220.6	219.8	216.9	214.6	213.1	214.6	213.1
67.5°	225.8	212.4	200.5	193.8	190.8	190.0	187.8	186.3	187.0	184.8	186.3
70°	188.5	175.1	167.7	163.9	162.5	160.2	160.2	160.2	160.2	158.7	158.0
72.5°	158.7	145.3	140.1	137.9	136.4	135.6	133.4	134.1	133.4	132.6	135.6
75°	125.9	117.7	112.5	110.3	111.8	109.5	107.3	108.8	106.6	107.3	110.3
77.5°	95.4	91.7	88.7	87.2	85.7	84.2	84.2	82.7	82.7	82.7	82.7
80°	69.3	68.6	63.3	62.6	62.6	61.1	61.1	61.1	61.1	60.4	61.1
82.5°	46.2	45.5	44.0	43.2	41.7	42.5	42.5	41.0	41.0	40.2	41.0
85°	26.8	26.8	25.3	24.6	23.8	24.6	23.1	22.4	23.1	22.4	23.1
87.5°	12.7	11.2	11.9	11.2	9.7	10.4	8.9	9.7	8.9	8.2	9.7
90°	8.0	8.4	8.9	9.4	9.6	9.7	9.8	10.0	10.1	10.3	10.1
92.5°	7.6	8.1	8.5	9.0	9.2	9.2	9.2	9.2	9.2	9.2	9.2
95°	8.0	8.4	8.9	9.4	9.6	9.6	9.7	9.8	9.8	9.9	9.8
97.5°	7.9	8.3	8.6	9.0	9.2	9.2	9.3	9.4	9.5	9.6	9.5
100°	13.7	12.4	11.1	9.8	9.2	9.2	9.3	9.4	9.5	9.6	9.5
102.5°	69.7	52.6	35.5	18.4	9.9	9.9	9.9	9.9	9.9	9.9	9.9
105°	107.3	108.0	108.7	109.4	109.7	108.3	105.6	102.9	100.1	97.4	100.1
107.5°	128.9	129.3	129.6	130.0	130.2	130.4	130.7	131.0	131.3	131.6	131.3
110°	150.9	151.0	151.2	151.3	151.4	151.5	151.7	152.0	152.2	152.4	152.2

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	172.2	172.1	172.0	171.9	171.9	172.1	172.4	172.7	173.0	173.3	173.0
115°	193.0	193.1	193.3	193.4	193.5	193.5	193.5	193.5	193.5	193.5	193.5
117.5°	214.5	214.5	214.4	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3
120°	234.0	234.1	234.3	234.4	234.5	234.4	234.3	234.1	234.0	233.8	234.0
122.5°	253.4	253.4	253.5	253.6	253.6	253.5	253.4	253.2	253.1	252.9	253.1
125°	270.9	271.1	271.4	271.6	271.7	271.7	271.8	271.9	272.0	272.1	272.0
127.5°	289.4	289.4	289.3	289.2	289.2	289.2	289.1	289.0	288.9	288.8	288.9
130°	305.7	305.7	305.8	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9
132.5°	321.7	321.8	321.9	322.0	322.0	322.0	321.9	321.8	321.7	321.6	321.7
135°	336.2	336.3	336.5	336.6	336.7	336.8	336.9	337.1	337.2	337.4	337.2
137.5°	350.5	350.6	350.8	350.9	351.0	351.0	350.9	350.8	350.8	350.7	350.8
140°	363.5	363.8	364.0	364.3	364.4	364.4	364.5	364.6	364.6	364.7	364.6
142.5°	375.8	375.9	376.1	376.2	376.3	376.3	376.3	376.3	376.3	376.3	376.3
145°	387.4	387.4	387.5	387.6	387.6	387.7	387.8	388.0	388.1	388.3	388.1
147.5°	397.6	397.6	397.7	397.8	397.8	397.8	397.9	398.0	398.1	398.2	398.1
150°	407.4	407.4	407.4	407.4	407.4	407.4	407.5	407.6	407.7	407.8	407.7
152.5°	415.8	415.9	416.1	416.2	416.3	416.3	416.2	416.1	416.1	416.0	416.1
155°	423.1	423.4	423.7	424.0	424.2	424.1	423.8	423.6	423.3	423.1	423.3
157.5°	429.7	430.1	430.4	430.8	431.0	430.8	430.4	430.1	429.7	429.3	429.7
160°	435.9	436.3	436.8	437.3	437.5	437.3	436.8	436.3	435.9	435.4	435.9
162.5°	441.0	441.5	441.9	442.4	442.6	442.3	441.8	441.3	440.7	440.2	440.7
165°	445.6	446.2	446.9	447.5	447.8	447.5	446.8	446.1	445.4	444.7	445.4
167.5°	449.1	449.8	450.5	451.2	451.5	451.1	450.4	449.6	448.9	448.1	448.9
170°	452.5	453.1	453.7	454.3	454.6	454.2	453.5	452.7	452.0	451.2	452.0
172.5°	454.5	455.1	455.7	456.3	456.6	456.2	455.4	454.5	453.7	452.9	453.7
175°	456.0	456.6	457.3	458.0	458.3	457.8	456.9	456.0	455.1	454.2	455.1
177.5°	456.9	457.5	458.1	458.7	459.0	458.5	457.6	456.7	455.8	454.9	455.8
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	970.3	968.0	965.0	965.0	961.3	961.3	955.4	944.9	936.0	933.0	934.5
5°	1053.0	1053.7	1049.2	1045.5	1038.8	1033.6	1023.9	1005.3	999.3	987.4	979.2
7.5°	1147.6	1144.6	1136.4	1130.5	1129.0	1117.1	1096.2	1073.8	1056.0	1044.0	1026.9
10°	1254.2	1242.3	1230.3	1226.6	1217.7	1197.5	1173.7	1149.1	1124.5	1098.4	1069.4
12.5°	1343.6	1320.5	1319.8	1310.8	1293.7	1282.5	1254.2	1219.2	1176.7	1147.6	1114.8
15°	1439.7	1418.1	1400.2	1383.8	1375.6	1342.9	1319.0	1275.0	1224.4	1193.1	1170.7
17.5°	1508.3	1498.6	1468.1	1460.6	1449.4	1411.4	1373.4	1330.2	1286.2	1242.3	1181.9
20°	1563.4	1557.5	1537.4	1526.9	1509.0	1479.2	1433.0	1383.1	1332.4	1269.8	1213.2
22.5°	1587.3	1579.8	1563.4	1554.5	1543.3	1518.0	1478.5	1421.9	1355.5	1299.6	1239.3
25°	1540.3	1553.8	1549.3	1545.6	1541.1	1526.2	1496.4	1446.4	1381.6	1318.3	1243.0
27.5°	1434.5	1457.6	1480.0	1483.0	1490.4	1496.4	1484.4	1448.7	1394.3	1327.2	1244.5
30°	1292.2	1302.6	1348.1	1361.5	1371.9	1409.9	1432.3	1423.3	1381.6	1321.2	1245.2
32.5°	1109.6	1137.2	1183.4	1215.4	1243.7	1286.2	1344.3	1367.5	1352.5	1303.4	1228.1
35°	936.7	969.5	1023.2	1064.2	1092.5	1152.8	1221.4	1271.3	1289.9	1265.4	1198.3
37.5°	795.1	834.6	882.3	898.0	930.8	1005.3	1099.9	1169.2	1214.7	1216.9	1164.8
40°	688.6	708.7	746.7	770.5	802.6	865.2	957.6	1049.2	1117.8	1140.9	1113.3
42.5°	598.4	614.0	642.4	671.4	700.5	748.2	833.1	918.8	1011.2	1057.4	1056.7
45°	526.9	543.3	562.6	586.5	606.6	658.0	725.1	813.0	892.8	964.3	982.2
47.5°	464.3	478.4	502.3	512.7	526.1	574.6	632.7	714.7	797.4	879.3	900.2
50°	418.1	430.0	446.4	453.1	468.0	503.8	551.5	617.8	709.4	784.7	823.5
52.5°	376.3	385.3	397.9	403.2	413.6	440.4	483.6	535.8	611.8	689.3	743.7
55°	340.6	346.5	355.5	361.4	368.9	392.7	424.8	471.7	537.3	604.4	657.3
57.5°	307.0	311.5	320.4	323.4	329.4	348.0	370.4	409.9	470.2	529.8	581.3
60°	275.7	278.7	283.9	290.6	295.1	307.8	328.6	361.4	409.9	464.3	506.0
62.5°	245.9	250.4	251.9	254.9	258.6	270.5	286.9	310.8	353.2	397.9	441.9
65°	215.4	219.1	222.1	222.8	226.5	235.5	250.4	271.3	298.8	337.6	378.6
67.5°	187.0	189.3	190.8	193.8	197.5	202.0	213.9	229.5	254.9	286.2	318.9
70°	161.0	161.0	163.2	163.9	168.4	173.6	178.8	193.8	216.1	241.4	263.8
72.5°	132.6	136.4	135.6	139.4	138.6	142.3	149.0	158.7	175.1	195.2	216.9
75°	108.1	110.3	110.3	110.3	111.8	114.8	118.5	127.4	140.1	156.5	169.2
77.5°	84.2	85.7	85.7	85.7	86.4	89.4	93.2	99.1	108.1	117.7	125.2
80°	60.4	61.9	61.9	63.3	63.3	64.1	67.8	70.8	75.3	82.7	90.2
82.5°	41.0	41.7	43.2	43.2	42.5	44.0	44.7	47.7	52.2	53.7	58.9
85°	22.4	23.1	23.8	23.8	24.6	26.1	25.3	28.3	28.3	31.3	32.8
87.5°	8.9	10.4	10.4	9.7	10.4	10.4	10.4	11.9	12.7	13.4	12.7
90°	10.0	9.8	9.7	9.6	9.4	8.9	8.4	8.0	7.5	6.9	6.3
92.5°	9.2	9.2	9.2	9.2	9.0	8.5	8.1	7.6	7.2	6.6	6.0
95°	9.8	9.7	9.6	9.6	9.4	8.9	8.4	8.0	7.5	7.4	7.4
97.5°	9.4	9.3	9.2	9.2	9.0	8.6	8.3	7.9	7.5	15.5	23.5
100°	9.4	9.3	9.2	9.2	9.8	11.1	12.4	13.7	15.0	25.5	36.0
102.5°	9.9	9.9	9.9	9.9	18.4	35.5	52.6	69.7	86.8	85.9	85.0
105°	102.9	105.6	108.3	109.7	109.4	108.7	108.0	107.3	106.6	106.2	105.8
107.5°	131.0	130.7	130.4	130.2	130.0	129.6	129.3	128.9	128.5	128.0	127.4
110°	152.0	151.7	151.5	151.4	151.3	151.2	151.0	150.9	150.7	150.3	149.8

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	172.7	172.4	172.1	171.9	171.9	172.0	172.1	172.2	172.3	172.1	172.0
115°	193.5	193.5	193.5	193.5	193.4	193.3	193.1	193.0	192.8	192.9	192.9
117.5°	214.3	214.3	214.3	214.3	214.3	214.4	214.5	214.5	214.6	214.4	214.2
120°	234.1	234.3	234.4	234.5	234.4	234.3	234.1	234.0	233.8	233.9	233.9
122.5°	253.2	253.4	253.5	253.6	253.6	253.5	253.4	253.4	253.3	253.1	253.0
125°	271.9	271.8	271.7	271.7	271.6	271.4	271.1	270.9	270.7	270.9	271.0
127.5°	289.0	289.1	289.2	289.2	289.2	289.3	289.4	289.4	289.5	289.1	288.7
130°	305.9	305.9	305.9	305.9	305.9	305.8	305.7	305.7	305.6	305.4	305.1
132.5°	321.8	321.9	322.0	322.0	322.0	321.9	321.8	321.7	321.6	321.3	321.0
135°	337.1	336.9	336.8	336.7	336.6	336.5	336.3	336.2	336.0	335.7	335.4
137.5°	350.8	350.9	351.0	351.0	350.9	350.8	350.6	350.5	350.3	349.9	349.5
140°	364.6	364.5	364.4	364.4	364.3	364.0	363.8	363.5	363.3	363.1	363.0
142.5°	376.3	376.3	376.3	376.3	376.2	376.1	375.9	375.8	375.6	375.5	375.5
145°	388.0	387.8	387.7	387.6	387.6	387.5	387.4	387.4	387.3	387.3	387.3
147.5°	398.0	397.9	397.8	397.8	397.8	397.7	397.6	397.6	397.5	397.6	397.6
150°	407.6	407.5	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.5	407.6
152.5°	416.1	416.2	416.3	416.3	416.2	416.1	415.9	415.8	415.6	415.8	415.9
155°	423.6	423.8	424.1	424.2	424.0	423.7	423.4	423.1	422.8	423.0	423.2
157.5°	430.1	430.4	430.8	431.0	430.8	430.4	430.1	429.7	429.3	429.6	429.9
160°	436.3	436.8	437.3	437.5	437.3	436.8	436.3	435.9	435.4	435.5	435.6
162.5°	441.3	441.8	442.3	442.6	442.4	441.9	441.5	441.0	440.6	440.7	440.7
165°	446.1	446.8	447.5	447.8	447.5	446.9	446.2	445.6	445.0	445.0	445.0
167.5°	449.6	450.4	451.1	451.5	451.2	450.5	449.8	449.1	448.4	448.5	448.6
170°	452.7	453.5	454.2	454.6	454.3	453.7	453.1	452.5	451.9	451.8	451.7
172.5°	454.5	455.4	456.2	456.6	456.3	455.7	455.1	454.5	453.9	453.8	453.8
175°	456.0	456.9	457.8	458.3	458.0	457.3	456.6	456.0	455.3	455.2	455.1
177.5°	456.7	457.6	458.5	459.0	458.7	458.1	457.5	456.9	456.3	456.1	456.0
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	927.8	924.8	922.6	922.6	915.9	909.1	905.4	903.9	902.4	896.5	888.3
5°	965.8	956.1	949.4	942.7	931.5	919.6	907.7	901.0	891.3	877.9	868.2
7.5°	1008.3	985.2	977.7	969.5	947.2	927.0	910.6	896.5	880.8	863.7	846.6
10°	1044.0	1019.4	1003.0	988.9	959.8	933.0	908.4	887.5	867.4	845.1	824.2
12.5°	1078.3	1043.3	1026.1	1005.3	974.7	936.0	903.9	877.9	848.0	824.9	799.6
15°	1126.0	1067.1	1038.8	1025.4	984.4	939.0	900.2	861.5	836.9	801.8	779.5
17.5°	1133.5	1085.8	1067.1	1032.9	983.7	932.3	887.5	848.8	811.5	780.2	751.2
20°	1159.5	1096.9	1067.1	1045.5	980.7	928.5	879.3	829.4	793.6	760.1	727.3
22.5°	1175.9	1105.1	1073.8	1039.6	977.7	915.1	857.0	813.8	769.8	735.5	709.4
25°	1171.5	1100.7	1065.6	1033.6	958.3	895.7	843.6	788.4	747.4	710.2	675.9
27.5°	1169.2	1089.5	1052.2	1016.5	945.7	880.1	814.5	769.8	724.3	681.1	655.8
30°	1163.3	1075.3	1032.1	993.4	919.6	851.0	795.1	743.0	697.5	658.0	624.5
32.5°	1143.1	1051.5	1009.8	968.0	891.3	822.7	766.1	717.6	672.2	631.2	599.1
35°	1116.3	1023.2	977.7	933.7	857.0	787.7	735.5	684.8	642.4	602.9	572.3
37.5°	1089.5	990.4	947.9	897.2	826.4	754.1	700.5	655.0	615.5	574.6	541.0
40°	1050.7	951.6	904.7	861.5	778.7	710.9	661.7	620.8	582.0	543.3	514.9
42.5°	997.8	909.1	860.7	813.0	735.5	668.4	620.8	584.2	547.7	515.7	484.4
45°	944.2	857.7	814.5	772.0	687.8	624.5	580.5	547.0	516.4	481.4	456.1
47.5°	879.3	806.3	763.1	721.4	641.6	578.3	538.0	506.7	478.4	449.4	425.5
50°	813.0	749.7	710.2	667.0	590.9	533.6	494.1	468.0	444.9	417.3	397.9
52.5°	741.5	686.3	652.8	611.1	544.0	491.1	450.8	424.8	405.4	385.3	368.1
55°	665.5	625.2	589.5	555.9	492.6	444.9	409.1	386.0	372.6	354.0	339.1
57.5°	596.9	558.2	536.5	498.5	443.4	396.4	368.1	348.8	333.1	321.9	310.0
60°	525.4	494.1	470.2	442.7	394.2	354.7	324.9	313.7	297.3	289.1	283.9
62.5°	456.8	434.5	412.1	391.2	348.0	310.8	288.4	274.2	264.5	256.4	251.9
65°	392.0	371.1	355.5	336.8	301.1	271.3	250.4	239.2	229.5	227.3	222.1
67.5°	328.6	319.7	302.6	287.6	257.1	234.0	218.3	204.2	199.0	196.7	192.3
70°	275.0	264.5	251.1	238.5	215.4	195.2	181.1	175.9	168.4	167.7	162.5
72.5°	226.5	213.9	204.2	194.5	177.4	159.5	152.0	144.6	140.8	137.9	135.6
75°	179.6	170.7	163.9	155.7	140.8	128.9	118.5	115.5	113.3	112.5	111.0
77.5°	134.1	128.2	125.2	117.0	106.6	96.1	91.7	87.2	87.2	85.7	86.4
80°	95.4	91.7	87.9	83.5	74.5	70.0	66.3	63.3	61.9	61.1	61.9
82.5°	60.4	58.1	57.4	54.4	48.4	46.2	43.2	41.0	41.0	41.0	41.0
85°	33.5	33.5	33.5	29.1	26.8	24.6	23.1	22.4	22.4	22.4	23.1
87.5°	14.2	14.2	11.9	11.9	11.2	9.7	8.9	8.9	9.7	9.7	10.4
90°	5.7	5.1	4.8	4.4	3.5	2.7	1.8	1.0	1.8	2.7	3.5
92.5°	5.3	4.7	4.4	4.5	4.6	4.8	4.9	5.1	4.9	4.8	4.6
95°	7.3	7.2	7.2	8.5	11.1	13.6	16.2	18.8	16.2	13.6	11.1
97.5°	31.4	39.4	43.4	42.6	40.9	39.2	37.6	35.9	37.6	39.2	40.9
100°	46.5	57.0	62.2	61.5	60.2	58.8	57.5	56.1	57.5	58.8	60.2
102.5°	84.1	83.2	82.7	82.2	81.3	80.4	79.5	78.6	79.5	80.4	81.3
105°	105.5	105.1	104.9	104.7	104.2	103.8	103.3	102.9	103.3	103.8	104.2
107.5°	126.9	126.4	126.1	126.0	125.8	125.5	125.3	125.1	125.3	125.5	125.8
110°	149.4	148.9	148.7	148.6	148.4	148.1	147.9	147.7	147.9	148.1	148.4

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	171.8	171.7	171.6	171.4	170.9	170.4	170.0	169.5	170.0	170.4	170.9
115°	193.0	193.1	193.1	193.0	192.8	192.5	192.3	192.1	192.3	192.5	192.8
117.5°	213.9	213.7	213.6	213.5	213.2	212.9	212.6	212.3	212.6	212.9	213.2
120°	234.0	234.1	234.1	234.0	233.7	233.4	233.1	232.8	233.1	233.4	233.7
122.5°	252.8	252.7	252.6	252.5	252.4	252.2	252.1	251.9	252.1	252.2	252.4
125°	271.2	271.3	271.4	271.2	270.9	270.6	270.3	270.0	270.3	270.6	270.9
127.5°	288.4	288.0	287.8	287.8	287.7	287.6	287.5	287.4	287.5	287.6	287.7
130°	304.9	304.6	304.5	304.5	304.4	304.3	304.3	304.2	304.3	304.3	304.4
132.5°	320.7	320.4	320.3	320.2	320.1	319.9	319.8	319.6	319.8	319.9	320.1
135°	335.1	334.8	334.6	334.6	334.7	334.8	334.9	335.0	334.9	334.8	334.7
137.5°	349.2	348.8	348.6	348.6	348.6	348.6	348.6	348.6	348.6	348.6	348.6
140°	362.8	362.7	362.6	362.5	362.4	362.3	362.1	362.0	362.1	362.3	362.4
142.5°	375.4	375.3	375.3	375.1	374.8	374.5	374.2	373.9	374.2	374.5	374.8
145°	387.3	387.3	387.3	387.2	386.9	386.7	386.4	386.2	386.4	386.7	386.9
147.5°	397.7	397.8	397.8	397.6	397.1	396.7	396.2	395.8	396.2	396.7	397.1
150°	407.7	407.8	407.8	407.6	407.3	407.0	406.7	406.4	406.7	407.0	407.3
152.5°	416.1	416.2	416.3	416.2	416.0	415.7	415.5	415.3	415.5	415.7	416.0
155°	423.5	423.7	423.8	423.8	423.7	423.6	423.6	423.5	423.6	423.6	423.7
157.5°	430.2	430.5	430.7	430.7	430.7	430.7	430.7	430.7	430.7	430.7	430.7
160°	435.7	435.8	435.8	435.9	436.1	436.4	436.6	436.8	436.6	436.4	436.1
162.5°	440.8	440.9	440.9	441.1	441.4	441.7	442.0	442.3	442.0	441.7	441.4
165°	445.0	445.0	445.0	445.2	445.6	445.9	446.3	446.7	446.3	445.9	445.6
167.5°	448.7	448.8	448.8	449.0	449.4	449.7	450.1	450.5	450.1	449.7	449.4
170°	451.6	451.5	451.5	451.7	452.2	452.7	453.1	453.6	453.1	452.7	452.2
172.5°	453.7	453.6	453.6	453.8	454.3	454.7	455.2	455.6	455.2	454.7	454.3
175°	455.0	454.9	454.9	455.1	455.6	456.1	456.5	457.0	456.5	456.1	455.6
177.5°	455.8	455.7	455.6	455.9	456.4	456.9	457.5	458.0	457.5	456.9	456.4
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	886.0	883.1	884.6	877.1	870.4	860.7	852.5	851.0	849.5	854.0	851.0
5°	860.7	857.0	853.3	844.3	830.9	822.7	810.8	810.0	805.6	798.9	800.3
7.5°	833.1	830.9	825.7	811.5	799.6	785.4	775.8	767.6	763.8	757.9	755.6
10°	810.8	802.6	798.1	782.5	768.3	753.4	740.7	734.8	728.1	722.8	719.1
12.5°	780.2	778.0	765.3	752.7	740.7	723.6	713.9	696.8	687.8	692.3	690.8
15°	760.1	749.7	746.7	728.8	708.7	697.5	679.6	668.4	664.7	658.0	649.8
17.5°	733.3	726.6	716.1	699.7	676.6	661.0	648.3	637.9	633.4	624.5	617.8
20°	707.9	696.8	688.6	673.7	651.3	631.2	615.5	608.8	597.7	590.2	586.5
22.5°	684.8	676.6	664.7	642.4	623.0	603.6	585.0	575.3	564.9	560.4	554.4
25°	656.5	643.1	634.9	610.3	589.5	573.8	556.7	544.0	538.0	530.6	529.1
27.5°	629.0	616.3	606.6	585.0	559.6	539.5	529.1	520.2	509.7	509.7	506.0
30°	601.4	592.4	577.5	556.7	532.8	513.4	501.5	493.3	489.6	486.6	485.9
32.5°	573.8	561.9	552.9	524.6	506.7	488.9	479.9	473.2	468.7	468.0	468.7
35°	545.5	532.1	523.1	497.8	479.9	463.5	459.8	453.8	451.6	450.8	454.6
37.5°	515.7	505.2	494.1	473.2	453.1	443.4	435.9	433.7	433.0	437.4	438.9
40°	488.1	479.2	468.7	446.4	431.5	421.0	417.3	415.1	418.1	422.5	424.8
42.5°	462.0	449.4	441.2	421.0	407.6	401.7	397.2	397.2	400.2	405.4	409.1
45°	434.5	424.8	416.6	398.7	386.8	380.1	379.3	380.1	383.8	387.5	392.0
47.5°	407.6	397.9	389.0	374.1	363.7	359.9	359.2	359.9	365.9	371.1	376.3
50°	383.0	372.6	364.4	350.2	342.0	337.6	338.3	342.0	346.5	354.0	360.7
52.5°	354.0	346.5	339.1	326.4	318.9	316.0	318.2	321.2	329.4	334.6	342.8
55°	325.7	318.9	313.0	303.3	297.3	295.1	296.6	301.1	307.8	316.7	326.4
57.5°	299.6	292.1	286.2	279.5	272.7	273.5	274.2	280.2	288.4	296.6	307.8
60°	270.5	266.0	260.8	252.6	249.6	249.6	251.9	258.6	266.0	279.5	289.1
62.5°	244.4	238.5	234.7	229.5	225.1	225.8	231.0	237.0	245.9	257.1	269.8
65°	217.6	210.9	207.9	203.4	202.0	202.7	206.4	215.4	225.1	234.7	246.7
67.5°	187.8	185.6	182.6	178.1	179.6	180.3	184.1	191.5	202.0	211.6	225.1
70°	162.5	158.0	157.2	153.5	153.5	155.7	163.2	168.4	178.1	188.5	202.7
72.5°	135.6	131.9	131.9	128.9	131.2	133.4	137.1	144.6	153.5	163.9	175.9
75°	108.1	106.6	108.1	106.6	106.6	110.3	114.8	120.7	130.4	141.6	151.3
77.5°	83.5	83.5	82.7	85.0	85.0	87.2	93.2	99.1	106.6	115.5	125.9
80°	61.1	61.1	61.1	63.3	65.6	65.6	69.3	76.8	83.5	89.4	99.1
82.5°	41.7	41.7	41.7	43.2	46.2	46.2	50.7	55.1	62.6	67.8	72.3
85°	25.3	25.3	24.6	26.1	26.8	29.1	32.8	35.8	39.5	44.0	48.4
87.5°	11.2	11.2	11.9	12.7	13.4	14.9	16.4	17.9	21.6	23.1	25.3
90°	4.4	4.8	5.1	5.7	6.3	6.9	7.5	8.0	8.4	8.9	9.4
92.5°	4.5	4.4	4.7	5.3	6.0	6.6	7.2	7.6	8.1	8.5	9.0
95°	8.5	7.2	7.2	7.3	7.4	7.4	7.5	8.0	8.4	8.9	9.4
97.5°	42.6	43.4	39.4	31.4	23.5	15.5	7.5	7.9	8.3	8.6	9.0
100°	61.5	62.2	57.0	46.5	36.0	25.5	15.0	13.7	12.4	11.1	9.8
102.5°	82.2	82.7	83.2	84.1	85.0	85.9	86.8	69.7	52.6	35.5	18.4
105°	104.7	104.9	105.1	105.5	105.8	106.2	106.6	107.3	108.0	108.7	109.4
107.5°	126.0	126.1	126.4	126.9	127.4	128.0	128.5	128.9	129.3	129.6	130.0
110°	148.6	148.7	148.9	149.4	149.8	150.3	150.7	150.9	151.0	151.2	151.3

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	171.4	171.6	171.7	171.8	172.0	172.1	172.3	172.2	172.1	172.0	171.9
115°	193.0	193.1	193.1	193.0	192.9	192.9	192.8	193.0	193.1	193.3	193.4
117.5°	213.5	213.6	213.7	213.9	214.2	214.4	214.6	214.5	214.5	214.4	214.3
120°	234.0	234.1	234.1	234.0	233.9	233.9	233.8	234.0	234.1	234.3	234.4
122.5°	252.5	252.6	252.7	252.8	253.0	253.1	253.3	253.4	253.4	253.5	253.6
125°	271.2	271.4	271.3	271.2	271.0	270.9	270.7	270.9	271.1	271.4	271.6
127.5°	287.8	287.8	288.0	288.4	288.7	289.1	289.5	289.4	289.4	289.3	289.2
130°	304.5	304.5	304.6	304.9	305.1	305.4	305.6	305.7	305.7	305.8	305.9
132.5°	320.2	320.3	320.4	320.7	321.0	321.3	321.6	321.7	321.8	321.9	322.0
135°	334.6	334.6	334.8	335.1	335.4	335.7	336.0	336.2	336.3	336.5	336.6
137.5°	348.6	348.6	348.8	349.2	349.5	349.9	350.3	350.5	350.6	350.8	350.9
140°	362.5	362.6	362.7	362.8	363.0	363.1	363.3	363.5	363.8	364.0	364.3
142.5°	375.1	375.3	375.3	375.4	375.5	375.5	375.6	375.8	375.9	376.1	376.2
145°	387.2	387.3	387.3	387.3	387.3	387.3	387.3	387.4	387.4	387.5	387.6
147.5°	397.6	397.8	397.8	397.7	397.6	397.6	397.5	397.6	397.6	397.7	397.8
150°	407.6	407.8	407.8	407.7	407.6	407.5	407.4	407.4	407.4	407.4	407.4
152.5°	416.2	416.3	416.2	416.1	415.9	415.8	415.6	415.8	415.9	416.1	416.2
155°	423.8	423.8	423.7	423.5	423.2	423.0	422.8	423.1	423.4	423.7	424.0
157.5°	430.7	430.7	430.5	430.2	429.9	429.6	429.3	429.7	430.1	430.4	430.8
160°	435.9	435.8	435.8	435.7	435.6	435.5	435.4	435.9	436.3	436.8	437.3
162.5°	441.1	440.9	440.9	440.8	440.7	440.7	440.6	441.0	441.5	441.9	442.4
165°	445.2	445.0	445.0	445.0	445.0	445.0	445.0	445.6	446.2	446.9	447.5
167.5°	449.0	448.8	448.8	448.7	448.6	448.5	448.4	449.1	449.8	450.5	451.2
170°	451.7	451.5	451.5	451.6	451.7	451.8	451.9	452.5	453.1	453.7	454.3
172.5°	453.8	453.6	453.6	453.7	453.8	453.8	453.9	454.5	455.1	455.7	456.3
175°	455.1	454.9	454.9	455.0	455.1	455.2	455.3	456.0	456.6	457.3	458.0
177.5°	455.9	455.6	455.7	455.8	456.0	456.1	456.3	456.9	457.5	458.1	458.7
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	848.8	848.0	844.3	845.8	841.3	842.8	845.1	845.8	848.8	846.6	845.8
5°	796.6	795.1	792.9	790.7	789.9	792.9	787.7	789.2	790.7	792.9	795.9
7.5°	754.1	753.4	751.2	747.4	745.9	744.5	745.2	750.4	749.7	748.9	754.1
10°	715.4	716.1	711.7	710.9	706.5	705.7	706.5	707.9	710.2	713.2	713.9
12.5°	675.2	684.8	676.6	673.7	667.0	670.7	672.2	665.5	669.2	671.4	682.6
15°	649.8	645.3	640.1	640.1	637.1	635.7	631.9	637.1	640.1	644.6	643.1
17.5°	614.8	607.3	604.4	601.4	602.1	605.1	596.9	608.8	608.8	611.1	607.3
20°	584.2	578.3	574.6	573.1	570.8	569.3	568.6	571.6	576.0	577.5	581.3
22.5°	552.2	552.2	546.2	544.0	542.5	540.3	544.0	541.8	544.7	547.7	553.7
25°	525.4	525.4	523.1	520.2	517.9	516.4	518.7	517.9	520.2	523.9	525.4
27.5°	503.8	501.5	500.8	500.0	499.3	500.0	499.3	501.5	503.8	504.5	503.0
30°	485.1	482.9	483.6	483.6	484.4	483.6	482.9	485.1	485.9	484.4	485.1
32.5°	468.0	468.0	469.5	470.2	470.2	471.0	471.7	470.2	471.0	468.7	469.5
35°	453.8	455.3	456.8	457.6	458.3	457.6	459.0	458.3	456.8	455.3	454.6
37.5°	439.7	441.2	444.1	444.9	447.1	447.9	446.4	446.4	445.6	442.7	441.2
40°	424.8	426.3	430.0	432.2	433.7	435.9	434.5	434.5	431.5	428.5	426.3
42.5°	410.6	413.6	417.3	419.6	422.5	422.5	422.5	421.0	417.3	414.3	412.1
45°	396.4	397.2	402.4	406.1	409.1	409.1	409.1	406.9	404.6	398.7	395.7
47.5°	380.8	383.0	389.0	392.7	395.7	396.4	396.4	394.2	389.7	384.5	380.8
50°	363.7	367.4	374.1	379.3	383.0	384.5	382.3	380.8	375.6	369.6	365.2
52.5°	347.3	351.7	359.9	364.4	369.6	370.4	369.6	367.4	361.4	353.2	349.5
55°	330.9	334.6	343.5	351.0	355.5	357.0	355.5	351.7	344.3	336.1	332.4
57.5°	313.0	318.2	327.9	335.3	340.6	341.3	339.8	336.1	330.1	319.7	314.5
60°	294.4	301.1	310.8	318.2	324.9	325.7	324.2	318.9	311.5	301.1	296.6
62.5°	275.7	280.9	292.1	300.3	305.5	309.3	306.3	301.1	293.6	283.2	276.5
65°	254.1	261.6	271.3	278.7	284.7	285.4	283.9	279.5	271.3	260.1	254.9
67.5°	233.2	238.5	248.2	257.8	260.1	262.3	260.1	255.6	248.9	239.2	231.8
70°	207.9	212.4	224.3	231.0	234.0	236.2	234.7	230.3	224.3	215.4	209.4
72.5°	182.6	186.3	197.5	202.7	208.7	207.9	207.2	204.2	196.0	190.0	186.3
75°	155.7	160.2	167.7	174.4	176.6	176.6	176.6	174.4	169.2	159.5	155.7
77.5°	131.2	133.4	139.4	143.1	145.3	146.1	145.3	141.6	138.6	131.9	129.7
80°	100.6	106.6	111.0	111.8	114.8	114.8	114.8	113.3	110.3	103.6	102.8
82.5°	76.0	77.5	82.0	84.2	85.7	85.0	85.0	82.0	81.2	77.5	76.0
85°	51.4	53.7	52.9	55.9	56.6	55.1	55.1	56.6	52.9	53.7	51.4
87.5°	28.3	28.3	29.8	29.1	32.0	32.0	30.6	31.3	29.8	29.1	28.3
90°	9.6	9.7	9.8	10.0	10.1	10.3	10.1	10.0	9.8	9.7	9.6
92.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
95°	9.6	9.6	9.7	9.8	9.8	9.9	9.8	9.8	9.7	9.6	9.6
97.5°	9.2	9.2	9.3	9.4	9.5	9.6	9.5	9.4	9.3	9.2	9.2
100°	9.2	9.2	9.3	9.4	9.5	9.6	9.5	9.4	9.3	9.2	9.2
102.5°	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
105°	109.7	108.3	105.6	102.9	100.1	97.4	100.1	102.9	105.6	108.3	109.7
107.5°	130.2	130.4	130.7	131.0	131.3	131.6	131.3	131.0	130.7	130.4	130.2
110°	151.4	151.5	151.7	152.0	152.2	152.4	152.2	152.0	151.7	151.5	151.4

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	171.9	172.1	172.4	172.7	173.0	173.3	173.0	172.7	172.4	172.1	171.9
115°	193.5	193.5	193.5	193.5	193.5	193.5	193.5	193.5	193.5	193.5	193.5
117.5°	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3	214.3
120°	234.5	234.4	234.3	234.1	234.0	233.8	234.0	234.1	234.3	234.4	234.5
122.5°	253.6	253.5	253.4	253.2	253.1	252.9	253.1	253.2	253.4	253.5	253.6
125°	271.7	271.7	271.8	271.9	272.0	272.1	272.0	271.9	271.8	271.7	271.7
127.5°	289.2	289.2	289.1	289.0	288.9	288.8	288.9	289.0	289.1	289.2	289.2
130°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9
132.5°	322.0	322.0	321.9	321.8	321.7	321.6	321.7	321.8	321.9	322.0	322.0
135°	336.7	336.8	336.9	337.1	337.2	337.4	337.2	337.1	336.9	336.8	336.7
137.5°	351.0	351.0	350.9	350.8	350.8	350.7	350.8	350.8	350.9	351.0	351.0
140°	364.4	364.4	364.5	364.6	364.6	364.7	364.6	364.6	364.5	364.4	364.4
142.5°	376.3	376.3	376.3	376.3	376.3	376.3	376.3	376.3	376.3	376.3	376.3
145°	387.6	387.7	387.8	388.0	388.1	388.3	388.1	388.0	387.8	387.7	387.6
147.5°	397.8	397.8	397.9	398.0	398.1	398.2	398.1	398.0	397.9	397.8	397.8
150°	407.4	407.4	407.5	407.6	407.7	407.8	407.7	407.6	407.5	407.4	407.4
152.5°	416.3	416.3	416.2	416.1	416.1	416.0	416.1	416.1	416.2	416.3	416.3
155°	424.2	424.1	423.8	423.6	423.3	423.1	423.3	423.6	423.8	424.1	424.2
157.5°	431.0	430.8	430.4	430.1	429.7	429.3	429.7	430.1	430.4	430.8	431.0
160°	437.5	437.3	436.8	436.3	435.9	435.4	435.9	436.3	436.8	437.3	437.5
162.5°	442.6	442.3	441.8	441.3	440.7	440.2	440.7	441.3	441.8	442.3	442.6
165°	447.8	447.5	446.8	446.1	445.4	444.7	445.4	446.1	446.8	447.5	447.8
167.5°	451.5	451.1	450.4	449.6	448.9	448.1	448.9	449.6	450.4	451.1	451.5
170°	454.6	454.2	453.5	452.7	452.0	451.2	452.0	452.7	453.5	454.2	454.6
172.5°	456.6	456.2	455.4	454.5	453.7	452.9	453.7	454.5	455.4	456.2	456.6
175°	458.3	457.8	456.9	456.0	455.1	454.2	455.1	456.0	456.9	457.8	458.3
177.5°	459.0	458.5	457.6	456.7	455.8	454.9	455.8	456.7	457.6	458.5	459.0
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	845.8	850.3	845.8	848.8	850.3	854.0	855.5	862.2	864.4	869.7	869.7
5°	795.1	797.4	798.1	801.1	804.1	811.5	816.7	826.4	837.6	839.1	845.8
7.5°	754.1	757.9	763.8	761.6	766.8	778.0	784.7	796.6	807.8	813.8	822.0
10°	717.6	722.1	724.3	726.6	736.3	745.9	756.4	764.6	779.5	788.4	795.1
12.5°	687.8	684.1	688.6	696.8	707.9	713.9	728.1	740.7	751.9	761.6	767.6
15°	649.1	652.1	656.5	670.7	673.7	688.6	693.8	707.9	728.8	737.8	745.2
17.5°	611.8	621.5	630.4	635.7	644.6	656.5	671.4	687.1	700.5	710.9	719.9
20°	582.0	591.7	596.9	600.6	609.6	626.0	640.1	659.5	676.6	684.8	696.8
22.5°	558.2	558.2	565.6	576.8	582.0	597.7	609.6	630.4	649.1	659.5	670.7
25°	528.3	532.8	538.8	548.5	555.9	568.6	585.7	603.6	623.7	632.7	646.8
27.5°	503.8	509.0	517.2	519.4	526.9	538.0	555.9	575.3	596.2	605.9	617.8
30°	485.1	488.1	491.1	495.6	502.3	512.0	526.9	544.0	569.3	576.8	591.7
32.5°	468.7	470.2	471.7	475.4	479.2	488.9	500.8	519.4	540.3	551.5	564.9
35°	453.8	452.3	453.1	455.3	459.0	462.8	475.4	491.1	510.5	523.9	534.3
37.5°	439.7	436.7	435.9	435.9	437.4	441.9	451.6	465.0	485.9	497.1	507.5
40°	424.0	421.0	419.6	418.8	418.1	421.0	428.5	441.9	458.3	468.7	480.7
42.5°	409.1	406.1	402.4	401.7	400.2	401.7	406.9	419.6	433.7	444.1	453.8
45°	394.2	389.0	384.5	381.5	382.3	380.1	383.8	393.5	409.9	416.6	426.3
47.5°	377.8	371.9	365.9	362.9	359.9	361.4	362.9	371.1	385.3	392.0	401.7
50°	362.2	354.0	347.3	343.5	341.3	339.8	341.3	349.5	359.9	365.9	374.1
52.5°	344.3	336.1	329.4	323.4	320.4	318.2	318.9	326.4	336.1	342.0	350.2
55°	327.9	317.5	308.5	301.1	298.8	298.1	297.3	302.6	310.8	316.7	323.4
57.5°	309.3	298.8	289.1	280.2	275.7	275.0	275.0	276.5	286.9	291.4	295.1
60°	290.6	279.5	269.0	260.8	254.1	251.9	251.1	254.1	259.3	263.8	269.0
62.5°	269.8	258.6	245.9	238.5	231.8	225.8	228.0	228.8	236.2	238.5	242.9
65°	249.6	237.0	226.5	214.6	207.2	203.4	202.0	203.4	209.4	210.1	213.1
67.5°	226.5	214.6	202.0	193.8	187.0	180.3	178.8	178.8	181.8	184.1	187.8
70°	204.2	192.3	178.1	169.2	162.5	156.5	154.3	153.5	155.7	157.2	161.0
72.5°	178.1	166.2	155.7	146.1	137.9	133.4	131.2	129.7	131.9	133.4	134.1
75°	150.5	140.8	130.4	120.7	115.5	111.0	108.1	105.8	107.3	107.3	107.3
77.5°	124.4	114.8	106.6	99.9	93.2	87.9	85.7	83.5	84.2	84.2	85.7
80°	96.9	90.2	83.5	77.5	71.5	67.1	65.6	63.3	61.9	61.1	61.1
82.5°	71.5	66.3	60.4	55.1	52.2	47.7	46.2	43.2	43.2	42.5	42.5
85°	47.7	44.7	38.8	35.0	32.8	30.6	29.1	27.6	25.3	25.3	24.6
87.5°	25.3	23.8	22.4	17.9	17.9	15.6	14.9	14.2	11.9	12.7	12.7
90°	9.4	8.9	8.4	8.0	7.5	6.9	6.3	5.7	5.1	4.8	4.4
92.5°	9.0	8.5	8.1	7.6	7.2	6.6	6.0	5.3	4.7	4.4	4.5
95°	9.4	8.9	8.4	8.0	7.5	7.4	7.4	7.3	7.2	7.2	8.5
97.5°	9.0	8.6	8.3	7.9	7.5	15.5	23.5	31.4	39.4	43.4	42.6
100°	9.8	11.1	12.4	13.7	15.0	25.5	36.0	46.5	57.0	62.2	61.5
102.5°	18.4	35.5	52.6	69.7	86.8	85.9	85.0	84.1	83.2	82.7	82.2
105°	109.4	108.7	108.0	107.3	106.6	106.2	105.8	105.5	105.1	104.9	104.7
107.5°	130.0	129.6	129.3	128.9	128.5	128.0	127.4	126.9	126.4	126.1	126.0
110°	151.3	151.2	151.0	150.9	150.7	150.3	149.8	149.4	148.9	148.7	148.6

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	171.9	172.0	172.1	172.2	172.3	172.1	172.0	171.8	171.7	171.6	171.4
115°	193.4	193.3	193.1	193.0	192.8	192.9	192.9	193.0	193.1	193.1	193.0
117.5°	214.3	214.4	214.5	214.5	214.6	214.4	214.2	213.9	213.7	213.6	213.5
120°	234.4	234.3	234.1	234.0	233.8	233.9	233.9	234.0	234.1	234.1	234.0
122.5°	253.6	253.5	253.4	253.4	253.3	253.1	253.0	252.8	252.7	252.6	252.5
125°	271.6	271.4	271.1	270.9	270.7	270.9	271.0	271.2	271.3	271.4	271.2
127.5°	289.2	289.3	289.4	289.4	289.5	289.1	288.7	288.4	288.0	287.8	287.8
130°	305.9	305.8	305.7	305.7	305.6	305.4	305.1	304.9	304.6	304.5	304.5
132.5°	322.0	321.9	321.8	321.7	321.6	321.3	321.0	320.7	320.4	320.3	320.2
135°	336.6	336.5	336.3	336.2	336.0	335.7	335.4	335.1	334.8	334.6	334.6
137.5°	350.9	350.8	350.6	350.5	350.3	349.9	349.5	349.2	348.8	348.6	348.6
140°	364.3	364.0	363.8	363.5	363.3	363.1	363.0	362.8	362.7	362.6	362.5
142.5°	376.2	376.1	375.9	375.8	375.6	375.5	375.5	375.4	375.3	375.3	375.1
145°	387.6	387.5	387.4	387.4	387.3	387.3	387.3	387.3	387.3	387.3	387.2
147.5°	397.8	397.7	397.6	397.6	397.5	397.6	397.6	397.7	397.8	397.8	397.6
150°	407.4	407.4	407.4	407.4	407.4	407.5	407.6	407.7	407.8	407.8	407.6
152.5°	416.2	416.1	415.9	415.8	415.6	415.8	415.9	416.1	416.2	416.3	416.2
155°	424.0	423.7	423.4	423.1	422.8	423.0	423.2	423.5	423.7	423.8	423.8
157.5°	430.8	430.4	430.1	429.7	429.3	429.6	429.9	430.2	430.5	430.7	430.7
160°	437.3	436.8	436.3	435.9	435.4	435.5	435.6	435.7	435.8	435.8	435.9
162.5°	442.4	441.9	441.5	441.0	440.6	440.7	440.7	440.8	440.9	440.9	441.1
165°	447.5	446.9	446.2	445.6	445.0	445.0	445.0	445.0	445.0	445.0	445.2
167.5°	451.2	450.5	449.8	449.1	448.4	448.5	448.6	448.7	448.8	448.8	449.0
170°	454.3	453.7	453.1	452.5	451.9	451.8	451.7	451.6	451.5	451.5	451.7
172.5°	456.3	455.7	455.1	454.5	453.9	453.8	453.8	453.7	453.6	453.6	453.8
175°	458.0	457.3	456.6	456.0	455.3	455.2	455.1	455.0	454.9	454.9	455.1
177.5°	458.7	458.1	457.5	456.9	456.3	456.1	456.0	455.8	455.7	455.6	455.9
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	899.5	899.5	899.5	899.5
2.5°	874.9	882.3	889.0	899.5
5°	855.5	865.9	880.1	895.7
7.5°	833.1	849.5	868.2	889.8
10°	812.3	830.9	854.7	880.8
12.5°	790.7	813.0	839.1	867.4
15°	766.1	788.4	817.5	855.5
17.5°	743.7	770.5	801.8	842.1
20°	717.6	743.0	777.2	823.5
22.5°	694.5	723.6	761.6	801.8
25°	669.2	694.5	732.5	781.0
27.5°	643.9	675.2	711.7	758.6
30°	619.3	645.3	684.8	734.0
32.5°	592.4	623.7	660.3	706.5
35°	563.4	593.2	627.5	677.4
37.5°	537.3	566.4	601.4	645.3
40°	508.2	538.8	570.8	614.8
42.5°	479.9	507.5	539.5	579.8
45°	452.3	476.2	505.2	540.3
47.5°	424.0	444.1	471.0	502.3
50°	393.5	415.1	435.2	461.3
52.5°	365.2	383.8	400.2	421.8
55°	337.6	350.2	363.7	380.1
57.5°	308.5	318.2	327.9	345.0
60°	279.5	288.4	293.6	304.8
62.5°	251.1	254.9	261.6	268.3
65°	219.8	225.1	228.8	237.0
67.5°	191.5	193.8	197.5	202.7
70°	161.7	166.9	168.4	172.1
72.5°	136.4	138.6	140.1	140.8
75°	108.1	110.3	111.8	116.3
77.5°	85.0	84.2	87.2	87.9
80°	62.6	60.4	61.1	64.1
82.5°	41.0	41.7	41.0	41.0
85°	25.3	24.6	23.1	23.8
87.5°	11.2	11.2	10.4	10.4
90°	3.5	2.7	1.8	1.0
92.5°	4.6	4.8	4.9	5.1
95°	11.1	13.6	16.2	18.8
97.5°	40.9	39.2	37.6	35.9
100°	60.2	58.8	57.5	56.1
102.5°	81.3	80.4	79.5	78.6
105°	104.2	103.8	103.3	102.9
107.5°	125.8	125.5	125.3	125.1
110°	148.4	148.1	147.9	147.7

TEST NUMBER: P1001568

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	170.9	170.4	170.0	169.5
115°	192.8	192.5	192.3	192.1
117.5°	213.2	212.9	212.6	212.3
120°	233.7	233.4	233.1	232.8
122.5°	252.4	252.2	252.1	251.9
125°	270.9	270.6	270.3	270.0
127.5°	287.7	287.6	287.5	287.4
130°	304.4	304.3	304.3	304.2
132.5°	320.1	319.9	319.8	319.6
135°	334.7	334.8	334.9	335.0
137.5°	348.6	348.6	348.6	348.6
140°	362.4	362.3	362.1	362.0
142.5°	374.8	374.5	374.2	373.9
145°	386.9	386.7	386.4	386.2
147.5°	397.1	396.7	396.2	395.8
150°	407.3	407.0	406.7	406.4
152.5°	416.0	415.7	415.5	415.3
155°	423.7	423.6	423.6	423.5
157.5°	430.7	430.7	430.7	430.7
160°	436.1	436.4	436.6	436.8
162.5°	441.4	441.7	442.0	442.3
165°	445.6	445.9	446.3	446.7
167.5°	449.4	449.7	450.1	450.5
170°	452.2	452.7	453.1	453.6
172.5°	454.3	454.7	455.2	455.6
175°	455.6	456.1	456.5	457.0
177.5°	456.4	456.9	457.5	458.0
180°	457.0	457.0	457.0	457.0

(END OF REPORT)