

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001611

Luminaire Tested: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001611
REPORT IS A COMBINATION OF REPORTS P996233 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4653.0 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	69	62	57	59	55	51	51	47	44	43	40	38
4	76	65	57	51	70	61	54	49	53	48	43	46	41	38	39	36	33
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	30	51	41	34	29	36	30	26	31	27	23	27	23	21
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7660	7660	7660	7660
5°	7640	8788	7685	6603
10°	7584	10252	7641	5793
15°	7492	11819	7544	5183
20°	7395	12816	7449	4647
25°	7254	12669	7323	4252
30°	7116	10472	7202	4048
35°	6921	7803	6997	3924
40°	6694	5878	6759	3864
45°	6348	4718	6427	3781
50°	5934	3975	6020	3743
55°	5448	3459	5533	3699
60°	4976	3046	5121	3637
65°	4533	2621	4575	3486
70°	4011	2157	4098	3210
75°	3498	1657	3475	2726
80°	2751	1088	2719	2069
85°	1812	488	1696	1207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9904 cd/sqm

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	2.0
10°-20°	282.2	6.1
20°-30°	448.3	9.6
30°-40°	498.1	10.7
40°-50°	453.0	9.7
50°-60°	370.2	8.0
60°-70°	264.2	5.7
70°-80°	145.4	3.1
80°-90°	40.9	0.9
90°-100°	48.4	1.0
100°-110°	144.9	3.1
110°-120°	246.2	5.3
120°-130°	324.7	7.0
130°-140°	364.7	7.8
140°-150°	358.4	7.7
150°-160°	301.4	6.5
160°-170°	200.6	4.3
170°-180°	70.2	1.5
0°-30°	821.9	17.7
0°-40°	1320.0	28.4
0°-60°	2143.1	46.1
0°-90°	2593.6	55.7
90°-120°	439.5	9.4
90°-150°	1487.2	32.0
90°-180°	2059.0	44.3
0°-180°	4653.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	939	939	939	939	939	
5°	935	1102	941	828	935	89
15°	893	1514	900	664	893	252
25°	816	1607	823	539	816	376
35°	707	950	715	478	707	442
45°	564	533	571	427	564	435
55°	397	349	403	373	397	357
65°	248	224	250	298	248	244
75°	121	112	121	184	121	127
85°	25	23	23	58	25	29
90°	2	17	2	17	2	4
95°	34	45	34	45	34	37
105°	134	140	134	140	134	142
115°	250	248	250	248	250	247
125°	364	362	364	362	364	325
135°	470	471	470	471	470	364
145°	571	572	571	572	571	358
155°	654	654	654	654	654	301
165°	712	711	712	711	712	201
175°	741	738	741	738	741	70
180°	742	742	742	742	742	

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	939.3	948.7	952.6	955.7	965.8	968.9	969.7	974.3	978.2	979.0	979.0
5°	935.4	950.2	961.9	972.8	989.1	996.1	1004.7	1014.0	1026.5	1034.3	1038.2
7.5°	929.2	951.0	968.9	987.6	1010.1	1024.2	1031.9	1056.8	1074.0	1088.0	1105.1
10°	919.9	947.9	973.6	1000.8	1032.7	1049.8	1067.0	1097.3	1121.4	1148.7	1170.5
12.5°	905.9	942.4	973.6	1011.7	1051.4	1071.6	1091.9	1144.8	1172.8	1196.9	1235.8
15°	893.4	930.0	974.3	1013.3	1062.3	1092.6	1122.2	1156.5	1200.8	1253.0	1290.3
17.5°	879.4	925.3	966.6	1021.0	1075.5	1104.3	1128.4	1181.4	1243.6	1295.0	1329.2
20°	859.9	906.6	961.1	1018.7	1083.3	1105.9	1137.8	1208.6	1264.6	1315.2	1371.2
22.5°	837.4	891.9	949.4	1004.7	1071.6	1119.1	1154.1	1216.4	1284.1	1342.4	1405.5
25°	815.6	874.7	925.3	1000.8	1071.6	1103.5	1143.2	1217.2	1291.1	1361.9	1426.5
27.5°	792.2	847.5	916.0	975.9	1056.1	1091.1	1133.9	1214.8	1293.4	1364.2	1433.5
30°	766.6	825.7	882.5	953.3	1031.2	1076.3	1116.0	1203.9	1284.1	1358.0	1422.6
32.5°	737.8	793.8	854.5	921.4	1003.1	1049.1	1098.9	1189.1	1274.7	1338.6	1388.4
35°	707.4	764.2	817.1	885.6	969.7	1015.6	1063.8	1163.5	1248.3	1300.4	1329.2
37.5°	673.9	727.6	779.8	847.5	931.5	980.6	1029.6	1126.1	1206.3	1249.8	1242.1
40°	642.0	690.3	738.5	802.4	890.3	942.4	985.2	1082.5	1152.6	1171.2	1145.6
42.5°	605.5	646.7	693.4	758.8	844.4	893.4	947.1	1035.8	1088.0	1080.2	1036.6
45°	564.2	600.8	647.5	709.0	796.1	846.7	891.9	975.9	1014.0	994.6	915.2
47.5°	524.5	560.3	598.5	659.9	744.8	787.6	833.5	909.0	930.8	889.5	810.1
50°	481.7	511.3	551.0	609.4	688.7	733.9	772.0	832.7	840.5	789.9	707.4
52.5°	440.5	465.4	503.5	561.1	635.0	670.8	708.2	761.9	755.7	703.5	624.1
55°	396.9	420.2	455.3	508.2	573.6	607.8	639.7	687.2	673.9	620.3	551.0
57.5°	360.3	376.7	410.9	459.9	513.6	551.0	578.2	615.6	595.3	541.6	477.1
60°	318.3	338.5	367.3	407.0	459.9	484.8	509.0	533.9	519.9	468.5	410.9
62.5°	280.2	295.7	320.6	358.8	400.0	422.6	448.3	463.8	449.8	402.3	354.1
65°	247.5	259.9	279.4	310.5	350.2	368.9	383.7	398.5	386.8	342.4	307.4
67.5°	211.7	222.6	238.9	263.8	297.3	310.5	324.5	334.6	321.4	291.8	257.6
70°	179.8	187.6	203.1	221.8	245.1	257.6	269.3	279.4	267.7	242.8	217.1
72.5°	147.1	153.3	167.3	180.5	201.6	210.1	218.7	226.5	222.6	199.2	178.2
75°	121.4	123.7	133.1	144.0	157.2	166.5	172.8	177.4	174.3	155.6	142.4
77.5°	91.8	94.9	101.9	110.5	122.2	127.6	131.5	136.2	132.3	117.5	108.2
80°	66.9	67.7	71.6	79.4	87.2	87.9	91.8	98.1	95.7	85.6	78.6
82.5°	42.8	45.1	46.7	51.4	56.8	58.4	60.7	62.3	61.5	55.3	52.9
85°	24.9	24.9	26.5	29.6	31.1	33.5	34.2	35.0	36.6	32.7	30.4
87.5°	10.9	11.7	11.7	12.5	14.0	14.0	14.8	15.6	16.3	15.6	13.2
90°	1.7	3.1	4.5	5.9	7.3	8.0	8.5	9.5	10.6	11.6	12.6
92.5°	14.9	16.6	18.2	19.9	21.6	22.4	22.7	23.4	24.0	24.7	25.3
95°	34.4	35.6	36.7	37.9	39.0	39.6	40.0	40.9	41.8	42.7	43.6
97.5°	55.1	56.1	57.1	58.2	59.2	59.7	60.2	61.2	62.3	63.3	64.3
100°	80.4	80.9	81.4	81.9	82.4	82.7	83.3	84.4	85.5	86.7	87.8
102.5°	106.8	106.9	107.0	107.1	107.2	107.3	107.8	108.8	109.9	110.9	111.9
105°	133.8	133.9	134.0	134.1	134.2	134.3	134.6	135.1	135.6	136.1	136.6
107.5°	161.9	162.0	162.2	162.3	162.4	162.5	162.6	162.7	162.8	162.9	163.0
110°	190.6	190.8	191.1	191.3	191.6	191.7	191.6	191.5	191.4	191.3	191.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	220.4	220.4	220.4	220.4	220.4	220.4	220.3	220.0	219.8	219.5	219.3
115°	250.3	250.3	250.3	250.3	250.3	250.3	250.2	249.9	249.6	249.4	249.1
117.5°	278.4	278.4	278.4	278.4	278.4	278.4	278.3	278.2	278.1	277.9	277.8
120°	306.5	307.0	307.5	308.0	308.5	308.8	308.6	308.2	307.9	307.5	307.1
122.5°	335.8	335.9	336.1	336.2	336.3	336.4	336.3	336.2	336.1	335.9	335.8
125°	364.5	364.5	364.5	364.5	364.5	364.5	364.4	364.3	364.2	364.0	363.9
127.5°	390.3	390.7	391.1	391.5	391.9	392.1	392.0	391.7	391.4	391.2	390.9
130°	417.9	418.3	418.7	419.0	419.4	419.6	419.6	419.6	419.6	419.6	419.6
132.5°	446.0	446.3	446.5	446.8	447.1	447.2	447.1	447.0	446.9	446.7	446.6
135°	470.1	470.9	471.7	472.4	473.2	473.6	473.6	473.6	473.6	473.6	473.6
137.5°	497.1	497.5	497.9	498.2	498.6	498.8	498.9	499.2	499.5	499.7	500.0
140°	524.1	524.3	524.6	524.8	525.1	525.2	525.2	525.2	525.2	525.2	525.2
142.5°	548.8	549.0	549.3	549.5	549.8	549.9	549.8	549.7	549.6	549.5	549.4
145°	571.2	571.7	572.2	572.7	573.2	573.5	573.6	573.7	573.8	573.9	574.0
147.5°	594.1	594.7	595.4	596.0	596.7	597.0	596.9	596.8	596.7	596.5	596.4
150°	614.8	615.3	615.8	616.3	616.8	617.1	617.1	617.1	617.1	617.1	617.1
152.5°	634.3	634.6	634.8	635.1	635.4	635.5	635.6	635.7	635.8	635.9	636.0
155°	654.4	654.4	654.4	654.4	654.4	654.4	654.3	654.2	654.1	653.9	653.8
157.5°	671.6	671.4	671.1	670.9	670.6	670.5	670.5	670.5	670.5	670.5	670.5
160°	686.5	686.4	686.3	686.2	686.1	686.0	685.9	685.8	685.7	685.5	685.4
162.5°	700.3	699.9	699.5	699.2	698.8	698.6	698.5	698.4	698.3	698.1	698.0
165°	712.4	712.0	711.6	711.3	710.9	710.7	710.6	710.3	710.0	709.8	709.5
167.5°	722.1	721.6	721.1	720.6	720.1	719.8	719.8	719.8	719.8	719.8	719.8
170°	730.2	729.6	728.9	728.3	727.6	727.3	727.4	727.5	727.6	727.8	727.9
172.5°	735.9	735.4	734.9	734.4	733.9	733.6	733.6	733.6	733.6	733.6	733.6
175°	741.1	740.5	739.8	739.2	738.5	738.2	738.1	738.0	737.9	737.7	737.6
177.5°	743.4	742.8	742.1	741.5	740.8	740.5	740.5	740.5	740.5	740.5	740.5
180°	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	981.3	995.4	1001.6	1003.1	1011.7	1006.3	1008.6	1007.8	1014.0	1014.8	1014.8
5°	1052.9	1069.3	1074.7	1082.5	1094.2	1097.3	1095.0	1099.6	1108.2	1102.0	1111.3
7.5°	1128.4	1146.3	1158.8	1175.9	1179.8	1189.9	1196.1	1201.6	1203.1	1203.9	1205.5
10°	1198.5	1221.0	1238.2	1267.0	1273.2	1278.6	1305.9	1295.0	1309.0	1304.3	1305.9
12.5°	1255.3	1299.6	1313.7	1361.9	1366.6	1385.3	1383.7	1400.8	1403.9	1410.2	1403.9
15°	1330.0	1381.4	1403.9	1431.2	1446.7	1468.5	1472.4	1495.8	1505.1	1513.7	1505.1
17.5°	1398.5	1425.7	1483.3	1505.1	1515.2	1526.9	1556.5	1565.0	1579.0	1573.6	1589.1
20°	1432.7	1471.6	1532.3	1569.7	1585.3	1596.2	1621.1	1634.3	1639.7	1639.7	1641.3
22.5°	1463.1	1519.1	1564.2	1607.0	1621.1	1628.8	1643.6	1653.7	1656.1	1657.6	1659.2
25°	1490.3	1540.9	1577.5	1601.6	1607.0	1607.0	1615.6	1609.4	1599.3	1607.0	1611.7
27.5°	1490.3	1526.1	1542.5	1551.0	1551.0	1530.0	1517.6	1491.9	1470.1	1463.9	1477.9
30°	1465.4	1481.8	1459.2	1438.2	1421.8	1407.8	1358.8	1319.9	1312.1	1306.7	1327.7
32.5°	1407.8	1386.8	1342.4	1281.7	1257.6	1225.7	1187.6	1158.0	1140.1	1133.9	1129.2
35°	1305.9	1251.4	1193.8	1112.1	1095.0	1054.5	1002.4	980.6	951.0	950.2	960.3
37.5°	1194.6	1110.5	1048.3	970.5	946.3	903.5	854.5	831.9	811.7	796.1	814.8
40°	1064.6	991.5	896.5	832.7	798.5	775.9	734.7	709.7	700.4	692.6	704.3
42.5°	943.2	863.1	789.1	723.8	695.7	670.1	642.8	618.7	611.7	610.9	619.5
45°	822.6	744.0	675.5	619.5	601.6	586.0	559.5	552.5	540.9	533.1	537.0
47.5°	726.1	645.2	588.3	545.5	530.0	516.7	499.6	488.0	477.8	474.7	479.4
50°	631.1	576.7	518.3	482.5	470.8	458.4	445.1	434.3	429.6	426.5	429.6
52.5°	554.9	496.5	456.8	428.0	416.4	407.0	397.7	393.0	386.8	388.3	391.5
55°	486.4	435.0	401.6	380.6	373.6	369.7	358.0	352.5	350.2	348.6	350.2
57.5°	421.8	384.4	359.5	341.6	332.3	330.0	320.6	320.6	318.3	316.0	316.7
60°	370.4	338.5	314.4	300.4	298.8	294.9	288.7	287.9	282.5	284.8	285.6
62.5°	318.3	292.6	276.3	267.7	262.3	260.7	256.8	256.0	253.7	254.5	252.9
65°	277.1	256.0	239.7	232.7	230.4	229.6	226.5	224.1	222.6	224.1	222.6
67.5°	235.8	221.8	209.3	202.3	199.2	198.4	196.1	194.6	195.3	193.0	194.6
70°	196.9	182.9	175.1	171.2	169.7	167.3	167.3	167.3	167.3	165.8	165.0
72.5°	165.8	151.8	146.3	144.0	142.4	141.6	139.3	140.1	139.3	138.5	141.6
75°	131.5	123.0	117.5	115.2	116.7	114.4	112.1	113.6	111.3	112.1	115.2
77.5°	99.6	95.7	92.6	91.1	89.5	87.9	87.9	86.4	86.4	86.4	86.4
80°	72.4	71.6	66.1	65.4	65.4	63.8	63.8	63.8	63.8	63.0	63.8
82.5°	48.3	47.5	45.9	45.1	43.6	44.4	44.4	42.8	42.8	42.0	42.8
85°	28.0	28.0	26.5	25.7	24.9	25.7	24.1	23.3	24.1	23.3	24.1
87.5°	13.2	11.7	12.5	11.7	10.1	10.9	9.3	10.1	9.3	8.6	10.1
90°	13.4	14.2	14.9	15.7	16.1	16.2	16.5	16.7	17.0	17.2	17.0
92.5°	25.7	26.1	26.4	26.8	27.0	27.1	27.2	27.3	27.5	27.6	27.5
95°	44.0	44.4	44.7	45.1	45.3	45.3	45.3	45.3	45.3	45.3	45.3
97.5°	64.8	65.3	65.8	66.3	66.6	66.6	66.6	66.6	66.6	66.6	66.6
100°	88.1	88.3	88.6	88.9	89.0	89.0	89.0	89.0	89.0	89.0	89.0
102.5°	112.3	112.7	113.1	113.5	113.7	113.8	113.9	114.0	114.1	114.2	114.1
105°	137.0	137.4	137.7	138.1	138.3	138.5	138.9	139.3	139.7	140.1	139.7
107.5°	163.5	164.0	164.5	165.0	165.3	165.2	165.1	165.0	164.8	164.7	164.8
110°	190.9	190.7	190.4	190.1	190.0	190.2	190.6	190.9	191.3	191.7	191.3

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3
115°	249.0	248.9	248.8	248.7	248.6	248.5	248.4	248.3	248.1	248.0	248.1
117.5°	277.4	277.0	276.7	276.3	276.1	275.9	275.5	275.2	274.8	274.4	274.8
120°	306.5	305.8	305.2	304.5	304.2	304.3	304.6	304.9	305.1	305.4	305.1
122.5°	335.4	335.0	334.7	334.3	334.1	333.8	333.1	332.5	331.8	331.2	331.8
125°	363.7	363.4	363.2	362.9	362.8	362.7	362.4	362.1	361.9	361.6	361.9
127.5°	390.7	390.4	390.2	389.9	389.8	389.7	389.6	389.5	389.3	389.2	389.3
130°	419.4	419.1	418.9	418.6	418.5	418.2	417.7	417.2	416.7	416.2	416.7
132.5°	446.4	446.1	445.9	445.6	445.5	445.4	445.3	445.2	445.0	444.9	445.0
135°	473.3	473.1	472.8	472.5	472.4	472.2	471.8	471.5	471.1	470.7	471.1
137.5°	499.6	499.2	498.9	498.5	498.3	498.4	498.5	498.6	498.7	498.8	498.7
140°	525.1	525.0	524.9	524.8	524.7	524.6	524.5	524.4	524.2	524.1	524.2
142.5°	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4
145°	573.9	573.8	573.7	573.6	573.5	573.3	572.9	572.5	572.1	571.7	572.1
147.5°	596.3	596.1	596.0	595.9	595.8	595.7	595.6	595.5	595.4	595.3	595.4
150°	617.1	617.1	617.1	617.1	617.1	617.0	616.9	616.8	616.6	616.5	616.6
152.5°	636.4	636.8	637.2	637.6	637.8	637.6	637.2	636.8	636.4	636.0	636.4
155°	654.3	654.8	655.3	655.8	656.1	655.8	655.3	654.8	654.3	653.8	654.3
157.5°	670.9	671.3	671.6	672.0	672.2	672.0	671.6	671.3	670.9	670.5	670.9
160°	685.8	686.2	686.5	686.9	687.1	686.8	686.2	685.5	684.9	684.3	684.9
162.5°	698.8	699.6	700.3	701.1	701.5	701.2	700.5	699.9	699.2	698.6	699.2
165°	710.3	711.1	711.8	712.6	713.0	712.7	712.2	711.7	711.2	710.7	711.2
167.5°	720.6	721.4	722.1	722.9	723.3	722.9	722.1	721.4	720.6	719.8	720.6
170°	728.7	729.4	730.2	730.9	731.3	730.9	730.0	729.1	728.2	727.3	728.2
172.5°	734.5	735.4	736.3	737.2	737.6	737.2	736.3	735.4	734.5	733.6	734.5
175°	738.5	739.4	740.3	741.2	741.7	741.2	740.3	739.4	738.5	737.6	738.5
177.5°	741.4	742.3	743.2	744.1	744.5	744.0	743.0	741.9	740.9	739.9	740.9
180°	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	1013.3	1010.9	1007.8	1007.8	1003.9	1003.9	997.7	986.8	977.5	974.3	975.9
5°	1099.6	1100.4	1095.7	1091.9	1084.9	1079.4	1069.3	1049.8	1043.6	1031.2	1022.6
7.5°	1198.5	1195.4	1186.8	1180.6	1179.0	1166.6	1144.8	1121.4	1102.8	1090.3	1072.4
10°	1309.8	1297.3	1284.9	1281.0	1271.6	1250.6	1225.7	1200.0	1174.4	1147.1	1116.8
12.5°	1403.2	1379.0	1378.2	1368.9	1351.0	1339.3	1309.8	1273.2	1228.8	1198.5	1164.2
15°	1503.5	1481.0	1462.3	1445.2	1436.6	1402.4	1377.5	1331.6	1278.6	1245.9	1222.6
17.5°	1575.1	1565.0	1533.1	1525.3	1513.7	1474.0	1434.3	1389.1	1343.2	1297.3	1234.3
20°	1632.7	1626.5	1605.5	1594.6	1575.9	1544.8	1496.5	1444.4	1391.5	1326.1	1267.0
22.5°	1657.6	1649.9	1632.7	1623.4	1611.7	1585.3	1544.0	1484.9	1415.6	1357.2	1294.2
25°	1608.6	1622.6	1617.9	1614.1	1609.4	1593.8	1562.7	1510.5	1442.8	1376.7	1298.1
27.5°	1498.1	1522.2	1545.6	1548.7	1556.5	1562.7	1550.2	1512.9	1456.1	1386.0	1299.6
30°	1349.5	1360.3	1407.8	1421.8	1432.7	1472.4	1495.8	1486.4	1442.8	1379.8	1300.4
32.5°	1158.8	1187.6	1235.8	1269.3	1298.9	1343.2	1403.9	1428.1	1412.5	1361.1	1282.5
35°	978.2	1012.5	1068.5	1111.3	1140.9	1203.9	1275.5	1327.7	1347.1	1321.4	1251.4
37.5°	830.4	871.6	921.4	937.8	972.0	1049.8	1148.7	1221.0	1268.5	1270.9	1216.4
40°	719.1	740.1	779.8	804.7	838.2	903.5	1000.0	1095.7	1167.3	1191.5	1162.7
42.5°	624.9	641.3	670.8	701.2	731.5	781.3	870.1	959.6	1056.1	1104.3	1103.5
45°	550.2	567.3	587.6	612.5	633.5	687.2	757.2	849.1	932.3	1007.0	1025.7
47.5°	484.8	499.6	524.5	535.4	549.4	600.0	660.7	746.3	832.7	918.3	940.1
50°	436.6	449.0	466.2	473.2	488.7	526.1	575.9	645.2	740.9	819.5	859.9
52.5°	393.0	402.3	415.6	421.0	431.9	459.9	505.1	559.5	638.9	719.9	776.7
55°	355.7	361.9	371.2	377.4	385.2	410.1	443.6	492.6	561.1	631.1	686.4
57.5°	320.6	325.3	334.6	337.8	344.0	363.4	386.8	428.0	491.1	553.3	607.0
60°	287.9	291.1	296.5	303.5	308.2	321.4	343.2	377.4	428.0	484.8	528.4
62.5°	256.8	261.5	263.0	266.2	270.0	282.5	299.6	324.5	368.9	415.6	461.5
65°	224.9	228.8	231.9	232.7	236.6	245.9	261.5	283.3	312.1	352.5	395.3
67.5°	195.3	197.7	199.2	202.3	206.2	210.9	223.4	239.7	266.2	298.8	333.1
70°	168.1	168.1	170.4	171.2	175.9	181.3	186.8	202.3	225.7	252.1	275.5
72.5°	138.5	142.4	141.6	145.5	144.8	148.6	155.6	165.8	182.9	203.9	226.5
75°	112.8	115.2	115.2	115.2	116.7	119.8	123.7	133.1	146.3	163.4	176.7
77.5°	87.9	89.5	89.5	89.5	90.3	93.4	97.3	103.5	112.8	123.0	130.7
80°	63.0	64.6	64.6	66.1	66.1	66.9	70.8	73.9	78.6	86.4	94.2
82.5°	42.8	43.6	45.1	45.1	44.4	45.9	46.7	49.8	54.5	56.0	61.5
85°	23.3	24.1	24.9	24.9	25.7	27.2	26.5	29.6	29.6	32.7	34.2
87.5°	9.3	10.9	10.9	10.1	10.9	10.9	10.9	12.5	13.2	14.0	13.2
90°	16.7	16.5	16.2	16.1	15.7	14.9	14.2	13.4	12.6	11.6	10.6
92.5°	27.3	27.2	27.1	27.0	26.8	26.4	26.1	25.7	25.3	24.7	24.0
95°	45.3	45.3	45.3	45.3	45.1	44.7	44.4	44.0	43.6	42.7	41.8
97.5°	66.6	66.6	66.6	66.6	66.3	65.8	65.3	64.8	64.3	63.3	62.3
100°	89.0	89.0	89.0	89.0	88.9	88.6	88.3	88.1	87.8	86.7	85.5
102.5°	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.9	109.9
105°	139.3	138.9	138.5	138.3	138.1	137.7	137.4	137.0	136.6	136.1	135.6
107.5°	165.0	165.1	165.2	165.3	165.0	164.5	164.0	163.5	163.0	162.9	162.8
110°	190.9	190.6	190.2	190.0	190.1	190.4	190.7	190.9	191.2	191.3	191.4

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.5	219.8
115°	248.3	248.4	248.5	248.6	248.7	248.8	248.9	249.0	249.1	249.4	249.6
117.5°	275.2	275.5	275.9	276.1	276.3	276.7	277.0	277.4	277.8	277.9	278.1
120°	304.9	304.6	304.3	304.2	304.5	305.2	305.8	306.5	307.1	307.5	307.9
122.5°	332.5	333.1	333.8	334.1	334.3	334.7	335.0	335.4	335.8	335.9	336.1
125°	362.1	362.4	362.7	362.8	362.9	363.2	363.4	363.7	363.9	364.0	364.2
127.5°	389.5	389.6	389.7	389.8	389.9	390.2	390.4	390.7	390.9	391.2	391.4
130°	417.2	417.7	418.2	418.5	418.6	418.9	419.1	419.4	419.6	419.6	419.6
132.5°	445.2	445.3	445.4	445.5	445.6	445.9	446.1	446.4	446.6	446.7	446.9
135°	471.5	471.8	472.2	472.4	472.5	472.8	473.1	473.3	473.6	473.6	473.6
137.5°	498.6	498.5	498.4	498.3	498.5	498.9	499.2	499.6	500.0	499.7	499.5
140°	524.4	524.5	524.6	524.7	524.8	524.9	525.0	525.1	525.2	525.2	525.2
142.5°	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.5	549.6
145°	572.5	572.9	573.3	573.5	573.6	573.7	573.8	573.9	574.0	573.9	573.8
147.5°	595.5	595.6	595.7	595.8	595.9	596.0	596.1	596.3	596.4	596.5	596.7
150°	616.8	616.9	617.0	617.1	617.1	617.1	617.1	617.1	617.1	617.1	617.1
152.5°	636.8	637.2	637.6	637.8	637.6	637.2	636.8	636.4	636.0	635.9	635.8
155°	654.8	655.3	655.8	656.1	655.8	655.3	654.8	654.3	653.8	653.9	654.1
157.5°	671.3	671.6	672.0	672.2	672.0	671.6	671.3	670.9	670.5	670.5	670.5
160°	685.5	686.2	686.8	687.1	686.9	686.5	686.2	685.8	685.4	685.5	685.7
162.5°	699.9	700.5	701.2	701.5	701.1	700.3	699.6	698.8	698.0	698.1	698.3
165°	711.7	712.2	712.7	713.0	712.6	711.8	711.1	710.3	709.5	709.8	710.0
167.5°	721.4	722.1	722.9	723.3	722.9	722.1	721.4	720.6	719.8	719.8	719.8
170°	729.1	730.0	730.9	731.3	730.9	730.2	729.4	728.7	727.9	727.8	727.6
172.5°	735.4	736.3	737.2	737.6	737.2	736.3	735.4	734.5	733.6	733.6	733.6
175°	739.4	740.3	741.2	741.7	741.2	740.3	739.4	738.5	737.6	737.7	737.9
177.5°	741.9	743.0	744.0	744.5	744.1	743.2	742.3	741.4	740.5	740.5	740.5
180°	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	968.9	965.8	963.5	963.5	956.4	949.4	945.6	944.0	942.4	936.2	927.7
5°	1008.6	998.5	991.5	984.5	972.8	960.3	947.9	940.9	930.8	916.8	906.6
7.5°	1052.9	1028.8	1021.0	1012.5	989.1	968.1	951.0	936.2	919.9	902.0	884.1
10°	1090.3	1064.6	1047.5	1032.7	1002.4	974.3	948.7	926.9	905.9	882.5	860.7
12.5°	1126.1	1089.5	1071.6	1049.8	1017.9	977.5	944.0	916.8	885.6	861.5	835.0
15°	1175.9	1114.4	1084.9	1070.8	1028.0	980.6	940.1	899.6	874.0	837.4	814.0
17.5°	1183.7	1133.9	1114.4	1078.6	1027.3	973.6	926.9	886.4	847.5	814.8	784.5
20°	1210.9	1145.6	1114.4	1091.9	1024.2	969.7	918.3	866.2	828.8	793.8	759.6
22.5°	1228.0	1154.1	1121.4	1085.6	1021.0	955.7	895.0	849.8	803.9	768.1	740.9
25°	1223.4	1149.4	1112.9	1079.4	1000.8	935.4	881.0	823.4	780.6	741.7	705.9
27.5°	1221.0	1137.8	1098.9	1061.5	987.6	919.1	850.6	803.9	756.4	711.3	684.8
30°	1214.8	1123.0	1077.9	1037.4	960.3	888.7	830.4	775.9	728.4	687.2	652.2
32.5°	1193.8	1098.1	1054.5	1010.9	930.8	859.2	800.0	749.4	702.0	659.2	625.7
35°	1165.8	1068.5	1021.0	975.1	895.0	822.6	768.1	715.2	670.8	629.6	597.7
37.5°	1137.8	1034.3	989.9	937.0	863.1	787.6	731.5	684.1	642.8	600.0	565.0
40°	1097.3	993.8	944.8	899.6	813.3	742.4	691.1	648.3	607.8	567.3	537.8
42.5°	1042.1	949.4	898.9	849.1	768.1	698.1	648.3	610.1	572.0	538.5	505.9
45°	986.0	895.7	850.6	806.2	718.3	652.2	606.2	571.2	539.3	502.7	476.3
47.5°	918.3	842.0	796.9	753.3	670.1	603.9	561.9	529.2	499.6	469.3	444.4
50°	849.1	782.9	741.7	696.5	617.1	557.2	516.0	488.7	464.6	435.8	415.6
52.5°	774.3	716.8	681.7	638.1	568.1	512.9	470.8	443.6	423.4	402.3	384.4
55°	695.0	652.9	615.6	580.6	514.4	464.6	427.2	403.1	389.1	369.7	354.1
57.5°	623.4	582.9	560.3	520.6	463.0	414.0	384.4	364.2	347.9	336.2	323.7
60°	548.7	516.0	491.1	462.3	411.7	370.4	339.3	327.6	310.5	302.0	296.5
62.5°	477.1	453.7	430.4	408.6	363.4	324.5	301.2	286.4	276.3	267.7	263.0
65°	409.3	387.6	371.2	351.8	314.4	283.3	261.5	249.8	239.7	237.4	231.9
67.5°	343.2	333.9	316.0	300.4	268.5	244.4	228.0	213.2	207.8	205.5	200.8
70°	287.2	276.3	262.3	249.0	224.9	203.9	189.1	183.7	175.9	175.1	169.7
72.5°	236.6	223.4	213.2	203.1	185.2	166.5	158.8	151.0	147.1	144.0	141.6
75°	187.6	178.2	171.2	162.7	147.1	134.6	123.7	120.6	118.3	117.5	116.0
77.5°	140.1	133.9	130.7	122.2	111.3	100.4	95.7	91.1	91.1	89.5	90.3
80°	99.6	95.7	91.8	87.2	77.8	73.2	69.3	66.1	64.6	63.8	64.6
82.5°	63.0	60.7	59.9	56.8	50.6	48.3	45.1	42.8	42.8	42.8	42.8
85°	35.0	35.0	35.0	30.4	28.0	25.7	24.1	23.3	23.3	23.3	24.1
87.5°	14.8	14.8	12.5	12.5	11.7	10.1	9.3	9.3	10.1	10.1	10.9
90°	9.5	8.5	8.0	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	23.4	22.7	22.4	21.6	19.9	18.2	16.6	14.9	16.6	18.2	19.9
95°	40.9	40.0	39.6	39.0	37.9	36.7	35.6	34.4	35.6	36.7	37.9
97.5°	61.2	60.2	59.7	59.2	58.2	57.1	56.1	55.1	56.1	57.1	58.2
100°	84.4	83.3	82.7	82.4	81.9	81.4	80.9	80.4	80.9	81.4	81.9
102.5°	108.8	107.8	107.3	107.2	107.1	107.0	106.9	106.8	106.9	107.0	107.1
105°	135.1	134.6	134.3	134.2	134.1	134.0	133.9	133.8	133.9	134.0	134.1
107.5°	162.7	162.6	162.5	162.4	162.3	162.2	162.0	161.9	162.0	162.2	162.3
110°	191.5	191.6	191.7	191.6	191.3	191.1	190.8	190.6	190.8	191.1	191.3

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	220.0	220.3	220.4	220.4	220.4	220.4	220.4	220.4	220.4	220.4	220.4
115°	249.9	250.2	250.3	250.3	250.3	250.3	250.3	250.3	250.3	250.3	250.3
117.5°	278.2	278.3	278.4	278.4	278.4	278.4	278.4	278.4	278.4	278.4	278.4
120°	308.2	308.6	308.8	308.5	308.0	307.5	307.0	306.5	307.0	307.5	308.0
122.5°	336.2	336.3	336.4	336.3	336.2	336.1	335.9	335.8	335.9	336.1	336.2
125°	364.3	364.4	364.5	364.5	364.5	364.5	364.5	364.5	364.5	364.5	364.5
127.5°	391.7	392.0	392.1	391.9	391.5	391.1	390.7	390.3	390.7	391.1	391.5
130°	419.6	419.6	419.6	419.4	419.0	418.7	418.3	417.9	418.3	418.7	419.0
132.5°	447.0	447.1	447.2	447.1	446.8	446.5	446.3	446.0	446.3	446.5	446.8
135°	473.6	473.6	473.6	473.2	472.4	471.7	470.9	470.1	470.9	471.7	472.4
137.5°	499.2	498.9	498.8	498.6	498.2	497.9	497.5	497.1	497.5	497.9	498.2
140°	525.2	525.2	525.2	525.1	524.8	524.6	524.3	524.1	524.3	524.6	524.8
142.5°	549.7	549.8	549.9	549.8	549.5	549.3	549.0	548.8	549.0	549.3	549.5
145°	573.7	573.6	573.5	573.2	572.7	572.2	571.7	571.2	571.7	572.2	572.7
147.5°	596.8	596.9	597.0	596.7	596.0	595.4	594.7	594.1	594.7	595.4	596.0
150°	617.1	617.1	617.1	616.8	616.3	615.8	615.3	614.8	615.3	615.8	616.3
152.5°	635.7	635.6	635.5	635.4	635.1	634.8	634.6	634.3	634.6	634.8	635.1
155°	654.2	654.3	654.4	654.4	654.4	654.4	654.4	654.4	654.4	654.4	654.4
157.5°	670.5	670.5	670.5	670.6	670.9	671.1	671.4	671.6	671.4	671.1	670.9
160°	685.8	685.9	686.0	686.1	686.2	686.3	686.4	686.5	686.4	686.3	686.2
162.5°	698.4	698.5	698.6	698.8	699.2	699.5	699.9	700.3	699.9	699.5	699.2
165°	710.3	710.6	710.7	710.9	711.3	711.6	712.0	712.4	712.0	711.6	711.3
167.5°	719.8	719.8	719.8	720.1	720.6	721.1	721.6	722.1	721.6	721.1	720.6
170°	727.5	727.4	727.3	727.6	728.3	728.9	729.6	730.2	729.6	728.9	728.3
172.5°	733.6	733.6	733.6	733.9	734.4	734.9	735.4	735.9	735.4	734.9	734.4
175°	738.0	738.1	738.2	738.5	739.2	739.8	740.5	741.1	740.5	739.8	739.2
177.5°	740.5	740.5	740.5	740.8	741.5	742.1	742.8	743.4	742.8	742.1	741.5
180°	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	925.3	922.2	923.8	916.0	909.0	898.9	890.3	888.7	887.2	891.9	888.7
5°	898.9	895.0	891.1	881.7	867.7	859.2	846.7	845.9	841.3	834.3	835.8
7.5°	870.1	867.7	862.3	847.5	835.0	820.3	810.1	801.6	797.7	791.5	789.1
10°	846.7	838.2	833.5	817.1	802.4	786.8	773.6	767.3	760.3	754.9	751.0
12.5°	814.8	812.5	799.2	786.0	773.6	755.7	745.5	727.6	718.3	723.0	721.4
15°	793.8	782.9	779.8	761.1	740.1	728.4	709.7	698.1	694.2	687.2	678.6
17.5°	765.8	758.8	747.9	730.8	706.6	690.3	677.1	666.2	661.5	652.2	645.2
20°	739.3	727.6	719.1	703.5	680.2	659.2	642.8	635.8	624.1	616.4	612.5
22.5°	715.2	706.6	694.2	670.8	650.6	630.4	610.9	600.8	589.9	585.2	579.0
25°	685.6	671.6	663.1	637.4	615.6	599.2	581.3	568.1	561.9	554.1	552.5
27.5°	656.8	643.6	633.5	610.9	584.5	563.4	552.5	543.2	532.3	532.3	528.4
30°	628.0	618.7	603.1	581.3	556.4	536.2	523.7	515.2	511.3	508.2	507.4
32.5°	599.2	586.8	577.4	547.9	529.2	510.5	501.2	494.2	489.5	488.7	489.5
35°	569.7	555.7	546.3	519.9	501.2	484.1	480.2	473.9	471.6	470.8	474.7
37.5°	538.5	527.6	516.0	494.2	473.2	463.0	455.3	452.9	452.2	456.8	458.4
40°	509.7	500.4	489.5	466.2	450.6	439.7	435.8	433.5	436.6	441.3	443.6
42.5°	482.5	469.3	460.7	439.7	425.7	419.5	414.8	414.8	417.9	423.4	427.2
45°	453.7	443.6	435.0	416.4	403.9	396.9	396.1	396.9	400.8	404.7	409.3
47.5°	425.7	415.6	406.2	390.7	379.8	375.9	375.1	375.9	382.1	387.6	393.0
50°	400.0	389.1	380.6	365.8	357.2	352.5	353.3	357.2	361.9	369.7	376.7
52.5°	369.7	361.9	354.1	340.9	333.1	330.0	332.3	335.4	344.0	349.4	358.0
55°	340.1	333.1	326.9	316.7	310.5	308.2	309.7	314.4	321.4	330.7	340.9
57.5°	312.8	305.1	298.8	291.8	284.8	285.6	286.4	292.6	301.2	309.7	321.4
60°	282.5	277.8	272.4	263.8	260.7	260.7	263.0	270.0	277.8	291.8	302.0
62.5°	255.3	249.0	245.1	239.7	235.0	235.8	241.3	247.5	256.8	268.5	281.7
65°	227.2	220.2	217.1	212.5	210.9	211.7	215.6	224.9	235.0	245.1	257.6
67.5°	196.1	193.8	190.7	186.0	187.6	188.3	192.2	200.0	210.9	221.0	235.0
70°	169.7	165.0	164.2	160.3	160.3	162.7	170.4	175.9	186.0	196.9	211.7
72.5°	141.6	137.7	137.7	134.6	137.0	139.3	143.2	151.0	160.3	171.2	183.7
75°	112.8	111.3	112.8	111.3	111.3	115.2	119.8	126.1	136.2	147.9	158.0
77.5°	87.2	87.2	86.4	88.7	88.7	91.1	97.3	103.5	111.3	120.6	131.5
80°	63.8	63.8	63.8	66.1	68.5	68.5	72.4	80.2	87.2	93.4	103.5
82.5°	43.6	43.6	43.6	45.1	48.3	48.3	52.9	57.6	65.4	70.8	75.5
85°	26.5	26.5	25.7	27.2	28.0	30.4	34.2	37.4	41.2	45.9	50.6
87.5°	11.7	11.7	12.5	13.2	14.0	15.6	17.1	18.7	22.6	24.1	26.5
90°	7.3	8.0	8.5	9.5	10.6	11.6	12.6	13.4	14.2	14.9	15.7
92.5°	21.6	22.4	22.7	23.4	24.0	24.7	25.3	25.7	26.1	26.4	26.8
95°	39.0	39.6	40.0	40.9	41.8	42.7	43.6	44.0	44.4	44.7	45.1
97.5°	59.2	59.7	60.2	61.2	62.3	63.3	64.3	64.8	65.3	65.8	66.3
100°	82.4	82.7	83.3	84.4	85.5	86.7	87.8	88.1	88.3	88.6	88.9
102.5°	107.2	107.3	107.8	108.8	109.9	110.9	111.9	112.3	112.7	113.1	113.5
105°	134.2	134.3	134.6	135.1	135.6	136.1	136.6	137.0	137.4	137.7	138.1
107.5°	162.4	162.5	162.6	162.7	162.8	162.9	163.0	163.5	164.0	164.5	165.0
110°	191.6	191.7	191.6	191.5	191.4	191.3	191.2	190.9	190.7	190.4	190.1

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	220.4	220.4	220.3	220.0	219.8	219.5	219.3	219.3	219.3	219.3	219.3
115°	250.3	250.3	250.2	249.9	249.6	249.4	249.1	249.0	248.9	248.8	248.7
117.5°	278.4	278.4	278.3	278.2	278.1	277.9	277.8	277.4	277.0	276.7	276.3
120°	308.5	308.8	308.6	308.2	307.9	307.5	307.1	306.5	305.8	305.2	304.5
122.5°	336.3	336.4	336.3	336.2	336.1	335.9	335.8	335.4	335.0	334.7	334.3
125°	364.5	364.5	364.4	364.3	364.2	364.0	363.9	363.7	363.4	363.2	362.9
127.5°	391.9	392.1	392.0	391.7	391.4	391.2	390.9	390.7	390.4	390.2	389.9
130°	419.4	419.6	419.6	419.6	419.6	419.6	419.6	419.4	419.1	418.9	418.6
132.5°	447.1	447.2	447.1	447.0	446.9	446.7	446.6	446.4	446.1	445.9	445.6
135°	473.2	473.6	473.6	473.6	473.6	473.6	473.6	473.3	473.1	472.8	472.5
137.5°	498.6	498.8	498.9	499.2	499.5	499.7	500.0	499.6	499.2	498.9	498.5
140°	525.1	525.2	525.2	525.2	525.2	525.2	525.2	525.1	525.0	524.9	524.8
142.5°	549.8	549.9	549.8	549.7	549.6	549.5	549.4	549.4	549.4	549.4	549.4
145°	573.2	573.5	573.6	573.7	573.8	573.9	574.0	573.9	573.8	573.7	573.6
147.5°	596.7	597.0	596.9	596.8	596.7	596.5	596.4	596.3	596.1	596.0	595.9
150°	616.8	617.1	617.1	617.1	617.1	617.1	617.1	617.1	617.1	617.1	617.1
152.5°	635.4	635.5	635.6	635.7	635.8	635.9	636.0	636.4	636.8	637.2	637.6
155°	654.4	654.4	654.3	654.2	654.1	653.9	653.8	654.3	654.8	655.3	655.8
157.5°	670.6	670.5	670.5	670.5	670.5	670.5	670.5	670.9	671.3	671.6	672.0
160°	686.1	686.0	685.9	685.8	685.7	685.5	685.4	685.8	686.2	686.5	686.9
162.5°	698.8	698.6	698.5	698.4	698.3	698.1	698.0	698.8	699.6	700.3	701.1
165°	710.9	710.7	710.6	710.3	710.0	709.8	709.5	710.3	711.1	711.8	712.6
167.5°	720.1	719.8	719.8	719.8	719.8	719.8	719.8	720.6	721.4	722.1	722.9
170°	727.6	727.3	727.4	727.5	727.6	727.8	727.9	728.7	729.4	730.2	730.9
172.5°	733.9	733.6	733.6	733.6	733.6	733.6	733.6	734.5	735.4	736.3	737.2
175°	738.5	738.2	738.1	738.0	737.9	737.7	737.6	738.5	739.4	740.3	741.2
177.5°	740.8	740.5	740.5	740.5	740.5	740.5	740.5	741.4	742.3	743.2	744.1
180°	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	886.4	885.6	881.7	883.3	878.6	880.2	882.5	883.3	886.4	884.1	883.3
5°	831.9	830.4	828.0	825.7	824.9	828.0	822.6	824.1	825.7	828.0	831.2
7.5°	787.6	786.8	784.5	780.6	779.0	777.5	778.2	783.7	782.9	782.1	787.6
10°	747.1	747.9	743.2	742.4	737.8	737.0	737.8	739.3	741.7	744.8	745.5
12.5°	705.1	715.2	706.6	703.5	696.5	700.4	702.0	695.0	698.9	701.2	712.9
15°	678.6	673.9	668.5	668.5	665.4	663.8	659.9	665.4	668.5	673.2	671.6
17.5°	642.0	634.3	631.1	628.0	628.8	631.9	623.4	635.8	635.8	638.1	634.3
20°	610.1	603.9	600.0	598.5	596.1	594.6	593.8	596.9	601.6	603.1	607.0
22.5°	576.7	576.7	570.4	568.1	566.6	564.2	568.1	565.8	568.9	572.0	578.2
25°	548.7	548.7	546.3	543.2	540.9	539.3	541.6	540.9	543.2	547.1	548.7
27.5°	526.1	523.7	523.0	522.2	521.4	522.2	521.4	523.7	526.1	526.9	525.3
30°	506.6	504.3	505.1	505.1	505.9	505.1	504.3	506.6	507.4	505.9	506.6
32.5°	488.7	488.7	490.3	491.1	491.1	491.8	492.6	491.1	491.8	489.5	490.3
35°	473.9	475.5	477.1	477.8	478.6	477.8	479.4	478.6	477.1	475.5	474.7
37.5°	459.2	460.7	463.8	464.6	466.9	467.7	466.2	466.2	465.4	462.3	460.7
40°	443.6	445.1	449.0	451.4	452.9	455.3	453.7	453.7	450.6	447.5	445.1
42.5°	428.8	431.9	435.8	438.1	441.3	441.3	441.3	439.7	435.8	432.7	430.4
45°	414.0	414.8	420.2	424.1	427.2	427.2	427.2	424.9	422.6	416.4	413.2
47.5°	397.7	400.0	406.2	410.1	413.2	414.0	414.0	411.7	407.0	401.6	397.7
50°	379.8	383.7	390.7	396.1	400.0	401.6	399.2	397.7	392.2	386.0	381.3
52.5°	362.7	367.3	375.9	380.6	386.0	386.8	386.0	383.7	377.4	368.9	365.0
55°	345.5	349.4	358.8	366.5	371.2	372.8	371.2	367.3	359.5	351.0	347.1
57.5°	326.9	332.3	342.4	350.2	355.7	356.4	354.9	351.0	344.8	333.9	328.4
60°	307.4	314.4	324.5	332.3	339.3	340.1	338.5	333.1	325.3	314.4	309.7
62.5°	287.9	293.4	305.1	313.6	319.1	323.0	319.9	314.4	306.6	295.7	288.7
65°	265.4	273.2	283.3	291.1	297.3	298.1	296.5	291.8	283.3	271.6	266.2
67.5°	243.6	249.0	259.2	269.3	271.6	273.9	271.6	266.9	259.9	249.8	242.0
70°	217.1	221.8	234.2	241.3	244.4	246.7	245.1	240.5	234.2	224.9	218.7
72.5°	190.7	194.6	206.2	211.7	217.9	217.1	216.3	213.2	204.7	198.4	194.6
75°	162.7	167.3	175.1	182.1	184.4	184.4	184.4	182.1	176.7	166.5	162.7
77.5°	137.0	139.3	145.5	149.4	151.8	152.5	151.8	147.9	144.8	137.7	135.4
80°	105.1	111.3	116.0	116.7	119.8	119.8	119.8	118.3	115.2	108.2	107.4
82.5°	79.4	80.9	85.6	87.9	89.5	88.7	88.7	85.6	84.8	80.9	79.4
85°	53.7	56.0	55.3	58.4	59.1	57.6	57.6	59.1	55.3	56.0	53.7
87.5°	29.6	29.6	31.1	30.4	33.5	33.5	31.9	32.7	31.1	30.4	29.6
90°	16.1	16.2	16.5	16.7	17.0	17.2	17.0	16.7	16.5	16.2	16.1
92.5°	27.0	27.1	27.2	27.3	27.5	27.6	27.5	27.3	27.2	27.1	27.0
95°	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3
97.5°	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6
100°	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0
102.5°	113.7	113.8	113.9	114.0	114.1	114.2	114.1	114.0	113.9	113.8	113.7
105°	138.3	138.5	138.9	139.3	139.7	140.1	139.7	139.3	138.9	138.5	138.3
107.5°	165.3	165.2	165.1	165.0	164.8	164.7	164.8	165.0	165.1	165.2	165.3
110°	190.0	190.2	190.6	190.9	191.3	191.7	191.3	190.9	190.6	190.2	190.0

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3	219.3
115°	248.6	248.5	248.4	248.3	248.1	248.0	248.1	248.3	248.4	248.5	248.6
117.5°	276.1	275.9	275.5	275.2	274.8	274.4	274.8	275.2	275.5	275.9	276.1
120°	304.2	304.3	304.6	304.9	305.1	305.4	305.1	304.9	304.6	304.3	304.2
122.5°	334.1	333.8	333.1	332.5	331.8	331.2	331.8	332.5	333.1	333.8	334.1
125°	362.8	362.7	362.4	362.1	361.9	361.6	361.9	362.1	362.4	362.7	362.8
127.5°	389.8	389.7	389.6	389.5	389.3	389.2	389.3	389.5	389.6	389.7	389.8
130°	418.5	418.2	417.7	417.2	416.7	416.2	416.7	417.2	417.7	418.2	418.5
132.5°	445.5	445.4	445.3	445.2	445.0	444.9	445.0	445.2	445.3	445.4	445.5
135°	472.4	472.2	471.8	471.5	471.1	470.7	471.1	471.5	471.8	472.2	472.4
137.5°	498.3	498.4	498.5	498.6	498.7	498.8	498.7	498.6	498.5	498.4	498.3
140°	524.7	524.6	524.5	524.4	524.2	524.1	524.2	524.4	524.5	524.6	524.7
142.5°	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4	549.4
145°	573.5	573.3	572.9	572.5	572.1	571.7	572.1	572.5	572.9	573.3	573.5
147.5°	595.8	595.7	595.6	595.5	595.4	595.3	595.4	595.5	595.6	595.7	595.8
150°	617.1	617.0	616.9	616.8	616.6	616.5	616.6	616.8	616.9	617.0	617.1
152.5°	637.8	637.6	637.2	636.8	636.4	636.0	636.4	636.8	637.2	637.6	637.8
155°	656.1	655.8	655.3	654.8	654.3	653.8	654.3	654.8	655.3	655.8	656.1
157.5°	672.2	672.0	671.6	671.3	670.9	670.5	670.9	671.3	671.6	672.0	672.2
160°	687.1	686.8	686.2	685.5	684.9	684.3	684.9	685.5	686.2	686.8	687.1
162.5°	701.5	701.2	700.5	699.9	699.2	698.6	699.2	699.9	700.5	701.2	701.5
165°	713.0	712.7	712.2	711.7	711.2	710.7	711.2	711.7	712.2	712.7	713.0
167.5°	723.3	722.9	722.1	721.4	720.6	719.8	720.6	721.4	722.1	722.9	723.3
170°	731.3	730.9	730.0	729.1	728.2	727.3	728.2	729.1	730.0	730.9	731.3
172.5°	737.6	737.2	736.3	735.4	734.5	733.6	734.5	735.4	736.3	737.2	737.6
175°	741.7	741.2	740.3	739.4	738.5	737.6	738.5	739.4	740.3	741.2	741.7
177.5°	744.5	744.0	743.0	741.9	740.9	739.9	740.9	741.9	743.0	744.0	744.5
180°	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3	939.3
2.5°	883.3	888.0	883.3	886.4	888.0	891.9	893.4	900.4	902.7	908.2	908.2
5°	830.4	832.7	833.5	836.6	839.7	847.5	852.9	863.1	874.7	876.3	883.3
7.5°	787.6	791.5	797.7	795.4	800.8	812.5	819.5	831.9	843.6	849.8	858.4
10°	749.4	754.1	756.4	758.8	768.9	779.0	789.9	798.5	814.0	823.4	830.4
12.5°	718.3	714.4	719.1	727.6	739.3	745.5	760.3	773.6	785.2	795.4	801.6
15°	677.8	681.0	685.6	700.4	703.5	719.1	724.5	739.3	761.1	770.4	778.2
17.5°	638.9	649.0	658.4	663.8	673.2	685.6	701.2	717.5	731.5	742.4	751.8
20°	607.8	617.9	623.4	627.3	636.6	653.7	668.5	688.7	706.6	715.2	727.6
22.5°	582.9	582.9	590.7	602.4	607.8	624.1	636.6	658.4	677.8	688.7	700.4
25°	551.8	556.4	562.7	572.8	580.6	593.8	611.7	630.4	651.4	660.7	675.5
27.5°	526.1	531.5	540.1	542.4	550.2	561.9	580.6	600.8	622.6	632.7	645.2
30°	506.6	509.7	512.9	517.5	524.5	534.6	550.2	568.1	594.6	602.4	617.9
32.5°	489.5	491.1	492.6	496.5	500.4	510.5	523.0	542.4	564.2	575.9	589.9
35°	473.9	472.4	473.2	475.5	479.4	483.3	496.5	512.9	533.1	547.1	558.0
37.5°	459.2	456.0	455.3	455.3	456.8	461.5	471.6	485.6	507.4	519.1	530.0
40°	442.8	439.7	438.1	437.4	436.6	439.7	447.5	461.5	478.6	489.5	502.0
42.5°	427.2	424.1	420.2	419.5	417.9	419.5	424.9	438.1	452.9	463.8	473.9
45°	411.7	406.2	401.6	398.5	399.2	396.9	400.8	410.9	428.0	435.0	445.1
47.5°	394.6	388.3	382.1	379.0	375.9	377.4	379.0	387.6	402.3	409.3	419.5
50°	378.2	369.7	362.7	358.8	356.4	354.9	356.4	365.0	375.9	382.1	390.7
52.5°	359.5	351.0	344.0	337.8	334.6	332.3	333.1	340.9	351.0	357.2	365.8
55°	342.4	331.5	322.2	314.4	312.1	311.3	310.5	316.0	324.5	330.7	337.8
57.5°	323.0	312.1	302.0	292.6	287.9	287.2	287.2	288.7	299.6	304.3	308.2
60°	303.5	291.8	280.9	272.4	265.4	263.0	262.3	265.4	270.8	275.5	280.9
62.5°	281.7	270.0	256.8	249.0	242.0	235.8	238.1	238.9	246.7	249.0	253.7
65°	260.7	247.5	236.6	224.1	216.3	212.5	210.9	212.5	218.7	219.5	222.6
67.5°	236.6	224.1	210.9	202.3	195.3	188.3	186.8	186.8	189.9	192.2	196.1
70°	213.2	200.8	186.0	176.7	169.7	163.4	161.1	160.3	162.7	164.2	168.1
72.5°	186.0	173.5	162.7	152.5	144.0	139.3	137.0	135.4	137.7	139.3	140.1
75°	157.2	147.1	136.2	126.1	120.6	116.0	112.8	110.5	112.1	112.1	112.1
77.5°	130.0	119.8	111.3	104.3	97.3	91.8	89.5	87.2	87.9	87.9	89.5
80°	101.2	94.2	87.2	80.9	74.7	70.0	68.5	66.1	64.6	63.8	63.8
82.5°	74.7	69.3	63.0	57.6	54.5	49.8	48.3	45.1	45.1	44.4	44.4
85°	49.8	46.7	40.5	36.6	34.2	31.9	30.4	28.8	26.5	26.5	25.7
87.5°	26.5	24.9	23.3	18.7	18.7	16.3	15.6	14.8	12.5	13.2	13.2
90°	15.7	14.9	14.2	13.4	12.6	11.6	10.6	9.5	8.5	8.0	7.3
92.5°	26.8	26.4	26.1	25.7	25.3	24.7	24.0	23.4	22.7	22.4	21.6
95°	45.1	44.7	44.4	44.0	43.6	42.7	41.8	40.9	40.0	39.6	39.0
97.5°	66.3	65.8	65.3	64.8	64.3	63.3	62.3	61.2	60.2	59.7	59.2
100°	88.9	88.6	88.3	88.1	87.8	86.7	85.5	84.4	83.3	82.7	82.4
102.5°	113.5	113.1	112.7	112.3	111.9	110.9	109.9	108.8	107.8	107.3	107.2
105°	138.1	137.7	137.4	137.0	136.6	136.1	135.6	135.1	134.6	134.3	134.2
107.5°	165.0	164.5	164.0	163.5	163.0	162.9	162.8	162.7	162.6	162.5	162.4
110°	190.1	190.4	190.7	190.9	191.2	191.3	191.4	191.5	191.6	191.7	191.6

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	219.3	219.3	219.3	219.3	219.3	219.5	219.8	220.0	220.3	220.4	220.4
115°	248.7	248.8	248.9	249.0	249.1	249.4	249.6	249.9	250.2	250.3	250.3
117.5°	276.3	276.7	277.0	277.4	277.8	277.9	278.1	278.2	278.3	278.4	278.4
120°	304.5	305.2	305.8	306.5	307.1	307.5	307.9	308.2	308.6	308.8	308.5
122.5°	334.3	334.7	335.0	335.4	335.8	335.9	336.1	336.2	336.3	336.4	336.3
125°	362.9	363.2	363.4	363.7	363.9	364.0	364.2	364.3	364.4	364.5	364.5
127.5°	389.9	390.2	390.4	390.7	390.9	391.2	391.4	391.7	392.0	392.1	391.9
130°	418.6	418.9	419.1	419.4	419.6	419.6	419.6	419.6	419.6	419.6	419.4
132.5°	445.6	445.9	446.1	446.4	446.6	446.7	446.9	447.0	447.1	447.2	447.1
135°	472.5	472.8	473.1	473.3	473.6	473.6	473.6	473.6	473.6	473.6	473.2
137.5°	498.5	498.9	499.2	499.6	500.0	499.7	499.5	499.2	498.9	498.8	498.6
140°	524.8	524.9	525.0	525.1	525.2	525.2	525.2	525.2	525.2	525.2	525.1
142.5°	549.4	549.4	549.4	549.4	549.4	549.5	549.6	549.7	549.8	549.9	549.8
145°	573.6	573.7	573.8	573.9	574.0	573.9	573.8	573.7	573.6	573.5	573.2
147.5°	595.9	596.0	596.1	596.3	596.4	596.5	596.7	596.8	596.9	597.0	596.7
150°	617.1	617.1	617.1	617.1	617.1	617.1	617.1	617.1	617.1	617.1	616.8
152.5°	637.6	637.2	636.8	636.4	636.0	635.9	635.8	635.7	635.6	635.5	635.4
155°	655.8	655.3	654.8	654.3	653.8	653.9	654.1	654.2	654.3	654.4	654.4
157.5°	672.0	671.6	671.3	670.9	670.5	670.5	670.5	670.5	670.5	670.5	670.6
160°	686.9	686.5	686.2	685.8	685.4	685.5	685.7	685.8	685.9	686.0	686.1
162.5°	701.1	700.3	699.6	698.8	698.0	698.1	698.3	698.4	698.5	698.6	698.8
165°	712.6	711.8	711.1	710.3	709.5	709.8	710.0	710.3	710.6	710.7	710.9
167.5°	722.9	722.1	721.4	720.6	719.8	719.8	719.8	719.8	719.8	719.8	720.1
170°	730.9	730.2	729.4	728.7	727.9	727.8	727.6	727.5	727.4	727.3	727.6
172.5°	737.2	736.3	735.4	734.5	733.6	733.6	733.6	733.6	733.6	733.6	733.9
175°	741.2	740.3	739.4	738.5	737.6	737.7	737.9	738.0	738.1	738.2	738.5
177.5°	744.1	743.2	742.3	741.4	740.5	740.5	740.5	740.5	740.5	740.5	740.8
180°	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2	742.2

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	939.3	939.3	939.3	939.3
2.5°	913.6	921.4	928.4	939.3
5°	893.4	904.3	919.1	935.4
7.5°	870.1	887.2	906.6	929.2
10°	848.3	867.7	892.6	919.9
12.5°	825.7	849.1	876.3	905.9
15°	800.0	823.4	853.7	893.4
17.5°	776.7	804.7	837.4	879.4
20°	749.4	775.9	811.7	859.9
22.5°	725.3	755.7	795.4	837.4
25°	698.9	725.3	765.0	815.6
27.5°	672.4	705.1	743.2	792.2
30°	646.7	673.9	715.2	766.6
32.5°	618.7	651.4	689.5	737.8
35°	588.3	619.5	655.3	707.4
37.5°	561.1	591.5	628.0	673.9
40°	530.8	562.7	596.1	642.0
42.5°	501.2	530.0	563.4	605.5
45°	472.4	497.3	527.6	564.2
47.5°	442.8	463.8	491.8	524.5
50°	410.9	433.5	454.5	481.7
52.5°	381.3	400.8	417.9	440.5
55°	352.5	365.8	379.8	396.9
57.5°	322.2	332.3	342.4	360.3
60°	291.8	301.2	306.6	318.3
62.5°	262.3	266.2	273.2	280.2
65°	229.6	235.0	238.9	247.5
67.5°	200.0	202.3	206.2	211.7
70°	168.9	174.3	175.9	179.8
72.5°	142.4	144.8	146.3	147.1
75°	112.8	115.2	116.7	121.4
77.5°	88.7	87.9	91.1	91.8
80°	65.4	63.0	63.8	66.9
82.5°	42.8	43.6	42.8	42.8
85°	26.5	25.7	24.1	24.9
87.5°	11.7	11.7	10.9	10.9
90°	5.9	4.5	3.1	1.7
92.5°	19.9	18.2	16.6	14.9
95°	37.9	36.7	35.6	34.4
97.5°	58.2	57.1	56.1	55.1
100°	81.9	81.4	80.9	80.4
102.5°	107.1	107.0	106.9	106.8
105°	134.1	134.0	133.9	133.8
107.5°	162.3	162.2	162.0	161.9
110°	191.3	191.1	190.8	190.6

TEST NUMBER: P1001611

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	220.4	220.4	220.4	220.4
115°	250.3	250.3	250.3	250.3
117.5°	278.4	278.4	278.4	278.4
120°	308.0	307.5	307.0	306.5
122.5°	336.2	336.1	335.9	335.8
125°	364.5	364.5	364.5	364.5
127.5°	391.5	391.1	390.7	390.3
130°	419.0	418.7	418.3	417.9
132.5°	446.8	446.5	446.3	446.0
135°	472.4	471.7	470.9	470.1
137.5°	498.2	497.9	497.5	497.1
140°	524.8	524.6	524.3	524.1
142.5°	549.5	549.3	549.0	548.8
145°	572.7	572.2	571.7	571.2
147.5°	596.0	595.4	594.7	594.1
150°	616.3	615.8	615.3	614.8
152.5°	635.1	634.8	634.6	634.3
155°	654.4	654.4	654.4	654.4
157.5°	670.9	671.1	671.4	671.6
160°	686.2	686.3	686.4	686.5
162.5°	699.2	699.5	699.9	700.3
165°	711.3	711.6	712.0	712.4
167.5°	720.6	721.1	721.6	722.1
170°	728.3	728.9	729.6	730.2
172.5°	734.4	734.9	735.4	735.9
175°	739.2	739.8	740.5	741.1
177.5°	741.5	742.1	742.8	743.4
180°	742.2	742.2	742.2	742.2

(END OF REPORT)