

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008040

Luminaire Tested: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008040
REPORT IS A COMBINATION OF REPORTS P984008 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4101.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	103	103	103	103	92	92	92	92		73	73	73		55	55	55		39	39	39
1	94	90	86	83	84	81	78	75		64	62	60		49	47	46		35	34	33
2	86	79	73	68	77	71	66	62		56	53	50		43	41	39		31	30	28
3	78	69	62	57	70	63	57	52		50	46	43		38	36	33		28	26	24
4	72	61	54	48	64	56	49	44		45	40	36		34	31	29		25	23	21
5	66	55	47	41	59	50	43	38		40	35	31		31	28	25		22	20	19
6	61	49	41	36	54	45	38	33		36	31	27		28	25	22		20	18	17
7	56	44	37	31	50	40	34	29		33	28	24		25	22	20		19	17	15
8	52	40	33	28	47	37	30	26		30	25	22		23	20	17		17	15	13
9	48	37	30	25	43	33	27	23		27	23	19		21	18	16		16	14	12
10	45	34	27	22	41	31	25	20		25	20	17		20	16	14		15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9105	9105	9105	9105
5°	9126	9708	9161	7724
10°	9021	10597	9077	6367
15°	8802	11178	8924	5364
20°	8664	10495	8664	4662
25°	8389	9016	8427	4169
30°	7933	7088	8085	3777
35°	7532	4901	7657	3455
40°	7070	3701	7148	3199
45°	6497	3040	6604	2922
50°	6005	2670	6017	2675
55°	5441	2274	5478	2407
60°	4843	1899	4910	2101
65°	4305	1545	4383	1794
70°	3772	1212	3867	1447
75°	3166	880	3289	1049
80°	2467	557	2651	622
85°	1624	280	1752	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9412 cd/sqm

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	1.3
10°-20°	159.5	3.9
20°-30°	231.4	5.6
30°-40°	244.0	5.9
40°-50°	215.9	5.3
50°-60°	172.4	4.2
60°-70°	117.1	2.9
70°-80°	59.9	1.5
80°-90°	15.9	0.4
90°-100°	31.8	0.8
100°-110°	118.7	2.9
110°-120°	314.7	7.7
120°-130°	522.0	12.7
130°-140°	554.5	13.5
140°-150°	515.4	12.6
150°-160°	414.3	10.1
160°-170°	267.0	6.5
170°-180°	91.9	2.2
0°-30°	445.7	10.9
0°-40°	689.6	16.8
0°-60°	1077.9	26.3
0°-90°	1270.7	31.0
90°-120°	465.3	11.3
90°-150°	2057.1	50.2
90°-180°	2830.0	69.0
0°-180°	4101.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	575	575	575	575	575	
5°	576	642	578	511	576	55
15°	541	790	548	379	541	153
25°	486	658	488	304	486	222
35°	397	358	403	252	397	248
45°	298	216	302	207	298	231
55°	204	152	206	160	204	182
65°	121	93	123	108	121	120
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	19	1	19	1	3
95°	45	30	45	30	45	54
105°	212	53	212	53	212	227
115°	402	57	402	57	402	395
125°	568	597	568	597	568	507
135°	703	726	703	726	703	543
145°	815	828	815	828	815	510
155°	898	898	898	898	898	414
165°	946	944	946	944	946	267
175°	968	962	968	962	968	92
180°	965	965	965	965	965	

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	578.3	579.6	581.8	582.2	586.7	590.2	594.2	594.2	595.5	595.1	591.5
5°	575.6	579.6	585.3	590.2	598.2	601.7	607.0	611.0	614.5	617.2	616.7
7.5°	571.2	578.3	586.7	595.9	606.6	612.7	620.3	627.3	632.2	636.6	639.7
10°	563.7	575.6	587.1	599.5	613.2	621.6	630.4	639.7	647.2	655.6	663.6
12.5°	553.5	570.7	584.9	601.3	618.1	627.3	641.5	648.6	663.1	684.4	690.1
15°	540.7	564.1	577.4	598.2	620.3	627.8	647.2	658.7	688.8	702.1	718.0
17.5°	528.7	554.8	572.5	596.4	618.1	632.6	651.7	675.1	700.3	719.3	737.0
20°	519.0	544.2	565.4	592.0	619.4	637.9	657.8	686.1	713.5	733.0	746.7
22.5°	496.9	529.2	553.9	583.6	616.7	642.4	661.4	692.3	721.9	733.9	745.8
25°	485.9	513.7	542.5	576.1	615.0	645.5	661.8	696.3	722.4	726.8	729.5
27.5°	465.5	496.9	530.5	569.0	614.5	640.2	660.9	692.3	713.1	710.0	702.1
30°	440.3	478.8	515.9	557.5	608.3	636.2	655.6	684.4	695.0	679.1	664.9
32.5°	421.8	458.0	499.1	547.3	601.3	627.8	646.8	669.3	671.5	642.8	618.9
35°	396.6	436.8	483.2	534.1	589.3	613.2	630.9	644.6	634.0	593.7	565.4
37.5°	374.0	413.8	463.3	515.0	573.0	596.4	610.5	612.7	586.7	551.3	509.7
40°	349.3	390.4	442.1	496.5	554.8	575.2	584.0	577.4	539.8	498.7	450.5
42.5°	324.5	365.2	420.9	476.6	531.8	549.1	552.6	534.5	488.5	440.3	384.6
45°	297.5	340.0	395.7	451.8	505.3	515.0	515.5	489.4	435.0	384.6	332.9
47.5°	275.4	314.8	370.0	426.2	471.3	477.9	475.3	445.2	386.0	329.4	284.3
50°	251.1	288.7	343.5	398.8	437.2	439.0	432.4	389.5	331.6	279.8	244.0
52.5°	225.0	263.0	313.4	366.5	401.0	398.3	385.5	339.5	285.2	242.3	214.9
55°	204.2	237.8	285.2	336.9	361.2	353.7	339.5	292.7	249.8	213.5	189.7
57.5°	181.3	210.9	257.3	302.4	316.5	309.5	295.3	251.6	211.8	184.4	168.4
60°	159.6	186.6	227.2	264.8	275.9	268.4	252.0	212.6	183.9	160.9	149.0
62.5°	139.7	163.1	197.2	231.7	236.1	228.6	214.4	182.6	157.8	139.7	130.9
65°	121.1	143.2	170.6	196.7	200.7	192.8	178.2	155.2	134.4	122.9	114.5
67.5°	103.0	120.7	145.0	164.0	166.2	158.7	146.8	128.2	115.4	103.0	96.8
70°	87.1	100.4	119.4	134.8	135.7	128.7	122.5	105.7	95.9	87.1	82.2
72.5°	71.6	80.9	95.5	107.0	107.4	103.0	97.3	86.7	78.3	72.1	67.2
75°	56.6	64.5	73.4	83.6	83.1	79.6	75.2	68.5	61.5	57.5	55.3
77.5°	43.3	48.2	55.3	61.9	61.9	60.1	57.5	52.6	48.2	44.2	42.0
80°	30.9	34.0	39.8	42.0	42.9	42.4	40.2	36.7	34.9	31.8	30.9
82.5°	19.9	22.1	24.8	27.0	28.3	27.4	27.0	25.2	22.5	21.7	20.8
85°	11.5	12.4	13.7	15.0	15.5	15.0	15.9	14.6	13.3	13.3	12.8
87.5°	4.9	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.4	40.3	35.2	30.1	25.0	22.4	22.9	24.0	25.1	26.1	27.2
97.5°	81.7	69.0	56.3	43.6	30.9	24.5	25.7	28.2	30.7	33.1	35.6
100°	123.6	102.3	81.1	59.8	38.5	27.9	29.2	31.9	34.5	37.2	39.8
102.5°	169.8	169.5	169.2	168.9	168.6	168.4	154.3	126.0	97.7	69.5	41.2
105°	212.4	217.0	221.7	226.3	231.0	233.3	212.1	169.7	127.4	85.0	42.6
107.5°	262.0	265.9	269.7	273.6	277.5	279.4	253.2	200.9	148.6	96.3	44.0
110°	309.5	312.7	316.0	319.2	322.5	324.1	301.7	256.8	212.0	167.1	122.3

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	354.2	357.0	359.8	362.6	365.4	366.8	365.5	362.8	360.2	357.5	354.9
115°	401.7	404.3	407.0	409.6	412.3	413.6	415.5	419.4	423.3	427.1	431.0
117.5°	442.9	446.0	449.1	452.2	455.3	456.9	458.2	460.8	463.5	466.1	468.7
120°	489.0	491.3	493.7	496.0	498.3	499.5	500.9	503.7	506.5	509.3	512.1
122.5°	528.1	530.6	533.1	535.6	538.1	539.3	540.9	544.0	547.1	550.2	553.3
125°	567.9	569.9	571.9	574.0	576.0	577.0	578.5	581.4	584.4	587.3	590.3
127.5°	604.3	606.5	608.6	610.8	612.9	614.0	615.2	617.5	619.8	622.2	624.5
130°	638.5	641.0	643.5	646.0	648.5	649.7	650.6	652.3	654.0	655.7	657.4
132.5°	673.4	675.4	677.4	679.5	681.5	682.5	683.4	685.1	686.8	688.5	690.2
135°	702.8	705.3	707.7	710.2	712.7	713.9	714.6	716.0	717.4	718.8	720.2
137.5°	733.5	735.4	737.2	739.1	741.0	741.9	742.7	744.2	745.8	747.3	748.9
140°	763.5	764.7	766.0	767.2	768.5	769.1	770.0	771.7	773.4	775.1	776.8
142.5°	788.7	789.8	790.9	792.0	793.1	793.6	794.6	796.6	798.7	800.7	802.7
145°	815.2	815.0	814.9	814.7	814.6	814.5	815.8	818.5	821.1	823.8	826.4
147.5°	838.3	837.8	837.4	836.9	836.4	836.2	837.5	840.2	842.8	845.5	848.1
150°	860.6	859.5	858.5	857.4	856.3	855.8	857.0	859.5	862.0	864.4	866.9
152.5°	879.5	878.3	877.0	875.8	874.5	873.9	875.1	877.4	879.7	882.1	884.4
155°	897.7	896.3	894.9	893.5	892.1	891.4	892.3	894.2	896.1	897.9	899.8
157.5°	912.3	911.1	909.8	908.6	907.3	906.7	907.4	908.8	910.2	911.6	913.0
160°	924.9	924.0	923.0	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9
162.5°	936.1	935.2	934.2	933.3	932.4	931.9	932.3	933.1	933.8	934.6	935.4
165°	945.9	945.0	944.0	943.1	942.2	941.7	941.9	942.4	942.9	943.3	943.8
167.5°	953.6	952.7	951.7	950.8	949.9	949.4	949.6	950.1	950.6	951.0	951.5
170°	959.8	958.9	957.9	957.0	956.1	955.6	955.8	956.1	956.4	956.7	957.0
172.5°	964.0	963.1	962.1	961.2	960.3	959.8	960.0	960.3	960.6	960.9	961.2
175°	967.5	966.4	965.3	964.2	963.1	962.6	962.8	963.1	963.4	963.7	964.0
177.5°	968.9	967.8	966.7	965.6	964.5	964.0	964.1	964.2	964.4	964.5	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	597.7	598.2	599.0	603.5	605.7	606.1	604.3	608.3	609.7	608.3	607.4
5°	626.0	628.7	634.0	639.7	639.3	639.7	642.4	645.0	645.9	642.4	643.7
7.5°	650.8	656.1	661.8	670.7	670.7	675.1	676.9	679.1	684.4	681.7	680.8
10°	679.1	686.1	696.7	710.9	711.3	715.8	720.2	727.3	729.5	727.7	728.6
12.5°	714.4	728.1	729.0	744.5	751.6	752.5	759.5	758.2	762.6	762.6	770.1
15°	729.9	751.1	763.1	778.1	782.5	777.2	783.0	789.1	789.6	789.6	789.1
17.5°	757.8	766.2	778.1	786.1	787.8	787.8	788.3	790.9	789.1	785.6	788.3
20°	763.5	767.0	771.5	770.6	771.5	767.0	762.6	758.2	758.6	756.4	763.1
22.5°	752.9	752.0	741.8	735.2	735.2	726.4	718.0	714.0	710.0	711.3	713.5
25°	726.4	712.7	700.3	690.6	688.3	674.2	662.7	659.2	652.5	657.8	658.7
27.5°	683.9	668.5	648.6	640.2	628.7	622.9	615.0	604.3	590.6	598.6	597.3
30°	638.4	615.4	599.0	578.7	560.6	559.3	544.2	526.5	519.5	519.5	523.4
32.5°	587.5	557.0	533.2	504.4	486.8	479.2	461.1	443.4	447.4	434.1	439.0
35°	528.3	488.1	458.0	430.2	416.9	408.1	384.6	374.9	364.3	358.1	369.6
37.5°	471.7	425.3	386.8	356.3	351.5	335.6	319.6	313.4	307.3	309.9	309.5
40°	402.8	361.6	327.2	303.3	294.9	287.4	276.8	269.2	265.3	267.5	267.9
42.5°	340.4	305.9	280.3	263.5	256.4	251.1	245.8	239.6	238.3	238.3	240.1
45°	292.2	263.9	246.7	233.0	229.0	225.0	221.0	218.4	217.5	215.7	217.1
47.5°	253.8	231.2	220.6	210.4	206.0	205.1	201.6	200.3	198.5	198.1	198.5
50°	221.5	207.3	197.6	191.9	188.8	187.4	185.7	183.0	182.1	184.4	183.5
52.5°	198.9	185.7	180.4	174.6	172.9	171.1	168.4	168.9	168.4	167.6	167.6
55°	176.4	168.0	162.7	158.3	157.8	156.1	153.9	153.0	152.5	151.6	153.0
57.5°	158.3	151.6	146.8	142.8	141.0	141.0	138.8	137.1	137.1	136.6	137.1
60°	140.1	133.5	130.4	126.4	125.1	124.7	123.3	122.5	121.1	121.1	121.1
62.5°	123.3	118.0	114.5	111.0	111.4	109.2	107.4	106.5	106.5	107.0	107.0
65°	107.4	103.9	99.5	96.4	95.5	95.1	94.2	93.7	92.4	93.3	93.3
67.5°	92.8	88.0	85.3	84.0	82.7	82.2	81.3	80.5	80.0	79.6	80.5
70°	78.3	74.3	72.1	71.2	69.9	69.4	69.0	67.6	68.1	68.5	69.0
72.5°	65.0	61.5	61.0	58.4	58.4	58.4	56.6	57.5	57.0	56.1	57.0
75°	51.3	49.5	48.6	47.3	47.7	47.3	46.9	45.5	45.5	46.0	46.4
77.5°	40.7	38.9	38.5	37.1	36.3	37.1	36.3	35.8	35.8	36.3	36.3
80°	30.1	29.2	27.9	27.9	27.9	27.4	27.4	27.4	27.0	26.5	27.0
82.5°	19.9	19.9	19.5	19.0	19.5	18.6	19.0	19.0	19.0	19.0	19.0
85°	12.8	12.4	12.4	11.9	11.9	11.9	12.4	11.5	11.5	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.0	28.8	29.5	30.3	30.7	30.6	30.5	30.3	30.2	30.0	30.2
97.5°	36.1	36.5	37.0	37.5	37.7	37.8	37.9	38.1	38.2	38.4	38.2
100°	41.0	42.3	43.5	44.8	45.4	45.6	45.9	46.2	46.5	46.8	46.5
102.5°	42.9	44.6	46.3	48.0	48.9	49.1	49.6	50.1	50.5	51.0	50.5
105°	44.3	46.0	47.7	49.4	50.3	50.6	51.2	51.9	52.5	53.1	52.5
107.5°	45.7	47.4	49.1	50.8	51.7	52.0	52.6	53.3	53.9	54.5	53.9
110°	106.8	91.2	75.7	60.2	52.4	52.7	53.3	54.0	54.6	55.2	54.6

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.0	221.1	154.2	87.3	53.8	54.0	54.5	55.0	55.4	55.9	55.4
115°	359.1	287.3	215.4	143.5	107.6	102.0	90.8	79.7	68.5	57.3	68.5
117.5°	446.5	424.3	402.1	379.9	368.8	348.5	307.8	267.1	226.5	185.8	226.5
120°	513.9	515.8	517.6	519.5	520.4	509.9	489.0	468.0	447.1	426.1	447.1
122.5°	554.2	555.2	556.1	557.0	557.5	557.6	557.7	557.9	558.0	558.2	558.0
125°	591.4	592.5	593.6	594.7	595.2	595.4	595.9	596.4	596.8	597.3	596.8
127.5°	626.1	627.6	629.2	630.7	631.5	631.6	631.7	631.9	632.0	632.2	632.0
130°	659.1	660.8	662.5	664.2	665.0	664.9	664.8	664.6	664.5	664.3	664.5
132.5°	691.6	693.0	694.4	695.8	696.5	696.4	696.3	696.1	696.0	695.8	696.0
135°	721.8	723.3	724.9	726.4	727.2	727.0	726.7	726.4	726.1	725.8	726.1
137.5°	750.5	752.0	753.6	755.1	755.9	755.7	755.2	754.7	754.3	753.8	754.3
140°	778.2	779.6	781.0	782.4	783.1	782.7	781.9	781.2	780.4	779.6	780.4
142.5°	803.9	805.2	806.4	807.7	808.3	807.9	807.1	806.4	805.6	804.8	805.6
145°	827.5	828.6	829.7	830.8	831.3	830.9	830.1	829.4	828.6	827.8	828.6
147.5°	848.9	849.7	850.4	851.2	851.6	851.3	850.7	850.0	849.4	848.8	849.4
150°	867.8	868.8	869.7	870.6	871.1	870.7	869.9	869.2	868.4	867.6	868.4
152.5°	885.3	886.3	887.2	888.1	888.6	888.1	887.0	885.9	884.8	883.7	884.8
155°	900.7	901.7	902.6	903.5	904.0	903.4	902.1	900.9	899.6	898.4	899.6
157.5°	914.1	915.2	916.3	917.4	917.9	917.3	916.0	914.8	913.5	912.3	913.5
160°	925.8	926.8	927.7	928.6	929.1	928.6	927.5	926.4	925.3	924.2	925.3
162.5°	936.5	937.6	938.7	939.8	940.3	939.6	938.2	936.8	935.4	934.0	935.4
165°	944.9	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	944.9
167.5°	952.6	953.6	954.7	955.8	956.3	955.6	954.2	952.9	951.5	950.1	951.5
170°	958.1	959.2	960.3	961.4	961.9	961.2	959.8	958.4	957.0	955.6	957.0
172.5°	962.3	963.4	964.5	965.6	966.1	965.4	964.0	962.6	961.2	959.8	961.2
175°	965.1	966.2	967.3	968.4	968.9	968.1	966.6	965.0	963.5	961.9	963.5
177.5°	965.8	966.9	968.0	969.1	969.6	968.9	967.5	966.1	964.7	963.3	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	609.7	606.6	603.9	604.3	606.6	604.8	600.4	594.6	592.4	589.8	592.4
5°	646.3	643.7	638.4	638.8	637.5	635.7	628.7	619.8	619.8	612.7	611.9
7.5°	682.6	678.6	675.1	674.2	669.3	665.8	659.6	647.2	642.4	634.0	629.1
10°	723.3	720.2	716.2	711.3	708.7	702.5	692.3	674.2	665.4	653.9	645.5
12.5°	764.4	763.9	755.1	745.4	744.9	735.2	728.1	703.8	691.9	676.4	656.5
15°	790.5	788.3	783.4	778.5	779.9	769.3	753.3	724.6	716.6	698.1	676.9
17.5°	790.0	790.0	788.7	787.8	786.5	783.4	774.6	755.5	742.7	719.3	699.4
20°	764.8	770.6	771.9	771.5	775.9	778.1	777.7	765.7	755.5	734.8	714.4
22.5°	714.4	727.7	733.4	737.0	746.3	751.1	762.6	758.2	755.5	740.1	722.8
25°	667.6	672.0	689.2	690.1	702.9	714.9	726.4	733.9	743.6	737.9	723.3
27.5°	607.0	617.2	629.5	638.8	641.5	665.8	684.8	699.0	721.1	722.8	718.0
30°	538.5	543.3	563.7	576.1	590.2	607.9	635.3	659.6	679.5	697.6	703.8
32.5°	454.9	474.8	486.8	501.8	514.2	545.5	579.1	610.5	633.5	664.0	677.3
35°	378.4	393.9	414.2	420.4	443.0	469.5	513.3	553.5	588.4	619.4	646.3
37.5°	315.2	327.6	349.3	359.0	372.2	406.3	443.0	492.9	534.9	573.0	606.6
40°	271.9	281.2	297.5	300.6	311.7	342.6	372.2	419.1	474.8	526.1	562.8
42.5°	242.3	246.7	257.7	261.7	268.8	289.6	316.1	360.3	412.0	465.1	516.8
45°	221.0	224.1	230.8	234.3	243.2	252.4	274.1	309.5	350.1	403.6	459.3
47.5°	202.0	206.0	208.7	210.9	215.7	225.9	240.1	266.1	305.0	354.1	408.1
50°	186.1	187.4	192.3	192.8	195.8	202.5	215.7	231.7	262.6	302.4	354.6
52.5°	170.2	171.5	174.6	177.7	179.0	184.4	193.2	206.5	229.4	260.8	307.3
55°	154.3	156.1	159.2	161.4	162.7	167.1	172.4	185.2	203.4	225.5	263.5
57.5°	138.4	142.4	143.2	144.6	146.8	151.6	156.5	164.0	178.2	198.5	226.4
60°	123.3	124.7	127.8	129.1	131.3	134.0	140.1	145.9	156.1	172.0	197.2
62.5°	107.9	111.0	112.3	113.6	115.4	118.5	122.5	128.7	137.5	150.3	170.2
65°	94.6	95.1	97.7	99.5	101.2	103.5	107.4	113.2	118.5	130.4	145.0
67.5°	81.8	82.7	83.6	85.3	87.5	89.7	93.3	96.4	103.0	111.0	122.5
70°	69.4	69.4	71.6	72.9	72.5	75.2	77.8	81.3	86.2	93.7	103.0
72.5°	58.4	57.9	59.7	60.1	61.0	62.8	64.5	68.1	70.7	76.5	83.6
75°	46.4	47.3	48.2	48.2	49.5	50.8	52.6	54.4	57.5	61.0	66.3
77.5°	36.7	36.7	37.6	38.0	39.3	38.9	40.7	42.4	44.7	47.7	51.7
80°	27.0	27.9	27.9	27.9	28.3	28.7	30.5	31.8	33.2	35.4	37.1
82.5°	19.0	19.0	19.9	19.9	19.9	20.8	20.8	21.2	22.1	23.4	24.8
85°	11.9	11.9	11.9	12.4	11.9	12.4	13.3	12.8	13.3	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.3	30.5	30.6	30.7	30.3	29.5	28.8	28.0	27.2	26.1	25.1
97.5°	38.1	37.9	37.8	37.7	37.5	37.0	36.5	36.1	35.6	33.1	30.7
100°	46.2	45.9	45.6	45.4	44.8	43.5	42.3	41.0	39.8	37.2	34.5
102.5°	50.1	49.6	49.1	48.9	48.0	46.3	44.6	42.9	41.2	39.5	37.7
105°	51.9	51.2	50.6	50.3	49.4	47.7	46.0	44.3	42.6	40.9	39.2
107.5°	53.3	52.6	52.0	51.7	50.8	49.1	47.4	45.7	44.0	42.3	40.6
110°	54.0	53.3	52.7	52.4	50.2	48.5	46.8	45.1	43.4	41.7	40.0

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.0	54.5	54.0	53.8	87.3	154.2	221.1	288.0	354.9	357.5	360.2
115°	79.7	90.8	102.0	107.6	143.5	215.4	287.3	359.1	431.0	427.1	423.3
117.5°	267.1	307.8	348.5	368.8	379.9	402.1	424.3	446.5	468.7	466.1	463.5
120°	468.0	489.0	509.9	520.4	519.5	517.6	515.8	513.9	512.1	509.3	506.5
122.5°	557.9	557.7	557.6	557.5	557.0	556.1	555.2	554.2	553.3	550.2	547.1
125°	596.4	595.9	595.4	595.2	594.7	593.6	592.5	591.4	590.3	587.3	584.4
127.5°	631.9	631.7	631.6	631.5	630.7	629.2	627.6	626.1	624.5	622.2	619.8
130°	664.6	664.8	664.9	665.0	664.2	662.5	660.8	659.1	657.4	655.7	654.0
132.5°	696.1	696.3	696.4	696.5	695.8	694.4	693.0	691.6	690.2	688.5	686.8
135°	726.4	726.7	727.0	727.2	726.4	724.9	723.3	721.8	720.2	718.8	717.4
137.5°	754.7	755.2	755.7	755.9	755.1	753.6	752.0	750.5	748.9	747.3	745.8
140°	781.2	781.9	782.7	783.1	782.4	781.0	779.6	778.2	776.8	775.1	773.4
142.5°	806.4	807.1	807.9	808.3	807.7	806.4	805.2	803.9	802.7	800.7	798.7
145°	829.4	830.1	830.9	831.3	830.8	829.7	828.6	827.5	826.4	823.8	821.1
147.5°	850.0	850.7	851.3	851.6	851.2	850.4	849.7	848.9	848.1	845.5	842.8
150°	869.2	869.9	870.7	871.1	870.6	869.7	868.8	867.8	866.9	864.4	862.0
152.5°	885.9	887.0	888.1	888.6	888.1	887.2	886.3	885.3	884.4	882.1	879.7
155°	900.9	902.1	903.4	904.0	903.5	902.6	901.7	900.7	899.8	897.9	896.1
157.5°	914.8	916.0	917.3	917.9	917.4	916.3	915.2	914.1	913.0	911.6	910.2
160°	926.4	927.5	928.6	929.1	928.6	927.7	926.8	925.8	924.9	924.0	923.0
162.5°	936.8	938.2	939.6	940.3	939.8	938.7	937.6	936.5	935.4	934.6	933.8
165°	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	943.3	942.9
167.5°	952.9	954.2	955.6	956.3	955.8	954.7	953.6	952.6	951.5	951.0	950.6
170°	958.4	959.8	961.2	961.9	961.4	960.3	959.2	958.1	957.0	956.7	956.4
172.5°	962.6	964.0	965.4	966.1	965.6	964.5	963.4	962.3	961.2	960.9	960.6
175°	965.0	966.6	968.1	968.9	968.4	967.3	966.2	965.1	964.0	963.7	963.4
177.5°	966.1	967.5	968.9	969.6	969.1	968.0	966.9	965.8	964.7	964.5	964.4
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	590.2	588.0	586.7	587.5	584.9	578.3	578.3	580.5	577.8	575.2	571.2
5°	606.6	602.1	599.5	599.0	592.9	582.2	580.0	577.8	572.1	565.9	559.3
7.5°	622.5	614.5	610.1	607.0	598.2	584.5	578.7	573.8	564.6	555.3	546.9
10°	635.7	624.2	618.9	614.1	602.6	585.3	576.1	567.2	555.3	543.3	532.7
12.5°	646.3	633.1	626.5	619.4	605.2	582.7	571.2	557.0	545.1	529.2	518.6
15°	664.0	636.6	630.4	623.8	609.2	578.3	564.1	548.2	531.8	510.6	499.1
17.5°	678.2	641.5	641.0	626.9	607.9	576.5	554.8	534.1	516.4	495.2	477.0
20°	686.6	649.0	641.9	627.3	603.5	564.6	542.0	519.0	500.0	474.4	456.2
22.5°	693.7	659.6	641.0	623.4	594.2	560.6	527.4	505.8	479.7	451.8	434.6
25°	696.3	661.8	642.4	622.0	587.5	549.1	511.5	488.1	458.9	433.7	410.3
27.5°	696.7	661.4	637.5	616.3	578.3	534.1	495.6	470.8	438.6	409.4	386.0
30°	692.3	656.5	634.9	611.9	569.4	520.3	476.1	448.7	414.2	385.1	360.8
32.5°	679.1	646.8	629.1	603.9	557.9	501.3	457.6	427.1	390.8	362.1	338.6
35°	657.0	634.9	615.4	592.0	542.9	483.7	439.0	403.2	366.5	339.1	317.0
37.5°	629.5	617.6	599.5	576.5	525.7	467.7	418.2	378.4	341.7	315.2	293.6
40°	592.4	595.5	577.8	557.0	505.3	446.1	391.3	353.2	318.8	294.0	272.8
42.5°	552.2	565.0	554.8	534.9	482.8	422.2	371.4	329.4	295.8	270.1	252.4
45°	508.9	531.0	524.8	510.2	459.3	397.0	343.1	302.4	272.8	248.0	232.5
47.5°	461.6	492.9	492.9	482.3	433.3	371.8	318.8	277.2	248.0	230.3	215.3
50°	413.4	448.7	454.5	447.4	404.1	343.1	289.1	251.6	226.4	209.1	198.1
52.5°	363.0	404.1	414.7	411.2	373.1	315.7	264.8	228.1	205.1	190.1	180.4
55°	314.8	362.5	374.0	375.3	340.0	285.6	237.8	205.6	183.5	173.3	164.9
57.5°	269.2	315.2	328.0	330.2	306.4	258.2	212.6	184.4	164.5	156.1	149.4
60°	230.3	268.8	285.6	290.5	269.7	226.4	189.2	161.8	146.8	138.8	132.6
62.5°	198.5	229.4	247.1	248.5	239.2	198.5	164.9	141.9	129.1	122.0	118.9
65°	167.6	195.4	206.0	211.3	203.8	172.0	142.4	123.3	113.2	107.0	103.9
67.5°	142.8	160.5	169.3	176.4	168.9	145.0	121.1	105.7	98.1	92.0	90.2
70°	117.2	131.7	138.4	145.5	138.8	120.7	103.5	89.3	82.7	77.8	75.6
72.5°	93.7	105.2	111.4	115.8	111.9	96.8	82.7	72.9	68.1	64.5	63.2
75°	74.3	82.2	85.8	88.9	87.1	75.6	66.8	58.8	54.4	51.3	50.4
77.5°	56.6	62.3	66.3	67.2	65.0	57.5	50.0	45.1	41.6	39.8	38.9
80°	40.2	43.8	46.0	47.3	45.1	42.0	36.7	33.2	30.1	27.9	27.4
82.5°	27.0	28.7	30.5	30.1	29.2	26.5	23.4	21.7	20.3	18.6	18.6
85°	15.5	15.9	16.8	17.2	16.8	15.0	13.3	12.4	11.5	10.2	10.2
87.5°	6.6	7.1	7.1	7.5	6.6	6.6	5.7	4.9	4.9	4.4	4.0
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.0	22.9	22.4	25.0	30.1	35.2	40.3	45.4	40.3	35.2	30.1
97.5°	28.2	25.7	24.5	30.9	43.6	56.3	69.0	81.7	69.0	56.3	43.6
100°	31.9	29.2	27.9	38.5	59.8	81.1	102.3	123.6	102.3	81.1	59.8
102.5°	126.0	154.3	168.4	168.6	168.9	169.2	169.5	169.8	169.5	169.2	168.9
105°	169.7	212.1	233.3	231.0	226.3	221.7	217.0	212.4	217.0	221.7	226.3
107.5°	200.9	253.2	279.4	277.5	273.6	269.7	265.9	262.0	265.9	269.7	273.6
110°	256.8	301.7	324.1	322.5	319.2	316.0	312.7	309.5	312.7	316.0	319.2

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	362.8	365.5	366.8	365.4	362.6	359.8	357.0	354.2	357.0	359.8	362.6
115°	419.4	415.5	413.6	412.3	409.6	407.0	404.3	401.7	404.3	407.0	409.6
117.5°	460.8	458.2	456.9	455.3	452.2	449.1	446.0	442.9	446.0	449.1	452.2
120°	503.7	500.9	499.5	498.3	496.0	493.7	491.3	489.0	491.3	493.7	496.0
122.5°	544.0	540.9	539.3	538.1	535.6	533.1	530.6	528.1	530.6	533.1	535.6
125°	581.4	578.5	577.0	576.0	574.0	571.9	569.9	567.9	569.9	571.9	574.0
127.5°	617.5	615.2	614.0	612.9	610.8	608.6	606.5	604.3	606.5	608.6	610.8
130°	652.3	650.6	649.7	648.5	646.0	643.5	641.0	638.5	641.0	643.5	646.0
132.5°	685.1	683.4	682.5	681.5	679.5	677.4	675.4	673.4	675.4	677.4	679.5
135°	716.0	714.6	713.9	712.7	710.2	707.7	705.3	702.8	705.3	707.7	710.2
137.5°	744.2	742.7	741.9	741.0	739.1	737.2	735.4	733.5	735.4	737.2	739.1
140°	771.7	770.0	769.1	768.5	767.2	766.0	764.7	763.5	764.7	766.0	767.2
142.5°	796.6	794.6	793.6	793.1	792.0	790.9	789.8	788.7	789.8	790.9	792.0
145°	818.5	815.8	814.5	814.6	814.7	814.9	815.0	815.2	815.0	814.9	814.7
147.5°	840.2	837.5	836.2	836.4	836.9	837.4	837.8	838.3	837.8	837.4	836.9
150°	859.5	857.0	855.8	856.3	857.4	858.5	859.5	860.6	859.5	858.5	857.4
152.5°	877.4	875.1	873.9	874.5	875.8	877.0	878.3	879.5	878.3	877.0	875.8
155°	894.2	892.3	891.4	892.1	893.5	894.9	896.3	897.7	896.3	894.9	893.5
157.5°	908.8	907.4	906.7	907.3	908.6	909.8	911.1	912.3	911.1	909.8	908.6
160°	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9	924.0	923.0	922.1
162.5°	933.1	932.3	931.9	932.4	933.3	934.2	935.2	936.1	935.2	934.2	933.3
165°	942.4	941.9	941.7	942.2	943.1	944.0	945.0	945.9	945.0	944.0	943.1
167.5°	950.1	949.6	949.4	949.9	950.8	951.7	952.7	953.6	952.7	951.7	950.8
170°	956.1	955.8	955.6	956.1	957.0	957.9	958.9	959.8	958.9	957.9	957.0
172.5°	960.3	960.0	959.8	960.3	961.2	962.1	963.1	964.0	963.1	962.1	961.2
175°	963.1	962.8	962.6	963.1	964.2	965.3	966.4	967.5	966.4	965.3	964.2
177.5°	964.2	964.1	964.0	964.5	965.6	966.7	967.8	968.9	967.8	966.7	965.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	569.0	571.2	570.7	566.3	561.5	557.5	550.0	550.9	548.2	548.6	551.3
5°	554.8	554.8	553.1	546.9	538.9	534.5	526.1	523.9	518.6	518.1	517.7
7.5°	539.8	537.6	535.4	526.5	516.8	509.7	498.2	495.6	490.3	486.8	485.0
10°	522.1	519.0	514.6	504.4	492.5	483.7	471.7	468.2	458.0	453.6	450.9
12.5°	502.7	500.9	493.8	485.4	466.0	456.2	439.0	442.5	432.4	423.5	422.2
15°	483.2	476.6	472.6	458.9	435.5	431.0	417.3	410.3	401.0	393.9	393.9
17.5°	464.2	454.0	445.2	430.6	413.4	401.0	390.8	387.3	375.8	368.7	367.4
20°	439.0	427.5	425.3	404.5	392.6	378.9	369.2	360.3	351.9	348.8	346.6
22.5°	415.1	401.9	398.3	380.6	368.7	355.0	345.3	339.1	332.9	330.7	326.7
25°	389.5	381.5	376.2	357.2	344.0	331.1	324.5	320.1	314.3	313.9	311.2
27.5°	364.7	357.2	351.9	333.8	324.1	312.1	306.8	302.0	298.9	297.5	296.2
30°	343.5	335.1	328.9	315.7	303.7	294.0	289.6	286.5	284.7	282.5	282.1
32.5°	320.1	315.2	306.8	296.6	287.4	278.1	275.4	273.2	270.6	269.7	269.2
35°	300.2	293.6	288.2	276.8	272.8	264.8	261.7	260.0	256.4	255.5	254.6
37.5°	280.7	274.5	268.8	261.7	254.2	249.8	248.0	245.4	243.6	244.0	243.2
40°	261.3	256.4	252.0	244.5	240.1	237.8	234.3	231.7	230.8	231.2	230.8
42.5°	242.3	237.8	235.2	229.4	225.0	222.8	220.6	218.0	219.3	219.3	220.6
45°	225.0	221.0	219.3	214.9	212.2	208.7	206.5	206.0	207.8	207.3	207.3
47.5°	207.3	206.0	203.8	199.8	196.3	194.1	193.6	193.6	195.4	196.3	195.8
50°	193.6	191.0	188.3	185.2	182.6	181.7	180.4	181.3	183.0	183.0	183.9
52.5°	176.4	174.6	173.7	171.1	169.3	169.3	169.3	169.8	171.1	172.4	172.0
55°	161.4	160.0	159.2	157.8	155.6	156.1	155.6	156.5	157.8	159.2	160.0
57.5°	145.5	145.0	144.1	141.9	141.9	141.5	142.8	143.2	145.5	146.3	147.7
60°	131.3	130.0	130.0	128.2	128.2	128.2	129.5	130.9	132.6	133.1	134.0
62.5°	116.3	116.3	115.8	114.5	114.5	115.8	116.3	118.0	118.9	118.9	120.3
65°	102.1	101.7	101.2	101.7	102.1	102.1	103.5	104.3	105.2	105.7	106.1
67.5°	88.0	87.5	88.4	88.0	88.9	90.6	90.2	91.5	92.8	92.8	93.3
70°	74.7	75.6	75.2	76.0	75.6	76.5	77.8	78.3	78.3	78.7	80.0
72.5°	62.3	62.3	62.3	61.9	62.3	63.2	64.1	64.5	65.4	65.9	67.2
75°	50.4	50.4	49.5	50.4	50.4	51.3	52.2	52.2	52.2	53.1	54.4
77.5°	38.0	38.5	38.0	38.9	38.9	39.3	40.2	39.8	40.7	41.1	41.6
80°	27.9	27.4	27.4	27.4	27.9	27.9	28.7	29.2	29.2	30.5	29.6
82.5°	17.7	18.1	17.7	18.1	18.1	18.6	18.1	18.6	19.0	19.9	19.5
85°	10.2	9.7	9.7	10.2	9.7	9.7	10.2	9.7	10.2	9.7	10.2
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.7	2.7	2.7	2.2
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	22.9	24.0	25.1	26.1	27.2	28.0	28.8	29.5	30.3
97.5°	30.9	24.5	25.7	28.2	30.7	33.1	35.6	36.1	36.5	37.0	37.5
100°	38.5	27.9	29.2	31.9	34.5	37.2	39.8	41.0	42.3	43.5	44.8
102.5°	168.6	168.4	154.3	126.0	97.7	69.5	41.2	42.9	44.6	46.3	48.0
105°	231.0	233.3	212.1	169.7	127.4	85.0	42.6	44.3	46.0	47.7	49.4
107.5°	277.5	279.4	253.2	200.9	148.6	96.3	44.0	45.7	47.4	49.1	50.8
110°	322.5	324.1	301.7	256.8	212.0	167.1	122.3	106.8	91.2	75.7	60.2

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	365.4	366.8	365.5	362.8	360.2	357.5	354.9	288.0	221.1	154.2	87.3
115°	412.3	413.6	415.5	419.4	423.3	427.1	431.0	359.1	287.3	215.4	143.5
117.5°	455.3	456.9	458.2	460.8	463.5	466.1	468.7	446.5	424.3	402.1	379.9
120°	498.3	499.5	500.9	503.7	506.5	509.3	512.1	513.9	515.8	517.6	519.5
122.5°	538.1	539.3	540.9	544.0	547.1	550.2	553.3	554.2	555.2	556.1	557.0
125°	576.0	577.0	578.5	581.4	584.4	587.3	590.3	591.4	592.5	593.6	594.7
127.5°	612.9	614.0	615.2	617.5	619.8	622.2	624.5	626.1	627.6	629.2	630.7
130°	648.5	649.7	650.6	652.3	654.0	655.7	657.4	659.1	660.8	662.5	664.2
132.5°	681.5	682.5	683.4	685.1	686.8	688.5	690.2	691.6	693.0	694.4	695.8
135°	712.7	713.9	714.6	716.0	717.4	718.8	720.2	721.8	723.3	724.9	726.4
137.5°	741.0	741.9	742.7	744.2	745.8	747.3	748.9	750.5	752.0	753.6	755.1
140°	768.5	769.1	770.0	771.7	773.4	775.1	776.8	778.2	779.6	781.0	782.4
142.5°	793.1	793.6	794.6	796.6	798.7	800.7	802.7	803.9	805.2	806.4	807.7
145°	814.6	814.5	815.8	818.5	821.1	823.8	826.4	827.5	828.6	829.7	830.8
147.5°	836.4	836.2	837.5	840.2	842.8	845.5	848.1	848.9	849.7	850.4	851.2
150°	856.3	855.8	857.0	859.5	862.0	864.4	866.9	867.8	868.8	869.7	870.6
152.5°	874.5	873.9	875.1	877.4	879.7	882.1	884.4	885.3	886.3	887.2	888.1
155°	892.1	891.4	892.3	894.2	896.1	897.9	899.8	900.7	901.7	902.6	903.5
157.5°	907.3	906.7	907.4	908.8	910.2	911.6	913.0	914.1	915.2	916.3	917.4
160°	921.2	920.7	921.2	922.1	923.0	924.0	924.9	925.8	926.8	927.7	928.6
162.5°	932.4	931.9	932.3	933.1	933.8	934.6	935.4	936.5	937.6	938.7	939.8
165°	942.2	941.7	941.9	942.4	942.9	943.3	943.8	944.9	946.0	947.1	948.2
167.5°	949.9	949.4	949.6	950.1	950.6	951.0	951.5	952.6	953.6	954.7	955.8
170°	956.1	955.6	955.8	956.1	956.4	956.7	957.0	958.1	959.2	960.3	961.4
172.5°	960.3	959.8	960.0	960.3	960.6	960.9	961.2	962.3	963.4	964.5	965.6
175°	963.1	962.6	962.8	963.1	963.4	963.7	964.0	965.1	966.2	967.3	968.4
177.5°	964.5	964.0	964.1	964.2	964.4	964.5	964.7	965.8	966.9	968.0	969.1
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	548.2	549.5	546.4	545.5	546.4	543.3	544.2	545.1	545.1	546.4	547.3
5°	516.4	514.6	511.5	510.6	509.7	511.1	510.2	511.5	511.9	515.0	515.5
7.5°	485.0	482.3	479.7	477.0	476.1	473.9	476.1	476.1	479.2	478.4	480.6
10°	447.8	447.4	443.9	442.5	440.8	437.2	442.1	440.8	443.0	447.0	447.8
12.5°	420.4	415.6	417.8	411.6	413.8	410.3	410.7	410.7	414.2	414.7	413.8
15°	394.4	390.4	384.6	382.0	380.6	378.9	384.6	385.1	382.4	388.6	386.4
17.5°	367.8	367.8	362.5	361.2	357.7	359.4	358.5	359.0	358.1	362.5	364.7
20°	344.8	342.6	340.9	341.3	336.9	336.0	335.1	336.0	339.1	342.2	343.1
22.5°	326.3	324.9	320.5	321.4	317.9	319.2	318.3	320.5	321.0	321.0	324.1
25°	308.6	306.8	307.3	305.5	304.2	304.2	302.8	304.2	305.9	306.8	307.3
27.5°	295.3	294.0	291.8	290.5	291.3	289.1	290.9	292.2	292.2	291.3	292.2
30°	279.4	280.3	280.3	275.9	277.6	276.8	278.1	279.0	279.0	279.4	278.5
32.5°	268.8	266.1	265.7	265.3	265.3	263.5	263.5	264.8	265.3	265.7	267.0
35°	254.6	254.6	252.4	253.8	252.0	252.4	252.0	252.4	253.3	252.0	253.3
37.5°	241.8	242.3	241.4	242.3	242.7	241.8	240.9	242.7	241.8	241.8	240.9
40°	230.8	230.3	230.8	230.8	230.8	231.2	230.3	230.3	230.3	229.4	228.6
42.5°	221.5	218.8	219.7	220.2	218.8	218.8	219.3	218.8	220.2	217.5	217.5
45°	208.2	207.3	207.8	207.8	208.7	207.3	208.2	208.7	207.3	206.9	206.0
47.5°	196.3	197.2	196.3	197.2	197.2	198.1	196.3	196.7	197.2	195.4	194.1
50°	184.4	184.4	185.7	185.2	185.7	184.8	184.8	184.4	184.8	183.9	182.6
52.5°	173.3	172.0	174.2	173.7	173.3	172.9	172.4	172.9	172.0	171.1	171.1
55°	159.6	159.6	160.9	161.4	161.4	160.5	159.6	160.0	159.6	159.2	158.7
57.5°	148.5	146.8	147.7	148.1	148.1	146.8	147.7	146.8	146.8	147.2	145.9
60°	134.4	134.4	133.5	134.8	134.8	134.0	134.0	134.4	133.5	133.1	132.6
62.5°	119.4	119.8	121.1	121.6	122.0	121.1	120.3	120.7	120.7	119.4	119.8
65°	106.5	107.4	109.2	108.8	107.9	108.3	107.4	107.9	106.5	107.0	105.7
67.5°	94.2	93.7	94.2	94.2	95.1	94.6	93.7	93.7	93.3	94.6	93.3
70°	80.9	80.9	80.9	80.9	81.3	81.8	80.9	80.0	80.5	79.6	79.1
72.5°	67.2	67.6	67.2	68.1	66.8	67.6	67.6	67.2	66.8	66.8	66.8
75°	54.4	55.3	53.9	54.4	53.9	54.8	54.4	54.4	53.5	53.1	53.5
77.5°	41.6	42.0	41.1	41.6	41.1	41.6	41.6	41.1	41.1	41.1	41.1
80°	29.6	30.1	29.6	29.2	28.7	29.6	28.7	29.2	29.6	29.2	30.1
82.5°	19.0	19.0	18.6	19.0	18.1	18.1	18.6	18.6	18.1	19.0	18.1
85°	9.3	9.3	10.2	9.3	8.8	8.8	8.8	9.3	8.8	9.7	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.7	30.6	30.5	30.3	30.2	30.0	30.2	30.3	30.5	30.6	30.7
97.5°	37.7	37.8	37.9	38.1	38.2	38.4	38.2	38.1	37.9	37.8	37.7
100°	45.4	45.6	45.9	46.2	46.5	46.8	46.5	46.2	45.9	45.6	45.4
102.5°	48.9	49.1	49.6	50.1	50.5	51.0	50.5	50.1	49.6	49.1	48.9
105°	50.3	50.6	51.2	51.9	52.5	53.1	52.5	51.9	51.2	50.6	50.3
107.5°	51.7	52.0	52.6	53.3	53.9	54.5	53.9	53.3	52.6	52.0	51.7
110°	52.4	52.7	53.3	54.0	54.6	55.2	54.6	54.0	53.3	52.7	52.4



TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.8	54.0	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	53.8
115°	107.6	102.0	90.8	79.7	68.5	57.3	68.5	79.7	90.8	102.0	107.6
117.5°	368.8	348.5	307.8	267.1	226.5	185.8	226.5	267.1	307.8	348.5	368.8
120°	520.4	509.9	489.0	468.0	447.1	426.1	447.1	468.0	489.0	509.9	520.4
122.5°	557.5	557.6	557.7	557.9	558.0	558.2	558.0	557.9	557.7	557.6	557.5
125°	595.2	595.4	595.9	596.4	596.8	597.3	596.8	596.4	595.9	595.4	595.2
127.5°	631.5	631.6	631.7	631.9	632.0	632.2	632.0	631.9	631.7	631.6	631.5
130°	665.0	664.9	664.8	664.6	664.5	664.3	664.5	664.6	664.8	664.9	665.0
132.5°	696.5	696.4	696.3	696.1	696.0	695.8	696.0	696.1	696.3	696.4	696.5
135°	727.2	727.0	726.7	726.4	726.1	725.8	726.1	726.4	726.7	727.0	727.2
137.5°	755.9	755.7	755.2	754.7	754.3	753.8	754.3	754.7	755.2	755.7	755.9
140°	783.1	782.7	781.9	781.2	780.4	779.6	780.4	781.2	781.9	782.7	783.1
142.5°	808.3	807.9	807.1	806.4	805.6	804.8	805.6	806.4	807.1	807.9	808.3
145°	831.3	830.9	830.1	829.4	828.6	827.8	828.6	829.4	830.1	830.9	831.3
147.5°	851.6	851.3	850.7	850.0	849.4	848.8	849.4	850.0	850.7	851.3	851.6
150°	871.1	870.7	869.9	869.2	868.4	867.6	868.4	869.2	869.9	870.7	871.1
152.5°	888.6	888.1	887.0	885.9	884.8	883.7	884.8	885.9	887.0	888.1	888.6
155°	904.0	903.4	902.1	900.9	899.6	898.4	899.6	900.9	902.1	903.4	904.0
157.5°	917.9	917.3	916.0	914.8	913.5	912.3	913.5	914.8	916.0	917.3	917.9
160°	929.1	928.6	927.5	926.4	925.3	924.2	925.3	926.4	927.5	928.6	929.1
162.5°	940.3	939.6	938.2	936.8	935.4	934.0	935.4	936.8	938.2	939.6	940.3
165°	948.7	948.2	947.1	946.0	944.9	943.8	944.9	946.0	947.1	948.2	948.7
167.5°	956.3	955.6	954.2	952.9	951.5	950.1	951.5	952.9	954.2	955.6	956.3
170°	961.9	961.2	959.8	958.4	957.0	955.6	957.0	958.4	959.8	961.2	961.9
172.5°	966.1	965.4	964.0	962.6	961.2	959.8	961.2	962.6	964.0	965.4	966.1
175°	968.9	968.1	966.6	965.0	963.5	961.9	963.5	965.0	966.6	968.1	968.9
177.5°	969.6	968.9	967.5	966.1	964.7	963.3	964.7	966.1	967.5	968.9	969.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	546.0	549.5	548.2	543.3	549.1	549.1	553.1	553.1	557.9	559.7	562.3
5°	515.0	517.7	519.9	517.7	521.7	527.9	531.4	534.5	541.1	543.8	547.8
7.5°	481.9	486.8	489.0	489.0	495.6	502.7	509.7	514.2	523.4	527.0	531.0
10°	449.6	455.4	459.8	459.3	470.4	474.8	483.7	493.8	503.1	508.4	514.2
12.5°	415.6	418.7	424.9	433.7	436.4	444.3	454.5	467.3	484.1	489.0	497.4
15°	387.3	395.7	400.5	404.5	410.7	418.2	429.3	441.7	458.5	469.1	477.9
17.5°	363.4	374.5	377.6	376.7	384.6	396.1	408.9	418.2	433.3	446.1	454.5
20°	344.0	348.4	353.7	355.9	362.1	374.5	386.8	397.4	409.8	420.0	429.7
22.5°	324.5	328.0	332.5	336.4	341.3	348.4	360.3	373.6	385.5	395.2	406.3
25°	308.6	310.8	314.8	317.9	323.2	328.0	336.4	351.0	365.2	370.9	380.6
27.5°	293.1	294.9	297.5	301.1	303.7	308.6	316.1	328.0	342.6	348.4	361.6
30°	279.4	280.7	283.4	285.2	286.5	292.2	298.0	307.3	318.3	326.3	336.0
32.5°	266.6	267.9	270.6	271.0	272.8	275.9	281.2	289.6	299.3	305.9	314.3
35°	252.4	253.3	256.0	256.9	258.2	260.8	264.8	271.0	279.8	284.7	292.2
37.5°	241.4	240.9	242.7	244.0	245.8	247.1	248.5	254.6	261.3	265.7	271.4
40°	229.4	228.6	229.0	230.8	231.7	233.4	233.4	239.6	244.0	247.6	252.0
42.5°	217.5	217.1	216.2	217.1	218.0	218.4	218.8	223.3	227.7	230.8	235.6
45°	205.6	205.1	204.2	204.7	204.7	205.6	206.9	208.7	211.8	214.4	217.1
47.5°	194.5	193.6	192.3	191.9	192.8	192.8	192.8	194.5	197.6	198.5	201.2
50°	183.0	181.7	179.9	179.0	179.0	178.6	179.5	179.9	182.6	183.5	185.7
52.5°	170.6	169.8	168.0	166.2	166.7	165.8	166.2	166.7	167.6	168.9	170.2
55°	158.3	156.5	155.2	154.7	153.4	153.4	152.1	153.9	153.4	153.9	155.6
57.5°	146.3	144.6	142.4	141.5	140.1	139.7	138.8	138.4	138.8	140.1	141.5
60°	132.2	131.3	130.0	128.7	127.8	126.4	125.6	125.6	125.1	125.1	125.6
62.5°	118.5	118.0	116.3	115.8	114.9	114.1	112.7	111.9	111.9	112.7	113.2
65°	105.2	104.8	103.5	103.0	100.8	99.9	99.5	99.0	98.1	98.1	98.1
67.5°	92.8	91.5	91.5	89.3	87.5	86.7	85.8	85.3	85.3	85.3	85.8
70°	79.1	79.1	77.8	76.5	74.7	75.2	73.8	72.5	72.5	71.6	72.1
72.5°	65.9	65.4	64.1	63.7	62.3	61.0	60.1	61.0	59.7	59.2	59.7
75°	53.1	52.6	51.7	50.8	51.3	50.0	48.6	48.2	48.2	47.3	47.3
77.5°	40.7	41.6	39.8	39.3	38.5	37.6	37.1	36.7	36.7	36.7	37.6
80°	28.3	28.7	28.7	27.9	28.3	27.0	27.0	27.0	25.6	26.1	26.5
82.5°	18.1	18.1	17.7	18.1	17.7	17.7	17.2	17.2	16.8	16.8	17.2
85°	10.2	9.7	9.3	10.2	9.7	9.7	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.5	3.5	3.5
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.3	29.5	28.8	28.0	27.2	26.1	25.1	24.0	22.9	22.4	25.0
97.5°	37.5	37.0	36.5	36.1	35.6	33.1	30.7	28.2	25.7	24.5	30.9
100°	44.8	43.5	42.3	41.0	39.8	37.2	34.5	31.9	29.2	27.9	38.5
102.5°	48.0	46.3	44.6	42.9	41.2	69.5	97.7	126.0	154.3	168.4	168.6
105°	49.4	47.7	46.0	44.3	42.6	85.0	127.4	169.7	212.1	233.3	231.0
107.5°	50.8	49.1	47.4	45.7	44.0	96.3	148.6	200.9	253.2	279.4	277.5
110°	60.2	75.7	91.2	106.8	122.3	167.1	212.0	256.8	301.7	324.1	322.5

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.3	154.2	221.1	288.0	354.9	357.5	360.2	362.8	365.5	366.8	365.4
115°	143.5	215.4	287.3	359.1	431.0	427.1	423.3	419.4	415.5	413.6	412.3
117.5°	379.9	402.1	424.3	446.5	468.7	466.1	463.5	460.8	458.2	456.9	455.3
120°	519.5	517.6	515.8	513.9	512.1	509.3	506.5	503.7	500.9	499.5	498.3
122.5°	557.0	556.1	555.2	554.2	553.3	550.2	547.1	544.0	540.9	539.3	538.1
125°	594.7	593.6	592.5	591.4	590.3	587.3	584.4	581.4	578.5	577.0	576.0
127.5°	630.7	629.2	627.6	626.1	624.5	622.2	619.8	617.5	615.2	614.0	612.9
130°	664.2	662.5	660.8	659.1	657.4	655.7	654.0	652.3	650.6	649.7	648.5
132.5°	695.8	694.4	693.0	691.6	690.2	688.5	686.8	685.1	683.4	682.5	681.5
135°	726.4	724.9	723.3	721.8	720.2	718.8	717.4	716.0	714.6	713.9	712.7
137.5°	755.1	753.6	752.0	750.5	748.9	747.3	745.8	744.2	742.7	741.9	741.0
140°	782.4	781.0	779.6	778.2	776.8	775.1	773.4	771.7	770.0	769.1	768.5
142.5°	807.7	806.4	805.2	803.9	802.7	800.7	798.7	796.6	794.6	793.6	793.1
145°	830.8	829.7	828.6	827.5	826.4	823.8	821.1	818.5	815.8	814.5	814.6
147.5°	851.2	850.4	849.7	848.9	848.1	845.5	842.8	840.2	837.5	836.2	836.4
150°	870.6	869.7	868.8	867.8	866.9	864.4	862.0	859.5	857.0	855.8	856.3
152.5°	888.1	887.2	886.3	885.3	884.4	882.1	879.7	877.4	875.1	873.9	874.5
155°	903.5	902.6	901.7	900.7	899.8	897.9	896.1	894.2	892.3	891.4	892.1
157.5°	917.4	916.3	915.2	914.1	913.0	911.6	910.2	908.8	907.4	906.7	907.3
160°	928.6	927.7	926.8	925.8	924.9	924.0	923.0	922.1	921.2	920.7	921.2
162.5°	939.8	938.7	937.6	936.5	935.4	934.6	933.8	933.1	932.3	931.9	932.4
165°	948.2	947.1	946.0	944.9	943.8	943.3	942.9	942.4	941.9	941.7	942.2
167.5°	955.8	954.7	953.6	952.6	951.5	951.0	950.6	950.1	949.6	949.4	949.9
170°	961.4	960.3	959.2	958.1	957.0	956.7	956.4	956.1	955.8	955.6	956.1
172.5°	965.6	964.5	963.4	962.3	961.2	960.9	960.6	960.3	960.0	959.8	960.3
175°	968.4	967.3	966.2	965.1	964.0	963.7	963.4	963.1	962.8	962.6	963.1
177.5°	969.1	968.0	966.9	965.8	964.7	964.5	964.4	964.2	964.1	964.0	964.5
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	575.2	575.2	575.2	575.2
2.5°	564.6	564.6	571.2	578.3
5°	552.2	555.3	565.9	575.6
7.5°	540.2	545.5	558.8	571.2
10°	525.7	532.7	549.1	563.7
12.5°	511.5	518.1	537.1	553.5
15°	491.6	500.0	520.3	540.7
17.5°	471.7	480.1	504.9	528.7
20°	448.3	459.3	487.2	519.0
22.5°	426.6	440.3	471.3	496.9
25°	402.8	424.0	452.7	485.9
27.5°	381.5	402.8	431.9	465.5
30°	357.7	379.3	409.4	440.3
32.5°	334.7	354.6	383.7	421.8
35°	310.8	329.8	358.1	396.6
37.5°	289.1	307.7	338.6	374.0
40°	267.9	287.4	313.9	349.3
42.5°	248.0	265.3	289.1	324.5
45°	229.9	242.3	264.4	297.5
47.5°	210.9	221.9	242.3	275.4
50°	193.2	202.5	220.2	251.1
52.5°	176.0	183.9	200.3	225.0
55°	160.5	168.0	179.9	204.2
57.5°	144.6	150.3	161.8	181.3
60°	129.1	134.4	143.7	159.6
62.5°	113.6	118.0	126.9	139.7
65°	99.9	103.5	110.1	121.1
67.5°	86.7	88.9	94.2	103.0
70°	73.8	75.6	80.0	87.1
72.5°	60.1	61.9	66.8	71.6
75°	48.6	49.1	52.6	56.6
77.5°	38.0	37.6	40.2	43.3
80°	26.1	27.4	29.6	30.9
82.5°	17.7	18.1	19.0	19.9
85°	9.7	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.2	40.3	45.4
97.5°	43.6	56.3	69.0	81.7
100°	59.8	81.1	102.3	123.6
102.5°	168.9	169.2	169.5	169.8
105°	226.3	221.7	217.0	212.4
107.5°	273.6	269.7	265.9	262.0
110°	319.2	316.0	312.7	309.5



TEST NUMBER: P1008040

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	362.6	359.8	357.0	354.2
115°	409.6	407.0	404.3	401.7
117.5°	452.2	449.1	446.0	442.9
120°	496.0	493.7	491.3	489.0
122.5°	535.6	533.1	530.6	528.1
125°	574.0	571.9	569.9	567.9
127.5°	610.8	608.6	606.5	604.3
130°	646.0	643.5	641.0	638.5
132.5°	679.5	677.4	675.4	673.4
135°	710.2	707.7	705.3	702.8
137.5°	739.1	737.2	735.4	733.5
140°	767.2	766.0	764.7	763.5
142.5°	792.0	790.9	789.8	788.7
145°	814.7	814.9	815.0	815.2
147.5°	836.9	837.4	837.8	838.3
150°	857.4	858.5	859.5	860.6
152.5°	875.8	877.0	878.3	879.5
155°	893.5	894.9	896.3	897.7
157.5°	908.6	909.8	911.1	912.3
160°	922.1	923.0	924.0	924.9
162.5°	933.3	934.2	935.2	936.1
165°	943.1	944.0	945.0	945.9
167.5°	950.8	951.7	952.7	953.6
170°	957.0	957.9	958.9	959.8
172.5°	961.2	962.1	963.1	964.0
175°	964.2	965.3	966.4	967.5
177.5°	965.6	966.7	967.8	968.9
180°	965.4	965.4	965.4	965.4

(END OF REPORT)