

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008041

Luminaire Tested: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008041
REPORT IS A COMBINATION OF REPORTS P984009 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4119.0 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	32	31	30	27
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	30	28	27	26	25	23
3	78	69	62	57	70	63	57	52	50	46	43	38	36	33	28	26	24	23	22	21	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	20	19	18	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	22	20	19	18	17	16	15
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	20	18	17	16	15	14	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	20	19	17	15	14	13	12	12
8	52	40	33	28	47	37	30	26	30	25	22	23	20	17	17	15	13	12	11	10	11
9	48	37	30	25	43	33	27	23	27	23	19	21	18	16	16	14	12	11	10	9	10
10	45	34	27	22	41	31	25	20	25	20	17	20	16	14	15	13	11	10	9	8	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9148	9148	9148	9148
5°	9169	9753	9205	7760
10°	9062	10647	9120	6398
15°	8843	11230	8966	5389
20°	8706	10545	8706	4684
25°	8428	9060	8466	4189
30°	7971	7121	8124	3794
35°	7566	4924	7693	3471
40°	7102	3717	7183	3214
45°	6528	3056	6635	2936
50°	6033	2681	6043	2688
55°	5468	2286	5502	2418
60°	4867	1908	4934	2111
65°	4326	1552	4405	1802
70°	3789	1217	3885	1454
75°	3183	884	3306	1055
80°	2483	561	2659	626
85°	1624	282	1752	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9457 cd/sqm

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	1.3
10°-20°	160.2	3.9
20°-30°	232.5	5.6
30°-40°	245.1	6.0
40°-50°	216.9	5.3
50°-60°	173.2	4.2
60°-70°	117.6	2.9
70°-80°	60.2	1.5
80°-90°	15.9	0.4
90°-100°	32.0	0.8
100°-110°	119.2	2.9
110°-120°	316.1	7.7
120°-130°	524.2	12.7
130°-140°	556.8	13.5
140°-150°	517.5	12.6
150°-160°	416.1	10.1
160°-170°	268.1	6.5
170°-180°	92.3	2.2
0°-30°	447.8	10.9
0°-40°	692.9	16.8
0°-60°	1083.0	26.3
0°-90°	1276.7	31.0
90°-120°	467.2	11.3
90°-150°	2065.8	50.2
90°-180°	2842.0	69.0
0°-180°	4119.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	578	578	578	578	578	
5°	578	645	581	514	578	55
15°	543	793	551	381	543	153
25°	488	661	490	306	488	223
35°	398	360	405	254	398	249
45°	299	217	304	208	299	232
55°	205	152	206	161	205	183
65°	122	94	124	109	122	121
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	19	1	19	1	3
95°	46	30	46	30	46	54
105°	213	53	213	53	213	228
115°	403	58	403	58	403	397
125°	570	600	570	600	570	509
135°	706	729	706	729	706	545
145°	819	831	819	831	819	512
155°	902	902	902	902	902	415
165°	950	948	950	948	950	268
175°	972	966	972	966	972	92
180°	970	970	970	970	970	

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	581.0	582.3	584.6	585.0	589.4	593.0	597.0	597.0	598.3	597.9	594.3
5°	578.3	582.3	588.1	593.0	601.0	604.5	609.9	613.9	617.4	620.1	619.6
7.5°	573.9	581.0	589.4	598.8	609.4	615.6	623.2	630.3	635.2	639.6	642.7
10°	566.3	578.3	589.9	602.3	616.1	624.5	633.4	642.7	650.3	658.7	666.7
12.5°	556.1	573.4	587.7	604.1	621.0	630.3	644.5	651.6	666.3	687.6	693.4
15°	543.2	566.8	580.1	601.0	623.2	630.7	650.3	661.8	692.0	705.4	721.4
17.5°	531.2	557.5	575.2	599.2	621.0	635.6	654.7	678.3	703.6	722.7	740.5
20°	521.5	546.8	568.1	594.8	622.3	641.0	661.0	689.4	716.9	736.5	750.2
22.5°	499.3	531.7	556.6	586.3	619.6	645.4	664.5	695.6	725.4	737.4	749.3
25°	488.2	516.1	545.0	578.8	617.9	648.5	665.0	699.6	725.8	730.2	732.9
27.5°	467.7	499.3	533.0	571.7	617.4	643.2	664.1	695.6	716.5	713.4	705.4
30°	442.4	481.1	518.4	560.1	611.2	639.2	658.7	687.6	698.3	682.3	668.1
32.5°	423.8	460.2	501.5	549.9	604.1	630.7	649.8	672.5	674.7	645.9	621.9
35°	398.4	438.9	485.5	536.6	592.1	616.1	633.9	647.6	637.0	596.5	568.1
37.5°	375.8	415.8	465.5	517.5	575.7	599.2	613.4	615.6	589.4	553.9	512.1
40°	350.9	392.2	444.2	498.8	557.5	577.9	586.8	580.1	542.4	501.0	452.6
42.5°	326.0	366.9	422.9	478.8	534.4	551.7	555.2	537.0	490.8	442.4	386.4
45°	298.9	341.6	397.5	454.0	507.7	517.5	517.9	491.7	437.1	386.4	334.5
47.5°	276.7	316.3	371.8	428.2	473.5	480.2	477.5	447.3	387.8	330.9	285.6
50°	252.3	290.1	345.1	400.7	439.3	441.1	434.4	391.3	333.1	281.2	245.2
52.5°	226.1	264.3	314.9	368.2	402.9	400.2	387.3	341.1	286.5	243.4	215.9
55°	205.2	239.0	286.5	338.5	362.9	355.4	341.1	294.1	251.0	214.5	190.6
57.5°	182.1	211.9	258.5	303.8	318.0	310.9	296.7	252.7	212.8	185.2	169.2
60°	160.4	187.4	228.3	266.1	277.2	269.6	253.2	213.7	184.8	161.7	149.7
62.5°	140.4	163.9	198.1	232.8	237.2	229.6	215.4	183.4	158.6	140.4	131.5
65°	121.7	143.9	171.5	197.7	201.7	193.7	179.0	155.9	135.0	123.5	115.0
67.5°	103.5	121.3	145.7	164.8	167.0	159.5	147.5	128.8	115.9	103.5	97.3
70°	87.5	100.8	119.9	135.5	136.4	129.3	123.0	106.2	96.4	87.5	82.6
72.5°	72.0	81.3	95.9	107.5	107.9	103.5	97.7	87.1	78.6	72.4	67.5
75°	56.9	64.9	73.7	84.0	83.5	80.0	75.5	68.8	61.7	57.7	55.5
77.5°	43.5	48.4	55.5	62.2	62.2	60.4	57.7	52.9	48.4	44.4	42.2
80°	31.1	34.2	40.0	42.2	43.1	42.6	40.4	36.9	35.1	32.0	31.1
82.5°	20.0	22.2	24.9	27.1	28.4	27.5	27.1	25.3	22.7	21.8	20.9
85°	11.5	12.4	13.8	15.1	15.5	15.1	16.0	14.7	13.3	13.3	12.9
87.5°	4.9	5.3	6.2	6.2	6.7	6.7	6.2	6.7	6.7	6.2	5.8
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.6	40.4	35.3	30.1	25.0	22.4	23.0	24.1	25.2	26.3	27.4
97.5°	82.1	69.3	56.5	43.8	31.0	24.6	25.8	28.3	30.8	33.3	35.8
100°	124.2	102.8	81.5	60.1	38.8	28.1	29.4	32.1	34.7	37.4	40.0
102.5°	170.5	170.2	169.9	169.6	169.3	169.1	154.9	126.5	98.2	69.8	41.4
105°	213.3	218.0	222.6	227.3	232.0	234.3	213.0	170.5	127.9	85.4	42.8
107.5°	263.1	267.0	270.9	274.8	278.7	280.6	254.3	201.8	149.3	96.7	44.2
110°	310.8	314.1	317.3	320.6	323.9	325.5	303.0	257.9	212.9	167.8	122.8



TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	355.7	358.5	361.3	364.1	366.9	368.3	367.0	364.3	361.7	359.0	356.4
115°	403.4	406.0	408.7	411.3	414.0	415.3	417.2	421.1	425.0	428.9	432.8
117.5°	444.8	447.9	451.0	454.1	457.2	458.8	460.1	462.8	465.4	468.1	470.7
120°	491.1	493.4	495.8	498.1	500.4	501.6	503.0	505.8	508.6	511.4	514.2
122.5°	530.4	532.9	535.4	537.9	540.4	541.6	543.2	546.3	549.4	552.5	555.6
125°	570.3	572.3	574.4	576.4	578.5	579.5	581.0	583.9	586.9	589.8	592.8
127.5°	606.8	609.0	611.2	613.3	615.5	616.6	617.8	620.1	622.5	624.8	627.2
130°	641.2	643.7	646.2	648.7	651.2	652.4	653.3	655.0	656.7	658.4	660.1
132.5°	676.3	678.3	680.3	682.4	684.4	685.4	686.3	688.0	689.7	691.4	693.1
135°	705.7	708.2	710.7	713.2	715.7	717.0	717.7	719.1	720.5	721.9	723.3
137.5°	736.6	738.5	740.3	742.2	744.1	745.0	745.8	747.3	748.9	750.4	752.0
140°	766.8	768.0	769.3	770.5	771.8	772.4	773.3	775.0	776.7	778.4	780.1
142.5°	792.0	793.1	794.2	795.3	796.4	796.9	797.9	800.0	802.0	804.1	806.1
145°	818.7	818.5	818.4	818.2	818.1	818.0	819.3	822.0	824.6	827.3	829.9
147.5°	841.8	841.3	840.9	840.4	839.9	839.7	841.0	843.7	846.4	849.0	851.7
150°	864.3	863.2	862.1	861.0	859.9	859.4	860.6	863.1	865.6	868.1	870.6
152.5°	883.2	882.0	880.7	879.5	878.2	877.6	878.8	881.1	883.4	885.8	888.1
155°	901.5	900.1	898.7	897.3	895.9	895.2	896.1	898.0	899.9	901.7	903.6
157.5°	916.2	915.0	913.7	912.5	911.2	910.6	911.3	912.7	914.1	915.5	916.9
160°	928.8	927.9	926.9	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8
162.5°	940.1	939.1	938.2	937.2	936.3	935.8	936.2	937.0	937.8	938.6	939.4
165°	949.9	949.0	948.0	947.1	946.2	945.7	945.9	946.4	946.9	947.3	947.8
167.5°	957.6	956.7	955.7	954.8	953.9	953.4	953.6	954.1	954.6	955.0	955.5
170°	963.9	963.0	962.0	961.1	960.2	959.7	959.9	960.2	960.5	960.8	961.1
172.5°	968.1	967.2	966.2	965.3	964.4	963.9	964.1	964.4	964.7	965.0	965.3
175°	971.6	970.5	969.4	968.3	967.2	966.7	966.9	967.2	967.5	967.8	968.1
177.5°	973.0	971.9	970.8	969.7	968.6	968.1	968.2	968.3	968.5	968.6	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	600.5	601.0	601.9	606.3	608.5	609.0	607.2	611.2	612.5	611.2	610.3
5°	629.0	631.6	637.0	642.7	642.3	642.7	645.4	648.1	649.0	645.4	646.7
7.5°	653.8	659.2	665.0	673.8	673.8	678.3	680.1	682.3	687.6	684.9	684.1
10°	682.3	689.4	700.0	714.3	714.7	719.1	723.6	730.7	732.9	731.1	732.0
12.5°	717.8	731.6	732.5	748.0	755.1	756.0	763.1	761.8	766.2	766.2	773.8
15°	733.4	754.7	766.7	781.8	786.2	780.9	786.7	792.9	793.3	793.3	792.9
17.5°	761.3	769.8	781.8	789.8	791.5	791.5	792.0	794.7	792.9	789.3	792.0
20°	767.1	770.7	775.1	774.2	775.1	770.7	766.2	761.8	762.2	760.0	766.7
22.5°	756.5	755.6	745.3	738.7	738.7	729.8	721.4	717.4	713.4	714.7	716.9
25°	729.8	716.0	703.6	693.8	691.6	677.4	665.8	662.3	655.6	661.0	661.8
27.5°	687.2	671.6	651.6	643.2	631.6	625.9	617.9	607.2	593.4	601.4	600.1
30°	641.4	618.3	601.9	581.4	563.2	561.9	546.8	529.0	521.9	521.9	525.9
32.5°	590.3	559.7	535.7	506.8	489.1	481.5	463.3	445.5	449.5	436.2	441.1
35°	530.8	490.4	460.2	432.2	418.9	410.0	386.4	376.7	366.0	359.8	371.3
37.5°	473.9	427.3	388.7	358.0	353.1	337.1	321.1	314.9	308.7	311.4	310.9
40°	404.7	363.3	328.7	304.7	296.3	288.7	278.1	270.5	266.5	268.7	269.2
42.5°	342.0	307.4	281.6	264.7	257.6	252.3	247.0	240.8	239.4	239.4	241.2
45°	293.6	265.2	247.9	234.1	230.1	226.1	222.1	219.4	218.5	216.8	218.1
47.5°	255.0	232.3	221.7	211.4	207.0	206.1	202.6	201.2	199.4	199.0	199.4
50°	222.5	208.3	198.6	192.8	189.7	188.3	186.6	183.9	183.0	185.2	184.3
52.5°	199.9	186.6	181.2	175.5	173.7	171.9	169.2	169.7	169.2	168.3	168.3
55°	177.2	168.8	163.5	159.0	158.6	156.8	154.6	153.7	153.2	152.4	153.7
57.5°	159.0	152.4	147.5	143.5	141.7	141.7	139.5	137.7	137.7	137.3	137.7
60°	140.8	134.1	131.0	127.0	125.7	125.3	123.9	123.0	121.7	121.7	121.7
62.5°	123.9	118.6	115.0	111.5	111.9	109.7	107.9	107.0	107.0	107.5	107.5
65°	107.9	104.4	99.9	96.8	95.9	95.5	94.6	94.2	92.8	93.7	93.7
67.5°	93.3	88.4	85.7	84.4	83.1	82.6	81.7	80.8	80.4	80.0	80.8
70°	78.6	74.6	72.4	71.5	70.2	69.7	69.3	68.0	68.4	68.8	69.3
72.5°	65.3	61.7	61.3	58.6	58.6	58.6	56.9	57.7	57.3	56.4	57.3
75°	51.5	49.7	48.9	47.5	48.0	47.5	47.1	45.8	45.8	46.2	46.6
77.5°	40.9	39.1	38.6	37.3	36.4	37.3	36.4	36.0	36.0	36.4	36.4
80°	30.2	29.3	28.0	28.0	28.0	27.5	27.5	27.5	27.1	26.7	27.1
82.5°	20.0	20.0	19.5	19.1	19.5	18.7	19.1	19.1	19.1	19.1	19.1
85°	12.9	12.4	12.4	12.0	12.0	12.0	12.4	11.5	11.5	12.0	12.0
87.5°	5.8	5.8	5.8	6.2	5.8	5.8	5.8	6.2	5.8	5.8	5.8
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.2	29.0	29.7	30.5	30.9	30.8	30.7	30.5	30.4	30.2	30.4
97.5°	36.3	36.7	37.2	37.7	37.9	38.0	38.1	38.3	38.4	38.6	38.4
100°	41.2	42.5	43.7	45.0	45.6	45.8	46.1	46.4	46.7	47.0	46.7
102.5°	43.1	44.8	46.5	48.2	49.1	49.3	49.8	50.3	50.7	51.2	50.7
105°	44.5	46.2	47.9	49.6	50.5	50.8	51.4	52.1	52.7	53.3	52.7
107.5°	45.9	47.6	49.3	51.0	51.9	52.2	52.8	53.5	54.1	54.7	54.1
110°	107.2	91.6	76.0	60.4	52.6	52.9	53.5	54.2	54.8	55.4	54.8

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	289.2	222.0	154.8	87.6	54.0	54.2	54.7	55.2	55.6	56.1	55.6
115°	360.6	288.4	216.3	144.1	108.0	102.4	91.2	79.9	68.7	57.5	68.7
117.5°	448.4	426.1	403.8	381.5	370.4	350.0	309.1	268.3	227.4	186.6	227.4
120°	516.1	517.9	519.8	521.7	522.6	512.1	491.0	470.0	448.9	427.9	448.9
122.5°	556.5	557.5	558.4	559.3	559.8	559.9	560.0	560.2	560.3	560.5	560.3
125°	593.9	595.0	596.1	597.2	597.7	597.9	598.4	598.9	599.3	599.8	599.3
127.5°	628.8	630.3	631.9	633.4	634.2	634.3	634.4	634.6	634.7	634.9	634.7
130°	661.8	663.6	665.3	667.0	667.9	667.8	667.7	667.5	667.4	667.2	667.4
132.5°	694.5	695.9	697.3	698.7	699.4	699.3	699.2	699.0	698.9	698.7	698.9
135°	724.9	726.4	728.0	729.5	730.3	730.1	729.8	729.5	729.2	728.9	729.2
137.5°	753.6	755.2	756.7	758.3	759.1	758.9	758.4	757.9	757.5	757.0	757.5
140°	781.5	782.9	784.3	785.7	786.4	786.0	785.2	784.5	783.7	782.9	783.7
142.5°	807.3	808.6	809.8	811.1	811.7	811.3	810.5	809.8	809.0	808.2	809.0
145°	831.0	832.1	833.2	834.3	834.8	834.4	833.6	832.9	832.1	831.3	832.1
147.5°	852.5	853.3	854.0	854.8	855.2	854.9	854.3	853.6	853.0	852.4	853.0
150°	871.5	872.5	873.4	874.3	874.8	874.4	873.6	872.9	872.1	871.3	872.1
152.5°	889.1	890.0	891.0	891.9	892.4	891.8	890.7	889.6	888.5	887.4	888.5
155°	904.5	905.5	906.4	907.3	907.8	907.2	905.9	904.7	903.4	902.2	903.4
157.5°	918.0	919.1	920.2	921.3	921.8	921.2	919.9	918.7	917.4	916.2	917.4
160°	929.7	930.7	931.6	932.5	933.0	932.5	931.4	930.3	929.2	928.1	929.2
162.5°	940.5	941.6	942.7	943.8	944.3	943.6	942.2	940.8	939.4	938.0	939.4
165°	948.9	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	948.9
167.5°	956.6	957.7	958.8	959.9	960.4	959.7	958.3	956.9	955.5	954.1	955.5
170°	962.2	963.3	964.4	965.5	966.0	965.3	963.9	962.5	961.1	959.7	961.1
172.5°	966.4	967.5	968.6	969.7	970.2	969.5	968.1	966.7	965.3	963.9	965.3
175°	969.2	970.3	971.4	972.5	973.0	972.2	970.7	969.1	967.6	966.0	967.6
177.5°	969.9	971.0	972.1	973.2	973.7	973.0	971.6	970.2	968.8	967.4	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	612.5	609.4	606.8	607.2	609.4	607.7	603.2	597.4	595.2	592.5	595.2
5°	649.4	646.7	641.4	641.9	640.5	638.7	631.6	622.8	622.8	615.6	614.8
7.5°	685.8	681.8	678.3	677.4	672.5	668.9	662.7	650.3	645.4	637.0	632.1
10°	726.7	723.6	719.6	714.7	712.0	705.8	695.6	677.4	668.5	657.0	648.5
12.5°	768.0	767.6	758.7	748.9	748.5	738.7	731.6	707.1	695.2	679.6	659.6
15°	794.2	792.0	787.1	782.2	783.5	772.9	756.9	728.0	720.0	701.4	680.1
17.5°	793.8	793.8	792.4	791.5	790.2	787.1	778.2	759.1	746.2	722.7	702.7
20°	768.4	774.2	775.6	775.1	779.6	781.8	781.3	769.3	759.1	738.2	717.8
22.5°	717.8	731.1	736.9	740.5	749.8	754.7	766.2	761.8	759.1	743.6	726.2
25°	670.7	675.2	692.5	693.4	706.3	718.3	729.8	737.4	747.1	741.4	726.7
27.5°	609.9	620.1	632.5	641.9	644.5	668.9	688.0	702.3	724.5	726.2	721.4
30°	541.0	545.9	566.3	578.8	593.0	610.8	638.3	662.7	682.7	700.9	707.1
32.5°	457.1	477.1	489.1	504.2	516.6	548.1	581.9	613.4	636.5	667.2	680.5
35°	380.2	395.8	416.2	422.4	445.1	471.7	515.7	556.1	591.2	622.3	649.4
37.5°	316.7	329.1	350.9	360.7	374.0	408.2	445.1	495.3	537.5	575.7	609.4
40°	273.2	282.5	298.9	302.0	313.2	344.2	374.0	421.1	477.1	528.6	565.5
42.5°	243.4	247.9	259.0	263.0	270.1	290.9	317.6	362.0	414.0	467.3	519.3
45°	222.1	225.2	231.9	235.4	244.3	253.6	275.4	310.9	351.8	405.5	461.5
47.5°	203.0	207.0	209.7	211.9	216.8	227.0	241.2	267.4	306.5	355.8	410.0
50°	187.0	188.3	193.2	193.7	196.8	203.4	216.8	232.8	263.8	303.8	356.2
52.5°	171.0	172.3	175.5	178.6	179.9	185.2	194.1	207.4	230.5	262.1	308.7
55°	155.0	156.8	159.9	162.1	163.5	167.9	173.2	186.1	204.3	226.5	264.7
57.5°	139.0	143.0	143.9	145.2	147.5	152.4	157.2	164.8	179.0	199.4	227.4
60°	123.9	125.3	128.4	129.7	131.9	134.6	140.8	146.6	156.8	172.8	198.1
62.5°	108.4	111.5	112.8	114.2	115.9	119.0	123.0	129.3	138.1	151.0	171.0
65°	95.1	95.5	98.2	99.9	101.7	103.9	107.9	113.7	119.0	131.0	145.7
67.5°	82.2	83.1	84.0	85.7	87.9	90.2	93.7	96.8	103.5	111.5	123.0
70°	69.7	69.7	72.0	73.3	72.8	75.5	78.2	81.7	86.6	94.2	103.5
72.5°	58.6	58.2	60.0	60.4	61.3	63.1	64.9	68.4	71.1	76.8	84.0
75°	46.6	47.5	48.4	48.4	49.7	51.1	52.9	54.6	57.7	61.3	66.6
77.5°	36.9	36.9	37.8	38.2	39.5	39.1	40.9	42.6	44.9	48.0	52.0
80°	27.1	28.0	28.0	28.0	28.4	28.9	30.6	32.0	33.3	35.5	37.3
82.5°	19.1	19.1	20.0	20.0	20.0	20.9	20.9	21.3	22.2	23.5	24.9
85°	12.0	12.0	12.0	12.4	12.0	12.4	13.3	12.9	13.3	14.2	14.2
87.5°	5.8	5.8	5.8	5.8	5.8	6.2	5.8	6.2	6.7	6.7	6.7
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.5	30.7	30.8	30.9	30.5	29.7	29.0	28.2	27.4	26.3	25.2
97.5°	38.3	38.1	38.0	37.9	37.7	37.2	36.7	36.3	35.8	33.3	30.8
100°	46.4	46.1	45.8	45.6	45.0	43.7	42.5	41.2	40.0	37.4	34.7
102.5°	50.3	49.8	49.3	49.1	48.2	46.5	44.8	43.1	41.4	39.8	38.2
105°	52.1	51.4	50.8	50.5	49.6	47.9	46.2	44.5	42.8	41.2	39.6
107.5°	53.5	52.8	52.2	51.9	51.0	49.3	47.6	45.9	44.2	42.6	41.0
110°	54.2	53.5	52.9	52.6	50.4	48.7	47.0	45.3	43.7	42.1	40.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.2	54.7	54.2	54.0	87.6	154.8	222.0	289.2	356.4	359.0	361.7
115°	79.9	91.2	102.4	108.0	144.1	216.3	288.4	360.6	432.8	428.9	425.0
117.5°	268.3	309.1	350.0	370.4	381.5	403.8	426.1	448.4	470.7	468.1	465.4
120°	470.0	491.0	512.1	522.6	521.7	519.8	517.9	516.1	514.2	511.4	508.6
122.5°	560.2	560.0	559.9	559.8	559.3	558.4	557.5	556.5	555.6	552.5	549.4
125°	598.9	598.4	597.9	597.7	597.2	596.1	595.0	593.9	592.8	589.8	586.9
127.5°	634.6	634.4	634.3	634.2	633.4	631.9	630.3	628.8	627.2	624.8	622.5
130°	667.5	667.7	667.8	667.9	667.0	665.3	663.6	661.8	660.1	658.4	656.7
132.5°	699.0	699.2	699.3	699.4	698.7	697.3	695.9	694.5	693.1	691.4	689.7
135°	729.5	729.8	730.1	730.3	729.5	728.0	726.4	724.9	723.3	721.9	720.5
137.5°	757.9	758.4	758.9	759.1	758.3	756.7	755.2	753.6	752.0	750.4	748.9
140°	784.5	785.2	786.0	786.4	785.7	784.3	782.9	781.5	780.1	778.4	776.7
142.5°	809.8	810.5	811.3	811.7	811.1	809.8	808.6	807.3	806.1	804.1	802.0
145°	832.9	833.6	834.4	834.8	834.3	833.2	832.1	831.0	829.9	827.3	824.6
147.5°	853.6	854.3	854.9	855.2	854.8	854.0	853.3	852.5	851.7	849.0	846.4
150°	872.9	873.6	874.4	874.8	874.3	873.4	872.5	871.5	870.6	868.1	865.6
152.5°	889.6	890.7	891.8	892.4	891.9	891.0	890.0	889.1	888.1	885.8	883.4
155°	904.7	905.9	907.2	907.8	907.3	906.4	905.5	904.5	903.6	901.7	899.9
157.5°	918.7	919.9	921.2	921.8	921.3	920.2	919.1	918.0	916.9	915.5	914.1
160°	930.3	931.4	932.5	933.0	932.5	931.6	930.7	929.7	928.8	927.9	926.9
162.5°	940.8	942.2	943.6	944.3	943.8	942.7	941.6	940.5	939.4	938.6	937.8
165°	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	947.3	946.9
167.5°	956.9	958.3	959.7	960.4	959.9	958.8	957.7	956.6	955.5	955.0	954.6
170°	962.5	963.9	965.3	966.0	965.5	964.4	963.3	962.2	961.1	960.8	960.5
172.5°	966.7	968.1	969.5	970.2	969.7	968.6	967.5	966.4	965.3	965.0	964.7
175°	969.1	970.7	972.2	973.0	972.5	971.4	970.3	969.2	968.1	967.8	967.5
177.5°	970.2	971.6	973.0	973.7	973.2	972.1	971.0	969.9	968.8	968.6	968.5
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	593.0	590.8	589.4	590.3	587.7	581.0	581.0	583.2	580.6	577.9	573.9
5°	609.4	605.0	602.3	601.9	595.7	585.0	582.8	580.6	574.8	568.6	561.9
7.5°	625.4	617.4	613.0	609.9	601.0	587.2	581.4	576.6	567.2	557.9	549.5
10°	638.7	627.2	621.9	617.0	605.4	588.1	578.8	569.9	557.9	545.9	535.2
12.5°	649.4	636.1	629.4	622.3	608.1	585.4	573.9	559.7	547.7	531.7	521.0
15°	667.2	639.6	633.4	626.8	612.1	581.0	566.8	550.8	534.4	513.0	501.5
17.5°	681.4	644.5	644.1	629.9	610.8	579.2	557.5	536.6	518.8	497.5	479.3
20°	689.8	652.1	645.0	630.3	606.3	567.2	544.6	521.5	502.4	476.6	458.4
22.5°	696.9	662.7	644.1	626.3	597.0	563.2	529.9	508.2	481.9	454.0	436.6
25°	699.6	665.0	645.4	625.0	590.3	551.7	513.9	490.4	461.1	435.7	412.2
27.5°	700.0	664.5	640.5	619.2	581.0	536.6	497.9	473.1	440.6	411.3	387.8
30°	695.6	659.6	637.9	614.8	572.1	522.8	478.4	450.9	416.2	386.9	362.5
32.5°	682.3	649.8	632.1	606.8	560.6	503.7	459.7	429.1	392.7	363.8	340.2
35°	660.1	637.9	618.3	594.8	545.5	485.9	441.1	405.1	368.2	340.7	318.5
37.5°	632.5	620.5	602.3	579.2	528.1	470.0	420.2	380.2	343.4	316.7	294.9
40°	595.2	598.3	580.6	559.7	507.7	448.2	393.1	354.9	320.3	295.4	274.1
42.5°	554.8	567.7	557.5	537.5	485.1	424.2	373.1	330.9	297.2	271.4	253.6
45°	511.3	533.5	527.3	512.6	461.5	398.9	344.7	303.8	274.1	249.2	233.6
47.5°	463.7	495.3	495.3	484.6	435.3	373.6	320.3	278.5	249.2	231.4	216.3
50°	415.3	450.9	456.6	449.5	406.0	344.7	290.5	252.7	227.4	210.1	199.0
52.5°	364.7	406.0	416.6	413.1	374.9	317.2	266.1	229.2	206.1	191.0	181.2
55°	316.3	364.2	375.8	377.1	341.6	286.9	239.0	206.5	184.3	174.1	165.7
57.5°	270.5	316.7	329.6	331.8	307.8	259.4	213.7	185.2	165.2	156.8	150.1
60°	231.4	270.1	286.9	291.8	271.0	227.4	190.1	162.6	147.5	139.5	133.3
62.5°	199.4	230.5	248.3	249.6	240.3	199.4	165.7	142.6	129.7	122.6	119.5
65°	168.3	196.3	207.0	212.3	204.8	172.8	143.0	123.9	113.7	107.5	104.4
67.5°	143.5	161.2	170.1	177.2	169.7	145.7	121.7	106.2	98.6	92.4	90.6
70°	117.7	132.4	139.0	146.1	139.5	121.3	103.9	89.7	83.1	78.2	76.0
72.5°	94.2	105.7	111.9	116.4	112.4	97.3	83.1	73.3	68.4	64.9	63.5
75°	74.6	82.6	86.2	89.3	87.5	76.0	67.1	59.1	54.6	51.5	50.6
77.5°	56.9	62.6	66.6	67.5	65.3	57.7	50.2	45.3	41.8	40.0	39.1
80°	40.4	44.0	46.2	47.5	45.3	42.2	36.9	33.3	30.2	28.0	27.5
82.5°	27.1	28.9	30.6	30.2	29.3	26.7	23.5	21.8	20.4	18.7	18.7
85°	15.5	16.0	16.9	17.3	16.9	15.1	13.3	12.4	11.5	10.2	10.2
87.5°	6.7	7.1	7.1	7.6	6.7	6.7	5.8	4.9	4.9	4.4	4.0
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.1	23.0	22.4	25.0	30.1	35.3	40.4	45.6	40.4	35.3	30.1
97.5°	28.3	25.8	24.6	31.0	43.8	56.5	69.3	82.1	69.3	56.5	43.8
100°	32.1	29.4	28.1	38.8	60.1	81.5	102.8	124.2	102.8	81.5	60.1
102.5°	126.5	154.9	169.1	169.3	169.6	169.9	170.2	170.5	170.2	169.9	169.6
105°	170.5	213.0	234.3	232.0	227.3	222.6	218.0	213.3	218.0	222.6	227.3
107.5°	201.8	254.3	280.6	278.7	274.8	270.9	267.0	263.1	267.0	270.9	274.8
110°	257.9	303.0	325.5	323.9	320.6	317.3	314.1	310.8	314.1	317.3	320.6

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	364.3	367.0	368.3	366.9	364.1	361.3	358.5	355.7	358.5	361.3	364.1
115°	421.1	417.2	415.3	414.0	411.3	408.7	406.0	403.4	406.0	408.7	411.3
117.5°	462.8	460.1	458.8	457.2	454.1	451.0	447.9	444.8	447.9	451.0	454.1
120°	505.8	503.0	501.6	500.4	498.1	495.8	493.4	491.1	493.4	495.8	498.1
122.5°	546.3	543.2	541.6	540.4	537.9	535.4	532.9	530.4	532.9	535.4	537.9
125°	583.9	581.0	579.5	578.5	576.4	574.4	572.3	570.3	572.3	574.4	576.4
127.5°	620.1	617.8	616.6	615.5	613.3	611.2	609.0	606.8	609.0	611.2	613.3
130°	655.0	653.3	652.4	651.2	648.7	646.2	643.7	641.2	643.7	646.2	648.7
132.5°	688.0	686.3	685.4	684.4	682.4	680.3	678.3	676.3	678.3	680.3	682.4
135°	719.1	717.7	717.0	715.7	713.2	710.7	708.2	705.7	708.2	710.7	713.2
137.5°	747.3	745.8	745.0	744.1	742.2	740.3	738.5	736.6	738.5	740.3	742.2
140°	775.0	773.3	772.4	771.8	770.5	769.3	768.0	766.8	768.0	769.3	770.5
142.5°	800.0	797.9	796.9	796.4	795.3	794.2	793.1	792.0	793.1	794.2	795.3
145°	822.0	819.3	818.0	818.1	818.2	818.4	818.5	818.7	818.5	818.4	818.2
147.5°	843.7	841.0	839.7	839.9	840.4	840.9	841.3	841.8	841.3	840.9	840.4
150°	863.1	860.6	859.4	859.9	861.0	862.1	863.2	864.3	863.2	862.1	861.0
152.5°	881.1	878.8	877.6	878.2	879.5	880.7	882.0	883.2	882.0	880.7	879.5
155°	898.0	896.1	895.2	895.9	897.3	898.7	900.1	901.5	900.1	898.7	897.3
157.5°	912.7	911.3	910.6	911.2	912.5	913.7	915.0	916.2	915.0	913.7	912.5
160°	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8	927.9	926.9	926.0
162.5°	937.0	936.2	935.8	936.3	937.2	938.2	939.1	940.1	939.1	938.2	937.2
165°	946.4	945.9	945.7	946.2	947.1	948.0	949.0	949.9	949.0	948.0	947.1
167.5°	954.1	953.6	953.4	953.9	954.8	955.7	956.7	957.6	956.7	955.7	954.8
170°	960.2	959.9	959.7	960.2	961.1	962.0	963.0	963.9	963.0	962.0	961.1
172.5°	964.4	964.1	963.9	964.4	965.3	966.2	967.2	968.1	967.2	966.2	965.3
175°	967.2	966.9	966.7	967.2	968.3	969.4	970.5	971.6	970.5	969.4	968.3
177.5°	968.3	968.2	968.1	968.6	969.7	970.8	971.9	973.0	971.9	970.8	969.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	571.7	573.9	573.4	569.0	564.1	560.1	552.6	553.5	550.8	551.2	553.9
5°	557.5	557.5	555.7	549.5	541.5	537.0	528.6	526.4	521.0	520.6	520.1
7.5°	542.4	540.1	537.9	529.0	519.3	512.1	500.6	497.9	492.6	489.1	487.3
10°	524.6	521.5	517.0	506.8	494.8	485.9	473.9	470.4	460.2	455.7	453.1
12.5°	505.0	503.3	496.2	487.7	468.2	458.4	441.1	444.6	434.4	425.5	424.2
15°	485.5	478.8	474.8	461.1	437.5	433.1	419.3	412.2	402.9	395.8	395.8
17.5°	466.4	456.2	447.3	432.6	415.3	402.9	392.7	389.1	377.6	370.5	369.1
20°	441.1	429.5	427.3	406.4	394.4	380.7	370.9	362.0	353.6	350.5	348.2
22.5°	417.1	403.8	400.2	382.4	370.5	356.7	346.9	340.7	334.5	332.3	328.3
25°	391.3	383.3	378.0	358.9	345.6	332.7	326.0	321.6	315.8	315.4	312.7
27.5°	366.5	358.9	353.6	335.4	325.6	313.6	308.3	303.4	300.3	298.9	297.6
30°	345.1	336.7	330.5	317.2	305.2	295.4	290.9	287.8	286.1	283.8	283.4
32.5°	321.6	316.7	308.3	298.1	288.7	279.4	276.7	274.5	271.8	271.0	270.5
35°	301.6	294.9	289.6	278.1	274.1	266.1	263.0	261.2	257.6	256.7	255.9
37.5°	282.1	275.8	270.1	263.0	255.4	251.0	249.2	246.5	244.7	245.2	244.3
40°	262.5	257.6	253.2	245.6	241.2	239.0	235.4	232.8	231.9	232.3	231.9
42.5°	243.4	239.0	236.3	230.5	226.1	223.9	221.7	219.0	220.3	220.3	221.7
45°	226.1	222.1	220.3	215.9	213.2	209.7	207.4	207.0	208.8	208.3	208.3
47.5°	208.3	207.0	204.8	200.8	197.2	195.0	194.6	194.6	196.3	197.2	196.8
50°	194.6	191.9	189.2	186.1	183.4	182.6	181.2	182.1	183.9	183.9	184.8
52.5°	177.2	175.5	174.6	171.9	170.1	170.1	170.1	170.6	171.9	173.2	172.8
55°	162.1	160.8	159.9	158.6	156.4	156.8	156.4	157.2	158.6	159.9	160.8
57.5°	146.1	145.7	144.8	142.6	142.6	142.1	143.5	143.9	146.1	147.0	148.4
60°	131.9	130.6	130.6	128.8	128.8	128.8	130.1	131.5	133.3	133.7	134.6
62.5°	116.8	116.8	116.4	115.0	115.0	116.4	116.8	118.6	119.5	119.5	120.8
65°	102.6	102.2	101.7	102.2	102.6	102.6	103.9	104.8	105.7	106.2	106.6
67.5°	88.4	87.9	88.8	88.4	89.3	91.1	90.6	91.9	93.3	93.3	93.7
70°	75.1	76.0	75.5	76.4	76.0	76.8	78.2	78.6	78.6	79.1	80.4
72.5°	62.6	62.6	62.6	62.2	62.6	63.5	64.4	64.9	65.7	66.2	67.5
75°	50.6	50.6	49.7	50.6	50.6	51.5	52.4	52.4	52.4	53.3	54.6
77.5°	38.2	38.6	38.2	39.1	39.1	39.5	40.4	40.0	40.9	41.3	41.8
80°	28.0	27.5	27.5	27.5	28.0	28.0	28.9	29.3	29.3	30.6	29.8
82.5°	17.8	18.2	17.8	18.2	18.2	18.7	18.2	18.7	19.1	20.0	19.5
85°	10.2	9.8	9.8	10.2	9.8	9.8	10.2	9.8	10.2	9.8	10.2
87.5°	4.0	3.6	3.6	3.6	3.6	3.1	3.1	2.7	2.7	2.7	2.2
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	23.0	24.1	25.2	26.3	27.4	28.2	29.0	29.7	30.5
97.5°	31.0	24.6	25.8	28.3	30.8	33.3	35.8	36.3	36.7	37.2	37.7
100°	38.8	28.1	29.4	32.1	34.7	37.4	40.0	41.2	42.5	43.7	45.0
102.5°	169.3	169.1	154.9	126.5	98.2	69.8	41.4	43.1	44.8	46.5	48.2
105°	232.0	234.3	213.0	170.5	127.9	85.4	42.8	44.5	46.2	47.9	49.6
107.5°	278.7	280.6	254.3	201.8	149.3	96.7	44.2	45.9	47.6	49.3	51.0
110°	323.9	325.5	303.0	257.9	212.9	167.8	122.8	107.2	91.6	76.0	60.4

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	366.9	368.3	367.0	364.3	361.7	359.0	356.4	289.2	222.0	154.8	87.6
115°	414.0	415.3	417.2	421.1	425.0	428.9	432.8	360.6	288.4	216.3	144.1
117.5°	457.2	458.8	460.1	462.8	465.4	468.1	470.7	448.4	426.1	403.8	381.5
120°	500.4	501.6	503.0	505.8	508.6	511.4	514.2	516.1	517.9	519.8	521.7
122.5°	540.4	541.6	543.2	546.3	549.4	552.5	555.6	556.5	557.5	558.4	559.3
125°	578.5	579.5	581.0	583.9	586.9	589.8	592.8	593.9	595.0	596.1	597.2
127.5°	615.5	616.6	617.8	620.1	622.5	624.8	627.2	628.8	630.3	631.9	633.4
130°	651.2	652.4	653.3	655.0	656.7	658.4	660.1	661.8	663.6	665.3	667.0
132.5°	684.4	685.4	686.3	688.0	689.7	691.4	693.1	694.5	695.9	697.3	698.7
135°	715.7	717.0	717.7	719.1	720.5	721.9	723.3	724.9	726.4	728.0	729.5
137.5°	744.1	745.0	745.8	747.3	748.9	750.4	752.0	753.6	755.2	756.7	758.3
140°	771.8	772.4	773.3	775.0	776.7	778.4	780.1	781.5	782.9	784.3	785.7
142.5°	796.4	796.9	797.9	800.0	802.0	804.1	806.1	807.3	808.6	809.8	811.1
145°	818.1	818.0	819.3	822.0	824.6	827.3	829.9	831.0	832.1	833.2	834.3
147.5°	839.9	839.7	841.0	843.7	846.4	849.0	851.7	852.5	853.3	854.0	854.8
150°	859.9	859.4	860.6	863.1	865.6	868.1	870.6	871.5	872.5	873.4	874.3
152.5°	878.2	877.6	878.8	881.1	883.4	885.8	888.1	889.1	890.0	891.0	891.9
155°	895.9	895.2	896.1	898.0	899.9	901.7	903.6	904.5	905.5	906.4	907.3
157.5°	911.2	910.6	911.3	912.7	914.1	915.5	916.9	918.0	919.1	920.2	921.3
160°	925.1	924.6	925.1	926.0	926.9	927.9	928.8	929.7	930.7	931.6	932.5
162.5°	936.3	935.8	936.2	937.0	937.8	938.6	939.4	940.5	941.6	942.7	943.8
165°	946.2	945.7	945.9	946.4	946.9	947.3	947.8	948.9	950.0	951.1	952.2
167.5°	953.9	953.4	953.6	954.1	954.6	955.0	955.5	956.6	957.7	958.8	959.9
170°	960.2	959.7	959.9	960.2	960.5	960.8	961.1	962.2	963.3	964.4	965.5
172.5°	964.4	963.9	964.1	964.4	964.7	965.0	965.3	966.4	967.5	968.6	969.7
175°	967.2	966.7	966.9	967.2	967.5	967.8	968.1	969.2	970.3	971.4	972.5
177.5°	968.6	968.1	968.2	968.3	968.5	968.6	968.8	969.9	971.0	972.1	973.2
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	550.8	552.1	549.0	548.1	549.0	545.9	546.8	547.7	547.7	549.0	549.9
5°	518.8	517.0	513.9	513.0	512.1	513.5	512.6	513.9	514.4	517.5	517.9
7.5°	487.3	484.6	481.9	479.3	478.4	476.2	478.4	478.4	481.5	480.6	482.8
10°	450.0	449.5	446.0	444.6	442.9	439.3	444.2	442.9	445.1	449.1	450.0
12.5°	422.4	417.5	419.8	413.5	415.8	412.2	412.7	412.7	416.2	416.6	415.8
15°	396.2	392.2	386.4	383.8	382.4	380.7	386.4	386.9	384.2	390.4	388.2
17.5°	369.6	369.6	364.2	362.9	359.3	361.1	360.2	360.7	359.8	364.2	366.5
20°	346.5	344.2	342.5	342.9	338.5	337.6	336.7	337.6	340.7	343.8	344.7
22.5°	327.8	326.5	322.0	322.9	319.4	320.7	319.8	322.0	322.5	322.5	325.6
25°	310.0	308.3	308.7	306.9	305.6	305.6	304.3	305.6	307.4	308.3	308.7
27.5°	296.7	295.4	293.2	291.8	292.7	290.5	292.3	293.6	293.6	292.7	293.6
30°	280.7	281.6	281.6	277.2	279.0	278.1	279.4	280.3	280.3	280.7	279.8
32.5°	270.1	267.4	267.0	266.5	266.5	264.7	264.7	266.1	266.5	267.0	268.3
35°	255.9	255.9	253.6	255.0	253.2	253.6	253.2	253.6	254.5	253.2	254.5
37.5°	243.0	243.4	242.5	243.4	243.9	243.0	242.1	243.9	243.0	243.0	242.1
40°	231.9	231.4	231.9	231.9	231.9	232.3	231.4	231.4	231.4	230.5	229.6
42.5°	222.5	219.9	220.8	221.2	219.9	219.9	220.3	219.9	221.2	218.5	218.5
45°	209.2	208.3	208.8	208.8	209.7	208.3	209.2	209.7	208.3	207.9	207.0
47.5°	197.2	198.1	197.2	198.1	198.1	199.0	197.2	197.7	198.1	196.3	195.0
50°	185.2	185.2	186.6	186.1	186.6	185.7	185.7	185.2	185.7	184.8	183.4
52.5°	174.1	172.8	175.0	174.6	174.1	173.7	173.2	173.7	172.8	171.9	171.9
55°	160.4	160.4	161.7	162.1	162.1	161.2	160.4	160.8	160.4	159.9	159.5
57.5°	149.2	147.5	148.4	148.8	148.8	147.5	148.4	147.5	147.5	147.9	146.6
60°	135.0	135.0	134.1	135.5	135.5	134.6	134.6	135.0	134.1	133.7	133.3
62.5°	119.9	120.4	121.7	122.2	122.6	121.7	120.8	121.3	121.3	119.9	120.4
65°	107.0	107.9	109.7	109.3	108.4	108.8	107.9	108.4	107.0	107.5	106.2
67.5°	94.6	94.2	94.6	94.6	95.5	95.1	94.2	94.2	93.7	95.1	93.7
70°	81.3	81.3	81.3	81.3	81.7	82.2	81.3	80.4	80.8	80.0	79.5
72.5°	67.5	68.0	67.5	68.4	67.1	68.0	68.0	67.5	67.1	67.1	67.1
75°	54.6	55.5	54.2	54.6	54.2	55.1	54.6	54.6	53.7	53.3	53.7
77.5°	41.8	42.2	41.3	41.8	41.3	41.8	41.8	41.3	41.3	41.3	41.3
80°	29.8	30.2	29.8	29.3	28.9	29.8	28.9	29.3	29.8	29.3	30.2
82.5°	19.1	19.1	18.7	19.1	18.2	18.2	18.7	18.7	18.2	19.1	18.2
85°	9.3	9.3	10.2	9.3	8.9	8.9	8.9	9.3	8.9	9.8	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.9	30.8	30.7	30.5	30.4	30.2	30.4	30.5	30.7	30.8	30.9
97.5°	37.9	38.0	38.1	38.3	38.4	38.6	38.4	38.3	38.1	38.0	37.9
100°	45.6	45.8	46.1	46.4	46.7	47.0	46.7	46.4	46.1	45.8	45.6
102.5°	49.1	49.3	49.8	50.3	50.7	51.2	50.7	50.3	49.8	49.3	49.1
105°	50.5	50.8	51.4	52.1	52.7	53.3	52.7	52.1	51.4	50.8	50.5
107.5°	51.9	52.2	52.8	53.5	54.1	54.7	54.1	53.5	52.8	52.2	51.9
110°	52.6	52.9	53.5	54.2	54.8	55.4	54.8	54.2	53.5	52.9	52.6

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	54.0	54.2	54.7	55.2	55.6	56.1	55.6	55.2	54.7	54.2	54.0
115°	108.0	102.4	91.2	79.9	68.7	57.5	68.7	79.9	91.2	102.4	108.0
117.5°	370.4	350.0	309.1	268.3	227.4	186.6	227.4	268.3	309.1	350.0	370.4
120°	522.6	512.1	491.0	470.0	448.9	427.9	448.9	470.0	491.0	512.1	522.6
122.5°	559.8	559.9	560.0	560.2	560.3	560.5	560.3	560.2	560.0	559.9	559.8
125°	597.7	597.9	598.4	598.9	599.3	599.8	599.3	598.9	598.4	597.9	597.7
127.5°	634.2	634.3	634.4	634.6	634.7	634.9	634.7	634.6	634.4	634.3	634.2
130°	667.9	667.8	667.7	667.5	667.4	667.2	667.4	667.5	667.7	667.8	667.9
132.5°	699.4	699.3	699.2	699.0	698.9	698.7	698.9	699.0	699.2	699.3	699.4
135°	730.3	730.1	729.8	729.5	729.2	728.9	729.2	729.5	729.8	730.1	730.3
137.5°	759.1	758.9	758.4	757.9	757.5	757.0	757.5	757.9	758.4	758.9	759.1
140°	786.4	786.0	785.2	784.5	783.7	782.9	783.7	784.5	785.2	786.0	786.4
142.5°	811.7	811.3	810.5	809.8	809.0	808.2	809.0	809.8	810.5	811.3	811.7
145°	834.8	834.4	833.6	832.9	832.1	831.3	832.1	832.9	833.6	834.4	834.8
147.5°	855.2	854.9	854.3	853.6	853.0	852.4	853.0	853.6	854.3	854.9	855.2
150°	874.8	874.4	873.6	872.9	872.1	871.3	872.1	872.9	873.6	874.4	874.8
152.5°	892.4	891.8	890.7	889.6	888.5	887.4	888.5	889.6	890.7	891.8	892.4
155°	907.8	907.2	905.9	904.7	903.4	902.2	903.4	904.7	905.9	907.2	907.8
157.5°	921.8	921.2	919.9	918.7	917.4	916.2	917.4	918.7	919.9	921.2	921.8
160°	933.0	932.5	931.4	930.3	929.2	928.1	929.2	930.3	931.4	932.5	933.0
162.5°	944.3	943.6	942.2	940.8	939.4	938.0	939.4	940.8	942.2	943.6	944.3
165°	952.7	952.2	951.1	950.0	948.9	947.8	948.9	950.0	951.1	952.2	952.7
167.5°	960.4	959.7	958.3	956.9	955.5	954.1	955.5	956.9	958.3	959.7	960.4
170°	966.0	965.3	963.9	962.5	961.1	959.7	961.1	962.5	963.9	965.3	966.0
172.5°	970.2	969.5	968.1	966.7	965.3	963.9	965.3	966.7	968.1	969.5	970.2
175°	973.0	972.2	970.7	969.1	967.6	966.0	967.6	969.1	970.7	972.2	973.0
177.5°	973.7	973.0	971.6	970.2	968.8	967.4	968.8	970.2	971.6	973.0	973.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	548.6	552.1	550.8	545.9	551.7	551.7	555.7	555.7	560.6	562.3	565.0
5°	517.5	520.1	522.4	520.1	524.1	530.4	533.9	537.0	543.7	546.4	550.3
7.5°	484.2	489.1	491.3	491.3	497.9	505.0	512.1	516.6	525.9	529.5	533.5
10°	451.7	457.5	462.0	461.5	472.6	477.1	485.9	496.2	505.5	510.8	516.6
12.5°	417.5	420.6	426.9	435.7	438.4	446.4	456.6	469.5	486.4	491.3	499.7
15°	389.1	397.5	402.4	406.4	412.7	420.2	431.3	443.7	460.6	471.3	480.2
17.5°	365.1	376.2	379.3	378.4	386.4	398.0	410.9	420.2	435.3	448.2	456.6
20°	345.6	350.0	355.4	357.6	363.8	376.2	388.7	399.3	411.8	422.0	431.8
22.5°	326.0	329.6	334.0	338.0	342.9	350.0	362.0	375.3	387.3	397.1	408.2
25°	310.0	312.3	316.3	319.4	324.7	329.6	338.0	352.7	366.9	372.7	382.4
27.5°	294.5	296.3	298.9	302.5	305.2	310.0	317.6	329.6	344.2	350.0	363.3
30°	280.7	282.1	284.7	286.5	287.8	293.6	299.4	308.7	319.8	327.8	337.6
32.5°	267.8	269.2	271.8	272.3	274.1	277.2	282.5	290.9	300.7	307.4	315.8
35°	253.6	254.5	257.2	258.1	259.4	262.1	266.1	272.3	281.2	286.1	293.6
37.5°	242.5	242.1	243.9	245.2	247.0	248.3	249.6	255.9	262.5	267.0	272.7
40°	230.5	229.6	230.1	231.9	232.8	234.5	234.5	240.8	245.2	248.7	253.2
42.5°	218.5	218.1	217.2	218.1	219.0	219.4	219.9	224.3	228.8	231.9	236.8
45°	206.5	206.1	205.2	205.7	205.7	206.5	207.9	209.7	212.8	215.4	218.1
47.5°	195.4	194.6	193.2	192.8	193.7	193.7	193.7	195.4	198.6	199.4	202.1
50°	183.9	182.6	180.8	179.9	179.9	179.5	180.3	180.8	183.4	184.3	186.6
52.5°	171.5	170.6	168.8	167.0	167.5	166.6	167.0	167.5	168.3	169.7	171.0
55°	159.0	157.2	155.9	155.5	154.1	154.1	152.8	154.6	154.1	154.6	156.4
57.5°	147.0	145.2	143.0	142.1	140.8	140.4	139.5	139.0	139.5	140.8	142.1
60°	132.8	131.9	130.6	129.3	128.4	127.0	126.1	126.1	125.7	125.7	126.1
62.5°	119.0	118.6	116.8	116.4	115.5	114.6	113.3	112.4	112.4	113.3	113.7
65°	105.7	105.3	103.9	103.5	101.3	100.4	99.9	99.5	98.6	98.6	98.6
67.5°	93.3	91.9	91.9	89.7	87.9	87.1	86.2	85.7	85.7	85.7	86.2
70°	79.5	79.5	78.2	76.8	75.1	75.5	74.2	72.8	72.8	72.0	72.4
72.5°	66.2	65.7	64.4	64.0	62.6	61.3	60.4	61.3	60.0	59.5	60.0
75°	53.3	52.9	52.0	51.1	51.5	50.2	48.9	48.4	48.4	47.5	47.5
77.5°	40.9	41.8	40.0	39.5	38.6	37.8	37.3	36.9	36.9	36.9	37.8
80°	28.4	28.9	28.9	28.0	28.4	27.1	27.1	27.1	25.8	26.2	26.7
82.5°	18.2	18.2	17.8	18.2	17.8	17.8	17.3	17.3	16.9	16.9	17.3
85°	10.2	9.8	9.3	10.2	9.8	9.8	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.6	3.6	3.6
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.5	29.7	29.0	28.2	27.4	26.3	25.2	24.1	23.0	22.4	25.0
97.5°	37.7	37.2	36.7	36.3	35.8	33.3	30.8	28.3	25.8	24.6	31.0
100°	45.0	43.7	42.5	41.2	40.0	37.4	34.7	32.1	29.4	28.1	38.8
102.5°	48.2	46.5	44.8	43.1	41.4	69.8	98.2	126.5	154.9	169.1	169.3
105°	49.6	47.9	46.2	44.5	42.8	85.4	127.9	170.5	213.0	234.3	232.0
107.5°	51.0	49.3	47.6	45.9	44.2	96.7	149.3	201.8	254.3	280.6	278.7
110°	60.4	76.0	91.6	107.2	122.8	167.8	212.9	257.9	303.0	325.5	323.9

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.6	154.8	222.0	289.2	356.4	359.0	361.7	364.3	367.0	368.3	366.9
115°	144.1	216.3	288.4	360.6	432.8	428.9	425.0	421.1	417.2	415.3	414.0
117.5°	381.5	403.8	426.1	448.4	470.7	468.1	465.4	462.8	460.1	458.8	457.2
120°	521.7	519.8	517.9	516.1	514.2	511.4	508.6	505.8	503.0	501.6	500.4
122.5°	559.3	558.4	557.5	556.5	555.6	552.5	549.4	546.3	543.2	541.6	540.4
125°	597.2	596.1	595.0	593.9	592.8	589.8	586.9	583.9	581.0	579.5	578.5
127.5°	633.4	631.9	630.3	628.8	627.2	624.8	622.5	620.1	617.8	616.6	615.5
130°	667.0	665.3	663.6	661.8	660.1	658.4	656.7	655.0	653.3	652.4	651.2
132.5°	698.7	697.3	695.9	694.5	693.1	691.4	689.7	688.0	686.3	685.4	684.4
135°	729.5	728.0	726.4	724.9	723.3	721.9	720.5	719.1	717.7	717.0	715.7
137.5°	758.3	756.7	755.2	753.6	752.0	750.4	748.9	747.3	745.8	745.0	744.1
140°	785.7	784.3	782.9	781.5	780.1	778.4	776.7	775.0	773.3	772.4	771.8
142.5°	811.1	809.8	808.6	807.3	806.1	804.1	802.0	800.0	797.9	796.9	796.4
145°	834.3	833.2	832.1	831.0	829.9	827.3	824.6	822.0	819.3	818.0	818.1
147.5°	854.8	854.0	853.3	852.5	851.7	849.0	846.4	843.7	841.0	839.7	839.9
150°	874.3	873.4	872.5	871.5	870.6	868.1	865.6	863.1	860.6	859.4	859.9
152.5°	891.9	891.0	890.0	889.1	888.1	885.8	883.4	881.1	878.8	877.6	878.2
155°	907.3	906.4	905.5	904.5	903.6	901.7	899.9	898.0	896.1	895.2	895.9
157.5°	921.3	920.2	919.1	918.0	916.9	915.5	914.1	912.7	911.3	910.6	911.2
160°	932.5	931.6	930.7	929.7	928.8	927.9	926.9	926.0	925.1	924.6	925.1
162.5°	943.8	942.7	941.6	940.5	939.4	938.6	937.8	937.0	936.2	935.8	936.3
165°	952.2	951.1	950.0	948.9	947.8	947.3	946.9	946.4	945.9	945.7	946.2
167.5°	959.9	958.8	957.7	956.6	955.5	955.0	954.6	954.1	953.6	953.4	953.9
170°	965.5	964.4	963.3	962.2	961.1	960.8	960.5	960.2	959.9	959.7	960.2
172.5°	969.7	968.6	967.5	966.4	965.3	965.0	964.7	964.4	964.1	963.9	964.4
175°	972.5	971.4	970.3	969.2	968.1	967.8	967.5	967.2	966.9	966.7	967.2
177.5°	973.2	972.1	971.0	969.9	968.8	968.6	968.5	968.3	968.2	968.1	968.6
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	577.9	577.9	577.9	577.9
2.5°	567.2	567.2	573.9	581.0
5°	554.8	557.9	568.6	578.3
7.5°	542.8	548.1	561.5	573.9
10°	528.1	535.2	551.7	566.3
12.5°	513.9	520.6	539.7	556.1
15°	493.9	502.4	522.8	543.2
17.5°	473.9	482.4	507.3	531.2
20°	450.4	461.5	489.5	521.5
22.5°	428.6	442.4	473.5	499.3
25°	404.7	426.0	454.8	488.2
27.5°	383.3	404.7	434.0	467.7
30°	359.3	381.1	411.3	442.4
32.5°	336.3	356.2	385.6	423.8
35°	312.3	331.4	359.8	398.4
37.5°	290.5	309.2	340.2	375.8
40°	269.2	288.7	315.4	350.9
42.5°	249.2	266.5	290.5	326.0
45°	231.0	243.4	265.6	298.9
47.5°	211.9	223.0	243.4	276.7
50°	194.1	203.4	221.2	252.3
52.5°	176.8	184.8	201.2	226.1
55°	161.2	168.8	180.8	205.2
57.5°	145.2	151.0	162.6	182.1
60°	129.7	135.0	144.4	160.4
62.5°	114.2	118.6	127.5	140.4
65°	100.4	103.9	110.6	121.7
67.5°	87.1	89.3	94.6	103.5
70°	74.2	76.0	80.4	87.5
72.5°	60.4	62.2	67.1	72.0
75°	48.9	49.3	52.9	56.9
77.5°	38.2	37.8	40.4	43.5
80°	26.2	27.5	29.8	31.1
82.5°	17.8	18.2	19.1	20.0
85°	9.8	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.3	40.4	45.6
97.5°	43.8	56.5	69.3	82.1
100°	60.1	81.5	102.8	124.2
102.5°	169.6	169.9	170.2	170.5
105°	227.3	222.6	218.0	213.3
107.5°	274.8	270.9	267.0	263.1
110°	320.6	317.3	314.1	310.8



TEST NUMBER: P1008041

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	364.1	361.3	358.5	355.7
115°	411.3	408.7	406.0	403.4
117.5°	454.1	451.0	447.9	444.8
120°	498.1	495.8	493.4	491.1
122.5°	537.9	535.4	532.9	530.4
125°	576.4	574.4	572.3	570.3
127.5°	613.3	611.2	609.0	606.8
130°	648.7	646.2	643.7	641.2
132.5°	682.4	680.3	678.3	676.3
135°	713.2	710.7	708.2	705.7
137.5°	742.2	740.3	738.5	736.6
140°	770.5	769.3	768.0	766.8
142.5°	795.3	794.2	793.1	792.0
145°	818.2	818.4	818.5	818.7
147.5°	840.4	840.9	841.3	841.8
150°	861.0	862.1	863.2	864.3
152.5°	879.5	880.7	882.0	883.2
155°	897.3	898.7	900.1	901.5
157.5°	912.5	913.7	915.0	916.2
160°	926.0	926.9	927.9	928.8
162.5°	937.2	938.2	939.1	940.1
165°	947.1	948.0	949.0	949.9
167.5°	954.8	955.7	956.7	957.6
170°	961.1	962.0	963.0	963.9
172.5°	965.3	966.2	967.2	968.1
175°	968.3	969.4	970.5	971.6
177.5°	969.7	970.8	971.9	973.0
180°	969.5	969.5	969.5	969.5

(END OF REPORT)