

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008115

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008115
REPORT IS A COMBINATION OF REPORTS P984308 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4967.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15318	15318	15318	15318
5°	15354	16332	15413	12993
10°	15176	17829	15272	10713
15°	14809	18805	15014	9023
20°	14577	17657	14577	7843
25°	14112	15170	14178	7013
30°	13348	11925	13604	6353
35°	12671	8246	12882	5813
40°	11892	6226	12028	5382
45°	10933	5116	11112	4916
50°	10103	4491	10120	4501
55°	9156	3826	9217	4049
60°	8148	3196	8260	3535
65°	7245	2599	7376	3018
70°	6344	2040	6505	2434
75°	5326	1481	5533	1765
80°	4160	938	4455	1047
85°	2726	473	2938	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15834 cd/sqm

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	1.9
10°-20°	268.3	5.4
20°-30°	389.3	7.8
30°-40°	410.4	8.3
40°-50°	363.2	7.3
50°-60°	290.0	5.8
60°-70°	197.0	4.0
70°-80°	100.8	2.0
80°-90°	25.5	0.5
90°-100°	31.8	0.6
100°-110°	118.7	2.4
110°-120°	314.7	6.3
120°-130°	522.0	10.5
130°-140°	554.5	11.2
140°-150°	515.4	10.4
150°-160°	414.3	8.3
160°-170°	267.0	5.4
170°-180°	91.9	1.8
0°-30°	749.8	15.1
0°-40°	1160.2	23.4
0°-60°	1813.4	36.5
0°-90°	2136.7	43.0
90°-120°	465.3	9.4
90°-150°	2057.1	41.4
90°-180°	2830.0	57.0
0°-180°	4967.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	968	968	968	968	968	
5°	968	1081	972	860	968	92
15°	910	1328	922	637	910	257
25°	817	1107	821	512	817	374
35°	667	602	678	425	667	417
45°	501	363	509	349	501	388
55°	344	255	346	270	344	307
65°	204	157	208	182	204	203
75°	95	77	99	92	95	102
85°	19	20	21	15	19	23
90°	1	19	1	19	1	4
95°	45	30	45	30	45	54
105°	212	53	212	53	212	227
115°	402	57	402	57	402	395
125°	568	597	568	597	568	507
135°	703	726	703	726	703	543
145°	815	828	815	828	815	510
155°	898	898	898	898	898	414
165°	946	944	946	944	946	267
175°	968	962	968	962	968	92
180°	965	965	965	965	965	

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	972.9	975.1	978.8	979.6	987.0	993.0	999.7	999.7	1001.9	1001.2	995.2
5°	968.4	975.1	984.8	993.0	1006.4	1012.3	1021.2	1027.9	1033.9	1038.3	1037.6
7.5°	961.0	972.9	987.0	1002.6	1020.5	1030.9	1043.5	1055.4	1063.6	1071.1	1076.3
10°	948.3	968.4	987.8	1008.6	1031.6	1045.8	1060.7	1076.3	1088.9	1103.1	1116.4
12.5°	931.2	960.2	984.0	1011.6	1039.8	1055.4	1079.3	1091.2	1115.7	1151.4	1161.1
15°	909.7	949.1	971.4	1006.4	1043.5	1056.2	1088.9	1108.3	1158.8	1181.2	1207.9
17.5°	889.6	933.5	963.2	1003.4	1039.8	1064.4	1096.4	1135.8	1178.2	1210.2	1239.9
20°	873.2	915.6	951.3	995.9	1042.1	1073.3	1106.8	1154.4	1200.5	1233.2	1256.3
22.5°	836.0	890.3	932.0	981.8	1037.6	1080.7	1112.7	1164.8	1214.6	1234.7	1254.8
25°	817.4	864.3	912.6	969.2	1034.6	1085.9	1113.5	1171.5	1215.4	1222.8	1227.3
27.5°	783.2	836.0	892.6	957.3	1033.9	1077.0	1112.0	1164.8	1199.7	1194.5	1181.2
30°	740.8	805.5	868.0	937.9	1023.5	1070.3	1103.1	1151.4	1169.3	1142.5	1118.7
32.5°	709.6	770.6	839.7	920.8	1011.6	1056.2	1088.2	1126.1	1129.8	1081.5	1041.3
35°	667.2	734.9	813.0	898.5	991.5	1031.6	1061.4	1084.5	1066.6	998.9	951.3
37.5°	629.3	696.2	779.5	866.5	964.0	1003.4	1027.2	1030.9	987.0	927.5	857.6
40°	587.6	656.8	743.8	835.3	933.5	967.7	982.6	971.4	908.2	839.0	757.9
42.5°	545.9	614.4	708.1	801.8	894.8	923.8	929.7	899.3	821.9	740.8	647.1
45°	500.6	572.0	665.7	760.2	850.2	866.5	867.3	823.4	731.9	647.1	560.1
47.5°	463.4	529.6	622.6	717.0	792.9	804.0	799.6	749.0	649.3	554.1	478.3
50°	422.5	485.7	577.9	670.9	735.6	738.6	727.4	655.3	557.8	470.8	410.6
52.5°	378.6	442.6	527.4	616.6	674.6	670.2	648.6	571.2	479.7	407.6	361.5
55°	343.6	400.2	479.7	566.8	607.7	595.0	571.2	492.4	420.2	359.3	319.1
57.5°	305.0	354.8	432.9	508.8	532.6	520.7	496.9	423.2	356.3	310.2	283.4
60°	268.5	313.9	382.3	445.5	464.1	451.5	424.0	357.8	309.4	270.7	250.7
62.5°	235.0	274.5	331.7	389.8	397.2	384.5	360.7	307.2	265.5	235.0	220.2
65°	203.8	241.0	287.1	331.0	337.7	324.3	299.8	261.1	226.1	206.8	192.6
67.5°	173.3	203.1	244.0	275.9	279.7	267.0	246.9	215.7	194.1	173.3	162.9
70°	146.5	168.8	200.8	226.9	228.3	216.4	206.0	177.8	161.4	146.5	138.3
72.5°	120.5	136.1	160.7	180.0	180.7	173.3	163.6	145.8	131.7	121.2	113.1
75°	95.2	108.6	123.5	140.6	139.8	133.9	126.4	115.3	103.4	96.7	93.0
77.5°	72.9	81.1	93.0	104.1	104.1	101.2	96.7	88.5	81.1	74.4	70.7
80°	52.1	57.3	66.9	70.7	72.1	71.4	67.7	61.7	58.8	53.6	52.1
82.5°	33.5	37.2	41.7	45.4	47.6	46.1	45.4	42.4	37.9	36.4	35.0
85°	19.3	20.8	23.1	25.3	26.0	25.3	26.8	24.5	22.3	22.3	21.6
87.5°	8.2	8.9	10.4	10.4	11.2	11.2	10.4	11.2	11.2	10.4	9.7
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.4	40.3	35.2	30.1	25.0	22.4	22.9	24.0	25.1	26.1	27.2
97.5°	81.7	69.0	56.3	43.6	30.9	24.5	25.7	28.2	30.7	33.1	35.6
100°	123.6	102.3	81.1	59.8	38.5	27.9	29.2	31.9	34.5	37.2	39.8
102.5°	169.8	169.5	169.2	168.9	168.6	168.4	154.3	126.0	97.7	69.5	41.2
105°	212.4	217.0	221.7	226.3	231.0	233.3	212.1	169.7	127.4	85.0	42.6
107.5°	262.0	265.9	269.7	273.6	277.5	279.4	253.2	200.9	148.6	96.3	44.0
110°	309.5	312.7	316.0	319.2	322.5	324.1	301.7	256.8	212.0	167.1	122.3

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	354.2	357.0	359.8	362.6	365.4	366.8	365.5	362.8	360.2	357.5	354.9
115°	401.7	404.3	407.0	409.6	412.3	413.6	415.5	419.4	423.3	427.1	431.0
117.5°	442.9	446.0	449.1	452.2	455.3	456.9	458.2	460.8	463.5	466.1	468.7
120°	489.0	491.3	493.7	496.0	498.3	499.5	500.9	503.7	506.5	509.3	512.1
122.5°	528.1	530.6	533.1	535.6	538.1	539.3	540.9	544.0	547.1	550.2	553.3
125°	567.9	569.9	571.9	574.0	576.0	577.0	578.5	581.4	584.4	587.3	590.3
127.5°	604.3	606.5	608.6	610.8	612.9	614.0	615.2	617.5	619.8	622.2	624.5
130°	638.5	641.0	643.5	646.0	648.5	649.7	650.6	652.3	654.0	655.7	657.4
132.5°	673.4	675.4	677.4	679.5	681.5	682.5	683.4	685.1	686.8	688.5	690.2
135°	702.8	705.3	707.7	710.2	712.7	713.9	714.6	716.0	717.4	718.8	720.2
137.5°	733.5	735.4	737.2	739.1	741.0	741.9	742.7	744.2	745.8	747.3	748.9
140°	763.5	764.7	766.0	767.2	768.5	769.1	770.0	771.7	773.4	775.1	776.8
142.5°	788.7	789.8	790.9	792.0	793.1	793.6	794.6	796.6	798.7	800.7	802.7
145°	815.2	815.0	814.9	814.7	814.6	814.5	815.8	818.5	821.1	823.8	826.4
147.5°	838.3	837.8	837.4	836.9	836.4	836.2	837.5	840.2	842.8	845.5	848.1
150°	860.6	859.5	858.5	857.4	856.3	855.8	857.0	859.5	862.0	864.4	866.9
152.5°	879.5	878.3	877.0	875.8	874.5	873.9	875.1	877.4	879.7	882.1	884.4
155°	897.7	896.3	894.9	893.5	892.1	891.4	892.3	894.2	896.1	897.9	899.8
157.5°	912.3	911.1	909.8	908.6	907.3	906.7	907.4	908.8	910.2	911.6	913.0
160°	924.9	924.0	923.0	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9
162.5°	936.1	935.2	934.2	933.3	932.4	931.9	932.3	933.1	933.8	934.6	935.4
165°	945.9	945.0	944.0	943.1	942.2	941.7	941.9	942.4	942.9	943.3	943.8
167.5°	953.6	952.7	951.7	950.8	949.9	949.4	949.6	950.1	950.6	951.0	951.5
170°	959.8	958.9	957.9	957.0	956.1	955.6	955.8	956.1	956.4	956.7	957.0
172.5°	964.0	963.1	962.1	961.2	960.3	959.8	960.0	960.3	960.6	960.9	961.2
175°	967.5	966.4	965.3	964.2	963.1	962.6	962.8	963.1	963.4	963.7	964.0
177.5°	968.9	967.8	966.7	965.6	964.5	964.0	964.1	964.2	964.4	964.5	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1005.6	1006.4	1007.8	1015.3	1019.0	1019.7	1016.8	1023.5	1025.7	1023.5	1022.0
5°	1053.2	1057.7	1066.6	1076.3	1075.5	1076.3	1080.7	1085.2	1086.7	1080.7	1083.0
7.5°	1094.9	1103.8	1113.5	1128.3	1128.3	1135.8	1138.8	1142.5	1151.4	1146.9	1145.4
10°	1142.5	1154.4	1172.2	1196.0	1196.8	1204.2	1211.6	1223.5	1227.3	1224.3	1225.8
12.5°	1202.0	1225.0	1226.5	1252.6	1264.5	1265.9	1277.8	1275.6	1283.1	1283.1	1295.7
15°	1228.0	1263.7	1283.8	1309.1	1316.5	1307.6	1317.3	1327.7	1328.4	1328.4	1327.7
17.5°	1274.9	1289.0	1309.1	1322.5	1325.4	1325.4	1326.2	1330.7	1327.7	1321.7	1326.2
20°	1284.5	1290.5	1297.9	1296.4	1297.9	1290.5	1283.1	1275.6	1276.4	1272.6	1283.8
22.5°	1266.7	1265.2	1248.1	1236.9	1236.9	1222.1	1207.9	1201.2	1194.5	1196.8	1200.5
25°	1222.1	1199.0	1178.2	1161.8	1158.1	1134.3	1115.0	1109.0	1097.8	1106.8	1108.3
27.5°	1150.7	1124.6	1091.2	1077.0	1057.7	1048.0	1034.6	1016.8	993.7	1007.1	1004.9
30°	1074.0	1035.4	1007.8	973.6	943.1	940.9	915.6	885.9	874.0	874.0	880.7
32.5°	988.5	937.2	897.0	848.7	818.9	806.3	775.8	746.0	752.7	730.4	738.6
35°	888.8	821.2	770.6	723.7	701.4	686.5	647.1	630.7	612.9	602.5	621.8
37.5°	793.6	715.5	650.8	599.5	591.3	564.5	537.8	527.4	516.9	521.4	520.7
40°	677.6	608.4	550.4	510.2	496.1	483.5	465.6	453.0	446.3	450.0	450.7
42.5°	572.7	514.7	471.6	443.3	431.4	422.5	413.6	403.1	400.9	400.9	403.9
45°	491.7	444.0	415.0	392.0	385.3	378.6	371.9	367.4	365.9	363.0	365.2
47.5°	426.9	389.0	371.2	354.0	346.6	345.1	339.2	336.9	334.0	333.2	334.0
50°	372.6	348.8	332.5	322.8	317.6	315.4	312.4	307.9	306.4	310.2	308.7
52.5°	334.7	312.4	303.5	293.8	290.8	287.8	283.4	284.1	283.4	281.9	281.9
55°	296.8	282.6	273.7	266.3	265.5	262.6	258.8	257.4	256.6	255.1	257.4
57.5°	266.3	255.1	246.9	240.2	237.3	237.3	233.6	230.6	230.6	229.8	230.6
60°	235.8	224.6	219.4	212.7	210.5	209.8	207.5	206.0	203.8	203.8	203.8
62.5°	207.5	198.6	192.6	186.7	187.4	183.7	180.7	179.3	179.3	180.0	180.0
65°	180.7	174.8	167.4	162.1	160.7	159.9	158.4	157.7	155.5	156.9	156.9
67.5°	156.2	148.0	143.6	141.3	139.1	138.3	136.9	135.4	134.6	133.9	135.4
70°	131.7	125.0	121.2	119.8	117.5	116.8	116.0	113.8	114.5	115.3	116.0
72.5°	109.3	103.4	102.6	98.2	98.2	98.2	95.2	96.7	95.9	94.5	95.9
75°	86.3	83.3	81.8	79.6	80.3	79.6	78.8	76.6	76.6	77.4	78.1
77.5°	68.4	65.5	64.7	62.5	61.0	62.5	61.0	60.2	60.2	61.0	61.0
80°	50.6	49.1	46.9	46.9	46.9	46.1	46.1	46.1	45.4	44.6	45.4
82.5°	33.5	33.5	32.7	32.0	32.7	31.2	32.0	32.0	32.0	32.0	32.0
85°	21.6	20.8	20.8	20.1	20.1	20.1	20.8	19.3	19.3	20.1	20.1
87.5°	9.7	9.7	9.7	10.4	9.7	9.7	9.7	10.4	9.7	9.7	9.7
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.0	28.8	29.5	30.3	30.7	30.6	30.5	30.3	30.2	30.0	30.2
97.5°	36.1	36.5	37.0	37.5	37.7	37.8	37.9	38.1	38.2	38.4	38.2
100°	41.0	42.3	43.5	44.8	45.4	45.6	45.9	46.2	46.5	46.8	46.5
102.5°	42.9	44.6	46.3	48.0	48.9	49.1	49.6	50.1	50.5	51.0	50.5
105°	44.3	46.0	47.7	49.4	50.3	50.6	51.2	51.9	52.5	53.1	52.5
107.5°	45.7	47.4	49.1	50.8	51.7	52.0	52.6	53.3	53.9	54.5	53.9
110°	106.8	91.2	75.7	60.2	52.4	52.7	53.3	54.0	54.6	55.2	54.6

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.0	221.1	154.2	87.3	53.8	54.0	54.5	55.0	55.4	55.9	55.4
115°	359.1	287.3	215.4	143.5	107.6	102.0	90.8	79.7	68.5	57.3	68.5
117.5°	446.5	424.3	402.1	379.9	368.8	348.5	307.8	267.1	226.5	185.8	226.5
120°	513.9	515.8	517.6	519.5	520.4	509.9	489.0	468.0	447.1	426.1	447.1
122.5°	554.2	555.2	556.1	557.0	557.5	557.6	557.7	557.9	558.0	558.2	558.0
125°	591.4	592.5	593.6	594.7	595.2	595.4	595.9	596.4	596.8	597.3	596.8
127.5°	626.1	627.6	629.2	630.7	631.5	631.6	631.7	631.9	632.0	632.2	632.0
130°	659.1	660.8	662.5	664.2	665.0	664.9	664.8	664.6	664.5	664.3	664.5
132.5°	691.6	693.0	694.4	695.8	696.5	696.4	696.3	696.1	696.0	695.8	696.0
135°	721.8	723.3	724.9	726.4	727.2	727.0	726.7	726.4	726.1	725.8	726.1
137.5°	750.5	752.0	753.6	755.1	755.9	755.7	755.2	754.7	754.3	753.8	754.3
140°	778.2	779.6	781.0	782.4	783.1	782.7	781.9	781.2	780.4	779.6	780.4
142.5°	803.9	805.2	806.4	807.7	808.3	807.9	807.1	806.4	805.6	804.8	805.6
145°	827.5	828.6	829.7	830.8	831.3	830.9	830.1	829.4	828.6	827.8	828.6
147.5°	848.9	849.7	850.4	851.2	851.6	851.3	850.7	850.0	849.4	848.8	849.4
150°	867.8	868.8	869.7	870.6	871.1	870.7	869.9	869.2	868.4	867.6	868.4
152.5°	885.3	886.3	887.2	888.1	888.6	888.1	887.0	885.9	884.8	883.7	884.8
155°	900.7	901.7	902.6	903.5	904.0	903.4	902.1	900.9	899.6	898.4	899.6
157.5°	914.1	915.2	916.3	917.4	917.9	917.3	916.0	914.8	913.5	912.3	913.5
160°	925.8	926.8	927.7	928.6	929.1	928.6	927.5	926.4	925.3	924.2	925.3
162.5°	936.5	937.6	938.7	939.8	940.3	939.6	938.2	936.8	935.4	934.0	935.4
165°	944.9	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	944.9
167.5°	952.6	953.6	954.7	955.8	956.3	955.6	954.2	952.9	951.5	950.1	951.5
170°	958.1	959.2	960.3	961.4	961.9	961.2	959.8	958.4	957.0	955.6	957.0
172.5°	962.3	963.4	964.5	965.6	966.1	965.4	964.0	962.6	961.2	959.8	961.2
175°	965.1	966.2	967.3	968.4	968.9	968.1	966.6	965.0	963.5	961.9	963.5
177.5°	965.8	966.9	968.0	969.1	969.6	968.9	967.5	966.1	964.7	963.3	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1025.7	1020.5	1016.0	1016.8	1020.5	1017.5	1010.1	1000.4	996.7	992.2	996.7
5°	1087.4	1083.0	1074.0	1074.8	1072.6	1069.6	1057.7	1042.8	1042.8	1030.9	1029.4
7.5°	1148.4	1141.7	1135.8	1134.3	1126.1	1120.2	1109.7	1088.9	1080.7	1066.6	1058.4
10°	1216.9	1211.6	1205.0	1196.8	1192.3	1181.9	1164.8	1134.3	1119.4	1100.1	1085.9
12.5°	1286.0	1285.3	1270.4	1254.0	1253.3	1236.9	1225.0	1184.1	1164.0	1138.0	1104.5
15°	1329.9	1326.2	1318.0	1309.8	1312.1	1294.2	1267.4	1219.1	1205.7	1174.5	1138.8
17.5°	1329.2	1329.2	1326.9	1325.4	1323.2	1318.0	1303.1	1271.2	1249.6	1210.2	1176.7
20°	1286.8	1296.4	1298.7	1297.9	1305.4	1309.1	1308.3	1288.3	1271.2	1236.2	1202.0
22.5°	1202.0	1224.3	1234.0	1239.9	1255.5	1263.7	1283.1	1275.6	1271.2	1245.1	1216.1
25°	1123.1	1130.6	1159.6	1161.1	1182.6	1202.7	1222.1	1234.7	1251.1	1241.4	1216.9
27.5°	1021.2	1038.3	1059.2	1074.8	1079.3	1120.2	1152.1	1175.9	1213.1	1216.1	1207.9
30°	905.9	914.1	948.3	969.2	993.0	1022.7	1068.8	1109.7	1143.2	1173.7	1184.1
32.5°	765.4	798.8	818.9	844.2	865.0	917.8	974.4	1027.2	1065.9	1117.2	1139.5
35°	636.7	662.7	696.9	707.4	745.3	789.9	863.5	931.2	990.0	1042.1	1087.4
37.5°	530.3	551.2	587.6	604.0	626.3	683.6	745.3	829.3	900.0	964.0	1020.5
40°	457.4	473.1	500.6	505.8	524.4	576.4	626.3	705.1	798.8	885.1	946.9
42.5°	407.6	415.0	433.6	440.3	452.2	487.2	531.8	606.2	693.2	782.5	869.5
45°	371.9	377.1	388.3	394.2	409.1	424.7	461.2	520.7	589.1	679.1	772.8
47.5°	339.9	346.6	351.1	354.8	363.0	380.1	403.9	447.8	513.2	595.8	686.5
50°	313.1	315.4	323.6	324.3	329.5	340.7	363.0	389.8	441.8	508.8	596.5
52.5°	286.4	288.6	293.8	299.0	301.2	310.2	325.0	347.4	386.0	438.8	516.9
55°	259.6	262.6	267.8	271.5	273.7	281.2	290.1	311.7	342.1	379.3	443.3
57.5°	232.8	239.5	241.0	243.2	246.9	255.1	263.3	275.9	299.8	334.0	380.8
60°	207.5	209.8	215.0	217.2	220.9	225.4	235.8	245.5	262.6	289.3	331.7
62.5°	181.5	186.7	188.9	191.2	194.1	199.3	206.0	216.4	231.3	252.9	286.4
65°	159.2	159.9	164.4	167.4	170.3	174.0	180.7	190.4	199.3	219.4	244.0
67.5°	137.6	139.1	140.6	143.6	147.3	151.0	156.9	162.1	173.3	186.7	206.0
70°	116.8	116.8	120.5	122.7	122.0	126.4	130.9	136.9	145.0	157.7	173.3
72.5°	98.2	97.4	100.4	101.2	102.6	105.6	108.6	114.5	119.0	128.7	140.6
75°	78.1	79.6	81.1	81.1	83.3	85.5	88.5	91.5	96.7	102.6	111.6
77.5°	61.7	61.7	63.2	64.0	66.2	65.5	68.4	71.4	75.1	80.3	87.0
80°	45.4	46.9	46.9	46.9	47.6	48.3	51.3	53.6	55.8	59.5	62.5
82.5°	32.0	32.0	33.5	33.5	33.5	35.0	35.0	35.7	37.2	39.4	41.7
85°	20.1	20.1	20.1	20.8	20.1	20.8	22.3	21.6	22.3	23.8	23.8
87.5°	9.7	9.7	9.7	9.7	9.7	10.4	9.7	10.4	11.2	11.2	11.2
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.3	30.5	30.6	30.7	30.3	29.5	28.8	28.0	27.2	26.1	25.1
97.5°	38.1	37.9	37.8	37.7	37.5	37.0	36.5	36.1	35.6	33.1	30.7
100°	46.2	45.9	45.6	45.4	44.8	43.5	42.3	41.0	39.8	37.2	34.5
102.5°	50.1	49.6	49.1	48.9	48.0	46.3	44.6	42.9	41.2	39.5	37.7
105°	51.9	51.2	50.6	50.3	49.4	47.7	46.0	44.3	42.6	40.0	38.3
107.5°	53.3	52.6	52.0	51.7	50.8	49.1	47.4	45.7	44.0	42.3	40.6
110°	54.0	53.3	52.7	52.4	50.2	48.5	46.8	45.1	43.4	41.7	40.0

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.0	54.5	54.0	53.8	87.3	154.2	221.1	288.0	354.9	357.5	360.2
115°	79.7	90.8	102.0	107.6	143.5	215.4	287.3	359.1	431.0	427.1	423.3
117.5°	267.1	307.8	348.5	368.8	379.9	402.1	424.3	446.5	468.7	466.1	463.5
120°	468.0	489.0	509.9	520.4	519.5	517.6	515.8	513.9	512.1	509.3	506.5
122.5°	557.9	557.7	557.6	557.5	557.0	556.1	555.2	554.2	553.3	550.2	547.1
125°	596.4	595.9	595.4	595.2	594.7	593.6	592.5	591.4	590.3	587.3	584.4
127.5°	631.9	631.7	631.6	631.5	630.7	629.2	627.6	626.1	624.5	622.2	619.8
130°	664.6	664.8	664.9	665.0	664.2	662.5	660.8	659.1	657.4	655.7	654.0
132.5°	696.1	696.3	696.4	696.5	695.8	694.4	693.0	691.6	690.2	688.5	686.8
135°	726.4	726.7	727.0	727.2	726.4	724.9	723.3	721.8	720.2	718.8	717.4
137.5°	754.7	755.2	755.7	755.9	755.1	753.6	752.0	750.5	748.9	747.3	745.8
140°	781.2	781.9	782.7	783.1	782.4	781.0	779.6	778.2	776.8	775.1	773.4
142.5°	806.4	807.1	807.9	808.3	807.7	806.4	805.2	803.9	802.7	800.7	798.7
145°	829.4	830.1	830.9	831.3	830.8	829.7	828.6	827.5	826.4	823.8	821.1
147.5°	850.0	850.7	851.3	851.6	851.2	850.4	849.7	848.9	848.1	845.5	842.8
150°	869.2	869.9	870.7	871.1	870.6	869.7	868.8	867.8	866.9	864.4	862.0
152.5°	885.9	887.0	888.1	888.6	888.1	887.2	886.3	885.3	884.4	882.1	879.7
155°	900.9	902.1	903.4	904.0	903.5	902.6	901.7	900.7	899.8	897.9	896.1
157.5°	914.8	916.0	917.3	917.9	917.4	916.3	915.2	914.1	913.0	911.6	910.2
160°	926.4	927.5	928.6	929.1	928.6	927.7	926.8	925.8	924.9	924.0	923.0
162.5°	936.8	938.2	939.6	940.3	939.8	938.7	937.6	936.5	935.4	934.6	933.8
165°	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	943.3	942.9
167.5°	952.9	954.2	955.6	956.3	955.8	954.7	953.6	952.6	951.5	951.0	950.6
170°	958.4	959.8	961.2	961.9	961.4	960.3	959.2	958.1	957.0	956.7	956.4
172.5°	962.6	964.0	965.4	966.1	965.6	964.5	963.4	962.3	961.2	960.9	960.6
175°	965.0	966.6	968.1	968.9	968.4	967.3	966.2	965.1	964.0	963.7	963.4
177.5°	966.1	967.5	968.9	969.6	969.1	968.0	966.9	965.8	964.7	964.5	964.4
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	993.0	989.3	987.0	988.5	984.0	972.9	972.9	976.6	972.1	967.7	961.0
5°	1020.5	1013.1	1008.6	1007.8	997.4	979.6	975.9	972.1	962.5	952.1	940.9
7.5°	1047.3	1033.9	1026.4	1021.2	1006.4	983.3	973.6	965.5	949.8	934.2	920.1
10°	1069.6	1050.2	1041.3	1033.1	1013.8	984.8	969.2	954.3	934.2	914.1	896.3
12.5°	1087.4	1065.1	1054.0	1042.1	1018.3	980.3	961.0	937.2	917.1	890.3	872.5
15°	1117.2	1071.1	1060.7	1049.5	1025.0	972.9	949.1	922.3	894.8	859.1	839.7
17.5°	1141.0	1079.3	1078.5	1054.7	1022.7	969.9	933.5	898.5	868.8	833.1	802.6
20°	1155.1	1091.9	1080.0	1055.4	1015.3	949.8	911.9	873.2	841.2	798.1	767.6
22.5°	1167.0	1109.7	1078.5	1048.8	999.7	943.1	887.4	850.9	807.0	760.2	731.2
25°	1171.5	1113.5	1080.7	1046.5	988.5	923.8	860.6	821.2	772.1	729.7	690.2
27.5°	1172.2	1112.7	1072.6	1036.9	972.9	898.5	833.8	792.1	737.8	688.8	649.3
30°	1164.8	1104.5	1068.1	1029.4	958.0	875.5	801.1	755.0	696.9	647.8	606.9
32.5°	1142.5	1088.2	1058.4	1016.0	938.7	843.5	769.8	718.5	657.5	609.2	569.7
35°	1105.3	1068.1	1035.4	995.9	913.4	813.7	738.6	678.3	616.6	570.5	533.3
37.5°	1059.2	1039.1	1008.6	969.9	884.4	786.9	703.6	636.7	575.0	530.3	493.9
40°	996.7	1001.9	972.1	937.2	850.2	750.5	658.3	594.3	536.3	494.6	458.9
42.5°	929.0	950.6	933.5	900.0	812.2	710.3	624.8	554.1	497.6	454.5	424.7
45°	856.1	893.3	882.9	858.3	772.8	667.9	577.2	508.8	458.9	417.3	391.2
47.5°	776.5	829.3	829.3	811.5	728.9	625.5	536.3	466.4	417.3	387.5	362.2
50°	695.5	755.0	764.6	752.7	679.8	577.2	486.4	423.2	380.8	351.8	333.2
52.5°	610.7	679.8	697.7	691.7	627.8	531.1	445.5	383.8	345.1	319.8	303.5
55°	529.6	609.9	629.3	631.5	572.0	480.5	400.2	345.9	308.7	291.6	277.4
57.5°	453.0	530.3	551.9	555.6	515.5	434.4	357.8	310.2	276.7	262.6	251.4
60°	387.5	452.2	480.5	488.7	453.7	380.8	318.3	272.2	246.9	233.6	223.1
62.5°	334.0	386.0	415.8	418.0	402.4	334.0	277.4	238.8	217.2	205.3	200.1
65°	281.9	328.8	346.6	355.5	342.9	289.3	239.5	207.5	190.4	180.0	174.8
67.5°	240.2	270.0	284.9	296.8	284.1	244.0	203.8	177.8	165.1	154.7	151.7
70°	197.1	221.7	232.8	244.7	233.6	203.1	174.0	150.2	139.1	130.9	127.2
72.5°	157.7	177.0	187.4	194.9	188.2	162.9	139.1	122.7	114.5	108.6	106.4
75°	125.0	138.3	144.3	149.5	146.5	127.2	112.3	98.9	91.5	86.3	84.8
77.5°	95.2	104.9	111.6	113.1	109.3	96.7	84.0	75.9	69.9	66.9	65.5
80°	67.7	73.6	77.4	79.6	75.9	70.7	61.7	55.8	50.6	46.9	46.1
82.5°	45.4	48.3	51.3	50.6	49.1	44.6	39.4	36.4	34.2	31.2	31.2
85°	26.0	26.8	28.3	29.0	28.3	25.3	22.3	20.8	19.3	17.1	17.1
87.5°	11.2	11.9	11.9	12.6	11.2	11.2	9.7	8.2	8.2	7.4	6.7
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.0	22.9	22.4	25.0	30.1	35.2	40.3	45.4	40.3	35.2	30.1
97.5°	28.2	25.7	24.5	30.9	43.6	56.3	69.0	81.7	69.0	56.3	43.6
100°	31.9	29.2	27.9	38.5	59.8	81.1	102.3	123.6	102.3	81.1	59.8
102.5°	126.0	154.3	168.4	168.6	168.9	169.2	169.5	169.8	169.5	169.2	168.9
105°	169.7	212.1	233.3	231.0	226.3	221.7	217.0	212.4	217.0	221.7	226.3
107.5°	200.9	253.2	279.4	277.5	273.6	269.7	265.9	262.0	265.9	269.7	273.6
110°	256.8	301.7	324.1	322.5	319.2	316.0	312.7	309.5	312.7	316.0	319.2

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	362.8	365.5	366.8	365.4	362.6	359.8	357.0	354.2	357.0	359.8	362.6
115°	419.4	415.5	413.6	412.3	409.6	407.0	404.3	401.7	404.3	407.0	409.6
117.5°	460.8	458.2	456.9	455.3	452.2	449.1	446.0	442.9	446.0	449.1	452.2
120°	503.7	500.9	499.5	498.3	496.0	493.7	491.3	489.0	491.3	493.7	496.0
122.5°	544.0	540.9	539.3	538.1	535.6	533.1	530.6	528.1	530.6	533.1	535.6
125°	581.4	578.5	577.0	576.0	574.0	571.9	569.9	567.9	569.9	571.9	574.0
127.5°	617.5	615.2	614.0	612.9	610.8	608.6	606.5	604.3	606.5	608.6	610.8
130°	652.3	650.6	649.7	648.5	646.0	643.5	641.0	638.5	641.0	643.5	646.0
132.5°	685.1	683.4	682.5	681.5	679.5	677.4	675.4	673.4	675.4	677.4	679.5
135°	716.0	714.6	713.9	712.7	710.2	707.7	705.3	702.8	705.3	707.7	710.2
137.5°	744.2	742.7	741.9	741.0	739.1	737.2	735.4	733.5	735.4	737.2	739.1
140°	771.7	770.0	769.1	768.5	767.2	766.0	764.7	763.5	764.7	766.0	767.2
142.5°	796.6	794.6	793.6	793.1	792.0	790.9	789.8	788.7	789.8	790.9	792.0
145°	818.5	815.8	814.5	814.6	814.7	814.9	815.0	815.2	815.0	814.9	814.7
147.5°	840.2	837.5	836.2	836.4	836.9	837.4	837.8	838.3	837.8	837.4	836.9
150°	859.5	857.0	855.8	856.3	857.4	858.5	859.5	860.6	859.5	858.5	857.4
152.5°	877.4	875.1	873.9	874.5	875.8	877.0	878.3	879.5	878.3	877.0	875.8
155°	894.2	892.3	891.4	892.1	893.5	894.9	896.3	897.7	896.3	894.9	893.5
157.5°	908.8	907.4	906.7	907.3	908.6	909.8	911.1	912.3	911.1	909.8	908.6
160°	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9	924.0	923.0	922.1
162.5°	933.1	932.3	931.9	932.4	933.3	934.2	935.2	936.1	935.2	934.2	933.3
165°	942.4	941.9	941.7	942.2	943.1	944.0	945.0	945.9	945.0	944.0	943.1
167.5°	950.1	949.6	949.4	949.9	950.8	951.7	952.7	953.6	952.7	951.7	950.8
170°	956.1	955.8	955.6	956.1	957.0	957.9	958.9	959.8	958.9	957.9	957.0
172.5°	960.3	960.0	959.8	960.3	961.2	962.1	963.1	964.0	963.1	962.1	961.2
175°	963.1	962.8	962.6	963.1	964.2	965.3	966.4	967.5	966.4	965.3	964.2
177.5°	964.2	964.1	964.0	964.5	965.6	966.7	967.8	968.9	967.8	966.7	965.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	957.3	961.0	960.2	952.8	944.6	937.9	925.3	926.8	922.3	923.1	927.5
5°	933.5	933.5	930.5	920.1	906.7	899.3	885.1	881.4	872.5	871.7	871.0
7.5°	908.2	904.5	900.7	885.9	869.5	857.6	838.3	833.8	824.9	818.9	815.9
10°	878.4	873.2	865.8	848.7	828.6	813.7	793.6	787.7	770.6	763.1	758.7
12.5°	845.7	842.7	830.8	816.7	784.0	767.6	738.6	744.5	727.4	712.6	710.3
15°	813.0	801.8	795.1	772.1	732.6	725.2	702.1	690.2	674.6	662.7	662.7
17.5°	781.0	763.9	749.0	724.5	695.5	674.6	657.5	651.6	632.2	620.3	618.1
20°	738.6	719.3	715.5	680.6	660.5	637.4	621.1	606.2	592.1	586.9	583.1
22.5°	698.4	676.1	670.2	640.4	620.3	597.3	580.9	570.5	560.1	556.4	549.7
25°	655.3	641.9	633.0	601.0	578.7	557.1	545.9	538.5	528.8	528.1	523.6
27.5°	613.6	601.0	592.1	561.6	545.2	525.1	516.2	508.0	502.8	500.6	498.3
30°	577.9	563.8	553.4	531.1	511.0	494.6	487.2	482.0	479.0	475.3	474.5
32.5°	538.5	530.3	516.2	499.1	483.5	467.8	463.4	459.7	455.2	453.7	453.0
35°	505.0	493.9	485.0	465.6	458.9	445.5	440.3	437.4	431.4	429.9	428.4
37.5°	472.3	461.9	452.2	440.3	427.7	420.2	417.3	412.8	409.8	410.6	409.1
40°	439.6	431.4	424.0	411.3	403.9	400.2	394.2	389.8	388.3	389.0	388.3
42.5°	407.6	400.2	395.7	386.0	378.6	374.9	371.2	366.7	368.9	368.9	371.2
45°	378.6	371.9	368.9	361.5	357.0	351.1	347.4	346.6	349.6	348.8	348.8
47.5°	348.8	346.6	342.9	336.2	330.2	326.5	325.8	325.8	328.8	330.2	329.5
50°	325.8	321.3	316.9	311.7	307.2	305.7	303.5	305.0	307.9	307.9	309.4
52.5°	296.8	293.8	292.3	287.8	284.9	284.9	284.9	285.6	287.8	290.1	289.3
55°	271.5	269.3	267.8	265.5	261.8	262.6	261.8	263.3	265.5	267.8	269.3
57.5°	244.7	244.0	242.5	238.8	238.8	238.0	240.2	241.0	244.7	246.2	248.4
60°	220.9	218.7	218.7	215.7	215.7	215.7	217.9	220.2	223.1	223.9	225.4
62.5°	195.6	195.6	194.9	192.6	192.6	194.9	195.6	198.6	200.1	200.1	202.3
65°	171.8	171.1	170.3	171.1	171.8	171.8	174.0	175.5	177.0	177.8	178.5
67.5°	148.0	147.3	148.8	148.0	149.5	152.5	151.7	154.0	156.2	156.2	156.9
70°	125.7	127.2	126.4	127.9	127.2	128.7	130.9	131.7	131.7	132.4	134.6
72.5°	104.9	104.9	104.9	104.1	104.9	106.4	107.9	108.6	110.1	110.8	113.1
75°	84.8	84.8	83.3	84.8	84.8	86.3	87.8	87.8	87.8	89.3	91.5
77.5°	64.0	64.7	64.0	65.5	65.5	66.2	67.7	66.9	68.4	69.2	69.9
80°	46.9	46.1	46.1	46.1	46.9	46.9	48.3	49.1	49.1	51.3	49.8
82.5°	29.8	30.5	29.8	30.5	30.5	31.2	30.5	31.2	32.0	33.5	32.7
85°	17.1	16.4	16.4	17.1	16.4	16.4	17.1	16.4	17.1	16.4	17.1
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	22.9	24.0	25.1	26.1	27.2	28.0	28.8	29.5	30.3
97.5°	30.9	24.5	25.7	28.2	30.7	33.1	35.6	36.1	36.5	37.0	37.5
100°	38.5	27.9	29.2	31.9	34.5	37.2	39.8	41.0	42.3	43.5	44.8
102.5°	168.6	168.4	154.3	126.0	97.7	69.5	41.2	42.9	44.6	46.3	48.0
105°	231.0	233.3	212.1	169.7	127.4	85.0	42.6	44.3	46.0	47.7	49.4
107.5°	277.5	279.4	253.2	200.9	148.6	96.3	44.0	45.7	47.4	49.1	50.8
110°	322.5	324.1	301.7	256.8	212.0	167.1	122.3	106.8	91.2	75.7	60.2

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	365.4	366.8	365.5	362.8	360.2	357.5	354.9	288.0	221.1	154.2	87.3
115°	412.3	413.6	415.5	419.4	423.3	427.1	431.0	359.1	287.3	215.4	143.5
117.5°	455.3	456.9	458.2	460.8	463.5	466.1	468.7	446.5	424.3	402.1	379.9
120°	498.3	499.5	500.9	503.7	506.5	509.3	512.1	513.9	515.8	517.6	519.5
122.5°	538.1	539.3	540.9	544.0	547.1	550.2	553.3	554.2	555.2	556.1	557.0
125°	576.0	577.0	578.5	581.4	584.4	587.3	590.3	591.4	592.5	593.6	594.7
127.5°	612.9	614.0	615.2	617.5	619.8	622.2	624.5	626.1	627.6	629.2	630.7
130°	648.5	649.7	650.6	652.3	654.0	655.7	657.4	659.1	660.8	662.5	664.2
132.5°	681.5	682.5	683.4	685.1	686.8	688.5	690.2	691.6	693.0	694.4	695.8
135°	712.7	713.9	714.6	716.0	717.4	718.8	720.2	721.8	723.3	724.9	726.4
137.5°	741.0	741.9	742.7	744.2	745.8	747.3	748.9	750.5	752.0	753.6	755.1
140°	768.5	769.1	770.0	771.7	773.4	775.1	776.8	778.2	779.6	781.0	782.4
142.5°	793.1	793.6	794.6	796.6	798.7	800.7	802.7	803.9	805.2	806.4	807.7
145°	814.6	814.5	815.8	818.5	821.1	823.8	826.4	827.5	828.6	829.7	830.8
147.5°	836.4	836.2	837.5	840.2	842.8	845.5	848.1	848.9	849.7	850.4	851.2
150°	856.3	855.8	857.0	859.5	862.0	864.4	866.9	867.8	868.8	869.7	870.6
152.5°	874.5	873.9	875.1	877.4	879.7	882.1	884.4	885.3	886.3	887.2	888.1
155°	892.1	891.4	892.3	894.2	896.1	897.9	899.8	900.7	901.7	902.6	903.5
157.5°	907.3	906.7	907.4	908.8	910.2	911.6	913.0	914.1	915.2	916.3	917.4
160°	921.2	920.7	921.2	922.1	923.0	924.0	924.9	925.8	926.8	927.7	928.6
162.5°	932.4	931.9	932.3	933.1	933.8	934.6	935.4	936.5	937.6	938.7	939.8
165°	942.2	941.7	941.9	942.4	942.9	943.3	943.8	944.9	946.0	947.1	948.2
167.5°	949.9	949.4	949.6	950.1	950.6	951.0	951.5	952.6	953.6	954.7	955.8
170°	956.1	955.6	955.8	956.1	956.4	956.7	957.0	958.1	959.2	960.3	961.4
172.5°	960.3	959.8	960.0	960.3	960.6	960.9	961.2	962.3	963.4	964.5	965.6
175°	963.1	962.6	962.8	963.1	963.4	963.7	964.0	965.1	966.2	967.3	968.4
177.5°	964.5	964.0	964.1	964.2	964.4	964.5	964.7	965.8	966.9	968.0	969.1
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	922.3	924.5	919.3	917.8	919.3	914.1	915.6	917.1	917.1	919.3	920.8
5°	868.8	865.8	860.6	859.1	857.6	859.8	858.3	860.6	861.3	866.5	867.3
7.5°	815.9	811.5	807.0	802.6	801.1	797.4	801.1	801.1	806.3	804.8	808.5
10°	753.5	752.7	746.8	744.5	741.6	735.6	743.8	741.6	745.3	752.0	753.5
12.5°	707.4	699.2	702.9	692.5	696.2	690.2	691.0	691.0	696.9	697.7	696.2
15°	663.5	656.8	647.1	642.6	640.4	637.4	647.1	647.8	643.4	653.8	650.1
17.5°	618.8	618.8	609.9	607.7	601.7	604.7	603.2	604.0	602.5	609.9	613.6
20°	580.2	576.4	573.5	574.2	566.8	565.3	563.8	565.3	570.5	575.7	577.2
22.5°	548.9	546.7	539.3	540.7	534.8	537.0	535.5	539.3	540.0	540.0	545.2
25°	519.2	516.2	516.9	514.0	511.7	511.7	509.5	511.7	514.7	516.2	516.9
27.5°	496.9	494.6	490.9	488.7	490.2	486.4	489.4	491.7	491.7	490.2	491.7
30°	470.1	471.6	471.6	464.1	467.1	465.6	467.8	469.3	469.3	470.1	468.6
32.5°	452.2	447.8	447.0	446.3	446.3	443.3	443.3	445.5	446.3	447.0	449.3
35°	428.4	428.4	424.7	426.9	424.0	424.7	424.0	424.7	426.2	424.0	426.2
37.5°	406.9	407.6	406.1	407.6	408.3	406.9	405.4	408.3	406.9	406.9	405.4
40°	388.3	387.5	388.3	388.3	388.3	389.0	387.5	387.5	387.5	386.0	384.5
42.5°	372.6	368.2	369.7	370.4	368.2	368.2	368.9	368.2	370.4	365.9	365.9
45°	350.3	348.8	349.6	349.6	351.1	348.8	350.3	351.1	348.8	348.1	346.6
47.5°	330.2	331.7	330.2	331.7	331.7	333.2	330.2	331.0	331.7	328.8	326.5
50°	310.2	310.2	312.4	311.7	312.4	310.9	310.9	310.2	310.9	309.4	307.2
52.5°	291.6	289.3	293.1	292.3	291.6	290.8	290.1	290.8	289.3	287.8	287.8
55°	268.5	268.5	270.7	271.5	271.5	270.0	268.5	269.3	268.5	267.8	267.0
57.5°	249.9	246.9	248.4	249.2	249.2	246.9	248.4	246.9	246.9	247.7	245.5
60°	226.1	226.1	224.6	226.9	226.9	225.4	225.4	226.1	224.6	223.9	223.1
62.5°	200.8	201.6	203.8	204.5	205.3	203.8	202.3	203.1	203.1	200.8	201.6
65°	179.3	180.7	183.7	183.0	181.5	182.2	180.7	181.5	179.3	180.0	177.8
67.5°	158.4	157.7	158.4	158.4	159.9	159.2	157.7	157.7	156.9	159.2	156.9
70°	136.1	136.1	136.1	136.1	136.9	137.6	136.1	134.6	135.4	133.9	133.1
72.5°	113.1	113.8	113.1	114.5	112.3	113.8	113.8	113.1	112.3	112.3	112.3
75°	91.5	93.0	90.7	91.5	90.7	92.2	91.5	91.5	90.0	89.3	90.0
77.5°	69.9	70.7	69.2	69.9	69.2	69.9	69.9	69.2	69.2	69.2	69.2
80°	49.8	50.6	49.8	49.1	48.3	49.8	48.3	49.1	49.8	49.1	50.6
82.5°	32.0	32.0	31.2	32.0	30.5	30.5	31.2	31.2	30.5	32.0	30.5
85°	15.6	15.6	17.1	15.6	14.9	14.9	14.9	15.6	14.9	16.4	15.6
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.7	30.6	30.5	30.3	30.2	30.0	30.2	30.3	30.5	30.6	30.7
97.5°	37.7	37.8	37.9	38.1	38.2	38.4	38.2	38.1	37.9	37.8	37.7
100°	45.4	45.6	45.9	46.2	46.5	46.8	46.5	46.2	45.9	45.6	45.4
102.5°	48.9	49.1	49.6	50.1	50.5	51.0	50.5	50.1	49.6	49.1	48.9
105°	50.3	50.6	51.2	51.9	52.5	53.1	52.5	51.9	51.2	50.6	50.3
107.5°	51.7	52.0	52.6	53.3	53.9	54.5	53.9	53.3	52.6	52.0	51.7
110°	52.4	52.7	53.3	54.0	54.6	55.2	54.6	54.0	53.3	52.7	52.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.8	54.0	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	53.8
115°	107.6	102.0	90.8	79.7	68.5	57.3	68.5	79.7	90.8	102.0	107.6
117.5°	368.8	348.5	307.8	267.1	226.5	185.8	226.5	267.1	307.8	348.5	368.8
120°	520.4	509.9	489.0	468.0	447.1	426.1	447.1	468.0	489.0	509.9	520.4
122.5°	557.5	557.6	557.7	557.9	558.0	558.2	558.0	557.9	557.7	557.6	557.5
125°	595.2	595.4	595.9	596.4	596.8	597.3	596.8	596.4	595.9	595.4	595.2
127.5°	631.5	631.6	631.7	631.9	632.0	632.2	632.0	631.9	631.7	631.6	631.5
130°	665.0	664.9	664.8	664.6	664.5	664.3	664.5	664.6	664.8	664.9	665.0
132.5°	696.5	696.4	696.3	696.1	696.0	695.8	696.0	696.1	696.3	696.4	696.5
135°	727.2	727.0	726.7	726.4	726.1	725.8	726.1	726.4	726.7	727.0	727.2
137.5°	755.9	755.7	755.2	754.7	754.3	753.8	754.3	754.7	755.2	755.7	755.9
140°	783.1	782.7	781.9	781.2	780.4	779.6	780.4	781.2	781.9	782.7	783.1
142.5°	808.3	807.9	807.1	806.4	805.6	804.8	805.6	806.4	807.1	807.9	808.3
145°	831.3	830.9	830.1	829.4	828.6	827.8	828.6	829.4	830.1	830.9	831.3
147.5°	851.6	851.3	850.7	850.0	849.4	848.8	849.4	850.0	850.7	851.3	851.6
150°	871.1	870.7	869.9	869.2	868.4	867.6	868.4	869.2	869.9	870.7	871.1
152.5°	888.6	888.1	887.0	885.9	884.8	883.7	884.8	885.9	887.0	888.1	888.6
155°	904.0	903.4	902.1	900.9	899.6	898.4	899.6	900.9	902.1	903.4	904.0
157.5°	917.9	917.3	916.0	914.8	913.5	912.3	913.5	914.8	916.0	917.3	917.9
160°	929.1	928.6	927.5	926.4	925.3	924.2	925.3	926.4	927.5	928.6	929.1
162.5°	940.3	939.6	938.2	936.8	935.4	934.0	935.4	936.8	938.2	939.6	940.3
165°	948.7	948.2	947.1	946.0	944.9	943.8	944.9	946.0	947.1	948.2	948.7
167.5°	956.3	955.6	954.2	952.9	951.5	950.1	951.5	952.9	954.2	955.6	956.3
170°	961.9	961.2	959.8	958.4	957.0	955.6	957.0	958.4	959.8	961.2	961.9
172.5°	966.1	965.4	964.0	962.6	961.2	959.8	961.2	962.6	964.0	965.4	966.1
175°	968.9	968.1	966.6	965.0	963.5	961.9	963.5	965.0	966.6	968.1	968.9
177.5°	969.6	968.9	967.5	966.1	964.7	963.3	964.7	966.1	967.5	968.9	969.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	918.6	924.5	922.3	914.1	923.8	923.8	930.5	930.5	938.7	941.6	946.1
5°	866.5	871.0	874.7	871.0	877.7	888.1	894.0	899.3	910.4	914.9	921.6
7.5°	810.7	818.9	822.6	822.6	833.8	845.7	857.6	865.0	880.7	886.6	893.3
10°	756.4	766.1	773.6	772.8	791.4	798.8	813.7	830.8	846.4	855.4	865.0
12.5°	699.2	704.4	714.8	729.7	734.1	747.5	764.6	786.2	814.5	822.6	836.8
15°	651.6	665.7	673.9	680.6	691.0	703.6	722.2	743.1	771.3	789.2	804.0
17.5°	611.4	630.0	635.2	633.7	647.1	666.4	688.0	703.6	728.9	750.5	764.6
20°	578.7	586.1	595.0	598.8	609.2	630.0	650.8	668.7	689.5	706.6	723.0
22.5°	545.9	551.9	559.3	566.0	574.2	586.1	606.2	628.5	648.6	665.0	683.6
25°	519.2	522.9	529.6	534.8	543.7	551.9	566.0	590.6	614.4	624.0	640.4
27.5°	493.1	496.1	500.6	506.5	511.0	519.2	531.8	551.9	576.4	586.1	608.4
30°	470.1	472.3	476.8	479.7	482.0	491.7	501.3	516.9	535.5	548.9	565.3
32.5°	448.5	450.7	455.2	455.9	458.9	464.1	473.1	487.2	503.6	514.7	528.8
35°	424.7	426.2	430.7	432.1	434.4	438.8	445.5	455.9	470.8	479.0	491.7
37.5°	406.1	405.4	408.3	410.6	413.6	415.8	418.0	428.4	439.6	447.0	456.7
40°	386.0	384.5	385.3	388.3	389.8	392.7	392.7	403.1	410.6	416.5	424.0
42.5°	365.9	365.2	363.7	365.2	366.7	367.4	368.2	375.6	383.1	388.3	396.4
45°	345.9	345.1	343.6	344.4	344.4	345.9	348.1	351.1	356.3	360.7	365.2
47.5°	327.3	325.8	323.6	322.8	324.3	324.3	324.3	327.3	332.5	334.0	338.4
50°	307.9	305.7	302.7	301.2	301.2	300.5	302.0	302.7	307.2	308.7	312.4
52.5°	287.1	285.6	282.6	279.7	280.4	278.9	279.7	280.4	281.9	284.1	286.4
55°	266.3	263.3	261.1	260.3	258.1	258.1	255.9	258.8	258.1	258.8	261.8
57.5°	246.2	243.2	239.5	238.0	235.8	235.0	233.6	232.8	233.6	235.8	238.0
60°	222.4	220.9	218.7	216.4	215.0	212.7	211.2	211.2	210.5	210.5	211.2
62.5°	199.3	198.6	195.6	194.9	193.4	191.9	189.7	188.2	188.2	189.7	190.4
65°	177.0	176.3	174.0	173.3	169.6	168.1	167.4	166.6	165.1	165.1	165.1
67.5°	156.2	154.0	154.0	150.2	147.3	145.8	144.3	143.6	143.6	143.6	144.3
70°	133.1	133.1	130.9	128.7	125.7	126.4	124.2	122.0	122.0	120.5	121.2
72.5°	110.8	110.1	107.9	107.1	104.9	102.6	101.2	102.6	100.4	99.7	100.4
75°	89.3	88.5	87.0	85.5	86.3	84.0	81.8	81.1	81.1	79.6	79.6
77.5°	68.4	69.9	66.9	66.2	64.7	63.2	62.5	61.7	61.7	61.7	63.2
80°	47.6	48.3	48.3	46.9	47.6	45.4	45.4	45.4	43.1	43.9	44.6
82.5°	30.5	30.5	29.8	30.5	29.8	29.8	29.0	29.0	28.3	28.3	29.0
85°	17.1	16.4	15.6	17.1	16.4	16.4	15.6	15.6	15.6	15.6	15.6
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.3	29.5	28.8	28.0	27.2	26.1	25.1	24.0	22.9	22.4	25.0
97.5°	37.5	37.0	36.5	36.1	35.6	33.1	30.7	28.2	25.7	24.5	30.9
100°	44.8	43.5	42.3	41.0	39.8	37.2	34.5	31.9	29.2	27.9	38.5
102.5°	48.0	46.3	44.6	42.9	41.2	69.5	97.7	126.0	154.3	168.4	168.6
105°	49.4	47.7	46.0	44.3	42.6	85.0	127.4	169.7	212.1	233.3	231.0
107.5°	50.8	49.1	47.4	45.7	44.0	96.3	148.6	200.9	253.2	279.4	277.5
110°	60.2	75.7	91.2	106.8	122.3	167.1	212.0	256.8	301.7	324.1	322.5

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.3	154.2	221.1	288.0	354.9	357.5	360.2	362.8	365.5	366.8	365.4
115°	143.5	215.4	287.3	359.1	431.0	427.1	423.3	419.4	415.5	413.6	412.3
117.5°	379.9	402.1	424.3	446.5	468.7	466.1	463.5	460.8	458.2	456.9	455.3
120°	519.5	517.6	515.8	513.9	512.1	509.3	506.5	503.7	500.9	499.5	498.3
122.5°	557.0	556.1	555.2	554.2	553.3	550.2	547.1	544.0	540.9	539.3	538.1
125°	594.7	593.6	592.5	591.4	590.3	587.3	584.4	581.4	578.5	577.0	576.0
127.5°	630.7	629.2	627.6	626.1	624.5	622.2	619.8	617.5	615.2	614.0	612.9
130°	664.2	662.5	660.8	659.1	657.4	655.7	654.0	652.3	650.6	649.7	648.5
132.5°	695.8	694.4	693.0	691.6	690.2	688.5	686.8	685.1	683.4	682.5	681.5
135°	726.4	724.9	723.3	721.8	720.2	718.8	717.4	716.0	714.6	713.9	712.7
137.5°	755.1	753.6	752.0	750.5	748.9	747.3	745.8	744.2	742.7	741.9	741.0
140°	782.4	781.0	779.6	778.2	776.8	775.1	773.4	771.7	770.0	769.1	768.5
142.5°	807.7	806.4	805.2	803.9	802.7	800.7	798.7	796.6	794.6	793.6	793.1
145°	830.8	829.7	828.6	827.5	826.4	823.8	821.1	818.5	815.8	814.5	814.6
147.5°	851.2	850.4	849.7	848.9	848.1	845.5	842.8	840.2	837.5	836.2	836.4
150°	870.6	869.7	868.8	867.8	866.9	864.4	862.0	859.5	857.0	855.8	856.3
152.5°	888.1	887.2	886.3	885.3	884.4	882.1	879.7	877.4	875.1	873.9	874.5
155°	903.5	902.6	901.7	900.7	899.8	897.9	896.1	894.2	892.3	891.4	892.1
157.5°	917.4	916.3	915.2	914.1	913.0	911.6	910.2	908.8	907.4	906.7	907.3
160°	928.6	927.7	926.8	925.8	924.9	924.0	923.0	922.1	921.2	920.7	921.2
162.5°	939.8	938.7	937.6	936.5	935.4	934.6	933.8	933.1	932.3	931.9	932.4
165°	948.2	947.1	946.0	944.9	943.8	943.3	942.9	942.4	941.9	941.7	942.2
167.5°	955.8	954.7	953.6	952.6	951.5	951.0	950.6	950.1	949.6	949.4	949.9
170°	961.4	960.3	959.2	958.1	957.0	956.7	956.4	956.1	955.8	955.6	956.1
172.5°	965.6	964.5	963.4	962.3	961.2	960.9	960.6	960.3	960.0	959.8	960.3
175°	968.4	967.3	966.2	965.1	964.0	963.7	963.4	963.1	962.8	962.6	963.1
177.5°	969.1	968.0	966.9	965.8	964.7	964.5	964.4	964.2	964.1	964.0	964.5
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	967.7	967.7	967.7	967.7
2.5°	949.8	949.8	961.0	972.9
5°	929.0	934.2	952.1	968.4
7.5°	908.9	917.8	940.2	961.0
10°	884.4	896.3	923.8	948.3
12.5°	860.6	871.7	903.7	931.2
15°	827.1	841.2	875.5	909.7
17.5°	793.6	807.8	849.4	889.6
20°	754.2	772.8	819.7	873.2
22.5°	717.8	740.8	792.9	836.0
25°	677.6	713.3	761.6	817.4
27.5°	641.9	677.6	726.7	783.2
30°	601.7	638.2	688.8	740.8
32.5°	563.1	596.5	645.6	709.6
35°	522.9	554.9	602.5	667.2
37.5°	486.4	517.7	569.7	629.3
40°	450.7	483.5	528.1	587.6
42.5°	417.3	446.3	486.4	545.9
45°	386.8	407.6	444.8	500.6
47.5°	354.8	373.4	407.6	463.4
50°	325.0	340.7	370.4	422.5
52.5°	296.0	309.4	336.9	378.6
55°	270.0	282.6	302.7	343.6
57.5°	243.2	252.9	272.2	305.0
60°	217.2	226.1	241.7	268.5
62.5°	191.2	198.6	213.5	235.0
65°	168.1	174.0	185.2	203.8
67.5°	145.8	149.5	158.4	173.3
70°	124.2	127.2	134.6	146.5
72.5°	101.2	104.1	112.3	120.5
75°	81.8	82.6	88.5	95.2
77.5°	64.0	63.2	67.7	72.9
80°	43.9	46.1	49.8	52.1
82.5°	29.8	30.5	32.0	33.5
85°	16.4	17.1	17.1	19.3
87.5°	6.7	7.4	7.4	8.2
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.2	40.3	45.4
97.5°	43.6	56.3	69.0	81.7
100°	59.8	81.1	102.3	123.6
102.5°	168.9	169.2	169.5	169.8
105°	226.3	221.7	217.0	212.4
107.5°	273.6	269.7	265.9	262.0
110°	319.2	316.0	312.7	309.5

TEST NUMBER: P1008115

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	362.6	359.8	357.0	354.2
115°	409.6	407.0	404.3	401.7
117.5°	452.2	449.1	446.0	442.9
120°	496.0	493.7	491.3	489.0
122.5°	535.6	533.1	530.6	528.1
125°	574.0	571.9	569.9	567.9
127.5°	610.8	608.6	606.5	604.3
130°	646.0	643.5	641.0	638.5
132.5°	679.5	677.4	675.4	673.4
135°	710.2	707.7	705.3	702.8
137.5°	739.1	737.2	735.4	733.5
140°	767.2	766.0	764.7	763.5
142.5°	792.0	790.9	789.8	788.7
145°	814.7	814.9	815.0	815.2
147.5°	836.9	837.4	837.8	838.3
150°	857.4	858.5	859.5	860.6
152.5°	875.8	877.0	878.3	879.5
155°	893.5	894.9	896.3	897.7
157.5°	908.6	909.8	911.1	912.3
160°	922.1	923.0	924.0	924.9
162.5°	933.3	934.2	935.2	936.1
165°	943.1	944.0	945.0	945.9
167.5°	950.8	951.7	952.7	953.6
170°	957.0	957.9	958.9	959.8
172.5°	961.2	962.1	963.1	964.0
175°	964.2	965.3	966.4	967.5
177.5°	965.6	966.7	967.8	968.9
180°	965.4	965.4	965.4	965.4

(END OF REPORT)