

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008118

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008118
REPORT IS A COMBINATION OF REPORTS P984311 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4776.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14729	14729	14729	14729
5°	14764	15704	14821	12495
10°	14593	17145	14684	10302
15°	14239	18083	14438	8678
20°	14017	16980	14017	7542
25°	13570	14587	13632	6745
30°	12836	11467	13081	6109
35°	12185	7929	12388	5590
40°	11435	5986	11567	5176
45°	10514	4919	10684	4727
50°	9716	4319	9733	4329
55°	8804	3679	8863	3893
60°	7835	3074	7944	3398
65°	6968	2499	7092	2902
70°	6102	1962	6258	2340
75°	5119	1424	5320	1698
80°	4000	902	4279	1007
85°	2627	454	2825	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15226 cd/sqm

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	1.9
10°-20°	258.0	5.4
20°-30°	374.4	7.8
30°-40°	394.7	8.3
40°-50°	349.2	7.3
50°-60°	278.9	5.8
60°-70°	189.4	4.0
70°-80°	96.9	2.0
80°-90°	24.5	0.5
90°-100°	30.6	0.6
100°-110°	114.1	2.4
110°-120°	302.6	6.3
120°-130°	501.9	10.5
130°-140°	533.2	11.2
140°-150°	495.5	10.4
150°-160°	398.4	8.3
160°-170°	256.7	5.4
170°-180°	88.4	1.8
0°-30°	721.0	15.1
0°-40°	1115.7	23.4
0°-60°	1743.8	36.5
0°-90°	2054.6	43.0
90°-120°	447.4	9.4
90°-150°	1977.9	41.4
90°-180°	2721.0	57.0
0°-180°	4776.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	931	1039	935	827	931	88
15°	875	1277	887	613	875	247
25°	786	1064	790	492	786	359
35°	642	579	652	408	642	401
45°	481	349	489	335	481	373
55°	330	245	333	260	330	295
65°	196	151	200	175	196	195
75°	92	74	95	89	92	98
85°	19	19	20	14	19	22
90°	1	18	1	18	1	4
95°	44	29	44	29	44	52
105°	204	51	204	51	204	218
115°	386	55	386	55	386	380
125°	546	574	546	574	546	487
135°	676	698	676	698	676	522
145°	784	796	784	796	784	490
155°	863	864	863	864	863	398
165°	910	907	910	907	910	257
175°	930	925	930	925	930	89
180°	928	928	928	928	928	

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	935.5	937.7	941.2	942.0	949.1	954.8	961.3	961.3	963.4	962.7	957.0
5°	931.2	937.7	947.0	954.8	967.7	973.4	982.0	988.4	994.2	998.5	997.7
7.5°	924.1	935.5	949.1	964.1	981.3	991.3	1003.5	1014.9	1022.8	1029.9	1034.9
10°	911.9	931.2	949.8	969.9	992.0	1005.6	1019.9	1034.9	1047.1	1060.7	1073.6
12.5°	895.5	923.4	946.3	972.7	999.9	1014.9	1037.8	1049.2	1072.8	1107.2	1116.5
15°	874.7	912.6	934.1	967.7	1003.5	1015.6	1047.1	1065.7	1114.3	1135.8	1161.5
17.5°	855.4	897.6	926.2	964.8	999.9	1023.5	1054.3	1092.2	1132.9	1163.7	1192.3
20°	839.7	880.4	914.8	957.7	1002.0	1032.1	1064.3	1110.0	1154.4	1185.9	1208.0
22.5°	803.9	856.1	896.2	944.1	997.7	1039.2	1070.0	1120.1	1168.0	1187.3	1206.6
25°	786.0	831.1	877.6	931.9	994.9	1044.2	1070.7	1126.5	1168.7	1175.8	1180.1
27.5°	753.1	803.9	858.3	920.5	994.2	1035.7	1069.3	1120.1	1153.7	1148.7	1135.8
30°	712.4	774.6	834.7	901.9	984.2	1029.2	1060.7	1107.2	1124.3	1098.6	1075.7
32.5°	682.3	741.0	807.5	885.5	972.7	1015.6	1046.4	1082.9	1086.4	1039.9	1001.3
35°	641.6	706.6	781.7	864.0	953.4	992.0	1020.6	1042.8	1025.6	960.6	914.8
37.5°	605.1	669.5	749.6	833.2	926.9	964.8	987.7	991.3	949.1	891.9	824.7
40°	565.0	631.5	715.2	803.2	897.6	930.5	944.8	934.1	873.3	806.8	728.8
42.5°	525.0	590.8	680.9	771.0	860.4	888.3	894.0	864.7	790.3	712.4	622.3
45°	481.4	550.0	640.1	731.0	817.5	833.2	834.0	791.8	703.8	622.3	538.6
47.5°	445.6	509.2	598.6	689.5	762.4	773.2	768.9	720.2	624.4	532.8	459.9
50°	406.3	467.0	555.7	645.1	707.4	710.2	699.5	630.1	536.4	452.7	394.8
52.5°	364.1	425.6	507.1	592.9	648.7	644.4	623.7	549.3	461.3	391.9	347.6
55°	330.4	384.8	461.3	545.0	584.3	572.2	549.3	473.5	404.1	345.5	306.8
57.5°	293.2	341.2	416.3	489.2	512.1	500.7	477.8	407.0	342.6	298.3	272.5
60°	258.2	301.8	367.6	428.4	446.3	434.1	407.7	344.0	297.5	260.3	241.0
62.5°	226.0	263.9	319.0	374.8	381.9	369.8	346.9	295.4	255.3	226.0	211.7
65°	196.0	231.7	276.1	318.3	324.7	311.8	288.2	251.0	217.4	198.8	185.2
67.5°	166.6	195.3	234.6	265.4	268.9	256.8	237.5	207.4	186.7	166.6	156.6
70°	140.9	162.4	193.1	218.1	219.6	208.1	198.1	170.9	155.2	140.9	133.0
72.5°	115.9	130.9	154.5	173.1	173.8	166.6	157.4	140.2	126.6	116.6	108.7
75°	91.5	104.4	118.7	135.2	134.5	128.7	121.6	110.9	99.4	93.0	89.4
77.5°	70.1	78.0	89.4	100.1	100.1	97.3	93.0	85.1	78.0	71.5	67.9
80°	50.1	55.1	64.4	67.9	69.4	68.7	65.1	59.4	56.5	51.5	50.1
82.5°	32.2	35.8	40.1	43.6	45.8	44.3	43.6	40.8	36.5	35.0	33.6
85°	18.6	20.0	22.2	24.3	25.0	24.3	25.7	23.6	21.5	21.5	20.7
87.5°	7.9	8.6	10.0	10.0	10.7	10.7	10.0	10.7	10.7	10.0	9.3
90°	0.7	2.3	4.0	5.6	7.3	8.1	8.7	9.9	11.0	12.2	13.4
92.5°	16.8	16.2	15.6	15.0	14.4	14.1	14.3	14.8	15.2	15.7	16.1
95°	43.7	38.8	33.8	28.9	24.0	21.5	22.0	23.1	24.1	25.2	26.2
97.5°	78.6	66.4	54.1	41.9	29.6	23.5	24.7	27.1	29.5	31.9	34.3
100°	118.9	98.5	78.0	57.6	37.1	26.9	28.2	30.7	33.2	35.8	38.3
102.5°	163.2	162.9	162.6	162.3	162.0	161.9	148.3	121.1	94.0	66.8	39.6
105°	204.2	208.7	213.1	217.6	222.1	224.3	203.9	163.2	122.5	81.7	41.0
107.5°	251.9	255.6	259.4	263.1	266.8	268.7	243.5	193.2	142.9	92.6	42.3
110°	297.6	300.7	303.9	307.0	310.1	311.7	290.1	247.0	203.8	160.7	117.5

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	340.5	343.2	345.9	348.6	351.3	352.6	351.3	348.8	346.3	343.7	341.2
115°	386.2	388.7	391.3	393.8	396.3	397.6	399.5	403.2	406.9	410.7	414.4
117.5°	425.8	428.8	431.8	434.8	437.8	439.3	440.6	443.1	445.6	448.2	450.7
120°	470.2	472.4	474.7	476.9	479.2	480.3	481.6	484.3	487.0	489.6	492.3
122.5°	507.8	510.2	512.6	514.9	517.3	518.5	520.0	523.0	526.0	529.0	532.0
125°	546.1	548.0	550.0	551.9	553.8	554.8	556.2	559.1	561.9	564.8	567.6
127.5°	581.0	583.1	585.2	587.3	589.4	590.4	591.5	593.8	596.0	598.3	600.5
130°	613.9	616.3	618.7	621.1	623.5	624.7	625.5	627.2	628.8	630.5	632.1
132.5°	647.5	649.4	651.4	653.3	655.2	656.2	657.0	658.7	660.3	662.0	663.6
135°	675.7	678.1	680.5	682.9	685.3	686.5	687.2	688.5	689.8	691.2	692.5
137.5°	705.3	707.1	708.9	710.6	712.4	713.3	714.0	715.5	717.0	718.5	720.0
140°	734.2	735.4	736.6	737.7	738.9	739.5	740.3	742.0	743.6	745.3	746.9
142.5°	758.3	759.3	760.4	761.4	762.5	763.0	764.0	765.9	767.9	769.8	771.8
145°	783.9	783.7	783.6	783.4	783.3	783.2	784.5	787.0	789.5	792.1	794.6
147.5°	806.0	805.6	805.1	804.7	804.2	804.0	805.3	807.8	810.3	812.9	815.4
150°	827.5	826.5	825.4	824.4	823.3	822.8	824.0	826.4	828.8	831.2	833.6
152.5°	845.7	844.5	843.3	842.1	840.9	840.3	841.4	843.7	845.9	848.2	850.4
155°	863.1	861.8	860.4	859.1	857.8	857.1	858.0	859.8	861.5	863.3	865.1
157.5°	877.2	876.0	874.8	873.6	872.4	871.8	872.5	873.8	875.2	876.5	877.9
160°	889.3	888.4	887.5	886.6	885.7	885.3	885.7	886.6	887.5	888.4	889.3
162.5°	900.1	899.2	898.3	897.4	896.5	896.0	896.4	897.1	897.9	898.6	899.4
165°	909.5	908.6	907.7	906.8	905.9	905.4	905.6	906.1	906.5	907.0	907.4
167.5°	916.9	916.0	915.1	914.2	913.3	912.8	913.0	913.5	913.9	914.4	914.8
170°	922.9	922.0	921.1	920.2	919.3	918.9	919.0	919.3	919.6	919.9	920.2
172.5°	926.9	926.0	925.1	924.2	923.3	922.9	923.0	923.3	923.6	923.9	924.2
175°	930.3	929.3	928.2	927.2	926.1	925.6	925.7	926.0	926.3	926.6	926.9
177.5°	931.6	930.6	929.5	928.5	927.4	926.9	927.0	927.1	927.3	927.4	927.6
180°	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	967.0	967.7	969.1	976.3	979.9	980.6	977.7	984.2	986.3	984.2	982.7
5°	1012.8	1017.1	1025.6	1034.9	1034.2	1034.9	1039.2	1043.5	1045.0	1039.2	1041.4
7.5°	1052.8	1061.4	1070.7	1085.0	1085.0	1092.2	1095.0	1098.6	1107.2	1102.9	1101.5
10°	1098.6	1110.0	1127.2	1150.1	1150.8	1158.0	1165.1	1176.6	1180.1	1177.3	1178.7
12.5°	1155.8	1178.0	1179.4	1204.4	1215.9	1217.3	1228.8	1226.6	1233.8	1233.8	1245.9
15°	1180.8	1215.2	1234.5	1258.8	1266.0	1257.4	1266.7	1276.7	1277.4	1277.4	1276.7
17.5°	1225.9	1239.5	1258.8	1271.7	1274.5	1274.5	1275.3	1279.5	1276.7	1271.0	1275.3
20°	1235.2	1240.9	1248.1	1246.6	1248.1	1240.9	1233.8	1226.6	1227.3	1223.8	1234.5
22.5°	1218.0	1216.6	1200.2	1189.4	1189.4	1175.1	1161.5	1155.1	1148.7	1150.8	1154.4
25°	1175.1	1153.0	1132.9	1117.2	1113.6	1090.7	1072.1	1066.4	1055.7	1064.3	1065.7
27.5°	1106.5	1081.4	1049.2	1035.7	1017.1	1007.8	994.9	977.7	955.5	968.4	966.3
30°	1032.8	995.6	969.1	936.2	906.9	904.8	880.4	851.8	840.4	840.4	846.8
32.5°	950.5	901.2	862.6	816.1	787.5	775.3	746.0	717.4	723.8	702.4	710.2
35°	854.7	789.6	741.0	695.9	674.5	660.2	622.3	606.5	589.4	579.3	597.9
37.5°	763.2	688.1	625.8	576.5	568.6	542.9	517.1	507.1	497.1	501.4	500.7
40°	651.6	585.1	529.3	490.6	477.1	464.9	447.7	435.6	429.1	432.7	433.4
42.5°	550.7	494.9	453.5	426.3	414.8	406.3	397.7	387.7	385.5	385.5	388.4
45°	472.8	427.0	399.1	376.9	370.5	364.1	357.6	353.3	351.9	349.0	351.2
47.5°	410.5	374.1	356.9	340.4	333.3	331.9	326.1	324.0	321.1	320.4	321.1
50°	358.3	335.4	319.7	310.4	305.4	303.3	300.4	296.1	294.7	298.3	296.8
52.5°	321.9	300.4	291.8	282.5	279.7	276.8	272.5	273.2	272.5	271.1	271.1
55°	285.4	271.8	263.2	256.1	255.3	252.5	248.9	247.5	246.8	245.3	247.5
57.5°	256.1	245.3	237.5	231.0	228.2	228.2	224.6	221.7	221.7	221.0	221.7
60°	226.7	216.0	211.0	204.6	202.4	201.7	199.5	198.1	196.0	196.0	196.0
62.5°	199.5	191.0	185.2	179.5	180.2	176.7	173.8	172.4	172.4	173.1	173.1
65°	173.8	168.1	160.9	155.9	154.5	153.8	152.3	151.6	149.5	150.9	150.9
67.5°	150.2	142.3	138.0	135.9	133.7	133.0	131.6	130.2	129.5	128.7	130.2
70°	126.6	120.2	116.6	115.2	113.0	112.3	111.6	109.4	110.1	110.9	111.6
72.5°	105.1	99.4	98.7	94.4	94.4	94.4	91.5	93.0	92.3	90.8	92.3
75°	83.0	80.1	78.7	76.5	77.2	76.5	75.8	73.7	73.7	74.4	75.1
77.5°	65.8	62.9	62.2	60.1	58.6	60.1	58.6	57.9	57.9	58.6	58.6
80°	48.6	47.2	45.1	45.1	45.1	44.3	44.3	44.3	43.6	42.9	43.6
82.5°	32.2	32.2	31.5	30.8	31.5	30.0	30.8	30.8	30.8	30.8	30.8
85°	20.7	20.0	20.0	19.3	19.3	19.3	20.0	18.6	18.6	19.3	19.3
87.5°	9.3	9.3	9.3	10.0	9.3	9.3	9.3	10.0	9.3	9.3	9.3
90°	14.2	14.9	15.7	16.4	16.8	16.9	17.2	17.5	17.8	18.1	17.8
92.5°	16.4	16.7	17.0	17.3	17.5	17.6	17.7	17.8	18.0	18.1	18.0
95°	27.0	27.7	28.5	29.2	29.6	29.5	29.4	29.2	29.1	28.9	29.1
97.5°	34.7	35.2	35.6	36.1	36.3	36.4	36.5	36.6	36.8	36.9	36.8
100°	39.5	40.7	41.9	43.1	43.7	43.8	44.1	44.4	44.7	45.0	44.7
102.5°	41.2	42.9	44.5	46.2	47.0	47.2	47.7	48.1	48.6	49.0	48.6
105°	42.6	44.3	45.9	47.6	48.4	48.7	49.3	49.8	50.4	51.0	50.4
107.5°	43.9	45.6	47.2	48.9	49.7	50.0	50.6	51.2	51.8	52.4	51.8
110°	102.6	87.7	72.8	57.9	50.4	50.7	51.3	51.9	52.5	53.1	52.5

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	276.9	212.5	148.2	83.9	51.7	51.9	52.4	52.8	53.3	53.7	53.3
115°	345.3	276.2	207.1	138.0	103.4	98.0	87.3	76.6	65.8	55.1	65.8
117.5°	429.4	408.0	386.7	365.4	354.7	335.1	296.0	256.9	217.8	178.7	217.8
120°	494.1	495.9	497.7	499.5	500.4	490.3	470.2	450.0	429.9	409.7	429.9
122.5°	532.9	533.8	534.7	535.6	536.0	536.1	536.2	536.4	536.5	536.7	536.5
125°	568.6	569.7	570.7	571.8	572.3	572.5	573.0	573.4	573.9	574.3	573.9
127.5°	602.0	603.5	605.0	606.5	607.2	607.3	607.4	607.6	607.7	607.9	607.7
130°	633.7	635.3	637.0	638.6	639.4	639.3	639.2	639.1	638.9	638.8	638.9
132.5°	665.0	666.3	667.7	669.0	669.7	669.6	669.5	669.3	669.2	669.0	669.2
135°	694.0	695.5	697.0	698.5	699.2	699.1	698.8	698.5	698.2	697.9	698.2
137.5°	721.5	723.0	724.5	726.0	726.8	726.6	726.1	725.7	725.2	724.8	725.2
140°	748.3	749.6	751.0	752.3	753.0	752.6	751.9	751.1	750.4	749.6	750.4
142.5°	773.0	774.2	775.3	776.5	777.1	776.7	776.0	775.3	774.5	773.8	774.5
145°	795.6	796.7	797.7	798.8	799.3	798.9	798.2	797.4	796.7	795.9	796.7
147.5°	816.2	816.9	817.7	818.4	818.8	818.5	817.9	817.3	816.7	816.1	816.7
150°	834.5	835.4	836.3	837.2	837.6	837.2	836.5	835.7	835.0	834.2	835.0
152.5°	851.3	852.2	853.1	854.0	854.4	853.9	852.8	851.8	850.7	849.7	850.7
155°	866.0	866.9	867.8	868.7	869.2	868.6	867.4	866.2	865.0	863.8	865.0
157.5°	878.9	880.0	881.0	882.1	882.6	882.0	880.8	879.6	878.4	877.2	878.4
160°	890.2	891.1	892.0	892.9	893.3	892.8	891.7	890.7	889.6	888.6	889.6
162.5°	900.4	901.5	902.5	903.6	904.1	903.4	902.1	900.7	899.4	898.0	899.4
165°	908.5	909.5	910.6	911.7	912.2	911.7	910.6	909.5	908.5	907.4	908.5
167.5°	915.8	916.9	917.9	919.0	919.5	918.8	917.5	916.2	914.8	913.5	914.8
170°	921.2	922.3	923.3	924.4	924.9	924.2	922.9	921.6	920.2	918.9	920.2
172.5°	925.2	926.3	927.3	928.4	928.9	928.2	926.9	925.6	924.2	922.9	924.2
175°	927.9	929.0	930.0	931.1	931.6	930.9	929.4	927.9	926.4	924.9	926.4
177.5°	928.6	929.7	930.7	931.8	932.3	931.6	930.3	929.0	927.6	926.3	927.6
180°	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	986.3	981.3	977.0	977.7	981.3	978.4	971.3	962.0	958.4	954.1	958.4
5°	1045.7	1041.4	1032.8	1033.5	1031.4	1028.5	1017.1	1002.8	1002.8	991.3	989.9
7.5°	1104.3	1097.9	1092.2	1090.7	1082.9	1077.1	1067.1	1047.1	1039.2	1025.6	1017.8
10°	1170.1	1165.1	1158.7	1150.8	1146.5	1136.5	1120.1	1090.7	1076.4	1057.8	1044.2
12.5°	1236.6	1235.9	1221.6	1205.9	1205.2	1189.4	1178.0	1138.6	1119.3	1094.3	1062.1
15°	1278.8	1275.3	1267.4	1259.5	1261.7	1244.5	1218.8	1172.3	1159.4	1129.3	1095.0
17.5°	1278.1	1278.1	1276.0	1274.5	1272.4	1267.4	1253.1	1222.3	1201.6	1163.7	1131.5
20°	1237.3	1246.6	1248.8	1248.1	1255.2	1258.8	1258.1	1238.8	1222.3	1188.7	1155.8
22.5°	1155.8	1177.3	1186.6	1192.3	1207.3	1215.2	1233.8	1226.6	1222.3	1197.3	1169.4
25°	1080.0	1087.2	1115.0	1116.5	1137.2	1156.5	1175.1	1187.3	1203.0	1193.7	1170.1
27.5°	982.0	998.5	1018.5	1033.5	1037.8	1077.1	1107.9	1130.8	1166.5	1169.4	1161.5
30°	871.2	879.0	911.9	931.9	954.8	983.4	1027.8	1067.1	1099.3	1128.6	1138.6
32.5°	736.0	768.2	787.5	811.8	831.8	882.6	937.0	987.7	1024.9	1074.3	1095.7
35°	612.2	637.3	670.2	680.2	716.7	759.6	830.4	895.5	952.0	1002.0	1045.7
37.5°	510.0	530.0	565.0	580.8	602.2	657.3	716.7	797.5	865.4	926.9	981.3
40°	439.9	454.9	481.4	486.4	504.2	554.3	602.2	678.0	768.2	851.1	910.5
42.5°	391.9	399.1	417.0	423.4	434.9	468.5	511.4	582.9	666.6	752.4	836.1
45°	357.6	362.6	373.4	379.1	393.4	408.4	443.4	500.7	566.5	653.0	743.1
47.5°	326.9	333.3	337.6	341.2	349.0	365.5	388.4	430.6	493.5	572.9	660.2
50°	301.1	303.3	311.1	311.8	316.8	327.6	349.0	374.8	424.8	489.2	573.6
52.5°	275.4	277.5	282.5	287.5	289.7	298.3	312.6	334.0	371.2	422.0	497.1
55°	249.6	252.5	257.5	261.1	263.2	270.4	278.9	299.7	329.0	364.8	426.3
57.5°	223.9	230.3	231.7	233.9	237.5	245.3	253.2	265.4	288.2	321.1	366.2
60°	199.5	201.7	206.7	208.8	212.4	216.7	226.7	236.0	252.5	278.2	319.0
62.5°	174.5	179.5	181.7	183.8	186.7	191.7	198.1	208.1	222.4	243.2	275.4
65°	153.1	153.8	158.1	160.9	163.8	167.4	173.8	183.1	191.7	211.0	234.6
67.5°	132.3	133.7	135.2	138.0	141.6	145.2	150.9	155.9	166.6	179.5	198.1
70°	112.3	112.3	115.9	118.0	117.3	121.6	125.9	131.6	139.5	151.6	166.6
72.5°	94.4	93.7	96.6	97.3	98.7	101.6	104.4	110.1	114.4	123.7	135.2
75°	75.1	76.5	78.0	78.0	80.1	82.3	85.1	88.0	93.0	98.7	107.3
77.5°	59.4	59.4	60.8	61.5	63.7	62.9	65.8	68.7	72.2	77.2	83.7
80°	43.6	45.1	45.1	45.1	45.8	46.5	49.4	51.5	53.6	57.2	60.1
82.5°	30.8	30.8	32.2	32.2	32.2	33.6	33.6	34.3	35.8	37.9	40.1
85°	19.3	19.3	19.3	20.0	19.3	20.0	21.5	20.7	21.5	22.9	22.9
87.5°	9.3	9.3	9.3	9.3	9.3	10.0	9.3	10.0	10.7	10.7	10.7
90°	17.5	17.2	16.9	16.8	16.4	15.7	14.9	14.2	13.4	12.2	11.0
92.5°	17.8	17.7	17.6	17.5	17.3	17.0	16.7	16.4	16.1	15.7	15.2
95°	29.2	29.4	29.5	29.6	29.2	28.5	27.7	27.0	26.2	25.2	24.1
97.5°	36.6	36.5	36.4	36.3	36.1	35.6	35.2	34.7	34.3	31.9	29.5
100°	44.4	44.1	43.8	43.7	43.1	41.9	40.7	39.5	38.3	35.8	33.2
102.5°	48.1	47.7	47.2	47.0	46.2	44.5	42.9	41.2	39.6	66.8	94.0
105°	49.8	49.3	48.7	48.4	47.6	45.9	44.3	42.6	41.0	81.7	122.5
107.5°	51.2	50.6	50.0	49.7	48.9	47.2	45.6	43.9	42.3	92.6	142.9
110°	51.9	51.3	50.7	50.4	57.9	72.8	87.7	102.6	117.5	160.7	203.8

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	52.8	52.4	51.9	51.7	83.9	148.2	212.5	276.9	341.2	343.7	346.3
115°	76.6	87.3	98.0	103.4	138.0	207.1	276.2	345.3	414.4	410.7	406.9
117.5°	256.9	296.0	335.1	354.7	365.4	386.7	408.0	429.4	450.7	448.2	445.6
120°	450.0	470.2	490.3	500.4	499.5	497.7	495.9	494.1	492.3	489.6	487.0
122.5°	536.4	536.2	536.1	536.0	535.6	534.7	533.8	532.9	532.0	529.0	526.0
125°	573.4	573.0	572.5	572.3	571.8	570.7	569.7	568.6	567.6	564.8	561.9
127.5°	607.6	607.4	607.3	607.2	606.5	605.0	603.5	602.0	600.5	598.3	596.0
130°	639.1	639.2	639.3	639.4	638.6	637.0	635.3	633.7	632.1	630.5	628.8
132.5°	669.3	669.5	669.6	669.7	669.0	667.7	666.3	665.0	663.6	662.0	660.3
135°	698.5	698.8	699.1	699.2	698.5	697.0	695.5	694.0	692.5	691.2	689.8
137.5°	725.7	726.1	726.6	726.8	726.0	724.5	723.0	721.5	720.0	718.5	717.0
140°	751.1	751.9	752.6	753.0	752.3	751.0	749.6	748.3	746.9	745.3	743.6
142.5°	775.3	776.0	776.7	777.1	776.5	775.3	774.2	773.0	771.8	769.8	767.9
145°	797.4	798.2	798.9	799.3	798.8	797.7	796.7	795.6	794.6	792.1	789.5
147.5°	817.3	817.9	818.5	818.8	818.4	817.7	816.9	816.2	815.4	812.9	810.3
150°	835.7	836.5	837.2	837.6	837.2	836.3	835.4	834.5	833.6	831.2	828.8
152.5°	851.8	852.8	853.9	854.4	854.0	853.1	852.2	851.3	850.4	848.2	845.9
155°	866.2	867.4	868.6	869.2	868.7	867.8	866.9	866.0	865.1	863.3	861.5
157.5°	879.6	880.8	882.0	882.6	882.1	881.0	880.0	878.9	877.9	876.5	875.2
160°	890.7	891.7	892.8	893.3	892.9	892.0	891.1	890.2	889.3	888.4	887.5
162.5°	900.7	902.1	903.4	904.1	903.6	902.5	901.5	900.4	899.4	898.6	897.9
165°	909.5	910.6	911.7	912.2	911.7	910.6	909.5	908.5	907.4	907.0	906.5
167.5°	916.2	917.5	918.8	919.5	919.0	917.9	916.9	915.8	914.8	914.4	913.9
170°	921.6	922.9	924.2	924.9	924.4	923.3	922.3	921.2	920.2	919.9	919.6
172.5°	925.6	926.9	928.2	928.9	928.4	927.3	926.3	925.2	924.2	923.9	923.6
175°	927.9	929.4	930.9	931.6	931.1	930.0	929.0	927.9	926.9	926.6	926.3
177.5°	929.0	930.3	931.6	932.3	931.8	930.7	929.7	928.6	927.6	927.4	927.3
180°	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	954.8	951.3	949.1	950.5	946.3	935.5	935.5	939.1	934.8	930.5	924.1
5°	981.3	974.1	969.9	969.1	959.1	942.0	938.4	934.8	925.5	915.5	904.8
7.5°	1007.0	994.2	987.0	982.0	967.7	945.5	936.2	928.4	913.3	898.3	884.7
10°	1028.5	1009.9	1001.3	993.5	974.9	947.0	931.9	917.6	898.3	879.0	861.9
12.5°	1045.7	1024.2	1013.5	1002.0	979.2	942.7	924.1	901.2	881.9	856.1	839.0
15°	1074.3	1029.9	1019.9	1009.2	985.6	935.5	912.6	886.9	860.4	826.1	807.5
17.5°	1097.2	1037.8	1037.1	1014.2	983.4	932.7	897.6	864.0	835.4	801.1	771.7
20°	1110.8	1050.0	1038.5	1014.9	976.3	913.3	876.9	839.7	808.9	767.4	738.1
22.5°	1122.2	1067.1	1037.1	1008.5	961.3	906.9	853.3	818.2	776.0	731.0	703.1
25°	1126.5	1070.7	1039.2	1006.3	950.5	888.3	827.5	789.6	742.4	701.6	663.7
27.5°	1127.2	1070.0	1031.4	997.0	935.5	864.0	801.8	761.7	709.5	662.3	624.4
30°	1120.1	1062.1	1027.1	989.9	921.2	841.8	770.3	726.0	670.2	623.0	583.6
32.5°	1098.6	1046.4	1017.8	977.0	902.6	811.1	740.3	690.9	632.3	585.8	547.9
35°	1062.8	1027.1	995.6	957.7	878.3	782.5	710.2	652.3	592.9	548.6	512.8
37.5°	1018.5	999.2	969.9	932.7	850.4	756.7	676.6	612.2	552.9	510.0	474.9
40°	958.4	963.4	934.8	901.2	817.5	721.7	633.0	571.5	515.7	475.6	441.3
42.5°	893.3	914.1	897.6	865.4	781.0	683.0	600.8	532.8	478.5	437.0	408.4
45°	823.2	859.0	849.0	825.4	743.1	642.3	555.0	489.2	441.3	401.2	376.2
47.5°	746.7	797.5	797.5	780.3	700.9	601.5	515.7	448.4	401.2	372.6	348.3
50°	668.7	726.0	735.3	723.8	653.7	555.0	467.8	407.0	366.2	338.3	320.4
52.5°	587.2	653.7	670.9	665.2	603.7	510.7	428.4	369.1	331.9	307.5	291.8
55°	509.2	586.5	605.1	607.2	550.0	462.0	384.8	332.6	296.8	280.4	266.8
57.5°	435.6	510.0	530.7	534.3	495.7	417.7	344.0	298.3	266.1	252.5	241.7
60°	372.6	434.9	462.0	469.9	436.3	366.2	306.1	261.8	237.5	224.6	214.6
62.5°	321.1	371.2	399.8	402.0	386.9	321.1	266.8	229.6	208.8	197.4	192.4
65°	271.1	316.1	333.3	341.9	329.7	278.2	230.3	199.5	183.1	173.1	168.1
67.5°	231.0	259.6	273.9	285.4	273.2	234.6	196.0	170.9	158.8	148.8	145.9
70°	189.5	213.1	223.9	235.3	224.6	195.3	167.4	144.5	133.7	125.9	122.3
72.5°	151.6	170.2	180.2	187.4	181.0	156.6	133.7	118.0	110.1	104.4	102.3
75°	120.2	133.0	138.8	143.8	140.9	122.3	108.0	95.1	88.0	83.0	81.5
77.5°	91.5	100.8	107.3	108.7	105.1	93.0	80.8	73.0	67.2	64.4	62.9
80°	65.1	70.8	74.4	76.5	73.0	67.9	59.4	53.6	48.6	45.1	44.3
82.5°	43.6	46.5	49.4	48.6	47.2	42.9	37.9	35.0	32.9	30.0	30.0
85°	25.0	25.7	27.2	27.9	27.2	24.3	21.5	20.0	18.6	16.5	16.5
87.5°	10.7	11.4	11.4	12.2	10.7	10.7	9.3	7.9	7.9	7.2	6.4
90°	9.9	8.7	8.1	7.3	5.6	4.0	2.3	0.7	2.3	4.0	5.6
92.5°	14.8	14.3	14.1	14.4	15.0	15.6	16.2	16.8	16.2	15.6	15.0
95°	23.1	22.0	21.5	24.0	28.9	33.8	38.8	43.7	38.8	33.8	28.9
97.5°	27.1	24.7	23.5	29.6	41.9	54.1	66.4	78.6	66.4	54.1	41.9
100°	30.7	28.2	26.9	37.1	57.6	78.0	98.5	118.9	98.5	78.0	57.6
102.5°	121.1	148.3	161.9	162.0	162.3	162.6	162.9	163.2	162.9	162.6	162.3
105°	163.2	203.9	224.3	222.1	217.6	213.1	208.7	204.2	208.7	213.1	217.6
107.5°	193.2	243.5	268.7	266.8	263.1	259.4	255.6	251.9	255.6	259.4	263.1
110°	247.0	290.1	311.7	310.1	307.0	303.9	300.7	297.6	300.7	303.9	307.0

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	348.8	351.3	352.6	351.3	348.6	345.9	343.2	340.5	343.2	345.9	348.6
115°	403.2	399.5	397.6	396.3	393.8	391.3	388.7	386.2	388.7	391.3	393.8
117.5°	443.1	440.6	439.3	437.8	434.8	431.8	428.8	425.8	428.8	431.8	434.8
120°	484.3	481.6	480.3	479.2	476.9	474.7	472.4	470.2	472.4	474.7	476.9
122.5°	523.0	520.0	518.5	517.3	514.9	512.6	510.2	507.8	510.2	512.6	514.9
125°	559.1	556.2	554.8	553.8	551.9	550.0	548.0	546.1	548.0	550.0	551.9
127.5°	593.8	591.5	590.4	589.4	587.3	585.2	583.1	581.0	583.1	585.2	587.3
130°	627.2	625.5	624.7	623.5	621.1	618.7	616.3	613.9	616.3	618.7	621.1
132.5°	658.7	657.0	656.2	655.2	653.3	651.4	649.4	647.5	649.4	651.4	653.3
135°	688.5	687.2	686.5	685.3	682.9	680.5	678.1	675.7	678.1	680.5	682.9
137.5°	715.5	714.0	713.3	712.4	710.6	708.9	707.1	705.3	707.1	708.9	710.6
140°	742.0	740.3	739.5	738.9	737.7	736.6	735.4	734.2	735.4	736.6	737.7
142.5°	765.9	764.0	763.0	762.5	761.4	760.4	759.3	758.3	759.3	760.4	761.4
145°	787.0	784.5	783.2	783.3	783.4	783.6	783.7	783.9	783.7	783.6	783.4
147.5°	807.8	805.3	804.0	804.2	804.7	805.1	805.6	806.0	805.6	805.1	804.7
150°	826.4	824.0	822.8	823.3	824.4	825.4	826.5	827.5	826.5	825.4	824.4
152.5°	843.7	841.4	840.3	840.9	842.1	843.3	844.5	845.7	844.5	843.3	842.1
155°	859.8	858.0	857.1	857.8	859.1	860.4	861.8	863.1	861.8	860.4	859.1
157.5°	873.8	872.5	871.8	872.4	873.6	874.8	876.0	877.2	876.0	874.8	873.6
160°	886.6	885.7	885.3	885.7	886.6	887.5	888.4	889.3	888.4	887.5	886.6
162.5°	897.1	896.4	896.0	896.5	897.4	898.3	899.2	900.1	899.2	898.3	897.4
165°	906.1	905.6	905.4	905.9	906.8	907.7	908.6	909.5	908.6	907.7	906.8
167.5°	913.5	913.0	912.8	913.3	914.2	915.1	916.0	916.9	916.0	915.1	914.2
170°	919.3	919.0	918.9	919.3	920.2	921.1	922.0	922.9	922.0	921.1	920.2
172.5°	923.3	923.0	922.9	923.3	924.2	925.1	926.0	926.9	926.0	925.1	924.2
175°	926.0	925.7	925.6	926.1	927.2	928.2	929.3	930.3	929.3	928.2	927.2
177.5°	927.1	927.0	926.9	927.4	928.5	929.5	930.6	931.6	930.6	929.5	928.5
180°	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	920.5	924.1	923.4	916.2	908.3	901.9	889.7	891.2	886.9	887.6	891.9
5°	897.6	897.6	894.8	884.7	871.9	864.7	851.1	847.5	839.0	838.3	837.5
7.5°	873.3	869.7	866.1	851.8	836.1	824.7	806.1	801.8	793.2	787.5	784.6
10°	844.7	839.7	832.5	816.1	796.8	782.5	763.2	757.4	741.0	733.8	729.5
12.5°	813.2	810.4	798.9	785.3	753.9	738.1	710.2	715.9	699.5	685.2	683.0
15°	781.7	771.0	764.6	742.4	704.5	697.3	675.2	663.7	648.7	637.3	637.3
17.5°	751.0	734.5	720.2	696.6	668.7	648.7	632.3	626.5	607.9	596.5	594.4
20°	710.2	691.6	688.1	654.4	635.1	613.0	597.2	582.9	569.3	564.3	560.7
22.5°	671.6	650.1	644.4	615.8	596.5	574.3	558.6	548.6	538.6	535.0	528.6
25°	630.1	617.2	608.7	577.9	556.4	535.7	525.0	517.8	508.5	507.8	503.5
27.5°	590.1	577.9	569.3	540.0	524.3	505.0	496.4	488.5	483.5	481.4	479.2
30°	555.7	542.1	532.1	510.7	491.4	475.6	468.5	463.5	460.6	457.0	456.3
32.5°	517.8	510.0	496.4	479.9	464.9	449.9	445.6	442.0	437.7	436.3	435.6
35°	485.6	474.9	466.3	447.7	441.3	428.4	423.4	420.6	414.8	413.4	412.0
37.5°	454.2	444.2	434.9	423.4	411.3	404.1	401.2	397.0	394.1	394.8	393.4
40°	422.7	414.8	407.7	395.5	388.4	384.8	379.1	374.8	373.4	374.1	373.4
42.5°	391.9	384.8	380.5	371.2	364.1	360.5	356.9	352.6	354.8	354.8	356.9
45°	364.1	357.6	354.8	347.6	343.3	337.6	334.0	333.3	336.2	335.4	335.4
47.5°	335.4	333.3	329.7	323.3	317.6	314.0	313.3	313.3	316.1	317.6	316.8
50°	313.3	309.0	304.7	299.7	295.4	294.0	291.8	293.2	296.1	296.1	297.5
52.5°	285.4	282.5	281.1	276.8	273.9	273.9	273.9	274.6	276.8	278.9	278.2
55°	261.1	258.9	257.5	255.3	251.8	252.5	251.8	253.2	255.3	257.5	258.9
57.5°	235.3	234.6	233.2	229.6	229.6	228.9	231.0	231.7	235.3	236.7	238.9
60°	212.4	210.3	210.3	207.4	207.4	207.4	209.6	211.7	214.6	215.3	216.7
62.5°	188.1	188.1	187.4	185.2	185.2	187.4	188.1	191.0	192.4	192.4	194.5
65°	165.2	164.5	163.8	164.5	165.2	165.2	167.4	168.8	170.2	170.9	171.7
67.5°	142.3	141.6	143.0	142.3	143.8	146.6	145.9	148.1	150.2	150.2	150.9
70°	120.9	122.3	121.6	123.0	122.3	123.7	125.9	126.6	126.6	127.3	129.5
72.5°	100.8	100.8	100.8	100.1	100.8	102.3	103.7	104.4	105.9	106.6	108.7
75°	81.5	81.5	80.1	81.5	81.5	83.0	84.4	84.4	84.4	85.8	88.0
77.5°	61.5	62.2	61.5	62.9	62.9	63.7	65.1	64.4	65.8	66.5	67.2
80°	45.1	44.3	44.3	44.3	45.1	45.1	46.5	47.2	47.2	49.4	47.9
82.5°	28.6	29.3	28.6	29.3	29.3	30.0	29.3	30.0	30.8	32.2	31.5
85°	16.5	15.7	15.7	16.5	15.7	15.7	16.5	15.7	16.5	15.7	16.5
87.5°	6.4	5.7	5.7	5.7	5.7	5.0	5.0	4.3	4.3	4.3	3.6
90°	7.3	8.1	8.7	9.9	11.0	12.2	13.4	14.2	14.9	15.7	16.4
92.5°	14.4	14.1	14.3	14.8	15.2	15.7	16.1	16.4	16.7	17.0	17.3
95°	24.0	21.5	22.0	23.1	24.1	25.2	26.2	27.0	27.7	28.5	29.2
97.5°	29.6	23.5	24.7	27.1	29.5	31.9	34.3	34.7	35.2	35.6	36.1
100°	37.1	26.9	28.2	30.7	33.2	35.8	38.3	39.5	40.7	41.9	43.1
102.5°	162.0	161.9	148.3	121.1	94.0	66.8	39.6	41.2	42.9	44.5	46.2
105°	222.1	224.3	203.9	163.2	122.5	81.7	41.0	42.6	44.3	45.9	47.6
107.5°	266.8	268.7	243.5	193.2	142.9	92.6	42.3	43.9	45.6	47.2	48.9
110°	310.1	311.7	290.1	247.0	203.8	160.7	117.5	102.6	87.7	72.8	57.9

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	351.3	352.6	351.3	348.8	346.3	343.7	341.2	276.9	212.5	148.2	83.9
115°	396.3	397.6	399.5	403.2	406.9	410.7	414.4	345.3	276.2	207.1	138.0
117.5°	437.8	439.3	440.6	443.1	445.6	448.2	450.7	429.4	408.0	386.7	365.4
120°	479.2	480.3	481.6	484.3	487.0	489.6	492.3	494.1	495.9	497.7	499.5
122.5°	517.3	518.5	520.0	523.0	526.0	529.0	532.0	532.9	533.8	534.7	535.6
125°	553.8	554.8	556.2	559.1	561.9	564.8	567.6	568.6	569.7	570.7	571.8
127.5°	589.4	590.4	591.5	593.8	596.0	598.3	600.5	602.0	603.5	605.0	606.5
130°	623.5	624.7	625.5	627.2	628.8	630.5	632.1	633.7	635.3	637.0	638.6
132.5°	655.2	656.2	657.0	658.7	660.3	662.0	663.6	665.0	666.3	667.7	669.0
135°	685.3	686.5	687.2	688.5	689.8	691.2	692.5	694.0	695.5	697.0	698.5
137.5°	712.4	713.3	714.0	715.5	717.0	718.5	720.0	721.5	723.0	724.5	726.0
140°	738.9	739.5	740.3	742.0	743.6	745.3	746.9	748.3	749.6	751.0	752.3
142.5°	762.5	763.0	764.0	765.9	767.9	769.8	771.8	773.0	774.2	775.3	776.5
145°	783.3	783.2	784.5	787.0	789.5	792.1	794.6	795.6	796.7	797.7	798.8
147.5°	804.2	804.0	805.3	807.8	810.3	812.9	815.4	816.2	816.9	817.7	818.4
150°	823.3	822.8	824.0	826.4	828.8	831.2	833.6	834.5	835.4	836.3	837.2
152.5°	840.9	840.3	841.4	843.7	845.9	848.2	850.4	851.3	852.2	853.1	854.0
155°	857.8	857.1	858.0	859.8	861.5	863.3	865.1	866.0	866.9	867.8	868.7
157.5°	872.4	871.8	872.5	873.8	875.2	876.5	877.9	878.9	880.0	881.0	882.1
160°	885.7	885.3	885.7	886.6	887.5	888.4	889.3	890.2	891.1	892.0	892.9
162.5°	896.5	896.0	896.4	897.1	897.9	898.6	899.4	900.4	901.5	902.5	903.6
165°	905.9	905.4	905.6	906.1	906.5	907.0	907.4	908.5	909.5	910.6	911.7
167.5°	913.3	912.8	913.0	913.5	913.9	914.4	914.8	915.8	916.9	917.9	919.0
170°	919.3	918.9	919.0	919.3	919.6	919.9	920.2	921.2	922.3	923.3	924.4
172.5°	923.3	922.9	923.0	923.3	923.6	923.9	924.2	925.2	926.3	927.3	928.4
175°	926.1	925.6	925.7	926.0	926.3	926.6	926.9	927.9	929.0	930.0	931.1
177.5°	927.4	926.9	927.0	927.1	927.3	927.4	927.6	928.6	929.7	930.7	931.8
180°	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	886.9	889.0	884.0	882.6	884.0	879.0	880.4	881.9	881.9	884.0	885.5
5°	835.4	832.5	827.5	826.1	824.7	826.8	825.4	827.5	828.2	833.2	834.0
7.5°	784.6	780.3	776.0	771.7	770.3	766.7	770.3	770.3	775.3	773.9	777.5
10°	724.5	723.8	718.1	715.9	713.1	707.4	715.2	713.1	716.7	723.1	724.5
12.5°	680.2	672.3	675.9	665.9	669.5	663.7	664.4	664.4	670.2	670.9	669.5
15°	638.0	631.5	622.3	618.0	615.8	613.0	622.3	623.0	618.7	628.7	625.1
17.5°	595.1	595.1	586.5	584.3	578.6	581.5	580.1	580.8	579.3	586.5	590.1
20°	557.9	554.3	551.4	552.2	545.0	543.6	542.1	543.6	548.6	553.6	555.0
22.5°	527.8	525.7	518.5	520.0	514.3	516.4	515.0	518.5	519.3	519.3	524.3
25°	499.2	496.4	497.1	494.2	492.1	492.1	489.9	492.1	494.9	496.4	497.1
27.5°	477.8	475.6	472.1	469.9	471.3	467.8	470.6	472.8	472.8	471.3	472.8
30°	452.0	453.5	453.5	446.3	449.2	447.7	449.9	451.3	451.3	452.0	450.6
32.5°	434.9	430.6	429.9	429.1	429.1	426.3	426.3	428.4	429.1	429.9	432.0
35°	412.0	412.0	408.4	410.5	407.7	408.4	407.7	408.4	409.8	407.7	409.8
37.5°	391.2	391.9	390.5	391.9	392.7	391.2	389.8	392.7	391.2	391.2	389.8
40°	373.4	372.6	373.4	373.4	373.4	374.1	372.6	372.6	372.6	371.2	369.8
42.5°	358.3	354.0	355.5	356.2	354.0	354.0	354.8	354.0	356.2	351.9	351.9
45°	336.9	335.4	336.2	336.2	337.6	335.4	336.9	337.6	335.4	334.7	333.3
47.5°	317.6	319.0	317.6	319.0	319.0	320.4	317.6	318.3	319.0	316.1	314.0
50°	298.3	298.3	300.4	299.7	300.4	299.0	299.0	298.3	299.0	297.5	295.4
52.5°	280.4	278.2	281.8	281.1	280.4	279.7	278.9	279.7	278.2	276.8	276.8
55°	258.2	258.2	260.3	261.1	261.1	259.6	258.2	258.9	258.2	257.5	256.8
57.5°	240.3	237.5	238.9	239.6	239.6	237.5	238.9	237.5	237.5	238.2	236.0
60°	217.4	217.4	216.0	218.1	218.1	216.7	216.7	217.4	216.0	215.3	214.6
62.5°	193.1	193.8	196.0	196.7	197.4	196.0	194.5	195.3	195.3	193.1	193.8
65°	172.4	173.8	176.7	175.9	174.5	175.2	173.8	174.5	172.4	173.1	170.9
67.5°	152.3	151.6	152.3	152.3	153.8	153.1	151.6	151.6	150.9	153.1	150.9
70°	130.9	130.9	130.9	130.9	131.6	132.3	130.9	129.5	130.2	128.7	128.0
72.5°	108.7	109.4	108.7	110.1	108.0	109.4	109.4	108.7	108.0	108.0	108.0
75°	88.0	89.4	87.3	88.0	87.3	88.7	88.0	88.0	86.5	85.8	86.5
77.5°	67.2	67.9	66.5	67.2	66.5	67.2	67.2	66.5	66.5	66.5	66.5
80°	47.9	48.6	47.9	47.2	46.5	47.9	46.5	47.2	47.9	47.2	48.6
82.5°	30.8	30.8	30.0	30.8	29.3	29.3	30.0	30.0	29.3	30.8	29.3
85°	15.0	15.0	16.5	15.0	14.3	14.3	14.3	15.0	14.3	15.7	15.0
87.5°	3.6	2.9	3.6	3.6	2.9	2.9	3.6	2.9	3.6	4.3	2.9
90°	16.8	16.9	17.2	17.5	17.8	18.1	17.8	17.5	17.2	16.9	16.8
92.5°	17.5	17.6	17.7	17.8	18.0	18.1	18.0	17.8	17.7	17.6	17.5
95°	29.6	29.5	29.4	29.2	29.1	28.9	29.1	29.2	29.4	29.5	29.6
97.5°	36.3	36.4	36.5	36.6	36.8	36.9	36.8	36.6	36.5	36.4	36.3
100°	43.7	43.8	44.1	44.4	44.7	45.0	44.7	44.4	44.1	43.8	43.7
102.5°	47.0	47.2	47.7	48.1	48.6	49.0	48.6	48.1	47.7	47.2	47.0
105°	48.4	48.7	49.3	49.8	50.4	51.0	50.4	49.8	49.3	48.7	48.4
107.5°	49.7	50.0	50.6	51.2	51.8	52.4	51.8	51.2	50.6	50.0	49.7
110°	50.4	50.7	51.3	51.9	52.5	53.1	52.5	51.9	51.3	50.7	50.4

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	51.7	51.9	52.4	52.8	53.3	53.7	53.3	52.8	52.4	51.9	51.7
115°	103.4	98.0	87.3	76.6	65.8	55.1	65.8	76.6	87.3	98.0	103.4
117.5°	354.7	335.1	296.0	256.9	217.8	178.7	217.8	256.9	296.0	335.1	354.7
120°	500.4	490.3	470.2	450.0	429.9	409.7	429.9	450.0	470.2	490.3	500.4
122.5°	536.0	536.1	536.2	536.4	536.5	536.7	536.5	536.4	536.2	536.1	536.0
125°	572.3	572.5	573.0	573.4	573.9	574.3	573.9	573.4	573.0	572.5	572.3
127.5°	607.2	607.3	607.4	607.6	607.7	607.9	607.7	607.6	607.4	607.3	607.2
130°	639.4	639.3	639.2	639.1	638.9	638.8	638.9	639.1	639.2	639.3	639.4
132.5°	669.7	669.6	669.5	669.3	669.2	669.0	669.2	669.3	669.5	669.6	669.7
135°	699.2	699.1	698.8	698.5	698.2	697.9	698.2	698.5	698.8	699.1	699.2
137.5°	726.8	726.6	726.1	725.7	725.2	724.8	725.2	725.7	726.1	726.6	726.8
140°	753.0	752.6	751.9	751.1	750.4	749.6	750.4	751.1	751.9	752.6	753.0
142.5°	777.1	776.7	776.0	775.3	774.5	773.8	774.5	775.3	776.0	776.7	777.1
145°	799.3	798.9	798.2	797.4	796.7	795.9	796.7	797.4	798.2	798.9	799.3
147.5°	818.8	818.5	817.9	817.3	816.7	816.1	816.7	817.3	817.9	818.5	818.8
150°	837.6	837.2	836.5	835.7	835.0	834.2	835.0	835.7	836.5	837.2	837.6
152.5°	854.4	853.9	852.8	851.8	850.7	849.7	850.7	851.8	852.8	853.9	854.4
155°	869.2	868.6	867.4	866.2	865.0	863.8	865.0	866.2	867.4	868.6	869.2
157.5°	882.6	882.0	880.8	879.6	878.4	877.2	878.4	879.6	880.8	882.0	882.6
160°	893.3	892.8	891.7	890.7	889.6	888.6	889.6	890.7	891.7	892.8	893.3
162.5°	904.1	903.4	902.1	900.7	899.4	898.0	899.4	900.7	902.1	903.4	904.1
165°	912.2	911.7	910.6	909.5	908.5	907.4	908.5	909.5	910.6	911.7	912.2
167.5°	919.5	918.8	917.5	916.2	914.8	913.5	914.8	916.2	917.5	918.8	919.5
170°	924.9	924.2	922.9	921.6	920.2	918.9	920.2	921.6	922.9	924.2	924.9
172.5°	928.9	928.2	926.9	925.6	924.2	922.9	924.2	925.6	926.9	928.2	928.9
175°	931.6	930.9	929.4	927.9	926.4	924.9	926.4	927.9	929.4	930.9	931.6
177.5°	932.3	931.6	930.3	929.0	927.6	926.3	927.6	929.0	930.3	931.6	932.3
180°	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	883.3	889.0	886.9	879.0	888.3	888.3	894.8	894.8	902.6	905.5	909.8
5°	833.2	837.5	841.1	837.5	844.0	854.0	859.7	864.7	875.4	879.7	886.2
7.5°	779.6	787.5	791.0	791.0	801.8	813.2	824.7	831.8	846.8	852.6	859.0
10°	727.4	736.7	743.8	743.1	761.0	768.2	782.5	798.9	813.9	822.5	831.8
12.5°	672.3	677.3	687.3	701.6	705.9	718.8	735.3	756.0	783.2	791.0	804.6
15°	626.5	640.1	648.0	654.4	664.4	676.6	694.5	714.5	741.7	758.9	773.2
17.5°	587.9	605.8	610.8	609.4	622.3	640.8	661.6	676.6	700.9	721.7	735.3
20°	556.4	563.6	572.2	575.8	585.8	605.8	625.8	643.0	663.0	679.5	695.2
22.5°	525.0	530.7	537.9	544.3	552.2	563.6	582.9	604.4	623.7	639.4	657.3
25°	499.2	502.8	509.2	514.3	522.8	530.7	544.3	567.9	590.8	600.1	615.8
27.5°	474.2	477.1	481.4	487.1	491.4	499.2	511.4	530.7	554.3	563.6	585.1
30°	452.0	454.2	458.5	461.3	463.5	472.8	482.1	497.1	515.0	527.8	543.6
32.5°	431.3	433.4	437.7	438.4	441.3	446.3	454.9	468.5	484.2	494.9	508.5
35°	408.4	409.8	414.1	415.5	417.7	422.0	428.4	438.4	452.7	460.6	472.8
37.5°	390.5	389.8	392.7	394.8	397.7	399.8	402.0	412.0	422.7	429.9	439.2
40°	371.2	369.8	370.5	373.4	374.8	377.6	377.6	387.7	394.8	400.5	407.7
42.5°	351.9	351.2	349.7	351.2	352.6	353.3	354.0	361.2	368.3	373.4	381.2
45°	332.6	331.9	330.4	331.2	331.2	332.6	334.7	337.6	342.6	346.9	351.2
47.5°	314.7	313.3	311.1	310.4	311.8	311.8	311.8	314.7	319.7	321.1	325.4
50°	296.1	294.0	291.1	289.7	289.7	289.0	290.4	291.1	295.4	296.8	300.4
52.5°	276.1	274.6	271.8	268.9	269.6	268.2	268.9	269.6	271.1	273.2	275.4
55°	256.1	253.2	251.0	250.3	248.2	248.2	246.0	248.9	248.2	248.9	251.8
57.5°	236.7	233.9	230.3	228.9	226.7	226.0	224.6	223.9	224.6	226.7	228.9
60°	213.9	212.4	210.3	208.1	206.7	204.6	203.1	203.1	202.4	202.4	203.1
62.5°	191.7	191.0	188.1	187.4	186.0	184.5	182.4	181.0	181.0	182.4	183.1
65°	170.2	169.5	167.4	166.6	163.1	161.6	160.9	160.2	158.8	158.8	158.8
67.5°	150.2	148.1	148.1	144.5	141.6	140.2	138.8	138.0	138.0	138.0	138.8
70°	128.0	128.0	125.9	123.7	120.9	121.6	119.4	117.3	117.3	115.9	116.6
72.5°	106.6	105.9	103.7	103.0	100.8	98.7	97.3	98.7	96.6	95.8	96.6
75°	85.8	85.1	83.7	82.3	83.0	80.8	78.7	78.0	78.0	76.5	76.5
77.5°	65.8	67.2	64.4	63.7	62.2	60.8	60.1	59.4	59.4	59.4	60.8
80°	45.8	46.5	46.5	45.1	45.8	43.6	43.6	43.6	41.5	42.2	42.9
82.5°	29.3	29.3	28.6	29.3	28.6	28.6	27.9	27.9	27.2	27.2	27.9
85°	16.5	15.7	15.0	16.5	15.7	15.7	15.0	15.0	15.0	15.0	15.0
87.5°	3.6	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.7	5.7	5.7
90°	16.4	15.7	14.9	14.2	13.4	12.2	11.0	9.9	8.7	8.1	7.3
92.5°	17.3	17.0	16.7	16.4	16.1	15.7	15.2	14.8	14.3	14.1	14.4
95°	29.2	28.5	27.7	27.0	26.2	25.2	24.1	23.1	22.0	21.5	24.0
97.5°	36.1	35.6	35.2	34.7	34.3	31.9	29.5	27.1	24.7	23.5	29.6
100°	43.1	41.9	40.7	39.5	38.3	35.8	33.2	30.7	28.2	26.9	37.1
102.5°	46.2	44.5	42.9	41.2	39.6	66.8	94.0	121.1	148.3	161.9	162.0
105°	47.6	45.9	44.3	42.6	41.0	81.7	122.5	163.2	203.9	224.3	222.1
107.5°	48.9	47.2	45.6	43.9	42.3	92.6	142.9	193.2	243.5	268.7	266.8
110°	57.9	72.8	87.7	102.6	117.5	160.7	203.8	247.0	290.1	311.7	310.1

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	83.9	148.2	212.5	276.9	341.2	343.7	346.3	348.8	351.3	352.6	351.3
115°	138.0	207.1	276.2	345.3	414.4	410.7	406.9	403.2	399.5	397.6	396.3
117.5°	365.4	386.7	408.0	429.4	450.7	448.2	445.6	443.1	440.6	439.3	437.8
120°	499.5	497.7	495.9	494.1	492.3	489.6	487.0	484.3	481.6	480.3	479.2
122.5°	535.6	534.7	533.8	532.9	532.0	529.0	526.0	523.0	520.0	518.5	517.3
125°	571.8	570.7	569.7	568.6	567.6	564.8	561.9	559.1	556.2	554.8	553.8
127.5°	606.5	605.0	603.5	602.0	600.5	598.3	596.0	593.8	591.5	590.4	589.4
130°	638.6	637.0	635.3	633.7	632.1	630.5	628.8	627.2	625.5	624.7	623.5
132.5°	669.0	667.7	666.3	665.0	663.6	662.0	660.3	658.7	657.0	656.2	655.2
135°	698.5	697.0	695.5	694.0	692.5	691.2	689.8	688.5	687.2	686.5	685.3
137.5°	726.0	724.5	723.0	721.5	720.0	718.5	717.0	715.5	714.0	713.3	712.4
140°	752.3	751.0	749.6	748.3	746.9	745.3	743.6	742.0	740.3	739.5	738.9
142.5°	776.5	775.3	774.2	773.0	771.8	769.8	767.9	765.9	764.0	763.0	762.5
145°	798.8	797.7	796.7	795.6	794.6	792.1	789.5	787.0	784.5	783.2	783.3
147.5°	818.4	817.7	816.9	816.2	815.4	812.9	810.3	807.8	805.3	804.0	804.2
150°	837.2	836.3	835.4	834.5	833.6	831.2	828.8	826.4	824.0	822.8	823.3
152.5°	854.0	853.1	852.2	851.3	850.4	848.2	845.9	843.7	841.4	840.3	840.9
155°	868.7	867.8	866.9	866.0	865.1	863.3	861.5	859.8	858.0	857.1	857.8
157.5°	882.1	881.0	880.0	878.9	877.9	876.5	875.2	873.8	872.5	871.8	872.4
160°	892.9	892.0	891.1	890.2	889.3	888.4	887.5	886.6	885.7	885.3	885.7
162.5°	903.6	902.5	901.5	900.4	899.4	898.6	897.9	897.1	896.4	896.0	896.5
165°	911.7	910.6	909.5	908.5	907.4	907.0	906.5	906.1	905.6	905.4	905.9
167.5°	919.0	917.9	916.9	915.8	914.8	914.4	913.9	913.5	913.0	912.8	913.3
170°	924.4	923.3	922.3	921.2	920.2	919.9	919.6	919.3	919.0	918.9	919.3
172.5°	928.4	927.3	926.3	925.2	924.2	923.9	923.6	923.3	923.0	922.9	923.3
175°	931.1	930.0	929.0	927.9	926.9	926.6	926.3	926.0	925.7	925.6	926.1
177.5°	931.8	930.7	929.7	928.6	927.6	927.4	927.3	927.1	927.0	926.9	927.4
180°	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	930.5	930.5	930.5	930.5
2.5°	913.3	913.3	924.1	935.5
5°	893.3	898.3	915.5	931.2
7.5°	874.0	882.6	904.1	924.1
10°	850.4	861.9	888.3	911.9
12.5°	827.5	838.3	869.0	895.5
15°	795.3	808.9	841.8	874.7
17.5°	763.2	776.7	816.8	855.4
20°	725.2	743.1	788.2	839.7
22.5°	690.2	712.4	762.4	803.9
25°	651.6	685.9	732.4	786.0
27.5°	617.2	651.6	698.8	753.1
30°	578.6	613.7	662.3	712.4
32.5°	541.4	573.6	620.8	682.3
35°	502.8	533.6	579.3	641.6
37.5°	467.8	497.8	547.9	605.1
40°	433.4	464.9	507.8	565.0
42.5°	401.2	429.1	467.8	525.0
45°	371.9	391.9	427.7	481.4
47.5°	341.2	359.0	391.9	445.6
50°	312.6	327.6	356.2	406.3
52.5°	284.7	297.5	324.0	364.1
55°	259.6	271.8	291.1	330.4
57.5°	233.9	243.2	261.8	293.2
60°	208.8	217.4	232.4	258.2
62.5°	183.8	191.0	205.3	226.0
65°	161.6	167.4	178.1	196.0
67.5°	140.2	143.8	152.3	166.6
70°	119.4	122.3	129.5	140.9
72.5°	97.3	100.1	108.0	115.9
75°	78.7	79.4	85.1	91.5
77.5°	61.5	60.8	65.1	70.1
80°	42.2	44.3	47.9	50.1
82.5°	28.6	29.3	30.8	32.2
85°	15.7	16.5	16.5	18.6
87.5°	6.4	7.2	7.2	7.9
90°	5.6	4.0	2.3	0.7
92.5°	15.0	15.6	16.2	16.8
95°	28.9	33.8	38.8	43.7
97.5°	41.9	54.1	66.4	78.6
100°	57.6	78.0	98.5	118.9
102.5°	162.3	162.6	162.9	163.2
105°	217.6	213.1	208.7	204.2
107.5°	263.1	259.4	255.6	251.9
110°	307.0	303.9	300.7	297.6

TEST NUMBER: P1008118

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	348.6	345.9	343.2	340.5
115°	393.8	391.3	388.7	386.2
117.5°	434.8	431.8	428.8	425.8
120°	476.9	474.7	472.4	470.2
122.5°	514.9	512.6	510.2	507.8
125°	551.9	550.0	548.0	546.1
127.5°	587.3	585.2	583.1	581.0
130°	621.1	618.7	616.3	613.9
132.5°	653.3	651.4	649.4	647.5
135°	682.9	680.5	678.1	675.7
137.5°	710.6	708.9	707.1	705.3
140°	737.7	736.6	735.4	734.2
142.5°	761.4	760.4	759.3	758.3
145°	783.4	783.6	783.7	783.9
147.5°	804.7	805.1	805.6	806.0
150°	824.4	825.4	826.5	827.5
152.5°	842.1	843.3	844.5	845.7
155°	859.1	860.4	861.8	863.1
157.5°	873.6	874.8	876.0	877.2
160°	886.6	887.5	888.4	889.3
162.5°	897.4	898.3	899.2	900.1
165°	906.8	907.7	908.6	909.5
167.5°	914.2	915.1	916.0	916.9
170°	920.2	921.1	922.0	922.9
172.5°	924.2	925.1	926.0	926.9
175°	927.2	928.2	929.3	930.3
177.5°	928.5	929.5	930.6	931.6
180°	928.3	928.3	928.3	928.3

(END OF REPORT)