

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008129

Luminaire Tested: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008129
REPORT IS A COMBINATION OF REPORTS P984367 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5751.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	39	38	38	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	32	32	27
3	80	71	64	58	72	64	58	54	52	48	45	42	39	36	31	30	28	28	28	23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	24	24	20
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	21	21	21	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	19	19	16
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	17	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	15	15	13
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14	14	14	12
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15188	15188	15188	15188
5°	15226	16194	15283	12885
10°	15048	17679	15142	10622
15°	14683	18647	14887	8948
20°	14455	17508	14455	7777
25°	13993	15041	14057	6954
30°	13236	11824	13488	6300
35°	12565	8176	12774	5763
40°	11791	6173	11927	5336
45°	10841	5073	11018	4875
50°	10017	4452	10037	4463
55°	9078	3794	9140	4015
60°	8078	3169	8190	3505
65°	7185	2577	7316	2993
70°	6293	2022	6453	2413
75°	5281	1468	5488	1751
80°	4120	931	4415	1039
85°	2712	468	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15700 cd/sqm

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.6
10°-20°	266.0	4.6
20°-30°	386.1	6.7
30°-40°	407.0	7.1
40°-50°	360.1	6.3
50°-60°	287.6	5.0
60°-70°	195.3	3.4
70°-80°	99.9	1.7
80°-90°	25.8	0.4
90°-100°	40.9	0.7
100°-110°	152.3	2.6
110°-120°	403.9	7.0
120°-130°	669.8	11.6
130°-140°	711.5	12.4
140°-150°	661.3	11.5
150°-160°	531.6	9.2
160°-170°	342.6	6.0
170°-180°	117.9	2.1
0°-30°	743.5	12.9
0°-40°	1150.4	20.0
0°-60°	1798.1	31.3
0°-90°	2119.2	36.8
90°-120°	597.0	10.4
90°-150°	2639.7	45.9
90°-180°	3632.0	63.2
0°-180°	5751.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	960	960	960	960	960	
5°	960	1072	964	853	960	91
15°	902	1317	914	632	902	255
25°	810	1097	814	507	810	371
35°	662	597	673	421	662	414
45°	496	360	504	346	496	385
55°	341	253	343	268	341	304
65°	202	156	206	181	202	201
75°	94	77	98	92	94	101
85°	19	20	21	15	19	22
90°	1	24	1	24	1	4
95°	58	38	58	38	58	69
105°	272	68	272	68	272	291
115°	515	74	515	74	515	507
125°	729	766	729	766	729	650
135°	902	931	902	931	902	697
145°	1046	1062	1046	1062	1046	654
155°	1152	1153	1152	1153	1152	531
165°	1214	1211	1214	1211	1214	343
175°	1242	1234	1242	1234	1242	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	964.7	966.9	970.6	971.3	978.7	984.6	991.2	991.2	993.4	992.7	986.8
5°	960.3	966.9	976.5	984.6	997.9	1003.8	1012.6	1019.3	1025.2	1029.6	1028.9
7.5°	952.9	964.7	978.7	994.2	1011.9	1022.2	1034.8	1046.6	1054.7	1062.0	1067.2
10°	940.3	960.3	979.4	1000.1	1023.0	1037.0	1051.7	1067.2	1079.7	1093.8	1107.0
12.5°	923.4	952.1	975.7	1003.0	1031.1	1046.6	1070.2	1082.0	1106.3	1141.7	1151.3
15°	902.0	941.1	963.2	997.9	1034.8	1047.3	1079.7	1098.9	1149.1	1171.2	1197.7
17.5°	882.1	925.6	955.1	994.9	1031.1	1055.4	1087.1	1126.2	1168.2	1200.0	1229.5
20°	865.9	907.9	943.3	987.5	1033.3	1064.3	1097.4	1144.6	1190.4	1222.8	1245.7
22.5°	829.0	882.8	924.1	973.5	1028.9	1071.6	1103.3	1155.0	1204.4	1224.3	1244.2
25°	810.5	857.0	904.9	961.0	1025.9	1076.8	1104.1	1161.6	1205.1	1212.5	1216.9
27.5°	776.6	829.0	885.0	949.2	1025.2	1067.9	1102.6	1155.0	1189.6	1184.5	1171.2
30°	734.6	798.7	860.7	930.0	1014.8	1061.3	1093.8	1141.7	1159.4	1132.8	1109.2
32.5°	703.6	764.1	832.7	913.1	1003.0	1047.3	1079.0	1116.6	1120.3	1072.4	1032.5
35°	661.6	728.7	806.1	890.9	983.1	1023.0	1052.5	1075.3	1057.6	990.5	943.3
37.5°	623.9	690.3	772.9	859.2	955.8	994.9	1018.5	1022.2	978.7	919.7	850.4
40°	582.6	651.2	737.5	828.2	925.6	959.5	974.3	963.2	900.5	831.9	751.5
42.5°	541.3	609.2	702.1	795.1	887.2	916.0	921.9	891.7	815.0	734.6	641.6
45°	496.4	567.2	660.1	753.8	843.0	859.2	860.0	816.4	725.7	641.6	555.4
47.5°	459.5	525.1	617.3	711.0	786.2	797.3	792.8	742.7	643.9	549.5	474.2
50°	418.9	481.6	573.1	665.2	729.4	732.4	721.3	649.8	553.1	466.9	407.1
52.5°	375.4	438.8	522.9	611.4	668.9	664.5	643.1	566.4	475.7	404.2	358.4
55°	340.7	396.8	475.7	562.0	602.6	590.0	566.4	488.2	416.7	356.2	316.4
57.5°	302.4	351.8	429.2	504.5	528.1	516.3	492.7	419.7	353.3	307.5	281.0
60°	266.2	311.2	379.1	441.8	460.2	447.7	420.4	354.8	306.8	268.5	248.5
62.5°	233.1	272.1	328.9	386.5	393.8	381.3	357.7	304.6	263.3	233.1	218.3
65°	202.1	239.0	284.7	328.2	334.8	321.6	297.2	258.9	224.2	205.0	191.0
67.5°	171.8	201.3	241.9	273.6	277.3	264.8	244.9	213.9	192.5	171.8	161.5
70°	145.3	167.4	199.1	224.9	226.4	214.6	204.3	176.3	160.0	145.3	137.2
72.5°	119.5	135.0	159.3	178.5	179.2	171.8	162.3	144.6	130.5	120.2	112.1
75°	94.4	107.7	122.4	139.4	138.7	132.8	125.4	114.3	102.5	95.9	92.2
77.5°	72.3	80.4	92.2	103.3	103.3	100.3	95.9	87.8	80.4	73.8	70.1
80°	51.6	56.8	66.4	70.1	71.5	70.8	67.1	61.2	58.3	53.1	51.6
82.5°	33.2	36.9	41.3	45.0	47.2	45.7	45.0	42.0	37.6	36.1	34.7
85°	19.2	20.7	22.9	25.1	25.8	25.1	26.6	24.3	22.1	22.1	21.4
87.5°	8.1	8.9	10.3	10.3	11.1	11.1	10.3	11.1	11.1	10.3	9.6
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.7	16.3	17.9
92.5°	22.4	21.6	20.8	20.0	19.2	18.8	19.1	19.7	20.3	20.9	21.5
95°	58.3	51.7	45.1	38.6	32.0	28.7	29.4	30.8	32.2	33.6	35.0
97.5°	104.9	88.6	72.2	55.9	39.6	31.4	33.0	36.2	39.3	42.5	45.7
100°	158.7	131.4	104.1	76.8	49.5	35.9	37.6	41.0	44.3	47.7	51.1
102.5°	217.8	217.4	217.0	216.6	216.2	216.0	197.9	161.6	125.4	89.1	52.9
105°	272.5	278.5	284.5	290.4	296.4	299.4	272.2	217.8	163.5	109.1	54.7
107.5°	336.2	341.2	346.2	351.1	356.1	358.6	325.0	257.9	190.8	123.6	56.5
110°	397.1	401.3	405.5	409.6	413.8	415.9	387.1	329.6	272.0	214.5	156.9

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	454.5	458.1	461.7	465.2	468.8	470.6	468.9	465.5	462.2	458.8	455.4
115°	515.4	518.8	522.2	525.6	529.0	530.7	533.2	538.2	543.1	548.1	553.1
117.5°	568.3	572.3	576.3	580.2	584.2	586.2	587.9	591.3	594.7	598.1	601.5
120°	627.5	630.5	633.5	636.4	639.4	640.9	642.7	646.3	649.9	653.5	657.1
122.5°	677.7	680.9	684.1	687.2	690.4	692.0	694.0	698.0	702.0	706.0	710.0
125°	728.8	731.4	734.0	736.5	739.1	740.4	742.3	746.1	749.9	753.7	757.5
127.5°	775.4	778.2	781.0	783.7	786.5	787.9	789.4	792.4	795.4	798.4	801.4
130°	819.3	822.5	825.7	828.9	832.1	833.7	834.8	837.0	839.1	841.3	843.5
132.5°	864.1	866.7	869.3	871.9	874.5	875.8	876.9	879.1	881.2	883.4	885.6
135°	901.8	905.0	908.2	911.3	914.5	916.1	917.0	918.8	920.6	922.4	924.2
137.5°	941.2	943.6	946.0	948.4	950.8	952.0	953.0	955.0	956.9	958.9	960.9
140°	979.8	981.4	983.0	984.5	986.1	986.9	988.0	990.2	992.4	994.6	996.8
142.5°	1012.0	1013.4	1014.8	1016.2	1017.6	1018.3	1019.6	1022.2	1024.8	1027.4	1030.0
145°	1046.1	1045.9	1045.7	1045.5	1045.3	1045.2	1046.9	1050.3	1053.6	1057.0	1060.4
147.5°	1075.7	1075.1	1074.5	1073.9	1073.3	1073.0	1074.7	1078.1	1081.4	1084.8	1088.2
150°	1104.4	1103.0	1101.6	1100.2	1098.8	1098.1	1099.7	1102.9	1106.0	1109.2	1112.4
152.5°	1128.6	1127.0	1125.4	1123.8	1122.2	1121.4	1122.9	1125.9	1128.8	1131.8	1134.8
155°	1151.9	1150.1	1148.3	1146.5	1144.7	1143.8	1145.0	1147.4	1149.8	1152.2	1154.6
157.5°	1170.7	1169.1	1167.5	1165.9	1164.3	1163.5	1164.4	1166.2	1168.0	1169.8	1171.6
160°	1186.8	1185.6	1184.4	1183.3	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8
162.5°	1201.2	1200.0	1198.8	1197.6	1196.4	1195.8	1196.3	1197.3	1198.3	1199.3	1200.3
165°	1213.7	1212.5	1211.3	1210.2	1209.0	1208.4	1208.7	1209.3	1209.8	1210.4	1211.0
167.5°	1223.6	1222.4	1221.2	1220.0	1218.8	1218.2	1218.5	1219.1	1219.7	1220.3	1220.9
170°	1231.7	1230.5	1229.3	1228.1	1226.9	1226.3	1226.5	1226.9	1227.3	1227.7	1228.1
172.5°	1237.0	1235.8	1234.6	1233.5	1232.3	1231.7	1231.9	1232.3	1232.7	1233.1	1233.5
175°	1241.5	1240.1	1238.7	1237.3	1235.9	1235.2	1235.4	1235.8	1236.2	1236.6	1237.0
177.5°	1243.3	1241.9	1240.5	1239.1	1237.7	1237.0	1237.1	1237.3	1237.5	1237.7	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	997.1	997.9	999.3	1006.7	1010.4	1011.1	1008.2	1014.8	1017.1	1014.8	1013.4
5°	1044.3	1048.8	1057.6	1067.2	1066.5	1067.2	1071.6	1076.1	1077.5	1071.6	1073.8
7.5°	1085.6	1094.5	1104.1	1118.8	1118.8	1126.2	1129.2	1132.8	1141.7	1137.3	1135.8
10°	1132.8	1144.6	1162.3	1185.9	1186.7	1194.1	1201.4	1213.2	1216.9	1214.0	1215.4
12.5°	1191.8	1214.7	1216.2	1242.0	1253.8	1255.3	1267.1	1264.9	1272.2	1272.2	1284.8
15°	1217.7	1253.1	1273.0	1298.0	1305.4	1296.6	1306.2	1316.5	1317.2	1317.2	1316.5
17.5°	1264.1	1278.1	1298.0	1311.3	1314.3	1314.3	1315.0	1319.4	1316.5	1310.6	1315.0
20°	1273.7	1279.6	1287.0	1285.5	1287.0	1279.6	1272.2	1264.9	1265.6	1261.9	1273.0
22.5°	1256.0	1254.5	1237.6	1226.5	1226.5	1211.8	1197.7	1191.1	1184.5	1186.7	1190.4
25°	1211.8	1188.9	1168.2	1152.0	1148.3	1124.7	1105.6	1099.7	1088.6	1097.4	1098.9
27.5°	1141.0	1115.1	1082.0	1067.9	1048.8	1039.2	1025.9	1008.2	985.3	998.6	996.4
30°	1065.0	1026.6	999.3	965.4	935.2	933.0	907.9	878.4	866.6	866.6	873.2
32.5°	980.2	929.3	889.5	841.5	812.0	799.5	769.2	739.7	746.4	724.3	732.4
35°	881.3	814.2	764.1	717.6	695.5	680.7	641.6	625.4	607.7	597.4	616.6
37.5°	786.9	709.5	645.3	594.4	586.3	559.8	533.2	522.9	512.6	517.0	516.3
40°	671.9	603.3	545.8	505.9	491.9	479.4	461.7	449.2	442.5	446.2	446.9
42.5°	567.9	510.4	467.6	439.6	427.8	418.9	410.1	399.7	397.5	397.5	400.5
45°	487.5	440.3	411.5	388.7	382.0	375.4	368.8	364.3	362.9	359.9	362.1
47.5°	423.3	385.7	368.0	351.1	343.7	342.2	336.3	334.1	331.1	330.4	331.1
50°	369.5	345.9	329.7	320.1	314.9	312.7	309.8	305.3	303.9	307.5	306.1
52.5°	331.9	309.8	300.9	291.3	288.4	285.4	281.0	281.7	281.0	279.5	279.5
55°	294.3	280.3	271.4	264.0	263.3	260.3	256.7	255.2	254.4	253.0	255.2
57.5°	264.0	253.0	244.9	238.2	235.3	235.3	231.6	228.6	228.6	227.9	228.6
60°	233.8	222.7	217.6	210.9	208.7	208.0	205.8	204.3	202.1	202.1	202.1
62.5°	205.8	196.9	191.0	185.1	185.9	182.2	179.2	177.7	177.7	178.5	178.5
65°	179.2	173.3	165.9	160.8	159.3	158.6	157.1	156.4	154.1	155.6	155.6
67.5°	154.9	146.8	142.3	140.1	137.9	137.2	135.7	134.2	133.5	132.8	134.2
70°	130.5	123.9	120.2	118.7	116.5	115.8	115.1	112.8	113.6	114.3	115.1
72.5°	108.4	102.5	101.8	97.4	97.4	97.4	94.4	95.9	95.1	93.7	95.1
75°	85.6	82.6	81.1	78.9	79.7	78.9	78.2	76.0	76.0	76.7	77.4
77.5°	67.9	64.9	64.2	62.0	60.5	62.0	60.5	59.7	59.7	60.5	60.5
80°	50.2	48.7	46.5	46.5	46.5	45.7	45.7	45.7	45.0	44.3	45.0
82.5°	33.2	33.2	32.5	31.7	32.5	31.0	31.7	31.7	31.7	31.7	31.7
85°	21.4	20.7	20.7	19.9	19.9	19.9	20.7	19.2	19.2	19.9	19.9
87.5°	9.6	9.6	9.6	10.3	9.6	9.6	9.6	10.3	9.6	9.6	9.6
90°	18.9	19.9	20.9	21.9	22.4	22.6	23.0	23.4	23.8	24.2	23.8
92.5°	21.9	22.3	22.7	23.1	23.3	23.4	23.6	23.8	24.0	24.2	24.0
95°	36.0	37.0	37.9	38.9	39.4	39.3	39.1	38.9	38.7	38.5	38.7
97.5°	46.3	46.9	47.5	48.1	48.4	48.5	48.7	48.9	49.1	49.3	49.1
100°	52.7	54.3	55.9	57.5	58.3	58.5	58.9	59.3	59.7	60.1	59.7
102.5°	55.1	57.3	59.4	61.6	62.7	63.0	63.6	64.2	64.8	65.4	64.8
105°	56.9	59.1	61.2	63.4	64.5	64.9	65.7	66.5	67.3	68.1	67.3
107.5°	58.7	60.9	63.0	65.2	66.3	66.7	67.5	68.3	69.1	69.9	69.1
110°	137.0	117.0	97.1	77.2	67.2	67.6	68.4	69.2	70.0	70.8	70.0

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	369.5	283.7	197.8	111.9	69.0	69.3	69.9	70.5	71.1	71.7	71.1
115°	460.9	368.6	276.4	184.1	138.0	130.8	116.5	102.2	87.8	73.5	87.8
117.5°	573.0	544.5	516.0	487.5	473.3	447.2	395.0	342.8	290.6	238.4	290.6
120°	659.5	661.9	664.2	666.6	667.8	654.4	627.5	600.6	573.7	546.8	573.7
122.5°	711.2	712.4	713.5	714.7	715.3	715.4	715.6	715.8	716.0	716.2	716.0
125°	758.9	760.3	761.6	763.0	763.7	764.0	764.6	765.2	765.8	766.4	765.8
127.5°	803.4	805.4	807.4	809.4	810.4	810.5	810.7	810.8	811.0	811.2	811.0
130°	845.7	847.9	850.1	852.3	853.4	853.3	853.1	852.9	852.7	852.5	852.7
132.5°	887.4	889.2	891.0	892.8	893.7	893.6	893.4	893.2	893.0	892.8	893.0
135°	926.2	928.2	930.2	932.2	933.2	933.0	932.6	932.2	931.8	931.4	931.8
137.5°	962.9	964.9	966.9	968.9	969.9	969.6	969.0	968.4	967.8	967.2	967.8
140°	998.6	1000.4	1002.2	1004.0	1004.9	1004.4	1003.4	1002.4	1001.4	1000.4	1001.4
142.5°	1031.6	1033.2	1034.7	1036.3	1037.1	1036.6	1035.6	1034.7	1033.7	1032.7	1033.7
145°	1061.8	1063.2	1064.6	1066.0	1066.7	1066.2	1065.2	1064.2	1063.2	1062.2	1063.2
147.5°	1089.2	1090.2	1091.2	1092.2	1092.7	1092.3	1091.5	1090.7	1089.9	1089.1	1089.9
150°	1113.6	1114.8	1116.0	1117.2	1117.8	1117.3	1116.3	1115.3	1114.3	1113.3	1114.3
152.5°	1136.0	1137.2	1138.4	1139.6	1140.2	1139.5	1138.1	1136.8	1135.4	1134.0	1135.4
155°	1155.8	1157.0	1158.1	1159.3	1159.9	1159.1	1157.5	1156.0	1154.4	1152.8	1154.4
157.5°	1173.0	1174.4	1175.8	1177.2	1177.9	1177.1	1175.5	1173.9	1172.3	1170.7	1172.3
160°	1188.0	1189.2	1190.4	1191.6	1192.2	1191.5	1190.1	1188.7	1187.3	1185.9	1187.3
162.5°	1201.7	1203.1	1204.5	1205.9	1206.6	1205.7	1203.9	1202.1	1200.3	1198.5	1200.3
165°	1212.4	1213.8	1215.2	1216.6	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1212.4
167.5°	1222.3	1223.7	1225.1	1226.5	1227.2	1226.3	1224.5	1222.7	1220.9	1219.1	1220.9
170°	1229.5	1230.9	1232.2	1233.6	1234.3	1233.4	1231.6	1229.9	1228.1	1226.3	1228.1
172.5°	1234.9	1236.3	1237.6	1239.0	1239.7	1238.8	1237.0	1235.3	1233.5	1231.7	1233.5
175°	1238.4	1239.8	1241.2	1242.6	1243.3	1242.3	1240.3	1238.3	1236.3	1234.3	1236.3
177.5°	1239.3	1240.7	1242.1	1243.5	1244.2	1243.3	1241.5	1239.7	1237.9	1236.1	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	1017.1	1011.9	1007.5	1008.2	1011.9	1008.9	1001.6	992.0	988.3	983.9	988.3
5°	1078.3	1073.8	1065.0	1065.7	1063.5	1060.6	1048.8	1034.0	1034.0	1022.2	1020.7
7.5°	1138.7	1132.1	1126.2	1124.7	1116.6	1110.7	1100.4	1079.7	1071.6	1057.6	1049.5
10°	1206.6	1201.4	1194.8	1186.7	1182.3	1171.9	1155.0	1124.7	1110.0	1090.8	1076.8
12.5°	1275.2	1274.4	1259.7	1243.5	1242.7	1226.5	1214.7	1174.1	1154.2	1128.4	1095.2
15°	1318.7	1315.0	1306.9	1298.8	1301.0	1283.3	1256.7	1208.8	1195.5	1164.6	1129.2
17.5°	1318.0	1318.0	1315.7	1314.3	1312.1	1306.9	1292.1	1260.4	1239.0	1200.0	1166.8
20°	1275.9	1285.5	1287.7	1287.0	1294.4	1298.0	1297.3	1277.4	1260.4	1225.8	1191.8
22.5°	1191.8	1214.0	1223.6	1229.5	1244.9	1253.1	1272.2	1264.9	1260.4	1234.6	1205.9
25°	1113.7	1121.0	1149.8	1151.3	1172.7	1192.6	1211.8	1224.3	1240.5	1230.9	1206.6
27.5°	1012.6	1029.6	1050.2	1065.7	1070.2	1110.7	1142.4	1166.0	1202.9	1205.9	1197.7
30°	898.3	906.4	940.3	961.0	984.6	1014.1	1059.8	1100.4	1133.6	1163.8	1174.1
32.5°	758.9	792.1	812.0	837.1	857.7	910.1	966.2	1018.5	1056.9	1107.8	1129.9
35°	631.3	657.1	691.1	701.4	739.0	783.3	856.3	923.4	981.6	1033.3	1078.3
37.5°	525.9	546.5	582.6	598.9	621.0	677.8	739.0	822.3	892.4	955.8	1011.9
40°	453.6	469.1	496.4	501.5	520.0	571.6	621.0	699.2	792.1	877.7	938.9
42.5°	404.2	411.5	430.0	436.6	448.4	483.1	527.3	601.1	687.4	775.9	862.2
45°	368.8	373.9	385.0	390.9	405.6	421.1	457.3	516.3	584.1	673.4	766.3
47.5°	337.0	343.7	348.1	351.8	359.9	376.9	400.5	444.0	508.9	590.8	680.7
50°	310.5	312.7	320.8	321.6	326.7	337.8	359.9	386.5	438.1	504.5	591.5
52.5°	283.9	286.2	291.3	296.5	298.7	307.5	322.3	344.4	382.8	435.1	512.6
55°	257.4	260.3	265.5	269.2	271.4	278.8	287.6	309.0	339.3	376.1	439.6
57.5°	230.8	237.5	239.0	241.2	244.9	253.0	261.1	273.6	297.2	331.1	377.6
60°	205.8	208.0	213.1	215.4	219.0	223.5	233.8	243.4	260.3	286.9	328.9
62.5°	180.0	185.1	187.3	189.5	192.5	197.7	204.3	214.6	229.4	250.8	283.9
65°	157.8	158.6	163.0	165.9	168.9	172.6	179.2	188.8	197.7	217.6	241.9
67.5°	136.4	137.9	139.4	142.3	146.0	149.7	155.6	160.8	171.8	185.1	204.3
70°	115.8	115.8	119.5	121.7	121.0	125.4	129.8	135.7	143.8	156.4	171.8
72.5°	97.4	96.6	99.6	100.3	101.8	104.7	107.7	113.6	118.0	127.6	139.4
75°	77.4	78.9	80.4	80.4	82.6	84.8	87.8	90.7	95.9	101.8	110.6
77.5°	61.2	61.2	62.7	63.4	65.6	64.9	67.9	70.8	74.5	79.7	86.3
80°	45.0	46.5	46.5	46.5	47.2	47.9	50.9	53.1	55.3	59.0	62.0
82.5°	31.7	31.7	33.2	33.2	33.2	34.7	34.7	35.4	36.9	39.1	41.3
85°	19.9	19.9	19.9	20.7	19.9	20.7	22.1	21.4	22.1	23.6	23.6
87.5°	9.6	9.6	9.6	9.6	9.6	10.3	9.6	10.3	11.1	11.1	11.1
90°	23.4	23.0	22.6	22.4	21.9	20.9	19.9	18.9	17.9	16.3	14.7
92.5°	23.8	23.6	23.4	23.3	23.1	22.7	22.3	21.9	21.5	20.9	20.3
95°	38.9	39.1	39.3	39.4	38.9	37.9	37.0	36.0	35.0	33.6	32.2
97.5°	48.9	48.7	48.5	48.4	48.1	47.5	46.9	46.3	45.7	42.5	39.3
100°	59.3	58.9	58.5	58.3	57.5	55.9	54.3	52.7	51.1	47.7	44.3
102.5°	64.2	63.6	63.0	62.7	61.6	59.4	57.3	55.1	52.9	49.1	45.4
105°	66.5	65.7	64.9	64.5	63.4	61.2	59.1	56.9	54.7	50.1	46.5
107.5°	68.3	67.5	66.7	66.3	65.2	63.0	60.9	58.7	56.5	52.6	49.0
110°	69.2	68.4	67.6	67.2	77.2	97.1	117.0	137.0	156.9	214.5	272.0

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	70.5	69.9	69.3	69.0	111.9	197.8	283.7	369.5	455.4	458.8	462.2
115°	102.2	116.5	130.8	138.0	184.1	276.4	368.6	460.9	553.1	548.1	543.1
117.5°	342.8	395.0	447.2	473.3	487.5	516.0	544.5	573.0	601.5	598.1	594.7
120°	600.6	627.5	654.4	667.8	666.6	664.2	661.9	659.5	657.1	653.5	649.9
122.5°	715.8	715.6	715.4	715.3	714.7	713.5	712.4	711.2	710.0	706.0	702.0
125°	765.2	764.6	764.0	763.7	763.0	761.6	760.3	758.9	757.5	753.7	749.9
127.5°	810.8	810.7	810.5	810.4	809.4	807.4	805.4	803.4	801.4	798.4	795.4
130°	852.9	853.1	853.3	853.4	852.3	850.1	847.9	845.7	843.5	841.3	839.1
132.5°	893.2	893.4	893.6	893.7	892.8	891.0	889.2	887.4	885.6	883.4	881.2
135°	932.2	932.6	933.0	933.2	932.2	930.2	928.2	926.2	924.2	922.4	920.6
137.5°	968.4	969.0	969.6	969.9	968.9	966.9	964.9	962.9	960.9	958.9	956.9
140°	1002.4	1003.4	1004.4	1004.9	1004.0	1002.2	1000.4	998.6	996.8	994.6	992.4
142.5°	1034.7	1035.6	1036.6	1037.1	1036.3	1034.7	1033.2	1031.6	1030.0	1027.4	1024.8
145°	1064.2	1065.2	1066.2	1066.7	1066.0	1064.6	1063.2	1061.8	1060.4	1057.0	1053.6
147.5°	1090.7	1091.5	1092.3	1092.7	1092.2	1091.2	1090.2	1089.2	1088.2	1084.8	1081.4
150°	1115.3	1116.3	1117.3	1117.8	1117.2	1116.0	1114.8	1113.6	1112.4	1109.2	1106.0
152.5°	1136.8	1138.1	1139.5	1140.2	1139.6	1138.4	1137.2	1136.0	1134.8	1131.8	1128.8
155°	1156.0	1157.5	1159.1	1159.9	1159.3	1158.1	1157.0	1155.8	1154.6	1152.2	1149.8
157.5°	1173.9	1175.5	1177.1	1177.9	1177.2	1175.8	1174.4	1173.0	1171.6	1169.8	1168.0
160°	1188.7	1190.1	1191.5	1192.2	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1184.4
162.5°	1202.1	1203.9	1205.7	1206.6	1205.9	1204.5	1203.1	1201.7	1200.3	1199.3	1198.3
165°	1213.8	1215.2	1216.6	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1210.4	1209.8
167.5°	1222.7	1224.5	1226.3	1227.2	1226.5	1225.1	1223.7	1222.3	1220.9	1220.3	1219.7
170°	1229.9	1231.6	1233.4	1234.3	1233.6	1232.2	1230.9	1229.5	1228.1	1227.7	1227.3
172.5°	1235.3	1237.0	1238.8	1239.7	1239.0	1237.6	1236.3	1234.9	1233.5	1233.1	1232.7
175°	1238.3	1240.3	1242.3	1243.3	1242.6	1241.2	1239.8	1238.4	1237.0	1236.6	1236.2
177.5°	1239.7	1241.5	1243.3	1244.2	1243.5	1242.1	1240.7	1239.3	1237.9	1237.7	1237.5
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	984.6	980.9	978.7	980.2	975.7	964.7	964.7	968.4	963.9	959.5	952.9
5°	1011.9	1004.5	1000.1	999.3	989.0	971.3	967.6	963.9	954.4	944.0	933.0
7.5°	1038.4	1025.2	1017.8	1012.6	997.9	975.0	965.4	957.3	941.8	926.3	912.3
10°	1060.6	1041.4	1032.5	1024.4	1005.2	976.5	961.0	946.2	926.3	906.4	888.7
12.5°	1078.3	1056.1	1045.1	1033.3	1009.7	972.1	952.9	929.3	909.4	882.8	865.1
15°	1107.8	1062.0	1051.7	1040.7	1016.3	964.7	941.1	914.5	887.2	851.8	832.7
17.5°	1131.4	1070.2	1069.4	1045.8	1014.1	961.7	925.6	890.9	861.4	826.0	795.8
20°	1145.4	1082.7	1070.9	1046.6	1006.7	941.8	904.2	865.9	834.1	791.4	761.1
22.5°	1157.2	1100.4	1069.4	1039.9	991.2	935.2	879.9	843.7	800.2	753.8	725.0
25°	1161.6	1104.1	1071.6	1037.7	980.2	916.0	853.3	814.2	765.6	723.5	684.4
27.5°	1162.3	1103.3	1063.5	1028.1	964.7	890.9	826.8	785.5	731.6	683.0	643.9
30°	1155.0	1095.2	1059.1	1020.7	949.9	868.1	794.3	748.6	691.1	642.4	601.8
32.5°	1132.8	1079.0	1049.5	1007.5	930.8	836.4	763.3	712.5	652.0	604.0	564.9
35°	1096.0	1059.1	1026.6	987.5	905.7	806.9	732.4	672.6	611.4	565.7	528.8
37.5°	1050.2	1030.3	1000.1	961.7	876.9	780.3	697.7	631.3	570.1	525.9	489.7
40°	988.3	993.4	963.9	929.3	843.0	744.2	652.7	589.3	531.8	490.5	455.1
42.5°	921.2	942.6	925.6	892.4	805.4	704.3	619.5	549.5	493.4	450.6	421.1
45°	848.9	885.8	875.4	851.1	766.3	662.3	572.3	504.5	455.1	413.8	387.9
47.5°	770.0	822.3	822.3	804.6	722.8	620.3	531.8	462.4	413.8	384.3	359.2
50°	689.6	748.6	758.2	746.4	674.1	572.3	482.3	419.7	377.6	348.9	330.4
52.5°	605.5	674.1	691.8	685.9	622.5	526.6	441.8	380.6	342.2	317.1	300.9
55°	525.1	604.8	623.9	626.2	567.2	476.4	396.8	343.0	306.1	289.1	275.1
57.5°	449.2	525.9	547.2	550.9	511.1	430.7	354.8	307.5	274.4	260.3	249.3
60°	384.3	448.4	476.4	484.6	449.9	377.6	315.7	269.9	244.9	231.6	221.3
62.5°	331.1	382.8	412.3	414.5	399.0	331.1	275.1	236.7	215.4	203.6	198.4
65°	279.5	326.0	343.7	352.5	340.0	286.9	237.5	205.8	188.8	178.5	173.3
67.5°	238.2	267.7	282.5	294.3	281.7	241.9	202.1	176.3	163.7	153.4	150.5
70°	195.4	219.8	230.8	242.6	231.6	201.3	172.6	149.0	137.9	129.8	126.1
72.5°	156.4	175.5	185.9	193.2	186.6	161.5	137.9	121.7	113.6	107.7	105.5
75°	123.9	137.2	143.1	148.2	145.3	126.1	111.4	98.1	90.7	85.6	84.1
77.5°	94.4	104.0	110.6	112.1	108.4	95.9	83.3	75.2	69.3	66.4	64.9
80°	67.1	73.0	76.7	78.9	75.2	70.1	61.2	55.3	50.2	46.5	45.7
82.5°	45.0	47.9	50.9	50.2	48.7	44.3	39.1	36.1	33.9	31.0	31.0
85°	25.8	26.6	28.0	28.8	28.0	25.1	22.1	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.5	11.1	11.1	9.6	8.1	8.1	7.4	6.6
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.7	19.1	18.8	19.2	20.0	20.8	21.6	22.4	21.6	20.8	20.0
95°	30.8	29.4	28.7	32.0	38.6	45.1	51.7	58.3	51.7	45.1	38.6
97.5°	36.2	33.0	31.4	39.6	55.9	72.2	88.6	104.9	88.6	72.2	55.9
100°	41.0	37.6	35.9	49.5	76.8	104.1	131.4	158.7	131.4	104.1	76.8
102.5°	161.6	197.9	216.0	216.2	216.6	217.0	217.4	217.8	217.4	217.0	216.6
105°	217.8	272.2	299.4	296.4	290.4	284.5	278.5	272.5	278.5	284.5	290.4
107.5°	257.9	325.0	358.6	356.1	351.1	346.2	341.2	336.2	341.2	346.2	351.1
110°	329.6	387.1	415.9	413.8	409.6	405.5	401.3	397.1	401.3	405.5	409.6

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	465.5	468.9	470.6	468.8	465.2	461.7	458.1	454.5	458.1	461.7	465.2
115°	538.2	533.2	530.7	529.0	525.6	522.2	518.8	515.4	518.8	522.2	525.6
117.5°	591.3	587.9	586.2	584.2	580.2	576.3	572.3	568.3	572.3	576.3	580.2
120°	646.3	642.7	640.9	639.4	636.4	633.5	630.5	627.5	630.5	633.5	636.4
122.5°	698.0	694.0	692.0	690.4	687.2	684.1	680.9	677.7	680.9	684.1	687.2
125°	746.1	742.3	740.4	739.1	736.5	734.0	731.4	728.8	731.4	734.0	736.5
127.5°	792.4	789.4	787.9	786.5	783.7	781.0	778.2	775.4	778.2	781.0	783.7
130°	837.0	834.8	833.7	832.1	828.9	825.7	822.5	819.3	822.5	825.7	828.9
132.5°	879.1	876.9	875.8	874.5	871.9	869.3	866.7	864.1	866.7	869.3	871.9
135°	918.8	917.0	916.1	914.5	911.3	908.2	905.0	901.8	905.0	908.2	911.3
137.5°	955.0	953.0	952.0	950.8	948.4	946.0	943.6	941.2	943.6	946.0	948.4
140°	990.2	988.0	986.9	986.1	984.5	983.0	981.4	979.8	981.4	983.0	984.5
142.5°	1022.2	1019.6	1018.3	1017.6	1016.2	1014.8	1013.4	1012.0	1013.4	1014.8	1016.2
145°	1050.3	1046.9	1045.2	1045.3	1045.5	1045.7	1045.9	1046.1	1045.9	1045.7	1045.5
147.5°	1078.1	1074.7	1073.0	1073.3	1073.9	1074.5	1075.1	1075.7	1075.1	1074.5	1073.9
150°	1102.9	1099.7	1098.1	1098.8	1100.2	1101.6	1103.0	1104.4	1103.0	1101.6	1100.2
152.5°	1125.9	1122.9	1121.4	1122.2	1123.8	1125.4	1127.0	1128.6	1127.0	1125.4	1123.8
155°	1147.4	1145.0	1143.8	1144.7	1146.5	1148.3	1150.1	1151.9	1150.1	1148.3	1146.5
157.5°	1166.2	1164.4	1163.5	1164.3	1165.9	1167.5	1169.1	1170.7	1169.1	1167.5	1165.9
160°	1183.3	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8	1185.6	1184.4	1183.3
162.5°	1197.3	1196.3	1195.8	1196.4	1197.6	1198.8	1200.0	1201.2	1200.0	1198.8	1197.6
165°	1209.3	1208.7	1208.4	1209.0	1210.2	1211.3	1212.5	1213.7	1212.5	1211.3	1210.2
167.5°	1219.1	1218.5	1218.2	1218.8	1220.0	1221.2	1222.4	1223.6	1222.4	1221.2	1220.0
170°	1226.9	1226.5	1226.3	1226.9	1228.1	1229.3	1230.5	1231.7	1230.5	1229.3	1228.1
172.5°	1232.3	1231.9	1231.7	1232.3	1233.5	1234.6	1235.8	1237.0	1235.8	1234.6	1233.5
175°	1235.8	1235.4	1235.2	1235.9	1237.3	1238.7	1240.1	1241.5	1240.1	1238.7	1237.3
177.5°	1237.3	1237.1	1237.0	1237.7	1239.1	1240.5	1241.9	1243.3	1241.9	1240.5	1239.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	949.2	952.9	952.1	944.8	936.7	930.0	917.5	919.0	914.5	915.3	919.7
5°	925.6	925.6	922.6	912.3	899.0	891.7	877.7	874.0	865.1	864.4	863.6
7.5°	900.5	896.8	893.1	878.4	862.2	850.4	831.2	826.8	817.9	812.0	809.1
10°	871.0	865.9	858.5	841.5	821.6	806.9	786.9	781.0	764.1	756.7	752.3
12.5°	838.6	835.6	823.8	809.8	777.4	761.1	732.4	738.3	721.3	706.6	704.3
15°	806.1	795.1	788.4	765.6	726.5	719.1	696.2	684.4	668.9	657.1	657.1
17.5°	774.4	757.4	742.7	718.4	689.6	668.9	652.0	646.1	626.9	615.1	612.9
20°	732.4	713.2	709.5	674.8	654.9	632.1	615.8	601.1	587.1	581.9	578.2
22.5°	692.5	670.4	664.5	635.0	615.1	592.2	576.0	565.7	555.4	551.7	545.0
25°	649.8	636.5	627.6	595.9	573.8	552.4	541.3	534.0	524.4	523.6	519.2
27.5°	608.5	595.9	587.1	556.8	540.6	520.7	511.8	503.7	498.6	496.4	494.1
30°	573.1	559.0	548.7	526.6	506.7	490.5	483.1	477.9	475.0	471.3	470.5
32.5°	534.0	525.9	511.8	494.9	479.4	463.9	459.5	455.8	451.4	449.9	449.2
35°	500.8	489.7	480.9	461.7	455.1	441.8	436.6	433.7	427.8	426.3	424.8
37.5°	468.3	458.0	448.4	436.6	424.1	416.7	413.8	409.3	406.4	407.1	405.6
40°	435.9	427.8	420.4	407.9	400.5	396.8	390.9	386.5	385.0	385.7	385.0
42.5°	404.2	396.8	392.4	382.8	375.4	371.7	368.0	363.6	365.8	365.8	368.0
45°	375.4	368.8	365.8	358.4	354.0	348.1	344.4	343.7	346.6	345.9	345.9
47.5°	345.9	343.7	340.0	333.4	327.5	323.8	323.0	323.0	326.0	327.5	326.7
50°	323.0	318.6	314.2	309.0	304.6	303.1	300.9	302.4	305.3	305.3	306.8
52.5°	294.3	291.3	289.8	285.4	282.5	282.5	282.5	283.2	285.4	287.6	286.9
55°	269.2	267.0	265.5	263.3	259.6	260.3	259.6	261.1	263.3	265.5	267.0
57.5°	242.6	241.9	240.4	236.7	236.7	236.0	238.2	239.0	242.6	244.1	246.3
60°	219.0	216.8	216.8	213.9	213.9	213.9	216.1	218.3	221.3	222.0	223.5
62.5°	194.0	194.0	193.2	191.0	191.0	193.2	194.0	196.9	198.4	198.4	200.6
65°	170.4	169.6	168.9	169.6	170.4	170.4	172.6	174.1	175.5	176.3	177.0
67.5°	146.8	146.0	147.5	146.8	148.2	151.2	150.5	152.7	154.9	154.9	155.6
70°	124.6	126.1	125.4	126.9	126.1	127.6	129.8	130.5	130.5	131.3	133.5
72.5°	104.0	104.0	104.0	103.3	104.0	105.5	106.9	107.7	109.2	109.9	112.1
75°	84.1	84.1	82.6	84.1	84.1	85.6	87.0	87.0	87.0	88.5	90.7
77.5°	63.4	64.2	63.4	64.9	64.9	65.6	67.1	66.4	67.9	68.6	69.3
80°	46.5	45.7	45.7	45.7	46.5	46.5	47.9	48.7	48.7	50.9	49.4
82.5°	29.5	30.2	29.5	30.2	30.2	31.0	30.2	31.0	31.7	33.2	32.5
85°	17.0	16.2	16.2	17.0	16.2	16.2	17.0	16.2	17.0	16.2	17.0
87.5°	6.6	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	9.7	10.8	11.6	13.2	14.7	16.3	17.9	18.9	19.9	20.9	21.9
92.5°	19.2	18.8	19.1	19.7	20.3	20.9	21.5	21.9	22.3	22.7	23.1
95°	32.0	28.7	29.4	30.8	32.2	33.6	35.0	36.0	37.0	37.9	38.9
97.5°	39.6	31.4	33.0	36.2	39.3	42.5	45.7	46.3	46.9	47.5	48.1
100°	49.5	35.9	37.6	41.0	44.3	47.7	51.1	52.7	54.3	55.9	57.5
102.5°	216.2	216.0	197.9	161.6	125.4	89.1	52.9	55.1	57.3	59.4	61.6
105°	296.4	299.4	272.2	217.8	163.5	109.1	54.7	56.9	59.1	61.2	63.4
107.5°	356.1	358.6	325.0	257.9	190.8	123.6	56.5	58.7	60.9	63.0	65.2
110°	413.8	415.9	387.1	329.6	272.0	214.5	156.9	137.0	117.0	97.1	77.2

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	468.8	470.6	468.9	465.5	462.2	458.8	455.4	369.5	283.7	197.8	111.9
115°	529.0	530.7	533.2	538.2	543.1	548.1	553.1	460.9	368.6	276.4	184.1
117.5°	584.2	586.2	587.9	591.3	594.7	598.1	601.5	573.0	544.5	516.0	487.5
120°	639.4	640.9	642.7	646.3	649.9	653.5	657.1	659.5	661.9	664.2	666.6
122.5°	690.4	692.0	694.0	698.0	702.0	706.0	710.0	711.2	712.4	713.5	714.7
125°	739.1	740.4	742.3	746.1	749.9	753.7	757.5	758.9	760.3	761.6	763.0
127.5°	786.5	787.9	789.4	792.4	795.4	798.4	801.4	803.4	805.4	807.4	809.4
130°	832.1	833.7	834.8	837.0	839.1	841.3	843.5	845.7	847.9	850.1	852.3
132.5°	874.5	875.8	876.9	879.1	881.2	883.4	885.6	887.4	889.2	891.0	892.8
135°	914.5	916.1	917.0	918.8	920.6	922.4	924.2	926.2	928.2	930.2	932.2
137.5°	950.8	952.0	953.0	955.0	956.9	958.9	960.9	962.9	964.9	966.9	968.9
140°	986.1	986.9	988.0	990.2	992.4	994.6	996.8	998.6	1000.4	1002.2	1004.0
142.5°	1017.6	1018.3	1019.6	1022.2	1024.8	1027.4	1030.0	1031.6	1033.2	1034.7	1036.3
145°	1045.3	1045.2	1046.9	1050.3	1053.6	1057.0	1060.4	1061.8	1063.2	1064.6	1066.0
147.5°	1073.3	1073.0	1074.7	1078.1	1081.4	1084.8	1088.2	1089.2	1090.2	1091.2	1092.2
150°	1098.8	1098.1	1099.7	1102.9	1106.0	1109.2	1112.4	1113.6	1114.8	1116.0	1117.2
152.5°	1122.2	1121.4	1122.9	1125.9	1128.8	1131.8	1134.8	1136.0	1137.2	1138.4	1139.6
155°	1144.7	1143.8	1145.0	1147.4	1149.8	1152.2	1154.6	1155.8	1157.0	1158.1	1159.3
157.5°	1164.3	1163.5	1164.4	1166.2	1168.0	1169.8	1171.6	1173.0	1174.4	1175.8	1177.2
160°	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8	1188.0	1189.2	1190.4	1191.6
162.5°	1196.4	1195.8	1196.3	1197.3	1198.3	1199.3	1200.3	1201.7	1203.1	1204.5	1205.9
165°	1209.0	1208.4	1208.7	1209.3	1209.8	1210.4	1211.0	1212.4	1213.8	1215.2	1216.6
167.5°	1218.8	1218.2	1218.5	1219.1	1219.7	1220.3	1220.9	1222.3	1223.7	1225.1	1226.5
170°	1226.9	1226.3	1226.5	1226.9	1227.3	1227.7	1228.1	1229.5	1230.9	1232.2	1233.6
172.5°	1232.3	1231.7	1231.9	1232.3	1232.7	1233.1	1233.5	1234.9	1236.3	1237.6	1239.0
175°	1235.9	1235.2	1235.4	1235.8	1236.2	1236.6	1237.0	1238.4	1239.8	1241.2	1242.6
177.5°	1237.7	1237.0	1237.1	1237.3	1237.5	1237.7	1237.9	1239.3	1240.7	1242.1	1243.5
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	914.5	916.7	911.6	910.1	911.6	906.4	907.9	909.4	909.4	911.6	913.1
5°	861.4	858.5	853.3	851.8	850.4	852.6	851.1	853.3	854.1	859.2	860.0
7.5°	809.1	804.6	800.2	795.8	794.3	790.6	794.3	794.3	799.5	798.0	801.7
10°	747.1	746.4	740.5	738.3	735.3	729.4	737.5	735.3	739.0	745.6	747.1
12.5°	701.4	693.3	697.0	686.6	690.3	684.4	685.2	685.2	691.1	691.8	690.3
15°	657.9	651.2	641.6	637.2	635.0	632.1	641.6	642.4	638.0	648.3	644.6
17.5°	613.6	613.6	604.8	602.6	596.7	599.6	598.1	598.9	597.4	604.8	608.5
20°	575.3	571.6	568.6	569.4	562.0	560.5	559.0	560.5	565.7	570.8	572.3
22.5°	544.3	542.1	534.7	536.2	530.3	532.5	531.0	534.7	535.4	535.4	540.6
25°	514.8	511.8	512.6	509.6	507.4	507.4	505.2	507.4	510.4	511.8	512.6
27.5°	492.7	490.5	486.8	484.6	486.0	482.3	485.3	487.5	487.5	486.0	487.5
30°	466.1	467.6	467.6	460.2	463.2	461.7	463.9	465.4	465.4	466.1	464.6
32.5°	448.4	444.0	443.3	442.5	442.5	439.6	439.6	441.8	442.5	443.3	445.5
35°	424.8	424.8	421.1	423.3	420.4	421.1	420.4	421.1	422.6	420.4	422.6
37.5°	403.4	404.2	402.7	404.2	404.9	403.4	402.0	404.9	403.4	403.4	402.0
40°	385.0	384.3	385.0	385.0	385.0	385.7	384.3	384.3	384.3	382.8	381.3
42.5°	369.5	365.1	366.6	367.3	365.1	365.1	365.8	365.1	367.3	362.9	362.9
45°	347.4	345.9	346.6	346.6	348.1	345.9	347.4	348.1	345.9	345.2	343.7
47.5°	327.5	328.9	327.5	328.9	328.9	330.4	327.5	328.2	328.9	326.0	323.8
50°	307.5	307.5	309.8	309.0	309.8	308.3	308.3	307.5	308.3	306.8	304.6
52.5°	289.1	286.9	290.6	289.8	289.1	288.4	287.6	288.4	286.9	285.4	285.4
55°	266.2	266.2	268.5	269.2	269.2	267.7	266.2	267.0	266.2	265.5	264.8
57.5°	247.8	244.9	246.3	247.1	247.1	244.9	246.3	244.9	244.9	245.6	243.4
60°	224.2	224.2	222.7	224.9	224.9	223.5	223.5	224.2	222.7	222.0	221.3
62.5°	199.1	199.9	202.1	202.8	203.6	202.1	200.6	201.3	201.3	199.1	199.9
65°	177.7	179.2	182.2	181.4	180.0	180.7	179.2	180.0	177.7	178.5	176.3
67.5°	157.1	156.4	157.1	157.1	158.6	157.8	156.4	156.4	155.6	157.8	155.6
70°	135.0	135.0	135.0	135.0	135.7	136.4	135.0	133.5	134.2	132.8	132.0
72.5°	112.1	112.8	112.1	113.6	111.4	112.8	112.8	112.1	111.4	111.4	111.4
75°	90.7	92.2	90.0	90.7	90.0	91.5	90.7	90.7	89.2	88.5	89.2
77.5°	69.3	70.1	68.6	69.3	68.6	69.3	69.3	68.6	68.6	68.6	68.6
80°	49.4	50.2	49.4	48.7	47.9	49.4	47.9	48.7	49.4	48.7	50.2
82.5°	31.7	31.7	31.0	31.7	30.2	30.2	31.0	31.0	30.2	31.7	30.2
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.2	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	22.4	22.6	23.0	23.4	23.8	24.2	23.8	23.4	23.0	22.6	22.4
92.5°	23.3	23.4	23.6	23.8	24.0	24.2	24.0	23.8	23.6	23.4	23.3
95°	39.4	39.3	39.1	38.9	38.7	38.5	38.7	38.9	39.1	39.3	39.4
97.5°	48.4	48.5	48.7	48.9	49.1	49.3	49.1	48.9	48.7	48.5	48.4
100°	58.3	58.5	58.9	59.3	59.7	60.1	59.7	59.3	58.9	58.5	58.3
102.5°	62.7	63.0	63.6	64.2	64.8	65.4	64.8	64.2	63.6	63.0	62.7
105°	64.5	64.9	65.7	66.5	67.3	68.1	67.3	66.5	65.7	64.9	64.5
107.5°	66.3	66.7	67.5	68.3	69.1	69.9	69.1	68.3	67.5	66.7	66.3
110°	67.2	67.6	68.4	69.2	70.0	70.8	70.0	69.2	68.4	67.6	67.2

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.0	69.3	69.9	70.5	71.1	71.7	71.1	70.5	69.9	69.3	69.0
115°	138.0	130.8	116.5	102.2	87.8	73.5	87.8	102.2	116.5	130.8	138.0
117.5°	473.3	447.2	395.0	342.8	290.6	238.4	290.6	342.8	395.0	447.2	473.3
120°	667.8	654.4	627.5	600.6	573.7	546.8	573.7	600.6	627.5	654.4	667.8
122.5°	715.3	715.4	715.6	715.8	716.0	716.2	716.0	715.8	715.6	715.4	715.3
125°	763.7	764.0	764.6	765.2	765.8	766.4	765.8	765.2	764.6	764.0	763.7
127.5°	810.4	810.5	810.7	810.8	811.0	811.2	811.0	810.8	810.7	810.5	810.4
130°	853.4	853.3	853.1	852.9	852.7	852.5	852.7	852.9	853.1	853.3	853.4
132.5°	893.7	893.6	893.4	893.2	893.0	892.8	893.0	893.2	893.4	893.6	893.7
135°	933.2	933.0	932.6	932.2	931.8	931.4	931.8	932.2	932.6	933.0	933.2
137.5°	969.9	969.6	969.0	968.4	967.8	967.2	967.8	968.4	969.0	969.6	969.9
140°	1004.9	1004.4	1003.4	1002.4	1001.4	1000.4	1001.4	1002.4	1003.4	1004.4	1004.9
142.5°	1037.1	1036.6	1035.6	1034.7	1033.7	1032.7	1033.7	1034.7	1035.6	1036.6	1037.1
145°	1066.7	1066.2	1065.2	1064.2	1063.2	1062.2	1063.2	1064.2	1065.2	1066.2	1066.7
147.5°	1092.7	1092.3	1091.5	1090.7	1089.9	1089.1	1089.9	1090.7	1091.5	1092.3	1092.7
150°	1117.8	1117.3	1116.3	1115.3	1114.3	1113.3	1114.3	1115.3	1116.3	1117.3	1117.8
152.5°	1140.2	1139.5	1138.1	1136.8	1135.4	1134.0	1135.4	1136.8	1138.1	1139.5	1140.2
155°	1159.9	1159.1	1157.5	1156.0	1154.4	1152.8	1154.4	1156.0	1157.5	1159.1	1159.9
157.5°	1177.9	1177.1	1175.5	1173.9	1172.3	1170.7	1172.3	1173.9	1175.5	1177.1	1177.9
160°	1192.2	1191.5	1190.1	1188.7	1187.3	1185.9	1187.3	1188.7	1190.1	1191.5	1192.2
162.5°	1206.6	1205.7	1203.9	1202.1	1200.3	1198.5	1200.3	1202.1	1203.9	1205.7	1206.6
165°	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1212.4	1213.8	1215.2	1216.6	1217.3
167.5°	1227.2	1226.3	1224.5	1222.7	1220.9	1219.1	1220.9	1222.7	1224.5	1226.3	1227.2
170°	1234.3	1233.4	1231.6	1229.9	1228.1	1226.3	1228.1	1229.9	1231.6	1233.4	1234.3
172.5°	1239.7	1238.8	1237.0	1235.3	1233.5	1231.7	1233.5	1235.3	1237.0	1238.8	1239.7
175°	1243.3	1242.3	1240.3	1238.3	1236.3	1234.3	1236.3	1238.3	1240.3	1242.3	1243.3
177.5°	1244.2	1243.3	1241.5	1239.7	1237.9	1236.1	1237.9	1239.7	1241.5	1243.3	1244.2
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	910.8	916.7	914.5	906.4	916.0	916.0	922.6	922.6	930.8	933.7	938.1
5°	859.2	863.6	867.3	863.6	870.3	880.6	886.5	891.7	902.7	907.2	913.8
7.5°	803.9	812.0	815.7	815.7	826.8	838.6	850.4	857.7	873.2	879.1	885.8
10°	750.1	759.7	767.0	766.3	784.7	792.1	806.9	823.8	839.3	848.2	857.7
12.5°	693.3	698.4	708.8	723.5	727.9	741.2	758.2	779.6	807.6	815.7	829.7
15°	646.1	660.1	668.2	674.8	685.2	697.7	716.1	736.8	764.8	782.5	797.3
17.5°	606.2	624.7	629.8	628.4	641.6	660.8	682.2	697.7	722.8	744.2	758.2
20°	573.8	581.2	590.0	593.7	604.0	624.7	645.3	663.0	683.7	700.7	716.9
22.5°	541.3	547.2	554.6	561.3	569.4	581.2	601.1	623.2	643.1	659.3	677.8
25°	514.8	518.5	525.1	530.3	539.1	547.2	561.3	585.6	609.2	618.8	635.0
27.5°	489.0	491.9	496.4	502.3	506.7	514.8	527.3	547.2	571.6	581.2	603.3
30°	466.1	468.3	472.8	475.7	477.9	487.5	497.1	512.6	531.0	544.3	560.5
32.5°	444.7	446.9	451.4	452.1	455.1	460.2	469.1	483.1	499.3	510.4	524.4
35°	421.1	422.6	427.0	428.5	430.7	435.1	441.8	452.1	466.9	475.0	487.5
37.5°	402.7	402.0	404.9	407.1	410.1	412.3	414.5	424.8	435.9	443.3	452.8
40°	382.8	381.3	382.0	385.0	386.5	389.4	389.4	399.7	407.1	413.0	420.4
42.5°	362.9	362.1	360.7	362.1	363.6	364.3	365.1	372.5	379.8	385.0	393.1
45°	343.0	342.2	340.7	341.5	341.5	343.0	345.2	348.1	353.3	357.7	362.1
47.5°	324.5	323.0	320.8	320.1	321.6	321.6	321.6	324.5	329.7	331.1	335.6
50°	305.3	303.1	300.2	298.7	298.7	298.0	299.4	300.2	304.6	306.1	309.8
52.5°	284.7	283.2	280.3	277.3	278.0	276.6	277.3	278.0	279.5	281.7	283.9
55°	264.0	261.1	258.9	258.1	255.9	255.9	253.7	256.7	255.9	256.7	259.6
57.5°	244.1	241.2	237.5	236.0	233.8	233.1	231.6	230.8	231.6	233.8	236.0
60°	220.5	219.0	216.8	214.6	213.1	210.9	209.5	209.5	208.7	208.7	209.5
62.5°	197.7	196.9	194.0	193.2	191.8	190.3	188.1	186.6	186.6	188.1	188.8
65°	175.5	174.8	172.6	171.8	168.2	166.7	165.9	165.2	163.7	163.7	163.7
67.5°	154.9	152.7	152.7	149.0	146.0	144.6	143.1	142.3	142.3	142.3	143.1
70°	132.0	132.0	129.8	127.6	124.6	125.4	123.2	121.0	121.0	119.5	120.2
72.5°	109.9	109.2	106.9	106.2	104.0	101.8	100.3	101.8	99.6	98.8	99.6
75°	88.5	87.8	86.3	84.8	85.6	83.3	81.1	80.4	80.4	78.9	78.9
77.5°	67.9	69.3	66.4	65.6	64.2	62.7	62.0	61.2	61.2	61.2	62.7
80°	47.2	47.9	47.9	46.5	47.2	45.0	45.0	45.0	42.8	43.5	44.3
82.5°	30.2	30.2	29.5	30.2	29.5	29.5	28.8	28.8	28.0	28.0	28.8
85°	17.0	16.2	15.5	17.0	16.2	16.2	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	21.9	20.9	19.9	18.9	17.9	16.3	14.7	13.2	11.6	10.8	9.7
92.5°	23.1	22.7	22.3	21.9	21.5	20.9	20.3	19.7	19.1	18.8	19.2
95°	38.9	37.9	37.0	36.0	35.0	33.6	32.2	30.8	29.4	28.7	32.0
97.5°	48.1	47.5	46.9	46.3	45.7	42.5	39.3	36.2	33.0	31.4	39.6
100°	57.5	55.9	54.3	52.7	51.1	47.7	44.3	41.0	37.6	35.9	49.5
102.5°	61.6	59.4	57.3	55.1	52.9	89.1	125.4	161.6	197.9	216.0	216.2
105°	63.4	61.2	59.1	56.9	54.7	109.1	163.5	217.8	272.2	299.4	296.4
107.5°	65.2	63.0	60.9	58.7	56.5	123.6	190.8	257.9	325.0	358.6	356.1
110°	77.2	97.1	117.0	137.0	156.9	214.5	272.0	329.6	387.1	415.9	413.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	111.9	197.8	283.7	369.5	455.4	458.8	462.2	465.5	468.9	470.6	468.8
115°	184.1	276.4	368.6	460.9	553.1	548.1	543.1	538.2	533.2	530.7	529.0
117.5°	487.5	516.0	544.5	573.0	601.5	598.1	594.7	591.3	587.9	586.2	584.2
120°	666.6	664.2	661.9	659.5	657.1	653.5	649.9	646.3	642.7	640.9	639.4
122.5°	714.7	713.5	712.4	711.2	710.0	706.0	702.0	698.0	694.0	692.0	690.4
125°	763.0	761.6	760.3	758.9	757.5	753.7	749.9	746.1	742.3	740.4	739.1
127.5°	809.4	807.4	805.4	803.4	801.4	798.4	795.4	792.4	789.4	787.9	786.5
130°	852.3	850.1	847.9	845.7	843.5	841.3	839.1	837.0	834.8	833.7	832.1
132.5°	892.8	891.0	889.2	887.4	885.6	883.4	881.2	879.1	876.9	875.8	874.5
135°	932.2	930.2	928.2	926.2	924.2	922.4	920.6	918.8	917.0	916.1	914.5
137.5°	968.9	966.9	964.9	962.9	960.9	958.9	956.9	955.0	953.0	952.0	950.8
140°	1004.0	1002.2	1000.4	998.6	996.8	994.6	992.4	990.2	988.0	986.9	986.1
142.5°	1036.3	1034.7	1033.2	1031.6	1030.0	1027.4	1024.8	1022.2	1019.6	1018.3	1017.6
145°	1066.0	1064.6	1063.2	1061.8	1060.4	1057.0	1053.6	1050.3	1046.9	1045.2	1045.3
147.5°	1092.2	1091.2	1090.2	1089.2	1088.2	1084.8	1081.4	1078.1	1074.7	1073.0	1073.3
150°	1117.2	1116.0	1114.8	1113.6	1112.4	1109.2	1106.0	1102.9	1099.7	1098.1	1098.8
152.5°	1139.6	1138.4	1137.2	1136.0	1134.8	1131.8	1128.8	1125.9	1122.9	1121.4	1122.2
155°	1159.3	1158.1	1157.0	1155.8	1154.6	1152.2	1149.8	1147.4	1145.0	1143.8	1144.7
157.5°	1177.2	1175.8	1174.4	1173.0	1171.6	1169.8	1168.0	1166.2	1164.4	1163.5	1164.3
160°	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1184.4	1183.3	1182.1	1181.5	1182.1
162.5°	1205.9	1204.5	1203.1	1201.7	1200.3	1199.3	1198.3	1197.3	1196.3	1195.8	1196.4
165°	1216.6	1215.2	1213.8	1212.4	1211.0	1210.4	1209.8	1209.3	1208.7	1208.4	1209.0
167.5°	1226.5	1225.1	1223.7	1222.3	1220.9	1220.3	1219.7	1219.1	1218.5	1218.2	1218.8
170°	1233.6	1232.2	1230.9	1229.5	1228.1	1227.7	1227.3	1226.9	1226.5	1226.3	1226.9
172.5°	1239.0	1237.6	1236.3	1234.9	1233.5	1233.1	1232.7	1232.3	1231.9	1231.7	1232.3
175°	1242.6	1241.2	1239.8	1238.4	1237.0	1236.6	1236.2	1235.8	1235.4	1235.2	1235.9
177.5°	1243.5	1242.1	1240.7	1239.3	1237.9	1237.7	1237.5	1237.3	1237.1	1237.0	1237.7
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	959.5	959.5	959.5	959.5
2.5°	941.8	941.8	952.9	964.7
5°	921.2	926.3	944.0	960.3
7.5°	901.3	910.1	932.2	952.9
10°	876.9	888.7	916.0	940.3
12.5°	853.3	864.4	896.1	923.4
15°	820.1	834.1	868.1	902.0
17.5°	786.9	801.0	842.3	882.1
20°	747.9	766.3	812.8	865.9
22.5°	711.7	734.6	786.2	829.0
25°	671.9	707.3	755.2	810.5
27.5°	636.5	671.9	720.6	776.6
30°	596.7	632.8	683.0	734.6
32.5°	558.3	591.5	640.2	703.6
35°	518.5	550.2	597.4	661.6
37.5°	482.3	513.3	564.9	623.9
40°	446.9	479.4	523.6	582.6
42.5°	413.8	442.5	482.3	541.3
45°	383.5	404.2	441.0	496.4
47.5°	351.8	370.2	404.2	459.5
50°	322.3	337.8	367.3	418.9
52.5°	293.5	306.8	334.1	375.4
55°	267.7	280.3	300.2	340.7
57.5°	241.2	250.8	269.9	302.4
60°	215.4	224.2	239.7	266.2
62.5°	189.5	196.9	211.7	233.1
65°	166.7	172.6	183.6	202.1
67.5°	144.6	148.2	157.1	171.8
70°	123.2	126.1	133.5	145.3
72.5°	100.3	103.3	111.4	119.5
75°	81.1	81.9	87.8	94.4
77.5°	63.4	62.7	67.1	72.3
80°	43.5	45.7	49.4	51.6
82.5°	29.5	30.2	31.7	33.2
85°	16.2	17.0	17.0	19.2
87.5°	6.6	7.4	7.4	8.1
90°	7.5	5.3	3.1	0.9
92.5°	20.0	20.8	21.6	22.4
95°	38.6	45.1	51.7	58.3
97.5°	55.9	72.2	88.6	104.9
100°	76.8	104.1	131.4	158.7
102.5°	216.6	217.0	217.4	217.8
105°	290.4	284.5	278.5	272.5
107.5°	351.1	346.2	341.2	336.2
110°	409.6	405.5	401.3	397.1

TEST NUMBER: P1008129

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	465.2	461.7	458.1	454.5
115°	525.6	522.2	518.8	515.4
117.5°	580.2	576.3	572.3	568.3
120°	636.4	633.5	630.5	627.5
122.5°	687.2	684.1	680.9	677.7
125°	736.5	734.0	731.4	728.8
127.5°	783.7	781.0	778.2	775.4
130°	828.9	825.7	822.5	819.3
132.5°	871.9	869.3	866.7	864.1
135°	911.3	908.2	905.0	901.8
137.5°	948.4	946.0	943.6	941.2
140°	984.5	983.0	981.4	979.8
142.5°	1016.2	1014.8	1013.4	1012.0
145°	1045.5	1045.7	1045.9	1046.1
147.5°	1073.9	1074.5	1075.1	1075.7
150°	1100.2	1101.6	1103.0	1104.4
152.5°	1123.8	1125.4	1127.0	1128.6
155°	1146.5	1148.3	1150.1	1151.9
157.5°	1165.9	1167.5	1169.1	1170.7
160°	1183.3	1184.4	1185.6	1186.8
162.5°	1197.6	1198.8	1200.0	1201.2
165°	1210.2	1211.3	1212.5	1213.7
167.5°	1220.0	1221.2	1222.4	1223.6
170°	1228.1	1229.3	1230.5	1231.7
172.5°	1233.5	1234.6	1235.8	1237.0
175°	1237.3	1238.7	1240.1	1241.5
177.5°	1239.1	1240.5	1241.9	1243.3
180°	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)