

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008178

Luminaire Tested: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008178
REPORT IS A COMBINATION OF REPORTS P984551 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4870.0 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58		
1	100	96	92	89	93	90	87	84	78	76	73	67	65	64	57	56	55	50		
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43		
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41	37		
4	77	67	59	53	72	63	56	50	55	50	45	48	44	40	41	38	36	32		
5	71	60	52	46	66	56	49	44	49	44	40	43	39	35	37	34	31	28		
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28	25		
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	28	25	23		
8	57	45	37	32	53	42	35	30	37	32	28	33	29	25	29	25	23	20		
9	53	41	33	28	49	39	32	27	34	29	25	31	26	23	27	23	21	19		
10	50	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	2.5
10°-20°	355.8	7.3
20°-30°	516.4	10.6
30°-40°	544.4	11.2
40°-50°	481.8	9.9
50°-60°	384.7	7.9
60°-70°	261.3	5.4
70°-80°	133.7	2.7
80°-90°	32.8	0.7
90°-100°	22.9	0.5
100°-110°	85.4	1.8
110°-120°	226.5	4.7
120°-130°	375.7	7.7
130°-140°	399.0	8.2
140°-150°	370.9	7.6
150°-160°	298.2	6.1
160°-170°	192.1	3.9
170°-180°	66.1	1.4
0°-30°	994.6	20.4
0°-40°	1539.0	31.6
0°-60°	2405.4	49.4
0°-90°	2833.2	58.2
90°-120°	334.8	6.9
90°-150°	1480.4	30.4
90°-180°	2037.0	41.8
0°-180°	4870.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	0	14	0	14	0	3
95°	33	22	33	22	33	39
105°	153	38	153	38	153	163
115°	289	41	289	41	289	285
125°	409	430	409	430	409	365
135°	506	522	506	522	506	391
145°	587	596	587	596	587	367
155°	646	646	646	646	646	298
165°	681	679	681	679	681	192
175°	696	692	696	692	696	66
180°	695	695	695	695	695	

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.5	7.4	8.3	9.2	10.1
92.5°	12.6	12.2	11.7	11.3	10.8	10.6	10.8	11.1	11.4	11.8	12.1
95°	32.7	29.0	25.3	21.6	17.9	16.1	16.5	17.3	18.0	18.8	19.6
97.5°	58.8	49.6	40.5	31.3	22.2	17.6	18.5	20.3	22.0	23.8	25.6
100°	89.0	73.7	58.4	43.1	27.8	20.1	21.1	23.0	24.9	26.8	28.7
102.5°	122.2	122.0	121.8	121.5	121.3	121.2	111.0	90.7	70.4	50.0	29.7
105°	152.8	156.2	159.5	162.9	166.2	167.9	152.7	122.2	91.7	61.2	30.7
107.5°	188.5	191.3	194.1	196.9	199.7	201.1	182.3	144.6	107.0	69.3	31.7
110°	222.7	225.1	227.4	229.8	232.1	233.3	217.2	184.9	152.6	120.3	88.0

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	254.9	256.9	258.9	260.9	262.9	263.9	263.0	261.1	259.2	257.3	255.4
115°	289.1	291.0	292.9	294.8	296.7	297.6	299.0	301.8	304.6	307.4	310.2
117.5°	318.7	320.9	323.2	325.4	327.7	328.8	329.7	331.6	333.5	335.4	337.3
120°	351.9	353.6	355.2	356.9	358.6	359.4	360.4	362.4	364.5	366.5	368.5
122.5°	380.1	381.9	383.7	385.4	387.2	388.1	389.2	391.5	393.7	396.0	398.2
125°	408.7	410.1	411.6	413.0	414.5	415.2	416.3	418.4	420.5	422.7	424.8
127.5°	434.9	436.5	438.0	439.6	441.1	441.9	442.7	444.4	446.1	447.7	449.4
130°	459.5	461.3	463.1	464.8	466.6	467.5	468.1	469.4	470.6	471.9	473.1
132.5°	484.6	486.1	487.5	489.0	490.5	491.2	491.8	493.0	494.3	495.5	496.7
135°	505.7	507.5	509.3	511.1	512.9	513.8	514.3	515.3	516.3	517.3	518.3
137.5°	527.9	529.2	530.6	531.9	533.2	533.9	534.5	535.6	536.7	537.8	538.9
140°	549.5	550.4	551.3	552.2	553.1	553.5	554.1	555.3	556.6	557.8	559.0
142.5°	567.6	568.4	569.2	569.9	570.7	571.1	571.8	573.3	574.7	576.2	577.6
145°	586.7	586.6	586.5	586.4	586.3	586.2	587.1	589.0	590.9	592.8	594.7
147.5°	603.3	603.0	602.6	602.3	602.0	601.8	602.7	604.6	606.5	608.4	610.3
150°	619.3	618.5	617.7	617.0	616.2	615.8	616.7	618.5	620.3	622.1	623.9
152.5°	632.9	632.0	631.1	630.2	629.3	628.9	629.7	631.4	633.1	634.7	636.4
155°	646.0	645.0	644.0	643.0	642.0	641.5	642.2	643.5	644.8	646.2	647.5
157.5°	656.5	655.6	654.7	653.8	652.9	652.5	653.0	654.0	655.1	656.1	657.1
160°	665.6	664.9	664.3	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6
162.5°	673.6	672.9	672.3	671.6	670.9	670.6	670.9	671.4	672.0	672.5	673.1
165°	680.7	680.0	679.4	678.7	678.0	677.7	677.9	678.2	678.5	678.9	679.2
167.5°	686.2	685.5	684.9	684.2	683.5	683.2	683.4	683.7	684.0	684.4	684.7
170°	690.7	690.0	689.4	688.7	688.0	687.7	687.8	688.0	688.3	688.5	688.7
172.5°	693.7	693.0	692.4	691.7	691.0	690.7	690.8	691.0	691.3	691.5	691.7
175°	696.3	695.5	694.7	693.9	693.1	692.7	692.8	693.0	693.3	693.5	693.7
177.5°	697.3	696.5	695.7	694.9	694.1	693.7	693.8	693.9	694.0	694.2	694.3
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	10.7	11.2	11.8	12.3	12.6	12.7	12.9	13.2	13.4	13.6	13.4
92.5°	12.3	12.5	12.8	13.0	13.1	13.2	13.3	13.4	13.5	13.6	13.5
95°	20.2	20.7	21.3	21.8	22.1	22.0	21.9	21.8	21.7	21.6	21.7
97.5°	25.9	26.3	26.6	26.9	27.1	27.2	27.3	27.4	27.5	27.6	27.5
100°	29.6	30.5	31.4	32.3	32.7	32.8	33.0	33.3	33.5	33.7	33.5
102.5°	30.9	32.1	33.4	34.6	35.2	35.4	35.7	36.0	36.4	36.7	36.4
105°	31.9	33.1	34.4	35.6	36.2	36.4	36.9	37.3	37.8	38.2	37.8
107.5°	32.9	34.1	35.4	36.6	37.2	37.4	37.9	38.3	38.8	39.2	38.8
110°	76.8	65.6	54.5	43.3	37.7	37.9	38.4	38.8	39.3	39.7	39.3

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	207.2	159.1	110.9	62.8	38.7	38.9	39.2	39.5	39.9	40.2	39.9
115°	258.5	206.7	155.0	103.3	77.4	73.4	65.3	57.3	49.2	41.2	49.2
117.5°	321.3	305.3	289.4	273.4	265.4	250.8	221.5	192.2	163.0	133.7	163.0
120°	369.8	371.2	372.5	373.8	374.5	367.0	351.9	336.8	321.8	306.7	321.8
122.5°	398.9	399.5	400.2	400.9	401.2	401.3	401.4	401.5	401.6	401.7	401.6
125°	425.6	426.4	427.1	427.9	428.3	428.5	428.8	429.1	429.5	429.8	429.5
127.5°	450.5	451.7	452.8	453.9	454.5	454.6	454.7	454.8	454.9	455.0	454.9
130°	474.3	475.5	476.8	478.0	478.6	478.5	478.4	478.3	478.2	478.1	478.2
132.5°	497.7	498.7	499.7	500.7	501.2	501.1	501.0	500.9	500.8	500.7	500.8
135°	519.4	520.5	521.6	522.7	523.3	523.2	523.0	522.7	522.5	522.3	522.5
137.5°	540.0	541.1	542.2	543.3	543.9	543.7	543.4	543.1	542.7	542.4	542.7
140°	560.0	561.0	562.0	563.0	563.5	563.2	562.7	562.1	561.6	561.0	561.6
142.5°	578.5	579.4	580.3	581.2	581.6	581.3	580.8	580.2	579.7	579.1	579.7
145°	595.5	596.3	597.0	597.8	598.2	597.9	597.4	596.8	596.3	595.7	596.3
147.5°	610.9	611.4	612.0	612.5	612.8	612.6	612.1	611.7	611.2	610.8	611.2
150°	624.6	625.2	625.9	626.6	626.9	626.6	626.1	625.5	625.0	624.4	625.0
152.5°	637.1	637.8	638.5	639.2	639.5	639.1	638.3	637.5	636.7	635.9	636.7
155°	648.2	648.8	649.5	650.2	650.5	650.1	649.2	648.3	647.4	646.5	647.4
157.5°	657.9	658.7	659.4	660.2	660.6	660.1	659.2	658.3	657.4	656.5	657.4
160°	666.3	666.9	667.6	668.3	668.6	668.2	667.4	666.7	665.9	665.1	665.9
162.5°	673.9	674.7	675.5	676.3	676.7	676.2	675.2	674.1	673.1	672.1	673.1
165°	680.0	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	680.0
167.5°	685.5	686.3	687.0	687.8	688.2	687.7	686.7	685.7	684.7	683.7	684.7
170°	689.5	690.3	691.0	691.8	692.2	691.7	690.7	689.7	688.7	687.7	688.7
172.5°	692.5	693.3	694.1	694.9	695.3	694.8	693.8	692.7	691.7	690.7	691.7
175°	694.5	695.3	696.1	696.9	697.3	696.7	695.6	694.5	693.3	692.2	693.3
177.5°	695.1	695.9	696.6	697.4	697.8	697.3	696.3	695.2	694.2	693.2	694.2
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	13.2	12.9	12.7	12.6	12.3	11.8	11.2	10.7	10.1	9.2	8.3
92.5°	13.4	13.3	13.2	13.1	13.0	12.8	12.5	12.3	12.1	11.8	11.4
95°	21.8	21.9	22.0	22.1	21.8	21.3	20.7	20.2	19.6	18.8	18.0
97.5°	27.4	27.3	27.2	27.1	26.9	26.6	26.3	25.9	25.6	23.8	22.0
100°	33.3	33.0	32.8	32.7	32.3	31.4	30.5	29.6	28.7	26.8	24.9
102.5°	36.0	35.7	35.4	35.2	34.6	33.4	32.1	30.9	29.7	50.0	70.4
105°	37.3	36.9	36.4	36.2	35.6	34.4	33.1	31.9	30.7	61.2	91.7
107.5°	38.3	37.9	37.4	37.2	36.6	35.4	34.1	32.9	31.7	69.3	107.0
110°	38.8	38.4	37.9	37.7	43.3	54.5	65.6	76.8	88.0	120.3	152.6

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	39.5	39.2	38.9	38.7	62.8	110.9	159.1	207.2	255.4	257.3	259.2
115°	57.3	65.3	73.4	77.4	103.3	155.0	206.7	258.5	310.2	307.4	304.6
117.5°	192.2	221.5	250.8	265.4	273.4	289.4	305.3	321.3	337.3	335.4	333.5
120°	336.8	351.9	367.0	374.5	373.8	372.5	371.2	369.8	368.5	366.5	364.5
122.5°	401.5	401.4	401.3	401.2	400.9	400.2	399.5	398.9	398.2	396.0	393.7
125°	429.1	428.8	428.5	428.3	427.9	427.1	426.4	425.6	424.8	422.7	420.5
127.5°	454.8	454.7	454.6	454.5	453.9	452.8	451.7	450.5	449.4	447.7	446.1
130°	478.3	478.4	478.5	478.6	478.0	476.8	475.5	474.3	473.1	471.9	470.6
132.5°	500.9	501.0	501.1	501.2	500.7	499.7	498.7	497.7	496.7	495.5	494.3
135°	522.7	523.0	523.2	523.3	522.7	521.6	520.5	519.4	518.3	517.3	516.3
137.5°	543.1	543.4	543.7	543.9	543.3	542.2	541.1	540.0	538.9	537.8	536.7
140°	562.1	562.7	563.2	563.5	563.0	562.0	561.0	560.0	559.0	557.8	556.6
142.5°	580.2	580.8	581.3	581.6	581.2	580.3	579.4	578.5	577.6	576.2	574.7
145°	596.8	597.4	597.9	598.2	597.8	597.0	596.3	595.5	594.7	592.8	590.9
147.5°	611.7	612.1	612.6	612.8	612.5	612.0	611.4	610.9	610.3	608.4	606.5
150°	625.5	626.1	626.6	626.9	626.6	625.9	625.2	624.6	623.9	622.1	620.3
152.5°	637.5	638.3	639.1	639.5	639.2	638.5	637.8	637.1	636.4	634.7	633.1
155°	648.3	649.2	650.1	650.5	650.2	649.5	648.8	648.2	647.5	646.2	644.8
157.5°	658.3	659.2	660.1	660.6	660.2	659.4	658.7	657.9	657.1	656.1	655.1
160°	666.7	667.4	668.2	668.6	668.3	667.6	666.9	666.3	665.6	664.9	664.3
162.5°	674.1	675.2	676.2	676.7	676.3	675.5	674.7	673.9	673.1	672.5	672.0
165°	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	678.9	678.5
167.5°	685.7	686.7	687.7	688.2	687.8	687.0	686.3	685.5	684.7	684.4	684.0
170°	689.7	690.7	691.7	692.2	691.8	691.0	690.3	689.5	688.7	688.5	688.3
172.5°	692.7	693.8	694.8	695.3	694.9	694.1	693.3	692.5	691.7	691.5	691.3
175°	694.5	695.6	696.7	697.3	696.9	696.1	695.3	694.5	693.7	693.5	693.3
177.5°	695.2	696.3	697.3	697.8	697.4	696.6	695.9	695.1	694.3	694.2	694.0
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	7.4	6.5	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	11.1	10.8	10.6	10.8	11.3	11.7	12.2	12.6	12.2	11.7	11.3
95°	17.3	16.5	16.1	17.9	21.6	25.3	29.0	32.7	29.0	25.3	21.6
97.5°	20.3	18.5	17.6	22.2	31.3	40.5	49.6	58.8	49.6	40.5	31.3
100°	23.0	21.1	20.1	27.8	43.1	58.4	73.7	89.0	73.7	58.4	43.1
102.5°	90.7	111.0	121.2	121.3	121.5	121.8	122.0	122.2	122.0	121.8	121.5
105°	122.2	152.7	167.9	166.2	162.9	159.5	156.2	152.8	156.2	159.5	162.9
107.5°	144.6	182.3	201.1	199.7	196.9	194.1	191.3	188.5	191.3	194.1	196.9
110°	184.9	217.2	233.3	232.1	229.8	227.4	225.1	222.7	225.1	227.4	229.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	261.1	263.0	263.9	262.9	260.9	258.9	256.9	254.9	256.9	258.9	260.9
115°	301.8	299.0	297.6	296.7	294.8	292.9	291.0	289.1	291.0	292.9	294.8
117.5°	331.6	329.7	328.8	327.7	325.4	323.2	320.9	318.7	320.9	323.2	325.4
120°	362.4	360.4	359.4	358.6	356.9	355.2	353.6	351.9	353.6	355.2	356.9
122.5°	391.5	389.2	388.1	387.2	385.4	383.7	381.9	380.1	381.9	383.7	385.4
125°	418.4	416.3	415.2	414.5	413.0	411.6	410.1	408.7	410.1	411.6	413.0
127.5°	444.4	442.7	441.9	441.1	439.6	438.0	436.5	434.9	436.5	438.0	439.6
130°	469.4	468.1	467.5	466.6	464.8	463.1	461.3	459.5	461.3	463.1	464.8
132.5°	493.0	491.8	491.2	490.5	489.0	487.5	486.1	484.6	486.1	487.5	489.0
135°	515.3	514.3	513.8	512.9	511.1	509.3	507.5	505.7	507.5	509.3	511.1
137.5°	535.6	534.5	533.9	533.2	531.9	530.6	529.2	527.9	529.2	530.6	531.9
140°	555.3	554.1	553.5	553.1	552.2	551.3	550.4	549.5	550.4	551.3	552.2
142.5°	573.3	571.8	571.1	570.7	569.9	569.2	568.4	567.6	568.4	569.2	569.9
145°	589.0	587.1	586.2	586.3	586.4	586.5	586.6	586.7	586.6	586.5	586.4
147.5°	604.6	602.7	601.8	602.0	602.3	602.6	603.0	603.3	603.0	602.6	602.3
150°	618.5	616.7	615.8	616.2	617.0	617.7	618.5	619.3	618.5	617.7	617.0
152.5°	631.4	629.7	628.9	629.3	630.2	631.1	632.0	632.9	632.0	631.1	630.2
155°	643.5	642.2	641.5	642.0	643.0	644.0	645.0	646.0	645.0	644.0	643.0
157.5°	654.0	653.0	652.5	652.9	653.8	654.7	655.6	656.5	655.6	654.7	653.8
160°	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6	664.9	664.3	663.6
162.5°	671.4	670.9	670.6	670.9	671.6	672.3	672.9	673.6	672.9	672.3	671.6
165°	678.2	677.9	677.7	678.0	678.7	679.4	680.0	680.7	680.0	679.4	678.7
167.5°	683.7	683.4	683.2	683.5	684.2	684.9	685.5	686.2	685.5	684.9	684.2
170°	688.0	687.8	687.7	688.0	688.7	689.4	690.0	690.7	690.0	689.4	688.7
172.5°	691.0	690.8	690.7	691.0	691.7	692.4	693.0	693.7	693.0	692.4	691.7
175°	693.0	692.8	692.7	693.1	693.9	694.7	695.5	696.3	695.5	694.7	693.9
177.5°	693.9	693.8	693.7	694.1	694.9	695.7	696.5	697.3	696.5	695.7	694.9
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	5.4	6.0	6.5	7.4	8.3	9.2	10.1	10.7	11.2	11.8	12.3
92.5°	10.8	10.6	10.8	11.1	11.4	11.8	12.1	12.3	12.5	12.8	13.0
95°	17.9	16.1	16.5	17.3	18.0	18.8	19.6	20.2	20.7	21.3	21.8
97.5°	22.2	17.6	18.5	20.3	22.0	23.8	25.6	25.9	26.3	26.6	26.9
100°	27.8	20.1	21.1	23.0	24.9	26.8	28.7	29.6	30.5	31.4	32.3
102.5°	121.3	121.2	111.0	90.7	70.4	50.0	29.7	30.9	32.1	33.4	34.6
105°	166.2	167.9	152.7	122.2	91.7	61.2	30.7	31.9	33.1	34.4	35.6
107.5°	199.7	201.1	182.3	144.6	107.0	69.3	31.7	32.9	34.1	35.4	36.6
110°	232.1	233.3	217.2	184.9	152.6	120.3	88.0	76.8	65.6	54.5	43.3

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	262.9	263.9	263.0	261.1	259.2	257.3	255.4	207.2	159.1	110.9	62.8
115°	296.7	297.6	299.0	301.8	304.6	307.4	310.2	258.5	206.7	155.0	103.3
117.5°	327.7	328.8	329.7	331.6	333.5	335.4	337.3	321.3	305.3	289.4	273.4
120°	358.6	359.4	360.4	362.4	364.5	366.5	368.5	369.8	371.2	372.5	373.8
122.5°	387.2	388.1	389.2	391.5	393.7	396.0	398.2	398.9	399.5	400.2	400.9
125°	414.5	415.2	416.3	418.4	420.5	422.7	424.8	425.6	426.4	427.1	427.9
127.5°	441.1	441.9	442.7	444.4	446.1	447.7	449.4	450.5	451.7	452.8	453.9
130°	466.6	467.5	468.1	469.4	470.6	471.9	473.1	474.3	475.5	476.8	478.0
132.5°	490.5	491.2	491.8	493.0	494.3	495.5	496.7	497.7	498.7	499.7	500.7
135°	512.9	513.8	514.3	515.3	516.3	517.3	518.3	519.4	520.5	521.6	522.7
137.5°	533.2	533.9	534.5	535.6	536.7	537.8	538.9	540.0	541.1	542.2	543.3
140°	553.1	553.5	554.1	555.3	556.6	557.8	559.0	560.0	561.0	562.0	563.0
142.5°	570.7	571.1	571.8	573.3	574.7	576.2	577.6	578.5	579.4	580.3	581.2
145°	586.3	586.2	587.1	589.0	590.9	592.8	594.7	595.5	596.3	597.0	597.8
147.5°	602.0	601.8	602.7	604.6	606.5	608.4	610.3	610.9	611.4	612.0	612.5
150°	616.2	615.8	616.7	618.5	620.3	622.1	623.9	624.6	625.2	625.9	626.6
152.5°	629.3	628.9	629.7	631.4	633.1	634.7	636.4	637.1	637.8	638.5	639.2
155°	642.0	641.5	642.2	643.5	644.8	646.2	647.5	648.2	648.8	649.5	650.2
157.5°	652.9	652.5	653.0	654.0	655.1	656.1	657.1	657.9	658.7	659.4	660.2
160°	662.9	662.6	662.9	663.6	664.3	664.9	665.6	666.3	666.9	667.6	668.3
162.5°	670.9	670.6	670.9	671.4	672.0	672.5	673.1	673.9	674.7	675.5	676.3
165°	678.0	677.7	677.9	678.2	678.5	678.9	679.2	680.0	680.8	681.5	682.3
167.5°	683.5	683.2	683.4	683.7	684.0	684.4	684.7	685.5	686.3	687.0	687.8
170°	688.0	687.7	687.8	688.0	688.3	688.5	688.7	689.5	690.3	691.0	691.8
172.5°	691.0	690.7	690.8	691.0	691.3	691.5	691.7	692.5	693.3	694.1	694.9
175°	693.1	692.7	692.8	693.0	693.3	693.5	693.7	694.5	695.3	696.1	696.9
177.5°	694.1	693.7	693.8	693.9	694.0	694.2	694.3	695.1	695.9	696.6	697.4
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	12.6	12.7	12.9	13.2	13.4	13.6	13.4	13.2	12.9	12.7	12.6
92.5°	13.1	13.2	13.3	13.4	13.5	13.6	13.5	13.4	13.3	13.2	13.1
95°	22.1	22.0	21.9	21.8	21.7	21.6	21.7	21.8	21.9	22.0	22.1
97.5°	27.1	27.2	27.3	27.4	27.5	27.6	27.5	27.4	27.3	27.2	27.1
100°	32.7	32.8	33.0	33.3	33.5	33.7	33.5	33.3	33.0	32.8	32.7
102.5°	35.2	35.4	35.7	36.0	36.4	36.7	36.4	36.0	35.7	35.4	35.2
105°	36.2	36.4	36.9	37.3	37.8	38.2	37.8	37.3	36.9	36.4	36.2
107.5°	37.2	37.4	37.9	38.3	38.8	39.2	38.8	38.3	37.9	37.4	37.2
110°	37.7	37.9	38.4	38.8	39.3	39.7	39.3	38.8	38.4	37.9	37.7

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	38.7	38.9	39.2	39.5	39.9	40.2	39.9	39.5	39.2	38.9	38.7
115°	77.4	73.4	65.3	57.3	49.2	41.2	49.2	57.3	65.3	73.4	77.4
117.5°	265.4	250.8	221.5	192.2	163.0	133.7	163.0	192.2	221.5	250.8	265.4
120°	374.5	367.0	351.9	336.8	321.8	306.7	321.8	336.8	351.9	367.0	374.5
122.5°	401.2	401.3	401.4	401.5	401.6	401.7	401.6	401.5	401.4	401.3	401.2
125°	428.3	428.5	428.8	429.1	429.5	429.8	429.5	429.1	428.8	428.5	428.3
127.5°	454.5	454.6	454.7	454.8	454.9	455.0	454.9	454.8	454.7	454.6	454.5
130°	478.6	478.5	478.4	478.3	478.2	478.1	478.2	478.3	478.4	478.5	478.6
132.5°	501.2	501.1	501.0	500.9	500.8	500.7	500.8	500.9	501.0	501.1	501.2
135°	523.3	523.2	523.0	522.7	522.5	522.3	522.5	522.7	523.0	523.2	523.3
137.5°	543.9	543.7	543.4	543.1	542.7	542.4	542.7	543.1	543.4	543.7	543.9
140°	563.5	563.2	562.7	562.1	561.6	561.0	561.6	562.1	562.7	563.2	563.5
142.5°	581.6	581.3	580.8	580.2	579.7	579.1	579.7	580.2	580.8	581.3	581.6
145°	598.2	597.9	597.4	596.8	596.3	595.7	596.3	596.8	597.4	597.9	598.2
147.5°	612.8	612.6	612.1	611.7	611.2	610.8	611.2	611.7	612.1	612.6	612.8
150°	626.9	626.6	626.1	625.5	625.0	624.4	625.0	625.5	626.1	626.6	626.9
152.5°	639.5	639.1	638.3	637.5	636.7	635.9	636.7	637.5	638.3	639.1	639.5
155°	650.5	650.1	649.2	648.3	647.4	646.5	647.4	648.3	649.2	650.1	650.5
157.5°	660.6	660.1	659.2	658.3	657.4	656.5	657.4	658.3	659.2	660.1	660.6
160°	668.6	668.2	667.4	666.7	665.9	665.1	665.9	666.7	667.4	668.2	668.6
162.5°	676.7	676.2	675.2	674.1	673.1	672.1	673.1	674.1	675.2	676.2	676.7
165°	682.7	682.3	681.5	680.8	680.0	679.2	680.0	680.8	681.5	682.3	682.7
167.5°	688.2	687.7	686.7	685.7	684.7	683.7	684.7	685.7	686.7	687.7	688.2
170°	692.2	691.7	690.7	689.7	688.7	687.7	688.7	689.7	690.7	691.7	692.2
172.5°	695.3	694.8	693.8	692.7	691.7	690.7	691.7	692.7	693.8	694.8	695.3
175°	697.3	696.7	695.6	694.5	693.3	692.2	693.3	694.5	695.6	696.7	697.3
177.5°	697.8	697.3	696.3	695.2	694.2	693.2	694.2	695.2	696.3	697.3	697.8
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	12.3	11.8	11.2	10.7	10.1	9.2	8.3	7.4	6.5	6.0	5.4
92.5°	13.0	12.8	12.5	12.3	12.1	11.8	11.4	11.1	10.8	10.6	10.8
95°	21.8	21.3	20.7	20.2	19.6	18.8	18.0	17.3	16.5	16.1	17.9
97.5°	26.9	26.6	26.3	25.9	25.6	23.8	22.0	20.3	18.5	17.6	22.2
100°	32.3	31.4	30.5	29.6	28.7	26.8	24.9	23.0	21.1	20.1	27.8
102.5°	34.6	33.4	32.1	30.9	29.7	50.0	70.4	90.7	111.0	121.2	121.3
105°	35.6	34.4	33.1	31.9	30.7	61.2	91.7	122.2	152.7	167.9	166.2
107.5°	36.6	35.4	34.1	32.9	31.7	69.3	107.0	144.6	182.3	201.1	199.7
110°	43.3	54.5	65.6	76.8	88.0	120.3	152.6	184.9	217.2	233.3	232.1

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	62.8	110.9	159.1	207.2	255.4	257.3	259.2	261.1	263.0	263.9	262.9
115°	103.3	155.0	206.7	258.5	310.2	307.4	304.6	301.8	299.0	297.6	296.7
117.5°	273.4	289.4	305.3	321.3	337.3	335.4	333.5	331.6	329.7	328.8	327.7
120°	373.8	372.5	371.2	369.8	368.5	366.5	364.5	362.4	360.4	359.4	358.6
122.5°	400.9	400.2	399.5	398.9	398.2	396.0	393.7	391.5	389.2	388.1	387.2
125°	427.9	427.1	426.4	425.6	424.8	422.7	420.5	418.4	416.3	415.2	414.5
127.5°	453.9	452.8	451.7	450.5	449.4	447.7	446.1	444.4	442.7	441.9	441.1
130°	478.0	476.8	475.5	474.3	473.1	471.9	470.6	469.4	468.1	467.5	466.6
132.5°	500.7	499.7	498.7	497.7	496.7	495.5	494.3	493.0	491.8	491.2	490.5
135°	522.7	521.6	520.5	519.4	518.3	517.3	516.3	515.3	514.3	513.8	512.9
137.5°	543.3	542.2	541.1	540.0	538.9	537.8	536.7	535.6	534.5	533.9	533.2
140°	563.0	562.0	561.0	560.0	559.0	557.8	556.6	555.3	554.1	553.5	553.1
142.5°	581.2	580.3	579.4	578.5	577.6	576.2	574.7	573.3	571.8	571.1	570.7
145°	597.8	597.0	596.3	595.5	594.7	592.8	590.9	589.0	587.1	586.2	586.3
147.5°	612.5	612.0	611.4	610.9	610.3	608.4	606.5	604.6	602.7	601.8	602.0
150°	626.6	625.9	625.2	624.6	623.9	622.1	620.3	618.5	616.7	615.8	616.2
152.5°	639.2	638.5	637.8	637.1	636.4	634.7	633.1	631.4	629.7	628.9	629.3
155°	650.2	649.5	648.8	648.2	647.5	646.2	644.8	643.5	642.2	641.5	642.0
157.5°	660.2	659.4	658.7	657.9	657.1	656.1	655.1	654.0	653.0	652.5	652.9
160°	668.3	667.6	666.9	666.3	665.6	664.9	664.3	663.6	662.9	662.6	662.9
162.5°	676.3	675.5	674.7	673.9	673.1	672.5	672.0	671.4	670.9	670.6	670.9
165°	682.3	681.5	680.8	680.0	679.2	678.9	678.5	678.2	677.9	677.7	678.0
167.5°	687.8	687.0	686.3	685.5	684.7	684.4	684.0	683.7	683.4	683.2	683.5
170°	691.8	691.0	690.3	689.5	688.7	688.5	688.3	688.0	687.8	687.7	688.0
172.5°	694.9	694.1	693.3	692.5	691.7	691.5	691.3	691.0	690.8	690.7	691.0
175°	696.9	696.1	695.3	694.5	693.7	693.5	693.3	693.0	692.8	692.7	693.1
177.5°	697.4	696.6	695.9	695.1	694.3	694.2	694.0	693.9	693.8	693.7	694.1
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	4.2	2.9	1.7	0.5
92.5°	11.3	11.7	12.2	12.6
95°	21.6	25.3	29.0	32.7
97.5°	31.3	40.5	49.6	58.8
100°	43.1	58.4	73.7	89.0
102.5°	121.5	121.8	122.0	122.2
105°	162.9	159.5	156.2	152.8
107.5°	196.9	194.1	191.3	188.5
110°	229.8	227.4	225.1	222.7

TEST NUMBER: P1008178

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	260.9	258.9	256.9	254.9
115°	294.8	292.9	291.0	289.1
117.5°	325.4	323.2	320.9	318.7
120°	356.9	355.2	353.6	351.9
122.5°	385.4	383.7	381.9	380.1
125°	413.0	411.6	410.1	408.7
127.5°	439.6	438.0	436.5	434.9
130°	464.8	463.1	461.3	459.5
132.5°	489.0	487.5	486.1	484.6
135°	511.1	509.3	507.5	505.7
137.5°	531.9	530.6	529.2	527.9
140°	552.2	551.3	550.4	549.5
142.5°	569.9	569.2	568.4	567.6
145°	586.4	586.5	586.6	586.7
147.5°	602.3	602.6	603.0	603.3
150°	617.0	617.7	618.5	619.3
152.5°	630.2	631.1	632.0	632.9
155°	643.0	644.0	645.0	646.0
157.5°	653.8	654.7	655.6	656.5
160°	663.6	664.3	664.9	665.6
162.5°	671.6	672.3	672.9	673.6
165°	678.7	679.4	680.0	680.7
167.5°	684.2	684.9	685.5	686.2
170°	688.7	689.4	690.0	690.7
172.5°	691.7	692.4	693.0	693.7
175°	693.9	694.7	695.5	696.3
177.5°	694.9	695.7	696.5	697.3
180°	694.8	694.8	694.8	694.8

(END OF REPORT)