

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008249

Luminaire Tested: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008249
REPORT IS A COMBINATION OF REPORTS P984847 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5856.0 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	102	97	94	90	95	92	88	85	81	79	76	71	69	68	62	61	60	55		
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	55	53	51	47		
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	50	47	44	41		
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39	36		
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	31		
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	30	28		
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25		
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25	22		
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	22	20		
10	51	38	31	26	48	37	30	26	33	28	24	30	26	22	27	23	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26934	26934	26934	26934
5°	26998	28717	27101	22848
10°	26685	31350	26851	18836
15°	26038	33067	26399	15866
20°	25631	31047	25631	13791
25°	24814	26673	24926	12333
30°	23470	20967	23917	11171
35°	22279	14498	22651	10221
40°	20911	10946	21150	9463
45°	19224	8995	19538	8646
50°	17763	7896	17796	7915
55°	16100	6728	16204	7120
60°	14326	5619	14526	6215
65°	12737	4571	12972	5307
70°	11156	3586	11442	4279
75°	9364	2603	9728	3105
80°	7305	1650	7832	1842
85°	4803	830	5170	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27842 cd/sqm

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.1	2.8
10°-20°	471.7	8.1
20°-30°	684.6	11.7
30°-40°	721.7	12.3
40°-50°	638.6	10.9
50°-60°	509.9	8.7
60°-70°	346.4	5.9
70°-80°	177.2	3.0
80°-90°	43.1	0.7
90°-100°	23.6	0.4
100°-110°	88.1	1.5
110°-120°	233.6	4.0
120°-130°	387.5	6.6
130°-140°	411.6	7.0
140°-150°	382.5	6.5
150°-160°	307.5	5.3
160°-170°	198.2	3.4
170°-180°	68.2	1.2
0°-30°	1318.3	22.5
0°-40°	2040.0	34.8
0°-60°	3188.6	54.4
0°-90°	3755.3	64.1
90°-120°	345.3	5.9
90°-150°	1526.9	26.1
90°-180°	2101.0	35.9
0°-180°	5856.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1702	1702	1702	1702	1702	
5°	1703	1900	1709	1512	1703	161
15°	1600	2336	1622	1121	1600	452
25°	1437	1946	1444	900	1437	657
35°	1173	1059	1193	747	1173	734
45°	880	638	895	613	880	683
55°	604	449	608	475	604	539
65°	358	276	365	320	358	356
75°	167	136	174	162	167	180
85°	34	35	37	26	34	40
90°	0	14	0	14	0	4
95°	34	22	34	22	34	40
105°	158	39	158	39	158	168
115°	298	42	298	42	298	293
125°	422	443	422	443	422	376
135°	522	539	522	539	522	403
145°	605	614	605	614	605	378
155°	666	667	666	667	666	307
165°	702	700	702	700	702	198
175°	718	714	718	714	718	68
180°	717	717	717	717	717	

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1710.6	1714.6	1721.1	1722.4	1735.5	1746.0	1757.7	1757.7	1761.6	1760.3	1749.9
5°	1702.8	1714.6	1731.6	1746.0	1769.5	1780.0	1795.7	1807.4	1817.9	1825.7	1824.4
7.5°	1689.7	1710.6	1735.5	1763.0	1794.3	1812.7	1834.9	1855.8	1870.2	1883.3	1892.4
10°	1667.5	1702.8	1736.8	1773.4	1814.0	1838.8	1865.0	1892.4	1914.7	1939.5	1963.1
12.5°	1637.4	1688.4	1730.3	1778.6	1828.3	1855.8	1897.7	1918.6	1961.7	2024.5	2041.5
15°	1599.5	1668.8	1708.0	1769.5	1834.9	1857.1	1914.7	1948.7	2037.6	2076.8	2123.9
17.5°	1564.2	1641.3	1693.6	1764.3	1828.3	1871.5	1927.7	1997.1	2071.6	2127.8	2180.2
20°	1535.4	1609.9	1672.7	1751.2	1832.3	1887.2	1946.1	2029.8	2110.8	2168.4	2208.9
22.5°	1470.0	1565.5	1638.7	1726.3	1824.4	1900.3	1956.5	2048.1	2135.7	2171.0	2206.3
25°	1437.3	1519.7	1604.7	1704.1	1819.2	1909.4	1957.8	2059.8	2137.0	2150.1	2157.9
27.5°	1377.1	1470.0	1569.4	1683.2	1817.9	1893.7	1955.2	2048.1	2109.5	2100.4	2076.8
30°	1302.6	1416.4	1526.2	1649.2	1799.6	1882.0	1939.5	2024.5	2055.9	2008.8	1967.0
32.5°	1247.7	1354.9	1476.5	1619.1	1778.6	1857.1	1913.4	1980.1	1986.6	1901.6	1831.0
35°	1173.1	1292.1	1429.5	1579.9	1743.3	1814.0	1866.3	1906.8	1875.4	1756.4	1672.7
37.5°	1106.4	1224.1	1370.6	1523.6	1694.9	1764.3	1806.1	1812.7	1735.5	1630.9	1507.9
40°	1033.2	1154.8	1307.8	1468.7	1641.3	1701.5	1727.6	1708.0	1596.9	1475.2	1332.7
42.5°	959.9	1080.3	1245.1	1409.8	1573.3	1624.3	1634.8	1581.2	1445.2	1302.6	1137.8
45°	880.2	1005.7	1170.5	1336.6	1494.9	1523.6	1524.9	1447.8	1286.9	1137.8	984.8
47.5°	814.8	931.2	1094.7	1260.7	1394.1	1413.8	1405.9	1317.0	1141.7	974.3	840.9
50°	742.8	854.0	1016.2	1179.7	1293.4	1298.7	1279.1	1152.2	980.9	827.9	721.9
52.5°	665.7	778.2	927.3	1084.2	1186.2	1178.4	1140.4	1004.4	843.6	716.7	635.6
55°	604.2	703.6	843.6	996.6	1068.5	1046.3	1004.4	865.8	738.9	631.7	561.1
57.5°	536.2	623.8	761.2	894.6	936.4	915.5	873.6	744.2	626.5	545.4	498.3
60°	472.1	551.9	672.2	783.4	816.1	793.9	745.5	629.1	544.1	476.1	440.7
62.5°	413.3	482.6	583.3	685.3	698.4	676.1	634.3	540.1	466.9	413.3	387.1
65°	358.3	423.7	504.8	582.0	593.8	570.2	527.1	459.0	397.6	363.6	338.7
67.5°	304.7	357.0	429.0	485.2	491.7	469.5	434.2	379.3	341.3	304.7	286.4
70°	257.6	296.9	353.1	398.9	401.5	380.6	362.3	312.6	283.8	257.6	243.3
72.5°	211.9	239.3	282.5	316.5	317.8	304.7	287.7	256.3	231.5	213.2	198.8
75°	167.4	190.9	217.1	247.2	245.9	235.4	222.3	202.7	181.8	170.0	163.5
77.5°	128.2	142.6	163.5	183.1	183.1	177.9	170.0	155.6	142.6	130.8	124.2
80°	91.5	100.7	117.7	124.2	126.9	125.6	119.0	108.5	103.3	94.2	91.5
82.5°	58.9	65.4	73.2	79.8	83.7	81.1	79.8	74.5	66.7	64.1	61.5
85°	34.0	36.6	40.5	44.5	45.8	44.5	47.1	43.2	39.2	39.2	37.9
87.5°	14.4	15.7	18.3	18.3	19.6	19.6	18.3	19.6	19.6	18.3	17.0
90°	0.5	1.8	3.0	4.3	5.6	6.2	6.7	7.6	8.5	9.5	10.4
92.5°	13.0	12.5	12.1	11.6	11.1	10.9	11.1	11.4	11.7	12.1	12.4
95°	33.7	29.9	26.1	22.3	18.5	16.6	17.0	17.8	18.6	19.4	20.2
97.5°	60.7	51.2	41.8	32.3	22.8	18.1	19.0	20.9	22.7	24.6	26.4
100°	91.8	76.0	60.2	44.4	28.6	20.7	21.7	23.7	25.6	27.6	29.6
102.5°	126.0	125.8	125.6	125.3	125.1	125.0	114.5	93.5	72.6	51.6	30.6
105°	157.6	161.1	164.5	168.0	171.5	173.2	157.5	126.0	94.5	63.1	31.6
107.5°	194.4	197.3	200.2	203.1	206.0	207.4	188.0	149.2	110.3	71.5	32.7
110°	229.7	232.1	234.5	237.0	239.4	240.6	223.9	190.6	157.3	124.0	90.7

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	262.9	265.0	267.0	269.1	271.2	272.2	271.2	269.3	267.3	265.4	263.4
115°	298.1	300.1	302.1	304.0	306.0	307.0	308.4	311.3	314.2	317.0	319.9
117.5°	328.7	331.0	333.3	335.6	337.9	339.1	340.1	342.0	344.0	345.9	347.9
120°	363.0	364.7	366.4	368.1	369.8	370.7	371.7	373.8	375.9	378.0	380.1
122.5°	392.0	393.8	395.7	397.5	399.4	400.3	401.5	403.8	406.1	408.4	410.7
125°	421.5	423.0	424.5	426.0	427.5	428.3	429.4	431.6	433.7	435.9	438.1
127.5°	448.5	450.1	451.7	453.4	455.0	455.8	456.7	458.4	460.1	461.8	463.5
130°	473.9	475.7	477.6	479.4	481.3	482.2	482.8	484.1	485.4	486.6	487.9
132.5°	499.8	501.3	502.8	504.3	505.8	506.6	507.2	508.5	509.8	511.0	512.3
135°	521.6	523.4	525.3	527.1	529.0	529.9	530.4	531.5	532.5	533.6	534.6
137.5°	544.4	545.8	547.2	548.6	550.0	550.7	551.3	552.4	553.5	554.7	555.8
140°	566.7	567.6	568.6	569.5	570.4	570.9	571.5	572.8	574.1	575.3	576.6
142.5°	585.4	586.2	587.0	587.8	588.6	589.0	589.8	591.3	592.8	594.3	595.8
145°	605.1	605.0	604.9	604.8	604.7	604.6	605.6	607.5	609.5	611.4	613.4
147.5°	622.2	621.8	621.5	621.1	620.8	620.6	621.6	623.6	625.5	627.5	629.5
150°	638.8	638.0	637.2	636.4	635.6	635.2	636.1	638.0	639.8	641.7	643.5
152.5°	652.8	651.9	650.9	650.0	649.1	648.6	649.5	651.2	652.9	654.7	656.4
155°	666.3	665.3	664.2	663.2	662.1	661.6	662.3	663.7	665.0	666.4	667.8
157.5°	677.2	676.3	675.3	674.4	673.5	673.0	673.5	674.6	675.6	676.7	677.7
160°	686.5	685.8	685.1	684.4	683.7	683.4	683.7	684.4	685.1	685.8	686.5
162.5°	694.8	694.1	693.4	692.7	692.0	691.7	692.0	692.6	693.1	693.7	694.3
165°	702.1	701.4	700.7	700.0	699.3	698.9	699.1	699.4	699.8	700.1	700.5
167.5°	707.8	707.1	706.4	705.7	705.0	704.6	704.8	705.1	705.5	705.8	706.2
170°	712.4	711.7	711.0	710.3	709.6	709.3	709.4	709.7	709.9	710.2	710.4
172.5°	715.5	714.8	714.1	713.4	712.7	712.4	712.5	712.8	713.0	713.3	713.5
175°	718.1	717.3	716.5	715.7	714.9	714.5	714.6	714.8	715.1	715.3	715.5
177.5°	719.2	718.4	717.6	716.7	715.9	715.5	715.6	715.7	715.8	716.0	716.1
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1768.2	1769.5	1772.1	1785.2	1791.7	1793.0	1787.8	1799.6	1803.5	1799.6	1797.0
5°	1851.9	1859.7	1875.4	1892.4	1891.1	1892.4	1900.3	1908.1	1910.7	1900.3	1904.2
7.5°	1925.1	1940.8	1957.8	1984.0	1984.0	1997.1	2002.3	2008.8	2024.5	2016.7	2014.1
10°	2008.8	2029.8	2061.1	2103.0	2104.3	2117.4	2130.5	2151.4	2157.9	2152.7	2155.3
12.5°	2113.5	2154.0	2156.6	2202.4	2223.3	2225.9	2246.9	2242.9	2256.0	2256.0	2278.2
15°	2159.2	2222.0	2257.3	2301.8	2314.9	2299.2	2316.2	2334.5	2335.8	2335.8	2334.5
17.5°	2241.6	2266.5	2301.8	2325.3	2330.6	2330.6	2331.9	2339.7	2334.5	2324.0	2331.9
20°	2258.6	2269.1	2282.2	2279.5	2282.2	2269.1	2256.0	2242.9	2244.2	2237.7	2257.3
22.5°	2227.2	2224.6	2194.5	2174.9	2174.9	2148.8	2123.9	2112.1	2100.4	2104.3	2110.8
25°	2148.8	2108.2	2071.6	2042.8	2036.3	1994.4	1960.4	1950.0	1930.4	1946.1	1948.7
27.5°	2023.2	1977.4	1918.6	1893.7	1859.7	1842.7	1819.2	1787.8	1747.3	1770.8	1766.9
30°	1888.5	1820.5	1772.1	1712.0	1658.3	1654.4	1609.9	1557.6	1536.7	1536.7	1548.5
32.5°	1738.1	1647.9	1577.2	1492.2	1439.9	1417.7	1364.1	1311.8	1323.5	1284.3	1298.7
35°	1562.9	1443.8	1354.9	1272.5	1233.3	1207.1	1137.8	1109.0	1077.7	1059.3	1093.3
37.5°	1395.5	1258.1	1144.4	1054.1	1039.7	992.6	945.6	927.3	908.9	916.8	915.5
40°	1191.4	1069.8	967.8	897.2	872.3	850.1	818.7	796.5	784.7	791.2	792.5
42.5°	1007.0	905.0	829.2	779.5	758.5	742.8	727.2	708.8	704.9	704.9	710.2
45°	864.5	780.8	729.8	689.2	677.5	665.7	653.9	646.1	643.5	638.2	642.1
47.5°	750.7	684.0	652.6	622.5	609.4	606.8	596.4	592.4	587.2	585.9	587.2
50°	655.2	613.4	584.6	567.6	558.4	554.5	549.3	541.4	538.8	545.4	542.7
52.5°	588.5	549.3	533.6	516.6	511.4	506.1	498.3	499.6	498.3	495.7	495.7
55°	521.8	497.0	481.3	468.2	466.9	461.7	455.1	452.5	451.2	448.6	452.5
57.5°	468.2	448.6	434.2	422.4	417.2	417.2	410.7	405.4	405.4	404.1	405.4
60°	414.6	395.0	385.8	374.0	370.1	368.8	364.9	362.3	358.3	358.3	358.3
62.5°	364.9	349.2	338.7	328.3	329.6	323.0	317.8	315.2	315.2	316.5	316.5
65°	317.8	307.3	294.3	285.1	282.5	281.2	278.6	277.3	273.3	276.0	276.0
67.5°	274.6	260.3	252.4	248.5	244.6	243.3	240.6	238.0	236.7	235.4	238.0
70°	231.5	219.7	213.2	210.6	206.6	205.3	204.0	200.1	201.4	202.7	204.0
72.5°	192.3	181.8	180.5	172.6	172.6	172.6	167.4	170.0	168.7	166.1	168.7
75°	151.7	146.5	143.9	139.9	141.2	139.9	138.6	134.7	134.7	136.0	137.3
77.5°	120.3	115.1	113.8	109.9	107.2	109.9	107.2	105.9	105.9	107.2	107.2
80°	88.9	86.3	82.4	82.4	82.4	81.1	81.1	81.1	79.8	78.5	79.8
82.5°	58.9	58.9	57.5	56.2	57.5	54.9	56.2	56.2	56.2	56.2	56.2
85°	37.9	36.6	36.6	35.3	35.3	35.3	36.6	34.0	34.0	35.3	35.3
87.5°	17.0	17.0	17.0	18.3	17.0	17.0	17.0	18.3	17.0	17.0	17.0
90°	11.0	11.6	12.1	12.7	13.0	13.1	13.3	13.6	13.8	14.0	13.8
92.5°	12.6	12.9	13.1	13.4	13.5	13.6	13.7	13.8	13.9	14.0	13.9
95°	20.8	21.4	21.9	22.5	22.8	22.7	22.6	22.5	22.4	22.3	22.4
97.5°	26.8	27.1	27.5	27.8	28.0	28.1	28.2	28.3	28.4	28.5	28.4
100°	30.5	31.4	32.3	33.2	33.7	33.8	34.0	34.3	34.5	34.7	34.5
102.5°	31.9	33.1	34.4	35.7	36.3	36.5	36.8	37.2	37.5	37.9	37.5
105°	32.9	34.1	35.4	36.7	37.3	37.5	38.0	38.5	38.9	39.4	38.9
107.5°	34.0	35.2	36.5	37.8	38.4	38.6	39.1	39.5	40.0	40.4	40.0
110°	79.2	67.7	56.2	44.7	38.9	39.1	39.6	40.1	40.5	41.0	40.5

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	213.7	164.1	114.4	64.7	39.9	40.1	40.4	40.8	41.1	41.5	41.1
115°	266.5	213.2	159.8	106.5	79.8	75.7	67.4	59.1	50.8	42.5	50.8
117.5°	331.4	315.0	298.5	282.0	273.8	258.7	228.5	198.3	168.1	137.9	168.1
120°	381.5	382.9	384.2	385.6	386.3	378.5	363.0	347.4	331.9	316.3	331.9
122.5°	411.4	412.1	412.8	413.5	413.8	413.9	414.0	414.1	414.2	414.3	414.2
125°	438.9	439.7	440.6	441.4	441.8	442.0	442.3	442.6	443.0	443.3	443.0
127.5°	464.7	465.8	467.0	468.1	468.7	468.8	468.9	469.0	469.1	469.2	469.1
130°	489.2	490.4	491.7	493.0	493.6	493.5	493.4	493.3	493.2	493.1	493.2
132.5°	513.3	514.3	515.4	516.4	516.9	516.8	516.7	516.6	516.5	516.4	516.5
135°	535.8	536.9	538.1	539.2	539.8	539.7	539.4	539.2	538.9	538.7	538.9
137.5°	557.0	558.1	559.3	560.4	561.0	560.8	560.5	560.2	559.8	559.5	559.8
140°	577.6	578.6	579.7	580.7	581.2	580.9	580.4	579.8	579.3	578.7	579.3
142.5°	596.7	597.6	598.5	599.4	599.9	599.6	599.0	598.5	597.9	597.3	597.9
145°	614.2	615.0	615.8	616.6	617.0	616.7	616.1	615.6	615.0	614.4	615.0
147.5°	630.1	630.7	631.2	631.8	632.1	631.9	631.4	630.9	630.5	630.0	630.5
150°	644.2	644.9	645.6	646.3	646.6	646.3	645.7	645.2	644.6	644.0	644.6
152.5°	657.1	657.8	658.5	659.2	659.5	659.1	658.3	657.5	656.7	655.9	656.7
155°	668.5	669.2	669.9	670.6	670.9	670.4	669.5	668.6	667.7	666.8	667.7
157.5°	678.5	679.3	680.1	680.9	681.3	680.8	679.9	679.0	678.1	677.2	678.1
160°	687.2	687.9	688.6	689.3	689.6	689.2	688.4	687.6	686.8	686.0	686.8
162.5°	695.1	695.9	696.7	697.5	697.9	697.4	696.3	695.3	694.2	693.2	694.2
165°	701.3	702.1	702.9	703.7	704.1	703.7	702.9	702.1	701.3	700.5	701.3
167.5°	707.0	707.8	708.6	709.4	709.8	709.3	708.3	707.2	706.2	705.2	706.2
170°	711.2	712.0	712.8	713.6	714.0	713.5	712.4	711.4	710.3	709.3	710.3
172.5°	714.3	715.1	715.9	716.7	717.1	716.6	715.5	714.5	713.4	712.4	713.4
175°	716.3	717.1	718.0	718.8	719.2	718.6	717.5	716.3	715.2	714.0	715.2
177.5°	716.9	717.7	718.5	719.3	719.7	719.2	718.1	717.1	716.0	715.0	716.0
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1803.5	1794.3	1786.5	1787.8	1794.3	1789.1	1776.0	1759.0	1752.5	1744.6	1752.5
5°	1912.0	1904.2	1888.5	1889.8	1885.9	1880.7	1859.7	1833.6	1833.6	1812.7	1810.0
7.5°	2019.3	2007.5	1997.1	1994.4	1980.1	1969.6	1951.3	1914.7	1900.3	1875.4	1861.0
10°	2139.6	2130.5	2118.7	2104.3	2096.5	2078.1	2048.1	1994.4	1968.3	1934.3	1909.4
12.5°	2261.2	2259.9	2233.8	2205.0	2203.7	2174.9	2154.0	2082.1	2046.8	2001.0	1942.1
15°	2338.4	2331.9	2317.5	2303.1	2307.0	2275.6	2228.5	2143.5	2120.0	2065.1	2002.3
17.5°	2337.1	2337.1	2333.2	2330.6	2326.6	2317.5	2291.3	2235.1	2197.2	2127.8	2069.0
20°	2262.5	2279.5	2283.5	2282.2	2295.2	2301.8	2300.5	2265.2	2235.1	2173.6	2113.5
22.5°	2113.5	2152.7	2169.7	2180.2	2207.6	2222.0	2256.0	2242.9	2235.1	2189.3	2138.3
25°	1974.8	1987.9	2038.9	2041.5	2079.5	2114.8	2148.8	2171.0	2199.8	2182.8	2139.6
27.5°	1795.7	1825.7	1862.4	1889.8	1897.7	1969.6	2025.8	2067.7	2133.1	2138.3	2123.9
30°	1592.9	1607.3	1667.5	1704.1	1746.0	1798.3	1879.4	1951.3	2010.1	2063.8	2082.1
32.5°	1345.8	1404.6	1439.9	1484.4	1521.0	1613.9	1713.3	1806.1	1874.1	1964.4	2003.6
35°	1119.5	1165.3	1225.4	1243.7	1310.4	1388.9	1518.4	1637.4	1740.7	1832.3	1912.0
37.5°	932.5	969.1	1033.2	1062.0	1101.2	1201.9	1310.4	1458.2	1582.5	1694.9	1794.3
40°	804.3	831.8	880.2	889.3	922.0	1013.6	1101.2	1239.8	1404.6	1556.3	1664.9
42.5°	716.7	729.8	762.5	774.2	795.2	856.6	935.1	1065.9	1218.9	1375.8	1528.9
45°	653.9	663.1	682.7	693.2	719.3	746.8	810.9	915.5	1035.8	1194.0	1358.8
47.5°	597.7	609.4	617.3	623.8	638.2	668.3	710.2	787.3	902.4	1047.6	1207.1
50°	550.6	554.5	568.9	570.2	579.4	599.0	638.2	685.3	776.9	894.6	1048.9
52.5°	503.5	507.4	516.6	525.7	529.7	545.4	571.5	610.8	678.8	771.6	908.9
55°	456.4	461.7	470.8	477.4	481.3	494.4	510.1	548.0	601.6	667.0	779.5
57.5°	409.4	421.1	423.7	427.7	434.2	448.6	463.0	485.2	527.1	587.2	669.6
60°	364.9	368.8	378.0	381.9	388.4	396.3	414.6	431.6	461.7	508.7	583.3
62.5°	319.1	328.3	332.2	336.1	341.3	350.5	362.3	380.6	406.7	444.7	503.5
65°	279.9	281.2	289.0	294.3	299.5	306.0	317.8	334.8	350.5	385.8	429.0
67.5°	241.9	244.6	247.2	252.4	259.0	265.5	276.0	285.1	304.7	328.3	362.3
70°	205.3	205.3	211.9	215.8	214.5	222.3	230.2	240.6	255.0	277.3	304.7
72.5°	172.6	171.3	176.6	177.9	180.5	185.7	190.9	201.4	209.3	226.3	247.2
75°	137.3	139.9	142.6	142.6	146.5	150.4	155.6	160.9	170.0	180.5	196.2
77.5°	108.5	108.5	111.2	112.5	116.4	115.1	120.3	125.6	132.1	141.2	153.0
80°	79.8	82.4	82.4	82.4	83.7	85.0	90.2	94.2	98.1	104.6	109.9
82.5°	56.2	56.2	58.9	58.9	58.9	61.5	61.5	62.8	65.4	69.3	73.2
85°	35.3	35.3	35.3	36.6	35.3	36.6	39.2	37.9	39.2	41.9	41.9
87.5°	17.0	17.0	17.0	17.0	17.0	18.3	17.0	18.3	19.6	19.6	19.6
90°	13.6	13.3	13.1	13.0	12.7	12.1	11.6	11.0	10.4	9.5	8.5
92.5°	13.8	13.7	13.6	13.5	13.4	13.1	12.9	12.6	12.4	12.1	11.7
95°	22.5	22.6	22.7	22.8	22.5	21.9	21.4	20.8	20.2	19.4	18.6
97.5°	28.3	28.2	28.1	28.0	27.8	27.5	27.1	26.8	26.4	24.6	22.7
100°	34.3	34.0	33.8	33.7	33.2	32.3	31.4	30.5	29.6	27.6	25.6
102.5°	37.2	36.8	36.5	36.3	35.7	34.4	33.1	31.9	30.6	51.6	72.6
105°	38.5	38.0	37.5	37.3	36.7	35.4	34.1	32.9	31.6	63.1	94.5
107.5°	39.5	39.1	38.6	38.4	37.8	36.5	35.2	34.0	32.7	71.5	110.3
110°	40.1	39.6	39.1	38.9	44.7	56.2	67.7	79.2	90.7	124.0	157.3

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	40.8	40.4	40.1	39.9	64.7	114.4	164.1	213.7	263.4	265.4	267.3
115°	59.1	67.4	75.7	79.8	106.5	159.8	213.2	266.5	319.9	317.0	314.2
117.5°	198.3	228.5	258.7	273.8	282.0	298.5	315.0	331.4	347.9	345.9	344.0
120°	347.4	363.0	378.5	386.3	385.6	384.2	382.9	381.5	380.1	378.0	375.9
122.5°	414.1	414.0	413.9	413.8	413.5	412.8	412.1	411.4	410.7	408.4	406.1
125°	442.6	442.3	442.0	441.8	441.4	440.6	439.7	438.9	438.1	435.9	433.7
127.5°	469.0	468.9	468.8	468.7	468.1	467.0	465.8	464.7	463.5	461.8	460.1
130°	493.3	493.4	493.5	493.6	493.0	491.7	490.4	489.2	487.9	486.6	485.4
132.5°	516.6	516.7	516.8	516.9	516.4	515.4	514.3	513.3	512.3	511.0	509.8
135°	539.2	539.4	539.7	539.8	539.2	538.1	536.9	535.8	534.6	533.6	532.5
137.5°	560.2	560.5	560.8	561.0	560.4	559.3	558.1	557.0	555.8	554.7	553.5
140°	579.8	580.4	580.9	581.2	580.7	579.7	578.6	577.6	576.6	575.3	574.1
142.5°	598.5	599.0	599.6	599.9	599.4	598.5	597.6	596.7	595.8	594.3	592.8
145°	615.6	616.1	616.7	617.0	616.6	615.8	615.0	614.2	613.4	611.4	609.5
147.5°	630.9	631.4	631.9	632.1	631.8	631.2	630.7	630.1	629.5	627.5	625.5
150°	645.2	645.7	646.3	646.6	646.3	645.6	644.9	644.2	643.5	641.7	639.8
152.5°	657.5	658.3	659.1	659.5	659.2	658.5	657.8	657.1	656.4	654.7	652.9
155°	668.6	669.5	670.4	670.9	670.6	669.9	669.2	668.5	667.8	666.4	665.0
157.5°	679.0	679.9	680.8	681.3	680.9	680.1	679.3	678.5	677.7	676.7	675.6
160°	687.6	688.4	689.2	689.6	689.3	688.6	687.9	687.2	686.5	685.8	685.1
162.5°	695.3	696.3	697.4	697.9	697.5	696.7	695.9	695.1	694.3	693.7	693.1
165°	702.1	702.9	703.7	704.1	703.7	702.9	702.1	701.3	700.5	700.1	699.8
167.5°	707.2	708.3	709.3	709.8	709.4	708.6	707.8	707.0	706.2	705.8	705.5
170°	711.4	712.4	713.5	714.0	713.6	712.8	712.0	711.2	710.4	710.2	709.9
172.5°	714.5	715.5	716.6	717.1	716.7	715.9	715.1	714.3	713.5	713.3	713.0
175°	716.3	717.5	718.6	719.2	718.8	718.0	717.1	716.3	715.5	715.3	715.1
177.5°	717.1	718.1	719.2	719.7	719.3	718.5	717.7	716.9	716.1	716.0	715.8
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1746.0	1739.4	1735.5	1738.1	1730.3	1710.6	1710.6	1717.2	1709.3	1701.5	1689.7
5°	1794.3	1781.3	1773.4	1772.1	1753.8	1722.4	1715.9	1709.3	1692.3	1674.0	1654.4
7.5°	1841.4	1817.9	1804.8	1795.7	1769.5	1729.0	1712.0	1697.6	1670.1	1642.6	1617.8
10°	1880.7	1846.7	1831.0	1816.6	1782.6	1731.6	1704.1	1677.9	1642.6	1607.3	1575.9
12.5°	1912.0	1872.8	1853.2	1832.3	1790.4	1723.7	1689.7	1647.9	1612.6	1565.5	1534.1
15°	1964.4	1883.3	1865.0	1845.3	1802.2	1710.6	1668.8	1621.7	1573.3	1510.5	1476.5
17.5°	2006.2	1897.7	1896.4	1854.5	1798.3	1705.4	1641.3	1579.9	1527.5	1464.8	1411.1
20°	2031.1	1919.9	1899.0	1855.8	1785.2	1670.1	1603.4	1535.4	1479.2	1403.3	1349.7
22.5°	2052.0	1951.3	1896.4	1844.0	1757.7	1658.3	1560.2	1496.2	1419.0	1336.6	1285.6
25°	2059.8	1957.8	1900.3	1840.1	1738.1	1624.3	1513.2	1443.8	1357.5	1283.0	1213.7
27.5°	2061.1	1956.5	1885.9	1823.1	1710.6	1579.9	1466.1	1392.8	1297.4	1211.1	1141.7
30°	2048.1	1942.1	1878.0	1810.0	1684.5	1539.3	1408.5	1327.4	1225.4	1139.1	1067.2
32.5°	2008.8	1913.4	1861.0	1786.5	1650.5	1483.1	1353.6	1263.4	1156.1	1071.1	1001.8
35°	1943.4	1878.0	1820.5	1751.2	1606.0	1430.8	1298.7	1192.7	1084.2	1003.1	937.7
37.5°	1862.4	1827.0	1773.4	1705.4	1555.0	1383.7	1237.2	1119.5	1011.0	932.5	868.4
40°	1752.5	1761.6	1709.3	1647.9	1494.9	1319.6	1157.4	1045.0	942.9	869.7	806.9
42.5°	1633.5	1671.4	1641.3	1582.5	1428.2	1249.0	1098.6	974.3	874.9	799.1	746.8
45°	1505.3	1570.7	1552.4	1509.2	1358.8	1174.4	1014.9	894.6	806.9	733.7	687.9
47.5°	1365.4	1458.2	1458.2	1426.8	1281.7	1099.9	942.9	820.0	733.7	681.4	636.9
50°	1222.8	1327.4	1344.4	1323.5	1195.4	1014.9	855.3	744.2	669.6	618.6	585.9
52.5°	1073.7	1195.4	1226.7	1216.3	1103.8	933.8	783.4	674.8	606.8	562.4	533.6
55°	931.2	1072.4	1106.4	1110.3	1005.7	844.9	703.6	608.1	542.7	512.7	487.8
57.5°	796.5	932.5	970.4	976.9	906.3	763.8	629.1	545.4	486.5	461.7	442.0
60°	681.4	795.2	844.9	859.2	797.8	669.6	559.8	478.7	434.2	410.7	392.3
62.5°	587.2	678.8	731.1	735.0	707.5	587.2	487.8	419.8	381.9	361.0	351.8
65°	495.7	578.1	609.4	625.1	602.9	508.7	421.1	364.9	334.8	316.5	307.3
67.5°	422.4	474.7	500.9	521.8	499.6	429.0	358.3	312.6	290.3	272.0	266.8
70°	346.6	389.7	409.4	430.3	410.7	357.0	306.0	264.2	244.6	230.2	223.6
72.5°	277.3	311.3	329.6	342.7	330.9	286.4	244.6	215.8	201.4	190.9	187.0
75°	219.7	243.3	253.7	262.9	257.6	223.6	197.5	173.9	160.9	151.7	149.1
77.5°	167.4	184.4	196.2	198.8	192.3	170.0	147.8	133.4	122.9	117.7	115.1
80°	119.0	129.5	136.0	139.9	133.4	124.2	108.5	98.1	88.9	82.4	81.1
82.5°	79.8	85.0	90.2	88.9	86.3	78.5	69.3	64.1	60.2	54.9	54.9
85°	45.8	47.1	49.7	51.0	49.7	44.5	39.2	36.6	34.0	30.1	30.1
87.5°	19.6	20.9	20.9	22.2	19.6	19.6	17.0	14.4	14.4	13.1	11.8
90°	7.6	6.7	6.2	5.6	4.3	3.0	1.8	0.5	1.8	3.0	4.3
92.5°	11.4	11.1	10.9	11.1	11.6	12.1	12.5	13.0	12.5	12.1	11.6
95°	17.8	17.0	16.6	18.5	22.3	26.1	29.9	33.7	29.9	26.1	22.3
97.5°	20.9	19.0	18.1	22.8	32.3	41.8	51.2	60.7	51.2	41.8	32.3
100°	23.7	21.7	20.7	28.6	44.4	60.2	76.0	91.8	76.0	60.2	44.4
102.5°	93.5	114.5	125.0	125.1	125.3	125.6	125.8	126.0	125.8	125.6	125.3
105°	126.0	157.5	173.2	171.5	168.0	164.5	161.1	157.6	161.1	164.5	168.0
107.5°	149.2	188.0	207.4	206.0	203.1	200.2	197.3	194.4	197.3	200.2	203.1
110°	190.6	223.9	240.6	239.4	237.0	234.5	232.1	229.7	232.1	234.5	237.0

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	269.3	271.2	272.2	271.2	269.1	267.0	265.0	262.9	265.0	267.0	269.1
115°	311.3	308.4	307.0	306.0	304.0	302.1	300.1	298.1	300.1	302.1	304.0
117.5°	342.0	340.1	339.1	337.9	335.6	333.3	331.0	328.7	331.0	333.3	335.6
120°	373.8	371.7	370.7	369.8	368.1	366.4	364.7	363.0	364.7	366.4	368.1
122.5°	403.8	401.5	400.3	399.4	397.5	395.7	393.8	392.0	393.8	395.7	397.5
125°	431.6	429.4	428.3	427.5	426.0	424.5	423.0	421.5	423.0	424.5	426.0
127.5°	458.4	456.7	455.8	455.0	453.4	451.7	450.1	448.5	450.1	451.7	453.4
130°	484.1	482.8	482.2	481.3	479.4	477.6	475.7	473.9	475.7	477.6	479.4
132.5°	508.5	507.2	506.6	505.8	504.3	502.8	501.3	499.8	501.3	502.8	504.3
135°	531.5	530.4	529.9	529.0	527.1	525.3	523.4	521.6	523.4	525.3	527.1
137.5°	552.4	551.3	550.7	550.0	548.6	547.2	545.8	544.4	545.8	547.2	548.6
140°	572.8	571.5	570.9	570.4	569.5	568.6	567.6	566.7	567.6	568.6	569.5
142.5°	591.3	589.8	589.0	588.6	587.8	587.0	586.2	585.4	586.2	587.0	587.8
145°	607.5	605.6	604.6	604.7	604.8	604.9	605.0	605.1	605.0	604.9	604.8
147.5°	623.6	621.6	620.6	620.8	621.1	621.5	621.8	622.2	621.8	621.5	621.1
150°	638.0	636.1	635.2	635.6	636.4	637.2	638.0	638.8	638.0	637.2	636.4
152.5°	651.2	649.5	648.6	649.1	650.0	650.9	651.9	652.8	651.9	650.9	650.0
155°	663.7	662.3	661.6	662.1	663.2	664.2	665.3	666.3	665.3	664.2	663.2
157.5°	674.6	673.5	673.0	673.5	674.4	675.3	676.3	677.2	676.3	675.3	674.4
160°	684.4	683.7	683.4	683.7	684.4	685.1	685.8	686.5	685.8	685.1	684.4
162.5°	692.6	692.0	691.7	692.0	692.7	693.4	694.1	694.8	694.1	693.4	692.7
165°	699.4	699.1	698.9	699.3	700.0	700.7	701.4	702.1	701.4	700.7	700.0
167.5°	705.1	704.8	704.6	705.0	705.7	706.4	707.1	707.8	707.1	706.4	705.7
170°	709.7	709.4	709.3	709.6	710.3	711.0	711.7	712.4	711.7	711.0	710.3
172.5°	712.8	712.5	712.4	712.7	713.4	714.1	714.8	715.5	714.8	714.1	713.4
175°	714.8	714.6	714.5	714.9	715.7	716.5	717.3	718.1	717.3	716.5	715.7
177.5°	715.7	715.6	715.5	715.9	716.7	717.6	718.4	719.2	718.4	717.6	716.7
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1683.2	1689.7	1688.4	1675.3	1660.9	1649.2	1626.9	1629.6	1621.7	1623.0	1630.9
5°	1641.3	1641.3	1636.1	1617.8	1594.2	1581.2	1556.3	1549.8	1534.1	1532.8	1531.5
7.5°	1596.9	1590.3	1583.8	1557.6	1528.9	1507.9	1473.9	1466.1	1450.4	1439.9	1434.7
10°	1544.5	1535.4	1522.3	1492.2	1456.9	1430.8	1395.5	1385.0	1354.9	1341.8	1334.0
12.5°	1487.0	1481.8	1460.8	1436.0	1378.5	1349.7	1298.7	1309.1	1279.1	1252.9	1249.0
15°	1429.5	1409.8	1398.1	1357.5	1288.2	1275.1	1234.6	1213.7	1186.2	1165.3	1165.3
17.5°	1373.2	1343.1	1317.0	1273.8	1222.8	1186.2	1156.1	1145.7	1111.7	1090.7	1086.8
20°	1298.7	1264.7	1258.1	1196.7	1161.4	1120.8	1092.0	1065.9	1041.0	1031.9	1025.3
22.5°	1228.1	1188.8	1178.4	1126.0	1090.7	1050.2	1021.4	1003.1	984.8	978.3	966.5
25°	1152.2	1128.7	1113.0	1056.7	1017.5	979.6	959.9	946.9	929.9	928.6	920.7
27.5°	1079.0	1056.7	1041.0	987.4	958.6	923.3	907.6	893.2	884.1	880.2	876.2
30°	1016.2	991.3	973.0	933.8	898.5	869.7	856.6	847.5	842.2	835.7	834.4
32.5°	946.9	932.5	907.6	877.6	850.1	822.6	814.8	808.2	800.4	797.8	796.5
35°	888.0	868.4	852.7	818.7	806.9	783.4	774.2	769.0	758.5	755.9	753.3
37.5°	830.5	812.2	795.2	774.2	752.0	738.9	733.7	725.8	720.6	721.9	719.3
40°	772.9	758.5	745.5	723.2	710.2	703.6	693.2	685.3	682.7	684.0	682.7
42.5°	716.7	703.6	695.8	678.8	665.7	659.1	652.6	644.8	648.7	648.7	652.6
45°	665.7	653.9	648.7	635.6	627.8	617.3	610.8	609.4	614.7	613.4	613.4
47.5°	613.4	609.4	602.9	591.1	580.7	574.1	572.8	572.8	578.1	580.7	579.4
50°	572.8	565.0	557.1	548.0	540.1	537.5	533.6	536.2	541.4	541.4	544.1
52.5°	521.8	516.6	514.0	506.1	500.9	500.9	500.9	502.2	506.1	510.1	508.7
55°	477.4	473.4	470.8	466.9	460.4	461.7	460.4	463.0	466.9	470.8	473.4
57.5°	430.3	429.0	426.4	419.8	419.8	418.5	422.4	423.7	430.3	432.9	436.8
60°	388.4	384.5	384.5	379.3	379.3	379.3	383.2	387.1	392.3	393.7	396.3
62.5°	344.0	344.0	342.7	338.7	338.7	342.7	344.0	349.2	351.8	351.8	355.7
65°	302.1	300.8	299.5	300.8	302.1	302.1	306.0	308.6	311.3	312.6	313.9
67.5°	260.3	259.0	261.6	260.3	262.9	268.1	266.8	270.7	274.6	274.6	276.0
70°	221.0	223.6	222.3	224.9	223.6	226.3	230.2	231.5	231.5	232.8	236.7
72.5°	184.4	184.4	184.4	183.1	184.4	187.0	189.6	190.9	193.6	194.9	198.8
75°	149.1	149.1	146.5	149.1	149.1	151.7	154.3	154.3	154.3	156.9	160.9
77.5°	112.5	113.8	112.5	115.1	115.1	116.4	119.0	117.7	120.3	121.6	122.9
80°	82.4	81.1	81.1	81.1	82.4	82.4	85.0	86.3	86.3	90.2	87.6
82.5°	52.3	53.6	52.3	53.6	53.6	54.9	53.6	54.9	56.2	58.9	57.5
85°	30.1	28.8	28.8	30.1	28.8	28.8	30.1	28.8	30.1	28.8	30.1
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.8	7.8	7.8	6.5
90°	5.6	6.2	6.7	7.6	8.5	9.5	10.4	11.0	11.6	12.1	12.7
92.5°	11.1	10.9	11.1	11.4	11.7	12.1	12.4	12.6	12.9	13.1	13.4
95°	18.5	16.6	17.0	17.8	18.6	19.4	20.2	20.8	21.4	21.9	22.5
97.5°	22.8	18.1	19.0	20.9	22.7	24.6	26.4	26.8	27.1	27.5	27.8
100°	28.6	20.7	21.7	23.7	25.6	27.6	29.6	30.5	31.4	32.3	33.2
102.5°	125.1	125.0	114.5	93.5	72.6	51.6	30.6	31.9	33.1	34.4	35.7
105°	171.5	173.2	157.5	126.0	94.5	63.1	31.6	32.9	34.1	35.4	36.7
107.5°	206.0	207.4	188.0	149.2	110.3	71.5	32.7	34.0	35.2	36.5	37.8
110°	239.4	240.6	223.9	190.6	157.3	124.0	90.7	79.2	67.7	56.2	44.7

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.2	272.2	271.2	269.3	267.3	265.4	263.4	213.7	164.1	114.4	64.7
115°	306.0	307.0	308.4	311.3	314.2	317.0	319.9	266.5	213.2	159.8	106.5
117.5°	337.9	339.1	340.1	342.0	344.0	345.9	347.9	331.4	315.0	298.5	282.0
120°	369.8	370.7	371.7	373.8	375.9	378.0	380.1	381.5	382.9	384.2	385.6
122.5°	399.4	400.3	401.5	403.8	406.1	408.4	410.7	411.4	412.1	412.8	413.5
125°	427.5	428.3	429.4	431.6	433.7	435.9	438.1	438.9	439.7	440.6	441.4
127.5°	455.0	455.8	456.7	458.4	460.1	461.8	463.5	464.7	465.8	467.0	468.1
130°	481.3	482.2	482.8	484.1	485.4	486.6	487.9	489.2	490.4	491.7	493.0
132.5°	505.8	506.6	507.2	508.5	509.8	511.0	512.3	513.3	514.3	515.4	516.4
135°	529.0	529.9	530.4	531.5	532.5	533.6	534.6	535.8	536.9	538.1	539.2
137.5°	550.0	550.7	551.3	552.4	553.5	554.7	555.8	557.0	558.1	559.3	560.4
140°	570.4	570.9	571.5	572.8	574.1	575.3	576.6	577.6	578.6	579.7	580.7
142.5°	588.6	589.0	589.8	591.3	592.8	594.3	595.8	596.7	597.6	598.5	599.4
145°	604.7	604.6	605.6	607.5	609.5	611.4	613.4	614.2	615.0	615.8	616.6
147.5°	620.8	620.6	621.6	623.6	625.5	627.5	629.5	630.1	630.7	631.2	631.8
150°	635.6	635.2	636.1	638.0	639.8	641.7	643.5	644.2	644.9	645.6	646.3
152.5°	649.1	648.6	649.5	651.2	652.9	654.7	656.4	657.1	657.8	658.5	659.2
155°	662.1	661.6	662.3	663.7	665.0	666.4	667.8	668.5	669.2	669.9	670.6
157.5°	673.5	673.0	673.5	674.6	675.6	676.7	677.7	678.5	679.3	680.1	680.9
160°	683.7	683.4	683.7	684.4	685.1	685.8	686.5	687.2	687.9	688.6	689.3
162.5°	692.0	691.7	692.0	692.6	693.1	693.7	694.3	695.1	695.9	696.7	697.5
165°	699.3	698.9	699.1	699.4	699.8	700.1	700.5	701.3	702.1	702.9	703.7
167.5°	705.0	704.6	704.8	705.1	705.5	705.8	706.2	707.0	707.8	708.6	709.4
170°	709.6	709.3	709.4	709.7	709.9	710.2	710.4	711.2	712.0	712.8	713.6
172.5°	712.7	712.4	712.5	712.8	713.0	713.3	713.5	714.3	715.1	715.9	716.7
175°	714.9	714.5	714.6	714.8	715.1	715.3	715.5	716.3	717.1	718.0	718.8
177.5°	715.9	715.5	715.6	715.7	715.8	716.0	716.1	716.9	717.7	718.5	719.3
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1621.7	1625.6	1616.5	1613.9	1616.5	1607.3	1609.9	1612.6	1612.6	1616.5	1619.1
5°	1527.5	1522.3	1513.2	1510.5	1507.9	1511.9	1509.2	1513.2	1514.5	1523.6	1524.9
7.5°	1434.7	1426.8	1419.0	1411.1	1408.5	1402.0	1408.5	1408.5	1417.7	1415.1	1421.6
10°	1324.8	1323.5	1313.1	1309.1	1303.9	1293.4	1307.8	1303.9	1310.4	1322.2	1324.8
12.5°	1243.7	1229.4	1235.9	1217.6	1224.1	1213.7	1215.0	1215.0	1225.4	1226.7	1224.1
15°	1166.6	1154.8	1137.8	1130.0	1126.0	1120.8	1137.8	1139.1	1131.3	1149.6	1143.0
17.5°	1088.1	1088.1	1072.4	1068.5	1058.0	1063.3	1060.7	1062.0	1059.3	1072.4	1079.0
20°	1020.1	1013.6	1008.3	1009.6	996.6	994.0	991.3	994.0	1003.1	1012.3	1014.9
22.5°	965.2	961.3	948.2	950.8	940.3	944.3	941.6	948.2	949.5	949.5	958.6
25°	912.9	907.6	908.9	903.7	899.8	899.8	895.9	899.8	905.0	907.6	908.9
27.5°	873.6	869.7	863.2	859.2	861.9	855.3	860.6	864.5	864.5	861.9	864.5
30°	826.5	829.2	829.2	816.1	821.3	818.7	822.6	825.2	825.2	826.5	823.9
32.5°	795.2	787.3	786.0	784.7	784.7	779.5	779.5	783.4	784.7	786.0	789.9
35°	753.3	753.3	746.8	750.7	745.5	746.8	745.5	746.8	749.4	745.5	749.4
37.5°	715.4	716.7	714.1	716.7	718.0	715.4	712.8	718.0	715.4	715.4	712.8
40°	682.7	681.4	682.7	682.7	682.7	684.0	681.4	681.4	681.4	678.8	676.1
42.5°	655.2	647.4	650.0	651.3	647.4	647.4	648.7	647.4	651.3	643.5	643.5
45°	616.0	613.4	614.7	614.7	617.3	613.4	616.0	617.3	613.4	612.1	609.4
47.5°	580.7	583.3	580.7	583.3	583.3	585.9	580.7	582.0	583.3	578.1	574.1
50°	545.4	545.4	549.3	548.0	549.3	546.7	546.7	545.4	546.7	544.1	540.1
52.5°	512.7	508.7	515.3	514.0	512.7	511.4	510.1	511.4	508.7	506.1	506.1
55°	472.1	472.1	476.1	477.4	477.4	474.7	472.1	473.4	472.1	470.8	469.5
57.5°	439.4	434.2	436.8	438.1	438.1	434.2	436.8	434.2	434.2	435.5	431.6
60°	397.6	397.6	395.0	398.9	398.9	396.3	396.3	397.6	395.0	393.7	392.3
62.5°	353.1	354.4	358.3	359.7	361.0	358.3	355.7	357.0	357.0	353.1	354.4
65°	315.2	317.8	323.0	321.7	319.1	320.4	317.8	319.1	315.2	316.5	312.6
67.5°	278.6	277.3	278.6	278.6	281.2	279.9	277.3	277.3	276.0	279.9	276.0
70°	239.3	239.3	239.3	239.3	240.6	241.9	239.3	236.7	238.0	235.4	234.1
72.5°	198.8	200.1	198.8	201.4	197.5	200.1	200.1	198.8	197.5	197.5	197.5
75°	160.9	163.5	159.6	160.9	159.6	162.2	160.9	160.9	158.2	156.9	158.2
77.5°	122.9	124.2	121.6	122.9	121.6	122.9	122.9	121.6	121.6	121.6	121.6
80°	87.6	88.9	87.6	86.3	85.0	87.6	85.0	86.3	87.6	86.3	88.9
82.5°	56.2	56.2	54.9	56.2	53.6	53.6	54.9	54.9	53.6	56.2	53.6
85°	27.5	27.5	30.1	27.5	26.2	26.2	26.2	27.5	26.2	28.8	27.5
87.5°	6.5	5.2	6.5	6.5	5.2	5.2	6.5	5.2	6.5	7.8	5.2
90°	13.0	13.1	13.3	13.6	13.8	14.0	13.8	13.6	13.3	13.1	13.0
92.5°	13.5	13.6	13.7	13.8	13.9	14.0	13.9	13.8	13.7	13.6	13.5
95°	22.8	22.7	22.6	22.5	22.4	22.3	22.4	22.5	22.6	22.7	22.8
97.5°	28.0	28.1	28.2	28.3	28.4	28.5	28.4	28.3	28.2	28.1	28.0
100°	33.7	33.8	34.0	34.3	34.5	34.7	34.5	34.3	34.0	33.8	33.7
102.5°	36.3	36.5	36.8	37.2	37.5	37.9	37.5	37.2	36.8	36.5	36.3
105°	37.3	37.5	38.0	38.5	38.9	39.4	38.9	38.5	38.0	37.5	37.3
107.5°	38.4	38.6	39.1	39.5	40.0	40.4	40.0	39.5	39.1	38.6	38.4
110°	38.9	39.1	39.6	40.1	40.5	41.0	40.5	40.1	39.6	39.1	38.9

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	39.9	40.1	40.4	40.8	41.1	41.5	41.1	40.8	40.4	40.1	39.9
115°	79.8	75.7	67.4	59.1	50.8	42.5	50.8	59.1	67.4	75.7	79.8
117.5°	273.8	258.7	228.5	198.3	168.1	137.9	168.1	198.3	228.5	258.7	273.8
120°	386.3	378.5	363.0	347.4	331.9	316.3	331.9	347.4	363.0	378.5	386.3
122.5°	413.8	413.9	414.0	414.1	414.2	414.3	414.2	414.1	414.0	413.9	413.8
125°	441.8	442.0	442.3	442.6	443.0	443.3	443.0	442.6	442.3	442.0	441.8
127.5°	468.7	468.8	468.9	469.0	469.1	469.2	469.1	469.0	468.9	468.8	468.7
130°	493.6	493.5	493.4	493.3	493.2	493.1	493.2	493.3	493.4	493.5	493.6
132.5°	516.9	516.8	516.7	516.6	516.5	516.4	516.5	516.6	516.7	516.8	516.9
135°	539.8	539.7	539.4	539.2	538.9	538.7	538.9	539.2	539.4	539.7	539.8
137.5°	561.0	560.8	560.5	560.2	559.8	559.5	559.8	560.2	560.5	560.8	561.0
140°	581.2	580.9	580.4	579.8	579.3	578.7	579.3	579.8	580.4	580.9	581.2
142.5°	599.9	599.6	599.0	598.5	597.9	597.3	597.9	598.5	599.0	599.6	599.9
145°	617.0	616.7	616.1	615.6	615.0	614.4	615.0	615.6	616.1	616.7	617.0
147.5°	632.1	631.9	631.4	630.9	630.5	630.0	630.5	630.9	631.4	631.9	632.1
150°	646.6	646.3	645.7	645.2	644.6	644.0	644.6	645.2	645.7	646.3	646.6
152.5°	659.5	659.1	658.3	657.5	656.7	655.9	656.7	657.5	658.3	659.1	659.5
155°	670.9	670.4	669.5	668.6	667.7	666.8	667.7	668.6	669.5	670.4	670.9
157.5°	681.3	680.8	679.9	679.0	678.1	677.2	678.1	679.0	679.9	680.8	681.3
160°	689.6	689.2	688.4	687.6	686.8	686.0	686.8	687.6	688.4	689.2	689.6
162.5°	697.9	697.4	696.3	695.3	694.2	693.2	694.2	695.3	696.3	697.4	697.9
165°	704.1	703.7	702.9	702.1	701.3	700.5	701.3	702.1	702.9	703.7	704.1
167.5°	709.8	709.3	708.3	707.2	706.2	705.2	706.2	707.2	708.3	709.3	709.8
170°	714.0	713.5	712.4	711.4	710.3	709.3	710.3	711.4	712.4	713.5	714.0
172.5°	717.1	716.6	715.5	714.5	713.4	712.4	713.4	714.5	715.5	716.6	717.1
175°	719.2	718.6	717.5	716.3	715.2	714.0	715.2	716.3	717.5	718.6	719.2
177.5°	719.7	719.2	718.1	717.1	716.0	715.0	716.0	717.1	718.1	719.2	719.7
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1615.2	1625.6	1621.7	1607.3	1624.3	1624.3	1636.1	1636.1	1650.5	1655.7	1663.6
5°	1523.6	1531.5	1538.0	1531.5	1543.2	1561.5	1572.0	1581.2	1600.8	1608.6	1620.4
7.5°	1425.5	1439.9	1446.5	1446.5	1466.1	1487.0	1507.9	1521.0	1548.5	1558.9	1570.7
10°	1330.1	1347.1	1360.1	1358.8	1391.5	1404.6	1430.8	1460.8	1488.3	1504.0	1521.0
12.5°	1229.4	1238.5	1256.8	1283.0	1290.8	1314.4	1344.4	1382.4	1432.1	1446.5	1471.3
15°	1145.7	1170.5	1184.9	1196.7	1215.0	1237.2	1269.9	1306.5	1356.2	1387.6	1413.8
17.5°	1075.0	1107.7	1116.9	1114.3	1137.8	1171.8	1209.7	1237.2	1281.7	1319.6	1344.4
20°	1017.5	1030.6	1046.3	1052.8	1071.1	1107.7	1144.4	1175.7	1212.4	1242.4	1271.2
22.5°	959.9	970.4	983.5	995.3	1009.6	1030.6	1065.9	1105.1	1140.4	1169.2	1201.9
25°	912.9	919.4	931.2	940.3	956.0	970.4	995.3	1038.4	1080.3	1097.3	1126.0
27.5°	867.1	872.3	880.2	890.6	898.5	912.9	935.1	970.4	1013.6	1030.6	1069.8
30°	826.5	830.5	838.3	843.6	847.5	864.5	881.5	908.9	941.6	965.2	994.0
32.5°	788.6	792.5	800.4	801.7	806.9	816.1	831.8	856.6	885.4	905.0	929.9
35°	746.8	749.4	757.2	759.8	763.8	771.6	783.4	801.7	827.9	842.2	864.5
37.5°	714.1	712.8	718.0	721.9	727.2	731.1	735.0	753.3	772.9	786.0	803.0
40°	678.8	676.1	677.5	682.7	685.3	690.5	690.5	708.8	721.9	732.4	745.5
42.5°	643.5	642.1	639.5	642.1	644.8	646.1	647.4	660.5	673.5	682.7	697.1
45°	608.1	606.8	604.2	605.5	605.5	608.1	612.1	617.3	626.5	634.3	642.1
47.5°	575.4	572.8	568.9	567.6	570.2	570.2	570.2	575.4	584.6	587.2	595.1
50°	541.4	537.5	532.3	529.7	529.7	528.4	531.0	532.3	540.1	542.7	549.3
52.5°	504.8	502.2	497.0	491.7	493.1	490.4	491.7	493.1	495.7	499.6	503.5
55°	468.2	463.0	459.0	457.7	453.8	453.8	449.9	455.1	453.8	455.1	460.4
57.5°	432.9	427.7	421.1	418.5	414.6	413.3	410.7	409.4	410.7	414.6	418.5
60°	391.0	388.4	384.5	380.6	378.0	374.0	371.4	371.4	370.1	370.1	371.4
62.5°	350.5	349.2	344.0	342.7	340.0	337.4	333.5	330.9	330.9	333.5	334.8
65°	311.3	310.0	306.0	304.7	298.2	295.6	294.3	293.0	290.3	290.3	290.3
67.5°	274.6	270.7	270.7	264.2	259.0	256.3	253.7	252.4	252.4	252.4	253.7
70°	234.1	234.1	230.2	226.3	221.0	222.3	218.4	214.5	214.5	211.9	213.2
72.5°	194.9	193.6	189.6	188.3	184.4	180.5	177.9	180.5	176.6	175.2	176.6
75°	156.9	155.6	153.0	150.4	151.7	147.8	143.9	142.6	142.6	139.9	139.9
77.5°	120.3	122.9	117.7	116.4	113.8	111.2	109.9	108.5	108.5	108.5	111.2
80°	83.7	85.0	85.0	82.4	83.7	79.8	79.8	79.8	75.9	77.2	78.5
82.5°	53.6	53.6	52.3	53.6	52.3	52.3	51.0	51.0	49.7	49.7	51.0
85°	30.1	28.8	27.5	30.1	28.8	28.8	27.5	27.5	27.5	27.5	27.5
87.5°	6.5	7.8	7.8	7.8	7.8	9.2	9.2	9.2	10.5	10.5	10.5
90°	12.7	12.1	11.6	11.0	10.4	9.5	8.5	7.6	6.7	6.2	5.6
92.5°	13.4	13.1	12.9	12.6	12.4	12.1	11.7	11.4	11.1	10.9	11.1
95°	22.5	21.9	21.4	20.8	20.2	19.4	18.6	17.8	17.0	16.6	18.5
97.5°	27.8	27.5	27.1	26.8	26.4	24.6	22.7	20.9	19.0	18.1	22.8
100°	33.2	32.3	31.4	30.5	29.6	27.6	25.6	23.7	21.7	20.7	28.6
102.5°	35.7	34.4	33.1	31.9	30.6	51.6	72.6	93.5	114.5	125.0	125.1
105°	36.7	35.4	34.1	32.9	31.6	63.1	94.5	126.0	157.5	173.2	171.5
107.5°	37.8	36.5	35.2	34.0	32.7	71.5	110.3	149.2	188.0	207.4	206.0
110°	44.7	56.2	67.7	79.2	90.7	124.0	157.3	190.6	223.9	240.6	239.4

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	64.7	114.4	164.1	213.7	263.4	265.4	267.3	269.3	271.2	272.2	271.2
115°	106.5	159.8	213.2	266.5	319.9	317.0	314.2	311.3	308.4	307.0	306.0
117.5°	282.0	298.5	315.0	331.4	347.9	345.9	344.0	342.0	340.1	339.1	337.9
120°	385.6	384.2	382.9	381.5	380.1	378.0	375.9	373.8	371.7	370.7	369.8
122.5°	413.5	412.8	412.1	411.4	410.7	408.4	406.1	403.8	401.5	400.3	399.4
125°	441.4	440.6	439.7	438.9	438.1	435.9	433.7	431.6	429.4	428.3	427.5
127.5°	468.1	467.0	465.8	464.7	463.5	461.8	460.1	458.4	456.7	455.8	455.0
130°	493.0	491.7	490.4	489.2	487.9	486.6	485.4	484.1	482.8	482.2	481.3
132.5°	516.4	515.4	514.3	513.3	512.3	511.0	509.8	508.5	507.2	506.6	505.8
135°	539.2	538.1	536.9	535.8	534.6	533.6	532.5	531.5	530.4	529.9	529.0
137.5°	560.4	559.3	558.1	557.0	555.8	554.7	553.5	552.4	551.3	550.7	550.0
140°	580.7	579.7	578.6	577.6	576.6	575.3	574.1	572.8	571.5	570.9	570.4
142.5°	599.4	598.5	597.6	596.7	595.8	594.3	592.8	591.3	589.8	589.0	588.6
145°	616.6	615.8	615.0	614.2	613.4	611.4	609.5	607.5	605.6	604.6	604.7
147.5°	631.8	631.2	630.7	630.1	629.5	627.5	625.5	623.6	621.6	620.6	620.8
150°	646.3	645.6	644.9	644.2	643.5	641.7	639.8	638.0	636.1	635.2	635.6
152.5°	659.2	658.5	657.8	657.1	656.4	654.7	652.9	651.2	649.5	648.6	649.1
155°	670.6	669.9	669.2	668.5	667.8	666.4	665.0	663.7	662.3	661.6	662.1
157.5°	680.9	680.1	679.3	678.5	677.7	676.7	675.6	674.6	673.5	673.0	673.5
160°	689.3	688.6	687.9	687.2	686.5	685.8	685.1	684.4	683.7	683.4	683.7
162.5°	697.5	696.7	695.9	695.1	694.3	693.7	693.1	692.6	692.0	691.7	692.0
165°	703.7	702.9	702.1	701.3	700.5	700.1	699.8	699.4	699.1	698.9	699.3
167.5°	709.4	708.6	707.8	707.0	706.2	705.8	705.5	705.1	704.8	704.6	705.0
170°	713.6	712.8	712.0	711.2	710.4	710.2	709.9	709.7	709.4	709.3	709.6
172.5°	716.7	715.9	715.1	714.3	713.5	713.3	713.0	712.8	712.5	712.4	712.7
175°	718.8	718.0	717.1	716.3	715.5	715.3	715.1	714.8	714.6	714.5	714.9
177.5°	719.3	718.5	717.7	716.9	716.1	716.0	715.8	715.7	715.6	715.5	715.9
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1701.5	1701.5	1701.5	1701.5
2.5°	1670.1	1670.1	1689.7	1710.6
5°	1633.5	1642.6	1674.0	1702.8
7.5°	1598.2	1613.9	1653.1	1689.7
10°	1555.0	1575.9	1624.3	1667.5
12.5°	1513.2	1532.8	1589.0	1637.4
15°	1454.3	1479.2	1539.3	1599.5
17.5°	1395.5	1420.3	1493.5	1564.2
20°	1326.1	1358.8	1441.2	1535.4
22.5°	1262.1	1302.6	1394.1	1470.0
25°	1191.4	1254.2	1339.2	1437.3
27.5°	1128.7	1191.4	1277.8	1377.1
30°	1058.0	1122.1	1211.1	1302.6
32.5°	990.0	1048.9	1135.2	1247.7
35°	919.4	975.6	1059.3	1173.1
37.5°	855.3	910.3	1001.8	1106.4
40°	792.5	850.1	928.6	1033.2
42.5°	733.7	784.7	855.3	959.9
45°	680.1	716.7	782.1	880.2
47.5°	623.8	656.5	716.7	814.8
50°	571.5	599.0	651.3	742.8
52.5°	520.5	544.1	592.4	665.7
55°	474.7	497.0	532.3	604.2
57.5°	427.7	444.7	478.7	536.2
60°	381.9	397.6	425.0	472.1
62.5°	336.1	349.2	375.3	413.3
65°	295.6	306.0	325.6	358.3
67.5°	256.3	262.9	278.6	304.7
70°	218.4	223.6	236.7	257.6
72.5°	177.9	183.1	197.5	211.9
75°	143.9	145.2	155.6	167.4
77.5°	112.5	111.2	119.0	128.2
80°	77.2	81.1	87.6	91.5
82.5°	52.3	53.6	56.2	58.9
85°	28.8	30.1	30.1	34.0
87.5°	11.8	13.1	13.1	14.4
90°	4.3	3.0	1.8	0.5
92.5°	11.6	12.1	12.5	13.0
95°	22.3	26.1	29.9	33.7
97.5°	32.3	41.8	51.2	60.7
100°	44.4	60.2	76.0	91.8
102.5°	125.3	125.6	125.8	126.0
105°	168.0	164.5	161.1	157.6
107.5°	203.1	200.2	197.3	194.4
110°	237.0	234.5	232.1	229.7



TEST NUMBER: P1008249

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	269.1	267.0	265.0	262.9
115°	304.0	302.1	300.1	298.1
117.5°	335.6	333.3	331.0	328.7
120°	368.1	366.4	364.7	363.0
122.5°	397.5	395.7	393.8	392.0
125°	426.0	424.5	423.0	421.5
127.5°	453.4	451.7	450.1	448.5
130°	479.4	477.6	475.7	473.9
132.5°	504.3	502.8	501.3	499.8
135°	527.1	525.3	523.4	521.6
137.5°	548.6	547.2	545.8	544.4
140°	569.5	568.6	567.6	566.7
142.5°	587.8	587.0	586.2	585.4
145°	604.8	604.9	605.0	605.1
147.5°	621.1	621.5	621.8	622.2
150°	636.4	637.2	638.0	638.8
152.5°	650.0	650.9	651.9	652.8
155°	663.2	664.2	665.3	666.3
157.5°	674.4	675.3	676.3	677.2
160°	684.4	685.1	685.8	686.5
162.5°	692.7	693.4	694.1	694.8
165°	700.0	700.7	701.4	702.1
167.5°	705.7	706.4	707.1	707.8
170°	710.3	711.0	711.7	712.4
172.5°	713.4	714.1	714.8	715.5
175°	715.7	716.5	717.3	718.1
177.5°	716.7	717.6	718.4	719.2
180°	716.6	716.6	716.6	716.6

(END OF REPORT)