

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008347

Luminaire Tested: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008347
REPORT IS A COMBINATION OF REPORTS P988027 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5375.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	29	29	29
1	91	87	84	81	81	77	75	72	59	57	55	42	41	40	26	25	25	25	25	18
2	83	77	71	66	74	68	63	59	52	49	46	37	35	34	23	22	21	21	21	15
3	76	68	61	56	67	60	55	50	46	42	39	33	31	29	21	20	19	19	19	13
4	70	60	53	47	62	53	47	43	41	37	34	30	27	25	19	18	16	16	16	12
5	64	53	46	40	57	48	41	37	37	32	29	27	24	22	17	16	14	14	14	11
6	59	48	40	35	52	43	36	32	33	29	25	24	21	19	16	14	13	13	13	10
7	55	43	36	31	48	39	32	28	30	26	22	22	19	17	14	13	12	12	12	9
8	51	39	32	27	45	35	29	25	27	23	20	20	17	15	13	12	10	10	10	8
9	47	36	29	24	42	32	26	22	25	21	18	18	16	14	12	11	10	10	10	7
10	44	33	26	21	39	29	23	19	23	19	16	17	14	12	11	10	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10012	10012	10012	10012
5°	10035	10634	10070	8496
10°	9925	11240	9995	7015
15°	9709	11243	9873	5270
20°	9450	9293	9655	4348
25°	9136	5807	9333	3699
30°	8735	3718	8973	3185
35°	8248	2858	8514	2725
40°	7703	2402	8033	2384
45°	7122	2044	7421	2001
50°	6526	1737	6832	1731
55°	5867	1510	6185	1489
60°	5283	1151	5562	1137
65°	4735	866	5016	982
70°	4131	692	4452	801
75°	3491	530	3810	605
80°	2770	359	2986	397
85°	1921	186	2105	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9159 cd/sqm

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	1.1
10°-20°	167.5	3.1
20°-30°	215.5	4.0
30°-40°	204.5	3.8
40°-50°	175.2	3.3
50°-60°	133.4	2.5
60°-70°	84.2	1.6
70°-80°	42.0	0.8
80°-90°	13.4	0.2
90°-100°	48.2	0.9
100°-110°	179.4	3.3
110°-120°	475.9	8.9
120°-130°	789.3	14.7
130°-140°	838.4	15.6
140°-150°	779.2	14.5
150°-160°	626.5	11.7
160°-170°	403.7	7.5
170°-180°	138.9	2.6
0°-30°	443.0	8.2
0°-40°	647.4	12.0
0°-60°	956.1	17.8
0°-90°	1095.6	20.4
90°-120°	703.5	13.1
90°-150°	3110.4	57.9
90°-180°	4279.0	79.6
0°-180°	5375.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	632	632	632	632	632	
5°	633	704	635	562	633	60
15°	596	794	606	372	596	168
25°	529	424	541	270	529	243
35°	434	209	448	199	434	272
45°	326	145	340	142	326	252
55°	220	101	232	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	68
85°	14	8	15	8	14	15
90°	1	28	1	28	1	5
95°	69	45	69	45	69	81
105°	321	80	321	80	321	343
115°	607	87	607	87	607	598
125°	859	903	859	903	859	766
135°	1063	1097	1063	1097	1063	821
145°	1233	1252	1233	1252	1233	771
155°	1357	1358	1357	1358	1357	625
165°	1430	1427	1430	1427	1430	404
175°	1463	1454	1463	1454	1463	139
180°	1460	1460	1460	1460	1460	

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	636.4	639.1	640.4	642.1	646.1	648.7	652.7	653.6	653.1	654.9	650.1
5°	632.9	638.6	643.9	648.3	655.3	659.7	664.6	670.3	671.6	678.2	674.2
7.5°	628.1	636.4	643.9	652.7	663.2	669.0	676.4	685.2	689.2	697.1	699.3
10°	620.2	632.0	644.8	654.0	668.5	678.6	685.7	699.7	709.0	720.8	719.1
12.5°	607.4	622.8	639.9	655.3	674.2	680.8	694.0	708.5	720.4	731.4	741.0
15°	596.4	614.0	632.9	651.8	673.4	685.7	698.8	717.7	730.5	749.8	758.2
17.5°	581.5	603.9	626.3	647.4	672.9	687.0	703.2	721.7	740.6	759.1	765.7
20°	566.1	590.3	614.5	643.0	672.0	685.7	702.4	725.2	743.7	758.2	758.2
22.5°	547.6	577.1	604.8	632.0	663.7	683.5	700.6	727.4	740.6	743.7	731.8
25°	529.2	558.6	589.0	622.8	658.8	676.4	695.8	720.8	725.2	712.9	682.1
27.5°	507.2	540.2	574.5	610.9	648.7	670.7	688.3	705.0	696.6	663.7	615.8
30°	484.8	520.4	559.1	593.8	639.5	659.7	674.7	679.5	653.1	599.5	537.5
32.5°	461.5	496.2	537.1	578.9	625.0	644.3	654.0	641.3	592.9	525.2	449.6
35°	434.3	473.4	516.0	559.5	605.2	619.7	625.4	594.2	532.3	444.8	369.6
37.5°	409.6	448.8	494.5	538.9	583.3	591.2	585.4	536.7	458.0	371.4	298.0
40°	380.6	422.4	467.2	516.9	553.4	555.6	541.5	478.2	380.6	299.3	254.0
42.5°	353.8	396.0	440.8	491.4	519.1	511.6	492.7	409.6	317.8	258.0	221.5
45°	326.1	366.1	414.5	459.3	479.1	461.5	432.9	344.6	266.8	222.0	193.8
47.5°	299.3	336.7	384.6	427.7	431.2	411.4	377.6	288.8	231.2	195.1	172.3
50°	272.9	310.3	355.1	390.7	387.2	360.0	321.7	251.0	200.9	172.3	153.4
52.5°	246.6	280.4	323.9	352.1	337.1	310.7	272.9	212.7	175.4	150.3	135.8
55°	220.2	251.8	289.2	312.5	288.8	258.4	231.6	182.4	152.1	131.9	120.9
57.5°	198.2	223.3	257.6	271.6	243.1	219.3	196.0	156.9	131.9	117.4	104.6
60°	174.1	196.9	225.0	233.4	203.9	184.6	164.8	132.7	113.0	100.2	91.9
62.5°	153.4	172.3	193.8	193.8	167.9	153.4	138.5	111.2	94.9	84.8	80.9
65°	133.2	146.8	162.2	160.4	138.5	125.7	113.8	91.9	79.6	72.5	68.6
67.5°	113.4	123.9	134.1	127.9	112.1	101.1	90.1	74.3	65.9	61.1	55.8
70°	95.4	103.7	109.0	103.3	87.5	78.2	70.3	59.8	53.2	47.0	44.0
72.5°	80.0	83.5	85.3	78.2	65.0	59.8	54.1	46.6	40.9	37.8	36.9
75°	62.4	65.5	64.2	58.9	47.9	44.0	39.6	34.3	33.0	31.2	30.3
77.5°	48.8	48.8	46.6	41.8	34.3	31.2	29.4	26.8	25.5	25.1	24.2
80°	34.7	34.3	33.0	27.7	23.3	21.5	21.5	19.8	19.3	18.5	18.5
82.5°	22.9	22.9	21.1	16.7	15.4	14.9	14.5	13.6	13.6	13.2	13.2
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.4	7.9	8.4	7.9	7.9
87.5°	6.2	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	1.1	3.7	6.3	8.8	11.4	12.7	13.6	15.5	17.4	19.2	21.1
92.5°	26.4	25.5	24.5	23.6	22.7	22.2	22.5	23.2	23.9	24.6	25.3
95°	68.7	60.9	53.2	45.4	37.7	33.8	34.6	36.3	37.9	39.6	41.2
97.5°	123.6	104.4	85.1	65.9	46.6	37.0	38.9	42.6	46.4	50.1	53.9
100°	187.0	154.8	122.6	90.5	58.3	42.2	44.2	48.2	52.2	56.2	60.2
102.5°	256.7	256.2	255.8	255.3	254.8	254.6	233.2	190.5	147.8	105.0	62.3
105°	321.1	328.1	335.2	342.2	349.3	352.8	320.8	256.7	192.6	128.5	64.4
107.5°	396.1	402.0	407.8	413.7	419.6	422.5	382.9	303.8	224.7	145.6	66.5
110°	467.9	472.8	477.8	482.7	487.6	490.1	456.2	388.3	320.5	252.6	184.8

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	535.5	539.7	543.9	548.2	552.4	554.5	552.5	548.5	544.6	540.6	536.6
115°	607.3	611.3	615.3	619.3	623.3	625.3	628.2	634.1	640.0	645.8	651.7
117.5°	669.7	674.4	679.1	683.8	688.5	690.8	692.8	696.8	700.7	704.7	708.7
120°	739.4	742.9	746.4	749.9	753.4	755.2	757.3	761.5	765.8	770.0	774.2
122.5°	798.5	802.3	806.0	809.8	813.5	815.4	817.7	822.4	827.1	831.8	836.5
125°	858.7	861.8	864.8	867.9	871.0	872.5	874.7	879.2	883.6	888.1	892.5
127.5°	913.7	917.0	920.2	923.5	926.8	928.4	930.2	933.7	937.2	940.8	944.3
130°	965.4	969.2	972.9	976.7	980.4	982.3	983.6	986.2	988.7	991.3	993.9
132.5°	1018.2	1021.3	1024.3	1027.4	1030.5	1032.0	1033.3	1035.9	1038.4	1041.0	1043.6
135°	1062.6	1066.4	1070.1	1073.9	1077.6	1079.5	1080.6	1082.7	1084.8	1086.9	1089.0
137.5°	1109.1	1111.9	1114.7	1117.5	1120.3	1121.7	1122.9	1125.2	1127.6	1129.9	1132.3
140°	1154.5	1156.4	1158.2	1160.1	1162.0	1162.9	1164.2	1166.8	1169.3	1171.9	1174.5
142.5°	1192.5	1194.1	1195.8	1197.4	1199.1	1199.9	1201.4	1204.5	1207.5	1210.6	1213.6
145°	1232.6	1232.4	1232.2	1231.9	1231.7	1231.6	1233.6	1237.6	1241.5	1245.5	1249.5
147.5°	1267.5	1266.8	1266.1	1265.4	1264.7	1264.3	1266.3	1270.3	1274.3	1278.3	1282.3
150°	1301.3	1299.7	1298.0	1296.4	1294.7	1293.9	1295.8	1299.5	1303.3	1307.0	1310.8
152.5°	1329.8	1327.9	1326.1	1324.2	1322.3	1321.4	1323.2	1326.7	1330.2	1333.7	1337.2
155°	1357.3	1355.2	1353.1	1351.0	1348.9	1347.8	1349.2	1352.0	1354.8	1357.6	1360.4
157.5°	1379.5	1377.6	1375.7	1373.8	1371.9	1371.0	1372.1	1374.2	1376.3	1378.4	1380.5
160°	1398.5	1397.1	1395.7	1394.2	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5
162.5°	1415.4	1414.0	1412.6	1411.1	1409.7	1409.0	1409.6	1410.8	1411.9	1413.1	1414.3
165°	1430.2	1428.8	1427.4	1425.9	1424.5	1423.8	1424.2	1424.9	1425.6	1426.3	1427.0
167.5°	1441.8	1440.4	1439.0	1437.5	1436.1	1435.4	1435.8	1436.5	1437.2	1437.9	1438.6
170°	1451.3	1449.9	1448.5	1447.0	1445.6	1444.9	1445.1	1445.6	1446.1	1446.6	1447.1
172.5°	1457.6	1456.2	1454.8	1453.4	1452.0	1451.3	1451.5	1452.0	1452.5	1452.9	1453.4
175°	1462.9	1461.3	1459.6	1458.0	1456.3	1455.5	1455.7	1456.2	1456.7	1457.1	1457.6
177.5°	1465.0	1463.4	1461.7	1460.1	1458.4	1457.6	1457.7	1458.0	1458.2	1458.5	1458.7
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	654.9	655.8	657.1	663.2	664.1	665.9	665.0	665.0	665.4	664.6	665.0
5°	683.0	684.3	690.9	698.4	700.2	698.4	700.6	703.7	703.7	703.7	702.8
7.5°	709.4	714.2	721.7	732.7	734.9	737.1	741.0	738.4	739.3	743.2	741.9
10°	734.9	741.9	750.3	759.5	764.3	767.4	769.2	773.1	782.4	771.8	775.8
12.5°	759.1	769.2	778.0	788.1	791.6	795.5	796.9	800.4	800.4	799.9	803.0
15°	774.9	784.1	792.0	798.6	799.5	798.6	797.7	798.2	799.5	794.2	797.3
17.5°	778.4	779.3	781.9	779.3	779.7	770.5	765.2	763.9	751.6	752.0	762.1
20°	761.3	746.3	742.4	727.9	719.1	695.3	694.5	687.9	661.9	669.8	668.1
22.5°	714.2	688.7	654.9	638.2	629.8	604.8	585.4	571.8	562.6	553.4	549.4
25°	652.3	610.9	563.0	530.1	525.2	501.9	466.3	449.6	429.9	423.7	434.3
27.5°	572.3	518.6	464.6	414.0	404.8	383.7	365.7	353.8	331.0	329.6	330.5
30°	463.7	409.6	364.4	331.4	308.5	298.9	287.0	278.2	269.0	272.5	273.4
32.5°	381.1	329.6	287.4	269.9	259.3	253.2	243.1	237.3	233.4	232.1	231.6
35°	302.8	268.6	249.7	232.5	226.4	222.0	214.5	211.9	208.3	208.8	208.8
37.5°	259.3	230.8	216.7	207.9	202.2	200.0	195.1	192.5	190.3	189.4	190.8
40°	223.7	203.9	195.1	187.2	182.4	181.5	178.9	175.8	173.2	173.6	174.9
42.5°	197.8	186.4	175.8	169.7	166.1	164.8	162.6	160.4	160.4	159.1	158.7
45°	177.1	167.9	159.1	153.4	151.2	149.4	146.8	146.4	144.6	145.0	145.5
47.5°	158.7	151.2	144.6	138.9	136.7	136.3	133.6	131.9	131.9	131.4	131.0
50°	142.0	134.5	128.8	125.7	122.6	121.7	121.3	120.9	120.0	120.0	120.4
52.5°	128.3	120.9	116.5	113.8	112.1	111.2	111.2	110.8	110.8	110.8	110.3
55°	113.4	107.2	103.7	102.8	102.0	101.5	101.1	100.2	99.8	100.7	99.8
57.5°	99.3	97.1	94.1	93.2	91.0	91.0	89.7	88.8	87.9	88.8	88.8
60°	88.3	85.3	83.5	80.9	79.1	77.4	75.2	74.7	73.8	73.4	73.0
62.5°	76.9	74.3	69.9	65.9	63.3	61.5	60.7	60.2	60.2	59.8	59.8
65°	64.2	58.0	55.8	54.5	54.1	53.6	52.7	52.3	52.7	52.3	52.7
67.5°	50.1	49.2	47.9	47.0	46.6	46.2	46.2	45.7	45.7	45.7	45.7
70°	43.5	41.3	40.9	40.0	40.0	39.6	39.6	39.6	39.6	39.1	40.0
72.5°	36.0	34.7	34.3	33.8	33.8	33.8	33.4	33.4	33.4	33.0	33.4
75°	29.4	29.0	28.1	28.1	27.7	28.1	27.7	27.7	27.3	27.7	27.7
77.5°	23.7	23.3	22.9	22.9	22.4	22.4	22.4	22.4	22.4	22.4	22.9
80°	18.0	17.6	17.1	17.6	17.1	17.6	17.1	17.1	17.6	17.1	17.1
82.5°	13.2	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	4.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0
90°	22.3	23.5	24.6	25.8	26.4	26.6	27.1	27.6	28.0	28.5	28.0
92.5°	25.8	26.3	26.8	27.3	27.5	27.6	27.8	28.1	28.3	28.5	28.3
95°	42.4	43.6	44.7	45.9	46.5	46.4	46.1	45.9	45.6	45.4	45.6
97.5°	54.6	55.3	56.0	56.7	57.0	57.1	57.4	57.6	57.9	58.1	57.9
100°	62.1	64.0	65.9	67.8	68.7	68.9	69.4	69.9	70.3	70.8	70.3
102.5°	64.9	67.5	70.0	72.6	73.9	74.3	75.0	75.7	76.4	77.1	76.4
105°	67.0	69.6	72.1	74.7	76.0	76.5	77.4	78.4	79.3	80.3	79.3
107.5°	69.1	71.7	74.3	76.9	78.2	78.7	79.6	80.5	81.5	82.4	81.5
110°	161.3	137.9	114.4	90.9	79.2	79.7	80.6	81.5	82.5	83.4	82.5

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	435.4	334.2	233.1	131.9	81.3	81.7	82.4	83.1	83.8	84.5	83.8
115°	543.0	434.4	325.7	217.0	162.7	154.2	137.3	120.4	103.5	86.6	103.5
117.5°	675.1	641.6	608.0	574.5	557.7	527.0	465.5	404.0	342.5	281.0	342.5
120°	777.0	779.8	782.7	785.5	786.9	771.1	739.4	707.7	676.0	644.3	676.0
122.5°	837.9	839.3	840.8	842.2	842.9	843.0	843.2	843.5	843.7	843.9	843.7
125°	894.1	895.8	897.4	899.1	899.9	900.3	901.0	901.7	902.4	903.1	902.4
127.5°	946.6	949.0	951.3	953.6	954.8	954.9	955.2	955.4	955.7	955.9	955.7
130°	996.5	999.1	1001.6	1004.2	1005.5	1005.4	1005.2	1004.9	1004.7	1004.5	1004.7
132.5°	1045.7	1047.8	1049.9	1052.0	1053.1	1053.0	1052.7	1052.5	1052.2	1052.0	1052.2
135°	1091.4	1093.7	1096.1	1098.4	1099.6	1099.4	1098.9	1098.4	1097.9	1097.4	1097.9
137.5°	1134.7	1137.0	1139.4	1141.7	1142.9	1142.5	1141.8	1141.1	1140.4	1139.7	1140.4
140°	1176.6	1178.8	1180.9	1183.0	1184.1	1183.5	1182.3	1181.2	1180.0	1178.8	1180.0
142.5°	1215.5	1217.4	1219.3	1221.2	1222.1	1221.5	1220.3	1219.2	1218.0	1216.8	1218.0
145°	1251.1	1252.8	1254.4	1256.1	1256.3	1256.3	1255.2	1254.0	1252.9	1251.7	1252.9
147.5°	1283.5	1284.7	1285.8	1287.0	1287.6	1287.1	1286.2	1285.2	1284.3	1283.3	1284.3
150°	1312.2	1313.6	1315.0	1316.4	1317.1	1316.5	1315.4	1314.2	1313.1	1311.9	1313.1
152.5°	1338.6	1340.0	1341.4	1342.8	1343.5	1342.7	1341.1	1339.4	1337.8	1336.2	1337.8
155°	1361.8	1363.2	1364.7	1366.1	1366.8	1365.9	1364.0	1362.1	1360.2	1358.3	1360.2
157.5°	1382.1	1383.8	1385.4	1387.1	1387.9	1387.0	1385.1	1383.2	1381.4	1379.5	1381.4
160°	1399.9	1401.3	1402.7	1404.1	1404.8	1404.0	1402.3	1400.7	1399.0	1397.4	1399.0
162.5°	1415.9	1417.6	1419.2	1420.9	1421.7	1420.6	1418.5	1416.4	1414.3	1412.2	1414.3
165°	1428.6	1430.3	1431.9	1433.6	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1428.6
167.5°	1440.2	1441.9	1443.5	1445.2	1446.0	1444.9	1442.8	1440.7	1438.6	1436.5	1438.6
170°	1448.7	1450.4	1452.0	1453.7	1454.5	1453.4	1451.3	1449.2	1447.0	1444.9	1447.0
172.5°	1455.0	1456.7	1458.3	1460.0	1460.8	1459.7	1457.6	1455.5	1453.4	1451.3	1453.4
175°	1459.2	1460.9	1462.5	1464.2	1465.0	1463.8	1461.5	1459.2	1456.8	1454.5	1456.8
177.5°	1460.3	1462.0	1463.6	1465.3	1466.1	1465.0	1462.9	1460.8	1458.7	1456.6	1458.7
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	666.8	663.7	662.8	663.7	662.8	663.2	660.2	648.7	651.8	647.0	649.6
5°	704.6	701.9	696.2	695.3	694.5	693.6	689.2	679.1	675.1	668.5	668.1
7.5°	740.6	740.6	736.2	733.1	729.2	726.1	720.4	705.4	699.3	691.4	687.0
10°	776.2	764.8	769.6	766.5	756.9	755.1	744.6	735.8	723.9	716.0	709.0
12.5°	801.7	798.2	793.8	791.1	788.5	782.8	775.8	753.3	747.2	731.4	723.5
15°	800.8	798.6	799.9	799.9	799.1	797.7	792.0	775.8	765.2	749.8	736.2
17.5°	757.7	763.5	769.2	773.1	781.9	785.9	791.1	781.5	774.9	761.7	747.2
20°	682.6	696.6	713.4	716.9	724.8	748.1	758.6	767.0	769.6	765.2	753.3
22.5°	578.0	589.8	630.3	629.4	640.8	668.5	699.3	724.3	744.1	755.1	750.7
25°	452.7	469.4	491.0	507.2	544.6	585.9	624.1	664.1	698.4	728.7	736.2
27.5°	342.4	364.4	381.5	403.0	421.9	470.7	520.0	582.4	622.4	679.9	709.8
30°	276.9	287.0	304.2	314.3	323.5	360.9	416.7	478.2	548.5	614.9	666.3
32.5°	236.5	243.5	256.2	260.6	270.3	295.4	330.5	386.8	459.3	539.7	607.4
35°	212.3	219.8	222.4	226.4	234.3	250.1	274.3	315.1	380.6	459.3	540.2
37.5°	191.6	195.6	203.1	205.7	208.3	220.2	236.5	265.0	308.5	373.2	462.8
40°	177.1	179.3	183.3	185.5	187.2	195.6	210.1	229.4	261.5	310.7	393.4
42.5°	161.7	164.4	167.0	169.7	171.9	178.4	187.2	205.7	227.2	264.6	324.4
45°	146.8	148.6	151.6	153.4	156.5	161.7	169.7	182.4	201.7	225.5	273.8
47.5°	133.2	135.4	136.7	138.9	141.1	146.8	154.3	162.6	178.4	201.7	236.9
50°	120.9	123.5	125.3	125.7	127.5	132.7	138.9	148.1	158.2	176.2	207.0
52.5°	112.1	112.5	113.8	115.6	115.2	118.2	123.9	131.0	141.5	156.0	178.4
55°	102.0	103.3	104.2	104.6	104.6	107.2	110.3	116.9	125.3	137.1	156.0
57.5°	89.2	90.5	93.2	94.1	95.4	96.7	98.0	102.4	109.4	120.9	136.3
60°	76.0	76.9	79.6	81.3	82.2	85.7	87.5	91.0	94.9	103.3	117.8
62.5°	61.1	62.0	63.3	65.0	66.8	72.1	76.5	80.0	83.1	88.8	100.7
65°	53.2	53.6	54.5	54.9	55.4	57.6	61.5	66.4	72.1	76.5	83.5
67.5°	46.2	46.6	47.0	47.9	48.3	48.8	50.5	51.9	57.6	63.7	69.0
70°	39.6	40.4	40.9	40.9	41.3	42.2	43.1	44.8	46.6	49.7	56.3
72.5°	33.4	33.8	34.7	34.7	34.7	35.6	36.5	37.4	38.2	40.0	42.6
75°	27.7	28.6	28.6	28.6	29.0	29.0	29.9	30.8	31.6	33.0	33.8
77.5°	22.9	22.9	22.9	22.9	23.3	23.3	23.7	24.6	25.1	25.5	26.4
80°	17.1	17.6	17.6	17.6	18.0	18.0	18.0	18.9	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.2	12.7	13.2	13.2	13.6	13.2	13.6	14.1
85°	7.9	7.9	7.9	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.8
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	27.6	27.1	26.6	26.4	25.8	24.6	23.5	22.3	21.1	19.2	17.4
92.5°	28.1	27.8	27.6	27.5	27.3	26.8	26.3	25.8	25.3	24.6	23.9
95°	45.9	46.1	46.4	46.5	45.9	44.7	43.6	42.4	41.2	39.6	37.9
97.5°	57.6	57.4	57.1	57.0	56.7	56.0	55.3	54.6	53.9	50.1	46.4
100°	69.9	69.4	68.9	68.7	67.8	65.9	64.0	62.1	60.2	56.2	52.2
102.5°	75.7	75.0	74.3	73.9	72.6	70.0	67.5	64.9	62.3	105.0	147.8
105°	78.4	77.4	76.5	76.0	74.7	72.1	69.6	67.0	64.4	128.5	192.6
107.5°	80.5	79.6	78.7	78.2	76.9	74.3	71.7	69.1	66.5	145.6	224.7
110°	81.5	80.6	79.7	79.2	90.9	114.4	137.9	161.3	184.8	252.6	320.5

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.1	82.4	81.7	81.3	131.9	233.1	334.2	435.4	536.6	540.6	544.6
115°	120.4	137.3	154.2	162.7	217.0	325.7	434.4	543.0	651.7	645.8	640.0
117.5°	404.0	465.5	527.0	557.7	574.5	608.0	641.6	675.1	708.7	704.7	700.7
120°	707.7	739.4	771.1	786.9	785.5	782.7	779.8	777.0	774.2	770.0	765.8
122.5°	843.5	843.2	843.0	842.9	842.2	840.8	839.3	837.9	836.5	831.8	827.1
125°	901.7	901.0	900.3	899.9	899.1	897.4	895.8	894.1	892.5	888.1	883.6
127.5°	955.4	955.2	954.9	954.8	953.6	951.3	949.0	946.6	944.3	940.8	937.2
130°	1004.9	1005.2	1005.4	1005.5	1004.2	1001.6	999.1	996.5	993.9	991.3	988.7
132.5°	1052.5	1052.7	1053.0	1053.1	1052.0	1049.9	1047.8	1045.7	1043.6	1041.0	1038.4
135°	1098.4	1098.9	1099.4	1099.6	1098.4	1096.1	1093.7	1091.4	1089.0	1086.9	1084.8
137.5°	1141.1	1141.8	1142.5	1142.9	1141.7	1139.4	1137.0	1134.7	1132.3	1129.9	1127.6
140°	1181.2	1182.3	1183.5	1184.1	1183.0	1180.9	1178.8	1176.6	1174.5	1171.9	1169.3
142.5°	1219.2	1220.3	1221.5	1222.1	1221.2	1219.3	1217.4	1215.5	1213.6	1210.6	1207.5
145°	1254.0	1255.2	1256.3	1256.9	1256.1	1254.4	1252.8	1251.1	1249.5	1245.5	1241.5
147.5°	1285.2	1286.2	1287.1	1287.6	1287.0	1285.8	1284.7	1283.5	1282.3	1278.3	1274.3
150°	1314.2	1315.4	1316.5	1317.1	1316.4	1315.0	1313.6	1312.2	1310.8	1307.0	1303.3
152.5°	1339.4	1341.1	1342.7	1343.5	1342.8	1341.4	1340.0	1338.6	1337.2	1333.7	1330.2
155°	1362.1	1364.0	1365.9	1366.8	1366.1	1364.7	1363.2	1361.8	1360.4	1357.6	1354.8
157.5°	1383.2	1385.1	1387.0	1387.9	1387.1	1385.4	1383.8	1382.1	1380.5	1378.4	1376.3
160°	1400.7	1402.3	1404.0	1404.8	1404.1	1402.7	1401.3	1399.9	1398.5	1397.1	1395.7
162.5°	1416.4	1418.5	1420.6	1421.7	1420.9	1419.2	1417.6	1415.9	1414.3	1413.1	1411.9
165°	1430.3	1431.9	1433.6	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1426.3	1425.6
167.5°	1440.7	1442.8	1444.9	1446.0	1445.2	1443.5	1441.9	1440.2	1438.6	1437.9	1437.2
170°	1449.2	1451.3	1453.4	1454.5	1453.7	1452.0	1450.4	1448.7	1447.1	1446.6	1446.1
172.5°	1455.5	1457.6	1459.7	1460.8	1460.0	1458.3	1456.7	1455.0	1453.4	1452.9	1452.5
175°	1459.2	1461.5	1463.8	1465.0	1464.2	1462.5	1460.9	1459.2	1457.6	1457.1	1456.7
177.5°	1460.8	1462.9	1465.0	1466.1	1465.3	1463.6	1462.0	1460.3	1458.7	1458.5	1458.2
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	645.7	643.5	643.5	642.1	642.1	635.1	635.1	637.3	634.7	631.6	627.2
5°	662.4	657.5	656.2	654.5	648.7	639.9	636.4	635.1	629.8	623.2	615.8
7.5°	678.2	670.3	666.3	662.4	654.9	642.6	635.6	630.7	622.8	612.7	603.0
10°	693.6	683.5	673.4	668.5	658.0	642.6	632.5	624.6	613.1	599.5	585.9
12.5°	707.6	686.5	684.8	675.1	659.7	642.1	626.8	615.3	600.8	585.0	569.2
15°	719.9	698.4	687.9	679.1	658.8	636.9	620.6	606.5	587.2	569.2	549.8
17.5°	726.1	702.8	695.8	681.3	660.6	632.0	610.1	592.9	571.8	550.3	528.3
20°	732.3	705.0	693.6	683.5	655.3	622.8	598.2	578.4	555.1	529.6	505.5
22.5°	735.3	705.0	691.4	677.3	650.1	612.7	583.7	560.4	533.1	507.2	478.2
25°	730.1	702.4	686.1	671.6	640.8	600.4	567.0	540.6	511.6	482.2	452.7
27.5°	716.9	696.2	677.3	662.4	628.1	584.6	549.4	519.5	489.6	456.7	426.8
30°	692.3	683.0	668.1	651.4	614.0	570.5	528.7	498.0	465.0	432.1	400.8
32.5°	654.0	661.9	652.3	637.8	597.3	551.2	506.8	475.6	439.5	403.9	375.4
35°	607.4	635.6	630.3	620.2	579.7	530.5	486.1	448.3	412.3	376.2	347.7
37.5°	556.4	599.1	603.5	597.3	559.5	509.4	460.6	423.7	386.8	350.3	321.3
40°	486.6	552.0	566.1	568.7	538.4	483.9	432.9	396.9	360.4	324.8	289.6
42.5°	422.4	505.0	522.6	533.6	511.6	458.9	407.4	367.4	331.4	299.3	264.2
45°	362.2	448.3	476.9	491.0	481.3	430.3	377.1	339.8	306.8	277.3	243.5
47.5°	300.2	386.8	426.8	449.2	449.2	401.3	348.1	311.2	279.5	254.5	224.6
50°	258.9	331.0	372.3	401.7	409.6	371.8	321.7	285.7	255.8	228.6	205.7
52.5°	220.6	285.3	319.5	350.3	373.2	340.2	292.3	259.8	230.3	204.8	186.8
55°	190.8	239.1	270.3	304.2	329.6	308.1	263.7	232.1	206.6	185.5	170.1
57.5°	162.2	204.4	229.9	259.8	287.0	270.7	235.1	207.9	185.5	167.0	153.4
60°	138.0	172.3	192.1	215.4	249.2	237.8	208.3	183.3	165.3	148.6	137.1
62.5°	117.4	144.6	161.3	178.0	208.8	203.5	180.6	161.3	145.9	131.9	122.2
65°	96.3	118.7	131.9	146.4	171.0	173.2	154.7	141.1	127.0	114.7	105.9
67.5°	77.8	95.4	107.2	119.6	139.3	145.5	132.7	121.3	109.4	99.3	91.4
70°	62.9	75.2	83.9	93.6	109.9	117.4	110.8	102.8	93.2	84.8	77.8
72.5°	49.7	57.6	62.9	70.3	83.5	91.0	90.5	83.5	76.5	70.8	65.0
75°	36.5	42.6	47.0	51.9	62.4	69.4	71.2	68.1	61.1	56.7	52.3
77.5°	27.7	31.2	33.4	36.9	44.4	50.5	53.2	52.3	47.5	44.0	40.9
80°	21.1	22.0	22.9	24.2	30.3	36.0	37.8	37.4	34.7	33.4	29.9
82.5°	14.9	15.4	15.8	16.3	18.5	23.3	25.1	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.9	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	4.0	4.0	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	15.5	13.6	12.7	11.4	8.8	6.3	3.7	1.1	3.7	6.3	8.8
92.5°	23.2	22.5	22.2	22.7	23.6	24.5	25.5	26.4	25.5	24.5	23.6
95°	36.3	34.6	33.8	37.7	45.4	53.2	60.9	68.7	60.9	53.2	45.4
97.5°	42.6	38.9	37.0	46.6	65.9	85.1	104.4	123.6	104.4	85.1	65.9
100°	48.2	44.2	42.2	58.3	90.5	122.6	154.8	187.0	154.8	122.6	90.5
102.5°	190.5	233.2	254.6	254.8	255.3	255.8	256.2	256.7	256.2	255.8	255.3
105°	256.7	320.8	352.8	349.3	342.2	335.2	328.1	321.1	328.1	335.2	342.2
107.5°	303.8	382.9	422.5	419.6	413.7	407.8	402.0	396.1	402.0	407.8	413.7
110°	388.3	456.2	490.1	487.6	482.7	477.8	472.8	467.9	472.8	477.8	482.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	548.5	552.5	554.5	552.4	548.2	543.9	539.7	535.5	539.7	543.9	548.2
115°	634.1	628.2	625.3	623.3	619.3	615.3	611.3	607.3	611.3	615.3	619.3
117.5°	696.8	692.8	690.8	688.5	683.8	679.1	674.4	669.7	674.4	679.1	683.8
120°	761.5	757.3	755.2	753.4	749.9	746.4	742.9	739.4	742.9	746.4	749.9
122.5°	822.4	817.7	815.4	813.5	809.8	806.0	802.3	798.5	802.3	806.0	809.8
125°	879.2	874.7	872.5	871.0	867.9	864.8	861.8	858.7	861.8	864.8	867.9
127.5°	933.7	930.2	928.4	926.8	923.5	920.2	917.0	913.7	917.0	920.2	923.5
130°	986.2	983.6	982.3	980.4	976.7	972.9	969.2	965.4	969.2	972.9	976.7
132.5°	1035.9	1033.3	1032.0	1030.5	1027.4	1024.3	1021.3	1018.2	1021.3	1024.3	1027.4
135°	1082.7	1080.6	1079.5	1077.6	1073.9	1070.1	1066.4	1062.6	1066.4	1070.1	1073.9
137.5°	1125.2	1122.9	1121.7	1120.3	1117.5	1114.7	1111.9	1109.1	1111.9	1114.7	1117.5
140°	1166.8	1164.2	1162.9	1162.0	1160.1	1158.2	1156.4	1154.5	1156.4	1158.2	1160.1
142.5°	1204.5	1201.4	1199.9	1199.1	1197.4	1195.8	1194.1	1192.5	1194.1	1195.8	1197.4
145°	1237.6	1233.6	1231.6	1231.7	1231.9	1232.2	1232.4	1232.6	1232.4	1232.2	1231.9
147.5°	1270.3	1266.3	1264.3	1264.7	1265.4	1266.1	1266.8	1267.5	1266.8	1266.1	1265.4
150°	1299.5	1295.8	1293.9	1294.7	1296.4	1298.0	1299.7	1301.3	1299.7	1298.0	1296.4
152.5°	1326.7	1323.2	1321.4	1322.3	1324.2	1326.1	1327.9	1329.8	1327.9	1326.1	1324.2
155°	1352.0	1349.2	1347.8	1348.9	1351.0	1353.1	1355.2	1357.3	1355.2	1353.1	1351.0
157.5°	1374.2	1372.1	1371.0	1371.9	1373.8	1375.7	1377.6	1379.5	1377.6	1375.7	1373.8
160°	1394.2	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5	1397.1	1395.7	1394.2
162.5°	1410.8	1409.6	1409.0	1409.7	1411.1	1412.6	1414.0	1415.4	1414.0	1412.6	1411.1
165°	1424.9	1424.2	1423.8	1424.5	1425.9	1427.4	1428.8	1430.2	1428.8	1427.4	1425.9
167.5°	1436.5	1435.8	1435.4	1436.1	1437.5	1439.0	1440.4	1441.8	1440.4	1439.0	1437.5
170°	1445.6	1445.1	1444.9	1445.6	1447.0	1448.5	1449.9	1451.3	1449.9	1448.5	1447.0
172.5°	1452.0	1451.5	1451.3	1452.0	1453.4	1454.8	1456.2	1457.6	1456.2	1454.8	1453.4
175°	1456.2	1455.7	1455.5	1456.3	1458.0	1459.6	1461.3	1462.9	1461.3	1459.6	1458.0
177.5°	1458.0	1457.7	1457.6	1458.4	1460.1	1461.7	1463.4	1465.0	1463.4	1461.7	1460.1
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	625.4	625.9	627.2	623.2	617.1	614.5	606.5	605.2	603.9	603.9	605.2
5°	611.4	609.6	610.1	602.6	593.8	588.5	577.5	579.3	573.6	570.1	570.9
7.5°	596.0	591.2	590.7	581.1	570.1	560.4	549.0	546.3	541.1	534.9	532.3
10°	576.7	573.1	566.5	555.6	541.5	533.6	518.2	509.0	507.7	498.4	494.9
12.5°	556.9	550.7	544.1	528.7	512.9	500.2	488.8	478.6	471.6	463.7	458.4
15°	534.0	526.6	519.1	502.8	484.4	471.6	454.5	439.5	418.9	402.6	393.4
17.5°	509.0	500.6	490.5	472.5	454.5	436.9	405.2	387.7	373.2	363.5	357.8
20°	483.0	473.8	463.7	445.7	414.5	383.7	366.1	352.5	343.7	334.0	327.0
22.5°	455.8	446.1	435.1	407.0	374.0	352.5	338.9	326.1	313.4	308.1	304.6
25°	430.3	421.5	407.4	369.2	343.3	323.5	308.1	299.8	293.2	286.1	279.5
27.5°	403.9	387.7	367.9	335.8	319.5	299.3	288.3	282.2	270.7	265.9	262.8
30°	372.3	354.3	335.4	312.5	293.6	279.5	269.4	259.3	252.7	247.9	242.6
32.5°	340.2	323.1	311.2	287.4	273.4	258.9	249.2	243.1	233.4	230.3	228.1
35°	312.5	298.0	287.4	268.1	254.9	241.7	234.7	225.5	219.3	213.6	210.1
37.5°	285.3	277.3	266.4	250.1	236.0	225.5	215.8	212.7	204.4	201.3	197.8
40°	266.4	254.5	245.3	231.2	219.3	207.9	201.7	194.7	189.0	184.2	182.8
42.5°	243.5	234.7	229.4	214.0	201.7	195.1	187.7	179.8	175.4	171.4	166.6
45°	226.4	218.4	211.0	198.7	187.7	179.3	172.7	167.5	160.0	158.2	150.8
47.5°	208.3	200.4	194.7	182.4	172.3	164.4	159.5	152.5	146.4	142.4	138.9
50°	190.3	183.7	178.4	167.9	159.1	150.8	144.2	137.1	134.5	127.9	125.7
52.5°	173.2	168.8	163.1	153.0	144.2	137.1	130.1	124.4	120.4	116.9	114.3
55°	158.7	151.6	149.0	138.0	130.5	123.1	116.9	113.4	108.6	106.4	104.2
57.5°	142.4	138.5	134.1	125.7	117.4	110.3	105.9	100.7	98.0	95.4	93.6
60°	128.3	122.6	119.1	112.1	104.6	98.0	94.1	90.1	86.6	84.4	80.9
62.5°	112.1	107.7	105.5	98.0	91.9	85.7	82.2	78.2	75.6	71.6	67.2
65°	98.0	94.5	91.9	85.7	80.0	74.3	70.8	65.9	62.4	60.2	59.8
67.5°	85.7	83.1	79.1	73.4	67.7	63.3	59.3	55.4	54.9	54.1	54.1
70°	72.1	69.4	67.2	61.1	56.3	51.4	50.5	49.2	47.9	47.5	46.6
72.5°	60.2	58.0	55.4	50.1	45.3	44.0	43.1	42.2	40.9	40.4	40.0
75°	48.8	45.7	44.0	39.1	37.8	36.9	36.0	34.7	33.8	33.4	32.5
77.5°	37.4	34.3	34.3	31.6	30.8	29.4	28.6	27.7	27.3	26.4	26.4
80°	26.4	26.4	25.5	24.2	22.9	22.4	21.1	20.7	20.2	20.7	19.8
82.5°	19.3	17.6	17.6	16.7	15.8	15.4	14.5	14.5	14.1	14.1	14.1
85°	11.0	11.0	10.5	9.7	9.2	9.2	8.8	8.8	8.4	8.4	7.9
87.5°	4.4	4.0	4.4	4.0	4.0	3.5	3.5	3.5	3.1	3.5	3.1
90°	11.4	12.7	13.6	15.5	17.4	19.2	21.1	22.3	23.5	24.6	25.8
92.5°	22.7	22.2	22.5	23.2	23.9	24.6	25.3	25.8	26.3	26.8	27.3
95°	37.7	33.8	34.6	36.3	37.9	39.6	41.2	42.4	43.6	44.7	45.9
97.5°	46.6	37.0	38.9	42.6	46.4	50.1	53.9	54.6	55.3	56.0	56.7
100°	58.3	42.2	44.2	48.2	52.2	56.2	60.2	62.1	64.0	65.9	67.8
102.5°	254.8	254.6	233.2	190.5	147.8	105.0	62.3	64.9	67.5	70.0	72.6
105°	349.3	352.8	320.8	256.7	192.6	128.5	64.4	67.0	69.6	72.1	74.7
107.5°	419.6	422.5	382.9	303.8	224.7	145.6	66.5	69.1	71.7	74.3	76.9
110°	487.6	490.1	456.2	388.3	320.5	252.6	184.8	161.3	137.9	114.4	90.9

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	552.4	554.5	552.5	548.5	544.6	540.6	536.6	435.4	334.2	233.1	131.9
115°	623.3	625.3	628.2	634.1	640.0	645.8	651.7	543.0	434.4	325.7	217.0
117.5°	688.5	690.8	692.8	696.8	700.7	704.7	708.7	675.1	641.6	608.0	574.5
120°	753.4	755.2	757.3	761.5	765.8	770.0	774.2	777.0	779.8	782.7	785.5
122.5°	813.5	815.4	817.7	822.4	827.1	831.8	836.5	837.9	839.3	840.8	842.2
125°	871.0	872.5	874.7	879.2	883.6	888.1	892.5	894.1	895.8	897.4	899.1
127.5°	926.8	928.4	930.2	933.7	937.2	940.8	944.3	946.6	949.0	951.3	953.6
130°	980.4	982.3	983.6	986.2	988.7	991.3	993.9	996.5	999.1	1001.6	1004.2
132.5°	1030.5	1032.0	1033.3	1035.9	1038.4	1041.0	1043.6	1045.7	1047.8	1049.9	1052.0
135°	1077.6	1079.5	1080.6	1082.7	1084.8	1086.9	1089.0	1091.4	1093.7	1096.1	1098.4
137.5°	1120.3	1121.7	1122.9	1125.2	1127.6	1129.9	1132.3	1134.7	1137.0	1139.4	1141.7
140°	1162.0	1162.9	1164.2	1166.8	1169.3	1171.9	1174.5	1176.6	1178.8	1180.9	1183.0
142.5°	1199.1	1199.9	1201.4	1204.5	1207.5	1210.6	1213.6	1215.5	1217.4	1219.3	1221.2
145°	1231.7	1231.6	1233.6	1237.6	1241.5	1245.5	1249.5	1251.1	1252.8	1254.4	1256.1
147.5°	1264.7	1264.3	1266.3	1270.3	1274.3	1278.3	1282.3	1283.5	1284.7	1285.8	1287.0
150°	1294.7	1293.9	1295.8	1299.5	1303.3	1307.0	1310.8	1312.2	1313.6	1315.0	1316.4
152.5°	1322.3	1321.4	1323.2	1326.7	1330.2	1333.7	1337.2	1338.6	1340.0	1341.4	1342.8
155°	1348.9	1347.8	1349.2	1352.0	1354.8	1357.6	1360.4	1361.8	1363.2	1364.7	1366.1
157.5°	1371.9	1371.0	1372.1	1374.2	1376.3	1378.4	1380.5	1382.1	1383.8	1385.4	1387.1
160°	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5	1399.9	1401.3	1402.7	1404.1
162.5°	1409.7	1409.0	1409.6	1410.8	1411.9	1413.1	1414.3	1415.9	1417.6	1419.2	1420.9
165°	1424.5	1423.8	1424.2	1424.9	1425.6	1426.3	1427.0	1428.6	1430.3	1431.9	1433.6
167.5°	1436.1	1435.4	1435.8	1436.5	1437.2	1437.9	1438.6	1440.2	1441.9	1443.5	1445.2
170°	1445.6	1444.9	1445.1	1445.6	1446.1	1446.6	1447.1	1448.7	1450.4	1452.0	1453.7
172.5°	1452.0	1451.3	1451.5	1452.0	1452.5	1452.9	1453.4	1455.0	1456.7	1458.3	1460.0
175°	1456.3	1455.5	1455.7	1456.2	1456.7	1457.1	1457.6	1459.2	1460.9	1462.5	1464.2
177.5°	1458.4	1457.6	1457.7	1458.0	1458.2	1458.5	1458.7	1460.3	1462.0	1463.6	1465.3
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	605.2	604.3	601.7	602.6	601.3	601.3	600.4	600.4	600.4	602.6	601.3
5°	572.3	569.2	566.1	564.8	563.5	562.2	562.2	561.7	565.7	564.8	568.3
7.5°	531.4	530.5	524.4	524.4	522.2	521.3	523.5	523.9	524.4	525.2	527.4
10°	494.9	492.7	483.9	484.8	483.5	481.7	483.0	482.2	485.2	486.1	485.2
12.5°	451.8	447.9	438.2	433.4	428.1	424.1	429.0	425.5	437.8	441.3	451.0
15°	394.7	387.2	380.6	380.6	375.8	372.3	374.5	378.4	381.1	385.0	386.8
17.5°	356.5	353.4	348.1	345.0	343.7	342.4	342.4	344.1	349.9	349.4	352.9
20°	323.9	322.2	319.5	315.6	314.3	313.4	313.4	313.4	317.3	320.9	323.1
22.5°	301.5	300.2	298.4	293.2	290.5	289.6	291.8	293.2	296.2	298.9	301.1
25°	279.1	276.0	272.9	271.2	269.9	269.9	270.7	271.2	272.5	273.8	276.5
27.5°	260.6	258.4	254.0	249.2	249.2	247.9	248.8	249.7	252.7	257.1	259.3
30°	240.0	239.5	237.8	236.0	234.3	233.4	235.1	236.5	236.9	239.1	239.1
32.5°	225.0	222.0	218.9	217.1	216.2	215.8	216.2	218.0	218.0	220.6	223.7
35°	210.1	208.3	205.3	202.2	201.3	199.1	200.9	202.6	205.7	207.0	208.3
37.5°	193.8	191.6	190.3	189.4	187.7	188.1	186.8	189.4	192.1	191.6	192.5
40°	181.5	177.6	173.6	173.2	172.7	172.3	172.3	172.7	174.5	176.2	178.9
42.5°	165.7	164.4	160.9	157.4	156.5	155.6	154.7	156.5	160.0	163.1	164.4
45°	149.4	147.7	146.8	144.2	142.4	142.0	141.1	143.3	146.4	147.7	148.6
47.5°	134.5	134.1	131.4	131.9	130.5	131.0	130.5	131.9	131.9	133.2	134.1
50°	124.4	123.1	121.7	120.9	119.6	119.6	119.1	119.6	121.3	123.1	122.6
52.5°	114.3	112.1	111.6	111.2	110.3	111.2	109.9	110.3	112.1	113.0	112.5
55°	102.4	102.0	101.1	100.2	99.8	99.3	99.3	99.3	101.1	102.4	102.8
57.5°	93.2	91.0	89.2	89.2	87.5	87.0	87.9	88.3	89.7	90.5	91.4
60°	80.4	79.6	76.9	75.6	73.0	72.5	72.5	74.3	76.5	79.6	80.4
62.5°	66.8	65.5	65.0	65.0	65.0	65.0	65.0	65.0	65.0	65.5	65.5
65°	59.3	59.8	59.3	58.9	59.3	59.3	58.9	58.9	58.9	59.3	59.8
67.5°	53.2	52.7	53.2	52.7	52.3	52.3	51.9	52.3	52.7	53.2	53.2
70°	46.2	46.2	45.7	46.2	45.7	45.3	44.8	44.8	45.7	46.2	46.2
72.5°	39.6	39.6	39.1	39.1	38.2	38.2	38.7	38.2	38.2	39.6	39.6
75°	33.0	32.5	32.1	32.1	31.6	31.6	31.6	31.2	32.1	32.1	32.5
77.5°	25.9	25.9	25.9	25.5	25.5	25.1	25.1	25.5	25.5	25.5	25.9
80°	19.8	19.8	19.8	19.3	18.9	18.9	18.9	18.9	18.9	19.3	18.9
82.5°	13.6	13.6	13.6	13.6	13.6	13.2	13.2	13.2	13.6	13.6	13.2
85°	8.4	7.9	8.4	8.4	7.9	8.4	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	26.4	26.6	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.6	26.4
92.5°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
95°	46.5	46.4	46.1	45.9	45.6	45.4	45.6	45.9	46.1	46.4	46.5
97.5°	57.0	57.1	57.4	57.6	57.9	58.1	57.9	57.6	57.4	57.1	57.0
100°	68.7	68.9	69.4	69.9	70.3	70.8	70.3	69.9	69.4	68.9	68.7
102.5°	73.9	74.3	75.0	75.7	76.4	77.1	76.4	75.7	75.0	74.3	73.9
105°	76.0	76.5	77.4	78.4	79.3	80.3	79.3	78.4	77.4	76.5	76.0
107.5°	78.2	78.7	79.6	80.5	81.5	82.4	81.5	80.5	79.6	78.7	78.2
110°	79.2	79.7	80.6	81.5	82.5	83.4	82.5	81.5	80.6	79.7	79.2

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.3	81.7	82.4	83.1	83.8	84.5	83.8	83.1	82.4	81.7	81.3
115°	162.7	154.2	137.3	120.4	103.5	86.6	103.5	120.4	137.3	154.2	162.7
117.5°	557.7	527.0	465.5	404.0	342.5	281.0	342.5	404.0	465.5	527.0	557.7
120°	786.9	771.1	739.4	707.7	676.0	644.3	676.0	707.7	739.4	771.1	786.9
122.5°	842.9	843.0	843.2	843.5	843.7	843.9	843.7	843.5	843.2	843.0	842.9
125°	899.9	900.3	901.0	901.7	902.4	903.1	902.4	901.7	901.0	900.3	899.9
127.5°	954.8	954.9	955.2	955.4	955.7	955.9	955.7	955.4	955.2	954.9	954.8
130°	1005.5	1005.4	1005.2	1004.9	1004.7	1004.5	1004.7	1004.9	1005.2	1005.4	1005.5
132.5°	1053.1	1053.0	1052.7	1052.5	1052.2	1052.0	1052.2	1052.5	1052.7	1053.0	1053.1
135°	1099.6	1099.4	1098.9	1098.4	1097.9	1097.4	1097.9	1098.4	1098.9	1099.4	1099.6
137.5°	1142.9	1142.5	1141.8	1141.1	1140.4	1139.7	1140.4	1141.1	1141.8	1142.5	1142.9
140°	1184.1	1183.5	1182.3	1181.2	1180.0	1178.8	1180.0	1181.2	1182.3	1183.5	1184.1
142.5°	1222.1	1221.5	1220.3	1219.2	1218.0	1216.8	1218.0	1219.2	1220.3	1221.5	1222.1
145°	1256.9	1256.3	1255.2	1254.0	1252.9	1251.7	1252.9	1254.0	1255.2	1256.3	1256.9
147.5°	1287.6	1287.1	1286.2	1285.2	1284.3	1283.3	1284.3	1285.2	1286.2	1287.1	1287.6
150°	1317.1	1316.5	1315.4	1314.2	1313.1	1311.9	1313.1	1314.2	1315.4	1316.5	1317.1
152.5°	1343.5	1342.7	1341.1	1339.4	1337.8	1336.2	1337.8	1339.4	1341.1	1342.7	1343.5
155°	1366.8	1365.9	1364.0	1362.1	1360.2	1358.3	1360.2	1362.1	1364.0	1365.9	1366.8
157.5°	1387.9	1387.0	1385.1	1383.2	1381.4	1379.5	1381.4	1383.2	1385.1	1387.0	1387.9
160°	1404.8	1404.0	1402.3	1400.7	1399.0	1397.4	1399.0	1400.7	1402.3	1404.0	1404.8
162.5°	1421.7	1420.6	1418.5	1416.4	1414.3	1412.2	1414.3	1416.4	1418.5	1420.6	1421.7
165°	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1428.6	1430.3	1431.9	1433.6	1434.4
167.5°	1446.0	1444.9	1442.8	1440.7	1438.6	1436.5	1438.6	1440.7	1442.8	1444.9	1446.0
170°	1454.5	1453.4	1451.3	1449.2	1447.0	1444.9	1447.0	1449.2	1451.3	1453.4	1454.5
172.5°	1460.8	1459.7	1457.6	1455.5	1453.4	1451.3	1453.4	1455.5	1457.6	1459.7	1460.8
175°	1465.0	1463.8	1461.5	1459.2	1456.8	1454.5	1456.8	1459.2	1461.5	1463.8	1465.0
177.5°	1466.1	1465.0	1462.9	1460.8	1458.7	1456.6	1458.7	1460.8	1462.9	1465.0	1466.1
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	602.6	604.8	603.9	599.1	603.9	605.2	607.9	610.5	612.3	614.9	617.1
5°	564.8	569.2	571.8	569.2	578.0	579.3	585.4	589.0	594.2	598.6	602.2
7.5°	529.2	532.7	538.0	538.9	544.1	550.3	559.1	567.9	576.2	580.6	584.6
10°	491.0	497.1	505.0	503.3	511.2	520.8	530.1	544.1	551.2	559.1	566.1
12.5°	452.7	456.7	467.2	470.7	482.2	489.6	502.4	511.2	528.7	538.0	544.1
15°	385.9	402.2	415.4	431.2	446.1	460.2	471.6	487.4	502.8	509.9	520.0
17.5°	355.6	363.0	371.0	378.9	398.2	423.3	443.5	460.6	473.8	483.0	494.9
20°	323.9	331.4	340.2	347.7	359.5	377.6	402.6	432.1	447.9	457.5	469.0
22.5°	301.5	308.5	314.3	320.9	330.1	343.3	362.2	398.6	419.7	431.6	441.7
25°	277.3	286.1	292.3	297.1	304.6	319.1	334.5	355.1	392.9	402.2	416.2
27.5°	260.6	263.3	270.3	277.8	285.3	293.2	309.0	326.6	352.1	372.3	389.4
30°	240.9	247.5	254.0	257.1	263.7	275.1	284.8	303.7	323.5	339.3	360.0
32.5°	225.9	229.9	234.3	241.7	247.9	255.8	265.5	281.3	298.0	308.1	323.9
35°	209.2	211.9	221.1	224.2	230.3	238.2	247.9	260.2	278.2	286.1	297.6
37.5°	193.4	199.5	202.2	209.2	214.9	222.8	229.9	243.9	255.8	265.0	275.6
40°	181.1	183.7	188.6	194.7	199.5	205.7	214.5	224.6	237.3	244.8	254.0
42.5°	166.1	168.3	174.5	178.0	185.9	191.6	196.9	209.2	220.6	226.4	235.6
45°	149.9	155.2	159.1	166.1	170.5	177.6	184.2	193.0	203.5	210.1	215.4
47.5°	135.8	141.1	145.0	151.6	158.7	161.7	168.8	178.0	187.7	193.0	200.4
50°	124.4	126.1	133.6	136.7	144.2	150.3	155.2	163.1	173.6	176.7	182.8
52.5°	113.4	114.7	119.6	123.5	130.1	135.4	141.5	149.0	157.8	162.6	167.5
55°	103.7	104.6	106.8	111.2	115.6	122.2	127.9	134.9	142.4	147.7	152.1
57.5°	92.7	94.5	96.3	98.9	103.3	109.4	115.6	122.2	128.3	131.9	137.6
60°	80.0	82.6	85.7	88.8	91.9	96.3	103.3	109.4	115.2	118.2	122.6
62.5°	66.4	71.6	74.3	77.8	80.4	84.4	89.7	96.7	100.7	104.6	108.1
65°	59.8	60.2	60.7	64.2	69.0	73.0	77.8	83.1	89.2	91.9	94.5
67.5°	53.2	53.6	54.5	54.9	56.7	61.1	66.4	72.1	76.9	78.7	81.3
70°	46.6	46.6	48.3	48.8	49.2	49.7	54.1	59.8	64.2	66.4	69.4
72.5°	39.6	40.0	40.9	41.3	42.2	43.1	44.4	47.5	52.7	54.9	58.5
75°	32.5	33.0	33.4	33.8	35.2	35.6	36.9	38.7	40.9	43.5	45.7
77.5°	25.9	25.9	26.4	27.3	28.1	28.6	29.9	30.8	31.6	33.0	34.7
80°	19.3	19.8	19.8	20.7	20.7	21.1	21.5	22.9	23.7	24.6	25.5
82.5°	13.2	14.1	14.1	14.1	14.5	14.9	15.4	15.4	16.3	16.7	18.0
85°	7.9	8.4	8.4	8.4	7.9	8.8	8.8	9.2	9.2	9.2	9.7
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	4.0	4.0
90°	25.8	24.6	23.5	22.3	21.1	19.2	17.4	15.5	13.6	12.7	11.4
92.5°	27.3	26.8	26.3	25.8	25.3	24.6	23.9	23.2	22.5	22.2	22.7
95°	45.9	44.7	43.6	42.4	41.2	39.6	37.9	36.3	34.6	33.8	37.7
97.5°	56.7	56.0	55.3	54.6	53.9	50.1	46.4	42.6	38.9	37.0	46.6
100°	67.8	65.9	64.0	62.1	60.2	56.2	52.2	48.2	44.2	42.2	58.3
102.5°	72.6	70.0	67.5	64.9	62.3	105.0	147.8	190.5	233.2	254.6	254.8
105°	74.7	72.1	69.6	67.0	64.4	128.5	192.6	256.7	320.8	352.8	349.3
107.5°	76.9	74.3	71.7	69.1	66.5	145.6	224.7	303.8	382.9	422.5	419.6
110°	90.9	114.4	137.9	161.3	184.8	252.6	320.5	388.3	456.2	490.1	487.6

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	131.9	233.1	334.2	435.4	536.6	540.6	544.6	548.5	552.5	554.5	552.4
115°	217.0	325.7	434.4	543.0	651.7	645.8	640.0	634.1	628.2	625.3	623.3
117.5°	574.5	608.0	641.6	675.1	708.7	704.7	700.7	696.8	692.8	690.8	688.5
120°	785.5	782.7	779.8	777.0	774.2	770.0	765.8	761.5	757.3	755.2	753.4
122.5°	842.2	840.8	839.3	837.9	836.5	831.8	827.1	822.4	817.7	815.4	813.5
125°	899.1	897.4	895.8	894.1	892.5	888.1	883.6	879.2	874.7	872.5	871.0
127.5°	953.6	951.3	949.0	946.6	944.3	940.8	937.2	933.7	930.2	928.4	926.8
130°	1004.2	1001.6	999.1	996.5	993.9	991.3	988.7	986.2	983.6	982.3	980.4
132.5°	1052.0	1049.9	1047.8	1045.7	1043.6	1041.0	1038.4	1035.9	1033.3	1032.0	1030.5
135°	1098.4	1096.1	1093.7	1091.4	1089.0	1086.9	1084.8	1082.7	1080.6	1079.5	1077.6
137.5°	1141.7	1139.4	1137.0	1134.7	1132.3	1129.9	1127.6	1125.2	1122.9	1121.7	1120.3
140°	1183.0	1180.9	1178.8	1176.6	1174.5	1171.9	1169.3	1166.8	1164.2	1162.9	1162.0
142.5°	1221.2	1219.3	1217.4	1215.5	1213.6	1210.6	1207.5	1204.5	1201.4	1199.9	1199.1
145°	1256.1	1254.4	1252.8	1251.1	1249.5	1245.5	1241.5	1237.6	1233.6	1231.6	1231.7
147.5°	1287.0	1285.8	1284.7	1283.5	1282.3	1278.3	1274.3	1270.3	1266.3	1264.3	1264.7
150°	1316.4	1315.0	1313.6	1312.2	1310.8	1307.0	1303.3	1299.5	1295.8	1293.9	1294.7
152.5°	1342.8	1341.4	1340.0	1338.6	1337.2	1333.7	1330.2	1326.7	1323.2	1321.4	1322.3
155°	1366.1	1364.7	1363.2	1361.8	1360.4	1357.6	1354.8	1352.0	1349.2	1347.8	1348.9
157.5°	1387.1	1385.4	1383.8	1382.1	1380.5	1378.4	1376.3	1374.2	1372.1	1371.0	1371.9
160°	1404.1	1402.7	1401.3	1399.9	1398.5	1397.1	1395.7	1394.2	1392.8	1392.1	1392.8
162.5°	1420.9	1419.2	1417.6	1415.9	1414.3	1413.1	1411.9	1410.8	1409.6	1409.0	1409.7
165°	1433.6	1431.9	1430.3	1428.6	1427.0	1426.3	1425.6	1424.9	1424.2	1423.8	1424.5
167.5°	1445.2	1443.5	1441.9	1440.2	1438.6	1437.9	1437.2	1436.5	1435.8	1435.4	1436.1
170°	1453.7	1452.0	1450.4	1448.7	1447.1	1446.6	1446.1	1445.6	1445.1	1444.9	1445.6
172.5°	1460.0	1458.3	1456.7	1455.0	1453.4	1452.9	1452.5	1452.0	1451.5	1451.3	1452.0
175°	1464.2	1462.5	1460.9	1459.2	1457.6	1457.1	1456.7	1456.2	1455.7	1455.5	1456.3
177.5°	1465.3	1463.6	1462.0	1460.3	1458.7	1458.5	1458.2	1458.0	1457.7	1457.6	1458.4
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	632.5	632.5	632.5	632.5
2.5°	621.1	619.7	627.6	636.4
5°	608.3	610.5	620.6	632.9
7.5°	595.1	600.0	611.8	628.1
10°	576.7	585.4	603.5	620.2
12.5°	558.6	570.5	587.6	607.4
15°	538.4	551.6	572.7	596.4
17.5°	516.0	530.9	555.6	581.5
20°	492.3	512.0	538.0	566.1
22.5°	465.9	489.6	516.4	547.6
25°	440.4	466.3	493.1	529.2
27.5°	415.4	440.8	470.7	507.2
30°	390.3	413.6	445.7	484.8
32.5°	363.5	387.7	421.5	461.5
35°	338.9	363.0	394.7	434.3
37.5°	312.5	338.4	368.8	409.6
40°	281.7	312.1	341.5	380.6
42.5°	256.2	288.3	316.9	353.8
45°	236.0	266.4	290.1	326.1
47.5°	217.1	241.7	265.9	299.3
50°	199.1	218.0	243.1	272.9
52.5°	180.6	196.9	218.4	246.6
55°	163.9	179.3	198.7	220.2
57.5°	148.6	159.5	178.9	198.2
60°	131.4	142.8	157.8	174.1
62.5°	116.9	125.7	139.8	153.4
65°	101.5	109.9	120.4	133.2
67.5°	87.5	94.9	103.3	113.4
70°	74.7	80.4	86.6	95.4
72.5°	61.1	67.2	73.0	80.0
75°	50.1	52.7	57.6	62.4
77.5°	38.7	42.2	44.8	48.8
80°	27.7	30.8	31.6	34.7
82.5°	18.5	20.2	22.0	22.9
85°	10.5	11.4	13.2	13.6
87.5°	4.0	4.4	5.3	6.2
90°	8.8	6.3	3.7	1.1
92.5°	23.6	24.5	25.5	26.4
95°	45.4	53.2	60.9	68.7
97.5°	65.9	85.1	104.4	123.6
100°	90.5	122.6	154.8	187.0
102.5°	255.3	255.8	256.2	256.7
105°	342.2	335.2	328.1	321.1
107.5°	413.7	407.8	402.0	396.1
110°	482.7	477.8	472.8	467.9

TEST NUMBER: P1008347

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	548.2	543.9	539.7	535.5
115°	619.3	615.3	611.3	607.3
117.5°	683.8	679.1	674.4	669.7
120°	749.9	746.4	742.9	739.4
122.5°	809.8	806.0	802.3	798.5
125°	867.9	864.8	861.8	858.7
127.5°	923.5	920.2	917.0	913.7
130°	976.7	972.9	969.2	965.4
132.5°	1027.4	1024.3	1021.3	1018.2
135°	1073.9	1070.1	1066.4	1062.6
137.5°	1117.5	1114.7	1111.9	1109.1
140°	1160.1	1158.2	1156.4	1154.5
142.5°	1197.4	1195.8	1194.1	1192.5
145°	1231.9	1232.2	1232.4	1232.6
147.5°	1265.4	1266.1	1266.8	1267.5
150°	1296.4	1298.0	1299.7	1301.3
152.5°	1324.2	1326.1	1327.9	1329.8
155°	1351.0	1353.1	1355.2	1357.3
157.5°	1373.8	1375.7	1377.6	1379.5
160°	1394.2	1395.7	1397.1	1398.5
162.5°	1411.1	1412.6	1414.0	1415.4
165°	1425.9	1427.4	1428.8	1430.2
167.5°	1437.5	1439.0	1440.4	1441.8
170°	1447.0	1448.5	1449.9	1451.3
172.5°	1453.4	1454.8	1456.2	1457.6
175°	1458.0	1459.6	1461.3	1462.9
177.5°	1460.1	1461.7	1463.4	1465.0
180°	1459.7	1459.7	1459.7	1459.7

(END OF REPORT)