

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008348

Luminaire Tested: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008348
REPORT IS A COMBINATION OF REPORTS P988028 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5198.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	29	29	29
1	91	87	84	81	81	77	75	72	59	57	55	42	41	40	26	25	25	25	25	18
2	83	77	71	66	74	68	63	59	52	49	46	37	35	34	23	22	21	21	21	15
3	76	68	61	56	67	60	55	50	46	42	39	33	31	29	21	20	19	19	19	13
4	70	60	53	47	62	53	47	43	41	37	34	30	27	25	19	18	16	16	16	12
5	64	53	46	40	57	48	41	37	37	32	29	27	24	22	17	16	14	14	14	11
6	59	48	40	35	52	43	36	32	33	29	25	24	21	19	16	14	13	13	13	10
7	55	43	36	31	48	39	32	28	30	26	22	22	19	17	14	13	12	12	12	9
8	51	39	32	27	45	35	29	25	27	23	20	20	17	15	13	12	10	10	10	8
9	47	36	29	24	42	32	26	22	25	21	18	18	16	14	12	11	10	10	10	7
10	44	33	26	21	39	29	23	19	23	19	16	17	14	12	11	10	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9681	9681	9681	9681
5°	9705	10284	9738	8215
10°	9597	10870	9666	6785
15°	9390	10874	9549	5096
20°	9140	8988	9338	4205
25°	8836	5615	9026	3577
30°	8447	3595	8677	3080
35°	7975	2763	8235	2635
40°	7450	2323	7768	2305
45°	6888	1978	7177	1935
50°	6313	1679	6607	1674
55°	5673	1459	5979	1441
60°	5107	1113	5377	1099
65°	4579	838	4849	951
70°	3993	669	4309	775
75°	3379	513	3686	586
80°	2683	349	2882	385
85°	1865	181	2048	190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 8856 cd/sqm

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	1.1
10°-20°	161.9	3.1
20°-30°	208.4	4.0
30°-40°	197.7	3.8
40°-50°	169.5	3.3
50°-60°	129.0	2.5
60°-70°	81.4	1.6
70°-80°	40.6	0.8
80°-90°	12.9	0.2
90°-100°	46.6	0.9
100°-110°	173.5	3.3
110°-120°	460.2	8.9
120°-130°	763.3	14.7
130°-140°	810.8	15.6
140°-150°	753.6	14.5
150°-160°	605.8	11.7
160°-170°	390.4	7.5
170°-180°	134.4	2.6
0°-30°	428.4	8.2
0°-40°	626.1	12.0
0°-60°	924.6	17.8
0°-90°	1059.5	20.4
90°-120°	680.3	13.1
90°-150°	3007.9	57.9
90°-180°	4139.0	79.6
0°-180°	5198.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	612	612	612	612	612	
5°	612	680	614	544	612	58
15°	577	768	587	360	577	162
25°	512	410	523	261	512	235
35°	420	202	434	192	420	263
45°	315	140	329	137	315	243
55°	213	97	224	96	213	192
65°	129	51	136	57	129	128
75°	60	27	66	31	60	65
85°	13	8	14	8	13	15
90°	1	28	1	28	1	5
95°	66	44	66	44	66	79
105°	310	78	310	78	310	332
115°	587	84	587	84	587	578
125°	830	873	830	873	830	741
135°	1028	1061	1028	1061	1028	794
145°	1192	1210	1192	1210	1192	746
155°	1313	1314	1313	1314	1313	605
165°	1383	1380	1383	1380	1383	391
175°	1415	1407	1415	1407	1415	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	615.5	618.0	619.3	621.0	624.8	627.4	631.2	632.0	631.6	633.3	628.6
5°	612.1	617.6	622.7	626.9	633.7	638.0	642.7	648.2	649.5	655.9	652.0
7.5°	607.4	615.5	622.7	631.2	641.4	646.9	654.2	662.7	666.5	674.1	676.3
10°	599.7	611.2	623.5	632.5	646.5	656.3	663.1	676.7	685.6	697.1	695.4
12.5°	587.4	602.3	618.9	633.7	652.0	658.4	671.2	685.2	696.7	707.3	716.6
15°	576.8	593.8	612.1	630.3	651.2	663.1	675.8	694.1	706.4	725.1	733.2
17.5°	562.3	584.0	605.7	626.1	650.8	664.4	680.1	697.9	716.2	734.1	740.4
20°	547.5	570.8	594.2	621.8	649.9	663.1	679.2	701.3	719.2	733.2	733.2
22.5°	529.6	558.1	584.9	611.2	641.8	661.0	677.5	703.5	716.2	719.2	707.7
25°	511.8	540.2	569.6	602.3	637.1	654.2	672.9	697.1	701.3	689.4	659.7
27.5°	490.5	522.4	555.5	590.8	627.4	648.6	665.6	681.8	673.7	641.8	595.5
30°	468.8	503.3	540.7	574.2	618.4	638.0	652.5	657.1	631.6	579.8	519.8
32.5°	446.3	479.9	519.4	559.8	604.4	623.1	632.5	620.1	573.4	507.9	434.8
35°	419.9	457.8	499.0	541.1	585.3	599.3	604.8	574.7	514.7	430.1	357.5
37.5°	396.1	434.0	478.2	521.1	564.0	571.7	566.2	519.0	442.9	359.2	288.2
40°	368.1	408.5	451.8	499.9	535.1	537.3	523.7	462.5	368.1	289.5	245.7
42.5°	342.2	383.0	426.3	475.2	502.0	494.8	476.5	396.1	307.3	249.5	214.2
45°	315.4	354.1	400.8	444.2	463.3	446.3	418.7	333.2	258.0	214.6	187.4
47.5°	289.5	325.6	371.9	413.6	417.0	397.8	365.1	279.3	223.6	188.7	166.6
50°	264.0	300.1	343.4	377.9	374.5	348.1	311.1	242.7	194.2	166.6	148.3
52.5°	238.5	271.2	313.3	340.5	326.0	300.5	264.0	205.7	169.6	145.4	131.3
55°	212.9	243.6	279.7	302.2	279.3	249.9	224.0	176.4	147.1	127.5	116.9
57.5°	191.7	215.9	249.1	262.7	235.1	212.1	189.6	151.7	127.5	113.5	101.2
60°	168.3	190.4	217.6	225.7	197.2	178.5	159.4	128.4	109.2	96.9	88.8
62.5°	148.3	166.6	187.4	187.4	162.4	148.3	133.9	107.5	91.8	82.0	78.2
65°	128.8	142.0	156.8	155.1	133.9	121.6	110.1	88.8	76.9	70.1	66.3
67.5°	109.7	119.9	129.6	123.7	108.4	97.8	87.1	71.8	63.8	59.1	54.0
70°	92.2	100.3	105.4	99.9	84.6	75.7	68.0	57.8	51.4	45.5	42.5
72.5°	77.4	80.8	82.5	75.7	62.9	57.8	52.3	45.1	39.5	36.6	35.7
75°	60.4	63.3	62.1	57.0	46.3	42.5	38.3	33.2	31.9	30.2	29.3
77.5°	47.2	47.2	45.1	40.4	33.2	30.2	28.5	25.9	24.7	24.2	23.4
80°	33.6	33.2	31.9	26.8	22.5	20.8	20.8	19.1	18.7	17.9	17.9
82.5°	22.1	22.1	20.4	16.2	14.9	14.5	14.0	13.2	13.2	12.8	12.8
85°	13.2	12.3	10.2	8.9	8.5	8.5	8.1	7.7	8.1	7.7	7.7
87.5°	6.0	4.7	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
90°	1.0	3.5	6.0	8.5	11.0	12.3	13.2	15.0	16.8	18.6	20.4
92.5°	25.5	24.6	23.7	22.8	21.9	21.5	21.8	22.5	23.2	23.8	24.5
95°	66.4	58.9	51.4	43.9	36.4	32.7	33.5	35.1	36.6	38.2	39.8
97.5°	119.5	100.9	82.3	63.7	45.1	35.8	37.6	41.2	44.9	48.5	52.1
100°	180.8	149.7	118.6	87.5	56.4	40.9	42.8	46.7	50.5	54.4	58.2
102.5°	248.2	247.8	247.3	246.9	246.4	246.2	225.5	184.2	142.9	101.6	60.3
105°	310.5	317.3	324.1	331.0	337.8	341.2	310.2	248.2	186.3	124.3	62.3
107.5°	383.1	388.8	394.4	400.1	405.8	408.6	370.4	293.9	217.4	140.9	64.4
110°	452.5	457.3	462.1	466.8	471.6	474.0	441.2	375.6	310.0	244.4	178.8

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	517.9	522.0	526.1	530.2	534.3	536.3	534.4	530.5	526.6	522.8	518.9
115°	587.3	591.2	595.0	598.9	602.8	604.7	607.5	613.2	618.9	624.5	630.2
117.5°	647.6	652.1	656.7	661.2	665.7	668.0	669.9	673.8	677.7	681.5	685.4
120°	715.0	718.4	721.8	725.2	728.6	730.3	732.3	736.4	740.5	744.6	748.7
122.5°	772.2	775.8	779.5	783.1	786.8	788.6	790.9	795.4	799.9	804.5	809.0
125°	830.5	833.4	836.4	839.3	842.2	843.7	845.9	850.2	854.5	858.8	863.1
127.5°	883.6	886.8	890.0	893.1	896.3	897.9	899.6	903.0	906.4	909.8	913.2
130°	933.6	937.2	940.9	944.5	948.2	950.0	951.2	953.7	956.2	958.7	961.2
132.5°	984.7	987.7	990.6	993.6	996.5	998.0	999.2	1001.7	1004.2	1006.7	1009.2
135°	1027.6	1031.2	1034.8	1038.5	1042.1	1043.9	1044.9	1047.0	1049.0	1051.1	1053.1
137.5°	1072.5	1075.2	1078.0	1080.7	1083.4	1084.8	1085.9	1088.2	1090.5	1092.7	1095.0
140°	1116.5	1118.3	1120.1	1121.9	1123.7	1124.6	1125.9	1128.4	1130.9	1133.4	1135.9
142.5°	1153.2	1154.8	1156.4	1158.0	1159.6	1160.4	1161.9	1164.8	1167.8	1170.7	1173.7
145°	1192.1	1191.9	1191.6	1191.4	1191.1	1191.0	1192.9	1196.8	1200.7	1204.5	1208.4
147.5°	1225.8	1225.1	1224.4	1223.7	1223.0	1222.7	1224.6	1228.5	1232.4	1236.2	1240.1
150°	1258.4	1256.8	1255.2	1253.7	1252.1	1251.3	1253.1	1256.7	1260.4	1264.0	1267.6
152.5°	1286.0	1284.2	1282.4	1280.6	1278.8	1277.9	1279.6	1283.0	1286.4	1289.8	1293.2
155°	1312.6	1310.6	1308.5	1306.5	1304.4	1303.4	1304.8	1307.5	1310.2	1313.0	1315.7
157.5°	1334.0	1332.2	1330.4	1328.6	1326.8	1325.9	1326.9	1329.0	1331.0	1333.1	1335.1
160°	1352.4	1351.0	1349.7	1348.3	1347.0	1346.3	1347.0	1348.3	1349.7	1351.0	1352.4
162.5°	1368.8	1367.4	1366.0	1364.7	1363.3	1362.6	1363.2	1364.3	1365.4	1366.6	1367.7
165°	1383.1	1381.7	1380.3	1379.0	1377.6	1376.9	1377.2	1377.9	1378.6	1379.3	1380.0
167.5°	1394.3	1392.9	1391.6	1390.2	1388.9	1388.2	1388.5	1389.2	1389.9	1390.5	1391.2
170°	1403.5	1402.1	1400.8	1399.4	1398.1	1397.4	1397.6	1398.1	1398.5	1399.0	1399.4
172.5°	1409.6	1408.2	1406.9	1405.5	1404.2	1403.5	1403.7	1404.2	1404.6	1405.1	1405.5
175°	1414.7	1413.1	1411.5	1410.0	1408.4	1407.6	1407.8	1408.3	1408.7	1409.2	1409.6
177.5°	1416.8	1415.2	1413.6	1412.0	1410.4	1409.6	1409.7	1409.9	1410.2	1410.4	1410.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	633.3	634.2	635.4	641.4	642.2	643.9	643.1	643.1	643.5	642.7	643.1
5°	660.5	661.8	668.2	675.4	677.1	675.4	677.5	680.5	680.5	680.5	679.7
7.5°	686.0	690.7	697.9	708.6	710.7	712.8	716.6	714.1	714.9	718.8	717.5
10°	710.7	717.5	725.6	734.5	739.2	742.1	743.8	747.7	756.6	746.4	750.2
12.5°	734.1	743.8	752.3	762.1	765.5	769.3	770.6	774.0	774.0	773.6	776.6
15°	749.4	758.3	765.9	772.3	773.2	772.3	771.5	771.9	773.2	768.1	771.0
17.5°	752.8	753.6	756.2	753.6	754.0	745.1	740.0	738.7	726.8	727.3	737.0
20°	736.2	721.7	717.9	703.9	695.4	672.4	671.6	665.2	640.1	647.8	646.1
22.5°	690.7	666.1	633.3	617.2	609.1	584.9	566.2	553.0	544.1	535.1	531.3
25°	630.8	590.8	544.5	512.6	507.9	485.4	451.0	434.8	415.7	409.7	419.9
27.5°	553.4	501.6	449.3	400.4	391.5	371.1	353.6	342.2	320.1	318.8	319.6
30°	448.4	396.1	352.4	320.5	298.4	289.0	277.6	269.1	260.1	263.5	264.4
32.5°	368.5	318.8	278.0	261.0	250.8	244.8	235.1	229.5	225.7	224.4	224.0
35°	292.9	259.7	241.4	224.9	218.9	214.6	207.4	204.9	201.5	201.9	201.9
37.5°	250.8	223.2	209.5	201.0	195.5	193.4	188.7	186.2	184.0	183.2	184.5
40°	216.4	197.2	188.7	181.1	176.4	175.5	173.0	170.0	167.5	167.9	169.2
42.5°	191.3	180.2	170.0	164.1	160.7	159.4	157.3	155.1	155.1	153.9	153.4
45°	171.3	162.4	153.9	148.3	146.2	144.5	142.0	141.5	139.8	140.3	140.7
47.5°	153.4	146.2	139.8	134.3	132.2	131.8	129.2	127.5	127.5	127.1	126.7
50°	137.3	130.1	124.5	121.6	118.6	117.7	117.3	116.9	116.0	116.0	116.5
52.5°	124.1	116.9	112.6	110.1	108.4	107.5	107.5	107.1	107.1	107.1	106.7
55°	109.7	103.7	100.3	99.5	98.6	98.2	97.8	96.9	96.5	97.3	96.5
57.5°	96.1	93.9	91.0	90.1	88.0	88.0	86.7	85.9	85.0	85.9	85.9
60°	85.4	82.5	80.8	78.2	76.5	74.8	72.7	72.3	71.4	71.0	70.6
62.5°	74.4	71.8	67.6	63.8	61.2	59.5	58.7	58.2	58.2	57.8	57.8
65°	62.1	56.1	54.0	52.7	52.3	51.9	51.0	50.6	51.0	50.6	51.0
67.5°	48.5	47.6	46.3	45.5	45.1	44.6	44.6	44.2	44.2	44.2	44.2
70°	42.1	40.0	39.5	38.7	38.7	38.3	38.3	38.3	38.3	37.8	38.7
72.5°	34.9	33.6	33.2	32.7	32.7	32.7	32.3	32.3	32.3	31.9	32.3
75°	28.5	28.1	27.2	27.2	26.8	27.2	26.8	26.8	26.4	26.8	26.8
77.5°	23.0	22.5	22.1	22.1	21.7	21.7	21.7	21.7	21.7	21.7	22.1
80°	17.4	17.0	16.6	17.0	16.6	17.0	16.6	16.6	17.0	16.6	16.6
82.5°	12.8	12.3	12.3	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
85°	7.7	7.2	7.2	7.7	7.2	7.7	7.2	7.2	7.2	7.7	7.7
87.5°	3.4	3.8	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.8
90°	21.5	22.7	23.8	24.9	25.5	25.7	26.2	26.7	27.1	27.6	27.1
92.5°	25.0	25.4	25.9	26.4	26.6	26.7	26.9	27.2	27.4	27.6	27.4
95°	40.9	42.1	43.2	44.3	44.9	44.8	44.6	44.3	44.1	43.9	44.1
97.5°	52.8	53.5	54.2	54.9	55.2	55.3	55.5	55.8	56.0	56.2	56.0
100°	60.0	61.8	63.7	65.5	66.4	66.6	67.1	67.5	68.0	68.4	68.0
102.5°	62.8	65.3	67.8	70.3	71.5	71.8	72.5	73.2	73.9	74.6	73.9
105°	64.8	67.3	69.8	72.3	73.5	74.0	74.9	75.8	76.7	77.6	76.7
107.5°	66.9	69.4	71.9	74.4	75.6	76.1	77.0	77.9	78.8	79.7	78.8
110°	156.1	133.4	110.7	88.0	76.6	77.1	78.0	78.9	79.8	80.7	79.8

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	421.1	323.3	225.4	127.6	78.7	79.0	79.7	80.4	81.0	81.7	81.0
115°	525.1	420.0	314.9	209.8	157.3	149.1	132.8	116.5	100.1	83.8	100.1
117.5°	652.9	620.5	588.0	555.5	539.3	509.6	450.1	390.6	331.2	271.7	331.2
120°	751.4	754.2	756.9	759.6	761.0	745.7	715.0	684.4	653.7	623.1	653.7
122.5°	810.4	811.7	813.1	814.4	815.1	815.2	815.5	815.7	816.0	816.2	816.0
125°	864.7	866.3	867.9	869.5	870.3	870.6	871.3	872.0	872.7	873.4	872.7
127.5°	915.5	917.7	920.0	922.3	923.4	923.5	923.7	924.0	924.2	924.4	924.2
130°	963.7	966.2	968.7	971.2	972.4	972.3	972.1	971.8	971.6	971.4	971.6
132.5°	1011.2	1013.3	1015.3	1017.4	1018.4	1018.3	1018.1	1017.8	1017.6	1017.4	1017.6
135°	1055.4	1057.6	1059.9	1062.2	1063.3	1063.1	1062.6	1062.2	1061.7	1061.3	1061.7
137.5°	1097.3	1099.5	1101.8	1104.1	1105.2	1104.9	1104.2	1103.5	1102.9	1102.2	1102.9
140°	1137.9	1140.0	1142.0	1144.1	1145.1	1144.5	1143.4	1142.3	1141.1	1140.0	1141.1
142.5°	1175.5	1177.3	1179.1	1180.9	1181.8	1181.2	1180.1	1179.0	1177.8	1176.7	1177.8
145°	1210.0	1211.6	1213.1	1214.7	1215.5	1214.9	1213.8	1212.7	1211.5	1210.4	1211.5
147.5°	1241.2	1242.4	1243.5	1244.6	1245.2	1244.7	1243.8	1242.9	1242.0	1241.1	1242.0
150°	1269.0	1270.4	1271.7	1273.1	1273.8	1273.2	1272.1	1271.0	1269.8	1268.7	1269.8
152.5°	1294.6	1295.9	1297.3	1298.6	1299.3	1298.5	1296.9	1295.4	1293.8	1292.2	1293.8
155°	1317.1	1318.4	1319.8	1321.1	1321.8	1320.9	1319.1	1317.2	1315.4	1313.6	1315.4
157.5°	1336.7	1338.3	1339.8	1341.4	1342.2	1341.3	1339.5	1337.6	1335.8	1334.0	1335.8
160°	1353.8	1355.2	1356.5	1357.9	1358.6	1357.8	1356.2	1354.6	1353.0	1351.4	1353.0
162.5°	1369.3	1370.9	1372.5	1374.1	1374.9	1373.9	1371.8	1369.8	1367.7	1365.7	1367.7
165°	1381.6	1383.2	1384.8	1386.4	1387.2	1386.4	1384.8	1383.2	1381.6	1380.0	1381.6
167.5°	1392.8	1394.4	1396.0	1397.6	1398.4	1397.4	1395.3	1393.3	1391.2	1389.2	1391.2
170°	1401.0	1402.6	1404.2	1405.8	1406.6	1405.6	1403.5	1401.5	1399.4	1397.4	1399.4
172.5°	1407.1	1408.7	1410.3	1411.9	1412.7	1411.7	1409.6	1407.6	1405.5	1403.5	1405.5
175°	1411.2	1412.8	1414.4	1416.0	1416.8	1415.7	1413.4	1411.1	1408.9	1406.6	1408.9
177.5°	1412.2	1413.8	1415.4	1417.0	1417.8	1416.8	1414.7	1412.7	1410.6	1408.6	1410.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	644.8	641.8	641.0	641.8	641.0	641.4	638.4	627.4	630.3	625.7	628.2
5°	681.4	678.8	673.3	672.4	671.6	670.7	666.5	656.7	652.9	646.5	646.1
7.5°	716.2	716.2	712.0	709.0	705.2	702.2	696.7	682.2	676.3	668.6	664.4
10°	750.6	739.6	744.3	741.3	731.9	730.2	720.0	711.5	700.1	692.4	685.6
12.5°	775.3	771.9	767.6	765.1	762.5	757.0	750.2	728.5	722.6	707.3	699.6
15°	774.4	772.3	773.6	773.6	772.7	771.5	765.9	750.2	740.0	725.1	712.0
17.5°	732.8	738.3	743.8	747.7	756.2	760.0	765.1	755.7	749.4	736.6	722.6
20°	660.1	673.7	689.9	693.3	700.9	723.4	733.6	741.7	744.3	740.0	728.5
22.5°	558.9	570.4	609.5	608.7	619.7	646.5	676.3	700.5	719.6	730.2	726.0
25°	437.8	454.0	474.8	490.5	526.6	566.6	603.6	642.2	675.4	704.7	712.0
27.5°	331.1	352.4	368.9	389.8	408.0	455.2	502.8	563.2	601.9	657.6	686.5
30°	267.8	277.6	294.1	303.9	312.8	349.0	402.9	462.5	530.5	594.6	644.4
32.5°	228.7	235.5	247.8	252.1	261.4	285.6	319.6	374.0	444.2	522.0	587.4
35°	205.3	212.5	215.1	218.9	226.6	241.9	265.2	304.8	368.1	444.2	522.4
37.5°	185.3	189.1	196.4	198.9	201.5	212.9	228.7	256.3	298.4	360.9	447.6
40°	171.3	173.4	177.2	179.4	181.1	189.1	203.2	221.9	252.9	300.5	380.4
42.5°	156.4	159.0	161.5	164.1	166.2	172.6	181.1	198.9	219.8	255.9	313.7
45°	142.0	143.7	146.6	148.3	151.3	156.4	164.1	176.4	195.1	218.1	264.8
47.5°	128.8	130.9	132.2	134.3	136.4	142.0	149.2	157.3	172.6	195.1	229.1
50°	116.9	119.4	121.1	121.6	123.3	128.4	134.3	143.2	153.0	170.4	200.2
52.5°	108.4	108.8	110.1	111.8	111.4	114.3	119.9	126.7	136.9	150.9	172.6
55°	98.6	99.9	100.7	101.2	101.2	103.7	106.7	113.1	121.1	132.6	150.9
57.5°	86.3	87.6	90.1	91.0	92.2	93.5	94.8	99.0	105.8	116.9	131.8
60°	73.5	74.4	76.9	78.6	79.5	82.9	84.6	88.0	91.8	99.9	113.9
62.5°	59.1	59.9	61.2	62.9	64.6	69.7	74.0	77.4	80.3	85.9	97.3
65°	51.4	51.9	52.7	53.1	53.6	55.7	59.5	64.2	69.7	74.0	80.8
67.5°	44.6	45.1	45.5	46.3	46.8	47.2	48.9	50.2	55.7	61.6	66.7
70°	38.3	39.1	39.5	39.5	40.0	40.8	41.7	43.4	45.1	48.0	54.4
72.5°	32.3	32.7	33.6	33.6	33.6	34.4	35.3	36.1	37.0	38.7	41.2
75°	26.8	27.6	27.6	27.6	28.1	28.1	28.9	29.8	30.6	31.9	32.7
77.5°	22.1	22.1	22.1	22.1	22.5	22.5	23.0	23.8	24.2	24.7	25.5
80°	16.6	17.0	17.0	17.0	17.4	17.4	17.4	18.3	18.7	18.7	19.6
82.5°	12.3	12.3	12.3	12.8	12.3	12.8	12.8	13.2	12.8	13.2	13.6
85°	7.7	7.7	7.7	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.5
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	4.3	3.8	3.8
90°	26.7	26.2	25.7	25.5	24.9	23.8	22.7	21.5	20.4	18.6	16.8
92.5°	27.2	26.9	26.7	26.6	26.4	25.9	25.4	25.0	24.5	23.8	23.2
95°	44.3	44.6	44.8	44.9	44.3	43.2	42.1	40.9	39.8	38.2	36.6
97.5°	55.8	55.5	55.3	55.2	54.9	54.2	53.5	52.8	52.1	48.5	44.9
100°	67.5	67.1	66.6	66.4	65.5	63.7	61.8	60.0	58.2	54.4	50.5
102.5°	73.2	72.5	71.8	71.5	70.3	67.8	65.3	62.8	60.3	101.6	142.9
105°	75.8	74.9	74.0	73.5	72.3	69.8	67.3	64.8	62.3	124.3	186.3
107.5°	77.9	77.0	76.1	75.6	74.4	71.9	69.4	66.9	64.4	140.9	217.4
110°	78.9	78.0	77.1	76.6	88.0	110.7	133.4	156.1	178.8	244.4	310.0

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	80.4	79.7	79.0	78.7	127.6	225.4	323.3	421.1	518.9	522.8	526.6
115°	116.5	132.8	149.1	157.3	209.8	314.9	420.0	525.1	630.2	624.5	618.9
117.5°	390.6	450.1	509.6	539.3	555.5	588.0	620.5	652.9	685.4	681.5	677.7
120°	684.4	715.0	745.7	761.0	759.6	756.9	754.2	751.4	748.7	744.6	740.5
122.5°	815.7	815.5	815.2	815.1	814.4	813.1	811.7	810.4	809.0	804.5	799.9
125°	872.0	871.3	870.6	870.3	869.5	867.9	866.3	864.7	863.1	858.8	854.5
127.5°	924.0	923.7	923.5	923.4	922.3	920.0	917.7	915.5	913.2	909.8	906.4
130°	971.8	972.1	972.3	972.4	971.2	968.7	966.2	963.7	961.2	958.7	956.2
132.5°	1017.8	1018.1	1018.3	1018.4	1017.4	1015.3	1013.3	1011.2	1009.2	1006.7	1004.2
135°	1062.2	1062.6	1063.1	1063.3	1062.2	1059.9	1057.6	1055.4	1053.1	1051.1	1049.0
137.5°	1103.5	1104.2	1104.9	1105.2	1104.1	1101.8	1099.5	1097.3	1095.0	1092.7	1090.5
140°	1142.3	1143.4	1144.5	1145.1	1144.1	1142.0	1140.0	1137.9	1135.9	1133.4	1130.9
142.5°	1179.0	1180.1	1181.2	1181.8	1180.9	1179.1	1177.3	1175.5	1173.7	1170.7	1167.8
145°	1212.7	1213.8	1214.9	1215.5	1214.7	1213.1	1211.6	1210.0	1208.4	1204.5	1200.7
147.5°	1242.9	1243.8	1244.7	1245.2	1244.6	1243.5	1242.4	1241.2	1240.1	1236.2	1232.4
150°	1271.0	1272.1	1273.2	1273.8	1273.1	1271.7	1270.4	1269.0	1267.6	1264.0	1260.4
152.5°	1295.4	1296.9	1298.5	1299.3	1298.6	1297.3	1295.9	1294.6	1293.2	1289.8	1286.4
155°	1317.2	1319.1	1320.9	1321.8	1321.1	1319.8	1318.4	1317.1	1315.7	1313.0	1310.2
157.5°	1337.6	1339.5	1341.3	1342.2	1341.4	1339.8	1338.3	1336.7	1335.1	1333.1	1331.0
160°	1354.6	1356.2	1357.8	1358.6	1357.9	1356.5	1355.2	1353.8	1352.4	1351.0	1349.7
162.5°	1369.8	1371.8	1373.9	1374.9	1374.1	1372.5	1370.9	1369.3	1367.7	1366.6	1365.4
165°	1383.2	1384.8	1386.4	1387.2	1386.4	1384.8	1383.2	1381.6	1380.0	1379.3	1378.6
167.5°	1393.3	1395.3	1397.4	1398.4	1397.6	1396.0	1394.4	1392.8	1391.2	1390.5	1389.9
170°	1401.5	1403.5	1405.6	1406.6	1405.8	1404.2	1402.6	1401.0	1399.4	1399.0	1398.5
172.5°	1407.6	1409.6	1411.7	1412.7	1411.9	1410.3	1408.7	1407.1	1405.5	1405.1	1404.6
175°	1411.1	1413.4	1415.7	1416.8	1416.0	1414.4	1412.8	1411.2	1409.6	1409.2	1408.7
177.5°	1412.7	1414.7	1416.8	1417.8	1417.0	1415.4	1413.8	1412.2	1410.6	1410.4	1410.2
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	624.4	622.3	622.3	621.0	621.0	614.2	614.2	616.3	613.8	610.8	606.5
5°	640.5	635.9	634.6	632.9	627.4	618.9	615.5	614.2	609.1	602.7	595.5
7.5°	655.9	648.2	644.4	640.5	633.3	621.4	614.6	609.9	602.3	592.5	583.2
10°	670.7	661.0	651.2	646.5	636.3	621.4	611.6	604.0	592.9	579.8	566.6
12.5°	684.3	663.9	662.2	652.9	638.0	621.0	606.1	595.1	581.0	565.7	550.4
15°	696.2	675.4	665.2	656.7	637.1	615.9	600.2	586.6	567.9	550.4	531.7
17.5°	702.2	679.7	672.9	658.8	638.8	611.2	590.0	573.4	553.0	532.2	510.9
20°	708.1	681.8	670.7	661.0	633.7	602.3	578.5	559.4	536.8	512.2	488.8
22.5°	711.1	681.8	668.6	655.0	628.6	592.5	564.5	541.9	515.6	490.5	462.5
25°	706.0	679.2	663.5	649.5	619.7	580.6	548.3	522.8	494.8	466.3	437.8
27.5°	693.3	673.3	655.0	640.5	607.4	565.3	531.3	502.4	473.5	441.6	412.7
30°	669.5	660.5	646.1	629.9	593.8	551.7	511.3	481.6	449.7	417.8	387.6
32.5°	632.5	640.1	630.8	616.7	577.6	533.0	490.1	459.9	425.0	390.6	363.0
35°	587.4	614.6	609.5	599.7	560.6	513.0	470.1	433.6	398.7	363.8	336.2
37.5°	538.1	579.3	583.6	577.6	541.1	492.6	445.5	409.7	374.0	338.8	310.7
40°	470.5	533.9	547.5	550.0	520.7	468.0	418.7	383.8	348.5	314.1	280.1
42.5°	408.5	488.4	505.4	516.0	494.8	443.8	394.0	355.3	320.5	289.5	255.5
45°	350.2	433.6	461.2	474.8	465.4	416.1	364.7	328.6	296.7	268.2	235.5
47.5°	290.3	374.0	412.7	434.4	434.4	388.1	336.6	300.9	270.3	246.1	217.2
50°	250.4	320.1	360.0	388.5	396.1	359.6	311.1	276.3	247.4	221.0	198.9
52.5°	213.4	275.9	309.0	338.8	360.9	329.0	282.7	251.2	222.7	198.1	180.6
55°	184.5	231.2	261.4	294.1	318.8	298.0	255.0	224.4	199.8	179.4	164.5
57.5°	156.8	197.6	222.3	251.2	277.6	261.8	227.4	201.0	179.4	161.5	148.3
60°	133.5	166.6	185.7	208.3	241.0	230.0	201.5	177.2	159.8	143.7	132.6
62.5°	113.5	139.8	156.0	172.1	201.9	196.8	174.7	156.0	141.1	127.5	118.2
65°	93.1	114.8	127.5	141.5	165.3	167.5	149.6	136.4	122.8	110.9	102.4
67.5°	75.2	92.2	103.7	115.6	134.7	140.7	128.4	117.3	105.8	96.1	88.4
70°	60.8	72.7	81.2	90.5	106.3	113.5	107.1	99.5	90.1	82.0	75.2
72.5°	48.0	55.7	60.8	68.0	80.8	88.0	87.6	80.8	74.0	68.4	62.9
75°	35.3	41.2	45.5	50.2	60.4	67.2	68.9	65.9	59.1	54.8	50.6
77.5°	26.8	30.2	32.3	35.7	42.9	48.9	51.4	50.6	45.9	42.5	39.5
80°	20.4	21.3	22.1	23.4	29.3	34.9	36.6	36.1	33.6	32.3	28.9
82.5°	14.5	14.9	15.3	15.7	17.9	22.5	24.2	25.1	23.0	21.7	18.7
85°	8.5	8.9	8.9	9.8	10.2	11.5	14.5	14.5	14.0	12.3	11.9
87.5°	4.3	4.3	3.8	3.8	4.3	4.7	5.5	6.4	5.5	5.1	4.7
90°	15.0	13.2	12.3	11.0	8.5	6.0	3.5	1.0	3.5	6.0	8.5
92.5°	22.5	21.8	21.5	21.9	22.8	23.7	24.6	25.5	24.6	23.7	22.8
95°	35.1	33.5	32.7	36.4	43.9	51.4	58.9	66.4	58.9	51.4	43.9
97.5°	41.2	37.6	35.8	45.1	63.7	82.3	100.9	119.5	100.9	82.3	63.7
100°	46.7	42.8	40.9	56.4	87.5	118.6	149.7	180.8	149.7	118.6	87.5
102.5°	184.2	225.5	246.2	246.4	246.9	247.3	247.8	248.2	247.8	247.3	246.9
105°	248.2	310.2	341.2	337.8	331.0	324.1	317.3	310.5	317.3	324.1	331.0
107.5°	293.9	370.4	408.6	405.8	400.1	394.4	388.8	383.1	388.8	394.4	400.1
110°	375.6	441.2	474.0	471.6	466.8	462.1	457.3	452.5	457.3	462.1	466.8

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	530.5	534.4	536.3	534.3	530.2	526.1	522.0	517.9	522.0	526.1	530.2
115°	613.2	607.5	604.7	602.8	598.9	595.0	591.2	587.3	591.2	595.0	598.9
117.5°	673.8	669.9	668.0	665.7	661.2	656.7	652.1	647.6	652.1	656.7	661.2
120°	736.4	732.3	730.3	728.6	725.2	721.8	718.4	715.0	718.4	721.8	725.2
122.5°	795.4	790.9	788.6	786.8	783.1	779.5	775.8	772.2	775.8	779.5	783.1
125°	850.2	845.9	843.7	842.2	839.3	836.4	833.4	830.5	833.4	836.4	839.3
127.5°	903.0	899.6	897.9	896.3	893.1	890.0	886.8	883.6	886.8	890.0	893.1
130°	953.7	951.2	950.0	948.2	944.5	940.9	937.2	933.6	937.2	940.9	944.5
132.5°	1001.7	999.2	998.0	996.5	993.6	990.6	987.7	984.7	987.7	990.6	993.6
135°	1047.0	1044.9	1043.9	1042.1	1038.5	1034.8	1031.2	1027.6	1031.2	1034.8	1038.5
137.5°	1088.2	1085.9	1084.8	1083.4	1080.7	1078.0	1075.2	1072.5	1075.2	1078.0	1080.7
140°	1128.4	1125.9	1124.6	1123.7	1121.9	1120.1	1118.3	1116.5	1118.3	1120.1	1121.9
142.5°	1164.8	1161.9	1160.4	1159.6	1158.0	1156.4	1154.8	1153.2	1154.8	1156.4	1158.0
145°	1196.8	1192.9	1191.0	1191.1	1191.4	1191.6	1191.9	1192.1	1191.9	1191.6	1191.4
147.5°	1228.5	1224.6	1222.7	1223.0	1223.7	1224.4	1225.1	1225.8	1225.1	1224.4	1223.7
150°	1256.7	1253.1	1251.3	1252.1	1253.7	1255.2	1256.8	1258.4	1256.8	1255.2	1253.7
152.5°	1283.0	1279.6	1277.9	1278.8	1280.6	1282.4	1284.2	1286.0	1284.2	1282.4	1280.6
155°	1307.5	1304.8	1303.4	1304.4	1306.5	1308.5	1310.6	1312.6	1310.6	1308.5	1306.5
157.5°	1329.0	1326.9	1325.9	1326.8	1328.6	1330.4	1332.2	1334.0	1332.2	1330.4	1328.6
160°	1348.3	1347.0	1346.3	1347.0	1348.3	1349.7	1351.0	1352.4	1351.0	1349.7	1348.3
162.5°	1364.3	1363.2	1362.6	1363.3	1364.7	1366.0	1367.4	1368.8	1367.4	1366.0	1364.7
165°	1377.9	1377.2	1376.9	1377.6	1379.0	1380.3	1381.7	1383.1	1381.7	1380.3	1379.0
167.5°	1389.2	1388.5	1388.2	1388.9	1390.2	1391.6	1392.9	1394.3	1392.9	1391.6	1390.2
170°	1398.1	1397.6	1397.4	1398.1	1399.4	1400.8	1402.1	1403.5	1402.1	1400.8	1399.4
172.5°	1404.2	1403.7	1403.5	1404.2	1405.5	1406.9	1408.2	1409.6	1408.2	1406.9	1405.5
175°	1408.3	1407.8	1407.6	1408.4	1410.0	1411.5	1413.1	1414.7	1413.1	1411.5	1410.0
177.5°	1409.9	1409.7	1409.6	1410.4	1412.0	1413.6	1415.2	1416.8	1415.2	1413.6	1412.0
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	604.8	605.3	606.5	602.7	596.8	594.2	586.6	585.3	584.0	584.0	585.3
5°	591.2	589.5	590.0	582.7	574.2	569.1	558.5	560.2	554.7	551.3	552.1
7.5°	576.4	571.7	571.3	561.9	551.3	541.9	530.9	528.3	523.2	517.3	514.7
10°	557.7	554.3	547.9	537.3	523.7	516.0	501.1	492.2	490.9	482.0	478.6
12.5°	538.5	532.6	526.2	511.3	496.0	483.7	472.7	462.9	456.1	448.4	443.3
15°	516.4	509.2	502.0	486.3	468.4	456.1	439.5	425.0	405.1	389.3	380.4
17.5°	492.2	484.1	474.4	456.9	439.5	422.5	391.9	374.9	360.9	351.5	346.0
20°	467.1	458.2	448.4	431.0	400.8	371.1	354.1	340.9	332.4	323.0	316.2
22.5°	440.8	431.4	420.8	393.6	361.7	340.9	327.7	315.4	303.1	298.0	294.6
25°	416.1	407.6	394.0	357.0	332.0	312.8	298.0	289.9	283.5	276.7	270.3
27.5°	390.6	374.9	355.8	324.7	309.0	289.5	278.8	272.9	261.8	257.2	254.2
30°	360.0	342.6	324.3	302.2	283.9	270.3	260.6	250.8	244.4	239.7	234.6
32.5°	329.0	312.4	300.9	278.0	264.4	250.4	241.0	235.1	225.7	222.7	220.6
35°	302.2	288.2	278.0	259.3	246.5	233.8	227.0	218.1	212.1	206.6	203.2
37.5°	275.9	268.2	257.6	241.9	228.3	218.1	208.7	205.7	197.6	194.7	191.3
40°	257.6	246.1	237.2	223.6	212.1	201.0	195.1	188.3	182.8	178.1	176.8
42.5°	235.5	227.0	221.9	207.0	195.1	188.7	181.5	173.8	169.6	165.8	161.1
45°	218.9	211.2	204.0	192.1	181.5	173.4	167.0	161.9	154.7	153.0	145.8
47.5°	201.5	193.8	188.3	176.4	166.6	159.0	154.3	147.5	141.5	137.7	134.3
50°	184.0	177.7	172.6	162.4	153.9	145.8	139.4	132.6	130.1	123.7	121.6
52.5°	167.5	163.2	157.7	147.9	139.4	132.6	125.8	120.3	116.5	113.1	110.5
55°	153.4	146.6	144.1	133.5	126.2	119.0	113.1	109.7	105.0	102.9	100.7
57.5°	137.7	133.9	129.6	121.6	113.5	106.7	102.4	97.3	94.8	92.2	90.5
60°	124.1	118.6	115.2	108.4	101.2	94.8	91.0	87.1	83.7	81.6	78.2
62.5°	108.4	104.1	102.0	94.8	88.8	82.9	79.5	75.7	73.1	69.3	65.0
65°	94.8	91.4	88.8	82.9	77.4	71.8	68.4	63.8	60.4	58.2	57.8
67.5°	82.9	80.3	76.5	71.0	65.5	61.2	57.4	53.6	53.1	52.3	52.3
70°	69.7	67.2	65.0	59.1	54.4	49.7	48.9	47.6	46.3	45.9	45.1
72.5°	58.2	56.1	53.6	48.5	43.8	42.5	41.7	40.8	39.5	39.1	38.7
75°	47.2	44.2	42.5	37.8	36.6	35.7	34.9	33.6	32.7	32.3	31.5
77.5°	36.1	33.2	33.2	30.6	29.8	28.5	27.6	26.8	26.4	25.5	25.5
80°	25.5	25.5	24.7	23.4	22.1	21.7	20.4	20.0	19.6	20.0	19.1
82.5°	18.7	17.0	17.0	16.2	15.3	14.9	14.0	14.0	13.6	13.6	13.6
85°	10.6	10.6	10.2	9.4	8.9	8.9	8.5	8.5	8.1	8.1	7.7
87.5°	4.3	3.8	4.3	3.8	3.8	3.4	3.4	3.4	3.0	3.4	3.0
90°	11.0	12.3	13.2	15.0	16.8	18.6	20.4	21.5	22.7	23.8	24.9
92.5°	21.9	21.5	21.8	22.5	23.2	23.8	24.5	25.0	25.4	25.9	26.4
95°	36.4	32.7	33.5	35.1	36.6	38.2	39.8	40.9	42.1	43.2	44.3
97.5°	45.1	35.8	37.6	41.2	44.9	48.5	52.1	52.8	53.5	54.2	54.9
100°	56.4	40.9	42.8	46.7	50.5	54.4	58.2	60.0	61.8	63.7	65.5
102.5°	246.4	246.2	225.5	184.2	142.9	101.6	60.3	62.8	65.3	67.8	70.3
105°	337.8	341.2	310.2	248.2	186.3	124.3	62.3	64.8	67.3	69.8	72.3
107.5°	405.8	408.6	370.4	293.9	217.4	140.9	64.4	66.9	69.4	71.9	74.4
110°	471.6	474.0	441.2	375.6	310.0	244.4	178.8	156.1	133.4	110.7	88.0

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	534.3	536.3	534.4	530.5	526.6	522.8	518.9	421.1	323.3	225.4	127.6
115°	602.8	604.7	607.5	613.2	618.9	624.5	630.2	525.1	420.0	314.9	209.8
117.5°	665.7	668.0	669.9	673.8	677.7	681.5	685.4	652.9	620.5	588.0	555.5
120°	728.6	730.3	732.3	736.4	740.5	744.6	748.7	751.4	754.2	756.9	759.6
122.5°	786.8	788.6	790.9	795.4	799.9	804.5	809.0	810.4	811.7	813.1	814.4
125°	842.2	843.7	845.9	850.2	854.5	858.8	863.1	864.7	866.3	867.9	869.5
127.5°	896.3	897.9	899.6	903.0	906.4	909.8	913.2	915.5	917.7	920.0	922.3
130°	948.2	950.0	951.2	953.7	956.2	958.7	961.2	963.7	966.2	968.7	971.2
132.5°	996.5	998.0	999.2	1001.7	1004.2	1006.7	1009.2	1011.2	1013.3	1015.3	1017.4
135°	1042.1	1043.9	1044.9	1047.0	1049.0	1051.1	1053.1	1055.4	1057.6	1059.9	1062.2
137.5°	1083.4	1084.8	1085.9	1088.2	1090.5	1092.7	1095.0	1097.3	1099.5	1101.8	1104.1
140°	1123.7	1124.6	1125.9	1128.4	1130.9	1133.4	1135.9	1137.9	1140.0	1142.0	1144.1
142.5°	1159.6	1160.4	1161.9	1164.8	1167.8	1170.7	1173.7	1175.5	1177.3	1179.1	1180.9
145°	1191.1	1191.0	1192.9	1196.8	1200.7	1204.5	1208.4	1210.0	1211.6	1213.1	1214.7
147.5°	1223.0	1222.7	1224.6	1228.5	1232.4	1236.2	1240.1	1241.2	1242.4	1243.5	1244.6
150°	1252.1	1251.3	1253.1	1256.7	1260.4	1264.0	1267.6	1269.0	1270.4	1271.7	1273.1
152.5°	1278.8	1277.9	1279.6	1283.0	1286.4	1289.8	1293.2	1294.6	1295.9	1297.3	1298.6
155°	1304.4	1303.4	1304.8	1307.5	1310.2	1313.0	1315.7	1317.1	1318.4	1319.8	1321.1
157.5°	1326.8	1325.9	1326.9	1329.0	1331.0	1333.1	1335.1	1336.7	1338.3	1339.8	1341.4
160°	1347.0	1346.3	1347.0	1348.3	1349.7	1351.0	1352.4	1353.8	1355.2	1356.5	1357.9
162.5°	1363.3	1362.6	1363.2	1364.3	1365.4	1366.6	1367.7	1369.3	1370.9	1372.5	1374.1
165°	1377.6	1376.9	1377.2	1377.9	1378.6	1379.3	1380.0	1381.6	1383.2	1384.8	1386.4
167.5°	1388.9	1388.2	1388.5	1389.2	1389.9	1390.5	1391.2	1392.8	1394.4	1396.0	1397.6
170°	1398.1	1397.4	1397.6	1398.1	1398.5	1399.0	1399.4	1401.0	1402.6	1404.2	1405.8
172.5°	1404.2	1403.5	1403.7	1404.2	1404.6	1405.1	1405.5	1407.1	1408.7	1410.3	1411.9
175°	1408.4	1407.6	1407.8	1408.3	1408.7	1409.2	1409.6	1411.2	1412.8	1414.4	1416.0
177.5°	1410.4	1409.6	1409.7	1409.9	1410.2	1410.4	1410.6	1412.2	1413.8	1415.4	1417.0
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	585.3	584.4	581.9	582.7	581.5	581.5	580.6	580.6	580.6	582.7	581.5
5°	553.4	550.4	547.5	546.2	544.9	543.6	543.6	543.2	547.0	546.2	549.6
7.5°	513.9	513.0	507.1	507.1	505.0	504.1	506.2	506.7	507.1	507.9	510.1
10°	478.6	476.5	468.0	468.8	467.6	465.9	467.1	466.3	469.3	470.1	469.3
12.5°	437.0	433.1	423.8	419.1	414.0	410.2	414.8	411.4	423.3	426.7	436.1
15°	381.7	374.5	368.1	368.1	363.4	360.0	362.1	366.0	368.5	372.3	374.0
17.5°	344.7	341.7	336.6	333.7	332.4	331.1	331.1	332.8	338.3	337.9	341.3
20°	313.3	311.6	309.0	305.2	303.9	303.1	303.1	303.1	306.9	310.3	312.4
22.5°	291.6	290.3	288.6	283.5	281.0	280.1	282.2	283.5	286.5	289.0	291.2
25°	269.9	266.9	264.0	262.3	261.0	261.0	261.8	262.3	263.5	264.8	267.4
27.5°	252.1	249.9	245.7	241.0	241.0	239.7	240.6	241.4	244.4	248.7	250.8
30°	232.1	231.7	230.0	228.3	226.6	225.7	227.4	228.7	229.1	231.2	231.2
32.5°	217.6	214.6	211.7	210.0	209.1	208.7	209.1	210.8	210.8	213.4	216.4
35°	203.2	201.5	198.5	195.5	194.7	192.5	194.2	195.9	198.9	200.2	201.5
37.5°	187.4	185.3	184.0	183.2	181.5	181.9	180.6	183.2	185.7	185.3	186.2
40°	175.5	171.7	167.9	167.5	167.0	166.6	166.6	167.0	168.7	170.4	173.0
42.5°	160.2	159.0	155.6	152.2	151.3	150.5	149.6	151.3	154.7	157.7	159.0
45°	144.5	142.8	142.0	139.4	137.7	137.3	136.4	138.6	141.5	142.8	143.7
47.5°	130.1	129.6	127.1	127.5	126.2	126.7	126.2	127.5	127.5	128.8	129.6
50°	120.3	119.0	117.7	116.9	115.6	115.6	115.2	115.6	117.3	119.0	118.6
52.5°	110.5	108.4	108.0	107.5	106.7	107.5	106.3	106.7	108.4	109.2	108.8
55°	99.0	98.6	97.8	96.9	96.5	96.1	96.1	96.1	97.8	99.0	99.5
57.5°	90.1	88.0	86.3	86.3	84.6	84.2	85.0	85.4	86.7	87.6	88.4
60°	77.8	76.9	74.4	73.1	70.6	70.1	70.1	71.8	74.0	76.9	77.8
62.5°	64.6	63.3	62.9	62.9	62.9	62.9	62.9	62.9	62.9	63.3	63.3
65°	57.4	57.8	57.4	57.0	57.4	57.4	57.0	57.0	57.0	57.4	57.8
67.5°	51.4	51.0	51.4	51.0	50.6	50.6	50.2	50.6	51.0	51.4	51.4
70°	44.6	44.6	44.2	44.6	44.2	43.8	43.4	43.4	44.2	44.6	44.6
72.5°	38.3	38.3	37.8	37.8	37.0	37.0	37.4	37.0	37.0	38.3	38.3
75°	31.9	31.5	31.0	31.0	30.6	30.6	30.6	30.2	31.0	31.0	31.5
77.5°	25.1	25.1	25.1	24.7	24.7	24.2	24.2	24.7	24.7	24.7	25.1
80°	19.1	19.1	19.1	18.7	18.3	18.3	18.3	18.3	18.3	18.7	18.3
82.5°	13.2	13.2	13.2	13.2	13.2	12.8	12.8	12.8	13.2	13.2	12.8
85°	8.1	7.7	8.1	8.1	7.7	8.1	7.7	7.7	7.2	7.2	7.7
87.5°	3.4	3.0	2.6	2.6	3.0	2.6	2.6	2.6	3.0	2.6	2.6
90°	25.5	25.7	26.2	26.7	27.1	27.6	27.1	26.7	26.2	25.7	25.5
92.5°	26.6	26.7	26.9	27.2	27.4	27.6	27.4	27.2	26.9	26.7	26.6
95°	44.9	44.8	44.6	44.3	44.1	43.9	44.1	44.3	44.6	44.8	44.9
97.5°	55.2	55.3	55.5	55.8	56.0	56.2	56.0	55.8	55.5	55.3	55.2
100°	66.4	66.6	67.1	67.5	68.0	68.4	68.0	67.5	67.1	66.6	66.4
102.5°	71.5	71.8	72.5	73.2	73.9	74.6	73.9	73.2	72.5	71.8	71.5
105°	73.5	74.0	74.9	75.8	76.7	77.6	76.7	75.8	74.9	74.0	73.5
107.5°	75.6	76.1	77.0	77.9	78.8	79.7	78.8	77.9	77.0	76.1	75.6
110°	76.6	77.1	78.0	78.9	79.8	80.7	79.8	78.9	78.0	77.1	76.6



TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	78.7	79.0	79.7	80.4	81.0	81.7	81.0	80.4	79.7	79.0	78.7
115°	157.3	149.1	132.8	116.5	100.1	83.8	100.1	116.5	132.8	149.1	157.3
117.5°	539.3	509.6	450.1	390.6	331.2	271.7	331.2	390.6	450.1	509.6	539.3
120°	761.0	745.7	715.0	684.4	653.7	623.1	653.7	684.4	715.0	745.7	761.0
122.5°	815.1	815.2	815.5	815.7	816.0	816.2	816.0	815.7	815.5	815.2	815.1
125°	870.3	870.6	871.3	872.0	872.7	873.4	872.7	872.0	871.3	870.6	870.3
127.5°	923.4	923.5	923.7	924.0	924.2	924.4	924.2	924.0	923.7	923.5	923.4
130°	972.4	972.3	972.1	971.8	971.6	971.4	971.6	971.8	972.1	972.3	972.4
132.5°	1018.4	1018.3	1018.1	1017.8	1017.6	1017.4	1017.6	1017.8	1018.1	1018.3	1018.4
135°	1063.3	1063.1	1062.6	1062.2	1061.7	1061.3	1061.7	1062.2	1062.6	1063.1	1063.3
137.5°	1105.2	1104.9	1104.2	1103.5	1102.9	1102.2	1102.9	1103.5	1104.2	1104.9	1105.2
140°	1145.1	1144.5	1143.4	1142.3	1141.1	1140.0	1141.1	1142.3	1143.4	1144.5	1145.1
142.5°	1181.8	1181.2	1180.1	1179.0	1177.8	1176.7	1177.8	1179.0	1180.1	1181.2	1181.8
145°	1215.5	1214.9	1213.8	1212.7	1211.5	1210.4	1211.5	1212.7	1213.8	1214.9	1215.5
147.5°	1245.2	1244.7	1243.8	1242.9	1242.0	1241.1	1242.0	1242.9	1243.8	1244.7	1245.2
150°	1273.8	1273.2	1272.1	1271.0	1269.8	1268.7	1269.8	1271.0	1272.1	1273.2	1273.8
152.5°	1299.3	1298.5	1296.9	1295.4	1293.8	1292.2	1293.8	1295.4	1296.9	1298.5	1299.3
155°	1321.8	1320.9	1319.1	1317.2	1315.4	1313.6	1315.4	1317.2	1319.1	1320.9	1321.8
157.5°	1342.2	1341.3	1339.5	1337.6	1335.8	1334.0	1335.8	1337.6	1339.5	1341.3	1342.2
160°	1358.6	1357.8	1356.2	1354.6	1353.0	1351.4	1353.0	1354.6	1356.2	1357.8	1358.6
162.5°	1374.9	1373.9	1371.8	1369.8	1367.7	1365.7	1367.7	1369.8	1371.8	1373.9	1374.9
165°	1387.2	1386.4	1384.8	1383.2	1381.6	1380.0	1381.6	1383.2	1384.8	1386.4	1387.2
167.5°	1398.4	1397.4	1395.3	1393.3	1391.2	1389.2	1391.2	1393.3	1395.3	1397.4	1398.4
170°	1406.6	1405.6	1403.5	1401.5	1399.4	1397.4	1399.4	1401.5	1403.5	1405.6	1406.6
172.5°	1412.7	1411.7	1409.6	1407.6	1405.5	1403.5	1405.5	1407.6	1409.6	1411.7	1412.7
175°	1416.8	1415.7	1413.4	1411.1	1408.9	1406.6	1408.9	1411.1	1413.4	1415.7	1416.8
177.5°	1417.8	1416.8	1414.7	1412.7	1410.6	1408.6	1410.6	1412.7	1414.7	1416.8	1417.8
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	582.7	584.9	584.0	579.3	584.0	585.3	587.8	590.4	592.1	594.6	596.8
5°	546.2	550.4	553.0	550.4	558.9	560.2	566.2	569.6	574.7	578.9	582.3
7.5°	511.8	515.2	520.3	521.1	526.2	532.2	540.7	549.2	557.2	561.5	565.3
10°	474.8	480.7	488.4	486.7	494.3	503.7	512.6	526.2	533.0	540.7	547.5
12.5°	437.8	441.6	451.8	455.2	466.3	473.5	485.8	494.3	511.3	520.3	526.2
15°	373.2	388.9	401.7	417.0	431.4	445.0	456.1	471.4	486.3	493.1	502.8
17.5°	343.9	351.1	358.7	366.4	385.1	409.3	428.9	445.5	458.2	467.1	478.6
20°	313.3	320.5	329.0	336.2	347.7	365.1	389.3	417.8	433.1	442.5	453.5
22.5°	291.6	298.4	303.9	310.3	319.2	332.0	350.2	385.5	405.9	417.4	427.2
25°	268.2	276.7	282.7	287.3	294.6	308.6	323.5	343.4	380.0	388.9	402.5
27.5°	252.1	254.6	261.4	268.6	275.9	283.5	298.8	315.8	340.5	360.0	376.6
30°	232.9	239.3	245.7	248.7	255.0	266.1	275.4	293.7	312.8	328.1	348.1
32.5°	218.5	222.3	226.6	233.8	239.7	247.4	256.7	272.0	288.2	298.0	313.3
35°	202.3	204.9	213.8	216.8	222.7	230.4	239.7	251.6	269.1	276.7	287.8
37.5°	187.0	193.0	195.5	202.3	207.8	215.5	222.3	235.9	247.4	256.3	266.5
40°	175.1	177.7	182.3	188.3	193.0	198.9	207.4	217.2	229.5	236.8	245.7
42.5°	160.7	162.8	168.7	172.1	179.8	185.3	190.4	202.3	213.4	218.9	227.8
45°	144.9	150.0	153.9	160.7	164.9	171.7	178.1	186.6	196.8	203.2	208.3
47.5°	131.3	136.4	140.3	146.6	153.4	156.4	163.2	172.1	181.5	186.6	193.8
50°	120.3	122.0	129.2	132.2	139.4	145.4	150.0	157.7	167.9	170.9	176.8
52.5°	109.7	110.9	115.6	119.4	125.8	130.9	136.9	144.1	152.6	157.3	161.9
55°	100.3	101.2	103.3	107.5	111.8	118.2	123.7	130.5	137.7	142.8	147.1
57.5°	89.7	91.4	93.1	95.6	99.9	105.8	111.8	118.2	124.1	127.5	133.0
60°	77.4	79.9	82.9	85.9	88.8	93.1	99.9	105.8	111.4	114.3	118.6
62.5°	64.2	69.3	71.8	75.2	77.8	81.6	86.7	93.5	97.3	101.2	104.6
65°	57.8	58.2	58.7	62.1	66.7	70.6	75.2	80.3	86.3	88.8	91.4
67.5°	51.4	51.9	52.7	53.1	54.8	59.1	64.2	69.7	74.4	76.1	78.6
70°	45.1	45.1	46.8	47.2	47.6	48.0	52.3	57.8	62.1	64.2	67.2
72.5°	38.3	38.7	39.5	40.0	40.8	41.7	42.9	45.9	51.0	53.1	56.5
75°	31.5	31.9	32.3	32.7	34.0	34.4	35.7	37.4	39.5	42.1	44.2
77.5°	25.1	25.1	25.5	26.4	27.2	27.6	28.9	29.8	30.6	31.9	33.6
80°	18.7	19.1	19.1	20.0	20.0	20.4	20.8	22.1	23.0	23.8	24.7
82.5°	12.8	13.6	13.6	13.6	14.0	14.5	14.9	14.9	15.7	16.2	17.4
85°	7.7	8.1	8.1	8.1	7.7	8.5	8.5	8.9	8.9	8.9	9.4
87.5°	3.0	2.6	3.0	3.0	3.0	3.4	3.0	3.0	3.4	3.8	3.8
90°	24.9	23.8	22.7	21.5	20.4	18.6	16.8	15.0	13.2	12.3	11.0
92.5°	26.4	25.9	25.4	25.0	24.5	23.8	23.2	22.5	21.8	21.5	21.9
95°	44.3	43.2	42.1	40.9	39.8	38.2	36.6	35.1	33.5	32.7	36.4
97.5°	54.9	54.2	53.5	52.8	52.1	48.5	44.9	41.2	37.6	35.8	45.1
100°	65.5	63.7	61.8	60.0	58.2	54.4	50.5	46.7	42.8	40.9	56.4
102.5°	70.3	67.8	65.3	62.8	60.3	101.6	142.9	184.2	225.5	246.2	246.4
105°	72.3	69.8	67.3	64.8	62.3	124.3	186.3	248.2	310.2	341.2	337.8
107.5°	74.4	71.9	69.4	66.9	64.4	140.9	217.4	293.9	370.4	408.6	405.8
110°	88.0	110.7	133.4	156.1	178.8	244.4	310.0	375.6	441.2	474.0	471.6

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	127.6	225.4	323.3	421.1	518.9	522.8	526.6	530.5	534.4	536.3	534.3
115°	209.8	314.9	420.0	525.1	630.2	624.5	618.9	613.2	607.5	604.7	602.8
117.5°	555.5	588.0	620.5	652.9	685.4	681.5	677.7	673.8	669.9	668.0	665.7
120°	759.6	756.9	754.2	751.4	748.7	744.6	740.5	736.4	732.3	730.3	728.6
122.5°	814.4	813.1	811.7	810.4	809.0	804.5	799.9	795.4	790.9	788.6	786.8
125°	869.5	867.9	866.3	864.7	863.1	858.8	854.5	850.2	845.9	843.7	842.2
127.5°	922.3	920.0	917.7	915.5	913.2	909.8	906.4	903.0	899.6	897.9	896.3
130°	971.2	968.7	966.2	963.7	961.2	958.7	956.2	953.7	951.2	950.0	948.2
132.5°	1017.4	1015.3	1013.3	1011.2	1009.2	1006.7	1004.2	1001.7	999.2	998.0	996.5
135°	1062.2	1059.9	1057.6	1055.4	1053.1	1051.1	1049.0	1047.0	1044.9	1043.9	1042.1
137.5°	1104.1	1101.8	1099.5	1097.3	1095.0	1092.7	1090.5	1088.2	1085.9	1084.8	1083.4
140°	1144.1	1142.0	1140.0	1137.9	1135.9	1133.4	1130.9	1128.4	1125.9	1124.6	1123.7
142.5°	1180.9	1179.1	1177.3	1175.5	1173.7	1170.7	1167.8	1164.8	1161.9	1160.4	1159.6
145°	1214.7	1213.1	1211.6	1210.0	1208.4	1204.5	1200.7	1196.8	1192.9	1191.0	1191.1
147.5°	1244.6	1243.5	1242.4	1241.2	1240.1	1236.2	1232.4	1228.5	1224.6	1222.7	1223.0
150°	1273.1	1271.7	1270.4	1269.0	1267.6	1264.0	1260.4	1256.7	1253.1	1251.3	1252.1
152.5°	1298.6	1297.3	1295.9	1294.6	1293.2	1289.8	1286.4	1283.0	1279.6	1277.9	1278.8
155°	1321.1	1319.8	1318.4	1317.1	1315.7	1313.0	1310.2	1307.5	1304.8	1303.4	1304.4
157.5°	1341.4	1339.8	1338.3	1336.7	1335.1	1333.1	1331.0	1329.0	1326.9	1325.9	1326.8
160°	1357.9	1356.5	1355.2	1353.8	1352.4	1351.0	1349.7	1348.3	1347.0	1346.3	1347.0
162.5°	1374.1	1372.5	1370.9	1369.3	1367.7	1366.6	1365.4	1364.3	1363.2	1362.6	1363.3
165°	1386.4	1384.8	1383.2	1381.6	1380.0	1379.3	1378.6	1377.9	1377.2	1376.9	1377.6
167.5°	1397.6	1396.0	1394.4	1392.8	1391.2	1390.5	1389.9	1389.2	1388.5	1388.2	1388.9
170°	1405.8	1404.2	1402.6	1401.0	1399.4	1399.0	1398.5	1398.1	1397.6	1397.4	1398.1
172.5°	1411.9	1410.3	1408.7	1407.1	1405.5	1405.1	1404.6	1404.2	1403.7	1403.5	1404.2
175°	1416.0	1414.4	1412.8	1411.2	1409.6	1409.2	1408.7	1408.3	1407.8	1407.6	1408.4
177.5°	1417.0	1415.4	1413.8	1412.2	1410.6	1410.4	1410.2	1409.9	1409.7	1409.6	1410.4
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	611.6	611.6	611.6	611.6
2.5°	600.6	599.3	607.0	615.5
5°	588.3	590.4	600.2	612.1
7.5°	575.5	580.2	591.7	607.4
10°	557.7	566.2	583.6	599.7
12.5°	540.2	551.7	568.3	587.4
15°	520.7	533.4	553.8	576.8
17.5°	499.0	513.5	537.3	562.3
20°	476.1	495.2	520.3	547.5
22.5°	450.6	473.5	499.4	529.6
25°	425.9	451.0	476.9	511.8
27.5°	401.7	426.3	455.2	490.5
30°	377.4	400.0	431.0	468.8
32.5°	351.5	374.9	407.6	446.3
35°	327.7	351.1	381.7	419.9
37.5°	302.2	327.3	356.6	396.1
40°	272.5	301.8	330.3	368.1
42.5°	247.8	278.8	306.5	342.2
45°	228.3	257.6	280.5	315.4
47.5°	210.0	233.8	257.2	289.5
50°	192.5	210.8	235.1	264.0
52.5°	174.7	190.4	211.2	238.5
55°	158.5	173.4	192.1	212.9
57.5°	143.7	154.3	173.0	191.7
60°	127.1	138.1	152.6	168.3
62.5°	113.1	121.6	135.2	148.3
65°	98.2	106.3	116.5	128.8
67.5°	84.6	91.8	99.9	109.7
70°	72.3	77.8	83.7	92.2
72.5°	59.1	65.0	70.6	77.4
75°	48.5	51.0	55.7	60.4
77.5°	37.4	40.8	43.4	47.2
80°	26.8	29.8	30.6	33.6
82.5°	17.9	19.6	21.3	22.1
85°	10.2	11.1	12.8	13.2
87.5°	3.8	4.3	5.1	6.0
90°	8.5	6.0	3.5	1.0
92.5°	22.8	23.7	24.6	25.5
95°	43.9	51.4	58.9	66.4
97.5°	63.7	82.3	100.9	119.5
100°	87.5	118.6	149.7	180.8
102.5°	246.9	247.3	247.8	248.2
105°	331.0	324.1	317.3	310.5
107.5°	400.1	394.4	388.8	383.1
110°	466.8	462.1	457.3	452.5

TEST NUMBER: P1008348

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	530.2	526.1	522.0	517.9
115°	598.9	595.0	591.2	587.3
117.5°	661.2	656.7	652.1	647.6
120°	725.2	721.8	718.4	715.0
122.5°	783.1	779.5	775.8	772.2
125°	839.3	836.4	833.4	830.5
127.5°	893.1	890.0	886.8	883.6
130°	944.5	940.9	937.2	933.6
132.5°	993.6	990.6	987.7	984.7
135°	1038.5	1034.8	1031.2	1027.6
137.5°	1080.7	1078.0	1075.2	1072.5
140°	1121.9	1120.1	1118.3	1116.5
142.5°	1158.0	1156.4	1154.8	1153.2
145°	1191.4	1191.6	1191.9	1192.1
147.5°	1223.7	1224.4	1225.1	1225.8
150°	1253.7	1255.2	1256.8	1258.4
152.5°	1280.6	1282.4	1284.2	1286.0
155°	1306.5	1308.5	1310.6	1312.6
157.5°	1328.6	1330.4	1332.2	1334.0
160°	1348.3	1349.7	1351.0	1352.4
162.5°	1364.7	1366.0	1367.4	1368.8
165°	1379.0	1380.3	1381.7	1383.1
167.5°	1390.2	1391.6	1392.9	1394.3
170°	1399.4	1400.8	1402.1	1403.5
172.5°	1405.5	1406.9	1408.2	1409.6
175°	1410.0	1411.5	1413.1	1414.7
177.5°	1412.0	1413.6	1415.2	1416.8
180°	1411.7	1411.7	1411.7	1411.7

(END OF REPORT)