

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008396

Luminaire Tested: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008396
REPORT IS A COMBINATION OF REPORTS P988226 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6183.0 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	33	33	26
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28	28	28	23
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	25	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	22	22	18
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	19	19	16
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17	17	17	14
7	57	45	38	32	51	41	34	30	33	28	25	26	23	20	19	17	16	16	16	13
8	52	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	14	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	16	14	13	13	13	11
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17020	17020	17020	17020
5°	17058	18077	17117	14441
10°	16870	19107	16990	11926
15°	16505	19113	16785	8958
20°	16064	15799	16415	7391
25°	15531	9873	15866	6288
30°	14849	6320	15252	5413
35°	14020	4857	14473	4633
40°	13095	4083	13655	4052
45°	12108	3476	12613	3401
50°	11096	2953	11612	2942
55°	9974	2566	10512	2533
60°	8979	1957	9455	1934
65°	8048	1472	8525	1671
70°	7020	1176	7570	1362
75°	5935	902	6478	1030
80°	4710	612	5070	675
85°	3277	315	3588	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15568 cd/sqm

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	1.6
10°-20°	284.7	4.6
20°-30°	366.3	5.9
30°-40°	347.6	5.6
40°-50°	297.9	4.8
50°-60°	226.8	3.7
60°-70°	143.1	2.3
70°-80°	71.4	1.2
80°-90°	20.9	0.3
90°-100°	48.6	0.8
100°-110°	181.2	2.9
110°-120°	480.7	7.8
120°-130°	797.2	12.9
130°-140°	846.8	13.7
140°-150°	787.0	12.7
150°-160°	632.7	10.2
160°-170°	407.7	6.6
170°-180°	140.3	2.3
0°-30°	753.0	12.2
0°-40°	1100.5	17.8
0°-60°	1625.2	26.3
0°-90°	1860.6	30.1
90°-120°	710.5	11.5
90°-150°	3141.6	50.8
90°-180°	4322.0	69.9
0°-180°	6183.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1076	1196	1080	956	1076	102
15°	1014	1350	1031	633	1014	285
25°	900	720	919	459	900	413
35°	738	355	762	338	738	462
45°	554	247	578	241	554	428
55°	374	171	394	169	374	337
65°	226	89	240	101	226	225
75°	106	47	116	54	106	115
85°	23	13	25	14	23	26
90°	1	29	1	29	1	5
95°	69	46	69	46	69	82
105°	324	81	324	81	324	347
115°	613	88	613	88	613	604
125°	867	912	867	912	867	774
135°	1073	1108	1073	1108	1073	829
145°	1245	1264	1245	1264	1245	779
155°	1371	1372	1371	1372	1371	632
165°	1444	1441	1444	1441	1444	408
175°	1478	1469	1478	1469	1478	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1081.9	1086.4	1088.6	1091.6	1098.3	1102.8	1109.5	1111.0	1110.3	1113.3	1105.0
5°	1075.9	1085.6	1094.6	1102.1	1114.0	1121.5	1129.7	1139.4	1141.7	1152.9	1146.1
7.5°	1067.7	1081.9	1094.6	1109.5	1127.5	1137.2	1149.9	1164.8	1171.5	1185.0	1188.7
10°	1054.2	1074.4	1096.1	1111.8	1136.4	1153.6	1165.6	1189.5	1205.2	1225.3	1222.3
12.5°	1032.6	1058.7	1087.9	1114.0	1146.1	1157.3	1179.8	1204.4	1224.6	1243.3	1259.7
15°	1013.9	1043.8	1075.9	1108.0	1144.6	1165.6	1188.0	1220.1	1241.8	1274.6	1288.8
17.5°	988.5	1026.6	1064.7	1100.6	1143.9	1167.8	1195.4	1226.8	1259.0	1290.3	1301.5
20°	962.3	1003.4	1044.5	1093.1	1142.4	1165.6	1194.0	1232.8	1264.2	1288.8	1288.8
22.5°	931.0	981.0	1028.1	1074.4	1128.2	1161.8	1191.0	1236.5	1259.0	1264.2	1244.0
25°	899.6	949.6	1001.2	1058.7	1120.0	1149.9	1182.7	1225.3	1232.8	1211.9	1159.6
27.5°	862.2	918.3	976.5	1038.5	1102.8	1140.2	1170.0	1198.4	1184.2	1128.2	1046.8
30°	824.1	884.6	950.4	1009.4	1087.1	1121.5	1146.9	1155.1	1110.3	1019.1	913.8
32.5°	784.5	843.5	913.0	984.0	1062.5	1095.3	1111.8	1090.1	1007.9	892.8	764.3
35°	738.2	804.7	877.2	951.1	1028.8	1053.5	1063.2	1010.2	904.8	756.1	628.4
37.5°	696.3	762.8	840.5	916.0	991.5	1004.9	995.2	912.3	778.5	631.3	506.6
40°	647.0	718.0	794.2	878.7	940.7	944.4	920.5	812.9	647.0	508.8	431.9
42.5°	601.5	673.2	749.4	835.3	882.4	869.7	837.6	696.3	540.2	438.6	376.6
45°	554.4	622.4	704.6	780.8	814.4	784.5	735.9	585.8	453.5	377.3	329.5
47.5°	508.8	572.3	653.8	727.0	733.0	699.3	641.8	490.9	393.0	331.7	292.9
50°	464.0	527.5	603.7	664.2	658.2	611.9	546.9	426.6	341.4	292.9	260.8
52.5°	419.2	476.7	550.7	598.5	573.1	528.2	464.0	361.6	298.1	255.5	230.9
55°	374.3	428.1	491.6	531.2	490.9	439.3	393.8	310.1	258.5	224.1	205.5
57.5°	337.0	379.6	437.8	461.7	413.2	372.8	333.2	266.7	224.1	199.5	177.8
60°	295.9	334.7	382.5	396.7	346.7	313.8	280.2	225.6	192.0	170.4	156.2
62.5°	260.8	292.9	329.5	329.5	285.4	260.8	235.4	189.0	161.4	144.2	137.5
65°	226.4	249.5	275.7	272.7	235.4	213.7	193.5	156.2	135.2	123.3	116.6
67.5°	192.8	210.7	227.9	217.4	190.5	171.8	153.2	126.3	112.1	103.9	94.9
70°	162.1	176.3	185.3	175.6	148.7	133.0	119.5	101.6	90.4	79.9	74.7
72.5°	136.0	142.0	144.9	133.0	110.6	101.6	91.9	79.2	69.5	64.3	62.8
75°	106.1	111.3	109.1	100.1	81.4	74.7	67.2	58.3	56.0	53.0	51.6
77.5°	82.9	82.9	79.2	71.0	58.3	53.0	50.1	45.6	43.3	42.6	41.1
80°	59.0	58.3	56.0	47.1	39.6	36.6	36.6	33.6	32.9	31.4	31.4
82.5°	38.9	38.9	35.9	28.4	26.2	25.4	24.7	23.2	23.2	22.4	22.4
85°	23.2	21.7	17.9	15.7	14.9	14.9	14.2	13.4	14.2	13.4	13.4
87.5°	10.5	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	1.1	3.7	6.3	8.9	11.5	12.8	13.7	15.6	17.5	19.4	21.3
92.5°	26.7	25.7	24.8	23.8	22.9	22.4	22.8	23.5	24.2	24.9	25.6
95°	69.3	61.5	53.7	45.8	38.0	34.1	34.9	36.6	38.3	39.9	41.6
97.5°	124.8	105.4	85.9	66.5	47.0	37.3	39.2	43.0	46.8	50.6	54.4
100°	188.8	156.3	123.9	91.4	58.9	42.7	44.7	48.7	52.8	56.8	60.8
102.5°	259.2	258.7	258.3	257.8	257.3	257.1	235.5	192.4	149.2	106.1	62.9
105°	324.3	331.4	338.5	345.6	352.7	356.3	323.9	259.2	194.5	129.8	65.1
107.5°	400.1	406.0	411.9	417.8	423.7	426.7	386.8	306.9	227.0	147.1	67.2
110°	472.6	477.6	482.6	487.5	492.5	495.0	460.7	392.2	323.7	255.2	186.7

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	540.9	545.2	549.4	553.7	558.0	560.1	558.1	554.1	550.0	546.0	542.0
115°	613.4	617.4	621.5	625.5	629.6	631.6	634.6	640.5	646.4	652.3	658.2
117.5°	676.4	681.1	685.9	690.6	695.3	697.7	699.7	703.8	707.8	711.9	715.9
120°	746.8	750.4	753.9	757.5	761.0	762.8	764.9	769.2	773.5	777.7	782.0
122.5°	806.5	810.3	814.1	817.9	821.7	823.6	826.0	830.7	835.4	840.2	844.9
125°	867.4	870.5	873.5	876.6	879.7	881.2	883.5	888.0	892.5	897.0	901.5
127.5°	922.8	926.1	929.5	932.8	936.1	937.8	939.6	943.1	946.7	950.2	953.8
130°	975.1	978.9	982.7	986.5	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9
132.5°	1028.4	1031.5	1034.6	1037.7	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1
135°	1073.3	1077.1	1080.9	1084.6	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9
137.5°	1120.2	1123.0	1125.9	1128.7	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7
140°	1166.1	1168.0	1169.9	1171.8	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3
142.5°	1204.5	1206.1	1207.8	1209.4	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8
145°	1245.0	1244.8	1244.6	1244.3	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1
147.5°	1280.2	1279.5	1278.8	1278.1	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2
150°	1314.4	1312.7	1311.1	1309.4	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0
152.5°	1343.2	1341.3	1339.4	1337.5	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6
155°	1370.9	1368.8	1366.6	1364.5	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1
157.5°	1393.3	1391.4	1389.5	1387.6	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4
160°	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5
162.5°	1429.6	1428.2	1426.8	1425.3	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5
165°	1444.5	1443.1	1441.7	1440.2	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3
167.5°	1456.3	1454.9	1453.5	1452.0	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1
170°	1465.9	1464.5	1463.1	1461.6	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6
172.5°	1472.3	1470.9	1469.5	1468.0	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0
175°	1477.6	1475.9	1474.3	1472.6	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3
177.5°	1479.7	1478.1	1476.4	1474.8	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1113.3	1114.8	1117.0	1127.5	1128.9	1131.9	1130.4	1130.4	1131.2	1129.7	1130.4
5°	1161.1	1163.3	1174.5	1187.2	1190.2	1187.2	1191.0	1196.2	1196.2	1196.2	1194.7
7.5°	1205.9	1214.1	1226.8	1245.5	1249.2	1253.0	1259.7	1255.2	1256.7	1263.4	1261.2
10°	1249.2	1261.2	1275.4	1291.1	1299.3	1304.5	1307.5	1314.2	1329.9	1312.0	1318.7
12.5°	1290.3	1307.5	1322.5	1339.6	1345.6	1352.3	1354.6	1360.6	1360.6	1359.8	1365.0
15°	1317.2	1332.9	1346.4	1357.6	1359.1	1357.6	1356.1	1356.8	1359.1	1350.1	1355.3
17.5°	1323.2	1324.7	1329.2	1324.7	1325.5	1309.8	1300.8	1298.6	1277.6	1278.4	1295.6
20°	1294.1	1268.7	1261.9	1237.3	1222.3	1182.0	1180.5	1169.3	1125.2	1138.7	1135.7
22.5°	1214.1	1170.8	1113.3	1084.9	1070.7	1028.1	995.2	972.0	956.4	940.7	933.9
25°	1108.8	1038.5	957.1	901.1	892.8	853.2	792.7	764.3	730.7	720.3	738.2
27.5°	972.8	881.6	789.7	703.8	688.1	652.3	621.6	601.5	562.6	560.4	561.9
30°	788.2	696.3	619.4	563.4	524.5	508.1	487.9	472.9	457.3	463.2	464.7
32.5°	647.8	560.4	488.6	458.8	440.8	430.4	413.2	403.5	396.7	394.5	393.8
35°	514.8	456.5	424.4	395.2	384.8	377.3	364.6	360.1	354.2	354.9	354.9
37.5°	440.8	392.3	368.3	353.4	343.7	340.0	331.7	327.3	323.5	322.0	324.3
40°	380.3	346.7	331.7	318.3	310.1	308.6	304.1	298.9	294.4	295.1	297.4
42.5°	336.2	316.8	298.9	288.4	282.4	280.2	276.4	272.7	272.7	270.5	269.7
45°	301.1	285.4	270.5	260.8	257.0	254.0	249.5	248.8	245.8	246.6	247.3
47.5°	269.7	257.0	245.8	236.1	232.4	231.6	227.1	224.1	224.1	223.4	222.7
50°	241.3	228.6	218.9	213.7	208.5	207.0	206.2	205.5	204.0	204.0	204.7
52.5°	218.2	205.5	198.0	193.5	190.5	189.0	189.0	188.3	188.3	188.3	187.5
55°	192.8	182.3	176.3	174.8	173.3	172.6	171.8	170.4	169.6	171.1	169.6
57.5°	168.9	165.1	159.9	158.4	154.7	154.7	152.4	150.9	149.4	150.9	150.9
60°	150.2	144.9	142.0	137.5	134.5	131.5	127.8	127.0	125.5	124.8	124.0
62.5°	130.8	126.3	118.8	112.1	107.6	104.6	103.1	102.4	102.4	101.6	101.6
65°	109.1	98.6	94.9	92.6	91.9	91.2	89.7	88.9	89.7	88.9	89.7
67.5°	85.2	83.7	81.4	79.9	79.2	78.5	78.5	77.7	77.7	77.7	77.7
70°	74.0	70.2	69.5	68.0	68.0	67.2	67.2	67.2	67.2	66.5	68.0
72.5°	61.3	59.0	58.3	57.5	57.5	57.5	56.8	56.8	56.8	56.0	56.8
75°	50.1	49.3	47.8	47.8	47.1	47.8	47.1	47.1	46.3	47.1	47.1
77.5°	40.3	39.6	38.9	38.9	38.1	38.1	38.1	38.1	38.1	38.1	38.9
80°	30.6	29.9	29.1	29.9	29.1	29.9	29.1	29.1	29.9	29.1	29.1
82.5°	22.4	21.7	21.7	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
85°	13.4	12.7	12.7	13.4	12.7	13.4	12.7	12.7	12.7	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	22.5	23.7	24.9	26.1	26.7	26.9	27.4	27.9	28.3	28.8	28.3
92.5°	26.1	26.5	27.0	27.5	27.7	27.8	28.1	28.3	28.6	28.8	28.6
95°	42.8	44.0	45.1	46.3	46.9	46.8	46.6	46.3	46.1	45.9	46.1
97.5°	55.1	55.8	56.5	57.2	57.6	57.7	58.0	58.2	58.5	58.7	58.5
100°	62.7	64.6	66.5	68.4	69.3	69.5	70.0	70.5	71.0	71.5	71.0
102.5°	65.5	68.1	70.8	73.4	74.7	75.1	75.8	76.5	77.2	77.9	77.2
105°	67.7	70.3	72.9	75.5	76.8	77.3	78.2	79.2	80.1	81.1	80.1
107.5°	69.8	72.4	75.0	77.6	78.9	79.4	80.3	81.3	82.2	83.2	82.2
110°	163.0	139.3	115.6	91.9	80.0	80.5	81.4	82.4	83.3	84.3	83.3

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	439.8	337.6	235.4	133.2	82.1	82.5	83.2	83.9	84.6	85.3	84.6
115°	548.4	438.7	328.9	219.2	164.3	155.8	138.7	121.6	104.6	87.5	104.6
117.5°	682.0	648.1	614.2	580.3	563.3	532.2	470.1	408.0	345.9	283.8	345.9
120°	784.8	787.7	790.5	793.4	794.8	778.8	746.8	714.8	682.8	650.8	682.8
122.5°	846.3	847.8	849.2	850.7	851.4	851.5	851.7	852.0	852.2	852.4	852.2
125°	903.2	904.8	906.5	908.2	909.0	909.4	910.1	910.8	911.5	912.2	911.5
127.5°	956.2	958.5	960.9	963.2	964.4	964.5	964.8	965.0	965.3	965.5	965.3
130°	1006.5	1009.1	1011.7	1014.3	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8
132.5°	1056.2	1058.4	1060.5	1062.6	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8
135°	1102.3	1104.7	1107.0	1109.4	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0
137.5°	1146.1	1148.4	1150.8	1153.1	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8
140°	1188.4	1190.6	1192.7	1194.8	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8
142.5°	1227.7	1229.6	1231.5	1233.4	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2
145°	1263.8	1265.4	1267.1	1268.8	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4
147.5°	1296.4	1297.6	1298.7	1299.9	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2
150°	1325.4	1326.8	1328.3	1329.7	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2
152.5°	1352.0	1353.4	1354.9	1356.3	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2
155°	1375.5	1376.9	1378.4	1379.8	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9
157.5°	1396.0	1397.7	1399.3	1401.0	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2
160°	1413.9	1415.3	1416.8	1418.2	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1
162.5°	1430.2	1431.8	1433.5	1435.2	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5
165°	1443.0	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0
167.5°	1454.7	1456.4	1458.0	1459.7	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0
170°	1463.3	1464.9	1466.6	1468.3	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6
172.5°	1469.7	1471.3	1473.0	1474.7	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0
175°	1473.9	1475.6	1477.2	1478.9	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5
177.5°	1475.0	1476.6	1478.3	1480.0	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1133.4	1128.2	1126.7	1128.2	1126.7	1127.5	1122.2	1102.8	1108.0	1099.8	1104.3
5°	1197.7	1193.2	1183.5	1182.0	1180.5	1179.0	1171.5	1154.4	1147.6	1136.4	1135.7
7.5°	1259.0	1259.0	1251.5	1246.3	1239.5	1234.3	1224.6	1199.2	1188.7	1175.3	1167.8
10°	1319.5	1300.0	1308.3	1303.0	1286.6	1283.6	1265.7	1250.7	1230.6	1217.1	1205.2
12.5°	1362.8	1356.8	1349.4	1344.9	1340.4	1330.7	1318.7	1280.6	1270.2	1243.3	1229.8
15°	1361.3	1357.6	1359.8	1359.8	1358.3	1356.1	1346.4	1318.7	1300.8	1274.6	1251.5
17.5°	1288.1	1297.8	1307.5	1314.2	1329.2	1335.9	1344.9	1328.4	1317.2	1294.8	1270.2
20°	1160.3	1184.2	1212.6	1218.6	1232.1	1271.7	1289.6	1303.8	1308.3	1300.8	1280.6
22.5°	982.5	1002.7	1071.4	1069.9	1089.4	1136.4	1188.7	1231.3	1264.9	1283.6	1276.1
25°	769.6	798.0	834.6	862.2	925.7	996.0	1061.0	1128.9	1187.2	1238.8	1251.5
27.5°	582.0	619.4	648.5	685.1	717.3	800.2	883.9	990.0	1058.0	1155.8	1206.7
30°	470.7	487.9	517.0	534.2	549.9	613.4	708.3	812.9	932.4	1045.3	1132.7
32.5°	402.0	413.9	435.6	443.1	459.5	502.1	561.9	657.5	780.8	917.5	1032.6
35°	360.9	373.6	378.1	384.8	398.2	425.1	466.2	535.7	647.0	780.8	918.3
37.5°	325.8	332.5	345.2	349.7	354.2	374.3	402.0	450.5	524.5	634.3	786.8
40°	301.1	304.8	311.6	315.3	318.3	332.5	357.1	390.0	444.6	528.2	668.7
42.5°	275.0	279.4	283.9	288.4	292.1	303.3	318.3	349.7	386.3	449.8	551.4
45°	249.5	252.5	257.8	260.8	266.0	275.0	288.4	310.1	342.9	383.3	465.5
47.5°	226.4	230.1	232.4	236.1	239.8	249.5	262.3	276.4	303.3	342.9	402.7
50°	205.5	210.0	212.9	213.7	216.7	225.6	236.1	251.8	269.0	299.6	351.9
52.5°	190.5	191.3	193.5	196.5	195.8	201.0	210.7	222.7	240.6	265.2	303.3
55°	173.3	175.6	177.1	177.8	177.8	182.3	187.5	198.7	212.9	233.1	265.2
57.5°	151.7	153.9	158.4	159.9	162.1	164.4	166.6	174.1	186.0	205.5	231.6
60°	129.3	130.8	135.2	138.2	139.7	145.7	148.7	154.7	161.4	175.6	200.2
62.5°	103.9	105.3	107.6	110.6	113.6	122.5	130.0	136.0	141.2	150.9	171.1
65°	90.4	91.2	92.6	93.4	94.1	97.9	104.6	112.8	122.5	130.0	142.0
67.5°	78.5	79.2	79.9	81.4	82.2	82.9	85.9	88.2	97.9	108.3	117.3
70°	67.2	68.7	69.5	69.5	70.2	71.7	73.2	76.2	79.2	84.4	95.6
72.5°	56.8	57.5	59.0	59.0	59.0	60.5	62.0	63.5	65.0	68.0	72.5
75°	47.1	48.6	48.6	48.6	49.3	49.3	50.8	52.3	53.8	56.0	57.5
77.5°	38.9	38.9	38.9	38.9	39.6	39.6	40.3	41.8	42.6	43.3	44.8
80°	29.1	29.9	29.9	29.9	30.6	30.6	30.6	32.1	32.9	32.9	34.4
82.5°	21.7	21.7	21.7	22.4	21.7	22.4	22.4	23.2	22.4	23.2	23.9
85°	13.4	13.4	13.4	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	6.7	6.7
90°	27.9	27.4	26.9	26.7	26.1	24.9	23.7	22.5	21.3	19.4	17.5
92.5°	28.3	28.1	27.8	27.7	27.5	27.0	26.5	26.1	25.6	24.9	24.2
95°	46.3	46.6	46.8	46.9	46.3	45.1	44.0	42.8	41.6	39.9	38.3
97.5°	58.2	58.0	57.7	57.6	57.2	56.5	55.8	55.1	54.4	50.6	46.8
100°	70.5	70.0	69.5	69.3	68.4	66.5	64.6	62.7	60.8	56.8	52.8
102.5°	76.5	75.8	75.1	74.7	73.4	70.8	68.1	65.5	62.9	106.1	149.2
105°	79.2	78.2	77.3	76.8	75.5	72.9	70.3	67.7	65.1	129.8	194.5
107.5°	81.3	80.3	79.4	78.9	77.6	75.0	72.4	69.8	67.2	147.1	227.0
110°	82.4	81.4	80.5	80.0	91.9	115.6	139.3	163.0	186.7	255.2	323.7

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.9	83.2	82.5	82.1	133.2	235.4	337.6	439.8	542.0	546.0	550.0
115°	121.6	138.7	155.8	164.3	219.2	328.9	438.7	548.4	658.2	652.3	646.4
117.5°	408.0	470.1	532.2	563.3	580.3	614.2	648.1	682.0	715.9	711.9	707.8
120°	714.8	746.8	778.8	794.8	793.4	790.5	787.7	784.8	782.0	777.7	773.5
122.5°	852.0	851.7	851.5	851.4	850.7	849.2	847.8	846.3	844.9	840.2	835.4
125°	910.8	910.1	909.4	909.0	908.2	906.5	904.8	903.2	901.5	897.0	892.5
127.5°	965.0	964.8	964.5	964.4	963.2	960.9	958.5	956.2	953.8	950.2	946.7
130°	1015.0	1015.3	1015.5	1015.6	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7
132.5°	1063.1	1063.3	1063.6	1063.7	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9
135°	1109.4	1109.9	1110.4	1110.6	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6
137.5°	1152.5	1153.2	1153.9	1154.3	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9
140°	1193.0	1194.1	1195.3	1195.9	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1
142.5°	1231.4	1232.6	1233.8	1234.4	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6
145°	1266.6	1267.8	1269.0	1269.6	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1
147.5°	1298.1	1299.1	1300.0	1300.5	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1
150°	1327.4	1328.6	1329.8	1330.4	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4
152.5°	1352.9	1354.5	1356.2	1357.0	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5
155°	1375.8	1377.7	1379.6	1380.5	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4
157.5°	1397.1	1399.0	1400.9	1401.8	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1
160°	1414.7	1416.4	1418.1	1418.9	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7
162.5°	1430.7	1432.8	1434.9	1436.0	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1
165°	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9
167.5°	1455.2	1457.3	1459.4	1460.5	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7
170°	1463.8	1465.9	1468.0	1469.1	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7
172.5°	1470.2	1472.3	1474.4	1475.5	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1
175°	1473.8	1476.2	1478.5	1479.7	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3
177.5°	1475.5	1477.6	1479.7	1480.8	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1097.6	1093.8	1093.8	1091.6	1091.6	1079.6	1079.6	1083.4	1078.9	1073.7	1066.2
5°	1126.0	1117.7	1115.5	1112.5	1102.8	1087.9	1081.9	1079.6	1070.7	1059.5	1046.8
7.5°	1152.9	1139.4	1132.7	1126.0	1113.3	1092.3	1080.4	1072.2	1058.7	1041.5	1025.1
10°	1179.0	1161.8	1144.6	1136.4	1118.5	1092.3	1075.2	1061.7	1042.3	1019.1	996.0
12.5°	1202.9	1167.1	1164.1	1147.6	1121.5	1091.6	1065.4	1046.0	1021.4	994.5	967.6
15°	1223.8	1187.2	1169.3	1154.4	1120.0	1082.6	1055.0	1031.1	998.2	967.6	934.7
17.5°	1234.3	1194.7	1182.7	1158.1	1123.0	1074.4	1037.0	1007.9	972.0	935.4	898.1
20°	1244.8	1198.4	1179.0	1161.8	1114.0	1058.7	1016.9	983.3	943.7	900.3	859.2
22.5°	1250.0	1198.4	1175.3	1151.4	1105.0	1041.5	992.2	952.6	906.3	862.2	812.9
25°	1241.0	1194.0	1166.3	1141.7	1089.4	1020.6	963.8	919.0	869.7	819.6	769.6
27.5°	1218.6	1183.5	1151.4	1126.0	1067.7	993.7	933.9	883.1	832.3	776.3	725.5
30°	1176.8	1161.1	1135.7	1107.3	1043.8	969.8	898.8	846.5	790.5	734.5	681.4
32.5°	1111.8	1125.2	1108.8	1084.1	1015.4	936.9	861.5	808.4	747.2	686.6	638.1
35°	1032.6	1080.4	1071.4	1054.2	985.5	901.8	826.4	762.1	700.8	639.6	591.0
37.5°	945.9	1018.4	1025.8	1015.4	951.1	866.0	783.0	720.3	657.5	595.5	546.2
40°	827.1	938.4	962.3	966.8	915.3	822.6	735.9	674.7	612.7	552.1	492.4
42.5°	718.0	858.5	888.4	907.0	869.7	780.0	692.6	624.6	563.4	508.8	449.0
45°	615.7	762.1	810.7	834.6	818.1	731.5	641.1	577.5	521.5	471.5	413.9
47.5°	510.3	657.5	725.5	763.6	763.6	682.2	591.7	529.0	475.2	432.6	381.8
50°	440.1	562.6	632.8	682.9	696.3	632.1	546.9	485.6	434.8	388.5	349.7
52.5°	375.1	484.9	543.2	595.5	634.3	578.3	496.9	441.6	391.5	348.2	317.5
55°	324.3	406.5	459.5	517.0	560.4	523.8	448.3	394.5	351.2	315.3	289.1
57.5°	275.7	347.4	390.8	441.6	487.9	460.2	399.7	353.4	315.3	283.9	260.8
60°	234.6	292.9	326.5	366.1	423.6	404.2	354.2	311.6	280.9	252.5	233.1
62.5°	199.5	245.8	274.2	302.6	354.9	345.9	307.1	274.2	248.1	224.1	207.7
65°	163.6	201.7	224.1	248.8	290.6	294.4	263.0	239.8	215.9	195.0	180.1
67.5°	132.2	162.1	182.3	203.2	236.8	247.3	225.6	206.2	186.0	168.9	155.4
70°	106.8	127.8	142.7	159.1	186.8	199.5	188.3	174.8	158.4	144.2	132.2
72.5°	84.4	97.9	106.8	119.5	142.0	154.7	153.9	142.0	130.0	120.3	110.6
75°	62.0	72.5	79.9	88.2	106.1	118.1	121.0	115.8	103.9	96.4	88.9
77.5°	47.1	53.0	56.8	62.8	75.5	85.9	90.4	88.9	80.7	74.7	69.5
80°	35.9	37.4	38.9	41.1	51.6	61.3	64.3	63.5	59.0	56.8	50.8
82.5°	25.4	26.2	26.9	27.6	31.4	39.6	42.6	44.1	40.3	38.1	32.9
85°	14.9	15.7	15.7	17.2	17.9	20.2	25.4	25.4	24.7	21.7	20.9
87.5°	7.5	7.5	6.7	6.7	7.5	8.2	9.7	11.2	9.7	9.0	8.2
90°	15.6	13.7	12.8	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	23.5	22.8	22.4	22.9	23.8	24.8	25.7	26.7	25.7	24.8	23.8
95°	36.6	34.9	34.1	38.0	45.8	53.7	61.5	69.3	61.5	53.7	45.8
97.5°	43.0	39.2	37.3	47.0	66.5	85.9	105.4	124.8	105.4	85.9	66.5
100°	48.7	44.7	42.7	58.9	91.4	123.9	156.3	188.8	156.3	123.9	91.4
102.5°	192.4	235.5	257.1	257.3	257.8	258.3	258.7	259.2	258.7	258.3	257.8
105°	259.2	323.9	356.3	352.7	345.6	338.5	331.4	324.3	331.4	338.5	345.6
107.5°	306.9	386.8	426.7	423.7	417.8	411.9	406.0	400.1	406.0	411.9	417.8
110°	392.2	460.7	495.0	492.5	487.5	482.6	477.6	472.6	477.6	482.6	487.5

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	554.1	558.1	560.1	558.0	553.7	549.4	545.2	540.9	545.2	549.4	553.7
115°	640.5	634.6	631.6	629.6	625.5	621.5	617.4	613.4	617.4	621.5	625.5
117.5°	703.8	699.7	697.7	695.3	690.6	685.9	681.1	676.4	681.1	685.9	690.6
120°	769.2	764.9	762.8	761.0	757.5	753.9	750.4	746.8	750.4	753.9	757.5
122.5°	830.7	826.0	823.6	821.7	817.9	814.1	810.3	806.5	810.3	814.1	817.9
125°	888.0	883.5	881.2	879.7	876.6	873.5	870.5	867.4	870.5	873.5	876.6
127.5°	943.1	939.6	937.8	936.1	932.8	929.5	926.1	922.8	926.1	929.5	932.8
130°	996.1	993.5	992.2	990.3	986.5	982.7	978.9	975.1	978.9	982.7	986.5
132.5°	1046.2	1043.6	1042.3	1040.8	1037.7	1034.6	1031.5	1028.4	1031.5	1034.6	1037.7
135°	1093.5	1091.4	1090.3	1088.4	1084.6	1080.9	1077.1	1073.3	1077.1	1080.9	1084.6
137.5°	1136.6	1134.2	1133.0	1131.6	1128.7	1125.9	1123.0	1120.2	1123.0	1125.9	1128.7
140°	1178.5	1175.9	1174.6	1173.7	1171.8	1169.9	1168.0	1166.1	1168.0	1169.9	1171.8
142.5°	1216.5	1213.4	1211.9	1211.1	1209.4	1207.8	1206.1	1204.5	1206.1	1207.8	1209.4
145°	1250.0	1246.0	1244.0	1244.1	1244.3	1244.6	1244.8	1245.0	1244.8	1244.6	1244.3
147.5°	1283.1	1279.0	1277.0	1277.4	1278.1	1278.8	1279.5	1280.2	1279.5	1278.8	1278.1
150°	1312.6	1308.8	1306.9	1307.7	1309.4	1311.1	1312.7	1314.4	1312.7	1311.1	1309.4
152.5°	1339.9	1336.4	1334.6	1335.6	1337.5	1339.4	1341.3	1343.2	1341.3	1339.4	1337.5
155°	1365.6	1362.7	1361.3	1362.4	1364.5	1366.6	1368.8	1370.9	1368.8	1366.6	1364.5
157.5°	1388.0	1385.9	1384.8	1385.7	1387.6	1389.5	1391.4	1393.3	1391.4	1389.5	1387.6
160°	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1411.1	1409.7	1408.2
162.5°	1425.0	1423.8	1423.2	1423.9	1425.3	1426.8	1428.2	1429.6	1428.2	1426.8	1425.3
165°	1439.2	1438.5	1438.1	1438.8	1440.2	1441.7	1443.1	1444.5	1443.1	1441.7	1440.2
167.5°	1451.0	1450.3	1449.9	1450.6	1452.0	1453.5	1454.9	1456.3	1454.9	1453.5	1452.0
170°	1460.2	1459.7	1459.5	1460.2	1461.6	1463.1	1464.5	1465.9	1464.5	1463.1	1461.6
172.5°	1466.6	1466.1	1465.9	1466.6	1468.0	1469.5	1470.9	1472.3	1470.9	1469.5	1468.0
175°	1470.8	1470.3	1470.1	1470.9	1472.6	1474.3	1475.9	1477.6	1475.9	1474.3	1472.6
177.5°	1472.6	1472.4	1472.3	1473.1	1474.8	1476.4	1478.1	1479.7	1478.1	1476.4	1474.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1063.2	1063.9	1066.2	1059.5	1049.0	1044.5	1031.1	1028.8	1026.6	1026.6	1028.8
5°	1039.3	1036.3	1037.0	1024.3	1009.4	1000.4	981.8	984.7	975.0	969.1	970.6
7.5°	1013.1	1004.9	1004.2	987.7	969.1	952.6	933.2	928.7	919.7	909.3	904.8
10°	980.3	974.3	963.1	944.4	920.5	907.0	880.9	865.2	863.0	847.3	841.3
12.5°	946.6	936.2	925.0	898.8	871.9	850.3	830.8	813.7	801.7	788.2	779.3
15°	907.8	895.1	882.4	854.7	823.4	801.7	772.6	747.2	712.0	684.4	668.7
17.5°	865.2	851.0	833.8	803.2	772.6	742.7	688.9	659.0	634.3	617.9	608.2
20°	821.1	805.4	788.2	757.6	704.6	652.3	622.4	599.2	584.3	567.8	555.9
22.5°	774.8	758.4	739.7	691.9	635.8	599.2	576.1	554.4	532.7	523.8	517.8
25°	731.5	716.5	692.6	627.6	583.5	549.9	523.8	509.6	498.4	486.4	475.2
27.5°	686.6	659.0	625.4	570.8	543.2	508.8	490.1	479.7	460.2	452.0	446.8
30°	632.8	602.2	570.1	531.2	499.1	475.2	458.0	440.8	429.6	421.4	412.4
32.5°	578.3	549.2	529.0	488.6	464.7	440.1	423.6	413.2	396.7	391.5	387.8
35°	531.2	506.6	488.6	455.8	433.3	410.9	399.0	383.3	372.8	363.1	357.1
37.5°	484.9	471.5	452.8	425.1	401.2	383.3	366.9	361.6	347.4	342.2	336.2
40°	452.8	432.6	416.9	393.0	372.8	353.4	342.9	331.0	321.3	313.1	310.8
42.5°	413.9	399.0	390.0	363.9	342.9	331.7	319.0	305.6	298.1	291.4	283.2
45°	384.8	371.3	358.6	337.7	319.0	304.8	293.6	284.7	272.0	269.0	256.3
47.5°	354.2	340.7	331.0	310.1	292.9	279.4	271.2	259.3	248.8	242.1	236.1
50°	323.5	312.3	303.3	285.4	270.5	256.3	245.1	233.1	228.6	217.4	213.7
52.5°	294.4	286.9	277.2	260.0	245.1	233.1	221.2	211.4	204.7	198.7	194.3
55°	269.7	257.8	253.3	234.6	221.9	209.2	198.7	192.8	184.5	180.8	177.1
57.5°	242.1	235.4	227.9	213.7	199.5	187.5	180.1	171.1	166.6	162.1	159.1
60°	218.2	208.5	202.5	190.5	177.8	166.6	159.9	153.2	147.2	143.5	137.5
62.5°	190.5	183.1	179.3	166.6	156.2	145.7	139.7	133.0	128.5	121.8	114.3
65°	166.6	160.6	156.2	145.7	136.0	126.3	120.3	112.1	106.1	102.4	101.6
67.5°	145.7	141.2	134.5	124.8	115.1	107.6	100.9	94.1	93.4	91.9	91.9
70°	122.5	118.1	114.3	103.9	95.6	87.4	85.9	83.7	81.4	80.7	79.2
72.5°	102.4	98.6	94.1	85.2	77.0	74.7	73.2	71.7	69.5	68.7	68.0
75°	82.9	77.7	74.7	66.5	64.3	62.8	61.3	59.0	57.5	56.8	55.3
77.5°	63.5	58.3	58.3	53.8	52.3	50.1	48.6	47.1	46.3	44.8	44.8
80°	44.8	44.8	43.3	41.1	38.9	38.1	35.9	35.1	34.4	35.1	33.6
82.5°	32.9	29.9	29.9	28.4	26.9	26.2	24.7	24.7	23.9	23.9	23.9
85°	18.7	18.7	17.9	16.4	15.7	15.7	14.9	14.9	14.2	14.2	13.4
87.5°	7.5	6.7	7.5	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	11.5	12.8	13.7	15.6	17.5	19.4	21.3	22.5	23.7	24.9	26.1
92.5°	22.9	22.4	22.8	23.5	24.2	24.9	25.6	26.1	26.5	27.0	27.5
95°	38.0	34.1	34.9	36.6	38.3	39.9	41.6	42.8	44.0	45.1	46.3
97.5°	47.0	37.3	39.2	43.0	46.8	50.6	54.4	55.1	55.8	56.5	57.2
100°	58.9	42.7	44.7	48.7	52.8	56.8	60.8	62.7	64.6	66.5	68.4
102.5°	257.3	257.1	235.5	192.4	149.2	106.1	62.9	65.5	68.1	70.8	73.4
105°	352.7	356.3	323.9	259.2	194.5	129.8	65.1	67.7	70.3	72.9	75.5
107.5°	423.7	426.7	386.8	306.9	227.0	147.1	67.2	69.8	72.4	75.0	77.6
110°	492.5	495.0	460.7	392.2	323.7	255.2	186.7	163.0	139.3	115.6	91.9

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	558.0	560.1	558.1	554.1	550.0	546.0	542.0	439.8	337.6	235.4	133.2
115°	629.6	631.6	634.6	640.5	646.4	652.3	658.2	548.4	438.7	328.9	219.2
117.5°	695.3	697.7	699.7	703.8	707.8	711.9	715.9	682.0	648.1	614.2	580.3
120°	761.0	762.8	764.9	769.2	773.5	777.7	782.0	784.8	787.7	790.5	793.4
122.5°	821.7	823.6	826.0	830.7	835.4	840.2	844.9	846.3	847.8	849.2	850.7
125°	879.7	881.2	883.5	888.0	892.5	897.0	901.5	903.2	904.8	906.5	908.2
127.5°	936.1	937.8	939.6	943.1	946.7	950.2	953.8	956.2	958.5	960.9	963.2
130°	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9	1006.5	1009.1	1011.7	1014.3
132.5°	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1	1056.2	1058.4	1060.5	1062.6
135°	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9	1102.3	1104.7	1107.0	1109.4
137.5°	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7	1146.1	1148.4	1150.8	1153.1
140°	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3	1188.4	1190.6	1192.7	1194.8
142.5°	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8	1227.7	1229.6	1231.5	1233.4
145°	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1	1263.8	1265.4	1267.1	1268.8
147.5°	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2	1296.4	1297.6	1298.7	1299.9
150°	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0	1325.4	1326.8	1328.3	1329.7
152.5°	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6	1352.0	1353.4	1354.9	1356.3
155°	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1	1375.5	1376.9	1378.4	1379.8
157.5°	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4	1396.0	1397.7	1399.3	1401.0
160°	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1413.9	1415.3	1416.8	1418.2
162.5°	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5	1430.2	1431.8	1433.5	1435.2
165°	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3	1443.0	1444.6	1446.3	1448.0
167.5°	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1	1454.7	1456.4	1458.0	1459.7
170°	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6	1463.3	1464.9	1466.6	1468.3
172.5°	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0	1469.7	1471.3	1473.0	1474.7
175°	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3	1473.9	1475.6	1477.2	1478.9
177.5°	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3	1475.0	1476.6	1478.3	1480.0
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1028.8	1027.3	1022.9	1024.3	1022.1	1022.1	1020.6	1020.6	1020.6	1024.3	1022.1
5°	972.8	967.6	962.3	960.1	957.9	955.6	955.6	954.9	961.6	960.1	966.1
7.5°	903.3	901.8	891.4	891.4	887.6	886.1	889.9	890.6	891.4	892.8	896.6
10°	841.3	837.6	822.6	824.1	821.9	818.9	821.1	819.6	824.9	826.4	824.9
12.5°	768.1	761.3	744.9	736.7	727.7	721.0	729.2	723.2	744.2	750.1	766.6
15°	670.9	658.2	647.0	647.0	638.8	632.8	636.6	643.3	647.8	654.5	657.5
17.5°	605.9	600.7	591.7	586.5	584.3	582.0	582.0	585.0	594.7	594.0	600.0
20°	550.7	547.7	543.2	536.5	534.2	532.7	532.7	532.7	539.4	545.4	549.2
22.5°	512.5	510.3	507.3	498.4	493.9	492.4	496.1	498.4	503.6	508.1	511.8
25°	474.4	469.2	464.0	461.0	458.8	458.8	460.2	461.0	463.2	465.5	470.0
27.5°	443.1	439.3	431.9	423.6	423.6	421.4	422.9	424.4	429.6	437.1	440.8
30°	407.9	407.2	404.2	401.2	398.2	396.7	399.7	402.0	402.7	406.5	406.5
32.5°	382.5	377.3	372.1	369.1	367.6	366.9	367.6	370.6	370.6	375.1	380.3
35°	357.1	354.2	348.9	343.7	342.2	338.5	341.4	344.4	349.7	351.9	354.2
37.5°	329.5	325.8	323.5	322.0	319.0	319.8	317.5	322.0	326.5	325.8	327.3
40°	308.6	301.9	295.1	294.4	293.6	292.9	292.9	293.6	296.6	299.6	304.1
42.5°	281.7	279.4	273.5	267.5	266.0	264.5	263.0	266.0	272.0	277.2	279.4
45°	254.0	251.0	249.5	245.1	242.1	241.3	239.8	243.6	248.8	251.0	252.5
47.5°	228.6	227.9	223.4	224.1	221.9	222.7	221.9	224.1	224.1	226.4	227.9
50°	211.4	209.2	207.0	205.5	203.2	203.2	202.5	203.2	206.2	209.2	208.5
52.5°	194.3	190.5	189.8	189.0	187.5	189.0	186.8	187.5	190.5	192.0	191.3
55°	174.1	173.3	171.8	170.4	169.6	168.9	168.9	168.9	171.8	174.1	174.8
57.5°	158.4	154.7	151.7	151.7	148.7	147.9	149.4	150.2	152.4	153.9	155.4
60°	136.7	135.2	130.8	128.5	124.0	123.3	123.3	126.3	130.0	135.2	136.7
62.5°	113.6	111.3	110.6	110.6	110.6	110.6	110.6	110.6	110.6	111.3	111.3
65°	100.9	101.6	100.9	100.1	100.9	100.9	100.1	100.1	100.1	100.9	101.6
67.5°	90.4	89.7	90.4	89.7	88.9	88.9	88.2	88.9	89.7	90.4	90.4
70°	78.5	78.5	77.7	78.5	77.7	77.0	76.2	76.2	77.7	78.5	78.5
72.5°	67.2	67.2	66.5	66.5	65.0	65.0	65.7	65.0	65.0	67.2	67.2
75°	56.0	55.3	54.5	54.5	53.8	53.8	53.8	53.0	54.5	54.5	55.3
77.5°	44.1	44.1	44.1	43.3	43.3	42.6	42.6	43.3	43.3	43.3	44.1
80°	33.6	33.6	33.6	32.9	32.1	32.1	32.1	32.1	32.1	32.9	32.1
82.5°	23.2	23.2	23.2	23.2	23.2	22.4	22.4	22.4	23.2	23.2	22.4
85°	14.2	13.4	14.2	14.2	13.4	14.2	13.4	13.4	12.7	12.7	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	26.7	26.9	27.4	27.9	28.3	28.8	28.3	27.9	27.4	26.9	26.7
92.5°	27.7	27.8	28.1	28.3	28.6	28.8	28.6	28.3	28.1	27.8	27.7
95°	46.9	46.8	46.6	46.3	46.1	45.9	46.1	46.3	46.6	46.8	46.9
97.5°	57.6	57.7	58.0	58.2	58.5	58.7	58.5	58.2	58.0	57.7	57.6
100°	69.3	69.5	70.0	70.5	71.0	71.5	71.0	70.5	70.0	69.5	69.3
102.5°	74.7	75.1	75.8	76.5	77.2	77.9	77.2	76.5	75.8	75.1	74.7
105°	76.8	77.3	78.2	79.2	80.1	81.1	80.1	79.2	78.2	77.3	76.8
107.5°	78.9	79.4	80.3	81.3	82.2	83.2	82.2	81.3	80.3	79.4	78.9
110°	80.0	80.5	81.4	82.4	83.3	84.3	83.3	82.4	81.4	80.5	80.0

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	82.1	82.5	83.2	83.9	84.6	85.3	84.6	83.9	83.2	82.5	82.1
115°	164.3	155.8	138.7	121.6	104.6	87.5	104.6	121.6	138.7	155.8	164.3
117.5°	563.3	532.2	470.1	408.0	345.9	283.8	345.9	408.0	470.1	532.2	563.3
120°	794.8	778.8	746.8	714.8	682.8	650.8	682.8	714.8	746.8	778.8	794.8
122.5°	851.4	851.5	851.7	852.0	852.2	852.4	852.2	852.0	851.7	851.5	851.4
125°	909.0	909.4	910.1	910.8	911.5	912.2	911.5	910.8	910.1	909.4	909.0
127.5°	964.4	964.5	964.8	965.0	965.3	965.5	965.3	965.0	964.8	964.5	964.4
130°	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8	1015.0	1015.3	1015.5	1015.6
132.5°	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8	1063.1	1063.3	1063.6	1063.7
135°	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0	1109.4	1109.9	1110.4	1110.6
137.5°	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8	1152.5	1153.2	1153.9	1154.3
140°	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8	1193.0	1194.1	1195.3	1195.9
142.5°	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2	1231.4	1232.6	1233.8	1234.4
145°	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4	1266.6	1267.8	1269.0	1269.6
147.5°	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2	1298.1	1299.1	1300.0	1300.5
150°	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2	1327.4	1328.6	1329.8	1330.4
152.5°	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2	1352.9	1354.5	1356.2	1357.0
155°	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9	1375.8	1377.7	1379.6	1380.5
157.5°	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2	1397.1	1399.0	1400.9	1401.8
160°	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1	1414.7	1416.4	1418.1	1418.9
162.5°	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5	1430.7	1432.8	1434.9	1436.0
165°	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0	1444.6	1446.3	1448.0	1448.8
167.5°	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0	1455.2	1457.3	1459.4	1460.5
170°	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6	1463.8	1465.9	1468.0	1469.1
172.5°	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0	1470.2	1472.3	1474.4	1475.5
175°	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5	1473.8	1476.2	1478.5	1479.7
177.5°	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3	1475.5	1477.6	1479.7	1480.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1024.3	1028.1	1026.6	1018.4	1026.6	1028.8	1033.3	1037.8	1040.8	1045.3	1049.0
5°	960.1	967.6	972.0	967.6	982.5	984.7	995.2	1001.2	1010.2	1017.6	1023.6
7.5°	899.6	905.6	914.5	916.0	925.0	935.4	950.4	965.3	979.5	987.0	993.7
10°	834.6	845.0	858.5	855.5	868.9	885.4	901.1	925.0	936.9	950.4	962.3
12.5°	769.6	776.3	794.2	800.2	819.6	832.3	854.0	868.9	898.8	914.5	925.0
15°	656.0	683.6	706.1	733.0	758.4	782.3	801.7	828.6	854.7	866.7	883.9
17.5°	604.4	617.1	630.6	644.0	676.9	719.5	753.9	783.0	805.4	821.1	841.3
20°	550.7	563.4	578.3	591.0	611.2	641.8	684.4	734.5	761.3	777.8	797.2
22.5°	512.5	524.5	534.2	545.4	561.1	583.5	615.7	677.7	713.5	733.7	750.9
25°	471.5	486.4	496.9	505.1	517.8	542.4	568.6	603.7	668.0	683.6	707.6
27.5°	443.1	447.5	459.5	472.2	484.9	498.4	525.2	555.1	598.5	632.8	662.0
30°	409.4	420.6	431.9	437.1	448.3	467.7	484.2	516.3	549.9	576.8	611.9
32.5°	384.0	390.8	398.2	410.9	421.4	434.8	451.3	478.2	506.6	523.8	550.7
35°	355.6	360.1	375.8	381.0	391.5	405.0	421.4	442.3	472.9	486.4	505.8
37.5°	328.7	339.2	343.7	355.6	365.4	378.8	390.8	414.7	434.8	450.5	468.5
40°	307.8	312.3	320.5	331.0	339.2	349.7	364.6	381.8	403.5	416.2	431.9
42.5°	282.4	286.2	296.6	302.6	316.0	325.8	334.7	355.6	375.1	384.8	400.5
45°	254.8	263.7	270.5	282.4	289.9	301.9	313.1	328.0	345.9	357.1	366.1
47.5°	230.9	239.8	246.6	257.8	269.7	275.0	286.9	302.6	319.0	328.0	340.7
50°	211.4	214.4	227.1	232.4	245.1	255.5	263.7	277.2	295.1	300.4	310.8
52.5°	192.8	195.0	203.2	210.0	221.2	230.1	240.6	253.3	268.2	276.4	284.7
55°	176.3	177.8	181.6	189.0	196.5	207.7	217.4	229.4	242.1	251.0	258.5
57.5°	157.6	160.6	163.6	168.1	175.6	186.0	196.5	207.7	218.2	224.1	233.9
60°	136.0	140.5	145.7	150.9	156.2	163.6	175.6	186.0	195.8	201.0	208.5
62.5°	112.8	121.8	126.3	132.2	136.7	143.5	152.4	164.4	171.1	177.8	183.8
65°	101.6	102.4	103.1	109.1	117.3	124.0	132.2	141.2	151.7	156.2	160.6
67.5°	90.4	91.2	92.6	93.4	96.4	103.9	112.8	122.5	130.8	133.7	138.2
70°	79.2	79.2	82.2	82.9	83.7	84.4	91.9	101.6	109.1	112.8	118.1
72.5°	67.2	68.0	69.5	70.2	71.7	73.2	75.5	80.7	89.7	93.4	99.4
75°	55.3	56.0	56.8	57.5	59.8	60.5	62.8	65.7	69.5	74.0	77.7
77.5°	44.1	44.1	44.8	46.3	47.8	48.6	50.8	52.3	53.8	56.0	59.0
80°	32.9	33.6	33.6	35.1	35.1	35.9	36.6	38.9	40.3	41.8	43.3
82.5°	22.4	23.9	23.9	23.9	24.7	25.4	26.2	26.2	27.6	28.4	30.6
85°	13.4	14.2	14.2	14.2	13.4	14.9	14.9	15.7	15.7	15.7	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	26.1	24.9	23.7	22.5	21.3	19.4	17.5	15.6	13.7	12.8	11.5
92.5°	27.5	27.0	26.5	26.1	25.6	24.9	24.2	23.5	22.8	22.4	22.9
95°	46.3	45.1	44.0	42.8	41.6	39.9	38.3	36.6	34.9	34.1	38.0
97.5°	57.2	56.5	55.8	55.1	54.4	50.6	46.8	43.0	39.2	37.3	47.0
100°	68.4	66.5	64.6	62.7	60.8	56.8	52.8	48.7	44.7	42.7	58.9
102.5°	73.4	70.8	68.1	65.5	62.9	106.1	149.2	192.4	235.5	257.1	257.3
105°	75.5	72.9	70.3	67.7	65.1	129.8	194.5	259.2	323.9	356.3	352.7
107.5°	77.6	75.0	72.4	69.8	67.2	147.1	227.0	306.9	386.8	426.7	423.7
110°	91.9	115.6	139.3	163.0	186.7	255.2	323.7	392.2	460.7	495.0	492.5

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	133.2	235.4	337.6	439.8	542.0	546.0	550.0	554.1	558.1	560.1	558.0
115°	219.2	328.9	438.7	548.4	658.2	652.3	646.4	640.5	634.6	631.6	629.6
117.5°	580.3	614.2	648.1	682.0	715.9	711.9	707.8	703.8	699.7	697.7	695.3
120°	793.4	790.5	787.7	784.8	782.0	777.7	773.5	769.2	764.9	762.8	761.0
122.5°	850.7	849.2	847.8	846.3	844.9	840.2	835.4	830.7	826.0	823.6	821.7
125°	908.2	906.5	904.8	903.2	901.5	897.0	892.5	888.0	883.5	881.2	879.7
127.5°	963.2	960.9	958.5	956.2	953.8	950.2	946.7	943.1	939.6	937.8	936.1
130°	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7	996.1	993.5	992.2	990.3
132.5°	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9	1046.2	1043.6	1042.3	1040.8
135°	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6	1093.5	1091.4	1090.3	1088.4
137.5°	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9	1136.6	1134.2	1133.0	1131.6
140°	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1	1178.5	1175.9	1174.6	1173.7
142.5°	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6	1216.5	1213.4	1211.9	1211.1
145°	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1	1250.0	1246.0	1244.0	1244.1
147.5°	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1	1283.1	1279.0	1277.0	1277.4
150°	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4	1312.6	1308.8	1306.9	1307.7
152.5°	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5	1339.9	1336.4	1334.6	1335.6
155°	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4	1365.6	1362.7	1361.3	1362.4
157.5°	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1	1388.0	1385.9	1384.8	1385.7
160°	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8
162.5°	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1	1425.0	1423.8	1423.2	1423.9
165°	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9	1439.2	1438.5	1438.1	1438.8
167.5°	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7	1451.0	1450.3	1449.9	1450.6
170°	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7	1460.2	1459.7	1459.5	1460.2
172.5°	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1	1466.6	1466.1	1465.9	1466.6
175°	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3	1470.8	1470.3	1470.1	1470.9
177.5°	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9	1472.6	1472.4	1472.3	1473.1
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1075.2	1075.2	1075.2	1075.2
2.5°	1055.7	1053.5	1066.9	1081.9
5°	1034.1	1037.8	1055.0	1075.9
7.5°	1011.6	1019.9	1040.0	1067.7
10°	980.3	995.2	1025.8	1054.2
12.5°	949.6	969.8	998.9	1032.6
15°	915.3	937.7	973.5	1013.9
17.5°	877.2	902.6	944.4	988.5
20°	836.8	870.4	914.5	962.3
22.5°	792.0	832.3	877.9	931.0
25°	748.6	792.7	838.3	899.6
27.5°	706.1	749.4	800.2	862.2
30°	663.5	703.1	757.6	824.1
32.5°	617.9	659.0	716.5	784.5
35°	576.1	617.1	670.9	738.2
37.5°	531.2	575.3	626.9	696.3
40°	478.9	530.5	580.5	647.0
42.5°	435.6	490.1	538.7	601.5
45°	401.2	452.8	493.1	554.4
47.5°	369.1	410.9	452.0	508.8
50°	338.5	370.6	413.2	464.0
52.5°	307.1	334.7	371.3	419.2
55°	278.7	304.8	337.7	374.3
57.5°	252.5	271.2	304.1	337.0
60°	223.4	242.8	268.2	295.9
62.5°	198.7	213.7	237.6	260.8
65°	172.6	186.8	204.7	226.4
67.5°	148.7	161.4	175.6	192.8
70°	127.0	136.7	147.2	162.1
72.5°	103.9	114.3	124.0	136.0
75°	85.2	89.7	97.9	106.1
77.5°	65.7	71.7	76.2	82.9
80°	47.1	52.3	53.8	59.0
82.5°	31.4	34.4	37.4	38.9
85°	17.9	19.4	22.4	23.2
87.5°	6.7	7.5	9.0	10.5
90°	8.9	6.3	3.7	1.1
92.5°	23.8	24.8	25.7	26.7
95°	45.8	53.7	61.5	69.3
97.5°	66.5	85.9	105.4	124.8
100°	91.4	123.9	156.3	188.8
102.5°	257.8	258.3	258.7	259.2
105°	345.6	338.5	331.4	324.3
107.5°	417.8	411.9	406.0	400.1
110°	487.5	482.6	477.6	472.6

TEST NUMBER: P1008396

CATALOG NUMBER: S122RDIP-B485D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	553.7	549.4	545.2	540.9
115°	625.5	621.5	617.4	613.4
117.5°	690.6	685.9	681.1	676.4
120°	757.5	753.9	750.4	746.8
122.5°	817.9	814.1	810.3	806.5
125°	876.6	873.5	870.5	867.4
127.5°	932.8	929.5	926.1	922.8
130°	986.5	982.7	978.9	975.1
132.5°	1037.7	1034.6	1031.5	1028.4
135°	1084.6	1080.9	1077.1	1073.3
137.5°	1128.7	1125.9	1123.0	1120.2
140°	1171.8	1169.9	1168.0	1166.1
142.5°	1209.4	1207.8	1206.1	1204.5
145°	1244.3	1244.6	1244.8	1245.0
147.5°	1278.1	1278.8	1279.5	1280.2
150°	1309.4	1311.1	1312.7	1314.4
152.5°	1337.5	1339.4	1341.3	1343.2
155°	1364.5	1366.6	1368.8	1370.9
157.5°	1387.6	1389.5	1391.4	1393.3
160°	1408.2	1409.7	1411.1	1412.5
162.5°	1425.3	1426.8	1428.2	1429.6
165°	1440.2	1441.7	1443.1	1444.5
167.5°	1452.0	1453.5	1454.9	1456.3
170°	1461.6	1463.1	1464.5	1465.9
172.5°	1468.0	1469.5	1470.9	1472.3
175°	1472.6	1474.3	1475.9	1477.6
177.5°	1474.8	1476.4	1478.1	1479.7
180°	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)