

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008426

Luminaire Tested: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008426
REPORT IS A COMBINATION OF REPORTS P988346 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4702.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40	40	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	35	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	31	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	27	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	24	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	22	22	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	19	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	18	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	16	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17020	17020	17020	17020
5°	17058	18077	17117	14441
10°	16870	19107	16990	11926
15°	16505	19113	16785	8958
20°	16064	15799	16415	7391
25°	15531	9873	15866	6288
30°	14849	6320	15252	5413
35°	14020	4857	14473	4633
40°	13095	4083	13655	4052
45°	12108	3476	12613	3401
50°	11096	2953	11612	2942
55°	9974	2566	10512	2533
60°	8979	1957	9455	1934
65°	8048	1472	8525	1671
70°	7020	1176	7570	1362
75°	5935	902	6478	1030
80°	4710	612	5070	675
85°	3277	315	3588	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15568 cd/sqm

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	2.2
10°-20°	284.7	6.1
20°-30°	366.3	7.8
30°-40°	347.6	7.4
40°-50°	297.9	6.3
50°-60°	226.8	4.8
60°-70°	143.1	3.0
70°-80°	71.4	1.5
80°-90°	20.0	0.4
90°-100°	32.0	0.7
100°-110°	119.2	2.5
110°-120°	316.1	6.7
120°-130°	524.2	11.1
130°-140°	556.8	11.8
140°-150°	517.5	11.0
150°-160°	416.1	8.8
160°-170°	268.1	5.7
170°-180°	92.3	2.0
0°-30°	753.0	16.0
0°-40°	1100.5	23.4
0°-60°	1625.2	34.6
0°-90°	1859.7	39.6
90°-120°	467.2	9.9
90°-150°	2065.8	43.9
90°-180°	2842.0	60.4
0°-180°	4702.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1076	1196	1080	956	1076	102
15°	1014	1350	1031	633	1014	285
25°	900	720	919	459	900	413
35°	738	355	762	338	738	462
45°	554	247	578	241	554	428
55°	374	171	394	169	374	337
65°	226	89	240	101	226	225
75°	106	47	116	54	106	115
85°	23	13	25	14	23	26
90°	1	19	1	19	1	4
95°	46	30	46	30	46	54
105°	213	53	213	53	213	228
115°	403	58	403	58	403	397
125°	570	600	570	600	570	509
135°	706	729	706	729	706	545
145°	819	831	819	831	819	512
155°	902	902	902	902	902	415
165°	950	948	950	948	950	268
175°	972	966	972	966	972	92
180°	970	970	970	970	970	

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1081.9	1086.4	1088.6	1091.6	1098.3	1102.8	1109.5	1111.0	1110.3	1113.3	1105.0
5°	1075.9	1085.6	1094.6	1102.1	1114.0	1121.5	1129.7	1139.4	1141.7	1152.9	1146.1
7.5°	1067.7	1081.9	1094.6	1109.5	1127.5	1137.2	1149.9	1164.8	1171.5	1185.0	1188.7
10°	1054.2	1074.4	1096.1	1111.8	1136.4	1153.6	1165.6	1189.5	1205.2	1225.3	1222.3
12.5°	1032.6	1058.7	1087.9	1114.0	1146.1	1157.3	1179.8	1204.4	1224.6	1243.3	1259.7
15°	1013.9	1043.8	1075.9	1108.0	1144.6	1165.6	1188.0	1220.1	1241.8	1274.6	1288.8
17.5°	988.5	1026.6	1064.7	1100.6	1143.9	1167.8	1195.4	1226.8	1259.0	1290.3	1301.5
20°	962.3	1003.4	1044.5	1093.1	1142.4	1165.6	1194.0	1232.8	1264.2	1288.8	1288.8
22.5°	931.0	981.0	1028.1	1074.4	1128.2	1161.8	1191.0	1236.5	1259.0	1264.2	1244.0
25°	899.6	949.6	1001.2	1058.7	1120.0	1149.9	1182.7	1225.3	1232.8	1211.9	1159.6
27.5°	862.2	918.3	976.5	1038.5	1102.8	1140.2	1170.0	1198.4	1184.2	1128.2	1046.8
30°	824.1	884.6	950.4	1009.4	1087.1	1121.5	1146.9	1155.1	1110.3	1019.1	913.8
32.5°	784.5	843.5	913.0	984.0	1062.5	1095.3	1111.8	1090.1	1007.9	892.8	764.3
35°	738.2	804.7	877.2	951.1	1028.8	1053.5	1063.2	1010.2	904.8	756.1	628.4
37.5°	696.3	762.8	840.5	916.0	991.5	1004.9	995.2	912.3	778.5	631.3	506.6
40°	647.0	718.0	794.2	878.7	940.7	944.4	920.5	812.9	647.0	508.8	431.9
42.5°	601.5	673.2	749.4	835.3	882.4	869.7	837.6	696.3	540.2	438.6	376.6
45°	554.4	622.4	704.6	780.8	814.4	784.5	735.9	585.8	453.5	377.3	329.5
47.5°	508.8	572.3	653.8	727.0	733.0	699.3	641.8	490.9	393.0	331.7	292.9
50°	464.0	527.5	603.7	664.2	658.2	611.9	546.9	426.6	341.4	292.9	260.8
52.5°	419.2	476.7	550.7	598.5	573.1	528.2	464.0	361.6	298.1	255.5	230.9
55°	374.3	428.1	491.6	531.2	490.9	439.3	393.8	310.1	258.5	224.1	205.5
57.5°	337.0	379.6	437.8	461.7	413.2	372.8	333.2	266.7	224.1	199.5	177.8
60°	295.9	334.7	382.5	396.7	346.7	313.8	280.2	225.6	192.0	170.4	156.2
62.5°	260.8	292.9	329.5	329.5	285.4	260.8	235.4	189.0	161.4	144.2	137.5
65°	226.4	249.5	275.7	272.7	235.4	213.7	193.5	156.2	135.2	123.3	116.6
67.5°	192.8	210.7	227.9	217.4	190.5	171.8	153.2	126.3	112.1	103.9	94.9
70°	162.1	176.3	185.3	175.6	148.7	133.0	119.5	101.6	90.4	79.9	74.7
72.5°	136.0	142.0	144.9	133.0	110.6	101.6	91.9	79.2	69.5	64.3	62.8
75°	106.1	111.3	109.1	100.1	81.4	74.7	67.2	58.3	56.0	53.0	51.6
77.5°	82.9	82.9	79.2	71.0	58.3	53.0	50.1	45.6	43.3	42.6	41.1
80°	59.0	58.3	56.0	47.1	39.6	36.6	36.6	33.6	32.9	31.4	31.4
82.5°	38.9	38.9	35.9	28.4	26.2	25.4	24.7	23.2	23.2	22.4	22.4
85°	23.2	21.7	17.9	15.7	14.9	14.9	14.2	13.4	14.2	13.4	13.4
87.5°	10.5	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.6	40.4	35.3	30.1	25.0	22.4	23.0	24.1	25.2	26.3	27.4
97.5°	82.1	69.3	56.5	43.8	31.0	24.6	25.8	28.3	30.8	33.3	35.8
100°	124.2	102.8	81.5	60.1	38.8	28.1	29.4	32.1	34.7	37.4	40.0
102.5°	170.5	170.2	169.9	169.6	169.3	169.1	154.9	126.5	98.2	69.8	41.4
105°	213.3	218.0	222.6	227.3	232.0	234.3	213.0	170.5	127.9	85.4	42.8
107.5°	263.1	267.0	270.9	274.8	278.7	280.6	254.3	201.8	149.3	96.7	44.2
110°	310.8	314.1	317.3	320.6	323.9	325.5	303.0	257.9	212.9	167.8	122.8

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	355.7	358.5	361.3	364.1	366.9	368.3	367.0	364.3	361.7	359.0	356.4
115°	403.4	406.0	408.7	411.3	414.0	415.3	417.2	421.1	425.0	428.9	432.8
117.5°	444.8	447.9	451.0	454.1	457.2	458.8	460.1	462.8	465.4	468.1	470.7
120°	491.1	493.4	495.8	498.1	500.4	501.6	503.0	505.8	508.6	511.4	514.2
122.5°	530.4	532.9	535.4	537.9	540.4	541.6	543.2	546.3	549.4	552.5	555.6
125°	570.3	572.3	574.4	576.4	578.5	579.5	581.0	583.9	586.9	589.8	592.8
127.5°	606.8	609.0	611.2	613.3	615.5	616.6	617.8	620.1	622.5	624.8	627.2
130°	641.2	643.7	646.2	648.7	651.2	652.4	653.3	655.0	656.7	658.4	660.1
132.5°	676.3	678.3	680.3	682.4	684.4	685.4	686.3	688.0	689.7	691.4	693.1
135°	705.7	708.2	710.7	713.2	715.7	717.0	717.7	719.1	720.5	721.9	723.3
137.5°	736.6	738.5	740.3	742.2	744.1	745.0	745.8	747.3	748.9	750.4	752.0
140°	766.8	768.0	769.3	770.5	771.8	772.4	773.3	775.0	776.7	778.4	780.1
142.5°	792.0	793.1	794.2	795.3	796.4	796.9	797.9	800.0	802.0	804.1	806.1
145°	818.7	818.5	818.4	818.2	818.1	818.0	819.3	822.0	824.6	827.3	829.9
147.5°	841.8	841.3	840.9	840.4	839.9	839.7	841.0	843.7	846.4	849.0	851.7
150°	864.3	863.2	862.1	861.0	859.9	859.4	860.6	863.1	865.6	868.1	870.6
152.5°	883.2	882.0	880.7	879.5	878.2	877.6	878.8	881.1	883.4	885.8	888.1
155°	901.5	900.1	898.7	897.3	895.9	895.2	896.1	898.0	899.9	901.7	903.6
157.5°	916.2	915.0	913.7	912.5	911.2	910.6	911.3	912.7	914.1	915.5	916.9
160°	928.8	927.9	926.9	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8
162.5°	940.1	939.1	938.2	937.2	936.3	935.8	936.2	937.0	937.8	938.6	939.4
165°	949.9	949.0	948.0	947.1	946.2	945.7	945.9	946.4	946.9	947.3	947.8
167.5°	957.6	956.7	955.7	954.8	953.9	953.4	953.6	954.1	954.6	955.0	955.5
170°	963.9	963.0	962.0	961.1	960.2	959.7	959.9	960.2	960.5	960.8	961.1
172.5°	968.1	967.2	966.2	965.3	964.4	963.9	964.1	964.4	964.7	965.0	965.3
175°	971.6	970.5	969.4	968.3	967.2	966.7	966.9	967.2	967.5	967.8	968.1
177.5°	973.0	971.9	970.8	969.7	968.6	968.1	968.2	968.3	968.5	968.6	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1113.3	1114.8	1117.0	1127.5	1128.9	1131.9	1130.4	1130.4	1131.2	1129.7	1130.4
5°	1161.1	1163.3	1174.5	1187.2	1190.2	1187.2	1191.0	1196.2	1196.2	1196.2	1194.7
7.5°	1205.9	1214.1	1226.8	1245.5	1249.2	1253.0	1259.7	1255.2	1256.7	1263.4	1261.2
10°	1249.2	1261.2	1275.4	1291.1	1299.3	1304.5	1307.5	1314.2	1329.9	1312.0	1318.7
12.5°	1290.3	1307.5	1322.5	1339.6	1345.6	1352.3	1354.6	1360.6	1360.6	1359.8	1365.0
15°	1317.2	1332.9	1346.4	1357.6	1359.1	1357.6	1356.1	1356.8	1359.1	1350.1	1355.3
17.5°	1323.2	1324.7	1329.2	1324.7	1325.5	1309.8	1300.8	1298.6	1277.6	1278.4	1295.6
20°	1294.1	1268.7	1261.9	1237.3	1222.3	1182.0	1180.5	1169.3	1125.2	1138.7	1135.7
22.5°	1214.1	1170.8	1113.3	1084.9	1070.7	1028.1	995.2	972.0	956.4	940.7	933.9
25°	1108.8	1038.5	957.1	901.1	892.8	853.2	792.7	764.3	730.7	720.3	738.2
27.5°	972.8	881.6	789.7	703.8	688.1	652.3	621.6	601.5	562.6	560.4	561.9
30°	788.2	696.3	619.4	563.4	524.5	508.1	487.9	472.9	457.3	463.2	464.7
32.5°	647.8	560.4	488.6	458.8	440.8	430.4	413.2	403.5	396.7	394.5	393.8
35°	514.8	456.5	424.4	395.2	384.8	377.3	364.6	360.1	354.2	354.9	354.9
37.5°	440.8	392.3	368.3	353.4	343.7	340.0	331.7	327.3	323.5	322.0	324.3
40°	380.3	346.7	331.7	318.3	310.1	308.6	304.1	298.9	294.4	295.1	297.4
42.5°	336.2	316.8	298.9	288.4	282.4	280.2	276.4	272.7	272.7	270.5	269.7
45°	301.1	285.4	270.5	260.8	257.0	254.0	249.5	248.8	245.8	246.6	247.3
47.5°	269.7	257.0	245.8	236.1	232.4	231.6	227.1	224.1	224.1	223.4	222.7
50°	241.3	228.6	218.9	213.7	208.5	207.0	206.2	205.5	204.0	204.0	204.7
52.5°	218.2	205.5	198.0	193.5	190.5	189.0	189.0	188.3	188.3	188.3	187.5
55°	192.8	182.3	176.3	174.8	173.3	172.6	171.8	170.4	169.6	171.1	169.6
57.5°	168.9	165.1	159.9	158.4	154.7	154.7	152.4	150.9	149.4	150.9	150.9
60°	150.2	144.9	142.0	137.5	134.5	131.5	127.8	127.0	125.5	124.8	124.0
62.5°	130.8	126.3	118.8	112.1	107.6	104.6	103.1	102.4	102.4	101.6	101.6
65°	109.1	98.6	94.9	92.6	91.9	91.2	89.7	88.9	89.7	88.9	89.7
67.5°	85.2	83.7	81.4	79.9	79.2	78.5	78.5	77.7	77.7	77.7	77.7
70°	74.0	70.2	69.5	68.0	68.0	67.2	67.2	67.2	67.2	66.5	68.0
72.5°	61.3	59.0	58.3	57.5	57.5	57.5	56.8	56.8	56.8	56.0	56.8
75°	50.1	49.3	47.8	47.8	47.1	47.8	47.1	47.1	46.3	47.1	47.1
77.5°	40.3	39.6	38.9	38.9	38.1	38.1	38.1	38.1	38.1	38.1	38.9
80°	30.6	29.9	29.1	29.9	29.1	29.9	29.1	29.1	29.9	29.1	29.1
82.5°	22.4	21.7	21.7	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
85°	13.4	12.7	12.7	13.4	12.7	13.4	12.7	12.7	12.7	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.2	29.0	29.7	30.5	30.9	30.8	30.7	30.5	30.4	30.2	30.4
97.5°	36.3	36.7	37.2	37.7	37.9	38.0	38.1	38.3	38.4	38.6	38.4
100°	41.2	42.5	43.7	45.0	45.6	45.8	46.1	46.4	46.7	47.0	46.7
102.5°	43.1	44.8	46.5	48.2	49.1	49.3	49.8	50.3	50.7	51.2	50.7
105°	44.5	46.2	47.9	49.6	50.5	50.8	51.4	52.1	52.7	53.3	52.7
107.5°	45.9	47.6	49.3	51.0	51.9	52.2	52.8	53.5	54.1	54.7	54.1
110°	107.2	91.6	76.0	60.4	52.6	52.9	53.5	54.2	54.8	55.4	54.8

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	289.2	222.0	154.8	87.6	54.0	54.2	54.7	55.2	55.6	56.1	55.6
115°	360.6	288.4	216.3	144.1	108.0	102.4	91.2	79.9	68.7	57.5	68.7
117.5°	448.4	426.1	403.8	381.5	370.4	350.0	309.1	268.3	227.4	186.6	227.4
120°	516.1	517.9	519.8	521.7	522.6	512.1	491.0	470.0	448.9	427.9	448.9
122.5°	556.5	557.5	558.4	559.3	559.8	559.9	560.0	560.2	560.3	560.5	560.3
125°	593.9	595.0	596.1	597.2	597.7	597.9	598.4	598.9	599.3	599.8	599.3
127.5°	628.8	630.3	631.9	633.4	634.2	634.3	634.4	634.6	634.7	634.9	634.7
130°	661.8	663.6	665.3	667.0	667.9	667.8	667.7	667.5	667.4	667.2	667.4
132.5°	694.5	695.9	697.3	698.7	699.4	699.3	699.2	699.0	698.9	698.7	698.9
135°	724.9	726.4	728.0	729.5	730.3	730.1	729.8	729.5	729.2	728.9	729.2
137.5°	753.6	755.2	756.7	758.3	759.1	758.9	758.4	757.9	757.5	757.0	757.5
140°	781.5	782.9	784.3	785.7	786.4	786.0	785.2	784.5	783.7	782.9	783.7
142.5°	807.3	808.6	809.8	811.1	811.7	811.3	810.5	809.8	809.0	808.2	809.0
145°	831.0	832.1	833.2	834.3	834.8	834.4	833.6	832.9	832.1	831.3	832.1
147.5°	852.5	853.3	854.0	854.8	855.2	854.9	854.3	853.6	853.0	852.4	853.0
150°	871.5	872.5	873.4	874.3	874.8	874.4	873.6	872.9	872.1	871.3	872.1
152.5°	889.1	890.0	891.0	891.9	892.4	891.8	890.7	889.6	888.5	887.4	888.5
155°	904.5	905.5	906.4	907.3	907.8	907.2	905.9	904.7	903.4	902.2	903.4
157.5°	918.0	919.1	920.2	921.3	921.8	921.2	919.9	918.7	917.4	916.2	917.4
160°	929.7	930.7	931.6	932.5	933.0	932.5	931.4	930.3	929.2	928.1	929.2
162.5°	940.5	941.6	942.7	943.8	944.3	943.6	942.2	940.8	939.4	938.0	939.4
165°	948.9	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	948.9
167.5°	956.6	957.7	958.8	959.9	960.4	959.7	958.3	956.9	955.5	954.1	955.5
170°	962.2	963.3	964.4	965.5	966.0	965.3	963.9	962.5	961.1	959.7	961.1
172.5°	966.4	967.5	968.6	969.7	970.2	969.5	968.1	966.7	965.3	963.9	965.3
175°	969.2	970.3	971.4	972.5	973.0	972.2	970.7	969.1	967.6	966.0	967.6
177.5°	969.9	971.0	972.1	973.2	973.7	973.0	971.6	970.2	968.8	967.4	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1133.4	1128.2	1126.7	1128.2	1126.7	1127.5	1122.2	1102.8	1108.0	1099.8	1104.3
5°	1197.7	1193.2	1183.5	1182.0	1180.5	1179.0	1171.5	1154.4	1147.6	1136.4	1135.7
7.5°	1259.0	1259.0	1251.5	1246.3	1239.5	1234.3	1224.6	1199.2	1188.7	1175.3	1167.8
10°	1319.5	1300.0	1308.3	1303.0	1286.6	1283.6	1265.7	1250.7	1230.6	1217.1	1205.2
12.5°	1362.8	1356.8	1349.4	1344.9	1340.4	1330.7	1318.7	1280.6	1270.2	1243.3	1229.8
15°	1361.3	1357.6	1359.8	1359.8	1358.3	1356.1	1346.4	1318.7	1300.8	1274.6	1251.5
17.5°	1288.1	1297.8	1307.5	1314.2	1329.2	1335.9	1344.9	1328.4	1317.2	1294.8	1270.2
20°	1160.3	1184.2	1212.6	1218.6	1232.1	1271.7	1289.6	1303.8	1308.3	1300.8	1280.6
22.5°	982.5	1002.7	1071.4	1069.9	1089.4	1136.4	1188.7	1231.3	1264.9	1283.6	1276.1
25°	769.6	798.0	834.6	862.2	925.7	996.0	1061.0	1128.9	1187.2	1238.8	1251.5
27.5°	582.0	619.4	648.5	685.1	717.3	800.2	883.9	990.0	1058.0	1155.8	1206.7
30°	470.7	487.9	517.0	534.2	549.9	613.4	708.3	812.9	932.4	1045.3	1132.7
32.5°	402.0	413.9	435.6	443.1	459.5	502.1	561.9	657.5	780.8	917.5	1032.6
35°	360.9	373.6	378.1	384.8	398.2	425.1	466.2	535.7	647.0	780.8	918.3
37.5°	325.8	332.5	345.2	349.7	354.2	374.3	402.0	450.5	524.5	634.3	786.8
40°	301.1	304.8	311.6	315.3	318.3	332.5	357.1	390.0	444.6	528.2	668.7
42.5°	275.0	279.4	283.9	288.4	292.1	303.3	318.3	349.7	386.3	449.8	551.4
45°	249.5	252.5	257.8	260.8	266.0	275.0	288.4	310.1	342.9	383.3	465.5
47.5°	226.4	230.1	232.4	236.1	239.8	249.5	262.3	276.4	303.3	342.9	402.7
50°	205.5	210.0	212.9	213.7	216.7	225.6	236.1	251.8	269.0	299.6	351.9
52.5°	190.5	191.3	193.5	196.5	195.8	201.0	210.7	222.7	240.6	265.2	303.3
55°	173.3	175.6	177.1	177.8	177.8	182.3	187.5	198.7	212.9	233.1	265.2
57.5°	151.7	153.9	158.4	159.9	162.1	164.4	166.6	174.1	186.0	205.5	231.6
60°	129.3	130.8	135.2	138.2	139.7	145.7	148.7	154.7	161.4	175.6	200.2
62.5°	103.9	105.3	107.6	110.6	113.6	122.5	130.0	136.0	141.2	150.9	171.1
65°	90.4	91.2	92.6	93.4	94.1	97.9	104.6	112.8	122.5	130.0	142.0
67.5°	78.5	79.2	79.9	81.4	82.2	82.9	85.9	88.2	97.9	108.3	117.3
70°	67.2	68.7	69.5	69.5	70.2	71.7	73.2	76.2	79.2	84.4	95.6
72.5°	56.8	57.5	59.0	59.0	59.0	60.5	62.0	63.5	65.0	68.0	72.5
75°	47.1	48.6	48.6	48.6	49.3	49.3	50.8	52.3	53.8	56.0	57.5
77.5°	38.9	38.9	38.9	38.9	39.6	39.6	40.3	41.8	42.6	43.3	44.8
80°	29.1	29.9	29.9	29.9	30.6	30.6	30.6	32.1	32.9	32.9	34.4
82.5°	21.7	21.7	21.7	22.4	21.7	22.4	22.4	23.2	22.4	23.2	23.9
85°	13.4	13.4	13.4	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	6.7	6.7
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.5	30.7	30.8	30.9	30.5	29.7	29.0	28.2	27.4	26.3	25.2
97.5°	38.3	38.1	38.0	37.9	37.7	37.2	36.7	36.3	35.8	33.3	30.8
100°	46.4	46.1	45.8	45.6	45.0	43.7	42.5	41.2	40.0	37.4	34.7
102.5°	50.3	49.8	49.3	49.1	48.2	46.5	44.8	43.1	41.4	39.8	38.2
105°	52.1	51.4	50.8	50.5	49.6	47.9	46.2	44.5	42.8	41.1	39.4
107.5°	53.5	52.8	52.2	51.9	51.0	49.3	47.6	45.9	44.2	42.5	40.8
110°	54.2	53.5	52.9	52.6	50.4	48.7	47.0	45.3	43.6	41.9	40.2

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.2	54.7	54.2	54.0	87.6	154.8	222.0	289.2	356.4	359.0	361.7
115°	79.9	91.2	102.4	108.0	144.1	216.3	288.4	360.6	432.8	428.9	425.0
117.5°	268.3	309.1	350.0	370.4	381.5	403.8	426.1	448.4	470.7	468.1	465.4
120°	470.0	491.0	512.1	522.6	521.7	519.8	517.9	516.1	514.2	511.4	508.6
122.5°	560.2	560.0	559.9	559.8	559.3	558.4	557.5	556.5	555.6	552.5	549.4
125°	598.9	598.4	597.9	597.7	597.2	596.1	595.0	593.9	592.8	589.8	586.9
127.5°	634.6	634.4	634.3	634.2	633.4	631.9	630.3	628.8	627.2	624.8	622.5
130°	667.5	667.7	667.8	667.9	667.0	665.3	663.6	661.8	660.1	658.4	656.7
132.5°	699.0	699.2	699.3	699.4	698.7	697.3	695.9	694.5	693.1	691.4	689.7
135°	729.5	729.8	730.1	730.3	729.5	728.0	726.4	724.9	723.3	721.9	720.5
137.5°	757.9	758.4	758.9	759.1	758.3	756.7	755.2	753.6	752.0	750.4	748.9
140°	784.5	785.2	786.0	786.4	785.7	784.3	782.9	781.5	780.1	778.4	776.7
142.5°	809.8	810.5	811.3	811.7	811.1	809.8	808.6	807.3	806.1	804.1	802.0
145°	832.9	833.6	834.4	834.8	834.3	833.2	832.1	831.0	829.9	827.3	824.6
147.5°	853.6	854.3	854.9	855.2	854.8	854.0	853.3	852.5	851.7	849.0	846.4
150°	872.9	873.6	874.4	874.8	874.3	873.4	872.5	871.5	870.6	868.1	865.6
152.5°	889.6	890.7	891.8	892.4	891.9	891.0	890.0	889.1	888.1	885.8	883.4
155°	904.7	905.9	907.2	907.8	907.3	906.4	905.5	904.5	903.6	901.7	899.9
157.5°	918.7	919.9	921.2	921.8	921.3	920.2	919.1	918.0	916.9	915.5	914.1
160°	930.3	931.4	932.5	933.0	932.5	931.6	930.7	929.7	928.8	927.9	926.9
162.5°	940.8	942.2	943.6	944.3	943.8	942.7	941.6	940.5	939.4	938.6	937.8
165°	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	947.3	946.9
167.5°	956.9	958.3	959.7	960.4	959.9	958.8	957.7	956.6	955.5	955.0	954.6
170°	962.5	963.9	965.3	966.0	965.5	964.4	963.3	962.2	961.1	960.8	960.5
172.5°	966.7	968.1	969.5	970.2	969.7	968.6	967.5	966.4	965.3	965.0	964.7
175°	969.1	970.7	972.2	973.0	972.5	971.4	970.3	969.2	968.1	967.8	967.5
177.5°	970.2	971.6	973.0	973.7	973.2	972.1	971.0	969.9	968.8	968.6	968.5
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1097.6	1093.8	1093.8	1091.6	1091.6	1079.6	1079.6	1083.4	1078.9	1073.7	1066.2
5°	1126.0	1117.7	1115.5	1112.5	1102.8	1087.9	1081.9	1079.6	1070.7	1059.5	1046.8
7.5°	1152.9	1139.4	1132.7	1126.0	1113.3	1092.3	1080.4	1072.2	1058.7	1041.5	1025.1
10°	1179.0	1161.8	1144.6	1136.4	1118.5	1092.3	1075.2	1061.7	1042.3	1019.1	996.0
12.5°	1202.9	1167.1	1164.1	1147.6	1121.5	1091.6	1065.4	1046.0	1021.4	994.5	967.6
15°	1223.8	1187.2	1169.3	1154.4	1120.0	1082.6	1055.0	1031.1	998.2	967.6	934.7
17.5°	1234.3	1194.7	1182.7	1158.1	1123.0	1074.4	1037.0	1007.9	972.0	935.4	898.1
20°	1244.8	1198.4	1179.0	1161.8	1114.0	1058.7	1016.9	983.3	943.7	900.3	859.2
22.5°	1250.0	1198.4	1175.3	1151.4	1105.0	1041.5	992.2	952.6	906.3	862.2	812.9
25°	1241.0	1194.0	1166.3	1141.7	1089.4	1020.6	963.8	919.0	869.7	819.6	769.6
27.5°	1218.6	1183.5	1151.4	1126.0	1067.7	993.7	933.9	883.1	832.3	776.3	725.5
30°	1176.8	1161.1	1135.7	1107.3	1043.8	969.8	898.8	846.5	790.5	734.5	681.4
32.5°	1111.8	1125.2	1108.8	1084.1	1015.4	936.9	861.5	808.4	747.2	686.6	638.1
35°	1032.6	1080.4	1071.4	1054.2	985.5	901.8	826.4	762.1	700.8	639.6	591.0
37.5°	945.9	1018.4	1025.8	1015.4	951.1	866.0	783.0	720.3	657.5	595.5	546.2
40°	827.1	938.4	962.3	966.8	915.3	822.6	735.9	674.7	612.7	552.1	492.4
42.5°	718.0	858.5	888.4	907.0	869.7	780.0	692.6	624.6	563.4	508.8	449.0
45°	615.7	762.1	810.7	834.6	818.1	731.5	641.1	577.5	521.5	471.5	413.9
47.5°	510.3	657.5	725.5	763.6	763.6	682.2	591.7	529.0	475.2	432.6	381.8
50°	440.1	562.6	632.8	682.9	696.3	632.1	546.9	485.6	434.8	388.5	349.7
52.5°	375.1	484.9	543.2	595.5	634.3	578.3	496.9	441.6	391.5	348.2	317.5
55°	324.3	406.5	459.5	517.0	560.4	523.8	448.3	394.5	351.2	315.3	289.1
57.5°	275.7	347.4	390.8	441.6	487.9	460.2	399.7	353.4	315.3	283.9	260.8
60°	234.6	292.9	326.5	366.1	423.6	404.2	354.2	311.6	280.9	252.5	233.1
62.5°	199.5	245.8	274.2	302.6	354.9	345.9	307.1	274.2	248.1	224.1	207.7
65°	163.6	201.7	224.1	248.8	290.6	294.4	263.0	239.8	215.9	195.0	180.1
67.5°	132.2	162.1	182.3	203.2	236.8	247.3	225.6	206.2	186.0	168.9	155.4
70°	106.8	127.8	142.7	159.1	186.8	199.5	188.3	174.8	158.4	144.2	132.2
72.5°	84.4	97.9	106.8	119.5	142.0	154.7	153.9	142.0	130.0	120.3	110.6
75°	62.0	72.5	79.9	88.2	106.1	118.1	121.0	115.8	103.9	96.4	88.9
77.5°	47.1	53.0	56.8	62.8	75.5	85.9	90.4	88.9	80.7	74.7	69.5
80°	35.9	37.4	38.9	41.1	51.6	61.3	64.3	63.5	59.0	56.8	50.8
82.5°	25.4	26.2	26.9	27.6	31.4	39.6	42.6	44.1	40.3	38.1	32.9
85°	14.9	15.7	15.7	17.2	17.9	20.2	25.4	25.4	24.7	21.7	20.9
87.5°	7.5	7.5	6.7	6.7	7.5	8.2	9.7	11.2	9.7	9.0	8.2
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.1	23.0	22.4	25.0	30.1	35.3	40.4	45.6	40.4	35.3	30.1
97.5°	28.3	25.8	24.6	31.0	43.8	56.5	69.3	82.1	69.3	56.5	43.8
100°	32.1	29.4	28.1	38.8	60.1	81.5	102.8	124.2	102.8	81.5	60.1
102.5°	126.5	154.9	169.1	169.3	169.6	169.9	170.2	170.5	170.2	169.9	169.6
105°	170.5	213.0	234.3	232.0	227.3	222.6	218.0	213.3	218.0	222.6	227.3
107.5°	201.8	254.3	280.6	278.7	274.8	270.9	267.0	263.1	267.0	270.9	274.8
110°	257.9	303.0	325.5	323.9	320.6	317.3	314.1	310.8	314.1	317.3	320.6

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	364.3	367.0	368.3	366.9	364.1	361.3	358.5	355.7	358.5	361.3	364.1
115°	421.1	417.2	415.3	414.0	411.3	408.7	406.0	403.4	406.0	408.7	411.3
117.5°	462.8	460.1	458.8	457.2	454.1	451.0	447.9	444.8	447.9	451.0	454.1
120°	505.8	503.0	501.6	500.4	498.1	495.8	493.4	491.1	493.4	495.8	498.1
122.5°	546.3	543.2	541.6	540.4	537.9	535.4	532.9	530.4	532.9	535.4	537.9
125°	583.9	581.0	579.5	578.5	576.4	574.4	572.3	570.3	572.3	574.4	576.4
127.5°	620.1	617.8	616.6	615.5	613.3	611.2	609.0	606.8	609.0	611.2	613.3
130°	655.0	653.3	652.4	651.2	648.7	646.2	643.7	641.2	643.7	646.2	648.7
132.5°	688.0	686.3	685.4	684.4	682.4	680.3	678.3	676.3	678.3	680.3	682.4
135°	719.1	717.7	717.0	715.7	713.2	710.7	708.2	705.7	708.2	710.7	713.2
137.5°	747.3	745.8	745.0	744.1	742.2	740.3	738.5	736.6	738.5	740.3	742.2
140°	775.0	773.3	772.4	771.8	770.5	769.3	768.0	766.8	768.0	769.3	770.5
142.5°	800.0	797.9	796.9	796.4	795.3	794.2	793.1	792.0	793.1	794.2	795.3
145°	822.0	819.3	818.0	818.1	818.2	818.4	818.5	818.7	818.5	818.4	818.2
147.5°	843.7	841.0	839.7	839.9	840.4	840.9	841.3	841.8	841.3	840.9	840.4
150°	863.1	860.6	859.4	859.9	861.0	862.1	863.2	864.3	863.2	862.1	861.0
152.5°	881.1	878.8	877.6	878.2	879.5	880.7	882.0	883.2	882.0	880.7	879.5
155°	898.0	896.1	895.2	895.9	897.3	898.7	900.1	901.5	900.1	898.7	897.3
157.5°	912.7	911.3	910.6	911.2	912.5	913.7	915.0	916.2	915.0	913.7	912.5
160°	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8	927.9	926.9	926.0
162.5°	937.0	936.2	935.8	936.3	937.2	938.2	939.1	940.1	939.1	938.2	937.2
165°	946.4	945.9	945.7	946.2	947.1	948.0	949.0	949.9	949.0	948.0	947.1
167.5°	954.1	953.6	953.4	953.9	954.8	955.7	956.7	957.6	956.7	955.7	954.8
170°	960.2	959.9	959.7	960.2	961.1	962.0	963.0	963.9	963.0	962.0	961.1
172.5°	964.4	964.1	963.9	964.4	965.3	966.2	967.2	968.1	967.2	966.2	965.3
175°	967.2	966.9	966.7	967.2	968.3	969.4	970.5	971.6	970.5	969.4	968.3
177.5°	968.3	968.2	968.1	968.6	969.7	970.8	971.9	973.0	971.9	970.8	969.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1063.2	1063.9	1066.2	1059.5	1049.0	1044.5	1031.1	1028.8	1026.6	1026.6	1028.8
5°	1039.3	1036.3	1037.0	1024.3	1009.4	1000.4	981.8	984.7	975.0	969.1	970.6
7.5°	1013.1	1004.9	1004.2	987.7	969.1	952.6	933.2	928.7	919.7	909.3	904.8
10°	980.3	974.3	963.1	944.4	920.5	907.0	880.9	865.2	863.0	847.3	841.3
12.5°	946.6	936.2	925.0	898.8	871.9	850.3	830.8	813.7	801.7	788.2	779.3
15°	907.8	895.1	882.4	854.7	823.4	801.7	772.6	747.2	712.0	684.4	668.7
17.5°	865.2	851.0	833.8	803.2	772.6	742.7	688.9	659.0	634.3	617.9	608.2
20°	821.1	805.4	788.2	757.6	704.6	652.3	622.4	599.2	584.3	567.8	555.9
22.5°	774.8	758.4	739.7	691.9	635.8	599.2	576.1	554.4	532.7	523.8	517.8
25°	731.5	716.5	692.6	627.6	583.5	549.9	523.8	509.6	498.4	486.4	475.2
27.5°	686.6	659.0	625.4	570.8	543.2	508.8	490.1	479.7	460.2	452.0	446.8
30°	632.8	602.2	570.1	531.2	499.1	475.2	458.0	440.8	429.6	421.4	412.4
32.5°	578.3	549.2	529.0	488.6	464.7	440.1	423.6	413.2	396.7	391.5	387.8
35°	531.2	506.6	488.6	455.8	433.3	410.9	399.0	383.3	372.8	363.1	357.1
37.5°	484.9	471.5	452.8	425.1	401.2	383.3	366.9	361.6	347.4	342.2	336.2
40°	452.8	432.6	416.9	393.0	372.8	353.4	342.9	331.0	321.3	313.1	310.8
42.5°	413.9	399.0	390.0	363.9	342.9	331.7	319.0	305.6	298.1	291.4	283.2
45°	384.8	371.3	358.6	337.7	319.0	304.8	293.6	284.7	272.0	269.0	256.3
47.5°	354.2	340.7	331.0	310.1	292.9	279.4	271.2	259.3	248.8	242.1	236.1
50°	323.5	312.3	303.3	285.4	270.5	256.3	245.1	233.1	228.6	217.4	213.7
52.5°	294.4	286.9	277.2	260.0	245.1	233.1	221.2	211.4	204.7	198.7	194.3
55°	269.7	257.8	253.3	234.6	221.9	209.2	198.7	192.8	184.5	180.8	177.1
57.5°	242.1	235.4	227.9	213.7	199.5	187.5	180.1	171.1	166.6	162.1	159.1
60°	218.2	208.5	202.5	190.5	177.8	166.6	159.9	153.2	147.2	143.5	137.5
62.5°	190.5	183.1	179.3	166.6	156.2	145.7	139.7	133.0	128.5	121.8	114.3
65°	166.6	160.6	156.2	145.7	136.0	126.3	120.3	112.1	106.1	102.4	101.6
67.5°	145.7	141.2	134.5	124.8	115.1	107.6	100.9	94.1	93.4	91.9	91.9
70°	122.5	118.1	114.3	103.9	95.6	87.4	85.9	83.7	81.4	80.7	79.2
72.5°	102.4	98.6	94.1	85.2	77.0	74.7	73.2	71.7	69.5	68.7	68.0
75°	82.9	77.7	74.7	66.5	64.3	62.8	61.3	59.0	57.5	56.8	55.3
77.5°	63.5	58.3	58.3	53.8	52.3	50.1	48.6	47.1	46.3	44.8	44.8
80°	44.8	44.8	43.3	41.1	38.9	38.1	35.9	35.1	34.4	35.1	33.6
82.5°	32.9	29.9	29.9	28.4	26.9	26.2	24.7	24.7	23.9	23.9	23.9
85°	18.7	18.7	17.9	16.4	15.7	15.7	14.9	14.9	14.2	14.2	13.4
87.5°	7.5	6.7	7.5	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	23.0	24.1	25.2	26.3	27.4	28.2	29.0	29.7	30.5
97.5°	31.0	24.6	25.8	28.3	30.8	33.3	35.8	36.3	36.7	37.2	37.7
100°	38.8	28.1	29.4	32.1	34.7	37.4	40.0	41.2	42.5	43.7	45.0
102.5°	169.3	169.1	154.9	126.5	98.2	69.8	41.4	43.1	44.8	46.5	48.2
105°	232.0	234.3	213.0	170.5	127.9	85.4	42.8	44.5	46.2	47.9	49.6
107.5°	278.7	280.6	254.3	201.8	149.3	96.7	44.2	45.9	47.6	49.3	51.0
110°	323.9	325.5	303.0	257.9	212.9	167.8	122.8	107.2	91.6	76.0	60.4

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	366.9	368.3	367.0	364.3	361.7	359.0	356.4	289.2	222.0	154.8	87.6
115°	414.0	415.3	417.2	421.1	425.0	428.9	432.8	360.6	288.4	216.3	144.1
117.5°	457.2	458.8	460.1	462.8	465.4	468.1	470.7	448.4	426.1	403.8	381.5
120°	500.4	501.6	503.0	505.8	508.6	511.4	514.2	516.1	517.9	519.8	521.7
122.5°	540.4	541.6	543.2	546.3	549.4	552.5	555.6	556.5	557.5	558.4	559.3
125°	578.5	579.5	581.0	583.9	586.9	589.8	592.8	593.9	595.0	596.1	597.2
127.5°	615.5	616.6	617.8	620.1	622.5	624.8	627.2	628.8	630.3	631.9	633.4
130°	651.2	652.4	653.3	655.0	656.7	658.4	660.1	661.8	663.6	665.3	667.0
132.5°	684.4	685.4	686.3	688.0	689.7	691.4	693.1	694.5	695.9	697.3	698.7
135°	715.7	717.0	717.7	719.1	720.5	721.9	723.3	724.9	726.4	728.0	729.5
137.5°	744.1	745.0	745.8	747.3	748.9	750.4	752.0	753.6	755.2	756.7	758.3
140°	771.8	772.4	773.3	775.0	776.7	778.4	780.1	781.5	782.9	784.3	785.7
142.5°	796.4	796.9	797.9	800.0	802.0	804.1	806.1	807.3	808.6	809.8	811.1
145°	818.1	818.0	819.3	822.0	824.6	827.3	829.9	831.0	832.1	833.2	834.3
147.5°	839.9	839.7	841.0	843.7	846.4	849.0	851.7	852.5	853.3	854.0	854.8
150°	859.9	859.4	860.6	863.1	865.6	868.1	870.6	871.5	872.5	873.4	874.3
152.5°	878.2	877.6	878.8	881.1	883.4	885.8	888.1	889.1	890.0	891.0	891.9
155°	895.9	895.2	896.1	898.0	899.9	901.7	903.6	904.5	905.5	906.4	907.3
157.5°	911.2	910.6	911.3	912.7	914.1	915.5	916.9	918.0	919.1	920.2	921.3
160°	925.1	924.6	925.1	926.0	926.9	927.9	928.8	929.7	930.7	931.6	932.5
162.5°	936.3	935.8	936.2	937.0	937.8	938.6	939.4	940.5	941.6	942.7	943.8
165°	946.2	945.7	945.9	946.4	946.9	947.3	947.8	948.9	950.0	951.1	952.2
167.5°	953.9	953.4	953.6	954.1	954.6	955.0	955.5	956.6	957.7	958.8	959.9
170°	960.2	959.7	959.9	960.2	960.5	960.8	961.1	962.2	963.3	964.4	965.5
172.5°	964.4	963.9	964.1	964.4	964.7	965.0	965.3	966.4	967.5	968.6	969.7
175°	967.2	966.7	966.9	967.2	967.5	967.8	968.1	969.2	970.3	971.4	972.5
177.5°	968.6	968.1	968.2	968.3	968.5	968.6	968.8	969.9	971.0	972.1	973.2
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1028.8	1027.3	1022.9	1024.3	1022.1	1022.1	1020.6	1020.6	1020.6	1024.3	1022.1
5°	972.8	967.6	962.3	960.1	957.9	955.6	955.6	954.9	961.6	960.1	966.1
7.5°	903.3	901.8	891.4	891.4	887.6	886.1	889.9	890.6	891.4	892.8	896.6
10°	841.3	837.6	822.6	824.1	821.9	818.9	821.1	819.6	824.9	826.4	824.9
12.5°	768.1	761.3	744.9	736.7	727.7	721.0	729.2	723.2	744.2	750.1	766.6
15°	670.9	658.2	647.0	647.0	638.8	632.8	636.6	643.3	647.8	654.5	657.5
17.5°	605.9	600.7	591.7	586.5	584.3	582.0	582.0	585.0	594.7	594.0	600.0
20°	550.7	547.7	543.2	536.5	534.2	532.7	532.7	532.7	539.4	545.4	549.2
22.5°	512.5	510.3	507.3	498.4	493.9	492.4	496.1	498.4	503.6	508.1	511.8
25°	474.4	469.2	464.0	461.0	458.8	458.8	460.2	461.0	463.2	465.5	470.0
27.5°	443.1	439.3	431.9	423.6	423.6	421.4	422.9	424.4	429.6	437.1	440.8
30°	407.9	407.2	404.2	401.2	398.2	396.7	399.7	402.0	402.7	406.5	406.5
32.5°	382.5	377.3	372.1	369.1	367.6	366.9	367.6	370.6	370.6	375.1	380.3
35°	357.1	354.2	348.9	343.7	342.2	338.5	341.4	344.4	349.7	351.9	354.2
37.5°	329.5	325.8	323.5	322.0	319.0	319.8	317.5	322.0	326.5	325.8	327.3
40°	308.6	301.9	295.1	294.4	293.6	292.9	292.9	293.6	296.6	299.6	304.1
42.5°	281.7	279.4	273.5	267.5	266.0	264.5	263.0	266.0	272.0	277.2	279.4
45°	254.0	251.0	249.5	245.1	242.1	241.3	239.8	243.6	248.8	251.0	252.5
47.5°	228.6	227.9	223.4	224.1	221.9	222.7	221.9	224.1	224.1	226.4	227.9
50°	211.4	209.2	207.0	205.5	203.2	203.2	202.5	203.2	206.2	209.2	208.5
52.5°	194.3	190.5	189.8	189.0	187.5	189.0	186.8	187.5	190.5	192.0	191.3
55°	174.1	173.3	171.8	170.4	169.6	168.9	168.9	168.9	171.8	174.1	174.8
57.5°	158.4	154.7	151.7	151.7	148.7	147.9	149.4	150.2	152.4	153.9	155.4
60°	136.7	135.2	130.8	128.5	124.0	123.3	123.3	126.3	130.0	135.2	136.7
62.5°	113.6	111.3	110.6	110.6	110.6	110.6	110.6	110.6	110.6	111.3	111.3
65°	100.9	101.6	100.9	100.1	100.9	100.9	100.1	100.1	100.1	100.9	101.6
67.5°	90.4	89.7	90.4	89.7	88.9	88.9	88.2	88.9	89.7	90.4	90.4
70°	78.5	78.5	77.7	78.5	77.7	77.0	76.2	76.2	77.7	78.5	78.5
72.5°	67.2	67.2	66.5	66.5	65.0	65.0	65.7	65.0	65.0	67.2	67.2
75°	56.0	55.3	54.5	54.5	53.8	53.8	53.8	53.0	54.5	54.5	55.3
77.5°	44.1	44.1	44.1	43.3	43.3	42.6	42.6	43.3	43.3	43.3	44.1
80°	33.6	33.6	33.6	32.9	32.1	32.1	32.1	32.1	32.1	32.9	32.1
82.5°	23.2	23.2	23.2	23.2	23.2	22.4	22.4	22.4	23.2	23.2	22.4
85°	14.2	13.4	14.2	14.2	13.4	14.2	13.4	13.4	12.7	12.7	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.9	30.8	30.7	30.5	30.4	30.2	30.4	30.5	30.7	30.8	30.9
97.5°	37.9	38.0	38.1	38.3	38.4	38.6	38.4	38.3	38.1	38.0	37.9
100°	45.6	45.8	46.1	46.4	46.7	47.0	46.7	46.4	46.1	45.8	45.6
102.5°	49.1	49.3	49.8	50.3	50.7	51.2	50.7	50.3	49.8	49.3	49.1
105°	50.5	50.8	51.4	52.1	52.7	53.3	52.7	52.1	51.4	50.8	50.5
107.5°	51.9	52.2	52.8	53.5	54.1	54.7	54.1	53.5	52.8	52.2	51.9
110°	52.6	52.9	53.5	54.2	54.8	55.4	54.8	54.2	53.5	52.9	52.6

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	54.0	54.2	54.7	55.2	55.6	56.1	55.6	55.2	54.7	54.2	54.0
115°	108.0	102.4	91.2	79.9	68.7	57.5	68.7	79.9	91.2	102.4	108.0
117.5°	370.4	350.0	309.1	268.3	227.4	186.6	227.4	268.3	309.1	350.0	370.4
120°	522.6	512.1	491.0	470.0	448.9	427.9	448.9	470.0	491.0	512.1	522.6
122.5°	559.8	559.9	560.0	560.2	560.3	560.5	560.3	560.2	560.0	559.9	559.8
125°	597.7	597.9	598.4	598.9	599.3	599.8	599.3	598.9	598.4	597.9	597.7
127.5°	634.2	634.3	634.4	634.6	634.7	634.9	634.7	634.6	634.4	634.3	634.2
130°	667.9	667.8	667.7	667.5	667.4	667.2	667.4	667.5	667.7	667.8	667.9
132.5°	699.4	699.3	699.2	699.0	698.9	698.7	698.9	699.0	699.2	699.3	699.4
135°	730.3	730.1	729.8	729.5	729.2	728.9	729.2	729.5	729.8	730.1	730.3
137.5°	759.1	758.9	758.4	757.9	757.5	757.0	757.5	757.9	758.4	758.9	759.1
140°	786.4	786.0	785.2	784.5	783.7	782.9	783.7	784.5	785.2	786.0	786.4
142.5°	811.7	811.3	810.5	809.8	809.0	808.2	809.0	809.8	810.5	811.3	811.7
145°	834.8	834.4	833.6	832.9	832.1	831.3	832.1	832.9	833.6	834.4	834.8
147.5°	855.2	854.9	854.3	853.6	853.0	852.4	853.0	853.6	854.3	854.9	855.2
150°	874.8	874.4	873.6	872.9	872.1	871.3	872.1	872.9	873.6	874.4	874.8
152.5°	892.4	891.8	890.7	889.6	888.5	887.4	888.5	889.6	890.7	891.8	892.4
155°	907.8	907.2	905.9	904.7	903.4	902.2	903.4	904.7	905.9	907.2	907.8
157.5°	921.8	921.2	919.9	918.7	917.4	916.2	917.4	918.7	919.9	921.2	921.8
160°	933.0	932.5	931.4	930.3	929.2	928.1	929.2	930.3	931.4	932.5	933.0
162.5°	944.3	943.6	942.2	940.8	939.4	938.0	939.4	940.8	942.2	943.6	944.3
165°	952.7	952.2	951.1	950.0	948.9	947.8	948.9	950.0	951.1	952.2	952.7
167.5°	960.4	959.7	958.3	956.9	955.5	954.1	955.5	956.9	958.3	959.7	960.4
170°	966.0	965.3	963.9	962.5	961.1	959.7	961.1	962.5	963.9	965.3	966.0
172.5°	970.2	969.5	968.1	966.7	965.3	963.9	965.3	966.7	968.1	969.5	970.2
175°	973.0	972.2	970.7	969.1	967.6	966.0	967.6	969.1	970.7	972.2	973.0
177.5°	973.7	973.0	971.6	970.2	968.8	967.4	968.8	970.2	971.6	973.0	973.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1024.3	1028.1	1026.6	1018.4	1026.6	1028.8	1033.3	1037.8	1040.8	1045.3	1049.0
5°	960.1	967.6	972.0	967.6	982.5	984.7	995.2	1001.2	1010.2	1017.6	1023.6
7.5°	899.6	905.6	914.5	916.0	925.0	935.4	950.4	965.3	979.5	987.0	993.7
10°	834.6	845.0	858.5	855.5	868.9	885.4	901.1	925.0	936.9	950.4	962.3
12.5°	769.6	776.3	794.2	800.2	819.6	832.3	854.0	868.9	898.8	914.5	925.0
15°	656.0	683.6	706.1	733.0	758.4	782.3	801.7	828.6	854.7	866.7	883.9
17.5°	604.4	617.1	630.6	644.0	676.9	719.5	753.9	783.0	805.4	821.1	841.3
20°	550.7	563.4	578.3	591.0	611.2	641.8	684.4	734.5	761.3	777.8	797.2
22.5°	512.5	524.5	534.2	545.4	561.1	583.5	615.7	677.7	713.5	733.7	750.9
25°	471.5	486.4	496.9	505.1	517.8	542.4	568.6	603.7	668.0	683.6	707.6
27.5°	443.1	447.5	459.5	472.2	484.9	498.4	525.2	555.1	598.5	632.8	662.0
30°	409.4	420.6	431.9	437.1	448.3	467.7	484.2	516.3	549.9	576.8	611.9
32.5°	384.0	390.8	398.2	410.9	421.4	434.8	451.3	478.2	506.6	523.8	550.7
35°	355.6	360.1	375.8	381.0	391.5	405.0	421.4	442.3	472.9	486.4	505.8
37.5°	328.7	339.2	343.7	355.6	365.4	378.8	390.8	414.7	434.8	450.5	468.5
40°	307.8	312.3	320.5	331.0	339.2	349.7	364.6	381.8	403.5	416.2	431.9
42.5°	282.4	286.2	296.6	302.6	316.0	325.8	334.7	355.6	375.1	384.8	400.5
45°	254.8	263.7	270.5	282.4	289.9	301.9	313.1	328.0	345.9	357.1	366.1
47.5°	230.9	239.8	246.6	257.8	269.7	275.0	286.9	302.6	319.0	328.0	340.7
50°	211.4	214.4	227.1	232.4	245.1	255.5	263.7	277.2	295.1	300.4	310.8
52.5°	192.8	195.0	203.2	210.0	221.2	230.1	240.6	253.3	268.2	276.4	284.7
55°	176.3	177.8	181.6	189.0	196.5	207.7	217.4	229.4	242.1	251.0	258.5
57.5°	157.6	160.6	163.6	168.1	175.6	186.0	196.5	207.7	218.2	224.1	233.9
60°	136.0	140.5	145.7	150.9	156.2	163.6	175.6	186.0	195.8	201.0	208.5
62.5°	112.8	121.8	126.3	132.2	136.7	143.5	152.4	164.4	171.1	177.8	183.8
65°	101.6	102.4	103.1	109.1	117.3	124.0	132.2	141.2	151.7	156.2	160.6
67.5°	90.4	91.2	92.6	93.4	96.4	103.9	112.8	122.5	130.8	133.7	138.2
70°	79.2	79.2	82.2	82.9	83.7	84.4	91.9	101.6	109.1	112.8	118.1
72.5°	67.2	68.0	69.5	70.2	71.7	73.2	75.5	80.7	89.7	93.4	99.4
75°	55.3	56.0	56.8	57.5	59.8	60.5	62.8	65.7	69.5	74.0	77.7
77.5°	44.1	44.1	44.8	46.3	47.8	48.6	50.8	52.3	53.8	56.0	59.0
80°	32.9	33.6	33.6	35.1	35.1	35.9	36.6	38.9	40.3	41.8	43.3
82.5°	22.4	23.9	23.9	23.9	24.7	25.4	26.2	26.2	27.6	28.4	30.6
85°	13.4	14.2	14.2	14.2	13.4	14.9	14.9	15.7	15.7	15.7	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.5	29.7	29.0	28.2	27.4	26.3	25.2	24.1	23.0	22.4	25.0
97.5°	37.7	37.2	36.7	36.3	35.8	33.3	30.8	28.3	25.8	24.6	31.0
100°	45.0	43.7	42.5	41.2	40.0	37.4	34.7	32.1	29.4	28.1	38.8
102.5°	48.2	46.5	44.8	43.1	41.4	69.8	98.2	126.5	154.9	169.1	169.3
105°	49.6	47.9	46.2	44.5	42.8	85.4	127.9	170.5	213.0	234.3	232.0
107.5°	51.0	49.3	47.6	45.9	44.2	96.7	149.3	201.8	254.3	280.6	278.7
110°	60.4	76.0	91.6	107.2	122.8	167.8	212.9	257.9	303.0	325.5	323.9

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.6	154.8	222.0	289.2	356.4	359.0	361.7	364.3	367.0	368.3	366.9
115°	144.1	216.3	288.4	360.6	432.8	428.9	425.0	421.1	417.2	415.3	414.0
117.5°	381.5	403.8	426.1	448.4	470.7	468.1	465.4	462.8	460.1	458.8	457.2
120°	521.7	519.8	517.9	516.1	514.2	511.4	508.6	505.8	503.0	501.6	500.4
122.5°	559.3	558.4	557.5	556.5	555.6	552.5	549.4	546.3	543.2	541.6	540.4
125°	597.2	596.1	595.0	593.9	592.8	589.8	586.9	583.9	581.0	579.5	578.5
127.5°	633.4	631.9	630.3	628.8	627.2	624.8	622.5	620.1	617.8	616.6	615.5
130°	667.0	665.3	663.6	661.8	660.1	658.4	656.7	655.0	653.3	652.4	651.2
132.5°	698.7	697.3	695.9	694.5	693.1	691.4	689.7	688.0	686.3	685.4	684.4
135°	729.5	728.0	726.4	724.9	723.3	721.9	720.5	719.1	717.7	717.0	715.7
137.5°	758.3	756.7	755.2	753.6	752.0	750.4	748.9	747.3	745.8	745.0	744.1
140°	785.7	784.3	782.9	781.5	780.1	778.4	776.7	775.0	773.3	772.4	771.8
142.5°	811.1	809.8	808.6	807.3	806.1	804.1	802.0	800.0	797.9	796.9	796.4
145°	834.3	833.2	832.1	831.0	829.9	827.3	824.6	822.0	819.3	818.0	818.1
147.5°	854.8	854.0	853.3	852.5	851.7	849.0	846.4	843.7	841.0	839.7	839.9
150°	874.3	873.4	872.5	871.5	870.6	868.1	865.6	863.1	860.6	859.4	859.9
152.5°	891.9	891.0	890.0	889.1	888.1	885.8	883.4	881.1	878.8	877.6	878.2
155°	907.3	906.4	905.5	904.5	903.6	901.7	899.9	898.0	896.1	895.2	895.9
157.5°	921.3	920.2	919.1	918.0	916.9	915.5	914.1	912.7	911.3	910.6	911.2
160°	932.5	931.6	930.7	929.7	928.8	927.9	926.9	926.0	925.1	924.6	925.1
162.5°	943.8	942.7	941.6	940.5	939.4	938.6	937.8	937.0	936.2	935.8	936.3
165°	952.2	951.1	950.0	948.9	947.8	947.3	946.9	946.4	945.9	945.7	946.2
167.5°	959.9	958.8	957.7	956.6	955.5	955.0	954.6	954.1	953.6	953.4	953.9
170°	965.5	964.4	963.3	962.2	961.1	960.8	960.5	960.2	959.9	959.7	960.2
172.5°	969.7	968.6	967.5	966.4	965.3	965.0	964.7	964.4	964.1	963.9	964.4
175°	972.5	971.4	970.3	969.2	968.1	967.8	967.5	967.2	966.9	966.7	967.2
177.5°	973.2	972.1	971.0	969.9	968.8	968.6	968.5	968.3	968.2	968.1	968.6
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1075.2	1075.2	1075.2	1075.2
2.5°	1055.7	1053.5	1066.9	1081.9
5°	1034.1	1037.8	1055.0	1075.9
7.5°	1011.6	1019.9	1040.0	1067.7
10°	980.3	995.2	1025.8	1054.2
12.5°	949.6	969.8	998.9	1032.6
15°	915.3	937.7	973.5	1013.9
17.5°	877.2	902.6	944.4	988.5
20°	836.8	870.4	914.5	962.3
22.5°	792.0	832.3	877.9	931.0
25°	748.6	792.7	838.3	899.6
27.5°	706.1	749.4	800.2	862.2
30°	663.5	703.1	757.6	824.1
32.5°	617.9	659.0	716.5	784.5
35°	576.1	617.1	670.9	738.2
37.5°	531.2	575.3	626.9	696.3
40°	478.9	530.5	580.5	647.0
42.5°	435.6	490.1	538.7	601.5
45°	401.2	452.8	493.1	554.4
47.5°	369.1	410.9	452.0	508.8
50°	338.5	370.6	413.2	464.0
52.5°	307.1	334.7	371.3	419.2
55°	278.7	304.8	337.7	374.3
57.5°	252.5	271.2	304.1	337.0
60°	223.4	242.8	268.2	295.9
62.5°	198.7	213.7	237.6	260.8
65°	172.6	186.8	204.7	226.4
67.5°	148.7	161.4	175.6	192.8
70°	127.0	136.7	147.2	162.1
72.5°	103.9	114.3	124.0	136.0
75°	85.2	89.7	97.9	106.1
77.5°	65.7	71.7	76.2	82.9
80°	47.1	52.3	53.8	59.0
82.5°	31.4	34.4	37.4	38.9
85°	17.9	19.4	22.4	23.2
87.5°	6.7	7.5	9.0	10.5
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.3	40.4	45.6
97.5°	43.8	56.5	69.3	82.1
100°	60.1	81.5	102.8	124.2
102.5°	169.6	169.9	170.2	170.5
105°	227.3	222.6	218.0	213.3
107.5°	274.8	270.9	267.0	263.1
110°	320.6	317.3	314.1	310.8



TEST NUMBER: P1008426

CATALOG NUMBER: S122RDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	364.1	361.3	358.5	355.7
115°	411.3	408.7	406.0	403.4
117.5°	454.1	451.0	447.9	444.8
120°	498.1	495.8	493.4	491.1
122.5°	537.9	535.4	532.9	530.4
125°	576.4	574.4	572.3	570.3
127.5°	613.3	611.2	609.0	606.8
130°	648.7	646.2	643.7	641.2
132.5°	682.4	680.3	678.3	676.3
135°	713.2	710.7	708.2	705.7
137.5°	742.2	740.3	738.5	736.6
140°	770.5	769.3	768.0	766.8
142.5°	795.3	794.2	793.1	792.0
145°	818.2	818.4	818.5	818.7
147.5°	840.4	840.9	841.3	841.8
150°	861.0	862.1	863.2	864.3
152.5°	879.5	880.7	882.0	883.2
155°	897.3	898.7	900.1	901.5
157.5°	912.5	913.7	915.0	916.2
160°	926.0	926.9	927.9	928.8
162.5°	937.2	938.2	939.1	940.1
165°	947.1	948.0	949.0	949.9
167.5°	954.8	955.7	956.7	957.6
170°	961.1	962.0	963.0	963.9
172.5°	965.3	966.2	967.2	968.1
175°	968.3	969.4	970.5	971.6
177.5°	969.7	970.8	971.9	973.0
180°	969.5	969.5	969.5	969.5

(END OF REPORT)