

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008435

Luminaire Tested: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008435
REPORT IS A COMBINATION OF REPORTS P988385 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5515.0 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			34
1	95	91	87	84	85	82	79	76	66	64	62	51	49	48	37	36	36			29
2	87	80	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31			25
3	79	71	64	58	71	64	58	54	52	48	44	40	38	35	30	28	27			22
4	73	63	55	50	66	57	51	46	46	42	38	36	33	31	27	25	24			20
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21			17
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19			16
7	57	46	38	33	52	42	35	31	34	30	26	27	24	21	21	19	17			14
8	53	42	34	29	48	38	32	27	31	27	23	25	22	19	19	17	15			13
9	50	38	31	26	45	35	29	24	29	24	21	23	20	17	18	16	14			12
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16945	16945	16945	16945
5°	16986	17998	17044	14379
10°	16798	19025	16917	11875
15°	16433	19030	16712	8920
20°	15995	15731	16343	7359
25°	15464	9830	15797	6261
30°	14786	6293	15187	5389
35°	13959	4837	14411	4612
40°	13038	4066	13597	4034
45°	12056	3460	12560	3387
50°	11048	2940	11565	2930
55°	9931	2556	10467	2521
60°	8940	1948	9413	1924
65°	8013	1466	8489	1663
70°	6990	1171	7540	1355
75°	5907	898	6450	1026
80°	4694	610	5046	673
85°	3263	315	3574	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15501 cd/sqm

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	1.8
10°-20°	283.4	5.1
20°-30°	364.8	6.6
30°-40°	346.1	6.3
40°-50°	296.6	5.4
50°-60°	225.9	4.1
60°-70°	142.4	2.6
70°-80°	71.1	1.3
80°-90°	20.5	0.4
90°-100°	41.2	0.7
100°-110°	153.6	2.8
110°-120°	407.3	7.4
120°-130°	675.6	12.2
130°-140°	717.6	13.0
140°-150°	666.9	12.1
150°-160°	536.2	9.7
160°-170°	345.5	6.3
170°-180°	118.9	2.2
0°-30°	749.7	13.6
0°-40°	1095.8	19.9
0°-60°	1618.2	29.3
0°-90°	1852.2	33.6
90°-120°	602.1	10.9
90°-150°	2662.2	48.3
90°-180°	3663.0	66.4
0°-180°	5515.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1070	1070	1070	1070	1070	
5°	1071	1191	1075	952	1071	102
15°	1010	1344	1027	630	1010	284
25°	896	717	915	457	896	411
35°	735	353	759	337	735	460
45°	552	246	575	240	552	426
55°	373	170	393	168	373	336
65°	225	88	239	100	225	224
75°	106	47	115	54	106	114
85°	23	13	25	14	23	26
90°	1	24	1	24	1	5
95°	59	39	59	39	59	70
105°	275	69	275	69	275	294
115°	520	74	520	74	520	512
125°	735	773	735	773	735	656
135°	910	939	910	939	910	703
145°	1055	1071	1055	1071	1055	660
155°	1162	1163	1162	1163	1162	535
165°	1224	1221	1224	1221	1224	346
175°	1252	1245	1252	1245	1252	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1077.2	1081.7	1083.9	1086.9	1093.6	1098.1	1104.7	1106.2	1105.5	1108.5	1100.3
5°	1071.3	1080.9	1089.9	1097.3	1109.2	1116.6	1124.8	1134.5	1136.7	1147.9	1141.2
7.5°	1063.1	1077.2	1089.9	1104.7	1122.6	1132.3	1144.9	1159.8	1166.5	1179.9	1183.6
10°	1049.7	1069.8	1091.4	1107.0	1131.5	1148.6	1160.5	1184.3	1200.0	1220.1	1217.1
12.5°	1028.1	1054.2	1083.2	1109.2	1141.2	1152.4	1174.7	1199.2	1219.3	1237.9	1254.3
15°	1009.5	1039.3	1071.3	1103.3	1139.7	1160.5	1182.9	1214.8	1236.4	1269.2	1283.3
17.5°	984.2	1022.2	1060.1	1095.8	1139.0	1162.8	1190.3	1221.5	1253.5	1284.8	1295.9
20°	958.2	999.1	1040.0	1088.4	1137.5	1160.5	1188.8	1227.5	1258.7	1283.3	1283.3
22.5°	926.9	976.8	1023.7	1069.8	1123.3	1156.8	1185.8	1231.2	1253.5	1258.7	1238.7
25°	895.7	945.5	996.9	1054.2	1115.2	1144.9	1177.7	1220.1	1227.5	1206.7	1154.6
27.5°	858.5	914.3	972.3	1034.1	1098.1	1135.2	1165.0	1193.3	1179.1	1123.3	1042.3
30°	820.6	880.8	946.3	1005.1	1082.4	1116.6	1141.9	1150.1	1105.5	1014.7	909.8
32.5°	781.1	839.9	909.1	979.8	1057.9	1090.6	1107.0	1085.4	1003.6	889.0	761.0
35°	735.0	801.2	873.4	947.0	1024.4	1049.0	1058.6	1005.8	900.9	752.9	625.7
37.5°	693.3	759.6	836.9	912.1	987.2	1000.6	990.9	908.3	775.2	628.6	504.4
40°	644.2	714.9	790.8	874.9	936.6	940.3	916.5	809.4	644.2	506.6	430.0
42.5°	598.9	670.3	746.2	831.7	878.6	865.9	834.0	693.3	537.9	436.7	374.9
45°	552.0	619.7	701.5	777.4	810.9	781.1	732.8	583.2	451.6	375.7	328.1
47.5°	506.6	569.9	650.9	723.9	729.8	696.3	639.0	488.8	391.3	330.3	291.6
50°	462.0	525.2	601.1	661.4	655.4	609.3	544.6	424.8	340.0	291.6	259.6
52.5°	417.3	474.6	548.3	595.9	570.6	526.0	462.0	360.1	296.8	254.4	229.9
55°	372.7	426.3	489.5	528.9	488.8	437.4	392.1	308.7	257.4	223.2	204.6
57.5°	335.5	377.9	435.9	459.8	411.4	371.2	331.8	265.6	223.2	198.6	177.1
60°	294.6	333.3	380.9	395.0	345.2	312.5	279.0	224.7	191.2	169.6	155.5
62.5°	259.6	291.6	328.1	328.1	284.2	259.6	234.3	188.2	160.7	143.6	136.9
65°	225.4	248.5	274.5	271.5	234.3	212.8	192.7	155.5	134.7	122.7	116.1
67.5°	191.9	209.8	226.9	216.5	189.7	171.1	152.5	125.7	111.6	103.4	94.5
70°	161.4	175.6	184.5	174.8	148.0	132.4	119.0	101.2	90.0	79.6	74.4
72.5°	135.4	141.3	144.3	132.4	110.1	101.2	91.5	78.9	69.2	64.0	62.5
75°	105.6	110.8	108.6	99.7	81.1	74.4	67.0	58.0	55.8	52.8	51.3
77.5°	82.6	82.6	78.9	70.7	58.0	52.8	49.8	45.4	43.1	42.4	40.9
80°	58.8	58.0	55.8	46.9	39.4	36.5	36.5	33.5	32.7	31.2	31.2
82.5°	38.7	38.7	35.7	28.3	26.0	25.3	24.5	23.1	23.1	22.3	22.3
85°	23.1	21.6	17.9	15.6	14.9	14.9	14.1	13.4	14.1	13.4	13.4
87.5°	10.4	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.9	16.5	18.1
92.5°	22.6	21.8	21.0	20.2	19.4	19.0	19.3	19.9	20.5	21.1	21.7
95°	58.8	52.2	45.5	38.9	32.2	28.9	29.6	31.0	32.5	33.9	35.3
97.5°	105.8	89.3	72.8	56.3	39.8	31.6	33.2	36.4	39.7	42.9	46.1
100°	160.0	132.5	105.0	77.5	50.0	36.2	37.9	41.3	44.7	48.1	51.5
102.5°	219.7	219.3	218.9	218.5	218.1	217.9	199.6	163.0	126.5	89.9	53.3
105°	274.8	280.8	286.9	292.9	299.0	302.0	274.6	219.7	164.8	110.0	55.1
107.5°	339.0	344.0	349.0	354.1	359.1	361.6	327.8	260.1	192.4	124.7	57.0
110°	400.5	404.7	408.9	413.2	417.4	419.5	390.5	332.4	274.3	216.3	158.2

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	458.4	462.0	465.6	469.2	472.8	474.6	472.9	469.5	466.1	462.7	459.3
115°	519.8	523.2	526.6	530.1	533.5	535.2	537.7	542.7	547.8	552.8	557.8
117.5°	573.2	577.2	581.2	585.2	589.2	591.2	592.9	596.3	599.8	603.2	606.6
120°	632.8	635.8	638.8	641.9	644.9	646.4	648.2	651.8	655.5	659.1	662.7
122.5°	683.5	686.7	689.9	693.1	696.3	697.9	699.9	703.9	708.0	712.0	716.0
125°	735.0	737.6	740.2	742.8	745.4	746.7	748.6	752.4	756.3	760.1	763.9
127.5°	782.0	784.8	787.6	790.5	793.3	794.7	796.2	799.2	802.2	805.2	808.2
130°	826.3	829.5	832.7	836.0	839.2	840.8	841.9	844.1	846.3	848.5	850.7
132.5°	871.5	874.1	876.7	879.4	882.0	883.3	884.4	886.6	888.8	891.0	893.2
135°	909.5	912.7	915.9	919.1	922.3	923.9	924.8	926.6	928.5	930.3	932.1
137.5°	949.3	951.7	954.1	956.5	958.9	960.1	961.1	963.1	965.1	967.1	969.1
140°	988.1	989.7	991.3	993.0	994.6	995.4	996.5	998.7	1000.9	1003.1	1005.3
142.5°	1020.7	1022.1	1023.5	1024.9	1026.3	1027.0	1028.3	1030.9	1033.6	1036.2	1038.8
145°	1055.0	1054.8	1054.6	1054.4	1054.2	1054.1	1055.8	1059.2	1062.7	1066.1	1069.5
147.5°	1084.9	1084.3	1083.7	1083.1	1082.5	1082.2	1083.9	1087.3	1090.7	1094.1	1097.5
150°	1113.8	1112.4	1111.0	1109.6	1108.2	1107.5	1109.1	1112.3	1115.5	1118.7	1121.9
152.5°	1138.2	1136.6	1135.0	1133.4	1131.8	1131.0	1132.5	1135.5	1138.5	1141.5	1144.5
155°	1161.7	1159.9	1158.1	1156.3	1154.5	1153.6	1154.8	1157.2	1159.6	1162.0	1164.4
157.5°	1180.7	1179.1	1177.5	1175.9	1174.3	1173.5	1174.4	1176.2	1178.0	1179.8	1181.6
160°	1197.0	1195.8	1194.6	1193.3	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0
162.5°	1211.4	1210.2	1209.0	1207.8	1206.6	1206.0	1206.5	1207.5	1208.5	1209.5	1210.5
165°	1224.1	1222.9	1221.7	1220.5	1219.3	1218.7	1219.0	1219.6	1220.2	1220.8	1221.4
167.5°	1234.0	1232.8	1231.6	1230.4	1229.2	1228.6	1228.9	1229.5	1230.1	1230.7	1231.3
170°	1242.2	1241.0	1239.8	1238.5	1237.3	1236.7	1236.9	1237.3	1237.8	1238.2	1238.6
172.5°	1247.6	1246.4	1245.2	1244.0	1242.8	1242.2	1242.4	1242.8	1243.2	1243.6	1244.0
175°	1252.1	1250.7	1249.3	1247.9	1246.5	1245.8	1246.0	1246.4	1246.8	1247.2	1247.6
177.5°	1253.9	1252.5	1251.1	1249.7	1248.3	1247.6	1247.7	1247.9	1248.1	1248.3	1248.5
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1108.5	1110.0	1112.2	1122.6	1124.1	1127.1	1125.6	1125.6	1126.3	1124.8	1125.6
5°	1156.1	1158.3	1169.5	1182.1	1185.1	1182.1	1185.8	1191.0	1191.0	1191.0	1189.6
7.5°	1200.7	1208.9	1221.5	1240.1	1243.9	1247.6	1254.3	1249.8	1251.3	1258.0	1255.8
10°	1243.9	1255.8	1269.9	1285.5	1293.7	1298.9	1301.9	1308.6	1324.2	1306.4	1313.0
12.5°	1284.8	1301.9	1316.8	1333.9	1339.8	1346.5	1348.8	1354.7	1354.7	1354.0	1359.2
15°	1311.6	1327.2	1340.6	1351.7	1353.2	1351.7	1350.2	1351.0	1353.2	1344.3	1349.5
17.5°	1317.5	1319.0	1323.5	1319.0	1319.7	1304.1	1295.2	1293.0	1272.1	1272.9	1290.0
20°	1288.5	1263.2	1256.5	1232.0	1217.1	1176.9	1175.4	1164.3	1120.4	1133.8	1130.8
22.5°	1208.9	1165.7	1108.5	1080.2	1066.1	1023.7	990.9	967.9	952.2	936.6	929.9
25°	1104.0	1034.1	953.0	897.2	889.0	849.6	789.3	761.0	727.6	717.2	735.0
27.5°	968.6	877.8	786.3	700.8	685.2	649.5	619.0	598.9	560.2	558.0	559.4
30°	784.9	693.3	616.7	560.9	522.2	505.9	485.8	470.9	455.3	461.2	462.7
32.5°	645.0	558.0	486.5	456.8	438.9	428.5	411.4	401.7	395.0	392.8	392.1
35°	512.6	454.5	422.6	393.5	383.1	375.7	363.0	358.6	352.6	353.4	353.4
37.5°	438.9	390.6	366.8	351.9	342.2	338.5	330.3	325.8	322.1	320.6	322.9
40°	378.7	345.2	330.3	316.9	308.7	307.2	302.8	297.6	293.1	293.9	296.1
42.5°	334.8	315.4	297.6	287.2	281.2	279.0	275.3	271.5	271.5	269.3	268.6
45°	299.8	284.2	269.3	259.6	255.9	252.9	248.5	247.7	244.8	245.5	246.2
47.5°	268.6	255.9	244.8	235.1	231.4	230.6	226.2	223.2	223.2	222.4	221.7
50°	240.3	227.6	218.0	212.8	207.6	206.1	205.3	204.6	203.1	203.1	203.8
52.5°	217.2	204.6	197.1	192.7	189.7	188.2	188.2	187.5	187.5	187.5	186.7
55°	191.9	181.5	175.6	174.1	172.6	171.8	171.1	169.6	168.9	170.4	168.9
57.5°	168.1	164.4	159.2	157.7	154.0	154.0	151.8	150.3	148.8	150.3	150.3
60°	149.5	144.3	141.3	136.9	133.9	130.9	127.2	126.5	125.0	124.2	123.5
62.5°	130.2	125.7	118.3	111.6	107.1	104.2	102.7	101.9	101.9	101.2	101.2
65°	108.6	98.2	94.5	92.2	91.5	90.8	89.3	88.5	89.3	88.5	89.3
67.5°	84.8	83.3	81.1	79.6	78.9	78.1	78.1	77.4	77.4	77.4	77.4
70°	73.6	69.9	69.2	67.7	67.7	67.0	67.0	67.0	67.0	66.2	67.7
72.5°	61.0	58.8	58.0	57.3	57.3	57.3	56.5	56.5	56.5	55.8	56.5
75°	49.8	49.1	47.6	47.6	46.9	47.6	46.9	46.9	46.1	46.9	46.9
77.5°	40.2	39.4	38.7	38.7	37.9	37.9	37.9	37.9	37.9	37.9	38.7
80°	30.5	29.8	29.0	29.8	29.0	29.8	29.0	29.0	29.8	29.0	29.0
82.5°	22.3	21.6	21.6	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
85°	13.4	12.6	12.6	13.4	12.6	13.4	12.6	12.6	12.6	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	19.1	20.1	21.1	22.1	22.6	22.8	23.2	23.6	24.0	24.4	24.0
92.5°	22.1	22.5	22.9	23.3	23.5	23.6	23.8	24.0	24.2	24.4	24.2
95°	36.3	37.3	38.3	39.3	39.8	39.7	39.5	39.3	39.1	38.9	39.1
97.5°	46.7	47.3	47.9	48.5	48.8	48.9	49.1	49.3	49.5	49.7	49.5
100°	53.1	54.7	56.4	58.0	58.8	59.0	59.4	59.8	60.2	60.6	60.2
102.5°	55.5	57.7	60.0	62.2	63.3	63.6	64.2	64.8	65.4	66.0	65.4
105°	57.3	59.5	61.8	64.0	65.1	65.5	66.3	67.1	67.9	68.7	67.9
107.5°	59.2	61.4	63.6	65.8	66.9	67.3	68.1	68.9	69.7	70.5	69.7
110°	138.1	118.0	97.9	77.8	67.8	68.2	69.0	69.8	70.6	71.4	70.6

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	372.7	286.1	199.5	112.9	69.6	69.9	70.5	71.1	71.7	72.3	71.7
115°	464.8	371.8	278.7	185.7	139.2	132.0	117.5	103.0	88.6	74.1	88.6
117.5°	577.9	549.1	520.4	491.7	477.3	451.0	398.4	345.7	293.1	240.5	293.1
120°	665.1	667.5	669.9	672.3	673.5	659.9	632.8	605.7	578.6	551.5	578.6
122.5°	717.2	718.4	719.6	720.8	721.4	721.5	721.7	721.9	722.1	722.3	722.1
125°	765.3	766.7	768.2	769.6	770.3	770.6	771.2	771.8	772.4	773.0	772.4
127.5°	810.2	812.2	814.3	816.3	817.3	817.4	817.6	817.8	818.0	818.2	818.0
130°	852.9	855.1	857.4	859.6	860.7	860.6	860.4	860.2	860.0	859.8	860.0
132.5°	895.0	896.8	898.6	900.4	901.3	901.2	901.0	900.8	900.6	900.4	900.6
135°	934.1	936.1	938.1	940.1	941.1	940.9	940.5	940.1	939.7	939.3	939.7
137.5°	971.1	973.1	975.2	977.2	978.2	977.9	977.3	976.7	976.1	975.5	976.1
140°	1007.1	1008.9	1010.7	1012.5	1013.4	1012.9	1011.9	1010.9	1009.9	1008.9	1009.9
142.5°	1040.4	1042.0	1043.6	1045.2	1046.0	1045.5	1044.5	1043.5	1042.5	1041.5	1042.5
145°	1070.9	1072.3	1073.7	1075.1	1075.8	1075.3	1074.3	1073.3	1072.3	1071.3	1072.3
147.5°	1098.5	1099.5	1100.5	1101.5	1102.0	1101.6	1100.8	1100.0	1099.2	1098.4	1099.2
150°	1123.1	1124.3	1125.6	1126.8	1127.4	1126.9	1125.9	1124.8	1123.8	1122.8	1123.8
152.5°	1145.7	1146.9	1148.2	1149.4	1150.0	1149.3	1147.9	1146.4	1145.0	1143.6	1145.0
155°	1165.6	1166.8	1168.0	1169.2	1169.8	1169.0	1167.4	1165.8	1164.2	1162.6	1164.2
157.5°	1183.0	1184.4	1185.8	1187.2	1187.9	1187.1	1185.5	1183.9	1182.3	1180.7	1182.3
160°	1198.2	1199.4	1200.6	1201.8	1202.4	1201.7	1200.3	1198.9	1197.5	1196.1	1197.5
162.5°	1211.9	1213.3	1214.8	1216.2	1216.9	1216.0	1214.2	1212.3	1210.5	1208.7	1210.5
165°	1222.8	1224.2	1225.6	1227.0	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1222.8
167.5°	1232.7	1234.1	1235.5	1236.9	1237.6	1236.7	1234.9	1233.1	1231.3	1229.5	1231.3
170°	1240.0	1241.4	1242.8	1244.2	1244.9	1244.0	1242.2	1240.3	1238.5	1236.7	1238.5
172.5°	1245.4	1246.8	1248.2	1249.6	1250.3	1249.4	1247.6	1245.8	1244.0	1242.2	1244.0
175°	1249.0	1250.4	1251.8	1253.2	1253.9	1252.9	1250.9	1248.9	1246.9	1244.9	1246.9
177.5°	1249.9	1251.3	1252.7	1254.1	1254.8	1253.9	1252.1	1250.3	1248.5	1246.7	1248.5
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1128.6	1123.3	1121.9	1123.3	1121.9	1122.6	1117.4	1098.1	1103.3	1095.1	1099.5
5°	1192.5	1188.1	1178.4	1176.9	1175.4	1173.9	1166.5	1149.4	1142.7	1131.5	1130.8
7.5°	1253.5	1253.5	1246.1	1240.9	1234.2	1229.0	1219.3	1194.0	1183.6	1170.2	1162.8
10°	1313.8	1294.4	1302.6	1297.4	1281.1	1278.1	1260.2	1245.4	1225.3	1211.9	1200.0
12.5°	1356.9	1351.0	1343.5	1339.1	1334.6	1325.0	1313.0	1275.1	1264.7	1237.9	1224.5
15°	1355.5	1351.7	1354.0	1354.0	1352.5	1350.2	1340.6	1313.0	1295.2	1269.2	1246.1
17.5°	1282.5	1292.2	1301.9	1308.6	1323.5	1330.2	1339.1	1322.7	1311.6	1289.2	1264.7
20°	1155.3	1179.1	1207.4	1213.4	1226.8	1266.2	1284.0	1298.2	1302.6	1295.2	1275.1
22.5°	978.3	998.4	1066.8	1065.3	1084.7	1131.5	1183.6	1226.0	1259.5	1278.1	1270.6
25°	766.3	794.5	831.0	858.5	921.7	991.7	1056.4	1124.1	1182.1	1233.4	1246.1
27.5°	579.5	616.7	645.7	682.2	714.2	796.8	880.1	985.7	1053.4	1150.9	1201.5
30°	468.7	485.8	514.8	531.9	547.5	610.8	705.3	809.4	928.4	1040.8	1127.8
32.5°	400.2	412.1	433.7	441.2	457.5	499.9	559.4	654.7	777.4	913.6	1028.1
35°	359.3	372.0	376.4	383.1	396.5	423.3	464.2	533.4	644.2	777.4	914.3
37.5°	324.4	331.1	343.7	348.2	352.6	372.7	400.2	448.6	522.2	631.6	783.4
40°	299.8	303.5	310.2	313.9	316.9	331.1	355.6	388.3	442.6	526.0	665.8
42.5°	273.8	278.2	282.7	287.2	290.9	302.0	316.9	348.2	384.6	447.8	549.0
45°	248.5	251.5	256.7	259.6	264.8	273.8	287.2	308.7	341.5	381.6	463.5
47.5°	225.4	229.1	231.4	235.1	238.8	248.5	261.1	275.3	302.0	341.5	401.0
50°	204.6	209.0	212.0	212.8	215.7	224.7	235.1	250.7	267.8	298.3	350.4
52.5°	189.7	190.4	192.7	195.7	194.9	200.1	209.8	221.7	239.5	264.1	302.0
55°	172.6	174.8	176.3	177.1	177.1	181.5	186.7	197.9	212.0	232.1	264.1
57.5°	151.0	153.3	157.7	159.2	161.4	163.7	165.9	173.3	185.2	204.6	230.6
60°	128.7	130.2	134.7	137.6	139.1	145.1	148.0	154.0	160.7	174.8	199.4
62.5°	103.4	104.9	107.1	110.1	113.1	122.0	129.4	135.4	140.6	150.3	170.4
65°	90.0	90.8	92.2	93.0	93.7	97.5	104.2	112.3	122.0	129.4	141.3
67.5°	78.1	78.9	79.6	81.1	81.8	82.6	85.6	87.8	97.5	107.9	116.8
70°	67.0	68.4	69.2	69.2	69.9	71.4	72.9	75.9	78.9	84.1	95.2
72.5°	56.5	57.3	58.8	58.8	58.8	60.3	61.7	63.2	64.7	67.7	72.2
75°	46.9	48.4	48.4	48.4	49.1	49.1	50.6	52.1	53.6	55.8	57.3
77.5°	38.7	38.7	38.7	38.7	39.4	39.4	40.2	41.7	42.4	43.1	44.6
80°	29.0	29.8	29.8	29.8	30.5	30.5	30.5	32.0	32.7	32.7	34.2
82.5°	21.6	21.6	21.6	22.3	21.6	22.3	22.3	23.1	22.3	23.1	23.8
85°	13.4	13.4	13.4	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	23.6	23.2	22.8	22.6	22.1	21.1	20.1	19.1	18.1	16.5	14.9
92.5°	24.0	23.8	23.6	23.5	23.3	22.9	22.5	22.1	21.7	21.1	20.5
95°	39.3	39.5	39.7	39.8	39.3	38.3	37.3	36.3	35.3	33.9	32.5
97.5°	49.3	49.1	48.9	48.8	48.5	47.9	47.3	46.7	46.1	42.9	39.7
100°	59.8	59.4	59.0	58.8	58.0	56.4	54.7	53.1	51.5	48.1	44.7
102.5°	64.8	64.2	63.6	63.3	62.2	60.0	57.7	55.5	53.3	49.9	46.5
105°	67.1	66.3	65.5	65.1	64.0	61.8	59.5	57.3	55.1	51.0	47.8
107.5°	68.9	68.1	67.3	66.9	65.8	63.6	61.4	59.2	57.0	52.7	49.5
110°	69.8	69.0	68.2	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	71.1	70.5	69.9	69.6	112.9	199.5	286.1	372.7	459.3	462.7	466.1
115°	103.0	117.5	132.0	139.2	185.7	278.7	371.8	464.8	557.8	552.8	547.8
117.5°	345.7	398.4	451.0	477.3	491.7	520.4	549.1	577.9	606.6	603.2	599.8
120°	605.7	632.8	659.9	673.5	672.3	669.9	667.5	665.1	662.7	659.1	655.5
122.5°	721.9	721.7	721.5	721.4	720.8	719.6	718.4	717.2	716.0	712.0	708.0
125°	771.8	771.2	770.6	770.3	769.6	768.2	766.7	765.3	763.9	760.1	756.3
127.5°	817.8	817.6	817.4	817.3	816.3	814.3	812.2	810.2	808.2	805.2	802.2
130°	860.2	860.4	860.6	860.7	859.6	857.4	855.1	852.9	850.7	848.5	846.3
132.5°	900.8	901.0	901.2	901.3	900.4	898.6	896.8	895.0	893.2	891.0	888.8
135°	940.1	940.5	940.9	941.1	940.1	938.1	936.1	934.1	932.1	930.3	928.5
137.5°	976.7	977.3	977.9	978.2	977.2	975.2	973.1	971.1	969.1	967.1	965.1
140°	1010.9	1011.9	1012.9	1013.4	1012.5	1010.7	1008.9	1007.1	1005.3	1003.1	1000.9
142.5°	1043.5	1044.5	1045.5	1046.0	1045.2	1043.6	1042.0	1040.4	1038.8	1036.2	1033.6
145°	1073.3	1074.3	1075.3	1075.8	1075.1	1073.7	1072.3	1070.9	1069.5	1066.1	1062.7
147.5°	1100.0	1100.8	1101.6	1102.0	1101.5	1100.5	1099.5	1098.5	1097.5	1094.1	1090.7
150°	1124.8	1125.9	1126.9	1127.4	1126.8	1125.6	1124.3	1123.1	1121.9	1118.7	1115.5
152.5°	1146.4	1147.9	1149.3	1150.0	1149.4	1148.2	1146.9	1145.7	1144.5	1141.5	1138.5
155°	1165.8	1167.4	1169.0	1169.8	1169.2	1168.0	1166.8	1165.6	1164.4	1162.0	1159.6
157.5°	1183.9	1185.5	1187.1	1187.9	1187.2	1185.8	1184.4	1183.0	1181.6	1179.8	1178.0
160°	1198.9	1200.3	1201.7	1202.4	1201.8	1200.6	1199.4	1198.2	1197.0	1195.8	1194.6
162.5°	1212.3	1214.2	1216.0	1216.9	1216.2	1214.8	1213.3	1211.9	1210.5	1209.5	1208.5
165°	1224.2	1225.6	1227.0	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1220.8	1220.2
167.5°	1233.1	1234.9	1236.7	1237.6	1236.9	1235.5	1234.1	1232.7	1231.3	1230.7	1230.1
170°	1240.3	1242.2	1244.0	1244.9	1244.2	1242.8	1241.4	1240.0	1238.6	1238.2	1237.8
172.5°	1245.8	1247.6	1249.4	1250.3	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2
175°	1248.9	1250.9	1252.9	1253.9	1253.2	1251.8	1250.4	1249.0	1247.6	1247.2	1246.8
177.5°	1250.3	1252.1	1253.9	1254.8	1254.1	1252.7	1251.3	1249.9	1248.5	1248.3	1248.1
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1092.8	1089.1	1089.1	1086.9	1086.9	1075.0	1075.0	1078.7	1074.2	1069.0	1061.6
5°	1121.1	1112.9	1110.7	1107.7	1098.1	1083.2	1077.2	1075.0	1066.1	1054.9	1042.3
7.5°	1147.9	1134.5	1127.8	1121.1	1108.5	1087.6	1075.7	1067.5	1054.2	1037.0	1020.7
10°	1173.9	1156.8	1139.7	1131.5	1113.7	1087.6	1070.5	1057.1	1037.8	1014.7	991.7
12.5°	1197.7	1162.0	1159.1	1142.7	1116.6	1086.9	1060.9	1041.5	1017.0	990.2	963.4
15°	1218.6	1182.1	1164.3	1149.4	1115.2	1078.0	1050.4	1026.6	993.9	963.4	930.7
17.5°	1229.0	1189.6	1177.7	1153.1	1118.1	1069.8	1032.6	1003.6	967.9	931.4	894.2
20°	1239.4	1193.3	1173.9	1156.8	1109.2	1054.2	1012.5	979.0	939.6	896.4	855.5
22.5°	1244.6	1193.3	1170.2	1146.4	1100.3	1037.0	987.9	948.5	902.4	858.5	809.4
25°	1235.7	1188.8	1161.3	1136.7	1084.7	1016.2	959.7	915.0	865.9	816.1	766.3
27.5°	1213.4	1178.4	1146.4	1121.1	1063.1	989.4	929.9	879.3	828.7	773.0	722.4
30°	1171.7	1156.1	1130.8	1102.5	1039.3	965.6	895.0	842.9	787.1	731.3	678.5
32.5°	1107.0	1120.4	1104.0	1079.5	1011.0	932.9	857.8	804.9	743.9	683.7	635.3
35°	1028.1	1075.7	1066.8	1049.7	981.3	897.9	822.8	758.8	697.8	636.8	588.5
37.5°	941.8	1014.0	1021.4	1011.0	947.0	862.2	779.6	717.2	654.7	592.9	543.8
40°	823.5	934.4	958.2	962.7	911.3	819.1	732.8	671.8	610.0	549.8	490.3
42.5°	714.9	854.8	884.5	903.1	865.9	776.7	689.6	621.9	560.9	506.6	447.1
45°	613.0	758.8	807.2	831.0	814.6	728.3	638.3	575.1	519.3	469.4	412.1
47.5°	508.1	654.7	722.4	760.3	760.3	679.2	589.2	526.7	473.1	430.7	380.2
50°	438.2	560.2	630.1	680.0	693.3	629.4	544.6	483.6	433.0	386.8	348.2
52.5°	373.5	482.8	540.8	592.9	631.6	575.8	494.7	439.7	389.8	346.7	316.2
55°	322.9	404.7	457.5	514.8	558.0	521.5	446.4	392.8	349.7	313.9	287.9
57.5°	274.5	345.9	389.1	439.7	485.8	458.3	398.0	351.9	313.9	282.7	259.6
60°	233.6	291.6	325.1	364.5	421.8	402.5	352.6	310.2	279.7	251.5	232.1
62.5°	198.6	244.8	273.0	301.3	353.4	344.4	305.8	273.0	247.0	223.2	206.8
65°	162.9	200.9	223.2	247.7	289.4	293.1	261.9	238.8	215.0	194.2	179.3
67.5°	131.7	161.4	181.5	202.4	235.8	246.2	224.7	205.3	185.2	168.1	154.7
70°	106.4	127.2	142.1	158.5	186.0	198.6	187.5	174.1	157.7	143.6	131.7
72.5°	84.1	97.5	106.4	119.0	141.3	154.0	153.3	141.3	129.4	119.8	110.1
75°	61.7	72.2	79.6	87.8	105.6	117.5	120.5	115.3	103.4	96.0	88.5
77.5°	46.9	52.8	56.5	62.5	75.1	85.6	90.0	88.5	80.3	74.4	69.2
80°	35.7	37.2	38.7	40.9	51.3	61.0	64.0	63.2	58.8	56.5	50.6
82.5°	25.3	26.0	26.8	27.5	31.2	39.4	42.4	43.9	40.2	37.9	32.7
85°	14.9	15.6	15.6	17.1	17.9	20.1	25.3	25.3	24.5	21.6	20.8
87.5°	7.4	7.4	6.7	6.7	7.4	8.2	9.7	11.2	9.7	8.9	8.2
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.9	19.3	19.0	19.4	20.2	21.0	21.8	22.6	21.8	21.0	20.2
95°	31.0	29.6	28.9	32.2	38.9	45.5	52.2	58.8	52.2	45.5	38.9
97.5°	36.4	33.2	31.6	39.8	56.3	72.8	89.3	105.8	89.3	72.8	56.3
100°	41.3	37.9	36.2	50.0	77.5	105.0	132.5	160.0	132.5	105.0	77.5
102.5°	163.0	199.6	217.9	218.1	218.5	218.9	219.3	219.7	219.3	218.9	218.5
105°	219.7	274.6	302.0	299.0	292.9	286.9	280.8	274.8	280.8	286.9	292.9
107.5°	260.1	327.8	361.6	359.1	354.1	349.0	344.0	339.0	344.0	349.0	354.1
110°	332.4	390.5	419.5	417.4	413.2	408.9	404.7	400.5	404.7	408.9	413.2

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	469.5	472.9	474.6	472.8	469.2	465.6	462.0	458.4	462.0	465.6	469.2
115°	542.7	537.7	535.2	533.5	530.1	526.6	523.2	519.8	523.2	526.6	530.1
117.5°	596.3	592.9	591.2	589.2	585.2	581.2	577.2	573.2	577.2	581.2	585.2
120°	651.8	648.2	646.4	644.9	641.9	638.8	635.8	632.8	635.8	638.8	641.9
122.5°	703.9	699.9	697.9	696.3	693.1	689.9	686.7	683.5	686.7	689.9	693.1
125°	752.4	748.6	746.7	745.4	742.8	740.2	737.6	735.0	737.6	740.2	742.8
127.5°	799.2	796.2	794.7	793.3	790.5	787.6	784.8	782.0	784.8	787.6	790.5
130°	844.1	841.9	840.8	839.2	836.0	832.7	829.5	826.3	829.5	832.7	836.0
132.5°	886.6	884.4	883.3	882.0	879.4	876.7	874.1	871.5	874.1	876.7	879.4
135°	926.6	924.8	923.9	922.3	919.1	915.9	912.7	909.5	912.7	915.9	919.1
137.5°	963.1	961.1	960.1	958.9	956.5	954.1	951.7	949.3	951.7	954.1	956.5
140°	998.7	996.5	995.4	994.6	993.0	991.3	989.7	988.1	989.7	991.3	993.0
142.5°	1030.9	1028.3	1027.0	1026.3	1024.9	1023.5	1022.1	1020.7	1022.1	1023.5	1024.9
145°	1059.2	1055.8	1054.1	1054.2	1054.4	1054.6	1054.8	1055.0	1054.8	1054.6	1054.4
147.5°	1087.3	1083.9	1082.2	1082.5	1083.1	1083.7	1084.3	1084.9	1084.3	1083.7	1083.1
150°	1112.3	1109.1	1107.5	1108.2	1109.6	1111.0	1112.4	1113.8	1112.4	1111.0	1109.6
152.5°	1135.5	1132.5	1131.0	1131.8	1133.4	1135.0	1136.6	1138.2	1136.6	1135.0	1133.4
155°	1157.2	1154.8	1153.6	1154.5	1156.3	1158.1	1159.9	1161.7	1159.9	1158.1	1156.3
157.5°	1176.2	1174.4	1173.5	1174.3	1175.9	1177.5	1179.1	1180.7	1179.1	1177.5	1175.9
160°	1193.3	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0	1195.8	1194.6	1193.3
162.5°	1207.5	1206.5	1206.0	1206.6	1207.8	1209.0	1210.2	1211.4	1210.2	1209.0	1207.8
165°	1219.6	1219.0	1218.7	1219.3	1220.5	1221.7	1222.9	1224.1	1222.9	1221.7	1220.5
167.5°	1229.5	1228.9	1228.6	1229.2	1230.4	1231.6	1232.8	1234.0	1232.8	1231.6	1230.4
170°	1237.3	1236.9	1236.7	1237.3	1238.5	1239.8	1241.0	1242.2	1241.0	1239.8	1238.5
172.5°	1242.8	1242.4	1242.2	1242.8	1244.0	1245.2	1246.4	1247.6	1246.4	1245.2	1244.0
175°	1246.4	1246.0	1245.8	1246.5	1247.9	1249.3	1250.7	1252.1	1250.7	1249.3	1247.9
177.5°	1247.9	1247.7	1247.6	1248.3	1249.7	1251.1	1252.5	1253.9	1252.5	1251.1	1249.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1058.6	1059.4	1061.6	1054.9	1044.5	1040.0	1026.6	1024.4	1022.2	1022.2	1024.4
5°	1034.8	1031.8	1032.6	1019.9	1005.1	996.1	977.5	980.5	970.8	964.9	966.4
7.5°	1008.8	1000.6	999.9	983.5	964.9	948.5	929.2	924.7	915.8	905.4	900.9
10°	976.0	970.1	958.9	940.3	916.5	903.1	877.1	861.5	859.2	843.6	837.7
12.5°	942.6	932.2	921.0	895.0	868.2	846.6	827.3	810.1	798.2	784.9	775.9
15°	903.9	891.2	878.6	851.1	819.8	798.2	769.2	743.9	709.0	681.4	665.8
17.5°	861.5	847.3	830.2	799.7	769.2	739.5	685.9	656.2	631.6	615.2	605.6
20°	817.6	802.0	784.9	754.4	701.5	649.5	619.7	596.6	581.8	565.4	553.5
22.5°	771.5	755.1	736.5	688.9	633.1	596.6	573.6	552.0	530.4	521.5	515.5
25°	728.3	713.4	689.6	624.9	581.0	547.5	521.5	507.4	496.2	484.3	473.1
27.5°	683.7	656.2	622.7	568.4	540.8	506.6	488.0	477.6	458.3	450.1	444.9
30°	630.1	599.6	567.6	528.9	496.9	473.1	456.0	438.9	427.8	419.6	410.7
32.5°	575.8	546.8	526.7	486.5	462.7	438.2	421.8	411.4	395.0	389.8	386.1
35°	528.9	504.4	486.5	453.8	431.5	409.2	397.3	381.6	371.2	361.6	355.6
37.5°	482.8	469.4	450.8	423.3	399.5	381.6	365.3	360.1	345.9	340.7	334.8
40°	450.8	430.7	415.1	391.3	371.2	351.9	341.5	329.6	319.9	311.7	309.5
42.5°	412.1	397.3	388.3	362.3	341.5	330.3	317.7	304.3	296.8	290.1	282.0
45°	383.1	369.7	357.1	336.3	317.7	303.5	292.4	283.4	270.8	267.8	255.2
47.5°	352.6	339.2	329.6	308.7	291.6	278.2	270.0	258.1	247.7	241.0	235.1
50°	322.1	311.0	302.0	284.2	269.3	255.2	244.0	232.1	227.6	216.5	212.8
52.5°	293.1	285.7	276.0	258.9	244.0	232.1	220.2	210.5	203.8	197.9	193.4
55°	268.6	256.7	252.2	233.6	220.9	208.3	197.9	191.9	183.8	180.0	176.3
57.5°	241.0	234.3	226.9	212.8	198.6	186.7	179.3	170.4	165.9	161.4	158.5
60°	217.2	207.6	201.6	189.7	177.1	165.9	159.2	152.5	146.6	142.8	136.9
62.5°	189.7	182.3	178.5	165.9	155.5	145.1	139.1	132.4	128.0	121.3	113.8
65°	165.9	159.9	155.5	145.1	135.4	125.7	119.8	111.6	105.6	101.9	101.2
67.5°	145.1	140.6	133.9	124.2	114.6	107.1	100.4	93.7	93.0	91.5	91.5
70°	122.0	117.5	113.8	103.4	95.2	87.0	85.6	83.3	81.1	80.3	78.9
72.5°	101.9	98.2	93.7	84.8	76.6	74.4	72.9	71.4	69.2	68.4	67.7
75°	82.6	77.4	74.4	66.2	64.0	62.5	61.0	58.8	57.3	56.5	55.1
77.5°	63.2	58.0	58.0	53.6	52.1	49.8	48.4	46.9	46.1	44.6	44.6
80°	44.6	44.6	43.1	40.9	38.7	37.9	35.7	35.0	34.2	35.0	33.5
82.5°	32.7	29.8	29.8	28.3	26.8	26.0	24.5	24.5	23.8	23.8	23.8
85°	18.6	18.6	17.9	16.4	15.6	15.6	14.9	14.9	14.1	14.1	13.4
87.5°	7.4	6.7	7.4	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	9.7	10.8	11.6	13.2	14.9	16.5	18.1	19.1	20.1	21.1	22.1
92.5°	19.4	19.0	19.3	19.9	20.5	21.1	21.7	22.1	22.5	22.9	23.3
95°	32.2	28.9	29.6	31.0	32.5	33.9	35.3	36.3	37.3	38.3	39.3
97.5°	39.8	31.6	33.2	36.4	39.7	42.9	46.1	46.7	47.3	47.9	48.5
100°	50.0	36.2	37.9	41.3	44.7	48.1	51.5	53.1	54.7	56.4	58.0
102.5°	218.1	217.9	199.6	163.0	126.5	89.9	53.3	55.5	57.7	60.0	62.2
105°	299.0	302.0	274.6	219.7	164.8	110.0	55.1	57.3	59.5	61.8	64.0
107.5°	359.1	361.6	327.8	260.1	192.4	124.7	57.0	59.2	61.4	63.6	65.8
110°	417.4	419.5	390.5	332.4	274.3	216.3	158.2	138.1	118.0	97.9	77.8

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	472.8	474.6	472.9	469.5	466.1	462.7	459.3	372.7	286.1	199.5	112.9
115°	533.5	535.2	537.7	542.7	547.8	552.8	557.8	464.8	371.8	278.7	185.7
117.5°	589.2	591.2	592.9	596.3	599.8	603.2	606.6	577.9	549.1	520.4	491.7
120°	644.9	646.4	648.2	651.8	655.5	659.1	662.7	665.1	667.5	669.9	672.3
122.5°	696.3	697.9	699.9	703.9	708.0	712.0	716.0	717.2	718.4	719.6	720.8
125°	745.4	746.7	748.6	752.4	756.3	760.1	763.9	765.3	766.7	768.2	769.6
127.5°	793.3	794.7	796.2	799.2	802.2	805.2	808.2	810.2	812.2	814.3	816.3
130°	839.2	840.8	841.9	844.1	846.3	848.5	850.7	852.9	855.1	857.4	859.6
132.5°	882.0	883.3	884.4	886.6	888.8	891.0	893.2	895.0	896.8	898.6	900.4
135°	922.3	923.9	924.8	926.6	928.5	930.3	932.1	934.1	936.1	938.1	940.1
137.5°	958.9	960.1	961.1	963.1	965.1	967.1	969.1	971.1	973.1	975.2	977.2
140°	994.6	995.4	996.5	998.7	1000.9	1003.1	1005.3	1007.1	1008.9	1010.7	1012.5
142.5°	1026.3	1027.0	1028.3	1030.9	1033.6	1036.2	1038.8	1040.4	1042.0	1043.6	1045.2
145°	1054.2	1054.1	1055.8	1059.2	1062.7	1066.1	1069.5	1070.9	1072.3	1073.7	1075.1
147.5°	1082.5	1082.2	1083.9	1087.3	1090.7	1094.1	1097.5	1098.5	1099.5	1100.5	1101.5
150°	1108.2	1107.5	1109.1	1112.3	1115.5	1118.7	1121.9	1123.1	1124.3	1125.6	1126.8
152.5°	1131.8	1131.0	1132.5	1135.5	1138.5	1141.5	1144.5	1145.7	1146.9	1148.2	1149.4
155°	1154.5	1153.6	1154.8	1157.2	1159.6	1162.0	1164.4	1165.6	1166.8	1168.0	1169.2
157.5°	1174.3	1173.5	1174.4	1176.2	1178.0	1179.8	1181.6	1183.0	1184.4	1185.8	1187.2
160°	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0	1198.2	1199.4	1200.6	1201.8
162.5°	1206.6	1206.0	1206.5	1207.5	1208.5	1209.5	1210.5	1211.9	1213.3	1214.8	1216.2
165°	1219.3	1218.7	1219.0	1219.6	1220.2	1220.8	1221.4	1222.8	1224.2	1225.6	1227.0
167.5°	1229.2	1228.6	1228.9	1229.5	1230.1	1230.7	1231.3	1232.7	1234.1	1235.5	1236.9
170°	1237.3	1236.7	1236.9	1237.3	1237.8	1238.2	1238.6	1240.0	1241.4	1242.8	1244.2
172.5°	1242.8	1242.2	1242.4	1242.8	1243.2	1243.6	1244.0	1245.4	1246.8	1248.2	1249.6
175°	1246.5	1245.8	1246.0	1246.4	1246.8	1247.2	1247.6	1249.0	1250.4	1251.8	1253.2
177.5°	1248.3	1247.6	1247.7	1247.9	1248.1	1248.3	1248.5	1249.9	1251.3	1252.7	1254.1
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1024.4	1022.9	1018.4	1019.9	1017.7	1017.7	1016.2	1016.2	1016.2	1019.9	1017.7
5°	968.6	963.4	958.2	956.0	953.7	951.5	951.5	950.8	957.4	956.0	961.9
7.5°	899.4	897.9	887.5	887.5	883.8	882.3	886.0	886.8	887.5	889.0	892.7
10°	837.7	834.0	819.1	820.6	818.3	815.4	817.6	816.1	821.3	822.8	821.3
12.5°	764.8	758.1	741.7	733.5	724.6	717.9	726.1	720.1	741.0	746.9	763.3
15°	668.1	655.4	644.2	644.2	636.1	630.1	633.8	640.5	645.0	651.7	654.7
17.5°	603.3	598.1	589.2	584.0	581.8	579.5	579.5	582.5	592.2	591.4	597.4
20°	548.3	545.3	540.8	534.1	531.9	530.4	530.4	530.4	537.1	543.1	546.8
22.5°	510.3	508.1	505.1	496.2	491.7	490.3	494.0	496.2	501.4	505.9	509.6
25°	472.4	467.2	462.0	459.0	456.8	456.8	458.3	459.0	461.2	463.5	467.9
27.5°	441.2	437.4	430.0	421.8	421.8	419.6	421.1	422.6	427.8	435.2	438.9
30°	406.2	405.4	402.5	399.5	396.5	395.0	398.0	400.2	401.0	404.7	404.7
32.5°	380.9	375.7	370.5	367.5	366.0	365.3	366.0	369.0	369.0	373.5	378.7
35°	355.6	352.6	347.4	342.2	340.7	337.0	340.0	343.0	348.2	350.4	352.6
37.5°	328.1	324.4	322.1	320.6	317.7	318.4	316.2	320.6	325.1	324.4	325.8
40°	307.2	300.6	293.9	293.1	292.4	291.6	291.6	292.4	295.3	298.3	302.8
42.5°	280.5	278.2	272.3	266.3	264.8	263.4	261.9	264.8	270.8	276.0	278.2
45°	252.9	250.0	248.5	244.0	241.0	240.3	238.8	242.5	247.7	250.0	251.5
47.5°	227.6	226.9	222.4	223.2	220.9	221.7	220.9	223.2	223.2	225.4	226.9
50°	210.5	208.3	206.1	204.6	202.4	202.4	201.6	202.4	205.3	208.3	207.6
52.5°	193.4	189.7	189.0	188.2	186.7	188.2	186.0	186.7	189.7	191.2	190.4
55°	173.3	172.6	171.1	169.6	168.9	168.1	168.1	168.1	171.1	173.3	174.1
57.5°	157.7	154.0	151.0	151.0	148.0	147.3	148.8	149.5	151.8	153.3	154.7
60°	136.1	134.7	130.2	128.0	123.5	122.7	122.7	125.7	129.4	134.7	136.1
62.5°	113.1	110.8	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.8	110.8
65°	100.4	101.2	100.4	99.7	100.4	100.4	99.7	99.7	99.7	100.4	101.2
67.5°	90.0	89.3	90.0	89.3	88.5	88.5	87.8	88.5	89.3	90.0	90.0
70°	78.1	78.1	77.4	78.1	77.4	76.6	75.9	75.9	77.4	78.1	78.1
72.5°	67.0	67.0	66.2	66.2	64.7	64.7	65.5	64.7	64.7	67.0	67.0
75°	55.8	55.1	54.3	54.3	53.6	53.6	53.6	52.8	54.3	54.3	55.1
77.5°	43.9	43.9	43.9	43.1	43.1	42.4	42.4	43.1	43.1	43.1	43.9
80°	33.5	33.5	33.5	32.7	32.0	32.0	32.0	32.0	32.0	32.7	32.0
82.5°	23.1	23.1	23.1	23.1	23.1	22.3	22.3	22.3	23.1	23.1	22.3
85°	14.1	13.4	14.1	14.1	13.4	14.1	13.4	13.4	12.6	12.6	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	22.6	22.8	23.2	23.6	24.0	24.4	24.0	23.6	23.2	22.8	22.6
92.5°	23.5	23.6	23.8	24.0	24.2	24.4	24.2	24.0	23.8	23.6	23.5
95°	39.8	39.7	39.5	39.3	39.1	38.9	39.1	39.3	39.5	39.7	39.8
97.5°	48.8	48.9	49.1	49.3	49.5	49.7	49.5	49.3	49.1	48.9	48.8
100°	58.8	59.0	59.4	59.8	60.2	60.6	60.2	59.8	59.4	59.0	58.8
102.5°	63.3	63.6	64.2	64.8	65.4	66.0	65.4	64.8	64.2	63.6	63.3
105°	65.1	65.5	66.3	67.1	67.9	68.7	67.9	67.1	66.3	65.5	65.1
107.5°	66.9	67.3	68.1	68.9	69.7	70.5	69.7	68.9	68.1	67.3	66.9
110°	67.8	68.2	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	67.8

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.6	69.9	70.5	71.1	71.7	72.3	71.7	71.1	70.5	69.9	69.6
115°	139.2	132.0	117.5	103.0	88.6	74.1	88.6	103.0	117.5	132.0	139.2
117.5°	477.3	451.0	398.4	345.7	293.1	240.5	293.1	345.7	398.4	451.0	477.3
120°	673.5	659.9	632.8	605.7	578.6	551.5	578.6	605.7	632.8	659.9	673.5
122.5°	721.4	721.5	721.7	721.9	722.1	722.3	722.1	721.9	721.7	721.5	721.4
125°	770.3	770.6	771.2	771.8	772.4	773.0	772.4	771.8	771.2	770.6	770.3
127.5°	817.3	817.4	817.6	817.8	818.0	818.2	818.0	817.8	817.6	817.4	817.3
130°	860.7	860.6	860.4	860.2	860.0	859.8	860.0	860.2	860.4	860.6	860.7
132.5°	901.3	901.2	901.0	900.8	900.6	900.4	900.6	900.8	901.0	901.2	901.3
135°	941.1	940.9	940.5	940.1	939.7	939.3	939.7	940.1	940.5	940.9	941.1
137.5°	978.2	977.9	977.3	976.7	976.1	975.5	976.1	976.7	977.3	977.9	978.2
140°	1013.4	1012.9	1011.9	1010.9	1009.9	1008.9	1009.9	1010.9	1011.9	1012.9	1013.4
142.5°	1046.0	1045.5	1044.5	1043.5	1042.5	1041.5	1042.5	1043.5	1044.5	1045.5	1046.0
145°	1075.8	1075.3	1074.3	1073.3	1072.3	1071.3	1072.3	1073.3	1074.3	1075.3	1075.8
147.5°	1102.0	1101.6	1100.8	1100.0	1099.2	1098.4	1099.2	1100.0	1100.8	1101.6	1102.0
150°	1127.4	1126.9	1125.9	1124.8	1123.8	1122.8	1123.8	1124.8	1125.9	1126.9	1127.4
152.5°	1150.0	1149.3	1147.9	1146.4	1145.0	1143.6	1145.0	1146.4	1147.9	1149.3	1150.0
155°	1169.8	1169.0	1167.4	1165.8	1164.2	1162.6	1164.2	1165.8	1167.4	1169.0	1169.8
157.5°	1187.9	1187.1	1185.5	1183.9	1182.3	1180.7	1182.3	1183.9	1185.5	1187.1	1187.9
160°	1202.4	1201.7	1200.3	1198.9	1197.5	1196.1	1197.5	1198.9	1200.3	1201.7	1202.4
162.5°	1216.9	1216.0	1214.2	1212.3	1210.5	1208.7	1210.5	1212.3	1214.2	1216.0	1216.9
165°	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1222.8	1224.2	1225.6	1227.0	1227.7
167.5°	1237.6	1236.7	1234.9	1233.1	1231.3	1229.5	1231.3	1233.1	1234.9	1236.7	1237.6
170°	1244.9	1244.0	1242.2	1240.3	1238.5	1236.7	1238.5	1240.3	1242.2	1244.0	1244.9
172.5°	1250.3	1249.4	1247.6	1245.8	1244.0	1242.2	1244.0	1245.8	1247.6	1249.4	1250.3
175°	1253.9	1252.9	1250.9	1248.9	1246.9	1244.9	1246.9	1248.9	1250.9	1252.9	1253.9
177.5°	1254.8	1253.9	1252.1	1250.3	1248.5	1246.7	1248.5	1250.3	1252.1	1253.9	1254.8
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1019.9	1023.7	1022.2	1014.0	1022.2	1024.4	1028.9	1033.3	1036.3	1040.8	1044.5
5°	956.0	963.4	967.9	963.4	978.3	980.5	990.9	996.9	1005.8	1013.2	1019.2
7.5°	895.7	901.7	910.6	912.1	921.0	931.4	946.3	961.2	975.3	982.7	989.4
10°	831.0	841.4	854.8	851.8	865.2	881.6	897.2	921.0	932.9	946.3	958.2
12.5°	766.3	773.0	790.8	796.8	816.1	828.7	850.3	865.2	895.0	910.6	921.0
15°	653.2	680.7	703.0	729.8	755.1	778.9	798.2	825.0	851.1	863.0	880.1
17.5°	601.8	614.5	627.9	641.3	674.0	716.4	750.6	779.6	802.0	817.6	837.7
20°	548.3	560.9	575.8	588.5	608.5	639.0	681.4	731.3	758.1	774.4	793.8
22.5°	510.3	522.2	531.9	543.1	558.7	581.0	613.0	674.8	710.5	730.5	747.7
25°	469.4	484.3	494.7	502.9	515.5	540.1	566.1	601.1	665.1	680.7	704.5
27.5°	441.2	445.6	457.5	470.2	482.8	496.2	523.0	552.7	595.9	630.1	659.1
30°	407.7	418.8	430.0	435.2	446.4	465.7	482.1	514.1	547.5	574.3	609.3
32.5°	382.4	389.1	396.5	409.2	419.6	433.0	449.3	476.1	504.4	521.5	548.3
35°	354.1	358.6	374.2	379.4	389.8	403.2	419.6	440.4	470.9	484.3	503.6
37.5°	327.3	337.7	342.2	354.1	363.8	377.2	389.1	412.9	433.0	448.6	466.4
40°	306.5	311.0	319.1	329.6	337.7	348.2	363.0	380.2	401.7	414.4	430.0
42.5°	281.2	284.9	295.3	301.3	314.7	324.4	333.3	354.1	373.5	383.1	398.8
45°	253.7	262.6	269.3	281.2	288.6	300.6	311.7	326.6	344.4	355.6	364.5
47.5°	229.9	238.8	245.5	256.7	268.6	273.8	285.7	301.3	317.7	326.6	339.2
50°	210.5	213.5	226.2	231.4	244.0	254.4	262.6	276.0	293.9	299.1	309.5
52.5°	191.9	194.2	202.4	209.0	220.2	229.1	239.5	252.2	267.1	275.3	283.4
55°	175.6	177.1	180.8	188.2	195.7	206.8	216.5	228.4	241.0	250.0	257.4
57.5°	157.0	159.9	162.9	167.4	174.8	185.2	195.7	206.8	217.2	223.2	232.9
60°	135.4	139.9	145.1	150.3	155.5	162.9	174.8	185.2	194.9	200.1	207.6
62.5°	112.3	121.3	125.7	131.7	136.1	142.8	151.8	163.7	170.4	177.1	183.0
65°	101.2	101.9	102.7	108.6	116.8	123.5	131.7	140.6	151.0	155.5	159.9
67.5°	90.0	90.8	92.2	93.0	96.0	103.4	112.3	122.0	130.2	133.2	137.6
70°	78.9	78.9	81.8	82.6	83.3	84.1	91.5	101.2	108.6	112.3	117.5
72.5°	67.0	67.7	69.2	69.9	71.4	72.9	75.1	80.3	89.3	93.0	98.9
75°	55.1	55.8	56.5	57.3	59.5	60.3	62.5	65.5	69.2	73.6	77.4
77.5°	43.9	43.9	44.6	46.1	47.6	48.4	50.6	52.1	53.6	55.8	58.8
80°	32.7	33.5	33.5	35.0	35.0	35.7	36.5	38.7	40.2	41.7	43.1
82.5°	22.3	23.8	23.8	23.8	24.5	25.3	26.0	26.0	27.5	28.3	30.5
85°	13.4	14.1	14.1	14.1	13.4	14.9	14.9	15.6	15.6	15.6	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	22.1	21.1	20.1	19.1	18.1	16.5	14.9	13.2	11.6	10.8	9.7
92.5°	23.3	22.9	22.5	22.1	21.7	21.1	20.5	19.9	19.3	19.0	19.4
95°	39.3	38.3	37.3	36.3	35.3	33.9	32.5	31.0	29.6	28.9	32.2
97.5°	48.5	47.9	47.3	46.7	46.1	42.9	39.7	36.4	33.2	31.6	39.8
100°	58.0	56.4	54.7	53.1	51.5	48.1	44.7	41.3	37.9	36.2	50.0
102.5°	62.2	60.0	57.7	55.5	53.3	89.9	126.5	163.0	199.6	217.9	218.1
105°	64.0	61.8	59.5	57.3	55.1	110.0	164.8	219.7	274.6	302.0	299.0
107.5°	65.8	63.6	61.4	59.2	57.0	124.7	192.4	260.1	327.8	361.6	359.1
110°	77.8	97.9	118.0	138.1	158.2	216.3	274.3	332.4	390.5	419.5	417.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	112.9	199.5	286.1	372.7	459.3	462.7	466.1	469.5	472.9	474.6	472.8
115°	185.7	278.7	371.8	464.8	557.8	552.8	547.8	542.7	537.7	535.2	533.5
117.5°	491.7	520.4	549.1	577.9	606.6	603.2	599.8	596.3	592.9	591.2	589.2
120°	672.3	669.9	667.5	665.1	662.7	659.1	655.5	651.8	648.2	646.4	644.9
122.5°	720.8	719.6	718.4	717.2	716.0	712.0	708.0	703.9	699.9	697.9	696.3
125°	769.6	768.2	766.7	765.3	763.9	760.1	756.3	752.4	748.6	746.7	745.4
127.5°	816.3	814.3	812.2	810.2	808.2	805.2	802.2	799.2	796.2	794.7	793.3
130°	859.6	857.4	855.1	852.9	850.7	848.5	846.3	844.1	841.9	840.8	839.2
132.5°	900.4	898.6	896.8	895.0	893.2	891.0	888.8	886.6	884.4	883.3	882.0
135°	940.1	938.1	936.1	934.1	932.1	930.3	928.5	926.6	924.8	923.9	922.3
137.5°	977.2	975.2	973.1	971.1	969.1	967.1	965.1	963.1	961.1	960.1	958.9
140°	1012.5	1010.7	1008.9	1007.1	1005.3	1003.1	1000.9	998.7	996.5	995.4	994.6
142.5°	1045.2	1043.6	1042.0	1040.4	1038.8	1036.2	1033.6	1030.9	1028.3	1027.0	1026.3
145°	1075.1	1073.7	1072.3	1070.9	1069.5	1066.1	1062.7	1059.2	1055.8	1054.1	1054.2
147.5°	1101.5	1100.5	1099.5	1098.5	1097.5	1094.1	1090.7	1087.3	1083.9	1082.2	1082.5
150°	1126.8	1125.6	1124.3	1123.1	1121.9	1118.7	1115.5	1112.3	1109.1	1107.5	1108.2
152.5°	1149.4	1148.2	1146.9	1145.7	1144.5	1141.5	1138.5	1135.5	1132.5	1131.0	1131.8
155°	1169.2	1168.0	1166.8	1165.6	1164.4	1162.0	1159.6	1157.2	1154.8	1153.6	1154.5
157.5°	1187.2	1185.8	1184.4	1183.0	1181.6	1179.8	1178.0	1176.2	1174.4	1173.5	1174.3
160°	1201.8	1200.6	1199.4	1198.2	1197.0	1195.8	1194.6	1193.3	1192.1	1191.5	1192.1
162.5°	1216.2	1214.8	1213.3	1211.9	1210.5	1209.5	1208.5	1207.5	1206.5	1206.0	1206.6
165°	1227.0	1225.6	1224.2	1222.8	1221.4	1220.8	1220.2	1219.6	1219.0	1218.7	1219.3
167.5°	1236.9	1235.5	1234.1	1232.7	1231.3	1230.7	1230.1	1229.5	1228.9	1228.6	1229.2
170°	1244.2	1242.8	1241.4	1240.0	1238.6	1238.2	1237.8	1237.3	1236.9	1236.7	1237.3
172.5°	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2	1242.8	1242.4	1242.2	1242.8
175°	1253.2	1251.8	1250.4	1249.0	1247.6	1247.2	1246.8	1246.4	1246.0	1245.8	1246.5
177.5°	1254.1	1252.7	1251.3	1249.9	1248.5	1248.3	1248.1	1247.9	1247.7	1247.6	1248.3
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1070.5	1070.5	1070.5	1070.5
2.5°	1051.2	1049.0	1062.3	1077.2
5°	1029.6	1033.3	1050.4	1071.3
7.5°	1007.3	1015.5	1035.6	1063.1
10°	976.0	990.9	1021.4	1049.7
12.5°	945.5	965.6	994.6	1028.1
15°	911.3	933.6	969.3	1009.5
17.5°	873.4	898.7	940.3	984.2
20°	833.2	866.7	910.6	958.2
22.5°	788.6	828.7	874.1	926.9
25°	745.4	789.3	834.7	895.7
27.5°	703.0	746.2	796.8	858.5
30°	660.6	700.0	754.4	820.6
32.5°	615.2	656.2	713.4	781.1
35°	573.6	614.5	668.1	735.0
37.5°	528.9	572.8	624.2	693.3
40°	476.9	528.2	578.0	644.2
42.5°	433.7	488.0	536.4	598.9
45°	399.5	450.8	491.0	552.0
47.5°	367.5	409.2	450.1	506.6
50°	337.0	369.0	411.4	462.0
52.5°	305.8	333.3	369.7	417.3
55°	277.5	303.5	336.3	372.7
57.5°	251.5	270.0	302.8	335.5
60°	222.4	241.8	267.1	294.6
62.5°	197.9	212.8	236.6	259.6
65°	171.8	186.0	203.8	225.4
67.5°	148.0	160.7	174.8	191.9
70°	126.5	136.1	146.6	161.4
72.5°	103.4	113.8	123.5	135.4
75°	84.8	89.3	97.5	105.6
77.5°	65.5	71.4	75.9	82.6
80°	46.9	52.1	53.6	58.8
82.5°	31.2	34.2	37.2	38.7
85°	17.9	19.3	22.3	23.1
87.5°	6.7	7.4	8.9	10.4
90°	7.5	5.3	3.1	0.9
92.5°	20.2	21.0	21.8	22.6
95°	38.9	45.5	52.2	58.8
97.5°	56.3	72.8	89.3	105.8
100°	77.5	105.0	132.5	160.0
102.5°	218.5	218.9	219.3	219.7
105°	292.9	286.9	280.8	274.8
107.5°	354.1	349.0	344.0	339.0
110°	413.2	408.9	404.7	400.5

TEST NUMBER: P1008435

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	469.2	465.6	462.0	458.4
115°	530.1	526.6	523.2	519.8
117.5°	585.2	581.2	577.2	573.2
120°	641.9	638.8	635.8	632.8
122.5°	693.1	689.9	686.7	683.5
125°	742.8	740.2	737.6	735.0
127.5°	790.5	787.6	784.8	782.0
130°	836.0	832.7	829.5	826.3
132.5°	879.4	876.7	874.1	871.5
135°	919.1	915.9	912.7	909.5
137.5°	956.5	954.1	951.7	949.3
140°	993.0	991.3	989.7	988.1
142.5°	1024.9	1023.5	1022.1	1020.7
145°	1054.4	1054.6	1054.8	1055.0
147.5°	1083.1	1083.7	1084.3	1084.9
150°	1109.6	1111.0	1112.4	1113.8
152.5°	1133.4	1135.0	1136.6	1138.2
155°	1156.3	1158.1	1159.9	1161.7
157.5°	1175.9	1177.5	1179.1	1180.7
160°	1193.3	1194.6	1195.8	1197.0
162.5°	1207.8	1209.0	1210.2	1211.4
165°	1220.5	1221.7	1222.9	1224.1
167.5°	1230.4	1231.6	1232.8	1234.0
170°	1238.5	1239.8	1241.0	1242.2
172.5°	1244.0	1245.2	1246.4	1247.6
175°	1247.9	1249.3	1250.7	1252.1
177.5°	1249.7	1251.1	1252.5	1253.9
180°	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)