

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008436

Luminaire Tested: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008436
REPORT IS A COMBINATION OF REPORTS P988386 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5539.0 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	103	103	103	103	93	93	93	93		74	74	74		57	57	57		41	41	41
1	95	91	87	84	85	82	79	76		66	64	62		51	49	48		37	36	36
2	87	80	74	69	78	72	67	63		58	55	52		45	43	41		33	32	31
3	79	71	64	58	71	64	58	54		52	48	44		40	38	35		30	28	27
4	73	63	55	50	66	57	51	46		46	42	38		36	33	31		27	25	24
5	67	56	49	43	60	51	45	40		42	37	33		33	30	27		25	23	21
6	62	51	43	37	56	46	40	35		38	33	29		30	27	24		23	21	19
7	57	46	38	33	52	42	35	31		34	30	26		27	24	21		21	19	17
8	53	42	34	29	48	38	32	27		31	27	23		25	22	19		19	17	15
9	50	38	31	26	45	35	29	24		29	24	21		23	20	17		18	16	14
10	46	35	28	24	42	32	26	22		27	22	19		22	18	16		17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17020	17020	17020	17020
5°	17058	18077	17117	14441
10°	16870	19107	16990	11926
15°	16505	19113	16785	8958
20°	16064	15799	16415	7391
25°	15531	9873	15866	6288
30°	14849	6320	15252	5413
35°	14020	4857	14473	4633
40°	13095	4083	13655	4052
45°	12108	3476	12613	3401
50°	11096	2953	11612	2942
55°	9974	2566	10512	2533
60°	8979	1957	9455	1934
65°	8048	1472	8525	1671
70°	7020	1176	7570	1362
75°	5935	902	6478	1030
80°	4710	612	5070	675
85°	3277	315	3588	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15568 cd/sqm

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	1.8
10°-20°	284.7	5.1
20°-30°	366.3	6.6
30°-40°	347.6	6.3
40°-50°	297.9	5.4
50°-60°	226.8	4.1
60°-70°	143.1	2.6
70°-80°	71.4	1.3
80°-90°	20.6	0.4
90°-100°	41.4	0.7
100°-110°	154.2	2.8
110°-120°	409.1	7.4
120°-130°	678.5	12.2
130°-140°	720.7	13.0
140°-150°	669.9	12.1
150°-160°	538.5	9.7
160°-170°	347.0	6.3
170°-180°	119.4	2.2
0°-30°	753.0	13.6
0°-40°	1100.5	19.9
0°-60°	1625.2	29.3
0°-90°	1860.2	33.6
90°-120°	604.7	10.9
90°-150°	2673.8	48.3
90°-180°	3679.0	66.4
0°-180°	5539.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1076	1196	1080	956	1076	102
15°	1014	1350	1031	633	1014	285
25°	900	720	919	459	900	413
35°	738	355	762	338	738	462
45°	554	247	578	241	554	428
55°	374	171	394	169	374	337
65°	226	89	240	101	226	225
75°	106	47	116	54	106	115
85°	23	13	25	14	23	26
90°	1	24	1	24	1	5
95°	59	39	59	39	59	70
105°	276	69	276	69	276	295
115°	522	74	522	74	522	514
125°	738	776	738	776	738	658
135°	913	943	913	943	913	706
145°	1060	1076	1060	1076	1060	663
155°	1167	1168	1167	1168	1167	538
165°	1229	1227	1229	1227	1229	347
175°	1258	1250	1258	1250	1258	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1081.9	1086.4	1088.6	1091.6	1098.3	1102.8	1109.5	1111.0	1110.3	1113.3	1105.0
5°	1075.9	1085.6	1094.6	1102.1	1114.0	1121.5	1129.7	1139.4	1141.7	1152.9	1146.1
7.5°	1067.7	1081.9	1094.6	1109.5	1127.5	1137.2	1149.9	1164.8	1171.5	1185.0	1188.7
10°	1054.2	1074.4	1096.1	1111.8	1136.4	1153.6	1165.6	1189.5	1205.2	1225.3	1222.3
12.5°	1032.6	1058.7	1087.9	1114.0	1146.1	1157.3	1179.8	1204.4	1224.6	1243.3	1259.7
15°	1013.9	1043.8	1075.9	1108.0	1144.6	1165.6	1188.0	1220.1	1241.8	1274.6	1288.8
17.5°	988.5	1026.6	1064.7	1100.6	1143.9	1167.8	1195.4	1226.8	1259.0	1290.3	1301.5
20°	962.3	1003.4	1044.5	1093.1	1142.4	1165.6	1194.0	1232.8	1264.2	1288.8	1288.8
22.5°	931.0	981.0	1028.1	1074.4	1128.2	1161.8	1191.0	1236.5	1259.0	1264.2	1244.0
25°	899.6	949.6	1001.2	1058.7	1120.0	1149.9	1182.7	1225.3	1232.8	1211.9	1159.6
27.5°	862.2	918.3	976.5	1038.5	1102.8	1140.2	1170.0	1198.4	1184.2	1128.2	1046.8
30°	824.1	884.6	950.4	1009.4	1087.1	1121.5	1146.9	1155.1	1110.3	1019.1	913.8
32.5°	784.5	843.5	913.0	984.0	1062.5	1095.3	1111.8	1090.1	1007.9	892.8	764.3
35°	738.2	804.7	877.2	951.1	1028.8	1053.5	1063.2	1010.2	904.8	756.1	628.4
37.5°	696.3	762.8	840.5	916.0	991.5	1004.9	995.2	912.3	778.5	631.3	506.6
40°	647.0	718.0	794.2	878.7	940.7	944.4	920.5	812.9	647.0	508.8	431.9
42.5°	601.5	673.2	749.4	835.3	882.4	869.7	837.6	696.3	540.2	438.6	376.6
45°	554.4	622.4	704.6	780.8	814.4	784.5	735.9	585.8	453.5	377.3	329.5
47.5°	508.8	572.3	653.8	727.0	733.0	699.3	641.8	490.9	393.0	331.7	292.9
50°	464.0	527.5	603.7	664.2	658.2	611.9	546.9	426.6	341.4	292.9	260.8
52.5°	419.2	476.7	550.7	598.5	573.1	528.2	464.0	361.6	298.1	255.5	230.9
55°	374.3	428.1	491.6	531.2	490.9	439.3	393.8	310.1	258.5	224.1	205.5
57.5°	337.0	379.6	437.8	461.7	413.2	372.8	333.2	266.7	224.1	199.5	177.8
60°	295.9	334.7	382.5	396.7	346.7	313.8	280.2	225.6	192.0	170.4	156.2
62.5°	260.8	292.9	329.5	329.5	285.4	260.8	235.4	189.0	161.4	144.2	137.5
65°	226.4	249.5	275.7	272.7	235.4	213.7	193.5	156.2	135.2	123.3	116.6
67.5°	192.8	210.7	227.9	217.4	190.5	171.8	153.2	126.3	112.1	103.9	94.9
70°	162.1	176.3	185.3	175.6	148.7	133.0	119.5	101.6	90.4	79.9	74.7
72.5°	136.0	142.0	144.9	133.0	110.6	101.6	91.9	79.2	69.5	64.3	62.8
75°	106.1	111.3	109.1	100.1	81.4	74.7	67.2	58.3	56.0	53.0	51.6
77.5°	82.9	82.9	79.2	71.0	58.3	53.0	50.1	45.6	43.3	42.6	41.1
80°	59.0	58.3	56.0	47.1	39.6	36.6	36.6	33.6	32.9	31.4	31.4
82.5°	38.9	38.9	35.9	28.4	26.2	25.4	24.7	23.2	23.2	22.4	22.4
85°	23.2	21.7	17.9	15.7	14.9	14.9	14.2	13.4	14.2	13.4	13.4
87.5°	10.5	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.9	3.1	5.3	7.6	9.8	10.9	11.7	13.3	15.0	16.6	18.2
92.5°	22.7	21.9	21.1	20.3	19.5	19.1	19.4	20.0	20.6	21.2	21.8
95°	59.0	52.4	45.7	39.1	32.4	29.1	29.8	31.2	32.6	34.0	35.4
97.5°	106.2	89.7	73.1	56.6	40.1	31.8	33.4	36.6	39.9	43.1	46.3
100°	160.7	133.1	105.4	77.8	50.1	36.3	38.0	41.5	44.9	48.4	51.8
102.5°	220.6	220.2	219.8	219.4	219.0	218.8	200.4	163.7	127.0	90.3	53.6
105°	276.0	282.1	288.1	294.2	300.3	303.3	275.8	220.7	165.6	110.5	55.4
107.5°	340.5	345.5	350.6	355.6	360.7	363.2	329.2	261.2	193.2	125.2	57.2
110°	402.2	406.4	410.7	414.9	419.2	421.3	392.1	333.8	275.5	217.2	158.9



TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	460.4	464.0	467.6	471.3	474.9	476.7	475.0	471.6	468.1	464.7	461.3
115°	522.1	525.5	528.9	532.4	535.8	537.5	540.0	545.1	550.1	555.2	560.2
117.5°	575.7	579.7	583.7	587.8	591.8	593.8	595.5	599.0	602.4	605.9	609.3
120°	635.6	638.6	641.6	644.7	647.7	649.2	651.0	654.7	658.3	662.0	665.6
122.5°	686.4	689.6	692.9	696.1	699.4	701.0	703.0	707.0	711.1	715.1	719.1
125°	738.2	740.8	743.4	746.1	748.7	750.0	751.9	755.8	759.6	763.5	767.3
127.5°	785.4	788.2	791.0	793.9	796.7	798.1	799.6	802.7	805.7	808.8	811.8
130°	829.9	833.1	836.3	839.6	842.8	844.4	845.5	847.7	850.0	852.2	854.4
132.5°	875.3	877.9	880.5	883.2	885.8	887.1	888.2	890.4	892.7	894.9	897.1
135°	913.4	916.6	919.9	923.1	926.4	928.0	928.9	930.7	932.5	934.3	936.1
137.5°	953.4	955.8	958.2	960.7	963.1	964.3	965.3	967.3	969.4	971.4	973.4
140°	992.4	994.0	995.6	997.3	998.9	999.7	1000.8	1003.0	1005.3	1007.5	1009.7
142.5°	1025.1	1026.5	1027.9	1029.4	1030.8	1031.5	1032.8	1035.4	1038.1	1040.7	1043.3
145°	1059.6	1059.4	1059.2	1059.0	1058.8	1058.7	1060.4	1063.9	1067.3	1070.8	1074.2
147.5°	1089.6	1089.0	1088.4	1087.8	1087.2	1086.9	1088.6	1092.0	1095.5	1098.9	1102.3
150°	1118.7	1117.3	1115.9	1114.4	1113.0	1112.3	1113.9	1117.1	1120.4	1123.6	1126.8
152.5°	1143.2	1141.6	1140.0	1138.3	1136.7	1135.9	1137.4	1140.4	1143.5	1146.5	1149.5
155°	1166.8	1165.0	1163.2	1161.3	1159.5	1158.6	1159.8	1162.2	1164.7	1167.1	1169.5
157.5°	1185.8	1184.2	1182.6	1181.0	1179.4	1178.6	1179.5	1181.3	1183.2	1185.0	1186.8
160°	1202.2	1201.0	1199.8	1198.5	1197.3	1196.7	1197.3	1198.5	1199.8	1201.0	1202.2
162.5°	1216.7	1215.5	1214.3	1213.1	1211.9	1211.3	1211.8	1212.8	1213.8	1214.8	1215.8
165°	1229.4	1228.2	1227.0	1225.8	1224.6	1224.0	1224.3	1224.9	1225.5	1226.1	1226.7
167.5°	1239.4	1238.2	1237.0	1235.8	1234.6	1234.0	1234.3	1234.9	1235.5	1236.1	1236.7
170°	1247.6	1246.4	1245.2	1243.9	1242.7	1242.1	1242.3	1242.7	1243.2	1243.6	1244.0
172.5°	1253.0	1251.8	1250.6	1249.4	1248.2	1247.6	1247.8	1248.2	1248.6	1249.0	1249.4
175°	1257.6	1256.2	1254.8	1253.3	1251.9	1251.2	1251.4	1251.8	1252.2	1252.6	1253.0
177.5°	1259.4	1258.0	1256.6	1255.1	1253.7	1253.0	1253.1	1253.3	1253.5	1253.7	1253.9
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1113.3	1114.8	1117.0	1127.5	1128.9	1131.9	1130.4	1130.4	1131.2	1129.7	1130.4
5°	1161.1	1163.3	1174.5	1187.2	1190.2	1187.2	1191.0	1196.2	1196.2	1196.2	1194.7
7.5°	1205.9	1214.1	1226.8	1245.5	1249.2	1253.0	1259.7	1255.2	1256.7	1263.4	1261.2
10°	1249.2	1261.2	1275.4	1291.1	1299.3	1304.5	1307.5	1314.2	1329.9	1312.0	1318.7
12.5°	1290.3	1307.5	1322.5	1339.6	1345.6	1352.3	1354.6	1360.6	1360.6	1359.8	1365.0
15°	1317.2	1332.9	1346.4	1357.6	1359.1	1357.6	1356.1	1356.8	1359.1	1350.1	1355.3
17.5°	1323.2	1324.7	1329.2	1324.7	1325.5	1309.8	1300.8	1298.6	1277.6	1278.4	1295.6
20°	1294.1	1268.7	1261.9	1237.3	1222.3	1182.0	1180.5	1169.3	1125.2	1138.7	1135.7
22.5°	1214.1	1170.8	1113.3	1084.9	1070.7	1028.1	995.2	972.0	956.4	940.7	933.9
25°	1108.8	1038.5	957.1	901.1	892.8	853.2	792.7	764.3	730.7	720.3	738.2
27.5°	972.8	881.6	789.7	703.8	688.1	652.3	621.6	601.5	562.6	560.4	561.9
30°	788.2	696.3	619.4	563.4	524.5	508.1	487.9	472.9	457.3	463.2	464.7
32.5°	647.8	560.4	488.6	458.8	440.8	430.4	413.2	403.5	396.7	394.5	393.8
35°	514.8	456.5	424.4	395.2	384.8	377.3	364.6	360.1	354.2	354.9	354.9
37.5°	440.8	392.3	368.3	353.4	343.7	340.0	331.7	327.3	323.5	322.0	324.3
40°	380.3	346.7	331.7	318.3	310.1	308.6	304.1	298.9	294.4	295.1	297.4
42.5°	336.2	316.8	298.9	288.4	282.4	280.2	276.4	272.7	272.7	270.5	269.7
45°	301.1	285.4	270.5	260.8	257.0	254.0	249.5	248.8	245.8	246.6	247.3
47.5°	269.7	257.0	245.8	236.1	232.4	231.6	227.1	224.1	224.1	223.4	222.7
50°	241.3	228.6	218.9	213.7	208.5	207.0	206.2	205.5	204.0	204.0	204.7
52.5°	218.2	205.5	198.0	193.5	190.5	189.0	189.0	188.3	188.3	188.3	187.5
55°	192.8	182.3	176.3	174.8	173.3	172.6	171.8	170.4	169.6	171.1	169.6
57.5°	168.9	165.1	159.9	158.4	154.7	154.7	152.4	150.9	149.4	150.9	150.9
60°	150.2	144.9	142.0	137.5	134.5	131.5	127.8	127.0	125.5	124.8	124.0
62.5°	130.8	126.3	118.8	112.1	107.6	104.6	103.1	102.4	102.4	101.6	101.6
65°	109.1	98.6	94.9	92.6	91.9	91.2	89.7	88.9	89.7	88.9	89.7
67.5°	85.2	83.7	81.4	79.9	79.2	78.5	78.5	77.7	77.7	77.7	77.7
70°	74.0	70.2	69.5	68.0	68.0	67.2	67.2	67.2	67.2	66.5	68.0
72.5°	61.3	59.0	58.3	57.5	57.5	57.5	56.8	56.8	56.8	56.0	56.8
75°	50.1	49.3	47.8	47.8	47.1	47.8	47.1	47.1	46.3	47.1	47.1
77.5°	40.3	39.6	38.9	38.9	38.1	38.1	38.1	38.1	38.1	38.1	38.9
80°	30.6	29.9	29.1	29.9	29.1	29.9	29.1	29.1	29.9	29.1	29.1
82.5°	22.4	21.7	21.7	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
85°	13.4	12.7	12.7	13.4	12.7	13.4	12.7	12.7	12.7	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	19.2	20.2	21.2	22.2	22.7	22.9	23.3	23.7	24.1	24.5	24.1
92.5°	22.2	22.6	23.0	23.4	23.6	23.7	23.9	24.1	24.3	24.5	24.3
95°	36.4	37.4	38.5	39.5	40.0	39.9	39.7	39.4	39.2	39.0	39.2
97.5°	46.9	47.5	48.1	48.7	49.0	49.1	49.3	49.5	49.7	49.9	49.7
100°	53.4	55.0	56.6	58.2	59.0	59.2	59.6	60.0	60.4	60.8	60.4
102.5°	55.8	58.0	60.3	62.5	63.6	63.9	64.5	65.1	65.7	66.3	65.7
105°	57.6	59.8	62.1	64.3	65.4	65.8	66.6	67.4	68.2	69.0	68.2
107.5°	59.4	61.6	63.9	66.1	67.2	67.6	68.4	69.2	70.0	70.8	70.0
110°	138.7	118.5	98.4	78.2	68.1	68.5	69.3	70.1	70.9	71.7	70.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	374.3	287.3	200.4	113.4	69.9	70.2	70.8	71.4	72.0	72.6	72.0
115°	466.8	373.4	279.9	186.5	139.8	132.5	118.0	103.5	89.0	74.5	89.0
117.5°	580.4	551.6	522.7	493.8	479.4	453.0	400.1	347.2	294.4	241.5	294.4
120°	668.0	670.4	672.9	675.3	676.5	662.9	635.6	608.4	581.1	553.9	581.1
122.5°	720.3	721.5	722.8	724.0	724.6	724.7	724.9	725.1	725.3	725.5	725.3
125°	768.7	770.1	771.5	772.9	773.6	773.9	774.5	775.1	775.7	776.3	775.7
127.5°	813.8	815.8	817.8	819.8	820.8	820.9	821.1	821.3	821.5	821.7	821.5
130°	856.6	858.8	861.1	863.3	864.4	864.3	864.1	863.9	863.7	863.5	863.7
132.5°	898.9	900.7	902.6	904.4	905.3	905.2	905.0	904.8	904.6	904.4	904.6
135°	938.1	940.1	942.2	944.2	945.2	945.0	944.6	944.2	943.8	943.4	943.8
137.5°	975.4	977.4	979.5	981.5	982.5	982.2	981.6	980.9	980.3	979.7	980.3
140°	1011.5	1013.3	1015.2	1017.0	1017.9	1017.4	1016.4	1015.3	1014.3	1013.3	1014.3
142.5°	1044.9	1046.5	1048.2	1049.8	1050.6	1050.1	1049.1	1048.0	1047.0	1046.0	1047.0
145°	1075.6	1077.0	1078.4	1079.8	1080.5	1080.0	1079.0	1078.0	1077.0	1076.0	1077.0
147.5°	1103.3	1104.3	1105.4	1106.4	1106.9	1106.5	1105.7	1104.8	1104.0	1103.2	1104.0
150°	1128.0	1129.2	1130.5	1131.7	1132.3	1131.8	1130.8	1129.7	1128.7	1127.7	1128.7
152.5°	1150.7	1151.9	1153.2	1154.4	1155.0	1154.3	1152.9	1151.4	1150.0	1148.6	1150.0
155°	1170.7	1171.9	1173.2	1174.4	1175.0	1174.2	1172.6	1170.9	1169.3	1167.7	1169.3
157.5°	1188.2	1189.6	1191.0	1192.4	1193.1	1192.3	1190.7	1189.0	1187.4	1185.8	1187.4
160°	1203.4	1204.6	1205.8	1207.0	1207.6	1206.9	1205.5	1204.1	1202.7	1201.3	1202.7
162.5°	1217.2	1218.6	1220.1	1221.5	1222.2	1221.3	1219.5	1217.6	1215.8	1214.0	1215.8
165°	1228.1	1229.5	1231.0	1232.4	1233.1	1232.4	1231.0	1229.5	1228.1	1226.7	1228.1
167.5°	1238.1	1239.5	1241.0	1242.4	1243.1	1242.2	1240.4	1238.5	1236.7	1234.9	1236.7
170°	1245.4	1246.8	1248.2	1249.6	1250.3	1249.4	1247.6	1245.7	1243.9	1242.1	1243.9
172.5°	1250.8	1252.2	1253.7	1255.1	1255.8	1254.9	1253.1	1251.2	1249.4	1247.6	1249.4
175°	1254.4	1255.8	1257.3	1258.7	1259.4	1258.4	1256.4	1254.3	1252.3	1250.3	1252.3
177.5°	1255.3	1256.7	1258.2	1259.6	1260.3	1259.4	1257.6	1255.7	1253.9	1252.1	1253.9
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1133.4	1128.2	1126.7	1128.2	1126.7	1127.5	1122.2	1102.8	1108.0	1099.8	1104.3
5°	1197.7	1193.2	1183.5	1182.0	1180.5	1179.0	1171.5	1154.4	1147.6	1136.4	1135.7
7.5°	1259.0	1259.0	1251.5	1246.3	1239.5	1234.3	1224.6	1199.2	1188.7	1175.3	1167.8
10°	1319.5	1300.0	1308.3	1303.0	1286.6	1283.6	1265.7	1250.7	1230.6	1217.1	1205.2
12.5°	1362.8	1356.8	1349.4	1344.9	1340.4	1330.7	1318.7	1280.6	1270.2	1243.3	1229.8
15°	1361.3	1357.6	1359.8	1359.8	1358.3	1356.1	1346.4	1318.7	1300.8	1274.6	1251.5
17.5°	1288.1	1297.8	1307.5	1314.2	1329.2	1335.9	1344.9	1328.4	1317.2	1294.8	1270.2
20°	1160.3	1184.2	1212.6	1218.6	1232.1	1271.7	1289.6	1303.8	1308.3	1300.8	1280.6
22.5°	982.5	1002.7	1071.4	1069.9	1089.4	1136.4	1188.7	1231.3	1264.9	1283.6	1276.1
25°	769.6	798.0	834.6	862.2	925.7	996.0	1061.0	1128.9	1187.2	1238.8	1251.5
27.5°	582.0	619.4	648.5	685.1	717.3	800.2	883.9	990.0	1058.0	1155.8	1206.7
30°	470.7	487.9	517.0	534.2	549.9	613.4	708.3	812.9	932.4	1045.3	1132.7
32.5°	402.0	413.9	435.6	443.1	459.5	502.1	561.9	657.5	780.8	917.5	1032.6
35°	360.9	373.6	378.1	384.8	398.2	425.1	466.2	535.7	647.0	780.8	918.3
37.5°	325.8	332.5	345.2	349.7	354.2	374.3	402.0	450.5	524.5	634.3	786.8
40°	301.1	304.8	311.6	315.3	318.3	332.5	357.1	390.0	444.6	528.2	668.7
42.5°	275.0	279.4	283.9	288.4	292.1	303.3	318.3	349.7	386.3	449.8	551.4
45°	249.5	252.5	257.8	260.8	266.0	275.0	288.4	310.1	342.9	383.3	465.5
47.5°	226.4	230.1	232.4	236.1	239.8	249.5	262.3	276.4	303.3	342.9	402.7
50°	205.5	210.0	212.9	213.7	216.7	225.6	236.1	251.8	269.0	299.6	351.9
52.5°	190.5	191.3	193.5	196.5	195.8	201.0	210.7	222.7	240.6	265.2	303.3
55°	173.3	175.6	177.1	177.8	177.8	182.3	187.5	198.7	212.9	233.1	265.2
57.5°	151.7	153.9	158.4	159.9	162.1	164.4	166.6	174.1	186.0	205.5	231.6
60°	129.3	130.8	135.2	138.2	139.7	145.7	148.7	154.7	161.4	175.6	200.2
62.5°	103.9	105.3	107.6	110.6	113.6	122.5	130.0	136.0	141.2	150.9	171.1
65°	90.4	91.2	92.6	93.4	94.1	97.9	104.6	112.8	122.5	130.0	142.0
67.5°	78.5	79.2	79.9	81.4	82.2	82.9	85.9	88.2	97.9	108.3	117.3
70°	67.2	68.7	69.5	69.5	70.2	71.7	73.2	76.2	79.2	84.4	95.6
72.5°	56.8	57.5	59.0	59.0	59.0	60.5	62.0	63.5	65.0	68.0	72.5
75°	47.1	48.6	48.6	48.6	49.3	49.3	50.8	52.3	53.8	56.0	57.5
77.5°	38.9	38.9	38.9	38.9	39.6	39.6	40.3	41.8	42.6	43.3	44.8
80°	29.1	29.9	29.9	29.9	30.6	30.6	30.6	32.1	32.9	32.9	34.4
82.5°	21.7	21.7	21.7	22.4	21.7	22.4	22.4	23.2	22.4	23.2	23.9
85°	13.4	13.4	13.4	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	6.7	6.7
90°	23.7	23.3	22.9	22.7	22.2	21.2	20.2	19.2	18.2	16.6	15.0
92.5°	24.1	23.9	23.7	23.6	23.4	23.0	22.6	22.2	21.8	21.2	20.6
95°	39.4	39.7	39.9	40.0	39.5	38.5	37.4	36.4	35.4	34.0	32.6
97.5°	49.5	49.3	49.1	49.0	48.7	48.1	47.5	46.9	46.3	43.1	39.9
100°	60.0	59.6	59.2	59.0	58.2	56.6	55.0	53.4	51.8	48.4	44.9
102.5°	65.1	64.5	63.9	63.6	62.5	60.3	58.0	55.8	53.6	49.3	45.0
105°	67.4	66.6	65.8	65.4	64.3	62.1	59.8	57.6	55.4	51.0	46.6
107.5°	69.2	68.4	67.6	67.2	66.1	63.9	61.6	59.4	57.2	52.8	48.4
110°	70.1	69.3	68.5	68.1	78.2	98.4	118.5	138.7	158.9	217.2	275.5

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	71.4	70.8	70.2	69.9	113.4	200.4	287.3	374.3	461.3	464.7	468.1
115°	103.5	118.0	132.5	139.8	186.5	279.9	373.4	466.8	560.2	555.2	550.1
117.5°	347.2	400.1	453.0	479.4	493.8	522.7	551.6	580.4	609.3	605.9	602.4
120°	608.4	635.6	662.9	676.5	675.3	672.9	670.4	668.0	665.6	662.0	658.3
122.5°	725.1	724.9	724.7	724.6	724.0	722.8	721.5	720.3	719.1	715.1	711.1
125°	775.1	774.5	773.9	773.6	772.9	771.5	770.1	768.7	767.3	763.5	759.6
127.5°	821.3	821.1	820.9	820.8	819.8	817.8	815.8	813.8	811.8	808.8	805.7
130°	863.9	864.1	864.3	864.4	863.3	861.1	858.8	856.6	854.4	852.2	850.0
132.5°	904.8	905.0	905.2	905.3	904.4	902.6	900.7	898.9	897.1	894.9	892.7
135°	944.2	944.6	945.0	945.2	944.2	942.2	940.1	938.1	936.1	934.3	932.5
137.5°	980.9	981.6	982.2	982.5	981.5	979.5	977.4	975.4	973.4	971.4	969.4
140°	1015.3	1016.4	1017.4	1017.9	1017.0	1015.2	1013.3	1011.5	1009.7	1007.5	1005.3
142.5°	1048.0	1049.1	1050.1	1050.6	1049.8	1048.2	1046.5	1044.9	1043.3	1040.7	1038.1
145°	1078.0	1079.0	1080.0	1080.5	1079.8	1078.4	1077.0	1075.6	1074.2	1070.8	1067.3
147.5°	1104.8	1105.7	1106.5	1106.9	1106.4	1105.4	1104.3	1103.3	1102.3	1098.9	1095.5
150°	1129.7	1130.8	1131.8	1132.3	1131.7	1130.5	1129.2	1128.0	1126.8	1123.6	1120.4
152.5°	1151.4	1152.9	1154.3	1155.0	1154.4	1153.2	1151.9	1150.7	1149.5	1146.5	1143.5
155°	1170.9	1172.6	1174.2	1175.0	1174.4	1173.2	1171.9	1170.7	1169.5	1167.1	1164.7
157.5°	1189.0	1190.7	1192.3	1193.1	1192.4	1191.0	1189.6	1188.2	1186.8	1185.0	1183.2
160°	1204.1	1205.5	1206.9	1207.6	1207.0	1205.8	1204.6	1203.4	1202.2	1201.0	1199.8
162.5°	1217.6	1219.5	1221.3	1222.2	1221.5	1220.1	1218.6	1217.2	1215.8	1214.8	1213.8
165°	1229.5	1231.0	1232.4	1233.1	1232.4	1231.0	1229.5	1228.1	1226.7	1226.1	1225.5
167.5°	1238.5	1240.4	1242.2	1243.1	1242.4	1241.0	1239.5	1238.1	1236.7	1236.1	1235.5
170°	1245.7	1247.6	1249.4	1250.3	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2
172.5°	1251.2	1253.1	1254.9	1255.8	1255.1	1253.7	1252.2	1250.8	1249.4	1249.0	1248.6
175°	1254.3	1256.4	1258.4	1259.4	1258.7	1257.3	1255.8	1254.4	1253.0	1252.6	1252.2
177.5°	1255.7	1257.6	1259.4	1260.3	1259.6	1258.2	1256.7	1255.3	1253.9	1253.7	1253.5
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1097.6	1093.8	1093.8	1091.6	1091.6	1079.6	1079.6	1083.4	1078.9	1073.7	1066.2
5°	1126.0	1117.7	1115.5	1112.5	1102.8	1087.9	1081.9	1079.6	1070.7	1059.5	1046.8
7.5°	1152.9	1139.4	1132.7	1126.0	1113.3	1092.3	1080.4	1072.2	1058.7	1041.5	1025.1
10°	1179.0	1161.8	1144.6	1136.4	1118.5	1092.3	1075.2	1061.7	1042.3	1019.1	996.0
12.5°	1202.9	1167.1	1164.1	1147.6	1121.5	1091.6	1065.4	1046.0	1021.4	994.5	967.6
15°	1223.8	1187.2	1169.3	1154.4	1120.0	1082.6	1055.0	1031.1	998.2	967.6	934.7
17.5°	1234.3	1194.7	1182.7	1158.1	1123.0	1074.4	1037.0	1007.9	972.0	935.4	898.1
20°	1244.8	1198.4	1179.0	1161.8	1114.0	1058.7	1016.9	983.3	943.7	900.3	859.2
22.5°	1250.0	1198.4	1175.3	1151.4	1105.0	1041.5	992.2	952.6	906.3	862.2	812.9
25°	1241.0	1194.0	1166.3	1141.7	1089.4	1020.6	963.8	919.0	869.7	819.6	769.6
27.5°	1218.6	1183.5	1151.4	1126.0	1067.7	993.7	933.9	883.1	832.3	776.3	725.5
30°	1176.8	1161.1	1135.7	1107.3	1043.8	969.8	898.8	846.5	790.5	734.5	681.4
32.5°	1111.8	1125.2	1108.8	1084.1	1015.4	936.9	861.5	808.4	747.2	686.6	638.1
35°	1032.6	1080.4	1071.4	1054.2	985.5	901.8	826.4	762.1	700.8	639.6	591.0
37.5°	945.9	1018.4	1025.8	1015.4	951.1	866.0	783.0	720.3	657.5	595.5	546.2
40°	827.1	938.4	962.3	966.8	915.3	822.6	735.9	674.7	612.7	552.1	492.4
42.5°	718.0	858.5	888.4	907.0	869.7	780.0	692.6	624.6	563.4	508.8	449.0
45°	615.7	762.1	810.7	834.6	818.1	731.5	641.1	577.5	521.5	471.5	413.9
47.5°	510.3	657.5	725.5	763.6	763.6	682.2	591.7	529.0	475.2	432.6	381.8
50°	440.1	562.6	632.8	682.9	696.3	632.1	546.9	485.6	434.8	388.5	349.7
52.5°	375.1	484.9	543.2	595.5	634.3	578.3	496.9	441.6	391.5	348.2	317.5
55°	324.3	406.5	459.5	517.0	560.4	523.8	448.3	394.5	351.2	315.3	289.1
57.5°	275.7	347.4	390.8	441.6	487.9	460.2	399.7	353.4	315.3	283.9	260.8
60°	234.6	292.9	326.5	366.1	423.6	404.2	354.2	311.6	280.9	252.5	233.1
62.5°	199.5	245.8	274.2	302.6	354.9	345.9	307.1	274.2	248.1	224.1	207.7
65°	163.6	201.7	224.1	248.8	290.6	294.4	263.0	239.8	215.9	195.0	180.1
67.5°	132.2	162.1	182.3	203.2	236.8	247.3	225.6	206.2	186.0	168.9	155.4
70°	106.8	127.8	142.7	159.1	186.8	199.5	188.3	174.8	158.4	144.2	132.2
72.5°	84.4	97.9	106.8	119.5	142.0	154.7	153.9	142.0	130.0	120.3	110.6
75°	62.0	72.5	79.9	88.2	106.1	118.1	121.0	115.8	103.9	96.4	88.9
77.5°	47.1	53.0	56.8	62.8	75.5	85.9	90.4	88.9	80.7	74.7	69.5
80°	35.9	37.4	38.9	41.1	51.6	61.3	64.3	63.5	59.0	56.8	50.8
82.5°	25.4	26.2	26.9	27.6	31.4	39.6	42.6	44.1	40.3	38.1	32.9
85°	14.9	15.7	15.7	17.2	17.9	20.2	25.4	25.4	24.7	21.7	20.9
87.5°	7.5	7.5	6.7	6.7	7.5	8.2	9.7	11.2	9.7	9.0	8.2
90°	13.3	11.7	10.9	9.8	7.6	5.3	3.1	0.9	3.1	5.3	7.6
92.5°	20.0	19.4	19.1	19.5	20.3	21.1	21.9	22.7	21.9	21.1	20.3
95°	31.2	29.8	29.1	32.4	39.1	45.7	52.4	59.0	52.4	45.7	39.1
97.5°	36.6	33.4	31.8	40.1	56.6	73.1	89.7	106.2	89.7	73.1	56.6
100°	41.5	38.0	36.3	50.1	77.8	105.4	133.1	160.7	133.1	105.4	77.8
102.5°	163.7	200.4	218.8	219.0	219.4	219.8	220.2	220.6	220.2	219.8	219.4
105°	220.7	275.8	303.3	300.3	294.2	288.1	282.1	276.0	282.1	288.1	294.2
107.5°	261.2	329.2	363.2	360.7	355.6	350.6	345.5	340.5	345.5	350.6	355.6
110°	333.8	392.1	421.3	419.2	414.9	410.7	406.4	402.2	406.4	410.7	414.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	471.6	475.0	476.7	474.9	471.3	467.6	464.0	460.4	464.0	467.6	471.3
115°	545.1	540.0	537.5	535.8	532.4	528.9	525.5	522.1	525.5	528.9	532.4
117.5°	599.0	595.5	593.8	591.8	587.8	583.7	579.7	575.7	579.7	583.7	587.8
120°	654.7	651.0	649.2	647.7	644.7	641.6	638.6	635.6	638.6	641.6	644.7
122.5°	707.0	703.0	701.0	699.4	696.1	692.9	689.6	686.4	689.6	692.9	696.1
125°	755.8	751.9	750.0	748.7	746.1	743.4	740.8	738.2	740.8	743.4	746.1
127.5°	802.7	799.6	798.1	796.7	793.9	791.0	788.2	785.4	788.2	791.0	793.9
130°	847.7	845.5	844.4	842.8	839.6	836.3	833.1	829.9	833.1	836.3	839.6
132.5°	890.4	888.2	887.1	885.8	883.2	880.5	877.9	875.3	877.9	880.5	883.2
135°	930.7	928.9	928.0	926.4	923.1	919.9	916.6	913.4	916.6	919.9	923.1
137.5°	967.3	965.3	964.3	963.1	960.7	958.2	955.8	953.4	955.8	958.2	960.7
140°	1003.0	1000.8	999.7	998.9	997.3	995.6	994.0	992.4	994.0	995.6	997.3
142.5°	1035.4	1032.8	1031.5	1030.8	1029.4	1027.9	1026.5	1025.1	1026.5	1027.9	1029.4
145°	1063.9	1060.4	1058.7	1058.8	1059.0	1059.2	1059.4	1059.6	1059.4	1059.2	1059.0
147.5°	1092.0	1088.6	1086.9	1087.2	1087.8	1088.4	1089.0	1089.6	1089.0	1088.4	1087.8
150°	1117.1	1113.9	1112.3	1113.0	1114.4	1115.9	1117.3	1118.7	1117.3	1115.9	1114.4
152.5°	1140.4	1137.4	1135.9	1136.7	1138.3	1140.0	1141.6	1143.2	1141.6	1140.0	1138.3
155°	1162.2	1159.8	1158.6	1159.5	1161.3	1163.2	1165.0	1166.8	1165.0	1163.2	1161.3
157.5°	1181.3	1179.5	1178.6	1179.4	1181.0	1182.6	1184.2	1185.8	1184.2	1182.6	1181.0
160°	1198.5	1197.3	1196.7	1197.3	1198.5	1199.8	1201.0	1202.2	1201.0	1199.8	1198.5
162.5°	1212.8	1211.8	1211.3	1211.9	1213.1	1214.3	1215.5	1216.7	1215.5	1214.3	1213.1
165°	1224.9	1224.3	1224.0	1224.6	1225.8	1227.0	1228.2	1229.4	1228.2	1227.0	1225.8
167.5°	1234.9	1234.3	1234.0	1234.6	1235.8	1237.0	1238.2	1239.4	1238.2	1237.0	1235.8
170°	1242.7	1242.3	1242.1	1242.7	1243.9	1245.2	1246.4	1247.6	1246.4	1245.2	1243.9
172.5°	1248.2	1247.8	1247.6	1248.2	1249.4	1250.6	1251.8	1253.0	1251.8	1250.6	1249.4
175°	1251.8	1251.4	1251.2	1251.9	1253.3	1254.8	1256.2	1257.6	1256.2	1254.8	1253.3
177.5°	1253.3	1253.1	1253.0	1253.7	1255.1	1256.6	1258.0	1259.4	1258.0	1256.6	1255.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1063.2	1063.9	1066.2	1059.5	1049.0	1044.5	1031.1	1028.8	1026.6	1026.6	1028.8
5°	1039.3	1036.3	1037.0	1024.3	1009.4	1000.4	981.8	984.7	975.0	969.1	970.6
7.5°	1013.1	1004.9	1004.2	987.7	969.1	952.6	933.2	928.7	919.7	909.3	904.8
10°	980.3	974.3	963.1	944.4	920.5	907.0	880.9	865.2	863.0	847.3	841.3
12.5°	946.6	936.2	925.0	898.8	871.9	850.3	830.8	813.7	801.7	788.2	779.3
15°	907.8	895.1	882.4	854.7	823.4	801.7	772.6	747.2	712.0	684.4	668.7
17.5°	865.2	851.0	833.8	803.2	772.6	742.7	688.9	659.0	634.3	617.9	608.2
20°	821.1	805.4	788.2	757.6	704.6	652.3	622.4	599.2	584.3	567.8	555.9
22.5°	774.8	758.4	739.7	691.9	635.8	599.2	576.1	554.4	532.7	523.8	517.8
25°	731.5	716.5	692.6	627.6	583.5	549.9	523.8	509.6	498.4	486.4	475.2
27.5°	686.6	659.0	625.4	570.8	543.2	508.8	490.1	479.7	460.2	452.0	446.8
30°	632.8	602.2	570.1	531.2	499.1	475.2	458.0	440.8	429.6	421.4	412.4
32.5°	578.3	549.2	529.0	488.6	464.7	440.1	423.6	413.2	396.7	391.5	387.8
35°	531.2	506.6	488.6	455.8	433.3	410.9	399.0	383.3	372.8	363.1	357.1
37.5°	484.9	471.5	452.8	425.1	401.2	383.3	366.9	361.6	347.4	342.2	336.2
40°	452.8	432.6	416.9	393.0	372.8	353.4	342.9	331.0	321.3	313.1	310.8
42.5°	413.9	399.0	390.0	363.9	342.9	331.7	319.0	305.6	298.1	291.4	283.2
45°	384.8	371.3	358.6	337.7	319.0	304.8	293.6	284.7	272.0	269.0	256.3
47.5°	354.2	340.7	331.0	310.1	292.9	279.4	271.2	259.3	248.8	242.1	236.1
50°	323.5	312.3	303.3	285.4	270.5	256.3	245.1	233.1	228.6	217.4	213.7
52.5°	294.4	286.9	277.2	260.0	245.1	233.1	221.2	211.4	204.7	198.7	194.3
55°	269.7	257.8	253.3	234.6	221.9	209.2	198.7	192.8	184.5	180.8	177.1
57.5°	242.1	235.4	227.9	213.7	199.5	187.5	180.1	171.1	166.6	162.1	159.1
60°	218.2	208.5	202.5	190.5	177.8	166.6	159.9	153.2	147.2	143.5	137.5
62.5°	190.5	183.1	179.3	166.6	156.2	145.7	139.7	133.0	128.5	121.8	114.3
65°	166.6	160.6	156.2	145.7	136.0	126.3	120.3	112.1	106.1	102.4	101.6
67.5°	145.7	141.2	134.5	124.8	115.1	107.6	100.9	94.1	93.4	91.9	91.9
70°	122.5	118.1	114.3	103.9	95.6	87.4	85.9	83.7	81.4	80.7	79.2
72.5°	102.4	98.6	94.1	85.2	77.0	74.7	73.2	71.7	69.5	68.7	68.0
75°	82.9	77.7	74.7	66.5	64.3	62.8	61.3	59.0	57.5	56.8	55.3
77.5°	63.5	58.3	58.3	53.8	52.3	50.1	48.6	47.1	46.3	44.8	44.8
80°	44.8	44.8	43.3	41.1	38.9	38.1	35.9	35.1	34.4	35.1	33.6
82.5°	32.9	29.9	29.9	28.4	26.9	26.2	24.7	24.7	23.9	23.9	23.9
85°	18.7	18.7	17.9	16.4	15.7	15.7	14.9	14.9	14.2	14.2	13.4
87.5°	7.5	6.7	7.5	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	9.8	10.9	11.7	13.3	15.0	16.6	18.2	19.2	20.2	21.2	22.2
92.5°	19.5	19.1	19.4	20.0	20.6	21.2	21.8	22.2	22.6	23.0	23.4
95°	32.4	29.1	29.8	31.2	32.6	34.0	35.4	36.4	37.4	38.5	39.5
97.5°	40.1	31.8	33.4	36.6	39.9	43.1	46.3	46.9	47.5	48.1	48.7
100°	50.1	36.3	38.0	41.5	44.9	48.4	51.8	53.4	55.0	56.6	58.2
102.5°	219.0	218.8	200.4	163.7	127.0	90.3	53.6	55.8	58.0	60.3	62.5
105°	300.3	303.3	275.8	220.7	165.6	110.5	55.4	57.6	59.8	62.1	64.3
107.5°	360.7	363.2	329.2	261.2	193.2	125.2	57.2	59.4	61.6	63.9	66.1
110°	419.2	421.3	392.1	333.8	275.5	217.2	158.9	138.7	118.5	98.4	78.2

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	474.9	476.7	475.0	471.6	468.1	464.7	461.3	374.3	287.3	200.4	113.4
115°	535.8	537.5	540.0	545.1	550.1	555.2	560.2	466.8	373.4	279.9	186.5
117.5°	591.8	593.8	595.5	599.0	602.4	605.9	609.3	580.4	551.6	522.7	493.8
120°	647.7	649.2	651.0	654.7	658.3	662.0	665.6	668.0	670.4	672.9	675.3
122.5°	699.4	701.0	703.0	707.0	711.1	715.1	719.1	720.3	721.5	722.8	724.0
125°	748.7	750.0	751.9	755.8	759.6	763.5	767.3	768.7	770.1	771.5	772.9
127.5°	796.7	798.1	799.6	802.7	805.7	808.8	811.8	813.8	815.8	817.8	819.8
130°	842.8	844.4	845.5	847.7	850.0	852.2	854.4	856.6	858.8	861.1	863.3
132.5°	885.8	887.1	888.2	890.4	892.7	894.9	897.1	898.9	900.7	902.6	904.4
135°	926.4	928.0	928.9	930.7	932.5	934.3	936.1	938.1	940.1	942.2	944.2
137.5°	963.1	964.3	965.3	967.3	969.4	971.4	973.4	975.4	977.4	979.5	981.5
140°	998.9	999.7	1000.8	1003.0	1005.3	1007.5	1009.7	1011.5	1013.3	1015.2	1017.0
142.5°	1030.8	1031.5	1032.8	1035.4	1038.1	1040.7	1043.3	1044.9	1046.5	1048.2	1049.8
145°	1058.8	1058.7	1060.4	1063.9	1067.3	1070.8	1074.2	1075.6	1077.0	1078.4	1079.8
147.5°	1087.2	1086.9	1088.6	1092.0	1095.5	1098.9	1102.3	1103.3	1104.3	1105.4	1106.4
150°	1113.0	1112.3	1113.9	1117.1	1120.4	1123.6	1126.8	1128.0	1129.2	1130.5	1131.7
152.5°	1136.7	1135.9	1137.4	1140.4	1143.5	1146.5	1149.5	1150.7	1151.9	1153.2	1154.4
155°	1159.5	1158.6	1159.8	1162.2	1164.7	1167.1	1169.5	1170.7	1171.9	1173.2	1174.4
157.5°	1179.4	1178.6	1179.5	1181.3	1183.2	1185.0	1186.8	1188.2	1189.6	1191.0	1192.4
160°	1197.3	1196.7	1197.3	1198.5	1199.8	1201.0	1202.2	1203.4	1204.6	1205.8	1207.0
162.5°	1211.9	1211.3	1211.8	1212.8	1213.8	1214.8	1215.8	1217.2	1218.6	1220.1	1221.5
165°	1224.6	1224.0	1224.3	1224.9	1225.5	1226.1	1226.7	1228.1	1229.5	1231.0	1232.4
167.5°	1234.6	1234.0	1234.3	1234.9	1235.5	1236.1	1236.7	1238.1	1239.5	1241.0	1242.4
170°	1242.7	1242.1	1242.3	1242.7	1243.2	1243.6	1244.0	1245.4	1246.8	1248.2	1249.6
172.5°	1248.2	1247.6	1247.8	1248.2	1248.6	1249.0	1249.4	1250.8	1252.2	1253.7	1255.1
175°	1251.9	1251.2	1251.4	1251.8	1252.2	1252.6	1253.0	1254.4	1255.8	1257.3	1258.7
177.5°	1253.7	1253.0	1253.1	1253.3	1253.5	1253.7	1253.9	1255.3	1256.7	1258.2	1259.6
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1028.8	1027.3	1022.9	1024.3	1022.1	1022.1	1020.6	1020.6	1020.6	1024.3	1022.1
5°	972.8	967.6	962.3	960.1	957.9	955.6	955.6	954.9	961.6	960.1	966.1
7.5°	903.3	901.8	891.4	891.4	887.6	886.1	889.9	890.6	891.4	892.8	896.6
10°	841.3	837.6	822.6	824.1	821.9	818.9	821.1	819.6	824.9	826.4	824.9
12.5°	768.1	761.3	744.9	736.7	727.7	721.0	729.2	723.2	744.2	750.1	766.6
15°	670.9	658.2	647.0	647.0	638.8	632.8	636.6	643.3	647.8	654.5	657.5
17.5°	605.9	600.7	591.7	586.5	584.3	582.0	582.0	585.0	594.7	594.0	600.0
20°	550.7	547.7	543.2	536.5	534.2	532.7	532.7	532.7	539.4	545.4	549.2
22.5°	512.5	510.3	507.3	498.4	493.9	492.4	496.1	498.4	503.6	508.1	511.8
25°	474.4	469.2	464.0	461.0	458.8	458.8	460.2	461.0	463.2	465.5	470.0
27.5°	443.1	439.3	431.9	423.6	423.6	421.4	422.9	424.4	429.6	437.1	440.8
30°	407.9	407.2	404.2	401.2	398.2	396.7	399.7	402.0	402.7	406.5	406.5
32.5°	382.5	377.3	372.1	369.1	367.6	366.9	367.6	370.6	370.6	375.1	380.3
35°	357.1	354.2	348.9	343.7	342.2	338.5	341.4	344.4	349.7	351.9	354.2
37.5°	329.5	325.8	323.5	322.0	319.0	319.8	317.5	322.0	326.5	325.8	327.3
40°	308.6	301.9	295.1	294.4	293.6	292.9	292.9	293.6	296.6	299.6	304.1
42.5°	281.7	279.4	273.5	267.5	266.0	264.5	263.0	266.0	272.0	277.2	279.4
45°	254.0	251.0	249.5	245.1	242.1	241.3	239.8	243.6	248.8	251.0	252.5
47.5°	228.6	227.9	223.4	224.1	221.9	222.7	221.9	224.1	224.1	226.4	227.9
50°	211.4	209.2	207.0	205.5	203.2	203.2	202.5	203.2	206.2	209.2	208.5
52.5°	194.3	190.5	189.8	189.0	187.5	189.0	186.8	187.5	190.5	192.0	191.3
55°	174.1	173.3	171.8	170.4	169.6	168.9	168.9	168.9	171.8	174.1	174.8
57.5°	158.4	154.7	151.7	151.7	148.7	147.9	149.4	150.2	152.4	153.9	155.4
60°	136.7	135.2	130.8	128.5	124.0	123.3	123.3	126.3	130.0	135.2	136.7
62.5°	113.6	111.3	110.6	110.6	110.6	110.6	110.6	110.6	110.6	111.3	111.3
65°	100.9	101.6	100.9	100.1	100.9	100.9	100.1	100.1	100.1	100.9	101.6
67.5°	90.4	89.7	90.4	89.7	88.9	88.9	88.2	88.9	89.7	90.4	90.4
70°	78.5	78.5	77.7	78.5	77.7	77.0	76.2	76.2	77.7	78.5	78.5
72.5°	67.2	67.2	66.5	66.5	65.0	65.0	65.7	65.0	65.0	67.2	67.2
75°	56.0	55.3	54.5	54.5	53.8	53.8	53.8	53.0	54.5	54.5	55.3
77.5°	44.1	44.1	44.1	43.3	43.3	42.6	42.6	43.3	43.3	43.3	44.1
80°	33.6	33.6	33.6	32.9	32.1	32.1	32.1	32.1	32.1	32.9	32.1
82.5°	23.2	23.2	23.2	23.2	23.2	22.4	22.4	22.4	23.2	23.2	22.4
85°	14.2	13.4	14.2	14.2	13.4	14.2	13.4	13.4	12.7	12.7	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	22.7	22.9	23.3	23.7	24.1	24.5	24.1	23.7	23.3	22.9	22.7
92.5°	23.6	23.7	23.9	24.1	24.3	24.5	24.3	24.1	23.9	23.7	23.6
95°	40.0	39.9	39.7	39.4	39.2	39.0	39.2	39.4	39.7	39.9	40.0
97.5°	49.0	49.1	49.3	49.5	49.7	49.9	49.7	49.5	49.3	49.1	49.0
100°	59.0	59.2	59.6	60.0	60.4	60.8	60.4	60.0	59.6	59.2	59.0
102.5°	63.6	63.9	64.5	65.1	65.7	66.3	65.7	65.1	64.5	63.9	63.6
105°	65.4	65.8	66.6	67.4	68.2	69.0	68.2	67.4	66.6	65.8	65.4
107.5°	67.2	67.6	68.4	69.2	70.0	70.8	70.0	69.2	68.4	67.6	67.2
110°	68.1	68.5	69.3	70.1	70.9	71.7	70.9	70.1	69.3	68.5	68.1

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.9	70.2	70.8	71.4	72.0	72.6	72.0	71.4	70.8	70.2	69.9
115°	139.8	132.5	118.0	103.5	89.0	74.5	89.0	103.5	118.0	132.5	139.8
117.5°	479.4	453.0	400.1	347.2	294.4	241.5	294.4	347.2	400.1	453.0	479.4
120°	676.5	662.9	635.6	608.4	581.1	553.9	581.1	608.4	635.6	662.9	676.5
122.5°	724.6	724.7	724.9	725.1	725.3	725.5	725.3	725.1	724.9	724.7	724.6
125°	773.6	773.9	774.5	775.1	775.7	776.3	775.7	775.1	774.5	773.9	773.6
127.5°	820.8	820.9	821.1	821.3	821.5	821.7	821.5	821.3	821.1	820.9	820.8
130°	864.4	864.3	864.1	863.9	863.7	863.5	863.7	863.9	864.1	864.3	864.4
132.5°	905.3	905.2	905.0	904.8	904.6	904.4	904.6	904.8	905.0	905.2	905.3
135°	945.2	945.0	944.6	944.2	943.8	943.4	943.8	944.2	944.6	945.0	945.2
137.5°	982.5	982.2	981.6	980.9	980.3	979.7	980.3	980.9	981.6	982.2	982.5
140°	1017.9	1017.4	1016.4	1015.3	1014.3	1013.3	1014.3	1015.3	1016.4	1017.4	1017.9
142.5°	1050.6	1050.1	1049.1	1048.0	1047.0	1046.0	1047.0	1048.0	1049.1	1050.1	1050.6
145°	1080.5	1080.0	1079.0	1078.0	1077.0	1076.0	1077.0	1078.0	1079.0	1080.0	1080.5
147.5°	1106.9	1106.5	1105.7	1104.8	1104.0	1103.2	1104.0	1104.8	1105.7	1106.5	1106.9
150°	1132.3	1131.8	1130.8	1129.7	1128.7	1127.7	1128.7	1129.7	1130.8	1131.8	1132.3
152.5°	1155.0	1154.3	1152.9	1151.4	1150.0	1148.6	1150.0	1151.4	1152.9	1154.3	1155.0
155°	1175.0	1174.2	1172.6	1170.9	1169.3	1167.7	1169.3	1170.9	1172.6	1174.2	1175.0
157.5°	1193.1	1192.3	1190.7	1189.0	1187.4	1185.8	1187.4	1189.0	1190.7	1192.3	1193.1
160°	1207.6	1206.9	1205.5	1204.1	1202.7	1201.3	1202.7	1204.1	1205.5	1206.9	1207.6
162.5°	1222.2	1221.3	1219.5	1217.6	1215.8	1214.0	1215.8	1217.6	1219.5	1221.3	1222.2
165°	1233.1	1232.4	1231.0	1229.5	1228.1	1226.7	1228.1	1229.5	1231.0	1232.4	1233.1
167.5°	1243.1	1242.2	1240.4	1238.5	1236.7	1234.9	1236.7	1238.5	1240.4	1242.2	1243.1
170°	1250.3	1249.4	1247.6	1245.7	1243.9	1242.1	1243.9	1245.7	1247.6	1249.4	1250.3
172.5°	1255.8	1254.9	1253.1	1251.2	1249.4	1247.6	1249.4	1251.2	1253.1	1254.9	1255.8
175°	1259.4	1258.4	1256.4	1254.3	1252.3	1250.3	1252.3	1254.3	1256.4	1258.4	1259.4
177.5°	1260.3	1259.4	1257.6	1255.7	1253.9	1252.1	1253.9	1255.7	1257.6	1259.4	1260.3
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
2.5°	1024.3	1028.1	1026.6	1018.4	1026.6	1028.8	1033.3	1037.8	1040.8	1045.3	1049.0
5°	960.1	967.6	972.0	967.6	982.5	984.7	995.2	1001.2	1010.2	1017.6	1023.6
7.5°	899.6	905.6	914.5	916.0	925.0	935.4	950.4	965.3	979.5	987.0	993.7
10°	834.6	845.0	858.5	855.5	868.9	885.4	901.1	925.0	936.9	950.4	962.3
12.5°	769.6	776.3	794.2	800.2	819.6	832.3	854.0	868.9	898.8	914.5	925.0
15°	656.0	683.6	706.1	733.0	758.4	782.3	801.7	828.6	854.7	866.7	883.9
17.5°	604.4	617.1	630.6	644.0	676.9	719.5	753.9	783.0	805.4	821.1	841.3
20°	550.7	563.4	578.3	591.0	611.2	641.8	684.4	734.5	761.3	777.8	797.2
22.5°	512.5	524.5	534.2	545.4	561.1	583.5	615.7	677.7	713.5	733.7	750.9
25°	471.5	486.4	496.9	505.1	517.8	542.4	568.6	603.7	668.0	683.6	707.6
27.5°	443.1	447.5	459.5	472.2	484.9	498.4	525.2	555.1	598.5	632.8	662.0
30°	409.4	420.6	431.9	437.1	448.3	467.7	484.2	516.3	549.9	576.8	611.9
32.5°	384.0	390.8	398.2	410.9	421.4	434.8	451.3	478.2	506.6	523.8	550.7
35°	355.6	360.1	375.8	381.0	391.5	405.0	421.4	442.3	472.9	486.4	505.8
37.5°	328.7	339.2	343.7	355.6	365.4	378.8	390.8	414.7	434.8	450.5	468.5
40°	307.8	312.3	320.5	331.0	339.2	349.7	364.6	381.8	403.5	416.2	431.9
42.5°	282.4	286.2	296.6	302.6	316.0	325.8	334.7	355.6	375.1	384.8	400.5
45°	254.8	263.7	270.5	282.4	289.9	301.9	313.1	328.0	345.9	357.1	366.1
47.5°	230.9	239.8	246.6	257.8	269.7	275.0	286.9	302.6	319.0	328.0	340.7
50°	211.4	214.4	227.1	232.4	245.1	255.5	263.7	277.2	295.1	300.4	310.8
52.5°	192.8	195.0	203.2	210.0	221.2	230.1	240.6	253.3	268.2	276.4	284.7
55°	176.3	177.8	181.6	189.0	196.5	207.7	217.4	229.4	242.1	251.0	258.5
57.5°	157.6	160.6	163.6	168.1	175.6	186.0	196.5	207.7	218.2	224.1	233.9
60°	136.0	140.5	145.7	150.9	156.2	163.6	175.6	186.0	195.8	201.0	208.5
62.5°	112.8	121.8	126.3	132.2	136.7	143.5	152.4	164.4	171.1	177.8	183.8
65°	101.6	102.4	103.1	109.1	117.3	124.0	132.2	141.2	151.7	156.2	160.6
67.5°	90.4	91.2	92.6	93.4	96.4	103.9	112.8	122.5	130.8	133.7	138.2
70°	79.2	79.2	82.2	82.9	83.7	84.4	91.9	101.6	109.1	112.8	118.1
72.5°	67.2	68.0	69.5	70.2	71.7	73.2	75.5	80.7	89.7	93.4	99.4
75°	55.3	56.0	56.8	57.5	59.8	60.5	62.8	65.7	69.5	74.0	77.7
77.5°	44.1	44.1	44.8	46.3	47.8	48.6	50.8	52.3	53.8	56.0	59.0
80°	32.9	33.6	33.6	35.1	35.1	35.9	36.6	38.9	40.3	41.8	43.3
82.5°	22.4	23.9	23.9	23.9	24.7	25.4	26.2	26.2	27.6	28.4	30.6
85°	13.4	14.2	14.2	14.2	13.4	14.9	14.9	15.7	15.7	15.7	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	22.2	21.2	20.2	19.2	18.2	16.6	15.0	13.3	11.7	10.9	9.8
92.5°	23.4	23.0	22.6	22.2	21.8	21.2	20.6	20.0	19.4	19.1	19.5
95°	39.5	38.5	37.4	36.4	35.4	34.0	32.6	31.2	29.8	29.1	32.4
97.5°	48.7	48.1	47.5	46.9	46.3	43.1	39.9	36.6	33.4	31.8	40.1
100°	58.2	56.6	55.0	53.4	51.8	48.4	44.9	41.5	38.0	36.3	50.1
102.5°	62.5	60.3	58.0	55.8	53.6	90.3	127.0	163.7	200.4	218.8	219.0
105°	64.3	62.1	59.8	57.6	55.4	110.5	165.6	220.7	275.8	303.3	300.3
107.5°	66.1	63.9	61.6	59.4	57.2	125.2	193.2	261.2	329.2	363.2	360.7
110°	78.2	98.4	118.5	138.7	158.9	217.2	275.5	333.8	392.1	421.3	419.2

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	113.4	200.4	287.3	374.3	461.3	464.7	468.1	471.6	475.0	476.7	474.9
115°	186.5	279.9	373.4	466.8	560.2	555.2	550.1	545.1	540.0	537.5	535.8
117.5°	493.8	522.7	551.6	580.4	609.3	605.9	602.4	599.0	595.5	593.8	591.8
120°	675.3	672.9	670.4	668.0	665.6	662.0	658.3	654.7	651.0	649.2	647.7
122.5°	724.0	722.8	721.5	720.3	719.1	715.1	711.1	707.0	703.0	701.0	699.4
125°	772.9	771.5	770.1	768.7	767.3	763.5	759.6	755.8	751.9	750.0	748.7
127.5°	819.8	817.8	815.8	813.8	811.8	808.8	805.7	802.7	799.6	798.1	796.7
130°	863.3	861.1	858.8	856.6	854.4	852.2	850.0	847.7	845.5	844.4	842.8
132.5°	904.4	902.6	900.7	898.9	897.1	894.9	892.7	890.4	888.2	887.1	885.8
135°	944.2	942.2	940.1	938.1	936.1	934.3	932.5	930.7	928.9	928.0	926.4
137.5°	981.5	979.5	977.4	975.4	973.4	971.4	969.4	967.3	965.3	964.3	963.1
140°	1017.0	1015.2	1013.3	1011.5	1009.7	1007.5	1005.3	1003.0	1000.8	999.7	998.9
142.5°	1049.8	1048.2	1046.5	1044.9	1043.3	1040.7	1038.1	1035.4	1032.8	1031.5	1030.8
145°	1079.8	1078.4	1077.0	1075.6	1074.2	1070.8	1067.3	1063.9	1060.4	1058.7	1058.8
147.5°	1106.4	1105.4	1104.3	1103.3	1102.3	1098.9	1095.5	1092.0	1088.6	1086.9	1087.2
150°	1131.7	1130.5	1129.2	1128.0	1126.8	1123.6	1120.4	1117.1	1113.9	1112.3	1113.0
152.5°	1154.4	1153.2	1151.9	1150.7	1149.5	1146.5	1143.5	1140.4	1137.4	1135.9	1136.7
155°	1174.4	1173.2	1171.9	1170.7	1169.5	1167.1	1164.7	1162.2	1159.8	1158.6	1159.5
157.5°	1192.4	1191.0	1189.6	1188.2	1186.8	1185.0	1183.2	1181.3	1179.5	1178.6	1179.4
160°	1207.0	1205.8	1204.6	1203.4	1202.2	1201.0	1199.8	1198.5	1197.3	1196.7	1197.3
162.5°	1221.5	1220.1	1218.6	1217.2	1215.8	1214.8	1213.8	1212.8	1211.8	1211.3	1211.9
165°	1232.4	1231.0	1229.5	1228.1	1226.7	1226.1	1225.5	1224.9	1224.3	1224.0	1224.6
167.5°	1242.4	1241.0	1239.5	1238.1	1236.7	1236.1	1235.5	1234.9	1234.3	1234.0	1234.6
170°	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2	1242.7	1242.3	1242.1	1242.7
172.5°	1255.1	1253.7	1252.2	1250.8	1249.4	1249.0	1248.6	1248.2	1247.8	1247.6	1248.2
175°	1258.7	1257.3	1255.8	1254.4	1253.0	1252.6	1252.2	1251.8	1251.4	1251.2	1251.9
177.5°	1259.6	1258.2	1256.7	1255.3	1253.9	1253.7	1253.5	1253.3	1253.1	1253.0	1253.7
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1075.2	1075.2	1075.2	1075.2
2.5°	1055.7	1053.5	1066.9	1081.9
5°	1034.1	1037.8	1055.0	1075.9
7.5°	1011.6	1019.9	1040.0	1067.7
10°	980.3	995.2	1025.8	1054.2
12.5°	949.6	969.8	998.9	1032.6
15°	915.3	937.7	973.5	1013.9
17.5°	877.2	902.6	944.4	988.5
20°	836.8	870.4	914.5	962.3
22.5°	792.0	832.3	877.9	931.0
25°	748.6	792.7	838.3	899.6
27.5°	706.1	749.4	800.2	862.2
30°	663.5	703.1	757.6	824.1
32.5°	617.9	659.0	716.5	784.5
35°	576.1	617.1	670.9	738.2
37.5°	531.2	575.3	626.9	696.3
40°	478.9	530.5	580.5	647.0
42.5°	435.6	490.1	538.7	601.5
45°	401.2	452.8	493.1	554.4
47.5°	369.1	410.9	452.0	508.8
50°	338.5	370.6	413.2	464.0
52.5°	307.1	334.7	371.3	419.2
55°	278.7	304.8	337.7	374.3
57.5°	252.5	271.2	304.1	337.0
60°	223.4	242.8	268.2	295.9
62.5°	198.7	213.7	237.6	260.8
65°	172.6	186.8	204.7	226.4
67.5°	148.7	161.4	175.6	192.8
70°	127.0	136.7	147.2	162.1
72.5°	103.9	114.3	124.0	136.0
75°	85.2	89.7	97.9	106.1
77.5°	65.7	71.7	76.2	82.9
80°	47.1	52.3	53.8	59.0
82.5°	31.4	34.4	37.4	38.9
85°	17.9	19.4	22.4	23.2
87.5°	6.7	7.5	9.0	10.5
90°	7.6	5.3	3.1	0.9
92.5°	20.3	21.1	21.9	22.7
95°	39.1	45.7	52.4	59.0
97.5°	56.6	73.1	89.7	106.2
100°	77.8	105.4	133.1	160.7
102.5°	219.4	219.8	220.2	220.6
105°	294.2	288.1	282.1	276.0
107.5°	355.6	350.6	345.5	340.5
110°	414.9	410.7	406.4	402.2

TEST NUMBER: P1008436

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	471.3	467.6	464.0	460.4
115°	532.4	528.9	525.5	522.1
117.5°	587.8	583.7	579.7	575.7
120°	644.7	641.6	638.6	635.6
122.5°	696.1	692.9	689.6	686.4
125°	746.1	743.4	740.8	738.2
127.5°	793.9	791.0	788.2	785.4
130°	839.6	836.3	833.1	829.9
132.5°	883.2	880.5	877.9	875.3
135°	923.1	919.9	916.6	913.4
137.5°	960.7	958.2	955.8	953.4
140°	997.3	995.6	994.0	992.4
142.5°	1029.4	1027.9	1026.5	1025.1
145°	1059.0	1059.2	1059.4	1059.6
147.5°	1087.8	1088.4	1089.0	1089.6
150°	1114.4	1115.9	1117.3	1118.7
152.5°	1138.3	1140.0	1141.6	1143.2
155°	1161.3	1163.2	1165.0	1166.8
157.5°	1181.0	1182.6	1184.2	1185.8
160°	1198.5	1199.8	1201.0	1202.2
162.5°	1213.1	1214.3	1215.5	1216.7
165°	1225.8	1227.0	1228.2	1229.4
167.5°	1235.8	1237.0	1238.2	1239.4
170°	1243.9	1245.2	1246.4	1247.6
172.5°	1249.4	1250.6	1251.8	1253.0
175°	1253.3	1254.8	1256.2	1257.6
177.5°	1255.1	1256.6	1258.0	1259.4
180°	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)