

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008455

Luminaire Tested: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008455
REPORT IS A COMBINATION OF REPORTS P988465 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3871.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66		
1	102	98	95	91	96	93	90	87	82	80	78	73	71	70	64	63	62	58		
2	94	87	81	77	88	82	77	73	74	70	66	65	62	60	58	56	54	50		
3	87	78	71	65	81	74	67	62	66	61	57	59	55	52	52	49	47	44		
4	80	70	62	56	75	66	59	54	59	54	50	53	49	46	48	44	42	39		
5	74	63	55	49	70	60	53	47	54	48	44	49	44	40	43	40	37	34		
6	69	57	49	44	65	54	47	42	49	43	39	44	40	36	40	36	33	31		
7	64	52	44	39	60	50	43	38	45	39	35	41	36	33	37	33	30	28		
8	60	48	40	35	56	46	39	34	42	36	32	38	33	30	34	30	28	25		
9	56	44	37	32	53	42	35	31	38	33	29	35	30	27	32	28	25	23		
10	52	41	34	29	50	39	32	28	36	30	26	33	28	25	30	26	23	21		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23375	23375	23375	23375
5°	23431	24829	23511	19835
10°	23172	26244	23337	16379
15°	22670	26252	23054	12305
20°	22065	21700	22544	10152
25°	21332	13559	21793	8636
30°	20395	8682	20950	7435
35°	19256	6672	19880	6363
40°	17986	5609	18756	5566
45°	16631	4774	17326	4672
50°	15240	4056	15950	4041
55°	13699	3525	14437	3478
60°	12332	2688	12984	2655
65°	11052	2022	11710	2294
70°	9644	1615	10398	1870
75°	8151	1238	8900	1414
80°	6475	841	6962	927
85°	4492	435	4930	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21383 cd/sqm

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	3.6
10°-20°	391.0	10.1
20°-30°	503.2	13.0
30°-40°	477.4	12.3
40°-50°	409.1	10.6
50°-60°	311.6	8.0
60°-70°	196.5	5.1
70°-80°	98.0	2.5
80°-90°	26.0	0.7
90°-100°	14.8	0.4
100°-110°	55.3	1.4
110°-120°	146.6	3.8
120°-130°	243.1	6.3
130°-140°	258.3	6.7
140°-150°	240.0	6.2
150°-160°	193.0	5.0
160°-170°	124.3	3.2
170°-180°	42.8	1.1
0°-30°	1034.2	26.7
0°-40°	1511.6	39.0
0°-60°	2232.3	57.7
0°-90°	2552.8	65.9
90°-120°	216.7	5.6
90°-150°	958.1	24.8
90°-180°	1318.0	34.0
0°-180°	3871.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1477	1477	1477	1477	1477	
5°	1478	1643	1483	1312	1478	140
15°	1393	1854	1416	869	1393	392
25°	1236	989	1262	630	1236	567
35°	1014	488	1047	465	1014	634
45°	762	339	793	332	762	588
55°	514	235	542	232	514	463
65°	311	122	329	138	311	309
75°	146	65	159	74	146	158
85°	32	18	35	20	32	36
90°	0	9	0	9	0	3
95°	21	14	21	14	21	25
105°	99	25	99	25	99	106
115°	187	27	187	27	187	184
125°	264	278	264	278	264	236
135°	327	338	327	338	327	253
145°	380	386	380	386	380	237
155°	418	418	418	418	418	193
165°	440	440	440	440	440	124
175°	451	448	451	448	451	43
180°	450	450	450	450	450	

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1486.0	1492.1	1495.2	1499.3	1508.6	1514.7	1524.0	1526.0	1525.0	1529.1	1517.8
5°	1477.8	1491.1	1503.4	1513.7	1530.1	1540.4	1551.7	1565.0	1568.1	1583.5	1574.2
7.5°	1466.5	1486.0	1503.4	1524.0	1548.6	1561.9	1579.4	1599.9	1609.1	1627.6	1632.7
10°	1448.0	1475.7	1505.5	1527.0	1560.9	1584.5	1600.9	1633.8	1655.3	1683.0	1678.9
12.5°	1418.3	1454.2	1494.2	1530.1	1574.2	1589.6	1620.4	1654.3	1682.0	1707.6	1730.2
15°	1392.6	1433.6	1477.8	1521.9	1572.2	1600.9	1631.7	1675.8	1705.6	1750.7	1770.2
17.5°	1357.7	1410.0	1462.4	1511.6	1571.2	1604.0	1642.0	1685.1	1729.2	1772.3	1787.7
20°	1321.8	1378.2	1434.7	1501.4	1569.1	1600.9	1639.9	1693.3	1736.4	1770.2	1770.2
22.5°	1278.7	1347.4	1412.1	1475.7	1549.6	1595.8	1635.8	1698.4	1729.2	1736.4	1708.7
25°	1235.6	1304.3	1375.1	1454.2	1538.3	1579.4	1624.5	1683.0	1693.3	1664.5	1592.7
27.5°	1184.3	1261.2	1341.3	1426.5	1514.7	1566.0	1607.1	1646.1	1626.6	1549.6	1437.7
30°	1131.9	1215.1	1305.4	1386.4	1493.2	1540.4	1575.3	1586.6	1525.0	1399.8	1255.1
32.5°	1077.5	1158.6	1254.1	1351.5	1459.3	1504.5	1527.0	1497.3	1384.4	1226.3	1049.8
35°	1013.9	1105.3	1204.8	1306.4	1413.1	1447.0	1460.3	1387.5	1242.8	1038.5	863.1
37.5°	956.4	1047.8	1154.5	1258.2	1361.8	1380.3	1366.9	1253.0	1069.3	867.2	695.8
40°	888.7	986.2	1090.9	1206.8	1292.0	1297.2	1264.3	1116.5	888.7	698.9	593.2
42.5°	826.1	924.6	1029.3	1147.3	1212.0	1194.5	1150.4	956.4	742.0	602.4	517.2
45°	761.5	854.9	967.7	1072.4	1118.6	1077.5	1010.8	804.6	622.9	518.2	452.6
47.5°	698.9	786.1	898.0	998.5	1006.7	960.6	881.5	674.2	539.8	455.6	402.3
50°	637.3	724.5	829.2	912.3	904.1	840.5	751.2	586.0	469.0	402.3	358.2
52.5°	575.7	654.7	756.3	822.0	787.1	725.5	637.3	496.7	409.5	351.0	317.1
55°	514.1	588.0	675.3	729.6	674.2	603.4	540.8	425.9	355.1	307.9	282.2
57.5°	462.8	521.3	601.4	634.2	567.5	512.1	457.7	366.4	307.9	274.0	244.2
60°	406.4	459.8	525.4	544.9	476.2	431.0	384.8	309.9	263.7	234.0	214.5
62.5°	358.2	402.3	452.6	452.6	392.0	358.2	323.3	259.6	221.7	198.1	188.8
65°	310.9	342.8	378.7	374.6	323.3	293.5	265.8	214.5	185.7	169.3	160.1
67.5°	264.8	289.4	313.0	298.6	261.7	236.0	210.4	173.4	153.9	142.6	130.3
70°	222.7	242.2	254.5	241.2	204.2	182.7	164.2	139.6	124.2	109.8	102.6
72.5°	186.8	195.0	199.1	182.7	151.9	139.6	126.2	108.8	95.4	88.3	86.2
75°	145.7	152.9	149.8	137.5	111.9	102.6	92.4	80.0	77.0	72.9	70.8
77.5°	113.9	113.9	108.8	97.5	80.0	72.9	68.8	62.6	59.5	58.5	56.4
80°	81.1	80.0	77.0	64.7	54.4	50.3	50.3	46.2	45.2	43.1	43.1
82.5°	53.4	53.4	49.3	39.0	35.9	34.9	33.9	31.8	31.8	30.8	30.8
85°	31.8	29.8	24.6	21.6	20.5	20.5	19.5	18.5	19.5	18.5	18.5
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.3	1.1	1.9	2.7	3.5	3.9	4.2	4.8	5.3	5.9	6.5
92.5°	8.1	7.8	7.5	7.2	6.9	6.8	6.9	7.1	7.4	7.6	7.8
95°	21.1	18.7	16.3	14.0	11.6	10.4	10.7	11.2	11.7	12.2	12.7
97.5°	38.1	32.2	26.2	20.3	14.4	11.4	12.0	13.1	14.3	15.4	16.6
100°	57.6	47.7	37.8	27.9	18.0	13.0	13.6	14.8	16.1	17.3	18.5
102.5°	79.1	78.9	78.8	78.6	78.5	78.4	71.8	58.7	45.5	32.4	19.2
105°	98.9	101.1	103.3	105.4	107.6	108.7	98.8	79.1	59.3	39.6	19.8
107.5°	122.0	123.8	125.6	127.4	129.2	130.1	117.9	93.6	69.2	44.9	20.5
110°	144.1	145.6	147.2	148.7	150.2	151.0	140.5	119.6	98.7	77.8	56.9

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	165.0	166.3	167.6	168.9	170.2	170.8	170.2	169.0	167.7	166.5	165.3
115°	187.1	188.3	189.5	190.8	192.0	192.6	193.5	195.3	197.1	198.9	200.7
117.5°	206.3	207.7	209.2	210.6	212.1	212.8	213.4	214.6	215.9	217.1	218.3
120°	227.8	228.9	229.9	231.0	232.1	232.6	233.3	234.6	235.9	237.2	238.5
122.5°	246.0	247.2	248.3	249.5	250.6	251.2	251.9	253.4	254.8	256.3	257.7
125°	264.5	265.4	266.4	267.3	268.2	268.7	269.4	270.8	272.1	273.5	274.9
127.5°	281.4	282.4	283.4	284.5	285.5	286.0	286.5	287.6	288.7	289.8	290.9
130°	297.4	298.6	299.7	300.9	302.0	302.6	303.0	303.8	304.6	305.4	306.2
132.5°	313.6	314.6	315.5	316.5	317.4	317.9	318.3	319.1	319.9	320.7	321.5
135°	327.3	328.5	329.6	330.8	331.9	332.5	332.8	333.5	334.1	334.8	335.4
137.5°	341.6	342.5	343.3	344.2	345.1	345.5	345.9	346.6	347.3	348.1	348.8
140°	355.6	356.2	356.8	357.3	357.9	358.2	358.6	359.4	360.2	361.0	361.8
142.5°	367.3	367.8	368.3	368.8	369.3	369.6	370.1	371.0	371.9	372.9	373.8
145°	379.7	379.6	379.6	379.5	379.4	379.4	380.0	381.2	382.5	383.7	384.9
147.5°	390.4	390.2	390.0	389.8	389.6	389.5	390.1	391.3	392.6	393.8	395.0
150°	400.8	400.3	399.8	399.3	398.8	398.6	399.2	400.3	401.5	402.6	403.8
152.5°	409.6	409.0	408.4	407.9	407.3	407.0	407.5	408.6	409.7	410.8	411.9
155°	418.1	417.5	416.8	416.2	415.5	415.2	415.6	416.5	417.4	418.2	419.1
157.5°	424.9	424.3	423.7	423.2	422.6	422.3	422.6	423.3	423.9	424.6	425.2
160°	430.8	430.4	429.9	429.5	429.0	428.8	429.0	429.5	429.9	430.4	430.8
162.5°	436.0	435.6	435.1	434.7	434.2	434.0	434.2	434.6	434.9	435.3	435.7
165°	440.5	440.1	439.7	439.2	438.8	438.6	438.7	438.9	439.2	439.4	439.6
167.5°	444.1	443.7	443.3	442.8	442.4	442.2	442.3	442.5	442.7	442.9	443.1
170°	447.0	446.6	446.2	445.7	445.3	445.1	445.2	445.3	445.4	445.6	445.7
172.5°	449.0	448.6	448.1	447.7	447.2	447.0	447.1	447.2	447.4	447.5	447.7
175°	450.6	450.1	449.6	449.1	448.6	448.3	448.4	448.5	448.7	448.8	449.0
177.5°	451.3	450.8	450.3	449.8	449.3	449.0	449.0	449.1	449.2	449.2	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1529.1	1531.1	1534.2	1548.6	1550.6	1554.7	1552.7	1552.7	1553.7	1551.7	1552.7
5°	1594.8	1597.8	1613.2	1630.7	1634.8	1630.7	1635.8	1643.0	1643.0	1643.0	1640.9
7.5°	1656.3	1667.6	1685.1	1710.7	1715.9	1721.0	1730.2	1724.1	1726.1	1735.4	1732.3
10°	1715.9	1732.3	1751.8	1773.3	1784.6	1791.8	1795.9	1805.1	1826.7	1802.1	1811.3
12.5°	1772.3	1795.9	1816.4	1840.0	1848.2	1857.5	1860.6	1868.8	1868.8	1867.7	1874.9
15°	1809.2	1830.8	1849.3	1864.7	1866.7	1864.7	1862.6	1863.6	1866.7	1854.4	1861.6
17.5°	1817.5	1819.5	1825.7	1819.5	1820.5	1799.0	1786.7	1783.6	1754.9	1755.9	1779.5
20°	1777.4	1742.5	1733.3	1699.4	1678.9	1623.5	1621.4	1606.1	1545.5	1564.0	1559.9
22.5°	1667.6	1608.1	1529.1	1490.1	1470.6	1412.1	1366.9	1335.1	1313.6	1292.0	1282.8
25°	1522.9	1426.5	1314.6	1237.6	1226.3	1172.0	1088.8	1049.8	1003.7	989.3	1013.9
27.5°	1336.2	1211.0	1084.7	966.7	945.2	895.9	853.8	826.1	772.8	769.7	771.7
30°	1082.7	956.4	850.7	773.8	720.4	697.8	670.1	649.6	628.1	636.3	638.3
32.5°	889.7	769.7	671.2	630.1	605.5	591.1	567.5	554.2	544.9	541.8	540.8
35°	707.1	627.0	582.9	542.9	528.5	518.2	500.8	494.6	486.4	487.5	487.5
37.5°	605.5	538.8	505.9	485.4	472.1	466.9	455.6	449.5	444.4	442.3	445.4
40°	522.4	476.2	455.6	437.2	425.9	423.8	417.7	410.5	404.3	405.4	408.4
42.5°	461.8	435.1	410.5	396.1	387.9	384.8	379.7	374.6	374.6	371.5	370.5
45°	413.6	392.0	371.5	358.2	353.0	348.9	342.8	341.7	337.6	338.7	339.7
47.5°	370.5	353.0	337.6	324.3	319.2	318.1	312.0	307.9	307.9	306.8	305.8
50°	331.5	314.0	300.7	293.5	286.3	284.3	283.2	282.2	280.2	280.2	281.2
52.5°	299.7	282.2	272.0	265.8	261.7	259.6	259.6	258.6	258.6	258.6	257.6
55°	264.8	250.4	242.2	240.1	238.1	237.1	236.0	234.0	233.0	235.0	233.0
57.5°	231.9	226.8	219.6	217.6	212.4	212.4	209.4	207.3	205.2	207.3	207.3
60°	206.3	199.1	195.0	188.8	184.7	180.6	175.5	174.5	172.4	171.4	170.4
62.5°	179.6	173.4	163.2	153.9	147.8	143.7	141.6	140.6	140.6	139.6	139.6
65°	149.8	135.5	130.3	127.3	126.2	125.2	123.1	122.1	123.1	122.1	123.1
67.5°	117.0	114.9	111.9	109.8	108.8	107.8	107.8	106.7	106.7	106.7	106.7
70°	101.6	96.5	95.4	93.4	93.4	92.4	92.4	92.4	92.4	91.3	93.4
72.5°	84.2	81.1	80.0	79.0	79.0	79.0	78.0	78.0	78.0	77.0	78.0
75°	68.8	67.7	65.7	65.7	64.7	65.7	64.7	64.7	63.6	64.7	64.7
77.5°	55.4	54.4	53.4	53.4	52.3	52.3	52.3	52.3	52.3	52.3	53.4
80°	42.1	41.0	40.0	41.0	40.0	41.0	40.0	40.0	41.0	40.0	40.0
82.5°	30.8	29.8	29.8	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7
85°	18.5	17.4	17.4	18.5	17.4	18.5	17.4	17.4	17.4	18.5	18.5
87.5°	8.2	9.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.2
90°	6.9	7.2	7.6	7.9	8.1	8.2	8.3	8.5	8.6	8.8	8.6
92.5°	8.0	8.1	8.3	8.4	8.5	8.5	8.6	8.7	8.7	8.8	8.7
95°	13.1	13.4	13.8	14.1	14.3	14.3	14.2	14.1	14.1	14.0	14.1
97.5°	16.8	17.0	17.3	17.5	17.6	17.6	17.7	17.8	17.8	17.9	17.8
100°	19.1	19.7	20.2	20.8	21.1	21.2	21.3	21.5	21.6	21.8	21.6
102.5°	20.0	20.8	21.6	22.4	22.8	22.9	23.1	23.4	23.6	23.8	23.6
105°	20.6	21.4	22.2	23.0	23.4	23.5	23.8	24.1	24.4	24.7	24.4
107.5°	21.3	22.1	22.9	23.7	24.1	24.2	24.5	24.8	25.1	25.4	25.1
110°	49.7	42.5	35.2	28.0	24.4	24.5	24.8	25.1	25.4	25.7	25.4



TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	134.1	103.0	71.8	40.7	25.1	25.2	25.4	25.6	25.8	26.0	25.8
115°	167.2	133.8	100.3	66.8	50.1	47.5	42.3	37.1	31.9	26.7	31.9
117.5°	208.0	197.6	187.3	177.0	171.8	162.3	143.4	124.4	105.5	86.5	105.5
120°	239.4	240.2	241.1	242.0	242.4	237.5	227.8	218.0	208.3	198.5	208.3
122.5°	258.1	258.5	259.0	259.4	259.6	259.6	259.7	259.8	259.9	260.0	259.9
125°	275.4	275.9	276.4	276.9	277.2	277.3	277.5	277.8	278.0	278.2	278.0
127.5°	291.6	292.3	293.0	293.7	294.1	294.1	294.2	294.3	294.4	294.5	294.4
130°	307.0	307.8	308.5	309.3	309.7	309.7	309.6	309.5	309.5	309.4	309.5
132.5°	322.1	322.8	323.4	324.1	324.4	324.4	324.3	324.2	324.2	324.1	324.2
135°	336.1	336.9	337.6	338.3	338.7	338.6	338.5	338.3	338.2	338.0	338.2
137.5°	349.5	350.2	350.9	351.6	352.0	351.9	351.7	351.5	351.3	351.1	351.3
140°	362.4	363.1	363.7	364.4	364.7	364.5	364.2	363.8	363.5	363.1	363.5
142.5°	374.4	375.0	375.5	376.1	376.4	376.2	375.9	375.5	375.2	374.8	375.2
145°	385.4	385.9	386.4	386.9	387.2	387.0	386.7	386.3	386.0	385.6	386.0
147.5°	395.4	395.7	396.1	396.4	396.6	396.5	396.2	395.9	395.6	395.3	395.6
150°	404.2	404.6	405.1	405.5	405.7	405.5	405.2	404.8	404.5	404.1	404.5
152.5°	412.3	412.8	413.2	413.7	413.9	413.6	413.1	412.6	412.1	411.6	412.1
155°	419.5	419.9	420.4	420.8	421.0	420.7	420.1	419.6	419.0	418.4	419.0
157.5°	425.7	426.2	426.7	427.2	427.5	427.2	426.6	426.1	425.5	424.9	425.5
160°	431.2	431.6	432.1	432.5	432.7	432.5	432.0	431.5	431.0	430.5	431.0
162.5°	436.2	436.7	437.2	437.7	437.9	437.6	436.9	436.3	435.6	435.0	435.6
165°	440.1	440.6	441.1	441.6	441.8	441.6	441.1	440.6	440.1	439.6	440.1
167.5°	443.6	444.1	444.6	445.1	445.4	445.1	444.4	443.8	443.1	442.5	443.1
170°	446.2	446.7	447.2	447.7	448.0	447.7	447.0	446.4	445.7	445.1	445.7
172.5°	448.2	448.7	449.2	449.7	450.0	449.7	449.0	448.3	447.7	447.0	447.7
175°	449.5	450.0	450.5	451.0	451.3	450.9	450.2	449.5	448.7	448.0	448.7
177.5°	449.8	450.3	450.8	451.3	451.6	451.3	450.6	450.0	449.3	448.7	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1556.8	1549.6	1547.6	1549.6	1547.6	1548.6	1541.4	1514.7	1521.9	1510.6	1516.8
5°	1645.0	1638.9	1625.5	1623.5	1621.4	1619.4	1609.1	1585.5	1576.3	1560.9	1559.9
7.5°	1729.2	1729.2	1718.9	1711.8	1702.5	1695.3	1682.0	1647.1	1632.7	1614.3	1604.0
10°	1812.3	1785.6	1796.9	1789.7	1767.2	1763.1	1738.4	1717.9	1690.2	1671.7	1655.3
12.5°	1871.8	1863.6	1853.4	1847.2	1841.1	1827.7	1811.3	1759.0	1744.6	1707.6	1689.2
15°	1869.8	1864.7	1867.7	1867.7	1865.7	1862.6	1849.3	1811.3	1786.7	1750.7	1718.9
17.5°	1769.2	1782.6	1795.9	1805.1	1825.7	1834.9	1847.2	1824.6	1809.2	1778.5	1744.6
20°	1593.7	1626.6	1665.6	1673.8	1692.3	1746.6	1771.3	1790.8	1796.9	1786.7	1759.0
22.5°	1349.5	1377.2	1471.6	1469.6	1496.2	1560.9	1632.7	1691.2	1737.4	1763.1	1752.8
25°	1057.0	1096.0	1146.3	1184.3	1271.5	1368.0	1457.2	1550.6	1630.7	1701.5	1718.9
27.5°	799.4	850.7	890.8	941.1	985.2	1099.1	1214.0	1359.8	1453.1	1587.6	1657.4
30°	646.5	670.1	710.2	733.8	755.3	842.5	972.9	1116.5	1280.7	1435.7	1555.8
32.5°	552.1	568.5	598.3	608.6	631.1	689.6	771.7	903.1	1072.4	1260.2	1418.3
35°	495.7	513.1	519.3	528.5	547.0	583.9	640.4	735.8	888.7	1072.4	1261.2
37.5°	447.4	456.7	474.1	480.3	486.4	514.1	552.1	618.8	720.4	871.3	1080.6
40°	413.6	418.7	427.9	433.1	437.2	456.7	490.5	535.7	610.6	725.5	918.5
42.5°	377.7	383.8	390.0	396.1	401.3	416.6	437.2	480.3	530.6	617.8	757.4
45°	342.8	346.9	354.0	358.2	365.3	377.7	396.1	425.9	471.0	526.5	639.3
47.5°	310.9	316.1	319.2	324.3	329.4	342.8	360.2	379.7	416.6	471.0	553.1
50°	282.2	288.4	292.5	293.5	297.6	309.9	324.3	345.8	369.4	411.5	483.4
52.5°	261.7	262.7	265.8	269.9	268.9	276.1	289.4	305.8	330.4	364.3	416.6
55°	238.1	241.2	243.2	244.2	244.2	250.4	257.6	273.0	292.5	320.2	364.3
57.5°	208.3	211.4	217.6	219.6	222.7	225.8	228.8	239.1	255.5	282.2	318.1
60°	177.5	179.6	185.7	189.9	191.9	200.1	204.2	212.4	221.7	241.2	275.0
62.5°	142.6	144.7	147.8	151.9	156.0	168.3	178.6	186.8	194.0	207.3	235.0
65°	124.2	125.2	127.3	128.3	129.3	134.4	143.7	155.0	168.3	178.6	195.0
67.5°	107.8	108.8	109.8	111.9	112.9	113.9	118.0	121.1	134.4	148.8	161.1
70°	92.4	94.4	95.4	95.4	96.5	98.5	100.6	104.7	108.8	116.0	131.4
72.5°	78.0	79.0	81.1	81.1	81.1	83.1	85.2	87.2	89.3	93.4	99.5
75°	64.7	66.7	66.7	66.7	67.7	67.7	69.8	71.8	73.9	77.0	79.0
77.5°	53.4	53.4	53.4	53.4	54.4	54.4	55.4	57.5	58.5	59.5	61.6
80°	40.0	41.0	41.0	41.0	42.1	42.1	42.1	44.1	45.2	45.2	47.2
82.5°	29.8	29.8	29.8	30.8	29.8	30.8	30.8	31.8	30.8	31.8	32.8
85°	18.5	18.5	18.5	19.5	19.5	19.5	19.5	19.5	19.5	19.5	20.5
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.3	9.2	9.2
90°	8.5	8.3	8.2	8.1	7.9	7.6	7.2	6.9	6.5	5.9	5.3
92.5°	8.7	8.6	8.5	8.5	8.4	8.3	8.1	8.0	7.8	7.6	7.4
95°	14.1	14.2	14.3	14.3	14.1	13.8	13.4	13.1	12.7	12.2	11.7
97.5°	17.8	17.7	17.6	17.6	17.5	17.3	17.0	16.8	16.6	15.4	14.3
100°	21.5	21.3	21.2	21.1	20.8	20.2	19.7	19.1	18.5	17.3	16.1
102.5°	23.4	23.1	22.9	22.8	22.4	21.6	20.8	20.0	19.2	32.4	45.5
105°	24.1	23.8	23.5	23.4	23.0	22.2	21.4	20.6	19.8	39.6	59.3
107.5°	24.8	24.5	24.2	24.1	23.7	22.9	22.1	21.3	20.5	44.9	69.2
110°	25.1	24.8	24.5	24.4	28.0	35.2	42.5	49.7	56.9	77.8	98.7

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	25.6	25.4	25.2	25.1	40.7	71.8	103.0	134.1	165.3	166.5	167.7
115°	37.1	42.3	47.5	50.1	66.8	100.3	133.8	167.2	200.7	198.9	197.1
117.5°	124.4	143.4	162.3	171.8	177.0	187.3	197.6	208.0	218.3	217.1	215.9
120°	218.0	227.8	237.5	242.4	242.0	241.1	240.2	239.4	238.5	237.2	235.9
122.5°	259.8	259.7	259.6	259.6	259.4	259.0	258.5	258.1	257.7	256.3	254.8
125°	277.8	277.5	277.3	277.2	276.9	276.4	275.9	275.4	274.9	273.5	272.1
127.5°	294.3	294.2	294.1	294.1	293.7	293.0	292.3	291.6	290.9	289.8	288.7
130°	309.5	309.6	309.7	309.7	309.3	308.5	307.8	307.0	306.2	305.4	304.6
132.5°	324.2	324.3	324.4	324.4	324.1	323.4	322.8	322.1	321.5	320.7	319.9
135°	338.3	338.5	338.6	338.7	338.3	337.6	336.9	336.1	335.4	334.8	334.1
137.5°	351.5	351.7	351.9	352.0	351.6	350.9	350.2	349.5	348.8	348.1	347.3
140°	363.8	364.2	364.5	364.7	364.4	363.7	363.1	362.4	361.8	361.0	360.2
142.5°	375.5	375.9	376.2	376.4	376.1	375.5	375.0	374.4	373.8	372.9	371.9
145°	386.3	386.7	387.0	387.2	386.9	386.4	385.9	385.4	384.9	383.7	382.5
147.5°	395.9	396.2	396.5	396.6	396.4	396.1	395.7	395.4	395.0	393.8	392.6
150°	404.8	405.2	405.5	405.7	405.5	405.1	404.6	404.2	403.8	402.6	401.5
152.5°	412.6	413.1	413.6	413.9	413.7	413.2	412.8	412.3	411.9	410.8	409.7
155°	419.6	420.1	420.7	421.0	420.8	420.4	419.9	419.5	419.1	418.2	417.4
157.5°	426.1	426.6	427.2	427.5	427.2	426.7	426.2	425.7	425.2	424.6	423.9
160°	431.5	432.0	432.5	432.7	432.5	432.1	431.6	431.2	430.8	430.4	429.9
162.5°	436.3	436.9	437.6	437.9	437.7	437.2	436.7	436.2	435.7	435.3	434.9
165°	440.6	441.1	441.6	441.8	441.6	441.1	440.6	440.1	439.6	439.4	439.2
167.5°	443.8	444.4	445.1	445.4	445.1	444.6	444.1	443.6	443.1	442.9	442.7
170°	446.4	447.0	447.7	448.0	447.7	447.2	446.7	446.2	445.7	445.6	445.4
172.5°	448.3	449.0	449.7	450.0	449.7	449.2	448.7	448.2	447.7	447.5	447.4
175°	449.5	450.2	450.9	451.3	451.0	450.5	450.0	449.5	449.0	448.8	448.7
177.5°	450.0	450.6	451.3	451.6	451.3	450.8	450.3	449.8	449.3	449.2	449.2
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1507.5	1502.4	1502.4	1499.3	1499.3	1482.9	1482.9	1488.0	1481.9	1474.7	1464.4
5°	1546.5	1535.2	1532.2	1528.1	1514.7	1494.2	1486.0	1482.9	1470.6	1455.2	1437.7
7.5°	1583.5	1565.0	1555.8	1546.5	1529.1	1500.3	1483.9	1472.6	1454.2	1430.6	1408.0
10°	1619.4	1595.8	1572.2	1560.9	1536.3	1500.3	1476.7	1458.3	1431.6	1399.8	1368.0
12.5°	1652.2	1603.0	1598.9	1576.3	1540.4	1499.3	1463.4	1436.7	1402.9	1365.9	1329.0
15°	1681.0	1630.7	1606.1	1585.5	1538.3	1487.0	1449.0	1416.2	1371.0	1329.0	1283.8
17.5°	1695.3	1640.9	1624.5	1590.7	1542.4	1475.7	1424.4	1384.4	1335.1	1284.8	1233.5
20°	1709.7	1646.1	1619.4	1595.8	1530.1	1454.2	1396.7	1350.5	1296.1	1236.6	1180.2
22.5°	1716.9	1646.1	1614.3	1581.4	1517.8	1430.6	1362.8	1308.4	1244.8	1184.3	1116.5
25°	1704.6	1639.9	1601.9	1568.1	1496.2	1401.8	1323.8	1262.3	1194.5	1125.8	1057.0
27.5°	1673.8	1625.5	1581.4	1546.5	1466.5	1364.9	1282.8	1213.0	1143.2	1066.3	996.5
30°	1616.3	1594.8	1559.9	1520.9	1433.6	1332.0	1234.6	1162.7	1085.8	1008.8	935.9
32.5°	1527.0	1545.5	1522.9	1489.1	1394.6	1286.9	1183.2	1110.4	1026.2	943.1	876.4
35°	1418.3	1483.9	1471.6	1448.0	1353.6	1238.7	1135.0	1046.8	962.6	878.5	811.7
37.5°	1299.2	1398.8	1409.0	1394.6	1306.4	1189.4	1075.5	989.3	903.1	817.9	750.2
40°	1136.0	1288.9	1321.8	1327.9	1257.1	1129.9	1010.8	926.7	841.5	758.4	676.3
42.5°	986.2	1179.1	1220.2	1245.8	1194.5	1071.4	951.3	857.9	773.8	698.9	616.8
45°	845.6	1046.8	1113.5	1146.3	1123.7	1004.7	880.5	793.3	716.3	647.6	568.5
47.5°	700.9	903.1	996.5	1048.8	1048.8	936.9	812.8	726.6	652.7	594.2	524.4
50°	604.4	772.8	869.2	938.0	956.4	868.2	751.2	667.0	597.3	533.6	480.3
52.5°	515.2	666.0	746.1	817.9	871.3	794.3	682.4	606.5	537.7	478.2	436.1
55°	445.4	558.3	631.1	710.2	769.7	719.4	615.7	541.8	482.3	433.1	397.2
57.5°	378.7	477.2	536.7	606.5	670.1	632.2	549.0	485.4	433.1	390.0	358.2
60°	322.2	402.3	448.5	502.9	581.9	555.2	486.4	427.9	385.9	346.9	320.2
62.5°	274.0	337.6	376.6	415.6	487.5	475.1	421.8	376.6	340.7	307.9	285.3
65°	224.7	277.1	307.9	341.7	399.2	404.3	361.2	329.4	296.6	267.8	247.3
67.5°	181.6	222.7	250.4	279.1	325.3	339.7	309.9	283.2	255.5	231.9	213.5
70°	146.8	175.5	196.0	218.6	256.6	274.0	258.6	240.1	217.6	198.1	181.6
72.5°	116.0	134.4	146.8	164.2	195.0	212.4	211.4	195.0	178.6	165.2	151.9
75°	85.2	99.5	109.8	121.1	145.7	162.1	166.2	159.1	142.6	132.4	122.1
77.5°	64.7	72.9	78.0	86.2	103.6	118.0	124.2	122.1	110.8	102.6	95.4
80°	49.3	51.3	53.4	56.4	70.8	84.2	88.3	87.2	81.1	78.0	69.8
82.5°	34.9	35.9	36.9	38.0	43.1	54.4	58.5	60.5	55.4	52.3	45.2
85°	20.5	21.6	21.6	23.6	24.6	27.7	34.9	34.9	33.9	29.8	28.7
87.5°	10.3	10.3	9.2	9.2	10.3	11.3	13.3	15.4	13.3	12.3	11.3
90°	4.8	4.2	3.9	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.1	6.9	6.8	6.9	7.2	7.5	7.8	8.1	7.8	7.5	7.2
95°	11.2	10.7	10.4	11.6	14.0	16.3	18.7	21.1	18.7	16.3	14.0
97.5°	13.1	12.0	11.4	14.4	20.3	26.2	32.2	38.1	32.2	26.2	20.3
100°	14.8	13.6	13.0	18.0	27.9	37.8	47.7	57.6	47.7	37.8	27.9
102.5°	58.7	71.8	78.4	78.5	78.6	78.8	78.9	79.1	78.9	78.8	78.6
105°	79.1	98.8	108.7	107.6	105.4	103.3	101.1	98.9	101.1	103.3	105.4
107.5°	93.6	117.9	130.1	129.2	127.4	125.6	123.8	122.0	123.8	125.6	127.4
110°	119.6	140.5	151.0	150.2	148.7	147.2	145.6	144.1	145.6	147.2	148.7

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	169.0	170.2	170.8	170.2	168.9	167.6	166.3	165.0	166.3	167.6	168.9
115°	195.3	193.5	192.6	192.0	190.8	189.5	188.3	187.1	188.3	189.5	190.8
117.5°	214.6	213.4	212.8	212.1	210.6	209.2	207.7	206.3	207.7	209.2	210.6
120°	234.6	233.3	232.6	232.1	231.0	229.9	228.9	227.8	228.9	229.9	231.0
122.5°	253.4	251.9	251.2	250.6	249.5	248.3	247.2	246.0	247.2	248.3	249.5
125°	270.8	269.4	268.7	268.2	267.3	266.4	265.4	264.5	265.4	266.4	267.3
127.5°	287.6	286.5	286.0	285.5	284.5	283.4	282.4	281.4	282.4	283.4	284.5
130°	303.8	303.0	302.6	302.0	300.9	299.7	298.6	297.4	298.6	299.7	300.9
132.5°	319.1	318.3	317.9	317.4	316.5	315.5	314.6	313.6	314.6	315.5	316.5
135°	333.5	332.8	332.5	331.9	330.8	329.6	328.5	327.3	328.5	329.6	330.8
137.5°	346.6	345.9	345.5	345.1	344.2	343.3	342.5	341.6	342.5	343.3	344.2
140°	359.4	358.6	358.2	357.9	357.3	356.8	356.2	355.6	356.2	356.8	357.3
142.5°	371.0	370.1	369.6	369.3	368.8	368.3	367.8	367.3	367.8	368.3	368.8
145°	381.2	380.0	379.4	379.4	379.5	379.6	379.6	379.7	379.6	379.6	379.5
147.5°	391.3	390.1	389.5	389.6	389.8	390.0	390.2	390.4	390.2	390.0	389.8
150°	400.3	399.2	398.6	398.8	399.3	399.8	400.3	400.8	400.3	399.8	399.3
152.5°	408.6	407.5	407.0	407.3	407.9	408.4	409.0	409.6	409.0	408.4	407.9
155°	416.5	415.6	415.2	415.5	416.2	416.8	417.5	418.1	417.5	416.8	416.2
157.5°	423.3	422.6	422.3	422.6	423.2	423.7	424.3	424.9	424.3	423.7	423.2
160°	429.5	429.0	428.8	429.0	429.5	429.9	430.4	430.8	430.4	429.9	429.5
162.5°	434.6	434.2	434.0	434.2	434.7	435.1	435.6	436.0	435.6	435.1	434.7
165°	438.9	438.7	438.6	438.8	439.2	439.7	440.1	440.5	440.1	439.7	439.2
167.5°	442.5	442.3	442.2	442.4	442.8	443.3	443.7	444.1	443.7	443.3	442.8
170°	445.3	445.2	445.1	445.3	445.7	446.2	446.6	447.0	446.6	446.2	445.7
172.5°	447.2	447.1	447.0	447.2	447.7	448.1	448.6	449.0	448.6	448.1	447.7
175°	448.5	448.4	448.3	448.6	449.1	449.6	450.1	450.6	450.1	449.6	449.1
177.5°	449.1	449.0	449.0	449.3	449.8	450.3	450.8	451.3	450.8	450.3	449.8
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1460.3	1461.4	1464.4	1455.2	1440.8	1434.7	1416.2	1413.1	1410.0	1410.0	1413.1
5°	1427.5	1423.4	1424.4	1407.0	1386.4	1374.1	1348.5	1352.6	1339.2	1331.0	1333.1
7.5°	1391.6	1380.3	1379.3	1356.7	1331.0	1308.4	1281.8	1275.6	1263.3	1248.9	1242.8
10°	1346.4	1338.2	1322.8	1297.2	1264.3	1245.8	1209.9	1188.4	1185.3	1163.7	1155.5
12.5°	1300.2	1285.9	1270.5	1234.6	1197.6	1167.9	1141.2	1117.6	1101.1	1082.7	1070.4
15°	1246.9	1229.4	1212.0	1174.0	1130.9	1101.1	1061.1	1026.2	978.0	940.0	918.5
17.5°	1188.4	1168.9	1145.3	1103.2	1061.1	1020.1	946.2	905.1	871.3	848.7	835.4
20°	1127.8	1106.3	1082.7	1040.6	967.7	895.9	854.9	823.0	802.5	779.9	763.5
22.5°	1064.2	1041.6	1016.0	950.3	873.3	823.0	791.2	761.5	731.7	719.4	711.2
25°	1004.7	984.2	951.3	862.0	801.5	755.3	719.4	699.9	684.5	668.1	652.7
27.5°	943.1	905.1	859.0	784.0	746.1	698.9	673.2	658.8	632.2	620.9	613.7
30°	869.2	827.1	783.0	729.6	685.5	652.7	629.1	605.5	590.1	578.8	566.5
32.5°	794.3	754.3	726.6	671.2	638.3	604.4	581.9	567.5	544.9	537.7	532.6
35°	729.6	695.8	671.2	626.0	595.2	564.4	548.0	526.5	512.1	498.7	490.5
37.5°	666.0	647.6	621.9	583.9	551.1	526.5	503.9	496.7	477.2	470.0	461.8
40°	621.9	594.2	572.6	539.8	512.1	485.4	471.0	454.6	441.3	430.0	426.9
42.5°	568.5	548.0	535.7	499.8	471.0	455.6	438.2	419.7	409.5	400.2	388.9
45°	528.5	510.0	492.6	463.9	438.2	418.7	403.3	391.0	373.5	369.4	352.0
47.5°	486.4	468.0	454.6	425.9	402.3	383.8	372.5	356.1	341.7	332.5	324.3
50°	444.4	429.0	416.6	392.0	371.5	352.0	336.6	320.2	314.0	298.6	293.5
52.5°	404.3	394.1	380.7	357.1	336.6	320.2	303.8	290.4	281.2	273.0	266.8
55°	370.5	354.0	347.9	322.2	304.8	287.3	273.0	264.8	253.5	248.3	243.2
57.5°	332.5	323.3	313.0	293.5	274.0	257.6	247.3	235.0	228.8	222.7	218.6
60°	299.7	286.3	278.1	261.7	244.2	228.8	219.6	210.4	202.2	197.0	188.8
62.5°	261.7	251.4	246.3	228.8	214.5	200.1	191.9	182.7	176.5	167.3	157.0
65°	228.8	220.6	214.5	200.1	186.8	173.4	165.2	153.9	145.7	140.6	139.6
67.5°	200.1	194.0	184.7	171.4	158.0	147.8	138.5	129.3	128.3	126.2	126.2
70°	168.3	162.1	157.0	142.6	131.4	120.1	118.0	114.9	111.9	110.8	108.8
72.5°	140.6	135.5	129.3	117.0	105.7	102.6	100.6	98.5	95.4	94.4	93.4
75°	113.9	106.7	102.6	91.3	88.3	86.2	84.2	81.1	79.0	78.0	75.9
77.5°	87.2	80.0	80.0	73.9	71.8	68.8	66.7	64.7	63.6	61.6	61.6
80°	61.6	61.6	59.5	56.4	53.4	52.3	49.3	48.2	47.2	48.2	46.2
82.5°	45.2	41.0	41.0	39.0	36.9	35.9	33.9	33.9	32.8	32.8	32.8
85°	25.7	25.7	24.6	22.6	21.6	21.6	20.5	20.5	19.5	19.5	18.5
87.5°	10.3	9.2	10.3	9.2	9.2	8.2	8.2	8.2	7.2	8.2	7.2
90°	3.5	3.9	4.2	4.8	5.3	5.9	6.5	6.9	7.2	7.6	7.9
92.5°	6.9	6.8	6.9	7.1	7.4	7.6	7.8	8.0	8.1	8.3	8.4
95°	11.6	10.4	10.7	11.2	11.7	12.2	12.7	13.1	13.4	13.8	14.1
97.5°	14.4	11.4	12.0	13.1	14.3	15.4	16.6	16.8	17.0	17.3	17.5
100°	18.0	13.0	13.6	14.8	16.1	17.3	18.5	19.1	19.7	20.2	20.8
102.5°	78.5	78.4	71.8	58.7	45.5	32.4	19.2	20.0	20.8	21.6	22.4
105°	107.6	108.7	98.8	79.1	59.3	39.6	19.8	20.6	21.4	22.2	23.0
107.5°	129.2	130.1	117.9	93.6	69.2	44.9	20.5	21.3	22.1	22.9	23.7
110°	150.2	151.0	140.5	119.6	98.7	77.8	56.9	49.7	42.5	35.2	28.0

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	170.2	170.8	170.2	169.0	167.7	166.5	165.3	134.1	103.0	71.8	40.7
115°	192.0	192.6	193.5	195.3	197.1	198.9	200.7	167.2	133.8	100.3	66.8
117.5°	212.1	212.8	213.4	214.6	215.9	217.1	218.3	208.0	197.6	187.3	177.0
120°	232.1	232.6	233.3	234.6	235.9	237.2	238.5	239.4	240.2	241.1	242.0
122.5°	250.6	251.2	251.9	253.4	254.8	256.3	257.7	258.1	258.5	259.0	259.4
125°	268.2	268.7	269.4	270.8	272.1	273.5	274.9	275.4	275.9	276.4	276.9
127.5°	285.5	286.0	286.5	287.6	288.7	289.8	290.9	291.6	292.3	293.0	293.7
130°	302.0	302.6	303.0	303.8	304.6	305.4	306.2	307.0	307.8	308.5	309.3
132.5°	317.4	317.9	318.3	319.1	319.9	320.7	321.5	322.1	322.8	323.4	324.1
135°	331.9	332.5	332.8	333.5	334.1	334.8	335.4	336.1	336.9	337.6	338.3
137.5°	345.1	345.5	345.9	346.6	347.3	348.1	348.8	349.5	350.2	350.9	351.6
140°	357.9	358.2	358.6	359.4	360.2	361.0	361.8	362.4	363.1	363.7	364.4
142.5°	369.3	369.6	370.1	371.0	371.9	372.9	373.8	374.4	375.0	375.5	376.1
145°	379.4	379.4	380.0	381.2	382.5	383.7	384.9	385.4	385.9	386.4	386.9
147.5°	389.6	389.5	390.1	391.3	392.6	393.8	395.0	395.4	395.7	396.1	396.4
150°	398.8	398.6	399.2	400.3	401.5	402.6	403.8	404.2	404.6	405.1	405.5
152.5°	407.3	407.0	407.5	408.6	409.7	410.8	411.9	412.3	412.8	413.2	413.7
155°	415.5	415.2	415.6	416.5	417.4	418.2	419.1	419.5	419.9	420.4	420.8
157.5°	422.6	422.3	422.6	423.3	423.9	424.6	425.2	425.7	426.2	426.7	427.2
160°	429.0	428.8	429.0	429.5	429.9	430.4	430.8	431.2	431.6	432.1	432.5
162.5°	434.2	434.0	434.2	434.6	434.9	435.3	435.7	436.2	436.7	437.2	437.7
165°	438.8	438.6	438.7	438.9	439.2	439.4	439.6	440.1	440.6	441.1	441.6
167.5°	442.4	442.2	442.3	442.5	442.7	442.9	443.1	443.6	444.1	444.6	445.1
170°	445.3	445.1	445.2	445.3	445.4	445.6	445.7	446.2	446.7	447.2	447.7
172.5°	447.2	447.0	447.1	447.2	447.4	447.5	447.7	448.2	448.7	449.2	449.7
175°	448.6	448.3	448.4	448.5	448.7	448.8	449.0	449.5	450.0	450.5	451.0
177.5°	449.3	449.0	449.0	449.1	449.2	449.2	449.3	449.8	450.3	450.8	451.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1413.1	1411.1	1404.9	1407.0	1403.9	1403.9	1401.8	1401.8	1401.8	1407.0	1403.9
5°	1336.2	1329.0	1321.8	1318.7	1315.6	1312.5	1312.5	1311.5	1320.8	1318.7	1326.9
7.5°	1240.7	1238.7	1224.3	1224.3	1219.2	1217.1	1222.2	1223.3	1224.3	1226.3	1231.5
10°	1155.5	1150.4	1129.9	1131.9	1128.9	1124.7	1127.8	1125.8	1133.0	1135.0	1133.0
12.5°	1055.0	1045.7	1023.2	1011.9	999.5	990.3	1001.6	993.4	1022.1	1030.3	1052.9
15°	921.6	904.1	888.7	888.7	877.4	869.2	874.3	883.6	889.7	899.0	903.1
17.5°	832.3	825.1	812.8	805.6	802.5	799.4	799.4	803.5	816.9	815.9	824.1
20°	756.3	752.2	746.1	736.8	733.8	731.7	731.7	731.7	740.9	749.1	754.3
22.5°	704.0	700.9	696.8	684.5	678.3	676.3	681.4	684.5	691.7	697.8	703.0
25°	651.7	644.5	637.3	633.2	630.1	630.1	632.2	633.2	636.3	639.3	645.5
27.5°	608.6	603.4	593.2	581.9	581.9	578.8	580.8	582.9	590.1	600.3	605.5
30°	560.3	559.3	555.2	551.1	547.0	544.9	549.0	552.1	553.1	558.3	558.3
32.5°	525.4	518.2	511.1	507.0	504.9	503.9	504.9	509.0	509.0	515.2	522.4
35°	490.5	486.4	479.2	472.1	470.0	464.9	469.0	473.1	480.3	483.4	486.4
37.5°	452.6	447.4	444.4	442.3	438.2	439.2	436.1	442.3	448.5	447.4	449.5
40°	423.8	414.6	405.4	404.3	403.3	402.3	402.3	403.3	407.4	411.5	417.7
42.5°	386.9	383.8	375.6	367.4	365.3	363.3	361.2	365.3	373.5	380.7	383.8
45°	348.9	344.8	342.8	336.6	332.5	331.5	329.4	334.6	341.7	344.8	346.9
47.5°	314.0	313.0	306.8	307.9	304.8	305.8	304.8	307.9	307.9	310.9	313.0
50°	290.4	287.3	284.3	282.2	279.1	279.1	278.1	279.1	283.2	287.3	286.3
52.5°	266.8	261.7	260.7	259.6	257.6	259.6	256.6	257.6	261.7	263.7	262.7
55°	239.1	238.1	236.0	234.0	233.0	231.9	231.9	231.9	236.0	239.1	240.1
57.5°	217.6	212.4	208.3	208.3	204.2	203.2	205.2	206.3	209.4	211.4	213.5
60°	187.8	185.7	179.6	176.5	170.4	169.3	169.3	173.4	178.6	185.7	187.8
62.5°	156.0	152.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9	152.9	152.9
65°	138.5	139.6	138.5	137.5	138.5	138.5	137.5	137.5	137.5	138.5	139.6
67.5°	124.2	123.1	124.2	123.1	122.1	122.1	121.1	122.1	123.1	124.2	124.2
70°	107.8	107.8	106.7	107.8	106.7	105.7	104.7	104.7	106.7	107.8	107.8
72.5°	92.4	92.4	91.3	91.3	89.3	89.3	90.3	89.3	89.3	92.4	92.4
75°	77.0	75.9	74.9	74.9	73.9	73.9	73.9	72.9	74.9	74.9	75.9
77.5°	60.5	60.5	60.5	59.5	59.5	58.5	58.5	59.5	59.5	59.5	60.5
80°	46.2	46.2	46.2	45.2	44.1	44.1	44.1	44.1	44.1	45.2	44.1
82.5°	31.8	31.8	31.8	31.8	31.8	30.8	30.8	30.8	31.8	31.8	30.8
85°	19.5	18.5	19.5	19.5	18.5	19.5	18.5	18.5	17.4	17.4	18.5
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	8.1	8.2	8.3	8.5	8.6	8.8	8.6	8.5	8.3	8.2	8.1
92.5°	8.5	8.5	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.5
95°	14.3	14.3	14.2	14.1	14.1	14.0	14.1	14.1	14.2	14.3	14.3
97.5°	17.6	17.6	17.7	17.8	17.8	17.9	17.8	17.8	17.7	17.6	17.6
100°	21.1	21.2	21.3	21.5	21.6	21.8	21.6	21.5	21.3	21.2	21.1
102.5°	22.8	22.9	23.1	23.4	23.6	23.8	23.6	23.4	23.1	22.9	22.8
105°	23.4	23.5	23.8	24.1	24.4	24.7	24.4	24.1	23.8	23.5	23.4
107.5°	24.1	24.2	24.5	24.8	25.1	25.4	25.1	24.8	24.5	24.2	24.1
110°	24.4	24.5	24.8	25.1	25.4	25.7	25.4	25.1	24.8	24.5	24.4

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	25.1	25.2	25.4	25.6	25.8	26.0	25.8	25.6	25.4	25.2	25.1
115°	50.1	47.5	42.3	37.1	31.9	26.7	31.9	37.1	42.3	47.5	50.1
117.5°	171.8	162.3	143.4	124.4	105.5	86.5	105.5	124.4	143.4	162.3	171.8
120°	242.4	237.5	227.8	218.0	208.3	198.5	208.3	218.0	227.8	237.5	242.4
122.5°	259.6	259.6	259.7	259.8	259.9	260.0	259.9	259.8	259.7	259.6	259.6
125°	277.2	277.3	277.5	277.8	278.0	278.2	278.0	277.8	277.5	277.3	277.2
127.5°	294.1	294.1	294.2	294.3	294.4	294.5	294.4	294.3	294.2	294.1	294.1
130°	309.7	309.7	309.6	309.5	309.5	309.4	309.5	309.5	309.6	309.7	309.7
132.5°	324.4	324.4	324.3	324.2	324.2	324.1	324.2	324.2	324.3	324.4	324.4
135°	338.7	338.6	338.5	338.3	338.2	338.0	338.2	338.3	338.5	338.6	338.7
137.5°	352.0	351.9	351.7	351.5	351.3	351.1	351.3	351.5	351.7	351.9	352.0
140°	364.7	364.5	364.2	363.8	363.5	363.1	363.5	363.8	364.2	364.5	364.7
142.5°	376.4	376.2	375.9	375.5	375.2	374.8	375.2	375.5	375.9	376.2	376.4
145°	387.2	387.0	386.7	386.3	386.0	385.6	386.0	386.3	386.7	387.0	387.2
147.5°	396.6	396.5	396.2	395.9	395.6	395.3	395.6	395.9	396.2	396.5	396.6
150°	405.7	405.5	405.2	404.8	404.5	404.1	404.5	404.8	405.2	405.5	405.7
152.5°	413.9	413.6	413.1	412.6	412.1	411.6	412.1	412.6	413.1	413.6	413.9
155°	421.0	420.7	420.1	419.6	419.0	418.4	419.0	419.6	420.1	420.7	421.0
157.5°	427.5	427.2	426.6	426.1	425.5	424.9	425.5	426.1	426.6	427.2	427.5
160°	432.7	432.5	432.0	431.5	431.0	430.5	431.0	431.5	432.0	432.5	432.7
162.5°	437.9	437.6	436.9	436.3	435.6	435.0	435.6	436.3	436.9	437.6	437.9
165°	441.8	441.6	441.1	440.6	440.1	439.6	440.1	440.6	441.1	441.6	441.8
167.5°	445.4	445.1	444.4	443.8	443.1	442.5	443.1	443.8	444.4	445.1	445.4
170°	448.0	447.7	447.0	446.4	445.7	445.1	445.7	446.4	447.0	447.7	448.0
172.5°	450.0	449.7	449.0	448.3	447.7	447.0	447.7	448.3	449.0	449.7	450.0
175°	451.3	450.9	450.2	449.5	448.7	448.0	448.7	449.5	450.2	450.9	451.3
177.5°	451.6	451.3	450.6	450.0	449.3	448.7	449.3	450.0	450.6	451.3	451.6
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1407.0	1412.1	1410.0	1398.8	1410.0	1413.1	1419.3	1425.4	1429.5	1435.7	1440.8
5°	1318.7	1329.0	1335.1	1329.0	1349.5	1352.6	1366.9	1375.1	1387.5	1397.7	1405.9
7.5°	1235.6	1243.8	1256.1	1258.2	1270.5	1284.8	1305.4	1325.9	1345.4	1355.7	1364.9
10°	1146.3	1160.7	1179.1	1175.0	1193.5	1216.1	1237.6	1270.5	1286.9	1305.4	1321.8
12.5°	1057.0	1066.3	1090.9	1099.1	1125.8	1143.2	1173.0	1193.5	1234.6	1256.1	1270.5
15°	901.0	939.0	969.8	1006.7	1041.6	1074.5	1101.1	1138.1	1174.0	1190.4	1214.0
17.5°	830.2	847.7	866.1	884.6	929.8	988.3	1035.5	1075.5	1106.3	1127.8	1155.5
20°	756.3	773.8	794.3	811.7	839.5	881.5	940.0	1008.8	1045.7	1068.3	1095.0
22.5°	704.0	720.4	733.8	749.1	770.7	801.5	845.6	930.8	980.1	1007.8	1031.4
25°	647.6	668.1	682.4	693.7	711.2	745.0	781.0	829.2	917.5	939.0	971.8
27.5°	608.6	614.7	631.1	648.6	666.0	684.5	721.4	762.5	822.0	869.2	909.2
30°	562.4	577.8	593.2	600.3	615.7	642.4	665.0	709.1	755.3	792.3	840.5
32.5°	527.5	536.7	547.0	564.4	578.8	597.3	619.8	656.8	695.8	719.4	756.3
35°	488.5	494.6	516.2	523.4	537.7	556.2	578.8	607.5	649.6	668.1	694.8
37.5°	451.5	465.9	472.1	488.5	501.8	520.3	536.7	569.6	597.3	618.8	643.4
40°	422.8	429.0	440.3	454.6	465.9	480.3	500.8	524.4	554.2	571.6	593.2
42.5°	387.9	393.0	407.4	415.6	434.1	447.4	459.8	488.5	515.2	528.5	550.1
45°	349.9	362.3	371.5	387.9	398.2	414.6	430.0	450.5	475.1	490.5	502.9
47.5°	317.1	329.4	338.7	354.0	370.5	377.7	394.1	415.6	438.2	450.5	468.0
50°	290.4	294.5	312.0	319.2	336.6	351.0	362.3	380.7	405.4	412.5	426.9
52.5°	264.8	267.8	279.1	288.4	303.8	316.1	330.4	347.9	368.4	379.7	391.0
55°	242.2	244.2	249.4	259.6	269.9	285.3	298.6	315.1	332.5	344.8	355.1
57.5°	216.5	220.6	224.7	230.9	241.2	255.5	269.9	285.3	299.7	307.9	321.2
60°	186.8	192.9	200.1	207.3	214.5	224.7	241.2	255.5	268.9	276.1	286.3
62.5°	155.0	167.3	173.4	181.6	187.8	197.0	209.4	225.8	235.0	244.2	252.5
65°	139.6	140.6	141.6	149.8	161.1	170.4	181.6	194.0	208.3	214.5	220.6
67.5°	124.2	125.2	127.3	128.3	132.4	142.6	155.0	168.3	179.6	183.7	189.9
70°	108.8	108.8	112.9	113.9	114.9	116.0	126.2	139.6	149.8	155.0	162.1
72.5°	92.4	93.4	95.4	96.5	98.5	100.6	103.6	110.8	123.1	128.3	136.5
75°	75.9	77.0	78.0	79.0	82.1	83.1	86.2	90.3	95.4	101.6	106.7
77.5°	60.5	60.5	61.6	63.6	65.7	66.7	69.8	71.8	73.9	77.0	81.1
80°	45.2	46.2	46.2	48.2	48.2	49.3	50.3	53.4	55.4	57.5	59.5
82.5°	30.8	32.8	32.8	32.8	33.9	34.9	35.9	35.9	38.0	39.0	42.1
85°	18.5	19.5	19.5	19.5	18.5	20.5	20.5	21.6	21.6	21.6	22.6
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.2	9.2
90°	7.9	7.6	7.2	6.9	6.5	5.9	5.3	4.8	4.2	3.9	3.5
92.5°	8.4	8.3	8.1	8.0	7.8	7.6	7.4	7.1	6.9	6.8	6.9
95°	14.1	13.8	13.4	13.1	12.7	12.2	11.7	11.2	10.7	10.4	11.6
97.5°	17.5	17.3	17.0	16.8	16.6	15.4	14.3	13.1	12.0	11.4	14.4
100°	20.8	20.2	19.7	19.1	18.5	17.3	16.1	14.8	13.6	13.0	18.0
102.5°	22.4	21.6	20.8	20.0	19.2	32.4	45.5	58.7	71.8	78.4	78.5
105°	23.0	22.2	21.4	20.6	19.8	39.6	59.3	79.1	98.8	108.7	107.6
107.5°	23.7	22.9	22.1	21.3	20.5	44.9	69.2	93.6	117.9	130.1	129.2
110°	28.0	35.2	42.5	49.7	56.9	77.8	98.7	119.6	140.5	151.0	150.2

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	40.7	71.8	103.0	134.1	165.3	166.5	167.7	169.0	170.2	170.8	170.2
115°	66.8	100.3	133.8	167.2	200.7	198.9	197.1	195.3	193.5	192.6	192.0
117.5°	177.0	187.3	197.6	208.0	218.3	217.1	215.9	214.6	213.4	212.8	212.1
120°	242.0	241.1	240.2	239.4	238.5	237.2	235.9	234.6	233.3	232.6	232.1
122.5°	259.4	259.0	258.5	258.1	257.7	256.3	254.8	253.4	251.9	251.2	250.6
125°	276.9	276.4	275.9	275.4	274.9	273.5	272.1	270.8	269.4	268.7	268.2
127.5°	293.7	293.0	292.3	291.6	290.9	289.8	288.7	287.6	286.5	286.0	285.5
130°	309.3	308.5	307.8	307.0	306.2	305.4	304.6	303.8	303.0	302.6	302.0
132.5°	324.1	323.4	322.8	322.1	321.5	320.7	319.9	319.1	318.3	317.9	317.4
135°	338.3	337.6	336.9	336.1	335.4	334.8	334.1	333.5	332.8	332.5	331.9
137.5°	351.6	350.9	350.2	349.5	348.8	348.1	347.3	346.6	345.9	345.5	345.1
140°	364.4	363.7	363.1	362.4	361.8	361.0	360.2	359.4	358.6	358.2	357.9
142.5°	376.1	375.5	375.0	374.4	373.8	372.9	371.9	371.0	370.1	369.6	369.3
145°	386.9	386.4	385.9	385.4	384.9	383.7	382.5	381.2	380.0	379.4	379.4
147.5°	396.4	396.1	395.7	395.4	395.0	393.8	392.6	391.3	390.1	389.5	389.6
150°	405.5	405.1	404.6	404.2	403.8	402.6	401.5	400.3	399.2	398.6	398.8
152.5°	413.7	413.2	412.8	412.3	411.9	410.8	409.7	408.6	407.5	407.0	407.3
155°	420.8	420.4	419.9	419.5	419.1	418.2	417.4	416.5	415.6	415.2	415.5
157.5°	427.2	426.7	426.2	425.7	425.2	424.6	423.9	423.3	422.6	422.3	422.6
160°	432.5	432.1	431.6	431.2	430.8	430.4	429.9	429.5	429.0	428.8	429.0
162.5°	437.7	437.2	436.7	436.2	435.7	435.3	434.9	434.6	434.2	434.0	434.2
165°	441.6	441.1	440.6	440.1	439.6	439.4	439.2	438.9	438.7	438.6	438.8
167.5°	445.1	444.6	444.1	443.6	443.1	442.9	442.7	442.5	442.3	442.2	442.4
170°	447.7	447.2	446.7	446.2	445.7	445.6	445.4	445.3	445.2	445.1	445.3
172.5°	449.7	449.2	448.7	448.2	447.7	447.5	447.4	447.2	447.1	447.0	447.2
175°	451.0	450.5	450.0	449.5	449.0	448.8	448.7	448.5	448.4	448.3	448.6
177.5°	451.3	450.8	450.3	449.8	449.3	449.2	449.2	449.1	449.0	449.0	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1476.7	1476.7	1476.7	1476.7
2.5°	1450.1	1447.0	1465.5	1486.0
5°	1420.3	1425.4	1449.0	1477.8
7.5°	1389.5	1400.8	1428.5	1466.5
10°	1346.4	1366.9	1409.0	1448.0
12.5°	1304.3	1332.0	1372.1	1418.3
15°	1257.1	1287.9	1337.2	1392.6
17.5°	1204.8	1239.7	1297.2	1357.7
20°	1149.4	1195.6	1256.1	1321.8
22.5°	1087.8	1143.2	1205.8	1278.7
25°	1028.3	1088.8	1151.4	1235.6
27.5°	969.8	1029.3	1099.1	1184.3
30°	911.3	965.7	1040.6	1131.9
32.5°	848.7	905.1	984.2	1077.5
35°	791.2	847.7	921.6	1013.9
37.5°	729.6	790.2	861.0	956.4
40°	657.8	728.6	797.4	888.7
42.5°	598.3	673.2	739.9	826.1
45°	551.1	621.9	677.3	761.5
47.5°	507.0	564.4	620.9	698.9
50°	464.9	509.0	567.5	637.3
52.5°	421.8	459.8	510.0	575.7
55°	382.8	418.7	463.9	514.1
57.5°	346.9	372.5	417.7	462.8
60°	306.8	333.5	368.4	406.4
62.5°	273.0	293.5	326.3	358.2
65°	237.1	256.6	281.2	310.9
67.5°	204.2	221.7	241.2	264.8
70°	174.5	187.8	202.2	222.7
72.5°	142.6	157.0	170.4	186.8
75°	117.0	123.1	134.4	145.7
77.5°	90.3	98.5	104.7	113.9
80°	64.7	71.8	73.9	81.1
82.5°	43.1	47.2	51.3	53.4
85°	24.6	26.7	30.8	31.8
87.5°	9.2	10.3	12.3	14.4
90°	2.7	1.9	1.1	0.3
92.5°	7.2	7.5	7.8	8.1
95°	14.0	16.3	18.7	21.1
97.5°	20.3	26.2	32.2	38.1
100°	27.9	37.8	47.7	57.6
102.5°	78.6	78.8	78.9	79.1
105°	105.4	103.3	101.1	98.9
107.5°	127.4	125.6	123.8	122.0
110°	148.7	147.2	145.6	144.1

TEST NUMBER: P1008455

CATALOG NUMBER: S122RDIP-B675D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	168.9	167.6	166.3	165.0
115°	190.8	189.5	188.3	187.1
117.5°	210.6	209.2	207.7	206.3
120°	231.0	229.9	228.9	227.8
122.5°	249.5	248.3	247.2	246.0
125°	267.3	266.4	265.4	264.5
127.5°	284.5	283.4	282.4	281.4
130°	300.9	299.7	298.6	297.4
132.5°	316.5	315.5	314.6	313.6
135°	330.8	329.6	328.5	327.3
137.5°	344.2	343.3	342.5	341.6
140°	357.3	356.8	356.2	355.6
142.5°	368.8	368.3	367.8	367.3
145°	379.5	379.6	379.6	379.7
147.5°	389.8	390.0	390.2	390.4
150°	399.3	399.8	400.3	400.8
152.5°	407.9	408.4	409.0	409.6
155°	416.2	416.8	417.5	418.1
157.5°	423.2	423.7	424.3	424.9
160°	429.5	429.9	430.4	430.8
162.5°	434.7	435.1	435.6	436.0
165°	439.2	439.7	440.1	440.5
167.5°	442.8	443.3	443.7	444.1
170°	445.7	446.2	446.6	447.0
172.5°	447.7	448.1	448.6	449.0
175°	449.1	449.6	450.1	450.6
177.5°	449.8	450.3	450.8	451.3
180°	449.6	449.6	449.6	449.6

(END OF REPORT)