

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008777

Luminaire Tested: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008777
REPORT IS A COMBINATION OF REPORTS P983844 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D1080UB30-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5477.0 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32	23		
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	28	27	20		
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	17		
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	22	21	20	15		
4	70	60	53	47	62	54	47	43	42	37	34	30	28	25	20	19	17	13		
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15	11		
6	59	48	40	35	52	43	36	32	33	29	25	25	22	19	17	15	13	10		
7	55	43	36	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9		
8	51	39	32	27	45	35	29	24	28	23	20	21	17	15	14	12	11	8		
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7		
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9105	9105	9105	9105
5°	9126	9708	9161	7724
10°	9021	10597	9077	6367
15°	8802	11178	8924	5364
20°	8664	10495	8664	4662
25°	8389	9016	8427	4169
30°	7933	7088	8085	3777
35°	7532	4901	7657	3455
40°	7070	3701	7148	3199
45°	6497	3040	6604	2922
50°	6005	2670	6017	2675
55°	5441	2274	5478	2407
60°	4843	1899	4910	2101
65°	4305	1545	4383	1794
70°	3772	1212	3867	1447
75°	3166	880	3289	1049
80°	2467	557	2651	622
85°	1624	280	1752	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9412 cd/sqm

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	1.0
10°-20°	159.5	2.9
20°-30°	231.4	4.2
30°-40°	244.0	4.5
40°-50°	215.9	3.9
50°-60°	172.4	3.1
60°-70°	117.1	2.1
70°-80°	59.9	1.1
80°-90°	18.0	0.3
90°-100°	235.3	4.3
100°-110°	828.8	15.1
110°-120°	870.4	15.9
120°-130°	716.1	13.1
130°-140°	575.3	10.5
140°-150°	434.5	7.9
150°-160°	305.5	5.6
160°-170°	179.8	3.3
170°-180°	58.5	1.1
0°-30°	445.7	8.1
0°-40°	689.6	12.6
0°-60°	1077.9	19.7
0°-90°	1272.9	23.2
90°-120°	1934.5	35.3
90°-150°	3660.3	66.8
90°-180°	4204.0	76.8
0°-180°	5477.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	575	575	575	575	575	
5°	576	642	578	511	576	55
15°	541	790	548	379	541	153
25°	486	658	488	304	486	222
35°	397	358	403	252	397	248
45°	298	216	302	207	298	231
55°	204	152	206	160	204	182
65°	121	93	123	108	121	120
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	38	1	38	1	3
95°	41	132	41	132	41	42
105°	142	1308	142	1308	142	150
115°	250	1722	250	1722	250	248
125°	348	1397	348	1397	348	310
135°	409	1158	409	1158	409	316
145°	467	924	467	924	467	293
155°	531	777	531	777	531	244
165°	578	682	578	682	578	163
175°	602	614	602	614	602	57
180°	604	604	604	604	604	

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	578.3	579.6	581.8	582.2	586.7	590.2	594.2	594.2	595.5	595.1	591.5
5°	575.6	579.6	585.3	590.2	598.2	601.7	607.0	611.0	614.5	617.2	616.7
7.5°	571.2	578.3	586.7	595.9	606.6	612.7	620.3	627.3	632.2	636.6	639.7
10°	563.7	575.6	587.1	599.5	613.2	621.6	630.4	639.7	647.2	655.6	663.6
12.5°	553.5	570.7	584.9	601.3	618.1	627.3	641.5	648.6	663.1	684.4	690.1
15°	540.7	564.1	577.4	598.2	620.3	627.8	647.2	658.7	688.8	702.1	718.0
17.5°	528.7	554.8	572.5	596.4	618.1	632.6	651.7	675.1	700.3	719.3	737.0
20°	519.0	544.2	565.4	592.0	619.4	637.9	657.8	686.1	713.5	733.0	746.7
22.5°	496.9	529.2	553.9	583.6	616.7	642.4	661.4	692.3	721.9	733.9	745.8
25°	485.9	513.7	542.5	576.1	615.0	645.5	661.8	696.3	722.4	726.8	729.5
27.5°	465.5	496.9	530.5	569.0	614.5	640.2	660.9	692.3	713.1	710.0	702.1
30°	440.3	478.8	515.9	557.5	608.3	636.2	655.6	684.4	695.0	679.1	664.9
32.5°	421.8	458.0	499.1	547.3	601.3	627.8	646.8	669.3	671.5	642.8	618.9
35°	396.6	436.8	483.2	534.1	589.3	613.2	630.9	644.6	634.0	593.7	565.4
37.5°	374.0	413.8	463.3	515.0	573.0	596.4	610.5	612.7	586.7	551.3	509.7
40°	349.3	390.4	442.1	496.5	554.8	575.2	584.0	577.4	539.8	498.7	450.5
42.5°	324.5	365.2	420.9	476.6	531.8	549.1	552.6	534.5	488.5	440.3	384.6
45°	297.5	340.0	395.7	451.8	505.3	515.0	515.5	489.4	435.0	384.6	332.9
47.5°	275.4	314.8	370.0	426.2	471.3	477.9	475.3	445.2	386.0	329.4	284.3
50°	251.1	288.7	343.5	398.8	437.2	439.0	432.4	389.5	331.6	279.8	244.0
52.5°	225.0	263.0	313.4	366.5	401.0	398.3	385.5	339.5	285.2	242.3	214.9
55°	204.2	237.8	285.2	336.9	361.2	353.7	339.5	292.7	249.8	213.5	189.7
57.5°	181.3	210.9	257.3	302.4	316.5	309.5	295.3	251.6	211.8	184.4	168.4
60°	159.6	186.6	227.2	264.8	275.9	268.4	252.0	212.6	183.9	160.9	149.0
62.5°	139.7	163.1	197.2	231.7	236.1	228.6	214.4	182.6	157.8	139.7	130.9
65°	121.1	143.2	170.6	196.7	200.7	192.8	178.2	155.2	134.4	122.9	114.5
67.5°	103.0	120.7	145.0	164.0	166.2	158.7	146.8	128.2	115.4	103.0	96.8
70°	87.1	100.4	119.4	134.8	135.7	128.7	122.5	105.7	95.9	87.1	82.2
72.5°	71.6	80.9	95.5	107.0	107.4	103.0	97.3	86.7	78.3	72.1	67.2
75°	56.6	64.5	73.4	83.6	83.1	79.6	75.2	68.5	61.5	57.5	55.3
77.5°	43.3	48.2	55.3	61.9	61.9	60.1	57.5	52.6	48.2	44.2	42.0
80°	30.9	34.0	39.8	42.0	42.9	42.4	40.2	36.7	34.9	31.8	30.9
82.5°	19.9	22.1	24.8	27.0	28.3	27.4	27.0	25.2	22.5	21.7	20.8
85°	11.5	12.4	13.7	15.0	15.5	15.0	15.9	14.6	13.3	13.3	12.8
87.5°	4.9	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	1.2	4.6	9.3	11.6	13.9	15.6	17.4	23.2	31.3	38.3	39.5
92.5°	17.4	24.4	33.7	39.5	48.8	55.2	61.5	92.9	137.0	176.5	178.8
95°	40.6	45.3	56.9	67.3	85.9	99.8	113.8	167.2	268.2	402.8	455.1
97.5°	60.4	67.3	80.1	95.2	116.1	131.8	147.4	215.9	356.4	573.5	741.8
100°	89.4	92.9	103.3	121.9	145.1	161.4	177.6	239.2	380.8	631.6	917.1
102.5°	116.1	118.4	128.9	147.4	171.8	188.0	204.3	260.1	382.0	609.5	923.0
105°	141.6	146.3	154.4	171.8	197.4	213.6	229.9	284.4	387.8	579.3	860.3
107.5°	169.5	173.0	181.1	197.4	222.9	239.2	255.4	308.8	400.5	563.1	802.2
110°	197.4	202.0	209.0	224.1	248.4	265.2	282.1	333.2	416.8	558.4	762.7



TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	222.9	227.5	235.7	249.6	272.8	290.2	307.7	356.4	434.2	559.6	737.2
115°	249.6	255.4	262.4	276.3	299.5	315.2	330.9	380.8	451.6	564.2	719.8
117.5°	277.5	282.1	289.1	301.8	323.9	340.2	356.4	402.8	470.2	571.2	710.5
120°	303.0	307.7	314.6	325.1	348.3	364.6	380.8	426.1	488.8	578.2	702.4
122.5°	327.4	330.9	337.8	349.4	372.7	389.5	406.3	448.1	505.0	586.3	697.7
125°	348.3	351.8	358.7	372.7	395.9	412.2	428.4	470.2	522.4	594.4	691.9
127.5°	365.7	370.3	379.6	394.7	416.8	433.6	450.4	491.1	538.7	602.5	688.4
130°	380.8	385.4	397.0	413.3	436.5	452.8	469.0	509.7	553.8	611.8	686.1
132.5°	394.7	400.5	413.3	430.7	455.1	471.4	487.6	525.9	568.9	621.1	685.0
135°	408.7	413.3	427.2	444.6	471.3	487.6	503.8	541.0	581.6	628.1	683.8
137.5°	421.4	427.2	441.2	459.7	486.4	501.5	516.6	553.8	592.1	635.0	683.8
140°	436.5	441.2	455.1	473.7	499.2	514.3	529.4	564.2	600.2	639.7	682.6
142.5°	451.6	455.1	467.9	486.4	510.8	524.8	538.7	572.3	607.2	643.2	682.6
145°	466.7	471.3	483.0	500.4	523.6	536.4	549.1	580.5	613.0	645.5	680.3
147.5°	483.0	486.4	498.0	514.3	534.0	545.6	557.3	587.4	616.5	646.6	676.8
150°	499.2	502.7	512.0	527.1	544.5	555.0	565.4	592.1	618.8	645.5	673.3
152.5°	515.5	516.6	525.9	538.7	554.9	564.2	573.5	596.7	619.9	643.2	667.5
155°	530.6	531.7	538.7	551.4	564.2	572.9	581.6	601.4	621.1	640.8	660.6
157.5°	543.3	544.5	550.3	561.9	572.3	579.8	587.4	604.9	621.1	636.2	653.6
160°	556.1	557.3	561.9	571.2	580.5	586.8	593.2	607.2	621.1	632.7	646.6
162.5°	568.9	567.7	572.3	579.3	587.4	592.0	596.7	608.3	619.9	629.2	640.8
165°	578.2	577.0	579.3	586.3	592.1	595.6	599.0	609.5	617.6	624.6	632.7
167.5°	586.3	585.1	587.4	592.1	596.7	599.0	601.4	609.5	616.5	619.9	625.7
170°	594.4	592.1	593.2	596.7	599.0	600.8	602.5	608.3	614.1	616.5	619.9
172.5°	599.0	597.9	596.7	600.2	601.4	602.6	603.7	607.2	610.7	611.8	613.0
175°	602.5	601.4	600.2	602.5	602.5	603.1	603.7	606.0	608.3	607.2	608.3
177.5°	604.9	602.5	601.4	603.7	603.7	603.7	603.7	604.9	607.2	604.9	603.7
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	597.7	598.2	599.0	603.5	605.7	606.1	604.3	608.3	609.7	608.3	607.4
5°	626.0	628.7	634.0	639.7	639.3	639.7	642.4	645.0	645.9	642.4	643.7
7.5°	650.8	656.1	661.8	670.7	670.7	675.1	676.9	679.1	684.4	681.7	680.8
10°	679.1	686.1	696.7	710.9	711.3	715.8	720.2	727.3	729.5	727.7	728.6
12.5°	714.4	728.1	729.0	744.5	751.6	752.5	759.5	758.2	762.6	762.6	770.1
15°	729.9	751.1	763.1	778.1	782.5	777.2	783.0	789.1	789.6	789.6	789.1
17.5°	757.8	766.2	778.1	786.1	787.8	787.8	788.3	790.9	789.1	785.6	788.3
20°	763.5	767.0	771.5	770.6	771.5	767.0	762.6	758.2	758.6	756.4	763.1
22.5°	752.9	752.0	741.8	735.2	735.2	726.4	718.0	714.0	710.0	711.3	713.5
25°	726.4	712.7	700.3	690.6	688.3	674.2	662.7	659.2	652.5	657.8	658.7
27.5°	683.9	668.5	648.6	640.2	628.7	622.9	615.0	604.3	590.6	598.6	597.3
30°	638.4	615.4	599.0	578.7	560.6	559.3	544.2	526.5	519.5	519.5	523.4
32.5°	587.5	557.0	533.2	504.4	486.8	479.2	461.1	443.4	447.4	434.1	439.0
35°	528.3	488.1	458.0	430.2	416.9	408.1	384.6	374.9	364.3	358.1	369.6
37.5°	471.7	425.3	386.8	356.3	351.5	335.6	319.6	313.4	307.3	309.9	309.5
40°	402.8	361.6	327.2	303.3	294.9	287.4	276.8	269.2	265.3	267.5	267.9
42.5°	340.4	305.9	280.3	263.5	256.4	251.1	245.8	239.6	238.3	238.3	240.1
45°	292.2	263.9	246.7	233.0	229.0	225.0	221.0	218.4	217.5	215.7	217.1
47.5°	253.8	231.2	220.6	210.4	206.0	205.1	201.6	200.3	198.5	198.1	198.5
50°	221.5	207.3	197.6	191.9	188.8	187.4	185.7	183.0	182.1	184.4	183.5
52.5°	198.9	185.7	180.4	174.6	172.9	171.1	168.4	168.9	168.4	167.6	167.6
55°	176.4	168.0	162.7	158.3	157.8	156.1	153.9	153.0	152.5	151.6	153.0
57.5°	158.3	151.6	146.8	142.8	141.0	141.0	138.8	137.1	137.1	136.6	137.1
60°	140.1	133.5	130.4	126.4	125.1	124.7	123.3	122.5	121.1	121.1	121.1
62.5°	123.3	118.0	114.5	111.0	111.4	109.2	107.4	106.5	106.5	107.0	107.0
65°	107.4	103.9	99.5	96.4	95.5	95.1	94.2	93.7	92.4	93.3	93.3
67.5°	92.8	88.0	85.3	84.0	82.7	82.2	81.3	80.5	80.0	79.6	80.5
70°	78.3	74.3	72.1	71.2	69.9	69.4	69.0	67.6	68.1	68.5	69.0
72.5°	65.0	61.5	61.0	58.4	58.4	58.4	56.6	57.5	57.0	56.1	57.0
75°	51.3	49.5	48.6	47.3	47.7	47.3	46.9	45.5	45.5	46.0	46.4
77.5°	40.7	38.9	38.5	37.1	36.3	37.1	36.3	35.8	35.8	36.3	36.3
80°	30.1	29.2	27.9	27.9	27.9	27.4	27.4	27.4	27.0	26.5	27.0
82.5°	19.9	19.9	19.5	19.0	19.5	18.6	19.0	19.0	19.0	19.0	19.0
85°	12.8	12.4	12.4	11.9	11.9	11.9	12.4	11.5	11.5	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	38.3	37.2	34.8	37.2	37.8	38.3	38.3	38.3	38.3	38.3	38.3
92.5°	149.8	117.3	99.8	87.1	82.4	77.8	76.6	72.0	73.1	70.8	73.1
95°	398.2	304.2	233.3	184.6	171.8	159.0	144.0	134.7	131.2	132.3	131.2
97.5°	747.6	622.3	496.9	379.6	344.8	310.0	264.7	241.5	228.7	221.7	228.7
100°	1084.3	1059.9	916.0	756.9	686.7	616.5	520.1	470.2	436.5	415.6	436.5
102.5°	1209.7	1346.7	1342.1	1236.4	1161.0	1085.5	978.7	884.6	840.5	810.3	840.5
105°	1169.1	1410.5	1541.7	1556.8	1537.6	1518.5	1446.5	1374.6	1324.6	1308.4	1324.6
107.5°	1083.2	1342.1	1537.1	1650.9	1674.1	1697.3	1696.1	1685.7	1670.6	1643.9	1670.6
110°	1003.1	1248.0	1455.8	1604.4	1652.0	1699.6	1749.5	1771.6	1782.0	1780.9	1782.0

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	947.3	1162.1	1359.5	1520.8	1577.1	1633.4	1707.7	1748.4	1770.4	1778.6	1770.4
115°	903.2	1094.8	1273.6	1425.6	1485.4	1545.2	1627.6	1681.0	1711.2	1721.7	1711.2
117.5°	873.0	1039.0	1199.3	1340.9	1397.8	1454.7	1539.4	1596.3	1627.6	1635.8	1627.6
120°	849.8	999.6	1143.5	1266.6	1319.4	1372.2	1453.5	1508.1	1541.7	1553.3	1541.7
122.5°	830.1	968.2	1097.1	1212.0	1258.4	1304.9	1375.7	1429.1	1458.1	1467.4	1458.1
125°	811.5	938.0	1057.6	1159.8	1203.4	1246.9	1314.2	1358.3	1387.3	1396.6	1387.3
127.5°	794.1	907.9	1018.1	1115.7	1156.3	1196.9	1256.1	1297.9	1323.5	1330.4	1323.5
130°	776.7	878.8	978.7	1070.4	1108.7	1147.0	1203.9	1243.4	1266.6	1275.9	1266.6
132.5°	762.7	851.0	941.5	1024.0	1059.4	1094.8	1150.5	1190.0	1210.9	1219.0	1210.9
135°	750.0	825.4	902.1	978.7	1011.2	1043.7	1093.6	1131.9	1152.8	1157.5	1152.8
137.5°	740.7	804.5	870.7	933.4	962.4	991.4	1039.0	1072.7	1091.3	1098.3	1091.3
140°	732.6	784.8	840.5	893.9	919.4	945.0	982.2	1012.3	1029.8	1036.7	1029.8
142.5°	724.4	768.5	813.8	857.9	878.2	898.6	933.4	960.1	975.2	975.2	975.2
145°	717.5	753.5	791.8	827.8	844.6	861.4	889.3	909.0	920.6	924.1	920.6
147.5°	710.5	741.8	773.2	802.2	815.0	827.8	852.1	868.4	876.5	878.8	876.5
150°	701.2	729.1	754.6	779.0	789.4	799.9	817.3	831.2	838.2	839.4	838.2
152.5°	693.1	716.3	739.5	759.3	768.0	776.7	789.4	801.1	805.7	805.7	805.7
155°	682.6	704.7	723.3	740.7	747.1	753.5	766.2	774.3	779.0	776.7	779.0
157.5°	673.3	690.8	707.0	722.1	727.4	732.6	741.8	748.8	751.1	751.1	751.1
160°	662.9	678.0	690.8	703.5	707.6	711.7	719.8	725.6	726.8	726.8	726.8
162.5°	653.6	665.2	675.7	686.1	689.0	691.9	700.0	703.5	704.7	703.5	704.7
165°	643.2	652.5	660.6	668.7	671.0	673.3	678.0	682.6	682.6	681.5	682.6
167.5°	632.7	639.7	646.6	652.5	654.8	657.1	659.4	661.7	661.7	660.6	661.7
170°	624.6	630.4	633.9	638.5	639.6	640.8	642.0	645.5	644.3	642.0	644.3
172.5°	616.5	619.9	622.3	625.7	626.3	626.9	628.1	629.2	628.1	626.9	628.1
175°	609.5	613.0	614.1	615.3	615.9	616.5	616.5	617.6	616.5	614.1	616.5
177.5°	604.9	607.2	607.2	608.3	608.3	608.3	608.3	608.3	607.2	604.9	607.2
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	609.7	606.6	603.9	604.3	606.6	604.8	600.4	594.6	592.4	589.8	592.4
5°	646.3	643.7	638.4	638.8	637.5	635.7	628.7	619.8	619.8	612.7	611.9
7.5°	682.6	678.6	675.1	674.2	669.3	665.8	659.6	647.2	642.4	634.0	629.1
10°	723.3	720.2	716.2	711.3	708.7	702.5	692.3	674.2	665.4	653.9	645.5
12.5°	764.4	763.9	755.1	745.4	744.9	735.2	728.1	703.8	691.9	676.4	656.5
15°	790.5	788.3	783.4	778.5	779.9	769.3	753.3	724.6	716.6	698.1	676.9
17.5°	790.0	790.0	788.7	787.8	786.5	783.4	774.6	755.5	742.7	719.3	699.4
20°	764.8	770.6	771.9	771.5	775.9	778.1	777.7	765.7	755.5	734.8	714.4
22.5°	714.4	727.7	733.4	737.0	746.3	751.1	762.6	758.2	755.5	740.1	722.8
25°	667.6	672.0	689.2	690.1	702.9	714.9	726.4	733.9	743.6	737.9	723.3
27.5°	607.0	617.2	629.5	638.8	641.5	665.8	684.8	699.0	721.1	722.8	718.0
30°	538.5	543.3	563.7	576.1	590.2	607.9	635.3	659.6	679.5	697.6	703.8
32.5°	454.9	474.8	486.8	501.8	514.2	545.5	579.1	610.5	633.5	664.0	677.3
35°	378.4	393.9	414.2	420.4	443.0	469.5	513.3	553.5	588.4	619.4	646.3
37.5°	315.2	327.6	349.3	359.0	372.2	406.3	443.0	492.9	534.9	573.0	606.6
40°	271.9	281.2	297.5	300.6	311.7	342.6	372.2	419.1	474.8	526.1	562.8
42.5°	242.3	246.7	257.7	261.7	268.8	289.6	316.1	360.3	412.0	465.1	516.8
45°	221.0	224.1	230.8	234.3	243.2	252.4	274.1	309.5	350.1	403.6	459.3
47.5°	202.0	206.0	208.7	210.9	215.7	225.9	240.1	266.1	305.0	354.1	408.1
50°	186.1	187.4	192.3	192.8	195.8	202.5	215.7	231.7	262.6	302.4	354.6
52.5°	170.2	171.5	174.6	177.7	179.0	184.4	193.2	206.5	229.4	260.8	307.3
55°	154.3	156.1	159.2	161.4	162.7	167.1	172.4	185.2	203.4	225.5	263.5
57.5°	138.4	142.4	143.2	144.6	146.8	151.6	156.5	164.0	178.2	198.5	226.4
60°	123.3	124.7	127.8	129.1	131.3	134.0	140.1	145.9	156.1	172.0	197.2
62.5°	107.9	111.0	112.3	113.6	115.4	118.5	122.5	128.7	137.5	150.3	170.2
65°	94.6	95.1	97.7	99.5	101.2	103.5	107.4	113.2	118.5	130.4	145.0
67.5°	81.8	82.7	83.6	85.3	87.5	89.7	93.3	96.4	103.0	111.0	122.5
70°	69.4	69.4	71.6	72.9	72.5	75.2	77.8	81.3	86.2	93.7	103.0
72.5°	58.4	57.9	59.7	60.1	61.0	62.8	64.5	68.1	70.7	76.5	83.6
75°	46.4	47.3	48.2	48.2	49.5	50.8	52.6	54.4	57.5	61.0	66.3
77.5°	36.7	36.7	37.6	38.0	39.3	38.9	40.7	42.4	44.7	47.7	51.7
80°	27.0	27.9	27.9	27.9	28.3	28.7	30.5	31.8	33.2	35.4	37.1
82.5°	19.0	19.0	19.9	19.9	19.9	20.8	20.8	21.2	22.1	23.4	24.8
85°	11.9	11.9	11.9	12.4	11.9	12.4	13.3	12.8	13.3	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	38.3	38.3	38.3	37.8	37.2	34.8	37.2	38.3	39.5	38.3	31.3
92.5°	72.0	76.6	77.8	82.4	87.1	99.8	117.3	149.8	178.8	176.5	137.0
95°	134.7	144.0	159.0	171.8	184.6	233.3	304.2	398.2	455.1	402.8	268.2
97.5°	241.5	264.7	310.0	344.8	379.6	496.9	622.3	747.6	741.8	573.5	356.4
100°	470.2	520.1	616.5	686.7	756.9	916.0	1059.9	1084.3	917.1	631.6	380.8
102.5°	884.6	978.7	1085.5	1161.0	1236.4	1342.1	1346.7	1209.7	923.0	609.5	382.0
105°	1374.6	1446.5	1518.5	1537.6	1556.8	1541.7	1410.5	1169.1	860.3	579.3	387.8
107.5°	1685.7	1696.1	1697.3	1674.1	1650.9	1537.1	1342.1	1083.2	802.2	563.1	400.5
110°	1771.6	1749.5	1699.6	1652.0	1604.4	1455.8	1248.0	1003.1	762.7	558.4	416.8

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1748.4	1707.7	1633.4	1577.1	1520.8	1359.5	1162.1	947.3	737.2	559.6	434.2
115°	1681.0	1627.6	1545.2	1485.4	1425.6	1273.6	1094.8	903.2	719.8	564.2	451.6
117.5°	1596.3	1539.4	1454.7	1397.8	1340.9	1199.3	1039.0	873.0	710.5	571.2	470.2
120°	1508.1	1453.5	1372.2	1319.4	1266.6	1143.5	999.6	849.8	702.4	578.2	488.8
122.5°	1429.1	1375.7	1304.9	1258.4	1212.0	1097.1	968.2	830.1	697.7	586.3	505.0
125°	1358.3	1314.2	1246.9	1203.4	1159.8	1057.6	938.0	811.5	691.9	594.4	522.4
127.5°	1297.9	1256.1	1196.9	1156.3	1115.7	1018.1	907.9	794.1	688.4	602.5	538.7
130°	1243.4	1203.9	1147.0	1108.7	1070.4	978.7	878.8	776.7	686.1	611.8	553.8
132.5°	1190.0	1150.5	1094.8	1059.4	1024.0	941.5	851.0	762.7	685.0	621.1	568.9
135°	1131.9	1093.6	1043.7	1011.2	978.7	902.1	825.4	750.0	683.8	628.1	581.6
137.5°	1072.7	1039.0	991.4	962.4	933.4	870.7	804.5	740.7	683.8	635.0	592.1
140°	1012.3	982.2	945.0	919.4	893.9	840.5	784.8	732.6	682.6	639.7	600.2
142.5°	960.1	933.4	898.6	878.2	857.9	813.8	768.5	724.4	682.6	643.2	607.2
145°	909.0	889.3	861.4	844.6	827.8	791.8	753.5	717.5	680.3	645.5	613.0
147.5°	868.4	852.1	827.8	815.0	802.2	773.2	741.8	710.5	676.8	646.6	616.5
150°	831.2	817.3	799.9	789.4	779.0	754.6	729.1	701.2	673.3	645.5	618.8
152.5°	801.1	789.4	776.7	768.0	759.3	739.5	716.3	693.1	667.5	643.2	619.9
155°	774.3	766.2	753.5	747.1	740.7	723.3	704.7	682.6	660.6	640.8	621.1
157.5°	748.8	741.8	732.6	727.4	722.1	707.0	690.8	673.3	653.6	636.2	621.1
160°	725.6	719.8	711.7	707.6	703.5	690.8	678.0	662.9	646.6	632.7	621.1
162.5°	703.5	700.0	691.9	689.0	686.1	675.7	665.2	653.6	640.8	629.2	619.9
165°	682.6	678.0	673.3	671.0	668.7	660.6	652.5	643.2	632.7	624.6	617.6
167.5°	661.7	659.4	657.1	654.8	652.5	646.6	639.7	632.7	625.7	619.9	616.5
170°	645.5	642.0	640.8	639.6	638.5	633.9	630.4	624.6	619.9	616.5	614.1
172.5°	629.2	628.1	626.9	626.3	625.7	622.3	619.9	616.5	613.0	611.8	610.7
175°	617.6	616.5	616.5	615.9	615.3	614.1	613.0	609.5	608.3	607.2	608.3
177.5°	608.3	608.3	608.3	608.3	608.3	607.2	607.2	604.9	603.7	604.9	607.2
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	590.2	588.0	586.7	587.5	584.9	578.3	578.3	580.5	577.8	575.2	571.2
5°	606.6	602.1	599.5	599.0	592.9	582.2	580.0	577.8	572.1	565.9	559.3
7.5°	622.5	614.5	610.1	607.0	598.2	584.5	578.7	573.8	564.6	555.3	546.9
10°	635.7	624.2	618.9	614.1	602.6	585.3	576.1	567.2	555.3	543.3	532.7
12.5°	646.3	633.1	626.5	619.4	605.2	582.7	571.2	557.0	545.1	529.2	518.6
15°	664.0	636.6	630.4	623.8	609.2	578.3	564.1	548.2	531.8	510.6	499.1
17.5°	678.2	641.5	641.0	626.9	607.9	576.5	554.8	534.1	516.4	495.2	477.0
20°	686.6	649.0	641.9	627.3	603.5	564.6	542.0	519.0	500.0	474.4	456.2
22.5°	693.7	659.6	641.0	623.4	594.2	560.6	527.4	505.8	479.7	451.8	434.6
25°	696.3	661.8	642.4	622.0	587.5	549.1	511.5	488.1	458.9	433.7	410.3
27.5°	696.7	661.4	637.5	616.3	578.3	534.1	495.6	470.8	438.6	409.4	386.0
30°	692.3	656.5	634.9	611.9	569.4	520.3	476.1	448.7	414.2	385.1	360.8
32.5°	679.1	646.8	629.1	603.9	557.9	501.3	457.6	427.1	390.8	362.1	338.6
35°	657.0	634.9	615.4	592.0	542.9	483.7	439.0	403.2	366.5	339.1	317.0
37.5°	629.5	617.6	599.5	576.5	525.7	467.7	418.2	378.4	341.7	315.2	293.6
40°	592.4	595.5	577.8	557.0	505.3	446.1	391.3	353.2	318.8	294.0	272.8
42.5°	552.2	565.0	554.8	534.9	482.8	422.2	371.4	329.4	295.8	270.1	252.4
45°	508.9	531.0	524.8	510.2	459.3	397.0	343.1	302.4	272.8	248.0	232.5
47.5°	461.6	492.9	492.9	482.3	433.3	371.8	318.8	277.2	248.0	230.3	215.3
50°	413.4	448.7	454.5	447.4	404.1	343.1	289.1	251.6	226.4	209.1	198.1
52.5°	363.0	404.1	414.7	411.2	373.1	315.7	264.8	228.1	205.1	190.1	180.4
55°	314.8	362.5	374.0	375.3	340.0	285.6	237.8	205.6	183.5	173.3	164.9
57.5°	269.2	315.2	328.0	330.2	306.4	258.2	212.6	184.4	164.5	156.1	149.4
60°	230.3	268.8	285.6	290.5	269.7	226.4	189.2	161.8	146.8	138.8	132.6
62.5°	198.5	229.4	247.1	248.5	239.2	198.5	164.9	141.9	129.1	122.0	118.9
65°	167.6	195.4	206.0	211.3	203.8	172.0	142.4	123.3	113.2	107.0	103.9
67.5°	142.8	160.5	169.3	176.4	168.9	145.0	121.1	105.7	98.1	92.0	90.2
70°	117.2	131.7	138.4	145.5	138.8	120.7	103.5	89.3	82.7	77.8	75.6
72.5°	93.7	105.2	111.4	115.8	111.9	96.8	82.7	72.9	68.1	64.5	63.2
75°	74.3	82.2	85.8	88.9	87.1	75.6	66.8	58.8	54.4	51.3	50.4
77.5°	56.6	62.3	66.3	67.2	65.0	57.5	50.0	45.1	41.6	39.8	38.9
80°	40.2	43.8	46.0	47.3	45.1	42.0	36.7	33.2	30.1	27.9	27.4
82.5°	27.0	28.7	30.5	30.1	29.2	26.5	23.4	21.7	20.3	18.6	18.6
85°	15.5	15.9	16.8	17.2	16.8	15.0	13.3	12.4	11.5	10.2	10.2
87.5°	6.6	7.1	7.1	7.5	6.6	6.6	5.7	4.9	4.9	4.4	4.0
90°	23.2	17.4	15.6	13.9	11.6	9.3	4.6	1.2	4.6	9.3	11.6
92.5°	92.9	61.5	55.2	48.8	39.5	33.7	24.4	17.4	24.4	33.7	39.5
95°	167.2	113.8	99.8	85.9	67.3	56.9	45.3	40.6	45.3	56.9	67.3
97.5°	215.9	147.4	131.8	116.1	95.2	80.1	67.3	60.4	67.3	80.1	95.2
100°	239.2	177.6	161.4	145.1	121.9	103.3	92.9	89.4	92.9	103.3	121.9
102.5°	260.1	204.3	188.0	171.8	147.4	128.9	118.4	116.1	118.4	128.9	147.4
105°	284.4	229.9	213.6	197.4	171.8	154.4	146.3	141.6	146.3	154.4	171.8
107.5°	308.8	255.4	239.2	222.9	197.4	181.1	173.0	169.5	173.0	181.1	197.4
110°	333.2	282.1	265.2	248.4	224.1	209.0	202.0	197.4	202.0	209.0	224.1

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	356.4	307.7	290.2	272.8	249.6	235.7	227.5	222.9	227.5	235.7	249.6
115°	380.8	330.9	315.2	299.5	276.3	262.4	255.4	249.6	255.4	262.4	276.3
117.5°	402.8	356.4	340.2	323.9	301.8	289.1	282.1	277.5	282.1	289.1	301.8
120°	426.1	380.8	364.6	348.3	325.1	314.6	307.7	303.0	307.7	314.6	325.1
122.5°	448.1	406.3	389.5	372.7	349.4	337.8	330.9	327.4	330.9	337.8	349.4
125°	470.2	428.4	412.2	395.9	372.7	358.7	351.8	348.3	351.8	358.7	372.7
127.5°	491.1	450.4	433.6	416.8	394.7	379.6	370.3	365.7	370.3	379.6	394.7
130°	509.7	469.0	452.8	436.5	413.3	397.0	385.4	380.8	385.4	397.0	413.3
132.5°	525.9	487.6	471.4	455.1	430.7	413.3	400.5	394.7	400.5	413.3	430.7
135°	541.0	503.8	487.6	471.3	444.6	427.2	413.3	408.7	413.3	427.2	444.6
137.5°	553.8	516.6	501.5	486.4	459.7	441.2	427.2	421.4	427.2	441.2	459.7
140°	564.2	529.4	514.3	499.2	473.7	455.1	441.2	436.5	441.2	455.1	473.7
142.5°	572.3	538.7	524.8	510.8	486.4	467.9	455.1	451.6	455.1	467.9	486.4
145°	580.5	549.1	536.4	523.6	500.4	483.0	471.3	466.7	471.3	483.0	500.4
147.5°	587.4	557.3	545.6	534.0	514.3	498.0	486.4	483.0	486.4	498.0	514.3
150°	592.1	565.4	555.0	544.5	527.1	512.0	502.7	499.2	502.7	512.0	527.1
152.5°	596.7	573.5	564.2	554.9	538.7	525.9	516.6	515.5	516.6	525.9	538.7
155°	601.4	581.6	572.9	564.2	551.4	538.7	531.7	530.6	531.7	538.7	551.4
157.5°	604.9	587.4	579.8	572.3	561.9	550.3	544.5	543.3	544.5	550.3	561.9
160°	607.2	593.2	586.8	580.5	571.2	561.9	557.3	556.1	557.3	561.9	571.2
162.5°	608.3	596.7	592.0	587.4	579.3	572.3	567.7	568.9	567.7	572.3	579.3
165°	609.5	599.0	595.6	592.1	586.3	579.3	577.0	578.2	577.0	579.3	586.3
167.5°	609.5	601.4	599.0	596.7	592.1	587.4	585.1	586.3	585.1	587.4	592.1
170°	608.3	602.5	600.8	599.0	596.7	593.2	592.1	594.4	592.1	593.2	596.7
172.5°	607.2	603.7	602.6	601.4	600.2	596.7	597.9	599.0	597.9	596.7	600.2
175°	606.0	603.7	603.1	602.5	602.5	600.2	601.4	602.5	601.4	600.2	602.5
177.5°	604.9	603.7	603.7	603.7	603.7	601.4	602.5	604.9	602.5	601.4	603.7
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	569.0	571.2	570.7	566.3	561.5	557.5	550.0	550.9	548.2	548.6	551.3
5°	554.8	554.8	553.1	546.9	538.9	534.5	526.1	523.9	518.6	518.1	517.7
7.5°	539.8	537.6	535.4	526.5	516.8	509.7	498.2	495.6	490.3	486.8	485.0
10°	522.1	519.0	514.6	504.4	492.5	483.7	471.7	468.2	458.0	453.6	450.9
12.5°	502.7	500.9	493.8	485.4	466.0	456.2	439.0	442.5	432.4	423.5	422.2
15°	483.2	476.6	472.6	458.9	435.5	431.0	417.3	410.3	401.0	393.9	393.9
17.5°	464.2	454.0	445.2	430.6	413.4	401.0	390.8	387.3	375.8	368.7	367.4
20°	439.0	427.5	425.3	404.5	392.6	378.9	369.2	360.3	351.9	348.8	346.6
22.5°	415.1	401.9	398.3	380.6	368.7	355.0	345.3	339.1	332.9	330.7	326.7
25°	389.5	381.5	376.2	357.2	344.0	331.1	324.5	320.1	314.3	313.9	311.2
27.5°	364.7	357.2	351.9	333.8	324.1	312.1	306.8	302.0	298.9	297.5	296.2
30°	343.5	335.1	328.9	315.7	303.7	294.0	289.6	286.5	284.7	282.5	282.1
32.5°	320.1	315.2	306.8	296.6	287.4	278.1	275.4	273.2	270.6	269.7	269.2
35°	300.2	293.6	288.2	276.8	272.8	264.8	261.7	260.0	256.4	255.5	254.6
37.5°	280.7	274.5	268.8	261.7	254.2	249.8	248.0	245.4	243.6	244.0	243.2
40°	261.3	256.4	252.0	244.5	240.1	237.8	234.3	231.7	230.8	231.2	230.8
42.5°	242.3	237.8	235.2	229.4	225.0	222.8	220.6	218.0	219.3	219.3	220.6
45°	225.0	221.0	219.3	214.9	212.2	208.7	206.5	206.0	207.8	207.3	207.3
47.5°	207.3	206.0	203.8	199.8	196.3	194.1	193.6	193.6	195.4	196.3	195.8
50°	193.6	191.0	188.3	185.2	182.6	181.7	180.4	181.3	183.0	183.0	183.9
52.5°	176.4	174.6	173.7	171.1	169.3	169.3	169.3	169.8	171.1	172.4	172.0
55°	161.4	160.0	159.2	157.8	155.6	156.1	155.6	156.5	157.8	159.2	160.0
57.5°	145.5	145.0	144.1	141.9	141.9	141.5	142.8	143.2	145.5	146.3	147.7
60°	131.3	130.0	130.0	128.2	128.2	128.2	129.5	130.9	132.6	133.1	134.0
62.5°	116.3	116.3	115.8	114.5	114.5	115.8	116.3	118.0	118.9	118.9	120.3
65°	102.1	101.7	101.2	101.7	102.1	102.1	103.5	104.3	105.2	105.7	106.1
67.5°	88.0	87.5	88.4	88.0	88.9	90.6	90.2	91.5	92.8	92.8	93.3
70°	74.7	75.6	75.2	76.0	75.6	76.5	77.8	78.3	78.3	78.7	80.0
72.5°	62.3	62.3	62.3	61.9	62.3	63.2	64.1	64.5	65.4	65.9	67.2
75°	50.4	50.4	49.5	50.4	50.4	51.3	52.2	52.2	52.2	53.1	54.4
77.5°	38.0	38.5	38.0	38.9	38.9	39.3	40.2	39.8	40.7	41.1	41.6
80°	27.9	27.4	27.4	27.4	27.9	27.9	28.7	29.2	29.2	30.5	29.6
82.5°	17.7	18.1	17.7	18.1	18.1	18.6	18.1	18.6	19.0	19.9	19.5
85°	10.2	9.7	9.7	10.2	9.7	9.7	10.2	9.7	10.2	9.7	10.2
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.7	2.7	2.7	2.2
90°	13.9	15.6	17.4	23.2	31.3	38.3	39.5	38.3	37.2	34.8	37.2
92.5°	48.8	55.2	61.5	92.9	137.0	176.5	178.8	149.8	117.3	99.8	87.1
95°	85.9	99.8	113.8	167.2	268.2	402.8	455.1	398.2	304.2	233.3	184.6
97.5°	116.1	131.8	147.4	215.9	356.4	573.5	741.8	747.6	622.3	496.9	379.6
100°	145.1	161.4	177.6	239.2	380.8	631.6	917.1	1084.3	1059.9	916.0	756.9
102.5°	171.8	188.0	204.3	260.1	382.0	609.5	923.0	1209.7	1346.7	1342.1	1236.4
105°	197.4	213.6	229.9	284.4	387.8	579.3	860.3	1169.1	1410.5	1541.7	1556.8
107.5°	222.9	239.2	255.4	308.8	400.5	563.1	802.2	1083.2	1342.1	1537.1	1650.9
110°	248.4	265.2	282.1	333.2	416.8	558.4	762.7	1003.1	1248.0	1455.8	1604.4

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	272.8	290.2	307.7	356.4	434.2	559.6	737.2	947.3	1162.1	1359.5	1520.8
115°	299.5	315.2	330.9	380.8	451.6	564.2	719.8	903.2	1094.8	1273.6	1425.6
117.5°	323.9	340.2	356.4	402.8	470.2	571.2	710.5	873.0	1039.0	1199.3	1340.9
120°	348.3	364.6	380.8	426.1	488.8	578.2	702.4	849.8	999.6	1143.5	1266.6
122.5°	372.7	389.5	406.3	448.1	505.0	586.3	697.7	830.1	968.2	1097.1	1212.0
125°	395.9	412.2	428.4	470.2	522.4	594.4	691.9	811.5	938.0	1057.6	1159.8
127.5°	416.8	433.6	450.4	491.1	538.7	602.5	688.4	794.1	907.9	1018.1	1115.7
130°	436.5	452.8	469.0	509.7	553.8	611.8	686.1	776.7	878.8	978.7	1070.4
132.5°	455.1	471.4	487.6	525.9	568.9	621.1	685.0	762.7	851.0	941.5	1024.0
135°	471.3	487.6	503.8	541.0	581.6	628.1	683.8	750.0	825.4	902.1	978.7
137.5°	486.4	501.5	516.6	553.8	592.1	635.0	683.8	740.7	804.5	870.7	933.4
140°	499.2	514.3	529.4	564.2	600.2	639.7	682.6	732.6	784.8	840.5	893.9
142.5°	510.8	524.8	538.7	572.3	607.2	643.2	682.6	724.4	768.5	813.8	857.9
145°	523.6	536.4	549.1	580.5	613.0	645.5	680.3	717.5	753.5	791.8	827.8
147.5°	534.0	545.6	557.3	587.4	616.5	646.6	676.8	710.5	741.8	773.2	802.2
150°	544.5	555.0	565.4	592.1	618.8	645.5	673.3	701.2	729.1	754.6	779.0
152.5°	554.9	564.2	573.5	596.7	619.9	643.2	667.5	693.1	716.3	739.5	759.3
155°	564.2	572.9	581.6	601.4	621.1	640.8	660.6	682.6	704.7	723.3	740.7
157.5°	572.3	579.8	587.4	604.9	621.1	636.2	653.6	673.3	690.8	707.0	722.1
160°	580.5	586.8	593.2	607.2	621.1	632.7	646.6	662.9	678.0	690.8	703.5
162.5°	587.4	592.0	596.7	608.3	619.9	629.2	640.8	653.6	665.2	675.7	686.1
165°	592.1	595.6	599.0	609.5	617.6	624.6	632.7	643.2	652.5	660.6	668.7
167.5°	596.7	599.0	601.4	609.5	616.5	619.9	625.7	632.7	639.7	646.6	652.5
170°	599.0	600.8	602.5	608.3	614.1	616.5	619.9	624.6	630.4	633.9	638.5
172.5°	601.4	602.6	603.7	607.2	610.7	611.8	613.0	616.5	619.9	622.3	625.7
175°	602.5	603.1	603.7	606.0	608.3	607.2	608.3	609.5	613.0	614.1	615.3
177.5°	603.7	603.7	603.7	604.9	607.2	604.9	603.7	604.9	607.2	607.2	608.3
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	548.2	549.5	546.4	545.5	546.4	543.3	544.2	545.1	545.1	546.4	547.3
5°	516.4	514.6	511.5	510.6	509.7	511.1	510.2	511.5	511.9	515.0	515.5
7.5°	485.0	482.3	479.7	477.0	476.1	473.9	476.1	476.1	479.2	478.4	480.6
10°	447.8	447.4	443.9	442.5	440.8	437.2	442.1	440.8	443.0	447.0	447.8
12.5°	420.4	415.6	417.8	411.6	413.8	410.3	410.7	410.7	414.2	414.7	413.8
15°	394.4	390.4	384.6	382.0	380.6	378.9	384.6	385.1	382.4	388.6	386.4
17.5°	367.8	367.8	362.5	361.2	357.7	359.4	358.5	359.0	358.1	362.5	364.7
20°	344.8	342.6	340.9	341.3	336.9	336.0	335.1	336.0	339.1	342.2	343.1
22.5°	326.3	324.9	320.5	321.4	317.9	319.2	318.3	320.5	321.0	321.0	324.1
25°	308.6	306.8	307.3	305.5	304.2	304.2	302.8	304.2	305.9	306.8	307.3
27.5°	295.3	294.0	291.8	290.5	291.3	289.1	290.9	292.2	292.2	291.3	292.2
30°	279.4	280.3	280.3	275.9	277.6	276.8	278.1	279.0	279.0	279.4	278.5
32.5°	268.8	266.1	265.7	265.3	265.3	263.5	263.5	264.8	265.3	265.7	267.0
35°	254.6	254.6	252.4	253.8	252.0	252.4	252.0	252.4	253.3	252.0	253.3
37.5°	241.8	242.3	241.4	242.3	242.7	241.8	240.9	242.7	241.8	241.8	240.9
40°	230.8	230.3	230.8	230.8	230.8	231.2	230.3	230.3	230.3	229.4	228.6
42.5°	221.5	218.8	219.7	220.2	218.8	218.8	219.3	218.8	220.2	217.5	217.5
45°	208.2	207.3	207.8	207.8	208.7	207.3	208.2	208.7	207.3	206.9	206.0
47.5°	196.3	197.2	196.3	197.2	197.2	198.1	196.3	196.7	197.2	195.4	194.1
50°	184.4	184.4	185.7	185.2	185.7	184.8	184.8	184.4	184.8	183.9	182.6
52.5°	173.3	172.0	174.2	173.7	173.3	172.9	172.4	172.9	172.0	171.1	171.1
55°	159.6	159.6	160.9	161.4	161.4	160.5	159.6	160.0	159.6	159.2	158.7
57.5°	148.5	146.8	147.7	148.1	148.1	146.8	147.7	146.8	146.8	147.2	145.9
60°	134.4	134.4	133.5	134.8	134.8	134.0	134.0	134.4	133.5	133.1	132.6
62.5°	119.4	119.8	121.1	121.6	122.0	121.1	120.3	120.7	120.7	119.4	119.8
65°	106.5	107.4	109.2	108.8	107.9	108.3	107.4	107.9	106.5	107.0	105.7
67.5°	94.2	93.7	94.2	94.2	95.1	94.6	93.7	93.7	93.3	94.6	93.3
70°	80.9	80.9	80.9	80.9	81.3	81.8	80.9	80.0	80.5	79.6	79.1
72.5°	67.2	67.6	67.2	68.1	66.8	67.6	67.6	67.2	66.8	66.8	66.8
75°	54.4	55.3	53.9	54.4	53.9	54.8	54.4	54.4	53.5	53.1	53.5
77.5°	41.6	42.0	41.1	41.6	41.1	41.6	41.6	41.1	41.1	41.1	41.1
80°	29.6	30.1	29.6	29.2	28.7	29.6	28.7	29.2	29.6	29.2	30.1
82.5°	19.0	19.0	18.6	19.0	18.1	18.1	18.6	18.6	18.1	19.0	18.1
85°	9.3	9.3	10.2	9.3	8.8	8.8	8.8	9.3	8.8	9.7	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	37.8	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	37.8
92.5°	82.4	77.8	76.6	72.0	73.1	70.8	73.1	72.0	76.6	77.8	82.4
95°	171.8	159.0	144.0	134.7	131.2	132.3	131.2	134.7	144.0	159.0	171.8
97.5°	344.8	310.0	264.7	241.5	228.7	221.7	228.7	241.5	264.7	310.0	344.8
100°	686.7	616.5	520.1	470.2	436.5	415.6	436.5	470.2	520.1	616.5	686.7
102.5°	1161.0	1085.5	978.7	884.6	840.5	810.3	840.5	884.6	978.7	1085.5	1161.0
105°	1537.6	1518.5	1446.5	1374.6	1324.6	1308.4	1324.6	1374.6	1446.5	1518.5	1537.6
107.5°	1674.1	1697.3	1696.1	1685.7	1670.6	1643.9	1670.6	1685.7	1696.1	1697.3	1674.1
110°	1652.0	1699.6	1749.5	1771.6	1782.0	1780.9	1782.0	1771.6	1749.5	1699.6	1652.0



TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1577.1	1633.4	1707.7	1748.4	1770.4	1778.6	1770.4	1748.4	1707.7	1633.4	1577.1
115°	1485.4	1545.2	1627.6	1681.0	1711.2	1721.7	1711.2	1681.0	1627.6	1545.2	1485.4
117.5°	1397.8	1454.7	1539.4	1596.3	1627.6	1635.8	1627.6	1596.3	1539.4	1454.7	1397.8
120°	1319.4	1372.2	1453.5	1508.1	1541.7	1553.3	1541.7	1508.1	1453.5	1372.2	1319.4
122.5°	1258.4	1304.9	1375.7	1429.1	1458.1	1467.4	1458.1	1429.1	1375.7	1304.9	1258.4
125°	1203.4	1246.9	1314.2	1358.3	1387.3	1396.6	1387.3	1358.3	1314.2	1246.9	1203.4
127.5°	1156.3	1196.9	1256.1	1297.9	1323.5	1330.4	1323.5	1297.9	1256.1	1196.9	1156.3
130°	1108.7	1147.0	1203.9	1243.4	1266.6	1275.9	1266.6	1243.4	1203.9	1147.0	1108.7
132.5°	1059.4	1094.8	1150.5	1190.0	1210.9	1219.0	1210.9	1190.0	1150.5	1094.8	1059.4
135°	1011.2	1043.7	1093.6	1131.9	1152.8	1157.5	1152.8	1131.9	1093.6	1043.7	1011.2
137.5°	962.4	991.4	1039.0	1072.7	1091.3	1098.3	1091.3	1072.7	1039.0	991.4	962.4
140°	919.4	945.0	982.2	1012.3	1029.8	1036.7	1029.8	1012.3	982.2	945.0	919.4
142.5°	878.2	898.6	933.4	960.1	975.2	975.2	975.2	960.1	933.4	898.6	878.2
145°	844.6	861.4	889.3	909.0	920.6	924.1	920.6	909.0	889.3	861.4	844.6
147.5°	815.0	827.8	852.1	868.4	876.5	878.8	876.5	868.4	852.1	827.8	815.0
150°	789.4	799.9	817.3	831.2	838.2	839.4	838.2	831.2	817.3	799.9	789.4
152.5°	768.0	776.7	789.4	801.1	805.7	805.7	805.7	801.1	789.4	776.7	768.0
155°	747.1	753.5	766.2	774.3	779.0	776.7	779.0	774.3	766.2	753.5	747.1
157.5°	727.4	732.6	741.8	748.8	751.1	751.1	751.1	748.8	741.8	732.6	727.4
160°	707.6	711.7	719.8	725.6	726.8	726.8	726.8	725.6	719.8	711.7	707.6
162.5°	689.0	691.9	700.0	703.5	704.7	703.5	704.7	703.5	700.0	691.9	689.0
165°	671.0	673.3	678.0	682.6	682.6	681.5	682.6	682.6	678.0	673.3	671.0
167.5°	654.8	657.1	659.4	661.7	661.7	660.6	661.7	661.7	659.4	657.1	654.8
170°	639.6	640.8	642.0	645.5	644.3	642.0	644.3	645.5	642.0	640.8	639.6
172.5°	626.3	626.9	628.1	629.2	628.1	626.9	628.1	629.2	628.1	626.9	626.3
175°	615.9	616.5	616.5	617.6	616.5	614.1	616.5	617.6	616.5	616.5	615.9
177.5°	608.3	608.3	608.3	608.3	607.2	604.9	607.2	608.3	608.3	608.3	608.3
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	546.0	549.5	548.2	543.3	549.1	549.1	553.1	553.1	557.9	559.7	562.3
5°	515.0	517.7	519.9	517.7	521.7	527.9	531.4	534.5	541.1	543.8	547.8
7.5°	481.9	486.8	489.0	489.0	495.6	502.7	509.7	514.2	523.4	527.0	531.0
10°	449.6	455.4	459.8	459.3	470.4	474.8	483.7	493.8	503.1	508.4	514.2
12.5°	415.6	418.7	424.9	433.7	436.4	444.3	454.5	467.3	484.1	489.0	497.4
15°	387.3	395.7	400.5	404.5	410.7	418.2	429.3	441.7	458.5	469.1	477.9
17.5°	363.4	374.5	377.6	376.7	384.6	396.1	408.9	418.2	433.3	446.1	454.5
20°	344.0	348.4	353.7	355.9	362.1	374.5	386.8	397.4	409.8	420.0	429.7
22.5°	324.5	328.0	332.5	336.4	341.3	348.4	360.3	373.6	385.5	395.2	406.3
25°	308.6	310.8	314.8	317.9	323.2	328.0	336.4	351.0	365.2	370.9	380.6
27.5°	293.1	294.9	297.5	301.1	303.7	308.6	316.1	328.0	342.6	348.4	361.6
30°	279.4	280.7	283.4	285.2	286.5	292.2	298.0	307.3	318.3	326.3	336.0
32.5°	266.6	267.9	270.6	271.0	272.8	275.9	281.2	289.6	299.3	305.9	314.3
35°	252.4	253.3	256.0	256.9	258.2	260.8	264.8	271.0	279.8	284.7	292.2
37.5°	241.4	240.9	242.7	244.0	245.8	247.1	248.5	254.6	261.3	265.7	271.4
40°	229.4	228.6	229.0	230.8	231.7	233.4	233.4	239.6	244.0	247.6	252.0
42.5°	217.5	217.1	216.2	217.1	218.0	218.4	218.8	223.3	227.7	230.8	235.6
45°	205.6	205.1	204.2	204.7	204.7	205.6	206.9	208.7	211.8	214.4	217.1
47.5°	194.5	193.6	192.3	191.9	192.8	192.8	192.8	194.5	197.6	198.5	201.2
50°	183.0	181.7	179.9	179.0	179.0	178.6	179.5	179.9	182.6	183.5	185.7
52.5°	170.6	169.8	168.0	166.2	166.7	165.8	166.2	166.7	167.6	168.9	170.2
55°	158.3	156.5	155.2	154.7	153.4	153.4	152.1	153.9	153.4	153.9	155.6
57.5°	146.3	144.6	142.4	141.5	140.1	139.7	138.8	138.4	138.8	140.1	141.5
60°	132.2	131.3	130.0	128.7	127.8	126.4	125.6	125.6	125.1	125.1	125.6
62.5°	118.5	118.0	116.3	115.8	114.9	114.1	112.7	111.9	111.9	112.7	113.2
65°	105.2	104.8	103.5	103.0	100.8	99.9	99.5	99.0	98.1	98.1	98.1
67.5°	92.8	91.5	91.5	89.3	87.5	86.7	85.8	85.3	85.3	85.3	85.8
70°	79.1	79.1	77.8	76.5	74.7	75.2	73.8	72.5	72.5	71.6	72.1
72.5°	65.9	65.4	64.1	63.7	62.3	61.0	60.1	61.0	59.7	59.2	59.7
75°	53.1	52.6	51.7	50.8	51.3	50.0	48.6	48.2	48.2	47.3	47.3
77.5°	40.7	41.6	39.8	39.3	38.5	37.6	37.1	36.7	36.7	36.7	37.6
80°	28.3	28.7	28.7	27.9	28.3	27.0	27.0	27.0	25.6	26.1	26.5
82.5°	18.1	18.1	17.7	18.1	17.7	17.7	17.2	17.2	16.8	16.8	17.2
85°	10.2	9.7	9.3	10.2	9.7	9.7	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.5	3.5	3.5
90°	37.2	34.8	37.2	38.3	39.5	38.3	31.3	23.2	17.4	15.6	13.9
92.5°	87.1	99.8	117.3	149.8	178.8	176.5	137.0	92.9	61.5	55.2	48.8
95°	184.6	233.3	304.2	398.2	455.1	402.8	268.2	167.2	113.8	99.8	85.9
97.5°	379.6	496.9	622.3	747.6	741.8	573.5	356.4	215.9	147.4	131.8	116.1
100°	756.9	916.0	1059.9	1084.3	917.1	631.6	380.8	239.2	177.6	161.4	145.1
102.5°	1236.4	1342.1	1346.7	1209.7	923.0	609.5	382.0	260.1	204.3	188.0	171.8
105°	1556.8	1541.7	1410.5	1169.1	860.3	579.3	387.8	284.4	229.9	213.6	197.4
107.5°	1650.9	1537.1	1342.1	1083.2	802.2	563.1	400.5	308.8	255.4	239.2	222.9
110°	1604.4	1455.8	1248.0	1003.1	762.7	558.4	416.8	333.2	282.1	265.2	248.4

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1520.8	1359.5	1162.1	947.3	737.2	559.6	434.2	356.4	307.7	290.2	272.8
115°	1425.6	1273.6	1094.8	903.2	719.8	564.2	451.6	380.8	330.9	315.2	299.5
117.5°	1340.9	1199.3	1039.0	873.0	710.5	571.2	470.2	402.8	356.4	340.2	323.9
120°	1266.6	1143.5	999.6	849.8	702.4	578.2	488.8	426.1	380.8	364.6	348.3
122.5°	1212.0	1097.1	968.2	830.1	697.7	586.3	505.0	448.1	406.3	389.5	372.7
125°	1159.8	1057.6	938.0	811.5	691.9	594.4	522.4	470.2	428.4	412.2	395.9
127.5°	1115.7	1018.1	907.9	794.1	688.4	602.5	538.7	491.1	450.4	433.6	416.8
130°	1070.4	978.7	878.8	776.7	686.1	611.8	553.8	509.7	469.0	452.8	436.5
132.5°	1024.0	941.5	851.0	762.7	685.0	621.1	568.9	525.9	487.6	471.4	455.1
135°	978.7	902.1	825.4	750.0	683.8	628.1	581.6	541.0	503.8	487.6	471.3
137.5°	933.4	870.7	804.5	740.7	683.8	635.0	592.1	553.8	516.6	501.5	486.4
140°	893.9	840.5	784.8	732.6	682.6	639.7	600.2	564.2	529.4	514.3	499.2
142.5°	857.9	813.8	768.5	724.4	682.6	643.2	607.2	572.3	538.7	524.8	510.8
145°	827.8	791.8	753.5	717.5	680.3	645.5	613.0	580.5	549.1	536.4	523.6
147.5°	802.2	773.2	741.8	710.5	676.8	646.6	616.5	587.4	557.3	545.6	534.0
150°	779.0	754.6	729.1	701.2	673.3	645.5	618.8	592.1	565.4	555.0	544.5
152.5°	759.3	739.5	716.3	693.1	667.5	643.2	619.9	596.7	573.5	564.2	554.9
155°	740.7	723.3	704.7	682.6	660.6	640.8	621.1	601.4	581.6	572.9	564.2
157.5°	722.1	707.0	690.8	673.3	653.6	636.2	621.1	604.9	587.4	579.8	572.3
160°	703.5	690.8	678.0	662.9	646.6	632.7	621.1	607.2	593.2	586.8	580.5
162.5°	686.1	675.7	665.2	653.6	640.8	629.2	619.9	608.3	596.7	592.0	587.4
165°	668.7	660.6	652.5	643.2	632.7	624.6	617.6	609.5	599.0	595.6	592.1
167.5°	652.5	646.6	639.7	632.7	625.7	619.9	616.5	609.5	601.4	599.0	596.7
170°	638.5	633.9	630.4	624.6	619.9	616.5	614.1	608.3	602.5	600.8	599.0
172.5°	625.7	622.3	619.9	616.5	613.0	611.8	610.7	607.2	603.7	602.6	601.4
175°	615.3	614.1	613.0	609.5	608.3	607.2	608.3	606.0	603.7	603.1	602.5
177.5°	608.3	607.2	607.2	604.9	603.7	604.9	607.2	604.9	603.7	603.7	603.7
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	575.2	575.2	575.2	575.2
2.5°	564.6	564.6	571.2	578.3
5°	552.2	555.3	565.9	575.6
7.5°	540.2	545.5	558.8	571.2
10°	525.7	532.7	549.1	563.7
12.5°	511.5	518.1	537.1	553.5
15°	491.6	500.0	520.3	540.7
17.5°	471.7	480.1	504.9	528.7
20°	448.3	459.3	487.2	519.0
22.5°	426.6	440.3	471.3	496.9
25°	402.8	424.0	452.7	485.9
27.5°	381.5	402.8	431.9	465.5
30°	357.7	379.3	409.4	440.3
32.5°	334.7	354.6	383.7	421.8
35°	310.8	329.8	358.1	396.6
37.5°	289.1	307.7	338.6	374.0
40°	267.9	287.4	313.9	349.3
42.5°	248.0	265.3	289.1	324.5
45°	229.9	242.3	264.4	297.5
47.5°	210.9	221.9	242.3	275.4
50°	193.2	202.5	220.2	251.1
52.5°	176.0	183.9	200.3	225.0
55°	160.5	168.0	179.9	204.2
57.5°	144.6	150.3	161.8	181.3
60°	129.1	134.4	143.7	159.6
62.5°	113.6	118.0	126.9	139.7
65°	99.9	103.5	110.1	121.1
67.5°	86.7	88.9	94.2	103.0
70°	73.8	75.6	80.0	87.1
72.5°	60.1	61.9	66.8	71.6
75°	48.6	49.1	52.6	56.6
77.5°	38.0	37.6	40.2	43.3
80°	26.1	27.4	29.6	30.9
82.5°	17.7	18.1	19.0	19.9
85°	9.7	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	11.6	9.3	4.6	1.2
92.5°	39.5	33.7	24.4	17.4
95°	67.3	56.9	45.3	40.6
97.5°	95.2	80.1	67.3	60.4
100°	121.9	103.3	92.9	89.4
102.5°	147.4	128.9	118.4	116.1
105°	171.8	154.4	146.3	141.6
107.5°	197.4	181.1	173.0	169.5
110°	224.1	209.0	202.0	197.4

TEST NUMBER: P1008777

CATALOG NUMBER: S122DIP-B290D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	249.6	235.7	227.5	222.9
115°	276.3	262.4	255.4	249.6
117.5°	301.8	289.1	282.1	277.5
120°	325.1	314.6	307.7	303.0
122.5°	349.4	337.8	330.9	327.4
125°	372.7	358.7	351.8	348.3
127.5°	394.7	379.6	370.3	365.7
130°	413.3	397.0	385.4	380.8
132.5°	430.7	413.3	400.5	394.7
135°	444.6	427.2	413.3	408.7
137.5°	459.7	441.2	427.2	421.4
140°	473.7	455.1	441.2	436.5
142.5°	486.4	467.9	455.1	451.6
145°	500.4	483.0	471.3	466.7
147.5°	514.3	498.0	486.4	483.0
150°	527.1	512.0	502.7	499.2
152.5°	538.7	525.9	516.6	515.5
155°	551.4	538.7	531.7	530.6
157.5°	561.9	550.3	544.5	543.3
160°	571.2	561.9	557.3	556.1
162.5°	579.3	572.3	567.7	568.9
165°	586.3	579.3	577.0	578.2
167.5°	592.1	587.4	585.1	586.3
170°	596.7	593.2	592.1	594.4
172.5°	600.2	596.7	597.9	599.0
175°	602.5	600.2	601.4	602.5
177.5°	603.7	601.4	602.5	604.9
180°	603.7	603.7	603.7	603.7

(END OF REPORT)