

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008786

Luminaire Tested: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008786
REPORT IS A COMBINATION OF REPORTS P983853 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D1080UB35-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5501.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	28	27
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	22	21	20
4	70	60	53	47	62	54	47	43	42	37	34	30	28	25	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15
6	59	48	40	35	52	43	36	32	33	29	25	25	22	19	17	15	13
7	55	43	36	30	48	39	32	28	30	26	22	22	19	17	15	13	12
8	51	39	32	27	45	35	29	24	28	23	20	21	17	15	14	12	11
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9148	9148	9148	9148
5°	9169	9753	9205	7760
10°	9062	10647	9120	6398
15°	8843	11230	8966	5389
20°	8706	10545	8706	4684
25°	8428	9060	8466	4189
30°	7971	7121	8124	3794
35°	7566	4924	7693	3471
40°	7102	3717	7183	3214
45°	6528	3056	6635	2936
50°	6033	2681	6043	2688
55°	5468	2286	5502	2418
60°	4867	1908	4934	2111
65°	4326	1552	4405	1802
70°	3789	1217	3885	1454
75°	3183	884	3306	1055
80°	2483	561	2659	626
85°	1624	282	1752	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9457 cd/sqm

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	1.0
10°-20°	160.2	2.9
20°-30°	232.5	4.2
30°-40°	245.1	4.5
40°-50°	216.9	3.9
50°-60°	173.2	3.1
60°-70°	117.6	2.1
70°-80°	60.2	1.1
80°-90°	18.1	0.3
90°-100°	236.3	4.3
100°-110°	832.3	15.1
110°-120°	874.1	15.9
120°-130°	719.1	13.1
130°-140°	577.7	10.5
140°-150°	436.4	7.9
150°-160°	306.8	5.6
160°-170°	180.6	3.3
170°-180°	58.7	1.1
0°-30°	447.8	8.1
0°-40°	692.9	12.6
0°-60°	1083.0	19.7
0°-90°	1278.9	23.2
90°-120°	1942.8	35.3
90°-150°	3676.0	66.8
90°-180°	4222.0	76.7
0°-180°	5501.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	578	578	578	578	578	
5°	578	645	581	514	578	55
15°	543	793	551	381	543	153
25°	488	661	490	306	488	223
35°	398	360	405	254	398	249
45°	299	217	304	208	299	232
55°	205	152	206	161	205	183
65°	122	94	124	109	122	121
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	38	1	38	1	3
95°	41	133	41	133	41	42
105°	142	1314	142	1314	142	151
115°	251	1729	251	1729	251	249
125°	350	1403	350	1403	350	311
135°	410	1162	410	1162	410	317
145°	469	928	469	928	469	294
155°	533	780	533	780	533	245
165°	581	684	581	684	581	164
175°	605	617	605	617	605	57
180°	606	606	606	606	606	

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	581.0	582.3	584.6	585.0	589.4	593.0	597.0	597.0	598.3	597.9	594.3
5°	578.3	582.3	588.1	593.0	601.0	604.5	609.9	613.9	617.4	620.1	619.6
7.5°	573.9	581.0	589.4	598.8	609.4	615.6	623.2	630.3	635.2	639.6	642.7
10°	566.3	578.3	589.9	602.3	616.1	624.5	633.4	642.7	650.3	658.7	666.7
12.5°	556.1	573.4	587.7	604.1	621.0	630.3	644.5	651.6	666.3	687.6	693.4
15°	543.2	566.8	580.1	601.0	623.2	630.7	650.3	661.8	692.0	705.4	721.4
17.5°	531.2	557.5	575.2	599.2	621.0	635.6	654.7	678.3	703.6	722.7	740.5
20°	521.5	546.8	568.1	594.8	622.3	641.0	661.0	689.4	716.9	736.5	750.2
22.5°	499.3	531.7	556.6	586.3	619.6	645.4	664.5	695.6	725.4	737.4	749.3
25°	488.2	516.1	545.0	578.8	617.9	648.5	665.0	699.6	725.8	730.2	732.9
27.5°	467.7	499.3	533.0	571.7	617.4	643.2	664.1	695.6	716.5	713.4	705.4
30°	442.4	481.1	518.4	560.1	611.2	639.2	658.7	687.6	698.3	682.3	668.1
32.5°	423.8	460.2	501.5	549.9	604.1	630.7	649.8	672.5	674.7	645.9	621.9
35°	398.4	438.9	485.5	536.6	592.1	616.1	633.9	647.6	637.0	596.5	568.1
37.5°	375.8	415.8	465.5	517.5	575.7	599.2	613.4	615.6	589.4	553.9	512.1
40°	350.9	392.2	444.2	498.8	557.5	577.9	586.8	580.1	542.4	501.0	452.6
42.5°	326.0	366.9	422.9	478.8	534.4	551.7	555.2	537.0	490.8	442.4	386.4
45°	298.9	341.6	397.5	454.0	507.7	517.5	517.9	491.7	437.1	386.4	334.5
47.5°	276.7	316.3	371.8	428.2	473.5	480.2	477.5	447.3	387.8	330.9	285.6
50°	252.3	290.1	345.1	400.7	439.3	441.1	434.4	391.3	333.1	281.2	245.2
52.5°	226.1	264.3	314.9	368.2	402.9	400.2	387.3	341.1	286.5	243.4	215.9
55°	205.2	239.0	286.5	338.5	362.9	355.4	341.1	294.1	251.0	214.5	190.6
57.5°	182.1	211.9	258.5	303.8	318.0	310.9	296.7	252.7	212.8	185.2	169.2
60°	160.4	187.4	228.3	266.1	277.2	269.6	253.2	213.7	184.8	161.7	149.7
62.5°	140.4	163.9	198.1	232.8	237.2	229.6	215.4	183.4	158.6	140.4	131.5
65°	121.7	143.9	171.5	197.7	201.7	193.7	179.0	155.9	135.0	123.5	115.0
67.5°	103.5	121.3	145.7	164.8	167.0	159.5	147.5	128.8	115.9	103.5	97.3
70°	87.5	100.8	119.9	135.5	136.4	129.3	123.0	106.2	96.4	87.5	82.6
72.5°	72.0	81.3	95.9	107.5	107.9	103.5	97.7	87.1	78.6	72.4	67.5
75°	56.9	64.9	73.7	84.0	83.5	80.0	75.5	68.8	61.7	57.7	55.5
77.5°	43.5	48.4	55.5	62.2	62.2	60.4	57.7	52.9	48.4	44.4	42.2
80°	31.1	34.2	40.0	42.2	43.1	42.6	40.4	36.9	35.1	32.0	31.1
82.5°	20.0	22.2	24.9	27.1	28.4	27.5	27.1	25.3	22.7	21.8	20.9
85°	11.5	12.4	13.8	15.1	15.5	15.1	16.0	14.7	13.3	13.3	12.9
87.5°	4.9	5.3	6.2	6.2	6.7	6.7	6.2	6.7	6.7	6.2	5.8
90°	1.2	4.7	9.3	11.7	14.0	15.8	17.5	23.3	31.5	38.5	39.6
92.5°	17.5	24.5	33.8	39.6	49.0	55.4	61.8	93.3	137.6	177.2	179.6
95°	40.8	45.5	57.1	67.6	86.3	100.3	114.3	167.9	269.3	404.6	457.0
97.5°	60.6	67.6	80.4	95.6	116.6	132.4	148.1	216.9	357.9	576.0	745.0
100°	89.8	93.3	103.8	122.4	145.7	162.0	178.4	240.2	382.4	634.3	921.1
102.5°	116.6	118.9	129.4	148.1	172.6	188.9	205.2	261.2	383.6	612.1	926.9
105°	142.2	146.9	155.1	172.6	198.2	214.6	230.9	285.6	389.4	581.8	863.9
107.5°	170.2	173.7	181.9	198.2	223.9	240.2	256.5	310.1	402.2	565.5	805.6
110°	198.2	202.9	209.9	225.0	249.5	266.4	283.3	334.6	418.6	560.8	766.0

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	223.9	228.5	236.7	250.7	274.0	291.5	309.0	357.9	436.1	562.0	740.4
115°	250.7	256.5	263.5	277.5	300.8	316.6	332.3	382.4	453.5	566.6	722.9
117.5°	278.7	283.3	290.3	303.1	325.3	341.6	357.9	404.6	472.2	573.6	713.5
120°	304.3	309.0	316.0	326.5	349.8	366.1	382.4	427.9	490.8	580.6	705.4
122.5°	328.8	332.3	339.3	350.9	374.3	391.2	408.1	450.0	507.2	588.8	700.7
125°	349.8	353.3	360.3	374.3	397.6	413.9	430.2	472.2	524.7	596.9	694.9
127.5°	367.3	371.9	381.3	396.4	418.6	435.5	452.4	493.2	541.0	605.1	691.4
130°	382.4	387.1	398.7	415.1	438.4	454.7	471.0	511.8	556.1	614.4	689.1
132.5°	396.4	402.2	415.1	432.6	457.0	473.4	489.7	528.2	571.3	623.8	687.9
135°	410.4	415.1	429.1	446.5	473.4	489.7	506.0	543.3	584.1	630.8	686.7
137.5°	423.2	429.1	443.0	461.7	488.5	503.6	518.8	556.1	594.6	637.8	686.7
140°	438.4	443.0	457.0	475.7	501.3	516.5	531.7	566.6	602.8	642.4	685.6
142.5°	453.5	457.0	469.9	488.5	513.0	527.0	541.0	574.8	609.8	645.9	685.6
145°	468.7	473.4	485.0	502.5	525.8	538.6	551.5	583.0	615.6	648.2	683.2
147.5°	485.0	488.5	500.2	516.5	536.3	548.0	559.6	590.0	619.1	649.4	679.7
150°	501.3	504.8	514.2	529.3	546.8	557.3	567.8	594.6	621.4	648.2	676.2
152.5°	517.7	518.8	528.2	541.0	557.3	566.6	576.0	599.3	622.6	645.9	670.4
155°	532.8	534.0	541.0	553.8	566.6	575.4	584.1	603.9	623.8	643.6	663.4
157.5°	545.6	546.8	552.6	564.3	574.8	582.4	590.0	607.4	623.8	638.9	656.4
160°	558.5	559.6	564.3	573.6	583.0	589.4	595.8	609.8	623.8	635.4	649.4
162.5°	571.3	570.1	574.8	581.8	590.0	594.6	599.3	610.9	622.6	631.9	643.6
165°	580.6	579.5	581.8	588.8	594.6	598.1	601.6	612.1	620.3	627.3	635.4
167.5°	588.8	587.6	590.0	594.6	599.3	601.6	603.9	612.1	619.1	622.6	628.4
170°	596.9	594.6	595.8	599.3	601.6	603.4	605.1	610.9	616.8	619.1	622.6
172.5°	601.6	600.4	599.3	602.8	603.9	605.1	606.3	609.8	613.3	614.4	615.6
175°	605.1	603.9	602.8	605.1	605.1	605.7	606.3	608.6	610.9	609.8	610.9
177.5°	607.4	605.1	603.9	606.3	606.3	606.3	606.3	607.4	609.8	607.4	606.3
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	600.5	601.0	601.9	606.3	608.5	609.0	607.2	611.2	612.5	611.2	610.3
5°	629.0	631.6	637.0	642.7	642.3	642.7	645.4	648.1	649.0	645.4	646.7
7.5°	653.8	659.2	665.0	673.8	673.8	678.3	680.1	682.3	687.6	684.9	684.1
10°	682.3	689.4	700.0	714.3	714.7	719.1	723.6	730.7	732.9	731.1	732.0
12.5°	717.8	731.6	732.5	748.0	755.1	756.0	763.1	761.8	766.2	766.2	773.8
15°	733.4	754.7	766.7	781.8	786.2	780.9	786.7	792.9	793.3	793.3	792.9
17.5°	761.3	769.8	781.8	789.8	791.5	791.5	792.0	794.7	792.9	789.3	792.0
20°	767.1	770.7	775.1	774.2	775.1	770.7	766.2	761.8	762.2	760.0	766.7
22.5°	756.5	755.6	745.3	738.7	738.7	729.8	721.4	717.4	713.4	714.7	716.9
25°	729.8	716.0	703.6	693.8	691.6	677.4	665.8	662.3	655.6	661.0	661.8
27.5°	687.2	671.6	651.6	643.2	631.6	625.9	617.9	607.2	593.4	601.4	600.1
30°	641.4	618.3	601.9	581.4	563.2	561.9	546.8	529.0	521.9	521.9	525.9
32.5°	590.3	559.7	535.7	506.8	489.1	481.5	463.3	445.5	449.5	436.2	441.1
35°	530.8	490.4	460.2	432.2	418.9	410.0	386.4	376.7	366.0	359.8	371.3
37.5°	473.9	427.3	388.7	358.0	353.1	337.1	321.1	314.9	308.7	311.4	310.9
40°	404.7	363.3	328.7	304.7	296.3	288.7	278.1	270.5	266.5	268.7	269.2
42.5°	342.0	307.4	281.6	264.7	257.6	252.3	247.0	240.8	239.4	239.4	241.2
45°	293.6	265.2	247.9	234.1	230.1	226.1	222.1	219.4	218.5	216.8	218.1
47.5°	255.0	232.3	221.7	211.4	207.0	206.1	202.6	201.2	199.4	199.0	199.4
50°	222.5	208.3	198.6	192.8	189.7	188.3	186.6	183.9	183.0	185.2	184.3
52.5°	199.9	186.6	181.2	175.5	173.7	171.9	169.2	169.7	169.2	168.3	168.3
55°	177.2	168.8	163.5	159.0	158.6	156.8	154.6	153.7	153.2	152.4	153.7
57.5°	159.0	152.4	147.5	143.5	141.7	141.7	139.5	137.7	137.7	137.3	137.7
60°	140.8	134.1	131.0	127.0	125.7	125.3	123.9	123.0	121.7	121.7	121.7
62.5°	123.9	118.6	115.0	111.5	111.9	109.7	107.9	107.0	107.0	107.5	107.5
65°	107.9	104.4	99.9	96.8	95.9	95.5	94.6	94.2	92.8	93.7	93.7
67.5°	93.3	88.4	85.7	84.4	83.1	82.6	81.7	80.8	80.4	80.0	80.8
70°	78.6	74.6	72.4	71.5	70.2	69.7	69.3	68.0	68.4	68.8	69.3
72.5°	65.3	61.7	61.3	58.6	58.6	58.6	56.9	57.7	57.3	56.4	57.3
75°	51.5	49.7	48.9	47.5	48.0	47.5	47.1	45.8	45.8	46.2	46.6
77.5°	40.9	39.1	38.6	37.3	36.4	37.3	36.4	36.0	36.0	36.4	36.4
80°	30.2	29.3	28.0	28.0	28.0	27.5	27.5	27.5	27.1	26.7	27.1
82.5°	20.0	20.0	19.5	19.1	19.5	18.7	19.1	19.1	19.1	19.1	19.1
85°	12.9	12.4	12.4	12.0	12.0	12.0	12.4	11.5	11.5	12.0	12.0
87.5°	5.8	5.8	5.8	6.2	5.8	5.8	5.8	6.2	5.8	5.8	5.8
90°	38.5	37.3	35.0	37.3	37.9	38.5	38.5	38.5	38.5	38.5	38.5
92.5°	150.4	117.8	100.3	87.4	82.8	78.1	77.0	72.3	73.5	71.1	73.5
95°	399.9	305.5	234.3	185.4	172.6	159.7	144.6	135.2	131.7	132.9	131.7
97.5°	750.8	624.9	499.0	381.3	346.3	311.3	265.8	242.5	229.7	222.7	229.7
100°	1089.0	1064.5	919.9	760.2	689.7	619.1	522.3	472.2	438.4	417.4	438.4
102.5°	1214.9	1352.5	1347.8	1241.7	1165.9	1090.1	982.9	888.4	844.1	813.8	844.1
105°	1174.1	1416.6	1548.3	1563.5	1544.2	1525.0	1452.7	1380.4	1330.3	1314.0	1330.3
107.5°	1087.8	1347.8	1543.7	1657.9	1681.2	1704.6	1703.4	1692.9	1677.7	1650.9	1677.7
110°	1007.3	1253.4	1462.1	1611.3	1659.1	1706.9	1757.0	1779.2	1789.7	1788.5	1789.7

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	951.4	1167.1	1365.3	1527.3	1583.8	1640.4	1715.1	1755.9	1778.0	1786.2	1778.0
115°	907.1	1099.5	1279.0	1431.7	1491.8	1551.8	1634.6	1688.2	1718.6	1729.0	1718.6
117.5°	876.8	1043.5	1204.4	1346.6	1403.8	1460.9	1546.0	1603.1	1634.6	1642.8	1634.6
120°	853.4	1003.8	1148.4	1272.0	1325.0	1378.1	1459.7	1514.5	1548.3	1560.0	1548.3
122.5°	833.6	972.4	1101.8	1217.2	1263.8	1310.5	1381.6	1435.2	1464.4	1473.7	1464.4
125°	815.0	942.1	1062.1	1164.7	1208.4	1252.2	1319.8	1364.1	1393.3	1402.6	1393.3
127.5°	797.5	911.7	1022.5	1120.4	1161.2	1202.1	1261.5	1303.5	1329.1	1336.1	1329.1
130°	780.0	882.6	982.9	1075.0	1113.4	1151.9	1209.0	1248.7	1272.0	1281.3	1272.0
132.5°	766.0	854.6	945.6	1028.3	1063.9	1099.5	1155.4	1195.1	1216.0	1224.2	1216.0
135°	753.2	829.0	905.9	982.9	1015.6	1048.2	1098.3	1136.8	1157.7	1162.4	1157.7
137.5°	743.9	808.0	874.4	937.4	966.6	995.7	1043.5	1077.3	1096.0	1103.0	1096.0
140°	735.7	788.2	844.1	897.8	923.4	949.1	986.4	1016.7	1034.2	1041.2	1034.2
142.5°	727.5	771.8	817.3	861.6	882.0	902.4	937.4	964.2	979.4	979.4	979.4
145°	720.5	756.7	795.2	831.3	848.2	865.1	893.1	912.9	924.6	928.1	924.6
147.5°	713.5	745.0	776.5	805.6	818.4	831.3	855.8	872.1	880.3	882.6	880.3
150°	704.2	732.2	757.8	782.3	792.8	803.3	820.8	834.8	841.8	843.0	841.8
152.5°	696.0	719.4	742.7	762.5	771.2	780.0	792.8	804.5	809.1	809.1	809.1
155°	685.6	707.7	726.4	743.9	750.3	756.7	769.5	777.7	782.3	780.0	782.3
157.5°	676.2	693.7	710.0	725.2	730.4	735.7	745.0	752.0	754.3	754.3	754.3
160°	665.7	680.9	693.7	706.5	710.6	714.7	722.9	728.7	729.9	729.9	729.9
162.5°	656.4	668.1	678.6	689.1	692.0	694.9	703.0	706.5	707.7	706.5	707.7
165°	645.9	655.2	663.4	671.6	673.9	676.2	680.9	685.6	685.6	684.4	685.6
167.5°	635.4	642.4	649.4	655.2	657.6	659.9	662.2	664.6	664.6	663.4	664.6
170°	627.3	633.1	636.6	641.3	642.4	643.6	644.7	648.2	647.1	644.7	647.1
172.5°	619.1	622.6	624.9	628.4	629.0	629.6	630.8	631.9	630.8	629.6	630.8
175°	612.1	615.6	616.8	617.9	618.5	619.1	619.1	620.3	619.1	616.8	619.1
177.5°	607.4	609.8	609.8	610.9	610.9	610.9	610.9	610.9	609.8	607.4	609.8
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	612.5	609.4	606.8	607.2	609.4	607.7	603.2	597.4	595.2	592.5	595.2
5°	649.4	646.7	641.4	641.9	640.5	638.7	631.6	622.8	622.8	615.6	614.8
7.5°	685.8	681.8	678.3	677.4	672.5	668.9	662.7	650.3	645.4	637.0	632.1
10°	726.7	723.6	719.6	714.7	712.0	705.8	695.6	677.4	668.5	657.0	648.5
12.5°	768.0	767.6	758.7	748.9	748.5	738.7	731.6	707.1	695.2	679.6	659.6
15°	794.2	792.0	787.1	782.2	783.5	772.9	756.9	728.0	720.0	701.4	680.1
17.5°	793.8	793.8	792.4	791.5	790.2	787.1	778.2	759.1	746.2	722.7	702.7
20°	768.4	774.2	775.6	775.1	779.6	781.8	781.3	769.3	759.1	738.2	717.8
22.5°	717.8	731.1	736.9	740.5	749.8	754.7	766.2	761.8	759.1	743.6	726.2
25°	670.7	675.2	692.5	693.4	706.3	718.3	729.8	737.4	747.1	741.4	726.7
27.5°	609.9	620.1	632.5	641.9	644.5	668.9	688.0	702.3	724.5	726.2	721.4
30°	541.0	545.9	566.3	578.8	593.0	610.8	638.3	662.7	682.7	700.9	707.1
32.5°	457.1	477.1	489.1	504.2	516.6	548.1	581.9	613.4	636.5	667.2	680.5
35°	380.2	395.8	416.2	422.4	445.1	471.7	515.7	556.1	591.2	622.3	649.4
37.5°	316.7	329.1	350.9	360.7	374.0	408.2	445.1	495.3	537.5	575.7	609.4
40°	273.2	282.5	298.9	302.0	313.2	344.2	374.0	421.1	477.1	528.6	565.5
42.5°	243.4	247.9	259.0	263.0	270.1	290.9	317.6	362.0	414.0	467.3	519.3
45°	222.1	225.2	231.9	235.4	244.3	253.6	275.4	310.9	351.8	405.5	461.5
47.5°	203.0	207.0	209.7	211.9	216.8	227.0	241.2	267.4	306.5	355.8	410.0
50°	187.0	188.3	193.2	193.7	196.8	203.4	216.8	232.8	263.8	303.8	356.2
52.5°	171.0	172.3	175.5	178.6	179.9	185.2	194.1	207.4	230.5	262.1	308.7
55°	155.0	156.8	159.9	162.1	163.5	167.9	173.2	186.1	204.3	226.5	264.7
57.5°	139.0	143.0	143.9	145.2	147.5	152.4	157.2	164.8	179.0	199.4	227.4
60°	123.9	125.3	128.4	129.7	131.9	134.6	140.8	146.6	156.8	172.8	198.1
62.5°	108.4	111.5	112.8	114.2	115.9	119.0	123.0	129.3	138.1	151.0	171.0
65°	95.1	95.5	98.2	99.9	101.7	103.9	107.9	113.7	119.0	131.0	145.7
67.5°	82.2	83.1	84.0	85.7	87.9	90.2	93.7	96.8	103.5	111.5	123.0
70°	69.7	69.7	72.0	73.3	72.8	75.5	78.2	81.7	86.6	94.2	103.5
72.5°	58.6	58.2	60.0	60.4	61.3	63.1	64.9	68.4	71.1	76.8	84.0
75°	46.6	47.5	48.4	48.4	49.7	51.1	52.9	54.6	57.7	61.3	66.6
77.5°	36.9	36.9	37.8	38.2	39.5	39.1	40.9	42.6	44.9	48.0	52.0
80°	27.1	28.0	28.0	28.0	28.4	28.9	30.6	32.0	33.3	35.5	37.3
82.5°	19.1	19.1	20.0	20.0	20.0	20.9	20.9	21.3	22.2	23.5	24.9
85°	12.0	12.0	12.0	12.4	12.0	12.4	13.3	12.9	13.3	14.2	14.2
87.5°	5.8	5.8	5.8	5.8	5.8	6.2	5.8	6.2	6.7	6.7	6.7
90°	38.5	38.5	38.5	37.9	37.3	35.0	37.3	38.5	39.6	38.5	31.5
92.5°	72.3	77.0	78.1	82.8	87.4	100.3	117.8	150.4	179.6	177.2	137.6
95°	135.2	144.6	159.7	172.6	185.4	234.3	305.5	399.9	457.0	404.6	269.3
97.5°	242.5	265.8	311.3	346.3	381.3	499.0	624.9	750.8	745.0	576.0	357.9
100°	472.2	522.3	619.1	689.7	760.2	919.9	1064.5	1089.0	921.1	634.3	382.4
102.5°	888.4	982.9	1090.1	1165.9	1241.7	1347.8	1352.5	1214.9	926.9	612.1	383.6
105°	1380.4	1452.7	1525.0	1544.2	1563.5	1548.3	1416.6	1174.1	863.9	581.8	389.4
107.5°	1692.9	1703.4	1704.6	1681.2	1657.9	1543.7	1347.8	1087.8	805.6	565.5	402.2
110°	1779.2	1757.0	1706.9	1659.1	1611.3	1462.1	1253.4	1007.3	766.0	560.8	418.6

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1755.9	1715.1	1640.4	1583.8	1527.3	1365.3	1167.1	951.4	740.4	562.0	436.1
115°	1688.2	1634.6	1551.8	1491.8	1431.7	1279.0	1099.5	907.1	722.9	566.6	453.5
117.5°	1603.1	1546.0	1460.9	1403.8	1346.6	1204.4	1043.5	876.8	713.5	573.6	472.2
120°	1514.5	1459.7	1378.1	1325.0	1272.0	1148.4	1003.8	853.4	705.4	580.6	490.8
122.5°	1435.2	1381.6	1310.5	1263.8	1217.2	1101.8	972.4	833.6	700.7	588.8	507.2
125°	1364.1	1319.8	1252.2	1208.4	1164.7	1062.1	942.1	815.0	694.9	596.9	524.7
127.5°	1303.5	1261.5	1202.1	1161.2	1120.4	1022.5	911.7	797.5	691.4	605.1	541.0
130°	1248.7	1209.0	1151.9	1113.4	1075.0	982.9	882.6	780.0	689.1	614.4	556.1
132.5°	1195.1	1155.4	1099.5	1063.9	1028.3	945.6	854.6	766.0	687.9	623.8	571.3
135°	1136.8	1098.3	1048.2	1015.6	982.9	905.9	829.0	753.2	686.7	630.8	584.1
137.5°	1077.3	1043.5	995.7	966.6	937.4	874.4	808.0	743.9	686.7	637.8	594.6
140°	1016.7	986.4	949.1	923.4	897.8	844.1	788.2	735.7	685.6	642.4	602.8
142.5°	964.2	937.4	902.4	882.0	861.6	817.3	771.8	727.5	685.6	645.9	609.8
145°	912.9	893.1	865.1	848.2	831.3	795.2	756.7	720.5	683.2	648.2	615.6
147.5°	872.1	855.8	831.3	818.4	805.6	776.5	745.0	713.5	679.7	649.4	619.1
150°	834.8	820.8	803.3	792.8	782.3	757.8	732.2	704.2	676.2	648.2	621.4
152.5°	804.5	792.8	780.0	771.2	762.5	742.7	719.4	696.0	670.4	645.9	622.6
155°	777.7	769.5	756.7	750.3	743.9	726.4	707.7	685.6	663.4	643.6	623.8
157.5°	752.0	745.0	735.7	730.4	725.2	710.0	693.7	676.2	656.4	638.9	623.8
160°	728.7	722.9	714.7	710.6	706.5	693.7	680.9	665.7	649.4	635.4	623.8
162.5°	706.5	703.0	694.9	692.0	689.1	678.6	668.1	656.4	643.6	631.9	622.6
165°	685.6	680.9	676.2	673.9	671.6	663.4	655.2	645.9	635.4	627.3	620.3
167.5°	664.6	662.2	659.9	657.6	655.2	649.4	642.4	635.4	628.4	622.6	619.1
170°	648.2	644.7	643.6	642.4	641.3	636.6	633.1	627.3	622.6	619.1	616.8
172.5°	631.9	630.8	629.6	629.0	628.4	624.9	622.6	619.1	615.6	614.4	613.3
175°	620.3	619.1	619.1	618.5	617.9	616.8	615.6	612.1	610.9	609.8	610.9
177.5°	610.9	610.9	610.9	610.9	610.9	609.8	609.8	607.4	606.3	607.4	609.8
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	593.0	590.8	589.4	590.3	587.7	581.0	581.0	583.2	580.6	577.9	573.9
5°	609.4	605.0	602.3	601.9	595.7	585.0	582.8	580.6	574.8	568.6	561.9
7.5°	625.4	617.4	613.0	609.9	601.0	587.2	581.4	576.6	567.2	557.9	549.5
10°	638.7	627.2	621.9	617.0	605.4	588.1	578.8	569.9	557.9	545.9	535.2
12.5°	649.4	636.1	629.4	622.3	608.1	585.4	573.9	559.7	547.7	531.7	521.0
15°	667.2	639.6	633.4	626.8	612.1	581.0	566.8	550.8	534.4	513.0	501.5
17.5°	681.4	644.5	644.1	629.9	610.8	579.2	557.5	536.6	518.8	497.5	479.3
20°	689.8	652.1	645.0	630.3	606.3	567.2	544.6	521.5	502.4	476.6	458.4
22.5°	696.9	662.7	644.1	626.3	597.0	563.2	529.9	508.2	481.9	454.0	436.6
25°	699.6	665.0	645.4	625.0	590.3	551.7	513.9	490.4	461.1	435.7	412.2
27.5°	700.0	664.5	640.5	619.2	581.0	536.6	497.9	473.1	440.6	411.3	387.8
30°	695.6	659.6	637.9	614.8	572.1	522.8	478.4	450.9	416.2	386.9	362.5
32.5°	682.3	649.8	632.1	606.8	560.6	503.7	459.7	429.1	392.7	363.8	340.2
35°	660.1	637.9	618.3	594.8	545.5	485.9	441.1	405.1	368.2	340.7	318.5
37.5°	632.5	620.5	602.3	579.2	528.1	470.0	420.2	380.2	343.4	316.7	294.9
40°	595.2	598.3	580.6	559.7	507.7	448.2	393.1	354.9	320.3	295.4	274.1
42.5°	554.8	567.7	557.5	537.5	485.1	424.2	373.1	330.9	297.2	271.4	253.6
45°	511.3	533.5	527.3	512.6	461.5	398.9	344.7	303.8	274.1	249.2	233.6
47.5°	463.7	495.3	495.3	484.6	435.3	373.6	320.3	278.5	249.2	231.4	216.3
50°	415.3	450.9	456.6	449.5	406.0	344.7	290.5	252.7	227.4	210.1	199.0
52.5°	364.7	406.0	416.6	413.1	374.9	317.2	266.1	229.2	206.1	191.0	181.2
55°	316.3	364.2	375.8	377.1	341.6	286.9	239.0	206.5	184.3	174.1	165.7
57.5°	270.5	316.7	329.6	331.8	307.8	259.4	213.7	185.2	165.2	156.8	150.1
60°	231.4	270.1	286.9	291.8	271.0	227.4	190.1	162.6	147.5	139.5	133.3
62.5°	199.4	230.5	248.3	249.6	240.3	199.4	165.7	142.6	129.7	122.6	119.5
65°	168.3	196.3	207.0	212.3	204.8	172.8	143.0	123.9	113.7	107.5	104.4
67.5°	143.5	161.2	170.1	177.2	169.7	145.7	121.7	106.2	98.6	92.4	90.6
70°	117.7	132.4	139.0	146.1	139.5	121.3	103.9	89.7	83.1	78.2	76.0
72.5°	94.2	105.7	111.9	116.4	112.4	97.3	83.1	73.3	68.4	64.9	63.5
75°	74.6	82.6	86.2	89.3	87.5	76.0	67.1	59.1	54.6	51.5	50.6
77.5°	56.9	62.6	66.6	67.5	65.3	57.7	50.2	45.3	41.8	40.0	39.1
80°	40.4	44.0	46.2	47.5	45.3	42.2	36.9	33.3	30.2	28.0	27.5
82.5°	27.1	28.9	30.6	30.2	29.3	26.7	23.5	21.8	20.4	18.7	18.7
85°	15.5	16.0	16.9	17.3	16.9	15.1	13.3	12.4	11.5	10.2	10.2
87.5°	6.7	7.1	7.1	7.6	6.7	6.7	5.8	4.9	4.9	4.4	4.0
90°	23.3	17.5	15.8	14.0	11.7	9.3	4.7	1.2	4.7	9.3	11.7
92.5°	93.3	61.8	55.4	49.0	39.6	33.8	24.5	17.5	24.5	33.8	39.6
95°	167.9	114.3	100.3	86.3	67.6	57.1	45.5	40.8	45.5	57.1	67.6
97.5°	216.9	148.1	132.4	116.6	95.6	80.4	67.6	60.6	67.6	80.4	95.6
100°	240.2	178.4	162.0	145.7	122.4	103.8	93.3	89.8	93.3	103.8	122.4
102.5°	261.2	205.2	188.9	172.6	148.1	129.4	118.9	116.6	118.9	129.4	148.1
105°	285.6	230.9	214.6	198.2	172.6	155.1	146.9	142.2	146.9	155.1	172.6
107.5°	310.1	256.5	240.2	223.9	198.2	181.9	173.7	170.2	173.7	181.9	198.2
110°	334.6	283.3	266.4	249.5	225.0	209.9	202.9	198.2	202.9	209.9	225.0

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	357.9	309.0	291.5	274.0	250.7	236.7	228.5	223.9	228.5	236.7	250.7
115°	382.4	332.3	316.6	300.8	277.5	263.5	256.5	250.7	256.5	263.5	277.5
117.5°	404.6	357.9	341.6	325.3	303.1	290.3	283.3	278.7	283.3	290.3	303.1
120°	427.9	382.4	366.1	349.8	326.5	316.0	309.0	304.3	309.0	316.0	326.5
122.5°	450.0	408.1	391.2	374.3	350.9	339.3	332.3	328.8	332.3	339.3	350.9
125°	472.2	430.2	413.9	397.6	374.3	360.3	353.3	349.8	353.3	360.3	374.3
127.5°	493.2	452.4	435.5	418.6	396.4	381.3	371.9	367.3	371.9	381.3	396.4
130°	511.8	471.0	454.7	438.4	415.1	398.7	387.1	382.4	387.1	398.7	415.1
132.5°	528.2	489.7	473.4	457.0	432.6	415.1	402.2	396.4	402.2	415.1	432.6
135°	543.3	506.0	489.7	473.4	446.5	429.1	415.1	410.4	415.1	429.1	446.5
137.5°	556.1	518.8	503.6	488.5	461.7	443.0	429.1	423.2	429.1	443.0	461.7
140°	566.6	531.7	516.5	501.3	475.7	457.0	443.0	438.4	443.0	457.0	475.7
142.5°	574.8	541.0	527.0	513.0	488.5	469.9	457.0	453.5	457.0	469.9	488.5
145°	583.0	551.5	538.6	525.8	502.5	485.0	473.4	468.7	473.4	485.0	502.5
147.5°	590.0	559.6	548.0	536.3	516.5	500.2	488.5	485.0	488.5	500.2	516.5
150°	594.6	567.8	557.3	546.8	529.3	514.2	504.8	501.3	504.8	514.2	529.3
152.5°	599.3	576.0	566.6	557.3	541.0	528.2	518.8	517.7	518.8	528.2	541.0
155°	603.9	584.1	575.4	566.6	553.8	541.0	534.0	532.8	534.0	541.0	553.8
157.5°	607.4	590.0	582.4	574.8	564.3	552.6	546.8	545.6	546.8	552.6	564.3
160°	609.8	595.8	589.4	583.0	573.6	564.3	559.6	558.5	559.6	564.3	573.6
162.5°	610.9	599.3	594.6	590.0	581.8	574.8	570.1	571.3	570.1	574.8	581.8
165°	612.1	601.6	598.1	594.6	588.8	581.8	579.5	580.6	579.5	581.8	588.8
167.5°	612.1	603.9	601.6	599.3	594.6	590.0	587.6	588.8	587.6	590.0	594.6
170°	610.9	605.1	603.4	601.6	599.3	595.8	594.6	596.9	594.6	595.8	599.3
172.5°	609.8	606.3	605.1	603.9	602.8	599.3	600.4	601.6	600.4	599.3	602.8
175°	608.6	606.3	605.7	605.1	605.1	602.8	603.9	605.1	603.9	602.8	605.1
177.5°	607.4	606.3	606.3	606.3	606.3	603.9	605.1	607.4	605.1	603.9	606.3
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	571.7	573.9	573.4	569.0	564.1	560.1	552.6	553.5	550.8	551.2	553.9
5°	557.5	557.5	555.7	549.5	541.5	537.0	528.6	526.4	521.0	520.6	520.1
7.5°	542.4	540.1	537.9	529.0	519.3	512.1	500.6	497.9	492.6	489.1	487.3
10°	524.6	521.5	517.0	506.8	494.8	485.9	473.9	470.4	460.2	455.7	453.1
12.5°	505.0	503.3	496.2	487.7	468.2	458.4	441.1	444.6	434.4	425.5	424.2
15°	485.5	478.8	474.8	461.1	437.5	433.1	419.3	412.2	402.9	395.8	395.8
17.5°	466.4	456.2	447.3	432.6	415.3	402.9	392.7	389.1	377.6	370.5	369.1
20°	441.1	429.5	427.3	406.4	394.4	380.7	370.9	362.0	353.6	350.5	348.2
22.5°	417.1	403.8	400.2	382.4	370.5	356.7	346.9	340.7	334.5	332.3	328.3
25°	391.3	383.3	378.0	358.9	345.6	332.7	326.0	321.6	315.8	315.4	312.7
27.5°	366.5	358.9	353.6	335.4	325.6	313.6	308.3	303.4	300.3	298.9	297.6
30°	345.1	336.7	330.5	317.2	305.2	295.4	290.9	287.8	286.1	283.8	283.4
32.5°	321.6	316.7	308.3	298.1	288.7	279.4	276.7	274.5	271.8	271.0	270.5
35°	301.6	294.9	289.6	278.1	274.1	266.1	263.0	261.2	257.6	256.7	255.9
37.5°	282.1	275.8	270.1	263.0	255.4	251.0	249.2	246.5	244.7	245.2	244.3
40°	262.5	257.6	253.2	245.6	241.2	239.0	235.4	232.8	231.9	232.3	231.9
42.5°	243.4	239.0	236.3	230.5	226.1	223.9	221.7	219.0	220.3	220.3	221.7
45°	226.1	222.1	220.3	215.9	213.2	209.7	207.4	207.0	208.8	208.3	208.3
47.5°	208.3	207.0	204.8	200.8	197.2	195.0	194.6	194.6	196.3	197.2	196.8
50°	194.6	191.9	189.2	186.1	183.4	182.6	181.2	182.1	183.9	183.9	184.8
52.5°	177.2	175.5	174.6	171.9	170.1	170.1	170.1	170.6	171.9	173.2	172.8
55°	162.1	160.8	159.9	158.6	156.4	156.8	156.4	157.2	158.6	159.9	160.8
57.5°	146.1	145.7	144.8	142.6	142.6	142.1	143.5	143.9	146.1	147.0	148.4
60°	131.9	130.6	130.6	128.8	128.8	128.8	130.1	131.5	133.3	133.7	134.6
62.5°	116.8	116.8	116.4	115.0	115.0	116.4	116.8	118.6	119.5	119.5	120.8
65°	102.6	102.2	101.7	102.2	102.6	102.6	103.9	104.8	105.7	106.2	106.6
67.5°	88.4	87.9	88.8	88.4	89.3	91.1	90.6	91.9	93.3	93.3	93.7
70°	75.1	76.0	75.5	76.4	76.0	76.8	78.2	78.6	78.6	79.1	80.4
72.5°	62.6	62.6	62.6	62.2	62.6	63.5	64.4	64.9	65.7	66.2	67.5
75°	50.6	50.6	49.7	50.6	50.6	51.5	52.4	52.4	52.4	53.3	54.6
77.5°	38.2	38.6	38.2	39.1	39.1	39.5	40.4	40.0	40.9	41.3	41.8
80°	28.0	27.5	27.5	27.5	28.0	28.0	28.9	29.3	29.3	30.6	29.8
82.5°	17.8	18.2	17.8	18.2	18.2	18.7	18.2	18.7	19.1	20.0	19.5
85°	10.2	9.8	9.8	10.2	9.8	9.8	10.2	9.8	10.2	9.8	10.2
87.5°	4.0	3.6	3.6	3.6	3.6	3.1	3.1	2.7	2.7	2.7	2.2
90°	14.0	15.8	17.5	23.3	31.5	38.5	39.6	38.5	37.3	35.0	37.3
92.5°	49.0	55.4	61.8	93.3	137.6	177.2	179.6	150.4	117.8	100.3	87.4
95°	86.3	100.3	114.3	167.9	269.3	404.6	457.0	399.9	305.5	234.3	185.4
97.5°	116.6	132.4	148.1	216.9	357.9	576.0	745.0	750.8	624.9	499.0	381.3
100°	145.7	162.0	178.4	240.2	382.4	634.3	921.1	1089.0	1064.5	919.9	760.2
102.5°	172.6	188.9	205.2	261.2	383.6	612.1	926.9	1214.9	1352.5	1347.8	1241.7
105°	198.2	214.6	230.9	285.6	389.4	581.8	863.9	1174.1	1416.6	1548.3	1563.5
107.5°	223.9	240.2	256.5	310.1	402.2	565.5	805.6	1087.8	1347.8	1543.7	1657.9
110°	249.5	266.4	283.3	334.6	418.6	560.8	766.0	1007.3	1253.4	1462.1	1611.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	274.0	291.5	309.0	357.9	436.1	562.0	740.4	951.4	1167.1	1365.3	1527.3
115°	300.8	316.6	332.3	382.4	453.5	566.6	722.9	907.1	1099.5	1279.0	1431.7
117.5°	325.3	341.6	357.9	404.6	472.2	573.6	713.5	876.8	1043.5	1204.4	1346.6
120°	349.8	366.1	382.4	427.9	490.8	580.6	705.4	853.4	1003.8	1148.4	1272.0
122.5°	374.3	391.2	408.1	450.0	507.2	588.8	700.7	833.6	972.4	1101.8	1217.2
125°	397.6	413.9	430.2	472.2	524.7	596.9	694.9	815.0	942.1	1062.1	1164.7
127.5°	418.6	435.5	452.4	493.2	541.0	605.1	691.4	797.5	911.7	1022.5	1120.4
130°	438.4	454.7	471.0	511.8	556.1	614.4	689.1	780.0	882.6	982.9	1075.0
132.5°	457.0	473.4	489.7	528.2	571.3	623.8	687.9	766.0	854.6	945.6	1028.3
135°	473.4	489.7	506.0	543.3	584.1	630.8	686.7	753.2	829.0	905.9	982.9
137.5°	488.5	503.6	518.8	556.1	594.6	637.8	686.7	743.9	808.0	874.4	937.4
140°	501.3	516.5	531.7	566.6	602.8	642.4	685.6	735.7	788.2	844.1	897.8
142.5°	513.0	527.0	541.0	574.8	609.8	645.9	685.6	727.5	771.8	817.3	861.6
145°	525.8	538.6	551.5	583.0	615.6	648.2	683.2	720.5	756.7	795.2	831.3
147.5°	536.3	548.0	559.6	590.0	619.1	649.4	679.7	713.5	745.0	776.5	805.6
150°	546.8	557.3	567.8	594.6	621.4	648.2	676.2	704.2	732.2	757.8	782.3
152.5°	557.3	566.6	576.0	599.3	622.6	645.9	670.4	696.0	719.4	742.7	762.5
155°	566.6	575.4	584.1	603.9	623.8	643.6	663.4	685.6	707.7	726.4	743.9
157.5°	574.8	582.4	590.0	607.4	623.8	638.9	656.4	676.2	693.7	710.0	725.2
160°	583.0	589.4	595.8	609.8	623.8	635.4	649.4	665.7	680.9	693.7	706.5
162.5°	590.0	594.6	599.3	610.9	622.6	631.9	643.6	656.4	668.1	678.6	689.1
165°	594.6	598.1	601.6	612.1	620.3	627.3	635.4	645.9	655.2	663.4	671.6
167.5°	599.3	601.6	603.9	612.1	619.1	622.6	628.4	635.4	642.4	649.4	655.2
170°	601.6	603.4	605.1	610.9	616.8	619.1	622.6	627.3	633.1	636.6	641.3
172.5°	603.9	605.1	606.3	609.8	613.3	614.4	615.6	619.1	622.6	624.9	628.4
175°	605.1	605.7	606.3	608.6	610.9	609.8	610.9	612.1	615.6	616.8	617.9
177.5°	606.3	606.3	606.3	607.4	609.8	607.4	606.3	607.4	609.8	609.8	610.9
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	550.8	552.1	549.0	548.1	549.0	545.9	546.8	547.7	547.7	549.0	549.9
5°	518.8	517.0	513.9	513.0	512.1	513.5	512.6	513.9	514.4	517.5	517.9
7.5°	487.3	484.6	481.9	479.3	478.4	476.2	478.4	478.4	481.5	480.6	482.8
10°	450.0	449.5	446.0	444.6	442.9	439.3	444.2	442.9	445.1	449.1	450.0
12.5°	422.4	417.5	419.8	413.5	415.8	412.2	412.7	412.7	416.2	416.6	415.8
15°	396.2	392.2	386.4	383.8	382.4	380.7	386.4	386.9	384.2	390.4	388.2
17.5°	369.6	369.6	364.2	362.9	359.3	361.1	360.2	360.7	359.8	364.2	366.5
20°	346.5	344.2	342.5	342.9	338.5	337.6	336.7	337.6	340.7	343.8	344.7
22.5°	327.8	326.5	322.0	322.9	319.4	320.7	319.8	322.0	322.5	322.5	325.6
25°	310.0	308.3	308.7	306.9	305.6	305.6	304.3	305.6	307.4	308.3	308.7
27.5°	296.7	295.4	293.2	291.8	292.7	290.5	292.3	293.6	293.6	292.7	293.6
30°	280.7	281.6	281.6	277.2	279.0	278.1	279.4	280.3	280.3	280.7	279.8
32.5°	270.1	267.4	267.0	266.5	266.5	264.7	264.7	266.1	266.5	267.0	268.3
35°	255.9	255.9	253.6	255.0	253.2	253.6	253.2	253.6	254.5	253.2	254.5
37.5°	243.0	243.4	242.5	243.4	243.9	243.0	242.1	243.9	243.0	243.0	242.1
40°	231.9	231.4	231.9	231.9	231.9	232.3	231.4	231.4	231.4	230.5	229.6
42.5°	222.5	219.9	220.8	221.2	219.9	219.9	220.3	219.9	221.2	218.5	218.5
45°	209.2	208.3	208.8	208.8	209.7	208.3	209.2	209.7	208.3	207.9	207.0
47.5°	197.2	198.1	197.2	198.1	198.1	199.0	197.2	197.7	198.1	196.3	195.0
50°	185.2	185.2	186.6	186.1	186.6	185.7	185.7	185.2	185.7	184.8	183.4
52.5°	174.1	172.8	175.0	174.6	174.1	173.7	173.2	173.7	172.8	171.9	171.9
55°	160.4	160.4	161.7	162.1	162.1	161.2	160.4	160.8	160.4	159.9	159.5
57.5°	149.2	147.5	148.4	148.8	148.8	147.5	148.4	147.5	147.5	147.9	146.6
60°	135.0	135.0	134.1	135.5	135.5	134.6	134.6	135.0	134.1	133.7	133.3
62.5°	119.9	120.4	121.7	122.2	122.6	121.7	120.8	121.3	121.3	119.9	120.4
65°	107.0	107.9	109.7	109.3	108.4	108.8	107.9	108.4	107.0	107.5	106.2
67.5°	94.6	94.2	94.6	94.6	95.5	95.1	94.2	94.2	93.7	95.1	93.7
70°	81.3	81.3	81.3	81.3	81.7	82.2	81.3	80.4	80.8	80.0	79.5
72.5°	67.5	68.0	67.5	68.4	67.1	68.0	68.0	67.5	67.1	67.1	67.1
75°	54.6	55.5	54.2	54.6	54.2	55.1	54.6	54.6	53.7	53.3	53.7
77.5°	41.8	42.2	41.3	41.8	41.3	41.8	41.8	41.3	41.3	41.3	41.3
80°	29.8	30.2	29.8	29.3	28.9	29.8	28.9	29.3	29.8	29.3	30.2
82.5°	19.1	19.1	18.7	19.1	18.2	18.2	18.7	18.7	18.2	19.1	18.2
85°	9.3	9.3	10.2	9.3	8.9	8.9	8.9	9.3	8.9	9.8	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	37.9	38.5	38.5	38.5	38.5	38.5	38.5	38.5	38.5	38.5	37.9
92.5°	82.8	78.1	77.0	72.3	73.5	71.1	73.5	72.3	77.0	78.1	82.8
95°	172.6	159.7	144.6	135.2	131.7	132.9	131.7	135.2	144.6	159.7	172.6
97.5°	346.3	311.3	265.8	242.5	229.7	222.7	229.7	242.5	265.8	311.3	346.3
100°	689.7	619.1	522.3	472.2	438.4	417.4	438.4	472.2	522.3	619.1	689.7
102.5°	1165.9	1090.1	982.9	888.4	844.1	813.8	844.1	888.4	982.9	1090.1	1165.9
105°	1544.2	1525.0	1452.7	1380.4	1330.3	1314.0	1330.3	1380.4	1452.7	1525.0	1544.2
107.5°	1681.2	1704.6	1703.4	1692.9	1677.7	1650.9	1677.7	1692.9	1703.4	1704.6	1681.2
110°	1659.1	1706.9	1757.0	1779.2	1789.7	1788.5	1789.7	1779.2	1757.0	1706.9	1659.1

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1583.8	1640.4	1715.1	1755.9	1778.0	1786.2	1778.0	1755.9	1715.1	1640.4	1583.8
115°	1491.8	1551.8	1634.6	1688.2	1718.6	1729.0	1718.6	1688.2	1634.6	1551.8	1491.8
117.5°	1403.8	1460.9	1546.0	1603.1	1634.6	1642.8	1634.6	1603.1	1546.0	1460.9	1403.8
120°	1325.0	1378.1	1459.7	1514.5	1548.3	1560.0	1548.3	1514.5	1459.7	1378.1	1325.0
122.5°	1263.8	1310.5	1381.6	1435.2	1464.4	1473.7	1464.4	1435.2	1381.6	1310.5	1263.8
125°	1208.4	1252.2	1319.8	1364.1	1393.3	1402.6	1393.3	1364.1	1319.8	1252.2	1208.4
127.5°	1161.2	1202.1	1261.5	1303.5	1329.1	1336.1	1329.1	1303.5	1261.5	1202.1	1161.2
130°	1113.4	1151.9	1209.0	1248.7	1272.0	1281.3	1272.0	1248.7	1209.0	1151.9	1113.4
132.5°	1063.9	1099.5	1155.4	1195.1	1216.0	1224.2	1216.0	1195.1	1155.4	1099.5	1063.9
135°	1015.6	1048.2	1098.3	1136.8	1157.7	1162.4	1157.7	1136.8	1098.3	1048.2	1015.6
137.5°	966.6	995.7	1043.5	1077.3	1096.0	1103.0	1096.0	1077.3	1043.5	995.7	966.6
140°	923.4	949.1	986.4	1016.7	1034.2	1041.2	1034.2	1016.7	986.4	949.1	923.4
142.5°	882.0	902.4	937.4	964.2	979.4	979.4	979.4	964.2	937.4	902.4	882.0
145°	848.2	865.1	893.1	912.9	924.6	928.1	924.6	912.9	893.1	865.1	848.2
147.5°	818.4	831.3	855.8	872.1	880.3	882.6	880.3	872.1	855.8	831.3	818.4
150°	792.8	803.3	820.8	834.8	841.8	843.0	841.8	834.8	820.8	803.3	792.8
152.5°	771.2	780.0	792.8	804.5	809.1	809.1	809.1	804.5	792.8	780.0	771.2
155°	750.3	756.7	769.5	777.7	782.3	780.0	782.3	777.7	769.5	756.7	750.3
157.5°	730.4	735.7	745.0	752.0	754.3	754.3	754.3	752.0	745.0	735.7	730.4
160°	710.6	714.7	722.9	728.7	729.9	729.9	729.9	728.7	722.9	714.7	710.6
162.5°	692.0	694.9	703.0	706.5	707.7	706.5	707.7	706.5	703.0	694.9	692.0
165°	673.9	676.2	680.9	685.6	685.6	684.4	685.6	685.6	680.9	676.2	673.9
167.5°	657.6	659.9	662.2	664.6	664.6	663.4	664.6	664.6	662.2	659.9	657.6
170°	642.4	643.6	644.7	648.2	647.1	644.7	647.1	648.2	644.7	643.6	642.4
172.5°	629.0	629.6	630.8	631.9	630.8	629.6	630.8	631.9	630.8	629.6	629.0
175°	618.5	619.1	619.1	620.3	619.1	616.8	619.1	620.3	619.1	619.1	618.5
177.5°	610.9	610.9	610.9	610.9	609.8	607.4	609.8	610.9	610.9	610.9	610.9
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	548.6	552.1	550.8	545.9	551.7	551.7	555.7	555.7	560.6	562.3	565.0
5°	517.5	520.1	522.4	520.1	524.1	530.4	533.9	537.0	543.7	546.4	550.3
7.5°	484.2	489.1	491.3	491.3	497.9	505.0	512.1	516.6	525.9	529.5	533.5
10°	451.7	457.5	462.0	461.5	472.6	477.1	485.9	496.2	505.5	510.8	516.6
12.5°	417.5	420.6	426.9	435.7	438.4	446.4	456.6	469.5	486.4	491.3	499.7
15°	389.1	397.5	402.4	406.4	412.7	420.2	431.3	443.7	460.6	471.3	480.2
17.5°	365.1	376.2	379.3	378.4	386.4	398.0	410.9	420.2	435.3	448.2	456.6
20°	345.6	350.0	355.4	357.6	363.8	376.2	388.7	399.3	411.8	422.0	431.8
22.5°	326.0	329.6	334.0	338.0	342.9	350.0	362.0	375.3	387.3	397.1	408.2
25°	310.0	312.3	316.3	319.4	324.7	329.6	338.0	352.7	366.9	372.7	382.4
27.5°	294.5	296.3	298.9	302.5	305.2	310.0	317.6	329.6	344.2	350.0	363.3
30°	280.7	282.1	284.7	286.5	287.8	293.6	299.4	308.7	319.8	327.8	337.6
32.5°	267.8	269.2	271.8	272.3	274.1	277.2	282.5	290.9	300.7	307.4	315.8
35°	253.6	254.5	257.2	258.1	259.4	262.1	266.1	272.3	281.2	286.1	293.6
37.5°	242.5	242.1	243.9	245.2	247.0	248.3	249.6	255.9	262.5	267.0	272.7
40°	230.5	229.6	230.1	231.9	232.8	234.5	234.5	240.8	245.2	248.7	253.2
42.5°	218.5	218.1	217.2	218.1	219.0	219.4	219.9	224.3	228.8	231.9	236.8
45°	206.5	206.1	205.2	205.7	205.7	206.5	207.9	209.7	212.8	215.4	218.1
47.5°	195.4	194.6	193.2	192.8	193.7	193.7	193.7	195.4	198.6	199.4	202.1
50°	183.9	182.6	180.8	179.9	179.9	179.5	180.3	180.8	183.4	184.3	186.6
52.5°	171.5	170.6	168.8	167.0	167.5	166.6	167.0	167.5	168.3	169.7	171.0
55°	159.0	157.2	155.9	155.5	154.1	154.1	152.8	154.6	154.1	154.6	156.4
57.5°	147.0	145.2	143.0	142.1	140.8	140.4	139.5	139.0	139.5	140.8	142.1
60°	132.8	131.9	130.6	129.3	128.4	127.0	126.1	126.1	125.7	125.7	126.1
62.5°	119.0	118.6	116.8	116.4	115.5	114.6	113.3	112.4	112.4	113.3	113.7
65°	105.7	105.3	103.9	103.5	101.3	100.4	99.9	99.5	98.6	98.6	98.6
67.5°	93.3	91.9	91.9	89.7	87.9	87.1	86.2	85.7	85.7	85.7	86.2
70°	79.5	79.5	78.2	76.8	75.1	75.5	74.2	72.8	72.8	72.0	72.4
72.5°	66.2	65.7	64.4	64.0	62.6	61.3	60.4	61.3	60.0	59.5	60.0
75°	53.3	52.9	52.0	51.1	51.5	50.2	48.9	48.4	48.4	47.5	47.5
77.5°	40.9	41.8	40.0	39.5	38.6	37.8	37.3	36.9	36.9	36.9	37.8
80°	28.4	28.9	28.9	28.0	28.4	27.1	27.1	27.1	25.8	26.2	26.7
82.5°	18.2	18.2	17.8	18.2	17.8	17.8	17.3	17.3	16.9	16.9	17.3
85°	10.2	9.8	9.3	10.2	9.8	9.8	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.6	3.6	3.6
90°	37.3	35.0	37.3	38.5	39.6	38.5	31.5	23.3	17.5	15.8	14.0
92.5°	87.4	100.3	117.8	150.4	179.6	177.2	137.6	93.3	61.8	55.4	49.0
95°	185.4	234.3	305.5	399.9	457.0	404.6	269.3	167.9	114.3	100.3	86.3
97.5°	381.3	499.0	624.9	750.8	745.0	576.0	357.9	216.9	148.1	132.4	116.6
100°	760.2	919.9	1064.5	1089.0	921.1	634.3	382.4	240.2	178.4	162.0	145.7
102.5°	1241.7	1347.8	1352.5	1214.9	926.9	612.1	383.6	261.2	205.2	188.9	172.6
105°	1563.5	1548.3	1416.6	1174.1	863.9	581.8	389.4	285.6	230.9	214.6	198.2
107.5°	1657.9	1543.7	1347.8	1087.8	805.6	565.5	402.2	310.1	256.5	240.2	223.9
110°	1611.3	1462.1	1253.4	1007.3	766.0	560.8	418.6	334.6	283.3	266.4	249.5

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1527.3	1365.3	1167.1	951.4	740.4	562.0	436.1	357.9	309.0	291.5	274.0
115°	1431.7	1279.0	1099.5	907.1	722.9	566.6	453.5	382.4	332.3	316.6	300.8
117.5°	1346.6	1204.4	1043.5	876.8	713.5	573.6	472.2	404.6	357.9	341.6	325.3
120°	1272.0	1148.4	1003.8	853.4	705.4	580.6	490.8	427.9	382.4	366.1	349.8
122.5°	1217.2	1101.8	972.4	833.6	700.7	588.8	507.2	450.0	408.1	391.2	374.3
125°	1164.7	1062.1	942.1	815.0	694.9	596.9	524.7	472.2	430.2	413.9	397.6
127.5°	1120.4	1022.5	911.7	797.5	691.4	605.1	541.0	493.2	452.4	435.5	418.6
130°	1075.0	982.9	882.6	780.0	689.1	614.4	556.1	511.8	471.0	454.7	438.4
132.5°	1028.3	945.6	854.6	766.0	687.9	623.8	571.3	528.2	489.7	473.4	457.0
135°	982.9	905.9	829.0	753.2	686.7	630.8	584.1	543.3	506.0	489.7	473.4
137.5°	937.4	874.4	808.0	743.9	686.7	637.8	594.6	556.1	518.8	503.6	488.5
140°	897.8	844.1	788.2	735.7	685.6	642.4	602.8	566.6	531.7	516.5	501.3
142.5°	861.6	817.3	771.8	727.5	685.6	645.9	609.8	574.8	541.0	527.0	513.0
145°	831.3	795.2	756.7	720.5	683.2	648.2	615.6	583.0	551.5	538.6	525.8
147.5°	805.6	776.5	745.0	713.5	679.7	649.4	619.1	590.0	559.6	548.0	536.3
150°	782.3	757.8	732.2	704.2	676.2	648.2	621.4	594.6	567.8	557.3	546.8
152.5°	762.5	742.7	719.4	696.0	670.4	645.9	622.6	599.3	576.0	566.6	557.3
155°	743.9	726.4	707.7	685.6	663.4	643.6	623.8	603.9	584.1	575.4	566.6
157.5°	725.2	710.0	693.7	676.2	656.4	638.9	623.8	607.4	590.0	582.4	574.8
160°	706.5	693.7	680.9	665.7	649.4	635.4	623.8	609.8	595.8	589.4	583.0
162.5°	689.1	678.6	668.1	656.4	643.6	631.9	622.6	610.9	599.3	594.6	590.0
165°	671.6	663.4	655.2	645.9	635.4	627.3	620.3	612.1	601.6	598.1	594.6
167.5°	655.2	649.4	642.4	635.4	628.4	622.6	619.1	612.1	603.9	601.6	599.3
170°	641.3	636.6	633.1	627.3	622.6	619.1	616.8	610.9	605.1	603.4	601.6
172.5°	628.4	624.9	622.6	619.1	615.6	614.4	613.3	609.8	606.3	605.1	603.9
175°	617.9	616.8	615.6	612.1	610.9	609.8	610.9	608.6	606.3	605.7	605.1
177.5°	610.9	609.8	609.8	607.4	606.3	607.4	609.8	607.4	606.3	606.3	606.3
180°	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3	606.3

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	577.9	577.9	577.9	577.9
2.5°	567.2	567.2	573.9	581.0
5°	554.8	557.9	568.6	578.3
7.5°	542.8	548.1	561.5	573.9
10°	528.1	535.2	551.7	566.3
12.5°	513.9	520.6	539.7	556.1
15°	493.9	502.4	522.8	543.2
17.5°	473.9	482.4	507.3	531.2
20°	450.4	461.5	489.5	521.5
22.5°	428.6	442.4	473.5	499.3
25°	404.7	426.0	454.8	488.2
27.5°	383.3	404.7	434.0	467.7
30°	359.3	381.1	411.3	442.4
32.5°	336.3	356.2	385.6	423.8
35°	312.3	331.4	359.8	398.4
37.5°	290.5	309.2	340.2	375.8
40°	269.2	288.7	315.4	350.9
42.5°	249.2	266.5	290.5	326.0
45°	231.0	243.4	265.6	298.9
47.5°	211.9	223.0	243.4	276.7
50°	194.1	203.4	221.2	252.3
52.5°	176.8	184.8	201.2	226.1
55°	161.2	168.8	180.8	205.2
57.5°	145.2	151.0	162.6	182.1
60°	129.7	135.0	144.4	160.4
62.5°	114.2	118.6	127.5	140.4
65°	100.4	103.9	110.6	121.7
67.5°	87.1	89.3	94.6	103.5
70°	74.2	76.0	80.4	87.5
72.5°	60.4	62.2	67.1	72.0
75°	48.9	49.3	52.9	56.9
77.5°	38.2	37.8	40.4	43.5
80°	26.2	27.5	29.8	31.1
82.5°	17.8	18.2	19.1	20.0
85°	9.8	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	11.7	9.3	4.7	1.2
92.5°	39.6	33.8	24.5	17.5
95°	67.6	57.1	45.5	40.8
97.5°	95.6	80.4	67.6	60.6
100°	122.4	103.8	93.3	89.8
102.5°	148.1	129.4	118.9	116.6
105°	172.6	155.1	146.9	142.2
107.5°	198.2	181.9	173.7	170.2
110°	225.0	209.9	202.9	198.2

TEST NUMBER: P1008786

CATALOG NUMBER: S122DIP-B290D1080UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	250.7	236.7	228.5	223.9
115°	277.5	263.5	256.5	250.7
117.5°	303.1	290.3	283.3	278.7
120°	326.5	316.0	309.0	304.3
122.5°	350.9	339.3	332.3	328.8
125°	374.3	360.3	353.3	349.8
127.5°	396.4	381.3	371.9	367.3
130°	415.1	398.7	387.1	382.4
132.5°	432.6	415.1	402.2	396.4
135°	446.5	429.1	415.1	410.4
137.5°	461.7	443.0	429.1	423.2
140°	475.7	457.0	443.0	438.4
142.5°	488.5	469.9	457.0	453.5
145°	502.5	485.0	473.4	468.7
147.5°	516.5	500.2	488.5	485.0
150°	529.3	514.2	504.8	501.3
152.5°	541.0	528.2	518.8	517.7
155°	553.8	541.0	534.0	532.8
157.5°	564.3	552.6	546.8	545.6
160°	573.6	564.3	559.6	558.5
162.5°	581.8	574.8	570.1	571.3
165°	588.8	581.8	579.5	580.6
167.5°	594.6	590.0	587.6	588.8
170°	599.3	595.8	594.6	596.9
172.5°	602.8	599.3	600.4	601.6
175°	605.1	602.8	603.9	605.1
177.5°	606.3	603.9	605.1	607.4
180°	606.3	606.3	606.3	606.3

(END OF REPORT)