

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008855

Luminaire Tested: S122DIP-B290D530UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008855
REPORT IS A COMBINATION OF REPORTS P983940 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D530UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3311.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38		
1	95	91	88	84	87	83	80	77	68	66	64	53	52	51	40	40	39	33		
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28		
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24		
4	73	63	55	50	66	57	51	46	47	42	39	38	34	32	29	27	25	21		
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19		
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20	16		
7	57	46	38	33	52	42	35	30	35	30	26	28	24	22	22	19	18	15		
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13		
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12		
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9026	9026	9026	9026
5°	9047	9623	9082	7656
10°	8942	10506	8998	6312
15°	8725	11080	8846	5317
20°	8589	10405	8589	4622
25°	8316	8938	8353	4132
30°	7865	7027	8014	3744
35°	7466	4859	7591	3424
40°	7007	3669	7088	3171
45°	6443	3015	6548	2896
50°	5952	2646	5964	2652
55°	5396	2254	5430	2386
60°	4801	1883	4867	2082
65°	4269	1532	4348	1779
70°	3737	1201	3833	1435
75°	3138	873	3261	1039
80°	2451	553	2627	618
85°	1610	277	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9330 cd/sqm

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	1.6
10°-20°	158.1	4.8
20°-30°	229.4	6.9
30°-40°	241.8	7.3
40°-50°	214.0	6.5
50°-60°	170.9	5.2
60°-70°	116.1	3.5
70°-80°	59.4	1.8
80°-90°	15.9	0.5
90°-100°	114.8	3.5
100°-110°	404.3	12.2
110°-120°	424.7	12.8
120°-130°	349.4	10.6
130°-140°	280.7	8.5
140°-150°	212.0	6.4
150°-160°	149.0	4.5
160°-170°	87.7	2.6
170°-180°	28.5	0.9
0°-30°	441.8	13.3
0°-40°	683.6	20.6
0°-60°	1068.5	32.3
0°-90°	1259.9	38.1
90°-120°	943.8	28.5
90°-150°	1785.8	53.9
90°-180°	2051.0	61.9
0°-180°	3311.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	570	570	570	570	570	
5°	571	637	573	507	571	54
15°	536	783	543	376	536	151
25°	482	652	484	302	482	220
35°	393	355	400	250	393	246
45°	295	214	300	206	295	229
55°	202	150	204	159	202	181
65°	120	92	122	107	120	119
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	19	1	19	1	2
95°	20	65	20	65	20	20
105°	69	638	69	638	69	73
115°	122	840	122	840	122	121
125°	170	681	170	681	170	151
135°	199	565	199	565	199	154
145°	228	451	228	451	228	143
155°	259	379	259	379	259	119
165°	282	332	282	332	282	80
175°	294	300	294	300	294	28
180°	294	294	294	294	294	

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	573.3	574.6	576.8	577.2	581.6	585.1	589.0	589.0	590.3	589.9	586.4
5°	570.6	574.6	580.3	585.1	593.0	596.5	601.7	605.7	609.2	611.8	611.4
7.5°	566.2	573.3	581.6	590.8	601.3	607.4	614.9	621.9	626.7	631.1	634.2
10°	558.8	570.6	582.0	594.3	607.9	616.2	625.0	634.2	641.6	649.9	657.8
12.5°	548.7	565.8	579.8	596.0	612.7	621.9	635.9	642.9	657.4	678.4	684.1
15°	536.0	559.2	572.4	593.0	614.9	622.3	641.6	653.0	682.8	696.0	711.7
17.5°	524.2	550.0	567.6	591.2	612.7	627.2	646.0	669.2	694.2	713.1	730.6
20°	514.5	539.5	560.5	586.8	614.0	632.4	652.1	680.2	707.4	726.6	740.2
22.5°	492.6	524.6	549.1	578.5	611.4	636.8	655.6	686.3	715.7	727.5	739.4
25°	481.7	509.3	537.8	571.1	609.6	639.9	656.1	690.3	716.1	720.5	723.1
27.5°	461.5	492.6	525.9	564.0	609.2	634.6	655.2	686.3	706.9	703.9	696.0
30°	436.5	474.6	511.5	552.7	603.1	630.7	649.9	678.4	689.0	673.2	659.2
32.5°	418.1	454.0	494.8	542.6	596.0	622.3	641.2	663.5	665.7	637.2	613.6
35°	393.1	433.0	479.0	529.4	584.2	607.9	625.4	639.0	628.5	588.6	560.5
37.5°	370.8	410.2	459.3	510.6	568.0	591.2	605.2	607.4	581.6	546.5	505.3
40°	346.2	387.0	438.3	492.2	550.0	570.2	578.9	572.4	535.1	494.4	446.6
42.5°	321.7	362.0	417.2	472.5	527.2	544.3	547.8	529.9	484.3	436.5	381.3
45°	295.0	337.0	392.2	447.9	500.9	510.6	511.0	485.2	431.3	381.3	330.0
47.5°	273.0	312.0	366.8	422.5	467.2	473.8	471.1	441.3	382.6	326.5	281.8
50°	248.9	286.2	340.5	395.3	433.4	435.2	428.6	386.1	328.7	277.4	241.9
52.5°	223.1	260.8	310.7	363.3	397.5	394.9	382.2	336.6	282.7	240.2	213.0
55°	202.5	235.8	282.7	334.0	358.1	350.6	336.6	290.1	247.6	211.7	188.0
57.5°	179.7	209.1	255.1	299.8	313.8	306.8	292.8	249.4	209.9	182.8	167.0
60°	158.2	184.9	225.3	262.5	273.5	266.0	249.8	210.8	182.3	159.5	147.7
62.5°	138.5	161.7	195.5	229.7	234.0	226.6	212.6	181.0	156.5	138.5	129.7
65°	120.1	142.0	169.2	195.0	199.0	191.1	176.6	153.8	133.2	121.8	113.5
67.5°	102.1	119.6	143.8	162.6	164.8	157.3	145.5	127.1	114.4	102.1	96.0
70°	86.3	99.5	118.3	133.7	134.5	127.5	121.4	104.7	95.1	86.3	81.5
72.5°	71.0	80.2	94.7	106.1	106.5	102.1	96.4	85.9	77.6	71.4	66.6
75°	56.1	64.0	72.8	82.8	82.4	78.9	74.5	67.9	60.9	57.0	54.8
77.5°	43.0	47.8	54.8	61.4	61.4	59.6	57.0	52.2	47.8	43.8	41.6
80°	30.7	33.7	39.4	41.6	42.5	42.1	39.9	36.4	34.6	31.6	30.7
82.5°	19.7	21.9	24.5	26.7	28.0	27.2	26.7	25.0	22.4	21.5	20.6
85°	11.4	12.3	13.6	14.9	15.3	14.9	15.8	14.5	13.1	13.1	12.7
87.5°	4.8	5.3	6.1	6.1	6.6	6.6	6.1	6.6	6.6	6.1	5.7
90°	0.6	2.3	4.5	5.7	6.8	7.6	8.5	11.3	15.3	18.7	19.3
92.5°	8.5	11.9	16.4	19.3	23.8	26.9	30.0	45.3	66.8	86.1	87.2
95°	19.8	22.1	27.8	32.9	41.9	48.7	55.5	81.6	130.8	196.5	222.0
97.5°	29.5	32.9	39.1	46.4	56.6	64.2	71.9	105.4	173.9	279.8	361.9
100°	43.6	45.3	50.4	59.5	70.8	78.8	86.7	116.7	185.8	308.1	447.5
102.5°	56.6	57.8	62.9	71.9	83.8	91.8	99.7	126.9	186.3	297.4	450.3
105°	69.1	71.4	75.3	83.8	96.3	104.2	112.1	138.8	189.2	282.6	419.7
107.5°	82.7	84.4	88.4	96.3	108.7	116.6	124.6	150.7	195.4	274.7	391.4
110°	96.3	98.6	102.0	109.3	121.2	129.4	137.6	162.6	203.3	272.4	372.1

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	108.7	111.0	115.0	121.8	133.1	141.6	150.1	173.9	211.8	273.0	359.7
115°	121.8	124.6	128.0	134.8	146.1	153.8	161.4	185.8	220.3	275.3	351.2
117.5°	135.4	137.6	141.0	147.3	158.0	166.0	173.9	196.5	229.4	278.7	346.6
120°	147.8	150.1	153.5	158.6	169.9	177.9	185.8	207.9	238.5	282.1	342.7
122.5°	159.7	161.4	164.8	170.5	181.8	190.0	198.2	218.6	246.4	286.0	340.4
125°	169.9	171.6	175.0	181.8	193.1	201.0	209.0	229.4	254.9	290.0	337.6
127.5°	178.4	180.7	185.2	192.6	203.3	211.6	219.8	239.6	262.8	294.0	335.9
130°	185.8	188.0	193.7	201.6	213.0	220.9	228.8	248.7	270.2	298.5	334.7
132.5°	192.6	195.4	201.6	210.1	222.0	230.0	237.9	256.6	277.5	303.0	334.2
135°	199.4	201.6	208.4	216.9	230.0	237.9	245.8	263.9	283.8	306.4	333.6
137.5°	205.6	208.4	215.2	224.3	237.3	244.6	252.0	270.2	288.9	309.8	333.6
140°	213.0	215.2	222.0	231.1	243.6	251.0	258.3	275.3	292.8	312.1	333.0
142.5°	220.3	222.0	228.3	237.3	249.2	256.0	262.8	279.2	296.2	313.8	333.0
145°	227.7	230.0	235.6	244.1	255.4	261.6	267.9	283.2	299.1	314.9	331.9
147.5°	235.6	237.3	243.0	250.9	260.5	266.2	271.9	286.6	300.8	315.5	330.2
150°	243.6	245.3	249.8	257.1	265.6	270.7	275.8	288.9	301.9	314.9	328.5
152.5°	251.5	252.0	256.6	262.8	270.7	275.2	279.8	291.1	302.5	313.8	325.7
155°	258.8	259.4	262.8	269.0	275.3	279.6	283.8	293.4	303.0	312.7	322.3
157.5°	265.1	265.6	268.5	274.1	279.2	282.9	286.6	295.1	303.0	310.4	318.9
160°	271.3	271.9	274.1	278.7	283.2	286.3	289.4	296.2	303.0	308.7	315.5
162.5°	277.5	277.0	279.2	282.6	286.6	288.8	291.1	296.8	302.5	307.0	312.7
165°	282.1	281.5	282.6	286.0	288.9	290.6	292.3	297.4	301.3	304.7	308.7
167.5°	286.0	285.5	286.6	288.9	291.1	292.2	293.4	297.4	300.8	302.5	305.3
170°	290.0	288.9	289.4	291.1	292.3	293.2	294.0	296.8	299.6	300.8	302.5
172.5°	292.3	291.7	291.1	292.8	293.4	294.0	294.5	296.2	297.9	298.5	299.1
175°	294.0	293.4	292.8	294.0	294.0	294.2	294.5	295.7	296.8	296.2	296.8
177.5°	295.1	294.0	293.4	294.5	294.5	294.5	294.5	295.1	296.2	295.1	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	592.5	593.0	593.9	598.2	600.4	600.9	599.1	603.1	604.4	603.1	602.2
5°	620.6	623.2	628.5	634.2	633.7	634.2	636.8	639.4	640.3	636.8	638.1
7.5°	645.1	650.4	656.1	664.8	664.8	669.2	671.0	673.2	678.4	675.8	674.9
10°	673.2	680.2	690.7	704.7	705.2	709.6	713.9	720.9	723.1	721.4	722.3
12.5°	708.2	721.8	722.7	738.0	745.1	745.9	752.9	751.6	756.0	756.0	763.5
15°	723.6	744.6	756.4	771.3	775.7	770.5	776.2	782.3	782.7	782.7	782.3
17.5°	751.2	759.5	771.3	779.2	781.0	781.0	781.4	784.1	782.3	778.8	781.4
20°	756.9	760.4	764.8	763.9	764.8	760.4	756.0	751.6	752.1	749.9	756.4
22.5°	746.4	745.5	735.4	728.8	728.8	720.1	711.7	707.8	703.9	705.2	707.4
25°	720.1	706.5	694.2	684.6	682.4	668.4	657.0	653.5	646.9	652.1	653.0
27.5°	678.0	662.7	642.9	634.6	623.2	617.5	609.6	599.1	585.5	593.4	592.1
30°	632.9	610.1	593.9	573.7	555.7	554.4	539.5	522.0	515.0	515.0	518.9
32.5°	582.5	552.2	528.5	500.1	482.5	475.1	457.1	439.6	443.5	430.4	435.2
35°	523.7	483.8	454.0	426.4	413.3	404.5	381.3	371.6	361.1	355.0	366.4
37.5°	467.6	421.6	383.5	353.2	348.4	332.6	316.9	310.7	304.6	307.2	306.8
40°	399.3	358.5	324.3	300.7	292.3	284.9	274.4	266.9	263.0	265.2	265.6
42.5°	337.5	303.3	277.9	261.2	254.2	248.9	243.7	237.5	236.2	236.2	238.0
45°	289.7	261.6	244.6	231.0	227.0	223.1	219.1	216.5	215.6	213.9	215.2
47.5°	251.6	229.2	218.7	208.6	204.2	203.4	199.8	198.5	196.8	196.3	196.8
50°	219.6	205.5	195.9	190.2	187.1	185.8	184.1	181.4	180.6	182.8	181.9
52.5°	197.2	184.1	178.8	173.1	171.4	169.6	167.0	167.4	167.0	166.1	166.1
55°	174.9	166.5	161.3	156.9	156.5	154.7	152.5	151.6	151.2	150.3	151.6
57.5°	156.9	150.3	145.5	141.6	139.8	139.8	137.6	135.9	135.9	135.4	135.9
60°	138.9	132.4	129.3	125.3	124.0	123.6	122.3	121.4	120.1	120.1	120.1
62.5°	122.3	117.0	113.5	110.0	110.4	108.3	106.5	105.6	105.6	106.1	106.1
65°	106.5	103.0	98.6	95.5	94.7	94.2	93.4	92.9	91.6	92.5	92.5
67.5°	92.0	87.2	84.6	83.3	82.0	81.5	80.6	79.8	79.3	78.9	79.8
70°	77.6	73.6	71.4	70.6	69.2	68.8	68.4	67.1	67.5	67.9	68.4
72.5°	64.4	60.9	60.5	57.9	57.9	57.9	56.1	57.0	56.5	55.7	56.5
75°	50.8	49.1	48.2	46.9	47.3	46.9	46.5	45.1	45.1	45.6	46.0
77.5°	40.3	38.6	38.1	36.8	35.9	36.8	35.9	35.5	35.5	35.9	35.9
80°	29.8	28.9	27.6	27.6	27.6	27.2	27.2	27.2	26.7	26.3	26.7
82.5°	19.7	19.7	19.3	18.8	19.3	18.4	18.8	18.8	18.8	18.8	18.8
85°	12.7	12.3	12.3	11.8	11.8	11.8	12.3	11.4	11.4	11.8	11.8
87.5°	5.7	5.7	5.7	6.1	5.7	5.7	5.7	6.1	5.7	5.7	5.7
90°	18.7	18.1	17.0	18.1	18.4	18.7	18.7	18.7	18.7	18.7	18.7
92.5°	73.1	57.2	48.7	42.5	40.2	37.9	37.4	35.1	35.7	34.6	35.7
95°	194.3	148.4	113.8	90.1	83.8	77.6	70.2	65.7	64.0	64.6	64.0
97.5°	364.8	303.6	242.4	185.2	168.2	151.2	129.1	117.8	111.6	108.2	111.6
100°	529.0	517.1	446.9	369.3	335.0	300.8	253.7	229.4	213.0	202.8	213.0
102.5°	590.2	657.0	654.8	603.2	566.4	529.6	477.5	431.6	410.1	395.3	410.1
105°	570.4	688.2	752.2	759.5	750.2	740.9	705.7	670.6	646.3	638.3	646.3
107.5°	528.5	654.8	749.9	805.4	816.8	828.1	827.5	822.4	815.1	802.0	815.1
110°	489.4	608.9	710.3	782.8	806.0	829.2	853.6	864.3	869.4	868.9	869.4

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	462.2	567.0	663.3	742.0	769.4	796.9	833.2	853.0	863.8	867.7	863.8
115°	440.7	534.1	621.3	695.5	724.7	753.9	794.1	820.1	834.9	840.0	834.9
117.5°	425.9	506.9	585.1	654.2	682.0	709.7	751.0	778.8	794.1	798.1	794.1
120°	414.6	487.7	557.9	617.9	643.7	669.5	709.1	735.8	752.2	757.8	752.2
122.5°	405.0	472.4	535.2	591.3	614.0	636.6	671.2	697.2	711.4	715.9	711.4
125°	395.9	457.7	516.0	565.8	587.0	608.3	641.2	662.7	676.9	681.4	676.9
127.5°	387.4	442.9	496.7	544.3	564.2	584.0	612.8	633.2	645.7	649.1	645.7
130°	378.9	428.8	477.5	522.2	540.9	559.6	587.4	606.6	617.9	622.5	617.9
132.5°	372.1	415.2	459.4	499.6	516.8	534.1	561.3	580.6	590.8	594.7	590.8
135°	365.9	402.7	440.1	477.5	493.4	509.2	533.6	552.2	562.4	564.7	562.4
137.5°	361.4	392.5	424.8	455.4	469.6	483.7	506.9	523.4	532.4	535.8	532.4
140°	357.4	382.9	410.1	436.1	448.6	461.1	479.2	493.9	502.4	505.8	502.4
142.5°	353.4	375.0	397.0	418.6	428.5	438.4	455.4	468.4	475.8	475.8	475.8
145°	350.0	367.6	386.3	403.8	412.0	420.3	433.9	443.5	449.2	450.9	449.2
147.5°	346.6	361.9	377.2	391.4	397.6	403.8	415.7	423.7	427.6	428.8	427.6
150°	342.1	355.7	368.2	380.1	385.2	390.3	398.7	405.5	408.9	409.5	408.9
152.5°	338.1	349.5	360.8	370.4	374.6	378.9	385.2	390.8	393.1	393.1	393.1
155°	333.0	343.8	352.9	361.4	364.5	367.6	373.8	377.8	380.1	378.9	380.1
157.5°	328.5	337.0	344.9	352.3	354.8	357.4	361.9	365.3	366.5	366.5	366.5
160°	323.4	330.8	337.0	343.2	345.2	347.2	351.2	354.0	354.6	354.6	354.6
162.5°	318.9	324.5	329.6	334.7	336.2	337.6	341.5	343.2	343.8	343.2	343.8
165°	313.8	318.3	322.3	326.2	327.4	328.5	330.8	333.0	333.0	332.5	333.0
167.5°	308.7	312.1	315.5	318.3	319.5	320.6	321.7	322.8	322.8	322.3	322.8
170°	304.7	307.6	309.3	311.5	312.1	312.7	313.2	314.9	314.4	313.2	314.4
172.5°	300.8	302.5	303.6	305.3	305.6	305.9	306.4	307.0	306.4	305.9	306.4
175°	297.4	299.1	299.6	300.2	300.5	300.8	300.8	301.3	300.8	299.6	300.8
177.5°	295.1	296.2	296.2	296.8	296.8	296.8	296.8	296.8	296.2	295.1	296.2
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	604.4	601.3	598.7	599.1	601.3	599.5	595.2	589.5	587.3	584.6	587.3
5°	640.7	638.1	632.9	633.3	632.0	630.2	623.2	614.4	614.4	607.4	606.6
7.5°	676.7	672.7	669.2	668.4	663.5	660.0	653.9	641.6	636.8	628.5	623.7
10°	717.0	713.9	710.0	705.2	702.5	696.4	686.3	668.4	659.6	648.2	639.9
12.5°	757.8	757.3	748.6	738.9	738.5	728.8	721.8	697.7	685.9	670.5	650.8
15°	783.6	781.4	776.6	771.8	773.1	762.6	746.8	718.3	710.4	692.0	671.0
17.5°	783.2	783.2	781.9	781.0	779.7	776.6	767.8	749.0	736.3	713.1	693.3
20°	758.2	763.9	765.2	764.8	769.2	771.3	770.9	759.1	749.0	728.4	708.2
22.5°	708.2	721.4	727.1	730.6	739.8	744.6	756.0	751.6	749.0	733.7	716.6
25°	661.8	666.2	683.3	684.1	696.8	708.7	720.1	727.5	737.2	731.5	717.0
27.5°	601.7	611.8	624.1	633.3	635.9	660.0	678.9	692.9	714.8	716.6	711.7
30°	533.8	538.6	558.8	571.1	585.1	602.6	629.8	653.9	673.6	691.6	697.7
32.5°	451.0	470.7	482.5	497.4	509.7	540.8	574.1	605.2	628.0	658.3	671.4
35°	375.2	390.5	410.7	416.8	439.1	465.4	508.8	548.7	583.3	614.0	640.7
37.5°	312.5	324.8	346.2	355.9	369.0	402.8	439.1	488.7	530.3	568.0	601.3
40°	269.5	278.7	295.0	298.0	309.0	339.7	369.0	415.5	470.7	521.5	557.9
42.5°	240.2	244.6	255.5	259.5	266.5	287.1	313.4	357.2	408.5	461.1	512.3
45°	219.1	222.2	228.8	232.3	241.0	250.2	271.7	306.8	347.1	400.1	455.4
47.5°	200.3	204.2	206.9	209.1	213.9	224.0	238.0	263.8	302.4	351.1	404.5
50°	184.5	185.8	190.6	191.1	194.2	200.7	213.9	229.7	260.3	299.8	351.5
52.5°	168.7	170.0	173.1	176.2	177.5	182.8	191.5	204.7	227.5	258.6	304.6
55°	153.0	154.7	157.8	160.0	161.3	165.7	170.9	183.6	201.6	223.5	261.2
57.5°	137.2	141.1	142.0	143.3	145.5	150.3	155.1	162.6	176.6	196.8	224.4
60°	122.3	123.6	126.7	128.0	130.2	132.8	138.9	144.6	154.7	170.5	195.5
62.5°	106.9	110.0	111.3	112.6	114.4	117.5	121.4	127.5	136.3	149.0	168.7
65°	93.8	94.2	96.9	98.6	100.4	102.6	106.5	112.2	117.5	129.3	143.8
67.5°	81.1	82.0	82.8	84.6	86.8	89.0	92.5	95.5	102.1	110.0	121.4
70°	68.8	68.8	71.0	72.3	71.9	74.5	77.1	80.6	85.5	92.9	102.1
72.5°	57.9	57.4	59.2	59.6	60.5	62.2	64.0	67.5	70.1	75.8	82.8
75°	46.0	46.9	47.8	47.8	49.1	50.4	52.2	53.9	57.0	60.5	65.7
77.5°	36.4	36.4	37.3	37.7	39.0	38.6	40.3	42.1	44.3	47.3	51.3
80°	26.7	27.6	27.6	27.6	28.0	28.5	30.2	31.6	32.9	35.1	36.8
82.5°	18.8	18.8	19.7	19.7	19.7	20.6	20.6	21.0	21.9	23.2	24.5
85°	11.8	11.8	11.8	12.3	11.8	12.3	13.1	12.7	13.1	14.0	14.0
87.5°	5.7	5.7	5.7	5.7	5.7	6.1	5.7	6.1	6.6	6.6	6.6
90°	18.7	18.7	18.7	18.4	18.1	17.0	18.1	18.7	19.3	18.7	15.3
92.5°	35.1	37.4	37.9	40.2	42.5	48.7	57.2	73.1	87.2	86.1	66.8
95°	65.7	70.2	77.6	83.8	90.1	113.8	148.4	194.3	222.0	196.5	130.8
97.5°	117.8	129.1	151.2	168.2	185.2	242.4	303.6	364.8	361.9	279.8	173.9
100°	229.4	253.7	300.8	335.0	369.3	446.9	517.1	529.0	447.5	308.1	185.8
102.5°	431.6	477.5	529.6	566.4	603.2	654.8	657.0	590.2	450.3	297.4	186.3
105°	670.6	705.7	740.9	750.2	759.5	752.2	688.2	570.4	419.7	282.6	189.2
107.5°	822.4	827.5	828.1	816.8	805.4	749.9	654.8	528.5	391.4	274.7	195.4
110°	864.3	853.6	829.2	806.0	782.8	710.3	608.9	489.4	372.1	272.4	203.3

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	853.0	833.2	796.9	769.4	742.0	663.3	567.0	462.2	359.7	273.0	211.8
115°	820.1	794.1	753.9	724.7	695.5	621.3	534.1	440.7	351.2	275.3	220.3
117.5°	778.8	751.0	709.7	682.0	654.2	585.1	506.9	425.9	346.6	278.7	229.4
120°	735.8	709.1	669.5	643.7	617.9	557.9	487.7	414.6	342.7	282.1	238.5
122.5°	697.2	671.2	636.6	614.0	591.3	535.2	472.4	405.0	340.4	286.0	246.4
125°	662.7	641.2	608.3	587.0	565.8	516.0	457.7	395.9	337.6	290.0	254.9
127.5°	633.2	612.8	584.0	564.2	544.3	496.7	442.9	387.4	335.9	294.0	262.8
130°	606.6	587.4	559.6	540.9	522.2	477.5	428.8	378.9	334.7	298.5	270.2
132.5°	580.6	561.3	534.1	516.8	499.6	459.4	415.2	372.1	334.2	303.0	277.5
135°	552.2	533.6	509.2	493.4	477.5	440.1	402.7	365.9	333.6	306.4	283.8
137.5°	523.4	506.9	483.7	469.6	455.4	424.8	392.5	361.4	333.6	309.8	288.9
140°	493.9	479.2	461.1	448.6	436.1	410.1	382.9	357.4	333.0	312.1	292.8
142.5°	468.4	455.4	438.4	428.5	418.6	397.0	375.0	353.4	333.0	313.8	296.2
145°	443.5	433.9	420.3	412.0	403.8	386.3	367.6	350.0	331.9	314.9	299.1
147.5°	423.7	415.7	403.8	397.6	391.4	377.2	361.9	346.6	330.2	315.5	300.8
150°	405.5	398.7	390.3	385.2	380.1	368.2	355.7	342.1	328.5	314.9	301.9
152.5°	390.8	385.2	378.9	374.6	370.4	360.8	349.5	338.1	325.7	313.8	302.5
155°	377.8	373.8	367.6	364.5	361.4	352.9	343.8	333.0	322.3	312.7	303.0
157.5°	365.3	361.9	357.4	354.8	352.3	344.9	337.0	328.5	318.9	310.4	303.0
160°	354.0	351.2	347.2	345.2	343.2	337.0	330.8	323.4	315.5	308.7	303.0
162.5°	343.2	341.5	337.6	336.2	334.7	329.6	324.5	318.9	312.7	307.0	302.5
165°	333.0	330.8	328.5	327.4	326.2	322.3	318.3	313.8	308.7	304.7	301.3
167.5°	322.8	321.7	320.6	319.5	318.3	315.5	312.1	308.7	305.3	302.5	300.8
170°	314.9	313.2	312.7	312.1	311.5	309.3	307.6	304.7	302.5	300.8	299.6
172.5°	307.0	306.4	305.9	305.6	305.3	303.6	302.5	300.8	299.1	298.5	297.9
175°	301.3	300.8	300.8	300.5	300.2	299.6	299.1	297.4	296.8	296.2	296.8
177.5°	296.8	296.8	296.8	296.8	296.8	296.2	296.2	295.1	294.5	295.1	296.2
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	585.1	582.9	581.6	582.5	579.8	573.3	573.3	575.4	572.8	570.2	566.2
5°	601.3	596.9	594.3	593.9	587.7	577.2	575.0	572.8	567.1	561.0	554.4
7.5°	617.1	609.2	604.8	601.7	593.0	579.4	573.7	568.9	559.7	550.5	542.1
10°	630.2	618.8	613.6	608.8	597.4	580.3	571.1	562.3	550.5	538.6	528.1
12.5°	640.7	627.6	621.0	614.0	600.0	577.6	566.2	552.2	540.4	524.6	514.1
15°	658.3	631.1	625.0	618.4	603.9	573.3	559.2	543.4	527.2	506.2	494.8
17.5°	672.3	635.9	635.5	621.5	602.6	571.5	550.0	529.4	511.9	490.9	472.9
20°	680.6	643.4	636.4	621.9	598.2	559.7	537.3	514.5	495.7	470.3	452.3
22.5°	687.6	653.9	635.5	618.0	589.0	555.7	522.9	501.4	475.5	447.9	430.8
25°	690.3	656.1	636.8	616.6	582.5	544.3	507.1	483.8	454.9	429.9	406.7
27.5°	690.7	655.6	632.0	610.9	573.3	529.4	491.3	466.8	434.8	405.8	382.6
30°	686.3	650.8	629.4	606.6	564.5	515.8	472.0	444.8	410.7	381.7	357.6
32.5°	673.2	641.2	623.7	598.7	553.1	497.0	453.6	423.4	387.4	358.9	335.7
35°	651.3	629.4	610.1	586.8	538.2	479.5	435.2	399.7	363.3	336.2	314.2
37.5°	624.1	612.3	594.3	571.5	521.1	463.7	414.6	375.2	338.8	312.5	291.0
40°	587.3	590.3	572.8	552.2	500.9	442.2	387.9	350.2	316.0	291.4	270.4
42.5°	547.4	560.1	550.0	530.3	478.6	418.5	368.1	326.5	293.2	267.8	250.2
45°	504.4	526.4	520.2	505.8	455.4	393.6	340.1	299.8	270.4	245.9	230.5
47.5°	457.5	488.7	488.7	478.1	429.5	368.6	316.0	274.8	245.9	228.3	213.4
50°	409.8	444.8	450.5	443.5	400.6	340.1	286.6	249.4	224.4	207.3	196.3
52.5°	359.8	400.6	411.1	407.6	369.9	312.9	262.5	226.1	203.4	188.5	178.8
55°	312.0	359.4	370.8	372.1	337.0	283.1	235.8	203.8	181.9	171.8	163.5
57.5°	266.9	312.5	325.2	327.4	303.7	255.9	210.8	182.8	163.0	154.7	148.1
60°	228.3	266.5	283.1	287.9	267.3	224.4	187.6	160.4	145.5	137.6	131.5
62.5°	196.8	227.5	245.0	246.3	237.1	196.8	163.5	140.7	128.0	121.0	117.9
65°	166.1	193.7	204.2	209.5	202.0	170.5	141.1	122.3	112.2	106.1	103.0
67.5°	141.6	159.1	167.9	174.9	167.4	143.8	120.1	104.7	97.3	91.2	89.4
70°	116.1	130.6	137.2	144.2	137.6	119.6	102.6	88.5	82.0	77.1	74.9
72.5°	92.9	104.3	110.4	114.8	110.9	96.0	82.0	72.3	67.5	64.0	62.7
75°	73.6	81.5	85.0	88.1	86.3	74.9	66.2	58.3	53.9	50.8	50.0
77.5°	56.1	61.8	65.7	66.6	64.4	57.0	49.5	44.7	41.2	39.4	38.6
80°	39.9	43.4	45.6	46.9	44.7	41.6	36.4	32.9	29.8	27.6	27.2
82.5°	26.7	28.5	30.2	29.8	28.9	26.3	23.2	21.5	20.2	18.4	18.4
85°	15.3	15.8	16.7	17.1	16.7	14.9	13.1	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	3.9
90°	11.3	8.5	7.6	6.8	5.7	4.5	2.3	0.6	2.3	4.5	5.7
92.5°	45.3	30.0	26.9	23.8	19.3	16.4	11.9	8.5	11.9	16.4	19.3
95°	81.6	55.5	48.7	41.9	32.9	27.8	22.1	19.8	22.1	27.8	32.9
97.5°	105.4	71.9	64.2	56.6	46.4	39.1	32.9	29.5	32.9	39.1	46.4
100°	116.7	86.7	78.8	70.8	59.5	50.4	45.3	43.6	45.3	50.4	59.5
102.5°	126.9	99.7	91.8	83.8	71.9	62.9	57.8	56.6	57.8	62.9	71.9
105°	138.8	112.1	104.2	96.3	83.8	75.3	71.4	69.1	71.4	75.3	83.8
107.5°	150.7	124.6	116.6	108.7	96.3	88.4	84.4	82.7	84.4	88.4	96.3
110°	162.6	137.6	129.4	121.2	109.3	102.0	98.6	96.3	98.6	102.0	109.3

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	173.9	150.1	141.6	133.1	121.8	115.0	111.0	108.7	111.0	115.0	121.8
115°	185.8	161.4	153.8	146.1	134.8	128.0	124.6	121.8	124.6	128.0	134.8
117.5°	196.5	173.9	166.0	158.0	147.3	141.0	137.6	135.4	137.6	141.0	147.3
120°	207.9	185.8	177.9	169.9	158.6	153.5	150.1	147.8	150.1	153.5	158.6
122.5°	218.6	198.2	190.0	181.8	170.5	164.8	161.4	159.7	161.4	164.8	170.5
125°	229.4	209.0	201.0	193.1	181.8	175.0	171.6	169.9	171.6	175.0	181.8
127.5°	239.6	219.8	211.6	203.3	192.6	185.2	180.7	178.4	180.7	185.2	192.6
130°	248.7	228.8	220.9	213.0	201.6	193.7	188.0	185.8	188.0	193.7	201.6
132.5°	256.6	237.9	230.0	222.0	210.1	201.6	195.4	192.6	195.4	201.6	210.1
135°	263.9	245.8	237.9	230.0	216.9	208.4	201.6	199.4	201.6	208.4	216.9
137.5°	270.2	252.0	244.6	237.3	224.3	215.2	208.4	205.6	208.4	215.2	224.3
140°	275.3	258.3	251.0	243.6	231.1	222.0	215.2	213.0	215.2	222.0	231.1
142.5°	279.2	262.8	256.0	249.2	237.3	228.3	222.0	220.3	222.0	228.3	237.3
145°	283.2	267.9	261.6	255.4	244.1	235.6	230.0	227.7	230.0	235.6	244.1
147.5°	286.6	271.9	266.2	260.5	250.9	243.0	237.3	235.6	237.3	243.0	250.9
150°	288.9	275.8	270.7	265.6	257.1	249.8	245.3	243.6	245.3	249.8	257.1
152.5°	291.1	279.8	275.2	270.7	262.8	256.6	252.0	251.5	252.0	256.6	262.8
155°	293.4	283.8	279.6	275.3	269.0	262.8	259.4	258.8	259.4	262.8	269.0
157.5°	295.1	286.6	282.9	279.2	274.1	268.5	265.6	265.1	265.6	268.5	274.1
160°	296.2	289.4	286.3	283.2	278.7	274.1	271.9	271.3	271.9	274.1	278.7
162.5°	296.8	291.1	288.8	286.6	282.6	279.2	277.0	277.5	277.0	279.2	282.6
165°	297.4	292.3	290.6	288.9	286.0	282.6	281.5	282.1	281.5	282.6	286.0
167.5°	297.4	293.4	292.2	291.1	288.9	286.6	285.5	286.0	285.5	286.6	288.9
170°	296.8	294.0	293.2	292.3	291.1	289.4	288.9	290.0	288.9	289.4	291.1
172.5°	296.2	294.5	294.0	293.4	292.8	291.1	291.7	292.3	291.7	291.1	292.8
175°	295.7	294.5	294.2	294.0	294.0	292.8	293.4	294.0	293.4	292.8	294.0
177.5°	295.1	294.5	294.5	294.5	294.5	293.4	294.0	295.1	294.0	293.4	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	564.0	566.2	565.8	561.4	556.6	552.7	545.2	546.1	543.4	543.9	546.5
5°	550.0	550.0	548.3	542.1	534.2	529.9	521.5	519.3	514.1	513.6	513.2
7.5°	535.1	532.9	530.7	522.0	512.3	505.3	493.9	491.3	486.0	482.5	480.8
10°	517.6	514.5	510.1	500.1	488.2	479.5	467.6	464.1	454.0	449.7	447.0
12.5°	498.3	496.6	489.5	481.2	461.9	452.3	435.2	438.7	428.6	419.9	418.5
15°	479.0	472.5	468.5	454.9	431.7	427.3	413.7	406.7	397.5	390.5	390.5
17.5°	460.2	450.1	441.3	426.9	409.8	397.5	387.4	383.9	372.5	365.5	364.2
20°	435.2	423.8	421.6	401.0	389.2	375.6	366.0	357.2	348.9	345.8	343.6
22.5°	411.5	398.4	394.9	377.3	365.5	351.9	342.3	336.2	330.0	327.8	323.9
25°	386.1	378.2	373.0	354.1	341.0	328.3	321.7	317.3	311.6	311.2	308.5
27.5°	361.6	354.1	348.9	330.9	321.2	309.4	304.2	299.3	296.3	295.0	293.6
30°	340.5	332.2	326.1	312.9	301.1	291.4	287.1	284.0	282.2	280.1	279.6
32.5°	317.3	312.5	304.2	294.1	284.9	275.7	273.0	270.8	268.2	267.3	266.9
35°	297.6	291.0	285.7	274.4	270.4	262.5	259.5	257.7	254.2	253.3	252.4
37.5°	278.3	272.2	266.5	259.5	252.0	247.6	245.9	243.2	241.5	241.9	241.0
40°	259.0	254.2	249.8	242.4	238.0	235.8	232.3	229.7	228.8	229.2	228.8
42.5°	240.2	235.8	233.2	227.5	223.1	220.9	218.7	216.1	217.4	217.4	218.7
45°	223.1	219.1	217.4	213.0	210.4	206.9	204.7	204.2	206.0	205.5	205.5
47.5°	205.5	204.2	202.0	198.1	194.6	192.4	192.0	192.0	193.7	194.6	194.2
50°	192.0	189.3	186.7	183.6	181.0	180.1	178.8	179.7	181.4	181.4	182.3
52.5°	174.9	173.1	172.2	169.6	167.9	167.9	167.9	168.3	169.6	170.9	170.5
55°	160.0	158.7	157.8	156.5	154.3	154.7	154.3	155.1	156.5	157.8	158.7
57.5°	144.2	143.8	142.9	140.7	140.7	140.2	141.6	142.0	144.2	145.1	146.4
60°	130.2	128.9	128.9	127.1	127.1	127.1	128.4	129.7	131.5	131.9	132.8
62.5°	115.3	115.3	114.8	113.5	113.5	114.8	115.3	117.0	117.9	117.9	119.2
65°	101.2	100.8	100.4	100.8	101.2	101.2	102.6	103.4	104.3	104.7	105.2
67.5°	87.2	86.8	87.7	87.2	88.1	89.8	89.4	90.7	92.0	92.0	92.5
70°	74.1	74.9	74.5	75.4	74.9	75.8	77.1	77.6	77.6	78.0	79.3
72.5°	61.8	61.8	61.8	61.4	61.8	62.7	63.5	64.0	64.9	65.3	66.6
75°	50.0	50.0	49.1	50.0	50.0	50.8	51.7	51.7	51.7	52.6	53.9
77.5°	37.7	38.1	37.7	38.6	38.6	39.0	39.9	39.4	40.3	40.8	41.2
80°	27.6	27.2	27.2	27.2	27.6	27.6	28.5	28.9	28.9	30.2	29.4
82.5°	17.5	18.0	17.5	18.0	18.0	18.4	18.0	18.4	18.8	19.7	19.3
85°	10.1	9.6	9.6	10.1	9.6	9.6	10.1	9.6	10.1	9.6	10.1
87.5°	3.9	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	6.8	7.6	8.5	11.3	15.3	18.7	19.3	18.7	18.1	17.0	18.1
92.5°	23.8	26.9	30.0	45.3	66.8	86.1	87.2	73.1	57.2	48.7	42.5
95°	41.9	48.7	55.5	81.6	130.8	196.5	222.0	194.3	148.4	113.8	90.1
97.5°	56.6	64.2	71.9	105.4	173.9	279.8	361.9	364.8	303.6	242.4	185.2
100°	70.8	78.8	86.7	116.7	185.8	308.1	447.5	529.0	517.1	446.9	369.3
102.5°	83.8	91.8	99.7	126.9	186.3	297.4	450.3	590.2	657.0	654.8	603.2
105°	96.3	104.2	112.1	138.8	189.2	282.6	419.7	570.4	688.2	752.2	759.5
107.5°	108.7	116.6	124.6	150.7	195.4	274.7	391.4	528.5	654.8	749.9	805.4
110°	121.2	129.4	137.6	162.6	203.3	272.4	372.1	489.4	608.9	710.3	782.8

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	133.1	141.6	150.1	173.9	211.8	273.0	359.7	462.2	567.0	663.3	742.0
115°	146.1	153.8	161.4	185.8	220.3	275.3	351.2	440.7	534.1	621.3	695.5
117.5°	158.0	166.0	173.9	196.5	229.4	278.7	346.6	425.9	506.9	585.1	654.2
120°	169.9	177.9	185.8	207.9	238.5	282.1	342.7	414.6	487.7	557.9	617.9
122.5°	181.8	190.0	198.2	218.6	246.4	286.0	340.4	405.0	472.4	535.2	591.3
125°	193.1	201.0	209.0	229.4	254.9	290.0	337.6	395.9	457.7	516.0	565.8
127.5°	203.3	211.6	219.8	239.6	262.8	294.0	335.9	387.4	442.9	496.7	544.3
130°	213.0	220.9	228.8	248.7	270.2	298.5	334.7	378.9	428.8	477.5	522.2
132.5°	222.0	230.0	237.9	256.6	277.5	303.0	334.2	372.1	415.2	459.4	499.6
135°	230.0	237.9	245.8	263.9	283.8	306.4	333.6	365.9	402.7	440.1	477.5
137.5°	237.3	244.6	252.0	270.2	288.9	309.8	333.6	361.4	392.5	424.8	455.4
140°	243.6	251.0	258.3	275.3	292.8	312.1	333.0	357.4	382.9	410.1	436.1
142.5°	249.2	256.0	262.8	279.2	296.2	313.8	333.0	353.4	375.0	397.0	418.6
145°	255.4	261.6	267.9	283.2	299.1	314.9	331.9	350.0	367.6	386.3	403.8
147.5°	260.5	266.2	271.9	286.6	300.8	315.5	330.2	346.6	361.9	377.2	391.4
150°	265.6	270.7	275.8	288.9	301.9	314.9	328.5	342.1	355.7	368.2	380.1
152.5°	270.7	275.2	279.8	291.1	302.5	313.8	325.7	338.1	349.5	360.8	370.4
155°	275.3	279.6	283.8	293.4	303.0	312.7	322.3	333.0	343.8	352.9	361.4
157.5°	279.2	282.9	286.6	295.1	303.0	310.4	318.9	328.5	337.0	344.9	352.3
160°	283.2	286.3	289.4	296.2	303.0	308.7	315.5	323.4	330.8	337.0	343.2
162.5°	286.6	288.8	291.1	296.8	302.5	307.0	312.7	318.9	324.5	329.6	334.7
165°	288.9	290.6	292.3	297.4	301.3	304.7	308.7	313.8	318.3	322.3	326.2
167.5°	291.1	292.2	293.4	297.4	300.8	302.5	305.3	308.7	312.1	315.5	318.3
170°	292.3	293.2	294.0	296.8	299.6	300.8	302.5	304.7	307.6	309.3	311.5
172.5°	293.4	294.0	294.5	296.2	297.9	298.5	299.1	300.8	302.5	303.6	305.3
175°	294.0	294.2	294.5	295.7	296.8	296.2	296.8	297.4	299.1	299.6	300.2
177.5°	294.5	294.5	294.5	295.1	296.2	295.1	294.5	295.1	296.2	296.2	296.8
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	543.4	544.8	541.7	540.8	541.7	538.6	539.5	540.4	540.4	541.7	542.6
5°	511.9	510.1	507.1	506.2	505.3	506.6	505.8	507.1	507.5	510.6	511.0
7.5°	480.8	478.1	475.5	472.9	472.0	469.8	472.0	472.0	475.1	474.2	476.4
10°	444.0	443.5	440.0	438.7	437.0	433.4	438.3	437.0	439.1	443.1	444.0
12.5°	416.8	412.0	414.2	408.0	410.2	406.7	407.1	407.1	410.7	411.1	410.2
15°	390.9	387.0	381.3	378.7	377.3	375.6	381.3	381.7	379.1	385.2	383.0
17.5°	364.6	364.6	359.4	358.1	354.6	356.3	355.4	355.9	355.0	359.4	361.6
20°	341.8	339.7	337.9	338.3	334.0	333.1	332.2	333.1	336.2	339.2	340.1
22.5°	323.4	322.1	317.7	318.6	315.1	316.4	315.6	317.7	318.2	318.2	321.2
25°	305.9	304.2	304.6	302.8	301.5	301.5	300.2	301.5	303.3	304.2	304.6
27.5°	292.8	291.4	289.3	287.9	288.8	286.6	288.4	289.7	289.7	288.8	289.7
30°	277.0	277.9	277.9	273.5	275.2	274.4	275.7	276.5	276.5	277.0	276.1
32.5°	266.5	263.8	263.4	263.0	263.0	261.2	261.2	262.5	263.0	263.4	264.7
35°	252.4	252.4	250.2	251.6	249.8	250.2	249.8	250.2	251.1	249.8	251.1
37.5°	239.7	240.2	239.3	240.2	240.6	239.7	238.9	240.6	239.7	239.7	238.9
40°	228.8	228.3	228.8	228.8	228.8	229.2	228.3	228.3	228.3	227.5	226.6
42.5°	219.6	216.9	217.8	218.3	216.9	216.9	217.4	216.9	218.3	215.6	215.6
45°	206.4	205.5	206.0	206.0	206.9	205.5	206.4	206.9	205.5	205.1	204.2
47.5°	194.6	195.5	194.6	195.5	195.5	196.3	194.6	195.0	195.5	193.7	192.4
50°	182.8	182.8	184.1	183.6	184.1	183.2	183.2	182.8	183.2	182.3	181.0
52.5°	171.8	170.5	172.7	172.2	171.8	171.4	170.9	171.4	170.5	169.6	169.6
55°	158.2	158.2	159.5	160.0	160.0	159.1	158.2	158.7	158.2	157.8	157.3
57.5°	147.3	145.5	146.4	146.8	146.8	145.5	146.4	145.5	145.5	145.9	144.6
60°	133.2	133.2	132.4	133.7	133.7	132.8	132.8	133.2	132.4	131.9	131.5
62.5°	118.3	118.8	120.1	120.5	121.0	120.1	119.2	119.6	119.6	118.3	118.8
65°	105.6	106.5	108.3	107.8	106.9	107.4	106.5	106.9	105.6	106.1	104.7
67.5°	93.4	92.9	93.4	93.4	94.2	93.8	92.9	92.9	92.5	93.8	92.5
70°	80.2	80.2	80.2	80.2	80.6	81.1	80.2	79.3	79.8	78.9	78.4
72.5°	66.6	67.1	66.6	67.5	66.2	67.1	67.1	66.6	66.2	66.2	66.2
75°	53.9	54.8	53.5	53.9	53.5	54.3	53.9	53.9	53.0	52.6	53.0
77.5°	41.2	41.6	40.8	41.2	40.8	41.2	41.2	40.8	40.8	40.8	40.8
80°	29.4	29.8	29.4	28.9	28.5	29.4	28.5	28.9	29.4	28.9	29.8
82.5°	18.8	18.8	18.4	18.8	18.0	18.0	18.4	18.4	18.0	18.8	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.6	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	18.4	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.4
92.5°	40.2	37.9	37.4	35.1	35.7	34.6	35.7	35.1	37.4	37.9	40.2
95°	83.8	77.6	70.2	65.7	64.0	64.6	64.0	65.7	70.2	77.6	83.8
97.5°	168.2	151.2	129.1	117.8	111.6	108.2	111.6	117.8	129.1	151.2	168.2
100°	335.0	300.8	253.7	229.4	213.0	202.8	213.0	229.4	253.7	300.8	335.0
102.5°	566.4	529.6	477.5	431.6	410.1	395.3	410.1	431.6	477.5	529.6	566.4
105°	750.2	740.9	705.7	670.6	646.3	638.3	646.3	670.6	705.7	740.9	750.2
107.5°	816.8	828.1	827.5	822.4	815.1	802.0	815.1	822.4	827.5	828.1	816.8
110°	806.0	829.2	853.6	864.3	869.4	868.9	869.4	864.3	853.6	829.2	806.0

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	769.4	796.9	833.2	853.0	863.8	867.7	863.8	853.0	833.2	796.9	769.4
115°	724.7	753.9	794.1	820.1	834.9	840.0	834.9	820.1	794.1	753.9	724.7
117.5°	682.0	709.7	751.0	778.8	794.1	798.1	794.1	778.8	751.0	709.7	682.0
120°	643.7	669.5	709.1	735.8	752.2	757.8	752.2	735.8	709.1	669.5	643.7
122.5°	614.0	636.6	671.2	697.2	711.4	715.9	711.4	697.2	671.2	636.6	614.0
125°	587.0	608.3	641.2	662.7	676.9	681.4	676.9	662.7	641.2	608.3	587.0
127.5°	564.2	584.0	612.8	633.2	645.7	649.1	645.7	633.2	612.8	584.0	564.2
130°	540.9	559.6	587.4	606.6	617.9	622.5	617.9	606.6	587.4	559.6	540.9
132.5°	516.8	534.1	561.3	580.6	590.8	594.7	590.8	580.6	561.3	534.1	516.8
135°	493.4	509.2	533.6	552.2	562.4	564.7	562.4	552.2	533.6	509.2	493.4
137.5°	469.6	483.7	506.9	523.4	532.4	535.8	532.4	523.4	506.9	483.7	469.6
140°	448.6	461.1	479.2	493.9	502.4	505.8	502.4	493.9	479.2	461.1	448.6
142.5°	428.5	438.4	455.4	468.4	475.8	475.8	475.8	468.4	455.4	438.4	428.5
145°	412.0	420.3	433.9	443.5	449.2	450.9	449.2	443.5	433.9	420.3	412.0
147.5°	397.6	403.8	415.7	423.7	427.6	428.8	427.6	423.7	415.7	403.8	397.6
150°	385.2	390.3	398.7	405.5	408.9	409.5	408.9	405.5	398.7	390.3	385.2
152.5°	374.6	378.9	385.2	390.8	393.1	393.1	393.1	390.8	385.2	378.9	374.6
155°	364.5	367.6	373.8	377.8	380.1	378.9	380.1	377.8	373.8	367.6	364.5
157.5°	354.8	357.4	361.9	365.3	366.5	366.5	366.5	365.3	361.9	357.4	354.8
160°	345.2	347.2	351.2	354.0	354.6	354.6	354.6	354.0	351.2	347.2	345.2
162.5°	336.2	337.6	341.5	343.2	343.8	343.2	343.8	343.2	341.5	337.6	336.2
165°	327.4	328.5	330.8	333.0	333.0	332.5	333.0	333.0	330.8	328.5	327.4
167.5°	319.5	320.6	321.7	322.8	322.8	322.3	322.8	322.8	321.7	320.6	319.5
170°	312.1	312.7	313.2	314.9	314.4	313.2	314.4	314.9	313.2	312.7	312.1
172.5°	305.6	305.9	306.4	307.0	306.4	305.9	306.4	307.0	306.4	305.9	305.6
175°	300.5	300.8	300.8	301.3	300.8	299.6	300.8	301.3	300.8	300.8	300.5
177.5°	296.8	296.8	296.8	296.8	296.2	295.1	296.2	296.8	296.8	296.8	296.8
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	541.3	544.8	543.4	538.6	544.3	544.3	548.3	548.3	553.1	554.8	557.5
5°	510.6	513.2	515.4	513.2	517.2	523.3	526.8	529.9	536.4	539.1	543.0
7.5°	477.7	482.5	484.7	484.7	491.3	498.3	505.3	509.7	518.9	522.4	526.4
10°	445.7	451.4	455.8	455.4	466.3	470.7	479.5	489.5	498.7	504.0	509.7
12.5°	412.0	415.0	421.2	429.9	432.6	440.5	450.5	463.2	479.9	484.7	493.0
15°	383.9	392.2	397.1	401.0	407.1	414.6	425.6	437.8	454.5	465.0	473.8
17.5°	360.3	371.2	374.3	373.4	381.3	392.7	405.4	414.6	429.5	442.2	450.5
20°	341.0	345.4	350.6	352.8	358.9	371.2	383.5	394.0	406.3	416.4	426.0
22.5°	321.7	325.2	329.6	333.5	338.3	345.4	357.2	370.3	382.2	391.8	402.8
25°	305.9	308.1	312.0	315.1	320.4	325.2	333.5	348.0	362.0	367.7	377.3
27.5°	290.6	292.3	295.0	298.5	301.1	305.9	313.4	325.2	339.7	345.4	358.5
30°	277.0	278.3	280.9	282.7	284.0	289.7	295.4	304.6	315.6	323.4	333.1
32.5°	264.3	265.6	268.2	268.7	270.4	273.5	278.7	287.1	296.7	303.3	311.6
35°	250.2	251.1	253.8	254.6	255.9	258.6	262.5	268.7	277.4	282.2	289.7
37.5°	239.3	238.9	240.6	241.9	243.7	245.0	246.3	252.4	259.0	263.4	269.1
40°	227.5	226.6	227.0	228.8	229.7	231.4	231.4	237.5	241.9	245.4	249.8
42.5°	215.6	215.2	214.3	215.2	216.1	216.5	216.9	221.3	225.7	228.8	233.6
45°	203.8	203.4	202.5	202.9	202.9	203.8	205.1	206.9	209.9	212.6	215.2
47.5°	192.8	192.0	190.6	190.2	191.1	191.1	191.1	192.8	195.9	196.8	199.4
50°	181.4	180.1	178.4	177.5	177.5	177.1	177.9	178.4	181.0	181.9	184.1
52.5°	169.2	168.3	166.5	164.8	165.2	164.3	164.8	165.2	166.1	167.4	168.7
55°	156.9	155.1	153.8	153.4	152.1	152.1	150.8	152.5	152.1	152.5	154.3
57.5°	145.1	143.3	141.1	140.2	138.9	138.5	137.6	137.2	137.6	138.9	140.2
60°	131.0	130.2	128.9	127.5	126.7	125.3	124.5	124.5	124.0	124.0	124.5
62.5°	117.5	117.0	115.3	114.8	113.9	113.1	111.8	110.9	110.9	111.8	112.2
65°	104.3	103.9	102.6	102.1	99.9	99.0	98.6	98.2	97.3	97.3	97.3
67.5°	92.0	90.7	90.7	88.5	86.8	85.9	85.0	84.6	84.6	84.6	85.0
70°	78.4	78.4	77.1	75.8	74.1	74.5	73.2	71.9	71.9	71.0	71.4
72.5°	65.3	64.9	63.5	63.1	61.8	60.5	59.6	60.5	59.2	58.7	59.2
75°	52.6	52.2	51.3	50.4	50.8	49.5	48.2	47.8	47.8	46.9	46.9
77.5°	40.3	41.2	39.4	39.0	38.1	37.3	36.8	36.4	36.4	36.4	37.3
80°	28.0	28.5	28.5	27.6	28.0	26.7	26.7	26.7	25.4	25.9	26.3
82.5°	18.0	18.0	17.5	18.0	17.5	17.5	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.6	9.2	10.1	9.6	9.6	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	18.1	17.0	18.1	18.7	19.3	18.7	15.3	11.3	8.5	7.6	6.8
92.5°	42.5	48.7	57.2	73.1	87.2	86.1	66.8	45.3	30.0	26.9	23.8
95°	90.1	113.8	148.4	194.3	222.0	196.5	130.8	81.6	55.5	48.7	41.9
97.5°	185.2	242.4	303.6	364.8	361.9	279.8	173.9	105.4	71.9	64.2	56.6
100°	369.3	446.9	517.1	529.0	447.5	308.1	185.8	116.7	86.7	78.8	70.8
102.5°	603.2	654.8	657.0	590.2	450.3	297.4	186.3	126.9	99.7	91.8	83.8
105°	759.5	752.2	688.2	570.4	419.7	282.6	189.2	138.8	112.1	104.2	96.3
107.5°	805.4	749.9	654.8	528.5	391.4	274.7	195.4	150.7	124.6	116.6	108.7
110°	782.8	710.3	608.9	489.4	372.1	272.4	203.3	162.6	137.6	129.4	121.2

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	742.0	663.3	567.0	462.2	359.7	273.0	211.8	173.9	150.1	141.6	133.1
115°	695.5	621.3	534.1	440.7	351.2	275.3	220.3	185.8	161.4	153.8	146.1
117.5°	654.2	585.1	506.9	425.9	346.6	278.7	229.4	196.5	173.9	166.0	158.0
120°	617.9	557.9	487.7	414.6	342.7	282.1	238.5	207.9	185.8	177.9	169.9
122.5°	591.3	535.2	472.4	405.0	340.4	286.0	246.4	218.6	198.2	190.0	181.8
125°	565.8	516.0	457.7	395.9	337.6	290.0	254.9	229.4	209.0	201.0	193.1
127.5°	544.3	496.7	442.9	387.4	335.9	294.0	262.8	239.6	219.8	211.6	203.3
130°	522.2	477.5	428.8	378.9	334.7	298.5	270.2	248.7	228.8	220.9	213.0
132.5°	499.6	459.4	415.2	372.1	334.2	303.0	277.5	256.6	237.9	230.0	222.0
135°	477.5	440.1	402.7	365.9	333.6	306.4	283.8	263.9	245.8	237.9	230.0
137.5°	455.4	424.8	392.5	361.4	333.6	309.8	288.9	270.2	252.0	244.6	237.3
140°	436.1	410.1	382.9	357.4	333.0	312.1	292.8	275.3	258.3	251.0	243.6
142.5°	418.6	397.0	375.0	353.4	333.0	313.8	296.2	279.2	262.8	256.0	249.2
145°	403.8	386.3	367.6	350.0	331.9	314.9	299.1	283.2	267.9	261.6	255.4
147.5°	391.4	377.2	361.9	346.6	330.2	315.5	300.8	286.6	271.9	266.2	260.5
150°	380.1	368.2	355.7	342.1	328.5	314.9	301.9	288.9	275.8	270.7	265.6
152.5°	370.4	360.8	349.5	338.1	325.7	313.8	302.5	291.1	279.8	275.2	270.7
155°	361.4	352.9	343.8	333.0	322.3	312.7	303.0	293.4	283.8	279.6	275.3
157.5°	352.3	344.9	337.0	328.5	318.9	310.4	303.0	295.1	286.6	282.9	279.2
160°	343.2	337.0	330.8	323.4	315.5	308.7	303.0	296.2	289.4	286.3	283.2
162.5°	334.7	329.6	324.5	318.9	312.7	307.0	302.5	296.8	291.1	288.8	286.6
165°	326.2	322.3	318.3	313.8	308.7	304.7	301.3	297.4	292.3	290.6	288.9
167.5°	318.3	315.5	312.1	308.7	305.3	302.5	300.8	297.4	293.4	292.2	291.1
170°	311.5	309.3	307.6	304.7	302.5	300.8	299.6	296.8	294.0	293.2	292.3
172.5°	305.3	303.6	302.5	300.8	299.1	298.5	297.9	296.2	294.5	294.0	293.4
175°	300.2	299.6	299.1	297.4	296.8	296.2	296.8	295.7	294.5	294.2	294.0
177.5°	296.8	296.2	296.2	295.1	294.5	295.1	296.2	295.1	294.5	294.5	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	570.2	570.2	570.2	570.2
2.5°	559.7	559.7	566.2	573.3
5°	547.4	550.5	561.0	570.6
7.5°	535.6	540.8	554.0	566.2
10°	521.1	528.1	544.3	558.8
12.5°	507.1	513.6	532.5	548.7
15°	487.4	495.7	515.8	536.0
17.5°	467.6	476.0	500.5	524.2
20°	444.4	455.4	483.0	514.5
22.5°	422.9	436.5	467.2	492.6
25°	399.3	420.3	448.8	481.7
27.5°	378.2	399.3	428.2	461.5
30°	354.6	376.0	405.8	436.5
32.5°	331.8	351.5	380.4	418.1
35°	308.1	326.9	355.0	393.1
37.5°	286.6	305.0	335.7	370.8
40°	265.6	284.9	311.2	346.2
42.5°	245.9	263.0	286.6	321.7
45°	227.9	240.2	262.1	295.0
47.5°	209.1	220.0	240.2	273.0
50°	191.5	200.7	218.3	248.9
52.5°	174.4	182.3	198.5	223.1
55°	159.1	166.5	178.4	202.5
57.5°	143.3	149.0	160.4	179.7
60°	128.0	133.2	142.4	158.2
62.5°	112.6	117.0	125.8	138.5
65°	99.0	102.6	109.1	120.1
67.5°	85.9	88.1	93.4	102.1
70°	73.2	74.9	79.3	86.3
72.5°	59.6	61.4	66.2	71.0
75°	48.2	48.6	52.2	56.1
77.5°	37.7	37.3	39.9	43.0
80°	25.9	27.2	29.4	30.7
82.5°	17.5	18.0	18.8	19.7
85°	9.6	10.1	10.1	11.4
87.5°	3.9	4.4	4.4	4.8
90°	5.7	4.5	2.3	0.6
92.5°	19.3	16.4	11.9	8.5
95°	32.9	27.8	22.1	19.8
97.5°	46.4	39.1	32.9	29.5
100°	59.5	50.4	45.3	43.6
102.5°	71.9	62.9	57.8	56.6
105°	83.8	75.3	71.4	69.1
107.5°	96.3	88.4	84.4	82.7
110°	109.3	102.0	98.6	96.3

TEST NUMBER: P1008855

CATALOG NUMBER: S122DIP-B290D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	121.8	115.0	111.0	108.7
115°	134.8	128.0	124.6	121.8
117.5°	147.3	141.0	137.6	135.4
120°	158.6	153.5	150.1	147.8
122.5°	170.5	164.8	161.4	159.7
125°	181.8	175.0	171.6	169.9
127.5°	192.6	185.2	180.7	178.4
130°	201.6	193.7	188.0	185.8
132.5°	210.1	201.6	195.4	192.6
135°	216.9	208.4	201.6	199.4
137.5°	224.3	215.2	208.4	205.6
140°	231.1	222.0	215.2	213.0
142.5°	237.3	228.3	222.0	220.3
145°	244.1	235.6	230.0	227.7
147.5°	250.9	243.0	237.3	235.6
150°	257.1	249.8	245.3	243.6
152.5°	262.8	256.6	252.0	251.5
155°	269.0	262.8	259.4	258.8
157.5°	274.1	268.5	265.6	265.1
160°	278.7	274.1	271.9	271.3
162.5°	282.6	279.2	277.0	277.5
165°	286.0	282.6	281.5	282.1
167.5°	288.9	286.6	285.5	286.0
170°	291.1	289.4	288.9	290.0
172.5°	292.8	291.1	291.7	292.3
175°	294.0	292.8	293.4	294.0
177.5°	294.5	293.4	294.0	295.1
180°	294.5	294.5	294.5	294.5

(END OF REPORT)