

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008918

Luminaire Tested: S122DIP-B290D725UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008918
REPORT IS A COMBINATION OF REPORTS P984033 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB35-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4054.0 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25
4	72	62	54	48	64	56	49	44	45	40	37	35	31	29	25	23	22
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19
6	61	49	42	36	54	45	38	33	36	31	28	28	25	22	21	19	17
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	23	20	18	17	15	14
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9148	9148	9148	9148
5°	9169	9753	9205	7760
10°	9062	10647	9120	6398
15°	8843	11230	8966	5389
20°	8706	10545	8706	4684
25°	8428	9060	8466	4189
30°	7971	7121	8124	3794
35°	7566	4924	7693	3471
40°	7102	3717	7183	3214
45°	6528	3056	6635	2936
50°	6033	2681	6043	2688
55°	5468	2286	5502	2418
60°	4867	1908	4934	2111
65°	4326	1552	4405	1802
70°	3789	1217	3885	1454
75°	3183	884	3306	1055
80°	2483	561	2659	626
85°	1624	282	1752	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9457 cd/sqm

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	1.4
10°-20°	160.2	4.0
20°-30°	232.5	5.7
30°-40°	245.1	6.0
40°-50°	216.9	5.4
50°-60°	173.2	4.3
60°-70°	117.6	2.9
70°-80°	60.2	1.5
80°-90°	16.8	0.4
90°-100°	155.4	3.8
100°-110°	547.3	13.5
110°-120°	574.8	14.2
120°-130°	472.9	11.7
130°-140°	379.9	9.4
140°-150°	287.0	7.1
150°-160°	201.7	5.0
160°-170°	118.8	2.9
170°-180°	38.6	1.0
0°-30°	447.8	11.0
0°-40°	692.9	17.1
0°-60°	1083.0	26.7
0°-90°	1277.6	31.5
90°-120°	1277.5	31.5
90°-150°	2417.3	59.6
90°-180°	2776.0	68.5
0°-180°	4054.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	578	578	578	578	578	
5°	578	645	581	514	578	55
15°	543	793	551	381	543	153
25°	488	661	490	306	488	223
35°	398	360	405	254	398	249
45°	299	217	304	208	299	232
55°	205	152	206	161	205	183
65°	122	94	124	109	122	121
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	25	1	25	1	2
95°	27	87	27	87	27	28
105°	94	864	94	864	94	99
115°	165	1137	165	1137	165	163
125°	230	922	230	922	230	204
135°	270	764	270	764	270	208
145°	308	610	308	610	308	193
155°	350	513	350	513	350	161
165°	382	450	382	450	382	108
175°	398	406	398	406	398	38
180°	399	399	399	399	399	

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	581.0	582.3	584.6	585.0	589.4	593.0	597.0	597.0	598.3	597.9	594.3
5°	578.3	582.3	588.1	593.0	601.0	604.5	609.9	613.9	617.4	620.1	619.6
7.5°	573.9	581.0	589.4	598.8	609.4	615.6	623.2	630.3	635.2	639.6	642.7
10°	566.3	578.3	589.9	602.3	616.1	624.5	633.4	642.7	650.3	658.7	666.7
12.5°	556.1	573.4	587.7	604.1	621.0	630.3	644.5	651.6	666.3	687.6	693.4
15°	543.2	566.8	580.1	601.0	623.2	630.7	650.3	661.8	692.0	705.4	721.4
17.5°	531.2	557.5	575.2	599.2	621.0	635.6	654.7	678.3	703.6	722.7	740.5
20°	521.5	546.8	568.1	594.8	622.3	641.0	661.0	689.4	716.9	736.5	750.2
22.5°	499.3	531.7	556.6	586.3	619.6	645.4	664.5	695.6	725.4	737.4	749.3
25°	488.2	516.1	545.0	578.8	617.9	648.5	665.0	699.6	725.8	730.2	732.9
27.5°	467.7	499.3	533.0	571.7	617.4	643.2	664.1	695.6	716.5	713.4	705.4
30°	442.4	481.1	518.4	560.1	611.2	639.2	658.7	687.6	698.3	682.3	668.1
32.5°	423.8	460.2	501.5	549.9	604.1	630.7	649.8	672.5	674.7	645.9	621.9
35°	398.4	438.9	485.5	536.6	592.1	616.1	633.9	647.6	637.0	596.5	568.1
37.5°	375.8	415.8	465.5	517.5	575.7	599.2	613.4	615.6	589.4	553.9	512.1
40°	350.9	392.2	444.2	498.8	557.5	577.9	586.8	580.1	542.4	501.0	452.6
42.5°	326.0	366.9	422.9	478.8	534.4	551.7	555.2	537.0	490.8	442.4	386.4
45°	298.9	341.6	397.5	454.0	507.7	517.5	517.9	491.7	437.1	386.4	334.5
47.5°	276.7	316.3	371.8	428.2	473.5	480.2	477.5	447.3	387.8	330.9	285.6
50°	252.3	290.1	345.1	400.7	439.3	441.1	434.4	391.3	333.1	281.2	245.2
52.5°	226.1	264.3	314.9	368.2	402.9	400.2	387.3	341.1	286.5	243.4	215.9
55°	205.2	239.0	286.5	338.5	362.9	355.4	341.1	294.1	251.0	214.5	190.6
57.5°	182.1	211.9	258.5	303.8	318.0	310.9	296.7	252.7	212.8	185.2	169.2
60°	160.4	187.4	228.3	266.1	277.2	269.6	253.2	213.7	184.8	161.7	149.7
62.5°	140.4	163.9	198.1	232.8	237.2	229.6	215.4	183.4	158.6	140.4	131.5
65°	121.7	143.9	171.5	197.7	201.7	193.7	179.0	155.9	135.0	123.5	115.0
67.5°	103.5	121.3	145.7	164.8	167.0	159.5	147.5	128.8	115.9	103.5	97.3
70°	87.5	100.8	119.9	135.5	136.4	129.3	123.0	106.2	96.4	87.5	82.6
72.5°	72.0	81.3	95.9	107.5	107.9	103.5	97.7	87.1	78.6	72.4	67.5
75°	56.9	64.9	73.7	84.0	83.5	80.0	75.5	68.8	61.7	57.7	55.5
77.5°	43.5	48.4	55.5	62.2	62.2	60.4	57.7	52.9	48.4	44.4	42.2
80°	31.1	34.2	40.0	42.2	43.1	42.6	40.4	36.9	35.1	32.0	31.1
82.5°	20.0	22.2	24.9	27.1	28.4	27.5	27.1	25.3	22.7	21.8	20.9
85°	11.5	12.4	13.8	15.1	15.5	15.1	16.0	14.7	13.3	13.3	12.9
87.5°	4.9	5.3	6.2	6.2	6.7	6.7	6.2	6.7	6.7	6.2	5.8
90°	0.8	3.1	6.1	7.7	9.2	10.4	11.5	15.3	20.7	25.3	26.1
92.5°	11.5	16.1	22.2	26.1	32.2	36.4	40.6	61.3	90.5	116.5	118.1
95°	26.8	29.9	37.6	44.5	56.7	65.9	75.1	110.4	177.1	266.0	300.5
97.5°	39.9	44.5	52.9	62.9	76.7	87.1	97.4	142.6	235.4	378.7	489.9
100°	59.0	61.3	68.2	80.5	95.8	106.6	117.3	157.9	251.5	417.1	605.7
102.5°	76.7	78.2	85.1	97.4	113.5	124.2	134.9	171.7	252.2	402.5	609.5
105°	93.5	96.6	102.0	113.5	130.3	141.0	151.8	187.8	256.1	382.6	568.1
107.5°	111.9	114.2	119.6	130.3	147.2	158.0	168.7	203.9	264.5	371.8	529.8
110°	130.3	133.4	138.0	148.0	164.1	175.2	186.3	220.0	275.2	368.8	503.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	147.2	150.3	155.6	164.8	180.2	191.7	203.2	235.4	286.7	369.5	486.9
115°	164.8	168.7	173.3	182.5	197.8	208.2	218.5	251.5	298.2	372.6	475.4
117.5°	183.2	186.3	190.9	199.3	213.9	224.6	235.4	266.0	310.5	377.2	469.2
120°	200.1	203.2	207.8	214.7	230.0	240.8	251.5	281.4	322.8	381.8	463.9
122.5°	216.2	218.5	223.1	230.8	246.1	257.2	268.3	295.9	333.5	387.2	460.8
125°	230.0	232.3	236.9	246.1	261.4	272.2	282.9	310.5	345.0	392.5	457.0
127.5°	241.5	244.6	250.7	260.7	275.2	286.4	297.5	324.3	355.7	397.9	454.7
130°	251.5	254.5	262.2	272.9	288.3	299.0	309.7	336.6	365.7	404.0	453.1
132.5°	260.7	264.5	272.9	284.4	300.5	311.2	322.0	347.3	375.7	410.2	452.4
135°	269.9	272.9	282.1	293.6	311.3	322.0	332.7	357.3	384.1	414.8	451.6
137.5°	278.3	282.1	291.3	303.6	321.2	331.2	341.2	365.7	391.0	419.4	451.6
140°	288.3	291.3	300.5	312.8	329.7	339.6	349.6	372.6	396.4	422.5	450.8
142.5°	298.2	300.5	309.0	321.2	337.3	346.5	355.7	378.0	401.0	424.8	450.8
145°	308.2	311.3	318.9	330.4	345.8	354.2	362.6	383.3	404.8	426.3	449.3
147.5°	318.9	321.2	328.9	339.6	352.7	360.4	368.0	387.9	407.1	427.1	447.0
150°	329.7	332.0	338.1	348.1	359.6	366.5	373.4	391.0	408.6	426.3	444.7
152.5°	340.4	341.2	347.3	355.7	366.5	372.6	378.7	394.1	409.4	424.8	440.9
155°	350.4	351.1	355.7	364.2	372.6	378.4	384.1	397.1	410.2	423.2	436.3
157.5°	358.8	359.6	363.4	371.1	378.0	383.0	387.9	399.4	410.2	420.2	431.7
160°	367.2	368.0	371.1	377.2	383.3	387.6	391.8	401.0	410.2	417.9	427.1
162.5°	375.7	374.9	378.0	382.6	387.9	391.0	394.1	401.7	409.4	415.6	423.2
165°	381.8	381.0	382.6	387.2	391.0	393.3	395.6	402.5	407.9	412.5	417.9
167.5°	387.2	386.4	387.9	391.0	394.1	395.6	397.1	402.5	407.1	409.4	413.3
170°	392.5	391.0	391.8	394.1	395.6	396.8	397.9	401.7	405.6	407.1	409.4
172.5°	395.6	394.8	394.1	396.4	397.1	397.9	398.7	401.0	403.3	404.0	404.8
175°	397.9	397.1	396.4	397.9	397.9	398.3	398.7	400.2	401.7	401.0	401.7
177.5°	399.4	397.9	397.1	398.7	398.7	398.7	398.7	399.4	401.0	399.4	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	600.5	601.0	601.9	606.3	608.5	609.0	607.2	611.2	612.5	611.2	610.3
5°	629.0	631.6	637.0	642.7	642.3	642.7	645.4	648.1	649.0	645.4	646.7
7.5°	653.8	659.2	665.0	673.8	673.8	678.3	680.1	682.3	687.6	684.9	684.1
10°	682.3	689.4	700.0	714.3	714.7	719.1	723.6	730.7	732.9	731.1	732.0
12.5°	717.8	731.6	732.5	748.0	755.1	756.0	763.1	761.8	766.2	766.2	773.8
15°	733.4	754.7	766.7	781.8	786.2	780.9	786.7	792.9	793.3	793.3	792.9
17.5°	761.3	769.8	781.8	789.8	791.5	791.5	792.0	794.7	792.9	789.3	792.0
20°	767.1	770.7	775.1	774.2	775.1	770.7	766.2	761.8	762.2	760.0	766.7
22.5°	756.5	755.6	745.3	738.7	738.7	729.8	721.4	717.4	713.4	714.7	716.9
25°	729.8	716.0	703.6	693.8	691.6	677.4	665.8	662.3	655.6	661.0	661.8
27.5°	687.2	671.6	651.6	643.2	631.6	625.9	617.9	607.2	593.4	601.4	600.1
30°	641.4	618.3	601.9	581.4	563.2	561.9	546.8	529.0	521.9	521.9	525.9
32.5°	590.3	559.7	535.7	506.8	489.1	481.5	463.3	445.5	449.5	436.2	441.1
35°	530.8	490.4	460.2	432.2	418.9	410.0	386.4	376.7	366.0	359.8	371.3
37.5°	473.9	427.3	388.7	358.0	353.1	337.1	321.1	314.9	308.7	311.4	310.9
40°	404.7	363.3	328.7	304.7	296.3	288.7	278.1	270.5	266.5	268.7	269.2
42.5°	342.0	307.4	281.6	264.7	257.6	252.3	247.0	240.8	239.4	239.4	241.2
45°	293.6	265.2	247.9	234.1	230.1	226.1	222.1	219.4	218.5	216.8	218.1
47.5°	255.0	232.3	221.7	211.4	207.0	206.1	202.6	201.2	199.4	199.0	199.4
50°	222.5	208.3	198.6	192.8	189.7	188.3	186.6	183.9	183.0	185.2	184.3
52.5°	199.9	186.6	181.2	175.5	173.7	171.9	169.2	169.7	169.2	168.3	168.3
55°	177.2	168.8	163.5	159.0	158.6	156.8	154.6	153.7	153.2	152.4	153.7
57.5°	159.0	152.4	147.5	143.5	141.7	141.7	139.5	137.7	137.7	137.3	137.7
60°	140.8	134.1	131.0	127.0	125.7	125.3	123.9	123.0	121.7	121.7	121.7
62.5°	123.9	118.6	115.0	111.5	111.9	109.7	107.9	107.0	107.0	107.5	107.5
65°	107.9	104.4	99.9	96.8	95.9	95.5	94.6	94.2	92.8	93.7	93.7
67.5°	93.3	88.4	85.7	84.4	83.1	82.6	81.7	80.8	80.4	80.0	80.8
70°	78.6	74.6	72.4	71.5	70.2	69.7	69.3	68.0	68.4	68.8	69.3
72.5°	65.3	61.7	61.3	58.6	58.6	58.6	56.9	57.7	57.3	56.4	57.3
75°	51.5	49.7	48.9	47.5	48.0	47.5	47.1	45.8	45.8	46.2	46.6
77.5°	40.9	39.1	38.6	37.3	36.4	37.3	36.4	36.0	36.0	36.4	36.4
80°	30.2	29.3	28.0	28.0	28.0	27.5	27.5	27.5	27.1	26.7	27.1
82.5°	20.0	20.0	19.5	19.1	19.5	18.7	19.1	19.1	19.1	19.1	19.1
85°	12.9	12.4	12.4	12.0	12.0	12.0	12.4	11.5	11.5	12.0	12.0
87.5°	5.8	5.8	5.8	6.2	5.8	5.8	5.8	6.2	5.8	5.8	5.8
90°	25.3	24.5	23.0	24.5	24.9	25.3	25.3	25.3	25.3	25.3	25.3
92.5°	98.9	77.4	65.9	57.5	54.4	51.4	50.6	47.5	48.3	46.8	48.3
95°	263.0	200.9	154.1	121.9	113.4	105.0	95.1	88.9	86.6	87.4	86.6
97.5°	493.8	410.9	328.1	250.7	227.7	204.7	174.8	159.5	151.0	146.4	151.0
100°	716.1	700.0	604.9	499.9	453.5	407.1	343.5	310.5	288.3	274.5	288.3
102.5°	798.9	889.4	886.3	816.5	766.7	716.9	646.3	584.2	555.1	535.2	555.1
105°	772.1	931.5	1018.2	1028.1	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8
107.5°	715.3	886.3	1015.1	1090.2	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3
110°	662.4	824.2	961.4	1059.6	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	625.6	767.5	897.8	1004.4	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2
115°	596.5	723.0	841.1	941.5	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1
117.5°	576.6	686.2	792.0	885.5	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9
120°	561.2	660.1	755.2	836.5	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2
122.5°	548.2	639.4	724.5	800.4	831.1	861.8	908.5	943.8	963.0	969.1	963.0
125°	535.9	619.5	698.5	765.9	794.6	823.4	867.9	897.0	916.2	922.3	916.2
127.5°	524.4	599.6	672.4	736.8	763.6	790.5	829.6	857.2	874.0	878.6	874.0
130°	512.9	580.4	646.3	706.9	732.2	757.5	795.1	821.1	836.5	842.6	836.5
132.5°	503.7	562.0	621.8	676.2	699.6	723.0	759.8	785.9	799.7	805.0	799.7
135°	495.3	545.1	595.7	646.3	667.8	689.3	722.2	747.5	761.3	764.4	761.3
137.5°	489.2	531.3	575.0	616.4	635.6	654.8	686.2	708.4	720.7	725.3	720.7
140°	483.8	518.3	555.1	590.4	607.2	624.1	648.6	668.6	680.1	684.7	680.1
142.5°	478.4	507.6	537.5	566.6	580.0	593.4	616.4	634.1	644.0	644.0	644.0
145°	473.8	497.6	522.9	546.7	557.8	568.9	587.3	600.3	608.0	610.3	608.0
147.5°	469.2	489.9	510.6	529.8	538.2	546.7	562.8	573.5	578.9	580.4	578.9
150°	463.1	481.5	498.4	514.5	521.4	528.3	539.8	549.0	553.6	554.3	553.6
152.5°	457.7	473.1	488.4	501.4	507.2	512.9	521.4	529.0	532.1	532.1	532.1
155°	450.8	465.4	477.7	489.2	493.4	497.6	506.0	511.4	514.5	512.9	514.5
157.5°	444.7	456.2	466.9	476.9	480.4	483.8	489.9	494.5	496.1	496.1	496.1
160°	437.8	447.8	456.2	464.6	467.3	470.0	475.4	479.2	480.0	480.0	480.0
162.5°	431.7	439.3	446.2	453.1	455.0	457.0	462.3	464.6	465.4	464.6	465.4
165°	424.8	430.9	436.3	441.6	443.2	444.7	447.8	450.8	450.8	450.1	450.8
167.5°	417.9	422.5	427.1	430.9	432.4	434.0	435.5	437.0	437.0	436.3	437.0
170°	412.5	416.3	418.6	421.7	422.4	423.2	424.0	426.3	425.5	424.0	425.5
172.5°	407.1	409.4	410.9	413.3	413.6	414.0	414.8	415.6	414.8	414.0	414.8
175°	402.5	404.8	405.6	406.3	406.7	407.1	407.1	407.9	407.1	405.6	407.1
177.5°	399.4	401.0	401.0	401.7	401.7	401.7	401.7	401.7	401.0	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	612.5	609.4	606.8	607.2	609.4	607.7	603.2	597.4	595.2	592.5	595.2
5°	649.4	646.7	641.4	641.9	640.5	638.7	631.6	622.8	622.8	615.6	614.8
7.5°	685.8	681.8	678.3	677.4	672.5	668.9	662.7	650.3	645.4	637.0	632.1
10°	726.7	723.6	719.6	714.7	712.0	705.8	695.6	677.4	668.5	657.0	648.5
12.5°	768.0	767.6	758.7	748.9	748.5	738.7	731.6	707.1	695.2	679.6	659.6
15°	794.2	792.0	787.1	782.2	783.5	772.9	756.9	728.0	720.0	701.4	680.1
17.5°	793.8	793.8	792.4	791.5	790.2	787.1	778.2	759.1	746.2	722.7	702.7
20°	768.4	774.2	775.6	775.1	779.6	781.8	781.3	769.3	759.1	738.2	717.8
22.5°	717.8	731.1	736.9	740.5	749.8	754.7	766.2	761.8	759.1	743.6	726.2
25°	670.7	675.2	692.5	693.4	706.3	718.3	729.8	737.4	747.1	741.4	726.7
27.5°	609.9	620.1	632.5	641.9	644.5	668.9	688.0	702.3	724.5	726.2	721.4
30°	541.0	545.9	566.3	578.8	593.0	610.8	638.3	662.7	682.7	700.9	707.1
32.5°	457.1	477.1	489.1	504.2	516.6	548.1	581.9	613.4	636.5	667.2	680.5
35°	380.2	395.8	416.2	422.4	445.1	471.7	515.7	556.1	591.2	622.3	649.4
37.5°	316.7	329.1	350.9	360.7	374.0	408.2	445.1	495.3	537.5	575.7	609.4
40°	273.2	282.5	298.9	302.0	313.2	344.2	374.0	421.1	477.1	528.6	565.5
42.5°	243.4	247.9	259.0	263.0	270.1	290.9	317.6	362.0	414.0	467.3	519.3
45°	222.1	225.2	231.9	235.4	244.3	253.6	275.4	310.9	351.8	405.5	461.5
47.5°	203.0	207.0	209.7	211.9	216.8	227.0	241.2	267.4	306.5	355.8	410.0
50°	187.0	188.3	193.2	193.7	196.8	203.4	216.8	232.8	263.8	303.8	356.2
52.5°	171.0	172.3	175.5	178.6	179.9	185.2	194.1	207.4	230.5	262.1	308.7
55°	155.0	156.8	159.9	162.1	163.5	167.9	173.2	186.1	204.3	226.5	264.7
57.5°	139.0	143.0	143.9	145.2	147.5	152.4	157.2	164.8	179.0	199.4	227.4
60°	123.9	125.3	128.4	129.7	131.9	134.6	140.8	146.6	156.8	172.8	198.1
62.5°	108.4	111.5	112.8	114.2	115.9	119.0	123.0	129.3	138.1	151.0	171.0
65°	95.1	95.5	98.2	99.9	101.7	103.9	107.9	113.7	119.0	131.0	145.7
67.5°	82.2	83.1	84.0	85.7	87.9	90.2	93.7	96.8	103.5	111.5	123.0
70°	69.7	69.7	72.0	73.3	72.8	75.5	78.2	81.7	86.6	94.2	103.5
72.5°	58.6	58.2	60.0	60.4	61.3	63.1	64.9	68.4	71.1	76.8	84.0
75°	46.6	47.5	48.4	48.4	49.7	51.1	52.9	54.6	57.7	61.3	66.6
77.5°	36.9	36.9	37.8	38.2	39.5	39.1	40.9	42.6	44.9	48.0	52.0
80°	27.1	28.0	28.0	28.0	28.4	28.9	30.6	32.0	33.3	35.5	37.3
82.5°	19.1	19.1	20.0	20.0	20.0	20.9	20.9	21.3	22.2	23.5	24.9
85°	12.0	12.0	12.0	12.4	12.0	12.4	13.3	12.9	13.3	14.2	14.2
87.5°	5.8	5.8	5.8	5.8	5.8	6.2	5.8	6.2	6.7	6.7	6.7
90°	25.3	25.3	25.3	24.9	24.5	23.0	24.5	25.3	26.1	25.3	20.7
92.5°	47.5	50.6	51.4	54.4	57.5	65.9	77.4	98.9	118.1	116.5	90.5
95°	88.9	95.1	105.0	113.4	121.9	154.1	200.9	263.0	300.5	266.0	177.1
97.5°	159.5	174.8	204.7	227.7	250.7	328.1	410.9	493.8	489.9	378.7	235.4
100°	310.5	343.5	407.1	453.5	499.9	604.9	700.0	716.1	605.7	417.1	251.5
102.5°	584.2	646.3	716.9	766.7	816.5	886.3	889.4	798.9	609.5	402.5	252.2
105°	907.8	955.3	1002.8	1015.4	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1
107.5°	1113.2	1120.1	1120.9	1105.6	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5
110°	1170.0	1155.4	1122.4	1091.0	1059.6	961.4	824.2	662.4	503.7	368.8	275.2

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1154.6	1127.8	1078.7	1041.6	1004.4	897.8	767.5	625.6	486.9	369.5	286.7
115°	1110.2	1074.9	1020.5	981.0	941.5	841.1	723.0	596.5	475.4	372.6	298.2
117.5°	1054.2	1016.6	960.7	923.1	885.5	792.0	686.2	576.6	469.2	377.2	310.5
120°	995.9	959.9	906.2	871.4	836.5	755.2	660.1	561.2	463.9	381.8	322.8
122.5°	943.8	908.5	861.8	831.1	800.4	724.5	639.4	548.2	460.8	387.2	333.5
125°	897.0	867.9	823.4	794.6	765.9	698.5	619.5	535.9	457.0	392.5	345.0
127.5°	857.2	829.6	790.5	763.6	736.8	672.4	599.6	524.4	454.7	397.9	355.7
130°	821.1	795.1	757.5	732.2	706.9	646.3	580.4	512.9	453.1	404.0	365.7
132.5°	785.9	759.8	723.0	699.6	676.2	621.8	562.0	503.7	452.4	410.2	375.7
135°	747.5	722.2	689.3	667.8	646.3	595.7	545.1	495.3	451.6	414.8	384.1
137.5°	708.4	686.2	654.8	635.6	616.4	575.0	531.3	489.2	451.6	419.4	391.0
140°	668.6	648.6	624.1	607.2	590.4	555.1	518.3	483.8	450.8	422.5	396.4
142.5°	634.1	616.4	593.4	580.0	566.6	537.5	507.6	478.4	450.8	424.8	401.0
145°	600.3	587.3	568.9	557.8	546.7	522.9	497.6	473.8	449.3	426.3	404.8
147.5°	573.5	562.8	546.7	538.2	529.8	510.6	489.9	469.2	447.0	427.1	407.1
150°	549.0	539.8	528.3	521.4	514.5	498.4	481.5	463.1	444.7	426.3	408.6
152.5°	529.0	521.4	512.9	507.2	501.4	488.4	473.1	457.7	440.9	424.8	409.4
155°	511.4	506.0	497.6	493.4	489.2	477.7	465.4	450.8	436.3	423.2	410.2
157.5°	494.5	489.9	483.8	480.4	476.9	466.9	456.2	444.7	431.7	420.2	410.2
160°	479.2	475.4	470.0	467.3	464.6	456.2	447.8	437.8	427.1	417.9	410.2
162.5°	464.6	462.3	457.0	455.0	453.1	446.2	439.3	431.7	423.2	415.6	409.4
165°	450.8	447.8	444.7	443.2	441.6	436.3	430.9	424.8	417.9	412.5	407.9
167.5°	437.0	435.5	434.0	432.4	430.9	427.1	422.5	417.9	413.3	409.4	407.1
170°	426.3	424.0	423.2	422.4	421.7	418.6	416.3	412.5	409.4	407.1	405.6
172.5°	415.6	414.8	414.0	413.6	413.3	410.9	409.4	407.1	404.8	404.0	403.3
175°	407.9	407.1	407.1	406.7	406.3	405.6	404.8	402.5	401.7	401.0	401.7
177.5°	401.7	401.7	401.7	401.7	401.7	401.0	401.0	399.4	398.7	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	593.0	590.8	589.4	590.3	587.7	581.0	581.0	583.2	580.6	577.9	573.9
5°	609.4	605.0	602.3	601.9	595.7	585.0	582.8	580.6	574.8	568.6	561.9
7.5°	625.4	617.4	613.0	609.9	601.0	587.2	581.4	576.6	567.2	557.9	549.5
10°	638.7	627.2	621.9	617.0	605.4	588.1	578.8	569.9	557.9	545.9	535.2
12.5°	649.4	636.1	629.4	622.3	608.1	585.4	573.9	559.7	547.7	531.7	521.0
15°	667.2	639.6	633.4	626.8	612.1	581.0	566.8	550.8	534.4	513.0	501.5
17.5°	681.4	644.5	644.1	629.9	610.8	579.2	557.5	536.6	518.8	497.5	479.3
20°	689.8	652.1	645.0	630.3	606.3	567.2	544.6	521.5	502.4	476.6	458.4
22.5°	696.9	662.7	644.1	626.3	597.0	563.2	529.9	508.2	481.9	454.0	436.6
25°	699.6	665.0	645.4	625.0	590.3	551.7	513.9	490.4	461.1	435.7	412.2
27.5°	700.0	664.5	640.5	619.2	581.0	536.6	497.9	473.1	440.6	411.3	387.8
30°	695.6	659.6	637.9	614.8	572.1	522.8	478.4	450.9	416.2	386.9	362.5
32.5°	682.3	649.8	632.1	606.8	560.6	503.7	459.7	429.1	392.7	363.8	340.2
35°	660.1	637.9	618.3	594.8	545.5	485.9	441.1	405.1	368.2	340.7	318.5
37.5°	632.5	620.5	602.3	579.2	528.1	470.0	420.2	380.2	343.4	316.7	294.9
40°	595.2	598.3	580.6	559.7	507.7	448.2	393.1	354.9	320.3	295.4	274.1
42.5°	554.8	567.7	557.5	537.5	485.1	424.2	373.1	330.9	297.2	271.4	253.6
45°	511.3	533.5	527.3	512.6	461.5	398.9	344.7	303.8	274.1	249.2	233.6
47.5°	463.7	495.3	495.3	484.6	435.3	373.6	320.3	278.5	249.2	231.4	216.3
50°	415.3	450.9	456.6	449.5	406.0	344.7	290.5	252.7	227.4	210.1	199.0
52.5°	364.7	406.0	416.6	413.1	374.9	317.2	266.1	229.2	206.1	191.0	181.2
55°	316.3	364.2	375.8	377.1	341.6	286.9	239.0	206.5	184.3	174.1	165.7
57.5°	270.5	316.7	329.6	331.8	307.8	259.4	213.7	185.2	165.2	156.8	150.1
60°	231.4	270.1	286.9	291.8	271.0	227.4	190.1	162.6	147.5	139.5	133.3
62.5°	199.4	230.5	248.3	249.6	240.3	199.4	165.7	142.6	129.7	122.6	119.5
65°	168.3	196.3	207.0	212.3	204.8	172.8	143.0	123.9	113.7	107.5	104.4
67.5°	143.5	161.2	170.1	177.2	169.7	145.7	121.7	106.2	98.6	92.4	90.6
70°	117.7	132.4	139.0	146.1	139.5	121.3	103.9	89.7	83.1	78.2	76.0
72.5°	94.2	105.7	111.9	116.4	112.4	97.3	83.1	73.3	68.4	64.9	63.5
75°	74.6	82.6	86.2	89.3	87.5	76.0	67.1	59.1	54.6	51.5	50.6
77.5°	56.9	62.6	66.6	67.5	65.3	57.7	50.2	45.3	41.8	40.0	39.1
80°	40.4	44.0	46.2	47.5	45.3	42.2	36.9	33.3	30.2	28.0	27.5
82.5°	27.1	28.9	30.6	30.2	29.3	26.7	23.5	21.8	20.4	18.7	18.7
85°	15.5	16.0	16.9	17.3	16.9	15.1	13.3	12.4	11.5	10.2	10.2
87.5°	6.7	7.1	7.1	7.6	6.7	6.7	5.8	4.9	4.9	4.4	4.0
90°	15.3	11.5	10.4	9.2	7.7	6.1	3.1	0.8	3.1	6.1	7.7
92.5°	61.3	40.6	36.4	32.2	26.1	22.2	16.1	11.5	16.1	22.2	26.1
95°	110.4	75.1	65.9	56.7	44.5	37.6	29.9	26.8	29.9	37.6	44.5
97.5°	142.6	97.4	87.1	76.7	62.9	52.9	44.5	39.9	44.5	52.9	62.9
100°	157.9	117.3	106.6	95.8	80.5	68.2	61.3	59.0	61.3	68.2	80.5
102.5°	171.7	134.9	124.2	113.5	97.4	85.1	78.2	76.7	78.2	85.1	97.4
105°	187.8	151.8	141.0	130.3	113.5	102.0	96.6	93.5	96.6	102.0	113.5
107.5°	203.9	168.7	158.0	147.2	130.3	119.6	114.2	111.9	114.2	119.6	130.3
110°	220.0	186.3	175.2	164.1	148.0	138.0	133.4	130.3	133.4	138.0	148.0

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	235.4	203.2	191.7	180.2	164.8	155.6	150.3	147.2	150.3	155.6	164.8
115°	251.5	218.5	208.2	197.8	182.5	173.3	168.7	164.8	168.7	173.3	182.5
117.5°	266.0	235.4	224.6	213.9	199.3	190.9	186.3	183.2	186.3	190.9	199.3
120°	281.4	251.5	240.8	230.0	214.7	207.8	203.2	200.1	203.2	207.8	214.7
122.5°	295.9	268.3	257.2	246.1	230.8	223.1	218.5	216.2	218.5	223.1	230.8
125°	310.5	282.9	272.2	261.4	246.1	236.9	232.3	230.0	232.3	236.9	246.1
127.5°	324.3	297.5	286.4	275.2	260.7	250.7	244.6	241.5	244.6	250.7	260.7
130°	336.6	309.7	299.0	288.3	272.9	262.2	254.5	251.5	254.5	262.2	272.9
132.5°	347.3	322.0	311.2	300.5	284.4	272.9	264.5	260.7	264.5	272.9	284.4
135°	357.3	332.7	322.0	311.3	293.6	282.1	272.9	269.9	272.9	282.1	293.6
137.5°	365.7	341.2	331.2	321.2	303.6	291.3	282.1	278.3	282.1	291.3	303.6
140°	372.6	349.6	339.6	329.7	312.8	300.5	291.3	288.3	291.3	300.5	312.8
142.5°	378.0	355.7	346.5	337.3	321.2	309.0	300.5	298.2	300.5	309.0	321.2
145°	383.3	362.6	354.2	345.8	330.4	318.9	311.3	308.2	311.3	318.9	330.4
147.5°	387.9	368.0	360.4	352.7	339.6	328.9	321.2	318.9	321.2	328.9	339.6
150°	391.0	373.4	366.5	359.6	348.1	338.1	332.0	329.7	332.0	338.1	348.1
152.5°	394.1	378.7	372.6	366.5	355.7	347.3	341.2	340.4	341.2	347.3	355.7
155°	397.1	384.1	378.4	372.6	364.2	355.7	351.1	350.4	351.1	355.7	364.2
157.5°	399.4	387.9	383.0	378.0	371.1	363.4	359.6	358.8	359.6	363.4	371.1
160°	401.0	391.8	387.6	383.3	377.2	371.1	368.0	367.2	368.0	371.1	377.2
162.5°	401.7	394.1	391.0	387.9	382.6	378.0	374.9	375.7	374.9	378.0	382.6
165°	402.5	395.6	393.3	391.0	387.2	382.6	381.0	381.8	381.0	382.6	387.2
167.5°	402.5	397.1	395.6	394.1	391.0	387.9	386.4	387.2	386.4	387.9	391.0
170°	401.7	397.9	396.8	395.6	394.1	391.8	391.0	392.5	391.0	391.8	394.1
172.5°	401.0	398.7	397.9	397.1	396.4	394.1	394.8	395.6	394.8	394.1	396.4
175°	400.2	398.7	398.3	397.9	397.9	396.4	397.1	397.9	397.1	396.4	397.9
177.5°	399.4	398.7	398.7	398.7	398.7	397.1	397.9	399.4	397.9	397.1	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	571.7	573.9	573.4	569.0	564.1	560.1	552.6	553.5	550.8	551.2	553.9
5°	557.5	557.5	555.7	549.5	541.5	537.0	528.6	526.4	521.0	520.6	520.1
7.5°	542.4	540.1	537.9	529.0	519.3	512.1	500.6	497.9	492.6	489.1	487.3
10°	524.6	521.5	517.0	506.8	494.8	485.9	473.9	470.4	460.2	455.7	453.1
12.5°	505.0	503.3	496.2	487.7	468.2	458.4	441.1	444.6	434.4	425.5	424.2
15°	485.5	478.8	474.8	461.1	437.5	433.1	419.3	412.2	402.9	395.8	395.8
17.5°	466.4	456.2	447.3	432.6	415.3	402.9	392.7	389.1	377.6	370.5	369.1
20°	441.1	429.5	427.3	406.4	394.4	380.7	370.9	362.0	353.6	350.5	348.2
22.5°	417.1	403.8	400.2	382.4	370.5	356.7	346.9	340.7	334.5	332.3	328.3
25°	391.3	383.3	378.0	358.9	345.6	332.7	326.0	321.6	315.8	315.4	312.7
27.5°	366.5	358.9	353.6	335.4	325.6	313.6	308.3	303.4	300.3	298.9	297.6
30°	345.1	336.7	330.5	317.2	305.2	295.4	290.9	287.8	286.1	283.8	283.4
32.5°	321.6	316.7	308.3	298.1	288.7	279.4	276.7	274.5	271.8	271.0	270.5
35°	301.6	294.9	289.6	278.1	274.1	266.1	263.0	261.2	257.6	256.7	255.9
37.5°	282.1	275.8	270.1	263.0	255.4	251.0	249.2	246.5	244.7	245.2	244.3
40°	262.5	257.6	253.2	245.6	241.2	239.0	235.4	232.8	231.9	232.3	231.9
42.5°	243.4	239.0	236.3	230.5	226.1	223.9	221.7	219.0	220.3	220.3	221.7
45°	226.1	222.1	220.3	215.9	213.2	209.7	207.4	207.0	208.8	208.3	208.3
47.5°	208.3	207.0	204.8	200.8	197.2	195.0	194.6	194.6	196.3	197.2	196.8
50°	194.6	191.9	189.2	186.1	183.4	182.6	181.2	182.1	183.9	183.9	184.8
52.5°	177.2	175.5	174.6	171.9	170.1	170.1	170.1	170.6	171.9	173.2	172.8
55°	162.1	160.8	159.9	158.6	156.4	156.8	156.4	157.2	158.6	159.9	160.8
57.5°	146.1	145.7	144.8	142.6	142.6	142.1	143.5	143.9	146.1	147.0	148.4
60°	131.9	130.6	130.6	128.8	128.8	128.8	130.1	131.5	133.3	133.7	134.6
62.5°	116.8	116.8	116.4	115.0	115.0	116.4	116.8	118.6	119.5	119.5	120.8
65°	102.6	102.2	101.7	102.2	102.6	102.6	103.9	104.8	105.7	106.2	106.6
67.5°	88.4	87.9	88.8	88.4	89.3	91.1	90.6	91.9	93.3	93.3	93.7
70°	75.1	76.0	75.5	76.4	76.0	76.8	78.2	78.6	78.6	79.1	80.4
72.5°	62.6	62.6	62.6	62.2	62.6	63.5	64.4	64.9	65.7	66.2	67.5
75°	50.6	50.6	49.7	50.6	50.6	51.5	52.4	52.4	52.4	53.3	54.6
77.5°	38.2	38.6	38.2	39.1	39.1	39.5	40.4	40.0	40.9	41.3	41.8
80°	28.0	27.5	27.5	27.5	28.0	28.0	28.9	29.3	29.3	30.6	29.8
82.5°	17.8	18.2	17.8	18.2	18.2	18.7	18.2	18.7	19.1	20.0	19.5
85°	10.2	9.8	9.8	10.2	9.8	9.8	10.2	9.8	10.2	9.8	10.2
87.5°	4.0	3.6	3.6	3.6	3.6	3.1	3.1	2.7	2.7	2.7	2.2
90°	9.2	10.4	11.5	15.3	20.7	25.3	26.1	25.3	24.5	23.0	24.5
92.5°	32.2	36.4	40.6	61.3	90.5	116.5	118.1	98.9	77.4	65.9	57.5
95°	56.7	65.9	75.1	110.4	177.1	266.0	300.5	263.0	200.9	154.1	121.9
97.5°	76.7	87.1	97.4	142.6	235.4	378.7	489.9	493.8	410.9	328.1	250.7
100°	95.8	106.6	117.3	157.9	251.5	417.1	605.7	716.1	700.0	604.9	499.9
102.5°	113.5	124.2	134.9	171.7	252.2	402.5	609.5	798.9	889.4	886.3	816.5
105°	130.3	141.0	151.8	187.8	256.1	382.6	568.1	772.1	931.5	1018.2	1028.1
107.5°	147.2	158.0	168.7	203.9	264.5	371.8	529.8	715.3	886.3	1015.1	1090.2
110°	164.1	175.2	186.3	220.0	275.2	368.8	503.7	662.4	824.2	961.4	1059.6

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	180.2	191.7	203.2	235.4	286.7	369.5	486.9	625.6	767.5	897.8	1004.4
115°	197.8	208.2	218.5	251.5	298.2	372.6	475.4	596.5	723.0	841.1	941.5
117.5°	213.9	224.6	235.4	266.0	310.5	377.2	469.2	576.6	686.2	792.0	885.5
120°	230.0	240.8	251.5	281.4	322.8	381.8	463.9	561.2	660.1	755.2	836.5
122.5°	246.1	257.2	268.3	295.9	333.5	387.2	460.8	548.2	639.4	724.5	800.4
125°	261.4	272.2	282.9	310.5	345.0	392.5	457.0	535.9	619.5	698.5	765.9
127.5°	275.2	286.4	297.5	324.3	355.7	397.9	454.7	524.4	599.6	672.4	736.8
130°	288.3	299.0	309.7	336.6	365.7	404.0	453.1	512.9	580.4	646.3	706.9
132.5°	300.5	311.2	322.0	347.3	375.7	410.2	452.4	503.7	562.0	621.8	676.2
135°	311.3	322.0	332.7	357.3	384.1	414.8	451.6	495.3	545.1	595.7	646.3
137.5°	321.2	331.2	341.2	365.7	391.0	419.4	451.6	489.2	531.3	575.0	616.4
140°	329.7	339.6	349.6	372.6	396.4	422.5	450.8	483.8	518.3	555.1	590.4
142.5°	337.3	346.5	355.7	378.0	401.0	424.8	450.8	478.4	507.6	537.5	566.6
145°	345.8	354.2	362.6	383.3	404.8	426.3	449.3	473.8	497.6	522.9	546.7
147.5°	352.7	360.4	368.0	387.9	407.1	427.1	447.0	469.2	489.9	510.6	529.8
150°	359.6	366.5	373.4	391.0	408.6	426.3	444.7	463.1	481.5	498.4	514.5
152.5°	366.5	372.6	378.7	394.1	409.4	424.8	440.9	457.7	473.1	488.4	501.4
155°	372.6	378.4	384.1	397.1	410.2	423.2	436.3	450.8	465.4	477.7	489.2
157.5°	378.0	383.0	387.9	399.4	410.2	420.2	431.7	444.7	456.2	466.9	476.9
160°	383.3	387.6	391.8	401.0	410.2	417.9	427.1	437.8	447.8	456.2	464.6
162.5°	387.9	391.0	394.1	401.7	409.4	415.6	423.2	431.7	439.3	446.2	453.1
165°	391.0	393.3	395.6	402.5	407.9	412.5	417.9	424.8	430.9	436.3	441.6
167.5°	394.1	395.6	397.1	402.5	407.1	409.4	413.3	417.9	422.5	427.1	430.9
170°	395.6	396.8	397.9	401.7	405.6	407.1	409.4	412.5	416.3	418.6	421.7
172.5°	397.1	397.9	398.7	401.0	403.3	404.0	404.8	407.1	409.4	410.9	413.3
175°	397.9	398.3	398.7	400.2	401.7	401.0	401.7	402.5	404.8	405.6	406.3
177.5°	398.7	398.7	398.7	399.4	401.0	399.4	398.7	399.4	401.0	401.0	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	550.8	552.1	549.0	548.1	549.0	545.9	546.8	547.7	547.7	549.0	549.9
5°	518.8	517.0	513.9	513.0	512.1	513.5	512.6	513.9	514.4	517.5	517.9
7.5°	487.3	484.6	481.9	479.3	478.4	476.2	478.4	478.4	481.5	480.6	482.8
10°	450.0	449.5	446.0	444.6	442.9	439.3	444.2	442.9	445.1	449.1	450.0
12.5°	422.4	417.5	419.8	413.5	415.8	412.2	412.7	412.7	416.2	416.6	415.8
15°	396.2	392.2	386.4	383.8	382.4	380.7	386.4	386.9	384.2	390.4	388.2
17.5°	369.6	369.6	364.2	362.9	359.3	361.1	360.2	360.7	359.8	364.2	366.5
20°	346.5	344.2	342.5	342.9	338.5	337.6	336.7	337.6	340.7	343.8	344.7
22.5°	327.8	326.5	322.0	322.9	319.4	320.7	319.8	322.0	322.5	322.5	325.6
25°	310.0	308.3	308.7	306.9	305.6	305.6	304.3	305.6	307.4	308.3	308.7
27.5°	296.7	295.4	293.2	291.8	292.7	290.5	292.3	293.6	293.6	292.7	293.6
30°	280.7	281.6	281.6	277.2	279.0	278.1	279.4	280.3	280.3	280.7	279.8
32.5°	270.1	267.4	267.0	266.5	266.5	264.7	264.7	266.1	266.5	267.0	268.3
35°	255.9	255.9	253.6	255.0	253.2	253.6	253.2	253.6	254.5	253.2	254.5
37.5°	243.0	243.4	242.5	243.4	243.9	243.0	242.1	243.9	243.0	243.0	242.1
40°	231.9	231.4	231.9	231.9	231.9	232.3	231.4	231.4	231.4	230.5	229.6
42.5°	222.5	219.9	220.8	221.2	219.9	219.9	220.3	219.9	221.2	218.5	218.5
45°	209.2	208.3	208.8	208.8	209.7	208.3	209.2	209.7	208.3	207.9	207.0
47.5°	197.2	198.1	197.2	198.1	198.1	199.0	197.2	197.7	198.1	196.3	195.0
50°	185.2	185.2	186.6	186.1	186.6	185.7	185.7	185.2	185.7	184.8	183.4
52.5°	174.1	172.8	175.0	174.6	174.1	173.7	173.2	173.7	172.8	171.9	171.9
55°	160.4	160.4	161.7	162.1	162.1	161.2	160.4	160.8	160.4	159.9	159.5
57.5°	149.2	147.5	148.4	148.8	148.8	147.5	148.4	147.5	147.5	147.9	146.6
60°	135.0	135.0	134.1	135.5	135.5	134.6	134.6	135.0	134.1	133.7	133.3
62.5°	119.9	120.4	121.7	122.2	122.6	121.7	120.8	121.3	121.3	119.9	120.4
65°	107.0	107.9	109.7	109.3	108.4	108.8	107.9	108.4	107.0	107.5	106.2
67.5°	94.6	94.2	94.6	94.6	95.5	95.1	94.2	94.2	93.7	95.1	93.7
70°	81.3	81.3	81.3	81.3	81.7	82.2	81.3	80.4	80.8	80.0	79.5
72.5°	67.5	68.0	67.5	68.4	67.1	68.0	68.0	67.5	67.1	67.1	67.1
75°	54.6	55.5	54.2	54.6	54.2	55.1	54.6	54.6	53.7	53.3	53.7
77.5°	41.8	42.2	41.3	41.8	41.3	41.8	41.8	41.3	41.3	41.3	41.3
80°	29.8	30.2	29.8	29.3	28.9	29.8	28.9	29.3	29.8	29.3	30.2
82.5°	19.1	19.1	18.7	19.1	18.2	18.2	18.7	18.7	18.2	19.1	18.2
85°	9.3	9.3	10.2	9.3	8.9	8.9	8.9	9.3	8.9	9.8	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	24.9	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	24.9
92.5°	54.4	51.4	50.6	47.5	48.3	46.8	48.3	47.5	50.6	51.4	54.4
95°	113.4	105.0	95.1	88.9	86.6	87.4	86.6	88.9	95.1	105.0	113.4
97.5°	227.7	204.7	174.8	159.5	151.0	146.4	151.0	159.5	174.8	204.7	227.7
100°	453.5	407.1	343.5	310.5	288.3	274.5	288.3	310.5	343.5	407.1	453.5
102.5°	766.7	716.9	646.3	584.2	555.1	535.2	555.1	584.2	646.3	716.9	766.7
105°	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8	907.8	955.3	1002.8	1015.4
107.5°	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3	1113.2	1120.1	1120.9	1105.6
110°	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9	1170.0	1155.4	1122.4	1091.0

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2	1154.6	1127.8	1078.7	1041.6
115°	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1	1110.2	1074.9	1020.5	981.0
117.5°	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9	1054.2	1016.6	960.7	923.1
120°	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2	995.9	959.9	906.2	871.4
122.5°	831.1	861.8	908.5	943.8	963.0	969.1	963.0	943.8	908.5	861.8	831.1
125°	794.6	823.4	867.9	897.0	916.2	922.3	916.2	897.0	867.9	823.4	794.6
127.5°	763.6	790.5	829.6	857.2	874.0	878.6	874.0	857.2	829.6	790.5	763.6
130°	732.2	757.5	795.1	821.1	836.5	842.6	836.5	821.1	795.1	757.5	732.2
132.5°	699.6	723.0	759.8	785.9	799.7	805.0	799.7	785.9	759.8	723.0	699.6
135°	667.8	689.3	722.2	747.5	761.3	764.4	761.3	747.5	722.2	689.3	667.8
137.5°	635.6	654.8	686.2	708.4	720.7	725.3	720.7	708.4	686.2	654.8	635.6
140°	607.2	624.1	648.6	668.6	680.1	684.7	680.1	668.6	648.6	624.1	607.2
142.5°	580.0	593.4	616.4	634.1	644.0	644.0	644.0	634.1	616.4	593.4	580.0
145°	557.8	568.9	587.3	600.3	608.0	610.3	608.0	600.3	587.3	568.9	557.8
147.5°	538.2	546.7	562.8	573.5	578.9	580.4	578.9	573.5	562.8	546.7	538.2
150°	521.4	528.3	539.8	549.0	553.6	554.3	553.6	549.0	539.8	528.3	521.4
152.5°	507.2	512.9	521.4	529.0	532.1	532.1	532.1	529.0	521.4	512.9	507.2
155°	493.4	497.6	506.0	511.4	514.5	512.9	514.5	511.4	506.0	497.6	493.4
157.5°	480.4	483.8	489.9	494.5	496.1	496.1	496.1	494.5	489.9	483.8	480.4
160°	467.3	470.0	475.4	479.2	480.0	480.0	480.0	479.2	475.4	470.0	467.3
162.5°	455.0	457.0	462.3	464.6	465.4	464.6	465.4	464.6	462.3	457.0	455.0
165°	443.2	444.7	447.8	450.8	450.8	450.1	450.8	450.8	447.8	444.7	443.2
167.5°	432.4	434.0	435.5	437.0	437.0	436.3	437.0	437.0	435.5	434.0	432.4
170°	422.4	423.2	424.0	426.3	425.5	424.0	425.5	426.3	424.0	423.2	422.4
172.5°	413.6	414.0	414.8	415.6	414.8	414.0	414.8	415.6	414.8	414.0	413.6
175°	406.7	407.1	407.1	407.9	407.1	405.6	407.1	407.9	407.1	407.1	406.7
177.5°	401.7	401.7	401.7	401.7	401.0	399.4	401.0	401.7	401.7	401.7	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	548.6	552.1	550.8	545.9	551.7	551.7	555.7	555.7	560.6	562.3	565.0
5°	517.5	520.1	522.4	520.1	524.1	530.4	533.9	537.0	543.7	546.4	550.3
7.5°	484.2	489.1	491.3	491.3	497.9	505.0	512.1	516.6	525.9	529.5	533.5
10°	451.7	457.5	462.0	461.5	472.6	477.1	485.9	496.2	505.5	510.8	516.6
12.5°	417.5	420.6	426.9	435.7	438.4	446.4	456.6	469.5	486.4	491.3	499.7
15°	389.1	397.5	402.4	406.4	412.7	420.2	431.3	443.7	460.6	471.3	480.2
17.5°	365.1	376.2	379.3	378.4	386.4	398.0	410.9	420.2	435.3	448.2	456.6
20°	345.6	350.0	355.4	357.6	363.8	376.2	388.7	399.3	411.8	422.0	431.8
22.5°	326.0	329.6	334.0	338.0	342.9	350.0	362.0	375.3	387.3	397.1	408.2
25°	310.0	312.3	316.3	319.4	324.7	329.6	338.0	352.7	366.9	372.7	382.4
27.5°	294.5	296.3	298.9	302.5	305.2	310.0	317.6	329.6	344.2	350.0	363.3
30°	280.7	282.1	284.7	286.5	287.8	293.6	299.4	308.7	319.8	327.8	337.6
32.5°	267.8	269.2	271.8	272.3	274.1	277.2	282.5	290.9	300.7	307.4	315.8
35°	253.6	254.5	257.2	258.1	259.4	262.1	266.1	272.3	281.2	286.1	293.6
37.5°	242.5	242.1	243.9	245.2	247.0	248.3	249.6	255.9	262.5	267.0	272.7
40°	230.5	229.6	230.1	231.9	232.8	234.5	234.5	240.8	245.2	248.7	253.2
42.5°	218.5	218.1	217.2	218.1	219.0	219.4	219.9	224.3	228.8	231.9	236.8
45°	206.5	206.1	205.2	205.7	205.7	206.5	207.9	209.7	212.8	215.4	218.1
47.5°	195.4	194.6	193.2	192.8	193.7	193.7	193.7	195.4	198.6	199.4	202.1
50°	183.9	182.6	180.8	179.9	179.9	179.5	180.3	180.8	183.4	184.3	186.6
52.5°	171.5	170.6	168.8	167.0	167.5	166.6	167.0	167.5	168.3	169.7	171.0
55°	159.0	157.2	155.9	155.5	154.1	154.1	152.8	154.6	154.1	154.6	156.4
57.5°	147.0	145.2	143.0	142.1	140.8	140.4	139.5	139.0	139.5	140.8	142.1
60°	132.8	131.9	130.6	129.3	128.4	127.0	126.1	126.1	125.7	125.7	126.1
62.5°	119.0	118.6	116.8	116.4	115.5	114.6	113.3	112.4	112.4	113.3	113.7
65°	105.7	105.3	103.9	103.5	101.3	100.4	99.9	99.5	98.6	98.6	98.6
67.5°	93.3	91.9	91.9	89.7	87.9	87.1	86.2	85.7	85.7	85.7	86.2
70°	79.5	79.5	78.2	76.8	75.1	75.5	74.2	72.8	72.8	72.0	72.4
72.5°	66.2	65.7	64.4	64.0	62.6	61.3	60.4	61.3	60.0	59.5	60.0
75°	53.3	52.9	52.0	51.1	51.5	50.2	48.9	48.4	48.4	47.5	47.5
77.5°	40.9	41.8	40.0	39.5	38.6	37.8	37.3	36.9	36.9	36.9	37.8
80°	28.4	28.9	28.9	28.0	28.4	27.1	27.1	27.1	25.8	26.2	26.7
82.5°	18.2	18.2	17.8	18.2	17.8	17.8	17.3	17.3	16.9	16.9	17.3
85°	10.2	9.8	9.3	10.2	9.8	9.8	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.6	3.6	3.6
90°	24.5	23.0	24.5	25.3	26.1	25.3	20.7	15.3	11.5	10.4	9.2
92.5°	57.5	65.9	77.4	98.9	118.1	116.5	90.5	61.3	40.6	36.4	32.2
95°	121.9	154.1	200.9	263.0	300.5	266.0	177.1	110.4	75.1	65.9	56.7
97.5°	250.7	328.1	410.9	493.8	489.9	378.7	235.4	142.6	97.4	87.1	76.7
100°	499.9	604.9	700.0	716.1	605.7	417.1	251.5	157.9	117.3	106.6	95.8
102.5°	816.5	886.3	889.4	798.9	609.5	402.5	252.2	171.7	134.9	124.2	113.5
105°	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1	187.8	151.8	141.0	130.3
107.5°	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5	203.9	168.7	158.0	147.2
110°	1059.6	961.4	824.2	662.4	503.7	368.8	275.2	220.0	186.3	175.2	164.1

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1004.4	897.8	767.5	625.6	486.9	369.5	286.7	235.4	203.2	191.7	180.2
115°	941.5	841.1	723.0	596.5	475.4	372.6	298.2	251.5	218.5	208.2	197.8
117.5°	885.5	792.0	686.2	576.6	469.2	377.2	310.5	266.0	235.4	224.6	213.9
120°	836.5	755.2	660.1	561.2	463.9	381.8	322.8	281.4	251.5	240.8	230.0
122.5°	800.4	724.5	639.4	548.2	460.8	387.2	333.5	295.9	268.3	257.2	246.1
125°	765.9	698.5	619.5	535.9	457.0	392.5	345.0	310.5	282.9	272.2	261.4
127.5°	736.8	672.4	599.6	524.4	454.7	397.9	355.7	324.3	297.5	286.4	275.2
130°	706.9	646.3	580.4	512.9	453.1	404.0	365.7	336.6	309.7	299.0	288.3
132.5°	676.2	621.8	562.0	503.7	452.4	410.2	375.7	347.3	322.0	311.2	300.5
135°	646.3	595.7	545.1	495.3	451.6	414.8	384.1	357.3	332.7	322.0	311.3
137.5°	616.4	575.0	531.3	489.2	451.6	419.4	391.0	365.7	341.2	331.2	321.2
140°	590.4	555.1	518.3	483.8	450.8	422.5	396.4	372.6	349.6	339.6	329.7
142.5°	566.6	537.5	507.6	478.4	450.8	424.8	401.0	378.0	355.7	346.5	337.3
145°	546.7	522.9	497.6	473.8	449.3	426.3	404.8	383.3	362.6	354.2	345.8
147.5°	529.8	510.6	489.9	469.2	447.0	427.1	407.1	387.9	368.0	360.4	352.7
150°	514.5	498.4	481.5	463.1	444.7	426.3	408.6	391.0	373.4	366.5	359.6
152.5°	501.4	488.4	473.1	457.7	440.9	424.8	409.4	394.1	378.7	372.6	366.5
155°	489.2	477.7	465.4	450.8	436.3	423.2	410.2	397.1	384.1	378.4	372.6
157.5°	476.9	466.9	456.2	444.7	431.7	420.2	410.2	399.4	387.9	383.0	378.0
160°	464.6	456.2	447.8	437.8	427.1	417.9	410.2	401.0	391.8	387.6	383.3
162.5°	453.1	446.2	439.3	431.7	423.2	415.6	409.4	401.7	394.1	391.0	387.9
165°	441.6	436.3	430.9	424.8	417.9	412.5	407.9	402.5	395.6	393.3	391.0
167.5°	430.9	427.1	422.5	417.9	413.3	409.4	407.1	402.5	397.1	395.6	394.1
170°	421.7	418.6	416.3	412.5	409.4	407.1	405.6	401.7	397.9	396.8	395.6
172.5°	413.3	410.9	409.4	407.1	404.8	404.0	403.3	401.0	398.7	397.9	397.1
175°	406.3	405.6	404.8	402.5	401.7	401.0	401.7	400.2	398.7	398.3	397.9
177.5°	401.7	401.0	401.0	399.4	398.7	399.4	401.0	399.4	398.7	398.7	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	577.9	577.9	577.9	577.9
2.5°	567.2	567.2	573.9	581.0
5°	554.8	557.9	568.6	578.3
7.5°	542.8	548.1	561.5	573.9
10°	528.1	535.2	551.7	566.3
12.5°	513.9	520.6	539.7	556.1
15°	493.9	502.4	522.8	543.2
17.5°	473.9	482.4	507.3	531.2
20°	450.4	461.5	489.5	521.5
22.5°	428.6	442.4	473.5	499.3
25°	404.7	426.0	454.8	488.2
27.5°	383.3	404.7	434.0	467.7
30°	359.3	381.1	411.3	442.4
32.5°	336.3	356.2	385.6	423.8
35°	312.3	331.4	359.8	398.4
37.5°	290.5	309.2	340.2	375.8
40°	269.2	288.7	315.4	350.9
42.5°	249.2	266.5	290.5	326.0
45°	231.0	243.4	265.6	298.9
47.5°	211.9	223.0	243.4	276.7
50°	194.1	203.4	221.2	252.3
52.5°	176.8	184.8	201.2	226.1
55°	161.2	168.8	180.8	205.2
57.5°	145.2	151.0	162.6	182.1
60°	129.7	135.0	144.4	160.4
62.5°	114.2	118.6	127.5	140.4
65°	100.4	103.9	110.6	121.7
67.5°	87.1	89.3	94.6	103.5
70°	74.2	76.0	80.4	87.5
72.5°	60.4	62.2	67.1	72.0
75°	48.9	49.3	52.9	56.9
77.5°	38.2	37.8	40.4	43.5
80°	26.2	27.5	29.8	31.1
82.5°	17.8	18.2	19.1	20.0
85°	9.8	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	7.7	6.1	3.1	0.8
92.5°	26.1	22.2	16.1	11.5
95°	44.5	37.6	29.9	26.8
97.5°	62.9	52.9	44.5	39.9
100°	80.5	68.2	61.3	59.0
102.5°	97.4	85.1	78.2	76.7
105°	113.5	102.0	96.6	93.5
107.5°	130.3	119.6	114.2	111.9
110°	148.0	138.0	133.4	130.3



TEST NUMBER: P1008918

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	164.8	155.6	150.3	147.2
115°	182.5	173.3	168.7	164.8
117.5°	199.3	190.9	186.3	183.2
120°	214.7	207.8	203.2	200.1
122.5°	230.8	223.1	218.5	216.2
125°	246.1	236.9	232.3	230.0
127.5°	260.7	250.7	244.6	241.5
130°	272.9	262.2	254.5	251.5
132.5°	284.4	272.9	264.5	260.7
135°	293.6	282.1	272.9	269.9
137.5°	303.6	291.3	282.1	278.3
140°	312.8	300.5	291.3	288.3
142.5°	321.2	309.0	300.5	298.2
145°	330.4	318.9	311.3	308.2
147.5°	339.6	328.9	321.2	318.9
150°	348.1	338.1	332.0	329.7
152.5°	355.7	347.3	341.2	340.4
155°	364.2	355.7	351.1	350.4
157.5°	371.1	363.4	359.6	358.8
160°	377.2	371.1	368.0	367.2
162.5°	382.6	378.0	374.9	375.7
165°	387.2	382.6	381.0	381.8
167.5°	391.0	387.9	386.4	387.2
170°	394.1	391.8	391.0	392.5
172.5°	396.4	394.1	394.8	395.6
175°	397.9	396.4	397.1	397.9
177.5°	398.7	397.1	397.9	399.4
180°	398.7	398.7	398.7	398.7

(END OF REPORT)