

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008926

Luminaire Tested: S122DIP-B290D725UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008926
REPORT IS A COMBINATION OF REPORTS P984041 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB40-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3779.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	33	31	30
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	27	26
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9054	9054	9054	9054
5°	9075	9654	9110	7680
10°	8971	10539	9027	6332
15°	8753	11116	8875	5334
20°	8617	10438	8617	4636
25°	8342	8967	8380	4146
30°	7890	7049	8041	3755
35°	7490	4874	7616	3435
40°	7029	3680	7110	3181
45°	6462	3025	6567	2906
50°	5971	2654	5983	2661
55°	5412	2262	5446	2394
60°	4816	1890	4882	2089
65°	4284	1537	4362	1784
70°	3750	1205	3846	1438
75°	3149	875	3273	1043
80°	2459	555	2635	620
85°	1610	280	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9360 cd/sqm

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.4
10°-20°	158.6	4.2
20°-30°	230.1	6.1
30°-40°	242.6	6.4
40°-50°	214.7	5.7
50°-60°	171.4	4.5
60°-70°	116.4	3.1
70°-80°	59.6	1.6
80°-90°	16.6	0.4
90°-100°	55.6	1.5
100°-110°	176.9	4.7
110°-120°	302.6	8.0
120°-130°	398.0	10.5
130°-140°	446.8	11.8
140°-150°	438.1	11.6
150°-160°	367.5	9.7
160°-170°	243.7	6.4
170°-180°	85.2	2.3
0°-30°	443.2	11.7
0°-40°	685.8	18.1
0°-60°	1071.9	28.4
0°-90°	1264.6	33.5
90°-120°	535.2	14.2
90°-150°	1818.0	48.1
90°-180°	2514.0	66.5
0°-180°	3779.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	572	639	575	508	572	54
15°	538	785	545	377	538	152
25°	483	654	485	302	483	221
35°	394	356	401	251	394	247
45°	296	215	301	206	296	230
55°	203	151	204	160	203	181
65°	120	93	123	108	120	120
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	26	1	26	1	3
95°	40	47	40	47	40	44
105°	163	168	163	168	163	172
115°	304	304	304	304	304	300
125°	442	443	442	443	442	395
135°	572	578	572	578	572	442
145°	694	701	694	701	694	433
155°	793	799	793	799	793	365
165°	863	864	863	864	863	243
175°	898	895	898	895	898	85
180°	899	899	899	899	899	

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	575.1	576.4	578.6	579.0	583.4	586.9	590.9	590.9	592.2	591.8	588.3
5°	572.4	576.4	582.1	586.9	594.9	598.4	603.7	607.6	611.1	613.8	613.3
7.5°	568.0	575.1	583.4	592.7	603.2	609.4	616.8	623.9	628.7	633.1	636.2
10°	560.6	572.4	583.9	596.2	609.8	618.2	627.0	636.2	643.7	652.0	659.9
12.5°	550.5	567.6	581.7	597.9	614.6	623.9	637.9	645.0	659.5	680.6	686.3
15°	537.7	561.0	574.2	594.9	616.8	624.3	643.7	655.1	685.0	698.2	714.0
17.5°	525.8	551.8	569.4	593.1	614.6	629.2	648.1	671.4	696.4	715.3	732.9
20°	516.2	541.2	562.3	588.7	616.0	634.4	654.2	682.4	709.6	729.0	742.6
22.5°	494.2	526.3	550.9	580.4	613.3	638.8	657.7	688.5	718.0	729.8	741.7
25°	483.2	510.9	539.5	572.9	611.6	641.9	658.2	692.5	718.4	722.8	725.4
27.5°	463.0	494.2	527.6	565.8	611.1	636.6	657.3	688.5	709.2	706.1	698.2
30°	437.9	476.2	513.1	554.4	605.0	632.7	652.0	680.6	691.1	675.3	661.2
32.5°	419.4	455.5	496.4	544.3	597.9	624.3	643.2	665.6	667.8	639.3	615.5
35°	394.4	434.4	480.5	531.1	586.1	609.8	627.4	641.0	630.5	590.5	562.3
37.5°	372.0	411.5	460.8	512.2	569.8	593.1	607.2	609.4	583.4	548.3	506.9
40°	347.3	388.2	439.7	493.7	551.8	572.0	580.8	574.2	536.8	495.9	448.0
42.5°	322.7	363.2	418.6	474.0	528.9	546.1	549.6	531.5	485.8	437.9	382.5
45°	295.9	338.1	393.5	449.3	502.5	512.2	512.6	486.7	432.6	382.5	331.1
47.5°	273.9	313.0	368.0	423.8	468.7	475.3	472.6	442.7	383.8	327.5	282.7
50°	249.7	287.1	341.6	396.6	434.8	436.6	430.0	387.3	329.7	278.3	242.7
52.5°	223.8	261.6	311.7	364.5	398.8	396.1	383.4	337.7	283.6	240.9	213.7
55°	203.1	236.5	283.6	335.0	359.2	351.7	337.7	291.1	248.4	212.4	188.6
57.5°	180.3	209.7	255.9	300.7	314.8	307.8	293.7	250.2	210.6	183.3	167.5
60°	158.7	185.5	226.0	263.4	274.3	266.9	250.6	211.5	182.9	160.0	148.2
62.5°	138.9	162.2	196.1	230.4	234.8	227.3	213.2	181.6	157.0	138.9	130.1
65°	120.5	142.4	169.7	195.6	199.6	191.7	177.2	154.3	133.7	122.2	113.9
67.5°	102.4	120.0	144.2	163.1	165.3	157.8	146.0	127.5	114.8	102.4	96.3
70°	86.6	99.8	118.7	134.1	135.0	127.9	121.8	105.1	95.4	86.6	81.8
72.5°	71.2	80.5	95.0	106.4	106.8	102.4	96.7	86.2	77.8	71.7	66.8
75°	56.3	64.2	73.0	83.1	82.7	79.1	74.7	68.1	61.1	57.2	55.0
77.5°	43.1	47.9	55.0	61.6	61.6	59.8	57.2	52.3	47.9	44.0	41.8
80°	30.8	33.9	39.6	41.8	42.6	42.2	40.0	36.5	34.7	31.7	30.8
82.5°	19.8	22.0	24.6	26.8	28.1	27.3	26.8	25.1	22.4	21.5	20.7
85°	11.4	12.3	13.6	14.9	15.4	14.9	15.8	14.5	13.2	13.2	12.8
87.5°	4.8	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	0.8	2.8	4.8	6.9	8.9	9.9	11.8	15.5	19.2	22.9	26.6
92.5°	16.7	18.1	19.4	20.8	22.1	22.8	22.9	23.0	23.2	23.3	23.5
95°	39.5	41.2	42.9	44.6	46.3	47.1	47.3	47.6	47.9	48.3	48.6
97.5°	66.0	67.5	69.1	70.6	72.1	72.9	73.2	73.9	74.6	75.2	75.9
100°	96.4	97.8	99.1	100.5	101.8	102.5	102.7	103.2	103.7	104.2	104.7
102.5°	128.3	129.3	130.3	131.3	132.3	132.8	133.1	133.8	134.5	135.2	135.9
105°	163.2	163.7	164.2	164.7	165.2	165.5	165.7	166.0	166.3	166.7	167.0
107.5°	198.1	198.8	199.4	200.1	200.8	201.1	201.1	201.1	201.1	201.1	201.1
110°	231.5	232.5	233.5	234.5	235.5	236.0	236.0	236.0	236.0	236.0	236.0



TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	267.9	268.9	269.9	271.0	272.0	272.5	272.4	272.2	272.1	271.9	271.7
115°	303.6	304.6	305.6	306.6	307.6	308.1	307.9	307.6	307.3	306.9	306.6
117.5°	339.3	340.6	342.0	343.3	344.6	345.3	344.9	344.0	343.2	342.3	341.5
120°	374.9	376.3	377.6	379.0	380.3	381.0	380.3	379.0	377.6	376.3	374.9
122.5°	407.6	409.3	410.9	412.6	414.3	415.1	414.7	413.9	413.0	412.2	411.4
125°	441.7	443.2	444.7	446.2	447.7	448.5	448.3	447.8	447.3	446.8	446.3
127.5°	475.1	477.0	478.8	480.7	482.6	483.5	483.2	482.5	481.8	481.1	480.4
130°	506.2	508.4	510.6	512.8	515.0	516.1	515.9	515.6	515.3	514.9	514.6
132.5°	541.1	542.8	544.5	546.2	547.9	548.7	548.8	549.0	549.1	549.3	549.5
135°	571.5	573.3	575.2	577.0	578.9	579.8	580.0	580.3	580.7	581.0	581.4
137.5°	604.9	606.4	607.9	609.4	610.9	611.7	611.9	612.2	612.5	612.9	613.2
140°	634.5	636.0	637.5	639.0	640.5	641.3	641.7	642.6	643.4	644.3	645.1
142.5°	664.8	666.3	667.9	669.4	670.9	671.7	672.0	672.5	673.0	673.5	674.0
145°	693.7	694.9	696.1	697.2	698.4	699.0	699.5	700.5	701.6	702.6	703.6
147.5°	719.5	721.0	722.5	724.0	725.5	726.3	726.6	727.3	728.0	728.7	729.4
150°	746.1	747.1	748.1	749.1	750.1	750.6	750.9	751.6	752.3	752.9	753.6
152.5°	769.6	770.6	771.6	772.6	773.6	774.1	774.5	775.4	776.2	777.1	777.9
155°	793.1	793.6	794.1	794.6	795.1	795.4	795.7	796.2	796.7	797.2	797.7
157.5°	813.6	813.9	814.3	814.6	814.9	815.1	815.3	815.6	815.9	816.3	816.6
160°	831.8	832.1	832.5	832.8	833.1	833.3	833.4	833.6	833.7	833.9	834.1
162.5°	848.5	848.5	848.5	848.5	848.5	848.5	848.6	848.8	848.9	849.1	849.3
165°	862.9	862.7	862.6	862.4	862.3	862.2	862.2	862.2	862.2	862.2	862.2
167.5°	875.8	875.3	874.8	874.3	873.8	873.6	873.6	873.6	873.6	873.6	873.6
170°	885.7	885.2	884.7	884.2	883.7	883.4	883.3	883.2	883.0	882.9	882.7
172.5°	892.5	892.0	891.5	891.0	890.5	890.3	890.2	890.0	889.9	889.7	889.5
175°	897.8	897.3	896.8	896.3	895.8	895.6	895.4	895.1	894.7	894.4	894.0
177.5°	900.9	900.4	899.9	899.4	898.9	898.6	898.4	898.1	897.8	897.4	897.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	594.4	594.9	595.7	600.1	602.3	602.8	601.0	605.0	606.3	605.0	604.1
5°	622.6	625.2	630.5	636.2	635.7	636.2	638.8	641.5	642.3	638.8	640.1
7.5°	647.2	652.5	658.2	667.0	667.0	671.4	673.1	675.3	680.6	678.0	677.1
10°	675.3	682.4	692.9	707.0	707.4	711.8	716.2	723.2	725.4	723.7	724.6
12.5°	710.5	724.1	725.0	740.4	747.4	748.3	755.3	754.0	758.4	758.4	765.9
15°	725.9	747.0	758.9	773.8	778.2	772.9	778.6	784.8	785.2	785.2	784.8
17.5°	753.6	761.9	773.8	781.7	783.5	783.5	783.9	786.6	784.8	781.3	783.9
20°	759.3	762.8	767.2	766.3	767.2	762.8	758.4	754.0	754.5	752.3	758.9
22.5°	748.7	747.9	737.7	731.2	731.2	722.4	714.0	710.1	706.1	707.4	709.6
25°	722.4	708.7	696.4	686.7	684.6	670.5	659.0	655.5	648.9	654.2	655.1
27.5°	680.2	664.8	645.0	636.6	625.2	619.5	611.6	601.0	587.4	595.3	594.0
30°	634.9	612.0	595.7	575.5	557.5	556.2	541.2	523.6	516.6	516.6	520.6
32.5°	584.3	554.0	530.2	501.7	484.1	476.6	458.6	441.0	444.9	431.7	436.6
35°	525.4	485.4	455.5	427.8	414.6	405.8	382.5	372.8	362.3	356.1	367.6
37.5°	469.1	423.0	384.7	354.4	349.5	333.7	317.9	311.7	305.6	308.2	307.8
40°	400.5	359.6	325.3	301.6	293.3	285.8	275.2	267.8	263.8	266.0	266.4
42.5°	338.5	304.2	278.7	262.0	255.0	249.7	244.5	238.3	237.0	237.0	238.7
45°	290.6	262.5	245.3	231.7	227.7	223.8	219.8	217.2	216.3	214.6	215.9
47.5°	252.4	229.9	219.4	209.3	204.9	204.0	200.5	199.2	197.4	197.0	197.4
50°	220.3	206.2	196.5	190.8	187.7	186.4	184.7	182.0	181.1	183.3	182.5
52.5°	197.8	184.7	179.4	173.7	171.9	170.1	167.5	167.9	167.5	166.6	166.6
55°	175.4	167.1	161.8	157.4	157.0	155.2	153.0	152.1	151.7	150.8	152.1
57.5°	157.4	150.8	146.0	142.0	140.3	140.3	138.1	136.3	136.3	135.9	136.3
60°	139.4	132.8	129.7	125.7	124.4	124.0	122.7	121.8	120.5	120.5	120.5
62.5°	122.7	117.4	113.9	110.4	110.8	108.6	106.8	106.0	106.0	106.4	106.4
65°	106.8	103.3	98.9	95.8	95.0	94.5	93.6	93.2	91.9	92.8	92.8
67.5°	92.3	87.5	84.9	83.5	82.2	81.8	80.9	80.0	79.6	79.1	80.0
70°	77.8	73.9	71.7	70.8	69.5	69.0	68.6	67.3	67.7	68.1	68.6
72.5°	64.6	61.1	60.7	58.0	58.0	58.0	56.3	57.2	56.7	55.8	56.7
75°	51.0	49.2	48.4	47.0	47.5	47.0	46.6	45.3	45.3	45.7	46.2
77.5°	40.4	38.7	38.3	36.9	36.1	36.9	36.1	35.6	35.6	36.1	36.1
80°	29.9	29.0	27.7	27.7	27.7	27.3	27.3	27.3	26.8	26.4	26.8
82.5°	19.8	19.8	19.3	18.9	19.3	18.5	18.9	18.9	18.9	18.9	18.9
85°	12.8	12.3	12.3	11.9	11.9	11.9	12.3	11.4	11.4	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	26.2	25.9	25.5	25.2	25.0	25.1	25.3	25.4	25.6	25.8	25.6
92.5°	23.7	23.9	24.0	24.2	24.3	24.3	24.3	24.3	24.3	24.3	24.3
95°	48.6	48.6	48.6	48.6	48.6	48.4	48.1	47.8	47.4	47.1	47.4
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
100°	104.7	104.7	104.7	104.7	104.7	104.6	104.5	104.3	104.2	104.0	104.2
102.5°	136.1	136.2	136.4	136.5	136.6	136.5	136.4	136.2	136.1	135.9	136.1
105°	167.3	167.7	168.0	168.3	168.5	168.5	168.5	168.5	168.5	168.5	168.5
107.5°	201.3	201.5	201.6	201.8	201.9	201.5	200.6	199.8	198.9	198.1	198.9
110°	236.0	236.0	236.0	236.0	236.0	235.8	235.3	234.8	234.3	233.8	234.3

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	271.2	270.7	270.2	269.7	269.4	269.2	268.9	268.6	268.2	267.9	268.2
115°	306.4	306.3	306.1	306.0	305.9	305.6	305.1	304.6	304.1	303.6	304.1
117.5°	341.0	340.5	340.0	339.5	339.3	339.0	338.5	338.0	337.5	337.0	337.5
120°	374.9	374.9	374.9	374.9	374.9	374.6	374.1	373.6	373.1	372.6	373.1
122.5°	410.9	410.4	409.9	409.4	409.1	408.9	408.6	408.3	407.9	407.6	407.9
125°	445.8	445.3	444.8	444.3	444.0	443.9	443.7	443.6	443.4	443.2	443.4
127.5°	479.7	479.1	478.4	477.7	477.4	477.1	476.6	476.1	475.6	475.1	475.6
130°	514.3	513.9	513.6	513.3	513.1	512.8	512.1	511.4	510.7	510.0	510.7
132.5°	548.7	547.8	547.0	546.1	545.7	545.4	544.9	544.4	543.9	543.4	543.9
135°	581.2	581.0	580.9	580.7	580.6	580.3	579.8	579.3	578.8	578.3	578.8
137.5°	613.0	612.9	612.7	612.6	612.5	612.2	611.5	610.8	610.1	609.4	610.1
140°	645.1	645.1	645.1	645.1	645.1	644.8	644.1	643.4	642.8	642.1	642.8
142.5°	674.2	674.3	674.5	674.6	674.7	674.4	673.7	673.0	672.4	671.7	672.4
145°	703.8	703.9	704.1	704.2	704.3	704.0	703.3	702.6	702.0	701.3	702.0
147.5°	729.7	730.1	730.4	730.7	730.9	730.6	729.9	729.2	728.5	727.8	728.5
150°	754.1	754.6	755.1	755.6	755.9	755.6	755.1	754.6	754.1	753.6	754.1
152.5°	778.6	779.3	780.0	780.7	781.0	780.7	780.0	779.3	778.6	777.9	778.6
155°	798.5	799.4	800.2	801.1	801.5	801.2	800.7	800.2	799.7	799.2	799.7
157.5°	817.8	819.0	820.1	821.3	821.9	821.5	820.7	819.8	819.0	818.2	819.0
160°	835.1	836.1	837.1	838.1	838.6	838.3	837.6	836.9	836.3	835.6	836.3
162.5°	850.5	851.7	852.8	854.0	854.6	854.2	853.3	852.5	851.6	850.8	851.6
165°	863.4	864.6	865.7	866.9	867.5	867.1	866.2	865.4	864.5	863.7	864.5
167.5°	874.8	876.0	877.1	878.3	878.9	878.5	877.6	876.8	875.9	875.1	875.9
170°	883.9	885.1	886.2	887.4	888.0	887.5	886.5	885.4	884.4	883.4	884.4
172.5°	890.7	891.9	893.0	894.2	894.8	894.3	893.3	892.3	891.3	890.3	891.3
175°	895.2	896.4	897.6	898.8	899.4	898.9	897.9	896.8	895.8	894.8	895.8
177.5°	898.1	899.1	900.1	901.1	901.6	901.1	900.1	899.1	898.1	897.1	898.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	606.3	603.2	600.6	601.0	603.2	601.5	597.1	591.3	589.1	586.5	589.1
5°	642.8	640.1	634.9	635.3	634.0	632.2	625.2	616.4	616.4	609.4	608.5
7.5°	678.8	674.9	671.4	670.5	665.6	662.1	656.0	643.7	638.8	630.5	625.6
10°	719.3	716.2	712.2	707.4	704.8	698.6	688.5	670.5	661.7	650.3	641.9
12.5°	760.2	759.7	750.9	741.3	740.8	731.2	724.1	699.9	688.1	672.7	652.9
15°	786.1	783.9	779.1	774.2	775.6	765.0	749.2	720.6	712.7	694.2	673.1
17.5°	785.7	785.7	784.4	783.5	782.2	779.1	770.3	751.4	738.6	715.3	695.5
20°	760.6	766.3	767.6	767.2	771.6	773.8	773.4	761.5	751.4	730.7	710.5
22.5°	710.5	723.7	729.4	732.9	742.1	747.0	758.4	754.0	751.4	736.0	718.8
25°	663.9	668.3	685.4	686.3	699.1	710.9	722.4	729.8	739.5	733.8	719.3
27.5°	603.7	613.8	626.1	635.3	637.9	662.1	681.0	695.1	717.1	718.8	714.0
30°	535.5	540.3	560.6	572.9	586.9	604.5	631.8	656.0	675.8	693.8	699.9
32.5°	452.4	472.2	484.1	499.0	511.3	542.5	576.0	607.2	630.0	660.4	673.6
35°	376.3	391.7	412.0	418.1	440.5	466.9	510.4	550.5	585.2	616.0	642.8
37.5°	313.5	325.8	347.3	357.0	370.2	404.0	440.5	490.2	532.0	569.8	603.2
40°	270.4	279.6	295.9	299.0	310.0	340.7	370.2	416.8	472.2	523.2	559.7
42.5°	240.9	245.3	256.3	260.3	267.3	288.0	314.4	358.3	409.8	462.5	514.0
45°	219.8	222.9	229.5	233.0	241.8	251.0	272.6	307.8	348.2	401.4	456.8
47.5°	200.9	204.9	207.5	209.7	214.6	224.7	238.7	264.7	303.4	352.2	405.8
50°	185.1	186.4	191.3	191.7	194.8	201.4	214.6	230.4	261.2	300.7	352.6
52.5°	169.3	170.6	173.7	176.7	178.1	183.3	192.1	205.3	228.2	259.4	305.6
55°	153.4	155.2	158.3	160.5	161.8	166.2	171.5	184.2	202.2	224.2	262.0
57.5°	137.6	141.6	142.4	143.8	146.0	150.8	155.6	163.1	177.2	197.4	225.1
60°	122.7	124.0	127.1	128.4	130.6	133.2	139.4	145.1	155.2	171.0	196.1
62.5°	107.3	110.4	111.7	113.0	114.8	117.8	121.8	127.9	136.7	149.5	169.3
65°	94.1	94.5	97.2	98.9	100.7	102.9	106.8	112.6	117.8	129.7	144.2
67.5°	81.3	82.2	83.1	84.9	87.1	89.3	92.8	95.8	102.4	110.4	121.8
70°	69.0	69.0	71.2	72.5	72.1	74.7	77.4	80.9	85.7	93.2	102.4
72.5°	58.0	57.6	59.4	59.8	60.7	62.4	64.2	67.7	70.3	76.1	83.1
75°	46.2	47.0	47.9	47.9	49.2	50.6	52.3	54.1	57.2	60.7	65.9
77.5°	36.5	36.5	37.4	37.8	39.1	38.7	40.4	42.2	44.4	47.5	51.4
80°	26.8	27.7	27.7	27.7	28.1	28.6	30.3	31.7	33.0	35.2	36.9
82.5°	18.9	18.9	19.8	19.8	19.8	20.7	20.7	21.1	22.0	23.3	24.6
85°	11.9	11.9	11.9	12.3	11.9	12.3	13.2	12.8	13.2	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	25.4	25.3	25.1	25.0	25.2	25.5	25.9	26.2	26.6	22.9	19.2
92.5°	24.3	24.3	24.3	24.3	24.2	24.0	23.9	23.7	23.5	23.3	23.2
95°	47.8	48.1	48.4	48.6	48.6	48.6	48.6	48.6	48.6	48.3	47.9
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.2	74.6
100°	104.3	104.5	104.6	104.7	104.7	104.7	104.7	104.7	104.7	104.2	103.7
102.5°	136.2	136.4	136.5	136.6	136.5	136.4	136.2	136.1	135.9	135.2	134.5
105°	168.5	168.5	168.5	168.5	168.3	168.0	167.7	167.3	167.0	166.7	166.3
107.5°	199.8	200.6	201.5	201.9	201.8	201.6	201.5	201.3	201.1	201.1	201.1
110°	234.8	235.3	235.8	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	268.6	268.9	269.2	269.4	269.7	270.2	270.7	271.2	271.7	271.9	272.1
115°	304.6	305.1	305.6	305.9	306.0	306.1	306.3	306.4	306.6	306.9	307.3
117.5°	338.0	338.5	339.0	339.3	339.5	340.0	340.5	341.0	341.5	342.3	343.2
120°	373.6	374.1	374.6	374.9	374.9	374.9	374.9	374.9	374.9	376.3	377.6
122.5°	408.3	408.6	408.9	409.1	409.4	409.9	410.4	410.9	411.4	412.2	413.0
125°	443.6	443.7	443.9	444.0	444.3	444.8	445.3	445.8	446.3	446.8	447.3
127.5°	476.1	476.6	477.1	477.4	477.7	478.4	479.1	479.7	480.4	481.1	481.8
130°	511.4	512.1	512.8	513.1	513.3	513.6	513.9	514.3	514.6	514.9	515.3
132.5°	544.4	544.9	545.4	545.7	546.1	547.0	547.8	548.7	549.5	549.3	549.1
135°	579.3	579.8	580.3	580.6	580.7	580.9	581.0	581.2	581.4	581.0	580.7
137.5°	610.8	611.5	612.2	612.5	612.6	612.7	612.9	613.0	613.2	612.9	612.5
140°	643.4	644.1	644.8	645.1	645.1	645.1	645.1	645.1	645.1	644.3	643.4
142.5°	673.0	673.7	674.4	674.7	674.6	674.5	674.3	674.2	674.0	673.5	673.0
145°	702.6	703.3	704.0	704.3	704.2	704.1	703.9	703.8	703.6	702.6	701.6
147.5°	729.2	729.9	730.6	730.9	730.7	730.4	730.1	729.7	729.4	728.7	728.0
150°	754.6	755.1	755.6	755.9	755.6	755.1	754.6	754.1	753.6	752.9	752.3
152.5°	779.3	780.0	780.7	781.0	780.7	780.0	779.3	778.6	777.9	777.1	776.2
155°	800.2	800.7	801.2	801.5	801.1	800.2	799.4	798.5	797.7	797.2	796.7
157.5°	819.8	820.7	821.5	821.9	821.3	820.1	819.0	817.8	816.6	816.3	815.9
160°	836.9	837.6	838.3	838.6	838.1	837.1	836.1	835.1	834.1	833.9	833.7
162.5°	852.5	853.3	854.2	854.6	854.0	852.8	851.7	850.5	849.3	849.1	848.9
165°	865.4	866.2	867.1	867.5	866.9	865.7	864.6	863.4	862.2	862.2	862.2
167.5°	876.8	877.6	878.5	878.9	878.3	877.1	876.0	874.8	873.6	873.6	873.6
170°	885.4	886.5	887.5	888.0	887.4	886.2	885.1	883.9	882.7	882.9	883.0
172.5°	892.3	893.3	894.3	894.8	894.2	893.0	891.9	890.7	889.5	889.7	889.9
175°	896.8	897.9	898.9	899.4	898.8	897.6	896.4	895.2	894.0	894.4	894.7
177.5°	899.1	900.1	901.1	901.6	901.1	900.1	899.1	898.1	897.1	897.4	897.8
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	586.9	584.7	583.4	584.3	581.7	575.1	575.1	577.3	574.6	572.0	568.0
5°	603.2	598.8	596.2	595.7	589.6	579.0	576.8	574.6	568.9	562.8	556.2
7.5°	619.0	611.1	606.7	603.7	594.9	581.2	575.5	570.7	561.4	552.2	543.9
10°	632.2	620.8	615.5	610.7	599.3	582.1	572.9	564.1	552.2	540.3	529.8
12.5°	642.8	629.6	623.0	616.0	601.9	579.5	568.0	554.0	542.1	526.3	515.7
15°	660.4	633.1	627.0	620.4	605.9	575.1	561.0	545.2	528.9	507.8	496.4
17.5°	674.4	637.9	637.5	623.4	604.5	573.3	551.8	531.1	513.5	492.4	474.4
20°	682.8	645.4	638.4	623.9	600.1	561.4	539.0	516.2	497.3	471.8	453.7
22.5°	689.8	656.0	637.5	619.9	590.9	557.5	524.5	503.0	477.0	449.3	432.2
25°	692.5	658.2	638.8	618.6	584.3	546.1	508.7	485.4	456.4	431.3	408.0
27.5°	692.9	657.7	634.0	612.9	575.1	531.1	492.9	468.2	436.1	407.1	383.8
30°	688.5	652.9	631.4	608.5	566.3	517.5	473.5	446.3	412.0	382.9	358.8
32.5°	675.3	643.2	625.6	600.6	554.9	498.6	455.0	424.7	388.7	360.1	336.8
35°	653.3	631.4	612.0	588.7	539.9	481.0	436.6	401.0	364.5	337.2	315.2
37.5°	626.1	614.2	596.2	573.3	522.8	465.2	415.9	376.3	339.9	313.5	291.9
40°	589.1	592.2	574.6	554.0	502.5	443.6	389.1	351.3	317.0	292.4	271.3
42.5°	549.1	561.9	551.8	532.0	480.1	419.9	369.3	327.5	294.1	268.6	251.0
45°	506.0	528.0	521.9	507.4	456.8	394.8	341.2	300.7	271.3	246.6	231.3
47.5°	459.0	490.2	490.2	479.7	430.9	369.8	317.0	275.7	246.6	229.1	214.1
50°	411.1	446.3	452.0	444.9	401.8	341.2	287.5	250.2	225.1	208.0	197.0
52.5°	361.0	401.8	412.4	408.9	371.1	313.9	263.4	226.9	204.0	189.1	179.4
55°	313.0	360.5	372.0	373.3	338.1	284.0	236.5	204.4	182.5	172.3	164.0
57.5°	267.8	313.5	326.2	328.4	304.7	256.8	211.5	183.3	163.6	155.2	148.6
60°	229.1	267.3	284.0	288.9	268.2	225.1	188.2	160.9	146.0	138.1	131.9
62.5°	197.4	228.2	245.8	247.1	237.9	197.4	164.0	141.1	128.4	121.3	118.3
65°	166.6	194.3	204.9	210.2	202.7	171.0	141.6	122.7	112.6	106.4	103.3
67.5°	142.0	159.6	168.4	175.4	167.9	144.2	120.5	105.1	97.6	91.4	89.7
70°	116.5	131.0	137.6	144.6	138.1	120.0	102.9	88.8	82.2	77.4	75.2
72.5°	93.2	104.6	110.8	115.2	111.2	96.3	82.2	72.5	67.7	64.2	62.9
75°	73.9	81.8	85.3	88.4	86.6	75.2	66.4	58.5	54.1	51.0	50.1
77.5°	56.3	62.0	65.9	66.8	64.6	57.2	49.7	44.8	41.3	39.6	38.7
80°	40.0	43.5	45.7	47.0	44.8	41.8	36.5	33.0	29.9	27.7	27.3
82.5°	26.8	28.6	30.3	29.9	29.0	26.4	23.3	21.5	20.2	18.5	18.5
85°	15.4	15.8	16.7	17.1	16.7	14.9	13.2	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	4.0
90°	15.5	11.8	9.9	8.9	6.9	4.8	2.8	0.8	2.8	4.8	6.9
92.5°	23.0	22.9	22.8	22.1	20.8	19.4	18.1	16.7	18.1	19.4	20.8
95°	47.6	47.3	47.1	46.3	44.6	42.9	41.2	39.5	41.2	42.9	44.6
97.5°	73.9	73.2	72.9	72.1	70.6	69.1	67.5	66.0	67.5	69.1	70.6
100°	103.2	102.7	102.5	101.8	100.5	99.1	97.8	96.4	97.8	99.1	100.5
102.5°	133.8	133.1	132.8	132.3	131.3	130.3	129.3	128.3	129.3	130.3	131.3
105°	166.0	165.7	165.5	165.2	164.7	164.2	163.7	163.2	163.7	164.2	164.7
107.5°	201.1	201.1	201.1	200.8	200.1	199.4	198.8	198.1	198.8	199.4	200.1
110°	236.0	236.0	236.0	235.5	234.5	233.5	232.5	231.5	232.5	233.5	234.5

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	272.2	272.4	272.5	272.0	271.0	269.9	268.9	267.9	268.9	269.9	271.0
115°	307.6	307.9	308.1	307.6	306.6	305.6	304.6	303.6	304.6	305.6	306.6
117.5°	344.0	344.9	345.3	344.6	343.3	342.0	340.6	339.3	340.6	342.0	343.3
120°	379.0	380.3	381.0	380.3	379.0	377.6	376.3	374.9	376.3	377.6	379.0
122.5°	413.9	414.7	415.1	414.3	412.6	410.9	409.3	407.6	409.3	410.9	412.6
125°	447.8	448.3	448.5	447.7	446.2	444.7	443.2	441.7	443.2	444.7	446.2
127.5°	482.5	483.2	483.5	482.6	480.7	478.8	477.0	475.1	477.0	478.8	480.7
130°	515.6	515.9	516.1	515.0	512.8	510.6	508.4	506.2	508.4	510.6	512.8
132.5°	549.0	548.8	548.7	547.9	546.2	544.5	542.8	541.1	542.8	544.5	546.2
135°	580.3	580.0	579.8	578.9	577.0	575.2	573.3	571.5	573.3	575.2	577.0
137.5°	612.2	611.9	611.7	610.9	609.4	607.9	606.4	604.9	606.4	607.9	609.4
140°	642.6	641.7	641.3	640.5	639.0	637.5	636.0	634.5	636.0	637.5	639.0
142.5°	672.5	672.0	671.7	670.9	669.4	667.9	666.3	664.8	666.3	667.9	669.4
145°	700.5	699.5	699.0	698.4	697.2	696.1	694.9	693.7	694.9	696.1	697.2
147.5°	727.3	726.6	726.3	725.5	724.0	722.5	721.0	719.5	721.0	722.5	724.0
150°	751.6	750.9	750.6	750.1	749.1	748.1	747.1	746.1	747.1	748.1	749.1
152.5°	775.4	774.5	774.1	773.6	772.6	771.6	770.6	769.6	770.6	771.6	772.6
155°	796.2	795.7	795.4	795.1	794.6	794.1	793.6	793.1	793.6	794.1	794.6
157.5°	815.6	815.3	815.1	814.9	814.6	814.3	813.9	813.6	813.9	814.3	814.6
160°	833.6	833.4	833.3	833.1	832.8	832.5	832.1	831.8	832.1	832.5	832.8
162.5°	848.8	848.6	848.5	848.5	848.5	848.5	848.5	848.5	848.5	848.5	848.5
165°	862.2	862.2	862.2	862.3	862.4	862.6	862.7	862.9	862.7	862.6	862.4
167.5°	873.6	873.6	873.6	873.8	874.3	874.8	875.3	875.8	875.3	874.8	874.3
170°	883.2	883.3	883.4	883.7	884.2	884.7	885.2	885.7	885.2	884.7	884.2
172.5°	890.0	890.2	890.3	890.5	891.0	891.5	892.0	892.5	892.0	891.5	891.0
175°	895.1	895.4	895.6	895.8	896.3	896.8	897.3	897.8	897.3	896.8	896.3
177.5°	898.1	898.4	898.6	898.9	899.4	899.9	900.4	900.9	900.4	899.9	899.4
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	565.8	568.0	567.6	563.2	558.4	554.4	546.9	547.8	545.2	545.6	548.3
5°	551.8	551.8	550.0	543.9	535.9	531.5	523.2	521.0	515.7	515.3	514.8
7.5°	536.8	534.6	532.4	523.6	514.0	506.9	495.5	492.9	487.6	484.1	482.3
10°	519.2	516.2	511.8	501.7	489.8	481.0	469.1	465.6	455.5	451.1	448.5
12.5°	499.9	498.1	491.1	482.7	463.4	453.7	436.6	440.1	430.0	421.2	419.9
15°	480.5	474.0	470.0	456.4	433.1	428.7	415.0	408.0	398.8	391.7	391.7
17.5°	461.6	451.5	442.7	428.2	411.1	398.8	388.7	385.1	373.7	366.7	365.4
20°	436.6	425.2	423.0	402.3	390.4	376.8	367.1	358.3	350.0	346.9	344.7
22.5°	412.8	399.7	396.1	378.5	366.7	353.0	343.4	337.2	331.1	328.9	324.9
25°	387.3	379.4	374.2	355.2	342.1	329.3	322.7	318.3	312.6	312.2	309.5
27.5°	362.7	355.2	350.0	331.9	322.3	310.4	305.1	300.3	297.2	295.9	294.6
30°	341.6	333.3	327.1	313.9	302.0	292.4	288.0	284.9	283.1	280.9	280.5
32.5°	318.3	313.5	305.1	295.0	285.8	276.5	273.9	271.7	269.1	268.2	267.8
35°	298.5	291.9	286.7	275.2	271.3	263.4	260.3	258.5	255.0	254.1	253.2
37.5°	279.2	273.0	267.3	260.3	252.8	248.4	246.6	244.0	242.3	242.7	241.8
40°	259.8	255.0	250.6	243.1	238.7	236.5	233.0	230.4	229.5	229.9	229.5
42.5°	240.9	236.5	233.9	228.2	223.8	221.6	219.4	216.8	218.1	218.1	219.4
45°	223.8	219.8	218.1	213.7	211.0	207.5	205.3	204.9	206.6	206.2	206.2
47.5°	206.2	204.9	202.7	198.7	195.2	193.0	192.6	192.6	194.3	195.2	194.8
50°	192.6	189.9	187.3	184.2	181.6	180.7	179.4	180.3	182.0	182.0	182.9
52.5°	175.4	173.7	172.8	170.1	168.4	168.4	168.4	168.8	170.1	171.5	171.0
55°	160.5	159.2	158.3	157.0	154.8	155.2	154.8	155.6	157.0	158.3	159.2
57.5°	144.6	144.2	143.3	141.1	141.1	140.7	142.0	142.4	144.6	145.5	146.8
60°	130.6	129.3	129.3	127.5	127.5	127.5	128.8	130.1	131.9	132.3	133.2
62.5°	115.6	115.6	115.2	113.9	113.9	115.2	115.6	117.4	118.3	118.3	119.6
65°	101.6	101.1	100.7	101.1	101.6	101.6	102.9	103.8	104.6	105.1	105.5
67.5°	87.5	87.1	87.9	87.5	88.4	90.1	89.7	91.0	92.3	92.3	92.8
70°	74.3	75.2	74.7	75.6	75.2	76.1	77.4	77.8	77.8	78.3	79.6
72.5°	62.0	62.0	62.0	61.6	62.0	62.9	63.8	64.2	65.1	65.5	66.8
75°	50.1	50.1	49.2	50.1	50.1	51.0	51.9	51.9	51.9	52.8	54.1
77.5°	37.8	38.3	37.8	38.7	38.7	39.1	40.0	39.6	40.4	40.9	41.3
80°	27.7	27.3	27.3	27.3	27.7	27.7	28.6	29.0	29.0	30.3	29.5
82.5°	17.6	18.0	17.6	18.0	18.0	18.5	18.0	18.5	18.9	19.8	19.3
85°	10.1	9.7	9.7	10.1	9.7	9.7	10.1	9.7	10.1	9.7	10.1
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	8.9	9.9	11.8	15.5	19.2	22.9	26.6	26.2	25.9	25.5	25.2
92.5°	22.1	22.8	22.9	23.0	23.2	23.3	23.5	23.7	23.9	24.0	24.2
95°	46.3	47.1	47.3	47.6	47.9	48.3	48.6	48.6	48.6	48.6	48.6
97.5°	72.1	72.9	73.2	73.9	74.6	75.2	75.9	75.9	75.9	75.9	75.9
100°	101.8	102.5	102.7	103.2	103.7	104.2	104.7	104.7	104.7	104.7	104.7
102.5°	132.3	132.8	133.1	133.8	134.5	135.2	135.9	136.1	136.2	136.4	136.5
105°	165.2	165.5	165.7	166.0	166.3	166.7	167.0	167.3	167.7	168.0	168.3
107.5°	200.8	201.1	201.1	201.1	201.1	201.1	201.1	201.3	201.5	201.6	201.8
110°	235.5	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	272.0	272.5	272.4	272.2	272.1	271.9	271.7	271.2	270.7	270.2	269.7
115°	307.6	308.1	307.9	307.6	307.3	306.9	306.6	306.4	306.3	306.1	306.0
117.5°	344.6	345.3	344.9	344.0	343.2	342.3	341.5	341.0	340.5	340.0	339.5
120°	380.3	381.0	380.3	379.0	377.6	376.3	374.9	374.9	374.9	374.9	374.9
122.5°	414.3	415.1	414.7	413.9	413.0	412.2	411.4	410.9	410.4	409.9	409.4
125°	447.7	448.5	448.3	447.8	447.3	446.8	446.3	445.8	445.3	444.8	444.3
127.5°	482.6	483.5	483.2	482.5	481.8	481.1	480.4	479.7	479.1	478.4	477.7
130°	515.0	516.1	515.9	515.6	515.3	514.9	514.6	514.3	513.9	513.6	513.3
132.5°	547.9	548.7	548.8	549.0	549.1	549.3	549.5	548.7	547.8	547.0	546.1
135°	578.9	579.8	580.0	580.3	580.7	581.0	581.4	581.2	581.0	580.9	580.7
137.5°	610.9	611.7	611.9	612.2	612.5	612.9	613.2	613.0	612.9	612.7	612.6
140°	640.5	641.3	641.7	642.6	643.4	644.3	645.1	645.1	645.1	645.1	645.1
142.5°	670.9	671.7	672.0	672.5	673.0	673.5	674.0	674.2	674.3	674.5	674.6
145°	698.4	699.0	699.5	700.5	701.6	702.6	703.6	703.8	703.9	704.1	704.2
147.5°	725.5	726.3	726.6	727.3	728.0	728.7	729.4	729.7	730.1	730.4	730.7
150°	750.1	750.6	750.9	751.6	752.3	752.9	753.6	754.1	754.6	755.1	755.6
152.5°	773.6	774.1	774.5	775.4	776.2	777.1	777.9	778.6	779.3	780.0	780.7
155°	795.1	795.4	795.7	796.2	796.7	797.2	797.7	798.5	799.4	800.2	801.1
157.5°	814.9	815.1	815.3	815.6	815.9	816.3	816.6	817.8	819.0	820.1	821.3
160°	833.1	833.3	833.4	833.6	833.7	833.9	834.1	835.1	836.1	837.1	838.1
162.5°	848.5	848.5	848.6	848.8	848.9	849.1	849.3	850.5	851.7	852.8	854.0
165°	862.3	862.2	862.2	862.2	862.2	862.2	862.2	863.4	864.6	865.7	866.9
167.5°	873.8	873.6	873.6	873.6	873.6	873.6	873.6	874.8	876.0	877.1	878.3
170°	883.7	883.4	883.3	883.2	883.0	882.9	882.7	883.9	885.1	886.2	887.4
172.5°	890.5	890.3	890.2	890.0	889.9	889.7	889.5	890.7	891.9	893.0	894.2
175°	895.8	895.6	895.4	895.1	894.7	894.4	894.0	895.2	896.4	897.6	898.8
177.5°	898.9	898.6	898.4	898.1	897.8	897.4	897.1	898.1	899.1	900.1	901.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	545.2	546.5	543.4	542.5	543.4	540.3	541.2	542.1	542.1	543.4	544.3
5°	513.5	511.8	508.7	507.8	506.9	508.2	507.4	508.7	509.1	512.2	512.6
7.5°	482.3	479.7	477.0	474.4	473.5	471.3	473.5	473.5	476.6	475.7	477.9
10°	445.4	444.9	441.4	440.1	438.3	434.8	439.7	438.3	440.5	444.5	445.4
12.5°	418.1	413.3	415.5	409.3	411.5	408.0	408.4	408.4	412.0	412.4	411.5
15°	392.2	388.2	382.5	379.9	378.5	376.8	382.5	382.9	380.3	386.5	384.3
17.5°	365.8	365.8	360.5	359.2	355.7	357.4	356.6	357.0	356.1	360.5	362.7
20°	342.9	340.7	339.0	339.4	335.0	334.1	333.3	334.1	337.2	340.3	341.2
22.5°	324.5	323.1	318.8	319.6	316.1	317.4	316.6	318.8	319.2	319.2	322.3
25°	306.9	305.1	305.6	303.8	302.5	302.5	301.2	302.5	304.2	305.1	305.6
27.5°	293.7	292.4	290.2	288.9	289.7	287.5	289.3	290.6	290.6	289.7	290.6
30°	277.9	278.7	278.7	274.3	276.1	275.2	276.5	277.4	277.4	277.9	277.0
32.5°	267.3	264.7	264.2	263.8	263.8	262.0	262.0	263.4	263.8	264.2	265.6
35°	253.2	253.2	251.0	252.4	250.6	251.0	250.6	251.0	251.9	250.6	251.9
37.5°	240.5	240.9	240.1	240.9	241.4	240.5	239.6	241.4	240.5	240.5	239.6
40°	229.5	229.1	229.5	229.5	229.5	229.9	229.1	229.1	229.1	228.2	227.3
42.5°	220.3	217.6	218.5	219.0	217.6	217.6	218.1	217.6	219.0	216.3	216.3
45°	207.1	206.2	206.6	206.6	207.5	206.2	207.1	207.5	206.2	205.8	204.9
47.5°	195.2	196.1	195.2	196.1	196.1	197.0	195.2	195.6	196.1	194.3	193.0
50°	183.3	183.3	184.7	184.2	184.7	183.8	183.8	183.3	183.8	182.9	181.6
52.5°	172.3	171.0	173.2	172.8	172.3	171.9	171.5	171.9	171.0	170.1	170.1
55°	158.7	158.7	160.0	160.5	160.5	159.6	158.7	159.2	158.7	158.3	157.8
57.5°	147.7	146.0	146.8	147.3	147.3	146.0	146.8	146.0	146.0	146.4	145.1
60°	133.7	133.7	132.8	134.1	134.1	133.2	133.2	133.7	132.8	132.3	131.9
62.5°	118.7	119.1	120.5	120.9	121.3	120.5	119.6	120.0	120.0	118.7	119.1
65°	106.0	106.8	108.6	108.2	107.3	107.7	106.8	107.3	106.0	106.4	105.1
67.5°	93.6	93.2	93.6	93.6	94.5	94.1	93.2	93.2	92.8	94.1	92.8
70°	80.5	80.5	80.5	80.5	80.9	81.3	80.5	79.6	80.0	79.1	78.7
72.5°	66.8	67.3	66.8	67.7	66.4	67.3	67.3	66.8	66.4	66.4	66.4
75°	54.1	55.0	53.6	54.1	53.6	54.5	54.1	54.1	53.2	52.8	53.2
77.5°	41.3	41.8	40.9	41.3	40.9	41.3	41.3	40.9	40.9	40.9	40.9
80°	29.5	29.9	29.5	29.0	28.6	29.5	28.6	29.0	29.5	29.0	29.9
82.5°	18.9	18.9	18.5	18.9	18.0	18.0	18.5	18.5	18.0	18.9	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.7	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	25.0	25.1	25.3	25.4	25.6	25.8	25.6	25.4	25.3	25.1	25.0
92.5°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3
95°	48.6	48.4	48.1	47.8	47.4	47.1	47.4	47.8	48.1	48.4	48.6
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
100°	104.7	104.6	104.5	104.3	104.2	104.0	104.2	104.3	104.5	104.6	104.7
102.5°	136.6	136.5	136.4	136.2	136.1	135.9	136.1	136.2	136.4	136.5	136.6
105°	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5
107.5°	201.9	201.5	200.6	199.8	198.9	198.1	198.9	199.8	200.6	201.5	201.9
110°	236.0	235.8	235.3	234.8	234.3	233.8	234.3	234.8	235.3	235.8	236.0



TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	269.4	269.2	268.9	268.6	268.2	267.9	268.2	268.6	268.9	269.2	269.4
115°	305.9	305.6	305.1	304.6	304.1	303.6	304.1	304.6	305.1	305.6	305.9
117.5°	339.3	339.0	338.5	338.0	337.5	337.0	337.5	338.0	338.5	339.0	339.3
120°	374.9	374.6	374.1	373.6	373.1	372.6	373.1	373.6	374.1	374.6	374.9
122.5°	409.1	408.9	408.6	408.3	407.9	407.6	407.9	408.3	408.6	408.9	409.1
125°	444.0	443.9	443.7	443.6	443.4	443.2	443.4	443.6	443.7	443.9	444.0
127.5°	477.4	477.1	476.6	476.1	475.6	475.1	475.6	476.1	476.6	477.1	477.4
130°	513.1	512.8	512.1	511.4	510.7	510.0	510.7	511.4	512.1	512.8	513.1
132.5°	545.7	545.4	544.9	544.4	543.9	543.4	543.9	544.4	544.9	545.4	545.7
135°	580.6	580.3	579.8	579.3	578.8	578.3	578.8	579.3	579.8	580.3	580.6
137.5°	612.5	612.2	611.5	610.8	610.1	609.4	610.1	610.8	611.5	612.2	612.5
140°	645.1	644.8	644.1	643.4	642.8	642.1	642.8	643.4	644.1	644.8	645.1
142.5°	674.7	674.4	673.7	673.0	672.4	671.7	672.4	673.0	673.7	674.4	674.7
145°	704.3	704.0	703.3	702.6	702.0	701.3	702.0	702.6	703.3	704.0	704.3
147.5°	730.9	730.6	729.9	729.2	728.5	727.8	728.5	729.2	729.9	730.6	730.9
150°	755.9	755.6	755.1	754.6	754.1	753.6	754.1	754.6	755.1	755.6	755.9
152.5°	781.0	780.7	780.0	779.3	778.6	777.9	778.6	779.3	780.0	780.7	781.0
155°	801.5	801.2	800.7	800.2	799.7	799.2	799.7	800.2	800.7	801.2	801.5
157.5°	821.9	821.5	820.7	819.8	819.0	818.2	819.0	819.8	820.7	821.5	821.9
160°	838.6	838.3	837.6	836.9	836.3	835.6	836.3	836.9	837.6	838.3	838.6
162.5°	854.6	854.2	853.3	852.5	851.6	850.8	851.6	852.5	853.3	854.2	854.6
165°	867.5	867.1	866.2	865.4	864.5	863.7	864.5	865.4	866.2	867.1	867.5
167.5°	878.9	878.5	877.6	876.8	875.9	875.1	875.9	876.8	877.6	878.5	878.9
170°	888.0	887.5	886.5	885.4	884.4	883.4	884.4	885.4	886.5	887.5	888.0
172.5°	894.8	894.3	893.3	892.3	891.3	890.3	891.3	892.3	893.3	894.3	894.8
175°	899.4	898.9	897.9	896.8	895.8	894.8	895.8	896.8	897.9	898.9	899.4
177.5°	901.6	901.1	900.1	899.1	898.1	897.1	898.1	899.1	900.1	901.1	901.6
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	543.0	546.5	545.2	540.3	546.1	546.1	550.0	550.0	554.9	556.6	559.2
5°	512.2	514.8	517.0	514.8	518.8	525.0	528.5	531.5	538.1	540.8	544.7
7.5°	479.2	484.1	486.3	486.3	492.9	499.9	506.9	511.3	520.6	524.1	528.0
10°	447.1	452.8	457.2	456.8	467.8	472.2	481.0	491.1	500.3	505.6	511.3
12.5°	413.3	416.4	422.5	431.3	433.9	441.9	452.0	464.7	481.4	486.3	494.6
15°	385.1	393.5	398.3	402.3	408.4	415.9	426.9	439.2	455.9	466.5	475.3
17.5°	361.4	372.4	375.5	374.6	382.5	393.9	406.7	415.9	430.9	443.6	452.0
20°	342.1	346.5	351.7	353.9	360.1	372.4	384.7	395.3	407.6	417.7	427.3
22.5°	322.7	326.2	330.6	334.6	339.4	346.5	358.3	371.5	383.4	393.1	404.0
25°	306.9	309.1	313.0	316.1	321.4	326.2	334.6	349.1	363.2	368.9	378.5
27.5°	291.5	293.3	295.9	299.4	302.0	306.9	314.4	326.2	340.7	346.5	359.6
30°	277.9	279.2	281.8	283.6	284.9	290.6	296.3	305.6	316.6	324.5	334.1
32.5°	265.1	266.4	269.1	269.5	271.3	274.3	279.6	288.0	297.6	304.2	312.6
35°	251.0	251.9	254.6	255.4	256.8	259.4	263.4	269.5	278.3	283.1	290.6
37.5°	240.1	239.6	241.4	242.7	244.5	245.8	247.1	253.2	259.8	264.2	270.0
40°	228.2	227.3	227.7	229.5	230.4	232.1	232.1	238.3	242.7	246.2	250.6
42.5°	216.3	215.9	215.0	215.9	216.8	217.2	217.6	222.0	226.4	229.5	234.3
45°	204.4	204.0	203.1	203.6	203.6	204.4	205.8	207.5	210.6	213.2	215.9
47.5°	193.5	192.6	191.3	190.8	191.7	191.7	191.7	193.5	196.5	197.4	200.0
50°	182.0	180.7	178.9	178.1	178.1	177.6	178.5	178.9	181.6	182.5	184.7
52.5°	169.7	168.8	167.1	165.3	165.8	164.9	165.3	165.8	166.6	167.9	169.3
55°	157.4	155.6	154.3	153.9	152.6	152.6	151.2	153.0	152.6	153.0	154.8
57.5°	145.5	143.8	141.6	140.7	139.4	138.9	138.1	137.6	138.1	139.4	140.7
60°	131.5	130.6	129.3	127.9	127.1	125.7	124.9	124.9	124.4	124.4	124.9
62.5°	117.8	117.4	115.6	115.2	114.3	113.4	112.1	111.2	111.2	112.1	112.6
65°	104.6	104.2	102.9	102.4	100.2	99.4	98.9	98.5	97.6	97.6	97.6
67.5°	92.3	91.0	91.0	88.8	87.1	86.2	85.3	84.9	84.9	84.9	85.3
70°	78.7	78.7	77.4	76.1	74.3	74.7	73.4	72.1	72.1	71.2	71.7
72.5°	65.5	65.1	63.8	63.3	62.0	60.7	59.8	60.7	59.4	58.9	59.4
75°	52.8	52.3	51.4	50.6	51.0	49.7	48.4	47.9	47.9	47.0	47.0
77.5°	40.4	41.3	39.6	39.1	38.3	37.4	36.9	36.5	36.5	36.5	37.4
80°	28.1	28.6	28.6	27.7	28.1	26.8	26.8	26.8	25.5	25.9	26.4
82.5°	18.0	18.0	17.6	18.0	17.6	17.6	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.7	9.2	10.1	9.7	9.7	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	25.2	25.5	25.9	26.2	26.6	22.9	19.2	15.5	11.8	9.9	8.9
92.5°	24.2	24.0	23.9	23.7	23.5	23.3	23.2	23.0	22.9	22.8	22.1
95°	48.6	48.6	48.6	48.6	48.6	48.3	47.9	47.6	47.3	47.1	46.3
97.5°	75.9	75.9	75.9	75.9	75.9	75.2	74.6	73.9	73.2	72.9	72.1
100°	104.7	104.7	104.7	104.7	104.7	104.2	103.7	103.2	102.7	102.5	101.8
102.5°	136.5	136.4	136.2	136.1	135.9	135.2	134.5	133.8	133.1	132.8	132.3
105°	168.3	168.0	167.7	167.3	167.0	166.7	166.3	166.0	165.7	165.5	165.2
107.5°	201.8	201.6	201.5	201.3	201.1	201.1	201.1	201.1	201.1	201.1	200.8
110°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	235.5

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	269.7	270.2	270.7	271.2	271.7	271.9	272.1	272.2	272.4	272.5	272.0
115°	306.0	306.1	306.3	306.4	306.6	306.9	307.3	307.6	307.9	308.1	307.6
117.5°	339.5	340.0	340.5	341.0	341.5	342.3	343.2	344.0	344.9	345.3	344.6
120°	374.9	374.9	374.9	374.9	374.9	376.3	377.6	379.0	380.3	381.0	380.3
122.5°	409.4	409.9	410.4	410.9	411.4	412.2	413.0	413.9	414.7	415.1	414.3
125°	444.3	444.8	445.3	445.8	446.3	446.8	447.3	447.8	448.3	448.5	447.7
127.5°	477.7	478.4	479.1	479.7	480.4	481.1	481.8	482.5	483.2	483.5	482.6
130°	513.3	513.6	513.9	514.3	514.6	514.9	515.3	515.6	515.9	516.1	515.0
132.5°	546.1	547.0	547.8	548.7	549.5	549.3	549.1	549.0	548.8	548.7	547.9
135°	580.7	580.9	581.0	581.2	581.4	581.0	580.7	580.3	580.0	579.8	578.9
137.5°	612.6	612.7	612.9	613.0	613.2	612.9	612.5	612.2	611.9	611.7	610.9
140°	645.1	645.1	645.1	645.1	645.1	644.3	643.4	642.6	641.7	641.3	640.5
142.5°	674.6	674.5	674.3	674.2	674.0	673.5	673.0	672.5	672.0	671.7	670.9
145°	704.2	704.1	703.9	703.8	703.6	702.6	701.6	700.5	699.5	699.0	698.4
147.5°	730.7	730.4	730.1	729.7	729.4	728.7	728.0	727.3	726.6	726.3	725.5
150°	755.6	755.1	754.6	754.1	753.6	752.9	752.3	751.6	750.9	750.6	750.1
152.5°	780.7	780.0	779.3	778.6	777.9	777.1	776.2	775.4	774.5	774.1	773.6
155°	801.1	800.2	799.4	798.5	797.7	797.2	796.7	796.2	795.7	795.4	795.1
157.5°	821.3	820.1	819.0	817.8	816.6	816.3	815.9	815.6	815.3	815.1	814.9
160°	838.1	837.1	836.1	835.1	834.1	833.9	833.7	833.6	833.4	833.3	833.1
162.5°	854.0	852.8	851.7	850.5	849.3	849.1	848.9	848.8	848.6	848.5	848.5
165°	866.9	865.7	864.6	863.4	862.2	862.2	862.2	862.2	862.2	862.2	862.3
167.5°	878.3	877.1	876.0	874.8	873.6	873.6	873.6	873.6	873.6	873.6	873.8
170°	887.4	886.2	885.1	883.9	882.7	882.9	883.0	883.2	883.3	883.4	883.7
172.5°	894.2	893.0	891.9	890.7	889.5	889.7	889.9	890.0	890.2	890.3	890.5
175°	898.8	897.6	896.4	895.2	894.0	894.4	894.7	895.1	895.4	895.6	895.8
177.5°	901.1	900.1	899.1	898.1	897.1	897.4	897.8	898.1	898.4	898.6	898.9
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	572.0	572.0	572.0	572.0
2.5°	561.4	561.4	568.0	575.1
5°	549.1	552.2	562.8	572.4
7.5°	537.3	542.5	555.7	568.0
10°	522.8	529.8	546.1	560.6
12.5°	508.7	515.3	534.2	550.5
15°	488.9	497.3	517.5	537.7
17.5°	469.1	477.5	502.1	525.8
20°	445.8	456.8	484.5	516.2
22.5°	424.3	437.9	468.7	494.2
25°	400.5	421.6	450.2	483.2
27.5°	379.4	400.5	429.5	463.0
30°	355.7	377.2	407.1	437.9
32.5°	332.8	352.6	381.6	419.4
35°	309.1	328.0	356.1	394.4
37.5°	287.5	306.0	336.8	372.0
40°	266.4	285.8	312.2	347.3
42.5°	246.6	263.8	287.5	322.7
45°	228.6	240.9	262.9	295.9
47.5°	209.7	220.7	240.9	273.9
50°	192.1	201.4	219.0	249.7
52.5°	175.0	182.9	199.2	223.8
55°	159.6	167.1	178.9	203.1
57.5°	143.8	149.5	160.9	180.3
60°	128.4	133.7	142.9	158.7
62.5°	113.0	117.4	126.2	138.9
65°	99.4	102.9	109.5	120.5
67.5°	86.2	88.4	93.6	102.4
70°	73.4	75.2	79.6	86.6
72.5°	59.8	61.6	66.4	71.2
75°	48.4	48.8	52.3	56.3
77.5°	37.8	37.4	40.0	43.1
80°	25.9	27.3	29.5	30.8
82.5°	17.6	18.0	18.9	19.8
85°	9.7	10.1	10.1	11.4
87.5°	4.0	4.4	4.4	4.8
90°	6.9	4.8	2.8	0.8
92.5°	20.8	19.4	18.1	16.7
95°	44.6	42.9	41.2	39.5
97.5°	70.6	69.1	67.5	66.0
100°	100.5	99.1	97.8	96.4
102.5°	131.3	130.3	129.3	128.3
105°	164.7	164.2	163.7	163.2
107.5°	200.1	199.4	198.8	198.1
110°	234.5	233.5	232.5	231.5

TEST NUMBER: P1008926

CATALOG NUMBER: S122DIP-B290D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	271.0	269.9	268.9	267.9
115°	306.6	305.6	304.6	303.6
117.5°	343.3	342.0	340.6	339.3
120°	379.0	377.6	376.3	374.9
122.5°	412.6	410.9	409.3	407.6
125°	446.2	444.7	443.2	441.7
127.5°	480.7	478.8	477.0	475.1
130°	512.8	510.6	508.4	506.2
132.5°	546.2	544.5	542.8	541.1
135°	577.0	575.2	573.3	571.5
137.5°	609.4	607.9	606.4	604.9
140°	639.0	637.5	636.0	634.5
142.5°	669.4	667.9	666.3	664.8
145°	697.2	696.1	694.9	693.7
147.5°	724.0	722.5	721.0	719.5
150°	749.1	748.1	747.1	746.1
152.5°	772.6	771.6	770.6	769.6
155°	794.6	794.1	793.6	793.1
157.5°	814.6	814.3	813.9	813.6
160°	832.8	832.5	832.1	831.8
162.5°	848.5	848.5	848.5	848.5
165°	862.4	862.6	862.7	862.9
167.5°	874.3	874.8	875.3	875.8
170°	884.2	884.7	885.2	885.7
172.5°	891.0	891.5	892.0	892.5
175°	896.3	896.8	897.3	897.8
177.5°	899.4	899.9	900.4	900.9
180°	899.4	899.4	899.4	899.4

(END OF REPORT)