

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009077

Luminaire Tested: S122DIP-B485D530UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009077
REPORT IS A COMBINATION OF REPORTS P984240 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4170.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15188	15188	15188	15188
5°	15226	16194	15283	12885
10°	15048	17679	15142	10622
15°	14683	18647	14887	8948
20°	14455	17508	14455	7777
25°	13993	15041	14057	6954
30°	13236	11824	13488	6300
35°	12565	8176	12774	5763
40°	11791	6173	11927	5336
45°	10841	5073	11018	4875
50°	10017	4452	10037	4463
55°	9078	3794	9140	4015
60°	8078	3169	8190	3505
65°	7185	2577	7316	2993
70°	6293	2022	6453	2413
75°	5281	1468	5488	1751
80°	4120	931	4415	1039
85°	2712	468	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15700 cd/sqm

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	2.2
10°-20°	266.0	6.4
20°-30°	386.1	9.3
30°-40°	407.0	9.8
40°-50°	360.1	8.6
50°-60°	287.6	6.9
60°-70°	195.3	4.7
70°-80°	99.9	2.4
80°-90°	25.5	0.6
90°-100°	114.8	2.8
100°-110°	404.3	9.7
110°-120°	424.7	10.2
120°-130°	349.4	8.4
130°-140°	280.7	6.7
140°-150°	212.0	5.1
150°-160°	149.0	3.6
160°-170°	87.7	2.1
170°-180°	28.5	0.7
0°-30°	743.5	17.8
0°-40°	1150.4	27.6
0°-60°	1798.1	43.1
0°-90°	2118.9	50.8
90°-120°	943.8	22.6
90°-150°	1785.8	42.8
90°-180°	2051.0	49.2
0°-180°	4170.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	960	960	960	960	960	
5°	960	1072	964	853	960	91
15°	902	1317	914	632	902	255
25°	810	1097	814	507	810	371
35°	662	597	673	421	662	414
45°	496	360	504	346	496	385
55°	341	253	343	268	341	304
65°	202	156	206	181	202	201
75°	94	77	98	92	94	101
85°	19	20	21	15	19	22
90°	1	19	1	19	1	2
95°	20	65	20	65	20	20
105°	69	638	69	638	69	73
115°	122	840	122	840	122	121
125°	170	681	170	681	170	151
135°	199	565	199	565	199	154
145°	228	451	228	451	228	143
155°	259	379	259	379	259	119
165°	282	332	282	332	282	80
175°	294	300	294	300	294	28
180°	294	294	294	294	294	

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	964.7	966.9	970.6	971.3	978.7	984.6	991.2	991.2	993.4	992.7	986.8
5°	960.3	966.9	976.5	984.6	997.9	1003.8	1012.6	1019.3	1025.2	1029.6	1028.9
7.5°	952.9	964.7	978.7	994.2	1011.9	1022.2	1034.8	1046.6	1054.7	1062.0	1067.2
10°	940.3	960.3	979.4	1000.1	1023.0	1037.0	1051.7	1067.2	1079.7	1093.8	1107.0
12.5°	923.4	952.1	975.7	1003.0	1031.1	1046.6	1070.2	1082.0	1106.3	1141.7	1151.3
15°	902.0	941.1	963.2	997.9	1034.8	1047.3	1079.7	1098.9	1149.1	1171.2	1197.7
17.5°	882.1	925.6	955.1	994.9	1031.1	1055.4	1087.1	1126.2	1168.2	1200.0	1229.5
20°	865.9	907.9	943.3	987.5	1033.3	1064.3	1097.4	1144.6	1190.4	1222.8	1245.7
22.5°	829.0	882.8	924.1	973.5	1028.9	1071.6	1103.3	1155.0	1204.4	1224.3	1244.2
25°	810.5	857.0	904.9	961.0	1025.9	1076.8	1104.1	1161.6	1205.1	1212.5	1216.9
27.5°	776.6	829.0	885.0	949.2	1025.2	1067.9	1102.6	1155.0	1189.6	1184.5	1171.2
30°	734.6	798.7	860.7	930.0	1014.8	1061.3	1093.8	1141.7	1159.4	1132.8	1109.2
32.5°	703.6	764.1	832.7	913.1	1003.0	1047.3	1079.0	1116.6	1120.3	1072.4	1032.5
35°	661.6	728.7	806.1	890.9	983.1	1023.0	1052.5	1075.3	1057.6	990.5	943.3
37.5°	623.9	690.3	772.9	859.2	955.8	994.9	1018.5	1022.2	978.7	919.7	850.4
40°	582.6	651.2	737.5	828.2	925.6	959.5	974.3	963.2	900.5	831.9	751.5
42.5°	541.3	609.2	702.1	795.1	887.2	916.0	921.9	891.7	815.0	734.6	641.6
45°	496.4	567.2	660.1	753.8	843.0	859.2	860.0	816.4	725.7	641.6	555.4
47.5°	459.5	525.1	617.3	711.0	786.2	797.3	792.8	742.7	643.9	549.5	474.2
50°	418.9	481.6	573.1	665.2	729.4	732.4	721.3	649.8	553.1	466.9	407.1
52.5°	375.4	438.8	522.9	611.4	668.9	664.5	643.1	566.4	475.7	404.2	358.4
55°	340.7	396.8	475.7	562.0	602.6	590.0	566.4	488.2	416.7	356.2	316.4
57.5°	302.4	351.8	429.2	504.5	528.1	516.3	492.7	419.7	353.3	307.5	281.0
60°	266.2	311.2	379.1	441.8	460.2	447.7	420.4	354.8	306.8	268.5	248.5
62.5°	233.1	272.1	328.9	386.5	393.8	381.3	357.7	304.6	263.3	233.1	218.3
65°	202.1	239.0	284.7	328.2	334.8	321.6	297.2	258.9	224.2	205.0	191.0
67.5°	171.8	201.3	241.9	273.6	277.3	264.8	244.9	213.9	192.5	171.8	161.5
70°	145.3	167.4	199.1	224.9	226.4	214.6	204.3	176.3	160.0	145.3	137.2
72.5°	119.5	135.0	159.3	178.5	179.2	171.8	162.3	144.6	130.5	120.2	112.1
75°	94.4	107.7	122.4	139.4	138.7	132.8	125.4	114.3	102.5	95.9	92.2
77.5°	72.3	80.4	92.2	103.3	103.3	100.3	95.9	87.8	80.4	73.8	70.1
80°	51.6	56.8	66.4	70.1	71.5	70.8	67.1	61.2	58.3	53.1	51.6
82.5°	33.2	36.9	41.3	45.0	47.2	45.7	45.0	42.0	37.6	36.1	34.7
85°	19.2	20.7	22.9	25.1	25.8	25.1	26.6	24.3	22.1	22.1	21.4
87.5°	8.1	8.9	10.3	10.3	11.1	11.1	10.3	11.1	11.1	10.3	9.6
90°	0.6	2.3	4.5	5.7	6.8	7.6	8.5	11.3	15.3	18.7	19.3
92.5°	8.5	11.9	16.4	19.3	23.8	26.9	30.0	45.3	66.8	86.1	87.2
95°	19.8	22.1	27.8	32.9	41.9	48.7	55.5	81.6	130.8	196.5	222.0
97.5°	29.5	32.9	39.1	46.4	56.6	64.2	71.9	105.4	173.9	279.8	361.9
100°	43.6	45.3	50.4	59.5	70.8	78.8	86.7	116.7	185.8	308.1	447.5
102.5°	56.6	57.8	62.9	71.9	83.8	91.8	99.7	126.9	186.3	297.4	450.3
105°	69.1	71.4	75.3	83.8	96.3	104.2	112.1	138.8	189.2	282.6	419.7
107.5°	82.7	84.4	88.4	96.3	108.7	116.6	124.6	150.7	195.4	274.7	391.4
110°	96.3	98.6	102.0	109.3	121.2	129.4	137.6	162.6	203.3	272.4	372.1

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	108.7	111.0	115.0	121.8	133.1	141.6	150.1	173.9	211.8	273.0	359.7
115°	121.8	124.6	128.0	134.8	146.1	153.8	161.4	185.8	220.3	275.3	351.2
117.5°	135.4	137.6	141.0	147.3	158.0	166.0	173.9	196.5	229.4	278.7	346.6
120°	147.8	150.1	153.5	158.6	169.9	177.9	185.8	207.9	238.5	282.1	342.7
122.5°	159.7	161.4	164.8	170.5	181.8	190.0	198.2	218.6	246.4	286.0	340.4
125°	169.9	171.6	175.0	181.8	193.1	201.0	209.0	229.4	254.9	290.0	337.6
127.5°	178.4	180.7	185.2	192.6	203.3	211.6	219.8	239.6	262.8	294.0	335.9
130°	185.8	188.0	193.7	201.6	213.0	220.9	228.8	248.7	270.2	298.5	334.7
132.5°	192.6	195.4	201.6	210.1	222.0	230.0	237.9	256.6	277.5	303.0	334.2
135°	199.4	201.6	208.4	216.9	230.0	237.9	245.8	263.9	283.8	306.4	333.6
137.5°	205.6	208.4	215.2	224.3	237.3	244.6	252.0	270.2	288.9	309.8	333.6
140°	213.0	215.2	222.0	231.1	243.6	251.0	258.3	275.3	292.8	312.1	333.0
142.5°	220.3	222.0	228.3	237.3	249.2	256.0	262.8	279.2	296.2	313.8	333.0
145°	227.7	230.0	235.6	244.1	255.4	261.6	267.9	283.2	299.1	314.9	331.9
147.5°	235.6	237.3	243.0	250.9	260.5	266.2	271.9	286.6	300.8	315.5	330.2
150°	243.6	245.3	249.8	257.1	265.6	270.7	275.8	288.9	301.9	314.9	328.5
152.5°	251.5	252.0	256.6	262.8	270.7	275.2	279.8	291.1	302.5	313.8	325.7
155°	258.8	259.4	262.8	269.0	275.3	279.6	283.8	293.4	303.0	312.7	322.3
157.5°	265.1	265.6	268.5	274.1	279.2	282.9	286.6	295.1	303.0	310.4	318.9
160°	271.3	271.9	274.1	278.7	283.2	286.3	289.4	296.2	303.0	308.7	315.5
162.5°	277.5	277.0	279.2	282.6	286.6	288.8	291.1	296.8	302.5	307.0	312.7
165°	282.1	281.5	282.6	286.0	288.9	290.6	292.3	297.4	301.3	304.7	308.7
167.5°	286.0	285.5	286.6	288.9	291.1	292.2	293.4	297.4	300.8	302.5	305.3
170°	290.0	288.9	289.4	291.1	292.3	293.2	294.0	296.8	299.6	300.8	302.5
172.5°	292.3	291.7	291.1	292.8	293.4	294.0	294.5	296.2	297.9	298.5	299.1
175°	294.0	293.4	292.8	294.0	294.0	294.2	294.5	295.7	296.8	296.2	296.8
177.5°	295.1	294.0	293.4	294.5	294.5	294.5	294.5	295.1	296.2	295.1	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	997.1	997.9	999.3	1006.7	1010.4	1011.1	1008.2	1014.8	1017.1	1014.8	1013.4
5°	1044.3	1048.8	1057.6	1067.2	1066.5	1067.2	1071.6	1076.1	1077.5	1071.6	1073.8
7.5°	1085.6	1094.5	1104.1	1118.8	1118.8	1126.2	1129.2	1132.8	1141.7	1137.3	1135.8
10°	1132.8	1144.6	1162.3	1185.9	1186.7	1194.1	1201.4	1213.2	1216.9	1214.0	1215.4
12.5°	1191.8	1214.7	1216.2	1242.0	1253.8	1255.3	1267.1	1264.9	1272.2	1272.2	1284.8
15°	1217.7	1253.1	1273.0	1298.0	1305.4	1296.6	1306.2	1316.5	1317.2	1317.2	1316.5
17.5°	1264.1	1278.1	1298.0	1311.3	1314.3	1314.3	1315.0	1319.4	1316.5	1310.6	1315.0
20°	1273.7	1279.6	1287.0	1285.5	1287.0	1279.6	1272.2	1264.9	1265.6	1261.9	1273.0
22.5°	1256.0	1254.5	1237.6	1226.5	1226.5	1211.8	1197.7	1191.1	1184.5	1186.7	1190.4
25°	1211.8	1188.9	1168.2	1152.0	1148.3	1124.7	1105.6	1099.7	1088.6	1097.4	1098.9
27.5°	1141.0	1115.1	1082.0	1067.9	1048.8	1039.2	1025.9	1008.2	985.3	998.6	996.4
30°	1065.0	1026.6	999.3	965.4	935.2	933.0	907.9	878.4	866.6	866.6	873.2
32.5°	980.2	929.3	889.5	841.5	812.0	799.5	769.2	739.7	746.4	724.3	732.4
35°	881.3	814.2	764.1	717.6	695.5	680.7	641.6	625.4	607.7	597.4	616.6
37.5°	786.9	709.5	645.3	594.4	586.3	559.8	533.2	522.9	512.6	517.0	516.3
40°	671.9	603.3	545.8	505.9	491.9	479.4	461.7	449.2	442.5	446.2	446.9
42.5°	567.9	510.4	467.6	439.6	427.8	418.9	410.1	399.7	397.5	397.5	400.5
45°	487.5	440.3	411.5	388.7	382.0	375.4	368.8	364.3	362.9	359.9	362.1
47.5°	423.3	385.7	368.0	351.1	343.7	342.2	336.3	334.1	331.1	330.4	331.1
50°	369.5	345.9	329.7	320.1	314.9	312.7	309.8	305.3	303.9	307.5	306.1
52.5°	331.9	309.8	300.9	291.3	288.4	285.4	281.0	281.7	281.0	279.5	279.5
55°	294.3	280.3	271.4	264.0	263.3	260.3	256.7	255.2	254.4	253.0	255.2
57.5°	264.0	253.0	244.9	238.2	235.3	235.3	231.6	228.6	228.6	227.9	228.6
60°	233.8	222.7	217.6	210.9	208.7	208.0	205.8	204.3	202.1	202.1	202.1
62.5°	205.8	196.9	191.0	185.1	185.9	182.2	179.2	177.7	177.7	178.5	178.5
65°	179.2	173.3	165.9	160.8	159.3	158.6	157.1	156.4	154.1	155.6	155.6
67.5°	154.9	146.8	142.3	140.1	137.9	137.2	135.7	134.2	133.5	132.8	134.2
70°	130.5	123.9	120.2	118.7	116.5	115.8	115.1	112.8	113.6	114.3	115.1
72.5°	108.4	102.5	101.8	97.4	97.4	97.4	94.4	95.9	95.1	93.7	95.1
75°	85.6	82.6	81.1	78.9	79.7	78.9	78.2	76.0	76.0	76.7	77.4
77.5°	67.9	64.9	64.2	62.0	60.5	62.0	60.5	59.7	59.7	60.5	60.5
80°	50.2	48.7	46.5	46.5	46.5	45.7	45.7	45.7	45.0	44.3	45.0
82.5°	33.2	33.2	32.5	31.7	32.5	31.0	31.7	31.7	31.7	31.7	31.7
85°	21.4	20.7	20.7	19.9	19.9	19.9	20.7	19.2	19.2	19.9	19.9
87.5°	9.6	9.6	9.6	10.3	9.6	9.6	9.6	10.3	9.6	9.6	9.6
90°	18.7	18.1	17.0	18.1	18.4	18.7	18.7	18.7	18.7	18.7	18.7
92.5°	73.1	57.2	48.7	42.5	40.2	37.9	37.4	35.1	35.7	34.6	35.7
95°	194.3	148.4	113.8	90.1	83.8	77.6	70.2	65.7	64.0	64.6	64.0
97.5°	364.8	303.6	242.4	185.2	168.2	151.2	129.1	117.8	111.6	108.2	111.6
100°	529.0	517.1	446.9	369.3	335.0	300.8	253.7	229.4	213.0	202.8	213.0
102.5°	590.2	657.0	654.8	603.2	566.4	529.6	477.5	431.6	410.1	395.3	410.1
105°	570.4	688.2	752.2	759.5	750.2	740.9	705.7	670.6	646.3	638.3	646.3
107.5°	528.5	654.8	749.9	805.4	816.8	828.1	827.5	822.4	815.1	802.0	815.1
110°	489.4	608.9	710.3	782.8	806.0	829.2	853.6	864.3	869.4	868.9	869.4

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	462.2	567.0	663.3	742.0	769.4	796.9	833.2	853.0	863.8	867.7	863.8
115°	440.7	534.1	621.3	695.5	724.7	753.9	794.1	820.1	834.9	840.0	834.9
117.5°	425.9	506.9	585.1	654.2	682.0	709.7	751.0	778.8	794.1	798.1	794.1
120°	414.6	487.7	557.9	617.9	643.7	669.5	709.1	735.8	752.2	757.8	752.2
122.5°	405.0	472.4	535.2	591.3	614.0	636.6	671.2	697.2	711.4	715.9	711.4
125°	395.9	457.7	516.0	565.8	587.0	608.3	641.2	662.7	676.9	681.4	676.9
127.5°	387.4	442.9	496.7	544.3	564.2	584.0	612.8	633.2	645.7	649.1	645.7
130°	378.9	428.8	477.5	522.2	540.9	559.6	587.4	606.6	617.9	622.5	617.9
132.5°	372.1	415.2	459.4	499.6	516.8	534.1	561.3	580.6	590.8	594.7	590.8
135°	365.9	402.7	440.1	477.5	493.4	509.2	533.6	552.2	562.4	564.7	562.4
137.5°	361.4	392.5	424.8	455.4	469.6	483.7	506.9	523.4	532.4	535.8	532.4
140°	357.4	382.9	410.1	436.1	448.6	461.1	479.2	493.9	502.4	505.8	502.4
142.5°	353.4	375.0	397.0	418.6	428.5	438.4	455.4	468.4	475.8	475.8	475.8
145°	350.0	367.6	386.3	403.8	412.0	420.3	433.9	443.5	449.2	450.9	449.2
147.5°	346.6	361.9	377.2	391.4	397.6	403.8	415.7	423.7	427.6	428.8	427.6
150°	342.1	355.7	368.2	380.1	385.2	390.3	398.7	405.5	408.9	409.5	408.9
152.5°	338.1	349.5	360.8	370.4	374.6	378.9	385.2	390.8	393.1	393.1	393.1
155°	333.0	343.8	352.9	361.4	364.5	367.6	373.8	377.8	380.1	378.9	380.1
157.5°	328.5	337.0	344.9	352.3	354.8	357.4	361.9	365.3	366.5	366.5	366.5
160°	323.4	330.8	337.0	343.2	345.2	347.2	351.2	354.0	354.6	354.6	354.6
162.5°	318.9	324.5	329.6	334.7	336.2	337.6	341.5	343.2	343.8	343.2	343.8
165°	313.8	318.3	322.3	326.2	327.4	328.5	330.8	333.0	333.0	332.5	333.0
167.5°	308.7	312.1	315.5	318.3	319.5	320.6	321.7	322.8	322.8	322.3	322.8
170°	304.7	307.6	309.3	311.5	312.1	312.7	313.2	314.9	314.4	313.2	314.4
172.5°	300.8	302.5	303.6	305.3	305.6	305.9	306.4	307.0	306.4	305.9	306.4
175°	297.4	299.1	299.6	300.2	300.5	300.8	300.8	301.3	300.8	299.6	300.8
177.5°	295.1	296.2	296.2	296.8	296.8	296.8	296.8	296.8	296.2	295.1	296.2
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	1017.1	1011.9	1007.5	1008.2	1011.9	1008.9	1001.6	992.0	988.3	983.9	988.3
5°	1078.3	1073.8	1065.0	1065.7	1063.5	1060.6	1048.8	1034.0	1034.0	1022.2	1020.7
7.5°	1138.7	1132.1	1126.2	1124.7	1116.6	1110.7	1100.4	1079.7	1071.6	1057.6	1049.5
10°	1206.6	1201.4	1194.8	1186.7	1182.3	1171.9	1155.0	1124.7	1110.0	1090.8	1076.8
12.5°	1275.2	1274.4	1259.7	1243.5	1242.7	1226.5	1214.7	1174.1	1154.2	1128.4	1095.2
15°	1318.7	1315.0	1306.9	1298.8	1301.0	1283.3	1256.7	1208.8	1195.5	1164.6	1129.2
17.5°	1318.0	1318.0	1315.7	1314.3	1312.1	1306.9	1292.1	1260.4	1239.0	1200.0	1166.8
20°	1275.9	1285.5	1287.7	1287.0	1294.4	1298.0	1297.3	1277.4	1260.4	1225.8	1191.8
22.5°	1191.8	1214.0	1223.6	1229.5	1244.9	1253.1	1272.2	1264.9	1260.4	1234.6	1205.9
25°	1113.7	1121.0	1149.8	1151.3	1172.7	1192.6	1211.8	1224.3	1240.5	1230.9	1206.6
27.5°	1012.6	1029.6	1050.2	1065.7	1070.2	1110.7	1142.4	1166.0	1202.9	1205.9	1197.7
30°	898.3	906.4	940.3	961.0	984.6	1014.1	1059.8	1100.4	1133.6	1163.8	1174.1
32.5°	758.9	792.1	812.0	837.1	857.7	910.1	966.2	1018.5	1056.9	1107.8	1129.9
35°	631.3	657.1	691.1	701.4	739.0	783.3	856.3	923.4	981.6	1033.3	1078.3
37.5°	525.9	546.5	582.6	598.9	621.0	677.8	739.0	822.3	892.4	955.8	1011.9
40°	453.6	469.1	496.4	501.5	520.0	571.6	621.0	699.2	792.1	877.7	938.9
42.5°	404.2	411.5	430.0	436.6	448.4	483.1	527.3	601.1	687.4	775.9	862.2
45°	368.8	373.9	385.0	390.9	405.6	421.1	457.3	516.3	584.1	673.4	766.3
47.5°	337.0	343.7	348.1	351.8	359.9	376.9	400.5	444.0	508.9	590.8	680.7
50°	310.5	312.7	320.8	321.6	326.7	337.8	359.9	386.5	438.1	504.5	591.5
52.5°	283.9	286.2	291.3	296.5	298.7	307.5	322.3	344.4	382.8	435.1	512.6
55°	257.4	260.3	265.5	269.2	271.4	278.8	287.6	309.0	339.3	376.1	439.6
57.5°	230.8	237.5	239.0	241.2	244.9	253.0	261.1	273.6	297.2	331.1	377.6
60°	205.8	208.0	213.1	215.4	219.0	223.5	233.8	243.4	260.3	286.9	328.9
62.5°	180.0	185.1	187.3	189.5	192.5	197.7	204.3	214.6	229.4	250.8	283.9
65°	157.8	158.6	163.0	165.9	168.9	172.6	179.2	188.8	197.7	217.6	241.9
67.5°	136.4	137.9	139.4	142.3	146.0	149.7	155.6	160.8	171.8	185.1	204.3
70°	115.8	115.8	119.5	121.7	121.0	125.4	129.8	135.7	143.8	156.4	171.8
72.5°	97.4	96.6	99.6	100.3	101.8	104.7	107.7	113.6	118.0	127.6	139.4
75°	77.4	78.9	80.4	80.4	82.6	84.8	87.8	90.7	95.9	101.8	110.6
77.5°	61.2	61.2	62.7	63.4	65.6	64.9	67.9	70.8	74.5	79.7	86.3
80°	45.0	46.5	46.5	46.5	47.2	47.9	50.9	53.1	55.3	59.0	62.0
82.5°	31.7	31.7	33.2	33.2	33.2	34.7	34.7	35.4	36.9	39.1	41.3
85°	19.9	19.9	19.9	20.7	19.9	20.7	22.1	21.4	22.1	23.6	23.6
87.5°	9.6	9.6	9.6	9.6	9.6	10.3	9.6	10.3	11.1	11.1	11.1
90°	18.7	18.7	18.7	18.4	18.1	17.0	18.1	18.7	19.3	18.7	15.3
92.5°	35.1	37.4	37.9	40.2	42.5	48.7	57.2	73.1	87.2	86.1	66.8
95°	65.7	70.2	77.6	83.8	90.1	113.8	148.4	194.3	222.0	196.5	130.8
97.5°	117.8	129.1	151.2	168.2	185.2	242.4	303.6	364.8	361.9	279.8	173.9
100°	229.4	253.7	300.8	335.0	369.3	446.9	517.1	529.0	447.5	308.1	185.8
102.5°	431.6	477.5	529.6	566.4	603.2	654.8	657.0	590.2	450.3	297.4	186.3
105°	670.6	705.7	740.9	750.2	759.5	752.2	688.2	570.4	419.7	282.6	189.2
107.5°	822.4	827.5	828.1	816.8	805.4	749.9	654.8	528.5	391.4	274.7	195.4
110°	864.3	853.6	829.2	806.0	782.8	710.3	608.9	489.4	372.1	272.4	203.3

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	853.0	833.2	796.9	769.4	742.0	663.3	567.0	462.2	359.7	273.0	211.8
115°	820.1	794.1	753.9	724.7	695.5	621.3	534.1	440.7	351.2	275.3	220.3
117.5°	778.8	751.0	709.7	682.0	654.2	585.1	506.9	425.9	346.6	278.7	229.4
120°	735.8	709.1	669.5	643.7	617.9	557.9	487.7	414.6	342.7	282.1	238.5
122.5°	697.2	671.2	636.6	614.0	591.3	535.2	472.4	405.0	340.4	286.0	246.4
125°	662.7	641.2	608.3	587.0	565.8	516.0	457.7	395.9	337.6	290.0	254.9
127.5°	633.2	612.8	584.0	564.2	544.3	496.7	442.9	387.4	335.9	294.0	262.8
130°	606.6	587.4	559.6	540.9	522.2	477.5	428.8	378.9	334.7	298.5	270.2
132.5°	580.6	561.3	534.1	516.8	499.6	459.4	415.2	372.1	334.2	303.0	277.5
135°	552.2	533.6	509.2	493.4	477.5	440.1	402.7	365.9	333.6	306.4	283.8
137.5°	523.4	506.9	483.7	469.6	455.4	424.8	392.5	361.4	333.6	309.8	288.9
140°	493.9	479.2	461.1	448.6	436.1	410.1	382.9	357.4	333.0	312.1	292.8
142.5°	468.4	455.4	438.4	428.5	418.6	397.0	375.0	353.4	333.0	313.8	296.2
145°	443.5	433.9	420.3	412.0	403.8	386.3	367.6	350.0	331.9	314.9	299.1
147.5°	423.7	415.7	403.8	397.6	391.4	377.2	361.9	346.6	330.2	315.5	300.8
150°	405.5	398.7	390.3	385.2	380.1	368.2	355.7	342.1	328.5	314.9	301.9
152.5°	390.8	385.2	378.9	374.6	370.4	360.8	349.5	338.1	325.7	313.8	302.5
155°	377.8	373.8	367.6	364.5	361.4	352.9	343.8	333.0	322.3	312.7	303.0
157.5°	365.3	361.9	357.4	354.8	352.3	344.9	337.0	328.5	318.9	310.4	303.0
160°	354.0	351.2	347.2	345.2	343.2	337.0	330.8	323.4	315.5	308.7	303.0
162.5°	343.2	341.5	337.6	336.2	334.7	329.6	324.5	318.9	312.7	307.0	302.5
165°	333.0	330.8	328.5	327.4	326.2	322.3	318.3	313.8	308.7	304.7	301.3
167.5°	322.8	321.7	320.6	319.5	318.3	315.5	312.1	308.7	305.3	302.5	300.8
170°	314.9	313.2	312.7	312.1	311.5	309.3	307.6	304.7	302.5	300.8	299.6
172.5°	307.0	306.4	305.9	305.6	305.3	303.6	302.5	300.8	299.1	298.5	297.9
175°	301.3	300.8	300.8	300.5	300.2	299.6	299.1	297.4	296.8	296.2	296.8
177.5°	296.8	296.8	296.8	296.8	296.8	296.2	296.2	295.1	294.5	295.1	296.2
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	984.6	980.9	978.7	980.2	975.7	964.7	964.7	968.4	963.9	959.5	952.9
5°	1011.9	1004.5	1000.1	999.3	989.0	971.3	967.6	963.9	954.4	944.0	933.0
7.5°	1038.4	1025.2	1017.8	1012.6	997.9	975.0	965.4	957.3	941.8	926.3	912.3
10°	1060.6	1041.4	1032.5	1024.4	1005.2	976.5	961.0	946.2	926.3	906.4	888.7
12.5°	1078.3	1056.1	1045.1	1033.3	1009.7	972.1	952.9	929.3	909.4	882.8	865.1
15°	1107.8	1062.0	1051.7	1040.7	1016.3	964.7	941.1	914.5	887.2	851.8	832.7
17.5°	1131.4	1070.2	1069.4	1045.8	1014.1	961.7	925.6	890.9	861.4	826.0	795.8
20°	1145.4	1082.7	1070.9	1046.6	1006.7	941.8	904.2	865.9	834.1	791.4	761.1
22.5°	1157.2	1100.4	1069.4	1039.9	991.2	935.2	879.9	843.7	800.2	753.8	725.0
25°	1161.6	1104.1	1071.6	1037.7	980.2	916.0	853.3	814.2	765.6	723.5	684.4
27.5°	1162.3	1103.3	1063.5	1028.1	964.7	890.9	826.8	785.5	731.6	683.0	643.9
30°	1155.0	1095.2	1059.1	1020.7	949.9	868.1	794.3	748.6	691.1	642.4	601.8
32.5°	1132.8	1079.0	1049.5	1007.5	930.8	836.4	763.3	712.5	652.0	604.0	564.9
35°	1096.0	1059.1	1026.6	987.5	905.7	806.9	732.4	672.6	611.4	565.7	528.8
37.5°	1050.2	1030.3	1000.1	961.7	876.9	780.3	697.7	631.3	570.1	525.9	489.7
40°	988.3	993.4	963.9	929.3	843.0	744.2	652.7	589.3	531.8	490.5	455.1
42.5°	921.2	942.6	925.6	892.4	805.4	704.3	619.5	549.5	493.4	450.6	421.1
45°	848.9	885.8	875.4	851.1	766.3	662.3	572.3	504.5	455.1	413.8	387.9
47.5°	770.0	822.3	822.3	804.6	722.8	620.3	531.8	462.4	413.8	384.3	359.2
50°	689.6	748.6	758.2	746.4	674.1	572.3	482.3	419.7	377.6	348.9	330.4
52.5°	605.5	674.1	691.8	685.9	622.5	526.6	441.8	380.6	342.2	317.1	300.9
55°	525.1	604.8	623.9	626.2	567.2	476.4	396.8	343.0	306.1	289.1	275.1
57.5°	449.2	525.9	547.2	550.9	511.1	430.7	354.8	307.5	274.4	260.3	249.3
60°	384.3	448.4	476.4	484.6	449.9	377.6	315.7	269.9	244.9	231.6	221.3
62.5°	331.1	382.8	412.3	414.5	399.0	331.1	275.1	236.7	215.4	203.6	198.4
65°	279.5	326.0	343.7	352.5	340.0	286.9	237.5	205.8	188.8	178.5	173.3
67.5°	238.2	267.7	282.5	294.3	281.7	241.9	202.1	176.3	163.7	153.4	150.5
70°	195.4	219.8	230.8	242.6	231.6	201.3	172.6	149.0	137.9	129.8	126.1
72.5°	156.4	175.5	185.9	193.2	186.6	161.5	137.9	121.7	113.6	107.7	105.5
75°	123.9	137.2	143.1	148.2	145.3	126.1	111.4	98.1	90.7	85.6	84.1
77.5°	94.4	104.0	110.6	112.1	108.4	95.9	83.3	75.2	69.3	66.4	64.9
80°	67.1	73.0	76.7	78.9	75.2	70.1	61.2	55.3	50.2	46.5	45.7
82.5°	45.0	47.9	50.9	50.2	48.7	44.3	39.1	36.1	33.9	31.0	31.0
85°	25.8	26.6	28.0	28.8	28.0	25.1	22.1	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.5	11.1	11.1	9.6	8.1	8.1	7.4	6.6
90°	11.3	8.5	7.6	6.8	5.7	4.5	2.3	0.6	2.3	4.5	5.7
92.5°	45.3	30.0	26.9	23.8	19.3	16.4	11.9	8.5	11.9	16.4	19.3
95°	81.6	55.5	48.7	41.9	32.9	27.8	22.1	19.8	22.1	27.8	32.9
97.5°	105.4	71.9	64.2	56.6	46.4	39.1	32.9	29.5	32.9	39.1	46.4
100°	116.7	86.7	78.8	70.8	59.5	50.4	45.3	43.6	45.3	50.4	59.5
102.5°	126.9	99.7	91.8	83.8	71.9	62.9	57.8	56.6	57.8	62.9	71.9
105°	138.8	112.1	104.2	96.3	83.8	75.3	71.4	69.1	71.4	75.3	83.8
107.5°	150.7	124.6	116.6	108.7	96.3	88.4	84.4	82.7	84.4	88.4	96.3
110°	162.6	137.6	129.4	121.2	109.3	102.0	98.6	96.3	98.6	102.0	109.3

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	173.9	150.1	141.6	133.1	121.8	115.0	111.0	108.7	111.0	115.0	121.8
115°	185.8	161.4	153.8	146.1	134.8	128.0	124.6	121.8	124.6	128.0	134.8
117.5°	196.5	173.9	166.0	158.0	147.3	141.0	137.6	135.4	137.6	141.0	147.3
120°	207.9	185.8	177.9	169.9	158.6	153.5	150.1	147.8	150.1	153.5	158.6
122.5°	218.6	198.2	190.0	181.8	170.5	164.8	161.4	159.7	161.4	164.8	170.5
125°	229.4	209.0	201.0	193.1	181.8	175.0	171.6	169.9	171.6	175.0	181.8
127.5°	239.6	219.8	211.6	203.3	192.6	185.2	180.7	178.4	180.7	185.2	192.6
130°	248.7	228.8	220.9	213.0	201.6	193.7	188.0	185.8	188.0	193.7	201.6
132.5°	256.6	237.9	230.0	222.0	210.1	201.6	195.4	192.6	195.4	201.6	210.1
135°	263.9	245.8	237.9	230.0	216.9	208.4	201.6	199.4	201.6	208.4	216.9
137.5°	270.2	252.0	244.6	237.3	224.3	215.2	208.4	205.6	208.4	215.2	224.3
140°	275.3	258.3	251.0	243.6	231.1	222.0	215.2	213.0	215.2	222.0	231.1
142.5°	279.2	262.8	256.0	249.2	237.3	228.3	222.0	220.3	222.0	228.3	237.3
145°	283.2	267.9	261.6	255.4	244.1	235.6	230.0	227.7	230.0	235.6	244.1
147.5°	286.6	271.9	266.2	260.5	250.9	243.0	237.3	235.6	237.3	243.0	250.9
150°	288.9	275.8	270.7	265.6	257.1	249.8	245.3	243.6	245.3	249.8	257.1
152.5°	291.1	279.8	275.2	270.7	262.8	256.6	252.0	251.5	252.0	256.6	262.8
155°	293.4	283.8	279.6	275.3	269.0	262.8	259.4	258.8	259.4	262.8	269.0
157.5°	295.1	286.6	282.9	279.2	274.1	268.5	265.6	265.1	265.6	268.5	274.1
160°	296.2	289.4	286.3	283.2	278.7	274.1	271.9	271.3	271.9	274.1	278.7
162.5°	296.8	291.1	288.8	286.6	282.6	279.2	277.0	277.5	277.0	279.2	282.6
165°	297.4	292.3	290.6	288.9	286.0	282.6	281.5	282.1	281.5	282.6	286.0
167.5°	297.4	293.4	292.2	291.1	288.9	286.6	285.5	286.0	285.5	286.6	288.9
170°	296.8	294.0	293.2	292.3	291.1	289.4	288.9	290.0	288.9	289.4	291.1
172.5°	296.2	294.5	294.0	293.4	292.8	291.1	291.7	292.3	291.7	291.1	292.8
175°	295.7	294.5	294.2	294.0	294.0	292.8	293.4	294.0	293.4	292.8	294.0
177.5°	295.1	294.5	294.5	294.5	294.5	293.4	294.0	295.1	294.0	293.4	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	949.2	952.9	952.1	944.8	936.7	930.0	917.5	919.0	914.5	915.3	919.7
5°	925.6	925.6	922.6	912.3	899.0	891.7	877.7	874.0	865.1	864.4	863.6
7.5°	900.5	896.8	893.1	878.4	862.2	850.4	831.2	826.8	817.9	812.0	809.1
10°	871.0	865.9	858.5	841.5	821.6	806.9	786.9	781.0	764.1	756.7	752.3
12.5°	838.6	835.6	823.8	809.8	777.4	761.1	732.4	738.3	721.3	706.6	704.3
15°	806.1	795.1	788.4	765.6	726.5	719.1	696.2	684.4	668.9	657.1	657.1
17.5°	774.4	757.4	742.7	718.4	689.6	668.9	652.0	646.1	626.9	615.1	612.9
20°	732.4	713.2	709.5	674.8	654.9	632.1	615.8	601.1	587.1	581.9	578.2
22.5°	692.5	670.4	664.5	635.0	615.1	592.2	576.0	565.7	555.4	551.7	545.0
25°	649.8	636.5	627.6	595.9	573.8	552.4	541.3	534.0	524.4	523.6	519.2
27.5°	608.5	595.9	587.1	556.8	540.6	520.7	511.8	503.7	498.6	496.4	494.1
30°	573.1	559.0	548.7	526.6	506.7	490.5	483.1	477.9	475.0	471.3	470.5
32.5°	534.0	525.9	511.8	494.9	479.4	463.9	459.5	455.8	451.4	449.9	449.2
35°	500.8	489.7	480.9	461.7	455.1	441.8	436.6	433.7	427.8	426.3	424.8
37.5°	468.3	458.0	448.4	436.6	424.1	416.7	413.8	409.3	406.4	407.1	405.6
40°	435.9	427.8	420.4	407.9	400.5	396.8	390.9	386.5	385.0	385.7	385.0
42.5°	404.2	396.8	392.4	382.8	375.4	371.7	368.0	363.6	365.8	365.8	368.0
45°	375.4	368.8	365.8	358.4	354.0	348.1	344.4	343.7	346.6	345.9	345.9
47.5°	345.9	343.7	340.0	333.4	327.5	323.8	323.0	323.0	326.0	327.5	326.7
50°	323.0	318.6	314.2	309.0	304.6	303.1	300.9	302.4	305.3	305.3	306.8
52.5°	294.3	291.3	289.8	285.4	282.5	282.5	282.5	283.2	285.4	287.6	286.9
55°	269.2	267.0	265.5	263.3	259.6	260.3	259.6	261.1	263.3	265.5	267.0
57.5°	242.6	241.9	240.4	236.7	236.7	236.0	238.2	239.0	242.6	244.1	246.3
60°	219.0	216.8	216.8	213.9	213.9	213.9	216.1	218.3	221.3	222.0	223.5
62.5°	194.0	194.0	193.2	191.0	191.0	193.2	194.0	196.9	198.4	198.4	200.6
65°	170.4	169.6	168.9	169.6	170.4	170.4	172.6	174.1	175.5	176.3	177.0
67.5°	146.8	146.0	147.5	146.8	148.2	151.2	150.5	152.7	154.9	154.9	155.6
70°	124.6	126.1	125.4	126.9	126.1	127.6	129.8	130.5	130.5	131.3	133.5
72.5°	104.0	104.0	104.0	103.3	104.0	105.5	106.9	107.7	109.2	109.9	112.1
75°	84.1	84.1	82.6	84.1	84.1	85.6	87.0	87.0	87.0	88.5	90.7
77.5°	63.4	64.2	63.4	64.9	64.9	65.6	67.1	66.4	67.9	68.6	69.3
80°	46.5	45.7	45.7	45.7	46.5	46.5	47.9	48.7	48.7	50.9	49.4
82.5°	29.5	30.2	29.5	30.2	30.2	31.0	30.2	31.0	31.7	33.2	32.5
85°	17.0	16.2	16.2	17.0	16.2	16.2	17.0	16.2	17.0	16.2	17.0
87.5°	6.6	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	6.8	7.6	8.5	11.3	15.3	18.7	19.3	18.7	18.1	17.0	18.1
92.5°	23.8	26.9	30.0	45.3	66.8	86.1	87.2	73.1	57.2	48.7	42.5
95°	41.9	48.7	55.5	81.6	130.8	196.5	222.0	194.3	148.4	113.8	90.1
97.5°	56.6	64.2	71.9	105.4	173.9	279.8	361.9	364.8	303.6	242.4	185.2
100°	70.8	78.8	86.7	116.7	185.8	308.1	447.5	529.0	517.1	446.9	369.3
102.5°	83.8	91.8	99.7	126.9	186.3	297.4	450.3	590.2	657.0	654.8	603.2
105°	96.3	104.2	112.1	138.8	189.2	282.6	419.7	570.4	688.2	752.2	759.5
107.5°	108.7	116.6	124.6	150.7	195.4	274.7	391.4	528.5	654.8	749.9	805.4
110°	121.2	129.4	137.6	162.6	203.3	272.4	372.1	489.4	608.9	710.3	782.8

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	133.1	141.6	150.1	173.9	211.8	273.0	359.7	462.2	567.0	663.3	742.0
115°	146.1	153.8	161.4	185.8	220.3	275.3	351.2	440.7	534.1	621.3	695.5
117.5°	158.0	166.0	173.9	196.5	229.4	278.7	346.6	425.9	506.9	585.1	654.2
120°	169.9	177.9	185.8	207.9	238.5	282.1	342.7	414.6	487.7	557.9	617.9
122.5°	181.8	190.0	198.2	218.6	246.4	286.0	340.4	405.0	472.4	535.2	591.3
125°	193.1	201.0	209.0	229.4	254.9	290.0	337.6	395.9	457.7	516.0	565.8
127.5°	203.3	211.6	219.8	239.6	262.8	294.0	335.9	387.4	442.9	496.7	544.3
130°	213.0	220.9	228.8	248.7	270.2	298.5	334.7	378.9	428.8	477.5	522.2
132.5°	222.0	230.0	237.9	256.6	277.5	303.0	334.2	372.1	415.2	459.4	499.6
135°	230.0	237.9	245.8	263.9	283.8	306.4	333.6	365.9	402.7	440.1	477.5
137.5°	237.3	244.6	252.0	270.2	288.9	309.8	333.6	361.4	392.5	424.8	455.4
140°	243.6	251.0	258.3	275.3	292.8	312.1	333.0	357.4	382.9	410.1	436.1
142.5°	249.2	256.0	262.8	279.2	296.2	313.8	333.0	353.4	375.0	397.0	418.6
145°	255.4	261.6	267.9	283.2	299.1	314.9	331.9	350.0	367.6	386.3	403.8
147.5°	260.5	266.2	271.9	286.6	300.8	315.5	330.2	346.6	361.9	377.2	391.4
150°	265.6	270.7	275.8	288.9	301.9	314.9	328.5	342.1	355.7	368.2	380.1
152.5°	270.7	275.2	279.8	291.1	302.5	313.8	325.7	338.1	349.5	360.8	370.4
155°	275.3	279.6	283.8	293.4	303.0	312.7	322.3	333.0	343.8	352.9	361.4
157.5°	279.2	282.9	286.6	295.1	303.0	310.4	318.9	328.5	337.0	344.9	352.3
160°	283.2	286.3	289.4	296.2	303.0	308.7	315.5	323.4	330.8	337.0	343.2
162.5°	286.6	288.8	291.1	296.8	302.5	307.0	312.7	318.9	324.5	329.6	334.7
165°	288.9	290.6	292.3	297.4	301.3	304.7	308.7	313.8	318.3	322.3	326.2
167.5°	291.1	292.2	293.4	297.4	300.8	302.5	305.3	308.7	312.1	315.5	318.3
170°	292.3	293.2	294.0	296.8	299.6	300.8	302.5	304.7	307.6	309.3	311.5
172.5°	293.4	294.0	294.5	296.2	297.9	298.5	299.1	300.8	302.5	303.6	305.3
175°	294.0	294.2	294.5	295.7	296.8	296.2	296.8	297.4	299.1	299.6	300.2
177.5°	294.5	294.5	294.5	295.1	296.2	295.1	294.5	295.1	296.2	296.2	296.8
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	914.5	916.7	911.6	910.1	911.6	906.4	907.9	909.4	909.4	911.6	913.1
5°	861.4	858.5	853.3	851.8	850.4	852.6	851.1	853.3	854.1	859.2	860.0
7.5°	809.1	804.6	800.2	795.8	794.3	790.6	794.3	794.3	799.5	798.0	801.7
10°	747.1	746.4	740.5	738.3	735.3	729.4	737.5	735.3	739.0	745.6	747.1
12.5°	701.4	693.3	697.0	686.6	690.3	684.4	685.2	685.2	691.1	691.8	690.3
15°	657.9	651.2	641.6	637.2	635.0	632.1	641.6	642.4	638.0	648.3	644.6
17.5°	613.6	613.6	604.8	602.6	596.7	599.6	598.1	598.9	597.4	604.8	608.5
20°	575.3	571.6	568.6	569.4	562.0	560.5	559.0	560.5	565.7	570.8	572.3
22.5°	544.3	542.1	534.7	536.2	530.3	532.5	531.0	534.7	535.4	535.4	540.6
25°	514.8	511.8	512.6	509.6	507.4	507.4	505.2	507.4	510.4	511.8	512.6
27.5°	492.7	490.5	486.8	484.6	486.0	482.3	485.3	487.5	487.5	486.0	487.5
30°	466.1	467.6	467.6	460.2	463.2	461.7	463.9	465.4	465.4	466.1	464.6
32.5°	448.4	444.0	443.3	442.5	442.5	439.6	439.6	441.8	442.5	443.3	445.5
35°	424.8	424.8	421.1	423.3	420.4	421.1	420.4	421.1	422.6	420.4	422.6
37.5°	403.4	404.2	402.7	404.2	404.9	403.4	402.0	404.9	403.4	403.4	402.0
40°	385.0	384.3	385.0	385.0	385.0	385.7	384.3	384.3	384.3	382.8	381.3
42.5°	369.5	365.1	366.6	367.3	365.1	365.1	365.8	365.1	367.3	362.9	362.9
45°	347.4	345.9	346.6	346.6	348.1	345.9	347.4	348.1	345.9	345.2	343.7
47.5°	327.5	328.9	327.5	328.9	328.9	330.4	327.5	328.2	328.9	326.0	323.8
50°	307.5	307.5	309.8	309.0	309.8	308.3	308.3	307.5	308.3	306.8	304.6
52.5°	289.1	286.9	290.6	289.8	289.1	288.4	287.6	288.4	286.9	285.4	285.4
55°	266.2	266.2	268.5	269.2	269.2	267.7	266.2	267.0	266.2	265.5	264.8
57.5°	247.8	244.9	246.3	247.1	247.1	244.9	246.3	244.9	244.9	245.6	243.4
60°	224.2	224.2	222.7	224.9	224.9	223.5	223.5	224.2	222.7	222.0	221.3
62.5°	199.1	199.9	202.1	202.8	203.6	202.1	200.6	201.3	201.3	199.1	199.9
65°	177.7	179.2	182.2	181.4	180.0	180.7	179.2	180.0	177.7	178.5	176.3
67.5°	157.1	156.4	157.1	157.1	158.6	157.8	156.4	156.4	155.6	157.8	155.6
70°	135.0	135.0	135.0	135.0	135.7	136.4	135.0	133.5	134.2	132.8	132.0
72.5°	112.1	112.8	112.1	113.6	111.4	112.8	112.8	112.1	111.4	111.4	111.4
75°	90.7	92.2	90.0	90.7	90.0	91.5	90.7	90.7	89.2	88.5	89.2
77.5°	69.3	70.1	68.6	69.3	68.6	69.3	69.3	68.6	68.6	68.6	68.6
80°	49.4	50.2	49.4	48.7	47.9	49.4	47.9	48.7	49.4	48.7	50.2
82.5°	31.7	31.7	31.0	31.7	30.2	30.2	31.0	31.0	30.2	31.7	30.2
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.2	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	18.4	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.4
92.5°	40.2	37.9	37.4	35.1	35.7	34.6	35.7	35.1	37.4	37.9	40.2
95°	83.8	77.6	70.2	65.7	64.0	64.6	64.0	65.7	70.2	77.6	83.8
97.5°	168.2	151.2	129.1	117.8	111.6	108.2	111.6	117.8	129.1	151.2	168.2
100°	335.0	300.8	253.7	229.4	213.0	202.8	213.0	229.4	253.7	300.8	335.0
102.5°	566.4	529.6	477.5	431.6	410.1	395.3	410.1	431.6	477.5	529.6	566.4
105°	750.2	740.9	705.7	670.6	646.3	638.3	646.3	670.6	705.7	740.9	750.2
107.5°	816.8	828.1	827.5	822.4	815.1	802.0	815.1	822.4	827.5	828.1	816.8
110°	806.0	829.2	853.6	864.3	869.4	868.9	869.4	864.3	853.6	829.2	806.0

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	769.4	796.9	833.2	853.0	863.8	867.7	863.8	853.0	833.2	796.9	769.4
115°	724.7	753.9	794.1	820.1	834.9	840.0	834.9	820.1	794.1	753.9	724.7
117.5°	682.0	709.7	751.0	778.8	794.1	798.1	794.1	778.8	751.0	709.7	682.0
120°	643.7	669.5	709.1	735.8	752.2	757.8	752.2	735.8	709.1	669.5	643.7
122.5°	614.0	636.6	671.2	697.2	711.4	715.9	711.4	697.2	671.2	636.6	614.0
125°	587.0	608.3	641.2	662.7	676.9	681.4	676.9	662.7	641.2	608.3	587.0
127.5°	564.2	584.0	612.8	633.2	645.7	649.1	645.7	633.2	612.8	584.0	564.2
130°	540.9	559.6	587.4	606.6	617.9	622.5	617.9	606.6	587.4	559.6	540.9
132.5°	516.8	534.1	561.3	580.6	590.8	594.7	590.8	580.6	561.3	534.1	516.8
135°	493.4	509.2	533.6	552.2	562.4	564.7	562.4	552.2	533.6	509.2	493.4
137.5°	469.6	483.7	506.9	523.4	532.4	535.8	532.4	523.4	506.9	483.7	469.6
140°	448.6	461.1	479.2	493.9	502.4	505.8	502.4	493.9	479.2	461.1	448.6
142.5°	428.5	438.4	455.4	468.4	475.8	475.8	475.8	468.4	455.4	438.4	428.5
145°	412.0	420.3	433.9	443.5	449.2	450.9	449.2	443.5	433.9	420.3	412.0
147.5°	397.6	403.8	415.7	423.7	427.6	428.8	427.6	423.7	415.7	403.8	397.6
150°	385.2	390.3	398.7	405.5	408.9	409.5	408.9	405.5	398.7	390.3	385.2
152.5°	374.6	378.9	385.2	390.8	393.1	393.1	393.1	390.8	385.2	378.9	374.6
155°	364.5	367.6	373.8	377.8	380.1	378.9	380.1	377.8	373.8	367.6	364.5
157.5°	354.8	357.4	361.9	365.3	366.5	366.5	366.5	365.3	361.9	357.4	354.8
160°	345.2	347.2	351.2	354.0	354.6	354.6	354.6	354.0	351.2	347.2	345.2
162.5°	336.2	337.6	341.5	343.2	343.8	343.2	343.8	343.2	341.5	337.6	336.2
165°	327.4	328.5	330.8	333.0	333.0	332.5	333.0	333.0	330.8	328.5	327.4
167.5°	319.5	320.6	321.7	322.8	322.8	322.3	322.8	322.8	321.7	320.6	319.5
170°	312.1	312.7	313.2	314.9	314.4	313.2	314.4	314.9	313.2	312.7	312.1
172.5°	305.6	305.9	306.4	307.0	306.4	305.9	306.4	307.0	306.4	305.9	305.6
175°	300.5	300.8	300.8	301.3	300.8	299.6	300.8	301.3	300.8	300.8	300.5
177.5°	296.8	296.8	296.8	296.8	296.2	295.1	296.2	296.8	296.8	296.8	296.8
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	910.8	916.7	914.5	906.4	916.0	916.0	922.6	922.6	930.8	933.7	938.1
5°	859.2	863.6	867.3	863.6	870.3	880.6	886.5	891.7	902.7	907.2	913.8
7.5°	803.9	812.0	815.7	815.7	826.8	838.6	850.4	857.7	873.2	879.1	885.8
10°	750.1	759.7	767.0	766.3	784.7	792.1	806.9	823.8	839.3	848.2	857.7
12.5°	693.3	698.4	708.8	723.5	727.9	741.2	758.2	779.6	807.6	815.7	829.7
15°	646.1	660.1	668.2	674.8	685.2	697.7	716.1	736.8	764.8	782.5	797.3
17.5°	606.2	624.7	629.8	628.4	641.6	660.8	682.2	697.7	722.8	744.2	758.2
20°	573.8	581.2	590.0	593.7	604.0	624.7	645.3	663.0	683.7	700.7	716.9
22.5°	541.3	547.2	554.6	561.3	569.4	581.2	601.1	623.2	643.1	659.3	677.8
25°	514.8	518.5	525.1	530.3	539.1	547.2	561.3	585.6	609.2	618.8	635.0
27.5°	489.0	491.9	496.4	502.3	506.7	514.8	527.3	547.2	571.6	581.2	603.3
30°	466.1	468.3	472.8	475.7	477.9	487.5	497.1	512.6	531.0	544.3	560.5
32.5°	444.7	446.9	451.4	452.1	455.1	460.2	469.1	483.1	499.3	510.4	524.4
35°	421.1	422.6	427.0	428.5	430.7	435.1	441.8	452.1	466.9	475.0	487.5
37.5°	402.7	402.0	404.9	407.1	410.1	412.3	414.5	424.8	435.9	443.3	452.8
40°	382.8	381.3	382.0	385.0	386.5	389.4	389.4	399.7	407.1	413.0	420.4
42.5°	362.9	362.1	360.7	362.1	363.6	364.3	365.1	372.5	379.8	385.0	393.1
45°	343.0	342.2	340.7	341.5	341.5	343.0	345.2	348.1	353.3	357.7	362.1
47.5°	324.5	323.0	320.8	320.1	321.6	321.6	321.6	324.5	329.7	331.1	335.6
50°	305.3	303.1	300.2	298.7	298.7	298.0	299.4	300.2	304.6	306.1	309.8
52.5°	284.7	283.2	280.3	277.3	278.0	276.6	277.3	278.0	279.5	281.7	283.9
55°	264.0	261.1	258.9	258.1	255.9	255.9	253.7	256.7	255.9	256.7	259.6
57.5°	244.1	241.2	237.5	236.0	233.8	233.1	231.6	230.8	231.6	233.8	236.0
60°	220.5	219.0	216.8	214.6	213.1	210.9	209.5	209.5	208.7	208.7	209.5
62.5°	197.7	196.9	194.0	193.2	191.8	190.3	188.1	186.6	186.6	188.1	188.8
65°	175.5	174.8	172.6	171.8	168.2	166.7	165.9	165.2	163.7	163.7	163.7
67.5°	154.9	152.7	152.7	149.0	146.0	144.6	143.1	142.3	142.3	142.3	143.1
70°	132.0	132.0	129.8	127.6	124.6	125.4	123.2	121.0	121.0	119.5	120.2
72.5°	109.9	109.2	106.9	106.2	104.0	101.8	100.3	101.8	99.6	98.8	99.6
75°	88.5	87.8	86.3	84.8	85.6	83.3	81.1	80.4	80.4	78.9	78.9
77.5°	67.9	69.3	66.4	65.6	64.2	62.7	62.0	61.2	61.2	61.2	62.7
80°	47.2	47.9	47.9	46.5	47.2	45.0	45.0	45.0	42.8	43.5	44.3
82.5°	30.2	30.2	29.5	30.2	29.5	29.5	28.8	28.8	28.0	28.0	28.8
85°	17.0	16.2	15.5	17.0	16.2	16.2	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	18.1	17.0	18.1	18.7	19.3	18.7	15.3	11.3	8.5	7.6	6.8
92.5°	42.5	48.7	57.2	73.1	87.2	86.1	66.8	45.3	30.0	26.9	23.8
95°	90.1	113.8	148.4	194.3	222.0	196.5	130.8	81.6	55.5	48.7	41.9
97.5°	185.2	242.4	303.6	364.8	361.9	279.8	173.9	105.4	71.9	64.2	56.6
100°	369.3	446.9	517.1	529.0	447.5	308.1	185.8	116.7	86.7	78.8	70.8
102.5°	603.2	654.8	657.0	590.2	450.3	297.4	186.3	126.9	99.7	91.8	83.8
105°	759.5	752.2	688.2	570.4	419.7	282.6	189.2	138.8	112.1	104.2	96.3
107.5°	805.4	749.9	654.8	528.5	391.4	274.7	195.4	150.7	124.6	116.6	108.7
110°	782.8	710.3	608.9	489.4	372.1	272.4	203.3	162.6	137.6	129.4	121.2

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	742.0	663.3	567.0	462.2	359.7	273.0	211.8	173.9	150.1	141.6	133.1
115°	695.5	621.3	534.1	440.7	351.2	275.3	220.3	185.8	161.4	153.8	146.1
117.5°	654.2	585.1	506.9	425.9	346.6	278.7	229.4	196.5	173.9	166.0	158.0
120°	617.9	557.9	487.7	414.6	342.7	282.1	238.5	207.9	185.8	177.9	169.9
122.5°	591.3	535.2	472.4	405.0	340.4	286.0	246.4	218.6	198.2	190.0	181.8
125°	565.8	516.0	457.7	395.9	337.6	290.0	254.9	229.4	209.0	201.0	193.1
127.5°	544.3	496.7	442.9	387.4	335.9	294.0	262.8	239.6	219.8	211.6	203.3
130°	522.2	477.5	428.8	378.9	334.7	298.5	270.2	248.7	228.8	220.9	213.0
132.5°	499.6	459.4	415.2	372.1	334.2	303.0	277.5	256.6	237.9	230.0	222.0
135°	477.5	440.1	402.7	365.9	333.6	306.4	283.8	263.9	245.8	237.9	230.0
137.5°	455.4	424.8	392.5	361.4	333.6	309.8	288.9	270.2	252.0	244.6	237.3
140°	436.1	410.1	382.9	357.4	333.0	312.1	292.8	275.3	258.3	251.0	243.6
142.5°	418.6	397.0	375.0	353.4	333.0	313.8	296.2	279.2	262.8	256.0	249.2
145°	403.8	386.3	367.6	350.0	331.9	314.9	299.1	283.2	267.9	261.6	255.4
147.5°	391.4	377.2	361.9	346.6	330.2	315.5	300.8	286.6	271.9	266.2	260.5
150°	380.1	368.2	355.7	342.1	328.5	314.9	301.9	288.9	275.8	270.7	265.6
152.5°	370.4	360.8	349.5	338.1	325.7	313.8	302.5	291.1	279.8	275.2	270.7
155°	361.4	352.9	343.8	333.0	322.3	312.7	303.0	293.4	283.8	279.6	275.3
157.5°	352.3	344.9	337.0	328.5	318.9	310.4	303.0	295.1	286.6	282.9	279.2
160°	343.2	337.0	330.8	323.4	315.5	308.7	303.0	296.2	289.4	286.3	283.2
162.5°	334.7	329.6	324.5	318.9	312.7	307.0	302.5	296.8	291.1	288.8	286.6
165°	326.2	322.3	318.3	313.8	308.7	304.7	301.3	297.4	292.3	290.6	288.9
167.5°	318.3	315.5	312.1	308.7	305.3	302.5	300.8	297.4	293.4	292.2	291.1
170°	311.5	309.3	307.6	304.7	302.5	300.8	299.6	296.8	294.0	293.2	292.3
172.5°	305.3	303.6	302.5	300.8	299.1	298.5	297.9	296.2	294.5	294.0	293.4
175°	300.2	299.6	299.1	297.4	296.8	296.2	296.8	295.7	294.5	294.2	294.0
177.5°	296.8	296.2	296.2	295.1	294.5	295.1	296.2	295.1	294.5	294.5	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	959.5	959.5	959.5	959.5
2.5°	941.8	941.8	952.9	964.7
5°	921.2	926.3	944.0	960.3
7.5°	901.3	910.1	932.2	952.9
10°	876.9	888.7	916.0	940.3
12.5°	853.3	864.4	896.1	923.4
15°	820.1	834.1	868.1	902.0
17.5°	786.9	801.0	842.3	882.1
20°	747.9	766.3	812.8	865.9
22.5°	711.7	734.6	786.2	829.0
25°	671.9	707.3	755.2	810.5
27.5°	636.5	671.9	720.6	776.6
30°	596.7	632.8	683.0	734.6
32.5°	558.3	591.5	640.2	703.6
35°	518.5	550.2	597.4	661.6
37.5°	482.3	513.3	564.9	623.9
40°	446.9	479.4	523.6	582.6
42.5°	413.8	442.5	482.3	541.3
45°	383.5	404.2	441.0	496.4
47.5°	351.8	370.2	404.2	459.5
50°	322.3	337.8	367.3	418.9
52.5°	293.5	306.8	334.1	375.4
55°	267.7	280.3	300.2	340.7
57.5°	241.2	250.8	269.9	302.4
60°	215.4	224.2	239.7	266.2
62.5°	189.5	196.9	211.7	233.1
65°	166.7	172.6	183.6	202.1
67.5°	144.6	148.2	157.1	171.8
70°	123.2	126.1	133.5	145.3
72.5°	100.3	103.3	111.4	119.5
75°	81.1	81.9	87.8	94.4
77.5°	63.4	62.7	67.1	72.3
80°	43.5	45.7	49.4	51.6
82.5°	29.5	30.2	31.7	33.2
85°	16.2	17.0	17.0	19.2
87.5°	6.6	7.4	7.4	8.1
90°	5.7	4.5	2.3	0.6
92.5°	19.3	16.4	11.9	8.5
95°	32.9	27.8	22.1	19.8
97.5°	46.4	39.1	32.9	29.5
100°	59.5	50.4	45.3	43.6
102.5°	71.9	62.9	57.8	56.6
105°	83.8	75.3	71.4	69.1
107.5°	96.3	88.4	84.4	82.7
110°	109.3	102.0	98.6	96.3

TEST NUMBER: P1009077

CATALOG NUMBER: S122DIP-B485D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	121.8	115.0	111.0	108.7
115°	134.8	128.0	124.6	121.8
117.5°	147.3	141.0	137.6	135.4
120°	158.6	153.5	150.1	147.8
122.5°	170.5	164.8	161.4	159.7
125°	181.8	175.0	171.6	169.9
127.5°	192.6	185.2	180.7	178.4
130°	201.6	193.7	188.0	185.8
132.5°	210.1	201.6	195.4	192.6
135°	216.9	208.4	201.6	199.4
137.5°	224.3	215.2	208.4	205.6
140°	231.1	222.0	215.2	213.0
142.5°	237.3	228.3	222.0	220.3
145°	244.1	235.6	230.0	227.7
147.5°	250.9	243.0	237.3	235.6
150°	257.1	249.8	245.3	243.6
152.5°	262.8	256.6	252.0	251.5
155°	269.0	262.8	259.4	258.8
157.5°	274.1	268.5	265.6	265.1
160°	278.7	274.1	271.9	271.3
162.5°	282.6	279.2	277.0	277.5
165°	286.0	282.6	281.5	282.1
167.5°	288.9	286.6	285.5	286.0
170°	291.1	289.4	288.9	290.0
172.5°	292.8	291.1	291.7	292.3
175°	294.0	292.8	293.4	294.0
177.5°	294.5	293.4	294.0	295.1
180°	294.5	294.5	294.5	294.5

(END OF REPORT)