

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009094

Luminaire Tested: S122DIP-B485D530UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009094
REPORT IS A COMBINATION OF REPORTS P984272 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB35-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4047.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51
2	91	83	77	73	84	78	72	68	67	63	60	56	54	51	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29
6	65	53	45	39	60	50	43	37	43	38	33	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19
10	49	37	30	25	45	35	28	24	31	25	22	27	22	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15383	15383	15383	15383
5°	15419	16401	15478	13049
10°	15240	17905	15336	10758
15°	14871	18885	15077	9062
20°	14638	17732	14638	7877
25°	14172	15233	14236	7044
30°	13404	11974	13659	6380
35°	12724	8280	12937	5837
40°	11943	6252	12079	5404
45°	10979	5138	11158	4937
50°	10147	4510	10163	4520
55°	9196	3842	9254	4066
60°	8181	3210	8296	3549
65°	7277	2610	7408	3031
70°	6370	2049	6535	2445
75°	5348	1487	5555	1772
80°	4176	942	4471	1051
85°	2740	475	2952	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15901 cd/sqm

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	2.3
10°-20°	269.4	6.7
20°-30°	391.0	9.7
30°-40°	412.2	10.2
40°-50°	364.7	9.0
50°-60°	291.2	7.2
60°-70°	197.8	4.9
70°-80°	101.2	2.5
80°-90°	25.9	0.6
90°-100°	42.1	1.0
100°-110°	133.7	3.3
110°-120°	228.8	5.7
120°-130°	300.9	7.4
130°-140°	337.8	8.3
140°-150°	331.2	8.2
150°-160°	277.9	6.9
160°-170°	184.3	4.6
170°-180°	64.4	1.6
0°-30°	752.9	18.6
0°-40°	1165.1	28.8
0°-60°	1821.1	45.0
0°-90°	2145.9	53.0
90°-120°	404.6	10.0
90°-150°	1374.5	34.0
90°-180°	1901.0	47.0
0°-180°	4047.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	972	1085	976	864	972	92
15°	914	1334	926	640	914	258
25°	821	1111	825	514	821	375
35°	670	605	681	426	670	419
45°	503	364	511	350	503	390
55°	345	256	347	271	345	308
65°	205	158	208	183	205	203
75°	96	78	99	93	96	103
85°	19	20	21	15	19	23
90°	1	20	1	20	1	3
95°	30	36	30	36	30	33
105°	123	127	123	127	123	130
115°	230	230	230	230	230	227
125°	334	335	334	335	334	298
135°	432	437	432	437	432	334
145°	524	530	524	530	524	328
155°	600	604	600	604	600	276
165°	652	653	652	653	652	184
175°	679	676	679	676	679	64
180°	680	680	680	680	680	

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	977.0	979.2	983.0	983.7	991.2	997.2	1003.9	1003.9	1006.1	1005.4	999.4
5°	972.5	979.2	988.9	997.2	1010.6	1016.6	1025.5	1032.3	1038.2	1042.7	1042.0
7.5°	965.0	977.0	991.2	1006.9	1024.8	1035.3	1047.9	1059.9	1068.1	1075.6	1080.8
10°	952.3	972.5	991.9	1012.8	1036.0	1050.2	1065.1	1080.8	1093.5	1107.7	1121.1
12.5°	935.2	964.3	988.2	1015.8	1044.2	1059.9	1083.8	1095.8	1120.4	1156.3	1166.0
15°	913.5	953.1	975.5	1010.6	1047.9	1060.6	1093.5	1112.9	1163.7	1186.1	1213.0
17.5°	893.3	937.4	967.3	1007.6	1044.2	1068.9	1101.0	1140.6	1183.1	1215.3	1245.1
20°	876.9	919.5	955.3	1000.1	1046.5	1077.8	1111.4	1159.2	1205.6	1238.4	1261.6
22.5°	839.6	894.1	935.9	986.0	1042.0	1085.3	1117.4	1169.7	1219.7	1239.9	1260.1
25°	820.9	867.9	916.5	973.3	1039.0	1090.5	1118.2	1176.4	1220.5	1228.0	1232.4
27.5°	786.5	839.6	896.3	961.3	1038.2	1081.6	1116.7	1169.7	1204.8	1199.6	1186.1
30°	743.9	808.9	871.7	941.9	1027.8	1074.8	1107.7	1156.3	1174.2	1147.3	1123.4
32.5°	712.6	773.8	843.3	924.7	1015.8	1060.6	1092.8	1130.9	1134.6	1086.0	1045.7
35°	670.0	738.0	816.4	902.3	995.7	1036.0	1065.9	1089.0	1071.1	1003.1	955.3
37.5°	631.9	699.1	782.8	870.2	968.0	1007.6	1031.5	1035.3	991.2	931.4	861.2
40°	590.1	659.5	746.9	838.8	937.4	971.8	986.7	975.5	912.0	842.5	761.1
42.5°	548.2	617.0	711.1	805.2	898.6	927.7	933.7	903.0	825.4	743.9	649.8
45°	502.7	574.4	668.5	763.4	853.7	870.2	870.9	826.9	735.0	649.8	562.4
47.5°	465.3	531.8	625.2	720.0	796.2	807.4	803.0	752.2	652.1	556.5	480.3
50°	424.3	487.7	580.4	673.7	738.7	741.7	730.5	658.0	560.2	472.8	412.3
52.5°	380.2	444.4	529.6	619.2	677.5	673.0	651.3	573.6	481.8	409.3	363.0
55°	345.1	401.9	481.8	569.2	610.2	597.5	573.6	494.5	422.0	360.8	320.4
57.5°	306.2	356.3	434.7	510.9	534.8	522.9	499.0	425.0	357.8	311.5	284.6
60°	269.6	315.2	383.9	447.4	466.1	453.4	425.8	359.3	310.7	271.9	251.7
62.5°	236.0	275.6	333.1	391.4	398.9	386.2	362.3	308.5	266.7	236.0	221.1
65°	204.7	242.0	288.3	332.4	339.1	325.7	301.0	262.2	227.1	207.6	193.5
67.5°	174.0	203.9	245.0	277.1	280.8	268.1	248.0	216.6	194.9	174.0	163.6
70°	147.1	169.6	201.7	227.8	229.3	217.4	206.9	178.5	162.1	147.1	138.9
72.5°	121.0	136.7	161.3	180.8	181.5	174.0	164.3	146.4	132.2	121.8	113.5
75°	95.6	109.1	124.0	141.2	140.4	134.4	127.0	115.8	103.8	97.1	93.4
77.5°	73.2	81.4	93.4	104.6	104.6	101.6	97.1	88.9	81.4	74.7	71.0
80°	52.3	57.5	67.2	71.0	72.5	71.7	68.0	62.0	59.0	53.8	52.3
82.5°	33.6	37.3	41.8	45.6	47.8	46.3	45.6	42.6	38.1	36.6	35.1
85°	19.4	20.9	23.2	25.4	26.1	25.4	26.9	24.6	22.4	22.4	21.7
87.5°	8.2	9.0	10.5	10.5	11.2	11.2	10.5	11.2	11.2	10.5	9.7
90°	0.6	2.1	3.7	5.2	6.7	7.5	8.9	11.7	14.5	17.3	20.1
92.5°	12.6	13.6	14.6	15.7	16.7	17.2	17.3	17.4	17.5	17.7	17.8
95°	29.8	31.1	32.4	33.7	35.0	35.6	35.7	36.0	36.2	36.5	36.7
97.5°	49.9	51.1	52.2	53.4	54.5	55.1	55.4	55.9	56.4	56.9	57.4
100°	72.9	73.9	74.9	76.0	77.0	77.5	77.7	78.1	78.4	78.8	79.2
102.5°	97.0	97.8	98.5	99.3	100.0	100.4	100.7	101.2	101.7	102.2	102.7
105°	123.4	123.8	124.2	124.5	124.9	125.1	125.2	125.5	125.7	126.0	126.2
107.5°	149.8	150.3	150.8	151.3	151.8	152.1	152.1	152.1	152.1	152.1	152.1
110°	175.0	175.8	176.6	177.3	178.1	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	202.6	203.4	204.1	204.9	205.6	206.0	205.9	205.8	205.7	205.5	205.4
115°	229.5	230.3	231.1	231.8	232.6	233.0	232.9	232.6	232.3	232.1	231.8
117.5°	256.5	257.5	258.5	259.6	260.6	261.1	260.8	260.1	259.5	258.8	258.2
120°	283.5	284.5	285.5	286.6	287.6	288.1	287.6	286.6	285.5	284.5	283.5
122.5°	308.1	309.4	310.7	312.0	313.3	313.9	313.6	312.9	312.3	311.6	311.0
125°	334.0	335.1	336.3	337.4	338.5	339.1	338.9	338.5	338.2	337.8	337.4
127.5°	359.2	360.6	362.0	363.4	364.8	365.5	365.2	364.7	364.2	363.7	363.2
130°	382.7	384.4	386.0	387.7	389.4	390.2	390.1	389.8	389.5	389.3	389.0
132.5°	409.1	410.4	411.7	413.0	414.3	414.9	415.0	415.1	415.2	415.3	415.4
135°	432.1	433.5	434.9	436.3	437.7	438.4	438.5	438.8	439.0	439.3	439.5
137.5°	457.3	458.5	459.6	460.8	461.9	462.5	462.6	462.9	463.1	463.4	463.6
140°	479.7	480.9	482.0	483.2	484.3	484.9	485.2	485.8	486.5	487.1	487.7
142.5°	502.7	503.8	505.0	506.1	507.2	507.8	508.0	508.4	508.7	509.1	509.5
145°	524.5	525.4	526.3	527.2	528.1	528.5	528.9	529.6	530.4	531.1	531.9
147.5°	544.0	545.1	546.3	547.4	548.5	549.1	549.4	549.9	550.4	550.9	551.4
150°	564.1	564.9	565.6	566.4	567.1	567.5	567.8	568.3	568.8	569.3	569.8
152.5°	581.8	582.6	583.4	584.1	584.9	585.3	585.6	586.3	586.9	587.6	588.2
155°	599.6	600.0	600.4	600.8	601.2	601.4	601.6	602.0	602.3	602.7	603.1
157.5°	615.1	615.4	615.6	615.9	616.2	616.3	616.4	616.7	616.9	617.2	617.4
160°	628.9	629.1	629.4	629.6	629.9	630.0	630.1	630.2	630.3	630.5	630.6
162.5°	641.5	641.5	641.5	641.5	641.5	641.5	641.6	641.7	641.8	642.0	642.1
165°	652.4	652.3	652.2	652.1	652.0	651.9	651.9	651.9	651.9	651.9	651.9
167.5°	662.2	661.8	661.4	661.1	660.7	660.5	660.5	660.5	660.5	660.5	660.5
170°	669.6	669.2	668.8	668.5	668.1	667.9	667.8	667.7	667.6	667.4	667.3
172.5°	674.8	674.4	674.0	673.7	673.3	673.1	673.0	672.9	672.8	672.6	672.5
175°	678.8	678.4	678.0	677.7	677.3	677.1	677.0	676.7	676.5	676.2	676.0
177.5°	681.1	680.7	680.3	680.0	679.6	679.4	679.3	679.0	678.7	678.5	678.2
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1009.9	1010.6	1012.1	1019.6	1023.3	1024.0	1021.1	1027.8	1030.0	1027.8	1026.3
5°	1057.7	1062.1	1071.1	1080.8	1080.1	1080.8	1085.3	1089.8	1091.3	1085.3	1087.5
7.5°	1099.5	1108.4	1118.2	1133.1	1133.1	1140.6	1143.6	1147.3	1156.3	1151.8	1150.3
10°	1147.3	1159.2	1177.2	1201.1	1201.8	1209.3	1216.8	1228.7	1232.4	1229.5	1230.9
12.5°	1207.0	1230.2	1231.7	1257.8	1269.8	1271.3	1283.2	1281.0	1288.5	1288.5	1301.2
15°	1233.2	1269.0	1289.2	1314.6	1322.1	1313.1	1322.8	1333.3	1334.0	1334.0	1333.3
17.5°	1280.2	1294.4	1314.6	1328.0	1331.0	1331.0	1331.8	1336.3	1333.3	1327.3	1331.8
20°	1290.0	1295.9	1303.4	1301.9	1303.4	1295.9	1288.5	1281.0	1281.7	1278.0	1289.2
22.5°	1272.0	1270.5	1253.4	1242.2	1242.2	1227.2	1213.0	1206.3	1199.6	1201.8	1205.6
25°	1227.2	1204.1	1183.1	1166.7	1163.0	1139.1	1119.7	1113.7	1102.5	1111.4	1112.9
27.5°	1155.5	1129.4	1095.8	1081.6	1062.1	1052.4	1039.0	1021.1	997.9	1011.3	1009.1
30°	1078.6	1039.7	1012.1	977.7	947.1	944.9	919.5	889.6	877.6	877.6	884.4
32.5°	992.7	941.1	900.8	852.3	822.4	809.7	779.1	749.2	755.9	733.5	741.7
35°	892.6	824.6	773.8	726.8	704.4	689.4	649.8	633.4	615.5	605.0	624.4
37.5°	797.0	718.6	653.6	602.0	593.8	566.9	540.0	529.6	519.1	523.6	522.9
40°	680.5	611.0	552.7	512.4	498.2	485.5	467.6	454.9	448.2	451.9	452.6
42.5°	575.1	516.9	473.6	445.2	433.2	424.3	415.3	404.8	402.6	402.6	405.6
45°	493.7	445.9	416.8	393.6	386.9	380.2	373.5	369.0	367.5	364.5	366.7
47.5°	428.7	390.6	372.7	355.5	348.1	346.6	340.6	338.4	335.4	334.6	335.4
50°	374.2	350.3	333.9	324.2	318.9	316.7	313.7	309.2	307.7	311.5	310.0
52.5°	336.1	313.7	304.7	295.0	292.1	289.1	284.6	285.3	284.6	283.1	283.1
55°	298.0	283.8	274.9	267.4	266.7	263.7	259.9	258.4	257.7	256.2	258.4
57.5°	267.4	256.2	248.0	241.3	238.3	238.3	234.5	231.5	231.5	230.8	231.5
60°	236.8	225.6	220.3	213.6	211.4	210.6	208.4	206.9	204.7	204.7	204.7
62.5°	208.4	199.4	193.5	187.5	188.2	184.5	181.5	180.0	180.0	180.8	180.8
65°	181.5	175.5	168.1	162.8	161.3	160.6	159.1	158.3	156.1	157.6	157.6
67.5°	156.9	148.6	144.2	141.9	139.7	138.9	137.4	135.9	135.2	134.4	135.9
70°	132.2	125.5	121.8	120.3	118.0	117.3	116.5	114.3	115.0	115.8	116.5
72.5°	109.8	103.8	103.1	98.6	98.6	98.6	95.6	97.1	96.4	94.9	96.4
75°	86.6	83.7	82.2	79.9	80.7	79.9	79.2	76.9	76.9	77.7	78.4
77.5°	68.7	65.7	65.0	62.7	61.2	62.7	61.2	60.5	60.5	61.2	61.2
80°	50.8	49.3	47.1	47.1	47.1	46.3	46.3	46.3	45.6	44.8	45.6
82.5°	33.6	33.6	32.9	32.1	32.9	31.4	32.1	32.1	32.1	32.1	32.1
85°	21.7	20.9	20.9	20.2	20.2	20.2	20.9	19.4	19.4	20.2	20.2
87.5°	9.7	9.7	9.7	10.5	9.7	9.7	9.7	10.5	9.7	9.7	9.7
90°	19.8	19.6	19.3	19.0	18.9	19.0	19.1	19.2	19.4	19.5	19.4
92.5°	17.9	18.1	18.2	18.3	18.4	18.4	18.4	18.4	18.4	18.4	18.4
95°	36.7	36.7	36.7	36.7	36.7	36.6	36.3	36.1	35.8	35.6	35.8
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
100°	79.2	79.2	79.2	79.2	79.2	79.1	79.0	78.9	78.7	78.6	78.7
102.5°	102.8	103.0	103.1	103.2	103.3	103.2	103.1	103.0	102.8	102.7	102.8
105°	126.5	126.7	127.0	127.3	127.4	127.4	127.4	127.4	127.4	127.4	127.4
107.5°	152.2	152.3	152.4	152.5	152.6	152.3	151.7	151.0	150.4	149.8	150.4
110°	178.5	178.5	178.5	178.5	178.5	178.3	177.9	177.5	177.1	176.7	177.1

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	205.0	204.6	204.3	203.9	203.7	203.6	203.3	203.1	202.8	202.6	202.8
115°	231.7	231.5	231.4	231.3	231.2	231.0	230.6	230.3	229.9	229.5	229.9
117.5°	257.8	257.4	257.1	256.7	256.5	256.3	255.9	255.6	255.2	254.8	255.2
120°	283.5	283.5	283.5	283.5	283.5	283.3	282.9	282.5	282.1	281.7	282.1
122.5°	310.6	310.2	309.9	309.5	309.3	309.2	308.9	308.6	308.4	308.1	308.4
125°	337.0	336.6	336.3	335.9	335.7	335.6	335.5	335.4	335.2	335.1	335.2
127.5°	362.7	362.2	361.7	361.2	360.9	360.7	360.3	360.0	359.6	359.2	359.6
130°	388.8	388.5	388.3	388.0	387.9	387.6	387.1	386.6	386.1	385.6	386.1
132.5°	414.8	414.2	413.5	412.9	412.6	412.4	412.0	411.7	411.3	410.9	411.3
135°	439.4	439.3	439.2	439.1	439.0	438.8	438.4	438.0	437.6	437.2	437.6
137.5°	463.5	463.4	463.3	463.2	463.1	462.8	462.3	461.8	461.3	460.8	461.3
140°	487.7	487.7	487.7	487.7	487.7	487.4	486.9	486.4	485.9	485.4	485.9
142.5°	509.6	509.8	509.9	510.0	510.1	509.8	509.3	508.8	508.3	507.8	508.3
145°	532.0	532.2	532.3	532.4	532.5	532.2	531.7	531.2	530.7	530.2	530.7
147.5°	551.7	551.9	552.2	552.5	552.6	552.3	551.8	551.3	550.8	550.3	550.8
150°	570.2	570.6	570.9	571.3	571.5	571.3	570.9	570.6	570.2	569.8	570.2
152.5°	588.7	589.2	589.7	590.2	590.5	590.2	589.7	589.2	588.7	588.2	588.7
155°	603.7	604.3	605.0	605.6	605.9	605.7	605.3	605.0	604.6	604.2	604.6
157.5°	618.3	619.2	620.1	621.0	621.4	621.1	620.5	619.8	619.2	618.6	619.2
160°	631.4	632.2	632.9	633.7	634.1	633.8	633.3	632.8	632.3	631.8	632.3
162.5°	643.0	643.9	644.8	645.7	646.1	645.8	645.1	644.5	643.8	643.2	643.8
165°	652.8	653.7	654.6	655.5	655.9	655.6	654.9	654.3	653.6	653.0	653.6
167.5°	661.4	662.3	663.2	664.1	664.5	664.2	663.5	662.9	662.2	661.6	662.2
170°	668.2	669.1	670.0	670.9	671.4	671.0	670.2	669.5	668.7	667.9	668.7
172.5°	673.4	674.3	675.2	676.1	676.5	676.1	675.4	674.6	673.9	673.1	673.9
175°	676.9	677.8	678.7	679.6	680.0	679.6	678.8	678.1	677.3	676.5	677.3
177.5°	679.0	679.8	680.5	681.3	681.7	681.3	680.5	679.8	679.0	678.2	679.0
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1030.0	1024.8	1020.3	1021.1	1024.8	1021.8	1014.3	1004.6	1000.9	996.4	1000.9
5°	1092.0	1087.5	1078.6	1079.3	1077.1	1074.1	1062.1	1047.2	1047.2	1035.3	1033.8
7.5°	1153.3	1146.5	1140.6	1139.1	1130.9	1124.9	1114.4	1093.5	1085.3	1071.1	1062.9
10°	1222.0	1216.8	1210.0	1201.8	1197.3	1186.9	1169.7	1139.1	1124.1	1104.7	1090.5
12.5°	1291.4	1290.7	1275.8	1259.3	1258.6	1242.2	1230.2	1189.1	1169.0	1142.8	1109.2
15°	1335.5	1331.8	1323.6	1315.4	1317.6	1299.7	1272.8	1224.2	1210.8	1179.4	1143.6
17.5°	1334.8	1334.8	1332.5	1331.0	1328.8	1323.6	1308.6	1276.5	1254.8	1215.3	1181.6
20°	1292.2	1301.9	1304.1	1303.4	1310.9	1314.6	1313.9	1293.7	1276.5	1241.4	1207.0
22.5°	1207.0	1229.5	1239.2	1245.1	1260.8	1269.0	1288.5	1281.0	1276.5	1250.4	1221.2
25°	1127.9	1135.3	1164.5	1166.0	1187.6	1207.8	1227.2	1239.9	1256.3	1246.6	1222.0
27.5°	1025.5	1042.7	1063.6	1079.3	1083.8	1124.9	1157.0	1180.9	1218.2	1221.2	1213.0
30°	909.8	918.0	952.3	973.3	997.2	1027.0	1073.3	1114.4	1148.0	1178.7	1189.1
32.5°	768.6	802.2	822.4	847.8	868.7	921.7	978.5	1031.5	1070.4	1121.9	1144.3
35°	639.4	665.5	699.9	710.3	748.4	793.2	867.2	935.2	994.2	1046.5	1092.0
37.5°	532.6	553.5	590.1	606.5	628.9	686.4	748.4	832.8	903.8	968.0	1024.8
40°	459.4	475.0	502.7	507.9	526.6	578.9	628.9	708.1	802.2	888.9	950.8
42.5°	409.3	416.8	435.5	442.2	454.1	489.2	534.1	608.8	696.1	785.8	873.2
45°	373.5	378.7	389.9	395.9	410.8	426.5	463.1	522.9	591.6	682.0	776.1
47.5°	341.3	348.1	352.6	356.3	364.5	381.7	405.6	449.7	515.4	598.3	689.4
50°	314.5	316.7	324.9	325.7	330.9	342.1	364.5	391.4	443.7	510.9	599.0
52.5°	287.6	289.8	295.0	300.3	302.5	311.5	326.4	348.8	387.7	440.7	519.1
55°	260.7	263.7	268.9	272.6	274.9	282.3	291.3	313.0	343.6	380.9	445.2
57.5°	233.8	240.5	242.0	244.2	248.0	256.2	264.4	277.1	301.0	335.4	382.4
60°	208.4	210.6	215.9	218.1	221.8	226.3	236.8	246.5	263.7	290.6	333.1
62.5°	182.3	187.5	189.7	192.0	194.9	200.2	206.9	217.4	232.3	254.0	287.6
65°	159.8	160.6	165.1	168.1	171.0	174.8	181.5	191.2	200.2	220.3	245.0
67.5°	138.2	139.7	141.2	144.2	147.9	151.6	157.6	162.8	174.0	187.5	206.9
70°	117.3	117.3	121.0	123.2	122.5	127.0	131.5	137.4	145.7	158.3	174.0
72.5°	98.6	97.8	100.8	101.6	103.1	106.1	109.1	115.0	119.5	129.2	141.2
75°	78.4	79.9	81.4	81.4	83.7	85.9	88.9	91.9	97.1	103.1	112.0
77.5°	62.0	62.0	63.5	64.2	66.5	65.7	68.7	71.7	75.4	80.7	87.4
80°	45.6	47.1	47.1	47.1	47.8	48.6	51.5	53.8	56.0	59.8	62.7
82.5°	32.1	32.1	33.6	33.6	33.6	35.1	35.1	35.9	37.3	39.6	41.8
85°	20.2	20.2	20.2	20.9	20.2	20.9	22.4	21.7	22.4	23.9	23.9
87.5°	9.7	9.7	9.7	9.7	9.7	10.5	9.7	10.5	11.2	11.2	11.2
90°	19.2	19.1	19.0	18.9	19.0	19.3	19.6	19.8	20.1	17.3	14.5
92.5°	18.4	18.4	18.4	18.4	18.3	18.2	18.1	17.9	17.8	17.7	17.5
95°	36.1	36.3	36.6	36.7	36.7	36.7	36.7	36.7	36.7	36.5	36.2
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	56.9	56.4
100°	78.9	79.0	79.1	79.2	79.2	79.2	79.2	79.2	79.2	78.8	78.4
102.5°	103.0	103.1	103.2	103.3	103.2	103.1	103.0	102.8	102.7	102.2	101.7
105°	127.4	127.4	127.4	127.4	127.3	127.0	126.7	126.5	126.2	126.0	125.7
107.5°	151.0	151.7	152.3	152.6	152.5	152.4	152.3	152.2	152.1	152.1	152.1
110°	177.5	177.9	178.3	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	203.1	203.3	203.6	203.7	203.9	204.3	204.6	205.0	205.4	205.5	205.7
115°	230.3	230.6	231.0	231.2	231.3	231.4	231.5	231.7	231.8	232.1	232.3
117.5°	255.6	255.9	256.3	256.5	256.7	257.1	257.4	257.8	258.2	258.8	259.5
120°	282.5	282.9	283.3	283.5	283.5	283.5	283.5	283.5	283.5	284.5	285.5
122.5°	308.6	308.9	309.2	309.3	309.5	309.9	310.2	310.6	311.0	311.6	312.3
125°	335.4	335.5	335.6	335.7	335.9	336.3	336.6	337.0	337.4	337.8	338.2
127.5°	360.0	360.3	360.7	360.9	361.2	361.7	362.2	362.7	363.2	363.7	364.2
130°	386.6	387.1	387.6	387.9	388.0	388.3	388.5	388.8	389.0	389.3	389.5
132.5°	411.7	412.0	412.4	412.6	412.9	413.5	414.2	414.8	415.4	415.3	415.2
135°	438.0	438.4	438.8	439.0	439.1	439.2	439.3	439.4	439.5	439.3	439.0
137.5°	461.8	462.3	462.8	463.1	463.2	463.3	463.4	463.5	463.6	463.4	463.1
140°	486.4	486.9	487.4	487.7	487.7	487.7	487.7	487.7	487.7	487.1	486.5
142.5°	508.8	509.3	509.8	510.1	510.0	509.9	509.8	509.6	509.5	509.1	508.7
145°	531.2	531.7	532.2	532.5	532.4	532.3	532.2	532.0	531.9	531.1	530.4
147.5°	551.3	551.8	552.3	552.6	552.5	552.2	551.9	551.7	551.4	550.9	550.4
150°	570.6	570.9	571.3	571.5	571.3	570.9	570.6	570.2	569.8	569.3	568.8
152.5°	589.2	589.7	590.2	590.5	590.2	589.7	589.2	588.7	588.2	587.6	586.9
155°	605.0	605.3	605.7	605.9	605.6	605.0	604.3	603.7	603.1	602.7	602.3
157.5°	619.8	620.5	621.1	621.4	621.0	620.1	619.2	618.3	617.4	617.2	616.9
160°	632.8	633.3	633.8	634.1	633.7	632.9	632.2	631.4	630.6	630.5	630.3
162.5°	644.5	645.1	645.8	646.1	645.7	644.8	643.9	643.0	642.1	642.0	641.8
165°	654.3	654.9	655.6	655.9	655.5	654.6	653.7	652.8	651.9	651.9	651.9
167.5°	662.9	663.5	664.2	664.5	664.1	663.2	662.3	661.4	660.5	660.5	660.5
170°	669.5	670.2	671.0	671.4	670.9	670.0	669.1	668.2	667.3	667.4	667.6
172.5°	674.6	675.4	676.1	676.5	676.1	675.2	674.3	673.4	672.5	672.6	672.8
175°	678.1	678.8	679.6	680.0	679.6	678.7	677.8	676.9	676.0	676.2	676.5
177.5°	679.8	680.5	681.3	681.7	681.3	680.5	679.8	679.0	678.2	678.5	678.7
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	997.2	993.4	991.2	992.7	988.2	977.0	977.0	980.7	976.2	971.8	965.0
5°	1024.8	1017.3	1012.8	1012.1	1001.6	983.7	980.0	976.2	966.5	956.1	944.9
7.5°	1051.7	1038.2	1030.8	1025.5	1010.6	987.4	977.7	969.5	953.8	938.1	924.0
10°	1074.1	1054.7	1045.7	1037.5	1018.1	988.9	973.3	958.3	938.1	918.0	900.1
12.5°	1092.0	1069.6	1058.4	1046.5	1022.6	984.5	965.0	941.1	921.0	894.1	876.2
15°	1121.9	1075.6	1065.1	1053.9	1029.3	977.0	953.1	926.2	898.6	862.7	843.3
17.5°	1145.8	1083.8	1083.1	1059.2	1027.0	974.0	937.4	902.3	872.4	836.6	805.9
20°	1160.0	1096.5	1084.5	1059.9	1019.6	953.8	915.7	876.9	844.8	801.5	770.8
22.5°	1171.9	1114.4	1083.1	1053.2	1003.9	947.1	891.1	854.5	810.4	763.4	734.2
25°	1176.4	1118.2	1085.3	1050.9	992.7	927.7	864.2	824.6	775.3	732.7	693.2
27.5°	1177.2	1117.4	1077.1	1041.2	977.0	902.3	837.3	795.5	741.0	691.7	652.1
30°	1169.7	1109.2	1072.6	1033.8	962.1	879.1	804.4	758.1	699.9	650.6	609.5
32.5°	1147.3	1092.8	1062.9	1020.3	942.6	847.0	773.1	721.5	660.3	611.7	572.2
35°	1109.9	1072.6	1039.7	1000.1	917.2	817.1	741.7	681.2	619.2	572.9	535.6
37.5°	1063.6	1043.5	1012.8	974.0	888.1	790.3	706.6	639.4	577.4	532.6	496.0
40°	1000.9	1006.1	976.2	941.1	853.7	753.7	661.0	596.8	538.5	496.7	460.9
42.5°	932.9	954.6	937.4	903.8	815.7	713.3	627.4	556.5	499.7	456.4	426.5
45°	859.7	897.1	886.6	862.0	776.1	670.7	579.6	510.9	460.9	419.0	392.9
47.5°	779.8	832.8	832.8	814.9	732.0	628.2	538.5	468.3	419.0	389.2	363.8
50°	698.4	758.1	767.8	755.9	682.7	579.6	488.5	425.0	382.4	353.3	334.6
52.5°	613.2	682.7	700.6	694.6	630.4	533.3	447.4	385.4	346.6	321.2	304.7
55°	531.8	612.5	631.9	634.1	574.4	482.5	401.9	347.3	310.0	292.8	278.6
57.5°	454.9	532.6	554.2	558.0	517.6	436.2	359.3	311.5	277.9	263.7	252.5
60°	389.2	454.1	482.5	490.7	455.6	382.4	319.7	273.4	248.0	234.5	224.1
62.5°	335.4	387.7	417.5	419.8	404.1	335.4	278.6	239.8	218.1	206.2	200.9
65°	283.1	330.1	348.1	357.0	344.3	290.6	240.5	208.4	191.2	180.8	175.5
67.5°	241.3	271.1	286.1	298.0	285.3	245.0	204.7	178.5	165.8	155.4	152.4
70°	197.9	222.6	233.8	245.7	234.5	203.9	174.8	150.9	139.7	131.5	127.7
72.5°	158.3	177.8	188.2	195.7	189.0	163.6	139.7	123.2	115.0	109.1	106.8
75°	125.5	138.9	144.9	150.1	147.1	127.7	112.8	99.3	91.9	86.6	85.2
77.5°	95.6	105.3	112.0	113.5	109.8	97.1	84.4	76.2	70.2	67.2	65.7
80°	68.0	73.9	77.7	79.9	76.2	71.0	62.0	56.0	50.8	47.1	46.3
82.5°	45.6	48.6	51.5	50.8	49.3	44.8	39.6	36.6	34.4	31.4	31.4
85°	26.1	26.9	28.4	29.1	28.4	25.4	22.4	20.9	19.4	17.2	17.2
87.5°	11.2	12.0	12.0	12.7	11.2	11.2	9.7	8.2	8.2	7.5	6.7
90°	11.7	8.9	7.5	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	17.4	17.3	17.2	16.7	15.7	14.6	13.6	12.6	13.6	14.6	15.7
95°	36.0	35.7	35.6	35.0	33.7	32.4	31.1	29.8	31.1	32.4	33.7
97.5°	55.9	55.4	55.1	54.5	53.4	52.2	51.1	49.9	51.1	52.2	53.4
100°	78.1	77.7	77.5	77.0	76.0	74.9	73.9	72.9	73.9	74.9	76.0
102.5°	101.2	100.7	100.4	100.0	99.3	98.5	97.8	97.0	97.8	98.5	99.3
105°	125.5	125.2	125.1	124.9	124.5	124.2	123.8	123.4	123.8	124.2	124.5
107.5°	152.1	152.1	152.1	151.8	151.3	150.8	150.3	149.8	150.3	150.8	151.3
110°	178.5	178.5	178.5	178.1	177.3	176.6	175.8	175.0	175.8	176.6	177.3

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	205.8	205.9	206.0	205.6	204.9	204.1	203.4	202.6	203.4	204.1	204.9
115°	232.6	232.9	233.0	232.6	231.8	231.1	230.3	229.5	230.3	231.1	231.8
117.5°	260.1	260.8	261.1	260.6	259.6	258.5	257.5	256.5	257.5	258.5	259.6
120°	286.6	287.6	288.1	287.6	286.6	285.5	284.5	283.5	284.5	285.5	286.6
122.5°	312.9	313.6	313.9	313.3	312.0	310.7	309.4	308.1	309.4	310.7	312.0
125°	338.5	338.9	339.1	338.5	337.4	336.3	335.1	334.0	335.1	336.3	337.4
127.5°	364.7	365.2	365.5	364.8	363.4	362.0	360.6	359.2	360.6	362.0	363.4
130°	389.8	390.1	390.2	389.4	387.7	386.0	384.4	382.7	384.4	386.0	387.7
132.5°	415.1	415.0	414.9	414.3	413.0	411.7	410.4	409.1	410.4	411.7	413.0
135°	438.8	438.5	438.4	437.7	436.3	434.9	433.5	432.1	433.5	434.9	436.3
137.5°	462.9	462.6	462.5	461.9	460.8	459.6	458.5	457.3	458.5	459.6	460.8
140°	485.8	485.2	484.9	484.3	483.2	482.0	480.9	479.7	480.9	482.0	483.2
142.5°	508.4	508.0	507.8	507.2	506.1	505.0	503.8	502.7	503.8	505.0	506.1
145°	529.6	528.9	528.5	528.1	527.2	526.3	525.4	524.5	525.4	526.3	527.2
147.5°	549.9	549.4	549.1	548.5	547.4	546.3	545.1	544.0	545.1	546.3	547.4
150°	568.3	567.8	567.5	567.1	566.4	565.6	564.9	564.1	564.9	565.6	566.4
152.5°	586.3	585.6	585.3	584.9	584.1	583.4	582.6	581.8	582.6	583.4	584.1
155°	602.0	601.6	601.4	601.2	600.8	600.4	600.0	599.6	600.0	600.4	600.8
157.5°	616.7	616.4	616.3	616.2	615.9	615.6	615.4	615.1	615.4	615.6	615.9
160°	630.2	630.1	630.0	629.9	629.6	629.4	629.1	628.9	629.1	629.4	629.6
162.5°	641.7	641.6	641.5	641.5	641.5	641.5	641.5	641.5	641.5	641.5	641.5
165°	651.9	651.9	651.9	652.0	652.1	652.2	652.3	652.4	652.3	652.2	652.1
167.5°	660.5	660.5	660.5	660.7	661.1	661.4	661.8	662.2	661.8	661.4	661.1
170°	667.7	667.8	667.9	668.1	668.5	668.8	669.2	669.6	669.2	668.8	668.5
172.5°	672.9	673.0	673.1	673.3	673.7	674.0	674.4	674.8	674.4	674.0	673.7
175°	676.7	677.0	677.1	677.3	677.7	678.0	678.4	678.8	678.4	678.0	677.7
177.5°	679.0	679.3	679.4	679.6	680.0	680.3	680.7	681.1	680.7	680.3	680.0
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	961.3	965.0	964.3	956.8	948.6	941.9	929.2	930.7	926.2	926.9	931.4
5°	937.4	937.4	934.4	924.0	910.5	903.0	888.9	885.1	876.2	875.4	874.7
7.5°	912.0	908.3	904.5	889.6	873.2	861.2	841.8	837.3	828.3	822.4	819.4
10°	882.1	876.9	869.4	852.3	832.1	817.1	797.0	791.0	773.8	766.4	761.9
12.5°	849.3	846.3	834.3	820.1	787.3	770.8	741.7	747.7	730.5	715.6	713.3
15°	816.4	805.2	798.5	775.3	735.7	728.3	705.1	693.2	677.5	665.5	665.5
17.5°	784.3	767.1	752.2	727.5	698.4	677.5	660.3	654.3	634.9	622.9	620.7
20°	741.7	722.3	718.6	683.4	663.3	640.1	623.7	608.8	594.6	589.3	585.6
22.5°	701.4	679.0	673.0	643.1	622.9	599.8	583.4	572.9	562.4	558.7	552.0
25°	658.0	644.6	635.6	603.5	581.1	559.5	548.2	540.8	531.1	530.3	525.8
27.5°	616.2	603.5	594.6	563.9	547.5	527.3	518.4	510.2	504.9	502.7	500.4
30°	580.4	566.2	555.7	533.3	513.1	496.7	489.2	484.0	481.0	477.3	476.5
32.5°	540.8	532.6	518.4	501.2	485.5	469.8	465.3	461.6	457.1	455.6	454.9
35°	507.2	496.0	487.0	467.6	460.9	447.4	442.2	439.2	433.2	431.7	430.2
37.5°	474.3	463.8	454.1	442.2	429.5	422.0	419.0	414.5	411.6	412.3	410.8
40°	441.4	433.2	425.8	413.1	405.6	401.9	395.9	391.4	389.9	390.6	389.9
42.5°	409.3	401.9	397.4	387.7	380.2	376.5	372.7	368.2	370.5	370.5	372.7
45°	380.2	373.5	370.5	363.0	358.5	352.6	348.8	348.1	351.1	350.3	350.3
47.5°	350.3	348.1	344.3	337.6	331.6	327.9	327.2	327.2	330.1	331.6	330.9
50°	327.2	322.7	318.2	313.0	308.5	307.0	304.7	306.2	309.2	309.2	310.7
52.5°	298.0	295.0	293.5	289.1	286.1	286.1	286.1	286.8	289.1	291.3	290.6
55°	272.6	270.4	268.9	266.7	262.9	263.7	262.9	264.4	266.7	268.9	270.4
57.5°	245.7	245.0	243.5	239.8	239.8	239.0	241.3	242.0	245.7	247.2	249.5
60°	221.8	219.6	219.6	216.6	216.6	216.6	218.9	221.1	224.1	224.8	226.3
62.5°	196.4	196.4	195.7	193.5	193.5	195.7	196.4	199.4	200.9	200.9	203.2
65°	172.5	171.8	171.0	171.8	172.5	172.5	174.8	176.3	177.8	178.5	179.3
67.5°	148.6	147.9	149.4	148.6	150.1	153.1	152.4	154.6	156.9	156.9	157.6
70°	126.2	127.7	127.0	128.5	127.7	129.2	131.5	132.2	132.2	133.0	135.2
72.5°	105.3	105.3	105.3	104.6	105.3	106.8	108.3	109.1	110.5	111.3	113.5
75°	85.2	85.2	83.7	85.2	85.2	86.6	88.1	88.1	88.1	89.6	91.9
77.5°	64.2	65.0	64.2	65.7	65.7	66.5	68.0	67.2	68.7	69.5	70.2
80°	47.1	46.3	46.3	46.3	47.1	47.1	48.6	49.3	49.3	51.5	50.0
82.5°	29.9	30.6	29.9	30.6	30.6	31.4	30.6	31.4	32.1	33.6	32.9
85°	17.2	16.4	16.4	17.2	16.4	16.4	17.2	16.4	17.2	16.4	17.2
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	6.7	7.5	8.9	11.7	14.5	17.3	20.1	19.8	19.6	19.3	19.0
92.5°	16.7	17.2	17.3	17.4	17.5	17.7	17.8	17.9	18.1	18.2	18.3
95°	35.0	35.6	35.7	36.0	36.2	36.5	36.7	36.7	36.7	36.7	36.7
97.5°	54.5	55.1	55.4	55.9	56.4	56.9	57.4	57.4	57.4	57.4	57.4
100°	77.0	77.5	77.7	78.1	78.4	78.8	79.2	79.2	79.2	79.2	79.2
102.5°	100.0	100.4	100.7	101.2	101.7	102.2	102.7	102.8	103.0	103.1	103.2
105°	124.9	125.1	125.2	125.5	125.7	126.0	126.2	126.5	126.7	127.0	127.3
107.5°	151.8	152.1	152.1	152.1	152.1	152.1	152.1	152.2	152.3	152.4	152.5
110°	178.1	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	205.6	206.0	205.9	205.8	205.7	205.5	205.4	205.0	204.6	204.3	203.9
115°	232.6	233.0	232.9	232.6	232.3	232.1	231.8	231.7	231.5	231.4	231.3
117.5°	260.6	261.1	260.8	260.1	259.5	258.8	258.2	257.8	257.4	257.1	256.7
120°	287.6	288.1	287.6	286.6	285.5	284.5	283.5	283.5	283.5	283.5	283.5
122.5°	313.3	313.9	313.6	312.9	312.3	311.6	311.0	310.6	310.2	309.9	309.5
125°	338.5	339.1	338.9	338.5	338.2	337.8	337.4	337.0	336.6	336.3	335.9
127.5°	364.8	365.5	365.2	364.7	364.2	363.7	363.2	362.7	362.2	361.7	361.2
130°	389.4	390.2	390.1	389.8	389.5	389.3	389.0	388.8	388.5	388.3	388.0
132.5°	414.3	414.9	415.0	415.1	415.2	415.3	415.4	414.8	414.2	413.5	412.9
135°	437.7	438.4	438.5	438.8	439.0	439.3	439.5	439.4	439.3	439.2	439.1
137.5°	461.9	462.5	462.6	462.9	463.1	463.4	463.6	463.5	463.4	463.3	463.2
140°	484.3	484.9	485.2	485.8	486.5	487.1	487.7	487.7	487.7	487.7	487.7
142.5°	507.2	507.8	508.0	508.4	508.7	509.1	509.5	509.6	509.8	509.9	510.0
145°	528.1	528.5	528.9	529.6	530.4	531.1	531.9	532.0	532.2	532.3	532.4
147.5°	548.5	549.1	549.4	549.9	550.4	550.9	551.4	551.7	551.9	552.2	552.5
150°	567.1	567.5	567.8	568.3	568.8	569.3	569.8	570.2	570.6	570.9	571.3
152.5°	584.9	585.3	585.6	586.3	586.9	587.6	588.2	588.7	589.2	589.7	590.2
155°	601.2	601.4	601.6	602.0	602.3	602.7	603.1	603.7	604.3	605.0	605.6
157.5°	616.2	616.3	616.4	616.7	616.9	617.2	617.4	618.3	619.2	620.1	621.0
160°	629.9	630.0	630.1	630.2	630.3	630.5	630.6	631.4	632.2	632.9	633.7
162.5°	641.5	641.5	641.6	641.7	641.8	642.0	642.1	643.0	643.9	644.8	645.7
165°	652.0	651.9	651.9	651.9	651.9	651.9	651.9	652.8	653.7	654.6	655.5
167.5°	660.7	660.5	660.5	660.5	660.5	660.5	660.5	661.4	662.3	663.2	664.1
170°	668.1	667.9	667.8	667.7	667.6	667.4	667.3	668.2	669.1	670.0	670.9
172.5°	673.3	673.1	673.0	672.9	672.8	672.6	672.5	673.4	674.3	675.2	676.1
175°	677.3	677.1	677.0	676.7	676.5	676.2	676.0	676.9	677.8	678.7	679.6
177.5°	679.6	679.4	679.3	679.0	678.7	678.5	678.2	679.0	679.8	680.5	681.3
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	926.2	928.4	923.2	921.7	923.2	918.0	919.5	921.0	921.0	923.2	924.7
5°	872.4	869.4	864.2	862.7	861.2	863.5	862.0	864.2	864.9	870.2	870.9
7.5°	819.4	814.9	810.4	805.9	804.4	800.7	804.4	804.4	809.7	808.2	811.9
10°	756.6	755.9	749.9	747.7	744.7	738.7	746.9	744.7	748.4	755.1	756.6
12.5°	710.3	702.1	705.9	695.4	699.1	693.2	693.9	693.9	699.9	700.6	699.1
15°	666.3	659.5	649.8	645.4	643.1	640.1	649.8	650.6	646.1	656.6	652.8
17.5°	621.4	621.4	612.5	610.2	604.3	607.3	605.8	606.5	605.0	612.5	616.2
20°	582.6	578.9	575.9	576.6	569.2	567.7	566.2	567.7	572.9	578.1	579.6
22.5°	551.2	549.0	541.5	543.0	537.0	539.3	537.8	541.5	542.3	542.3	547.5
25°	521.4	518.4	519.1	516.1	513.9	513.9	511.6	513.9	516.9	518.4	519.1
27.5°	499.0	496.7	493.0	490.7	492.2	488.5	491.5	493.7	493.7	492.2	493.7
30°	472.1	473.6	473.6	466.1	469.1	467.6	469.8	471.3	471.3	472.1	470.6
32.5°	454.1	449.7	448.9	448.2	448.2	445.2	445.2	447.4	448.2	448.9	451.1
35°	430.2	430.2	426.5	428.7	425.8	426.5	425.8	426.5	428.0	425.8	428.0
37.5°	408.6	409.3	407.8	409.3	410.1	408.6	407.1	410.1	408.6	408.6	407.1
40°	389.9	389.2	389.9	389.9	389.9	390.6	389.2	389.2	389.2	387.7	386.2
42.5°	374.2	369.7	371.2	372.0	369.7	369.7	370.5	369.7	372.0	367.5	367.5
45°	351.8	350.3	351.1	351.1	352.6	350.3	351.8	352.6	350.3	349.6	348.1
47.5°	331.6	333.1	331.6	333.1	333.1	334.6	331.6	332.4	333.1	330.1	327.9
50°	311.5	311.5	313.7	313.0	313.7	312.2	312.2	311.5	312.2	310.7	308.5
52.5°	292.8	290.6	294.3	293.5	292.8	292.1	291.3	292.1	290.6	289.1	289.1
55°	269.6	269.6	271.9	272.6	272.6	271.1	269.6	270.4	269.6	268.9	268.1
57.5°	251.0	248.0	249.5	250.2	250.2	248.0	249.5	248.0	248.0	248.7	246.5
60°	227.1	227.1	225.6	227.8	227.8	226.3	226.3	227.1	225.6	224.8	224.1
62.5°	201.7	202.4	204.7	205.4	206.2	204.7	203.2	203.9	203.9	201.7	202.4
65°	180.0	181.5	184.5	183.7	182.3	183.0	181.5	182.3	180.0	180.8	178.5
67.5°	159.1	158.3	159.1	159.1	160.6	159.8	158.3	158.3	157.6	159.8	157.6
70°	136.7	136.7	136.7	136.7	137.4	138.2	136.7	135.2	135.9	134.4	133.7
72.5°	113.5	114.3	113.5	115.0	112.8	114.3	114.3	113.5	112.8	112.8	112.8
75°	91.9	93.4	91.1	91.9	91.1	92.6	91.9	91.9	90.4	89.6	90.4
77.5°	70.2	71.0	69.5	70.2	69.5	70.2	70.2	69.5	69.5	69.5	69.5
80°	50.0	50.8	50.0	49.3	48.6	50.0	48.6	49.3	50.0	49.3	50.8
82.5°	32.1	32.1	31.4	32.1	30.6	30.6	31.4	31.4	30.6	32.1	30.6
85°	15.7	15.7	17.2	15.7	14.9	14.9	14.9	15.7	14.9	16.4	15.7
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	18.9	19.0	19.1	19.2	19.4	19.5	19.4	19.2	19.1	19.0	18.9
92.5°	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4
95°	36.7	36.6	36.3	36.1	35.8	35.6	35.8	36.1	36.3	36.6	36.7
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
100°	79.2	79.1	79.0	78.9	78.7	78.6	78.7	78.9	79.0	79.1	79.2
102.5°	103.3	103.2	103.1	103.0	102.8	102.7	102.8	103.0	103.1	103.2	103.3
105°	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4
107.5°	152.6	152.3	151.7	151.0	150.4	149.8	150.4	151.0	151.7	152.3	152.6
110°	178.5	178.3	177.9	177.5	177.1	176.7	177.1	177.5	177.9	178.3	178.5

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	203.7	203.6	203.3	203.1	202.8	202.6	202.8	203.1	203.3	203.6	203.7
115°	231.2	231.0	230.6	230.3	229.9	229.5	229.9	230.3	230.6	231.0	231.2
117.5°	256.5	256.3	255.9	255.6	255.2	254.8	255.2	255.6	255.9	256.3	256.5
120°	283.5	283.3	282.9	282.5	282.1	281.7	282.1	282.5	282.9	283.3	283.5
122.5°	309.3	309.2	308.9	308.6	308.4	308.1	308.4	308.6	308.9	309.2	309.3
125°	335.7	335.6	335.5	335.4	335.2	335.1	335.2	335.4	335.5	335.6	335.7
127.5°	360.9	360.7	360.3	360.0	359.6	359.2	359.6	360.0	360.3	360.7	360.9
130°	387.9	387.6	387.1	386.6	386.1	385.6	386.1	386.6	387.1	387.6	387.9
132.5°	412.6	412.4	412.0	411.7	411.3	410.9	411.3	411.7	412.0	412.4	412.6
135°	439.0	438.8	438.4	438.0	437.6	437.2	437.6	438.0	438.4	438.8	439.0
137.5°	463.1	462.8	462.3	461.8	461.3	460.8	461.3	461.8	462.3	462.8	463.1
140°	487.7	487.4	486.9	486.4	485.9	485.4	485.9	486.4	486.9	487.4	487.7
142.5°	510.1	509.8	509.3	508.8	508.3	507.8	508.3	508.8	509.3	509.8	510.1
145°	532.5	532.2	531.7	531.2	530.7	530.2	530.7	531.2	531.7	532.2	532.5
147.5°	552.6	552.3	551.8	551.3	550.8	550.3	550.8	551.3	551.8	552.3	552.6
150°	571.5	571.3	570.9	570.6	570.2	569.8	570.2	570.6	570.9	571.3	571.5
152.5°	590.5	590.2	589.7	589.2	588.7	588.2	588.7	589.2	589.7	590.2	590.5
155°	605.9	605.7	605.3	605.0	604.6	604.2	604.6	605.0	605.3	605.7	605.9
157.5°	621.4	621.1	620.5	619.8	619.2	618.6	619.2	619.8	620.5	621.1	621.4
160°	634.1	633.8	633.3	632.8	632.3	631.8	632.3	632.8	633.3	633.8	634.1
162.5°	646.1	645.8	645.1	644.5	643.8	643.2	643.8	644.5	645.1	645.8	646.1
165°	655.9	655.6	654.9	654.3	653.6	653.0	653.6	654.3	654.9	655.6	655.9
167.5°	664.5	664.2	663.5	662.9	662.2	661.6	662.2	662.9	663.5	664.2	664.5
170°	671.4	671.0	670.2	669.5	668.7	667.9	668.7	669.5	670.2	671.0	671.4
172.5°	676.5	676.1	675.4	674.6	673.9	673.1	673.9	674.6	675.4	676.1	676.5
175°	680.0	679.6	678.8	678.1	677.3	676.5	677.3	678.1	678.8	679.6	680.0
177.5°	681.7	681.3	680.5	679.8	679.0	678.2	679.0	679.8	680.5	681.3	681.7
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	922.5	928.4	926.2	918.0	927.7	927.7	934.4	934.4	942.6	945.6	950.1
5°	870.2	874.7	878.4	874.7	881.4	891.8	897.8	903.0	914.2	918.7	925.5
7.5°	814.2	822.4	826.1	826.1	837.3	849.3	861.2	868.7	884.4	890.3	897.1
10°	759.6	769.3	776.8	776.1	794.7	802.2	817.1	834.3	850.0	859.0	868.7
12.5°	702.1	707.3	717.8	732.7	737.2	750.7	767.8	789.5	817.9	826.1	840.3
15°	654.3	668.5	676.7	683.4	693.9	706.6	725.3	746.2	774.6	792.5	807.4
17.5°	614.0	632.7	637.9	636.4	649.8	669.3	690.9	706.6	732.0	753.7	767.8
20°	581.1	588.6	597.5	601.3	611.7	632.7	653.6	671.5	692.4	709.6	726.0
22.5°	548.2	554.2	561.7	568.4	576.6	588.6	608.8	631.2	651.3	667.8	686.4
25°	521.4	525.1	531.8	537.0	546.0	554.2	568.4	593.1	617.0	626.7	643.1
27.5°	495.2	498.2	502.7	508.7	513.1	521.4	534.1	554.2	578.9	588.6	611.0
30°	472.1	474.3	478.8	481.8	484.0	493.7	503.4	519.1	537.8	551.2	567.7
32.5°	450.4	452.6	457.1	457.9	460.9	466.1	475.0	489.2	505.7	516.9	531.1
35°	426.5	428.0	432.5	434.0	436.2	440.7	447.4	457.9	472.8	481.0	493.7
37.5°	407.8	407.1	410.1	412.3	415.3	417.5	419.8	430.2	441.4	448.9	458.6
40°	387.7	386.2	386.9	389.9	391.4	394.4	394.4	404.8	412.3	418.3	425.8
42.5°	367.5	366.7	365.3	366.7	368.2	369.0	369.7	377.2	384.7	389.9	398.1
45°	347.3	346.6	345.1	345.8	345.8	347.3	349.6	352.6	357.8	362.3	366.7
47.5°	328.7	327.2	324.9	324.2	325.7	325.7	325.7	328.7	333.9	335.4	339.9
50°	309.2	307.0	304.0	302.5	302.5	301.8	303.3	304.0	308.5	310.0	313.7
52.5°	288.3	286.8	283.8	280.8	281.6	280.1	280.8	281.6	283.1	285.3	287.6
55°	267.4	264.4	262.2	261.4	259.2	259.2	256.9	259.9	259.2	259.9	262.9
57.5°	247.2	244.2	240.5	239.0	236.8	236.0	234.5	233.8	234.5	236.8	239.0
60°	223.3	221.8	219.6	217.4	215.9	213.6	212.1	212.1	211.4	211.4	212.1
62.5°	200.2	199.4	196.4	195.7	194.2	192.7	190.5	189.0	189.0	190.5	191.2
65°	177.8	177.0	174.8	174.0	170.3	168.8	168.1	167.3	165.8	165.8	165.8
67.5°	156.9	154.6	154.6	150.9	147.9	146.4	144.9	144.2	144.2	144.2	144.9
70°	133.7	133.7	131.5	129.2	126.2	127.0	124.7	122.5	122.5	121.0	121.8
72.5°	111.3	110.5	108.3	107.6	105.3	103.1	101.6	103.1	100.8	100.1	100.8
75°	89.6	88.9	87.4	85.9	86.6	84.4	82.2	81.4	81.4	79.9	79.9
77.5°	68.7	70.2	67.2	66.5	65.0	63.5	62.7	62.0	62.0	62.0	63.5
80°	47.8	48.6	48.6	47.1	47.8	45.6	45.6	45.6	43.3	44.1	44.8
82.5°	30.6	30.6	29.9	30.6	29.9	29.9	29.1	29.1	28.4	28.4	29.1
85°	17.2	16.4	15.7	17.2	16.4	16.4	15.7	15.7	15.7	15.7	15.7
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	19.0	19.3	19.6	19.8	20.1	17.3	14.5	11.7	8.9	7.5	6.7
92.5°	18.3	18.2	18.1	17.9	17.8	17.7	17.5	17.4	17.3	17.2	16.7
95°	36.7	36.7	36.7	36.7	36.7	36.5	36.2	36.0	35.7	35.6	35.0
97.5°	57.4	57.4	57.4	57.4	57.4	56.9	56.4	55.9	55.4	55.1	54.5
100°	79.2	79.2	79.2	79.2	79.2	78.8	78.4	78.1	77.7	77.5	77.0
102.5°	103.2	103.1	103.0	102.8	102.7	102.2	101.7	101.2	100.7	100.4	100.0
105°	127.3	127.0	126.7	126.5	126.2	126.0	125.7	125.5	125.2	125.1	124.9
107.5°	152.5	152.4	152.3	152.2	152.1	152.1	152.1	152.1	152.1	152.1	151.8
110°	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.1

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	203.9	204.3	204.6	205.0	205.4	205.5	205.7	205.8	205.9	206.0	205.6
115°	231.3	231.4	231.5	231.7	231.8	232.1	232.3	232.6	232.9	233.0	232.6
117.5°	256.7	257.1	257.4	257.8	258.2	258.8	259.5	260.1	260.8	261.1	260.6
120°	283.5	283.5	283.5	283.5	283.5	284.5	285.5	286.6	287.6	288.1	287.6
122.5°	309.5	309.9	310.2	310.6	311.0	311.6	312.3	312.9	313.6	313.9	313.3
125°	335.9	336.3	336.6	337.0	337.4	337.8	338.2	338.5	338.9	339.1	338.5
127.5°	361.2	361.7	362.2	362.7	363.2	363.7	364.2	364.7	365.2	365.5	364.8
130°	388.0	388.3	388.5	388.8	389.0	389.3	389.5	389.8	390.1	390.2	389.4
132.5°	412.9	413.5	414.2	414.8	415.4	415.3	415.2	415.1	415.0	414.9	414.3
135°	439.1	439.2	439.3	439.4	439.5	439.3	439.0	438.8	438.5	438.4	437.7
137.5°	463.2	463.3	463.4	463.5	463.6	463.4	463.1	462.9	462.6	462.5	461.9
140°	487.7	487.7	487.7	487.7	487.7	487.1	486.5	485.8	485.2	484.9	484.3
142.5°	510.0	509.9	509.8	509.6	509.5	509.1	508.7	508.4	508.0	507.8	507.2
145°	532.4	532.3	532.2	532.0	531.9	531.1	530.4	529.6	528.9	528.5	528.1
147.5°	552.5	552.2	551.9	551.7	551.4	550.9	550.4	549.9	549.4	549.1	548.5
150°	571.3	570.9	570.6	570.2	569.8	569.3	568.8	568.3	567.8	567.5	567.1
152.5°	590.2	589.7	589.2	588.7	588.2	587.6	586.9	586.3	585.6	585.3	584.9
155°	605.6	605.0	604.3	603.7	603.1	602.7	602.3	602.0	601.6	601.4	601.2
157.5°	621.0	620.1	619.2	618.3	617.4	617.2	616.9	616.7	616.4	616.3	616.2
160°	633.7	632.9	632.2	631.4	630.6	630.5	630.3	630.2	630.1	630.0	629.9
162.5°	645.7	644.8	643.9	643.0	642.1	642.0	641.8	641.7	641.6	641.5	641.5
165°	655.5	654.6	653.7	652.8	651.9	651.9	651.9	651.9	651.9	651.9	652.0
167.5°	664.1	663.2	662.3	661.4	660.5	660.5	660.5	660.5	660.5	660.5	660.7
170°	670.9	670.0	669.1	668.2	667.3	667.4	667.6	667.7	667.8	667.9	668.1
172.5°	676.1	675.2	674.3	673.4	672.5	672.6	672.8	672.9	673.0	673.1	673.3
175°	679.6	678.7	677.8	676.9	676.0	676.2	676.5	676.7	677.0	677.1	677.3
177.5°	681.3	680.5	679.8	679.0	678.2	678.5	678.7	679.0	679.3	679.4	679.6
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	971.8	971.8	971.8	971.8
2.5°	953.8	953.8	965.0	977.0
5°	932.9	938.1	956.1	972.5
7.5°	912.8	921.7	944.1	965.0
10°	888.1	900.1	927.7	952.3
12.5°	864.2	875.4	907.5	935.2
15°	830.6	844.8	879.1	913.5
17.5°	797.0	811.2	853.0	893.3
20°	757.4	776.1	823.1	876.9
22.5°	720.8	743.9	796.2	839.6
25°	680.5	716.3	764.9	820.9
27.5°	644.6	680.5	729.8	786.5
30°	604.3	640.9	691.7	743.9
32.5°	565.4	599.0	648.3	712.6
35°	525.1	557.2	605.0	670.0
37.5°	488.5	519.9	572.2	631.9
40°	452.6	485.5	530.3	590.1
42.5°	419.0	448.2	488.5	548.2
45°	388.4	409.3	446.7	502.7
47.5°	356.3	375.0	409.3	465.3
50°	326.4	342.1	372.0	424.3
52.5°	297.3	310.7	338.4	380.2
55°	271.1	283.8	304.0	345.1
57.5°	244.2	254.0	273.4	306.2
60°	218.1	227.1	242.8	269.6
62.5°	192.0	199.4	214.4	236.0
65°	168.8	174.8	186.0	204.7
67.5°	146.4	150.1	159.1	174.0
70°	124.7	127.7	135.2	147.1
72.5°	101.6	104.6	112.8	121.0
75°	82.2	82.9	88.9	95.6
77.5°	64.2	63.5	68.0	73.2
80°	44.1	46.3	50.0	52.3
82.5°	29.9	30.6	32.1	33.6
85°	16.4	17.2	17.2	19.4
87.5°	6.7	7.5	7.5	8.2
90°	5.2	3.7	2.1	0.6
92.5°	15.7	14.6	13.6	12.6
95°	33.7	32.4	31.1	29.8
97.5°	53.4	52.2	51.1	49.9
100°	76.0	74.9	73.9	72.9
102.5°	99.3	98.5	97.8	97.0
105°	124.5	124.2	123.8	123.4
107.5°	151.3	150.8	150.3	149.8
110°	177.3	176.6	175.8	175.0

TEST NUMBER: P1009094

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	204.9	204.1	203.4	202.6
115°	231.8	231.1	230.3	229.5
117.5°	259.6	258.5	257.5	256.5
120°	286.6	285.5	284.5	283.5
122.5°	312.0	310.7	309.4	308.1
125°	337.4	336.3	335.1	334.0
127.5°	363.4	362.0	360.6	359.2
130°	387.7	386.0	384.4	382.7
132.5°	413.0	411.7	410.4	409.1
135°	436.3	434.9	433.5	432.1
137.5°	460.8	459.6	458.5	457.3
140°	483.2	482.0	480.9	479.7
142.5°	506.1	505.0	503.8	502.7
145°	527.2	526.3	525.4	524.5
147.5°	547.4	546.3	545.1	544.0
150°	566.4	565.6	564.9	564.1
152.5°	584.1	583.4	582.6	581.8
155°	600.8	600.4	600.0	599.6
157.5°	615.9	615.6	615.4	615.1
160°	629.6	629.4	629.1	628.9
162.5°	641.5	641.5	641.5	641.5
165°	652.1	652.2	652.3	652.4
167.5°	661.1	661.4	661.8	662.2
170°	668.5	668.8	669.2	669.6
172.5°	673.7	674.0	674.4	674.8
175°	677.7	678.0	678.4	678.8
177.5°	680.0	680.3	680.7	681.1
180°	680.0	680.0	680.0	680.0

(END OF REPORT)